

# TXB0108 8-Bit Bidirectional Voltage-Level Translator with Auto-Direction Sensing and $\pm 15\text{-kV}$ ESD Protection

## 1 Features

- 1.2 V to 3.6 V on A Port and 1.65 V to 5.5 V on B Port ( $V_{CCA} \leq V_{CCB}$ )
- $V_{CC}$  Isolation Feature – If Either  $V_{CC}$  Input Is at GND, All Outputs Are in the High-Impedance State
- OE Input Circuit Referenced to  $V_{CCA}$
- Low Power Consumption, 4- $\mu\text{A}$  Max  $I_{CC}$
- $I_{off}$  Supports Partial-Power-Down Mode Operation
- Latch-Up Performance Exceeds 100 mA Per JESD 78, Class II
- ESD Protection Exceeds JESD 22
  - A Port
    - 2000-V Human-Body Model (A114-B)
    - 1000-V Charged-Device Model (C101)
  - B Port
    - $\pm 15\text{-kV}$  Human-Body Model (A114-B)
    - $\pm 8\text{-kV}$  Human-Body Model (A114-B) (YZP Package Only)
    - 1000-V Charged-Device Model (C101)

## 2 Applications

- Handset
- Smartphone
- Tablet
- Desktop PC

## 3 Description

This 8-bit noninverting translator uses two separate configurable power-supply rails. The A port is designed to track  $V_{CCA}$ .  $V_{CCA}$  accepts any supply voltage from 1.2 V to 3.6 V. The B port is designed to track  $V_{CCB}$ .  $V_{CCB}$  accepts any supply voltage from 1.65 V to 5.5 V. This allows for universal low-voltage bidirectional translation between any of the 1.2-V, 1.5-V, 1.8-V, 2.5-V, 3.3-V, and 5-V voltage nodes.  $V_{CCA}$  should not exceed  $V_{CCB}$ .

When the output-enable (OE) input is low, all outputs are placed in the high-impedance state.

The TXB0108 is designed so that the OE input circuit is supplied by  $V_{CCA}$ .


This device is fully specified for partial-power-down applications using  $I_{off}$ . The  $I_{off}$  circuitry disables the outputs, preventing damaging current backflow through the device when it is powered down.

To ensure the high-impedance state during power-up or power-down, OE should be tied to GND through a pulldown resistor; the minimum value of the resistor is determined by the current-sourcing capability of the driver.

### Device Information

| PART NUMBER | PACKAGE <sup>(1)</sup>    | BODY SIZE (NOM)   |
|-------------|---------------------------|-------------------|
| TXB0108DQS  | SON (20)                  | 2.00 mm x 4.00 mm |
| TXB0108ZXY  | BGA MICROSTAR JUNIOR (20) | 2.50 mm x 3.00 mm |
| TXB0108PW   | TSSOP (20)                | 6.50 mm x 4.40 mm |
| TXB0108RGY  | VQFN (20)                 | 4.50 mm x 3.50 mm |
| TXB0108YZP  | DSGBA (20)                | 1.90 mm x 2.40 mm |
| TXB0108NME  | nFBGA (20)                | 2.50 mm x 3.00 mm |

(1) For all available packages, see the orderable addendum at the end of the datasheet.



Typical Application Block Diagram for TXB0108



An IMPORTANT NOTICE at the end of this data sheet addresses availability, warranty, changes, use in safety-critical applications, intellectual property matters and other important disclaimers. PRODUCTION DATA.

## Table of Contents

|  |           |  |           |
|--|-----------|--|-----------|
| <b>1 Features</b> .....  | <b>1</b>  | <b>7 Parameter Measurement Information</b> .....                           | <b>12</b> |
| <b>2 Applications</b> .....  | <b>1</b>  | <b>8 Detailed Description</b> .....  | <b>13</b> |
| <b>3 Description</b> .....   | <b>1</b>  | 8.1 Overview.....  | <b>13</b> |
| <b>4 Revision History</b> .....  | <b>2</b>  | 8.2 Functional Block Diagram.....  | <b>13</b> |
| <b>5 Pin Configuration and Functions</b> .....                                   | <b>3</b>  | 8.3 Feature Description.....   | <b>14</b> |
| <b>6 Specifications</b> .....  | <b>5</b>  | 8.4 Device Functional Modes.....   | <b>15</b> |
| 6.1 Absolute Maximum Ratings.....  | <b>5</b>  | <b>9 Application and Implementation</b> .....                              | <b>16</b> |
| 6.2 Handling Ratings.....  | <b>5</b>  | 9.1 Application Information.....   | <b>16</b> |
| 6.3 Recommended Operating Conditions.....  | <b>5</b>  | 9.2 Typical Application.....   | <b>16</b> |
| 6.4 Thermal Information.....   | <b>6</b>  | <b>10 Power Supply Recommendations</b> .....                               | <b>18</b> |
| 6.5 Electrical Characteristics.....  | <b>6</b>  | <b>11 Layout</b> .....   | <b>18</b> |
| 6.6 Timing Requirements: $V_{CCA} = 1.2\text{ V}$ .....                          | <b>7</b>  | 11.1 Layout Guidelines.....  | <b>18</b> |
| 6.7 Timing Requirements: $V_{CCA} = 1.5\text{ V} \pm 0.1\text{ V}$ .....         | <b>7</b>  | 11.2 Layout Example.....   | <b>18</b> |
| 6.8 Timing Requirements: $V_{CCA} = 1.8\text{ V} \pm 0.15\text{ V}$ .....        | <b>7</b>  | <b>12 Device and Documentation Support</b> .....                           | <b>19</b> |
| 6.9 Timing Requirements: $V_{CCA} = 2.5\text{ V} \pm 0.2\text{ V}$ .....         | <b>7</b>  | 12.1 Receiving Notification of Documentation Updates.....                  | <b>19</b> |
| 6.10 Timing Requirements: $V_{CCA} = 3.3\text{ V} \pm 0.3\text{ V}$ .....        | <b>8</b>  | 12.2 Support Resources.....  | <b>19</b> |
| 6.11 Switching Characteristics: $V_{CCA} = 1.2\text{ V}$ .....                   | <b>8</b>  | 12.3 Trademarks.....   | <b>19</b> |
| 6.12 Switching Characteristics: $V_{CCA} = 1.5\text{ V} \pm 0.1\text{ V}$ .....  | <b>8</b>  | 12.4 Electrostatic Discharge Caution.....                                  | <b>19</b> |
| 6.13 Switching Characteristics: $V_{CCA} = 1.8\text{ V} \pm 0.15\text{ V}$ ..... | <b>9</b>  | 12.5 Glossary.....   | <b>19</b> |
| 6.14 Switching Characteristics: $V_{CCA} = 2.5\text{ V} \pm 0.2\text{ V}$ .....  | <b>9</b>  | <b>13 Mechanical, Packaging, and Orderable</b><br><b>Information</b> ..... | <b>19</b> |
| 6.15 Switching Characteristics: $V_{CCA} = 3.3\text{ V} \pm 0.3\text{ V}$ .....  | <b>9</b>  | 13.1 Package Addendum.....   | <b>20</b> |
| 6.16 Operating Characteristics.....  | <b>10</b> |  |           |
| 6.17 Typical Characteristics.....  | <b>11</b> |  |           |

## 4 Revision History

NOTE: Page numbers for previous revisions may differ from page numbers in the current version.

| <b>Changes from Revision G (December 2018) to Revision H (August 2020)</b>                           | <b>Page</b> |
|--|-------------|
| • Updated the numbering format for tables, figures and cross-references throughout the document..... | <b>1</b>    |
| • Added NME package option to <i>Device Information</i> table.....                                   | <b>1</b>    |
| • Added NME package to <a href="#">Figure 5-1</a> .....  | <b>3</b>    |
| • Added NME package to <i>Pin Assignments</i> table.....   | <b>3</b>    |
| • Added NME package to <i>Thermal Information</i> table.....   | <b>6</b>    |


| <b>Changes from Revision F (November 2014) to Revision G (December 2018)</b>  | <b>Page</b> |
|---|-------------|
| • Added pinout image for the ZYPR2 package option .....   | <b>3</b>    |
| • Added text string 'GRID LOCATOR' to Pin Functions table YZP column to clarify pin location from 'Signal Name' ..... | <b>3</b>    |

| <b>Changes from Revision E (April 2012) to Revision F (October 2014)</b>   | <b>Page</b> |
|--|-------------|
| • Added <i>Pin Configuration and Functions</i> section, <i>Handling Rating</i> table, <i>Feature Description</i> section, <i>Device Functional Modes</i> , <i>Application and Implementation</i> section, <i>Power Supply Recommendations</i> section, <i>Layout</i> section, <i>Device and Documentation Support</i> section, and <i>Mechanical, Packaging, and Orderable Information</i> section ..... | <b>1</b>    |
| • Changed $V_{OLA}$ value 0.9 to 0.3 .....   | <b>6</b>    |


| <b>Changes from Revision D (September 2011) to Revision E (April 2012)</b> | <b>Page</b> |
|--|-------------|
| • Added notes to pin out graphics.....                                     | <b>3</b>    |

| <b>Changes from Revision C (August 2011) to Revision D (September 2011)</b>             | <b>Page</b> |
|---|-------------|
| • Added $\pm 8\text{-kV}$ Human-Body Model (A114-B) (YZP Package Only) to Features..... | <b>1</b>    |


## 5 Pin Configuration and Functions



- For the RGY package, the exposed center thermal pad must be connected to ground.
- Pullup resistors are not required on both sides for Logic I/O.
- If pullup or pulldown resistors are needed, the resistor value must be over 50 k $\Omega$ .
- 50 k $\Omega$  is a safe recommended value, if the customer can accept higher  $V_{OL}$  or lower  $V_{OH}$ , smaller pullup or pulldown resistor is allowed, the draft estimation is  $V_{OL} = V_{CCOUT} \times 4.5 \text{ k} / (4.5 \text{ k} + R_{PU})$  and  $V_{OH} = V_{CCOUT} \times R_{DW} / (4.5 \text{ k} + R_{DW})$ .
- If pullup resistors are needed, please refer to the TXS0108 or contact TI.
- For detailed information, please refer to application note [SCEA043](#).



<sup>(1)</sup> See orderable addendum at the end of the data sheet



**Figure 5-1. NME/GXY/ZXY PACKAGE (BOTTOM VIEW)**

**Table 5-1. Pin Functions**

| PIN              |             |         |                  | I/O <sup>(1)</sup>   | FUNCTION  |
|------------------|-------------|---------|------------------|--|---|
| SIGNAL NAME      | PW, RGY NO. | DQS NO. | YZP GRID LOCATOR |  |   |
| A1               | 1           | 1       | A3               | I/O  | Input/output 1. Referenced to V <sub>CCA</sub> .  |
| V <sub>CCA</sub> | 2           | 5       | C4               | S  | A-port supply voltage. 1.1 V ≤ V <sub>CCA</sub> ≤ 3.6 V, V <sub>CCA</sub> ≤ V <sub>CCB</sub> .    |
| A2               | 3           | 2       | A4               | I/O  | Input/output 2. Referenced to V <sub>CCA</sub> .  |
| A3               | 4           | 3       | B3               | I/O  | Input/output 3. Referenced to V <sub>CCA</sub> .  |
| A4               | 5           | 4       | B4               | I/O  | Input/output 4. Referenced to V <sub>CCA</sub> .  |
| A5               | 6           | 7       | C3               | I/O  | Input/output 5. Referenced to V <sub>CCA</sub> .  |
| A6               | 7           | 8       | E4               | I/O  | Input/output 6. Referenced to V <sub>CCA</sub> .  |
| A7               | 8           | 9       | D3               | I/O  | Input/output 7. Referenced to V <sub>CCA</sub> .  |
| A8               | 9           | 10      | E3               | I/O  | Input/output 8. Referenced to V <sub>CCA</sub> .  |
| OE               | 10          | 6       | D4               | I  | Output enable. Pull OE low to place all outputs in 3-state mode. Referenced to V <sub>CCA</sub> . |
| GND              | 11          | 15      | D1               | S  | Ground  |
| B8               | 12          | 11      | E2               | I/O  | Input/output 8. Referenced to V <sub>CCB</sub> .  |
| B7               | 13          | 12      | D2               | I/O  | Input/output 7. Referenced to V <sub>CCB</sub> .  |
| B6               | 14          | 13      | E1               | I/O  | Input/output 6. Referenced to V <sub>CCB</sub> .  |
| B5               | 15          | 14      | C2               | I/O  | Input/output 5. Referenced to V <sub>CCB</sub> .  |
| B4               | 16          | 17      | B1               | I/O  | Input/output 4. Referenced to V <sub>CCB</sub> .  |
| B3               | 17          | 18      | B2               | I/O  | Input/output 3. Referenced to V <sub>CCB</sub> .  |
| B2               | 18          | 19      | A1               | I/O  | Input/output 2. Referenced to V <sub>CCB</sub> .  |
| V <sub>CCB</sub> | 19          | 16      | C1               | S  | B-port supply voltage. 1.65 V ≤ V <sub>CCB</sub> ≤ 5.5 V.   |
| B1               | 20          | 20      | A2               | I/O  | Input/output 1. Referenced to V <sub>CCB</sub> .  |
| Thermal Pad      | —           |         | —                | For the RGY package, the exposed center thermal pad must be connected to ground. |   |

(1) I = input, O = output, I/O = input and output, S = power supply

**Table 5-2. Pin Assignments (20-Ball NME/GXY/ZXY Package)**

|          | 1                | 2  | 3  | 4  | 5   |
|----------|------------------|----|----|----|-----|
| <b>D</b> | V <sub>CCB</sub> | B2 | B4 | B6 | B8  |
| <b>C</b> | B1               | B3 | B5 | B7 | GND |
| <b>B</b> | A1               | A3 | A5 | A7 | OE  |
| <b>A</b> | V <sub>CCA</sub> | A2 | A4 | A6 | A8  |

## 6 Specifications

### 6.1 Absolute Maximum Ratings

over operating free-air temperature range (unless otherwise noted)

| (1)       |   |           | MIN  | MAX             | UNIT |
|-----------|---|-----------|------|-----------------|------|
| $V_{CCA}$ | Supply voltage range  |           | -0.5 | 4.6             | V    |
| $V_{CCB}$ | Supply voltage range  |           | -0.5 | 6.5             | V    |
| $V_I$     | Input voltage range <sup>(2)</sup>  |           | -0.5 | 6.5             | V    |
| $V_O$     | Voltage range applied to any output in the high-impedance or power-off state <sup>(2)</sup> |           | -0.5 | 6.5             | V    |
| $V_O$     | Voltage range applied to any output in the high or low state <sup>(2) (3)</sup>             | A inputs  | -0.5 | $V_{CCA} + 0.5$ | V    |
|           |   | B inputs  | -0.5 | $V_{CCB} + 0.5$ |      |
| $I_{IK}$  | Input clamp current   | $V_I < 0$ |      | -50             | mA   |
| $I_{OK}$  | Output clamp current  | $V_O < 0$ |      | -50             | mA   |
| $I_O$     | Continuous output current   |           |      | $\pm 50$        | mA   |
|           | Continuous current through $V_{CCA}$ , $V_{CCB}$ , or GND                                   |           |      | $\pm 100$       | mA   |
| $T_{stg}$ | Storage temperature range   |           | -65  | 150             | °C   |
| $T_J$     | Junction temperature  |           |      | 150             | °C   |

(1) Stresses beyond those listed under *Absolute Maximum Ratings* may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated under *Recommended Operating Conditions* is not implied. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability.

(2) The input and output negative-voltage ratings may be exceeded if the input and output current ratings are observed.

(3) The value of  $V_{CCA}$  and  $V_{CCB}$  are provided in the recommended operating conditions table.

### 6.2 Handling Ratings

|             |                         |  | MIN | MAX | UNIT |
|-------------|-------------------------|--|-----|-----|------|
| $V_{(ESD)}$ | Electrostatic discharge | Human body model (HBM), per ANSI/ESDA/JEDEC JS-001, all pins <sup>(1)</sup> , A Port                                 |     | 2   | kV   |
|             |                         | Human body model (HBM), per ANSI/ESDA/JEDEC JS-001, all pins <sup>(1)</sup> , B Port                                 | -15 | 15  |      |
|             |                         | Charged device model (CDM), per JEDEC specification JESD22-C101, all pins <sup>(2)</sup> , A Port                    |     | 1   |      |
|             |                         | Charged device model (CDM), per JEDEC specification JESD22-C101, all pins <sup>(2)</sup> , A Port (YZP Package only) | -8  | 8   |      |
|             |                         | Charged device model (CDM), per JEDEC specification JESD22-C101, all pins <sup>(2)</sup> , B Port                    |     | 1   |      |

(1) JEDEC document JEP155 states that 500-V HBM allows safe manufacturing with a standard ESD control process.

(2) JEDEC document JEP157 states that 250-V CDM allows safe manufacturing with a standard ESD control process.

### 6.3 Recommended Operating Conditions

over operating free-air temperature range (unless otherwise noted)<sup>(1) (2)</sup>

|                     |                                    | $V_{CCA}$     | $V_{CCB}$      | MIN             | MAX                         | UNIT |
|---------------------|------------------------------------|---------------|----------------|-----------------|-----------------------------|------|
| $V_{CCA}$           | Supply voltage                     |               |                | 1.2             | 3.6                         | V    |
|                     |                                    |               |                | 1.65            | 5.5                         |      |
| $V_{IH}$            | High-level input voltage           | Data inputs   | 1.2 V to 3.6 V | 1.65 V to 5.5 V | $V_{CCI} \times 0.65^{(3)}$ | V    |
|                     |                                    | OE            |                |                 | $V_{CCA} \times 0.65$       |      |
| $V_{IL}$            | Low-level input voltage            | Data inputs   | 1.2 V to 5.5 V | 1.65 V to 5.5 V | 0                           | V    |
|                     |                                    | OE            | 1.2 V to 3.6 V |                 | 0                           |      |
| $\Delta t/\Delta v$ | Input transition rise or fall rate | A-port inputs | 1.2 V to 3.6 V | 1.65 V to 5.5 V |                             | 40   |
|                     |                                    | B-port inputs | 1.2 V to 3.6 V | 1.65 V to 3.6 V |                             | 40   |
|                     |                                    |               |                | 4.5 V to 5.5 V  |                             | 30   |

## 6.3 Recommended Operating Conditions (continued)

over operating free-air temperature range (unless otherwise noted)<sup>(1) (2)</sup>

|                                      | $V_{CCA}$ | $V_{CCB}$ | MIN | MAX | UNIT |
|--------------------------------------|-----------|-----------|-----|-----|------|
| $T_A$ Operating free-air temperature |           |           | -40 | 85  | °C   |

(1) The A and B sides of an unused data I/O pair must be held in the same state, i.e., both at  $V_{CCI}$  or both at GND.

(2)  $V_{CCA}$  must be less than or equal to  $V_{CCB}$  and must not exceed 3.6 V.

(3)  $V_{CCI}$  is the supply voltage associated with the input port.

## 6.4 Thermal Information

| THERMAL METRIC <sup>(1)</sup>  | TXB0108 |      |       |      |       |       |       | UNIT |
|--|---------|------|-------|------|-------|-------|-------|------|
|  | PW      | RGY  | DQS   | YZP  | GXY   | ZXY   | NME   |      |
|  | 20 PINS |      |       |      |       |       |       |      |
| $R_{\theta JA}$ Junction-to-ambient thermal resistance               | 101.8   | 35.3 | 108.5 | 66.2 | 156.7 | 156.7 | 131.4 | °C/W |
| $R_{\theta}$<br>JC(top) Junction-to-case (top) thermal resistance    | 35.5    | 42.1 | 32.3  | 0.4  | 39.9  | 39.9  | 56.5  | °C/W |
| $R_{\theta JB}$ Junction-to-board thermal resistance                 | 52.8    | 11.1 | 42.4  | 52.0 | 85.9  | 85.9  | 83.2  | °C/W |
| $\Psi_{JT}$ Junction-to-top characterization parameter               | 2.2     | 0.7  | 0.7   | 1.5  | 1.1   | 1.1   | 1.5   | °C/W |
| $\Psi_{JB}$ Junction-to-board characterization parameter             | 52.2    | 11.2 | 42    | 51.9 | 85.4  | 85.4  | 82.6  | °C/W |
| $R_{\theta}$<br>JC(bot) Junction-to-case (bottom) thermal resistance | –       | 3.8  | –     | –    | –     | –     | –     | °C/W |

(1) For more information about traditional and new thermal metrics, see the *IC Package Thermal Metrics* application report, [SPRA953](#).

## 6.5 Electrical Characteristics

over recommended operating free-air temperature range (unless otherwise noted)<sup>(1) (2)</sup>

| PARAMETER           | TEST CONDITIONS                                    | $V_{CCA}$      | $V_{CCB}$       | $T_A = 25^\circ C$ |         |         | $-40^\circ C$ to $85^\circ C$ |     | UNIT    |
|---------------------|--|----------------|-----------------|--------------------|---------|---------|-------------------------------|-----|---------|
|                     |  |                |                 | MIN                | TYP     | MAX     | MIN                           | MAX |         |
| $V_{OHA}$           | $I_{OH} = -20 \mu A$                               | 1.2 V          |                 | 1.1                |         |         | $V_{CCB} - 0.4$               |     | V       |
|                     |  | 1.4 V to 3.6 V |                 |                    |         |         |                               |     |         |
| $V_{OLA}$           | $I_{OL} = 20 \mu A$                                | 1.2 V          |                 | 0.3                |         |         | 0.4                           |     | V       |
|                     |  | 1.4 V to 3.6 V |                 |                    |         |         |                               |     |         |
| $V_{OHB}$           | $I_{OH} = -20 \mu A$                               |                | 1.65 V to 5.5 V |                    |         |         | $V_{CCB} - 0.4$               |     | V       |
| $V_{OLB}$           | $I_{OL} = 20 \mu A$                                |                | 1.65 V to 5.5 V |                    |         |         | 0.4                           |     | V       |
| $I_I$               | OE   | 1.2 V to 3.6 V | 1.65 V to 5.5 V |                    | $\pm 1$ |         | $\pm 2$                       |     | $\mu A$ |
| $I_{off}$           | A port   | 0 V            | 0 V to 5.5 V    |                    | $\pm 1$ |         | $\pm 2$                       |     | $\mu A$ |
|                     | B port   | 0 V to 3.6 V   | 0 V             |                    | $\pm 1$ |         | $\pm 2$                       |     |         |
| $I_{OZ}$            | A or B port  | OE = GND       | 1.2 V to 3.6 V  | 1.65 V to 5.5 V    |         | $\pm 1$ | $\pm 2$                       |     | $\mu A$ |
| $I_{CCA}$           | $V_I = V_{CCI}$ or GND,<br>$I_O = 0$               | 1.2 V          | 1.65 V to 5.5 V | 0.06               |         |         | 5                             |     | $\mu A$ |
|                     |  | 1.4 V to 3.6 V |                 |                    |         |         |                               |     |         |
|                     |  | 3.6 V          | 0 V             |                    |         |         | 2                             |     |         |
|                     |  | 0 V            | 5.5 V           |                    |         |         | -2                            |     |         |
| $I_{CCB}$           | $V_I = V_{CCI}$ or GND,<br>$I_O = 0$               | 1.2 V          | 1.65 V to 5.5 V | 3.4                |         |         | 10                            |     | $\mu A$ |
|                     |  | 1.4 V to 3.6 V |                 |                    |         |         |                               |     |         |
|                     |  | 3.6 V          | 0 V             |                    |         |         | -2                            |     |         |
|                     |  | 0 V            | 5.5 V           |                    |         |         | 2                             |     |         |
| $I_{CCA} + I_{CCB}$ | $V_I = V_{CCI}$ or GND,<br>$I_O = 0$               | 1.2 V          | 1.65 V to 5.5 V | 3.5                |         |         | 10                            |     | $\mu A$ |
|                     |  | 1.4 V to 3.6 V |                 |                    |         |         |                               |     |         |
| $I_{CCZA}$          | $V_I = V_{CCI}$ or GND,<br>$I_O = 0$ ,<br>OE = GND | 1.2 V          | 1.65 V to 5.5 V | 0.05               |         |         | 5                             |     | $\mu A$ |
|                     |  | 1.4 V to 3.6 V |                 |                    |         |         |                               |     |         |

## 6.5 Electrical Characteristics (continued)

over recommended operating free-air temperature range (unless otherwise noted)<sup>(1) (2)</sup>

| PARAMETER         | TEST CONDITIONS  | V <sub>CCA</sub> | V <sub>CCB</sub> | T <sub>A</sub> = 25°C |     |     | -40°C to 85°C |     | UNIT |
|-------------------|--|------------------|------------------|-----------------------|-----|-----|---------------|-----|------|
|                   |  |                  |                  | MIN                   | TYP | MAX | MIN           | MAX |      |
| I <sub>CCZB</sub> | V <sub>I</sub> = V <sub>CCI</sub> or GND,<br>I <sub>O</sub> = 0,<br>OE = GND | 1.2 V            | 1.65 V to 5.5 V  | 3.3                   |     |     | 5             |     | μA   |
|                   |  | 1.4 V to 3.6 V   |                  |                       |     |     |               |     |      |
| C <sub>I</sub>    | OE   | 1.2 V to 3.6 V   | 1.65 V to 5.5 V  | 5                     |     |     | 5.5           |     | pF   |
| C <sub>io</sub>   | A port   | 1.2 V to 3.6 V   | 1.65 V to 5.5 V  | 5                     |     |     | 6.5           |     | pF   |
|                   | B port   |                  |                  | 8                     |     |     | 10            |     |      |

(1) V<sub>CCI</sub> is the supply voltage associated with the input port.

(2) V<sub>CCO</sub> is the supply voltage associated with the output port.

## 6.6 Timing Requirements: V<sub>CCA</sub> = 1.2 V

T<sub>A</sub> = 25°C, V<sub>CCA</sub> = 1.2 V

|                |                | V <sub>CCB</sub> = 1.8 V | V <sub>CCB</sub> = 2.5 V | V <sub>CCB</sub> = 3.3 V | V <sub>CCB</sub> = 5 V | UNIT |
|----------------|----------------|--------------------------|--------------------------|--------------------------|------------------------|------|
|                |                | TYP                      | TYP                      | TYP                      | TYP                    |      |
| Data rate      |                | 20                       | 20                       | 20                       | 20                     | Mbps |
| t <sub>w</sub> | Pulse duration | Data inputs              | 50                       | 50                       | 50                     | ns   |

## 6.7 Timing Requirements: V<sub>CCA</sub> = 1.5 V ± 0.1 V

over recommended operating free-air temperature range, V<sub>CCA</sub> = 1.5 V ± 0.1 V (unless otherwise noted)

|                |                | V <sub>CCB</sub> = 1.8 V<br>± 0.15 V | V <sub>CCB</sub> = 2.5 V<br>± 0.2 V | V <sub>CCB</sub> = 3.3 V<br>± 0.3 V | V <sub>CCB</sub> = 5 V<br>± 0.5 V | UNIT |
|----------------|----------------|--------------------------------------|-------------------------------------|-------------------------------------|-----------------------------------|------|
|                |                | MIN                                  | MAX                                 | MIN                                 | MAX                               |      |
| Data rate      |                | 50                                   | 50                                  | 50                                  | 50                                | Mbps |
| t <sub>w</sub> | Pulse duration | Data inputs                          | 20                                  | 20                                  | 20                                | ns   |

## 6.8 Timing Requirements: V<sub>CCA</sub> = 1.8 V ± 0.15 V

over recommended operating free-air temperature range, V<sub>CCA</sub> = 1.8 V ± 0.15 V (unless otherwise noted)

|                |                | V <sub>CCB</sub> = 1.8 V<br>± 0.15 V | V <sub>CCB</sub> = 2.5 V<br>± 0.2 V | V <sub>CCB</sub> = 3.3 V<br>± 0.3 V | V <sub>CCB</sub> = 5 V<br>± 0.5 V | UNIT |
|----------------|----------------|--------------------------------------|-------------------------------------|-------------------------------------|-----------------------------------|------|
|                |                | MIN                                  | MAX                                 | MIN                                 | MAX                               |      |
| Data rate      |                | 52                                   | 60                                  | 60                                  | 60                                | Mbps |
| t <sub>w</sub> | Pulse duration | Data inputs                          | 19                                  | 17                                  | 17                                | 17   |

## 6.9 Timing Requirements: V<sub>CCA</sub> = 2.5 V ± 0.2 V

over recommended operating free-air temperature range, V<sub>CCA</sub> = 2.5 V ± 0.2 V (unless otherwise noted)

|                |                | V <sub>CCB</sub> = 2.5 V<br>± 0.2 V | V <sub>CCB</sub> = 3.3 V<br>± 0.3 V | V <sub>CCB</sub> = 5 V<br>± 0.5 V | UNIT |      |
|----------------|----------------|-------------------------------------|-------------------------------------|-----------------------------------|------|------|
|                |                | MIN                                 | MAX                                 | MIN                               | MAX  |      |
| Data rate      |                | 70                                  | 100                                 | 100                               | 100  | Mbps |
| t <sub>w</sub> | Pulse duration | Data inputs                         | 14                                  | 10                                | 10   | ns   |

## 6.10 Timing Requirements: $V_{CCA} = 3.3 \text{ V} \pm 0.3 \text{ V}$

over recommended operating free-air temperature range,  $V_{CCA} = 3.3 \text{ V} \pm 0.3 \text{ V}$  (unless otherwise noted)

|           |                |             |  | $V_{CCB} = 3.3 \text{ V} \pm 0.3 \text{ V}$ |     | $V_{CCB} = 5 \text{ V} \pm 0.5 \text{ V}$ |     | UNIT |
|-----------|----------------|-------------|--|---|-----|---|-----|------|
|           |                |             |  | MIN   | MAX | MIN                                       | MAX |      |
| Data rate |                |             |  |   | 100 |   | 100 | Mbps |
| $t_w$     | Pulse duration | Data inputs |  | 10  |     | 10  |     | ns   |

## 6.11 Switching Characteristics: $V_{CCA} = 1.2 \text{ V}$

$T_A = 25^\circ\text{C}$ ,  $V_{CCA} = 1.2 \text{ V}$

| PARAMETER        | FROM<br>(INPUT)            | TO<br>(OUTPUT) | $V_{CCB} = 1.8 \text{ V}$ | $V_{CCB} = 2.5 \text{ V}$ | $V_{CCB} = 3.3 \text{ V}$ | $V_{CCB} = 5 \text{ V}$ | UNIT          |
|------------------|----------------------------|----------------|---------------------------|---------------------------|---------------------------|-------------------------|---------------|
|                  |                            |                | TYP                       | TYP                       | TYP                       | TYP                     |               |
| $t_{pd}$         | A                          | B              | 9.5                       | 7.9                       | 7.6                       | 8.5                     | ns            |
|                  | B                          | A              | 9.2                       | 8.8                       | 8.4                       | 8                       |               |
| $t_{en}$         | OE                         | A              | 1                         | 1                         | 1                         | 1                       | $\mu\text{s}$ |
|                  |                            | B              | 1                         | 1                         | 1                         | 1                       |               |
| $t_{dis}$        | OE                         | A              | 20                        | 17                        | 17                        | 18                      | ns            |
|                  |                            | B              | 20                        | 16                        | 15                        | 15                      |               |
| $t_{rA}, t_{fA}$ | A-port rise and fall times |                | 4.1                       | 4.4                       | 4.1                       | 3.9                     | ns            |
| $t_{rB}, t_{fB}$ | B-port rise and fall times |                | 5                         | 5                         | 5.1                       | 5.1                     | ns            |
| $t_{SK(O)}$      | Channel-to-channel skew    |                | 2.4                       | 1.7                       | 1.9                       | 7                       | ns            |
| Max data rate    |                            |                | 20                        | 20                        | 20                        | 20                      | Mbps          |

## 6.12 Switching Characteristics: $V_{CCA} = 1.5 \text{ V} \pm 0.1 \text{ V}$

over recommended operating free-air temperature range,  $V_{CCA} = 1.5 \text{ V} \pm 0.1 \text{ V}$  (unless otherwise noted)

| PARAMETER        | FROM<br>(INPUT)            | TO<br>(OUTPUT) | $V_{CCB} = 1.8 \text{ V} \pm 0.15 \text{ V}$ | $V_{CCB} = 2.5 \text{ V} \pm 0.2 \text{ V}$ | $V_{CCB} = 3.3 \text{ V} \pm 0.3 \text{ V}$ | $V_{CCB} = 5 \text{ V} \pm 0.5 \text{ V}$ | UNIT |      |     |      |               |
|------------------|----------------------------|----------------|--|---|---|---|------|------|-----|------|---------------|
|                  |                            |                | MIN  | MAX   | MIN   | MAX                                       |      |      |     |      |               |
| $t_{pd}$         | A                          | B              | 1.4  | 12.9  | 1.2   | 10.1                                      | 1.1  | 10   | 0.8 | 9.9  | ns            |
|                  | B                          | A              | 0.9  | 14.2  | 0.7   | 12  | 0.4  | 11.7 | 0.3 | 13.7 |               |
| $t_{en}$         | OE                         | A              |  | 1   |   | 1   |      | 1    |     | 1    | $\mu\text{s}$ |
|                  |                            | B              |  | 1   |   | 1   |      | 1    |     | 1    |               |
| $t_{dis}$        | OE                         | A              | 6.6  | 33  | 6.4   | 25.3                                      | 6.1  | 23.1 | 5.9 | 24.6 | ns            |
|                  |                            | B              | 6.6  | 35.6  | 5.8   | 25.6                                      | 5.5  | 22.1 | 5.6 | 20.6 |               |
| $t_{rA}, t_{fA}$ | A-port rise and fall times |                | 0.8  | 6.5   | 0.8   | 6.3                                       | 0.8  | 6.3  | 0.8 | 6.3  | ns            |
| $t_{rB}, t_{fB}$ | B-port rise and fall times |                | 1  | 7.3   | 0.7   | 4.9                                       | 0.7  | 4.6  | 0.6 | 4.6  | ns            |
| $t_{SK(O)}$      | Channel-to-channel skew    |                |  | 2.6   |   | 1.9                                       |      | 1.6  |     | 1.3  | ns            |
| Max data rate    |                            |                | 50   |   | 50  |   | 50   |      | 50  |      | Mbps          |

### 6.13 Switching Characteristics: $V_{CCA} = 1.8 \text{ V} \pm 0.15 \text{ V}$

over recommended operating free-air temperature range,  $V_{CCA} = 1.8 \text{ V} \pm 0.15 \text{ V}$  (unless otherwise noted)

| PARAMETER        | FROM<br>(INPUT)            | TO<br>(OUTPUT) | $V_{CCB} = 1.8 \text{ V} \pm 0.15 \text{ V}$ |      | $V_{CCB} = 2.5 \text{ V} \pm 0.2 \text{ V}$ |      | $V_{CCB} = 3.3 \text{ V} \pm 0.3 \text{ V}$ |      | $V_{CCB} = 5 \text{ V} \pm 0.5 \text{ V}$ |      | UNIT          |
|------------------|----------------------------|----------------|--|------|---|------|---|------|---|------|---------------|
|                  |                            |                | MIN  | MAX  | MIN   | MAX  | MIN   | MAX  | MIN                                       | MAX  |               |
| $t_{pd}$         | A                          | B              | 1.6  | 11   | 1.4   | 7.7  | 1.3   | 6.8  | 1.2                                       | 6.5  | ns            |
|                  | B                          | A              | 1.5  | 12   | 1.2   | 8.4  | 0.8   | 7.6  | 0.5                                       | 7.1  |               |
| $t_{en}$         | OE                         | A              |  |      | 1   |      | 1   |      | 1   |      | $\mu\text{s}$ |
|                  |                            | B              |  |      | 1   |      | 1   |      | 1   |      |               |
| $t_{dis}$        | OE                         | A              | 5.9  | 26.7 | 5.6   | 21.6 | 5.4   | 18.9 | 4.8                                       | 18.7 | ns            |
|                  |                            | B              | 6.1  | 33.9 | 5.2   | 23.7 | 5   | 19.9 | 5   | 17.6 |               |
| $t_{rA}, t_{fA}$ | A-port rise and fall times |                | 0.7  | 5.1  | 0.7   | 5    | 1   | 5    | 0.7                                       | 5    | ns            |
| $t_{rB}, t_{fB}$ | B-port rise and fall times |                |  | 1    | 7.3   | 0.7  | 5   | 0.7  | 3.9                                       | 0.6  | 3.8           |
| $t_{SK(O)}$      | Channel-to-channel skew    |                |  |      | 0.8   |      | 0.7   |      | 0.6                                       |      | 0.6           |
| Max data rate    |                            |                | 52   |      | 60  |      | 60  |      | 60  |      | Mbps          |

### 6.14 Switching Characteristics: $V_{CCA} = 2.5 \text{ V} \pm 0.2 \text{ V}$

over recommended operating free-air temperature range,  $V_{CCA} = 2.5 \text{ V} \pm 0.2 \text{ V}$  (unless otherwise noted)

| PARAMETER        | FROM<br>(INPUT)            | TO<br>(OUTPUT) | $V_{CCB} = 2.5 \text{ V} \pm 0.2 \text{ V}$ |      | $V_{CCB} = 3.3 \text{ V} \pm 0.3 \text{ V}$ |      | $V_{CCB} = 5 \text{ V} \pm 0.5 \text{ V}$ |      | UNIT          |
|------------------|----------------------------|----------------|---|------|---|------|---|------|---------------|
|                  |                            |                | MIN   | MAX  | MIN   | MAX  | MIN                                       | MAX  |               |
| $t_{pd}$         | A                          | B              | 1.1   | 6.4  | 1   | 5.3  | 0.9                                       | 4.7  | ns            |
|                  | B                          | A              | 1   | 7    | 0.6   | 5.6  | 0.3                                       | 4.4  |               |
| $t_{en}$         | OE                         | A              |   |      | 1   |      | 1   |      | $\mu\text{s}$ |
|                  |                            | B              |   |      | 1   |      | 1   |      |               |
| $t_{dis}$        | OE                         | A              | 5   | 16.9 | 4.9   | 15   | 4.5                                       | 13.8 | ns            |
|                  |                            | B              | 4.8   | 21.8 | 4.5   | 17.9 | 4.4                                       | 15.2 |               |
| $t_{rA}, t_{fA}$ | A-port rise and fall times |                | 0.8   | 3.6  | 0.6   | 3.6  | 0.5                                       | 3.5  | ns            |
| $t_{rB}, t_{fB}$ | B-port rise and fall times |                | 0.6   | 4.9  | 0.7   | 3.9  | 0.6                                       | 3.2  | ns            |
| $t_{SK(O)}$      | Channel-to-channel skew    |                |   | 0.4  |   | 0.3  |   | 0.3  | ns            |
| Max data rate    |                            |                | 70  |      | 100   |      | 100                                       |      | Mbps          |

### 6.15 Switching Characteristics: $V_{CCA} = 3.3 \text{ V} \pm 0.3 \text{ V}$

over recommended operating free-air temperature range,  $V_{CCA} = 3.3 \text{ V} \pm 0.3 \text{ V}$  (unless otherwise noted)


| PARAMETER        | FROM<br>(INPUT)            | TO<br>(OUTPUT) | $V_{CCB} = 3.3 \text{ V} \pm 0.3 \text{ V}$ |      | $V_{CCB} = 5 \text{ V} \pm 0.5 \text{ V}$ |      | UNIT          |
|------------------|----------------------------|----------------|---|------|---|------|---------------|
|                  |                            |                | MIN   | MAX  | MIN                                       | MAX  |               |
| $t_{pd}$         | A                          | B              | 0.9   | 4.9  | 0.8                                       | 4    | ns            |
|                  | B                          | A              | 0.5   | 5.4  | 0.2                                       | 4    |               |
| $t_{en}$         | OE                         | A              |   |      | 1   |      | $\mu\text{s}$ |
|                  |                            | B              |   |      | 1   |      |               |
| $t_{dis}$        | OE                         | A              | 4.5   | 13.9 | 4.1                                       | 12.4 | ns            |
|                  |                            | B              | 4.1   | 17.3 | 4   | 14.4 |               |
| $t_{rA}, t_{fA}$ | A-port rise and fall times |                | 0.5   | 3    | 0.5                                       | 3    | ns            |
| $t_{rB}, t_{fB}$ | B-port rise and fall times |                | 0.7   | 3.9  | 0.6                                       | 3.2  | ns            |
| $t_{SK(O)}$      | Channel-to-channel skew    |                |   | 0.4  |   | 0.3  | ns            |
| Max data rate    |                            |                | 100   |      | 100                                       |      | Mbps          |

## 6.16 Operating Characteristics

$T_A = 25^\circ\text{C}$


| PARAMETER | TEST CONDITIONS             | $V_{CCA}$ |       |       |       |       |       |              | UNIT |  |
|-----------|-----------------------------|-----------|-------|-------|-------|-------|-------|--------------|------|--|
|           |                             | 1.2 V     | 1.2 V | 1.5 V | 1.8 V | 2.5 V | 2.5 V | 3.3 V        |      |  |
|           |                             | $V_{CCB}$ |       |       |       |       |       |              |      |  |
|           |                             | 5 V       | 1.8 V | 1.8 V | 1.8 V | 2.5 V | 5 V   | 3.3 V to 5 V |      |  |
|           |                             | TYP       | TYP   | TYP   | TYP   | TYP   | TYP   | TYP          |      |  |
| $C_{pdA}$ | A-port input, B-port output | 9         | 8     | 7     | 7     | 7     | 7     | 8            | pF   |  |
|           | B-port input, A-port output | 12        | 11    | 11    | 11    | 11    | 11    | 11           |      |  |
| $C_{pdB}$ | A-port input, B-port output | 35        | 26    | 27    | 27    | 27    | 27    | 28           |      |  |
|           | B-port input, A-port output | 26        | 19    | 18    | 18    | 18    | 20    | 21           |      |  |
| $C_{pdA}$ | A-port input, B-port output | 0.01      | 0.01  | 0.01  | 0.01  | 0.01  | 0.01  | 0.01         | pF   |  |
|           | B-port input, A-port output | 0.01      | 0.01  | 0.01  | 0.01  | 0.01  | 0.01  | 0.01         |      |  |
| $C_{pdB}$ | A-port input, B-port output | 0.01      | 0.01  | 0.01  | 0.01  | 0.01  | 0.01  | 0.03         |      |  |
|           | B-port input, A-port output | 0.01      | 0.01  | 0.01  | 0.01  | 0.01  | 0.01  | 0.03         |      |  |

## 6.17 Typical Characteristics




V<sub>CCB</sub> = 3.3 V

**Figure 6-1. Input Capacitance for OE Pin (C<sub>I</sub>) vs Power Supply (V<sub>CCA</sub>)**



V<sub>CCB</sub> = 3.3 V


**Figure 6-2. Capacitance for A Port I/O Pins (C<sub>IO</sub>) vs Power Supply (V<sub>CCA</sub>)**



V<sub>CCA</sub> = 1.8 V

**Figure 6-3. Capacitance for B Port I/O Pins (C<sub>IO</sub>) vs Power Supply (V<sub>CCB</sub>)**

## 7 Parameter Measurement Information



- A.  $C_L$  includes probe and jig capacitance.
- B. All input pulses are supplied by generators having the following characteristics: PRR  $\leq$  10 MHz,  $Z_O = 50 \Omega$ ,  $dv/dt \geq 1 \text{ V/ns}$ .
- C. The outputs are measured one at a time, with one transition per measurement.
- D.  $t_{PLH}$  and  $t_{PHL}$  are the same as  $t_{pd}$ .
- E.  $V_{CC}$  is the  $V_{CC}$  associated with the input port.
- F.  $V_{CCO}$  is the  $V_{CC}$  associated with the output port.
- G. All parameters and waveforms are not applicable to all devices.


**Figure 7-1. Load Circuits and Voltage Waveforms**

## 8 Detailed Description

### 8.1 Overview

The TXB0108 device is an 8-bit, directionless voltage-level translator specifically designed for translating logic voltage levels. The A port is able to accept I/O voltages ranging from 1.2 V to 3.6 V, while the B port can accept I/O voltages from 1.65 V to 5.5 V. The device is a buffered architecture with edge-rate accelerators (one-shots) to improve the overall data rate. This device can only translate push-pull CMOS logic outputs. If for open-drain signal translation, please refer to TI [TXS](#) products.


### 8.2 Functional Block Diagram



## 8.3 Feature Description

### 8.3.1 Architecture


The TXB0108 architecture (see [Figure 8-1](#)) does not require a direction-control signal to control the direction of data flow from A to B or from B to A. In a dc state, the output drivers of the TXB0108 can maintain a high or low, but are designed to be weak so that they can be overdriven by an external driver when data on the bus starts flowing the opposite direction. The output one-shots detect rising or falling edges on the A or B ports. During a rising edge, the one-shot turns on the PMOS transistors (T1, T3) for a short duration, which speeds up the low-to-high transition. Similarly, during a falling edge, the one-shot turns on the NMOS transistors (T2, T4) for a short duration, which speeds up the high-to-low transition. The typical output impedance during output transition is  $70\ \Omega$  at  $V_{CCO} = 1.2\text{ V}$  to  $1.8\text{ V}$ ,  $50\ \Omega$  at  $V_{CCO} = 1.8\text{ V}$  to  $3.3\text{ V}$  and  $40\ \Omega$  at  $V_{CCO} = 3.3\text{ V}$  to  $5\text{ V}$ .



**Figure 8-1. Architecture of TXB0108 I/O Cell**

### 8.3.2 Input Driver Requirements

Typical  $I_{IN}$  vs  $V_{IN}$  characteristics of the TXB0108 are shown in [Figure 8-2](#). For proper operation, the device driving the data I/Os of the TXB0108 must have drive strength of at least  $\pm 2\text{ mA}$ .



- A.  $V_T$  is the input threshold voltage of the TXB0108 (typically  $V_{CC}/2$ ).
- B.  $V_D$  is the supply voltage of the external driver.

**Figure 8-2. Typical  $I_{IN}$  vs  $V_{IN}$  Curve**

### 8.3.3 Output Load Considerations

TI recommends careful PCB layout practices with short PCB trace lengths to avoid excessive capacitive loading and to ensure that proper O.S. triggering takes place. PCB signal trace-lengths should be kept short enough such that the round-trip delay of any reflection is less than the one-shot duration. This improves signal integrity by ensuring that any reflection sees a low impedance at the driver. The O.S. circuits have been designed to stay on for approximately 10 ns. The maximum capacitance of the lumped load that can be driven also depends directly on the one-shot duration. With very heavy capacitive loads, the one-shot can time-out before the signal is driven fully to the positive rail. The O.S. duration has been set to best optimize trade-offs between dynamic ICC, load driving capability, and maximum bit-rate considerations. Both PCB trace length and connectors add to the capacitance that the TXB0108 output sees, so it is recommended that this lumped-load capacitance be considered to avoid O.S. re-triggering, bus contention, output signal oscillations, or other adverse system-level affects.

### 8.3.4 Enable and Disable

The TXB0108 has an OE input that is used to disable the device by setting OE = low, which places all I/Os in the high-impedance (Hi-Z) state. The disable time (tdis) indicates the delay between when OE goes low and when the outputs actually get disabled (Hi-Z). The enable time (ten) indicates the amount of time the user must allow for the one-shot circuitry to become operational after the OE is high.

### 8.3.5 Pullup or Pulldown Resistors on I/O Lines

The TXB0108 is designed to drive capacitive loads of up to 70 pF. The output drivers of the TXB0108 have low dc drive strength. If pullup or pulldown resistors are connected externally to the data I/Os, their values must be kept higher than 50 kΩ to ensure that they do not contend with the output drivers of the TXB0108. For the same reason, the TXB0108 should not be used in applications such as I2C or 1-Wire where an open-drain driver is connected on the bidirectional data I/O. For these applications, use a device from the TI TXS01xx series of level translators.

## 8.4 Device Functional Modes

The TXB0108 device has two functional modes, enabled and disabled. To disable the device, set the OE input low, which places all I/Os in a high impedance state. Setting the OE input high will enable the device.

## 9 Application and Implementation

### Note

Information in the following applications sections is not part of the TI component specification, and TI does not warrant its accuracy or completeness. TI's customers are responsible for determining suitability of components for their purposes, as well as validating and testing their design implementation to confirm system functionality.

### 9.1 Application Information

The TXB0108 can be used in level-translation applications for interfacing devices or systems operating at different interface voltages with one another. It can only translate push-pull CMOS logic outputs. If for open-drain signal translation, please refer to TI TXS010X products. Any external pulldown or pullup resistors are recommended to be larger than 50kΩ.

### 9.2 Typical Application




Figure 9-1. Typical Operating Circuit

#### 9.2.1 Design Requirements

For this design example, use the parameters listed in [Table 9-1](#). Make sure the VCCA ≤ VCCB.

Table 9-1. Design Parameters

| DESIGN PARAMETER     | EXAMPLE VALUE   |
|----------------------|-----------------|
| Input voltage range  | 1.2 V to 3.6 V  |
| Output voltage range | 1.65 V to 5.5 V |

#### 9.2.2 Detailed Design Procedure

To begin the design process, determine the following:

- Input voltage range

- Use the supply voltage of the device that is driving the TXB0108 device to determine the input voltage range. For a valid logic high the value must exceed the VIH of the input port. For a valid logic low, the value must be less than the VIL of the input port.

- Output voltage range

- Use the supply voltage of the device that the TXB0108 device is driving to determine the output voltage range.

- Do not recommend having the external pullup or pulldown resistors. If mandatory, it is recommended the value should be larger than 50 kΩ.

• An external pulldown or pullup resistor decreases the output  $V_{OH}$  and  $V_{OL}$ . Use the below equations to draft estimate the  $V_{OH}$  and  $V_{OL}$  as a result of an external pulldown and pullup resistor.

$$V_{OH} = V_{CCx} \times R_{PD} / (R_{PD} + 4.5 \text{ k}\Omega)$$

$$V_{OL} = V_{CCx} \times 4.5 \text{ k}\Omega / (R_{PU} + 4.5 \text{ k}\Omega)$$

Where:

- $V_{CCx}$  is the output port supply voltage on either VCCA or VCCB
- $R_{PD}$  is the value of the external pull down resistor
- $R_{PU}$  is the value of the external pull up resistor
- 4.5 kΩ is the counting the variation of the serial resistor 4 kΩ in the I/O line. Refer to the [Effects of external pullup and pulldown resistors on TXB](#) application note

### 9.2.3 Application Curves




Figure 9-2. Level-Translation of a 2.5-MHz Signal

## 10 Power Supply Recommendations

During operation, ensure that  $V_{CCA} \leq V_{CCB}$  at all times. During power-up sequencing,  $V_{CCA} \geq V_{CCB}$  does not damage the device, so any power supply can be ramped up first. The TXB0108 has circuitry that disables all output ports when either VCC is switched off ( $V_{CCA/B} = 0$  V).

The output-enable (OE) input circuit is designed so that it is supplied by  $V_{CCA}$  and when the (OE) input is low, all outputs are placed in the high-impedance state. To ensure the high-impedance state of the outputs during power-up or power-down, the OE input pin must be tied to GND through a pulldown resistor and must not be enabled until  $V_{CCA}$  and  $V_{CCB}$  are fully ramped and stable. The minimum value of the pulldown resistor to ground is determined by the current-sourcing capability of the driver.


## 11 Layout

### 11.1 Layout Guidelines

To ensure reliability of the device, the following common printed-circuit board layout guidelines is recommended.

- Bypass capacitors should be used on power supplies and should be placed as close as possible to the  $V_{CCA}$ ,  $V_{CCB}$  pin and GND pin.
- Short trace lengths should be used to avoid excessive loading.
- PCB signal trace-lengths must be kept short enough so that the round-trip delay of any reflection is less than the one-shot duration, approximately 10 ns, ensuring that any reflection encounters low impedance at the source driver.

### 11.2 Layout Example



## 12 Device and Documentation Support

### 12.1 Receiving Notification of Documentation Updates

To receive notification of documentation updates, navigate to the device product folder on [ti.com](http://ti.com). Click on *Subscribe to updates* to register and receive a weekly digest of any product information that has changed. For change details, review the revision history included in any revised document.

### 12.2 Support Resources

[TI E2E™ support forums](#) are an engineer's go-to source for fast, verified answers and design help — straight from the experts. Search existing answers or ask your own question to get the quick design help you need.

Linked content is provided "AS IS" by the respective contributors. They do not constitute TI specifications and do not necessarily reflect TI's views; see TI's [Terms of Use](#).

### 12.3 Trademarks

TI E2E™ is a trademark of Texas Instruments.

All trademarks are the property of their respective owners.

### 12.4 Electrostatic Discharge Caution



This integrated circuit can be damaged by ESD. Texas Instruments recommends that all integrated circuits be handled with appropriate precautions. Failure to observe proper handling and installation procedures can cause damage.

ESD damage can range from subtle performance degradation to complete device failure. Precision integrated circuits may be more susceptible to damage because very small parametric changes could cause the device not to meet its published specifications.

### 12.5 Glossary


[TI Glossary](#) This glossary lists and explains terms, acronyms, and definitions.

## 13 Mechanical, Packaging, and Orderable Information


The following pages include mechanical, packaging, and orderable information. This information is the most current data available for the designated devices. This data is subject to change without notice and revision of this document. For browser-based versions of this data sheet, refer to the left-hand navigation.

## 13.1 Package Addendum

### 13.1.1 Tape and Reel Information




#### QUADRANT ASSIGNMENTS FOR PIN 1 ORIENTATION IN TAPE



\*All dimensions are nominal

| Device       | Package Type               | Package Drawing | Pins | SPQ  | Reel Diameter (mm) | Reel Width W1 (mm) | A0 (mm) | B0 (mm) | K0 (mm) | P1 (mm) | W (mm) | Pin1 Quadrant |
|--------------|----------------------------|-----------------|------|------|--------------------|--------------------|---------|---------|---------|---------|--------|---------------|
| TXB0108DQSR  | USON                       | DQS             | 20   | 3000 | 177.8              | 12.4               | 2.21    | 4.22    | 0.81    | 4.0     | 12.0   | Q1            |
| TXB0108RGYR  | VQFN                       | RGY             | 20   | 3000 | 330.0              | 12.4               | 3.8     | 4.8     | 1.6     | 8.0     | 12.0   | Q1            |
| TXB0108YZPR  | DSBGA                      | YZP             | 20   | 3000 | 180.0              | 8.4                | 1.99    | 2.49    | 0.56    | 4.0     | 8.0    | Q1            |
| TXB0108YZPR2 | DSBGA                      | YZP             | 20   | 3000 | 180.0              | 8.4                | 1.99    | 2.49    | 0.56    | 4.0     | 8.0    | Q2            |
| TXB0108ZXYR  | BGA<br>MICROSTAR<br>JUNIOR | ZXY             | 20   | 2500 | 330.0              | 12.4               | 2.8     | 4.22    | 3.3     | 1.0     | 12.0   | Q2            |

**TAPE AND REEL BOX DIMENSIONS**



| Device       | Package Type               | Package Drawing | Pins | SPQ  | Length (mm) | Width (mm) | Height (mm) |
|--------------|----------------------------|-----------------|------|------|-------------|------------|-------------|
| TXB0108DQSR  | USON                       | DQS             | 20   | 3000 | 202.0       | 201.0      | 28.0        |
| TXB0108RGYR  | VQFN                       | RGY             | 20   | 3000 | 355.0       | 350.0      | 50.0        |
| TXB0108YZPR  | DSBGA                      | YZP             | 20   | 3000 | 182.0       | 182.0      | 20.0        |
| TXB0108YZPR2 | DSBGA                      | YZP             | 20   | 3000 | 182.0       | 182.0      | 20.0        |
| TXB0108ZXYR  | BGA<br>MICROSTAR<br>JUNIOR | ZXY             | 20   | 2500 | 336.6       | 336.6      | 28.6        |

**PACKAGING INFORMATION**

| Orderable part number        | Status<br>(1) | Material type<br>(2) | Package   Pins                     | Package qty   Carrier | RoHS<br>(3) | Lead finish/<br>Ball material<br>(4) | MSL rating/<br>Peak reflow<br>(5) | Op temp (°C) | Part marking<br>(6) |
|------------------------------|---------------|----------------------|------------------------------------|-----------------------|-------------|--------------------------------------|-----------------------------------|--------------|---------------------|
| <a href="#">TXB0108DGSR</a>  | Active        | Production           | VSSOP (DGS)   20                   | 5000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 85    | YE08                |
| TXB0108DGSR.A                | Active        | Production           | VSSOP (DGS)   20                   | 5000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 85    | YE08                |
| <a href="#">TXB0108DQSR</a>  | Active        | Production           | USON (DQS)   20                    | 3000   LARGE T&R      | Yes         | NIPDAUAG                             | Level-1-260C-UNLIM                | -40 to 85    | 5MR<br>5MH          |
| TXB0108DQSR.A                | Active        | Production           | USON (DQS)   20                    | 3000   LARGE T&R      | Yes         | NIPDAUAG                             | Level-1-260C-UNLIM                | -40 to 85    | 5MR<br>5MH          |
| TXB0108DQSR.B                | Active        | Production           | USON (DQS)   20                    | 3000   LARGE T&R      | Yes         | NIPDAUAG                             | Level-1-260C-UNLIM                | -40 to 85    | 5MR<br>5MH          |
| <a href="#">TXB0108NMER</a>  | Active        | Production           | NFBGA (NME)   20                   | 2500   LARGE T&R      | Yes         | SNAGCU                               | Level-2-260C-1 YEAR               | -40 to 85    | 29WW                |
| TXB0108NMER.B                | Active        | Production           | NFBGA (NME)   20                   | 2500   LARGE T&R      | Yes         | SNAGCU                               | Level-2-260C-1 YEAR               | -40 to 85    | 29WW                |
| <a href="#">TXB0108PWR</a>   | Active        | Production           | TSSOP (PW)   20                    | 2000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 85    | YE08                |
| TXB0108PWR.A                 | Active        | Production           | TSSOP (PW)   20                    | 2000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 85    | YE08                |
| TXB0108PWR.B                 | Active        | Production           | TSSOP (PW)   20                    | 2000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 85    | YE08                |
| TXB0108PWRG4                 | Active        | Production           | TSSOP (PW)   20                    | 2000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 85    | YE08                |
| <a href="#">TXB0108RGYR</a>  | Active        | Production           | VQFN (RGY)   20                    | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-2-260C-1 YEAR               | -40 to 85    | YE08                |
| TXB0108RGYR.A                | Active        | Production           | VQFN (RGY)   20                    | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-2-260C-1 YEAR               | -40 to 85    | YE08                |
| TXB0108RGYR.B                | Active        | Production           | VQFN (RGY)   20                    | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-2-260C-1 YEAR               | -40 to 85    | YE08                |
| TXB0108RGYRG4                | Active        | Production           | VQFN (RGY)   20                    | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-2-260C-1 YEAR               | -40 to 85    | YE08                |
| TXB0108RGYRG4.A              | Active        | Production           | VQFN (RGY)   20                    | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-2-260C-1 YEAR               | -40 to 85    | YE08                |
| TXB0108RGYRG4.B              | Active        | Production           | VQFN (RGY)   20                    | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-2-260C-1 YEAR               | -40 to 85    | YE08                |
| <a href="#">TXB0108RUKR</a>  | Active        | Production           | WQFN (RUK)   20                    | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 85    | YE08                |
| <a href="#">TXB0108YZPR</a>  | Active        | Production           | DSBGA (YZP)   20                   | 3000   LARGE T&R      | Yes         | SNAGCU                               | Level-1-260C-UNLIM                | -40 to 85    | 5M                  |
| TXB0108YZPR.B                | Active        | Production           | DSBGA (YZP)   20                   | 3000   LARGE T&R      | Yes         | SNAGCU                               | Level-1-260C-UNLIM                | -40 to 85    | 5M                  |
| <a href="#">TXB0108YZPR2</a> | Active        | Production           | DSBGA (YZP)   20                   | 3000   LARGE T&R      | Yes         | SNAGCU                               | Level-1-260C-UNLIM                | -40 to 85    | EK                  |
| TXB0108YZPR2.B               | Active        | Production           | DSBGA (YZP)   20                   | 3000   LARGE T&R      | Yes         | SNAGCU                               | Level-1-260C-UNLIM                | -40 to 85    | EK                  |
| <a href="#">TXB0108ZXYR</a>  | Obsolete      | Production           | BGA MICROSTAR<br>JUNIOR (ZXY)   20 | -                     | -           | Call TI                              | Call TI                           | -40 to 85    |                     |

<sup>(1)</sup> **Status:** For more details on status, see our [product life cycle](#).

<sup>(2)</sup> **Material type:** When designated, preproduction parts are prototypes/experimental devices, and are not yet approved or released for full production. Testing and final process, including without limitation quality assurance, reliability performance testing, and/or process qualification, may not yet be complete, and this item is subject to further changes or possible discontinuation. If available for ordering, purchases will be subject to an additional waiver at checkout, and are intended for early internal evaluation purposes only. These items are sold without warranties of any kind.

<sup>(3)</sup> **RoHS values:** Yes, No, RoHS Exempt. See the [TI RoHS Statement](#) for additional information and value definition.

<sup>(4)</sup> **Lead finish/Ball material:** Parts may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead finish/Ball material values may wrap to two lines if the finish value exceeds the maximum column width.

<sup>(5)</sup> **MSL rating/Peak reflow:** The moisture sensitivity level ratings and peak solder (reflow) temperatures. In the event that a part has multiple moisture sensitivity ratings, only the lowest level per JEDEC standards is shown. Refer to the shipping label for the actual reflow temperature that will be used to mount the part to the printed circuit board.

<sup>(6)</sup> **Part marking:** There may be an additional marking, which relates to the logo, the lot trace code information, or the environmental category of the part.

Multiple part markings will be inside parentheses. Only one part marking contained in parentheses and separated by a "~" will appear on a part. If a line is indented then it is a continuation of the previous line and the two combined represent the entire part marking for that device.

**Important Information and Disclaimer:** The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.


In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.

**OTHER QUALIFIED VERSIONS OF TXB0108 :**

- Automotive : [TXB0108-Q1](#)

**NOTE: Qualified Version Definitions:**

- Automotive - Q100 devices qualified for high-reliability automotive applications targeting zero defects


**TAPE AND REEL INFORMATION**


|    |   |
|----|---|
| A0 | Dimension designed to accommodate the component width     |
| B0 | Dimension designed to accommodate the component length    |
| K0 | Dimension designed to accommodate the component thickness |
| W  | Overall width of the carrier tape                         |
| P1 | Pitch between successive cavity centers                   |

**QUADRANT ASSIGNMENTS FOR PIN 1 ORIENTATION IN TAPE**


\*All dimensions are nominal

| Device        | Package Type | Package Drawing | Pins | SPQ  | Reel Diameter (mm) | Reel Width W1 (mm) | A0 (mm) | B0 (mm) | K0 (mm) | P1 (mm) | W (mm) | Pin1 Quadrant |
|---------------|--------------|-----------------|------|------|--------------------|--------------------|---------|---------|---------|---------|--------|---------------|
| TXB0108DGSR   | VSSOP        | DGS             | 20   | 5000 | 330.0              | 16.4               | 5.4     | 5.4     | 1.45    | 8.0     | 16.0   | Q1            |
| TXB0108DQSR   | USON         | DQS             | 20   | 3000 | 177.8              | 12.4               | 2.21    | 4.22    | 0.81    | 4.0     | 12.0   | Q1            |
| TXB0108NMER   | NFBGA        | NME             | 20   | 2500 | 330.0              | 12.4               | 2.85    | 3.4     | 1.34    | 4.0     | 12.0   | Q2            |
| TXB0108PWR    | TSSOP        | PW              | 20   | 2000 | 330.0              | 16.4               | 6.95    | 7.0     | 1.4     | 8.0     | 16.0   | Q1            |
| TXB0108RGYR   | VQFN         | RGY             | 20   | 3000 | 330.0              | 12.4               | 3.71    | 4.71    | 1.1     | 8.0     | 12.0   | Q1            |
| TXB0108RGYRG4 | VQFN         | RGY             | 20   | 3000 | 330.0              | 12.4               | 3.71    | 4.71    | 1.1     | 8.0     | 12.0   | Q1            |
| TXB0108RUKR   | WQFN         | RUK             | 20   | 3000 | 330.0              | 12.4               | 3.3     | 3.3     | 1.1     | 8.0     | 12.0   | Q2            |
| TXB0108YZPR   | DSBGA        | YZP             | 20   | 3000 | 180.0              | 8.4                | 1.99    | 2.49    | 0.56    | 4.0     | 8.0    | Q1            |
| TXB0108YZPR2  | DSBGA        | YZP             | 20   | 3000 | 180.0              | 8.4                | 1.99    | 2.49    | 0.56    | 4.0     | 8.0    | Q2            |


**TAPE AND REEL BOX DIMENSIONS**


\*All dimensions are nominal

| Device        | Package Type | Package Drawing | Pins | SPQ  | Length (mm) | Width (mm) | Height (mm) |
|---------------|--------------|-----------------|------|------|-------------|------------|-------------|
| TXB0108DGSR   | VSSOP        | DGS             | 20   | 5000 | 353.0       | 353.0      | 32.0        |
| TXB0108DQSR   | USON         | DQS             | 20   | 3000 | 202.0       | 201.0      | 28.0        |
| TXB0108NMR    | NFBGA        | NME             | 20   | 2500 | 336.6       | 336.6      | 31.8        |
| TXB0108PWR    | TSSOP        | PW              | 20   | 2000 | 353.0       | 353.0      | 32.0        |
| TXB0108RGYR   | VQFN         | RGY             | 20   | 3000 | 353.0       | 353.0      | 32.0        |
| TXB0108RGYRG4 | VQFN         | RGY             | 20   | 3000 | 353.0       | 353.0      | 32.0        |
| TXB0108RUKR   | WQFN         | RUK             | 20   | 3000 | 367.0       | 367.0      | 35.0        |
| TXB0108YZPR   | DSBGA        | YZP             | 20   | 3000 | 182.0       | 182.0      | 20.0        |
| TXB0108YZPR2  | DSBGA        | YZP             | 20   | 3000 | 182.0       | 182.0      | 20.0        |


# PACKAGE OUTLINE

ZXY0020A



VFBGA - 0.61 mm max height

PLASTIC BALL GRID ARRAY



4222996/A 12/2016

## NOTES:


1. All linear dimensions are in millimeters. Any dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.
2. This drawing is subject to change without notice.

# EXAMPLE BOARD LAYOUT


ZXY0020A

VFBGA - 0.61 mm max height

PLASTIC BALL GRID ARRAY



LAND PATTERN EXAMPLE  
EXPOSED METAL SHOWN  
SCALE:25X



4222996/A 12/2016

NOTES: (continued)


3. Final dimensions may vary due to manufacturing tolerance considerations and also routing constraints.  
For information, see Texas Instruments literature number SPRAA99 ([www.ti.com/lit/spraa99](http://www.ti.com/lit/spraa99)).

# EXAMPLE STENCIL DESIGN

ZXY0020A

VFBGA - 0.61 mm max height

PLASTIC BALL GRID ARRAY



SOLDER PASTE EXAMPLE  
BASED ON 0.1 mm THICK STENCIL  
SCALE: 25X


4222996/A 12/2016

NOTES: (continued)

4. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release.


## PACKAGE OUTLINE

**PW0020A**



## **TSSOP - 1.2 mm max height**

## SMALL OUTLINE PACKAGE



## NOTES:


1. All linear dimensions are in millimeters. Any dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.
2. This drawing is subject to change without notice.
3. This dimension does not include mold flash, protrusions, or gate burrs. Mold flash, protrusions, or gate burrs shall not exceed 0.15 mm per side.
4. This dimension does not include interlead flash. Interlead flash shall not exceed 0.25 mm per side.
5. Reference JEDEC registration MO-153.

## EXAMPLE BOARD LAYOUT



**PW0020A**

## **TSSOP - 1.2 mm max height**

## SMALL OUTLINE PACKAGE



LAND PATTERN EXAMPLE  
EXPOSED METAL SHOWN  
SCALE: 10X



4220206/A 02/2017

#### NOTES: (continued)


6. Publication IPC-7351 may have alternate designs.
7. Solder mask tolerances between and around signal pads can vary based on board fabrication site.

# EXAMPLE STENCIL DESIGN

PW0020A

TSSOP - 1.2 mm max height

SMALL OUTLINE PACKAGE



SOLDER PASTE EXAMPLE  
BASED ON 0.125 mm THICK STENCIL  
SCALE: 10X

4220206/A 02/2017

NOTES: (continued)

8. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.
9. Board assembly site may have different recommendations for stencil design.



## PACKAGE OUTLINE

**DGS0020A**



## **VSSOP - 1.1 mm max height**

## SMALL OUTLINE PACKAGE



4226367/A 10/2020

## NOTES:

PowerPAD is a trademark of Texas Instruments.



1. All linear dimensions are in millimeters. Any dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.
2. This drawing is subject to change without notice.
3. This dimension does not include mold flash, protrusions, or gate burrs. Mold flash, protrusions, or gate burrs shall not exceed 0.15 mm per side.
4. No JEDEC registration as of September 2020.
5. Features may differ or may not be present.

# EXAMPLE BOARD LAYOUT

DGS0020A

VSSOP - 1.1 mm max height

SMALL OUTLINE PACKAGE



4226367/A 10/2020

NOTES: (continued)


6. Publication IPC-7351 may have alternate designs.
7. Solder mask tolerances between and around signal pads can vary based on board fabrication site.
8. This package is designed to be soldered to a thermal pad on the board. For more information, see Texas Instruments literature numbers SLMA002 ([www.ti.com/lit/slma002](http://www.ti.com/lit/slma002)) and SLMA004 ([www.ti.com/lit/slma004](http://www.ti.com/lit/slma004)).
9. Size of metal pad may vary due to creepage requirement.
10. Vias are optional depending on application, refer to device data sheet. It is recommended that vias under paste be filled, plugged or tented.

# EXAMPLE STENCIL DESIGN

DGS0020A

VSSOP - 1.1 mm max height

SMALL OUTLINE PACKAGE



SOLDER PASTE EXAMPLE  
BASED ON 0.125 mm THICK STENCIL  
SCALE: 16X

4226367/A 10/2020




NOTES: (continued)

11. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.
12. Board assembly site may have different recommendations for stencil design.

## MECHANICAL DATA

DQS (R-PUSON-N20)

PLASTIC SMALL OUTLINE NO-LEAD



Bottom View

4210558/B 03/11


NOTES:

- A. All linear dimensions are in millimeters. Dimensioning and tolerancing per ASME Y14.5M-1994.
- B. This drawing is subject to change without notice.
- C. SON (Small Outline No-Lead) package configuration.

## LAND PATTERN DATA

DQS (R-PUSON-N20)

PLASTIC SMALL OUTLINE NO-LEAD




NOTES:

- A. All linear dimensions are in millimeters.
- B. This drawing is subject to change without notice.
- C. Publication IPC-7351 is recommended for alternate designs.
- D. Laser cutting apertures with trapezoidal walls and also rounding corners will offer better paste release. Customers should contact their board assembly site for stencil design recommendations. Refer to IPC 7525 for stencil design considerations.
- E. Customers should contact their board fabrication site for minimum solder mask web tolerances between signal pads.

YZP (R-XBGA-N20)

DIE-SIZE BALL GRID ARRAY



NOTES:

- All linear dimensions are in millimeters. Dimensioning and tolerancing per ASME Y14.5M-1994.
- This drawing is subject to change without notice.
- NanoFree™ package configuration.

NanoFree is a trademark of Texas Instruments.

# GENERIC PACKAGE VIEW


**RGY 20**

**VQFN - 1 mm max height**

**3.5 x 4.5, 0.5 mm pitch**


**PLASTIC QUAD FGLATPACK - NO LEAD**

This image is a representation of the package family, actual package may vary.  
Refer to the product data sheet for package details.



4225264/A


RGY0020A



# PACKAGE OUTLINE

## VQFN - 1 mm max height

PLASTIC QUAD FLATPACK - NO LEAD



4225320/A 09/2019

### NOTES:


1. All linear dimensions are in millimeters. Any dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.
2. This drawing is subject to change without notice.
3. The package thermal pad must be soldered to the printed circuit board for thermal and mechanical performance.

# EXAMPLE BOARD LAYOUT


RGY0020A

VQFN - 1 mm max height

PLASTIC QUAD FLATPACK - NO LEAD



LAND PATTERN EXAMPLE  
EXPOSED METAL SHOWN  
SCALE:18X



SOLDER MASK DETAILS

4225320/A 09/2019

NOTES: (continued)


4. This package is designed to be soldered to a thermal pad on the board. For more information, see Texas Instruments literature number SLUA271 ([www.ti.com/lit/slua271](http://www.ti.com/lit/slua271)).
5. Vias are optional depending on application, refer to device data sheet. If any vias are implemented, refer to their locations shown on this view. It is recommended that vias under paste be filled, plugged or tented.

# EXAMPLE STENCIL DESIGN

RGY0020A

VQFN - 1 mm max height

PLASTIC QUAD FLATPACK - NO LEAD



**SOLDER PASTE EXAMPLE**  
BASED ON 0.125 mm THICK STENCIL

EXPOSED PAD 21  
78% PRINTED SOLDER COVERAGE BY AREA UNDER PACKAGE  
SCALE:20X

4225320/A 09/2019

NOTES: (continued)

6. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.

## GENERIC PACKAGE VIEW


**RUK 20**

**WQFN - 0.8 mm max height**

**3 x 3, 0.4 mm pitch**

**PLASTIC QUAD FLATPACK - NO LEAD**


This image is a representation of the package family, actual package may vary.  
Refer to the product data sheet for package details.



4229651/A


# PACKAGE OUTLINE

RUK0020B



WQFN - 0.8 mm max height

PLASTIC QUAD FLATPACK - NO LEAD



## NOTES:


1. All linear dimensions are in millimeters. Any dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.
2. This drawing is subject to change without notice.
3. The package thermal pad must be soldered to the printed circuit board for thermal and mechanical performance.

## EXAMPLE BOARD LAYOUT


**RUK0020B**

## **WQFN - 0.8 mm max height**

#### PLASTIC QUAD FLATPACK - NO LEAD



## LAND PATTERN EXAMPLE



4222676/A 02/2016

#### NOTES: (continued)


4. This package is designed to be soldered to a thermal pad on the board. For more information, see Texas Instruments literature number SLUA271 ([www.ti.com/lit/slua271](http://www.ti.com/lit/slua271)).
5. Vias are optional depending on application, refer to device data sheet. If any vias are implemented, refer to their locations shown on this view. It is recommended that vias under paste be filled, plugged or tented.

# EXAMPLE STENCIL DESIGN

RUK0020B

WQFN - 0.8 mm max height

PLASTIC QUAD FLATPACK - NO LEAD



SOLDER PASTE EXAMPLE  
BASED ON 0.1 mm THICK STENCIL


EXPOSED PAD 21:  
78% PRINTED SOLDER COVERAGE BY AREA UNDER PACKAGE  
SCALE:20X

4222676/A 02/2016

NOTES: (continued)

6. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.


NME0020A



PACKAGE OUTLINE

NFBGA - 1 mm max height

PLASTIC BALL GRID ARRAY



4224888/C 05/2023

NOTES:


1. All linear dimensions are in millimeters. Any dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.
2. This drawing is subject to change without notice.

# EXAMPLE BOARD LAYOUT


NME0020A

NFBGA - 1 mm max height

PLASTIC BALL GRID ARRAY



LAND PATTERN EXAMPLE  
EXPOSED METAL SHOWN  
SCALE:25X



4224888/C 05/2023

NOTES: (continued)


3. Final dimensions may vary due to manufacturing tolerance considerations and also routing constraints.  
For information, see Texas Instruments literature number SPRAA99 ([www.ti.com/lit/spraa99](http://www.ti.com/lit/spraa99)).

# EXAMPLE STENCIL DESIGN

NME0020A

NFBGA - 1 mm max height

PLASTIC BALL GRID ARRAY



SOLDER PASTE EXAMPLE  
BASED ON 0.1 mm THICK STENCIL  
SCALE: 25X

4224888/C 05/2023

NOTES: (continued)

4. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release.

## IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATASHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, regulatory or other requirements.

These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you fully indemnify TI and its representatives against any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to [TI's Terms of Sale](#), [TI's General Quality Guidelines](#), or other applicable terms available either on [ti.com](#) or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products. Unless TI explicitly designates a product as custom or customer-specified, TI products are standard, catalog, general purpose devices.

TI objects to and rejects any additional or different terms you may propose.

Copyright © 2026, Texas Instruments Incorporated

Last updated 10/2025