

INA141 高精度、低消費電力、 $G = 10V/V$ または $100V/V$ 、計測アンプ

1 特長

- 低いオフセット電圧:
 - $G = 100V/V$ で最大 $50\mu V$
- 低いドリフト:
 - $G = 100V/V$ で最大 $0.5\mu V/^\circ C$
- 高精度のゲイン:
 - $G = 10V/V$ で $\pm 0.05\%$
- 低い入力バイアス電流:
 - $5nA$ (最大値)
- 高い CMR:
 - $117dB$ (最小値)
- $\pm 40V$ までの入力保護
- 広い電源電圧範囲: $\pm 2.25V \sim \pm 18V$
- 低い静止電流: $750\mu A$

2 アプリケーション

- 温度トランスミッタ
- 医療用計測機器
- データ・アキュイジション (DAQ)
- プロセス分析 (pH、ガス、濃度、力、湿度)

3 概要

INA141 は、精度の優れた低消費電力の汎用計測アンプです。本デバイスは、用途が広い 3 オペアンプ設計を採用しており、サイズが小型であるため、広範なアプリケーションに非常に適しています。電流帰還入力回路により、高いゲインでも広い帯域幅が得られます ($G = 100V/V$ で $200kHz$)。

シンプルなピン接続により、外付け抵抗なしで $10V/V$ または $100V/V$ の高精度ゲインを設定できます。内部入力保護機能は、損傷なしに $\pm 40V$ まで耐えられます。


INA141 はレーザー・トリムにより、非常に低いオフセット電圧 ($50\mu V$) とドリフト係数 ($0.5\mu V/^\circ C$)、高い同相除去 ($G = 100V/V$ で $117dB$) を実現しています。このデバイスは最低 $\pm 2.25V$ の電源で動作し、静止電流はわずか $750\mu A$ です。

INA141 は 8 ピン SOIC パッケージで供給され、 $-40^\circ C \sim +85^\circ C$ の温度範囲で動作が規定されています。

パッケージ情報

| 部品番号 | パッケージ(1) | パッケージ・サイズ(2) |
|--------|-------------|--------------|
| INA141 | D (SOIC, 8) | 4.9mm × 6mm |

- 利用可能なすべてのパッケージについては、データシートの末尾にある注文情報を参照してください。
- パッケージ・サイズ (長さ×幅) は公称値であり、該当する場合はピンも含まれます。



基本的な接続



Table of Contents

| | | | |
|---|---|---|-----------|
| 1 特長..... | 1 | 6.6 Typical Characteristics..... | 8 |
| 2 アプリケーション..... | 1 | 7 Application and Implementation..... | 12 |
| 3 概要..... | 1 | 7.1 Application Information..... | 12 |
| 4 Revision History..... | 2 | 8 Device and Documentation Support..... | 17 |
| 5 Pin Configuration and Functions..... | 4 | 8.1 ドキュメントの更新通知を受け取る方法..... | 17 |
| 6 Specifications..... | 5 | 8.2 サポート・リソース..... | 17 |
| 6.1 Absolute Maximum Ratings..... | 5 | 8.3 Trademarks..... | 17 |
| 6.2 ESD Ratings..... | 5 | 8.4 静電気放電に関する注意事項..... | 17 |
| 6.3 Recommended Operating Conditions..... | 5 | 8.5 用語集..... | 17 |
| 6.4 Thermal Information..... | 5 | 9 Mechanical, Packaging, and Orderable Information.. | 17 |
| 6.5 Electrical Characteristics..... | 6 | | |

4 Revision History

資料番号末尾の英字は改訂を表しています。その改訂履歴は英語版に準じています。

| Changes from Revision * (September 2000) to Revision A (August 2023) | Page |
|--|------|
| ドキュメント全体にわたって表、図、相互参照の採番方法を更新..... | 1 |
| 「パッケージ情報」表、「ピン構成および機能」セクション、「仕様」セクション、「ESD 定格」セクション、「推奨動作条件」セクション、「熱に関する情報」セクション、「アプリケーションと実装」セクション、「デバイスおよびドキュメントのサポート」セクション、「メカニカル、パッケージ、および注文情報」セクションを追加..... | 1 |
| データシートから PDIP パッケージを削除..... | 1 |
| Added single supply specification to Absolute Maximum Ratings..... | 5 |
| Added note that output short-circuit (to ground) means short-circuit to $V_S/2$ in Absolute Maximum Ratings..... | 5 |
| Added "TA = -40°C to +85°C" test condition to Offset voltage vs temperature specification in the Electrical Characteristics and renamed to Offset voltage drift..... | 6 |
| Added test conditions "VREF = 0 V, VCM = VS / 2 and G = 10 below the title..... | 6 |
| Deleted common-mode voltage typical values in the Electrical Characteristics and combined to one line..... | 6 |
| Added "TA = -40°C to +85°C" test condition to Bias current vs temperature specification in the Electrical Characteristics and renamed to Input bias current drift for clarity..... | 6 |
| Added "TA = -40°C to +85°C" test condition to Offset current vs temperature specification in Electrical Characteristics and renamed to Input offset current drift for clarity..... | 6 |
| Added "TA = -40°C to +85°C" test condition for Gain error vs temperature in the Electrical Characteristics and renamed to Gain drift for clarity..... | 6 |
| Changed parameter names from "Voltage - Positive" and "Voltage - Negative" to "Output voltage" in the Electrical Characteristics..... | 6 |
| Added "Continuous to VS / 2" test condition short-circuit current specification in the Electrical Characteristics for clarity..... | 6 |
| Changed short-circuit current typical value from +6/-15 mA ±20 mA..... | 6 |
| Changed bandwidth typical value from 1 MHz to 610 kHz in the Electrical Characteristics..... | 6 |
| Changed slew rate typical value from 4 V/μs to 2 V/μs in the Electrical Characteristics..... | 6 |
| Deleted redundant voltage range, operating temperature range, and specification temperature range specifications from Electrical Characteristics..... | 6 |
| Changed Figure 6-2, <i>Common-Mode Rejection vs Frequency</i> | 8 |
| Changed Figure 6-8, <i>Quiescent Current and Slew Rate vs Temperature</i> | 8 |
| Changed <i>Output Voltage Swing vs Output Current</i> single plot to Figure 6-12, <i>Positive Output Voltage Swing vs Output Current</i> and Figure 6-12, <i>Negative Output Voltage Swing vs Output Current</i> | 8 |
| Changed Figure 6-18, <i>Small-Signal Step Response</i> | 8 |
| Changed Figure 6-19, <i>Large-Signal Step Response</i> | 8 |
| Changed Figure 6-20, <i>0.1-Hz to 10-Hz Input-Referred Voltage Noise</i> | 8 |
| Changed G from 1 to 10 V/V at the end of the <i>Application Information</i> section..... | 12 |

-
- Deleted reference to *Input Bias Current vs Common-Mode Input Voltage* plot..... 14
-

5 Pin Configuration and Functions




図 5-1. D Package, 8-Pin SOIC (Top View)

表 5-1. Pin Functions

| PIN | | TYPE | DESCRIPTION |
|------------------------------|------|--------|---|
| NAME | NO. | | |
| J | 1, 8 | Input | Gain selection. G = 10 V/V if not shorted G = 100 V/V if shorted A resistance of 0.5 Ω decreases gain by 0.1%. |
| Ref | 5 | Input | Reference input. This pin must be driven by low impedance |
| V- | 4 | — | Negative supply |
| V+ | 7 | — | Positive supply |
| V ⁻ _{IN} | 2 | Input | Negative (inverting) input |
| V ⁺ _{IN} | 3 | Input | Positive (noninverting) input |
| V _O | 6 | Output | Output |

6 Specifications

6.1 Absolute Maximum Ratings

over operating free-air temperature range (unless otherwise noted)⁽¹⁾

| | | | MIN | MAX | UNIT |
|------------------|---|--|------------|-----|------|
| V _S | Supply voltage | Dual supply, V _S = (V+) – (V–) | | ±18 | V |
| | | Single supply, V _S = (V+) – 0 V | | 36 | |
| | Input voltage | | | ±40 | V |
| | Output short-circuit (to ground) ⁽²⁾ | | Continuous | | |
| T _A | Operating temperature | | –40 | 125 | °C |
| T _{stg} | Storage temperature | | –40 | 125 | °C |
| T _J | Junction temperature | | | 150 | °C |
| | Lead temperature (soldering, 10 s) | | | 300 | |

- (1) Operation outside the Absolute Maximum Ratings may cause permanent device damage. Absolute Maximum Ratings do not imply functional operation of the device at these or any other conditions beyond those listed under Recommended Operating Conditions. If used outside the Recommended Operating Conditions but within the Absolute Maximum Ratings, the device may not be fully functional, and this may affect device reliability, functionality, performance, and shorten the device lifetime.
- (2) Short-circuit to V_S / 2.

6.2 ESD Ratings

| | | | VALUE | UNIT |
|--------------------|-------------------------|---|-------|------|
| V _(ESD) | Electrostatic discharge | Human-body model (HBM), per ANSI/ESDA/JEDEC JS-001 ⁽¹⁾ | ±2000 | V |
| | | Charged-device model (CDM), per ANSI/ESDA/JEDEC JS-002 ⁽²⁾ | ±250 | |

- (1) JEDEC document JEP155 states that 500-V HBM allows safe manufacturing with a standard ESD control process.
- (2) JEDEC document JEP157 states that 250-V CDM allows safe manufacturing with a standard ESD control process.

6.3 Recommended Operating Conditions

over operating free-air temperature range (unless otherwise noted)

| | | | MIN | TYP | MAX | UNIT |
|----------------|-----------------------|---------------|-------|-----|-----|------|
| V _S | Supply voltage | Single-supply | 4.5 | 30 | 36 | V |
| | | Dual-supply | ±2.25 | ±15 | ±18 | |
| T _A | Specified temperature | | –40 | | 85 | °C |

6.4 Thermal Information

| THERMAL METRIC ⁽¹⁾ | | INA141 | UNIT |
|-------------------------------|--|----------|------|
| | | D (SOIC) | |
| | | 8 PINS | |
| θ _{JA} | Junction-to-ambient thermal resistance | 150 | °C/W |
| R _{θJA} | Junction-to-ambient thermal resistance | 110 | °C/W |
| R _{θJC(top)} | Junction-to-case (top) thermal resistance | 57 | °C/W |
| R _{θJB} | Junction-to-board thermal resistance | 54 | °C/W |
| ψ _{JT} | Junction-to-top characterization parameter | 11 | °C/W |
| ψ _{JB} | Junction-to-board characterization parameter | 53 | °C/W |

- (1) For more information about traditional and new thermal metrics, see the [Semiconductor and IC Package Thermal Metrics](#) application report.

6.5 Electrical Characteristics

at $T_A = 25^\circ\text{C}$, $V_S = \pm 15\text{ V}$, $R_L = 10\text{ k}\Omega$, $V_{\text{REF}} = 0\text{ V}$, $V_{\text{CM}} = V_S / 2$, and $G = 10\text{ V/V}$ (unless otherwise noted)

| PARAMETER | | TEST CONDITIONS | | MIN | TYP | MAX | UNIT |
|---------------------------|------------------------------------|--|----------------------|---|-----------|---------------------------------|------------------------------|
| INPUT | | | | | | | |
| V_{OS} | Offset voltage (RTI) | INA141P, INA141U | $G = 10\text{ V/V}$ | | ± 50 | ± 100 | μV |
| | | | $G = 100\text{ V/V}$ | | ± 20 | ± 50 | |
| | | INA141PA, INA141UA | $G = 10\text{ V/V}$ | | ± 50 | ± 250 | |
| | | | $G = 100\text{ V/V}$ | | ± 20 | ± 125 | |
| | Offset voltage drift (RTI) | $T_A = -40^\circ\text{C}$ to $+85^\circ\text{C}$ | INA141P, INA141U | $G = 10\text{ V/V}$ | ± 0.5 | ± 2 | $\mu\text{V}/^\circ\text{C}$ |
| | | | | $G = 100\text{ V/V}$ | ± 0.2 | ± 0.5 | |
| | | | INA141PA, INA141UA | $G = 10\text{ V/V}$ | ± 0.5 | ± 2.5 | |
| | | | | $G = 100\text{ V/V}$ | ± 0.2 | ± 1.5 | |
| PSRR | Power-supply rejection ratio (RTI) | $V_S = \pm 2.25\text{ V}$ to $\pm 18\text{ V}$ | INA141P, INA141U | $G = 10\text{ V/V}$ | ± 2 | ± 10 | $\mu\text{V/V}$ |
| | | | | $G = 100\text{ V/V}$ | ± 0.4 | ± 1 | |
| | | | INA141PA, INA141UA | $G = 10\text{ V/V}$ | ± 2 | ± 20 | |
| | | | | $G = 100\text{ V/V}$ | ± 0.4 | ± 3 | |
| | Long-term stability | $G = 10\text{ V/V}$ $G = 100\text{ V/V}$ | | 0.5 | | $\mu\text{V}/\text{mo}$ | |
| | | | | 0.2 | | $\mu\text{V}/\text{mo}$ | |
| | Input impedance | Differential Common-mode | | 100 2 | | $\text{G}\Omega$ pF | |
| | | | | 100 9 | | | |
| V_{CM} | Common-mode voltage ⁽¹⁾ | $V_O = 0\text{ V}$ | | $(V_-) + 2$ | | $(V_+) - 2$ | V |
| CMRR | Common-mode rejection | $V_{\text{CM}} = \pm 13\text{ V}$, $\Delta R_S = 1\text{ k}\Omega$ | INA141P, INA141U | $G = 10\text{ V/V}$ | 100 | 106 | dB |
| | | | | $G = 100\text{ V/V}$ | 117 | 125 | |
| | | | INA141PA, INA141UA | $G = 10\text{ V/V}$ | 93 | 100 | |
| | | | | $G = 100\text{ V/V}$ | 110 | 120 | |
| INPUT BIAS CURRENT | | | | | | | |
| I_B | Input bias current | INA141P, INA141U | | | ± 2 | ± 5 | nA |
| | | INA141PA, INA141UA | | | ± 2 | ± 10 | |
| | Input bias current drift | $T_A = -40^\circ\text{C}$ to $+85^\circ\text{C}$ | | | ± 30 | | $\text{pA}/^\circ\text{C}$ |
| I_{OS} | Input offset current | INA141P, INA141U | | | ± 1 | ± 5 | nA |
| | | INA141PA, INA141UA | | | ± 1 | ± 10 | nA |
| | Input offset current drift | $T_A = -40^\circ\text{C}$ to $+85^\circ\text{C}$ | | | ± 30 | | $\text{pA}/^\circ\text{C}$ |
| NOISE | | | | | | | |
| e_n | Voltage noise (RTI) | $R_S = 0\ \Omega$ | $G = 10\text{ V/V}$ | $f = 10\text{ Hz}$ | 22 | | $\text{nV}/\sqrt{\text{Hz}}$ |
| | | | | $f = 100\text{ Hz}$ | 13 | | |
| | | | | $f = 1\text{ kHz}$ | 12 | | |
| | | | | $f_B = 0.1\text{ Hz}$ to 10 Hz | 0.6 | | μV_{PP} |
| | | | $G = 100\text{ V/V}$ | $f = 10\text{ Hz}$ | 10 | | $\text{nV}/\sqrt{\text{Hz}}$ |
| | | | | $f = 100\text{ Hz}$ | 8 | | |
| | | | | $f = 1\text{ kHz}$ | 8 | | |
| | | | | $f_B = 0.1\text{ Hz}$ to 10 Hz | 0.2 | | μV_{PP} |
| I_n | Current noise | $f = 10\text{ Hz}$ | | | 0.9 | | $\text{pA}/\sqrt{\text{Hz}}$ |
| | | $f = 1\text{ kHz}$ | | | 0.3 | | |
| | | $f_B = 0.1\text{ Hz}$ to 10 Hz | | | 30 | | pA_{PP} |

6.5 Electrical Characteristics (続き)


at $T_A = 25^\circ\text{C}$, $V_S = \pm 15\text{ V}$, $R_L = 10\text{ k}\Omega$, $V_{REF} = 0\text{ V}$, $V_{CM} = V_S / 2$, and $G = 10\text{ V/V}$ (unless otherwise noted)

| PARAMETER | | TEST CONDITIONS | | MIN | TYP | MAX | UNIT |
|---------------------------|---------------------------|--|-----------------------|--------------|------------------|--------------|-----------------------|
| GAIN | | | | | | | |
| G | Gain | | | 10 | | 100 | V/V |
| GE | Gain error | $V_O = \pm 13.6\text{ V}$ | INA141P, INA141U | G = 10 V/V | ± 0.01 | ± 0.05 | % |
| | | | | G = 100 V/V | ± 0.03 | ± 0.075 | |
| | | | INA141PA, INA141UA | G = 10 V/V | ± 0.01 | ± 0.15 | |
| | | | | G = 100 V/V | ± 0.03 | ± 0.15 | |
| | Gain drift ⁽⁶⁾ | $G = 10\text{ V/V}$ or 100 V/V , $T_A = -40^\circ\text{C}$ to $+85^\circ\text{C}$ | | | ± 2 | ± 10 | ppm/ $^\circ\text{C}$ |
| | Gain nonlinearity | INA141P, INA141U INA141PA, INA141UA | G = 10 V/V | ± 0.0003 | ± 0.001 | % of FSR | |
| | | | G = 100 V/V | ± 0.0005 | ± 0.002 | | |
| | | | G = 10 V/V | ± 0.0003 | ± 0.002 | | |
| | | | G = 100 V/V | ± 0.0005 | ± 0.004 | | |
| OUTPUT | | | | | | | |
| | Output voltage | | | $(V-) + 1.4$ | $(V\pm) \mp 0.9$ | $(V+) - 1.4$ | V |
| C_L | Load capacitance | Stable operation | | | 1000 | | pF |
| I_{SC} | Short-circuit current | Continuous to $V_S / 2$ | | | ± 20 | | mA |
| FREQUENCY RESPONSE | | | | | | | |
| BW | Bandwidth, -3 dB | G = 10 V/V | | | 610 | | kHz |
| | | G = 100 V/V | | | 200 | | kHz |
| SR | Slew rate | G = 10 V/V, $V_O = \pm 10\text{ V}$ | | | 2 | | V/ μs |
| t_s | Settling time | T_o 0.01%, $V_O = \pm 5\text{ V}$ | | G = 10 V/V | 7 | | μs |
| | | | | G = 100 V/V | 9 | | |
| | Overload recovery | 50% input overload | | | 4 | | μs |
| POWER SUPPLY | | | | | | | |
| I_Q | Quiescent current | $V_{IN} = 0\text{ V}$ | | | ± 750 | ± 800 | μA |


- (1) Input common-mode voltage varies with output voltage; see *Typical Characteristics*.
 (2) Specified by wafer test.

6.6 Typical Characteristics


at $T_A = 25^\circ\text{C}$, $V_S = \pm 15\text{ V}$, $V_{\text{REF}} = 0\text{ V}$, $G = 10\text{ V/V}$, $V_{\text{CM}} = V_S / 2$, and $R_L = 10\text{ k}\Omega$ (unless otherwise noted)




6-1. Gain vs Frequency




6-2. Common-Mode Rejection vs Frequency




6-3. Positive Power Supply Rejection vs Frequency



6-4. Negative Power Supply Rejection vs Frequency



6-5. Input Common-Mode Range vs Output Voltage



6-6. Input Common-Mode Range vs Output Voltage

6.6 Typical Characteristics (continued)

at $T_A = 25^\circ\text{C}$, $V_S = \pm 15\text{ V}$, $V_{\text{REF}} = 0\text{ V}$, $G = 10\text{ V/V}$, $V_{\text{CM}} = V_S / 2$, and $R_L = 10\text{ k}\Omega$ (unless otherwise noted)




Figure 6-7. Input-Referred Noise vs Frequency




Figure 6-8. Quiescent Current and Slew Rate vs Temperature




Figure 6-9. Input Overvoltage V/I Characteristics




Figure 6-10. Input Offset Voltage Warmup




Figure 6-11. Input Bias Current vs Temperature






Figure 6-12. Positive Output Voltage Swing vs Output Current

6.6 Typical Characteristics (continued)


at $T_A = 25^\circ\text{C}$, $V_S = \pm 15\text{ V}$, $V_{REF} = 0\text{ V}$, $G = 10\text{ V/V}$, $V_{CM} = V_S / 2$, and $R_L = 10\text{ k}\Omega$ (unless otherwise noted)




6-13. Negative Output Voltage Swing vs Output Current




6-14. Output Voltage Swing vs Power Supply Voltage




6-15. Short-circuit Output Current vs Temperature



6-16. Maximum Output Voltage vs Frequency





6-17. Total Harmonic Distortion + Noise vs Frequency



6-18. Small-Signal Step Response

6.6 Typical Characteristics (continued)

at $T_A = 25^\circ\text{C}$, $V_S = \pm 15\text{ V}$, $V_{\text{REF}} = 0\text{ V}$, $G = 10\text{ V/V}$, $V_{\text{CM}} = V_S / 2$, and $R_L = 10\text{ k}\Omega$ (unless otherwise noted)



7 Application and Implementation

注

以下のアプリケーション情報は、TI の製品仕様に含まれるものではなく、TI ではその正確性または完全性を保証いたしません。個々の目的に対する製品の適合性については、お客様の責任で判断していただくこととなります。お客様は自身の設計実装を検証しテストすることで、システムの機能を確認する必要があります。

7.1 Application Information

図 7-1 shows the basic connections required for operation of the INA141. Applications with noisy or high impedance power supplies can require decoupling capacitors close to the device pins as shown.




図 7-1. Basic Connections.

The output is referred to the output reference (Ref) pin, which is normally grounded. This connection must be low-impedance to maintain good common-mode rejection. A resistance of 8 Ω in series with the Ref pin causes a typical device to degrade to approximately 80 dB CMR ($G = 10$ V/V).

7.1.1 Setting the Gain

Gain is selected with a jumper connection (see 図 7-1). With no jumper installed, $G = 10$ V/V. With a jumper installed, $G = 100$ V/V. To preserve good gain accuracy, this jumper must have low series resistance. A resistance of 0.5 Ω in series with the jumper decreases the gain by 0.1%.

Internal resistor ratios are laser trimmed to provide excellent gain accuracy. Actual resistor values can vary by approximately $\pm 25\%$ from the nominal values shown.

Gains between 10 V/V and 100 V/V are achieved by connecting an external resistor to the jumper pins. However, this configuration is not recommended because the $\pm 25\%$ variation of internal resistor values makes the required external resistor value uncertain. A companion model, the [INA128](#), features accurately trimmed internal resistors so that gains from 1 V/V to 10,000 V/V can be set with an external resistor.

7.1.2 Dynamic Performance

Typical performance curve *Gain vs Frequency* (Figure 6-1) shows that, despite the low quiescent current, the INA141 achieves wide bandwidth, even at $G = 100 \text{ V/V}$. This wide bandwidth is a result of the current-feedback topology of the INA141. Settling time also remains excellent at $G = 100 \text{ V/V}$.

7.1.3 Noise Performance

The INA141 provides very low noise in most applications. Low-frequency noise is approximately $0.2 \mu\text{V}_{\text{PP}}$ measured from 0.1 Hz to 10 Hz ($G = 100 \text{ V/V}$). The INA141 provides dramatically improved noise when compared to state-of-the-art, chopper-stabilized amplifiers.

7.1.4 Offset Trimming

The INA141 is laser trimmed for low offset voltage and offset voltage drift. Most applications require no external offset adjustment. Figure 7-2 shows an optional circuit for trimming the output offset voltage. The voltage applied to Ref pin is summed with the output. The op-amp buffer provides low impedance at the Ref pin to preserve good common-mode rejection.





Figure 7-2. Optional Trimming of Output Offset Voltage.

7.1.5 Input Bias Current Return Path

The input impedance of the INA141 is extremely high—approximately $10^{10} \Omega$. However, a path must be provided for the input bias current of both inputs. This input bias current is approximately $\pm 2 \text{ nA}$. High input impedance means that this input bias current changes very little with varying input voltage.

Input circuitry must provide a path for this input bias current for proper operation. Figure 7-3 shows various provisions for an input bias current path. Without a bias current path, the inputs float to a potential that exceeds the common-mode range of the INA141 and the input amplifiers saturate.

If the differential source resistance is low, the bias current return path can be connected to one input (see the thermocouple example in Figure 7-3). With higher source impedance, using two equal resistors provides a balanced input with possible advantages of lower input offset voltage due to bias current and better high-frequency common-mode rejection.



☒ 7-3. Providing an Input Common-Mode Current Path.

7.1.6 Input Common-Mode Range

The linear input voltage range of the input circuitry of the INA141 is from approximately 1.4 V less than the positive supply voltage to 1.7 V greater than the negative supply. As a differential input voltage causes the output voltage to increase, however, the linear input range is limited by the output voltage swing of amplifiers A_1 and A_2 . Therefore, the linear common-mode input range is related to the output voltage of the complete amplifier. This behavior also depends on supply voltage (see the *Input Common-Mode Range vs Output Voltage* plots, ☒ 6-5 and ☒ 6-6).

Input overload can produce an output voltage that appears normal. For example, if an input overload condition drives both input amplifiers to the positive output swing limit, the difference voltage measured by the output amplifier is near zero. The output of the INA141 is near 0 V even though both inputs are overloaded.

7.1.7 Low-Voltage Operation

The INA141 operates on power supplies as low as ± 2.25 V. Performance remains excellent with power supplies ranging from ± 2.25 V to ± 18 V. Most parameters vary only slightly through this supply voltage range—see Typical Performance Curves. Operation at a very low supply voltage requires careful attention to make sure that the input voltages remain within the linear range. Voltage swing requirements of internal nodes limit the input common-mode range with low power-supply voltage. The *Input Common-Mode Range vs Output Voltage* typical characteristics plots, ☒ 6-5 and ☒ 6-6, show the range of linear operation for ± 15 -V, ± 5 -V, and ± 2.5 -V supplies.

7.1.8 Input Protection

The inputs of the INA141 are individually protected for voltages up to ± 40 V. For example, a condition of -40 V on one input and $+40$ V on the other input does not cause damage. Internal circuitry on each input provides low series impedance under normal signal conditions. To provide equivalent protection, series input resistors contributes excessive noise. If the input is overloaded, the protection circuitry limits the input current to a safe value of approximately 1.50 mA to 5 mA. The inputs are protected even if the power supplies are disconnected or turned off.




図 7-4. ECG Amplifier With Right-Leg Drive




図 7-5. Bridge Amplifier






図 7-6. AC-Coupled Instrumentation Amplifier



| ISA TYPE | MATERIAL | SEEBECK COEFFICIENT (μV/°C) | R ₁ , R ₂ |
|----------|---------------------------|-----------------------------|---------------------------------|
| E | + Chromel - Constantan | 58.5 | 66.5kΩ |
| J | + Iron - Constantan | 50.2 | 76.8kΩ |
| K | + Chromel - Alumel | 39.4 | 97.6kΩ |
| T | + Copper - Constantan | 38.0 | 102kΩ |

図 7-7. Thermocouple Amplifier With RTD Cold-Junction Compensation



| A ₁ | I _B Error |
|----------------|----------------------|
| OPA177 | ±1.5nA |
| OPA131 | 50pA |
| OPA602 | ±1pA |
| OPA128 | ±75fA |

図 7-8. Differential Voltage-to-Current Converter

8 Device and Documentation Support

TI offers an extensive line of development tools. Tools and software to evaluate the performance of the device, generate code, and develop solutions are listed below.

8.1 ドキュメントの更新通知を受け取る方法

ドキュメントの更新についての通知を受け取るには、ti.com のデバイス製品フォルダを開いてください。「更新の通知を受け取る」をクリックして登録すると、変更されたすべての製品情報に関するダイジェストを毎週受け取れます。変更の詳細については、修正されたドキュメントに含まれている改訂履歴をご覧ください。

8.2 サポート・リソース

[TI E2E™ サポート・フォーラム](#)は、エンジニアが検証済みの回答と設計に関するヒントをエキスパートから迅速かつ直接得ることができる場所です。既存の回答を検索したり、独自の質問をしたりすることで、設計に必要な支援を迅速に得ることができます。

リンクされているコンテンツは、該当する貢献者により、現状のまま提供されるものです。これらは TI の仕様を構成するものではなく、必ずしも TI の見解を反映したものではありません。TI の[使用条件](#)を参照してください。

8.3 Trademarks

TI E2E™ is a trademark of Texas Instruments.

すべての商標は、それぞれの所有者に帰属します。

8.4 静電気放電に関する注意事項



この IC は、ESD によって破損する可能性があります。テキサス・インスツルメンツは、IC を取り扱う際には常に適切な注意を払うことを推奨します。正しい取り扱いおよび設置手順に従わない場合、デバイスを破損するおそれがあります。

ESD による破損は、わずかな性能低下からデバイスの完全な故障まで多岐にわたります。精密な IC の場合、パラメータがわずかに変化するだけで公表されている仕様から外れる可能性があるため、破損が発生しやすくなっています。

8.5 用語集

[テキサス・インスツルメンツ用語集](#) この用語集には、用語や略語の一覧および定義が記載されています。

9 Mechanical, Packaging, and Orderable Information

The following pages include mechanical, packaging, and orderable information. This information is the most current data available for the designated devices. This data is subject to change without notice and revision of this document. For browser-based versions of this data sheet, refer to the left-hand navigation.

PACKAGING INFORMATION

| Orderable part number | Status (1) | Material type (2) | Package Pins | Package qty Carrier | RoHS (3) | Lead finish/ Ball material (4) | MSL rating/ Peak reflow (5) | Op temp (°C) | Part marking (6) |
|------------------------------|---------------|----------------------|----------------|-----------------------|-------------|--------------------------------------|-----------------------------------|--------------|---------------------|
| INA141U | Active | Production | SOIC (D) 8 | 75 TUBE | Yes | Call TI Nipdau | Level-3-260C-168 HR | - | INA 141U |
| INA141U.Z | Active | Production | SOIC (D) 8 | 75 TUBE | Yes | Call TI | Level-3-260C-168 HR | -40 to 85 | INA 141U |
| INA141U/2K5 | Active | Production | SOIC (D) 8 | 2500 LARGE T&R | Yes | Call TI Nipdau | Level-3-260C-168 HR | - | INA 141U |
| INA141U/2K5.Z | Active | Production | SOIC (D) 8 | 2500 LARGE T&R | Yes | Call TI | Level-3-260C-168 HR | -40 to 85 | INA 141U |
| INA141UA | Active | Production | SOIC (D) 8 | 75 TUBE | Yes | Call TI Nipdau | Level-3-260C-168 HR | -40 to 85 | INA 141U A |
| INA141UA.Z | Active | Production | SOIC (D) 8 | 75 TUBE | Yes | Call TI | Level-3-260C-168 HR | -40 to 85 | INA 141U A |
| INA141UA/2K5 | Active | Production | SOIC (D) 8 | 2500 LARGE T&R | Yes | Call TI Nipdau | Level-3-260C-168 HR | -40 to 85 | INA 141U A |
| INA141UA/2K5.Z | Active | Production | SOIC (D) 8 | 2500 LARGE T&R | Yes | Call TI | Level-3-260C-168 HR | -40 to 85 | INA 141U A |

⁽¹⁾ **Status:** For more details on status, see our [product life cycle](#).

⁽²⁾ **Material type:** When designated, preproduction parts are prototypes/experimental devices, and are not yet approved or released for full production. Testing and final process, including without limitation quality assurance, reliability performance testing, and/or process qualification, may not yet be complete, and this item is subject to further changes or possible discontinuation. If available for ordering, purchases will be subject to an additional waiver at checkout, and are intended for early internal evaluation purposes only. These items are sold without warranties of any kind.

⁽³⁾ **RoHS values:** Yes, No, RoHS Exempt. See the [TI RoHS Statement](#) for additional information and value definition.

⁽⁴⁾ **Lead finish/Ball material:** Parts may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead finish/Ball material values may wrap to two lines if the finish value exceeds the maximum column width.

⁽⁵⁾ **MSL rating/Peak reflow:** The moisture sensitivity level ratings and peak solder (reflow) temperatures. In the event that a part has multiple moisture sensitivity ratings, only the lowest level per JEDEC standards is shown. Refer to the shipping label for the actual reflow temperature that will be used to mount the part to the printed circuit board.

⁽⁶⁾ **Part marking:** There may be an additional marking, which relates to the logo, the lot trace code information, or the environmental category of the part.

Multiple part markings will be inside parentheses. Only one part marking contained in parentheses and separated by a "~" will appear on a part. If a line is indented then it is a continuation of the previous line and the two combined represent the entire part marking for that device.

Important Information and Disclaimer: The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.

TAPE AND REEL INFORMATION

QUADRANT ASSIGNMENTS FOR PIN 1 ORIENTATION IN TAPE


*All dimensions are nominal

| Device | Package Type | Package Drawing | Pins | SPQ | Reel Diameter (mm) | Reel Width W1 (mm) | A0 (mm) | B0 (mm) | K0 (mm) | P1 (mm) | W (mm) | Pin1 Quadrant |
|--------------|--------------|-----------------|------|------|--------------------|--------------------|---------|---------|---------|---------|--------|---------------|
| INA141U/2K5 | SOIC | D | 8 | 2500 | 330.0 | 12.4 | 6.4 | 5.2 | 2.1 | 8.0 | 12.0 | Q1 |
| INA141U/2K5 | SOIC | D | 8 | 2500 | 330.0 | 12.4 | 6.4 | 5.2 | 2.1 | 8.0 | 12.0 | Q1 |
| INA141UA/2K5 | SOIC | D | 8 | 2500 | 330.0 | 12.4 | 6.4 | 5.2 | 2.1 | 8.0 | 12.0 | Q1 |

TAPE AND REEL BOX DIMENSIONS


*All dimensions are nominal

| Device | Package Type | Package Drawing | Pins | SPQ | Length (mm) | Width (mm) | Height (mm) |
|--------------|--------------|-----------------|------|------|-------------|------------|-------------|
| INA141U/2K5 | SOIC | D | 8 | 2500 | 367.0 | 367.0 | 35.0 |
| INA141U/2K5 | SOIC | D | 8 | 2500 | 353.0 | 353.0 | 32.0 |
| INA141UA/2K5 | SOIC | D | 8 | 2500 | 356.0 | 356.0 | 35.0 |

TUBE


*All dimensions are nominal

| Device | Package Name | Package Type | Pins | SPQ | L (mm) | W (mm) | T (μm) | B (mm) |
|------------|--------------|--------------|------|-----|--------|--------|--------|--------|
| INA141U | D | SOIC | 8 | 75 | 506.6 | 8 | 3940 | 4.32 |
| INA141U.Z | D | SOIC | 8 | 75 | 506.6 | 8 | 3940 | 4.32 |
| INA141UA | D | SOIC | 8 | 75 | 506.6 | 8 | 3940 | 4.32 |
| INA141UA.Z | D | SOIC | 8 | 75 | 506.6 | 8 | 3940 | 4.32 |

重要なお知らせと免責事項

テキサス・インスツルメンツは、技術データと信頼性データ(データシートを含みます)、設計リソース(リファレンス デザインを含みます)、アプリケーションや設計に関する各種アドバイス、Web ツール、安全性情報、その他のリソースを、欠陥が存在する可能性のある「現状のまま」提供しており、商品性および特定目的に対する適合性の黙示保証、第三者の知的財産権の非侵害保証を含むいかなる保証も、明示的または黙示的にかかわらず拒否します。

これらのリソースは、テキサス・インスツルメンツ製品を使用する設計の経験を積んだ開発者への提供を意図したものです。(1) お客様のアプリケーションに適したテキサス・インスツルメンツ製品の選定、(2) お客様のアプリケーションの設計、検証、試験、(3) お客様のアプリケーションに該当する各種規格や、その他のあらゆる安全性、セキュリティ、規制、または他の要件への確実な適合に関する責任を、お客様のみが単独で負うものとします。

上記の各種リソースは、予告なく変更される可能性があります。これらのリソースは、リソースで説明されているテキサス・インスツルメンツ製品を使用するアプリケーションの開発の目的でのみ、テキサス・インスツルメンツはその使用をお客様に許諾します。これらのリソースに関して、他の目的で複製することや掲載することは禁止されています。テキサス・インスツルメンツや第三者の知的財産権のライセンスが付与されている訳ではありません。お客様は、これらのリソースを自身で使用した結果発生するあらゆる申し立て、損害、費用、損失、責任について、テキサス・インスツルメンツおよびその代理人を完全に補償するものとし、テキサス・インスツルメンツは一切の責任を拒否します。

テキサス・インスツルメンツの製品は、[テキサス・インスツルメンツの販売条件](#)、または [ti.com](https://www.ti.com) やかかるテキサス・インスツルメンツ製品の関連資料などのいずれかを通じて提供する適用可能な条項の下で提供されています。テキサス・インスツルメンツがこれらのリソースを提供することは、適用されるテキサス・インスツルメンツの保証または他の保証の放棄の拡大や変更を意味するものではありません。

お客様がいかなる追加条項または代替条項を提案した場合でも、テキサス・インスツルメンツはそれらに異議を唱え、拒否します。

郵送先住所：Texas Instruments, Post Office Box 655303, Dallas, Texas 75265
Copyright © 2025, Texas Instruments Incorporated