

# SNx4HC541 3 ステート出力、オクタール・バッファ / ライン・ドライバ

## 1 特長

- 広い動作電圧範囲: 2V~6V
- バス・ラインを直接、または最大 15 の LSTTL 負荷を駆動する大電流 3 ステート出力
- 低い消費電力、最大  $I_{CC}$ : 80 $\mu$ A
- $t_{pd} = 10$ ns (標準値)
- 5V で  $\pm 6$ mA の出力駆動能力
- 低い入力電流: 最大値 1 $\mu$ A
- データ・フロースルーのピン配置 (すべての入力は出力の反対側)

## 2 アプリケーション

- LED
- サーバー
- PC およびノートパソコン
- ウェアラブルな健康機器
- 電子 POS

## 3 概要


これらのオクタール・バッファおよびライン・ドライバは、SNx4HC541 デバイスの性能を備え、入力と出力がパッケージを挟んで反対側に位置するようにピンを配置しています。この配置のおかげで、プリント基板のレイアウトが非常に簡単です。

3 ステート出力は、2 入力 NOR ゲートによって制御されます。いずれかの出力イネーブル ( $\overline{OE1}$  または  $\overline{OE2}$ ) 入力が High の場合、8 つの出力はすべて高インピーダンス状態になります。SNx4HC541 デバイスは、出力側に真のデータを提供します。

### 製品情報

| 部品番号        | パッケージ <sup>(1)</sup> | 本体サイズ (公称)       |
|-------------|----------------------|------------------|
| SN74HC541DW | SOIC (20)            | 12.80mm × 7.50mm |
| SN74HC541DB | SSOP (20)            | 7.20mm × 5.30mm  |
| SN74HC541N  | PDIP (20)            | 24.33mm × 6.35mm |
| SN74HC541NS | SO (20)              | 12.60mm × 5.30mm |
| SN74HC541PW | TSSOP (20)           | 6.50mm × 4.40mm  |
| SN54HC541J  | CDIP (20)            | 24.20mm × 6.92mm |
| SN54HC541FK | LCCC (20)            | 8.89mm × 8.89mm  |

(1) 利用可能なパッケージについては、このデータシートの末尾にある注文情報を参照してください。



To Seven Other Channels

Copyright © 2016, Texas Instruments Incorporated

### 機能ブロック図



## Table of Contents

|                                                                                             |          |                                                                      |           |
|---------------------------------------------------------------------------------------------|----------|----------------------------------------------------------------------|-----------|
| <b>1 特長</b> .....                                                                           | <b>1</b> | 6.14 Operating Characteristics.....                                  | <b>8</b>  |
| <b>2 アプリケーション</b> .....                                                                     | <b>1</b> | 6.15 Typical Characteristics.....                                    | <b>9</b>  |
| <b>3 概要</b> .....                                                                           | <b>1</b> | <b>7 Parameter Measurement Information</b> .....                     | <b>10</b> |
| <b>4 Revision History</b> .....                                                             | <b>2</b> | <b>8 Detailed Description</b> .....                                  | <b>11</b> |
| <b>5 Pin Configuration and Functions</b> .....                                              | <b>3</b> | 8.1 Overview.....                                                    | <b>11</b> |
| Pin Functions.....                                                                          | <b>3</b> | 8.2 Functional Block Diagram.....                                    | <b>11</b> |
| <b>6 Specifications</b> .....                                                               | <b>4</b> | 8.3 Feature Description.....                                         | <b>11</b> |
| 6.1 Absolute Maximum Ratings.....                                                           | <b>4</b> | 8.4 Device Functional Modes.....                                     | <b>11</b> |
| 6.2 ESD Ratings.....                                                                        | <b>4</b> | <b>9 Application and Implementation</b> .....                        | <b>12</b> |
| 6.3 Recommended Operating Conditions.....                                                   | <b>4</b> | 9.1 Application Information.....                                     | <b>12</b> |
| 6.4 Thermal Information.....                                                                | <b>5</b> | 9.2 Typical Application.....                                         | <b>12</b> |
| 6.5 Electrical Characteristics, $T_A = 25^\circ\text{C}$ .....                              | <b>5</b> | <b>10 Power Supply Recommendations</b> .....                         | <b>14</b> |
| 6.6 Electrical Characteristics, SN54HC541.....                                              | <b>5</b> | <b>11 Layout</b> .....                                               | <b>14</b> |
| 6.7 Electrical Characteristics, SN74HC541.....                                              | <b>6</b> | 11.1 Layout Guidelines.....                                          | <b>14</b> |
| 6.8 Switching Characteristics, $C_L = 50\text{ pF}$ , $T_A = 25^\circ\text{C}$ .....        | <b>6</b> | 11.2 Layout Example.....                                             | <b>14</b> |
| 6.9 Switching Characteristics, $C_L = 50\text{ pF}$ ,<br>SN54HC541.....                     | <b>7</b> | <b>12 Device and Documentation Support</b> .....                     | <b>15</b> |
| 6.10 Switching Characteristics, $C_L = 50\text{ pF}$ ,<br>SN74HC541.....                    | <b>7</b> | 12.1 Related Links.....                                              | <b>15</b> |
| 6.11 Switching Characteristics, $C_L = 150\text{ pF}$ , $T_A =$<br>$25^\circ\text{C}$ ..... | <b>7</b> | 12.2 Receiving Notification of Documentation Updates.....            | <b>15</b> |
| 6.12 Switching Characteristics, $C_L = 150\text{ pF}$ ,<br>SN54HC541.....                   | <b>8</b> | 12.3 サポート・リソース.....                                                  | <b>15</b> |
| 6.13 Switching Characteristics, $C_L = 150\text{ pF}$ ,<br>SN74HC541.....                   | <b>8</b> | 12.4 Trademarks.....                                                 | <b>15</b> |
|                                                                                             |          | 12.5 Electrostatic Discharge Caution.....                            | <b>15</b> |
|                                                                                             |          | 12.6 Glossary.....                                                   | <b>15</b> |
|                                                                                             |          | <b>13 Mechanical, Packaging, and Orderable<br/>Information</b> ..... | <b>15</b> |


## 4 Revision History

資料番号末尾の英字は改訂を表しています。その改訂履歴は英語版に準じています。


| <b>Changes from Revision D (September 2016) to Revision E (May 2022)</b>                                                                                                                       | <b>Page</b> |
|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-------------|
| • Updated ESD ratings table to include modern TI terminology.....                                                                                                                              | <b>4</b>    |
| • Junction-to-ambient thermal resistance values increased. DB was 90.2 is now 122.7, DW was 77.5 is now 109.1, N was 45.2 is now 84.6, NS was 72.8 is now 113.4, PW was 98.3 is now 131.8..... | <b>5</b>    |

| <b>Changes from Revision C (August 2003) to Revision D (September 2016)</b>                                                                                                         | <b>Page</b> |
|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-------------|
| • 「アプリケーション」セクション、「熱に関する情報」表、「ESD 定格」表、「機能説明」セクション、「デバイスの機能モード」セクション、「アプリケーションと実装」セクション、「電源に関する推奨事項」セクション、「レイアウト」セクション、「デバイスおよびドキュメントのサポート」セクション、「メカニカル、パッケージ、および注文情報」セクションを追加..... | <b>1</b>    |
| • 「注文情報」表を削除 (このデータシートの末尾にある「メカニカル、パッケージ、および注文情報」を参照).....                                                                                                                          | <b>1</b>    |
| • Changed $R_{\theta JA}$ for DB package from $70^\circ\text{C/W}$ : to $90.2^\circ\text{C/W}$ .....                                                                                | <b>5</b>    |
| • Changed $R_{\theta JA}$ for DW package from $58^\circ\text{C/W}$ : to $77.5^\circ\text{C/W}$ .....                                                                                | <b>5</b>    |
| • Changed $R_{\theta JA}$ for N package from $69^\circ\text{C/W}$ : to $45.2^\circ\text{C/W}$ .....                                                                                 | <b>5</b>    |
| • Changed $R_{\theta JA}$ for NS package from $60^\circ\text{C/W}$ : to $72.8^\circ\text{C/W}$ .....                                                                                | <b>5</b>    |
| • Changed $R_{\theta JA}$ for PW package from $83^\circ\text{C/W}$ : to $98.3^\circ\text{C/W}$ .....                                                                                | <b>5</b>    |

## 5 Pin Configuration and Functions



**DB, DW, N, NS, J, or PW Package**  
**20-Pin SSOP, SOIC, PDIP, SO, CDIP, or TSSOP**  
**Top View**



**FK Package**  
**20-Pin LCCC**  
**Top View**

## Pin Functions

| PIN |      | I/O <sup>(1)</sup> | DESCRIPTION                                                      |
|-----|------|--------------------|------------------------------------------------------------------|
| NO. | NAME |                    |                                                                  |
| 1   | OE1  | I                  | Output enable (active low) Both OE must be low to enable outputs |
| 2   | A1   | I                  | Channel 1 input                                                  |
| 3   | A2   | I                  | Channel 2 input                                                  |
| 4   | A3   | I                  | Channel 3 input                                                  |
| 5   | A4   | I                  | Channel 4 input                                                  |
| 6   | A5   | I                  | Channel 5 input                                                  |
| 7   | A6   | I                  | Channel 6 input                                                  |
| 8   | A7   | I                  | Channel 7 input                                                  |
| 9   | A8   | I                  | Channel 8 input                                                  |
| 10  | GND  | —                  | Ground                                                           |
| 11  | Y8   | O                  | Channel 8 output                                                 |
| 12  | Y7   | O                  | Channel 7 output                                                 |
| 13  | Y6   | O                  | Channel 6 output                                                 |
| 14  | Y5   | O                  | Channel 5 output                                                 |
| 15  | Y4   | O                  | Channel 4 output                                                 |
| 16  | Y3   | O                  | Channel 3 output                                                 |
| 17  | Y2   | O                  | Channel 2 output                                                 |
| 18  | Y1   | O                  | Channel 1 output                                                 |
| 19  | OE2  | I                  | Output enable (active low) both OE must be low to enable outputs |
| 20  | Vcc  | —                  | Power pin                                                        |

(1) Signal Types: I = Input, O = Output, I/O = Input or Output.

## 6 Specifications

### 6.1 Absolute Maximum Ratings

over operating free-air temperature range (unless otherwise noted)<sup>(1)</sup>

|                  |                                                   | MIN                                                    | MAX | UNIT   |
|------------------|---------------------------------------------------|--------------------------------------------------------|-----|--------|
| V <sub>CC</sub>  | Supply voltage                                    | −0.5                                                   | 7   | V      |
| I <sub>IK</sub>  | Input clamp current <sup>(2)</sup>                | V <sub>I</sub> < 0 or V <sub>I</sub> > V <sub>CC</sub> |     | ±20 mA |
| I <sub>OK</sub>  | Output clamp current <sup>(2)</sup>               | V <sub>O</sub> < 0 or V <sub>O</sub> > V <sub>CC</sub> |     | ±20 mA |
| I <sub>O</sub>   | Continuous output current                         | V <sub>O</sub> = 0 to V <sub>CC</sub>                  |     | ±35 mA |
|                  | Continuous current through V <sub>CC</sub> or GND |                                                        |     | ±70 mA |
| T <sub>stg</sub> | Storage temperature                               | −65                                                    | 150 | °C     |

- (1) Stresses beyond those listed under *Absolute Maximum Ratings* may cause permanent damage to the device. These are stress ratings only, which do not imply functional operation of the device at these or any other conditions beyond those indicated under *Recommended Operating Conditions*. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability.
- (2) The input and output voltage ratings may be exceeded if the input and output current ratings are observed.

### 6.2 ESD Ratings

|                    |                         | VALUE                                                                 | UNIT  |
|--------------------|-------------------------|-----------------------------------------------------------------------|-------|
| V <sub>(ESD)</sub> | Electrostatic discharge | Human-body model (HBM), per ANSI/ESDA/JEDEC JS-001 <sup>(1)</sup>     | ±2000 |
|                    |                         | Charged device model (CDM), per ANSI/ESDA/JEDEC JS-002 <sup>(2)</sup> | ±1000 |

- (1) JEDEC document JEP155 states that 500-V HBM allows safe manufacturing with a standard ESD control process.
- (2) JEDEC document JEP157 states that 250-V CDM allows safe manufacturing with a standard ESD control process.

### 6.3 Recommended Operating Conditions

See note<sup>(1)</sup>

|                 |                                     | MIN                     | NOM  | MAX             | UNIT |
|-----------------|-------------------------------------|-------------------------|------|-----------------|------|
| V <sub>CC</sub> | Supply voltage                      | 2                       | 5    | 6               | V    |
| V <sub>IH</sub> | High-level input voltage            | V <sub>CC</sub> = 2 V   | 1.5  |                 | V    |
|                 |                                     | V <sub>CC</sub> = 4.5 V | 3.15 |                 |      |
|                 |                                     | V <sub>CC</sub> = 6 V   | 4.2  |                 |      |
| V <sub>IL</sub> | Low-level input voltage             | V <sub>CC</sub> = 2 V   |      | 0.5             | V    |
|                 |                                     | V <sub>CC</sub> = 4.5 V |      | 1.35            |      |
|                 |                                     | V <sub>CC</sub> = 6 V   |      | 1.8             |      |
| V <sub>I</sub>  | Input voltage                       | 0                       |      | V <sub>CC</sub> | V    |
| V <sub>O</sub>  | Output voltage                      | 0                       |      | V <sub>CC</sub> | V    |
| Δt/Δv           | Input transition rise and fall time | V <sub>CC</sub> = 2 V   |      | 1000            | ns   |
|                 |                                     | V <sub>CC</sub> = 4.5 V |      | 500             |      |
|                 |                                     | V <sub>CC</sub> = 6 V   |      | 400             |      |
| T <sub>A</sub>  | Operating free-air temperature      | SN54HC541               | −55  | 125             | °C   |
|                 |                                     | SN74HC541               | −40  | 85              |      |

- (1) All unused inputs of the device must be held at V<sub>CC</sub> or GND to ensure proper device operation. See [Implications of Slow or Floating CMOS Inputs](#), SCBA004.

## 6.4 Thermal Information

| THERMAL METRIC        |                                                       | SN74HC541 |           |          |         |            | UNIT |
|-----------------------|-------------------------------------------------------|-----------|-----------|----------|---------|------------|------|
|                       |                                                       | DB (SSOP) | DW (SOIC) | N (PDIP) | NS (SO) | PW (TSSOP) |      |
|                       |                                                       | 20 PINS   | 20 PINS   | 20 PINS  | 20 PINS | 20 PINS    |      |
| $R_{\theta JA}$       | Junction-to-ambient thermal resistance <sup>(1)</sup> | 122.7     | 109.1     | 84.6     | 113.4   | 131.8      | °C/W |
| $R_{\theta JC (top)}$ | Junction-to-case (top) thermal resistance             | 81.6      | 76        | 72.5     | 78.6    | 72.2       | °C/W |
| $R_{\theta JB}$       | Junction-to-board thermal resistance                  | 77.5      | 77.6      | 65.3     | 78.4    | 82.8       | °C/W |
| $\Psi_{JT}$           | Junction-to-top characterization parameter            | 46.1      | 51.5      | 55.3     | 47.1    | 21.5       | °C/W |
| $\Psi_{JB}$           | Junction-to-board characterization parameter          | 77.1      | 77.1      | 65.2     | 78.1    | 82.4       | °C/W |
| $R_{\theta JC (bot)}$ | Junction-to-case (bottom) thermal resistance          | N/A       | N/A       | N/A      | N/A     | N/A        | °C/W |

(1) For more information about traditional and new thermal metrics, see the [Semiconductor and IC Package Thermal Metrics](#) application report.

## 6.5 Electrical Characteristics, $T_A = 25^\circ\text{C}$

over operating free-air temperature range (unless otherwise noted)

| PARAMETER       | TEST CONDITIONS                                           |                           | V <sub>CC</sub> | MIN   | TYP   | MAX  | UNIT |
|-----------------|-----------------------------------------------------------|---------------------------|-----------------|-------|-------|------|------|
| V <sub>OH</sub> | V <sub>I</sub> = V <sub>IH</sub> or V <sub>IL</sub>       | I <sub>OH</sub> = −20 μA  | 2 V             | 1.9   | 1.998 |      | V    |
|                 |                                                           |                           | 4.5 V           | 4.4   | 4.499 |      |      |
|                 |                                                           |                           | 6 V             | 5.9   | 5.999 |      |      |
|                 |                                                           | I <sub>OH</sub> = −6 mA   | 4.5 V           | 3.98  | 4.3   |      |      |
|                 |                                                           | I <sub>OH</sub> = −7.8 mA | 6 V             | 5.48  | 5.8   |      |      |
| V <sub>OL</sub> | V <sub>I</sub> = V <sub>IH</sub> or V <sub>IL</sub>       | I <sub>OL</sub> = 20 μA   | 2 V             | 0.002 |       | 0.1  | V    |
|                 |                                                           |                           | 4.5 V           | 0.001 |       | 0.1  |      |
|                 |                                                           |                           | 6 V             | 0.001 |       | 0.1  |      |
|                 |                                                           | I <sub>OL</sub> = 6 mA    | 4.5 V           | 0.17  |       | 0.26 |      |
|                 |                                                           | I <sub>OL</sub> = 7.8 mA  | 6 V             | 0.15  |       | 0.26 |      |
| I <sub>I</sub>  | V <sub>I</sub> = V <sub>CC</sub> or 0                     |                           | 6 V             | ±0.1  |       | ±100 | nA   |
| I <sub>OZ</sub> | V <sub>O</sub> = V <sub>CC</sub> or 0                     |                           | 6 V             | ±0.01 |       | ±0.5 | μA   |
| I <sub>CC</sub> | V <sub>I</sub> = V <sub>CC</sub> or 0, I <sub>O</sub> = 0 |                           | 6 V             |       |       | 8    | μA   |
| C <sub>i</sub>  |                                                           |                           | 2 V to 6 V      |       | 3     | 10   | pF   |

## 6.6 Electrical Characteristics, SN54HC541

over operating free-air temperature range (unless otherwise noted)

| PARAMETER | TEST CONDITIONS                   |                            | $V_{CC}$ | MIN | TYP | MAX | UNIT |
|-----------|-----------------------------------|----------------------------|----------|-----|-----|-----|------|
| $V_{OH}$  | $V_I = V_{IH} \text{ or } V_{IL}$ | $I_{OH} = -20 \mu\text{A}$ | 2 V      | 1.9 |     |     | V    |
|           |                                   |                            | 4.5 V    | 4.4 |     |     |      |
|           |                                   |                            | 6 V      | 5.9 |     |     |      |
|           |                                   | $I_{OH} = -6 \text{ mA}$   | 4.5 V    | 3.7 |     |     |      |
|           |                                   |                            | 6 V      | 5.2 |     |     |      |

over operating free-air temperature range (unless otherwise noted)

| PARAMETER       | TEST CONDITIONS                                           | V <sub>CC</sub>          | MIN   | TYP | MAX   | UNIT |
|-----------------|-----------------------------------------------------------|--------------------------|-------|-----|-------|------|
| V <sub>OL</sub> | V <sub>I</sub> = V <sub>IH</sub> or V <sub>IL</sub>       | I <sub>OL</sub> = 20 µA  | 2 V   |     | 0.1   | V    |
|                 |                                                           |                          | 4.5 V |     | 0.1   |      |
|                 |                                                           |                          | 6 V   |     | 0.1   |      |
|                 |                                                           | I <sub>OL</sub> = 6 mA   | 4.5 V |     | 0.4   |      |
|                 |                                                           | I <sub>OL</sub> = 7.8 mA | 6 V   |     | 0.4   |      |
| I <sub>I</sub>  | V <sub>I</sub> = V <sub>CC</sub> or 0                     | 6 V                      |       |     | ±1000 | nA   |
| I <sub>OZ</sub> | V <sub>O</sub> = V <sub>CC</sub> or 0                     | 6 V                      |       |     | ±10   | µA   |
| I <sub>CC</sub> | V <sub>I</sub> = V <sub>CC</sub> or 0, I <sub>O</sub> = 0 | 6 V                      |       |     | 160   | µA   |
| C <sub>i</sub>  |                                                           | 2 V to 6 V               |       |     | 10    | pF   |

## 6.7 Electrical Characteristics, SN74HC541

over operating free-air temperature range (unless otherwise noted)

| PARAMETER       | TEST CONDITIONS                                           | V <sub>CC</sub>           | MIN   | TYP  | MAX   | UNIT |
|-----------------|-----------------------------------------------------------|---------------------------|-------|------|-------|------|
| V <sub>OH</sub> | V <sub>I</sub> = V <sub>IH</sub> or V <sub>IL</sub>       | I <sub>OH</sub> = -20 µA  | 2 V   | 1.9  |       | V    |
|                 |                                                           |                           | 4.5 V | 4.4  |       |      |
|                 |                                                           |                           | 6 V   | 5.9  |       |      |
|                 |                                                           | I <sub>OH</sub> = -6 mA   | 4.5 V | 3.84 |       |      |
|                 |                                                           | I <sub>OH</sub> = -7.8 mA | 6 V   | 5.34 |       |      |
| V <sub>OL</sub> | V <sub>I</sub> = V <sub>IH</sub> or V <sub>IL</sub>       | I <sub>OL</sub> = 20 µA   | 2 V   |      | 0.1   | V    |
|                 |                                                           |                           | 4.5 V |      | 0.1   |      |
|                 |                                                           |                           | 6 V   |      | 0.1   |      |
|                 |                                                           | I <sub>OL</sub> = 6 mA    | 4.5 V |      | 0.33  |      |
|                 |                                                           | I <sub>OL</sub> = 7.8 mA  | 6 V   |      | 0.33  |      |
| I <sub>I</sub>  | V <sub>I</sub> = V <sub>CC</sub> or 0                     | 6 V                       |       |      | ±1000 | nA   |
| I <sub>OZ</sub> | V <sub>O</sub> = V <sub>CC</sub> or 0                     | 6 V                       |       |      | ±5    | µA   |
| I <sub>CC</sub> | V <sub>I</sub> = V <sub>CC</sub> or 0, I <sub>O</sub> = 0 | 6 V                       |       |      | 80    | µA   |
| C <sub>i</sub>  |                                                           | 2 V to 6 V                |       |      | 10    | pF   |

## 6.8 Switching Characteristics, C<sub>L</sub> = 50 pF, T<sub>A</sub> = 25°C

over recommended operating free-air temperature range, C<sub>L</sub> = 50 pF (unless otherwise noted) (see [Figure 7-1](#))

| PARAMETER        | FROM (INPUT) | TO (OUTPUT) | V <sub>CC</sub> | MIN | TYP | MAX | UNIT |
|------------------|--------------|-------------|-----------------|-----|-----|-----|------|
| t <sub>pd</sub>  | A            | Y           | 2 V             |     | 40  | 115 | ns   |
|                  |              |             | 4.5 V           |     | 12  | 23  |      |
|                  |              |             | 6 V             |     | 10  | 20  |      |
| t <sub>en</sub>  | OE           | Y           | 2 V             |     | 80  | 150 | ns   |
|                  |              |             | 4.5 V           |     | 17  | 30  |      |
|                  |              |             | 6 V             |     | 15  | 26  |      |
| t <sub>dis</sub> | OE           | Y           | 2 V             |     | 40  | 150 | ns   |
|                  |              |             | 4.5 V           |     | 18  | 30  |      |
|                  |              |             | 6 V             |     | 17  | 26  |      |
| t <sub>t</sub>   |              | Y           | 2 V             |     | 28  | 60  | ns   |
|                  |              |             | 4.5 V           |     | 8   | 12  |      |
|                  |              |             | 6 V             |     | 6   | 10  |      |

## 6.9 Switching Characteristics, $C_L = 50 \text{ pF}$ , SN54HC541

over recommended operating free-air temperature range,  $C_L = 50 \text{ pF}$  (unless otherwise noted) (see [Figure 7-1](#))

| PARAMETER | FROM<br>(INPUT) | TO<br>(OUTPUT) | $V_{CC}$ | MIN | TYP | MAX | UNIT |
|-----------|-----------------|----------------|----------|-----|-----|-----|------|
| $t_{pd}$  | A               | Y              | 2 V      |     |     | 171 | ns   |
|           |                 |                | 4.5 V    |     |     | 34  |      |
|           |                 |                | 6 V      |     |     | 29  |      |
| $t_{en}$  | $\overline{OE}$ | Y              | 2 V      |     |     | 224 | ns   |
|           |                 |                | 4.5 V    |     |     | 45  |      |
|           |                 |                | 6 V      |     |     | 38  |      |
| $t_{dis}$ | $\overline{OE}$ | Y              | 2 V      |     |     | 224 | ns   |
|           |                 |                | 4.5 V    |     |     | 45  |      |
|           |                 |                | 6 V      |     |     | 38  |      |
| $t_t$     |                 | Y              | 2 V      |     |     | 90  | ns   |
|           |                 |                | 4.5 V    |     |     | 18  |      |
|           |                 |                | 6 V      |     |     | 15  |      |

## 6.10 Switching Characteristics, $C_L = 50 \text{ pF}$ , SN74HC541

over recommended operating free-air temperature range,  $C_L = 50 \text{ pF}$  (unless otherwise noted) (see [Figure 7-1](#))

| PARAMETER | FROM<br>(INPUT) | TO<br>(OUTPUT) | $V_{CC}$ | MIN | TYP | MAX | UNIT |
|-----------|-----------------|----------------|----------|-----|-----|-----|------|
| $t_{pd}$  | A               | Y              | 2 V      |     |     | 144 | ns   |
|           |                 |                | 4.5 V    |     |     | 29  |      |
|           |                 |                | 6 V      |     |     | 25  |      |
| $t_{en}$  | $\overline{OE}$ | Y              | 2 V      |     |     | 188 | ns   |
|           |                 |                | 4.5 V    |     |     | 38  |      |
|           |                 |                | 6 V      |     |     | 32  |      |
| $t_{dis}$ | $\overline{OE}$ | Y              | 2 V      |     |     | 188 | ns   |
|           |                 |                | 4.5 V    |     |     | 38  |      |
|           |                 |                | 6 V      |     |     | 32  |      |
| $t_t$     |                 | Y              | 2 V      |     |     | 75  | ns   |
|           |                 |                | 4.5 V    |     |     | 15  |      |
|           |                 |                | 6 V      |     |     | 13  |      |

## 6.11 Switching Characteristics, $C_L = 150 \text{ pF}$ , $T_A = 25^\circ\text{C}$

over recommended operating free-air temperature range,  $C_L = 150 \text{ pF}$  (unless otherwise noted) (see [Figure 7-1](#))

| PARAMETER | FROM<br>(INPUT) | TO<br>(OUTPUT) | $V_{CC}$ | MIN | TYP | MAX | UNIT |
|-----------|-----------------|----------------|----------|-----|-----|-----|------|
| $t_{pd}$  | A               | Y              | 2 V      |     | 65  | 165 | ns   |
|           |                 |                | 4.5 V    |     | 16  | 33  |      |
|           |                 |                | 6 V      |     | 14  | 28  |      |
| $t_{en}$  | $\overline{OE}$ | Y              | 2 V      |     | 100 | 200 | ns   |
|           |                 |                | 4.5 V    |     | 20  | 40  |      |
|           |                 |                | 6 V      |     | 17  | 34  |      |
| $t_t$     |                 | Y              | 2 V      |     | 45  | 210 | ns   |
|           |                 |                | 4.5 V    |     | 17  | 42  |      |
|           |                 |                | 6 V      |     | 13  | 36  |      |

## 6.12 Switching Characteristics, $C_L = 150$ pF, SN54HC541

over recommended operating free-air temperature range,  $C_L = 150$  pF (unless otherwise noted) (see [Figure 7-1](#))

| PARAMETER | FROM<br>(INPUT) | TO<br>(OUTPUT) | $V_{CC}$ | MIN | TYP | MAX | UNIT |
|-----------|-----------------|----------------|----------|-----|-----|-----|------|
| $t_{pd}$  | A               | Y              | 2 V      |     |     | 246 | ns   |
|           |                 |                | 4.5 V    |     |     | 49  |      |
|           |                 |                | 6 V      |     |     | 42  |      |
| $t_{en}$  | $\overline{OE}$ | Y              | 2 V      |     |     | 298 | ns   |
|           |                 |                | 4.5 V    |     |     | 60  |      |
|           |                 |                | 6 V      |     |     | 51  |      |
| $t_t$     |                 | Y              | 2 V      |     |     | 315 | ns   |
|           |                 |                | 4.5 V    |     |     | 63  |      |
|           |                 |                | 6 V      |     |     | 53  |      |

## 6.13 Switching Characteristics, $C_L = 150$ pF, SN74HC541

over recommended operating free-air temperature range,  $C_L = 150$  pF (unless otherwise noted) (see [Figure 7-1](#))

| PARAMETER | FROM<br>(INPUT) | TO<br>(OUTPUT) | $V_{CC}$ | MIN | TYP | MAX | UNIT |
|-----------|-----------------|----------------|----------|-----|-----|-----|------|
| $t_{pd}$  | A               | Y              | 2 V      |     |     | 206 | ns   |
|           |                 |                | 4.5 V    |     |     | 41  |      |
|           |                 |                | 6 V      |     |     | 35  |      |
| $t_{en}$  | $\overline{OE}$ | Y              | 2 V      |     |     | 250 | ns   |
|           |                 |                | 4.5 V    |     |     | 50  |      |
|           |                 |                | 6 V      |     |     | 43  |      |
| $t_t$     |                 | Y              | 2 V      |     |     | 265 | ns   |
|           |                 |                | 4.5 V    |     |     | 53  |      |
|           |                 |                | 6 V      |     |     | 45  |      |


## 6.14 Operating Characteristics

$T_A = 25^\circ\text{C}$


| PARAMETER                                                | TEST CONDITIONS | TYP | UNIT |
|----------------------------------------------------------|-----------------|-----|------|
| $C_{pd}$ Power dissipation capacitance per buffer/driver | No load         | 35  | pF   |



## 6.15 Typical Characteristics




6-1. Typical Delay vs.  $V_{CC}$  for  $C_L = 50$  pF






6-2. Typical Delay vs.  $V_{CC}$  for  $C_L = 150$  pF

## 7 Parameter Measurement Information



| PARAMETER         | $R_L$        | $C_L$           | S1     | S2     |
|-------------------|--------------|-----------------|--------|--------|
| $t_{en}$          | 1 k $\Omega$ | 50 pF or 150 pF | Open   | Closed |
|                   |              |                 | Closed | Open   |
| $t_{dis}$         | 1 k $\Omega$ | 50 pF           | Open   | Closed |
|                   |              |                 | Closed | Open   |
| $t_{pd}$ or $t_t$ | —            | 50 pF or 150 pF | Open   | Open   |



- A.  $C_L$  includes probe and test-fixture capacitance.
- B. Waveform 1 is for an output with internal conditions such that the output is low except when disabled by the output control. Waveform 2 is for an output with internal conditions such that the output is high except when disabled by the output control.
- C. Phase relationships between waveforms were chosen arbitrarily. All input pulses are supplied by generators having the following characteristics:  $PRR \leq 1$  MHz,  $Z_O = 50 \Omega$ ,  $t_r = 6$  ns,  $t_f = 6$  ns.
- D. The outputs are measured one at a time with one input transition per measurement.
- E.  $t_{PLZ}$  and  $t_{PHZ}$  are the same as  $t_{dis}$ .
- F.  $t_{PZL}$  and  $t_{PZH}$  are the same as  $t_{en}$ .
- G.  $t_{PLH}$  and  $t_{PHL}$  are the same as  $t_{pd}$ .


7-1. Load Circuit and Voltage Waveforms

## 8 Detailed Description

### 8.1 Overview

The SN74HC541 device has 8 inputs and outputs where data from the A inputs go to the Y outputs. The output enables of the device control whether the information from the A inputs go to the Y outputs. These enable pins cause the device to go into high Z if either  $\overline{OE1}$  or  $\overline{OE2}$  are high. The  $\overline{OE}$ s should be tied to  $V_{CC}$  through a pull up resistor to ensure the high impedance state during power up or power down; the minimum value of the resistor is determined by the current sinking capability of the driver.

### 8.2 Functional Block Diagram



Copyright © 2016, Texas Instruments Incorporated

✎ 8-1. Logic Diagram (Positive Logic)

### 8.3 Feature Description

The SNx4HC541 has a wide operating voltage range of 2 V to 6 V. The device has multiple enable pins, and the device pinout enables simple board layout with outputs across from inputs.

### 8.4 Device Functional Modes

表 8-1 lists the functional modes of the SNx4HC541.

表 8-1. Function Table (Each Buffer/Driver)

| INPUTS |     |   | OUTPUT<br>Y |
|--------|-----|---|-------------|
| OE1    | OE2 | A |             |
| L      | L   | L | L           |
| L      | L   | H | H           |
| H      | X   | X | Hi-Z        |
| X      | H   | X | Hi-Z        |

## 9 Application and Implementation


### Note

以下のアプリケーション情報は、TI の製品仕様に含まれるものではなく、TI ではその正確性または完全性を保証いたしません。個々の目的に対する製品の適合性については、お客様の責任で判断していただくことになります。お客様は自身の設計実装を検証しテストすることで、システムの機能を確認する必要があります。

### 9.1 Application Information

SN74HC541 is a wide range CMOS device that can be used over large voltage ranges. The device can be used anywhere from 2 to 6 Volts. The device can drive up to 6 mA of current at 5 Volts. This makes it perfect for driving bus lines directly or up to 15 LSTTL Loads. It can be used to drive anything from micro controllers and system logic devices to LEDs.

### 9.2 Typical Application



Copyright © 2016, Texas Instruments Incorporated

 9-1. Typical Application Diagram

#### 9.2.1 Design Requirements

This device uses CMOS technology and has a wide voltage range. Take care to avoid pulling too much current from the outputs as to not exceed 6 mA. Also, take care to not go over  $V_{CC}$  voltage to avoid damage to the device.

#### 9.2.2 Detailed Design Procedure

- Recommended Input Conditions
  - Rise time and fall time specs: See  $(\Delta t/\Delta V)$  in the [セクション 6.3](#) table.
  - Specified high and low levels: See ( $V_{IH}$  and  $V_{IL}$ ) in the [セクション 6.3](#) table.
  - Inputs should not be pulled above  $V_{CC}$ .
- Recommended Output Conditions
  - Load currents should not exceed 6 mA for the part
  - Outputs should not be pulled above  $V_{CC}$ .

### 9.2.3 Application Curve




FIG 9-2. Input Transition Time vs.  $V_{CC}$

## 10 Power Supply Recommendations

The power supply can be any voltage between the MIN and MAX supply voltage rating located in the [セクション 6.3](#) table.

Each  $V_{CC}$  pin should have a good bypass capacitor to prevent power disturbance. For devices with a single supply, 0.1- $\mu\text{F}$  is recommended; if there are multiple  $V_{CC}$  pins, then 0.01- $\mu\text{F}$  or 0.022- $\mu\text{F}$  is recommended for each power pin. It is acceptable to parallel multiple bypass caps to reject different frequencies of noise. A 0.1- $\mu\text{F}$  and a 1- $\mu\text{F}$  are commonly used in parallel. The bypass capacitor should be installed as close to the power pin as possible for best results.


## 11 Layout

### 11.1 Layout Guidelines

When using multiple bit logic devices inputs should never float.

In many cases, functions or parts of functions of digital logic devices are unused, for example, when only two inputs of a triple-input AND gate are used or only 3 of the 4 buffer gates are used. Such input pins should not be left unconnected because the undefined voltages at the outside connections result in undefined operational states. The [セクション 6.3](#) section specifies the rules that must be observed under all circumstances. All unused inputs of digital logic devices must be connected to a high or low bias to prevent them from floating. The logic level that should be applied to any particular unused input depends on the function of the device. Generally they will be tied to GND or  $V_{CC}$  whichever makes more sense or is more convenient. It is generally acceptable to float outputs, unless the part is a transceiver. If the transceiver has an output enable pin, it disables the output section of the part when asserted. This does not disable the input section of the I/Os, so they cannot float when disabled.

### 11.2 Layout Example



❏ 11-1. Layout Diagram

## 12 Device and Documentation Support

### 12.1 Related Links

The table below lists quick access links. Categories include technical documents, support and community resources, tools and software, and quick access to sample or buy.

**表 12-1. Related Links**

| PARTS     | PRODUCT FOLDER             | SAMPLE & BUY               | TECHNICAL DOCUMENTS        | TOOLS & SOFTWARE           | SUPPORT & COMMUNITY        |
|-----------|----------------------------|----------------------------|----------------------------|----------------------------|----------------------------|
| SN54HC541 | <a href="#">Click here</a> | <a href="#">Click here</a> | <a href="#">Click here</a> | <a href="#">Click here</a> | <a href="#">Click here</a> |
| SN74HC541 | <a href="#">Click here</a> | <a href="#">Click here</a> | <a href="#">Click here</a> | <a href="#">Click here</a> | <a href="#">Click here</a> |

### 12.2 Receiving Notification of Documentation Updates

To receive notification of documentation updates, navigate to the device product folder on ti.com. In the upper right corner, click on *Alert me* to register and receive a weekly digest of any product information that has changed. For change details, review the revision history included in any revised document.

### 12.3 サポート・リソース

**TI E2E™ サポート・フォーラム**は、エンジニアが検証済みの回答と設計に関するヒントをエキスパートから迅速かつ直接得ることができる場所です。既存の回答を検索したり、独自の質問をしたりすることで、設計に必要な支援を迅速に得ることができます。

リンクされているコンテンツは、該当する貢献者により、現状のまま提供されるものです。これらは TI の仕様を構成するものではなく、必ずしも TI の見解を反映したものではありません。TI の[使用条件](#)を参照してください。

### 12.4 Trademarks

TI E2E™ is a trademark of Texas Instruments.

すべての商標は、それぞれの所有者に帰属します。

### 12.5 Electrostatic Discharge Caution



This integrated circuit can be damaged by ESD. Texas Instruments recommends that all integrated circuits be handled with appropriate precautions. Failure to observe proper handling and installation procedures can cause damage.

ESD damage can range from subtle performance degradation to complete device failure. Precision integrated circuits may be more susceptible to damage because very small parametric changes could cause the device not to meet its published specifications.

### 12.6 Glossary

[TI Glossary](#) This glossary lists and explains terms, acronyms, and definitions.

## 13 Mechanical, Packaging, and Orderable Information

The following pages include mechanical, packaging, and orderable information. This information is the most current data available for the designated devices. This data is subject to change without notice and revision of this document. For browser-based versions of this data sheet, refer to the left-hand navigation.

**PACKAGING INFORMATION**

| Orderable part number            | Status<br>(1) | Material type<br>(2) | Package   Pins  | Package qty   Carrier | RoHS<br>(3) | Lead finish/<br>Ball material<br>(4) | MSL rating/<br>Peak reflow<br>(5) | Op temp (°C) | Part marking<br>(6)  |
|----------------------------------|---------------|----------------------|-----------------|-----------------------|-------------|--------------------------------------|-----------------------------------|--------------|----------------------|
| <a href="#">JM38510/65711BRA</a> | Active        | Production           | CDIP (J)   20   | 20   TUBE             | No          | SNPB                                 | N/A for Pkg Type                  | -55 to 125   | JM38510/<br>65711BRA |
| JM38510/65711BRA.A               | Active        | Production           | CDIP (J)   20   | 20   TUBE             | No          | SNPB                                 | N/A for Pkg Type                  | -55 to 125   | JM38510/<br>65711BRA |
| <a href="#">M38510/65711BRA</a>  | Active        | Production           | CDIP (J)   20   | 20   TUBE             | No          | SNPB                                 | N/A for Pkg Type                  | -55 to 125   | JM38510/<br>65711BRA |
| <a href="#">SN54HC541J</a>       | Active        | Production           | CDIP (J)   20   | 20   TUBE             | No          | SNPB                                 | N/A for Pkg Type                  | -55 to 125   | SN54HC541J           |
| SN54HC541J.A                     | Active        | Production           | CDIP (J)   20   | 20   TUBE             | No          | SNPB                                 | N/A for Pkg Type                  | -55 to 125   | SN54HC541J           |
| <a href="#">SN74HC541DBR</a>     | Active        | Production           | SSOP (DB)   20  | 2000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 85    | HC541                |
| SN74HC541DBR.A                   | Active        | Production           | SSOP (DB)   20  | 2000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 85    | HC541                |
| <a href="#">SN74HC541DWR</a>     | Active        | Production           | SOIC (DW)   20  | 2000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 85    | HC541                |
| SN74HC541DWR.A                   | Active        | Production           | SOIC (DW)   20  | 2000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 85    | HC541                |
| <a href="#">SN74HC541N</a>       | Active        | Production           | PDIP (N)   20   | 20   TUBE             | Yes         | NIPDAU                               | N/A for Pkg Type                  | -40 to 85    | SN74HC541N           |
| SN74HC541N.A                     | Active        | Production           | PDIP (N)   20   | 20   TUBE             | Yes         | NIPDAU                               | N/A for Pkg Type                  | -40 to 85    | SN74HC541N           |
| SN74HC541NE4                     | Active        | Production           | PDIP (N)   20   | 20   TUBE             | Yes         | NIPDAU                               | N/A for Pkg Type                  | -40 to 85    | SN74HC541N           |
| <a href="#">SN74HC541NSR</a>     | Active        | Production           | SOP (NS)   20   | 2000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 85    | HC541                |
| SN74HC541NSR.A                   | Active        | Production           | SOP (NS)   20   | 2000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 85    | HC541                |
| <a href="#">SN74HC541PW</a>      | Obsolete      | Production           | TSSOP (PW)   20 | -                     | -           | Call TI                              | Call TI                           | -40 to 85    | HC541                |
| <a href="#">SN74HC541PWR</a>     | Active        | Production           | TSSOP (PW)   20 | 2000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 85    | HC541                |
| SN74HC541PWR.A                   | Active        | Production           | TSSOP (PW)   20 | 2000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 85    | HC541                |
| <a href="#">SN74HC541PWT</a>     | Obsolete      | Production           | TSSOP (PW)   20 | -                     | -           | Call TI                              | Call TI                           | -40 to 85    | HC541                |
| <a href="#">SNJ54HC541FK</a>     | Active        | Production           | LCCC (FK)   20  | 55   TUBE             | No          | SNPB                                 | N/A for Pkg Type                  | -55 to 125   | SNJ54HC<br>541FK     |
| SNJ54HC541FK.A                   | Active        | Production           | LCCC (FK)   20  | 55   TUBE             | No          | SNPB                                 | N/A for Pkg Type                  | -55 to 125   | SNJ54HC<br>541FK     |
| <a href="#">SNJ54HC541J</a>      | Active        | Production           | CDIP (J)   20   | 20   TUBE             | No          | SNPB                                 | N/A for Pkg Type                  | -55 to 125   | SNJ54HC541J          |
| SNJ54HC541J.A                    | Active        | Production           | CDIP (J)   20   | 20   TUBE             | No          | SNPB                                 | N/A for Pkg Type                  | -55 to 125   | SNJ54HC541J          |

<sup>(1)</sup> **Status:** For more details on status, see our [product life cycle](#).



**(2) Material type:** When designated, preproduction parts are prototypes/experimental devices, and are not yet approved or released for full production. Testing and final process, including without limitation quality assurance, reliability performance testing, and/or process qualification, may not yet be complete, and this item is subject to further changes or possible discontinuation. If available for ordering, purchases will be subject to an additional waiver at checkout, and are intended for early internal evaluation purposes only. These items are sold without warranties of any kind.

**(3) RoHS values:** Yes, No, RoHS Exempt. See the [TI RoHS Statement](#) for additional information and value definition.

**(4) Lead finish/Ball material:** Parts may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead finish/Ball material values may wrap to two lines if the finish value exceeds the maximum column width.

**(5) MSL rating/Peak reflow:** The moisture sensitivity level ratings and peak solder (reflow) temperatures. In the event that a part has multiple moisture sensitivity ratings, only the lowest level per JEDEC standards is shown. Refer to the shipping label for the actual reflow temperature that will be used to mount the part to the printed circuit board.

**(6) Part marking:** There may be an additional marking, which relates to the logo, the lot trace code information, or the environmental category of the part.

Multiple part markings will be inside parentheses. Only one part marking contained in parentheses and separated by a "~" will appear on a part. If a line is indented then it is a continuation of the previous line and the two combined represent the entire part marking for that device.

**Important Information and Disclaimer:** The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.


**OTHER QUALIFIED VERSIONS OF SN54HC541, SN74HC541 :**

- Catalog : [SN74HC541](#)
- Military : [SN54HC541](#)

NOTE: Qualified Version Definitions:

- Catalog - TI's standard catalog product
- Military - QML certified for Military and Defense Applications


## TAPE AND REEL INFORMATION



\*All dimensions are nominal

| Device       | Package Type | Package Drawing | Pins | SPQ  | Reel Diameter (mm) | Reel Width W1 (mm) | A0 (mm) | B0 (mm) | K0 (mm) | P1 (mm) | W (mm) | Pin1 Quadrant |
|--------------|--------------|-----------------|------|------|--------------------|--------------------|---------|---------|---------|---------|--------|---------------|
| SN74HC541DBR | SSOP         | DB              | 20   | 2000 | 330.0              | 16.4               | 8.2     | 7.5     | 2.5     | 12.0    | 16.0   | Q1            |
| SN74HC541DWR | SOIC         | DW              | 20   | 2000 | 330.0              | 24.4               | 10.9    | 13.3    | 2.7     | 12.0    | 24.0   | Q1            |
| SN74HC541NSR | SOP          | NS              | 20   | 2000 | 330.0              | 24.4               | 8.4     | 13.0    | 2.5     | 12.0    | 24.0   | Q1            |
| SN74HC541PWR | TSSOP        | PW              | 20   | 2000 | 330.0              | 16.4               | 6.95    | 7.0     | 1.4     | 8.0     | 16.0   | Q1            |


## TAPE AND REEL BOX DIMENSIONS



\*All dimensions are nominal



| Device       | Package Type | Package Drawing | Pins | SPQ  | Length (mm) | Width (mm) | Height (mm) |
|--------------|--------------|-----------------|------|------|-------------|------------|-------------|
| SN74HC541DBR | SSOP         | DB              | 20   | 2000 | 353.0       | 353.0      | 32.0        |
| SN74HC541DWR | SOIC         | DW              | 20   | 2000 | 356.0       | 356.0      | 45.0        |
| SN74HC541NSR | SOP          | NS              | 20   | 2000 | 356.0       | 356.0      | 45.0        |
| SN74HC541PWR | TSSOP        | PW              | 20   | 2000 | 353.0       | 353.0      | 32.0        |

## TUBE



\*All dimensions are nominal

| Device         | Package Name | Package Type | Pins | SPQ | L (mm) | W (mm) | T (μm) | B (mm) |
|----------------|--------------|--------------|------|-----|--------|--------|--------|--------|
| SN74HC541N     | N            | PDIP         | 20   | 20  | 506    | 13.97  | 11230  | 4.32   |
| SN74HC541N.A   | N            | PDIP         | 20   | 20  | 506    | 13.97  | 11230  | 4.32   |
| SN74HC541NE4   | N            | PDIP         | 20   | 20  | 506    | 13.97  | 11230  | 4.32   |
| SNJ54HC541FK   | FK           | LCCC         | 20   | 55  | 506.98 | 12.06  | 2030   | NA     |
| SNJ54HC541FK.A | FK           | LCCC         | 20   | 55  | 506.98 | 12.06  | 2030   | NA     |



4214851/B 08/2019

## NOTES:


1. All linear dimensions are in millimeters. Any dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.
2. This drawing is subject to change without notice.
3. This dimension does not include mold flash, protrusions, or gate burrs. Mold flash, protrusions, or gate burrs shall not exceed 0.15 mm per side.
4. This dimension does not include interlead flash. Interlead flash shall not exceed 0.25 mm per side.
5. Reference JEDEC registration MO-150.

# EXAMPLE BOARD LAYOUT



DB0020A

SSOP - 2 mm max height

SMALL OUTLINE PACKAGE



LAND PATTERN EXAMPLE  
EXPOSED METAL SHOWN  
SCALE: 10X



SOLDER MASK DETAILS

4214851/B 08/2019

NOTES: (continued)

6. Publication IPC-7351 may have alternate designs.


7. Solder mask tolerances between and around signal pads can vary based on board fabrication site.

## EXAMPLE STENCIL DESIGN

DB0020A

SSOP - 2 mm max height

SMALL OUTLINE PACKAGE



SOLDER PASTE EXAMPLE  
BASED ON 0.125 mm THICK STENCIL  
SCALE: 10X

4214851/B 08/2019

NOTES: (continued)


8. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.
9. Board assembly site may have different recommendations for stencil design.

# MECHANICAL DATA

NS (R-PDSO-G\*\*)

PLASTIC SMALL-OUTLINE PACKAGE

14-PINS SHOWN



| DIM \ PINS ** | 14    | 16    | 20    | 24    |
|---------------|-------|-------|-------|-------|
| A MAX         | 10,50 | 10,50 | 12,90 | 15,30 |
| A MIN         | 9,90  | 9,90  | 12,30 | 14,70 |

4040062/C 03/03


- NOTES:
- A. All linear dimensions are in millimeters.
  - B. This drawing is subject to change without notice.
  - C. Body dimensions do not include mold flash or protrusion, not to exceed 0,15.




J (R-GDIP-T\*\*)

14 LEADS SHOWN

# CERAMIC DUAL IN-LINE PACKAGE



| PINS **<br>DIM | 14                     | 16                     | 18                     | 20                     |
|----------------|------------------------|------------------------|------------------------|------------------------|
| A              | 0.300<br>(7,62)<br>BSC | 0.300<br>(7,62)<br>BSC | 0.300<br>(7,62)<br>BSC | 0.300<br>(7,62)<br>BSC |
| B MAX          | 0.785<br>(19,94)       | .840<br>(21,34)        | 0.960<br>(24,38)       | 1.060<br>(26,92)       |
| B MIN          | —                      | —                      | —                      | —                      |
| C MAX          | 0.300<br>(7,62)        | 0.300<br>(7,62)        | 0.310<br>(7,87)        | 0.300<br>(7,62)        |
| C MIN          | 0.245<br>(6,22)        | 0.245<br>(6,22)        | 0.220<br>(5,59)        | 0.245<br>(6,22)        |



4040083/F 03/03

- NOTES:
- A. All linear dimensions are in inches (millimeters).
  - B. This drawing is subject to change without notice.
  - C. This package is hermetically sealed with a ceramic lid using glass frit.
  - D. Index point is provided on cap for terminal identification only on press ceramic glass frit seal only.
  - E. Falls within MIL STD 1835 GDIP1-T14, GDIP1-T16, GDIP1-T18 and GDIP1-T20.

## GENERIC PACKAGE VIEW


**FK 20**

**LCCC - 2.03 mm max height**

8.89 x 8.89, 1.27 mm pitch

LEADLESS CERAMIC CHIP CARRIER

This image is a representation of the package family, actual package may vary.  
Refer to the product data sheet for package details.




4229370VA\


N (R-PDIP-T\*\*)

16 PINS SHOWN

## PLASTIC DUAL-IN-LINE PACKAGE




| PINS **<br>DIM      | 14               | 16               | 18               | 20               |
|---------------------|------------------|------------------|------------------|------------------|
| A MAX               | 0.775<br>(19,69) | 0.775<br>(19,69) | 0.920<br>(23,37) | 1.060<br>(26,92) |
| A MIN               | 0.745<br>(18,92) | 0.745<br>(18,92) | 0.850<br>(21,59) | 0.940<br>(23,88) |
| MS-001<br>VARIATION | AA               | BB               | AC               | AD               |



4040049/E 12/2002

NOTES:

- A. All linear dimensions are in inches (millimeters).  
B. This drawing is subject to change without notice.
-  Falls within JEDEC MS-001, except 18 and 20 pin minimum body length (Dim A).  
 The 20 pin end lead shoulder width is a vendor option, either half or full width.



4220724/A 05/2016

## NOTES:


1. All linear dimensions are in millimeters. Dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.
2. This drawing is subject to change without notice.
3. This dimension does not include mold flash, protrusions, or gate burrs. Mold flash, protrusions, or gate burrs shall not exceed 0.15 mm per side.
4. This dimension does not include interlead flash. Interlead flash shall not exceed 0.43 mm per side.
5. Reference JEDEC registration MS-013.

# EXAMPLE BOARD LAYOUT



DW0020A

SOIC - 2.65 mm max height

SOIC



LAND PATTERN EXAMPLE  
SCALE:6X



SOLDER MASK DETAILS

4220724/A 05/2016

NOTES: (continued)

6. Publication IPC-7351 may have alternate designs.


7. Solder mask tolerances between and around signal pads can vary based on board fabrication site.

## EXAMPLE STENCIL DESIGN

DW0020A

SOIC - 2.65 mm max height

SOIC





SOLDER PASTE EXAMPLE  
BASED ON 0.125 mm THICK STENCIL  
SCALE:6X

4220724/A 05/2016

NOTES: (continued)

8. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.
9. Board assembly site may have different recommendations for stencil design.



4220206/A 02/2017

## NOTES:


1. All linear dimensions are in millimeters. Any dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.
2. This drawing is subject to change without notice.
3. This dimension does not include mold flash, protrusions, or gate burrs. Mold flash, protrusions, or gate burrs shall not exceed 0.15 mm per side.
4. This dimension does not include interlead flash. Interlead flash shall not exceed 0.25 mm per side.
5. Reference JEDEC registration MO-153.

# EXAMPLE BOARD LAYOUT


PW0020A

TSSOP - 1.2 mm max height

SMALL OUTLINE PACKAGE



LAND PATTERN EXAMPLE  
EXPOSED METAL SHOWN  
SCALE: 10X



4220206/A 02/2017

NOTES: (continued)

6. Publication IPC-7351 may have alternate designs.

7. Solder mask tolerances between and around signal pads can vary based on board fabrication site.




## EXAMPLE STENCIL DESIGN

PW0020A

TSSOP - 1.2 mm max height

SMALL OUTLINE PACKAGE



SOLDER PASTE EXAMPLE  
BASED ON 0.125 mm THICK STENCIL  
SCALE: 10X

4220206/A 02/2017

NOTES: (continued)

8. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.
9. Board assembly site may have different recommendations for stencil design.

## 重要なお知らせと免責事項

TI は、技術データと信頼性データ (データシートを含みます)、設計リソース (リファレンス デザインを含みます)、アプリケーションや設計に関する各種アドバイス、Web ツール、安全性情報、その他のリソースを、欠陥が存在する可能性のある「現状のまま」提供しており、商品性および特定目的に対する適合性の黙示保証、第三者の知的財産権の非侵害保証を含みいかなる保証も、明示的または黙示的にかかわらず拒否します。

これらのリソースは、TI 製品を使用する設計の経験を積んだ開発者への提供を意図したものです。(1) お客様のアプリケーションに適した TI 製品の選定、(2) お客様のアプリケーションの設計、検証、試験、(3) お客様のアプリケーションに該当する各種規格や、その他のあらゆる安全性、セキュリティ、規制、または他の要件への確実な適合に関する責任を、お客様のみが単独で負うものとし、TI は一切の責任を拒否します。

上記の各種リソースは、予告なく変更される可能性があります。これらのリソースは、リソースで説明されている TI 製品を使用するアプリケーションの開発の目的でのみ、TI はその使用をお客様に許諾します。これらのリソースに関して、他の目的で複製することや掲載することは禁止されています。TI や第三者の知的財産権のライセンスが付与されている訳ではありません。お客様は、これらのリソースを自身で使用した結果発生するあらゆる申し立て、損害、費用、損失、責任について、TI およびその代理人を完全に補償するものとし、TI は一切の責任を拒否します。

TI の製品は、[TI の販売条件](#)、[TI の総合的な品質ガイドライン](#)、[ti.com](#) または TI 製品などに関連して提供される他の適用条件に従い提供されます。TI がこれらのリソースを提供することは、適用される TI の保証または他の保証の放棄の拡大や変更を意味するものではありません。TI がカスタム、またはカスタマー仕様として明示的に指定していない限り、TI の製品は標準的なカタログに掲載される汎用機器です。

お客様がいかなる追加条項または代替条項を提案する場合も、TI はそれらに異議を唱え、拒否します。

Copyright © 2026, Texas Instruments Incorporated

最終更新日：2025 年 10 月