TMP303 超小型パッケージに搭載した低消費電力、精度1°C、低電源電圧の使いやすい温度範囲モニタ

1 特長

- 低消費電流：5µA以下
- SOT-563パッケージ：1.60×1.60×0.6mm
- トリップ・ポイント精度：
  - ±0.2°C（標準値、-40°C～125°C）
- プッシュ - プル出力
- 選択可能なヒステリシス：1/2/5/10°C
- 電源電圧範囲：1.4V～3.6V

2 アプリケーション

- バッテリ充電
- バッテリの熱保護
- 消費者向け電子機器
- エンタープライズ
- 通信機器

3 概要

TMP303デバイスは、非常に小さなフットプリント(SOT-563)、小さな消費電流（5µA以下）、低い電源電圧への対応（最低1.4V）により、柔軟な設計が可能な温度範囲モニタです。

これらのデバイスを動作させるのに追加部品は不要です。マイクロプロセッサやマイクロコントローラと独立して動作できます。

7つのトリップ・ポイントを使用できます（デバイスのオプションを参照）。トリップ・ポイントは、出荷時に任意の温度にプログラム可能です。アプリケーションで別の値が必要な場合、お近くのTI代理店にお問い合わせください。


OUTピンはプッシュプル、アクティブHIGH出力です。Set Output High (SOH)ピンがLOWで、かつ測定温度がトリップ・ポイントの範囲を超えた場合、OUTピンがHIGHになります。SOHピンは入力ピンで、内部にプルダウン抵抗があります。SOHピンを強制的にHIGHにすると、測定された温度にかかわらず、OUTピンがHIGHになります。

製品情報(1)


型番	パッケージ	本体サイズ（公称）
TMP303	SOT-563 (6)	1.60mm×1.20mm

(1) 利用可能なすべてのパッケージについては、このデータシートの末尾にある注文情報を参照してください。

TMP303の機能ブロック図



トリップ・スレッショルドの精度（標準値）
－20°C～125°C



英語版のTI製品についての情報を翻訳したこの資料は、製品の概要を確認する目的で便宜的に提供しているものです。該当する正式な英語版の最新情報は、www.ti.comで閲覧でき、その内容が常に優先されます。TIでは翻訳の正確性および妥当性につきましては一切保証いたしません。実際の設計などの前には、必ず最新版の英語版をご参照くださいますようお願いいたします。

目次

1 特長 ... 1
2 アプリケーション ... 1
3 概要 ... 1
4 改訂履歴 ... 2
5 デバイスのオプション ... 3
6 **Pin Configuration and Functions** ... 3
7 **Specifications** ... 4
7.1 Absolute Maximum Ratings ... 4
7.2 ESD Ratings ... 4
7.3 Recommended Operating Conditions ... 4
7.4 Thermal Information ... 4
7.5 Electrical Characteristics ... 5
7.6 Typical Characteristics ... 6
8 **Detailed Description** ... 8
8.1 Overview ... 8
8.2 Functional Block Diagram ... 8
8.3 Feature Description ... 9
8.4 Device Functional Modes ... 11
9 **Application and Implementation** ... 12
9.1 Application Information ... 12
9.2 Typical Applications ... 12
10 **Power Supply Recommendations** ... 16
11 **Layout** ... 16
11.1 Layout Guidelines ... 16
11.2 Layout Example ... 16
12 デバイスおよびドキュメントのサポート ... 17
12.1 ドキュメントの更新通知を受け取る方法 ... 17
12.2 コミュニティ・リソース ... 17
12.3 商標 ... 17
12.4 静電気放電に関する注意事項 ... 17
12.5 Glossary ... 17
13 メカニカル、パッケージ、および注文情報 ... 17

4 改訂履歴

資料番号末尾の英字は改訂を表しています。その改訂履歴は英語版に準じています。

Revision H (October 2018) から **Revision I** に変更 — **Page**

- Changed input pin voltage maximum value in the *Absolute Maximum Ratings* table from: ((V+) + 0.5) and ≤ 4 to: ((V_S) + 0.3) and ≤ 4 ... 4
- Changed output pin voltage maximum value n the *Absolute Maximum Ratings* table from: ((V+) + 0.5) and ≤ 4 to: ((V_S) + 0.3) and ≤ 4 ... 4

Revision F (February 2016) から **Revision G** に変更 — **Page**

- TMP303E、TMP303F、TMP303Gデバイスをデータシートに 追加 ... 1
- デバイスのオプションの数を4から7に 変更 ... 1
- Changed Trip Point Accuracy in *Electrical Characteristics* from T_A = -20 to 125°C to T_A = 60 to 125°C ... 5

Revision E (October 2015) から **Revision F** に変更 — **Page**

- 「デバイスのオプション」表への相互参照を 追加 ... 1
- 「トリップのスレッショルド精度」に新しい画像を 追加 ... 1
- Added Trip Points covering range -20 to 125°C ... 5
- Added Trip Accuracy Error vs Temperature graph. ... 6

Revision D (September 2015) から **Revision E** に変更 — **Page**

- Changed I/O value of $HYST_{SET1}$ row in *Pin Functions* table ... 3

Revision C (September 2015) から **Revision D** に変更 — **Page**

- 型番を汎用のTMP303に統合 ... 1

Copyright © 2009–2018, Texas Instruments Incorporated

Revision B (January 2011) から Revision C に変更 **Page**

- 「*ESD定格*」表、「*機能説明*」セクション、「*デバイスの機能モード*」セクション、「*アプリケーションと実装*」セクション、「*電源に関する推奨事項*」セクション、「*レイアウト*」セクション、「*デバイスおよびドキュメントのサポート*」セクション、「*メカニカル、パッケージ、および注文情報*」セクション 追加 1

Revision A (September 2009) から Revision B に変更 **Page**

- データシートにTMP303Bデバイスを 追加 1


5 デバイスのオプション

デバイス	トリップ・ポイント(°C)
TMP303A	T_L = 0、T_H = 60 (1)
TMP303B	T_L = 0、T_H = 55 (1)
TMP303C	T_L = -20、T_H = 60 (1)
TMP303D	T_L = -15、T_H = 125 (1)
TMP303E	T_L = 0、T_H = 70 (1)
TMP303F	T_L = 0、T_H = 80 (1)
TMP303G	T_L = 0、T_H = 90 (1)

(1) 他のトリップ・ポイントについては、TI代理店にお問い合わせください。

6 Pin Configuration and Functions

DRL Package
6-Pin SOT-563
Top View



Pin Functions

PIN		I/O	DESCRIPTION
NAME	NO.		
HYST$_{SET0}$	1	Digital Input	This pin is used to set the amount of thermal hysteresis.
GND	2	Ground	Ground
OUT	3	Digital Output	Active high, push-pull output pin. Does not require a pullup resistor to V_S.
SOH	4	Digital Input	Set output high (SOH) pin. If the SOH pin is pulled high, the TMP303 forces the output high. If the SOH pin is grounded or left floating, this pin has no effect on the behavior of the TMP303.
V_S	5	Power Supply	Power supply
HYST$_{SET1}$	6	Digital Input	This pin is used to set the amount of thermal hysteresis.

Copyright © 2009–2018, Texas Instruments Incorporated

7 Specifications

7.1 Absolute Maximum Ratings

over operating free-air temperature range (unless otherwise noted)(1)

		MIN	MAX	UNIT
Supply Voltage, V_S – GND			4	V
Input Pins, Voltage	SOH, $HYST_{SET1}$, $HYST_{SET0}$	–0.5	$((V_S) + 0.3)$ and ≤ 4	V
Output Pin, Voltage	OUT	–0.5	$((V_S) + 0.3)$ and ≤ 4	V
Output Pin, Current	OUT	–55	8	mA
Operating Temperature			130	°C
Junction Temperature, T_J max			150	°C
Storage Temperature, T_{stg}		–60	150	°C

(1) Stresses beyond those listed under *Absolute Maximum Ratings* may cause permanent damage to the device. These are stress ratings only, which do not imply functional operation of the device at these or any other conditions beyond those indicated under *Recommended Operating Conditions*. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability.

7.2 ESD Ratings

			VALUE	UNIT
$V_{(ESD)}$	Electrostatic discharge	Human-body model (HBM), per ANSI/ESDA/JEDEC JS-001(1)	±2000	V
		Charged-device model (CDM), per JEDEC specification JESD22-C101(2)	±1000	
		Machine model (MM)	±200	

(1) JEDEC document JEP155 states that 500-V HBM allows safe manufacturing with a standard ESD control process.
(2) JEDEC document JEP157 states that 250-V CDM allows safe manufacturing with a standard ESD control process.

7.3 Recommended Operating Conditions

over operating free-air temperature range (unless otherwise noted)

		MIN	NOM	MAX	UNIT
V_S	Power Supply Voltage	1.4		3.6	V
T_A	Specified Temperature Range	–40		125	°C

7.4 Thermal Information

THERMAL METRIC(1)		TMP303 DRL (SOT-563) 6 PINS	UNIT
$R_{\theta JA}$	Junction-to-ambient thermal resistance	210.3	°C/W
$R_{\theta JC(top)}$	Junction-to-case (top) thermal resistance	105.0	°C/W
$R_{\theta JB}$	Junction-to-board thermal resistance	87.5	°C/W
ψ_{JT}	Junction-to-top characterization parameter	6.1	°C/W
ψ_{JB}	Junction-to-board characterization parameter	87.0	°C/W
$R_{\theta JC(bot)}$	Junction-to-case (bottom) thermal resistance	N/A	°C/W

(1) For more information about traditional and new thermal metrics, see the *Semiconductor and IC Package Thermal Metrics* application report, SPRA953.

Copyright © 2009–2018, Texas Instruments Incorporated

7.5 Electrical Characteristics

At T_A = –40°C to 125°C and V_S = 1.4 V to 3.6 V, unless otherwise noted.(1)

PARAMETER		CONDITIONS	MIN	TYP	MAX	UNIT
TEMPERATURE MEASUREMENT						
T_L, T_H Trip Point Accuracy(2)		T_A = 55°C to 60°C, V_S = 3.3 V		±0.2	±1	°C
		T_A = -20 to 60°C, V_S = 1.4 V to 3.6 V		±0.2	±1.5	
		T_A = 60 to 125°C, V_S = 1.4 V to 3.6 V		±0.2	±2.0	
		vs Supply		±0.1		°C/V
Hysteresis		See *Bit Setting vs Hysteresis Window*	1		10	°C
HYSTERESIS SET INPUT						
Input Logic Levels	V_{IH}		0.7 × V_S		3.6	V
	V_{IL}		–0.5		0.3 × V_S	
Input Current	I_{IN}	0 < V_{IN} < 3.6 V			1	µA
SOH INPUT						
Pulldown Resistor Value			80	100	120	kΩ
Input Logic Levels	V_{IH}		0.7 × V_S		3.6	V
	V_{IL}		–0.5		0.3 × V_S	
Input Current		V_{IN} = 3.6 V		36		µA
OUTPUT						
Output Logic Levels	V_{OH}	V_S > 2 V, I_{OH} = 0.5 mA	V_S – 0.4		V_S	V
		V_S < 2 V, I_{OH} = 0.5 mA	V_S – 0.2 × (V_S)		V_S	
	V_{OL}	V_S > 2 V, I_{OL} = 1 mA	0		0.4	
		V_S < 2 V, I_{OL} = 1 mA	0		0.2 × V_S	
POWER SUPPLY						
Specified Supply Voltage Range	V_S		1.4		3.6	V
Power-up Start-up Time		V_S > 1.4 V	20	28	35	ms
Quiescent Current	I_Q	T_A = –55°C to 60°C		3.5	5	µA
		T_A = –40°C to 125°C		4	8	
TEMPERATURE RANGE						
Specified Range			–40		125	°C
Operating Range			–55		130	°C

(1) 100% of all units are production tested at T_A = 25°C. Over temperature specifications are specified by design.
(2) T_L, T_H are device-specific. For example, TMP303A T_L = 0°C, T_H = 60°C; TMP303B T_L = 0°C, T_H = 55°C; TMP303C T_L = –20°C, T_H = 60°C; TMP303D T_L = –15°C, T_H = 125°C; TMP303E T_L = 0°C, T_H = 70°C; TMP303F T_L = 0°C, T_H = 80°C; TMP303G T_L = 0°C, T_H = 90°C

Copyright © 2009–2018, Texas Instruments Incorporated

7.6 Typical Characteristics

At V_S = 3.3 V and T_A = 25°C, unless otherwise noted.




Figure 1. Trip Accuracy Error vs Temperature




Figure 2. Quiescent Current vs Temperature




Figure 3. Temperature Step Response in Perfluorinated Fluid at 100°C vs Time




Figure 4. Thermal Step Response in Air at 100°C vs Time




Figure 5. Trip Threshold Accuracy at -20°C to 125°C




Figure 6. Power-Up and Power-Down Transient Response

Copyright © 2009–2018, Texas Instruments Incorporated

Typical Characteristics (continued)

At V_S = 3.3 V and T_A = 25°C, unless otherwise noted.




Figure 7. Power-Up, Trip, and Power-Down Response




Figure 8. Output Logic Level Low vs Temperature




Figure 9. Output Logic Level High vs Temperature

Copyright © 2009–2018, Texas Instruments Incorporated

8 Detailed Description


8.1 Overview

The TMP303 devices are temperature switches used in battery-powered applications that require accurate monitoring of a very specific temperature range from 0°C to 60°C (TMP303A), 0°C to 55°C (TMP303B), –20°C to 60°C (TMP303C), –15°C to 125°C (TMP303D), 0°C to 70°C (TMP303E), 0°C to 80°C (TMP303F) or 0°C to 90°C (TMP303G). This functionality is accomplished through the preset trip window and two hysteresis bits, $HYST_{SET0}$ and $HYST_{SET1}$. The preset trip window temperature thresholds are configured at the factory; for other trip points, contact a TI representative. Table 1 summarizes the bit setting versus hysteresis temperature window.

Table 1. Bit Setting vs Hysteresis Window

$HYST_{SET1}$	$HYST_{SET0}$	HYSTERESIS
GND	GND	1°C
GND	V_S	2°C
V_S	GND	5°C
V_S	V_S	10°C

8.2 Functional Block Diagram



Copyright © 2009–2018, Texas Instruments Incorporated

8.3 Feature Description

8.3.1 $HYST_{SET0}$, $HYST_{SET1}$ and SOH Functionality

The TMP303A temperature trip window resides within the range of 0°C to 60°C, the TMP303B within 0°C to 55°C, the TMP303C within –20°C to 60°C, the TMP303D within –15°C to 125°C, the TMP303E within 0°C to 70°C, the TMP303F within 0°C to 80°C, and the TMP303G within 0°C to 90°C. When any of these trip thresholds is crossed, the output (OUT) changes state from low to high. OUT does not return to its original low state until the temperature crosses the hysteresis threshold and returns within the range of the temperature trip window.

As an example, if the TMP303A is configured with a 10°C hysteresis window (that is, $HYST_{SET0}$ = $HYST_{SET1}$ = V_S), the output does not return to its low state until the temperature either crosses (T_L + *hysteresis*) = 10°C or (T_H – *hysteresis*) = 50°C. The Set Output High (SOH) pin is intended to add test functionality to verify the connectivity of the output (OUT) pin to the system controller or other temperature response system. The SOH pin is internally pulled down to ground with a 100-kΩ resistor. If the SOH pin is grounded or left floating, it has no effect on the behavior of the TMP303A. If the SOH pin is pulled high, the TMP303A immediately forces the output high, regardless of temperature.

NOTE

This response occurs even if the temperature falls within the 0°C to 60°C temperature window.

Figure 10 shows this design in graphical form.




Figure 10. TMP303A Output Transfer Curves With Hysteresis Change from 10°C to 5°C and SOH Functionality

Copyright © 2009–2018, Texas Instruments Incorporated

Feature Description (continued)

8.3.2 TMP303 Power Up and Timing

At device power up, the TMP303 exerts OUT = high, and typically requires 26 ms to return to a low state only if the temperature falls within the hysteresis window set by $HYST_{SET0}$ and $HYST_{SET1}$.

The tolerance of the thermal response time is largely a result of the differences in conversion time, which varies from 20 ms to 35 ms; likewise, this conversion does not take place after a power cycle until the supply voltage has reached a level of at least 1.4 V. This sequence is illustrated in Figure 11.




Figure 11. TMP303A Start-Up Delay vs Output Voltage ($HYST_{SET0}$ = $HYST_{SET1}$ = V_S)

After the TMP303 powers up, all successive thermal response results for the device are achieved in a time frame of 0.985 s to 1 s. This period is the minimum time frame required for the push-pull output (OUT) to change its state from high to low (or conversely) when the device is active.

Copyright © 2009–2018, Texas Instruments Incorporated

Feature Description (continued)

A maximum low output voltage is defined as a voltage level equivalent to (0.2 × V_S); likewise, a minimum high-output voltage is defined as (0.8 × V_S). The timing associated with start-up time and conversion is shown in Figure 12.




Figure 12. TMP303A Start-Up and Conversion Timing ($HYST_{SET0}$ = $HYST_{SET1}$ = V_S)

8.4 Device Functional Modes

The TMP303 family of devices has a single functional mode. Normal operation for the TMP303 family of devices occurs when the power-supply voltage applied between the V_S pin and GND is within the specified operating range of 1.4 to 3.6 V.The temperature threshold is configured at the factory and the hysteresis is selected by connecting the $HYST_{SET0}$ and $HYST_{SET1}$ pins to either the GND or Vs pins (see Table 1).

Copyright © 2009–2018, Texas Instruments Incorporated

9 Application and Implementation

NOTE

Information in the following applications sections is not part of the TI component specification, and TI does not warrant its accuracy or completeness. TI's customers are responsible for determining suitability of components for their purposes. Customers should validate and test their design implementation to confirm system functionality.

9.1 Application Information

The TMP303 family of devices is simple to configure. The TMP303 contains an active high, push-pull output stage and does not require a pullup resistor to V_S for proper operation. The only external component that the device requires is a bypass capacitor. TI strongly recommends using a 0.1-µF capacitor, placed as close as possible to the supply pin.

9.2 Typical Applications

9.2.1 TMP303 Typical Configuration

Figure 13 shows the typical circuit configuration for the TMP303 family of devices. These devices have preprogrammed trip-points. Select the TMP303 device that meets the application temperature trip requirement.




Figure 13. TMP303 Typical Application Configuration Schematic

9.2.1.1 Design Requirements

The TMP303 is a temperature switch commonly used to signal a microprocessor in the event of an over or under temperature condition. The temperature that the TMP303 issues a output is determined by the device preset trip window. The TMP303 issues an output when the temperature threshold is exceeded. To avoid the TMP303 signaling the microprocessor as soon as the temperature drops below the temperature threshold the TMP303 has a built-in hysteresis. The amount of hysteresis is determined by the hysteresis pins, $HYST_{SET0}$ and $HYST_{SET1}$. These pins are digital inputs and must be tied either high or low, according to Table 1.

9.2.1.2 Detailed Design Procedure

Select the appropriate TMP303 device that matches the application requirements; see the *デバイスのオプション* table for different trip point ranges. Connect the $HYST_{SET0}$ and $HYST_{SET1}$ pins according to the application requirements; see Table 1. In Figure 13 the TMP303 device is configured with a 1°C hysteresis window (that is, $HYST_{SET0}$ = $HYST_{SET1}$ = GND). Place a 0.1-µF bypass capacitor close to the TMP303 device to reduce the noise coupled from the power supply.

Copyright © 2009–2018, Texas Instruments Incorporated

Typical Applications (continued)

9.2.1.3 Application Curves

Figure 14 and Figure 15 show the TMP303A power-on response with the ambient temperature (T_A) less than 60°C and greater than 60°C respectively. TMP303B, TMP303C, TMP303D, TMP303E, TMP303F, and TMP303G devices behave similarly with regards to power-on response with T_A below or above the trip point.




Figure 14. TMP303A Power-On Response, T_A Less Than 60°C




Figure 15. TMP303A Power-On Response, T_A Greater Than 60°C

9.2.2 TMP303 With Switches

Figure 16 shows the most generic implementation of the TMP303 family of devices. Switches are shown connecting the $HYST_{SET0}$ and $HYST_{SET1}$ pins to either V_S or GND. The use of switches is not a requirement; the switches are shown only to illustrate the various pin connection combinations. In practice, connecting the $HYST_{SET0}$ and $HYST_{SET1}$ pins to ground or directly to the V_S pin is sufficient and minimizes board space and cost. If additional flexibility is desired, connections from the $HYST_{SET0}$ and $HYST_{SET1}$ pins can be made through 0-Ω resistors, which can be either populated or not, depending upon the desired connection.




Figure 16. TMP303 With Switches

Typical Applications (continued)

9.2.3 Simple Fan Controller

The circuit in Figure 17 senses system temperature and turns a cooling fan on when the sensor's temperature exceeds a preselected value. The TMP303 device can be used directly to control the fan. The OUT pin is active high, and it can be used directly to drive the DC fan. When temperature is within the temperature limits of the system, the fan turns off, and when the temperature exceeds the trip-point, the fan turns on. In this example, the TMP303A device is used and is configured with a 1°C hysteresis window ($HYST_{SET0}$ = $HYST_{SET1}$ = GND). The TMP303A high trip-point is 60°C. When this trip-point temperature is exceeded, the output (OUT) changes state from low to high. The output does not return to its low state until the temperature decreases below (T_H – *hysteresis*) = 59°C.




Figure 17. Simple Fan Controller

Copyright © 2009–2018, Texas Instruments Incorporated

Typical Applications (continued)

9.2.4 Wireless Fixed Temperature Heat Detector

Heat detectors are needed in building automation. Conventional heat detectors need cables to supply power and send the information back to a central system. Adding cables can be very costly and technically challenging in old buildings, this leads to wireless battery operated heat detectors as preferred solutions. Running on battery requires designing a very low power system for long haul. TMP303 can be used to design a low power heat detector due to its very low quiescent current (5 µA maximum). The TMP303 device does not require any additional components and can be interfaced with the MCU using only one GPIO. As an example, a wireless transceiver with internal MCU can be used to monitor the TMP303 and communicate with a central system or turn on an alarm in case of temperatures exceeding the trip-point. Figure 18 shows typical connections.




Figure 18. Wireless Fixed Temperature Heat Detector

10 Power Supply Recommendations

The TMP303 family of devices is designed to operate from a single power supply within the range of 1.4 V to 3.6 V. No specific power supply sequencing with respect to any of the input or output pins is required.

11 Layout

11.1 Layout Guidelines

Mount the TMP303 to a PCB as shown in Figure 19. For this example the $HYST_{SET0}$ and $HYST_{SET1}$ pins are connected directly to ground. Connecting these pins to ground configures the device for 1°C hysteresis. The SOH pin is grounded in this layout. Leaving this pin floating has no effect on the behavior of the TMP303.

- Bypass the V_S pin to ground with a low-ESR ceramic bypass capacitor. The typical recommended bypass capacitance is a 0.1-µF ceramic capacitor with a X5R or X7R dielectric. The optimum placement is closest to the V_S and GND pins of the device. Take care in minimizing the loop area formed by the bypass-capacitor connection, the V_S pin, and the GND pin of the IC. Additional bypass capacitance can be added to compensate for noisy or high-impedance power supplies.
- The OUT pin is a push-pull, active-high output and does not require a pullup resistor to V_S.

11.2 Layout Example




Figure 19. PCB Layout Example

Copyright © 2009–2018, Texas Instruments Incorporated

12 デバイスおよびドキュメントのサポート

12.1 ドキュメントの更新通知を受け取る方法

ドキュメントの更新についての通知を受け取るには、ti.comのデバイス製品フォルダを開いてください。右上の「アラートを受け取る」をクリックして登録すると、変更されたすべての製品情報に関するダイジェストを毎週受け取れます。変更の詳細については、修正されたドキュメントに含まれている改訂履歴をご覧ください。

12.2 コミュニティ・リソース

The following links connect to TI community resources. Linked contents are provided "AS IS" by the respective contributors. They do not constitute TI specifications and do not necessarily reflect TI's views; see TI's Terms of Use.

TI E2E™オンライン・コミュニティ ***TIのE2E（Engineer-to-Engineer）コミュニティ。*** **エンジニア間の共同作業を促進するために開設されたものです。e2e.ti.comでは、他のエンジニアに質問し、知識を共有し、アイディアを検討して、問題解決に役立てることができます。**

設計サポート ***TIの設計サポート*** **役に立つE2Eフォーラムや、設計サポート・ツールをすばやく見つけることができます。技術サポート用の連絡先情報も参照できます。**

12.3 商標

E2E is a trademark of Texas Instruments.
All other trademarks are the property of their respective owners.

12.4 静電気放電に関する注意事項



すべての集積回路は、適切なESD保護方法を用いて、取扱いと保存を行うようにして下さい。

静電気放電はわずかな性能の低下から完全なデバイスの故障に至るまで、様々な損傷を与えます。高精度の集積回路は、損傷に対して敏感であり、極めてわずかなパラメータの変化により、デバイスに規定された仕様に適合しなくなる場合があります。

12.5 Glossary

SLYZ022 — *TI Glossary*.

This glossary lists and explains terms, acronyms, and definitions.

13 メカニカル、パッケージ、および注文情報

以降のページには、メカニカル、パッケージ、および注文に関する情報が記載されています。この情報は、そのデバイスについて利用可能な最新のデータです。このデータは予告なく変更されることがあり、ドキュメントが改訂される場合もあります。本データシートのブラウザ版を使用されている場合は、画面左側の説明をご覧ください。

Copyright © 2009–2018, Texas Instruments Incorporated

PACKAGING INFORMATION

Orderable part number	Status (1)	Material type (2)	Package | Pins	Package qty | Carrier	RoHS (3)	Lead finish/ Ball material (4)	MSL rating/ Peak reflow (5)	Op temp (°C)	Part marking (6)
TMP303ADRLR	Active	Production	SOT-5X3 (DRL) | 6	4000 | LARGE T&R	Yes	NIPDAU | NIPDAUAG	Level-1-260C-UNLIM	-40 to 125	OCO
TMP303ADRLR.A	Active	Production	SOT-5X3 (DRL) | 6	4000 | LARGE T&R	Yes	NIPDAU	Level-1-260C-UNLIM	-40 to 125	OCO
TMP303ADRLR.B	Active	Production	SOT-5X3 (DRL) | 6	4000 | LARGE T&R	Yes	NIPDAU	Level-1-260C-UNLIM	-40 to 125	OCO
TMP303ADRLT	Obsolete	Production	SOT-5X3 (DRL) | 6	-	-	Call TI	Call TI	-40 to 125	OCO
TMP303BDRLR	Active	Production	SOT-5X3 (DRL) | 6	4000 | LARGE T&R	Yes	NIPDAU | NIPDAUAG	Level-1-260C-UNLIM	-40 to 125	QWM
TMP303BDRLR.A	Active	Production	SOT-5X3 (DRL) | 6	4000 | LARGE T&R	Yes	NIPDAU	Level-1-260C-UNLIM	-40 to 125	QWM
TMP303BDRLR.B	Active	Production	SOT-5X3 (DRL) | 6	4000 | LARGE T&R	Yes	NIPDAU	Level-1-260C-UNLIM	-40 to 125	QWM
TMP303BDRLT	Obsolete	Production	SOT-5X3 (DRL) | 6	-	-	Call TI	Call TI	-40 to 125	QWM
TMP303CDRLR	Active	Production	SOT-5X3 (DRL) | 6	4000 | LARGE T&R	Yes	NIPDAU	Level-1-260C-UNLIM	-40 to 125	11U
TMP303CDRLR.A	Active	Production	SOT-5X3 (DRL) | 6	4000 | LARGE T&R	Yes	NIPDAU	Level-1-260C-UNLIM	-40 to 125	11U
TMP303CDRLT	Obsolete	Production	SOT-5X3 (DRL) | 6	-	-	Call TI	Call TI	-40 to 125	11U
TMP303DDRLR	Active	Production	SOT-5X3 (DRL) | 6	4000 | LARGE T&R	Yes	NIPDAU	Level-1-260C-UNLIM	-40 to 125	(11U, 12Z)
TMP303DDRLR.A	Active	Production	SOT-5X3 (DRL) | 6	4000 | LARGE T&R	Yes	NIPDAU	Level-1-260C-UNLIM	-40 to 125	(11U, 12Z)
TMP303DDRLRG4	Active	Production	SOT-5X3 (DRL) | 6	4000 | LARGE T&R	Yes	NIPDAU	Level-1-260C-UNLIM	-40 to 125	11U
TMP303DDRLRG4.A	Active	Production	SOT-5X3 (DRL) | 6	4000 | LARGE T&R	Yes	NIPDAU	Level-1-260C-UNLIM	-40 to 125	11U
TMP303DDRLT	Obsolete	Production	SOT-5X3 (DRL) | 6	-	-	Call TI	Call TI	-40 to 125	12Z
TMP303EDRLR	Active	Production	SOT-5X3 (DRL) | 6	4000 | LARGE T&R	Yes	NIPDAU	Level-1-260C-UNLIM	-40 to 125	17Z
TMP303EDRLR.A	Active	Production	SOT-5X3 (DRL) | 6	4000 | LARGE T&R	Yes	NIPDAU	Level-1-260C-UNLIM	-40 to 125	17Z
TMP303EDRLR.B	Active	Production	SOT-5X3 (DRL) | 6	4000 | LARGE T&R	Yes	NIPDAU	Level-1-260C-UNLIM	-40 to 125	17Z
TMP303EDRLT	Obsolete	Production	SOT-5X3 (DRL) | 6	-	-	Call TI	Call TI	-40 to 125	17Z
TMP303FDRLR	Active	Production	SOT-5X3 (DRL) | 6	4000 | LARGE T&R	Yes	NIPDAU	Level-1-260C-UNLIM	-40 to 125	18A
TMP303FDRLR.A	Active	Production	SOT-5X3 (DRL) | 6	4000 | LARGE T&R	Yes	NIPDAU	Level-1-260C-UNLIM	-40 to 125	18A
TMP303FDRLR.B	Active	Production	SOT-5X3 (DRL) | 6	4000 | LARGE T&R	Yes	NIPDAU	Level-1-260C-UNLIM	-40 to 125	18A
TMP303FDRLT	Obsolete	Production	SOT-5X3 (DRL) | 6	-	-	Call TI	Call TI	-40 to 125	18A
TMP303GDRLR	Active	Production	SOT-5X3 (DRL) | 6	4000 | LARGE T&R	Yes	NIPDAU	Level-1-260C-UNLIM	-40 to 125	18B
TMP303GDRLR.A	Active	Production	SOT-5X3 (DRL) | 6	4000 | LARGE T&R	Yes	NIPDAU	Level-1-260C-UNLIM	-40 to 125	18B
TMP303GDRLR.B	Active	Production	SOT-5X3 (DRL) | 6	4000 | LARGE T&R	Yes	NIPDAU	Level-1-260C-UNLIM	-40 to 125	18B
TMP303GDRLT	Obsolete	Production	SOT-5X3 (DRL) | 6	-	-	Call TI	Call TI	-40 to 125	18B

(1) **Status:** For more details on status, see our product life cycle.

(2) **Material type:** When designated, preproduction parts are prototypes/experimental devices, and are not yet approved or released for full production. Testing and final process, including without limitation quality assurance, reliability performance testing, and/or process qualification, may not yet be complete, and this item is subject to further changes or possible discontinuation. If available for ordering, purchases will be subject to an additional waiver at checkout, and are intended for early internal evaluation purposes only. These items are sold without warranties of any kind.

(3) **RoHS values:** Yes, No, RoHS Exempt. See the TI RoHS Statement for additional information and value definition.

(4) **Lead finish/Ball material:** Parts may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead finish/Ball material values may wrap to two lines if the finish value exceeds the maximum column width.

(5) **MSL rating/Peak reflow:** The moisture sensitivity level ratings and peak solder (reflow) temperatures. In the event that a part has multiple moisture sensitivity ratings, only the lowest level per JEDEC standards is shown. Refer to the shipping label for the actual reflow temperature that will be used to mount the part to the printed circuit board.

(6) **Part marking:** There may be an additional marking, which relates to the logo, the lot trace code information, or the environmental category of the part.


Multiple part markings will be inside parentheses. Only one part marking contained in parentheses and separated by a "~" will appear on a part. If a line is indented then it is a continuation of the previous line and the two combined represent the entire part marking for that device.

Important Information and Disclaimer: The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.


In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.

TAPE AND REEL INFORMATION

REEL DIMENSIONS




TAPE DIMENSIONS



A0	Dimension designed to accommodate the component width
B0	Dimension designed to accommodate the component length
K0	Dimension designed to accommodate the component thickness
W	Overall width of the carrier tape
P1	Pitch between successive cavity centers


QUADRANT ASSIGNMENTS FOR PIN 1 ORIENTATION IN TAPE



*All dimensions are nominal

Device	Package Type	Package Drawing	Pins	SPQ	Reel Diameter (mm)	Reel Width W1 (mm)	A0 (mm)	B0 (mm)	K0 (mm)	P1 (mm)	W (mm)	Pin1 Quadrant
TMP303ADRLR	SOT-5X3	DRL	6	4000	180.0	8.4	1.98	1.78	0.69	4.0	8.0	Q3
TMP303ADRLR	SOT-5X3	DRL	6	4000	180.0	8.4	2.0	1.8	0.75	4.0	8.0	Q3
TMP303BDRLR	SOT-5X3	DRL	6	4000	180.0	8.4	2.0	1.8	0.75	4.0	8.0	Q3
TMP303BDRLR	SOT-5X3	DRL	6	4000	180.0	8.4	1.98	1.78	0.69	4.0	8.0	Q3
TMP303CDRLR	SOT-5X3	DRL	6	4000	180.0	8.4	2.0	1.8	0.75	4.0	8.0	Q3
TMP303DDRLR	SOT-5X3	DRL	6	4000	180.0	8.4	2.0	1.8	0.75	4.0	8.0	Q3
TMP303DDRLRG4	SOT-5X3	DRL	6	4000	180.0	8.4	2.0	1.8	0.75	4.0	8.0	Q3
TMP303EDRLR	SOT-5X3	DRL	6	4000	180.0	8.4	2.0	1.8	0.75	4.0	8.0	Q3
TMP303FDRLR	SOT-5X3	DRL	6	4000	180.0	8.4	2.0	1.8	0.75	4.0	8.0	Q3
TMP303GDRLR	SOT-5X3	DRL	6	4000	180.0	8.4	2.0	1.8	0.75	4.0	8.0	Q3

TAPE AND REEL BOX DIMENSIONS



*All dimensions are nominal

Device	Package Type	Package Drawing	Pins	SPQ	Length (mm)	Width (mm)	Height (mm)
TMP303ADRLR	SOT-5X3	DRL	6	4000	202.0	201.0	28.0
TMP303ADRLR	SOT-5X3	DRL	6	4000	210.0	185.0	35.0
TMP303BDRLR	SOT-5X3	DRL	6	4000	210.0	185.0	35.0
TMP303BDRLR	SOT-5X3	DRL	6	4000	202.0	201.0	28.0
TMP303CDRLR	SOT-5X3	DRL	6	4000	210.0	185.0	35.0
TMP303DDRLR	SOT-5X3	DRL	6	4000	210.0	185.0	35.0
TMP303DDRLRG4	SOT-5X3	DRL	6	4000	210.0	185.0	35.0
TMP303EDRLR	SOT-5X3	DRL	6	4000	210.0	185.0	35.0
TMP303FDRLR	SOT-5X3	DRL	6	4000	210.0	185.0	35.0
TMP303GDRLR	SOT-5X3	DRL	6	4000	210.0	185.0	35.0




PACKAGE OUTLINE

DRL0006A

SOT - 0.6 mm max height

PLASTIC SMALL OUTLINE



NOTES:


1. All linear dimensions are in millimeters. Any dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.
2. This drawing is subject to change without notice.
3. This dimension does not include mold flash, protrusions, or gate burrs. Mold flash, protrusions, or gate burrs shall not exceed 0.15 mm per side.
4. Reference JEDEC registration MO-293 Variation UAAD

EXAMPLE BOARD LAYOUT


DRL0006A

SOT - 0.6 mm max height

PLASTIC SMALL OUTLINE



LAND PATTERN EXAMPLE
SCALE:30X



SOLDERMASK DETAILS

4223266/F 11/2024

NOTES: (continued)


5. Publication IPC-7351 may have alternate designs.
6. Solder mask tolerances between and around signal pads can vary based on board fabrication site.
7. Land pattern design aligns to IPC-610, Bottom Termination Component (BTC) solder joint inspection criteria.

EXAMPLE STENCIL DESIGN

DRL0006A

SOT - 0.6 mm max height

PLASTIC SMALL OUTLINE



SOLDER PASTE EXAMPLE
BASED ON 0.1 mm THICK STENCIL
SCALE:30X

4223266/F 11/2024

NOTES: (continued)

8. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.
9. Board assembly site may have different recommendations for stencil design.

重要なお知らせと免責事項

TI は、技術データと信頼性データ (データシートを含みます)、設計リソース (リファレンス デザインを含みます)、アプリケーションや設計に関する各種アドバイス、Web ツール、安全性情報、その他のリソースを、欠陥が存在する可能性のある「現状のまま」提供しており、商品性および特定目的に対する適合性の黙示保証、第三者の知的財産権の非侵害保証を含むいかなる保証も、明示的または黙示的にかかわらず拒否します。

これらのリソースは、TI 製品を使用する設計の経験を積んだ開発者への提供を意図したものです。(1) お客様のアプリケーションに適した TI 製品の選定、(2) お客様のアプリケーションの設計、検証、試験、(3) お客様のアプリケーションに該当する各種規格や、その他のあらゆる安全性、セキュリティ、規制、または他の要件への確実な適合に関する責任を、お客様のみが単独で負うものとします。

上記の各種リソースは、予告なく変更される可能性があります。これらのリソースは、リソースで説明されている TI 製品を使用するアプリケーションの開発の目的でのみ、TI はその使用をお客様に許諾します。これらのリソースに関して、他の目的で複製することや掲載することは禁止されています。TI や第三者の知的財産権のライセンスが付与されている訳ではありません。お客様は、これらのリソースを自身で使用した結果発生するあらゆる申し立て、損害、費用、損失、責任について、TI およびその代理人を完全に補償するものとし、TI は一切の責任を拒否します。

TI の製品は、 TI の販売条件 、 TI の総合的な品質ガイドライン 、 ti.com または TI 製品などに関連して提供される他の適用条件に従い提供されます。TI がこれらのリソースを提供することは、適用される TI の保証または他の保証の放棄の拡大や変更を意味するものではありません。 TI がカスタム、またはカスタマー仕様として明示的に指定していない限り、TI の製品は標準的なカタログに掲載される汎用機器です。

お客様がいかなる追加条項または代替条項を提案する場合も、TI はそれらに異議を唱え、拒否します。

Copyright © 2026, Texas Instruments Incorporated

最終更新日：2025 年 10 月