TMP464













JAJSD83C - MAY 2017-REVISED OCTOBER 2019

TMP464 高精度5チャネル(リモート4、ローカル1)温度センサ

特長

- 4チャネルのリモート・ダイオード温度センサ
- ローカルおよびリモートの精度: ±0.75℃(最大値)
- 温度分解能: 0.0625℃
- 電源およびロジックの電圧範囲: 1.7V~3.6V
- 動作電流: 43µA (1SPS、全チャネルがアクティブ)
- シャットダウン時電流: 0.3µA
- リモート・ダイオード: 直列抵抗のキャンセル、 η-係数訂正、オフセット訂正、ダイオードの障害 検出
- レジスタ・ロック機能により主要レジスタを保護
- I²Cまたは SMBus™互換の2線式インターフェイ ス、アドレスはピンによりプログラム可能
- 16ピンVQFNパッケージ

2 アプリケーション

- MCU、GPU、ASIC、FPGA、DSP、CPUの温度
- テレコミュニケーション機器
- サーバーおよびパーソナル・コンピュータ
- クラウドEthernetスイッチ
- セキュアなデータ・センター
- 高度に統合された医療システム
- 高精度の計測およびテスト機器
- LEDライティングの熱制御

3 概要

TMP464デバイスは、高精度、低消費電力の温度センサ で、2線式のSMBusまたはI2C互換のインターフェイスを使 用します。ローカルの温度に加えて、最大4つのリモート・ ダイオード接続の温度ゾーンを同時に監視できます。シス テム全体にわたって温度測定結果を集計することにより、 より緊密なガードバンドを使用して性能を向上でき、基板 の複雑性も低減できます。代表的な使用例として、サー バーやテレコミュニケーション機器など複雑なシステムに 含まれているMCU、GPU、FPGAなど各プロセッサの温度 監視が挙げられます。直列抵抗のキャンセル、プログラム 可能な非理想係数、プログラム可能なオフセット、プログラ ム可能な温度制限などの高度な機能が搭載されているた め、堅牢な温度監視ソリューションとして、正確性とノイズ 耐性を向上できます。


4個のリモート・チャネル(およびローカル・チャネル)はそれ ぞれ独立に2つのスレッショルドをプログラム可能で、測定 された場所の温度がそのスレッショルドを超えるとトリガさ れます。また、スレッショルド周辺での継続的な切り替わり を回避するため、ヒステリシス設定をプログラムできます。

製品情報(1)

型番	パッケージ	本体サイズ(公称)
TMP464	VQFN (16)	3.00mm×3.00mm

(1) 提供されているすべてのパッケージについては、データシートの末 尾にある注文情報を参照してください。

代表的なアプリケーションの回路図



推奨されるリモート・ダイオードについては、設計要件セクションを参照してください。



	٠,
_	
	I

		•		
1	特長1		8.4 Device Functional Modes	13
2	アプリケーション1		8.5 Programming	13
3	概要 1		8.6 Register Maps	19
4	改訂履歴	9	Application and Implementation	29
5	概要(続き)		9.1 Application Information	29
6	Pin Configuration and Functions		9.2 Typical Application	29
-	_	10	Power Supply Recommendations	32
7	Specifications 5	11	Layout	
	7.1 Absolute Maximum Ratings		11.1 Layout Guidelines	
	7.2 ESD Ratings		11.2 Layout Example	
	7.3 Recommended Operating Conditions	12		
	7.4 Thermal Information		12.1 ドキュメントの更新通知を受け取る方法	
			12.2 コミュニティ・リソース	
	7.6 Two-Wire Timing Requirements		12.3 商標	
_	7.7 Typical Characteristics		12.4 静電気放電に関する注意事項	
8	Detailed Description		12.5 Glossary	
	8.1 Overview	13	メカニカル、パッケージ、および注文情報	
	8.2 Functional Block Diagram 10	13	グルースル、バグケーン、わよい住文情報	33
	8.3 Feature Description			

4 改訂履歴

資料番号末尾の英字は改訂を表しています。その改訂履歴は英語版に準じています。

Revision B (August 2017) から Revision C に変更	Page
Changed the Device ID code from: 0x0464 to: 0x1468	28
Revision A (June 2017) から Revision B に変更	Page
Changed 'QFN' to 'VQFN' in table header as per industry standard	5
2017年5月発行のものから更新	Page
パッケージ情報を更新	




5 概要(続き)

TMP464は高精度(0.75℃)と高分解能(0.0625℃)の測定能力があります。また、低電圧レール(1.7V~3.6V)と、一般的な 2線式インターフェイスをサポートし、小型で省スペースのパッケージ(3mm×3mm)で供給されるため、コンピュータ・システムに簡単に組み込めます。リモート接合は-55℃~+150℃の範囲の温度に対応できます。TMP464には125℃の温度制限があらかじめプログラムされています。



6 Pin Configuration and Functions

TMP464 RGT Package 16-Pin VQFN With Exposed Thermal Pad Top View



NC - No internal connection

Pin Functions

PIN NAME NO.		TV05	DESCRIPTION		
		TYPE			
ADD	9	Digital Input	Address select. Connect to GND, V+, SDA, or SCL.		
D1+	6	Analog input	Positive connection to remote temperature sensors. A total of 4 remote channels are supported. An unused channel must be connected to D–.		
D2+	5	Analog input	Positive connection to remote temperature sensors. A total of 4 remote channels are supported. An unused channel must be connected to D–.		
D3+	4	Analog input	Positive connection to remote temperature sensors. A total of 4 remote channels are supported. An unused channel must be connected to D–.		
D4+	3	Analog input	Positive connection to remote temperature sensors. A total of 4 remote channels are supported. An unused channel must be connected to D–.		
D-	7	Analog input	Negative connection to remote temperature sensors. Common for 4 remote channels.		
GND	8	Ground	Supply ground connection		
NC	1, 2, 15, 16	_	No connection, may be left floating or connected to GND or V+		
SCL	13	Digital input	Serial clock line for I ² C or SMBus compatible two-wire interface. Input; requires a pullup resistor to a voltage between 1.7 V and 3.6 V (not necessarily V+) if driven by an open-drain output.		
SDA	12	Bidirectional digital input-output	Serial data line for $\rm I^2C$ - or SMBus compatible two-wire interface. Open-drain; requires a pullup resistor to a voltage between 1.7 V and 3.6 V, not necessarily V+.		
THERM	10	Digital output	Thermal shutdown or fan-control pin. Active low; open-drain; requires a pullup resistor to a voltage between 1.7 V and 3.6 V, not necessarily V+. If this pin is not used it may be left open or grounded.		
THERM2	11	Digital output	Second THERM output. Active low; open-drain; requires a pullup resistor to a voltage between 1.7 V and 3.6 V, not necessarily V+. If this pin is not used it may be left open or grounded.		
V+	14	Power supply	Positive supply voltage, 1.7 V to 3.6 V; requires 0.1-µF bypass capacitor to ground.		



7 Specifications

7.1 Absolute Maximum Ratings

over operating free-air temperature range (unless otherwise noted)⁽¹⁾

		MIN	MAX	UNIT	
Power supply	V+	-0.3	6	V	
	THERM, THERM2, SDA, SCL, and ADD only	-0.3	6		
Input voltage	D1+ through D4+	-0.3	((V+) + 0.3) and ≤ 6	V	
	D– only	-0.3	0.3		
lament annuant	SDA sink	-25		mA	
Input current	All other pins	-10	10		
Operating temperature		-55	150	°C	
Junction temperature (T _J , maximum)			150	°C	
Storage temperature, T _{stg}		-60	150	°C	

⁽¹⁾ Stresses beyond those listed under Absolute Maximum Ratings may cause permanent damage to the device. These are stress ratings only, which do not imply functional operation of the device at these or any other conditions beyond those indicated under Recommended Operating Conditions. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability.

7.2 ESD Ratings

			VALUE	UNIT
V	Floatroototic disaborge	Human body model (HBM), per ANSI/ESDA/JEDEC JS-001 (1)	±2000	V
V _(ESD)	Electrostatic discharge	Charged device model (CDM), JEDEC specification JESD22-C101 ⁽²⁾	±750	V

⁽¹⁾ JEDEC document JEP155 states that 500-V HBM allows safe manufacturing with a standard ESD control process.

7.3 Recommended Operating Conditions

over operating free-air temperature range (unless otherwise noted)

		MIN	NOM MAX	UNIT
V+	Supply voltage	1.7	3.6	V
T _A	Operating free-air temperature	-40	125	°C
T_D	Remote junction temperature	-55	150	°C

7.4 Thermal Information

		TMP464	
	THERMAL METRIC	RGT (VQFN)	UNIT
		16 PINS	
$R_{\theta JA}$	Junction-to-ambient thermal resistance	46	°C/W
$R_{\theta JC(top)}$	Junction-to-case (top) thermal resistance	43	°C/W
$R_{\theta JB}$	Junction-to-board thermal resistance	17	°C/W
ΨЈТ	Junction-to-top characterization parameter	0.8	°C/W
ΨЈВ	Junction-to-board characterization parameter	5	°C/W

²⁾ JEDEC document JEP157 states that 250-V CDM allows safe manufacturing with a standard ESD control process.



7.5 Electrical Characteristics

at $T_A = -40$ °C to +125 °C and V+ = 1.7 V to 3.6 V (unless otherwise noted)

	PARAI	METER	TEST CONDITIONS	MIN	TYP	MAX	UNIT
TEMPER	ATURE MEASUR	EMENT					
_			$T_A = -40$ °C to 100°C, V+ = 1.7 V to 3.6 V	-0.75	±0.125	0.75	°C
T _{LOCAL}	Local temperatul	re sensor accuracy	$T_A = -40$ °C to 125°C, V+ = 1.7 V to 3.6 V	-1	±0.5	1	°C
_			T _A = -10°C to 85°C, T _D = -55°C to 150°C V+ = 1.7 V to 3.6 V	-0.75	±0.125	0.75	
T _{REMOTE}	Remote tempera	iture sensor accuracy	T _A = -40°C to 125°C, T _D = -55°C to 150°C V+ = 1.7 V to 3.6 V	-1	±0.5	1	°C
	Local temperatur	re error supply sensitivity	V+ = 1.7 V to 3.6 V	-0.15	±0.05	0.15	°C/V
	Remote tempera	ture error supply sensitivity	V+ = 1.7 V to 3.6 V	-0.25	±0.1	0.25	°C/V
	Temperature res				0.0625		°C
	ADC conversion	time	One-shot mode, per channel (local or remote)		16	17	ms
	ADC resolution				13		Bits
		High			120		
	Remote sensor	Medium	Series resistance 1 kΩ (maximum)		45		μΑ
	source current	Low	, , ,		7.5		•
η	Remote transisto				1.008		
-	INTERFACE (SCL	•					
V _{IH}	High-level input	·		0.7 × (V+)			V
V _{IL}	Low-level input v	-		0.1 × (V1)		0.3 × (V+)	V
VIL.	Hysteresis	olage			200	0.0 x (V1)	mV
	SDA output-low	sink current		20	200		mA
	ODA Output-low	Silk current	I _O = -20 mA, V+ ≥ 2 V	20	0.15	0.4	V
V_{OL}	Low-level output	voltage	I _O = -15 mA, V+ < 2 V		0.13	0.2 × V+	V
	Serial bus input	leakage current	$0 \lor \le V_{\text{IN}} \le 3.6 \lor$	-1		1	μА
	Serial bus input		0 V 2 V _{IN} 2 3.0 V	-1	4	'	pF
DIGITAL	INPUTS (ADD)	сараскансе			4		рі
V _{IH}		voltago		0.7 × (V+)			V
	High-level input			-0.3		0.2 × (\/1)	V
V _{IL}	Low-level input v		0.7.5.7. < 3.6.7.			0.3 × (V+)	
	Input leakage cu		$0 \text{ V} \le V_{\text{IN}} \le 3.6 \text{ V}$	-1	4	'	μA
DICITAL	Input capacitanc				4		pF
DIGITAL	•	•	V 04V				A
1/	Output-low sink		V _{OL} = 0.4 V	6	0.45	0.4	mA V
V _{OL}	Low-level output	-	I _O = -6 mA		0.15	0.4	V
I _{OH}		t leakage current	V _O = V+			1	μА
POWER		voltogo rongo		4 7		2.0	
V+	Specified supply	vollage range	Active conversion level server	1.7	040	3.6	V
			Active conversion, local sensor		240	375	
			Active conversion, remote sensors		400	600	μΑ
IQ	Quiescent currer	nt	Standby mode (between conversions)		15	21	
			Shutdown mode, serial bus inactive		0.3	4	
			Shutdown mode, serial bus active, f _S = 400 kHz		120		μA
			Shutdown mode, serial bus active, f _S = 2.56 MHz		300		μΑ
POR	Power-on-reset t	threshold	Rising edge		1.5	1.65	V
			Falling edge	1	1.2	1.35	
POH	Power-on-reset h	nysteresis			0.2		V



7.6 Two-Wire Timing Requirements

at $T_A = -40$ °C to +125°C and V+ = 1.7 V to 3.6 V (unless otherwise noted) The master and the slave have the same V+ value. Values are based on statistical analysis of samples tested during initial

			MIN	MAX	UNIT
	001	Fast mode	0.001	0.4	MHz
f _{SCL}	SCL operating frequency	High-speed mode	0.001	2.56	IVIHZ
	Bus free time between stop and start	Fast mode	1300		
t _{BUF}	condition	High-speed mode	160		ns
	Hold time after repeated start condition.	Fast mode	600		
t _{HD;STA}	After this period, the first clock is generated.	High-speed mode	160		ns
	December of the state of the st	Fast mode	600		
SU;STA	Repeated start condition setup time	High-speed mode	160		ns
	0	Fast mode	600		
t _{su;sto}	Stop condition setup time	High-speed mode	160		ns
	Data hold time	Fast mode	0		⁽¹⁾ ns
t _{HD;DAT}		High-speed mode	0	130	\''ns
	Data valid time ⁽²⁾	Fast mode	0	900	
VD;DAT		High-speed mode	_	_	ns
	Data setup time	Fast mode	100		
SU;DAT		High-speed mode	20		ns
	SCL clock low period	Fast mode	1300		
t _{LOW}		High-speed mode	250		ns
	001 1 11:1	Fast mode	600		
HIGH	SCL clock high period	High-speed mode	60		ns
004	D. CHE	Fast mode	20 × (V+ / 5.5)	300	
t _F – SDA	Data fall time	High-speed mode		100	ns
		Fast mode		300	
_F , t _R – SCL	Clock fall and rise time	High-speed mode		40	ns
	Disc time for COL < 400 kHz	Fast mode		1000	
R	Rise time for SCL ≤ 100 kHz	High-speed mode			ns
	Carial hua timagust	Fast mode	15	20	
	Serial bus timeout	High-speed mode	15	20	ms

- The maximum t_{HD:DAT} can be 0.9 µs for fast mode, and is less than the maximum t_{VD:DAT} by a transition time.
- t_{VD:DAT} = time for data signal from SCL LOW to SDA output (HIGH to LOW, depending on which is worse).





Figure 1. Two-Wire Timing Diagram


TEXAS INSTRUMENTS

7.7 Typical Characteristics

at $T_A = 25$ °C and V+ = 3.6 V (unless otherwise noted)





Typical behavior of 75 devices over temperature at V+ = 1.8 V



Typical behavior of 75 devices over temperature at V+ = 1.8 V with the remote diode junction at 150° C.

図 2. Local Temperature Error vs Ambient Temperature





Typical behavior of 30 devices over temperature with V+ from 1.8 V to 3.6 V $\,$




図 4. Remote Temperature Error Power Supply Sensitivity vs 図 5. Remote Temperature Error vs Leakage Resistance





図 6. Remote Temperature Error vs Series Resistance




No physical series resistance on D+, D- pins during measurement


☑ 7. Remote Temperature Error vs Differential Capacitance



Typical Characteristics (continued)

at $T_A = 25$ °C and V+ = 3.6 V (unless otherwise noted)








図 9. Shutdown Quiescent Current vs SCL Clock Frequency





図 10. Quiescent Current vs Supply Voltage (at Default Conversion Rate of 16 Conversions Per Second)



☑ 11. Shutdown Quiescent Current vs Supply Voltage




8 Detailed Description

8.1 Overview

The TMP464 device is a digital temperature sensor that combines a local temperature measurement channel and four remote-junction temperature measurement channels in a VQFN-16 package. The device has a two-wire-interface that is compatible with I²C or SMBus interfaces and includes four pin-programmable bus address options. The TMP464 is specified over a local device temperature range from –40°C to +125°C. The TMP464 device also contains multiple registers for programming and holding configuration settings, temperature limits, and temperature measurement results. The TMP464 pinout includes THERM and THERM2 outputs that signal overtemperature events based on the settings of temperature limit registers.

8.2 Functional Block Diagram





8.3 Feature Description

8.3.1 Temperature Measurement Data

The local and remote temperature sensors have a resolution of 13 bits (0.0625°C). Temperature data that result from conversions within the default measurement range are represented in binary form, as shown in the *Standard Binary* column of 表 1. Negative numbers are represented in two's-complement format. The resolution of the temperature registers extends to 255.9375°C and down to -256°C, but the actual device is limited to ranges as specified in the *Electrical Characteristics* table to meet the accuracy specifications. The TMP464 device is specified for ambient temperatures ranging from -40°C to +125°C; parameters in the *Absolute Maximum Ratings* table must be observed to prevent damage to the device.

表 1. Temperature Data Format (Local and Remote Temperature)

TEMPERATURE	LOCAL OR REMOTE TEMPERATURE REGISTER VALUE (0.0625°C RESOLUTION)		
(°C)	STANDARD BINAR	Y ⁽¹⁾	
	BINARY	HEX	
-64	1110 0000 0000 0000	E0 00	
-50	1110 0111 0000 0000	E7 00	
-25	1111 0011 1000 0000	F3 80	
-0.1250	1111 1111 1111 0000	FF F0	
-0.0625	1111 1111 1111 1000	FF F8	
0	0000 0000 0000 0000	00 00	
0.0625	0000 0000 0000 1000	00 08	
0.1250	0000 0000 0001 0000	00 10	
0.1875	0000 0000 0001 1000	00 18	
0.2500	0000 0000 0010 0000	00 20	
0.3125	0000 0000 0010 1000	00 28	
0.3750	0000 0000 0011 0000	00 30	
0.4375	0000 0000 0011 1000	00 38	
0.5000	0000 0000 0100 0000	00 40	
0.5625	0000 0000 0100 1000	00 48	
0.6250	0000 0000 0101 0000	00 50	
0.6875	0000 0000 0101 1000	00 58	
0.7500	0000 0000 0110 0000	00 60	
0.8125	0000 0000 0110 1000	00 68	
0.8750	0000 0000 0111 0000	00 70	
0.9375	0000 0000 0111 1000	00 78	
1	0000 0000 1000 0000	00 80	
5	0000 0010 1000 0000	02 80	
10	0000 0101 0000 0000	05 00	
25	0000 1100 1000 0000	0C 80	
50	0001 1001 0000 0000	19 00	
75	0010 0101 1000 0000	25 80	
100	0011 0010 0000 0000	32 00	
125	0011 1110 1000 0000	3E 80	
127	0011 1111 1000 0000	3F 80	
150	0100 1011 0000 0000	4B 00	
175	0101 0111 1000 0000	57 80	
191	0101 1111 1000 0000	5F 80	

⁽¹⁾ Resolution is 0.0625°C per count. Negative numbers are represented in two's-complement format.



Both local and remote temperature data use two bytes for data storage with a two's-complement format for negative numbers. The high byte stores the temperature with 2°C resolution. The second or low byte stores the decimal fraction value of the temperature and allows a higher measurement resolution, as shown in 表 1. The measurement resolution for both the local and the remote channels is 0.0625°C.

8.3.2 Series Resistance Cancellation

Series resistance cancellation automatically eliminates the temperature error caused by the resistance of the routing to the remote transistor or by the resistors of the optional external low-pass filter. A total up to $1-k\Omega$ series resistance can be cancelled by the TMP464 device, which eliminates the need for additional characterization and temperature offset correction. See \boxtimes 6 for details on the effects of series resistance on sensed remote temperature error.

8.3.3 Differential Input Capacitance

The TMP464 device tolerates differential input capacitance of up to 1000 pF with minimal change in temperature error. The effect of capacitance on the sensed remote temperature error is illustrated in \boxtimes 7.

8.3.4 Sensor Fault

The TMP464 device can sense a fault at the D+ resulting from an incorrect diode connection. The TMP464 device can also sense an open circuit. Short-circuit conditions return a value of -256° C. The detection circuitry consists of a voltage comparator that trips when the voltage at D+ exceeds (V+) -0.3 V (typical). The comparator output is continuously checked during a conversion. If a fault is detected, then the RxOP bit in the Remote Channel Status register is set to 1.

When not using the remote sensor with the TMP464 device, the corresponding D+ and D- inputs must be connected together to prevent meaningless fault warnings.

8.3.5 THERM Functions

Operation of the THERM (pin 10) and THERM2 (pin 11) interrupt pins are shown in 2 12.

The hysteresis value is stored in the $\overline{\text{THERM}}$ Hysteresis register and applies to both the $\overline{\text{THERM}}$ and THERM2 interrupts.




図 12. THERM and THERM2 Interrupt Operation



8.4 Device Functional Modes

8.4.1 Shutdown Mode (SD)

The TMP464 shutdown mode enables the user to save maximum power by shutting down all device circuitry other than the serial interface, and reducing current consumption to typically less than 0.3 μ A; see \square 11. Shutdown mode is enabled when the shutdown bit (SD, bit 5) of the Configuration Register is HIGH; the device shuts down immediately. When the SD bit is LOW, the device maintains a continuous-conversion state.

8.5 Programming

8.5.1 Serial Interface

The TMP464 device operates only as a slave device on the two-wire bus (I²C or SMBus). Connections to either bus are made using the open-drain I/O lines, SDA, and SCL. The SDA and SCL pins feature integrated spike suppression filters and Schmitt triggers to minimize the effects of input spikes and bus noise. The TMP464 device supports the transmission protocol for fast (1 kHz to 400 kHz) and high-speed (1 kHz to 2.56 MHz) modes. All data bytes are transmitted MSB first.

While the TMP464 device is unpowered bus traffic on SDA and SCL may continue without any adverse effects to the communication or to the TMP464 device itself. As the TMP464 device is powering up, the device does not load the bus, and as a result the bus traffic may continue undisturbed.

8.5.1.1 Bus Overview

The TMP464 device is compatible with the I^2C or SMBus interface. In I^2C or SMBus protocol, the device that initiates the transfer is called a *master*, and the devices controlled by the master are *slaves*. The bus must be controlled by a master device that generates the serial clock (SCL), controls the bus access, and generates the start and stop conditions.

To address a specific device, a start condition is initiated. A start condition is indicated by pulling the data line (SDA) from a high-to-low logic level when SCL is high. All slaves on the bus shift in the slave address byte, with the last bit indicating whether a read or write operation is intended. During the ninth clock pulse, the addressed slave responds to the master by generating an *acknowledge* (ACK) bit and pulling SDA low.

Data transfer is then initiated and sent over eight clock pulses followed by an acknowledge bit (ACK). During data transfer, SDA must remain stable when SCL is high. A change in SDA when SCL is high is interpreted as a control signal. The TMP464 device has a word register structure (16-bit wide), with data writes always requiring two bytes. Data transfer occurs during the ACK at the end of the second byte.

After all data are transferred, the master generates a stop condition. A stop condition is indicated by pulling SDA from low to high when SCL is high.



8.5.1.2 Bus Definitions

The TMP464 device has a two-wire interface that is compatible with the I²C or SMBus interface. ☑ 13 through ☑ 18 illustrate the timing for various operations on the TMP464 device. The bus definitions are as follows:

Bus Idle: Both SDA and SCL lines remain high.

Start Data Transfer: A change in the state of the SDA line (from high to low) when the SCL line is high defines a start condition. Each data transfer initiates with a start condition.

Stop Data Transfer: A change in the state of the SDA line (from low to high) when the SCL line is high defines a stop condition. Each data transfer terminates with a repeated start or stop condition.

Data Transfer: The number of data bytes transferred between a start and stop condition is not limited and is determined by the master device. The receiver acknowledges the data transfer.

Acknowledge: Each receiving device, when addressed, is obliged to generate an acknowledge bit. A device that acknowledges must pull down the SDA line during the acknowledge clock pulse in such a way that the SDA line is stable low during the high period of the acknowledge clock pulse. Take setup and hold times into account. On a master receive, data transfer termination can be signaled by the master generating a not-acknowledge on the last byte that is transmitted by the slave.




図 13. Two-Wire Timing Diagram for Write Pointer Byte





図 14. Two-Wire Timing Diagram for Write Pointer Byte and Value Word





(1) The master must leave SDA high to terminate a single-byte read operation.

図 15. Two-Wire Timing Diagram for Pointer Set Followed by a Repeat Start and Single-Byte Read Format




図 16. Two-Wire Timing Diagram for Pointer Byte Set Followed by a Repeat Start and Word (Two-Byte) Read






図 17. Two-Wire Timing Diagram for Pointer Byte Set Followed by a Repeat Start and Multiple-Word (N-Word) Read




図 18. Two-Wire Timing Diagram for Multiple-Word (N-Word) Read Without a Pointer Byte Set



8.5.1.3 Serial Bus Address

To communicate with the TMP464 device, the master must first address slave devices using a slave address byte. The slave address byte consists of seven address bits and a direction bit indicating the intent of executing a read or write operation. The TMP464 device allows up to four devices to be addressed on a single bus. The assigned device address depends on the ADD pin connection as described in 表 2.

表 2.	TMP464	Slave	Address	Options
------	---------------	-------	----------------	----------------

ADD PIN CONNECTION	SLAVE ADDRESS							
ADD FIN CONNECTION	BINARY	HEX						
GND	1001000	48						
V+	1001001	49						
SDA	1001010	4A						
SCL	1001011	4B						

8.5.1.4 Read and Write Operations

Accessing a particular register on the TMP464 device is accomplished by writing the appropriate value to the pointer register. The value for the pointer register is the first byte transferred after the slave address byte with the R/W bit low. Every write operation to the TMP464 device requires a value for the pointer register (see 2 14).

The TMP464 registers can be accessed with block or single register reads. Block reads are only supported for pointer values 80h to 84h. Registers at 80h through 84h mirror the Remote and Local Temperature registers (00h to 04h). Pointer values 00h to 04h are for single register reads.

8.5.1.4.1 Single Register Reads

When reading from the TMP464 device, the last value stored in the pointer register by a write operation is used to determine which register is read by a read operation. To change which register is read for a read operation, a new value must be written to the pointer register. This transaction is accomplished by issuing a slave address byte with the R/W bit low, followed by the pointer register byte; no additional data are required. The master can then generate a start condition and send the slave address byte with the R/W bit high to initiate the read command; see 2 15 through 2 17 for details of this sequence.

If repeated reads from the same register are desired, continually sending the pointer register bytes is not necessary because the TMP464 device retains the pointer register value until the value is changed by the next write operation. The register bytes are sent by the MSB first, followed by the LSB. If only one byte is read (MSB), a consecutive read of TMP464 device results in the MSB being transmitted first. The LSB can only be accessed through two-byte reads.

The master terminates a read operation by issuing a *not-acknowledge* (NACK) command at the end of the last byte to be read or transmitting a stop condition. For a single-byte operation, the master must leave the SDA line high during the acknowledge time of the first byte that is read from the slave.

The TMP464 register structure has a word (two-byte) length, so every write transaction must have an even number of bytes (MSB and LSB) following the pointer register value (see 214). Data transfers occur during the ACK at the end of the second byte or LSB. If the transaction does not finish, signaled by the ACK at the end of the second byte, then the data is ignored and not loaded into the TMP464 register. Read transactions do not have the same restrictions and may be terminated at the end of the last MSB.

8.5.1.4.2 Block Register Reads

The TMP464 supports block mode reads at address 80h through 84h for temperature results alone. Setting the pointer register to 80h signals to the TMP464 device that a block of more than two bytes must be transmitted before a stop is issued. In this mode, the TMP464 device auto increments the internal pointer. If the transmission is terminated before register 84h is read, the pointer increments so a consecutive read (without a pointer set) can access the next register.



8.5.1.5 Timeout Function

The TMP464 device resets the serial interface if either SCL or SDA are held low for 17.5 ms (typical) between a start and stop condition. If the TMP464 device is holding the bus low, the device releases the bus and waits for a start condition. To avoid activating the timeout function, maintain a communication speed of at least 1 kHz for the SCL operating frequency.

8.5.1.6 High-Speed Mode

For the two-wire bus to operate at frequencies above 1 MHz, the master device must issue a high-speed mode (HS-mode) master code (0000 1xxx) as the first byte after a start condition to switch the bus to high-speed operation. The TMP464 device does not acknowledge the master code byte, but switches the input filters on SDA and SCL and the output filter on SDA to operate in HS-mode, allowing transfers up to 2.56 MHz. After the HS-mode master code is issued, the master transmits a two-wire slave address to initiate a data transfer operation. The bus continues to operate in HS-mode until a stop condition occurs on the bus. Upon receiving the stop condition, the TMP464 device switches the input and output filters back to fast mode.

8.5.2 TMP464 Register Reset

The TMP464 registers can be software reset by setting bit 15 of the Software Reset register (20h) to 1. This software reset restores the power-on-reset state to all TMP464 registers and aborts any conversion in progress.

8.5.3 Lock Register

All of the configuration and limit registers may be locked for writes (making the registers write-protected), which decreases the chance of software runaway from issuing false changes to these registers. The *Lock* column in \$\frac{\pi}{\pi}\$ identifies which registers may be locked. Lock mode does not effect read operations. To activate the lock mode, Lock Register C4h must be set to 0x5CA6. The lock only remains active while the TMP464 device is powered up. Because the TMP464 device does not contain nonvolatile memory, the settings of the configuration and limit registers are lost once a power cycle occurs regardless if the registers are locked or unlocked.

In lock mode, the TMP464 device ignores a write operation to configuration and limit registers except for Lock Register C4h. The TMP464 device does not acknowledge the data bytes during a write operation to a locked register. To unlock the TMP464 registers, write 0xEB19 to register C4h. The TMP464 device powers up in locked mode, so the registers must be unlocked before the registers accept writes of new data.



www.tij.co.jp

8.6 Register Maps

表 3. Register Map

PTR	POR	Lock					TMF	2464 Fu	nctio	nal Re	gisters	- BIT C	DESCR	PTION					DEGICTED DEGODINE
(HEX)	(HEX)	(Y/N)	15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0	REGISTER DESCRIPTION
00	0000	N/A	LT12	LT11	LT1 0	LT9	LT8	LT7	LT6	LT5	LT4	LT3	LT2	LT1	LT0	0 ⁽¹⁾	0	0	Local temperature
01	0000	N/A	RT12	RT11	RT 10	RT9	RT8	RT7	RT 6	RT 5	RT4	RT3	RT2	RT1	RT0	0	0	0	Remote temperature 1
02	0000	N/A	RT12	RT11	RT 10	RT9	RT8	RT7	RT 6	RT 5	RT4	RT3	RT2	RT1	RT0	0	0	0	Remote temperature 2
03	0000	N/A	RT12	RT11	RT 10	RT9	RT8	RT7	RT 6	RT 5	RT4	RT3	RT2	RT1	RT0	0	0	0	Remote temperature 3
04	0000	N/A	RT12	RT11	RT 10	RT9	RT8	RT7	RT 6	RT 5	RT4	RT3	RT2	RT1	RT0	0	0	0	Remote temperature 4
20	0000	N/A	RST	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	Software Reset Register
21	N/A	N/A	0	0	0	0	R4TH	R3TH	R2 TH	R1 TH	LTH	0	0	0	0	0	0	0	THERM Status
22	N/A	N/A	0	0	0	0	R4TH 2	R3TH 2	R2 TH 2	R1 TH 2	LTH2	0	0	0	0	0	0	0	THERM2 Status
23	N/A	N/A	0	0	0	0	R4O PN	R3O PN	R2 OP N	R1 OP N	0	0	0	0	0	0	0	0	Remote channel OPEN Status
30	0F9C	Y	0	0	0	0	REN4	REN3	RE N2	RE N1	LEN	os	SD	CR2	CR1	CR0	BU SY	0	Configuration Register (Enables, OneShot, ShutDown, ConvRate, BUSY)
38	0080	Y	0	HYS1 1	HY S10	HYS9	HYS8	HYS7	HY S6	HY S5	HYS4	0	0	0	0	0	0	0	THERM hysteresis
39	3E80 (125°C)	Y	LTH1_ 12	LTH1 _11	LT H1 _10	LTH1 _09	LTH1 _08	LTH1 _07	LT H1 _06	LT H1 _05	LTH1 _04	LTH1 _03	0	0	0	0	0	0	Local temp THERM limit
ЗА	7FC0 (225.5°C)	Y	LTH2_ 12	LTH2 _11	LT H2 _10	LTH2 _09	LTH2 _08	LTH2 _07	LT H2 _06	LT H2 _05	LTH2 _04	LTH2 _03	0	0	0	0	0	0	Local temp THERM2 limit
40	0000	Υ	ROS12	ROS 12 ⁽²⁾	RO S10	ROS 9	ROS 8	ROS 7	RO S6	RO S5	ROS 4	ROS 3	ROS 2	ROS 1	ROS0	0	0	0	Remote temp 1 offset
41	0000	Y	RNC7	RNC 6	RN C5	RNC 4	RNC 3	RNC 2	RN C1	RN C0	0	0	0	0	0	0	0	0	Remote temp 1 η-factor correction

⁽¹⁾ Register bits highlighted in purple are reserved for future use and always reports 0; writes to these bits are ignored.(2) Register bits highlighted in green show sign extended values.

TEXAS INSTRUMENTS

Register Maps (continued)

表 3. Register Map (continued)

PTR	POR	Lock					TMF	464 Fu	nctio	nal Re	egisters	- BIT C	ESCRI	PTION					REGISTER DESCRIPTION
(HEX)	(HEX)	(Y/N)	15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0	REGISTER DESCRIPTION
42	3E80	Υ	RTH1_ 12	RTH1 _11	RT H1 _10	RTH1 _09	RTH1 _08	RTH1 _07	RT H1 _06	RT H1 _05	RTH1 _04	RTH1 _03	0	0	0	0	0	0	Remote temp 1 THERM limit
43	7FC0	Υ	RTH2_ 12	RTH2 _11	RT H2 _10	RTH2 _09	RTH2 _08	RTH2 _07	RT H2 _06	RT H2 _05	RTH2 _04	RTH2 _03	0	0	0	0	0	0	Remote temp 1 THERM2 limit
48	0000	Y	ROS12	ROS 12	RO S10	ROS 9	ROS 8	ROS 7	RO S6	RO S5	ROS 4	ROS 3	ROS 2	ROS 1	ROS0	0	0	0	Remote temp 2 offset
49	0000	Y	RNC7	RNC 6	RN C5	RNC 4	RNC 3	RNC 2	RN C1	RN C0	0	0	0	0	0	0	0	0	Remote temp 2 η-factor correction
4A	3E80	Y	RTH1_ 12	RTH1 _11	RT H1 _10	RTH1 _09	RTH1 _08	RTH1 _07	RT H1 _06	RT H1 _05	RTH1 _04	RTH1 _03	0	0	0	0	0	0	Remote temp 2 THERM limit
4B	7FC0	Y	RTH2_ 12	RTH2 _11	RT H2 _10	RTH2 _09	RTH2 _08	RTH2 _07	RT H2 _06	RT H2 _05	RTH2 _04	RTH2 _03	0	0	0	0	0	0	Remote temp 2 THERM2 limit
50	0000	Υ	ROS12	ROS 12	RO S10	ROS 9	ROS 8	ROS 7	RO S6	RO S5	ROS 4	ROS 3	ROS 2	ROS 1	ROS0	0	0	0	Remote temp 3 offset
51	0000	Y	RNC7	RNC 6	RN C5	RNC 4	RNC 3	RNC 2	RN C1	RN C0	0	0	0	0	0	0	0	0	Remote temp 3 η-factor correction
52	3E80	Y	RTH1_ 12	RTH1 _11	RT H1 _10	RTH1 _09	RTH1 _08	RTH1 _07	RT H1 _06	RT H1 _05	RTH1 _04	RTH1 _03	0	0	0	0	0	0	Remote temp 3 THERM limit
53	7FC0	Y	RTH2_ 12	RTH2 _11	RT H2 _10	RTH2 _09	RTH2 _08	RTH2 _07	RT H2 _06	RT H2 _05	RTH2 _04	RTH2 _03	0	0	0	0	0	0	Remote temp 3 THERM2 limit
58	0000	Y	ROS12	ROS 12	RO S10	ROS 9	ROS 8	ROS 7	RO S6	RO S5	ROS 4	ROS 3	ROS 2	ROS 1	ROS0	0	0	0	Remote temperature 4 offset
59	0000	Υ	RNC7	RNC 6	RN C5	RNC 4	RNC 3	RNC 2	RN C1	RN C0	0	0	0	0	0	0	0	0	Remote temp 4 η-factor correction
5A	3E80	Υ	RTH1_ 12	RTH1 _11	RT H1 _10	RTH1 _09	RTH1 _08	RTH1 _07	RT H1 _06	RT H1 _05	RTH1 _04	RTH1 _03	0	0	0	0	0	0	Remote temp 4 THERM limit
5B	7FC0	Y	RTH2_ 12	RTH2 _11	RT H2 _10	RTH2 _09	RTH2 _08	RTH2 _07	RT H2 _06	RT H2 _05	RTH2 _04	RTH2 _03	0	0	0	0	0	0	Remote temp 4 THERM2 limit
80	0000	N/A	LT12	LT11	LT1 0	LT9	LT8	LT7	LT6	LT5	LT4	LT3	LT2	LT1	LT0	0	0	0	Local temperature (Block read range - auto increment pointer register)



Register Maps (continued)

表 3. Register Map (continued)

PTR	POR	Lock		TMP464 Functional Registers - BIT DESCRIPTION										DECICTED DESCRIPTION					
(HEX)	(HEX)	(Y/N)	15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0	REGISTER DESCRIPTION
81	0000	N/A	RT12	RT11	RT 10	RT9	RT8	RT7	RT 6	RT 5	RT4	RT3	RT2	RT1	RT0	0	0	0	Remote temperature 1 (Block read range - auto increment pointer register)
82	0000	N/A	RT12	RT11	RT 10	RT9	RT8	RT7	RT 6	RT 5	RT4	RT3	RT2	RT1	RT0	0	0	0	Remote temperature 2 (Block read range - auto increment pointer register)
83	0000	N/A	RT12	RT11	RT 10	RT9	RT8	RT7	RT 6	RT 5	RT4	RT3	RT2	RT1	RT0	0	0	0	Remote temperature 3 (Block read range - auto increment pointer register)
84	0000	N/A	RT12	RT11	RT 10	RT9	RT8	RT7	RT 6	RT 5	RT4	RT3	RT2	RT1	RT0	0	0	0	Remote temperature 4 (Block read range - auto increment pointer register)
C4	8000	N/A		Write 0x5CA6 to lock registers and 0xEB19 to unlock registers								Lock Registers after initialization							
				Read back: locked 0x8000; unlocked 0x0000															
FE	5449	N/A	0	1	0	1	0	1	0	0	0	1	0	0	1	0	0	1	Manufacturers Identification Register
FF	1468	N/A	0	0	0	1	0	1	0	0	0	1	1	0	1	0	0	0	Device Identification/Revision Register



8.6.1 Register Information

The TMP464 device contains multiple registers for holding configuration information, temperature measurement results, and status information. These registers are described in 図 19 and 表 3.

8.6.1.1 Pointer Register

図 19 shows the internal register structure of the TMP464 device. The 8-bit pointer register addresses a given data register. The pointer register identifies which of the data registers must respond to a read or write command on the two-wire bus. This register is set with every write command. A write command must be issued to set the proper value in the pointer register before executing a read command. 表 3 describes the pointer register and the internal structure of the TMP464 registers. The power-on-reset (POR) value of the pointer register is 00h (0000 0000b). 表 3 lists a summary of the pointer values for the different registers. Writing data to unassigned pointer values are ignored and does not affect the operation of the device. Reading an unassigned register returns undefined data and is ACKed.




図 19. TMP464 Internal Register Structure

8.6.1.2 Local and Remote Temperature Value Registers

The TMP464 device has multiple 16-bit registers that hold 13-bit temperature measurement results. The 13 bits of the local temperature sensor result are stored in register 00h. The 13 bits of the four remote temperature sensor results are stored in registers 01h through 04h. The four assigned LSBs of both the local (LT3:LT0) and remote (RT3:RT0) sensors indicate the temperature value after the decimal point (for example, if the temperature result is 10.0625°C, then the high byte is 0000 0101 and the low byte is 0000 1000). These registers are read-only and are updated by the ADC each time a temperature measurement is complete. Asynchronous reads are supported, so a read operation can occur at any time and results in valid conversion results being transmitted once the first conversion is complete after power up for the channel being accessed. If after power up a read is initiated before a conversion is complete, the read operation results in all zeros (0x0000).

8.6.1.3 Software Reset Register

The Software Reset Register allows the user to reset the TMP464 registers through software by setting the reset bit (RST, bit 15) to 1. The power-on-reset value for this register is 0x0000. Resets are ignored when the device is in lock mode, so writing a 1 to the RST bit does not reset any registers.



表 4. Software Reset Register Format

	STATUS REGISTER (READ = 20h, WRITE = 20h, POR = 0x0000)									
BIT NUMBER BIT NAME FUNCTION										
15	RST	1 software reset device; writing a value of 0 is ignored								
14-0	0	Reserved for future use; always reports 0								

8.6.1.4 THERM Status Register

The THERM Status register reports the state of the THERM limit comparators for local and four remote temperatures. 表 5 lists the status register bits. The THERM Status register is read-only and is read by accessing pointer address 21h.

表 5. THERM Status Register Format

	THERM STATUS REGISTER (READ = 21h, WRITE = N/A)									
BIT NUMBER	BIT NAME	FUNCTION								
15:12	0	Reserved for future use; always reports 0.								
11	R4TH	1 when Remote 4 exceeds the THERM limit								
10	R3TH	1 when Remote 3 exceeds the THERM limit								
9	R2TH	1 when Remote 2 exceeds the THERM limit								
8	R1TH	1 when Remote 1 exceeds the THERM limit								
7	LTH	1 when Local sensor exceeds the THERM limit								
6:0	0	Reserved for future use; always reports 0.								

The R4TH:R1TH and LTH flags are set when the corresponding temperature exceeds the respective programmed THERM limit (39h, 42h, 4Ah, 52h, and 5Ah). These flags are reset automatically when the temperature returns below the THERM limit minus the value set in the THERM Hysteresis register (38h). The THERM output goes low in the case of overtemperature on either the local or remote channels, and goes high as soon as the measurements are less than the THERM limit minus the value set in the THERM Hysteresis register. The THERM Hysteresis register (38h) allows hysteresis to be added so that the flag resets and the output goes high when the temperature returns to or goes below the limit value minus the hysteresis value.



8.6.1.5 THERM2 Status Register

The THERM2 Status register reports the state of the THERM2 limit comparators for local and remote 1-4 temperatures. 表 6 lists the status register bits. The THERM2 Status register is read-only and is read by accessing pointer address 22h.

表 6. THERM2 Status Register Format

	THERM2 STATUS REGISTER (READ = 22h, WRITE = N/A)								
BIT NUMBER	BIT NAME	FUNCTION							
15:12	0	Reserved for future use; always reports 0.							
11	R4TH2	1 when Remote 4 exceeds the THERM2 limit							
10	R3TH2	1 when Remote 3 exceeds the THERM2 limit							
9	R2TH2	1 when Remote 2 exceeds the THERM2 limit							
8	R1TH2	1 when Remote 1 exceeds the THERM2 limit							
7	LTH2	1 when Local Sensor exceeds the THERM2 limit							
6:0	0	Reserved for future use; always reports 0.							

The R4TH2:R1TH2 and LTH2 flags are set when the corresponding temperature exceeds the respective programmed THERM2 limit (3Ah, 43h, 4Bh, 53h, 5Bh, 63h, 6Bh, 73h, 7Bh). These flags are reset automatically when the temperature returns below the THERM2 limit minus the value set in the THERM Hysteresis register (38h). The THERM2 output goes low in the case of overtemperature on either the local or remote channels, and goes high as soon as the measurements are less than the THERM2 limit minus the value set in the THERM Hysteresis register. The THERM Hysteresis register (38h) allows hysteresis to be added so that the flag resets and the output goes high when the temperature returns to or goes below the limit value minus the hysteresis value.

8.6.1.6 Remote Channel Open Status Register

The Remote Channel Open Status register reports the state of the connection of remote channels one through four. 表 7 lists the status register bits. The Remote Channel Open Status register is read-only and is read by accessing pointer address 23h.

表 7. Remote Channel Open Status Register Format

	REMOTE CHANNEL OPEN STATUS REGISTER (READ = 23h, WRITE = N/A)									
BIT NUMBER	BIT NAME	FUNCTION								
15:12	0	Reserved for future use; always reports 0.								
11	R4OPEN	1 when Remote 4 channel is an open circuit								
10	R3OPEN	1 when Remote 3 channel is an open circuit								
9	R2OPEN	1 when Remote 2 channel is an open circuit								
8	R10PEN	1 when Remote 1 channel is an open circuit								
7:0	0	Reserved for future use; always reports 0.								

The R4OPEN:R1OPEN bits indicate an open-circuit condition on <u>remote</u> sen<u>sors four</u> through one, respectively. The setting of these flags does not directly affect the state of the <u>THERM or THERM2</u> output pins. Indirectly, the <u>temperature reading(s)</u> may be erroneous and exceed the respective <u>THERM</u> and <u>THERM2</u> limits, activating the <u>THERM or THERM2</u> output pins.

0



8.6.1.7 Configuration Register

0

The Configuration Register sets the conversion rate, starts one-shot conversion of all enabled channels, enables conversion the temperature channels, controls the shutdown mode and reports when a conversion is in process. The Configuration Register is set by writing to pointer address 30h, and is read from pointer address 30h. 表 8 summarizes the bits of the Configuration Register.

CONFIGURATION REGISTER (READ = 30h, WRITE = 30h, POR = 0x0F9C) **BIT NUMBER NAME FUNCTION POWER-ON-RESET VALUE** Reserved for future use; always 0 15:12 0000 reports 0 1 = enable respective remote 11:8 REN4:REN1 1111 channel 4 through 1 conversions 1 = enable local channel 7 1 LEN conversion 1 = start one-shot conversion on os 0 enabled channels 5 SD 1 = enables device shutdown 0 Conversion rate control bits; control conversion rates for all 4:2 CR2:CR0 enabled channels from 16 111 seconds to continuous conversion 1 when the ADC is converting **BUSY** 0 (read-only bit ignores writes)

表 8. Configuration Register Bit Descriptions

The Remote Enable four through one (REN4:REN1, bits 11:8) bits enable conversions on the respective remote channels. The Local Enable (LEN, bit 7) bit enables conversions of the local temperature channel. If all LEN and REN are set to 1 (default), this enables the ADC to convert the local and all remote temperatures. If the LEN is set to 0, the local temperature conversion is skipped. Similarly if a REN is set to 0, that remote temperature conversion channel is skipped. The TMP464 device steps through each enabled channel in a round-robin fashion in the following order: LOC, REM1, REM2, REM4, LOC, REM1, and so on. All local and remote temperatures are converted by the internal ADC by default after power up. The configuration register LEN and REN bits can be configured to save power by reducing the total ADC conversion time for applications that do not require all of the four remote and local temperature information. Note writing all zeros to REN4:REN1 and LEN has the same effect as SD = 1 and OS = 0.

The shutdown bit (SD, bit 5) enables or disables the temperature-measurement circuitry. If SD = 0 (default), the TMP464 device converts continuously at the rate set in the conversion rate register. When SD is set to 1, the TMP464 device immediately stops the conversion in progress and instantly enters shutdown mode. When SD is set to 0 again, the TMP464 device resumes continuous conversions starting with the local temperature.

The BUSY bit = 1 if the ADC is making a conversion. This bit is set to 0 if the ADC is not converting.

Reserved

After the TMP464 device is in shutdown mode, writing a 1 to the one-shot (OS, bit 6) bit starts a single ADC conversion of all the enabled temperature channels. This write operation starts one conversion and comparison cycle on either the four remote and one local sensor or any combination of sensors, depending on the LEN and REN values in the Configuration Register (read address 30h). The TMP464 device returns to shutdown mode when the cycle is complete. 表 9 details the interaction of the SD, OS, LEN, and REN bits.

WRITE **READ FUNCTION REN[8:1], LEN** os SD **REN[8:1], LEN** os SD All 0 All 0 0 1 Shutdown 0 0 At least 1 enabled Written value 0 Continuous conversion At least 1 enabled 0 1 Written value 0 1 Shutdown 1 1 1 At least 1 enabled 1 Written value One-shot conversion

表 9. Conversion Modes



The conversion rate bits control the rate that the conversions occur (CR2:CR0, bits 4:2). The value of CR2:CR0 bits controls the idle time between conversions but not the conversion time itself, which allows the TMP464 device power dissipation to be balanced with the update rate of the temperature register. 表 10 describes the mapping for CR2:CR0 to the conversion rate or temperature register update rate.

表 1	I O	Con	vers	ion	Rate

CR2:CR0	DECIMAL VALUE	FREQUENCY (Hz)	TIME (s)
000	0	0.0625	16
001	1	0.125	8
010	2	0.25	4
011	3	0.5	2
100	4	1	1
101	5	2	0.5
110	6	4	0.25
111	7	Continuous conversion; depends on numb	

表 11. Continuous Conversion Times

NUMBER OF REMOTE CHANNELS ENABLED	CONVERSION TIME (ms)					
NUMBER OF REMOTE CHANNELS ENABLED	LOCAL DISABLED	LOCAL ENABLED				
0	0	15.5				
1	15.8	31.3				
2	31.6	47.1				
3	47.4	62.9				
4	63.2	78.7				

The remaining bits of the configuration register are reserved and must always be set to 0. The POR value for this register is 0x0F9C.

8.6.1.8 η-Factor Correction Register

The TMP464 device allows for a different η -factor value to be used for converting remote channel measurements to temperature for each temperature channel. There are four η -Factor Correction registers assigned: one to each of the remote input channels (addresses 41h, 49h, 51h, and 59h). Each remote channel uses sequential current excitation to extract a differential V_{BE} voltage measurement to determine the temperature of the remote transistor. \vec{x} 1 shows this voltage and temperature.

$$V_{BE2} - V_{BE1} = \frac{\eta kT}{q} ln \left(\frac{l_2}{l_1} \right)$$
(1)

The value η in $\vec{\pm}$ 1 is a characteristic of the particular transistor used for the remote channel. The POR value for the TMP464 device is η = 1.008. The value in the η -Factor Correction register can be used to adjust the effective η -factor, according to $\vec{\pm}$ 2 and $\vec{\pm}$ 3.

$$\eta_{\text{eff}} = \left(\frac{1.008 \times 2088}{2088 + N_{\text{ADJUST}}}\right) \tag{2}$$

$$N_{ADJUST} = \left(\frac{1.008 \times 2088}{\eta_{eff}}\right) - 2088 \tag{3}$$

The η -factor correction value must be stored in a two's-complement format, which yields an effective data range from –128 to +127. The POR value for each register is 0000h, which does not affect register values unless a different value is written to the register. The resolution of the η -factor register changes linearly as the code changes and has a range from 0.0004292 to 0.0005476, with an average of 0.0004848.



表 12. η-Factor Range

N _{ADJUST} ONLY BITS 15 TO 8 IN THE REGISTER ARE SHOWN									
BINARY	HEX	DECIMAL	η						
0111 1111	7F	127	0.950205						
0000 1010	0A	10	1.003195						
0000 1000	08	8	1.004153						
0000 0110	06	6	1.005112						
0000 0100	04	4	1.006073						
0000 0010	02	2	1.007035						
0000 0001	01	1	1.007517						
0000 0000	00	0	1.008						
1111 1111	FF	-1	1.008483						
1111 1110	FE	-2	1.008966						
1111 1100	FC	-4	1.009935						
1111 1010	FA	-6	1.010905						
1111 1000	F8	-8	1.011877						
1111 0110	F6	-10	1.012851						
1000 0000	80	-128	1.073829						

8.6.1.9 Remote Temperature Offset Register

The offset registers allow the TMP464 device to store any system offset compensation value that may result from precision calibration. The value in these registers is added to the remote temperature results upon every conversion. Each of the four temperature channels have an independent assigned offset register (addresses 40h, 48h, 50h, and 58h). Combined with the independent η -factor corrections, this function allows for very accurate system calibration over the entire temperature range for each remote channel. The format of these registers is the same as the temperature value registers with a range from +127.9375 to -128. Take care to program this register with sign extension, as values above +127.9375 and below -128 are not supported.

8.6.1.10 THERM Hysteresis Register

The THERM Hysteresis register (address 38h) sets the value of the hysteresis used by the temperature comparison logic. All temperature reading comparisons have a common hysteresis. Hysteresis prevents oscillations from occurring on the THERM and THERM2 outputs as the measured temperature approaches the comparator threshold (see the THERM Functions section). The resolution of the THERM Hysteresis register is 1°C and ranges from 0°C to 255°C.

8.6.1.11 Local and Remote THERM and THERM2 Limit Registers

Each of the four remote and the <u>local temperature</u> channels has associated independent <u>THERM</u> and <u>THERM2</u> Limit registers. There are five <u>THERM</u> registers (addresses 39h, 42h, 4Ah, 52h, and 5Ah) and five <u>THERM2</u> registers (addresses 39h, 43h, 4Bh, and 53h), 10 registers in total. The resolution of these registers is 0.5°C and ranges from +255.5°C to -255°C. See the <u>THERM Functions</u> section for more information.

Setting a THERM limit to 255.5°C disables the THERM limit comparison for that particular channel and disables the limit flag from being set in the THERM Status register. This prevents the associated channel from activating the THERM output. THERM2 limits, status, and outputs function similarly.

8.6.1.12 Block Read - Auto Increment Pointer

Block reads can be initiated by setting the pointer register to 80h to 84h. The temperature results are mirrored at pointer addresses 80h to 84h; temperature results for all the channels can be read with one read transaction. Setting the pointer register to any address from 80h to 84h signals to the TMP464 device that a block of more than two bytes must be transmitted before a design stop is issued. In block read mode, the TMP464 device auto increments the pointer address.



8.6.1.13 Lock Register

Register C4h allows the device configuration and limit registers to lock, as shown by the *Lock* column in 表 3. To lock the registers, write 0x5CA6. To unlock the registers, write 0xEB19. When the lock function is enabled, reading the register yields 0x8000; when unlocked, 0x0000 is transmitted.

8.6.1.14 Manufacturer and Device Identification Plus Revision Registers

The TMP464 device allows the two-wire bus controller to query the device for manufacturer and device identifications (IDs) to enable software identification of the device at the particular two-wire bus address. The manufacturer ID is obtained by reading from pointer address FEh; the device ID is obtained from register FFh. Note that the most significant byte of the Device ID register identifies the TMP464 device revision level. The TMP464 device reads 0x5449 for the manufacturer code and 0x1468 for the device ID code for the first release.



9 Application and Implementation


注

Information in the following applications sections is not part of the TI component specification, and TI does not warrant its accuracy or completeness. TI's customers are responsible for determining suitability of components for their purposes. Customers should validate and test their design implementation to confirm system functionality.

9.1 Application Information

The TMP464 device requires a transistor connected between the D+ and D- pins for remote temperature measurement. Tie the D+ pin to D- if the remote channel is not used and only the local temperature is measured. The SDA, ALERT, and $\overline{\text{THERM}}$ pins (and SCL, if driven by an open-drain output) require pullup resistors as part of the communication bus. TI recommends a 0.1- μ F power-supply decoupling capacitor for local bypassing. 20 and 21 illustrate the typical configurations for the TMP464 device.

9.2 Typical Application




Copyright © 2017, Texas Instruments Incorporated

- (1) The diode-connected configuration provides better settling time. The transistor-connected configuration provides better series resistance cancellation. TI recommends a MMBT3904 or MMBT3906 transistor with an η-factor of 1.008.
- (2) R_S (optional) is < 1 kΩ in most applications. R_S is the combined series resistance connected externally to the D+, D- pins. R_S selection depends on the application.
- (3) C_{DIFF} (optional) is < 1000 pF in most applications. C_{DIFF} selection depends on the application; see ☑ 7.
- (4) Unused diode channels must be tied to D-.

図 20. TMP464 Basic Connections Using a Discrete Remote Transistor



Typical Application (continued)



Copyright © 2017, Texas Instruments Incorporated

図 21. TMP464 Remote Transistor Configuration Options

9.2.1 Design Requirements

The TMP464 device is designed to be used with either discrete transistors or substrate transistors built into processor chips, field programmable gate arrays (FPGAs), and application-specific integrated circuits (ASICs); see 21. Either NPN or PNP transistors can be used, as long as the base-emitter junction is used as the remote temperature sensor. NPN transistors must be diode-connected. PNP transistors can either be transistor-or diode-connected (see 21).

Errors in remote temperature sensor readings are typically the consequence of the ideality factor (η -factor) and current excitation used by the TMP464 device versus the manufacturer-specified operating current for a given transistor. Some manufacturers specify a high-level and low-level current for the temperature-sensing substrate transistors. The TMP464 uses 7.5 μ A (typical) for I_{LOW} and 120 μ A (typical) for I_{HIGH}.

The ideality factor (η -factor) is a measured characteristic of a remote temperature sensor diode as compared to an ideal diode. The TMP464 allows for different η -factor values; see the η -Factor Correction Register section.

The η-factor for the TMP464 device is trimmed to 1.008. For transistors that have an ideality factor that does not match the TMP464 device, \pm 4 can be used to calculate the temperature error.

注

For 式 4 to be used correctly, the actual temperature (°C) must be converted to Kelvin (K).



Typical Application (continued)

$$T_{ERR} = \left(\frac{\eta - 1.008}{1.008}\right) \times \left(273.15 + T(^{\circ}C)\right)$$

where

- T_{ERR} = error in the TMP464 device because η ≠ 1.008
- η = ideality factor of the remote temperature sensor

In \pm 4, the degree of delta is the same for °C and K.

For $\eta = 1.004$ and $T(^{\circ}C) = 100^{\circ}C$:

$$T_{ERR} = \left(\frac{1.004 - 1.008}{1.008}\right) \times (273.15 + 100^{\circ}C)$$

$$T_{ERR} = -1.48^{\circ}C$$
(5)

If a discrete transistor is used as the remote temperature sensor with the TMP464 device, then select the transistor according to the following criteria for best accuracy:

- Base-emitter voltage is > 0.25 V at 7.5 μA, at the highest-sensed temperature.
- Base-emitter voltage is < 0.95 V at 120 μA, at the lowest-sensed temperature.
- Base resistance is $< 100 \Omega$.
- Tight control of V_{BF} characteristics indicated by small variations in h_{FF} (50 to 150).

Based on these criteria, TI recommends using a MMBT3904 (NPN) or a MMBT3906 (PNP) transistor.

9.2.2 Detailed Design Procedure

The local temperature sensor inside the TMP464 is influenced by the ambient air around the device but mainly monitors the PCB temperature that it is mounted to. The thermal time constant for the TMP464 device is approximately two seconds. This constant implies that if the ambient air changes quickly by 100°C, then the TMP464 device takes approximately 10 seconds (that is, five thermal time constants) to settle to within 1°C of the final value. In most applications, the TMP464 package is in electrical (and therefore thermal) contact with the printed-circuit board (PCB), and subjected to forced airflow. The accuracy of the measured temperature directly depends on how accurately the PCB and forced airflow temperatures represent the temperature that the TMP464 device is measuring. Additionally, the internal power dissipation of the TMP464 device can cause the temperature to rise above the ambient or PCB temperature. The internal power is negligible because of the small current drawn by the TMP464 device. \pm 6 can be used to calculate the average conversion current for power dissipation and self-heating based on the number of conversions per second and temperature sensor channel enabled. \pm 7 shows an example with local and all remote sensor channels enabled and conversion rate of 1 conversion per second; see the *Electrical Characteristics* table for typical values required for these calculations. For a 3.3-V supply and a conversion rate of 1 conversion per second, the TMP464 device dissipates 0.143 mW (PD_{IQ} = 3.3 V × 43 μA) when both the remote and local channels are enabled.

Average Conversion Current = (Local Conversion Time) × (Conversions Per Second) × (Local Active IQ) + (Remote Conversion Time) × (Conversions Per Second) × (Remote Active I_Q) × (Number of Active Channels + (Standby Mode) × [1 – ((Local Conversion Time) + (Remote Conversion Time) × (Number of Active Channels)) × (Conversions Per Second)]

(6)

(7)



Typical Application (continued)

Average Conversion Current =
$$(16 \text{ ms}) \times (\frac{1}{\text{sec}}) \times (240 \text{ }\mu\text{A})$$

 $+ (16 \text{ ms}) \times (\frac{1}{\text{sec}}) \times (200 \text{ }\mu\text{A}) \times (4)$
 $+ (15 \text{ }\mu\text{A}) \times \left[1 - ((16 \text{ ms}) + (16 \text{ ms}) \times (4)) \times (\frac{1}{\text{sec}})\right]$
 $= 43 \text{ }\mu\text{A}$ (8)

The temperature measurement accuracy of the TMP464 device depends on the remote and local temperature sensor being at the same temperature as the monitored system point. If the temperature sensor is not in good thermal contact with the part of the monitored system, then there is a delay between the sensor response and the system changing temperature. This delay is usually not a concern for remote temperature-sensing applications that use a substrate transistor (or a small, SOT-23 transistor) placed close to the monitored device.

9.2.3 Application Curve




図 22. TMP464 Temperature Step Response of Local Sensor

10 Power Supply Recommendations

The TMP464 device operates with a power-supply range from 1.7 V to 3.6 V. The device is optimized for operation at a 1.8-V supply, but can measure temperature accurately in the full supply range.

TI recommends a power-supply bypass capacitor. Place this capacitor as close as possible to the supply and ground pins of the device. A typical value for this supply bypass capacitor is 0.1 μ F. Applications with noisy or high-impedance power supplies may require additional decoupling capacitors to reject power-supply noise.




11 Layout

11.1 Layout Guidelines

Remote temperature sensing on the TMP464 device measures very small voltages using very low currents; therefore, noise at the device inputs must be minimized. Most applications using the TMP464 device have high digital content, with several clocks and a multitude of logic-level transitions that create a noisy environment. Layout must adhere to the following guidelines:

- 1. Place the TMP464 device as close to the remote junction sensor as possible.
- 2. Route the D+ and D− traces next to each other and shield them from adjacent signals through the use of ground guard traces, as shown in ☑ 23. If a multilayer PCB is used, bury these traces between the ground or V+ planes to shield them from extrinsic noise sources. TI recommends 5-mil (0.127 mm) PCB traces.
- 3. Minimize additional thermocouple junctions caused by copper-to-solder connections. If these junctions are used, make the same number and approximate locations of copper-to-solder connections in both the D+ and D- connections to cancel any thermocouple effects.
- 4. Use a 0.1-μF local bypass capacitor directly between the V+ and GND of the TMP464. For optimum measurement performance, minimize filter capacitance between D+ and D- to 1000 pF or less. This capacitance includes any cable capacitance between the remote temperature sensor and the TMP464.
- 5. If the connection between the remote temperature sensor and the TMP464 is wired and is less than eight inches (20.32 cm) long, use a twisted-wire pair connection. For lengths greater than eight inches, use a twisted, shielded pair with the shield grounded as close to the TMP464 device as possible. Leave the remote sensor connection end of the shield wire open to avoid ground loops and 60-Hz pickup.
- 6. Thoroughly clean and remove all flux residue in and around the pins of the TMP464 device to avoid temperature offset readings as a result of leakage paths between D+ and GND, or between D+ and V+.



NOTE: Use a minimum of 5-mil (0.127 mm) traces with 5-mil spacing.

図 23. Suggested PCB Layer Cross-Section



11.2 Layout Example

O VIA to Power or Ground Plane




図 24. TMP464 Layout Example



12 デバイスおよびドキュメントのサポート

12.1 ドキュメントの更新通知を受け取る方法

ドキュメントの更新についての通知を受け取るには、ti.comのデバイス製品フォルダを開いてください。右上の「アラートを受 け取る」をクリックして登録すると、変更されたすべての製品情報に関するダイジェストを毎週受け取れます。変更の詳細に ついては、修正されたドキュメントに含まれている改訂履歴をご覧ください。

12.2 コミュニティ・リソース

TI E2E™ support forums are an engineer's go-to source for fast, verified answers and design help — straight from the experts. Search existing answers or ask your own question to get the quick design help you need.

Linked content is provided "AS IS" by the respective contributors. They do not constitute TI specifications and do not necessarily reflect TI's views; see TI's Terms of Use.

12.3 商標

E2E is a trademark of Texas Instruments.

SMBus is a trademark of Intel Corporation.

All other trademarks are the property of their respective owners.

12.4 静電気放電に関する注意事項



これらのデバイスは、限定的なESD(静電破壊)保護機能を内 蔵しています。保存時または取り扱い時は、MOSゲートに対す る静電破壊を防 ▲ 上するために、リード線同士をショートさせておくか、デバイスを導電フォームに入れる必要があります。

12.5 Glossary

SLYZ022 — TI Glossary.

This glossary lists and explains terms, acronyms, and definitions.

13 メカニカル、パッケージ、および注文情報

以降のページには、メカニカル、パッケージ、および注文に関する情報が記載されています。この情報は、そのデバイスについて利用可能な最新のデータです。このデータは予告なく変更されることがあり、ドキュメントが改訂される場合もありま す。本データシートのブラウザ版を使用されている場合は、画面左側の説明をご覧ください。

www.ti.com 30-Jul-2024

PACKAGING INFORMATION

Orderable Device	Status	Package Type	Package Drawing	Pins	Package Qty	Eco Plan	Lead finish/ Ball material	MSL Peak Temp	Op Temp (°C)	Device Marking (4/5)	Samples
TMP464AIRGTR	ACTIVE	VQFN	RGT	16	3000	RoHS & Green	NIPDAU	Level-1-260C-UNLIM	-40 to 125	T464	Samples
TMP464AIRGTT	OBSOLETE	VQFN	RGT	16		TBD	Call TI	Call TI	-40 to 125	T464	

(1) The marketing status values are defined as follows:

ACTIVE: Product device recommended for new designs.

LIFEBUY: TI has announced that the device will be discontinued, and a lifetime-buy period is in effect.

NRND: Not recommended for new designs. Device is in production to support existing customers, but TI does not recommend using this part in a new design.

PREVIEW: Device has been announced but is not in production. Samples may or may not be available.

OBSOLETE: TI has discontinued the production of the device.

(2) RoHS: TI defines "RoHS" to mean semiconductor products that are compliant with the current EU RoHS requirements for all 10 RoHS substances, including the requirement that RoHS substance do not exceed 0.1% by weight in homogeneous materials. Where designed to be soldered at high temperatures, "RoHS" products are suitable for use in specified lead-free processes. TI may reference these types of products as "Pb-Free".

RoHS Exempt: TI defines "RoHS Exempt" to mean products that contain lead but are compliant with EU RoHS pursuant to a specific EU RoHS exemption.

Green: TI defines "Green" to mean the content of Chlorine (CI) and Bromine (Br) based flame retardants meet JS709B low halogen requirements of <=1000ppm threshold. Antimony trioxide based flame retardants must also meet the <=1000ppm threshold requirement.

- (3) MSL, Peak Temp. The Moisture Sensitivity Level rating according to the JEDEC industry standard classifications, and peak solder temperature.
- (4) There may be additional marking, which relates to the logo, the lot trace code information, or the environmental category on the device.
- (5) Multiple Device Markings will be inside parentheses. Only one Device Marking contained in parentheses and separated by a "~" will appear on a device. If a line is indented then it is a continuation of the previous line and the two combined represent the entire Device Marking for that device.
- (6) Lead finish/Ball material Orderable Devices may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead finish/Ball material values may wrap to two lines if the finish value exceeds the maximum column width.

Important Information and Disclaimer: The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.

PACKAGE MATERIALS INFORMATION

www.ti.com 20-Feb-2024

TAPE AND REEL INFORMATION



A0	Dimension designed to accommodate the component width
В0	Dimension designed to accommodate the component length
K0	Dimension designed to accommodate the component thickness
W	Overall width of the carrier tape
P1	Pitch between successive cavity centers

QUADRANT ASSIGNMENTS FOR PIN 1 ORIENTATION IN TAPE



*All dimensions are nominal

Device	Package Type	Package Drawing		SPQ	Reel Diameter (mm)	Reel Width W1 (mm)	A0 (mm)	B0 (mm)	K0 (mm)	P1 (mm)	W (mm)	Pin1 Quadrant
TMP464AIRGTR	VQFN	RGT	16	3000	330.0	12.4	3.3	3.3	1.1	8.0	12.0	Q2

PACKAGE MATERIALS INFORMATION

www.ti.com 20-Feb-2024



*All dimensions are nominal

	Device Package Type		Package Drawing	Pins	SPQ	Length (mm)	Width (mm)	Height (mm)	
ı	TMP464AIRGTR	VQFN	RGT	16	3000	367.0	367.0	35.0	




Images above are just a representation of the package family, actual package may vary. Refer to the product data sheet for package details.







PLASTIC QUAD FLATPACK - NO LEAD



NOTES:

- 1. All linear dimensions are in millimeters. Any dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.
 2. This drawing is subject to change without notice.
- 3. The package thermal pad must be soldered to the printed circuit board for thermal and mechanical performance.



PLASTIC QUAD FLATPACK - NO LEAD



NOTES: (continued)

- 4. This package is designed to be soldered to a thermal pad on the board. For more information, see Texas Instruments literature number SLUA271 (www.ti.com/lit/slua271).
- Vias are optional depending on application, refer to device data sheet. If any vias are implemented, refer to their locations shown on this view. It is recommended that vias under paste be filled, plugged or tented.



PLASTIC QUAD FLATPACK - NO LEAD



NOTES: (continued)

6. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.



重要なお知らせと免責事項

TI は、技術データと信頼性データ (データシートを含みます)、設計リソース (リファレンス・デザインを含みます)、アプリケーションや設計に関する各種アドバイス、Web ツール、安全性情報、その他のリソースを、欠陥が存在する可能性のある「現状のまま」提供しており、商品性および特定目的に対する適合性の黙示保証、第三者の知的財産権の非侵害保証を含むいかなる保証も、明示的または黙示的にかかわらず拒否します。

これらのリソースは、TI 製品を使用する設計の経験を積んだ開発者への提供を意図したものです。(1) お客様のアプリケーションに適した TI 製品の選定、(2) お客様のアプリケーションの設計、検証、試験、(3) お客様のアプリケーションに該当する各種規格や、その他のあら ゆる安全性、セキュリティ、規制、または他の要件への確実な適合に関する責任を、お客様のみが単独で負うものとします。

上記の各種リソースは、予告なく変更される可能性があります。これらのリソースは、リソースで説明されている TI 製品を使用するアプリケーションの開発の目的でのみ、TI はその使用をお客様に許諾します。これらのリソースに関して、他の目的で複製することや掲載することは禁止されています。TI や第三者の知的財産権のライセンスが付与されている訳ではありません。お客様は、これらのリソースを自身で使用した結果発生するあらゆる申し立て、損害、費用、損失、責任について、TI およびその代理人を完全に補償するものとし、TI は一切の責任を拒否します。

TIの製品は、TIの販売条件、または ti.com やかかる TI 製品の関連資料などのいずれかを通じて提供する適用可能な条項の下で提供されています。TI がこれらのリソースを提供することは、適用される TI の保証または他の保証の放棄の拡大や変更を意味するものではありません。

お客様がいかなる追加条項または代替条項を提案した場合でも、TIはそれらに異議を唱え、拒否します。

郵送先住所: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265 Copyright © 2024, Texas Instruments Incorporated