TEXAS INSTRUMENTS
TPSM53604
JAJSI64C – NOVEMBER 2019 – REVISED SEPTEMBER 2021


TPSM53604 36V 入力、4A 電源モジュール、Enhanced HotRod™ QFN パッケージ

1 特長

- 機能安全対応
  - 機能安全システムの設計に役立つ資料を利用可能
- 5mm × 5.5mm × 4mm の Enhanced HotRod™ QFN パッケージ
  - 業界最小の 36V、4A フットプリント: 85mm^2 のソリューション・サイズ (片面)
  - 低 EMI:CISPR11 放射エミッションに適合
  - 優れた放熱特性: 85℃、無気流で最大 20W の出力電力
  - 一般的なフットプリント:1 つの大型サーマル・パッド、すべてのピンに外周から接続可能
- 入力電圧範囲:3.8V～36V
- 出力電圧範囲:1V～7V
- 最大効率:95%
- パワー・グッド・フラグ
- 高精度のイネーブル
- 内蔵ヒカップ・モード短絡保護、過熱保護、出力プリバイアス・スタートアップ、ソフト・スタート、UVLO
- 動作時の IC 接合部温度範囲:–40℃～+125℃
- 動作時の周囲温度範囲:–40℃～+105℃
- Mil-STD-883D 衝撃 / 振動テスト済み
- 次の製品とピン互換:3A の TPSM53603、2A の TPSM53602
- WEBENCH® Power Designer により、TPSM53604 を使用するカスタム設計を作成
- 迅速な基板設計に役立つ EVM 設計ファイルをダウンロード

2 アプリケーション

- 広 VIN の汎用電源
- ファクトリ・オートメーション / 制御
- 試験 / 測定機器
- 航空宇宙 / 防衛
- 負出力電圧アプリケーション



概略回路図

3 概要


TPSM53604 電源モジュールは、36V 入力の降圧型 DC/DC コンバータとパワー MOSFET、シールド付きインダクタ、受動素子とを、放熱特性の優れた QFN パッケージに統合した高集積 4A 電源ソリューションです。5mm x 5.5mm x 4mm の 15 ピン・パッケージに *Enhanced HotRod QFN* テクノロジを採用し、放熱性能の向上、小さなフットプリント、低 EMI を実現しています。1 つの大型サーマル・パッドを搭載し、パッケージのすべてのピンに外周からアクセスできるため、レイアウトが単純で製造時の扱いも簡単です。

このトータル・ソリューションを使用すると、外付け部品はわずか 4 個で済み、設計プロセスでループ補償も磁気部品の選択も不要です。パワー・グッド、プログラム可能な UVLO、プリバイアス・スタートアップ、過電流および過熱保護などの完全な機能セットを備えているため、TPSM53604 は広範なアプリケーションの電源として非常に優れたデバイスです。


製品情報

部品番号(1)	パッケージ	本体サイズ (公称)
TPSM53604	B3QFN (15)	5.0mm × 5.5mm

(1) 利用可能なすべてのパッケージについては、このデータシートの末尾にある注文情報を参照してください。



Enhanced HotRod QFN と代表的なレイアウト



5V_{OUT} の効率

英語版の TI 製品についての情報を翻訳したこの資料は、製品の概要を確認する目的で便宜的に提供しているものです。該当する正式な英語版の最新情報は、www.ti.com で閲覧でき、その内容が常に優先されます。TI では翻訳の正確性および妥当性につきましては一切保証いたしません。実際の設計などの前には、必ず最新版の英語版をご参照くださいますようお願いいたします。

Table of Contents

1 特長 ... 1
2 アプリケーション ... 1
3 概要 ... 1
4 Revision History ... 2
5 Pin Configuration and Functions ... 3
6 Specifications ... 4
6.1 Absolute Maximum Ratings ... 4
6.2 ESD Ratings ... 4
6.3 Recommended Operating Conditions ... 4
6.4 Thermal Information ... 5
6.5 Electrical Characteristics ... 5
6.6 Typical Characteristics (V_{IN} = 5 V) ... 7
6.7 Typical Characteristics (V_{IN} = 12 V) ... 8
6.8 Typical Characteristics (V_{IN} = 24 V) ... 9
6.9 Typical Characteristics (V_{IN} = 36 V) ... 10
7 Detailed Description ... 11
7.1 Overview ... 11
7.2 Functional Block Diagram ... 11
7.3 Feature Description ... 12
7.4 Device Functional Modes ... 19
8 Application and Implementation ... 20
8.1 Application Information ... 20
8.2 Typical Application ... 20
9 Power Supply Recommendations ... 22
10 Layout ... 23
10.1 Layout Guidelines ... 23
10.2 Layout Examples ... 23
10.3 Theta JA versus PCB Area ... 24
10.4 Package Specifications ... 25
10.5 EMI ... 25
11 Device and Documentation Support ... 27
11.1 Device Support ... 27
11.2 Documentation Support ... 27
11.3 Receiving Notification of Documentation Updates ... 27
11.4 サポート・リソース ... 27
11.5 Trademarks ... 27
11.6 Electrostatic Discharge Caution ... 28
11.7 Glossary ... 28
12 Mechanical, Packaging, and Orderable Information ... 28

4 Revision History

資料番号末尾の英字は改訂を表しています。その改訂履歴は英語版に準じています。

Changes from Revision B (August 2020) to Revision C (September 2021) — **Page**

- 機能安全の箇条書き項目を追加 ... 1

Changes from Revision A (December 2019) to Revision B (August 2020) — **Page**

- パッケージ情報を正しいパッケージ・タイプに更新 ... 1
- 文書全体にわたって表、図、相互参照の採番方法を更新 ... 1

Copyright © 2021 Texas Instruments Incorporated

5 Pin Configuration and Functions




図 5-1. 15-Pin QFN RDA Package (Top View)

表 5-1. Pin Functions

PIN		TYPE	DESCRIPTION
NO.	NAME		
12	AGND	G	Analog ground. Zero voltage reference for internal references and logic. All electrical parameters are measured with respect to this pin. **This pin must be connected to PGND at a single point.** See *セクション 10* for a recommended layout.
4, 5	DNC	—	Do not connect. Do not connect these pins to ground, to another DNC pin, or to any other voltage. These pins are connected to internal circuitry. Each pin must be soldered to an isolated pad.
2	EN	I	Enable pin. This pin turns the converter on when pulled high and turns off the converter when pulled low. This pin can be connected directly to VIN. **Do not float.** This pin can be used to set the input under voltage lockout with two resistors. See *セクション 7.3.6*.
9	FB	I	Feedback input. Connect the mid-point of the feedback resistor divider to this pin. Connect the upper resistor (R_{FBT}) of the feedback divider to V_{OUT} at the desired point of regulation. Connect the lower resistor (R_{FBB}) of the feedback divider to AGND.
3, 10, 11	NC	—	Not connected. These pins are not connected to any circuitry within the module. It is recommended that these pins be connected to the PGND plane on the application board to enhance shielding and thermal performance.
15	PGND	G	Power ground. This is the return current path for the power stage of the device. Connect this pad to the input supply return, the load return, and the capacitors associated with the VIN and VOUT pins. See the *セクション 10* section for a recommended layout.
6	PGOOD	O	Power-good pin. Open-drain output that asserts low if the feedback voltage is not within the specified window thresholds. A 10-kΩ to 100-kΩ pullup resistor is required and can be tied to the V5V pin or other DC voltage less than 22 V. If not used, this pin can be left open or connected to PGND.
1, 14	VIN	I	Input supply voltage. Connect the input supply to these pins. Connect input capacitors between these pins and PGND in close proximity to the device.
7, 8	VOUT	O	Output voltage. These pins are connected to the internal output inductor. Connect these pins to the output load and connect external output capacitors between these pins and PGND.
13	V5V	O	Internal 5-V LDO output. Supplies internal control circuits. Do not connect to external loads. This pin can be used as logic supply for PGOOD pin.

Copyright © 2021 Texas Instruments Incorporated

6 Specifications

6.1 Absolute Maximum Ratings

Over the recommended operating junction temperature range(1)

PARAMETER		MIN	MAX	UNIT
Input voltage	VIN to PGND	–0.3	38	V
	EN to AGND(2)	–0.3	V_{IN} + 0.3	
	PGOOD to AGND(2)	–0.3	22	
	FB to AGND	–0.3	5.5	
	AGND to PGND	–0.3	0.3	
Output voltage	VOUT to PGND(2)	-0.3	V_{IN} + 0.3	V
	V5V to AGND	0	5.5	
Operating IC junction temperature, T_J (3)		–40	150	°C
Storage temperature, T_{stg}		–55	150	°C
Peak reflow case temperature			245	°C
Maximum number or reflows allowed			3	
Mechanical vibration	Mil-STD-883D, Method 2007.2, 20 to 2000 Hz		20	G
Mechanical shock	Mil-STD-883D, Method 2002.3, 1 msec, 1/2 sine, mounted		500	G

(1) Stresses beyond those listed under *Absolute Maximum Ratings* may cause permanent damage to the device. These are stress ratings only, which do not imply functional operation of the device at these or any other conditions beyond those indicated under *Recommended Operating Conditions*. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability.
(2) The voltage on this pin must not exceed the voltage on the VIN pin by more than 0.3 V.
(3) The ambient temperature is the air temperature of the surrounding environment. The junction temperature is the temperature of the internal power IC when the device is powered. Operating below the maximum ambient temperature, as shown in the safe operating area (SOA) curves in the typical characteristics sections, ensures that the maximum junction temperature of any component inside the module is never exceeded.

6.2 ESD Ratings

			VALUE	UNIT
$V_{(ESD)}$	Electrostatic discharge	Human-body model (HBM)(1)	±2500	V
		Charged-device model (CDM)(2)	±1000	

(1) JEDEC document JEP155 states that 500-V HBM allows safe manufacturing with a standard ESD control process.
(2) JEDEC document JEP157 states that 250-V CDM allows safe manufacturing with a standard ESD control process.

6.3 Recommended Operating Conditions

Over operating ambient temperature range (unless otherwise noted) (1)

	MIN	MAX	UNIT
Input voltage, V_{IN}	3.8 (3)	36	V
Output voltage, V_{OUT}	1	7 (4)	V
Output current, I_{OUT}	0	4	A
EN voltage, V_{EN} (2)	0	V_{IN}	V
PGOOD pullup voltage, V_{PGOOD} (2)	0	18	V
PGOOD sink current		3	mA
Operating ambient temperature, T_A	–40	105	°C
Input capacitance, C_{IN}	20 (5)		µF
Output capacitance, C_{OUT}	min (6)	1000	µF

(1) Recommended operating conditions indicate conditions for which the device is intended to be functional, but do not ensure specific performance limits. For ensured specifications, see *セクション 6.5*.
(2) The voltage on this pin must not exceed the voltage on the VIN pin by more than 0.3 V.
(3) The recommended minimum V_{IN} is 3.8 V or (VOUT + 1 V), whichever is greater. See the *Voltage Dropout* section for more information.
(4) The recommended maximum output voltage varies depending input voltage. See the *Voltage Dropout* section for more information.
(5) Minimum C_{IN} of 20 µF must be ceramic type.
(6) The minimum amount of required output capacitance varies depending on the output voltage (see 表 7-1).

Copyright © 2021 Texas Instruments Incorporated

6.4 Thermal Information

THERMAL METRIC(1)		TPSM53604 RDA (QFN) 15 PINS	UNIT
$R_{\theta JA}$	Junction-to-ambient thermal resistance (2)	19.5	°C/W
ψ_{JT}	Junction-to-top characterization parameter (3)	1.0	°C/W
ψ_{JB}	Junction-to-board characterization parameter (4)	5.5	°C/W
T_{SHDN}	Thermal shutdown temperature	165	°C
	Recovery temperature	148	°C

(1) For more information about traditional and new thermal metrics, see the *Semiconductor and IC Package Thermal Metrics* application report.
(2) The junction-to-ambient thermal resistance, $R_{\theta JA}$, applies to devices soldered directly to a 75 mm x 75 mm four-layer PCB with 2 oz. copper and natural convection cooling. Additional airflow and PCB copper area reduces $R_{\theta JA}$. For more information, see the *セクション 10.3* section.
(3) The junction-to-top board characterization parameter, ψ_{JT}, estimates the junction temperature, T_J, of a device in a real system, using a procedure described in JESD51-2A (section 6 and 7). $T_J = \psi_{JT} \times Pdis + T_T$; where Pdis is the power dissipated in the device and T_T is the temperature of the top of the device.
(4) The junction-to-board characterization parameter, ψ_{JB}, estimates the junction temperature, T_J, of a device in a real system, using a procedure described in JESD51-2A (sections 6 and 7). $T_J = \psi_{JB} \times Pdis + T_B$; where Pdis is the power dissipated in the device and T_B is the temperature of the board 1mm from the device.

6.5 Electrical Characteristics

Limits apply over T_A = –40°C to +105°C, V_{IN} = 12 V, V_{OUT} = 3.3 V, I_{OUT} = I_{OUT} maximum, (unless otherwise noted); C_{IN1} = 2x10 µF, 50-V, 1206 ceramic; C_{IN2} = 100 nF, 50-V, 0603 ceramic; C_{OUT} = 3x22 µF, 25-V, 1210 ceramic. Minimum and maximum limits are specified through production test or by design. Typical values represent the most likely parametric norm and are provided for reference only.

PARAMETER		TEST CONDITIONS	MIN	TYP	MAX	UNIT
INPUT VOLTAGE (V_{IN})						
V_{IN}	Input voltage range	Over I_{OUT} range	3.8 (1)		36	V
	V_{IN} turn on	V_{IN} increasing, I_{OUT} = 0.2 A		3.55		V
	V_{IN} turn off	V_{IN} decreasing, I_{OUT} = 0.2 A		3.05		V
I_Q	Quiescient current	Non-switching, V_{FB} = 1.2 V		24		µA
I_{SHDN}	Shutdown supply current	V_{EN} = 0 V, I_{OUT} = 0 A		5	10	µA
INTERNAL LDO (V5V)						
V5V	Internal LDO output voltage appearing at the V5V pin	6 V ≤ V_{IN} ≤ 36 V	4.75	5	5.25	V
FEEDBACK						
V_{FB}	Feedback voltage(2)	–40°C ≤ T_J ≤ +125°C, I_{OUT} = 0.75 A	0.985	1	1.015	V
	Load regulation	T_A = +25°C, 0.8 A ≤ I_{OUT} ≤ 4 A		0.06		%
	Line regulation	T_A = +25°C, I_{OUT} = 0.75 A, Over V_{IN} range		0.15		%
I_{FB}	Current into FB pin	FB = 1 V		0.2	50	nA
CURRENT						
I_{OUT}	Output current	T_A = 25°C	0		4	A
I_{OUT}	Over-current threshold			5.5		A
V_{HC}	FB pin voltage required to trip short-circuit hiccup mode			0.4		V
t_{HC}	Time between current-limit hiccup burst			94		ms
ENABLE (EN PIN)						
$V_{EN-LDO-H}$	EN input level required to turn on internal LDO	Rising threshold			1	V
$V_{EN-LDO-L}$	EN input level required to turn off internal LDO	Falling threshold	0.3			V
V_{EN-H}	EN input level required to start switching	Rising threshold	1.2	1.23	1.26	V
V_{EN-HYS}	Hysteresis below V_{EN-H}	Falling		100		mV
I_{LKG-EN}	Enable input leakage current	V_{EN} = 3.3 V		0.2		nA

Copyright © 2021 Texas Instruments Incorporated

Limits apply over T_A = –40°C to +105°C, V_{IN} = 12 V, V_{OUT} = 3.3 V, I_{OUT} = I_{OUT} maximum, (unless otherwise noted); C_{IN1} = 2x10 µF, 50-V, 1206 ceramic; C_{IN2} = 100 nF, 50-V, 0603 ceramic; C_{OUT} = 3x22 µF, 25-V, 1210 ceramic. Minimum and maximum limits are specified through production test or by design. Typical values represent the most likely parametric norm and are provided for reference only.


PARAMETER		TEST CONDITIONS	MIN	TYP	MAX	UNIT
POWER GOOD (PGOOD PIN)						
$V_{PG-HIGH-UP}$	V_{OUT} rising (fault)	% of FB voltage		107		%
$V_{PG-HIGH-DN}$	V_{OUT} falling (good)	% of FB voltage		105		%
$V_{PG-LOW-UP}$	V_{OUT} rising (good)	% of FB voltage		94		%
$V_{PG-LOW-DN}$	V_{OUT} falling (fault)	% of FB voltage		92		%
R_{PG}	Power-good flag R_{DSON}	V_{EN} = 0 V		35		Ω
V_{IN-PG}	Minimum input voltage for proper PGOOD function	50-µA, EN = 0 V			2	V
V_{PG}	PGOOD logic low output	50-µA, EN = 0 V, V_{IN} = 2 V			0.2	V
PERFORMANCE						
η	Efficiency	I_{OUT} = 2 A, T_A = 25°C		91		%
SOFT START						
t_{SS}	Internal soft-start time			4		ms
SWITCHING FREQUENCY						
f_{SW}	Switching frequency	I_{OUT} = 2 A, T_A = 25°C		1.4(3)		MHz

(1) The recommended minimum V_{IN} is 3.8 V or (VOUT + 1 V), whichever is greater. See the *セクション 7.3.9* section for more information.
(2) The overall output voltage tolerance will be affected by the tolerance of the external R_{FBT} and R_{FBB} resistors.
(3) The typical switching frequency of this device will change based on operating conditions. See the *セクション 7.4.2* section for more information.

Copyright © 2021 Texas Instruments Incorporated


6.6 Typical Characteristics (V_{IN} = 5 V)

The typical characteristic data has been developed from actual products tested at T_A = 25°C. This data is considered typical for the device.




V_{IN} = 5 V Linear Scale

図 6-1. Efficiency versus Output Current




V_{IN} = 5 V Log Scale

図 6-2. Efficiency versus Output Current




V_{IN} = 5 V

図 6-3. Power Dissipation versus Output Current




V_{IN} = 5 V C_{OUT} = 4x 47µF

図 6-4. Voltage Ripple versus Output Current



V_{IN} = 5 V V_{OUT} = 1.0 V
PCB = 85 mm × 65 mm, 4-layer, 2 oz. copper

図 6-5. Safe Operating Area




V_{IN} = 5 V V_{OUT} = 3.3 V
PCB = 85 mm × 65 mm, 4-layer, 2 oz. copper

図 6-6. Safe Operating Area

Copyright © 2021 Texas Instruments Incorporated


6.7 Typical Characteristics (V_{IN} = 12 V)

The typical characteristic data has been developed from actual products tested at T_A = 25°C. This data is considered typical for the device.




V_{IN} = 12 V Linear Scale

図 6-7. Efficiency versus Output Current




V_{IN} = 12 V Log Scale

図 6-8. Efficiency versus Output Current




V_{IN} = 12 V

図 6-9. Power Dissipation versus Output Current




V_{IN} = 12 V C_{OUT} = 4x 47µF

図 6-10. Voltage Ripple versus Output Current



V_{IN} = 12 V V_{OUT} = 1.8 V
PCB = 85 mm × 65 mm, 4-layer, 2 oz. copper

図 6-11. Safe Operating Area




V_{IN} = 12 V V_{OUT} = 5 V
PCB = 85 mm × 65 mm, 4-layer, 2 oz. copper

図 6-12. Safe Operating Area

Copyright © 2021 Texas Instruments Incorporated


6.8 Typical Characteristics (V_{IN} = 24 V)

The typical characteristic data has been developed from actual products tested at T_A = 25°C. This data is considered typical for the device.




V_{IN} = 24 V

図 6-13. Efficiency versus Output Current




V_{IN} = 24 V

図 6-14. Efficiency versus Output Current




V_{IN} = 24 V

図 6-15. Power Dissipation versus Output Current



V_{IN} = 24 V C_{OUT} = 4x 47µF


図 6-16. Voltage Ripple versus Output Current



V_{IN} = 24 V V_{OUT} = 1.8 V

PCB = 85 mm × 65 mm, 4-layer, 2 oz. copper

図 6-17. Safe Operating Area



V_{IN} = 24 V V_{OUT} = 5 V


PCB = 85 mm × 65 mm, 4-layer, 2 oz. copper

図 6-18. Safe Operating Area

Copyright © 2021 Texas Instruments Incorporated


6.9 Typical Characteristics (V_{IN} = 36 V)

The typical characteristic data has been developed from actual products tested at T_A = 25°C. This data is considered typical for the device.




V_{IN} = 36 V

図 6-19. Efficiency versus Output Current




V_{IN} = 36 V

図 6-20. Efficiency versus Output Current




V_{IN} = 36 V

図 6-21. Power Dissipation versus Output Current




V_{IN} = 36 V C_{OUT} = 4x 47µF

図 6-22. Voltage Ripple versus Output Current



V_{IN} = 36 V V_{OUT} = 1.8 V
PCB = 85 mm × 65 mm, 4-layer, 2 oz. copper

図 6-23. Safe Operating Area



V_{IN} = 36 V V_{OUT} = 5 V
PCB = 85 mm × 65 mm, 4-layer, 2 oz. copper

図 6-24. Safe Operating Area


Copyright © 2021 Texas Instruments Incorporated

7 Detailed Description

7.1 Overview

The TPSM53604 is a full-featured, 36-V input, 4-A, synchronous step-down converter with PWM, MOSFETs, shielded inductor, and control circuitry integrated into a low-profile, over-molded package. The device integration enables small designs while providing the ability to adjust key parameters to meet specific design requirements. The TPSM53604 provides an output voltage range of 1 V to 7 V. An external resistor divider is used to adjust the output voltage to the desired value. The device provides accurate voltage regulation over a wide load range by using a precision internal voltage reference. Input undervoltage lockout is internally set at 3.55 V (typical), but can be adjusted upward using a resistor divider on the EN pin of the device. The EN pin can also be pulled low to put the device into standby mode to reduce input current draw. A power-good signal is provided to indicate when the output is within its nominal voltage range. Thermal shutdown and current limit features protect the device during an overload condition. A 15-pin, QFN package that includes exposed bottom pads provides a thermally enhanced solution for space-constrained applications.

7.2 Functional Block Diagram



7.3 Feature Description

7.3.1 Adjusting the Output Voltage

A resistor divider connected to the FB pin (pin 9) sets the output voltage of the TPSM53604. The output voltage adjustment range is from 1 V to 7 V. 図 7-1 shows the feedback resistor connections for setting the output voltage. The recommended value of R_{FBT} is 10 kΩ. Use 式 1 to calculate the value for R_{FBB}. 表 7-1 lists the standard resistor values for several output voltages. The minimum required output capacitance for each output voltage is also included in 表 7-1. The capacitance values listed represent the *effective* capacitance, taking into account the effects of DC bias and temperature variation.

$$R_{FBB} = \frac{10}{(V_{OUT} - 1)} \text{ (k}\Omega\text{)} \quad (1)$$




図 7-1. Setting the Output Voltage

表 7-1. Setting the Output Voltage

V_{OUT} (V)	R_{FBB} (kΩ)(1)	$C_{OUT(MIN)}$ (µF) (EFFECTIVE)	V_{OUT} (V)	R_{FBB} (kΩ)(1)	$C_{OUT(MIN)}$ (µF) (EFFECTIVE)
1.0	open	150	3.0	4.99	57
1.1	100	143	3.3	4.32	52
1.2	49.9	132	4.0	3.32	43
1.3	33.2	123	4.5	2.87	39
1.4	24.9	115	5.0	2.49	35
1.5	20.0	107	5.5	2.21	32
1.8	12.4	91	6.0	2.00	30
2.0	10.0	82	6.5	1.82	28
2.5	6.65	67	7.0	1.65	26

(1) R_{FBT} = 10.0 kΩ

7.3.2 Switching Frequency

The switching frequency of the TPSM53604 is set to 1.4 MHz, internal to the device. The switching frequency cannot be adjusted. When the load current is high enough and the device is operating in PWM mode, the device operates at a fixed frequency. As the load current drops and the device switches to PFM mode, the switching frequency is reduced, resulting in reduced power dissipation. See *セクション 7.4.2* for typical information on when the device switches from PWM mode to PFM mode.

Copyright © 2021 Texas Instruments Incorporated

7.3.3 Input Capacitors

The TPSM53604 requires a minimum input capacitance of 20 µF (2 × 10 µF) of ceramic type. High-quality, ceramic-type X5R or X7R capacitors with sufficient voltage rating are recommended. TI recommends an additional 47 µF of non-ceramic capacitance for applications with transient load requirements. The voltage rating of input capacitors must be greater than the maximum input voltage.

表 7-2. Recommended Input Capacitors

VENDOR(1)	SERIES	SIZE	PART NUMBER	CAPACITOR CHARACTERISTICS	
				VOLTAGE RATING (V)	CAPACITANCE (3) (µF)
Murata	X5R	1206	GRT31CR61H106ME01L	50	10
TDK	X5R	1206	CGA5L3X5R1H106M160AB	50	10
TDK	X7R	1206	CGA5L1X7R1H106K160AC	50	10
Murata	X7R	1210	GRM32ER71H106KA12L	50	10
TDK	X7R	1210	C3225X7R1H106M250AC	50	10

(1) **Capacitor Supplier Verification, RoHS, Lead-free, and Material Details**
Consult capacitor suppliers regarding availability, material composition, RoHS and lead-free status, and manufacturing process requirements for any capacitors identified in this table.
(2) Maximum ESR at 100 kHz, 25°C.
(3) Standard capacitance values

7.3.4 Output Capacitors

表 7-1 lists the TPSM53604 minimum output capacitance. The effects of DC bias and temperature variation must be considered when using ceramic capacitance. For ceramic capacitors, the package size, voltage rating, and dielectric material contributes to differences between the standard rated value and the actual effective value of the capacitance.

When adding additional capacitance above $C_{OUT(min)}$, the capacitance can be ceramic type, low-ESR polymer type, or a combination of the two. See 表 7-3 for a preferred list of output capacitors by vendor.

表 7-3. Recommended Output Capacitors

VENDOR(1)	SERIES	PART NUMBER	CAPACITOR CHARACTERISTICS		
			VOLTAGE RATING (V)	CAPACITANCE (2) (µF)	ESR(2) (mΩ)
TDK	X5R	C3225X5R0J476K	6.3	47	2
Murata	X7R	GCM32ER70J476KE19L	6.3	47	2
Murata	X5R	GRM21BR61A476ME15L	10	47	2
TDK	X5R	C3216X5R1A476M160AB	10	47	2
Murata	X7R	GRM32ER71A476KE15L	10	47	2
Murata	X5R	GRM32ER61C476K	16	47	3
TDK	X5R	C3225X5R0J107M	6.3	100	2
Murata	X5R	GRM32ER60J107M	6.3	100	2
Murata	X5R	GRM32ER61A107M	10	100	2
Kemet	X5R	C1210C107M4PAC7800	16	100	2
Panasonic	POSCAP	6TPE100MI	6.3	100	18
Panasonic	POSCAP	10TPF150ML	10	150	15
Panasonic	POSCAP	6TPF220M9L	6.3	220	9
Panasonic	POSCAP	6TPF330M9L	6.3	330	9
Panasonic	POSCAP	6TPE470MAZU	6.3	470	35

(1) **Capacitor Supplier Verification, RoHS, Lead-free and Material Details**
Consult capacitor suppliers regarding availability, material composition, RoHS and lead-free status, and manufacturing process requirements for any capacitors identified in this table.
(2) Standard capacitance values.

Copyright © 2021 Texas Instruments Incorporated

7.3.5 Output On/Off Enable (EN)

The voltage on the EN pin provides electrical ON/OFF control of the device. This input features precision thresholds, allowing the use of an external voltage divider to provide a programmable UVLO (see *セクション 7.3.6*). Applying a voltage of $V_{EN} \geq V_{EN\text{-}LDO_H}$ causes the device to enter standby mode, powering the internal LDO, but not producing an output voltage. Increasing the EN voltage to $V_{EN\text{-}H}$ fully enables the device, allowing it to enter start-up mode and starting the soft-start period. When the EN input is brought below $V_{EN\text{-}H}$ by $V_{EN\text{-}HYS}$, the regulator stops running and enters standby mode. Further decrease in the EN voltage to below $V_{EN\text{-}LDO\text{-}L}$ completely shuts down the device. 図 7-2 shows this behavior. The values for the various EN thresholds can be found in *セクション 6.5*.




図 7-2. Precision Enable Behavior

The EN pin cannot be open circuit or floating. The simplest way to enable the operation of the TPSM53604 is to connect the EN pin to VIN directly as shown in 図 7-3. This allows self start-up of the TPSM53604 when VIN is within the operation range.

If an application requires controlling the EN pin, an external logic signal can be used to drive EN pin as shown in 図 7-4. Applications using an open drain/collector device to interface with this pin require a pullup resistor to a voltage above the enable threshold.




図 7-3. Enabling the Device




図 7-4. Typical Enable Control

Copyright © 2021 Texas Instruments Incorporated

7.3.6 Programmable Undervoltage Lockout (UVLO)

The TPSM53604 implements internal UVLO circuitry on the VIN pin. The device is disabled when the VIN pin voltage falls below the internal VIN UVLO threshold. The internal VIN UVLO rising threshold is 3.55 V (typical) with a typical hysteresis of 500 mV.

If an application requires a higher UVLO threshold, a resistor divider can be placed between VIN, the EN pin, and AGND as shown in 図 7-5. The enable rising threshold (V_{EN-H}) is 1.23 V (typ) with 100 mV (typ) hysteresis. 表 7-4 lists recommended resistor values for R_{ENT} and R_{ENB} to adjust the ULVO voltage.

To ensure proper start-up and reduce input current surges, TI recommends setting the UVLO threshold to approximately 80% to 85% of the minimum expected input voltage.




図 7-5. Adjustable UVLO

表 7-4. Resistor Values for Adjusting UVLO

VIN UVLO (V)	6.5	10	15	20	25	30
R_{ENT} (kΩ)	100	100	100	100	100	100
R_{ENB} (kΩ)	23.7	14.3	9.09	6.65	5.23	4.32

7.3.7 Power Good (PGOOD)

The TPSM53604 has a built-in power-good signal (PGOOD) which indicates whether the output voltage is within its regulation range. The PGOOD pin is an open-drain output that requires a pullup resistor to a nominal voltage source of 18 V or less. The internal 5-V LDO output (V5V pin), can be used as the pullup voltage source. A typical pull-up resistor value is between 10 kΩ and 100 kΩ. The maximum recommended PGOOD sink current is 3 mA.

Once the output voltage rises above 94% of the set voltage, the PGOOD pin rises to the pullup voltage level. The PGOOD pin is pulled low when the output voltage drops lower than 92% or rises higher than 107% of the nominal set voltage. See 図 7-6 for typical power-good thresholds.

Copyright © 2021 Texas Instruments Incorporated




図 7-6. Power-good Flag

7.3.8 Light Load Operation

In light load conditions, the device turns on the high-side MOSFET until the inductor current reaches a controlled minimum value of approximately 1 A. As the input voltage decreases, reducing the voltage headroom between V_{IN} and V_{OUT}, the amount of time required to reach this minimum current increases. During this time, additional energy flows from V_{IN} to V_{OUT}, resulting in increased output voltage ripple. To eliminate this behavior, the EN UVLO function must be used to maintain at least 1 V of headroom above V_{OUT}. Alternatively, additional output capacitance can be added to reduce the output voltage ripple in applications that operate at light loads with very low V_{IN} to V_{OUT} headroom.

7.3.9 Voltage Dropout

Voltage dropout is the difference between the input voltage and output voltage that is required to maintain output voltage regulation while providing the rated output current.


To ensure the TPSM53604 maintains output voltage regulation over the operating temperature range, the minimum V_{IN} is 3.8 V or (V_{OUT} + 1 V), whichever is greater.

The TPSM53604 operates in a frequency foldback mode when the dropout voltage is less than the recommendation above. Frequency foldback reduces the switching frequency to allow the output voltage to maintain regulation as input voltage decreases. At light load, the TPSM53604 operates in PFM mode which is a reduced frequency operation, see *セクション 7.4.2* for more information on PFM mode. 図 7-7 through 図 7-12 show typical dropout voltage and frequency foldback curves for 3.3 V, 5 V, and 7 V outputs at T_A = 25°C.

Note


As ambient temperature increases, dropout voltage and frequency foldback occur at higher input voltage.

Copyright © 2021 Texas Instruments Incorporated




V_{OUT} = 3.3 V

図 7-7. Voltage Dropout




V_{OUT} = 3.3 V

図 7-8. Frequency Foldback




V_{OUT} = 5 V

図 7-9. Voltage Dropout




V_{OUT} = 5 V

図 7-10. Frequency Foldback



V_{OUT} = 7 V

図 7-11. Voltage Dropout



V_{OUT} = 7 V

図 7-12. Frequency Foldback

7.3.10 Overcurrent Protection (OCP)

The TPSM53604 is protected from overcurrent conditions. Cycle-by-cycle current limit is used for overloads while hiccup mode is used for short circuits. Hiccup mode is activated if a fault condition persists on the output.

Copyright © 2021 Texas Instruments Incorporated

Hiccup mode reduces power dissipation under severe overcurrent conditions and prevents overheating and potential damage to the device. In hiccup mode, the regulator is shut down and kept off for 94 ms typical before the TPSM53604 tries to start again. If overcurrent or short-circuit fault condition still exist, hiccup repeats until the fault condition is removed. Once the fault is removed, the module automatically recovers with a normal soft-start power up.

The typical current limit threshold for the TPSM53604 varies slightly as a function of input voltage and output voltage. 図 7-13 shows the typical current limit threshold for several output voltages over the input voltage range.




図 7-13. Current Limit Threshold

7.3.11 Thermal Shutdown

The internal thermal shutdown circuitry forces the device to stop switching if the junction temperature exceeds 165°C typically. The device reinitiates the power-up sequence when the junction temperature drops below 148°C typically.

Copyright © 2021 Texas Instruments Incorporated

7.4 Device Functional Modes

7.4.1 Active Mode

The TPSM53604 is in active mode when VIN is above the turn-on threshold and the EN pin voltage is above the EN high threshold. The most direct way to enable the TPSM53604 is to connect the EN pin to VIN. This allows self start-up of the TPSM53604 when the input voltage is in the operation range of 3.8 V to 36 V. Connecting a resistor divider between VIN, EN, and AGND adjusts the UVLO to delay the turn on until V_{IN} is closer to its regulated voltage.

7.4.2 Auto Mode

In auto mode, the device moves between Pulse-Width Modulation (PWM) and Pulse-Frequency Modulation (PFM) as the load changes. At light loads, the regulator operates in PFM mode. At higher loads, the mode changes to PWM mode. The typical load current for which the device moves from PFM to PWM can be found in 図 7-14 and 図 7-15. The output current at which the device changes modes depends on the input voltage and the output voltage. For output currents above the curve, the device is in PWM mode. If the curve is a solid line, the PWM switching frequency is 1.4 MHz nominal. If the curve is a dashed line, the PWM switching frequency is reduced due to the minimum on-time of the internal controller to maintain output voltage regulation. For currents below the curves, the device is in PFM mode. For applications where the switching frequency must be known for a given condition, the above mentioned effects must be carefully tested before the design is finalized.

In PWM mode, the regulator operates at a constant frequency using PWM to regulate the output voltage. While operating in this mode, the output voltage is regulated by switching at a constant frequency and modulating the duty cycle to control the power to the load. This provides excellent line and load regulation and low output voltage ripple.

In PFM mode, the high-side MOSFET is turned on in a burst of one or more pulses to provide energy to the load. The duration of the burst and the actual switching frequency depends on the input voltage, output voltage, and load current. The frequency of these bursts is adjusted to regulate the output while diode emulation is used to maximize efficiency. This mode provides high light-load efficiency by reducing the amount of input supply current required to regulate the output voltage at small loads. However, in this mode, expect larger output voltage ripple and variable switching frequency.




図 7-14. PFM/PWM Thresholds (3.3 V, 5 V, and 7 V)




図 7-15. PFM/PWM Thresholds (1 V and 1.8 V)

7.4.3 Shutdown Mode

The EN pin provides electrical ON and OFF control for the TPSM53604. When the EN pin voltage is below the EN low threshold, the device is in shutdown mode. In shutdown mode, the standby current is 5 µA typical.

Copyright © 2021 Texas Instruments Incorporated

8 Application and Implementation

Note

Information in the following applications sections is not part of the TI component specification, and TI does not warrant its accuracy or completeness. TI's customers are responsible for determining suitability of components for their purposes. Customers should validate and test their design implementation to confirm system functionality.

8.1 Application Information

The TPSM53604 is a synchronous, step-down, DC/DC power module. It is used to convert a higher DC voltage to a lower DC voltage with a maximum output current of 4 A. The TPSM53604 can be configured in a negative output voltage, inverting buck-boost (IBB) topology. For more details, see the *Negative Output Voltage using the TPSM53602/3/4* application note. The following design procedure can be used to select components for the TPSM53604. Alternately, the WEBENCH® software can be used to generate complete designs. When generating a design, the WEBENCH® software uses an iterative design procedure and accesses comprehensive databases of components. See www.ti.com for more details.

8.2 Typical Application

The TPSM53604 only requires a few external components to convert from a wide input voltage supply range to a wide range of output voltages. 図 8-1 shows a basic TPSM53604 schematic for a typical design.




図 8-1. TPSM53604 Typical Schematic

8.2.1 Design Requirements

For this design example, use the parameters listed in 表 8-1 as the input parameters and follow the design procedures in *セクション 8.2.2*.

表 8-1. Design Example Parameters

DESIGN PARAMETER	VALUE
Input voltage V_{IN}	24 V typical
Output voltage V_{OUT}	5 V
Output current rating	4 A

Copyright © 2021 Texas Instruments Incorporated

8.2.2 Detailed Design Procedure

8.2.2.1 Custom Design With WEBENCH® Tools

Click here to create a custom design using the TPSM53604 device with the WEBENCH® Power Designer.

1. Start by entering the input voltage (V_{IN}), output voltage (V_{OUT}), and output current (I_{OUT}) requirements.
2. Optimize the design for key parameters such as efficiency, footprint, and cost using the optimizer dial.
3. Compare the generated design with other possible solutions from Texas Instruments.

The WEBENCH Power Designer provides a customized schematic along with a list of materials with real-time pricing and component availability.

In most cases, these actions are available:

- Run electrical simulations to see important waveforms and circuit performance
- Run thermal simulations to understand board thermal performance
- Export customized schematic and layout into popular CAD formats
- Print PDF reports for the design, and share the design with colleagues

Get more information about WEBENCH tools at www.ti.com/WEBENCH.

8.2.2.2 Output Voltage Setpoint

The output voltage of the TPSM53604 device is externally adjustable using a resistor divider. The recommended value of R_{FBT} is 10 kΩ. The value for R_{FBB} can be selected from 表 7-1 or calculated using 式 2:

$$R_{FBB} = \frac{10}{(V_{OUT} - 1)} \text{ (k}\Omega\text{)} \quad (2)$$

For the desired output voltage of 5 V, the formula yields a value of 2.5 kΩ. Choose the closest available value of 2.49 kΩ for R_{FBB}.

8.2.2.3 Input Capacitors

The TPSM53604 requires a minimum input capacitance of 20 µF (or 2 × 10 µF) ceramic type. High-quality ceramic type X5R or X7R capacitors with sufficient voltage rating are recommended. An additional 47 µF of non-ceramic capacitance is recommended for applications with transient load requirements. The voltage rating of the input capacitors must be greater than the maximum input voltage.

For this design example, two 10-µF, 50-V, ceramic capacitors are used.


8.2.2.4 Output Capacitor Selection

The TPSM53604 requires a minimum amount of output capacitance for proper operation. The minimum amount of required output varies depending on the output voltage. See 表 7-1 for the required output capacitance.

For this design example, two 47-µF, 10-V, ceramic capacitors are used.


Copyright © 2021 Texas Instruments Incorporated

8.2.3 Application Curves




V_{IN} = 24 V V_{OUT} = 5 V C_{OUT} = 2 × 47 µF

図 8-2. Enable Turn-ON



V_{IN} = 24 V V_{OUT} = 5 V C_{OUT} = 2 × 47 µF

図 8-3. Enable Turn-OFF



V_{IN} = 24 V V_{OUT} = 5 V C_{OUT} = 2 × 47 µF
I_{OUT} = 1 A to 3 A Slew rate: 1 A/µs

図 8-4. Transient Response

9 Power Supply Recommendations

The TPSM53604 is designed to operate from an input voltage supply range between 3.8 V and 36 V. This input supply must be well-regulated and able to withstand maximum input current and maintain a stable voltage. The resistance of the input supply rail must be low enough that an input current transient does not cause a high enough drop at the TPSM53604 supply voltage that can cause a false UVLO fault triggering and system reset.

If the input supply is located more than a few centimeters from the TPSM53604, additional bulk capacitance can be required in addition to the ceramic bypass capacitors. The typical amount of bulk capacitance is a 47-µF electrolytic capacitor.

Copyright © 2021 Texas Instruments Incorporated

10 Layout

The performance of any switching power supply depends as much upon the layout of the PCB as the component selection. The following guidelines help users design a PCB with the best power conversion performance, optimal thermal performance, and minimized generation of unwanted EMI.

10.1 Layout Guidelines

To achieve optimal electrical and thermal performance, an optimized PCB layout is required. 図 10-1 through 図 10-3 show a typical PCB layout. The following are some considerations for an optimized layout.

- Use large copper areas for power planes (VIN, VOUT, and PGND) to minimize conduction loss and thermal stress.
- Place ceramic input and output capacitors close to the device pins to minimize high frequency noise.
- Locate additional output capacitors between the ceramic capacitor and the load.
- Connect AGND to PGND at a single point.
- Place R_{FBT} and R_{FBB} as close as possible to the FB pin.
- Use multiple vias to connect the power planes to internal layers.
- Download the EVM Design Files for fast board design

10.2 Layout Examples




図 10-1. Typical Top-Layer Layout




図 10-2. Typical Layer-2 Layout




図 10-3. Typical PGND Layer

Copyright © 2021 Texas Instruments Incorporated

10.3 Theta JA versus PCB Area

The amount of PCB copper affects the thermal performance of the device. 図 10-4 shows the effects of copper area on the junction-to-ambient thermal resistance ($R_{\theta JA}$) of the TPSM53604. The junction-to-ambient thermal resistance is plotted for a 4-layer PCB with PCB area from 30 cm^2 to 80 cm^2.

To determine the required copper area for an application:

1. Determine the maximum power dissipation of the device in the application by referencing the power dissipation graphs in *セクション 6.6* through *セクション 6.9*.
2. Calculate the maximum $R_{\theta JA}$ using 式 3 and the maximum ambient temperature of the application.

$$R_{\theta JA} = \frac{(125°C - T_{A(max)})}{P_{D(max)}} (°C/W) \quad (3)$$

3. Reference 図 10-4 to determine the minimum required PCB area for the application conditions.




図 10-4. $R_{\theta JA}$ versus PCB Area (per Layer)

Copyright © 2021 Texas Instruments Incorporated

10.4 Package Specifications

TPSM53604		VALUE	UNIT
Weight		429	mg
Flammability	Meets UL 94 V-O		
MTBF Calculated Reliability	Per Bellcore TR-332, 50% stress, T_A = 40°C, ground benign	89.3	MHrs

10.5 EMI

The TPSM53604 is compliant with EN55011 Class-B radiated emissions. 図 10-5 and 図 10-6 show typical examples of radiated emissions plots for the TPSM53604. The graphs include the plots of the antenna in the horizontal and vertical positions.

EMI plots were measured using the standard TPSM53604EVM with no input filter.




図 10-5. Radiated Emissions 24-V Input, 5-V Output, 4-A Load




図 10-6. Radiated Emissions 12-V Input, 5-V Output, 4-A Load

Copyright © 2021 Texas Instruments Incorporated

11 Device and Documentation Support

11.1 Device Support

11.1.1 Third-Party Products Disclaimer

TI'S PUBLICATION OF INFORMATION REGARDING THIRD-PARTY PRODUCTS OR SERVICES DOES NOT CONSTITUTE AN ENDORSEMENT REGARDING THE SUITABILITY OF SUCH PRODUCTS OR SERVICES OR A WARRANTY, REPRESENTATION OR ENDORSEMENT OF SUCH PRODUCTS OR SERVICES, EITHER ALONE OR IN COMBINATION WITH ANY TI PRODUCT OR SERVICE.

11.1.2 Development Support

11.1.2.1 Custom Design With WEBENCH® Tools

Click here to create a custom design using the TPSM53604 device with the WEBENCH® Power Designer.

1. Start by entering the input voltage (V_{IN}), output voltage (V_{OUT}), and output current (I_{OUT}) requirements.
2. Optimize the design for key parameters such as efficiency, footprint, and cost using the optimizer dial.
3. Compare the generated design with other possible solutions from Texas Instruments.

The WEBENCH Power Designer provides a customized schematic along with a list of materials with real-time pricing and component availability.

In most cases, these actions are available:

- Run electrical simulations to see important waveforms and circuit performance
- Run thermal simulations to understand board thermal performance
- Export customized schematic and layout into popular CAD formats
- Print PDF reports for the design, and share the design with colleagues

Get more information about WEBENCH tools at www.ti.com/WEBENCH.

11.2 Documentation Support

11.2.1 Related Documentation

For related documentation see the following:

- Texas Instruments, *Negative Output Voltage Using the TPSM53602/3/4* application report

11.3 Receiving Notification of Documentation Updates

To receive notification of documentation updates, navigate to the device product folder on ti.com. Click on *Subscribe to updates* to register and receive a weekly digest of any product information that has changed. For change details, review the revision history included in any revised document.

11.4 サポート・リソース

TI E2E™ サポート・フォーラムは、エンジニアが検証済みの回答と設計に関するヒントをエキスパートから迅速かつ直接得ることができる場所です。既存の回答を検索したり、独自の質問をしたりすることで、設計で必要な支援を迅速に得ることができます。

リンクされているコンテンツは、該当する貢献者により、現状のまま提供されるものです。これらは TI の仕様を構成するものではなく、必ずしも TI の見解を反映したものではありません。TI の使用条件を参照してください。

11.5 Trademarks

の Enhanced HotRod™ and TI E2E™ are trademarks of Texas Instruments.
WEBENCH® are registered trademarks of Texas Instruments.
すべての商標は、それぞれの所有者に帰属します。

11.6 Electrostatic Discharge Caution



This integrated circuit can be damaged by ESD. Texas Instruments recommends that all integrated circuits be handled with appropriate precautions. Failure to observe proper handling and installation procedures can cause damage.

ESD damage can range from subtle performance degradation to complete device failure. Precision integrated circuits may be more susceptible to damage because very small parametric changes could cause the device not to meet its published specifications.

11.7 Glossary

TI Glossary This glossary lists and explains terms, acronyms, and definitions.

12 Mechanical, Packaging, and Orderable Information

The following pages include mechanical packaging and orderable information. This information is the most current data available for the designated devices. This data is subject to change without notice and revision of this document. For browser-based versions of this data sheet, refer to the left-hand navigation.

Copyright © 2021 Texas Instruments Incorporated

PACKAGING INFORMATION

Orderable part number	Status (1)	Material type (2)	Package | Pins	Package qty | Carrier	RoHS (3)	Lead finish/ Ball material (4)	MSL rating/ Peak reflow (5)	Op temp (°C)	Part marking (6)
PTPSM53604RDAR	Obsolete	Preproduction	B3QFN (RDA) | 15	-	-	Call TI	Call TI	-40 to 125	P53604
TPSM53604RDAR	Active	Production	B3QFN (RDA) | 15	1000 | LARGE T&R	Yes	NIPDAU	Level-3-245C-168 HR	-40 to 125	TPSM53604
TPSM53604RDAR.A	Active	Production	B3QFN (RDA) | 15	1000 | LARGE T&R	Yes	NIPDAU	Level-3-245C-168 HR	-40 to 125	TPSM53604
TPSM53604RDARG4	Active	Production	B3QFN (RDA) | 15	1000 | LARGE T&R	Yes	NIPDAU	Level-3-245C-168 HR	-40 to 125	TPSM53604
TPSM53604RDARG4.A	Active	Production	B3QFN (RDA) | 15	1000 | LARGE T&R	Yes	NIPDAU	Level-3-245C-168 HR	-40 to 125	TPSM53604

(1) **Status:** For more details on status, see our product life cycle.

(2) **Material type:** When designated, preproduction parts are prototypes/experimental devices, and are not yet approved or released for full production. Testing and final process, including without limitation quality assurance, reliability performance testing, and/or process qualification, may not yet be complete, and this item is subject to further changes or possible discontinuation. If available for ordering, purchases will be subject to an additional waiver at checkout, and are intended for early internal evaluation purposes only. These items are sold without warranties of any kind.

(3) **RoHS values:** Yes, No, RoHS Exempt. See the TI RoHS Statement for additional information and value definition.

(4) **Lead finish/Ball material:** Parts may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead finish/Ball material values may wrap to two lines if the finish value exceeds the maximum column width.

(5) **MSL rating/Peak reflow:** The moisture sensitivity level ratings and peak solder (reflow) temperatures. In the event that a part has multiple moisture sensitivity ratings, only the lowest level per JEDEC standards is shown. Refer to the shipping label for the actual reflow temperature that will be used to mount the part to the printed circuit board.

(6) **Part marking:** There may be an additional marking, which relates to the logo, the lot trace code information, or the environmental category of the part.


Multiple part markings will be inside parentheses. Only one part marking contained in parentheses and separated by a "~" will appear on a part. If a line is indented then it is a continuation of the previous line and the two combined represent the entire part marking for that device.

Important Information and Disclaimer: The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.


In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.

TAPE AND REEL INFORMATION

REEL DIMENSIONS




TAPE DIMENSIONS



A0	Dimension designed to accommodate the component width
B0	Dimension designed to accommodate the component length
K0	Dimension designed to accommodate the component thickness
W	Overall width of the carrier tape
P1	Pitch between successive cavity centers


QUADRANT ASSIGNMENTS FOR PIN 1 ORIENTATION IN TAPE



*All dimensions are nominal

Device	Package Type	Package Drawing	Pins	SPQ	Reel Diameter (mm)	Reel Width W1 (mm)	A0 (mm)	B0 (mm)	K0 (mm)	P1 (mm)	W (mm)	Pin1 Quadrant
TPSM53604RDAR	B3QFN	RDA	15	1000	330.0	16.4	5.28	5.78	4.28	8.0	16.0	Q1
TPSM53604RDARG4	B3QFN	RDA	15	1000	330.0	16.4	5.28	5.78	4.28	8.0	16.0	Q1

TAPE AND REEL BOX DIMENSIONS



*All dimensions are nominal


Device	Package Type	Package Drawing	Pins	SPQ	Length (mm)	Width (mm)	Height (mm)
TPSM53604RDAR	B3QFN	RDA	15	1000	336.0	336.0	48.0
TPSM53604RDARG4	B3QFN	RDA	15	1000	336.0	336.0	48.0

RDA0015A

PACKAGE OUTLINE

B3QFN - 4.1 mm max height

PLASTIC QUAD FLATPACK - NO LEAD



NOTES:


1. All linear dimensions are in millimeters. Any dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.
2. This drawing is subject to change without notice.
3. The package thermal pad must be soldered to the printed circuit board for optimal thermal and mechanical performance.

EXAMPLE BOARD LAYOUT

RDA0015A

B3QFN - 4.1 mm max height

PLASTIC QUAD FLATPACK - NO LEAD



LAND PATTERN EXAMPLE
EXPOSED METAL SHOWN
SCALE: 16X



SOLDER MASK DETAILS

4224086/C 03/2019

NOTES: (continued)


4. This package is designed to be soldered to a thermal pad on the board. For more information, see Texas Instruments literature number SLUA271 (www.ti.com/lit/slua271).
5. Vias are optional depending on application, refer to device data sheet. If any vias are implemented, refer to their locations shown on this view. It is recommended that vias under paste be filled, plugged or tented.

EXAMPLE STENCIL DESIGN

RDA0015A

B3QFN - 4.1 mm max height

PLASTIC QUAD FLATPACK - NO LEAD



SOLDER PASTE EXAMPLE
BASED ON 0.125 mm THICK STENCIL

EXPOSED PAD 15:
56% PRINTED SOLDER COVERAGE BY AREA
SCALE: 16X

4224086/C 03/2019

NOTES: (continued)

6. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.

重要なお知らせと免責事項

TI は、技術データと信頼性データ (データシートを含みます)、設計リソース (リファレンス デザインを含みます)、アプリケーションや設計に関する各種アドバイス、Web ツール、安全性情報、その他のリソースを、欠陥が存在する可能性のある「現状のまま」提供しており、商品性および特定目的に対する適合性の黙示保証、第三者の知的財産権の非侵害保証を含むいかなる保証も、明示的または黙示的にかかわらず拒否します。

これらのリソースは、TI 製品を使用する設計の経験を積んだ開発者への提供を意図したものです。(1) お客様のアプリケーションに適した TI 製品の選定、(2) お客様のアプリケーションの設計、検証、試験、(3) お客様のアプリケーションに該当する各種規格や、その他のあらゆる安全性、セキュリティ、規制、または他の要件への確実な適合に関する責任を、お客様のみが単独で負うものとします。

上記の各種リソースは、予告なく変更される可能性があります。これらのリソースは、リソースで説明されている TI 製品を使用するアプリケーションの開発の目的でのみ、TI はその使用をお客様に許諾します。これらのリソースに関して、他の目的で複製することや掲載することは禁止されています。TI や第三者の知的財産権のライセンスが付与されている訳ではありません。お客様は、これらのリソースを自身で使用した結果発生するあらゆる申し立て、損害、費用、損失、責任について、TI およびその代理人を完全に補償するものとし、TI は一切の責任を拒否します。

TI の製品は、 TI の販売条件 、 TI の総合的な品質ガイドライン 、 ti.com または TI 製品などに関連して提供される他の適用条件に従い提供されます。TI がこれらのリソースを提供することは、適用される TI の保証または他の保証の放棄の拡大や変更を意味するものではありません。 TI がカスタム、またはカスタマー仕様として明示的に指定していない限り、TI の製品は標準的なカタログに掲載される汎用機器です。

お客様がいかなる追加条項または代替条項を提案する場合も、TI はそれらに異議を唱え、拒否します。

Copyright © 2026, Texas Instruments Incorporated

最終更新日：2025 年 10 月