

# TSDxxC 双方向 TVS (過渡電圧サプレッサ) ダイオード、SOD-323 パッケージ

## 1 特長

- IEC 61000-4-2 ESD 保護:
  - ±30kV 接触放電
  - ±30kV エアギャップ放電
- IEC 61000-4-5 サージ保護:
  - 6.5-30A (8/20μs)
- 低い IO 容量 < 7pF (標準値)
- 超低リーク電流: 10nA (最大値)
- 産業用温度範囲: -55°C ~ +150°C
- 業界標準の SOD-323 リード付きパッケージ (2.65mm × 1.3mm)

## 2 アプリケーション

- I/O 保護
- 電源ライン保護
- USB VBUS
- 電化製品
- 医療/ヘルスケア
- リテールオートメーション

## 3 概要

TSDxxC は双方向 TVS 保護ダイオードであり、ESD やサージなどの有害な過渡電圧をクランプするよう設計されています。TSDxxC は、最大 ±30kV の ESD 衝撃 (接触放電および気中放電) を吸収する定格を備えており、IEC 61000-4-2 国際規格 (レベル 4) で規定されている最大レベルをクリアしています。


このデバイスの堅牢なクランプ性能と低容量を組み合わせることで TSDxxC は、優れた TVS ダイオードとなり、さまざまなアプリケーションでデータラインおよび電源ラインを保護します。

TSDxxC は、業界標準のリード付き SOD-323 パッケージで供給され、半田付けが容易です。

### パッケージ情報

| 部品番号   | パッケージ (1)        | パッケージ サイズ (2)  |
|--------|------------------|----------------|
| TSDxxC | DYF (SOD-323, 2) | 2.65mm × 1.3mm |

- 詳細については、[セクション 9](#) を参照してください。
- パッケージ サイズ (長さ × 幅) は公称値であり、該当する場合はピンも含まれます。



機能ブロック図



## Table of Contents

|                                                |          |                                                              |           |
|------------------------------------------------|----------|--------------------------------------------------------------|-----------|
| <b>1 特長</b> .....                              | <b>1</b> | 5.10 Electrical Characteristics - TSD24C.....                | <b>9</b>  |
| <b>2 アプリケーション</b> .....                        | <b>1</b> | 5.11 Electrical Characteristics - TSD36C.....                | <b>10</b> |
| <b>3 概要</b> .....                              | <b>1</b> | 5.12 Typical Characteristics.....                            | <b>11</b> |
| <b>4 Pin Configuration and Functions</b> ..... | <b>3</b> | <b>6 Application and Implementation</b> .....                | <b>13</b> |
| <b>5 Specifications</b> .....                  | <b>3</b> | 6.1 Application Information.....                             | <b>13</b> |
| 5.1 Absolute Maximum Ratings.....              | <b>3</b> | <b>7 Device and Documentation Support</b> .....              | <b>13</b> |
| 5.2 ESD Ratings—JEDEC Specification.....       | <b>4</b> | 7.1 Documentation Support.....                               | <b>13</b> |
| 5.3 ESD Ratings—IEC Specification.....         | <b>4</b> | 7.2 ドキュメントの更新通知を受け取る方法.....                                  | <b>13</b> |
| 5.4 Recommended Operating Conditions.....      | <b>4</b> | 7.3 サポート・リソース.....                                           | <b>13</b> |
| 5.5 Thermal Information.....                   | <b>4</b> | 7.4 Trademarks.....                                          | <b>13</b> |
| 5.6 Electrical Characteristics - TSD05C.....   | <b>5</b> | 7.5 静電気放電に関する注意事項.....                                       | <b>13</b> |
| 5.7 Electrical Characteristics - TSD12C.....   | <b>6</b> | 7.6 用語集.....                                                 | <b>13</b> |
| 5.8 Electrical Characteristics - TSD15C.....   | <b>7</b> | <b>8 Revision History</b> .....                              | <b>14</b> |
| 5.9 Electrical Characteristics - TSD18C.....   | <b>8</b> | <b>9 Mechanical, Packaging, and Orderable Information</b> .. | <b>14</b> |

## 4 Pin Configuration and Functions




図 4-1. DYF Package, 2-Pin SOD-323 (Top View)

表 4-1. Pin Functions

| PIN |      | TYPE <sup>(1)</sup> | DESCRIPTION                                               |
|-----|------|---------------------|-----------------------------------------------------------|
| NO. | NAME |                     |                                                           |
| 1   | IO   | I/O                 | Protected Channel. If used as IO, connect pin 2 to ground |
| 2   | IO   | I/O                 | Protected Channel. If used as IO, connect pin 1 to ground |

(1) I = input, O = output

## 5 Specifications

### 5.1 Absolute Maximum Ratings

over operating free-air temperature range (unless otherwise noted) <sup>(1)</sup>

| Parameter        |                                                                  | DEVICE | MIN | MAX | UNIT |
|------------------|------------------------------------------------------------------|--------|-----|-----|------|
| P <sub>PP</sub>  | IEC 61000-4-5 (t <sub>p</sub> 8/20μs) Peak Pulse Power at 25°C   | TSD05C |     | 400 | W    |
| P <sub>PP</sub>  | IEC 61000-4-5 (t <sub>p</sub> 8/20μs) Peak Pulse Power at 25°C   | TSD12C |     | 390 | W    |
|                  |                                                                  | TSD15C |     |     |      |
|                  |                                                                  | TSD18C |     |     |      |
|                  |                                                                  | TSD24C |     |     |      |
|                  |                                                                  | TSD36C |     | 400 | W    |
| I <sub>PP</sub>  | IEC 61000-4-5 (t <sub>p</sub> 8/20μs) Peak Pulse Current at 25°C | TSD05C |     | 30  | A    |
| I <sub>PP</sub>  | IEC 61000-4-5 (t <sub>p</sub> 8/20μs) Peak Pulse Current at 25°C | TSD12C |     | 15  | A    |
|                  |                                                                  | TSD15C |     | 12  | A    |
|                  |                                                                  | TSD18C |     |     |      |
|                  |                                                                  | TSD24C |     | 9   | A    |
|                  |                                                                  | TSD36C |     | 6.5 | A    |
| T <sub>A</sub>   | Ambient Operating Temperature                                    |        | -55 | 150 | °C   |
| T <sub>stg</sub> | Storage Temperature                                              |        | -65 | 155 | °C   |

(1) Operation outside the Absolute Maximum Ratings may cause permanent device damage. Absolute maximum ratings do not imply functional operation of the device at these or any other conditions beyond those listed under Recommended Operating Conditions. If briefly operating outside the Recommended Operating Conditions but within the Absolute Maximum Ratings, the device may not sustain damage, but it may not be fully functional. Operating the device in this manner may affect device reliability, functionality, performance, and shorten the device lifetime.

## 5.2 ESD Ratings—JEDEC Specification

|                    |                         |                                                                           | VALUE | UNIT |
|--------------------|-------------------------|---------------------------------------------------------------------------|-------|------|
| V <sub>(ESD)</sub> | Electrostatic discharge | Human body model (HBM), per ANSI/ESDA/JEDEC JS-001 <sup>(1)</sup>         | ±2500 | V    |
|                    |                         | Charged device model (CDM), per JEDEC specification JS-002 <sup>(2)</sup> | ±1000 | V    |

(1) JEDEC document JEP155 states that 500-V HBM allows safe manufacturing with a standard ESD control process.

(2) JEDEC document JEP157 states that 250-V CDM allows safe manufacturing with a standard ESD control process.

## 5.3 ESD Ratings—IEC Specification

|                    |                         |                                 | VALUE  | UNIT |
|--------------------|-------------------------|---------------------------------|--------|------|
| V <sub>(ESD)</sub> | Electrostatic discharge | IEC 61000-4-2 contact discharge | ±30000 | V    |
|                    |                         | IEC 61000-4-2 air-gap discharge | ±30000 |      |

## 5.4 Recommended Operating Conditions

over operating free-air temperature range (unless otherwise noted)

|                |                                | MIN | NOM | MAX | UNIT |
|----------------|--------------------------------|-----|-----|-----|------|
| T <sub>A</sub> | Operating free-air temperature | -55 |     | 150 | °C   |

## 5.5 Thermal Information

| THERMAL METRIC <sup>(1)</sup> |                                              | TSD05C        | TSD12C / TSD15C / TSD18C | TSD24C / TSD36C | UNIT |
|-------------------------------|----------------------------------------------|---------------|--------------------------|-----------------|------|
|                               |                                              | DYF (SOD-323) | DYF (SOD-323)            | DYF (SOD-323)   |      |
|                               |                                              | 2 PINS        | 2 PINS                   | 2 PINS          |      |
| R <sub>θJA</sub>              | Junction-to-ambient thermal resistance       | 672.0         | 683.8                    | 686.1           | °C/W |
| R <sub>θJC(top)</sub>         | Junction-to-case (top) thermal resistance    | 230.5         | 264.2                    | 267.0           | °C/W |
| R <sub>θJB</sub>              | Junction-to-board thermal resistance         | 541.4         | 559.0                    | 560.5           | °C/W |
| Ψ <sub>JT</sub>               | Junction-to-top characterization parameter   | 64.4          | 89.9                     | 91.4            | °C/W |
| Ψ <sub>JB</sub>               | Junction-to-board characterization parameter | 527.5         | 544.8                    | 546.2           | °C/W |
| R <sub>θJC(bot)</sub>         | Junction-to-case (bottom) thermal resistance | N/A           | N/A                      | N/A             | °C/W |

(1) For more information about traditional and new thermal metrics, see the [Semiconductor and IC Package Thermal Metrics](#) application report.

## 5.6 Electrical Characteristics - TSD05C

At TA=25°C (unless otherwise noted) <sup>(1)</sup>

| PARAMETER          |                                                                 | TEST CONDITION                                              | MIN  | TYP  | MAX  | UNIT |
|--------------------|-----------------------------------------------------------------|-------------------------------------------------------------|------|------|------|------|
| V <sub>RWM</sub>   | Reverse stand-off voltage                                       | I <sub>IO</sub> < 50 nA, across operating temperature range | -5.5 |      | 5.5  | V    |
| V <sub>BR</sub>    | Break-down voltage                                              | I <sub>IO</sub> = 1 mA, IO to GND and GND to IO             | 7    | 8    | 9    | V    |
| I <sub>LEAK</sub>  | Reverse leakage current                                         | V <sub>IO</sub> = 5.5 V, IO to GND or GND to IO             |      | 5    | 10   | nA   |
| V <sub>CLAMP</sub> | Surge clamping voltage, t <sub>p</sub> = 8/20 μs <sup>(2)</sup> | I <sub>PP</sub> = 24 A, IO to GND or GND to IO              |      | 10.7 | 13.8 | V    |
|                    |                                                                 | I <sub>PP</sub> = 30 A, IO to GND or GND to IO              |      | 11.5 | 15   | V    |
|                    | TLP clamping voltage, t <sub>p</sub> = 100 ns                   | I <sub>PP</sub> = 16 A, IO to GND or GND to IO              |      | 9.3  |      | V    |
| R <sub>DYN</sub>   | Dynamic resistance <sup>(3)</sup>                               | IO to GND                                                   |      | 0.15 |      | Ω    |
|                    |                                                                 | GND to IO                                                   |      |      |      |      |
| C <sub>L</sub>     | Line capacitance                                                | V <sub>IO</sub> = 0 V; f = 1 MHz, IO to GND                 |      | 4    | 7    | pF   |

(1) Typical parameters are measured at 25°C

(2) Nonrepetitive current pulse 8 to 20 μs exponentially decaying waveform according to IEC 61000-4-5

(3) Extraction of R<sub>DYN</sub> using least squares fit of TLP characteristics between I = 10 A and I = 20 A

## 5.7 Electrical Characteristics - TSD12C

At TA=25°C (unless otherwise noted) <sup>(1)</sup>

| PARAMETER          |                                                                 | TEST CONDITION                                              | MIN  | TYP  | MAX  | UNIT |
|--------------------|-----------------------------------------------------------------|-------------------------------------------------------------|------|------|------|------|
| V <sub>RWM</sub>   | Reverse stand-off voltage                                       | I <sub>IO</sub> < 10 nA, across operating temperature range |      |      | 12   | V    |
| V <sub>BRR</sub>   | Breakdown voltage                                               | I <sub>IO</sub> = 10 mA, IO to GND and GND to IO            | 13.2 | 15.6 | 19   | V    |
| I <sub>LEAK</sub>  | Reverse leakage current                                         | V <sub>IO</sub> = 12 V, IO to GND or GND to IO              |      | 5    | 10   | nA   |
| V <sub>CLAMP</sub> | Surge clamping voltage, t <sub>p</sub> = 8/20 μs <sup>(2)</sup> | I <sub>PP</sub> = 1 A, IO to GND or GND to IO               |      |      | 18.5 | V    |
|                    |                                                                 | I <sub>PP</sub> = 5 A, IO to GND or GND to IO               |      |      | 21   | V    |
|                    |                                                                 | I <sub>PP</sub> = 15 A, IO to GND or GND to IO              |      |      | 26   | V    |
|                    | TLP clamping voltage, t <sub>p</sub> = 100 ns                   | I <sub>PP</sub> = 16 A, IO to GND or GND to IO              |      | 19.4 |      | V    |
| R <sub>DYN</sub>   | Dynamic resistance <sup>(3)</sup>                               | IO to GND                                                   |      | 0.15 |      | Ω    |
|                    |                                                                 | GND to IO                                                   |      |      |      |      |
| C <sub>L</sub>     | Line capacitance                                                | V <sub>IO</sub> = 0 V; f = 1 MHz, IO to GND                 |      | 6.5  | 8    | pF   |

(1) Typical parameters are measured at 25°C

(2) Nonrepetitive current pulse 8 to 20 μs exponentially decaying waveform according to IEC 61000-4-5

(3) Extraction of R<sub>DYN</sub> using least squares fit of TLP characteristics between I = 10 A and I = 20 A

## 5.8 Electrical Characteristics - TSD15C

At TA=25°C (unless otherwise noted) <sup>(1)</sup>

| PARAMETER          |                                                                 | TEST CONDITION                                              | MIN | TYP | MAX  | UNIT |
|--------------------|-----------------------------------------------------------------|-------------------------------------------------------------|-----|-----|------|------|
| V <sub>RWM</sub>   | Reverse stand-off voltage                                       | I <sub>IO</sub> < 10 nA, across operating temperature range |     |     | 15   | V    |
| V <sub>BRR</sub>   | Breakdown voltage                                               | I <sub>IO</sub> = 10 mA, IO to GND and GND to IO            | 19  | 22  | 25   | V    |
| I <sub>LEAK</sub>  | Reverse leakage current                                         | V <sub>IO</sub> = 15 V, IO to GND or GND to IO              |     | 5   | 10   | nA   |
| V <sub>CLAMP</sub> | Surge clamping voltage, t <sub>p</sub> = 8/20 μs <sup>(2)</sup> | I <sub>PP</sub> = 1 A, IO to GND or GND to IO               |     |     | 25.6 | V    |
|                    |                                                                 | I <sub>PP</sub> = 5 A, IO to GND or GND to IO               |     |     | 28   | V    |
|                    |                                                                 | I <sub>PP</sub> = 12 A, IO to GND or GND to IO              |     |     | 33   | V    |
|                    | TLP clamping voltage, t <sub>p</sub> = 100 ns                   | I <sub>PP</sub> = 16 A, IO to GND or GND to IO              |     | 25  |      | V    |
| R <sub>DYN</sub>   | Dynamic resistance <sup>(3)</sup>                               | IO to GND                                                   |     | 0.2 |      | Ω    |
|                    |                                                                 | GND to IO                                                   |     |     |      |      |
| C <sub>L</sub>     | Line capacitance                                                | V <sub>IO</sub> = 0 V; f = 1 MHz, IO to GND                 |     | 6.7 | 9    | pF   |

(1) Typical parameters are measured at 25°C

(2) Nonrepetitive current pulse 8 to 20 μs exponentially decaying waveform according to IEC 61000-4-5

(3) Extraction of R<sub>DYN</sub> using least squares fit of TLP characteristics between I = 10 A and I = 20 A

## 5.9 Electrical Characteristics - TSD18C

At TA=25°C (unless otherwise noted) <sup>(1)</sup>

| PARAMETER          |                                                                 | TEST CONDITION                                              | MIN | TYP | MAX  | UNIT |
|--------------------|-----------------------------------------------------------------|-------------------------------------------------------------|-----|-----|------|------|
| V <sub>RWM</sub>   | Reverse stand-off voltage                                       | I <sub>IO</sub> < 10 nA, across operating temperature range |     |     | 18   | V    |
| V <sub>BRR</sub>   | Breakdown voltage                                               | I <sub>IO</sub> = 10 mA, IO to GND and GND to IO            | 19  | 22  | 25   | V    |
| I <sub>LEAK</sub>  | Reverse leakage current                                         | V <sub>IO</sub> = 18 V, IO to GND or GND to IO              |     | 5   | 10   | nA   |
| V <sub>CLAMP</sub> | Surge clamping voltage, t <sub>p</sub> = 8/20 μs <sup>(2)</sup> | I <sub>PP</sub> = 1 A, IO to GND or GND to IO               |     |     | 25.6 | V    |
|                    |                                                                 | I <sub>PP</sub> = 5 A, IO to GND or GND to IO               |     |     | 28   | V    |
|                    |                                                                 | I <sub>PP</sub> = 12 A, IO to GND or GND to IO              |     |     | 33   | V    |
|                    | TLP clamping voltage, t <sub>p</sub> = 100 ns                   | I <sub>PP</sub> = 16 A, IO to GND or GND to IO              |     | 25  |      | V    |
| R <sub>DYN</sub>   | Dynamic resistance <sup>(3)</sup>                               | IO to GND                                                   |     | 0.2 |      | Ω    |
|                    |                                                                 | GND to IO                                                   |     |     |      |      |
| C <sub>L</sub>     | Line capacitance                                                | V <sub>IO</sub> = 0 V; f = 1 MHz, IO to GND                 |     | 6.7 | 9    | pF   |

(1) Typical parameters are measured at 25°C

(2) Nonrepetitive current pulse 8 to 20 μs exponentially decaying waveform according to IEC 61000-4-5

(3) Extraction of R<sub>DYN</sub> using least squares fit of TLP characteristics between I = 10 A and I = 20 A

## 5.10 Electrical Characteristics - TSD24C

At TA=25°C (unless otherwise noted) <sup>(1)</sup>

| PARAMETER          |                                                                 | TEST CONDITION                                              | MIN  | TYP  | MAX  | UNIT |
|--------------------|-----------------------------------------------------------------|-------------------------------------------------------------|------|------|------|------|
| V <sub>RWM</sub>   | Reverse stand-off voltage                                       | I <sub>IO</sub> < 10 nA, across operating temperature range |      |      | 24   | V    |
| V <sub>BR</sub>    | Breakdown voltage                                               | I <sub>IO</sub> = 10 mA, IO to GND and GND to IO            | 25.5 | 30.5 | 35.5 | V    |
| I <sub>LEAK</sub>  | Reverse leakage current                                         | V <sub>IO</sub> = 24 V, IO to GND or GND to IO              |      | 5    | 10   | nA   |
| V <sub>CLAMP</sub> | Surge clamping voltage, t <sub>p</sub> = 8/20 μs <sup>(2)</sup> | I <sub>PP</sub> = 1 A, IO to GND or GND to IO               |      |      | 34   | V    |
|                    |                                                                 | I <sub>PP</sub> = 5 A, IO to GND or GND to IO               |      |      | 43   | V    |
|                    |                                                                 | I <sub>PP</sub> = 9 A, IO to GND or GND to IO               |      |      | 50   | V    |
|                    | TLP clamping voltage, t <sub>p</sub> = 100 ns                   | I <sub>PP</sub> = 16 A, IO to GND or GND to IO              |      | 36   |      | V    |
| R <sub>DYN</sub>   | Dynamic resistance <sup>(3)</sup>                               | IO to GND                                                   |      | 0.35 |      | Ω    |
|                    |                                                                 | GND to IO                                                   |      |      |      |      |
| C <sub>L</sub>     | Line capacitance                                                | V <sub>IO</sub> = 0 V; f = 1 MHz, IO to GND                 |      | 4.3  | 6    | pF   |

(1) Typical parameters are measured at 25°C

(2) Nonrepetitive current pulse 8 to 20 μs exponentially decaying waveform according to IEC 61000-4-5

(3) Extraction of R<sub>DYN</sub> using least squares fit of TLP characteristics between I = 10 A and I = 20 A

## 5.11 Electrical Characteristics - TSD36C

At TA=25°C (unless otherwise noted) <sup>(1)</sup>

| PARAMETER          |                                                                 | TEST CONDITION                                              | MIN  | TYP  | MAX  | UNIT |
|--------------------|-----------------------------------------------------------------|-------------------------------------------------------------|------|------|------|------|
| V <sub>RWM</sub>   | Reverse stand-off voltage                                       | I <sub>IO</sub> < 50 nA, across operating temperature range |      |      | 36   | V    |
| V <sub>BR</sub>    | Breakdown voltage                                               | I <sub>IO</sub> = 10 mA, I/O to GND and GND to I/O          | 37.8 | 41.2 | 44.2 | V    |
| I <sub>LEAK</sub>  | Reverse leakage current                                         | V <sub>IO</sub> = 36 V, IO to GND or GND to IO              |      | 5    | 10   | nA   |
| V <sub>CLAMP</sub> | Surge clamping voltage, t <sub>p</sub> = 8/20 μs <sup>(2)</sup> | I <sub>PP</sub> = 1 A, IO to GND or GND to IO               |      |      | 47   | V    |
|                    |                                                                 | I <sub>PP</sub> = 5 A, IO to GND or GND to IO               |      |      | 64   | V    |
|                    |                                                                 | I <sub>PP</sub> = 6.5 A, IO to GND or GND to IO             |      |      | 71   | V    |
|                    | TLP clamping voltage, t <sub>p</sub> = 100 ns                   | I <sub>PP</sub> = 16 A, IO to GND or GND to IO              |      | 56   |      | V    |
| R <sub>DYN</sub>   | Dynamic resistance <sup>(3)</sup>                               | IO to GND                                                   |      | 0.6  |      | Ω    |
|                    |                                                                 | GND to IO                                                   |      |      |      |      |
| C <sub>L</sub>     | Line capacitance                                                | V <sub>IO</sub> = 0 V; f = 1 MHz, IO to GND                 |      | 4.3  | 6    | pF   |

(1) Typical parameters are measured at 25°C

(2) Nonrepetitive current pulse 8 to 20 μs exponentially decaying waveform according to IEC 61000-4-5

(3) Extraction of R<sub>DYN</sub> using least squares fit of TLP characteristics between I = 10 A and I = 20 A

## 5.12 Typical Characteristics




図 5-1. Positive TLP Curve - TSD05C




図 5-2. Negative TLP Curve - TSD05C




図 5-3. Positive TLP Curve - TSD12C




図 5-4. Positive TLP Curve - TSD15C




図 5-5. Positive TLP Curve - TSD18C




図 5-6. Positive TLP Curve - TSD24C

## 5.12 Typical Characteristics (continued)




図 5-7. Positive TLP Curve - TSD36C




図 5-8. Capacitance vs Bias Voltage




図 5-9. Leakage Current vs Temperature




図 5-10. Capacitance vs Temperature - TSD05C




図 5-11. Peak Pulse Power Derating Curve




図 5-12. Pulse Power Rating Curve

## 6 Application and Implementation

### 注

Information in the following applications sections is not part of the TI component specification, and TI does not warrant its accuracy or completeness. TI's customers are responsible for determining suitability of components for their purposes, as well as validating and testing their design implementation to confirm system functionality.

### 6.1 Application Information

The TSDxxC are TVS diodes that provide a path to ground for dissipating transient voltage spikes (such as ESD or surge) on signal lines and power lines. Connect the device in parallel to the down stream circuitry for protection. As the current from the transient passes through the TVS, only a small voltage drop is present across the diode. The small voltage drop is presented to the protected IC. The low  $R_{DYN}$  of the triggered TVS holds this voltage ( $V_{CLAMP}$ ) to a safe level for the protected IC. For more information on how to properly use this device, refer to the [ESD Packaging and Layout Guide](#).

## 7 Device and Documentation Support

### 7.1 Documentation Support

#### 7.1.1 Related Documentation

For related documentation, see the following:

- Texas Instruments, [ESD Packaging and Layout Guide application reports](#)
- Texas Instruments, [ESD Layout Guide application reports](#)
- Texas Instruments, [Generic ESD Evaluation Module user's guide](#)
- Texas Instruments, [Reading and Understanding an ESD Protection data sheet](#)

### 7.2 ドキュメントの更新通知を受け取る方法

ドキュメントの更新についての通知を受け取るには、[www.tij.co.jp](http://www.tij.co.jp) のデバイス製品フォルダを開いてください。[通知] をクリックして登録すると、変更されたすべての製品情報に関するダイジェストを毎週受け取ることができます。変更の詳細については、改訂されたドキュメントに含まれている改訂履歴をご覧ください。

### 7.3 サポート・リソース

テキサス・インスツルメンツ E2E™ サポート・フォーラムは、エンジニアが検証済みの回答と設計に関するヒントをエキスパートから迅速かつ直接得ることができる場所です。既存の回答を検索したり、独自の質問をしたりすることで、設計に必要な支援を迅速に得ることができます。

リンクされているコンテンツは、各寄稿者により「現状のまま」提供されるものです。これらはテキサス・インスツルメンツの仕様を構成するものではなく、必ずしもテキサス・インスツルメンツの見解を反映したものではありません。テキサス・インスツルメンツの[使用条件](#)を参照してください。

### 7.4 Trademarks

テキサス・インスツルメンツ E2E™ is a trademark of Texas Instruments.

すべての商標は、それぞれの所有者に帰属します。

### 7.5 静電気放電に関する注意事項



この IC は、ESD によって破損する可能性があります。テキサス・インスツルメンツは、IC を取り扱う際には常に適切な注意を払うことを推奨します。正しい取り扱いおよび設置手順に従わない場合、デバイスを破損するおそれがあります。

ESD による破損は、わずかな性能低下からデバイスの完全な故障まで多岐にわたります。精密な IC の場合、パラメータがわずかに変化するだけで公表されている仕様から外れる可能性があるため、破損が発生しやすくなっています。

### 7.6 用語集

#### テキサス・インスツルメンツ用語集

この用語集には、用語や略語の一覧および定義が記載されています。

## 8 Revision History

資料番号末尾の英字は改訂を表しています。その改訂履歴は英語版に準じています。

### Changes from Revision B (July 2024) to Revision C (October 2024) Page

- TSD12C、TSD15C、TSD18C、TSD24C をデータシートに追加..... [1](#)

### Changes from Revision A (July 2023) to Revision B (July 2024) Page

- TSD36C をデータシートに追加..... [1](#)
- データシートのステータスを以下のように変更:「事前情報」から「量産データ」に変更 ..... [1](#)

## 9 Mechanical, Packaging, and Orderable Information

The following pages include mechanical, packaging, and orderable information. This information is the most current data available for the designated devices. This data is subject to change without notice and revision of this document. For browser-based versions of this data sheet, refer to the left-hand navigation

## 重要なお知らせと免責事項

テキサス・インスツルメンツは、技術データと信頼性データ (データシートを含みます)、設計リソース (リファレンス デザインを含みます)、アプリケーションや設計に関する各種アドバイス、Web ツール、安全性情報、その他のリソースを、欠陥が存在する可能性のある「現状のまま」提供しており、商品性および特定目的に対する適合性の黙示保証、第三者の知的財産権の非侵害保証を含むいかなる保証も、明示的または黙示的にかかわらず拒否します。

これらのリソースは、テキサス・インスツルメンツ製品を使用する設計の経験を積んだ開発者への提供を意図したものです。(1) お客様のアプリケーションに適した テキサス・インスツルメンツ製品の選定、(2) お客様のアプリケーションの設計、検証、試験、(3) お客様のアプリケーションに該当する各種規格や、その他のあらゆる安全性、セキュリティ、規制、または他の要件への確実な適合に関する責任を、お客様のみが単独で負うものとします。

上記の各種リソースは、予告なく変更される可能性があります。これらのリソースは、リソースで説明されている テキサス・インスツルメンツ製品を使用するアプリケーションの開発の目的でのみ、テキサス・インスツルメンツはその使用をお客様に許諾します。これらのリソースに関して、他の目的で複製することや掲載することは禁止されています。テキサス・インスツルメンツや第三者の知的財産権のライセンスが付与されている訳ではありません。お客様は、これらのリソースを自身で使用した結果発生するあらゆる申し立て、損害、費用、損失、責任について、テキサス・インスツルメンツおよびその代理人を完全に補償するものとし、テキサス・インスツルメンツは一切の責任を拒否します。

テキサス・インスツルメンツの製品は、[テキサス・インスツルメンツの販売条件](#)、または [ti.com](https://www.ti.com) やかかる テキサス・インスツルメンツ製品の関連資料などのいずれかを通じて提供する適用可能な条項の下で提供されています。テキサス・インスツルメンツがこれらのリソースを提供することは、適用されるテキサス・インスツルメンツの保証または他の保証の放棄の拡大や変更を意味するものではありません。

お客様がいかなる追加条項または代替条項を提案した場合でも、テキサス・インスツルメンツはそれらに異議を唱え、拒否します。

郵送先住所: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265  
Copyright © 2024, Texas Instruments Incorporated

## PACKAGING INFORMATION

| Orderable part number      | Status<br>(1) | Material type<br>(2) | Package   Pins | Package qty   Carrier | RoHS<br>(3) | Lead finish/<br>Ball material<br>(4) | MSL rating/<br>Peak reflow<br>(5) | Op temp (°C) | Part marking<br>(6) |
|----------------------------|---------------|----------------------|----------------|-----------------------|-------------|--------------------------------------|-----------------------------------|--------------|---------------------|
| <a href="#">TSD05CDYFR</a> | Active        | Production           | SOT (DYF)   2  | 3000   LARGE T&R      | Yes         | SN                                   | Level-3-260C-168 HR               | -40 to 125   | 33KF                |
| TSD05CDYFR.B               | Active        | Production           | SOT (DYF)   2  | 3000   LARGE T&R      | Yes         | SN                                   | Level-3-260C-168 HR               | -55 to 150   | 33KF                |
| <a href="#">TSD12CDYFR</a> | Active        | Production           | SOT (DYF)   2  | 3000   LARGE T&R      | Yes         | SN                                   | Level-3-260C-168 HR               | -55 to 150   | 3JMF                |
| TSD12CDYFR.B               | Active        | Production           | SOT (DYF)   2  | 3000   LARGE T&R      | Yes         | SN                                   | Level-3-260C-168 HR               | -55 to 150   | 3JMF                |
| <a href="#">TSD15CDYFR</a> | Active        | Production           | SOT (DYF)   2  | 3000   LARGE T&R      | Yes         | SN                                   | Level-3-260C-168 HR               | -55 to 150   | 3MLF                |
| TSD15CDYFR.B               | Active        | Production           | SOT (DYF)   2  | 3000   LARGE T&R      | Yes         | SN                                   | Level-3-260C-168 HR               | -55 to 150   | 3MLF                |
| <a href="#">TSD18CDYFR</a> | Active        | Production           | SOT (DYF)   2  | 3000   LARGE T&R      | Yes         | SN                                   | Level-3-260C-168 HR               | -55 to 150   | 3JQF                |
| TSD18CDYFR.B               | Active        | Production           | SOT (DYF)   2  | 3000   LARGE T&R      | Yes         | SN                                   | Level-3-260C-168 HR               | -55 to 150   | 3JQF                |
| <a href="#">TSD24CDYFR</a> | Active        | Production           | SOT (DYF)   2  | 3000   LARGE T&R      | Yes         | SN                                   | Level-3-260C-168 HR               | -55 to 150   | 3GWF                |
| TSD24CDYFR.B               | Active        | Production           | SOT (DYF)   2  | 3000   LARGE T&R      | Yes         | SN                                   | Level-3-260C-168 HR               | -55 to 150   | 3GWF                |
| <a href="#">TSD36CDYFR</a> | Active        | Production           | SOT (DYF)   2  | 3000   LARGE T&R      | Yes         | SN                                   | Level-3-260C-168 HR               | -55 to 150   | 3GNF                |
| TSD36CDYFR.B               | Active        | Production           | SOT (DYF)   2  | 3000   LARGE T&R      | Yes         | SN                                   | Level-3-260C-168 HR               | -55 to 150   | 3GNF                |

<sup>(1)</sup> **Status:** For more details on status, see our [product life cycle](#).

<sup>(2)</sup> **Material type:** When designated, preproduction parts are prototypes/experimental devices, and are not yet approved or released for full production. Testing and final process, including without limitation quality assurance, reliability performance testing, and/or process qualification, may not yet be complete, and this item is subject to further changes or possible discontinuation. If available for ordering, purchases will be subject to an additional waiver at checkout, and are intended for early internal evaluation purposes only. These items are sold without warranties of any kind.

<sup>(3)</sup> **RoHS values:** Yes, No, RoHS Exempt. See the [TI RoHS Statement](#) for additional information and value definition.

<sup>(4)</sup> **Lead finish/Ball material:** Parts may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead finish/Ball material values may wrap to two lines if the finish value exceeds the maximum column width.

<sup>(5)</sup> **MSL rating/Peak reflow:** The moisture sensitivity level ratings and peak solder (reflow) temperatures. In the event that a part has multiple moisture sensitivity ratings, only the lowest level per JEDEC standards is shown. Refer to the shipping label for the actual reflow temperature that will be used to mount the part to the printed circuit board.

<sup>(6)</sup> **Part marking:** There may be an additional marking, which relates to the logo, the lot trace code information, or the environmental category of the part.

Multiple part markings will be inside parentheses. Only one part marking contained in parentheses and separated by a "-" will appear on a part. If a line is indented then it is a continuation of the previous line and the two combined represent the entire part marking for that device.

**Important Information and Disclaimer:** The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.

**OTHER QUALIFIED VERSIONS OF TSD12C, TSD15C, TSD18C, TSD24C, TSD36C :**

- Automotive : [TSD12C-Q1](#), [TSD15C-Q1](#), [TSD18C-Q1](#), [TSD24C-Q1](#), [TSD36C-Q1](#)

NOTE: Qualified Version Definitions:

- Automotive - Q100 devices qualified for high-reliability automotive applications targeting zero defects

## TAPE AND REEL INFORMATION



\*All dimensions are nominal

| Device     | Package Type | Package Drawing | Pins | SPQ  | Reel Diameter (mm) | Reel Width W1 (mm) | A0 (mm) | B0 (mm) | K0 (mm) | P1 (mm) | W (mm) | Pin1 Quadrant |
|------------|--------------|-----------------|------|------|--------------------|--------------------|---------|---------|---------|---------|--------|---------------|
| TSD05CDYFR | SOT          | DYF             | 2    | 3000 | 178.0              | 9.5                | 1.48    | 3.3     | 1.25    | 4.0     | 8.0    | Q1            |
| TSD12CDYFR | SOT          | DYF             | 2    | 3000 | 178.0              | 9.5                | 1.48    | 3.3     | 1.25    | 4.0     | 8.0    | Q1            |
| TSD15CDYFR | SOT          | DYF             | 2    | 3000 | 178.0              | 9.5                | 1.48    | 3.3     | 1.25    | 4.0     | 8.0    | Q1            |
| TSD18CDYFR | SOT          | DYF             | 2    | 3000 | 178.0              | 9.5                | 1.48    | 3.3     | 1.25    | 4.0     | 8.0    | Q1            |
| TSD24CDYFR | SOT          | DYF             | 2    | 3000 | 178.0              | 9.5                | 1.48    | 3.3     | 1.25    | 4.0     | 8.0    | Q1            |
| TSD36CDYFR | SOT          | DYF             | 2    | 3000 | 178.0              | 9.5                | 1.48    | 3.3     | 1.25    | 4.0     | 8.0    | Q1            |

## TAPE AND REEL BOX DIMENSIONS



\*All dimensions are nominal

| Device     | Package Type | Package Drawing | Pins | SPQ  | Length (mm) | Width (mm) | Height (mm) |
|------------|--------------|-----------------|------|------|-------------|------------|-------------|
| TSD05CDYFR | SOT          | DYF             | 2    | 3000 | 210.0       | 200.0      | 42.0        |
| TSD12CDYFR | SOT          | DYF             | 2    | 3000 | 210.0       | 200.0      | 42.0        |
| TSD15CDYFR | SOT          | DYF             | 2    | 3000 | 210.0       | 200.0      | 42.0        |
| TSD18CDYFR | SOT          | DYF             | 2    | 3000 | 210.0       | 200.0      | 42.0        |
| TSD24CDYFR | SOT          | DYF             | 2    | 3000 | 210.0       | 200.0      | 42.0        |
| TSD36CDYFR | SOT          | DYF             | 2    | 3000 | 210.0       | 200.0      | 42.0        |


DYF0002A



## PACKAGE OUTLINE

SOT(SOD-323) - 1 mm max height

SMALL OUTLINE TRANSISTOR



4228484/C 12/2024

### NOTES:


1. All linear dimensions are in millimeters. Any dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.
2. This drawing is subject to change without notice.

# EXAMPLE BOARD LAYOUT


DYF0002A

SOT(SOD-323) - 1 mm max height

SMALL OUTLINE TRANSISTOR



LAND PATTERN EXAMPLE  
EXPOSED METAL SHOWN  
SCALE:25X



SOLDER MASK DETAILS

4228484/C 12/2024

NOTES: (continued)


3. Publication IPC-7351 may have alternate designs.
4. Solder mask tolerances between and around signal pads can vary based on board fabrication site.

## EXAMPLE STENCIL DESIGN

DYF0002A

SOT(SOD-323) - 1 mm max height

SMALL OUTLINE TRANSISTOR



SOLDER PASTE EXAMPLE  
BASED ON 0.125 mm THICK STENCIL  
SCALE:25X

4228484/C 12/2024

NOTES: (continued)

5. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.
6. Board assembly site may have different recommendations for stencil design.

## 重要なお知らせと免責事項

TI は、技術データと信頼性データ (データシートを含みます)、設計リソース (リファレンス デザインを含みます)、アプリケーションや設計に関する各種アドバイス、Web ツール、安全性情報、その他のリソースを、欠陥が存在する可能性のある「現状のまま」提供しており、商品性および特定目的に対する適合性の黙示保証、第三者の知的財産権の非侵害保証を含むいかなる保証も、明示的または黙示的にかかわらず拒否します。

これらのリソースは、TI 製品を使用する設計の経験を積んだ開発者への提供を意図したものです。(1) お客様のアプリケーションに適した TI 製品の選定、(2) お客様のアプリケーションの設計、検証、試験、(3) お客様のアプリケーションに該当する各種規格や、その他のあらゆる安全性、セキュリティ、規制、または他の要件への確実な適合に関する責任を、お客様のみが単独で負うものとし、TI は一切の責任を拒否します。

上記の各種リソースは、予告なく変更される可能性があります。これらのリソースは、リソースで説明されている TI 製品を使用するアプリケーションの開発の目的でのみ、TI はその使用をお客様に許諾します。これらのリソースに関して、他の目的で複製することや掲載することは禁止されています。TI や第三者の知的財産権のライセンスが付与されている訳ではありません。お客様は、これらのリソースを自身で使用した結果発生するあらゆる申し立て、損害、費用、損失、責任について、TI およびその代理人を完全に補償するものとし、TI は一切の責任を拒否します。

TI の製品は、[TI の販売条件](#)、[TI の総合的な品質ガイドライン](#)、[ti.com](https://www.ti.com) または TI 製品などに関連して提供される他の適用条件に従い提供されます。TI がこれらのリソースを提供することは、適用される TI の保証または他の保証の放棄の拡大や変更を意味するものではありません。TI がカスタム、またはカスタマー仕様として明示的に指定していない限り、TI の製品は標準的なカタログに掲載される汎用機器です。

お客様がいかなる追加条項または代替条項を提案する場合も、TI はそれらに異議を唱え、拒否します。

Copyright © 2026, Texas Instruments Incorporated

最終更新日：2025 年 10 月