





BQ25601 JAJSDT3A - MARCH 2017 - REVISED MARCH 2023

BQ25601 高入力電圧および NVDC パワー・パス管理向け I²C 制御 1 セル 3A 降 圧バッテリ・チャージャ

1 特長

- 高効率 1.5MHz 同期整流スイッチ・モード降圧チャー
 - 5V 入力から 2A で 92% の充電効率
 - USB 電圧入力 (5V) 用に最適化
 - 軽負荷動作向けに、低消費電力のパルス周波数 変調 (PFM) モードを選択可能
- USB On-The-Go (OTG) をサポート
 - 最大 1.2A を出力可能な昇圧コンバータ
 - 1A 出力で 92% の昇圧効率
 - 正確な定電流 (CC) 制限
 - 最大 500µF の容量性負荷に対するソフトスタート
 - 出力短絡保護
 - 軽負荷動作のための低消費電力 PFM モード
- 1 つの入力で USB 入力および高電圧アダプタに対応
 - 3.9V~13.5V の入力電圧範囲に対応、入力電圧 の絶対最大定格 22V
 - USB 2.0、USB 3.0 規格、高電圧アダプタ (IINDPM) に対応する、プログラム可能な入力電流 制限 (100mA の分解能で 100mA~3.2A)
 - 最高 5.4V の入力電圧制限による最大電力トラッキ ング (VINDPM)
 - バッテリ電圧に自動的に追従する VINDPM スレッ ショルド
 - USB SDP、DCP および非標準アダプタの自動検
- 19.5mΩ のバッテリ放電 MOSFET による高いバッテリ 放電効率
- ナロー VDC (NVDC) パワー・パス管理
 - バッテリ未接続または深放電状態でも即時オン
 - バッテリ補助モードで理想ダイオード動作
- BATFET 制御により出荷モード、ウェイクアップ、完全 システム・リセットをサポート
- 柔軟性の高い、自律および I²C モードにより最適なシ ステム性能を実現
- すべての MOSFET、電流センシング、ループ補償を 含む高度な統合
- 高精度
 - ±0.5% の充電電圧レギュレーション
 - 1.5A で±5% の充電電流レギュレーション
- 安全および規制の認定:
 - IEC 62368-1 最終機器規格

2 アプリケーション

- スマートフォン
- 携帯電話アクセサリ

医療用機器


3 概要

BQ25601 は、シングル・セル・リチウムイオンおよびリチウ ムポリマー・バッテリ向けの、高度に統合された 3A スイッ チ・モード・バッテリ充電管理およびシステム・パワー・パス 管理デバイスです。パワー・パスのインピーダンスが低い ため、スイッチ・モードの動作効率が最適化され、バッテリ 充電時間の短縮と、放電フェーズにおけるバッテリ駆動時 間の延長を実現できます。充電およびシステムの設定に I²C シリアル・インターフェイスを使用できるため、真に柔 軟なソリューションとなります。

製品情報

部品番号	パッケージ ⁽¹⁾	本体サイズ (公称)		
BQ25601	WQFN (24)	4.00mm × 4.00mm		

利用可能なすべてのパッケージについては、このデータシートの 末尾にある注文情報を参照してください。



簡略化されたアプリケーション



Table of Contents

1 特長	1	9.5 Programming	30
2 アプリケーション		9.6 Register Maps	33
3 概要		10 Application and Implementation	
4 Revision History		10.1 Application Information	44
5 概要 (続き)		10.2 Typical Application	45
6 Device Comparison Table		11 Power Supply Recommendations	<mark>5</mark> 1
7 Pin Configuration and Functions		12 Layout	52
8 Specifications		12.1 Layout Guidelines	<mark>52</mark>
8.1 Absolute Maximum Ratings		12.2 Layout Example	<mark>52</mark>
8.2 ESD Ratings		13 Device and Documentation Support	54
8.3 Recommended Operating Conditions		13.1 Device Support	54
8.4 Thermal Information		13.2 Documentation Support	<u>5</u> 4
8.5 Electrical Characteristics		13.3ドキュメントの更新通知を受け取る方法	<mark>5</mark> 4
8.6 Timing Requirements		13.4 サポート・リソース	<mark>5</mark> 4
8.7 Typical Characteristics		13.5 Trademarks	<mark>5</mark> 4
9 Detailed Description		13.6 静電気放電に関する注意事項	<u>5</u> 4
9.1 Overview.		13.7 用語集	54
9.2 Functional Block Diagram		14 Mechanical, Packaging, and Orderable	
9.3 Feature Description		Information	55
9.4 Device Functional Modes			

4 Revision History

Changes from Revision " (March 2017) to Revision A (March 2023)	Page
• IEC 62368-1 対応を追加	1
• データシート全体にわたって WEBENCH を削除	
• Added セクション 6	4
 Deleted OVPFET_DIS = 1 from Quiescent Currents I_{BAT} and I_{VBUS} HIZ Test Co 	nditions in セクション 8.58
• Deleted V _{REGN} MAX values in セクション 8.5	
• Deleted セクション 8.5 table note	8
• Added セクション 8.6	13
• Added last sentence to セクション 9.3.3.5	19
Changed 図 9-3	22
Changed 図 9-4	22
Added 図 9-5	22
· Added Charge termination is disabled for cool and warm conditions. to third pa	ragraph in セクション 9.3.7.5
	22
Changed 図 9-6	
• Changed "fault" to "the timer" in last paragraph of セクション 9.3.7.7	24
• Added セクション 9.4	26
Changed 図 9-7	26
• Changed first sentence in セクション 9.4.3	27
• Added セクション 9.5	30
Changed inclusive terminology throughout document	30
• Changed 010 to 011 in Description in 表 9-13	
Changed Power Path Management Application schematic	
• Added セクション 10.2.1	
• Changed > to ≤ in last paragraph in セクション 10.2.2.3	
• Added セクション 10.2.3	47
• Added セクション 13.2.1	54

Product Folder Links: BQ25601



5 概要 (続き)

BQ25601 は、広範なスマートフォン、タブレットおよび携帯デバイス向けに、高い入力電圧をサポートし、高速充電を行います。入力電圧 / 電流レギュレーションにより、バッテリに最大限の充電電力を供給できます。また、ハイサイド・ゲート・ドライブ用のブートストラップ・ダイオードを内蔵し、システム設計の簡素化を実現しています。 I²C シリアル・インターフェイスを使って充電とシステムの設定ができるので、真に柔軟性の高いソリューションとなります。

このデバイスは、標準の USB ホスト・ポート、USB 充電ポート、USB 対応高電圧アダプタなど、幅広い入力ソースをサポートしています。また、内蔵された USB インターフェイスによって、デフォルトの入力電流制限を設定しています。デフォルトの入力電流制限を設定するためには、USB PHY デバイスなどシステムに内蔵されている検出回路の結果を使用します。入力電流および電圧レギュレーションにより、USB 2.0 および USB 3.0 の電力仕様に準拠しています。また、このデバイスは USB On-the-Go (OTG) の動作電力定格仕様にも適合しており、VBUS 上で最大 1.2A までの定電流制限付きで 5.15V を供給します。

パワー・パス管理により、システムはバッテリ電圧より少し高く、かつ、最低システム電圧 (プログラム可能) の 3.5V より低下しないようにレギュレートされます。この機能により、システムはバッテリが完全に消耗したとき、または取り除かれたときでも動作を継続できます。入力電流制限または電圧制限に達すると、パワー・パス管理により、充電電流が自動的にゼロまで低下します。システム負荷が引き続き増大すると、パワー・パスは、システムの電力要件が満たされるまでバッテリを放電します。この補助モードにより入力ソースの過負荷を防止します。

このデバイスはソフトウェア制御なしに、充電サイクルを開始、終了できます。バッテリ電圧を感知し、プレコンディショニング、定電流、定電圧という3つのフェーズを移行してバッテリを充電します。充電サイクルの終了時、充電電流があらかじめ設定された制限値を下回り、バッテリ電圧が再充電スレッショルドを上回ると、チャージャは自動的に処理を終了します。十分に充電されたバッテリが再充電スレッショルドを下回ると、チャージャは自動的に次の充電サイクルを開始します。

このチャージャは、バッテリの負温度係数サーミスタ監視、充電安全タイマ、過電圧および過電流保護など、バッテリ充電とシステム運用のための多様な安全機能を備えています。サーマル・レギュレーションにより、接合部温度が 110℃ (プログラム可能) を超えると充電電流が低減されます。STAT 出力により、充電状態とフォルト状態がレポートされます。その他の安全機能として、充電および昇圧モードでのバッテリ温度センシング、サーマル・レギュレーションおよびサーマル・シャットダウン、入力 UVLO および過電圧保護があります。VBUS_GD ビットは、適切な電源が存在することを示します。フォルトが発生すると、INT 出力により即座にホストに通知します。

このデバイスは、QON ピンで BATFET イネーブルおよびリセットを制御することにより、低消費電力の出荷モードを終了したり、あるいはシステム全体のリセット機能を実行したりできます。

このデバイスは、24 ピン、4mm × 4mm × 0.75mm の薄型 WQFN パッケージで供給されます。



6 Device Comparison Table

	BQ25601	BQ25601D	BQ25611D
Programmable charge voltage	3.856 - 4.624 V, 32 mV per step	3.856 - 4.624 V, 32 mV per step	3.5 - 4.3 V (100 mV per step); 4.3 - 4.52 V (10 mV per step)
D+/D- USB detection	No	Yes	Yes
Default I _{CHG}	2.04 A	2.04 A	1 A
Default V _{ACOV}	6.4 V	6.4 V	14.2 V
VBUS OVP reaction time	200 ns	200 ns	130 ns
Battery remote sensing with open/ short detection	No	No	Yes
TS profile	JEITA, with fixed temperature thresholds	JEITA, with fixed temperature thresholds	JEITA, with adjustable temperature thresholds
TS ignore bit	No	No	Yes
Charge safety timer	5 hr, 10 hr (default)	5 hr, 10 hr (default)	20 hr, 10 hr (default)
Allow QON fire when adapter is present	No	No	Yes
Deglitch time for charge ternination	250 ms	250 ms	50 ms



7 Pin Configuration and Functions




図 7-1. RTW Package 24-Pin WQFN Top View

表 7-1. Pin Functions

F	PIN	TYPE ⁽¹⁾	DESCRIPTION				
NAME	NO.	ITPE	DESCRIPTION				
BAT	13	Р	Battery connection point to the positive terminal of the battery pack. The internal BATFET and current sensing is				
DAI	14		onnected between SYS and BAT. Connect a 10 μF close to the BAT pin.				
BTST	21	Р	PWM high side driver positive supply. Internally, the BTST pin is connected to the cathode of the boost-strap diode. Connect the 0.047-µF bootstrap capacitor from SW to BTST.				
CE	9	DI	Charge enable pin. When this pin is driven low, battery charging is enabled.				
GND	17	Р	Ground.				
GIND	18		Giodna.				
INT	7	DO	Open-drain interrupt Output. Connect the INT to a logic rail through 10-kΩ resistor. The INT pin sends an active low, 256-μs pulse to host to report charger device status and fault.				
NC 8 —							
			No Connect. Keep the pins float.				
PG	3	DO	Open drain active low power good indicator. Connect to the pull up rail through 10-k Ω resistor. LOW indicates a good input source if the input voltage is between UVLO and ACOV, above SLEEP mode threshold, and current limit is above 30 mA.				
PMID	23	DO	Connected to the drain of the reverse blocking MOSFET (RBFET) and the drain of HSFET. Put 10 µF ceramic capacitor on PMID to GND.				
PSEL	2	DI	Power source selection input. Set 500 mA input current limit by pulling this pin high and set 2.4A input current limit by pulling this pin low. Once the device gets into host mode, the host can program different input current limits to IINDPM register.				
QON	12	DI	BATFET enable/reset control input. When BATFET is in ship mode, a logic low of t _{SHIPMODE} duration turns on BATFET to exit shipping mode. When VBUS is not plugged in, a logic low of t _{QON_RST} (minimum 8 s) duration resets SYS (system power) by turning BATFET off for t _{BATFET_RST} (minimum 250 ms) and then re-enable BATFET to provide full system power reset. The pin contains an internal 200-kΩ pull-up to maintain default high logic.				
REGN	22	Р	LSFET driver and internal supply output. Internally, REGN is connected to the anode of the boost-strap diode. Connect a 4.7-µF (10-V rating) ceramic capacitor from REGN to GND. The capacitor should be placed close to the IC.				
SCL	5	DI	l ² C interface clock. Connect SCL to the logic rail through a 10-kΩ resistor.				
SDA	6	DIO	l²C interface data. Connect SDA to the logic rail through a 10-kΩ resistor.				



表 7-1. Pin Functions (continued)

PIN		TYPE ⁽¹⁾	DESCRIPTION
NAME	NO.	ITPE\/	DESCRIPTION
STAT	4	DO	Open-drain charge status output. Connect the STAT pin to a logic rail via $10\text{-}k\Omega$ resistor. The STAT pin indicates charger status. Collect a current limit resister and a LED from a rail to this pin. Charge in progress: LOW Charge complete or charger in SLEEP mode: HIGH Charge suspend (fault response): 1-Hz, 50% duty cycle Pulses This pin can be disabled via EN_ICHG_MON[1:0] register bits.
SW 19 P		В	Switching pade output. Connected to output industor. Connect the 0.047 UE heatstrap connector from SW to DTST
			Switching node output. Connected to output inductor. Connect the 0.047-µF bootstrap capacitor from SW to
SYS 15 P		Р	Converter output connection point. The internal current sensing network is connected between SYS and BAT.
515	16	- P	Connect a 20 µF capacitor close to the SYS pin.
TS	11	AI	Temperature qualification voltage input to support JEITA profile. Connect a negative temperature coefficient thermistor. Program temperature window with a resistor divider from REGN to TS to GND. Charge suspends when TS pin is out of range. When TS pin is not used, connect a 10- $k\Omega$ resistor from REGN to TS and connect a 10- $k\Omega$ resistor from TS to GND. It is recommended to use a 103AT-2 thermistor.
VAC	1	Al	Charge input voltage sense. This pin must be connected to VBUS pin.
VBUS	24	Р	Charger input. The internal n-channel reverse block MOSFET (RBFET) is connected between VBUS and PMID pins. Place a 1-uF ceramic capacitor from VBUS to GND close to device.
Thermal Pad	_	Р	Thermal pad and ground reference. This pad is ground reference for the device and it is also the thermal pad used to conduct heat from the device. This pad should be tied externally to a ground plane through PCB vias under the pad.

⁽¹⁾ Al = Analog input, AO = Analog Output, AIO = Analog input Output, DI = Digital input, DO = Digital Output, DIO = Digital input Output, P = Power



8 Specifications

8.1 Absolute Maximum Ratings

over operating free-air temperature range (unless otherwise noted)(1)

		MIN	MAX	UNIT
Voltage Range (with respect to GND)	VAC, VBUS (converter not switching) ⁽²⁾	-2	22	V
Voltage Range (with respect to GND)	BTST, PMID (converter not switching) ⁽²⁾	-0.3	22	V
Voltage Range (with respect to GND)	SW	-2	16	V
Voltage Range (with respect to GND)	BTST to SW	-0.3	7	V
Voltage Range (with respect to GND)	PSEL	-0.3	7	V
Voltage Range (with respect to GND)	REGN, TS, CE, PG, BAT, SYS (converter not switching)	-0.3	7	V
Output Sink Current	STAT		6	mA
Voltage Range (with respect to GND)	SDA, SCL, ĪNT, QON, STAT	-0.3	7	V
Voltage Range (with respect to GND)	PGND to GND (QFN package only)	-0.3	0.3	V
Output Sink Current	INT		6	mA
Operating junction temperature, T	J	-40	150	°C
Storage temperature, T _{stg}		-65	150	°C

⁽¹⁾ Stresses beyond those listed under Absolute maximum Ratings may cause permanent damage to the device. These are stress ratings only, which do not imply functional operation of the device at these or any other conditions beyond those indicated under Recommended Operating Conditions. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability. All voltage values are with respect to the network ground terminal unless otherwise noted.

(2) VBUS is specified up to 22 V for a maximum of one hour at room temperature

8.2 ESD Ratings

			VALUE	UNIT
		Human body model (HBM), per ANSI/ ESDA/JEDEC JS-001, all pins ⁽¹⁾	±2000	
V _(ESD)	Electrostatic discharge	Charged device model (CDM), per JEDEC specification JESD22-C101, all pins ⁽²⁾	±250	V

- (1) JEDEC document JEP155 states that 500-V HBM allows safe manufacturing with a standard ESD control process.
- (2) JEDEC document JEP157 states that 250-V CDM allows safe manufacturing with a standard ESD control process.

8.3 Recommended Operating Conditions

		MIN	NOM	MAX	UNIT
V _{BUS}	Input voltage	3.9		13.5 ⁽¹⁾	V
I _{in}	Input current (VBUS)			3.25	Α
I _{SWOP}	Output current (SW)			3.25	Α
V _{BATOP}	Battery voltage			4.624	V
I _{BATOP}	Fast charging current			3.0	Α
I _{BATOP}	Discharging current (continuous)			6	Α



8.3 Recommended Operating Conditions (continued)

		MIN	NOM	MAX	UNIT
T _A	Operating ambient temperature	-40		85	°C

⁽¹⁾ The inherent switching noise voltage spikes should not exceed the absolute maximum voltage rating on either the BTST or SW pins. A tight layout minimizes switching noise.

8.4 Thermal Information

		BQ25601	
	THERMAL METRIC ⁽¹⁾	RTW (WQFN)	UNIT
		24 PINS	
$R_{\theta JA}$	Junction-to-ambient thermal resistance	35.6	°C/W
R _{0JC(top)}	Junction-to-case (top) thermal resistance	22.7	°C/W
$R_{\theta JB}$	Junction-to-board thermal resistance	11.9	°C/W
Ψ_{JT}	Junction-to-top characterization parameter	0.2	°C/W
Ψ_{JB}	Junction-to-board characterization parameter	12	°C/W
R ₀ JC(bot)	Junction-to-case (bottom) thermal resistance	2.6	°C/W

⁽¹⁾ For more information about traditional and new thermal metrics, see the Semiconductor and IC Package Thermal Metrics application report, SPRA953.

8.5 Electrical Characteristics

 $V_{VAC_UVLOZ} < V_{VAC} < V_{VAC_OV}$ and $V_{VAC} > V_{BAT} + V_{SLEEP}$, $T_J = -40^{\circ}C$ to 125°C and $T_J = 25^{\circ}C$ for typical values (unless otherwise noted)

	PARAMETER	TEST CONDITIONS	MIN	TYP	MAX	UNIT
QUIESCENT CUR	RRENTS					
I _{BUS}	Battery discharge current (BAT, SW, SYS) in buck mode	V _{BAT} = 4.5 V, V _{BUS} < V _{AC-UVLOZ} , leakage between BAT and VBUS, T _J < 85°C			5	μA
I _{BAT}	Battery discharge current (BAT) in buck mode	V_{BAT} = 4.5 V, HIZ Mode or No VBUS, I2C disabled, BATFET Disabled. T_J < 85°C		17	33	μA
I _{BAT}	Battery discharge current (BAT, SW, SYS)	V _{BAT} = 4.5 V, HIZ Mode or No VBUS, I2C Disabled, BATFET Enabled. T _J < 85°C		58	85	μA
I _{VBUS_HIZ}	Input supply current (VBUS) in buck mode	V _{VBUS} = 5 V, High-Z Mode, No battery		37	50	μΑ
I _{VBUS_HIZ}	Input supply current (VBUS) in buck mode	V _{VBUS} = 12 V, High-Z Mode, No battery		68	90	μΑ
I _{VBUS}	Input supply current (VBUS) in buck mode	V _{VBUS} = 12 V, V _{VBUS} > V _{VBAT} , converter not switching		1.5	3	mA
I _{VBUS}	Input supply current (VBUS) in buck mode	V _{VBUS} > VUVLO, V _{VBUS} > V _{VBAT} , converter switching, VBAT = 3.8V, ISYS = 0A		3		mA
I _{BOOST}	Battery Discharge Current in boost mode	V _{BAT} = 4.2 V, boost mode, I _{VBUS} = 0 A, converter switching		3		mA
VBUS, VAC AND	BAT PIN POWER-UP				·	
V _{BUS_OP}	VBUS operating range	V _{VBUS} rising	3.9		13.5	V
V _{VAC_UVLOZ}	VBUS for active I ² C, no battery Sense VAC pin voltage	V _{VAC} rising		3.3	3.6	V
V _{VAC_UVLOZ_HYS}	I ² C active hysteresis	V _{AC} falling from above V _{VAC_UVLOZ}		300		mV
V _{VAC_PRESENT}	One of the conditions to turn on REGN	V _{VAC} rising		3.65	3.9	V

Submit Document Feedback

Copyright © 2023 Texas Instruments Incorporated



 $V_{VAC_UVLOZ} < V_{VAC} < V_{VAC_OV}$ and $V_{VAC} > V_{BAT} + V_{SLEEP}$, $T_J = -40^{\circ}$ C to 125°C and $T_J = 25^{\circ}$ C for typical values (unless otherwise noted)

	PARAMETER	TEST CONDITIONS	MIN	TYP	MAX	UNIT
V _{VAC_PRESENT_HYS}	One of the conditions to turn on REGN	V _{VAC} falling		500		mV
V _{SLEEP}	Sleep mode falling threshold	(V _{VAC} -V _{VBAT}), V _{BUSMIN_FALL} ≤ V _{BAT} ≤ V _{REG} , VAC falling	15	60	110	mV
V _{SLEEPZ}	Sleep mode rising threshold	$(V_{VAC}-V_{VBAT})$, $V_{BUSMIN_FALL} \le V_{BAT}$ $\le V_{REG}$, VAC rising	115	220	340	mV
V _{VAC_OV_RISE}	VAC 6.5-V Overvoltage rising threshold	VAC rising; OVP (REG06[7:6]) = '01'	6.1	6.4	6.7	V
V _{VAC_OV_RISE}	VAC 10.5-V Overvoltage rising threshold	VAC rising, OVP (REG06[7:6]) = '10'	10.35	10.9	11.5	V
V _{VAC_OV_RISE}	VAC 14-V Overvoltage rising threshold	VAC rising, OVP (REG06[7:6]) = '11'	13.5	14.2	14.85	V
V _{VAC_OV_HYS}	VAC 6.5-V Overvoltage hysteresis	VAC falling, OVP (REG06[7:6]) = '01'		320		mV
V _{VAC_OV_HYS}	VAC 10.5-V Overvoltage hysteresis	VAC falling, OVP (REG06[7:6]) = '10'		250		mV
V _{VAC_OV_HYS}	VAC 14-V Overvoltage hysteresis	VAC falling, OVP (REG06[7:6]) = '11'		300		mV
V _{BAT_UVLOZ}	BAT for active I ² C, no adapter	V _{BAT} rising	2.5			V
V _{BAT_DPL_FALL}	Battery Depletion Threshold	V _{BAT} falling	2.2		2.6	V
V _{BAT_DPL_RISE}	Battery Depletion Threshold	V _{BAT} rising	2.35		2.8	V
V _{BAT_DPL_HYST}	Battery Depletion rising hysteresis	V _{BAT} rising		180		mV
V _{BUSMIN_FALL}	Bad adapter detection falling threshold	V _{BUS} falling	3.75	3.9	4.0	V
V _{BUSMIN_HYST}	Bad adapter detection hysteresis			80		mV
I _{BADSRC}	Bad adapter detection current source	Sink current from VBUS to GND		30		mA
POWER-PATH						
V _{SYS_MIN}	System regulation voltage	V _{BAT} < SYS_MIN[2:0] = 101, BATFET Disabled (REG07[5] = 1)	3.5	3.68		V
V _{SYS}	System Regulation Voltage	I _{SYS} = 0 A, V _{VBAT} > V _{SYS_MIN} , V _{VBAT} = 4.400 V, BATFET disabled (REG07[5] = 1)	,	V _{BAT} + 50 mV		V
V _{SYSMAX}	Maximum DC system voltage output	$I_{SYS} = 0 \text{ A}$, Q4 off, $V_{VBAT} \le 4.400 \text{ V}$, $V_{VBAT} > V_{SYS_MIN} = 3.5 \text{V}$	4.4	4.45	4.48	V
R _{ON(RBFET)}	Top reverse blocking MOSFET on-resistance between VBUS and PMID - Q1	-40°C≤ T _A ≤ 125°C		45		mΩ
R _{ON(HSFET)}	Top switching MOSFET on- resistance between PMID and SW - Q2	V _{REGN} = 5 V , -40°C≤ T _A ≤ 125°C		62		mΩ
R _{ON(LSFET)}	Bottom switching MOSFET on- resistance between SW and GND - Q3	V _{REGN} = 5 V , -40°C≤ T _A ≤ 125°C		71		mΩ
V _{FWD}	BATFET forward voltage in supplement mode		-	30		mV
R _{ON(BAT-SYS)}	SYS-BAT MOSFET on-resistance	QFN package, Measured from BAT to SYS, V _{BAT} = 4.2V, T _J = 25°C		19.5	24	mΩ
R _{ON(BAT-SYS)}	SYS-BAT MOSFET on-resistance	QFN package, Measured from BAT to SYS, V _{BAT} = 4.2V, T _J = -40 - 125°C		19.5	30	mΩ



 $V_{VAC_UVLOZ} < V_{VAC} < V_{VAC_OV}$ and $V_{VAC} > V_{BAT} + V_{SLEEP}$, $T_J = -40^{\circ}C$ to 125°C and $T_J = 25^{\circ}C$ for typical values (unless otherwise noted)

	PARAMETER	TEST CONDITIONS	MIN	TYP	MAX	UNIT
BATTERY CHAR	GER					
V _{BATREG_RANGE}	Charge voltage program range		3.856		4.624	V
V _{BATREG_STEP}	Charge voltage step			32		mV
	Charge voltage cetting	VREG (REG04[7:3]) = 4.208 V (01011), V, -40 ≤ T _J ≤ 85°C	4.187	4.208	4.229	٧
V _{BATREG}	Charge voltage setting	VREG (REG04[7:3]) = 4.352 V (01111), V, –40 ≤ T _J ≤ 85°C	4.330	4.352	4.374	V
V _{BATREG_ACC}	Charge voltage setting accuracy	$V_{BAT} = 4.208 \text{ V or } V_{BAT} = 4.352 \text{ V}, -40 \le T_J \le 85^{\circ}\text{C}$	-0.5%		0.5%	
I _{CHG_REG_RANGE}	Charge current regulation range		0		3000	mA
I _{CHG_REG_STEP}	Charge current regulation step			60		mA
I _{CHG_REG}	Charge current regulation setting	I _{CHG} = 240 mA, V _{VBAT} = 3.1V or V _{VBAT} = 3.8 V	0.216	0.24	0.264	Α
I _{CHG_REG_ACC}	Charge current regulation accuracy	I _{CHG} = 240 mA, V _{VBAT} = 3.1 V or V _{VBAT} = 3.8 V	-10%		10%	
I _{CHG_REG}	Charge current regulation setting	I _{CHG} = 720 mA, V _{VBAT} = 3.1 V or V _{VBAT} = 3.8 V	0.685	0.720	0.755	Α
I _{CHG_REG}	Charge current regulation accuracy	I _{CHG_REG} = 720 mA, V _{BAT} = 3.1 V or V _{BAT} = 3.8 V	-5%		5%	
I _{PRECHG}	Precharge current regulation	IPRECHG[3:0] = '0010' = 180 mA	153	171	189	mA
I _{PRECHG_ACC}	Precharge current regulation accuracy	IPRECHG[3:0] = '0010' = 180 mA	-15		5	%
V _{BATLOWV_FALL}	Battery LOWV falling threshold	I _{CHG} = 240 mA	2.7	2.8	2.9	V
V _{BATLOWV_RISE}	Battery LOWV rising threshold	Pre-charge to fast charge	3.0	3.12	3.24	V
I _{CHG_REG}	Charge current regulation setting	I _{CHG} = 1.38 A, V _{VBAT} = 3.1 V or V _{VBAT} = 3.8 V	1.311	1.380	1.449	Α
I _{CHG_REG_ACC}	Charge current regulation accuracy	I _{CHG} = 720 mA or I _{CHG} = 1.38 A, V _{VBAT} = 3.1 V or V _{VBAT} = 3.8 V	-5%		5%	
I _{TERM}	Termination current regulation	I _{CHG} > 780 mA, ITERM[3:0] = '0010' = 180 mA, V _{VBAT} = 4.208 V	150	180	216	mA
I _{TERM_ACC}	Termination current regulation accuracy	I _{CHG} > 780 mA, , ITERM[3:0] = '0010' = 180 mA, V _{VBAT} = 4.208 V	-16.7%		20%	
I _{TERM}	Termination current regulation	I _{CHG} ≤ 780 mA, , ITERM[3:0] = '0010' = 180 mA	162	180	192	mA
I _{TERM_ACC}	Termination current regulation accuracy	I _{CHG} ≤ 780 mA, , ITERM[3:0] = '0010' = 180 mA	-10%		10%	
I _{TERM}	Termination current regulation	I _{CHG} = 600 mA, ITERM[3:0] = '0000' = 60 mA, V _{BAT} = 4.208 V	45	60	75	mA
I _{TERM_ACC}	Termination current regulation accuracy	I _{CHG} = 600 mA, ITERM[3:0] = '0000' = 60 mA, V _{BAT} = 4.208 V	-25%		25%	
V _{SHORT}	Battery short voltage	V _{BAT} falling	1.85	2	2.15	V
V _{SHORTZ}	Battery short voltage	V _{BAT} rising	2.15	2.25	2.35	V
I _{SHORT}	Battery short current	V _{BAT} < V _{SHORTZ}	70	90	110	mA
V _{RECHG}	Recharge Threshold below V _{BAT_REG}	V _{BAT} falling, REG04[0] = 0	90	120	150	mV
V _{RECHG}	Recharge Threshold below V _{BAT_REG}	V _{BAT} falling, REG04[0] = 1	200	230	265	mV
I _{SYSLOAD}	System discharge load current	V _{SYS} = 4.2 V		30		mA
INPUT VOLTAGE	AND CURRENT REGULATION					

English Data Sheet: SLUSCK5



 $V_{VAC_UVLOZ} < V_{VAC} < V_{VAC_OV}$ and $V_{VAC} > V_{BAT} + V_{SLEEP}$, $T_J = -40^{\circ}$ C to 125°C and $T_J = 25^{\circ}$ C for typical values (unless otherwise noted)

	PARAMETER	TEST CONDITIONS	MIN	TYP	MAX	UNIT
VINDPM	Input voltage regulation limit	VINDPM (REG06[3:0] = 0000) = 3.9 V	3.78	3.95	4.1	V
VINDPM_ACC	Input voltage regulation accuracy		-3%		5%	
VINDPM	Input voltage regulation limit	VINDPM (REG06[3:0] = 0110) = 4.4 V	4.268	4.4	4.532	V
VINDPM_ACC	Input voltage regulation accuracy		-3%		3%	
V _{DPM_VBAT}	Input voltage regulation limit tracking V _{BAT}	VINDPM = 3.9V, VDPM_VBAT_TRACK = 300mV, V _{BAT} = 4.0V	4.171	4.3	4.43	V
V _{DPM_} VBAT_ACC	Input voltage regulation accuracy tracking V _{BAT}		-3%		3%	
		V_{VBUS} = 5 V, current pulled from SW, IINDPM (REG[4:0] = 00100) = 500 mA, $-40 \le T_J \le 85^{\circ}C$	450		500	mA
IINDPM	USB input current regulation limit	V_{VBUS} = 5 V, current pulled from SW, IINDPM (REG[4:0] = 01000) = 900 mA, $-40 \le T_J \le 85^{\circ}C$	750		900	mA
		V_{VBUS} = 5 V, current pulled from SW, IINDPM (REG[4:0] = 01110) = 1.5 A, -40 \leq T _J \leq 85°C	1.3		1.5	Α
I _{IN_START}	Input current limit during system start-up sequence			200		mA
BAT PIN OVERVO	OLTAGE PROTECTION					
V _{BATOVP_RISE}	Battery overvoltage threshold	V _{BAT} rising, as percentage of V _{BAT_REG}	103	104	105	%
V _{BATOVP_FALL}	Battery overvoltage threshold	V _{BAT} falling, as percentage of V _{BAT_REG}	101	102	103	%
THERMAL REGU	LATION AND THERMAL SHUTDON	VN			<u> </u>	
T _{JUNCTION_REG}	Junction temperature regulation threshold	Temperature Increasing, TREG (REG05[1] = 1) = 110°C		110		°C
T _{JUNCTION_REG}	Junction temperature regulation threshold	Temperature Increasing, TREG (REG05[1] = 0) = 90°C		90		°C
T _{SHUT}	Thermal shutdown rising temperature	Temperature Increasing		160		°C
T _{SHUT_HYST}	Thermal shutdown hysteresis			30		°C
	r Comparator (BUCK MODE)					
V _{T1}	T1 (0°C) threshold, charge suspended T1 below this temperature.	Charger suspends charge. As Percentage to V _{REGN}	72.4%	73.3%	74.2%	
V _{T1}	Falling	As Percentage to V _{REGN}	69%	71.5%	74%	
V _{T2}	T2 (10°C) threshold, charge back to I _{CHG} /2 and 4.2 V below this temperature	As percentage of V _{REGN}	67.2%	68%	69%	
V _{T2}	Falling	As Percentage to V _{REGN}	66%	66.8%	67.7%	
V _{T3}	T3 (45°C) threshold, charge back to ICHG and 4.05V above this temperature.	Charger suspends charge. As Percentage to V _{REGN}	43.8%	44.7%	45.8%	
V _{T3}	Falling	As Percentage to V _{REGN}	45.1%	45.7%	46.2%	
V _{T5}	T5 (60°C) threshold, charge suspended above this temperature.	As Percentage to V _{REGN}	33.7%	34.2%	35.1%	



 $V_{VAC_UVLOZ} < V_{VAC} < V_{VAC_OV}$ and $V_{VAC} > V_{BAT} + V_{SLEEP}$, $T_J = -40^{\circ}C$ to 125°C and $T_J = 25^{\circ}C$ for typical values (unless otherwise noted)

	PARAMETER	TEST CONDITIONS	MIN	TYP	MAX	UNIT
V _{T5}	Falling	As Percentage to V _{REGN}	34.5%	35.3%	36.2%	
COLD OR HOT T	THERMISTER COMPARATOR (BOO	ST MODE)			<u> </u>	
Cold temperature threshold, TS pin voltage rising threshold		As Percentage to V _{REGN} (Approx20°C w/ 103AT), T _J = -20°C - 125°C	79.5%	80%	80.5%	
V _{BCOLD}	Falling	T _J = -20°C - 125°C	78.5%	79%	79.5%	
V _{BHOT}	Hot temperature threshold, TS pin voltage falling threshold	As Percentage to V _{REGN} (Approx. 60°C w/ 103AT), T _J = -20°C - 125°C	30.2%	31.2%	32.2%	
V _{BHOT}	Rising	T _J = -20°C - 125°C	33.8%	34.4%	34.9%	
CHARGE OVER	CURRENT COMPARATOR (CYCLE-	BY-CYCLE)		,		
HSFET_OCP	HSFET cycle-by-cycle over- current threshold		5.2		8.0	Α
I _{BATFET} OCP	System over load threshold		6.0			Α
CHARGE UNDE	R-CURRENT COMPARATOR (CYCL	E-BY-CYCLE)			I	
V _{LSFET_UCP}	LSFET under-current falling threshold	From sync mode to non-sync mode			160	mA
PWM						
	DIAMA avvitalain a ferroman	Oscillator frequency, buck mode	1320	1500	1680	kHz
f _{SW}	PWM switching frequency	Oscillator frequency, boost mode	1150	1412	1660	kHz
D _{MAX}	Maximum PWM duty cycle			97%		
BOOST MODE C	PERATION				<u> </u>	
V _{OTG_REG}	Boost mode regulation voltage	V _{BAT} = 3.8 V, I _(PMID) = 0 A, BOOSTV[1:0] = '10' = 5.15 V	4.972	5.126	5.280	V
V _{OTG_REG_ACC}	Boost mode regulation voltage accuracy	V _{BAT} = 3.8 V, I _(PMID) = 0 A, BOOSTV[1:0] = '10' = 5.15 V	-3		3	%
		V _{BAT} falling, MIN_V _{BAT} _SEL (REG01[0]) = 0	2.6	2.8	2.9	V
.,	Battery voltage exiting boost mode	V _{BAT} rising, MIN_V _{BAT} _SEL (REG01[0]) = 0	2.9	3.0	3.15	V
V _{BATLOWV_} OTG		V _{BAT} falling, MIN_V _{BAT} _SEL (REG01[0]) = 1	2.4	2.5	2.6	V
		V _{BAT} rising, MIN_V _{BAT} _SEL (REG01[0]) = 1	2.7	2.8	2.9	V
I _{OTG}	OTG mode output current	BOOST_LIM (REG02[7]) = 1	1.2	1.4	1.6	Α
OTG_OCP_ACC	Boost mode RBFET over-current protection accuracy	BOOST_LIM = 0.5 A (REG02[7] = 0)	0.5		0.722	Α
V _{OTG_OVP}	OTG overvoltage threshold	Rising threshold	5.55	5.8	6.15	V
I _{OTG_HSZCP}	HSFET under current falling threshold			100		mA
REGN LDO	ı					
V_{REGN}	REGN LDO output voltage	V _{VBUS} = 9V, I _{REGN} = 40mA	5.6	6		V
V _{REGN}	REGN LDO output voltage	V _{VBUS} = 5V, I _{REGN} = 20mA	4.6	4.7		V
LOGIC I/O PIN C	HARACTERISTICS (CE, PSEL, SCI	L, SDA,, ĪNT)				
V _{ILO}	Input low threshold CE				0.4	V
V _{IH}	Input high threshold CE		1.3			V
I _{BIAS}	High-level leakage current CE	Pull up rail 1.8 V			1	μA
V _{ILO}	Input low threshold PSEL		-		0.4	V
V _{IH}	Input high threshold PSEL		1.3			V

English Data Sheet: SLUSCK5

 $V_{VAC_UVLOZ} < V_{VAC} < V_{VAC_OV}$ and $V_{VAC} > V_{BAT} + V_{SLEEP}$, $T_J = -40^{\circ}C$ to 125°C and $T_J = 25^{\circ}C$ for typical values (unless otherwise noted)

PARAMETER		TEST CONDITIONS	MIN	TYP	MAX	UNIT		
I _{BIAS}	High-level leakage current PSEL	Pull up rail 1.8V			1	μΑ		
LOGIC I/O PIN CHARACTERISTICS (PG, STAT)								
V _{OL}	Low-level output voltage				0.4	V		


8.6 Timing Requirements

	PARAMETER	TEST CONDITIONS	MIN	NOM	MAX	UNIT
VBUS/BAT P	OWER UP					
t _{ACOV}	VAC OVP reaction time	VAC rising above ACOV threshold to turn off Q2		200		ns
t _{BADSRC}	Bad adapter detection duration			30		ms
BATTERY CH	IARGER				1	
t _{TERM_DGL}	Deglitch time for charge termination			250		ms
t _{RECHG_DGL}	Deglitch time for recharge			250		ms
t _{SYSOVLD_DGL}	System over-current deglitch time to turn off Q4			100		μs
t _{BATOVP}	Battery overvoltage deglitch time to disable charge			1		μs
t _{SAFETY}	Charge Safety Timer Range	CHG_TIMER = 1	8	10	12	hr
t _{TOP_OFF}	Top-Off Timer Accuracy	TOP_OFF_TIMER[1:0] = 10 (30 min)	24	30	36	min
QON Timing					•	
t _{SHIPMODE}	QON low time to turn on BATFET and exit ship mode	T _J = -10°C to 60°C	0.9		1.3	s
t _{QON_RST_2}	QON low time to reset BATFET	T _J = -10°C to 60°C	8		12	S
t _{BATFET_RST}	BATFET off time during full system reset	T _J = -10°C to 60°C	250		400	ms
t _{SM_DLY}	Enter ship mode delay	T _J = -10°C to 60°C	10		15	S
DIGITAL CLC	OCK AND WATCHDOG TIMER					
t _{WDT}	Watchdog reset time	REGN LDO disabled		40		s
f _{LPDIG}	Digital Low Power Clock	REGN LDO disabled	18	30	45	kHz
f _{DIG}	Digital Clock	REGN LDO enabled		500		kHz
f _{SCL}	SCL clock frequency				400	kHz

Product Folder Links: BQ25601




8.7 Typical Characteristics



Product Folder Links: BQ25601



8.7 Typical Characteristics (continued)





9 Detailed Description


9.1 Overview

The BQ25601 is a highly integrated 3.0-A switch-mode battery charger for single cell Li-ion and Li-polymer batteries. It includes an input reverse-blocking FET (RBFET, Q1), high-side switching FET (HSFET, Q2), low-side switching FET (LSFET, Q3), and battery FET (BATFET, Q4), and bootstrap diode for the high-side gate drive.

Product Folder Links: BQ25601



9.2 Functional Block Diagram





9.3 Feature Description

9.3.1 Power-On-Reset (POR)

The device powers internal bias circuits from the higher voltage of VBUS and BAT. When VBUS rises above V_{VBUS_UVLOZ} or BAT rises above V_{BAT_UVLOZ} , the sleep comparator, battery depletion comparator and BATFET driver are active. I²C interface is ready for communication and all the registers are reset to default value. The host can access all the registers after POR.

9.3.2 Device Power Up from Battery without Input Source

If only battery is present and the voltage is above depletion threshold (V_{BAT_DPL_RISE)}, the BATFET turns on and connects battery to system. The REGN stays off to minimize the quiescent current. The low RDSON of BATFET and the low quiescent current on BAT minimize the conduction loss and maximize the battery run time.

The device always monitors the discharge current through BATFET (Supplement Mode). When the system is overloaded or shorted ($I_{BAT} > I_{BATFET_OCP}$), the device turns off BATFET immediately and set BATFET_DIS bit to indicate BATFET is disabled until the input source plugs in again or one of the methods described in BATFET Enable (Exit Shipping Mode) is applied to re-enable BATFET.

9.3.3 Power Up from Input Source

When an input source is plugged in, the device checks the input source voltage to turn on REGN LDO and all the bias circuits. It detects and sets the input current limit before the buck converter is started. The power-up sequence from input source is as listed:

- 1. Power up REGN LDO
- 2. Poor source qualification
- 3. Input source type detection is based on or PSEL to set default input current limit (IINDPM) register or input source type.
- 4. Input voltage limit threshold setting (VINDPM threshold)
- 5. Converter power up

9.3.3.1 Power Up REGN Regulation

The REGN LDO supplies internal bias circuits as well as the HSFET and LSFET gate drive. The REGN also provides bias rail to TS external resistors. The pull-up rail of STAT can be connected to REGN as well. The REGN is enabled when all the below conditions are valid:

- V_{VAC} above V_{VAC_PRESENT}
- V_{VAC} above V_{BAT} + V_{SLEEPZ} in buck mode or VBUS below V_{BAT} + V_{SLEEP} in boost mode
- After 220-ms delay is completed

If any one of the above conditions is not valid, the device is in high impedance mode (HIZ) with REGN LDO off. The device draws less than IVBUS_HIZ from VBUS during HIZ state. The battery powers up the system when the device is in HIZ.

9.3.3.2 Poor Source Qualification

After REGN LDO powers up, the device confirms the current capability of the input source. The input source must meet both of the following requirements in order to start the buck converter.

- VBUS voltage below V_{VAC OV}
- VBUS voltage above V_{VBUSMIN} when pulling I_{BADSRC} (typical 30 mA)

Once the input source passes all the conditions above, the status register bit VBUS_GD is set high and the $\overline{\text{INT}}$ pin is pulsed to signal to the host. If the device fails the poor source detection, it repeats poor source qualification every 2 seconds.

9.3.3.3 Input Source Type Detection

After the VBUS_GD bit is set and REGN LDO is powered, the device runs input source detection through the PSEL pin. The BQ25601 sets input current limit through PSEL pins.

Submit Document Feedback

Copyright © 2023 Texas Instruments Incorporated

English Data Sheet: SLUSCK5

After input source type detection is completed, an INT pulse is asserted to the host. in addition, the following registers and pin are changed:

- 1. Input Current Limit (IINDPM) register is changed to set current limit
- 2. PG STAT bit is set
- 3. VBUS_STAT bit is updated to indicate USB or other input source

The host can overwrite IINDPM register to change the input current limit if needed. The charger input current is always limited by the IINDPM register.

9.3.3.3.1 PSEL Pins Sets Input Current Limit in BQ25601

The BQ25601 has PSEL pin for input current limit setting to interface with USB PHY. It directly takes the USB PHY device output to decide whether the input is USB host or charging port. When the device operates in host-control mode, the host needs to IINDET_EN bit to read the PSEL value and update the IINDPM register. When the device is in default mode, PSEL value updates IINDPM in real time.

表	9-1	. Input	Current	Limit	Setting	from	PSEL
---	-----	---------	---------	-------	---------	------	-------------

INPUT DETECTION	T DETECTION PSEL PIN		VBUS_STAT
USB SDP	USB SDP High		001
Adapter Low		2.4A	011

9.3.3.4 Input Voltage Limit Threshold Setting (VINDPM Threshold)

The device supports wide range of input voltage limit (3.9 V to 5.4 V) for USB. The device VINDPM is set at 4.5 V. The device supports dynamic VINDPM trackingsettings which tracks the battery voltage. This function can be enabled via the VDPM_BAT_TRACK[1:0] register bits. When enabled, the actual input voltage limit will be the higher of the VINDPM register and VBAT + VDPM_BAT_TRACK offset.

9.3.3.5 Converter Power Up

After the input current limit is set, the converter is enabled and the HSFET and LSFET start switching. If battery charging is disabled, BATFET turns off. Otherwise, BATFET stays on to charge the battery.

The device provides soft start when system rail is ramped up. When the system rail is below 2.2 V, the input current is limited to is to the lower of 200 mA or IINDPM register setting. After the system rises above 2.2 V, the device limits input current to the value set by IINDPM register.

As a battery charger, the device deploys a highly efficient 1.5 MHz step-down switching regulator. The fixed frequency oscillator keeps tight control of the switching frequency under all conditions of input voltage, battery voltage, charge current and temperature, simplifying output filter design.

The device switches to PFM control at light load or when battery is below minimum system voltage setting or charging is disabled. The PFM_DIS bit can be used to prevent PFM operation in either buck or boost configuration. PFM mode is only enabled when IINDPM is set \geq 500 mA. When IINDPM is set \leq 400 mA, PFM mode is disabled.

9.3.4 Boost Mode Operation From Battery

The device supports boost converter operation to deliver power from the battery to other portable devices through USB port. The boost mode output current rating meets the USB On-The-Go 500 mA output requirement. The maximum output current is up to 1.2 A. The boost operation can be enabled if the conditions are valid:

- BAT above V_{OTG BAT}
- 2. VBUS less than BAT+V_{SLEEP} (in sleep mode)
- 3. Boost mode operation is enabled (OTG_CONFIG bit = 1)
- 4. Voltage at TS (thermistor) pin as a percentage of V_{REGN} is within acceptable range ($V_{BHOT} < V_{TS} < V_{BCOLD}$)

Product Folder Links: BQ25601

5. After 30-ms delay from boost mode enable

Copyright © 2023 Texas Instruments Incorporated

Submit Document Feedback

19

During boost mode, the status register VBUS_STAT bits is set to 111, the VBUS output is 5.15 V and the output current can reach up to 1.2 A, selected through I²C (BOOST LIM bit). The boost output is maintained when BAT is above V_{OTG BAT} threshold.

When OTG is enabled, the device starts up with PFM and later transits to PWM to minimize the overshoot. The PFM DIS bit can be used to prevent PFM operation in either buck or boost configuration.

9.3.5 Host Mode and Standalone Power Management

9.3.5.1 Host Mode and Default Mode in BQ25601

The BQ25601 is a host controlled charger, but it can operate in default mode without host management. in default mode, the device can be used as an autonomous charger with no host or while host is in sleep mode. When the charger is in default mode, WATCHDOG FAULT bit is HIGH. When the charger is in host mode, WATCHDOG FAULT bit is LOW.

After power-on-reset, the device starts in default mode with watchdog timer expired, or default mode. All the registers are in the default settings. During default mode, any change on PSEL pin will make real time IINDPM register changes.

In default mode, the device keeps charging the battery with default 10-hour fast charging safety timer. At the end of the 10-hour, the charging is stopped and the buck converter continues to operate to supply system load.

Writing a 1 to the WD RST bit transitions the charger from default mode to host mode. All the device parameters can be programmed by the host. To keep the device in host mode, the host has to reset the watchdog timer by writing 1 to WD RST bit before the watchdog timer expires (WATCHDOG FAULT bit is set), or disable watchdog timer by setting WATCHDOG bits = 00.

When the watchdog timer expires (WATCHDOG_FAULT bit = 1), the device returns to default mode and all registers are reset to default values except IINDPM, VINDPM, BATFET RST EN, BATFET DLY, and BATFET DIS bits.




図 9-1. Watchdog Timer Flow Chart

9.3.6 Power Path Management

The device accommodates a wide range of input sources from USB, wall adapter, to car charger. The device provides automatic power path selection to supply the system (SYS) from input source (VBUS), battery (BAT), or both.

Product Folder Links: BQ25601

Copyright © 2023 Texas Instruments Incorporated

9.3.7 Battery Charging Management

The device charges 1-cell Li-lon battery with up to 3.0-A charge current for high capacity tablet battery. The 19.5- $m\Omega$ BATFET improves charging efficiency and minimize the voltage drop during discharging.

9.3.7.1 Autonomous Charging Cycle

With battery charging enabled (CHG_CONFIG bit = 1 and $\overline{\text{CE}}$ pin is LOW), the device autonomously completes a charging cycle without host involvement. The device default charging parameters are listed in $\frac{1}{2}$ 9-2. The host can always control the charging operations and optimize the charging parameters by writing to the corresponding registers through I²C.

表 9-2. Charging Parameter Default Setting

2 7 ·					
DEFAULT MODE	BQ25601				
Charging voltage	4.208V				
Charging current	2.048 A				
Precharge current	180 mA				
Termination current	180 mA				
Temperature profile	JEITA				
Safety timer	10 hours				

A new charge cycle starts when the following conditions are valid:

- · Converter starts
- Battery charging is enabled (CHG_CONFIG bit = 1 and I_{CHG} register is not 0 mA and CE is low)
- · No thermistor fault on TS
- No safety timer fault
- BATFET is not forced to turn off (BATFET DIS bit = 0)

The charger device automatically terminates the charging cycle when the charging current is below termination threshold, battery voltage is above recharge threshold, and device not is in DPM mode or thermal regulation. When a fully charged battery is discharged below recharge threshold (selectable through VRECHG bit), the device automatically starts a new charging cycle. After the charge is done, toggle $\overline{\text{CE}}$ pin or CHG_CONFIG bit can initiate a new charging cycle.

The STAT output indicates the charging status: charging (LOW), charging complete or charge disable (HIGH) or charging fault (blinking). The STAT output can be disabled by setting EN_ICHG_MON bits = 11. in addition, the status register (CHRG_STAT) indicates the different charging phases: 00-charging disable, 01-precharge, 10-fast charge (constant current) and constant voltage mode, 11-charging done. Once a charging cycle is completed, an INT is asserted to notify the host.

9.3.7.2 Battery Charging Profile

The device charges the battery in five phases: battery short, preconditioning, constant current, constant voltage and top-off trickle charging (optional). At the beginning of a charging cycle, the device checks the battery voltage and regulates current and voltage accordingly.

表 9-3. Charging Current Setting

V _{BAT}	CHARGING CURRENT	REGISTER DEFAULT SETTING	CHRG_STAT
< 2.2 V	I _{SHORT}	100 mA	01
2.2 V to 3 V	I _{PRECHG}	180 mA	01
> 3 V	I _{CHG}	2.048 A	10

If the charger device is in DPM regulation or thermal regulation during charging, the actual charging current will be less than the programmed value. in this case, termination is temporarily disabled and the charging safety timer is counted at half the clock rate.

Product Folder Links: BQ25601

Copyright © 2023 Texas Instruments Incorporated

Submit Document Feedback




図 9-2. Battery Charging Profile

9.3.7.3 Charging Termination

The device terminates a charge cycle when the battery voltage is above recharge threshold, and the current is below termination current. After the charging cycle is completed, the BATFET turns off. The converter keeps running to power the system, and BATFET can turn on again to engage Supplement Mode.

When termination occurs, the status register CHRG_STAT is set to 11, and an INT pulse is asserted to the host. Termination is temporarily disabled when the charger device is in input current, voltage, or thermal regulation. Termination can be disabled by writing 0 to EN_TERM bit prior to charge termination.

At low termination currents, due to the comparator offset, the actual termination current may be 10 mA-20 mA higher than the termination target. in order to compensate for comparator offset, a programmable top-off timer can be applied after termination is detected. The termination timer will follow safety timer constraints, such that if safety timer is suspended, so will the termination timer. Similarly, if safety timer is doubled, so will the termination timer. TOPOFF_ACTIVE bit reports whether the top off timer is active or not. The host can read CHRG_STAT and TOPOFF_ACTIVE to find out the termination status.

Top off timer gets reset at one of the following conditions:

- 1. Charge disable to enable
- 2. Termination status low to high
- 3. REG_RST register bit is set

The top-off timer settings are read in once termination is detected by the charger. Programming a top-off timer value after termination will have no effect unless a recharge cycle is initiated. An INT is asserted to the host when entering top-off timer segment as well as when top-off timer expires.

9.3.7.4 Thermistor Qualification

The charger device provides a single thermistor input for battery temperature monitor.

9.3.7.5 JEITA Guideline Compliance During Charging Mode

To improve the safety of charging Li-ion batteries, JEITA guideline was released on April 20, 2007. The guideline emphasized the importance of avoiding a high charge current and high charge voltage at certain low and high temperature ranges.


Submit Document Feedback

Copyright © 2023 Texas Instruments Incorporated

To initiate a charge cycle, the voltage on TS pin must be within the VT1 to VT5 thresholds. If TS voltage exceeds the T1-T5 range, the controller suspends charging and waits until the battery temperature is within the T1 to T5 range.

At cool temperature (T1-T2), JEITA recommends the charge current to be reduced to half of the charge current or lower. At warm temperature (T3-T5), JEITA recommends charge voltage less than 4.1 V. Charge termination is disabled for cool and warm conditions.

The charger provides flexible voltage/current settings beyond the JEITA requirement. The voltage setting at warm temperature (T3-T5) can be VREG or 4.1V (configured by JEITA_VSET). The current setting at cool temperature (T1-T2) can be further reduced to 20% of fast charge current (JEITA_ISET).






図 9-4. JEITA Profile: Charging Voltage

図 9-3. JEITA Profile: Charging Current




図 9-5. TS Resistor Network

式 1 through 式 2 describe updates to the resistor bias network.

$$RT2 = \frac{V_{REGN} \times RTH_{COLD} \times RTH_{HOT} \times \left(\frac{1}{VT1} - \frac{1}{VT5}\right)}{RTH_{HOT} \times \left(\frac{V_{REGN}}{VT5} - 1\right) - RTH_{COLD} \times \left(\frac{V_{REGN}}{VT1} - 1\right)}$$
(1)

$$RT1 = \frac{\left(\left(\frac{V_{REGN}}{VT1}\right) - 1\right)}{\left(\frac{1}{RT2}\right) + \left(\frac{1}{RTH_{COLD}}\right)}$$
(2)


Select 0°C to 60°C range for Li-ion or Li-polymer battery:



- RTH_{COLD} = 27.28 KΩ
- RTH_{HOT} = 3.02 KΩ
- RT1 = 5.23 KΩ
- RT2 = 30.9 KΩ

9.3.7.6 Boost Mode Thermistor Monitor During Battery Discharge Mode

For battery protection during boost mode, the device monitors the battery temperature to be within the V_{BCOLD} to V_{BHOT} thresholds. When temperature is outside of the temperature thresholds, the boost mode is suspended. In additional, VBUS_STAT bits are set to 000 and NTC_FAULT is reported. Once temperature returns within thresholds, the boost mode is recovered and NTC_FAULT is cleared.



2 9-6. TS Pin Thermistor Sense Threshold in Boost Mode

9.3.7.7 Charging Safety Timer

The device has built-in safety timer to prevent extended charging cycle due to abnormal battery conditions. The safety timer is two hours when the battery is below $V_{BATLOWV}$ threshold and 10 hours when the battery is higher than $V_{BATLOWV}$ threshold.

The user can program fast charge safety timer through I^2C (CHG_TIMER bits). When safety timer expires, the fault register CHRG_FAULT bits are set to 11 and an INT is asserted to the host. The safety timer feature can be disabled through I^2C by setting EN_TIMER bit.

During input voltage, current, JEITA cool or thermal regulation, the safety timer counts at half clock rate as the actual charge current is likely to be below the register setting. For example, if the charger is in input current regulation (IDPM_STAT = 1) throughout the whole charging cycle, and the safety time is set to five hours, the safety timer will expire in 10 hours. This half clock rate feature can be disabled by writing 0 to TMR2X_EN bit.

During the fault, timer is suspended. Once the fault goes away, the timer resumes counting. If user stops the current charging cycle, and start again, timer gets reset (toggle CE pin or CHRG_CONFIG bit).

9.3.8 Protections

9.3.8.1 Voltage and Current Monitoring in Converter Operation

The device closely monitors the input and system voltage, as well as internal FET currents for safe buck and boost mode operation.

9.3.8.1.1 Voltage and Current Monitoring in Buck Mode

9.3.8.1.1.1 Input Overvoltage (ACOV)

If VBUS voltage exceeds V_{VAC OV} (programmable via OVP[2:0] bits), the device stops switching immediately.

Product Folder Links: BQ25601

Copyright © 2023 Texas Instruments Incorporated

During input overvoltage event (ACOV), the fault register CHRG_FAULT bits are set to 01. An INT pulse is asserted to the host. The device will automatically resume normal operation once the input voltage drops back below the OVP threshold.

9.3.8.1.1.2 System Overvoltage Protection (SYSOVP)

The charger device clamps the system voltage during load transient so that the components connect to system would not be damaged due to high voltage. SYSOVP threshold is 350 mV above minimum system regulation voltage when the system is regulate at V_{SYS_MIN} . Upon SYSOVP, converter stops switching immediately to clamp the overshoot. The charger provides $\overline{30}$ -mA discharge current ($I_{SYSLOAD}$) to bring down the system voltage.

9.3.8.2 Voltage and Current Monitoring in Boost Mode

The device closely monitors the VBUS voltage, as well as RBFET and LSFET current to ensure safe boost mode operation.

9.3.8.2.1 VBUS Soft Start

When the boost function is enabled, the device soft-starts boost mode to avoid inrush current.

9.3.8.2.2 VBUS Output Protection

The device monitors boost output voltage and other conditions to provide output short circuit and overvoltage protection. The boost build in accurate constant current regulation to allow OTG to adapt to various types of load. If a short circuit is detected on VBUS, boost turns off and retries 7 times. If retries are not successful, OTG is disabled with OTG_CONFIG bit cleared. In addition, the BOOST_FAULT bit is set and $\overline{\text{INT}}$ pulse is generated. The BOOST_FAULT bit can be cleared by host by reenabling boost mode

9.3.8.2.3 Boost Mode Overvoltage Protection

When the VBUS voltage rises above regulation target and exceeds VOTG_OVP, the device enters overvoltage protection which stops switching, clears OTG_CONFIG bit and exits boost mode. At Boost overvoltage duration, the fault register bit (BOOST_FAULT) is set high to indicate fault in boost operation. An INT is also asserted to the host.

9.3.8.3 Thermal Regulation and Thermal Shutdown

9.3.8.3.1 Thermal Protection in Buck Mode

The BQ25601 monitors the internal junction temperature T_J to avoid overheat of the chip and limits the IC surface temperature in buck mode. When the internal junction temperature exceeds thermal regulation limit (110°C), the device lowers down the charge current. During thermal regulation, the actual charging current is usually below the programmed battery charging current. Therefore, termination is disabled, the safety timer runs at half the clock rate, and the status register THERM_STAT bit goes high.

Additionally, the device has thermal shutdown to turn off the converter and BATFET when IC surface temperature exceeds $T_{SHUT}(160^{\circ}C)$. The fault register CHRG_FAULT is set to 1 and an \overline{INT} is asserted to the host. The BATFET and converter is enabled to recover when IC temperature is T_{SHUT_HYS} (30°C) below $T_{SHUT}(160^{\circ}C)$.

9.3.8.3.2 Thermal Protection in Boost Mode

The device monitors the internal junction temperature to provide thermal shutdown during boost mode. When IC junction temperature exceeds T_{SHUT} (160°C), the boost mode is disabled by setting OTG_CONFIG bit low and BATFET is turned off. When IC junction temperature is below T_{SHUT} (160°C) - T_{SHUT_HYS} (30°C), the BATFET is enabled automatically to allow system to restore and the host can re-enable OTG_CONFIG bit to recover.

9.3.8.4 Battery Protection

9.3.8.4.1 Battery Overvoltage Protection (BATOVP)

The battery overvoltage limit is clamped at 4% above the battery regulation voltage. When battery over voltage occurs, the charger device immediately disables charging. The fault register BAT_FAULT bit goes high and an INT is asserted to the host.

Copyright © 2023 Texas Instruments Incorporated

Submit Document Feedback

9.3.8.4.2 Battery Overdischarge Protection

When battery is discharged below $V_{BAT_DPL_FALL}$, the BATFET is turned off to protect battery from overdischarge. To recover from overdischarge latch-off, an input source plug-in is required at VBUS. The battery is charged with I_{SHORT} (typically 100 mA) current when the $V_{BAT} < V_{SHORT}$, or precharge current as set in IPRECHG register when the battery voltage is between V_{SHORTZ} and V_{BAT_LOWV} .

9.3.8.4.3 System Overcurrent Protection

When the system is shorted or significantly overloaded ($I_{BAT} > I_{BATOP}$) and the current exceeds BATFET overcurrent limit, the BATFET latches off. Section BATFET Enable (Exit Shipping Mode) can reset the latch-off condition and turn on BATFET.

9.4 Device Functional Modes

9.4.1 Narrow VDC Architecture

The device deploys Narrow VDC architecture (NVDC) with BATFET separating system from battery. The minimum system voltage is set by SYS_MIN bits. Even with a fully depleted battery, the system is regulated above the minimum system voltage.

When the battery is below minimum system voltage setting, the BATFET operates in linear mode (LDO mode), and the system is typically 180 mV above the minimum system voltage setting. As the battery voltage rises above the minimum system voltage, BATFET is fully on and the voltage difference between the system and battery is the V_{DS} of BATFET.

When the battery charging is disabled and above minimum system voltage setting or charging is terminated, the system is always regulated at typically 50 mV above battery voltage. The status register VSYS_STAT bit goes high when the system is in minimum system voltage regulation.




図 9-7. System Voltage vs Battery Voltage

9.4.2 Dynamic Power Management

To meet maximum current limit in USB spec and avoid over loading the adapter, the device features Dynamic Power management (DPM), which continuously monitors the input current and input voltage. When input source is over-loaded, either the current exceeds the input current limit (IINDPM) or the voltage falls below the input voltage limit (VINDPM). The device then reduces the charge current until the input current falls below the input current limit and the input voltage rises above the input voltage limit.

When the charge current is reduced to zero, but the input source is still overloaded, the system voltage starts to drop. Once the system voltage falls below the battery voltage, the device automatically enters the supplement mode where the BATFET turns on and battery starts discharging so that the system is supported from both the input source and battery.

Product Folder Links: BQ25601

Copyright © 2023 Texas Instruments Incorporated

During DPM mode, the status register bits VDPM_STAT (VINDPM) or IDPM_STAT (IINDPM) goes high. ☑ 9-8 shows the DPM response with 9-V/1.2-A adapter, 3.2-V battery, 2.8-A charge current and 3.5-V minimum system voltage setting.




図 9-8. DPM Response

9.4.3 Supplement Mode

When the system voltage falls below the battery voltage, the BATFET turns on and the BATFET gate is regulated so that the minimum BATFET VDS stays at 30 mV when the current is low. This prevents oscillation from entering and exiting the supplement mode.

As the discharge current increases, the BATFET gate is regulated with a higher voltage to reduce R_{DSON} until the BATFET is in full conduction. At this point onwards, the BATFET V_{DS} linearly increases with discharge current. $\boxed{2}$ 9-9 shows the V-I curve of the BATFET gate regulation operation. BATFET turns off to exit supplement mode when the battery is below battery depletion threshold.




図 9-9. BAFET V-I Curve

9.4.4 Shipping Mode and QON Pin

9.4.4.1 BATFET Disable Mode (Shipping Mode)

To extend battery life and minimize power when system is powered off during system idle, shipping, or storage, the device can turn off BATFET so that the system voltage is zero to minimize the battery leakage current. When the host set BATFET_DIS bit, the charger can turn off BATFET immediately or delay by t_{SM_DLY} as configured by BATFET_DLY bit.

9.4.4.2 BATFET Enable (Exit Shipping Mode)

When the BATFET is disabled (in shipping mode) and indicated by setting BATFET_DIS, one of the following events can enable BATFET to restore system power:

- 1. Plug in adapter
- 2. Clear BATFET DIS bit
- 3. Set REG_RST bit to reset all registers including BATFET_DIS bit to default (0)
- 4. A logic high to low transition on $\overline{\text{QON}}$ pin with t_{SHIPMODE} deglitch time to enable BATFET to exit shipping mode

9.4.4.3 BATFET Full System Reset

The BATFET functions as a load switch between battery and system when input source is not plugged in. By changing the state of BATFET from on to off, systems connected to SYS can be effectively forced to have a power-on-reset. The $\overline{\text{QON}}$ pin supports push-button interface to reset system power without host by changing the state of BATFET.

When the $\overline{\text{QON}}$ pin is driven to logic low for $t_{\text{QON_RST}}$ while input source is not plugged in and BATFET is enabled (BATFET_DIS = 0), the BATFET is turned off for $t_{\text{BATFET_RST}}$ and then it is re-enabled to reset system power. This function can be disabled by setting BATFET_RST_EN bit to 0.

9.4.4.4 QON Pin Operations

The \overline{QON} pin incorporates two functions to control BATFET. \overline{QON} is pulled up to V_{QON} by an internal 200-k Ω pull-up resistor.

- BATFET Enable: A QON logic transition from high to low with longer than t_{SHIPMODE} deglitch turns on BATFET to exit shipping mode. When exiting shipping mode, HIZ is enabled (EN_HIZ = 1) as well. HIZ can be disabled (EN_HIZ = 0) by the host after exiting shipping mode. OTG cannot be enabled (OTG_CONFIG = 1) until HIZ is disabled.
- 2. BATFET Reset: When $\overline{\text{QON}}$ is driven to logic low by at least $t_{\text{QON_RST}}$ while adapter is not plugged in (and BATFET_DIS = 0), the BATFET is turned off for $t_{\text{BATFET_RST}}$. The BATFET is re-enabled after $t_{\text{BATFET_RST}}$ duration. This function allows systems connected to SYS to have power-on-reset. This function can be disabled by setting BATFET_RST_EN bit to 0.




図 9-10. QON Timing




図 9-11. QON Circuit

9.4.5 Status Outputs (PG, STAT, INT)

9.4.5.1 Power Good Indicator (PG Pin and PG STAT Bit)

The PG_STAT bit goes HIGH and \overline{PG} pin goes LOW to indicate a good input source when:

- VBUS above V_{VBUS UVLO}
- VBUS above battery (not in sleep)
- VBUS below V_{VAC} OV threshold
- VBUS above V_{VBUSMin} (typical 3.8 V) when I_{BADSRC} (typical 30 mA) current is applied (not a poor source)
- Completed input Source Type Detection

9.4.5.2 Charging Status Indicator (STAT)

The device indicates charging state on the open drain STAT pin. The STAT pin can drive LED. The STAT pin function can be disabled by setting the EN ICHG MON bits = 11.

表 9-4. STAT Pin State

CHARGING STATE	STAT INDICATOR
Charging in progress (including recharge)	LOW
Charging complete	HIGH
Sleep mode, charge disable	HIGH
Charge suspend (input overvoltage, TS fault, timer fault or system overvoltage) Boost Mode suspend (due to TS fault)	Blinking at 1 Hz

9.4.5.3 Interrupt to Host (INT)

In some applications, the host does not always monitor the charger operation. The INT pulse notifies the system on the device operation. The following events will generate 256-µs INT pulse.

- USB/adapter source identified (through PSEL pin)
- · Good input source detected
 - VBUS above battery (not in sleep)
 - VBUS below $V_{VAC\ OV}$ threshold
 - VBUS above V_{VBUSMin} (typical 3.8 V) when I_{BADSRC} (typical 30 mA) current is applied (not a poor source)
- Input removed
- · Charge complete
- Any FAULT event in REG09
- VINDPM / IINDPM event detected (maskable)

When a fault occurs, the charger device sends out INT and keeps the fault state in REG09 until the host reads the fault register. Before the host reads REG09 and all the faults are cleared, the charger device would not send

Product Folder Links: BQ25601

any INT upon new faults. To read the current fault status, the host has to read REG09 two times consecutively. The first read reports the pre-existing fault register status and the second read reports the current fault register status.

9.5 Programming

9.5.1 Serial Interface

The device uses I²C compatible interface for flexible charging parameter programming and instantaneous device status reporting. I²C is a bi-directional 2-wire serial interface developed by Philips Semiconductor (now NXP Semiconductors). Only two bus lines are required: a serial data line (SDA) and a serial clock line (SCL). Devices can be considered as hosts or targets when performing data transfers. A host is the device which initiates a data transfer on the bus and generates the clock signals to permit that transfer. At that time, any device addressed is considered a target.

The device operates as a target device with address 6BH, receiving control inputs from the host device like a microcontroller or a digital signal processor through REG00-REG0B. A register read beyond REG0B (0x0B) returns 0xFF. The I²C interface supports both standard mode (up to 100 kbits), and fast mode (up to 400 kbits), connecting to the positive supply voltage via a current source or pull-up resistor. When the bus is free, both lines are HIGH. The SDA and SCL pins are open drain.

9.5.1.1 Data Validity

The data on the SDA line must be stable during the HIGH period of the clock. The HIGH or LOW state of the data line can only change when the clock signal on the SCL line is LOW. One clock pulse is generated for each data bit transferred.




図 9-12. Bit Transfer on the I²C Bus

9.5.1.2 START and STOP Conditions

All transactions begin with a START (S) and can be terminated by a STOP (P). A HIGH to LOW transition on the SDA line while SCI is HIGH defines a START condition. A LOW to HIGH transition on the SDA line when the SCL is HIGH defines a STOP condition. START and STOP conditions are always generated by the host. The bus is considered busy after the START condition, and free after the STOP condition.




図 9-13. TS START and STOP conditions

Submit Document Feedback

Copyright © 2023 Texas Instruments Incorporated

9.5.1.3 Byte Format

Every byte on the SDA line must be 8 bits long. The number of bytes to be transmitted per transfer is unrestricted. Each byte has to be followed by an Acknowledge bit. Data is transferred with the Most Significant Bit (MSB) first. If a target cannot receive or transmit another complete byte of data until it has performed some other function, it can hold the clock line SCL low to force the host into a wait state (clock stretching). Data transfer then continues when the target is ready for another byte of data and release the clock line SCL.




図 9-14. Data Transfer on the I²C Bus

9.5.1.4 Acknowledge (ACK) and Not Acknowledge (NACK)

The acknowledge takes place after every byte. The acknowledge bit allows the receiver to signal the transmitter that the byte was successfully received and another byte may be sent. All clock pulses, including the acknowledge ninth clock pulse, are generated by the host. The transmitter releases the SDA line during the acknowledge clock pulse so the receiver can pull the SDA line LOW and it remains stable LOW during the HIGH period of this clock pulse.

When SDA remains HIGH during the ninth clock pulse, this is the Not Acknowledge signal. The host can then generate either a STOP to abort the transfer or a repeated START to start a new transfer.

9.5.1.5 Target Address and Data Direction Bit

After the START, a target address is sent. This address is 7 bits long followed by the eighth bit as a data direction bit (bit R/W). A zero indicates a transmission (WRITE) and a one indicates a request for data (READ).




図 9-15. Complete Data Transfer

9.5.1.6 Single Read and Write

If the register address is not defined, the charger IC send back NACK and go back to the idle state.




図 9-16. Single Write






図 9-17. Single Read

9.5.1.7 Multi-Read and Multi-Write

The charger device supports multi-read and multi-write on REG00 through REG0B.




図 9-18. Multi-Write




図 9-19. Multi-Read

REG09 is a fault register. It keeps all the fault information from last read until the host issues a new read. For example, if Charge Safety Timer Expiration fault occurs but recovers later, the fault register REG09 reports the fault when it is read the first time, but returns to normal when it is read the second time. in order to get the fault information at present, the host has to read REG09 for the second time. The only exception is NTC_FAULT which always reports the actual condition on the TS pin. in addition, REG09 does not support multi-read and multi-write.



9.6 Register Maps

I²C Target Address: 6BH

9.6.1 REG00

表 9-5. REG00 Field Descriptions

Bit	Field	POR	Type	Reset	Description	Comment
7	EN_HIZ	0	R/W	by REG_RST by Watchdog	0 – Disable, 1 – Enable	Enable HIZ Mode 0 – Disable (default) 1 – Enable
6	EN_ICHG_MON[1]	0	R/W	by REG_RST	00 – Enable STAT pin function	
5	EN_ICHG_MON[0]	0	R/W	by REG_RST	(default) 01 – Reserved 11 – Disable STAT pin function (float pin)	
4	IINDPM[4]	1	R/W	by REG_RST	1600 mA	Input Current Limit
3	IINDPM[3]	0	R/W	by REG_RST	800 mA	Offset: 100 mA Range: 100 mA (000000) – 3.2 A
2	IINDPM[2]	1	R/W	by REG_RST	400 mA	(11111)
1	IINDPM[1]	1	R/W	by REG_RST	200 mA	Default: 2400 mA (10111), maximum input current limit, not
0	IINDPM[0]	1	R/W	by REG_RST	100 mA	typical. IINDPM bits are changed automatically after input source detection is completed PSEL = Hi = 500 mA PSEL = Lo = 2.4 A Host can over-write IINDPM register bits after input source detection is completed.

Product Folder Links: BQ25601

LEGEND: R/W = Read/Write; R = Read only



9.6.2 REG01

表 9-6. REG01 Field Descriptions

Bit	Field	POR	Type	Reset	Description	Comment
7	PFM_DIS	0	R/W	by REG_RST	0 – Enable PFM 1 – Disable PFM	Default: 0 - Enable
6	WD_RST	0	R/W	by REG_RST by Watchdog	I ² C Watchdog Timer Reset 0 – Normal ; 1 – Reset	Default: Normal (0) Back to 0 after watchdog timer reset
5	OTG_CONFIG	0	R/W		0 – OTG Disable 1 – OTG Enable	Default: OTG disable (0) Note: 1. OTG_CONFIG would over-ride Charge Enable Function in CHG_CONFIG
4	CHG_CONFIG	1	R/W		0 – Charge Disable 1 – Charge Enable	Default: Charge Battery (1) Note: 1. Charge is enabled when both CE pin is pulled low AND CHG_CONFIG bit is 1.
3	SYS_MIN[2]	1	R/W	by REG_RST	System Minimum Voltage	000: 2.6 V 001: 2.8 V 010: 3 V 011: 3.2 V 100: 3.4 V 101: 3.5 V 110: 3.6 V 111: 3.7 V Default: 3.5 V (101)
2	SYS_MIN[1]	0	R/W	by REG_RST		
1	SYS_MIN[0]	1	R/W	by REG_RST		
0	MIN_V _{BAT} _SEL	0	R/W	by REG_RST	0 – 2.8 V BAT falling, 1 – 2.5 V BAT falling	Minimum battery voltage for OTG mode. Default falling 2.8 V (0); Rising threshold 3.0 V (0)

LEGEND: R/W = Read/Write; R = Read only

English Data Sheet: SLUSCK5



9.6.3 REG02

表 9-7. REG02 Field Descriptions

Bit	Field	POR	Type	Reset	Description	Comment
7	BOOST_LIM	1	R/W	by REG_RST by Watchdog	0 – 0.5 A 1 – 1.2 A	Default: 1.2 A (1) Note: The current limit options listed are minimum current limit specs.
6	Q1_FULLON	0	R/W	by REG_RST	0 – Use higher Q1 RDSON when programmed IINDPM < 700mA (better accuracy) 1 – Use lower Q1 RDSON always (better efficiency)	In boost mode, full FET is always used and this bit has no effect
5	ICHG[5]	1	R/W	by REG_RST by Watchdog	1920 mA	Fast Charge Current Default: 2040 mA (100010) Range: 0 mA (0000000) – 3000 mA (110010) Note: I _{CHG} = 0 mA disables charge. I _{CHG} > 3000 mA (110010 clamped to register value 3000 mA (110010))
4	ICHG[4]	0	R/W	by REG_RST by Watchdog	960 mA	
3	ICHG[3]	0	R/W	by REG_RST by Watchdog	480 mA	
2	ICHG[2]	0	R/W	by REG_RST by Watchdog	240 mA	
1	ICHG[1]	1	R/W	by REG_RST by Watchdog	120 mA	
0	ICHG[0]	0	R/W	by REG_RST by Watchdog	60 mA	

Product Folder Links: BQ25601

LEGEND: R/W = Read/Write; R = Read only



9.6.4 REG03

表 9-8. REG03 Field Descriptions

Bit	Field	POR	Туре	Reset	Description	Comment
7	IPRECHG[3]	0	R/W	by REG_RST by Watchdog	480 mA	Precharge Current Default: 180 mA (0010) Offset: 60 mA Note: IPRECHG > 780 mA clamped to 780 mA (1100)
6	IPRECHG[2]	0	R/W	by REG_RST by Watchdog	240 mA	
5	IPRECHG[1]	1	R/W	by REG_RST by Watchdog	120 mA	
4	IPRECHG[0]	0	R/W	by REG_RST by Watchdog	60 mA	
3	ITERM[3]	0	R/W	by REG_RST by Watchdog	480 mA	Termination Current Default: 180 mA (0010) Offset: 60 mA
2	ITERM[2]	0	R/W	by REG_RST by Watchdog	240 mA	
1	ITERM[1]	1	R/W	by REG_RST by Watchdog	120 mA	
0	ITERM[0]	0	R/W	by REG_RST by Watchdog	60 mA	

Product Folder Links: BQ25601

LEGEND: R/W = Read/Write; R = Read only



9.6.5 REG04

表 9-9. REG04 Field Descriptions

Bit	Field	POR	Type	Reset	Description	Comment
7	VREG[4]	0	R/W	by REG_RST by Watchdog	512 mV	Charge Voltage
6	VREG[3]	1	R/W	by REG_RST by Watchdog	256 mV	Offset: 3.856 V Range: 3.856 V to 4.624 V (11000)
5	VREG[2]	0	R/W	by REG_RST by Watchdog	128 mV	Default: 4.208 V (01011) Special Value:
4	VREG[1]	1	R/W	by REG_RST by Watchdog	64 mV	(01111): 4.352 V Note: Value above 11000 (4.624 V) is clamped to register value 11000
3	VREG[0]	1	R/W	by REG_RST by Watchdog	32 mV	(4.624 V)
2	TOPOFF_TIMER[1]	0	R/W	by REG_RST by Watchdog	00 – Disabled (Default) 01 – 15 minutes	The extended time following the termination condition is met. When
1	TOPOFF_TIMER[0]	0	R/W	by REG_RST by Watchdog	10 – 30 minutes 11 – 45 minutes	disabled, charge terminated when termination conditions are met
0	VRECHG	0	R/W	by REG_RST by Watchdog	0 – 100 mV 1 – 200 mV	Recharge threshold Default: 100 mV (0)

Product Folder Links: BQ25601



9.6.6 REG05

表 9-10. REG05 Field Descriptions

Bit	Field	POR	Type	Reset	Description	Comment		
7	EN_TERM	1	R/W	by REG_RST by Watchdog	0 – Disable 1 – Enable	Default: Enable termination (1)		
6	Reserved	0	R/W	by REG_RST by Watchdog	Reserved	Reserved		
5	WATCHDOG[1]	0	R/W	by REG_RST by Watchdog	00 – Disable timer, 01 – 40 s, 10 –	Default: 40 s (01)		
4	WATCHDOG[0]	1	R/W	by REG_RST by Watchdog	80 s,11 – 160 s	Delault. 40 5 (01)		
3	EN_TIMER	1	R/W	by REG_RST by Watchdog	0 – Disable 1 – Enable both fast charge and precharge timer	Default: Enable (1)		
2	CHG_TIMER	1	R/W	by REG_RST by Watchdog	0 – 5 hrs 1 – 10 hrs	Default: 10 hours (1)		
1	TREG	1	R/W	by REG_RST by Watchdog	Thermal Regulation Threshold: 0 – 90°C 1 – 110°C	Default: 110°C (1)		
0	JEITA_ISET (0C-10C)	1	R/W	by REG_RST by Watchdog	0 – 50% of ICHG 1 – 20% of ICHG	Default: 20% (1)		

Product Folder Links: BQ25601



9.6.7 REG06

表 9-11. REG06 Field Descriptions

Bit	Field	POR	Type	Reset	Description	Comment			
7	OVP[1]	0	R/W	by REG_RST		VAC OVP threshold:			
6	OVP[0]	1	R/W	by REG_RST	Default: 6.5 V (01)	00 - 5.5 V 01 - 6.5 V (5-V input) 10 - 10.5 V (9-V input) 11 - 14 V (12-V input)			
5	BOOSTV[1]	1	R/W	by REG_RST		Boost Regulation Voltage:			
4	BOOSTV[0]	0	R/W	by REG_RST		00 – 4.85 V 01 – 5.00 V 10 – 5.15 V 11 – 5.30 V			
3	VINDPM[3]	0	R/W	by REG_RST	800 mV	Absolute VINDPM Threshold			
2	VINDPM[2]	1	R/W	by REG_RST	400 mV	Offset: 3.9 V			
1	VINDPM[1]	1	R/W	by REG_RST	200 mV	Range: 3.9 V (0000) – 5.4 V (1111)			
0	VINDPM[0]	0	R/W	by REG_RST	100 mV	Default: 4.5 V (0110)			

Product Folder Links: BQ25601



9.6.8 REG07

表 9-12. REG07 Field Descriptions

Bit	Field	POR	Type	Reset	Description	Comment		
7	IINDET_EN	0	R/W	by REG_RST by Watchdog	0 – Not in input current limit detection 1 – Force input current limit detection when VBUS is present	Returns to 0 after input detection is complete		
6	TMR2X_EN	1	R/W	by REG_RST by Watchdog	0 – Disable 1 – Safety timer slowed by 2X during input DPM (both V and I) or JEITA cool, or thermal regulation			
5	BATFET_DIS	0	R/W	by REG_RST	0 – Allow Q4 turn on, 1 – Turn off Q4 with t _{BATFET_DLY} delay time (REG07[3])	Default: Allow Q4 turn on(0)		
4	JEITA_VSET (45C-60C)	0	R/W	by REG_RST by Watchdog	0 – Set Charge Voltage to 4.1V (max), 1 – Set Charge Voltage to VREG			
3	BATFET_DLY	1	R/W	by REG_RST	0 – Turn off BATFET immediately when BATFET_DIS bit is set 1 – Turn off BATFET after t _{BATFET_DLY} (typ. 10 s) when BATFET_DIS bit is set	Default: 1 Turn off BATFET after t _{BATFET_DLY} (typ. 10 s) when BATFET_DIS bit is set		
2	BATFET_RST_EN	1	R/W	by REG_RST by Watchdog	0 – Disable BATFET reset function 1 – Enable BATFET reset function	Default: 1 Enable BATFET reset function		
1	VDPM_BAT_TRACK[1]	0	R/W	by REG_RST	00 – Disable function (VINDPM set	Sets VINDPM to track BAT voltage.		
0	0 VDPM_BAT_TRACK[0] 0 R/W by F			by REG_RST	by register) 01 – VBAT + 200 mV 10 – VBAT + 250 mV 11 – VBAT + 300 mV	Actual VINDPM is higher of register value and VBAT + VDPM_BAT_TRACK		

LEGEND: R/W = Read/Write; R = Read only

Submit Document Feedback

Copyright © 2023 Texas Instruments Incorporated



9.6.9 REG08

表 9-13. REG08 Field Descriptions

Bit	Field	POR	Туре	Reset	Description
7	VBUS_STAT[2]	х	R	NA	VBUS Status register
6	VBUS_STAT[1]	х	R	NA	000 – No input 001 – USB Host SDP (500 mA) → PSEL HIGH
5	VBUS_STAT[0]	x	R	NA	011 – Adapter 2.4 A → PSEL LOW 111 – OTG Software current limit is reported in IINDPM register
4	CHRG_STAT[1]	х	R	NA	Charging status:
3	CHRG_STAT[0]	х	R	NA	00 – Not Charging 01 – Pre-charge (< V _{BATLOWV}) 10 – Fast Charging 11 – Charge Termination
2	PG_STAT	х	R	NA	Power Good status: 0 – Power Not Good 1 – Power Good
1	THERM_STAT	х	R	NA	0 – Not in thermal regulation 1 – In thermal regulation
0	VSYS_STAT	х	R	NA	0 – Not in V _{SYS_MIN} regulation (BAT > V _{SYS_MIN}) 1 – In V _{SYS_MIN} regulation (BAT < V _{SYS_MIN})

Product Folder Links: BQ25601

LEGEND: R/W = Read/Write



9.6.10 REG09

表 9-14. REG09 Field Descriptions

Bit	Field	POR	Type	Reset	Description					
7	WATCHDOG_FAULT	х	R	NA	0 – Normal, 1- Watchdog timer expiration					
6	BOOST_FAULT	х	R	NA	0 – Normal, 1 – VBUS overloaded in OTG, or VBUS OVP, or battery is too low (any conditions that cannot start boost function)					
5	CHRG_FAULT[1]	х	R	NA	00 - Normal, 01 - input fault (VAC OVP or VBAT < VBUS < 3.8 V), 10					
4	CHRG_FAULT[0]	х	R	NA	Thermal shutdown, 11 – Charge Safety Timer Expiration					
3	BAT_FAULT	х	R	NA	0 – Normal, 1 – BATOVP					
2	NTC_FAULT[2]	х	R	NA	JEITA					
1	NTC_FAULT[1]	х	R	NA	000 – Normal, 010 – Warm, 011 – Cool, 101 – Cold, 110 – Hot (Buck mode)					
0	NTC_FAULT[0]	Х	R	NA	000 – Normal, 101 – Cold, 110 – Hot (Boost mode)					

Product Folder Links: BQ25601



9.6.11 REG0A

表 9-15. REG0A Field Descriptions

Bit	Field	POR	Type	Reset	Description
7	VBUS_GD	х	R	NA	0 – Not VBUS attached, 1 – VBUS Attached
6	VINDPM_STAT	х	R	NA	0 – Not in VINDPM, 1 – in VINDPM
5	IINDPM_STAT	х	R	NA	0 – Not in IINDPM, 1 – in IINDPM
4	Reserved	х	R	NA	
3	TOPOFF_ACTIVE	х	R	NA	0 – Top off timer not counting. 1 – Top off timer counting
2	ACOV_STAT	х	R	NA	0 – Device is NOT in ACOV 1 – Device is in ACOV
1	VINDPM_INT_ MASK	0	R/W	by REG_RST	0 – Allow VINDPM INT pulse 1 – Mask VINDPM INT pulse
0	IINDPM_INT_ MASK	0	R/W	by REG_RST	0 – Allow IINDPM INT pulse 1 – Mask IINDPM INT pulse

Product Folder Links: BQ25601



9.6.12 REG0B

表 9-16. REG0B Field Descriptions

Bit	Field	POR	Type	Reset	Description
7	REG_RST	0	R/W	NA	Register reset 0 – Keep current register setting 1 – Reset to default register value and reset safety timer Note: Bit resets to 0 after register reset is completed
6	PN[3]	х	R	NA	
5	PN[2]	х	R	NA	BQ25601 : 0010
4	PN[1]	х	R	NA	DQ23001.0010
3	PN[0]	х	R	NA	
2	Reserved	Х	R	NA	
1	DEV_REV[1]	Х	R	NA	
0	DEV_REV[0]	х	R	NA	

LEGEND: R/W = Read/Write; R = Read only

10 Application and Implementation

注

以下のアプリケーション情報は、TIの製品仕様に含まれるものではなく、TIではその正確性または完全性を保証いたしません。個々の目的に対する製品の適合性については、お客様の責任で判断していただくことになります。お客様は自身の設計実装を検証しテストすることで、システムの機能を確認する必要があります。

10.1 Application Information

A typical application consists of the device configured as an I²C controlled power path management device and a single cell battery charger for Li-lon and Li-polymer batteries used in a wide range of Smartphone and other portable devices. It integrates an input reverse-block FET (RBFET, Q1), high-side switching FET (HSFET, Q2), low-side switching FET (LSFET, Q3), and battery FET (BATFET Q4) between the system and battery. The device also integrates a bootstrap diode for the high-side gate drive.

Product Folder Links: BQ25601

Submit Document Feedback

Copyright © 2023 Texas Instruments Incorporated



10.2 Typical Application




図 10-1. Power Path Management Application

10.2.1 Design Requirements

表 10-1. Design Parameters

PARAMETER	VALUE
V _{VBUS} voltage range	4 V to 13.5 V
Input current limit (REG00[4:0])	2.4 A
Fast charge current limit (REG02[5:0])	2.04 A
Minimum system voltage (REG01[3:1])	3.5 V
Battery regulation voltage (REG04[7:3])	4.2 V

10.2.2 Detailed Design Procedure

10.2.2.1 Inductor Selection

The 1.5-MHz switching frequency allows the use of small inductor and capacitor values to maintain an inductor saturation current higher than the charging current (I_{CHG}) plus half the ripple current (I_{RIPPLE}):

$$I_{SAT} \ge I_{CHG} + (1/2) I_{RIPPLE} \tag{3}$$

The inductor ripple current depends on the input voltage (V_{VBUS}), the duty cycle (D = V_{BAT}/V_{VBUS}), the switching frequency (f_S) and the inductance (L).



$$I_{RIPPLE} = \frac{V_{IN} \times D \times (1 - D)}{fs \times L}$$
(4)

The maximum inductor ripple current occurs when the duty cycle (D) is 0.5 or approximately 0.5. Usually inductor ripple is designed in the range between 20% and 40% maximum charging current as a trade-off between inductor size and efficiency for a practical design.

10.2.2.2 Input Capacitor

Design input capacitance to provide enough ripple current rating to absorb input switching ripple current. The worst case RMS ripple current is half of the charging current when duty cycle is 0.5. If the converter does not operate at 50% duty cycle, then the worst case capacitor RMS current I_{Cin} occurs where the duty cycle is closest to 50% and can be estimated using \pm 5.

$$I_{CIN} = I_{CHG} \times \sqrt{D \times (1 - D)}$$
(5)

Low ESR ceramic capacitor such as X7R or X5R is preferred for input decoupling capacitor and should be placed to the drain of the high-side MOSFET and source of the low-side MOSFET as close as possible. Voltage rating of the capacitor must be higher than normal input voltage level. A rating of 25 V or higher capacitor is preferred for 15-V input voltage. Capacitance of 22 µF is suggested for typical of 3-A charging current.

10.2.2.3 Output Capacitor

Ensure that the output capacitance has enough ripple current rating to absorb the output switching ripple current. \pm 6 shows the output capacitor RMS current I_{COUT} calculation.

$$I_{COUT} = \frac{I_{RIPPLE}}{2 \times \sqrt{3}} \approx 0.29 \times I_{RIPPLE}$$
(6)

The output capacitor voltage ripple can be calculated as follows:

$$\Delta V_{O} = \frac{V_{OUT}}{8LCfs^{2}} \left(1 - \frac{V_{OUT}}{V_{IN}} \right)$$
(7)

At certain input and output voltage and switching frequency, the voltage ripple can be reduced by increasing the output filter LC.


The charger device has internal loop compensation optimized for ≤20-µF ceramic output capacitance. The preferred ceramic capacitor is 10-V rating, X7R or X5R.




10.2.3 Application Curves








English Data Sheet: SLUSCK5









11 Power Supply Recommendations

In order to provide an output voltage on SYS, the BQ25601 device requires a power supply between 3.9-V and 13.5-V input with at least 100-mA current rating connected to VBUS and a single-cell Li-lon battery with voltage $> V_{BATUVLO}$ connected to BAT. The source current rating needs to be at least 3 A in order for the buck converter of the charger to provide maximum output power to SYS.



12 Layout

12.1 Layout Guidelines

The switching node rise and fall times should be minimized for minimum switching loss. Proper layout of the components to minimize high frequency current path loop (see 🗵 12-1) is important to prevent electrical and magnetic field radiation and high frequency resonant problems. Follow this specific order carefully to achieve the proper layout.

- 1. Place input capacitor as close as possible to PMID pin and GND pin connections and use shortest copper trace connection or GND plane.
- 2. Place inductor input pin to SW pin as close as possible. Minimize the copper area of this trace to lower electrical and magnetic field radiation but make the trace wide enough to carry the charging current. Do not use multiple layers in parallel for this connection. Minimize parasitic capacitance from this area to any other trace or plane.
- 3. Put output capacitor near to the inductor and the device. Ground connections need to be tied to the IC ground with a short copper trace connection or GND plane.
- 4. Route analog ground separately from power ground. Connect analog ground and connect power ground separately. Connect analog ground and power ground together using thermal pad as the single ground connection point. Or using a 0-Ω resistor to tie analog ground to power ground.
- 5. Use single ground connection to tie charger power ground to charger analog ground. Just beneath the device. Use ground copper pour but avoid power pins to reduce inductive and capacitive noise coupling.
- 6. Place decoupling capacitors next to the IC pins and make trace connection as short as possible.
- 7. It is critical that the exposed thermal pad on the backside of the device package be soldered to the PCB ground. Ensure that there are sufficient thermal vias directly under the IC, connecting to the ground plane on the other layers.
- 8. Ensure that the number and sizes of vias allow enough copper for a given current path.

Refer to the BQ25601 and BQ25601D (PWR877) Evaluation Module User's Guide for the recommended component placement with trace and via locations. For the VQFN information, refer to the Quad Flatpack No-Lead Logic Packages Application Report and QFN and SON PCB Attachment Application Report.

12.2 Layout Example




図 12-1. High Frequency Current Path






図 12-2. Layout Example



13 Device and Documentation Support

13.1 Device Support

13.1.1 サード・パーティ製品に関する免責事項

サード・パーティ製品またはサービスに関するテキサス・インスツルメンツの出版物は、単独またはテキサス・インスツルメン ツの製品、サービスと一緒に提供される場合に関係なく、サード・パーティ製品またはサービスの適合性に関する是認、サ ード・パーティ製品またはサービスの是認の表明を意味するものではありません。

13.2 Documentation Support

13.2.1 Related Documentation

For related documentation see the following:

BQ25601 and BQ25601D (PWR877) Evaluation Module User's Guide

13.3 ドキュメントの更新通知を受け取る方法

ドキュメントの更新についての通知を受け取るには、ti.com のデバイス製品フォルダを開いてください。「更新の通知を受 け取る」をクリックして登録すると、変更されたすべての製品情報に関するダイジェストを毎週受け取れます。変更の詳細 については、修正されたドキュメントに含まれている改訂履歴をご覧ください。

13.4 サポート・リソース

TI E2E™ サポート・フォーラムは、エンジニアが検証済みの回答と設計に関するヒントをエキスパートから迅速かつ直接 得ることができる場所です。既存の回答を検索したり、独自の質問をしたりすることで、設計で必要な支援を迅速に得るこ とができます。

リンクされているコンテンツは、該当する貢献者により、現状のまま提供されるものです。これらは TI の仕様を構成するも のではなく、必ずしも TI の見解を反映したものではありません。TI の使用条件を参照してください。

13.5 Trademarks

TI E2E[™] is a trademark of Texas Instruments.

すべての商標は、それぞれの所有者に帰属します。

13.6 静電気放電に関する注意事項



この IC は、ESD によって破損する可能性があります。テキサス・インスツルメンツは、IC を取り扱う際には常に適切な注意を払うこと を推奨します。正しい取り扱いおよび設置手順に従わない場合、デバイスを破損するおそれがあります。

ESD による破損は、わずかな性能低下からデバイスの完全な故障まで多岐にわたります。精密な IC の場合、パラメータがわずか に変化するだけで公表されている仕様から外れる可能性があるため、破損が発生しやすくなっています。

13.7 用語集

テキサス・インスツルメンツ用語集 この用語集には、用語や略語の一覧および定義が記載されています。

Product Folder Links: BQ25601

Copyright © 2023 Texas Instruments Incorporated



14 Mechanical, Packaging, and Orderable Information

The following pages include mechanical, packaging, and orderable information. This information is the most current data available for the designated devices. This data is subject to change without notice and revision of this document. For browser-based versions of this data sheet, refer to the left-hand navigation.



PACKAGE OPTION ADDENDUM

10-Dec-2020

PACKAGING INFORMATION

www.ti.com

Orderable Device	Status	Package Type	Package Drawing	Pins	Package Qty	Eco Plan	Lead finish/ Ball material	MSL Peak Temp	Op Temp (°C)	Device Marking (4/5)	Samples
BQ25601RTWR	ACTIVE	WQFN	RTW	24	3000	RoHS & Green	NIPDAU NIPDAUAG	Level-2-260C-1 YEAR	-40 to 85	BQ25601	Samples
BQ25601RTWT	ACTIVE	WQFN	RTW	24	250	RoHS & Green	NIPDAU NIPDAUAG	Level-2-260C-1 YEAR	-40 to 85	BQ25601	Samples

(1) The marketing status values are defined as follows:

ACTIVE: Product device recommended for new designs.

LIFEBUY: TI has announced that the device will be discontinued, and a lifetime-buy period is in effect.

NRND: Not recommended for new designs. Device is in production to support existing customers, but TI does not recommend using this part in a new design.

PREVIEW: Device has been announced but is not in production. Samples may or may not be available.

OBSOLETE: TI has discontinued the production of the device.

(2) RoHS: TI defines "RoHS" to mean semiconductor products that are compliant with the current EU RoHS requirements for all 10 RoHS substances, including the requirement that RoHS substance do not exceed 0.1% by weight in homogeneous materials. Where designed to be soldered at high temperatures, "RoHS" products are suitable for use in specified lead-free processes. TI may reference these types of products as "Pb-Free".

RoHS Exempt: TI defines "RoHS Exempt" to mean products that contain lead but are compliant with EU RoHS pursuant to a specific EU RoHS exemption.

Green: TI defines "Green" to mean the content of Chlorine (CI) and Bromine (Br) based flame retardants meet JS709B low halogen requirements of <=1000ppm threshold. Antimony trioxide based flame retardants must also meet the <=1000ppm threshold requirement.

- (3) MSL, Peak Temp. The Moisture Sensitivity Level rating according to the JEDEC industry standard classifications, and peak solder temperature.
- (4) There may be additional marking, which relates to the logo, the lot trace code information, or the environmental category on the device.
- (5) Multiple Device Markings will be inside parentheses. Only one Device Marking contained in parentheses and separated by a "~" will appear on a device. If a line is indented then it is a continuation of the previous line and the two combined represent the entire Device Marking for that device.
- (6) Lead finish/Ball material Orderable Devices may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead finish/Ball material values may wrap to two lines if the finish value exceeds the maximum column width.

Important Information and Disclaimer: The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.






10-Dec-2020

PACKAGE MATERIALS INFORMATION

www.ti.com 1-Jul-2023

TAPE AND REEL INFORMATION





A0	Dimension designed to accommodate the component width
В0	Dimension designed to accommodate the component length
K0	Dimension designed to accommodate the component thickness
W	Overall width of the carrier tape
P1	Pitch between successive cavity centers

QUADRANT ASSIGNMENTS FOR PIN 1 ORIENTATION IN TAPE



*All dimensions are nominal

Device	Package Type	Package Drawing		SPQ	Reel Diameter (mm)	Reel Width W1 (mm)	A0 (mm)	B0 (mm)	K0 (mm)	P1 (mm)	W (mm)	Pin1 Quadrant
BQ25601RTWR	WQFN	RTW	24	3000	330.0	12.4	4.25	4.25	1.15	8.0	12.0	Q2
BQ25601RTWT	WQFN	RTW	24	250	180.0	12.4	4.25	4.25	1.15	8.0	12.0	Q2

PACKAGE MATERIALS INFORMATION

www.ti.com 1-Jul-2023




*All dimensions are nominal


Device	Package Type	Package Drawing	Pins	SPQ	Length (mm)	Width (mm)	Height (mm)
BQ25601RTWR	WQFN	RTW	24	3000	367.0	367.0	35.0
BQ25601RTWT	WQFN	RTW	24	250	210.0	185.0	35.0

4 x 4, 0.5 mm pitch

PLASTIC QUAD FLATPACK - NO LEAD

This image is a representation of the package family, actual package may vary. Refer to the product data sheet for package details.





- NOTES: A. All linear dimensions are in millimeters. Dimensioning and tolerancing per ASME Y14.5M-1994.
 - B. This drawing is subject to change without notice.
 - C. Quad Flatpack, No-Leads (QFN) package configuration.
 - D. The package thermal pad must be soldered to the board for thermal and mechanical performance.
 - E. See the additional figure in the Product Data Sheet for details regarding the exposed thermal pad features and dimensions.
 - F. Falls within JEDEC MO-220.



RTW (S-PWQFN-N24)


PLASTIC QUAD FLATPACK NO-LEAD

THERMAL INFORMATION

This package incorporates an exposed thermal pad that is designed to be attached directly to an external heatsink. The thermal pad must be soldered directly to the printed circuit board (PCB). After soldering, the PCB can be used as a heatsink. In addition, through the use of thermal vias, the thermal pad can be attached directly to the appropriate copper plane shown in the electrical schematic for the device, or alternatively, can be attached to a special heatsink structure designed into the PCB. This design optimizes the heat transfer from the integrated circuit (IC).

For information on the Quad Flatpack No—Lead (QFN) package and its advantages, refer to Application Report, QFN/SON PCB Attachment, Texas Instruments Literature No. SLUA271. This document is available at www.ti.com.

The exposed thermal pad dimensions for this package are shown in the following illustration.



Bottom View
Exposed Thermal Pad Dimensions


4206249-5/P 05/15

NOTES: A. All linear dimensions are in millimeters



RTW (S-PWQFN-N24)

PLASTIC QUAD FLATPACK NO-LEAD



NOTES:

- A. All linear dimensions are in millimeters.
- B. This drawing is subject to change without notice.
- C. Publication IPC-7351 is recommended for alternate designs.
- D. This package is designed to be soldered to a thermal pad on the board. Refer to Application Note, Quad Flat—Pack Packages, Texas Instruments Literature No. SLUA271, and also the Product Data Sheets for specific thermal information, via requirements, and recommended board layout. These documents are available at www.ti.com www.ti.com.
- E. Laser cutting apertures with trapezoidal walls and also rounding corners will offer better paste release. Customers should contact their board assembly site for stencil design recommendations. Refer to IPC 7525 for stencil design considerations.
- F. Customers should contact their board fabrication site for recommended solder mask tolerances and via tenting recommendations for vias placed in the thermal pad.



重要なお知らせと免責事項

TI は、技術データと信頼性データ (データシートを含みます)、設計リソース (リファレンス・デザインを含みます)、アプリケーションや設計に関する各種アドバイス、Web ツール、安全性情報、その他のリソースを、欠陥が存在する可能性のある「現状のまま」提供しており、商品性および特定目的に対する適合性の黙示保証、第三者の知的財産権の非侵害保証を含むいかなる保証も、明示的または黙示的にかかわらず拒否します。

これらのリソースは、TI 製品を使用する設計の経験を積んだ開発者への提供を意図したものです。(1) お客様のアプリケーションに適した TI 製品の選定、(2) お客様のアプリケーションの設計、検証、試験、(3) お客様のアプリケーションに該当する各種規格や、その他のあらゆる安全性、セキュリティ、規制、または他の要件への確実な適合に関する責任を、お客様のみが単独で負うものとします。

上記の各種リソースは、予告なく変更される可能性があります。これらのリソースは、リソースで説明されている TI 製品を使用するアプリケーションの開発の目的でのみ、TI はその使用をお客様に許諾します。これらのリソースに関して、他の目的で複製することや掲載することは禁止されています。TI や第三者の知的財産権のライセンスが付与されている訳ではありません。お客様は、これらのリソースを自身で使用した結果発生するあらゆる申し立て、損害、費用、損失、責任について、TI およびその代理人を完全に補償するものとし、TI は一切の責任を拒否します。

TI の製品は、TI の販売条件、または ti.com やかかる TI 製品の関連資料などのいずれかを通じて提供する適用可能な条項の下で提供されています。TI がこれらのリソースを提供することは、適用される TI の保証または他の保証の放棄の拡大や変更を意味するものではありません。

お客様がいかなる追加条項または代替条項を提案した場合でも、TIはそれらに異議を唱え、拒否します。

郵送先住所:Texas Instruments, Post Office Box 655303, Dallas, Texas 75265 Copyright © 2023, Texas Instruments Incorporated