









BQ28Z610


BQ28Z610 Impedance Track™ バッテリ残量計および保護ソリューション、 1~2個の直列セルのリチウムイオン・バッテリ・パック用

1 特長

- 専用のマスタ・モード I2C インターフェイスを使った自 律的なバッテリ充電制御
- 内部バイパス付きのセル・バランス機能により、バッテリ の状態を最適化
- N-CH FET ドライブのハイサイド保護により、フォルト状 況でもシリアル・バス通信が可能
- 電圧、電流、温度について保護レベルをプログラム可
- 2 つの独立した ADC を持つアナログ・フロント・エンド
 - 電流と電圧の同時サンプリングに対応
 - 入力オフセット誤差 1µV 未満 (標準値) の高精度 クーロン・カウンタ
- 最低 1mΩ の電流センス抵抗をサポートし、1mA の電 流測定が可能
- Windows® のバッテリ・トリップ・ポイント (BTP) 機能の 統合をサポート
- SHA-1 認証レスポンダによるバッテリ・パックのセキュリ ティ強化
- 400kHz の I²C バス通信インターフェイスによる高速な プログラミングとデータ・アクセス
- 小型の 12 ピン VSON パッケージ (DRZ)

2 アプリケーション

- タブレット・コンピュータ
- 携帯およびウェアラブルの健康機器
- 携帯用オーディオ・デバイス
 - ワイヤレス (Bluetooth) スピーカ



簡略回路図

3 概要

テキサス・インスツルメンツの BQ28Z610 デバイスは、高 集積、高精度の 1S~2S (1~2 個の直列) セル向けバッ テリ残量計であり、保護ソリューションを搭載しているほか、 自律型の充電制御とセル・バランシングを実現します。

BQ28Z610 デバイスは、充電電流および電圧情報のマス タ・モード I²C ブロードキャストによって自律的に充電を制 御できるため、システムのホスト・コントローラに通常生じる ソフトウェアのオーバーヘッドを解消できます。


BQ28Z610 は、フラッシュ・プログラマブル・カスタム RISC (Reduced Instruction Set CPU)、安全保護機能、 1~2 シリーズ・セル・リチウムイオンおよびリチウムポリマ ー・バッテリ・パック認証機能を備えた完全統合型パック・ ベース・ソリューションです。

BQ28Z610 バッテリ残量計は I²C 互換のインターフェイス で通信を行い、超低消費電力かつ高速の TI BQBMP プ ロセッサ、高精度のアナログ測定機能、内蔵のフラッシュ・ メモリ、ペリフェラルおよび通信ポートのアレイ、N-CH FET ドライブ、SHA-1認証変換レスポンダを組み合わせた、完 全な高性能バッテリ管理ソリューションです。

製品情報

部品番号 ⁽¹⁾	パッケージ	本体サイズ (公称)
BQ28Z610	VSON (12)	4mm × 2.5mm

利用可能なすべてのパッケージについては、このデータシートの 末尾にある注文情報を参照してください。



ワイヤレス (Bluetooth) スピーカ・アプリケーション ブロック図



Table of Contents

1 特長	1	7.21 Instruction Flash	
2 アプリケーション		7.22 Data Flash	
3 概要		7.23 Current Protection Thresholds	10
4 Revision History		7.24 Current Protection Timing	10
5 Description (Continued)		7.25 N-CH FET Drive (CHG, DSG)	<mark>1</mark> 1
6 Pin Configuration and Functions		7.26 I ² C Interface I/O	<mark>1</mark> 1
7 Specifications		7.27 I ² C Interface Timing	12
7.1 Absolute Maximum Ratings		7.28 Typical Characteristics	13
7.2 ESD Ratings		8 Detailed Description	16
7.3 Recommended Operating Conditions		8.1 Overview	
7.4 Thermal Information		8.2 Functional Block Diagram	16
7.5 Supply Current		8.3 Feature Description	17
7.6 Power Supply Control		8.4 Device Functional Modes	<mark>2</mark> 1
7.7 Low-Voltage General Purpose I/O, TS1		9 Applications and Implementation	
7.8 Power-On Reset (POR)		9.1 Application Information	
7.9 Internal 1.8-V LDO		9.2 Typical Applications	
7.10 Current Wake Comparator		10 Layout	
7.11 Coulomb Counter		10.1 Layout Guidelines	
7.12 ADC Digital Filter	7	10.2 Layout Example	
7.13 ADC Multiplexer		11 Device and Documentation Support	
7.14 Cell Balancing Support		11.1 サード・パーティ製品に関する免責事項	29
7.15 Internal Temperature Sensor		11.2 Documentation Support	29
7.16 NTC Thermistor Measurement Support		11.3ドキュメントの更新通知を受け取る方法	29
7.17 High-Frequency Oscillator		11.4 静電気放電に関する注意事項	29
7.18 Low-Frequency Oscillator		11.5 サポート・リソース	29
7.19 Voltage Reference 1		11.6 Trademarks	
7.20 Voltage Reference 2	9	11.7 用語集	

4 Revision History

Changes from Revision C (October 2017) to Revision D (June 2021)	Page
Changed Absolute Maximum Ratings	
Changed I ² C Interface I/O	11
Changes from Revision B (December 2015) to Revision C (October 2017)	Page
• アプリケーション を変更	1
Added Wireless (Bluetooth) Speaker Application Block Diagram	<mark>23</mark>

5 Description (Continued)

The BQ28Z610 device provides an array of battery and system safety functions, including overcurrent in discharge, short circuit in charge, and short circuit in discharge protection for the battery, as well as FET protection for the N-channel FETs, internal AFE watchdog, and cell balancing. Through firmware, the devices can provide a larger array of features including protection against overvoltage, undervoltage, overtemperature, and more.

Product Folder Links: BQ28Z610



6 Pin Configuration and Functions




表 6-1. Pin Functions

PIN NUMBER	PIN NAME	TYPE	DESCRIPTION
1	VSS	P ⁽¹⁾	Device ground
2	SRN	Al	Analog input pin connected to the internal coulomb counter peripheral for integrating a small voltage between SRP and SRN where SRP is the top of the sense resistor.
3	SRP	Al	Analog input pin connected to the internal coulomb counter peripheral for integrating a small voltage between SRP and SRN where SRP is the top of the sense resistor.
4 TS1 Al Temperature input for ADC to the oversampled ADC channel, and optional Bat Point (BTP) output			Temperature input for ADC to the oversampled ADC channel, and optional Battery Trip Point (BTP) output
5	SCL	I/O	Serial Clock for I ² C interface; requires external pullup when used
6	SDA	I/O	Serial Data for I ² C interface; requires external pullup
7	DSG	0	N-CH FET drive output pin
8	PACK	AI, P	Pack sense input pin
9	CHG	0	N-CH FET drive output pin
10	PBI	Р	Power supply backup input pin
11	VC2	AI, P	Sense voltage input pin for most positive cell, balance current input for most positive cell. Primary power supply input and battery stack measurement input (BAT)
12	VC1	Al	Sense voltage input pin for least positive cell, balance current input for least positive cell
	PWPD	_	Exposed Pad, electrically connected to VSS (external trace)

⁽¹⁾ P = Power Connection, O = Digital Output, AI = Analog Input, I = Digital Input, I/O = Digital Input/Output



7 Specifications

7.1 Absolute Maximum Ratings

Over operating free-air temperature range (unless otherwise noted)(1)

		MIN	MAX	UNIT
Supply voltage range, V _{CC}	VC2, PBI	-0.3	30	V
	PACK	-0.3	30	V
	TS	-0.3	V _{REG} + 0.3	V
	SRP, SRN	-0.3	V _{REG} + 0.3	V
Input voltage range, V _{IN}	VC2	VC1 – 0.3	VC1 + 8.5 or VSS + 30	V
	VC1	VSS - 0.3	VSS + 8.5 or VSS + 30	V
Communications Interface	SDA, SCL	-0.3	6	
Output voltage range, V _O	CHG, DSG	-0.3	32	V
Maximum VSS current, I _{SS}			±50	mA
Functional Temperature, T _{FUNC}	·	-40	110	°C
Lead temperature (soldering, 10 s),	T _{SOLDER}	±300		°C
Storage temperature range, T _{STG}		-65	150	°C

⁽¹⁾ Stresses beyond those listed under absolute maximum ratings may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated under recommended operating conditions is not implied. Exposure to absolute—maximum—rated conditions for extended periods may affect device reliability.

7.2 ESD Ratings

		VALUE	UNIT
V _(ESD)	Human body model (HBM), per ANSI/ESDA/JEDEC JS-001, all pins ⁽¹⁾	±2000	V
	Charged device model (CDM), per JEDEC specification JESD22-C101, all pins ⁽²⁾	±500	

- (1) JEDEC document JEP155 states that 500-V HBM allows safe manufacturing with a standard ESD control process.
- (2) JEDEC document JEP157 states that 250-V CDM allows safe manufacturing with a standard ESD control process.

7.3 Recommended Operating Conditions

Typical values stated where $T_A = 25^{\circ}\text{C}$ and VCC = 7.2 V, Min/Max values stated where $T_A = -40^{\circ}\text{C}$ to 85°C and VCC = 2.2 V to 26 V (unless otherwise noted)

PARAMETER		TEST CONDITION	MIN	NOM	MAX	UNIT
V _{CC}	Supply voltage	VC2, PBI	2.2		26	V
V _{SHUTDOWN} -	Shutdown voltage	V _{PACK} < V _{SHUTDOWN} -	1.8	2.0	2.2	V
V _{SHUTDOWN+}	Start-up voltage	V _{PACK} > V _{SHUTDOWN} + V _{HYS}	2.05	2.25	2.45	V
V _{HYS}	Shutdown voltage hysteresis	V _{SHUTDOWN+} – V _{SHUTDOWN}		250		mV
		SDA, SCL			5.5	
		TS1			V_{REG}	٧
V	lanut valtaga ranga	SRP, SRN	-0.2		0.2	
V_{IN}	Input voltage range	VC2	V _{VC1}		V _{VC1} + 5	
		VC1	V _{VSS}		V _{VSS} + 5	
		PACK			26	
Vo	Output voltage range	CHG, DSG			26	V
C _{PBI}	External PBI capacitor		2.2			μF
T _{OPR}	Operating temperature		-40		85	°C

Submit Document Feedback

Copyright © 2023 Texas Instruments Incorporated

7.4 Thermal Information

		BQ28Z610	
	THERMAL METRIC ⁽¹⁾	DRZ	UNIT
		12 PINS	
R _{0JA, High K}	Junction-to-ambient thermal resistance	186.4	
R _{0JC(top)}	Junction-to-case(top) thermal resistance	90.4	
R _{θJB}	Junction-to-board thermal resistance	110.7	°C/W
ΨЈТ	Junction-to-top characterization parameter	96.7	C/VV
ΨЈВ	Junction-to-board characterization parameter	90	
R _{θJC(bottom)}	Junction-to-case(bottom) thermal resistance	n/a	

⁽¹⁾ For more information about traditional and new thermal metrics, see the Semiconductor and IC Package Thermal Metrics application report, SPRA953.

7.5 Supply Current

Typical values stated where $T_A = 25^{\circ}$ C and VCC = 7.2 V, Min/Max values stated where $T_A = -40^{\circ}$ C to 85°C and VCC = 2.2 V to 7.6 V (unless otherwise noted)

PARAMETER		TEST CONDITION	MIN TYP		MAX	UNIT
I _{NORMAL} (1)	NORMAL mode	CHG = ON, DSG = ON, No Flash Write		250		μA
I _{SLEEP} (1)	SLEEP mode	CHG = OFF, DSG = OFF, No Communication on Bus		100		
I _{SHUTDOWN}	SHUTDOWN mode			0.5	2	μΑ

⁽¹⁾ Dependent on the use of the correct firmware (FW) configuration

7.6 Power Supply Control

Typical values stated where $T_A = 25^{\circ}\text{C}$ and VCC = 7.2 V, Min/Max values stated where $T_A = -40^{\circ}\text{C}$ to 85°C and VCC = 2.2 V to 7.6 V (unless otherwise noted)

PAI	RAMETER	TEST CONDITION	MIN	TYP	MAX	UNIT
V _{SWITCHOVER} -	VC2 to PACK switchover voltage	V _{VC2} < V _{SWITCHOVER} -	2.0	2.1	2.2	V
V _{SWITCHOVER+}	PACK to VC2 switchover voltage	V _{VC2} > V _{SWITCHOVER} + V _{HYS}	3.0	3.1	3.2	V
V _{HYS}	Switchover voltage hysteresis	V _{SWITCHOVER+} – V _{SWITCHOVER}		1000		mV
		VC2 pin, VC2 = 0 V, PACK = 25 V			1	
I _{LKG}	Input Leakage	PACK pin, VC2 = 25 V, PACK = 0 V			1	μA
LKG	current	VC2 and PACK pins, VC2 = 0 V, PACK = 0 V, PBI = 25 V			1	F
R _{PACK(PD)}	Internal pulldown resistance	PACK	30	40	50	kΩ

7.7 Low-Voltage General Purpose I/O, TS1

Typical values stated where T_A = 25°C and VCC = 7.2 V, Min/Max values stated where T_A = -40°C to 85°C and VCC = 2.2 V to 7.6 V (unless otherwise noted)

to 7.0 V (unless otherwise noted)							
	PARAMETER	TEST CONDITION	MIN	TYP	MAX	UNIT	
V_{IH}	High-level input		0.65 x V _{REG}			V	
V_{IL}	Low-level input				0.35 x V _{REG}	V	
V _{OH}	Output voltage high	I _{OH} = - 1.0 mA	0.75 x V _{REG}			V	
V _{OL}	Output voltage low	I _{OL} = 1.0 mA			0.2 x V _{REG}	V	
C _{IN}	Input capacitance			5		pF	



Typical values stated where $T_A = 25^{\circ}C$ and VCC = 7.2 V, Min/Max values stated where $T_A = -40^{\circ}C$ to 85°C and VCC = 2.2 V to 7.6 V (unless otherwise noted)

	PARAMETER	TEST CONDITION	MIN	TYP	MAX	UNIT
I _{LKG}	Input leakage current				1	μА

7.8 Power-On Reset (POR)

Typical values stated where $T_A = 25^{\circ}C$ and VCC = 7.2 V, Min/Max values stated where $T_A = -40^{\circ}C$ to 85°C and VCC = 2.2 V to 7.6 V (unless otherwise noted)

	PARAMETER	TEST CONDITION	MIN	TYP	MAX	UNIT
V _{REGIT}	Negative-going voltage input	V _{REG}	1.51	1.55	1.59	V
V _{HYS}	Power-on reset hysteresis	V _{REGIT+} – V _{REGIT}	70	100	130	mV
t _{RST}	Power-on reset time		200	300	400	μs

7.9 Internal 1.8-V LDO

Typical values stated where $T_A = 25^{\circ}\text{C}$ and VCC = 7.2 V, Min/Max values stated where $T_A = -40^{\circ}\text{C}$ to 85°C and VCC = 2.2 V to 7.6 V (unless otherwise noted)

	PARAMETER	TEST CONDITION	MIN	TYP	MAX	UNIT
V_{REG}	Regulator voltage		1.6	1.8	2.0	V
$\Delta V_{O(TEMP)}$	Regulator output over temperature	$\Delta V_{REG}/\Delta T_A$, $I_{REG} = 10 \text{ mA}$		±0.25%		
$\Delta V_{O(LINE)}$	Line regulation	$\Delta V_{REG}/\Delta V_{BAT}$, $V_{BAT} = 10 \text{ mA}$	-0 .6%		0.5%	
$\Delta V_{O(LOAD)}$	Load regulation	$\Delta V_{REG}/\Delta I_{REG}$, $I_{REG} = 0$ mA to 10 mA	-1.5%		1.5%	
I _{REG}	Regulator output current limit	$V_{REG} = 0.9 \text{ x } V_{REG(NOM)}, V_{IN} > 2.2 \text{ V}$	20			mA
I _{SC}	Regulator short-circuit current limit	V _{REG} = 0 x V _{REG(NOM)}	25	40	50	mA
PSRR _{REG}	Power supply rejection ratio	$\Delta V_{BAT}/\Delta V_{REG}$, I _{REG} = 10 mA, V _{IN} > 2.5 V, f = 10 Hz		40		dB
V _{SLEW}	Slew rate enhancement voltage threshold	V _{REG}	1.58	1.65		V

7.10 Current Wake Comparator

Typical values stated where $T_A = 25^{\circ}\text{C}$ and VCC = 7.2 V, Min/Max values stated where $T_A = -40^{\circ}\text{C}$ to 85°C and VCC = 2.2 V to 7.6 V (unless otherwise noted)

PARAMETER	2	TEST CONDITION	MIN	TYP	MAX	UNIT
		V _{WAKE} = V _{SRP} - V _{SRN} WAKE_CONTROL[WK1, WK0] = 0,0	±0.3	±0.625	±0.9	mV
\ \ \ \ \ \ \ \ \ \ \ \ \ \ \ \ \ \ \	Wake voltage threshold	V _{WAKE} = V _{SRP} - V _{SRN} WAKE_CONTROL[WK1, WK0] = 0,1	±0.6	±1.25	±1.8	mV
V _{WAKE}		V _{WAKE} = V _{SRP} - V _{SRN} WAKE_CONTROL[WK1, WK0] = 1,0	±1.2	±2.5	±3.6	mV
		V _{WAKE} = V _{SRP} - V _{SRN} WAKE_CONTROL[WK1, WK0] = 1,1	±2.4	±5.0	±7.2	mV
V _{WAKE(DRIFT)}	Temperature drift of V _{WAKE} accuracy			0.5%		°C
t _{WAKE}	Time from application of current to wake			0.25	0.5	ms
t _{WAKE(SU)}	Wake up comparator startup time	[WKCHGEN] = 0 and [WKDSGEN] = 0 to [WKCHGEN] = 1 and [WKDSGEN] = 1		250	640	μs

Submit Document Feedback

Copyright © 2023 Texas Instruments Incorporated

7.11 Coulomb Counter

Typical values stated where $T_A = 25^{\circ}C$ and VCC = 7.2 V, Min/Max values stated where $T_A = -40^{\circ}C$ to 85°C and VCC = 2.2 V to 7.6 V (unless otherwise noted)

PARAMETER	TEST CONDITION	MIN	TYP	MAX	UNIT
Input voltage range		-100		100	mV
Full scale range		-V _{REF1} /10		+V _{REF1} /10	mV
Differential nonlinearity	16-bit, No missing codes			±1	LSB
Integral nonlinearity	16-bit, Best fit over input voltage range		±5.2	±22.3	LSB
Offset error	16-bit, Post-calibration		±1.3	±2.6	LSB
Offset error drift	15-bit + sign, Post-calibration		0.04	0.07	LSB/°C
Gain error	15-bit + sign, Over input voltage range		±131	±492	LSB
Gain error drift	15-bit + sign, Over input voltage range		4.3	9.8	LSB/°C
Effective input resistance		2.5			ΜΩ

7.12 ADC Digital Filter

Typical values stated where $T_A = 25^{\circ}\text{C}$ and VCC = 7.2 V, Min/Max values stated where $T_A = -40^{\circ}\text{C}$ to 85°C and VCC = 2.2 V to 7.6 V (unless otherwise noted)

PARAMETER	TEST CONDITION	MIN	TYP	MAX	UNIT
	ADCTL[SPEED1, SPEED0] = 0, 0		31.25		
	ADCTL[SPEED1, SPEED0] = 0, 1		15.63		ma
tconv	ADCTL[SPEED1, SPEED0] = 1, 0	ADCTL[SPEED1, SPEED0] = 1, 0	7.81		ms
	ADCTL[SPEED1, SPEED0] = 1, 1		1.95		
Resolution	No missing codes, ADCTL[SPEED1, SPEED0] = 0, 0		16		Bits
	With sign, ADCTL[SPEED1, SPEED0] = 0, 0	14	15		
Effective resolution	With sign, ADCTL[SPEED1, SPEED0] = 0, 1	13	14		Bits
Lifective resolution	With sign, ADCTL[SPEED1, SPEED0] = 1, 0	11	11 12		סווט
	With sign, ADCTL[SPEED1, SPEED0] = 1, 1	9	10		

7.13 ADC Multiplexer

Typical values stated where $T_A = 25^{\circ}$ C and VCC = 7.2 V, Min/Max values stated where $T_A = -40^{\circ}$ C to 85°C and VCC = 2.2 V to 7.6 V (unless otherwise noted)

PARAMETER		TEST CONDITION	MIN	TYP	MAX	UNIT
		VC1-VSS, VC2-VC1	0.1980	0.2000	0.2020	
K	K Scaling factor	VC2-VSS, PACK-VSS	0.0485	0.050	0.051	_
		V _{REF1} /2	0.490	0.500	0.510	
		VC2-VSS, PACK-VSS	-0.2		20	
V _{IN}	Input voltage range	TS1	-0.2		0.8 × V _{REF1}	V
		TS1	-0.2		0.8 × V _{REG}	
I _{LKG}	Input leakage current	VC1, VC2 cell balancing off, cell detach detection off, ADC multiplexer off			1	μA

7.14 Cell Balancing Support

Typical values stated where $T_A = 25^{\circ}C$ and VCC = 7.2 V, Min/Max values stated where $T_A = -40^{\circ}C$ to 85°C and VCC = 2.2 V to 7.6 V (unless otherwise noted)

PARAM	IETER	TEST CONDITION	MIN	TYP	MAX	UNIT
R _{CB}	Internal cell balance resistance	R _{DS(ON)} for internal FET switch at 2 V < V _{DS} < 4 V			200	Ω



7.15 Internal Temperature Sensor

Typical values stated where $T_A = 25^{\circ}\text{C}$ and VCC = 7.2 V, Min/Max values stated where $T_A = -40^{\circ}\text{C}$ to 85°C and VCC = 2.2 V to 7.6 V (unless otherwise noted)

PARAME	TER	TEST CONDITION	MIN	TYP	MAX	UNIT
V _{TEMP}	Internal temperature	V _{TEMPP}	-1.9	-2.0	-2.1	mV/°C
	sensor voltage drift	V _{TEMPP} – V _{TEMPN} ⁽¹⁾	0.177	0.178	0.179	

⁽¹⁾ Assured by design

7.16 NTC Thermistor Measurement Support

Typical values stated where $T_A = 25^{\circ}C$ and VCC = 7.2 V, Min/Max values stated where $T_A = -40^{\circ}C$ to 85°C and VCC = 2.2 V to 7.6 V (unless otherwise noted)

PARAMETEI	R	TEST CONDITION	MIN	TYP	MAX	UNIT
R _{NTC(PU)}	Internal pullup resistance	TS1	14.4	18	21.6	kΩ
R _{NTC(DRIFT)}	Resistance drift over temperature	TS1	-360	-280	-200	PPM/°C

7.17 High-Frequency Oscillator

Typical values stated where $T_A = 25^{\circ}$ C and VCC = 7.2 V, Min/Max values stated where $T_A = -40^{\circ}$ C to 85°C and VCC = 2.2 V to 7.6 V (unless otherwise noted)

PARAMET	ER	TEST CONDITION	MIN	TYP	MAX	UNIT
f _{HFO}	Operating frequency			16.78		MHz
f	Eroguanov orrar	$T_A = -20$ °C to 70°C, includes frequency drift	-2.5%	±0.25%	2.5%	
THFO(ERR)	Frequency error	$T_A = -40$ °C to 85°C, includes frequency drift	-3.5%	±0.25%	3.5%	
t	Start-up time	T _A = -20°C to 85°C, Oscillator frequency within +/-3% of nominal, CLKCTL[HFRAMP] = 1			4	ms
thfo(SU)	Otait-up time	Oscillator frequency within +/–3% of nominal, CLKCTL[HFRAMP] = 0			100	μs

7.18 Low-Frequency Oscillator

Typical values stated where $T_A = 25^{\circ}$ C and VCC = 7.2 V, Min/Max values stated where $T_A = -40^{\circ}$ C to 85°C and VCC = 2.2 V to 7.6 V (unless otherwise noted)

PARAMETI	ER	TEST CONDITION	MIN	TYP	MAX	UNIT
f _{LFO}	Operating frequency			262.144		kHz
f _{LFO(LP)}	Operating frequency in low power mode			247		kHz
f	Frequency error	T _A = -20°C to 70°C, includes frequency drift	-1.5%	±0.25%	1.5%	
TLFO(ERR)		T _A = -40°C to 85°C, includes frequency drift	-2.5%	±0.25%	2.5%	
f _{LFO(LPERR)}	Frequency error in low power mode		-5%		5%	
f _{LFO(FAIL)}	Failure detection frequency		30	80	100	kHz

7.19 Voltage Reference 1

Typical values stated where $T_A = 25^{\circ}\text{C}$ and VCC = 7.2 V, Min/Max values stated where $T_A = -40^{\circ}\text{C}$ to 85°C and VCC = 2.2 V to 7.6 V (unless otherwise noted)

PARAMETER		TEST CONDITION	MIN	TYP	MAX	UNIT
V _{REF1}	Internal reference voltage	T _A = 25°C, after trim	1.215	1.220	1.225	V

Submit Document Feedback

Copyright © 2023 Texas Instruments Incorporated

Typical values stated where $T_A = 25^{\circ}\text{C}$ and VCC = 7.2 V, Min/Max values stated where $T_A = -40^{\circ}\text{C}$ to 85°C and VCC = 2.2 V to 7.6 V (unless otherwise noted)

PARAMETER	₹	TEST CONDITION	MIN	TYP	MAX	UNIT
V	Internal reference	T _A = 0°C to 60°C, after trim		±50		PPM/°C
VREF1(DRIFT)	voltage drift	T _A = -40°C to 85°C, after trim		±80		FFIVI/ C

7.20 Voltage Reference 2

Typical values stated where $T_A = 25^{\circ}$ C and VCC = 7.2 V, Min/Max values stated where $T_A = -40^{\circ}$ C to 85°C and VCC = 2.2 V to 7.6 V (unless otherwise noted)

PARAMETER	R	TEST CONDITION	MIN	TYP	MAX	UNIT
V _{REF2}	Internal reference voltage	T _A = 25°C, after trim	1.215	1.220	1.225	V
V _{REF2(DRIFT)} Internal reference voltage drift	Internal reference	T _A = 0°C to 60°C, after trim		±50		PPM/°C
	voltage drift	$T_A = -40$ °C to 85°C, after trim		±80		PPIM/ C

7.21 Instruction Flash

Typical values stated where $T_A = 25^{\circ}\text{C}$ and VCC = 7.2 V, Min/Max values stated where $T_A = -40^{\circ}\text{C}$ to 85°C and VCC = 2.2 V to 7.6 V (unless otherwise noted)

PARAMETE	R	TEST CONDITION	MIN	TYP	MAX	UNIT
	Data retention		10			Years
	Flash programming write cycles		1000			Cycles
t _{PROGWORD}	Word programming time	T _A = -40°C to 85°C			40	μs
t _{MASSERASE}	Mass-erase time	T _A = -40°C to 85°C			40	ms
t _{PAGEERASE}	Page-erase time	T _A = -40°C to 85°C			40	ms
I _{FLASHREAD}	Flash-read current	T _A = -40°C to 85°C			2	mA
I _{FLASHWRITE}	Flash-write current	$T_A = -40$ °C to 85°C			5	mA
I _{FLASHERASE}	Flash-erase current	T _A = -40°C to 85°C			15	mA

7.22 Data Flash

Typical values stated where $T_A = 25^{\circ}\text{C}$ and VCC = 7.2 V, Min/Max values stated where $T_A = -40^{\circ}\text{C}$ to 85°C and VCC = 2.2 V to 7.6 V (unless otherwise noted)

PARAMETE	R	TEST CONDITION	MIN	TYP	MAX	UNIT
	Data retention		10			Years
	Flash programming write cycles		20000			Cycles
t _{PROGWORD}	Word programming time	T _A = -40°C to 85°C			40	μs
t _{MASSERASE}	Mass-erase time	$T_A = -40$ °C to 85°C			40	ms
t _{PAGEERASE}	Page-erase time	$T_A = -40$ °C to 85°C			40	ms
I _{FLASHREAD}	Flash-read current	$T_A = -40$ °C to 85°C			1	mA
I _{FLASHWRITE}	Flash-write current	$T_A = -40$ °C to 85°C			5	mA
I _{FLASHERASE}	Flash-erase current	$T_A = -40$ °C to 85°C			15	mA



7.23 Current Protection Thresholds

Typical values stated where $T_A = 25^{\circ}\text{C}$ and VCC = 7.2 V, Min/Max values stated where $T_A = -40^{\circ}\text{C}$ to 85°C and VCC = 2.2 V to 7.6 V (unless otherwise noted)

PARAME	TER	TEST CONDITION	MIN	TYP	MAX	UNIT
V _{OCD}	OCD detection threshold	V _{OCD} = V _{SRP} - V _{SRN} , PROTECTION_CONTROL[RSNS] = 1	-16.6		-100	mV
VOCD	voltage range	$V_{OCD} = V_{SRP} - V_{SRN}$ PROTECTION_CONTROL[RSNS] = 0	-8.3		-50	IIIV
$\Delta V_{ m OCD}$	OCD detection threshold	V _{OCD} = V _{SRP} - V _{SRN} , PROTECTION_CONTROL[RSNS] = 1		-5.56		mV
ΔV _{OCD}	voltage program step	$V_{OCD} = V_{SRP} - V_{SRN}$ PROTECTION_CONTROL[RSNS] = 0		-2.78		IIIV
/\// ₀₀₀	SCC detection threshold	V _{SCC} = V _{SRP} - V _{SRN} , PROTECTION_CONTROL[RSNS] = 1	44.4		200	mV
	voltage range	V _{SCC} = V _{SRP} - V _{SRN} , PROTECTION_CONTROL[RSNS] = 0	22.2		100	IIIV
ΔV_{SCC}	SCC detection threshold voltage program step	V _{SCC} = V _{SRP} - V _{SRN} , PROTECTION_CONTROL[RSNS] = 1		22.2		mV
		V _{SCC} = V _{SRP} - V _{SRN} , PROTECTION_CONTROL[RSNS] = 0		11.1		IIIV
V	SCD1 detection threshold	V _{SCD1} = V _{SRP} – V _{SRN,} PROTECTION_CONTROL[RSNS] = 1	-44.4		-200	mV
V _{SCD1}	voltage range	V _{SCD1} = V _{SRP} - V _{SRN} , PROTECTION_CONTROL[RSNS] = 0	-22.2		-100	IIIV
۸۱/	SCD1 detection threshold	V _{SCD1} = V _{SRP} – V _{SRN,} PROTECTION_CONTROL[RSNS] = 1		-22.2		mV
ΔV _{SCD1}	voltage program step	V _{SCD1} = V _{SRP} - V _{SRN,} PROTECTION_CONTROL[RSNS] = 0		-11.1		mv
V	SCD2 detection threshold	V _{SCD2} = V _{SRP} - V _{SRN} , PROTECTION_CONTROL[RSNS] = 1	-44.4		-200	mV
V _{SCD2}	voltage range	V _{SCD2} = V _{SRP} - V _{SRN} , PROTECTION_CONTROL[RSNS] = 0	-22.2		-100	IIIV
۸۱/	SCD2 detection threshold	V _{SCD2} = V _{SRP} – V _{SRN,} PROTECTION_CONTROL[RSNS] = 1		-22.2		mV
ΔV _{SCD2}	voltage program step	V _{SCD2} = V _{SRP} - V _{SRN,} PROTECTION_CONTROL[RSNS] = 0		-11.1		IIIV

7.24 Current Protection Timing

Typical values stated where T_A = 25°C and VCC = 7.2 V, Min/Max values stated where T_A = -40°C to 85°C and VCC = 2.2 V to 7.6 V (unless otherwise noted)

PARAME	ETER	TEST CONDITION	MIN	NOM	MAX	UNIT
t _{OCD}	OCD detection delay time		1		31	ms
Δt_{OCD}	OCD detection delay time program step			2		ms
t _{SCC}	SCC detection delay time		0		915	μs
Δt_{SCC}	SCC detection delay time program step			61		μs
	SCD1 detection delay	PROTECTION_CONTROL[SCDDx2] = 0	0		915	
t _{SCD1}	time	PROTECTION_CONTROL[SCDDx2] = 1	0		1850	μs
Δt _{SCD1}	SCD1 detection delay	PROTECTION_CONTROL[SCDDx2] = 0		61		
	time program step	PROTECTION_CONTROL[SCDDx2] = 1		121		μs

Typical values stated where T_A = 25°C and VCC = 7.2 V, Min/Max values stated where T_A = -40°C to 85°C and VCC = 2.2 V to 7.6 V (unless otherwise noted)

PARAMET	TER	TEST CONDITION	MIN	NOM	MAX	UNIT
Tecna	SCD2 detection delay time	PROTECTION_CONTROL[SCDDx2] = 0	0		458	II.C
		PROTECTION_CONTROL[SCDDx2] = 1	0		915	μs
Δt _{SCD2}	PROTECTION_CONTROL[SCDDx2] = 0		30.5		us	
	time program step	PROTECTION_CONTROL[SCDDx2] = 1		61		μδ
t _{DETECT}	Current fault detect time	$V_{SRP} - V_{SRN} = V_T - 3$ mV for OCD, SCD1, and SC2, $V_{SRP} - V_{SRN} = V_T + 3$ mV for SCC			160	μs
t _{ACC}	Current fault delay time accuracy	Max delay setting	-10%		10%	

7.25 N-CH FET Drive (CHG, DSG)

Typical values stated where $T_A = 25^{\circ}\text{C}$ and VCC = 7.2 V, Min/Max values stated where $T_A = -40^{\circ}\text{C}$ to 85°C and VCC = 2.2 V to 7.6 V (unless otherwise noted)

PARAMET	ER	TEST CONDITION	MIN	TYP	MAX	UNIT
	Output voltage ratio	Ratio DSG = $(V_{DSG} - V_{VC2})/V_{VC2}$, 2.2 V < V_{VC2} < 4.07 V, 10 M Ω between PACK and DSG	2.133	2.333	2.467	
	Output Voltage Fatio	Ratio _{CHG} = (V _{CHG} – V _{VC2})/V _{VC2} , 2.2 V < V _{VC2} < 4.07 V, 10 M Ω between BAT and CHG	2.133	2.333	2.467	_
V _(FETON)	Output voltage,	$V_{DSG(ON)}$ = V_{DSG} – V_{VC2} , 4.07 V ≤ V_{VC2} ≤ 18 V, 10 M Ω between PACK and DSG	8.75	9.5	10.25	V
	CHG and DSG on	$V_{CHG(ON)} = V_{CHG} - V_{VC2}$, 4.07 V \leq V _{VC2} \leq 18 V, 10 M Ω between VC2 and CHG	8.75	9.5	10.25	V
V _(FETOFF)	Output voltage, CHG and DSG off	$V_{DSG(OFF)}$ = V_{DSG} – V_{PACK} , 10 M Ω between PACK and DSG	-0.4		0.4	V
, ,		$V_{CHG(OFF)}$ = $V_{CHG} - V_{BAT}$, 10 M Ω between VC2 and CHG	-0.4		0.4	
•		V_{DSG} from 0% to 35% $V_{DSG~(ON)(TYP)}$, V_{BAT} ≥ 2.2 V, C_L = 4.7 nF between DSG and PACK, 5.1 kΩ between DSG and C_L , 10 MΩ between PACK and DSG		200	500	
t _R	Rise time	V_{CHG} from 0% to 35% $V_{CHG~(ON)(TYP)}$, V_{VC2} ≥ 2.2 V, C_L = 4.7 nF between CHG and VC2, 5.1 kΩ between CHG and C_L , 10 MΩ between VC2 and CHG		200	500	μs
t _F	Fall time	V_{DSG} from $V_{DSG(ON)(TYP)}$ to 1 V, V_{VC2} ≥ 2.2 V, C_L = 4.7 nF between DSG and PACK, 5.1 kΩ between DSG and C_L , 10 MΩ between PACK and DSG		40	300	lie.
	Fall time	V_{CHG} from $V_{CHG(ON)(TYP)}$ to 1 V, V_{VC2} ≥ 2.2 V, C_L = 4.7 nF between CHG and VC2, 5.1 kΩ between CHG and C_L , 10 MΩ between VC2 and CHG		40	200	μs

7.26 I²C Interface I/O

Typical values stated where $T_A = 25^{\circ}\text{C}$ and VCC = 7.2 V, Min/Max values stated where $T_A = -40^{\circ}\text{C}$ to 85°C and VCC = 2.2 V to 7.6 V (unless otherwise noted)

PARAMETER		TEST CONDITION	MIN	TYP	MAX	UNIT
V _{IH}	Input voltage high	SCL, SDA, V _{REG} = 1.8 V (STANDARD and FAST modes)	0.7 × V _{REG}			V
V _{IL}	Input voltage low	SCL, SDA, V _{REG} = 1.8 V (STANDARD and FAST modes)	-0.5		0.3 × V _{REG}	V
		SCL, SDA, V _{REG} = 1.8 V, I _{OL} = 1 mA (FAST mode)			0.2 × V _{REG}	V
V _{OL}	Output low voltage	SCL, SDA, V_{REG} > 2.0 V, I_{OL} = 1 mA (STANDARD and FAST modes)			0.4	V
C _{IN}	Input capacitance				10	pF
I _{LKG}	Input leakage current			1		μΑ



Typical values stated where T_A = 25°C and VCC = 7.2 V, Min/Max values stated where T_A = -40°C to 85°C and VCC = 2.2 V to 7.6 V (unless otherwise noted)

PARAME	TER	TEST CONDITION	MIN	TYP	MAX	UNIT
R _{PD}	Pull-down resistance			3.3		kΩ

7.27 I²C Interface Timing

Typical values stated where T_A = 25°C and VCC = 7.2 V, Min/Max values stated where T_A = -40°C to 85°C and VCC = 2.2 V to 7.6 V (unless otherwise noted)

F	ARAMETER	TEST CONDITION	MIN	NOM	MAX	UNIT
t _R	Clock rise time	10% to 90%			300	ns
t _F	Clock fall time	90% to 10%			300	ns
t _{HIGH}	Clock high period		600			ns
t _{LOW}	Clock low period		1.3			μs
t _{SU(START)}	Repeated start setup time		600			ns
t _{d(START)}	Start for first falling edge to SCL		600			ns
t _{SU(DATA)}	Data setup time		100			ns
t _{HD(DATA)}	Data hold time		0			μs
t _{SU(STOP)}	Stop setup time		600			ns
t _{BUF}	Bus free time between stop and start		1.3			μs
f _{SW}	Clock operating frequency	SLAVE mode, SCL 50% duty cycle			400	kHz





図 7-1. I²C Timing


Product Folder Links: BQ28Z610




7.28 Typical Characteristics











Threshold setting is -88.8 mV.

図 7-8. Short Circuit Charge Protection Threshold vs. Temperature

図 7-9. Short Circuit Discharge 1 Protection Threshold vs. Temperature







Threshold setting is -177.7 mV.

図 7-11. Overcurrent Delay Time vs. Temperature

図 7-10. Short Circuit Discharge 2 Protection Threshold vs. Temperature





Threshold setting is 465 μs (including internal delay).

図 7-12. Short Circuit Charge Current Delay Time vs. Temperature

図 7-13. Short Circuit Discharge 1 Delay Time vs. Temperature

Submit Document Feedback

Copyright © 2023 Texas Instruments Incorporated






図 7-14. V_{CELL} Measurement at 2.5-V vs. Temperature




This is the V_{CELL} average for single cell.

図 7-15. V_{CELL} Measurement at 3.5-V vs. Temperature



EZ 7.46 V Massurement at 4.4

図 7-16. V_{CELL} Measurement at 4.25-V vs. Temperature



 I_{SET} = 100 mA, RSNS= 1 Ω

図 7-17. I Measured vs. Temperature




8 Detailed Description

8.1 Overview

The BQ28Z610 gas gauge is a fully integrated battery manager that employs flash-based firmware and integrated hardware protection to provide a complete solution for battery-stack architectures composed of 1-series to 2-series cells. The BQ28Z610 device interfaces with a host system through an I^2C protocol. High-performance, integrated analog peripherals enable support for a sense resistor down to 1 m Ω and simultaneous current/voltage data conversion for instant power calculations. The following sections detail all of the major component blocks included as part of the BQ28Z610 device.

8.2 Functional Block Diagram

The Functional Block Diagram depicts the analog (AFE) and digital (AGG) peripheral content in the BQ28Z610 device.





8.3 Feature Description

8.3.1 Battery Parameter Measurements

The BQ28Z610 device measures cell voltage and current simultaneously, and also measures temperature to calculate the information related to remaining capacity, full charge capacity, state-of-health, and other gauging parameters.

8.3.1.1 BQ28Z610 Processor

The BQ28Z610 device uses a custom TI-proprietary processor design that features a Harvard architecture and operates at frequencies up to 4.2 MHz. Using an adaptive, three-stage instruction pipeline, the BQ28Z610 processor supports variable instruction length of 8, 16, or 24 bits.

8.3.2 Coulomb Counter (CC)

The first ADC is an integrating converter designed specifically for coulomb counting. The converter resolution is a function of its full-scale range and number of bits, yielding a 3.74-µV resolution.

8.3.3 CC Digital Filter

The CC digital filter generates a 16-bit conversion value from the delta-sigma CC front-end. Its FIR filter uses the LFO clock output, which allows it to stop the HFO clock during conversions. New conversions are available every 250 ms while CCTL[CC_ON] = 1. Proper use of this peripheral requires turning on the CC modulator in the AFE.

8.3.4 ADC Multiplexer

The ADC multiplexer provides selectable connections to the VCx inputs, TS1 inputs, internal temperature sensor, internal reference voltages, internal 1.8-V regulator, PACK input, and VSS ground reference input. In addition, the multiplexer can independently enable the TS1 input connection to the internal thermistor biasing circuitry, and also enables the user to short the multiplexer inputs for test and calibration purposes.

8.3.5 Analog-to-Digital Converter (ADC)

The second ADC is a 16-bit delta-sigma converter designed for general-purpose measurements. The ADC automatically scales the input voltage range during sampling based on channel selection. The converter resolution is a function of its full-scale range and number of bits, yielding a 38-µV resolution. The default conversion time of the ADC is 31.25 ms, but is user-configurable down to 1.95 ms. Decreasing the conversion time presents a tradeoff between conversion speed and accuracy, as the resolution decreases for faster conversion times.

8.3.6 ADC Digital Filter

The ADC digital filter generates a 24-bit conversion result from the delta-sigma ADC front end. Its FIR filter uses the LFO clock, which allows it to stop the HFO clock during conversions. The ADC digital filter is capable of providing two 24-bit results: one result from the delta-sigma ADC front-end and a second synchronous result from the delta-sigma CC front-end.

8.3.7 Internal Temperature Sensor

An internal temperature sensor is available on the BQ28Z610 device to reduce the cost, power, and size of the external components necessary to measure temperature. It is available for connection to the ADC using the multiplexer, and is ideal for quickly determining pack temperature under a variety of operating conditions.

8.3.8 External Temperature Sensor Support

The TS1 input is enabled with an internal $18-k\Omega$ (Typ.) linearization pullup resistor to support using a $10-k\Omega$ (25°C) NTC external thermistor, such as the Semitec 103AT-2. The NTC thermistor should be connected between VSS and the individual TS1 pin. The ADC, through its input multiplexer, then takes the analog measurement. If a different thermistor type is required, changes to configurations may be required.

Product Folder Links: BQ28Z610






図 8-1. External Thermistor Biasing

8.3.9 Power Supply Control

The BQ28Z610 device manages its supply voltage dynamically according to operating conditions. When $V_{VC2} > V_{SWITCHOVER-} + V_{HYS}$, the AFE connects an internal switch to BAT and uses this pin to supply power to its internal 1.8-V LDO, which subsequently powers all device logic and flash operations. Once VC2 decreases to $V_{VC2} < V_{SWITCHOVER-}$, the AFE disconnects its internal switch from VC2 and connects another switch to PACK, allowing sourcing of power from a charger (if present). An external capacitor connected to PBI provides a momentary supply voltage to help guard against system brownouts due to transient short-circuit or overload events that pull VC2 below $V_{SWITCHOVER-}$.

8.3.10 Power-On Reset

In the event of a power-cycle, the BQ28Z610 AFE holds its internal RESET output pin high for t_{RST} duration to allow its internal 1.8-V LDO and LFO to stabilize before running the AGG. The AFE enters power-on reset when the voltage at V_{REG} falls below V_{REGIT-} and exits reset when V_{REG} rises above $V_{REGIT-} + V_{HYS}$ for t_{RST} time. After t_{RST} , the BQ28Z610 AGG will write its trim values to the AFE.




図 8-2. POR Timing Diagram

8.3.11 Bus Communication Interface

The BQ28Z610 device has an I^2C bus communication interface. This device has the option to broadcast information to a smart charger to provide key information to adjust the charging current and charging voltage based on the temperature or individual cell voltages.

Submit Document Feedback

Copyright © 2023 Texas Instruments Incorporated



注意

If the device is configured as a single-master architecture (an application processor) and an occasional NACK is detected in the operation, the master can resend the transaction. However, in a multi-master architecture, an incorrect ACK leading to accidental loss of bus arbitration can cause a master to wait incorrectly for another master to clear the bus. If this master does not get a bus-free signal, then it must have in place a method to look for the bus and assume it is free after some period of time. Also, if possible, set the clock speed to be 100 kHz or less to significantly reduce the issue described above for multi-mode operation.

8.3.12 Cell Balancing Support

The integrated cell balancing FETs included in the BQ28Z610 device enable the AFE to bypass cell current around a given cell or numerous cells to effectively balance the entire battery stack. External series resistors placed between the cell connections and the VCx input pins set the balancing current magnitude. The cell balancing circuitry can be enabled or disabled through the *CELL_BAL_DET[CB2, CB1]* control register. Series input resistors between 100 Ω and 1 k Ω are recommended for effective cell balancing.




図 8-3. Internal Cell Balancing

8.3.13 N-Channel Protection FET Drive

The BQ28Z610 device controls two external N-Channel MOSFETs in a back-to-back configuration for battery protection. The charge (CHG) and discharge (DSG) FETs are automatically disabled if a safety fault (AOLD, ASSC, ASCD, SOV) is detected, and can also be manually turned off using **AFE_CONTROL[CHGEN, DSGEN]** = 0, 0. When the gate drive is disabled, an internal circuit discharges CHG to VC2 and DSG to PACK.

8.3.14 Low Frequency Oscillator

The BQ28Z610 AFE includes a low frequency oscillator (LFO) running at 262.144 kHz. The AFE monitors the LFO frequency and indicates a failure through *LATCH_STATUS[LFO]* if the output frequency is much lower than normal.

8.3.15 High Frequency Oscillator

The BQ28Z610 AGG includes a high frequency oscillator (HFO) running at 16.78 MHz. It is synthesized from the LFO output and scaled down to 8.388 MHz with 50% duty cycle.

8.3.16 1.8-V Low Dropout Regulator

The BQ28Z610 AFE contains an integrated 1.8-V LDO that provides regulated supply voltage for the device CPU and internal digital logic.

Product Folder Links: BQ28Z610



8.3.17 Internal Voltage References

The BQ28Z610 AFE provides two internal voltage references with V_{REF1}, used by the ADC and CC, while V_{REF2} is used by the LDO, LFO, current wake comparator, and OCD/SCC/SCD1/SCD2 current protection circuitry.

8.3.18 Overcurrent in Discharge Protection

The overcurrent in discharge (OCD) function detects abnormally high current in the discharge direction. The overload in discharge threshold and delay time are configurable through the OCD CONTROL register. The thresholds and timing can be fine-tuned even further, based on a sense resistor with lower resistance or wider tolerance through the PROTECTION CONTROL register. The detection circuit also incorporates a filtered delay before disabling the CHG and DSG FETs. When an OCD event occurs, the LATCH STATUS[OCD] bit is set to 1 and is latched until it is cleared and the fault condition has been removed.

8.3.19 Short-Circuit Current in Charge Protection

The short-circuit current in charge (SCC) function detects catastrophic current conditions in the charge direction. The short-circuit in charge threshold and delay time are configurable through the SCC CONTROL register. The thresholds and timing can be fine-tuned even further based on a sense resistor with lower resistance or wider tolerance through the PROTECTION CONTROL register. The detection circuit also incorporates a blanking delay before disabling the CHG and DSG FETs. When an SCC event occurs, the LATCH STATUS[SCC] bit is set to 1 and is latched until it is cleared and the fault condition has been removed.

8.3.20 Short-Circuit Current in Discharge 1 and 2 Protection

The short-circuit current in discharge (SCD) function detects catastrophic current conditions in the discharge direction. The short-circuit in discharge thresholds and delay times are configurable through the SCD1 CONTROL and SCD2 CONTROL registers. The thresholds and timing can be fine-tuned even further, based on a sense resistor with lower resistance or wider tolerance through the PROTECTION CONTROL register. The detection circuit also incorporates a blanking delay before disabling the CHG and DSG FETs. When an SCD event occurs, the LATCH STATUS[SCD1] or LATCH STATUS[SCD2] bit is set to 1 and is latched until it is cleared and the fault condition has been removed.

8.3.21 Primary Protection Features

The BQ28Z610 gas gauge supports the following battery and system level protection features, which can be configured using firmware:

- Cell Undervoltage Protection
- Cell Overvoltage Protection
- Overcurrent in CHARGE Mode Protection
- Overcurrent in DISCHARGE Mode Protection
- Overload in DISCHARGE Mode Protection
- Short Circuit in CHARGE Mode Protection
- Overtemperature in CHARGE Mode Protection
- Overtemperature in DISCHARGE Mode Protection
- **Precharge Timeout Protection**
- **Fast Charge Timeout Protection**

8.3.22 Gas Gauging

This device uses the Impedance Track™ technology to measure and determine the available charge in battery cells. The accuracy achieved using this method is better than 1% error over the lifetime of the battery. There is no full charge/discharge learning cycle required. See the Theory and Implementation of Impedance Track Battery Fuel-Gauging Algorithm Application Report (SLUA364B) for further details.

Product Folder Links: BQ28Z610

Copyright © 2023 Texas Instruments Incorporated

8.3.23 Charge Control Features

This device supports charge control features, such as:

- Reports charging voltage and charging current based on the active temperature range—JEITA temperature ranges T1, T2, T3, T4, T5, and T6
- Provides more complex charging profiles, including sub-ranges within a standard temperature range
- Reports the appropriate charging current required for constant current charging and the appropriate charging voltage needed for constant voltage charging to a smart charger, using the bus communication interface
- Selects the chemical state-of-charge of each battery cell using the Impedance Track method, and reduces the voltage difference between cells when cell balancing multiple cells in a series
- Provides pre-charging/zero-volt charging
- · Employs charge inhibit and charge suspend if battery pack temperature is out of programmed range
- Reports charging faults and indicates charge status from charge and discharge alarms

8.3.24 Authentication

This device supports security by:

- · Authentication by the host using the SHA-1 method
- The gas gauge requires SHA-1 authentication before the device can be unsealed or allow full access.

8.4 Device Functional Modes

This device supports three modes, but the current consumption varies, based on firmware control of certain functions and modes of operation:

- NORMAL mode: In this mode, the device performs measurements, calculations, protections, and data
 updates every 250-ms intervals. Between these intervals, the device is operating in a reduced power stage to
 minimize total average current consumption.
- SLEEP mode: In this mode, the device performs measurements, calculations, protections, and data updates in adjustable time intervals. Between these intervals, the device is operating in a reduced power stage to minimize total average current consumption.
- SHUTDOWN mode: The device is completely disabled.

8.4.1 Lifetime Logging Features

The device supports data logging of several key parameters for warranty and analysis:

- Maximum and Minimum Cell Temperature
- Maximum Current in CHARGE or DISCHARGE Mode
- · Maximum and Minimum Cell Voltages

8.4.2 Configuration

The device supports accurate data measurements and data logging of several key parameters.

8.4.2.1 Coulomb Counting

The device uses an integrating delta-sigma analog-to-digital converter (ADC) for current measurement. The ADC measures charge/discharge flow of the battery by measuring the voltage across a very small external sense resistor. The integrating ADC measures a bipolar signal from a range of -100 mV to 100 mV, with a positive value when $V_{(SRP)} - V_{(SRN)}$, indicating charge current and a negative value indicating discharge current. The integration method uses a continuous timer and internal counter, which has a rate of 0.65 nVh.

8.4.2.2 Cell Voltage Measurements

The BQ28Z610 measures the individual cell voltages at 250-ms intervals using an ADC. This measured value is internally scaled for the ADC and is calibrated to reduce any errors due to offsets. This data is also used for calculating the impedance of the individual cell for Impedance Track gas gauging.



8.4.2.3 Current Measurements

The current measurement is performed by measuring the voltage drop across the external sense resistor (1 m Ω to 3 m Ω) and the polarity of the differential voltage determines if the cell is in the CHARGE or DISCHARGE mode.

8.4.2.4 Auto Calibration

The auto-calibration feature helps to cancel any voltage offset across the SRP and SRN pins for accurate measurement of the cell voltage, charge/discharge current, and thermistor temperature. The auto-calibration is performed when there is no communication activity for a minimum of 5 s on the bus lines.

8.4.2.5 Temperature Measurements

This device has an internal sensor for on-die temperature measurements, and supports external temperature measurements through the external NTC on the TS1 pin. These two measurements are individually enabled and configured.

Submit Document Feedback

Copyright © 2023 Texas Instruments Incorporated



9 Applications and Implementation

注


以下のアプリケーション情報は、TIの製品仕様に含まれるものではなく、TIではその正確性または完全性を保証いたしません。個々の目的に対する製品の適合性については、お客様の責任で判断していただくことになります。お客様は自身の設計実装を検証しテストすることで、システムの機能を確認する必要があります。

9.1 Application Information

The BQ28Z610 gas gauge is a primary protection device that can be used with a 1-series to 2-series Li-ion/Li polymer battery pack. To implement and design a comprehensive set of parameters for a specific battery pack, the user needs Battery Management Studio (BQSTUDIO), which is a graphical user-interface tool installed on a PC during development. The firmware installed in the product has default values, which are summarized in the BQ28Z610 Technical Reference Manual (SLUUA65) for this product. Using the BQSTUDIO tool, these default values can be changed to cater to specific application requirements during development once the system parameters, such as fault trigger thresholds for protection, enable/disable of certain features for operation, configuration of cells, chemistry that best matches the cell used, and more are known. This data can be referred to as the "golden image."

9.2 Typical Applications

☑ 9-1 shows the BQ28Z610 application schematic for the 2-series configuration. ☑ 9-2 shows a wireless (Bluetooth) speaker application block diagram.



Note: The input filter capacitors of 0.1 μF for the SRN and SRP pins must be located near the pins of the device.

図 9-1. BQ28Z610 2-Series Cell Typical Implementation






図 9-2. Wireless (Bluetooth) Speaker Application Block Diagram

9.2.1 Design Requirements (Default)

Design Parameter	Example
Cell Configuration	2s1p (2-series with 1 Parallel)
Design Capacity	4400 mAh
Device Chemistry	100 (LiCoO ₂ /graphitized carbon)
Cell Overvoltage at Standard Temperature	4300 mV
Cell Undervoltage	2500 mV
Shutdown Voltage	2300 mV
Overcurrent in CHARGE Mode	6000 mA
Overcurrent in DISCHARGE Mode	–6000 mA
Short Circuit in CHARGE Mode	0.1 V/Rsense across SRP, SRN
Short Circuit in DISCHARGE 1 Mode	-0.1 V/Rsense across SRP, SRN
Safety Over Voltage	4500 mV
Cell Balancing	Disabled
Internal and External Temperature Sensor	Enabled
Under Temperature Charging	0°C
Under Temperature Discharging	0°C
BROADCAST Mode	Enabled

9.2.2 Detailed Design Procedure

9.2.2.1 Setting Design Parameters

For the firmware settings needed for the design requirements, refer to the *BQ28Z610 Technical Reference Manual* (SLUUA65).

- To set the 2s1p battery pack, go to data flash *Configuration: DA Configuration* register's bit 0 (CC0) = 1.
- To set design capacity, set the data flash value to 4400 in the Gas Gauging: Design: Design Capacity
 register.
- To set device chemistry, go to data flash SBS Configuration: Data: Device Chemistry. The BQSTUDIO software automatically populates the correct chemistry identification. This selection is derived from using the BQCHEM feature in the tools and choosing the option that matches the device chemistry from the list.
- To protect against cell overvoltage, set the data flash value to 4300 in *Protections: COV: Standard Temp*.
- To protect against cell undervoltage, set the data flash value to 2500 in the Protections: CUV register.

Submit Document Feedback

Copyright © 2023 Texas Instruments Incorporated

- To set the shutdown voltage to prevent further pack depletion due to low pack voltage, program Power:
 Shutdown: Shutdown voltage = 2300.
- To protect against large charging currents when the AC adapter is attached, set the data flash value to 6000 in the *Protections: OCC: Threshold* register.
- To protect against large discharging currents when heavy loads are attached, set the data flash value to 6000 in the *Protections: OCD: Threshold* register.
- Program a short circuit delay timer and threshold setting to enable the operating the system for large short transient current pulses. These two parameters are under *Protections: ASCC: Threshold* = 100 for charging current. The discharge current setting is *Protections: ASCD:Threshold* = -100 mV.
- To prevent the cells from overcharging and adding a second level of safety, there is a register setting that will shut down the device if any of the cells voltage measurement is greater than the Safety Over Voltage setting for greater than the delay time. Set this data flash value to 4500 in **Permanent Fail: SOV: Threshold**.
- To disable the cell balancing feature, set the data flash value to 0 in **Settings: Configuration: Balancing Configuration**: bit 0 (CB).
- To enable the internal temperature and the external temperature sensors: Set **Settings:Configuration: Temperature Enable**: Bit 0 (TSInt) = 1 for the internal sensor; set Bit 1 (TS1) = 1 for the external sensor.
- To prevent charging of the battery pack if the temperature falls below 0°C, set **Protections: UTC:Threshold** = 0.
- To prevent discharging of the battery pack if the temperature falls below 0°C, set *Protections: UTD:Threshold* = 0.
- To provide required information to the smart chargers, the gas gauge must operate in BROADCAST mode. To enable this, set the [BCAST] bit in *Configuration: SBS Configuration* 2: Bit 0 [BCAST] = 1.

Each parameter listed for fault trigger thresholds has a delay timer setting associated for any noise filtering. These values, along with the trigger thresholds for fault detection, may be changed based upon the application requirements using the data flash settings in the appropriate register stated in the *BQ28Z610 Technical Reference Manual* (SLUUA65).

9.2.3 Calibration Process

The calibration of current, voltage, and temperature readings is accessible by writing 0xF081 or 0xF082 to *ManufacturerAccess()*. A detailed procedure is included in the *BQ28Z610 Technical Reference Manual* (SLUUA65) in the *Calibration* section. The description allows for calibration of Cell Voltage Measurement Offset, Battery Voltage, Pack Voltage, Current Calibration, Coulomb Counter Offset, PCB Offset, CC Gain/Capacity Gain, and Temperature Measurement for both internal and external sensors.

9.2.4 Gauging Data Updates

When a battery pack enabled with the BQ28Z610 is first cycled, the value of FullChargeCapacity() updates several times. \boxtimes 9-3 shows RemainingCapacity() and FullChargeCapacity(), and where those updates occur. As part of the Impedance Track algorithm, it is expected that FullChargeCapacity() may update at the end of charge, at the end of discharge, and at rest.

9.2.4.1 Application Curve




図 9-3. Elapsed Time(s)

Power Supply Requirements


There are two inputs for this device, the PACK input and VC2. The PACK input can be an unregulated input from a typical AC adapter. This input should always be greater than the maximum voltage associated with the number of series cells configured. The input voltage for the VC2 pin will have a minimum of 2.2 V to a maximum of 26 V with the recommended external RC filter.



10 Layout

10.1 Layout Guidelines

- The layout for the high-current path begins at the PACK+ pin of the battery pack. As charge current travels through the pack, it finds its way through protection FETs, a chemical fuse, the Li-ion cells and cell connections, and the sense resistor, and then returns to the PACK- pin. In addition, some components are placed across the PACK+ and PACK- pins to reduce effects from electrostatic discharge.
- The N-channel charge and discharge FETs must be selected for a given application. Most portable battery applications are a good option for the CSD16412Q5A. These FETs are rated at 14-A, 25-V device with Rds(on) of 11 mΩ when the gate drive voltage is 10 V. The gates of all protection FETs are pulled to the source with a high-value resistor between the gate and source to ensure they are turned off if the gate drive is open. The capacitors (both 0.1 μF values) placed across the FETs are to help protect the FETs during an ESD event. The use of two devices ensures normal operation if one of them becomes shorted. For effective ESD protection, the copper trace inductance of the capacitor leads must be designed to be as short and wide as possible. Ensure that the voltage rating of both these capacitors is adequate to hold off the applied voltage if one of the capacitors becomes shorted.
- The quality of the Kelvin connections at the sense resistor is critical. The sense resistor must have a
 temperature coefficient no greater than 50 ppm in order to minimize current measurement drift with
 temperature. Choose the value of the sense resistor to correspond to the available overcurrent and shortcircuit ranges of the BQ28Z610. Select the smallest value possible in order to minimize the negative voltage
 generated on the BQ28Z610 VSS node(s) during a short circuit. This pin has an absolute minimum of –0.3 V.
 Parallel resistors can be used as long as good Kelvin sensing is ensured. The device is designed to support a
 1-mΩ to 3-mΩ sense resistor.
- A pair of series 0.1-µF ceramic capacitors is placed across the PACK+ and PACK- pins to help in the mitigation of external electrostatic discharges. The two devices in series ensure continued operation of the pack if one of the capacitors becomes shorted. Optionally, a transorb such as the SMBJ2A can be placed across the pins to further improve ESD immunity.
- In reference to the gas gauge circuit the following features require attention for component placement and layout: Differential Low-Pass Filter, I²C communication, and PBI (Power Backup Input).
- The BQ28Z610 uses an integrating delta-sigma ADC for current measurements. Add a 100-Ω resistor from
 the sense resistor to the SRP and SRN inputs of the device. Place a 0.1-μF filter capacitor across the SRP
 and SRN inputs. Optional 0.1-μF filter capacitors can be added for additional noise filtering for each sense
 input pin to ground, if required for your circuit. Place all filter components as close as possible to the device.
 Route the traces from the sense resistor in parallel to the filter circuit. Adding a ground plane around the filter
 network can add additional noise immunity.







図 10-1. BQ28Z610 Differential Filter

• The BQ28Z610 has an internal LDO that is internally compensated and does not require an external decoupling capacitor. The PBI pin is used as a power supply backup input pin, providing power during brief transient power outages. A standard 2.2-µF ceramic capacitor is connected from the PBI pin to ground, as shown in application example.



• The I²C clock and data pins have integrated high-voltage ESD protection circuits; however, adding a Zener diode and series resistor provides more robust ESD performance. The I²C clock and data lines have an internal pull-down. When the gas gauge senses that both lines are low (such as during removal of the pack), the device performs auto-offset calibration and then goes into SLEEP mode to conserve power.

10.2 Layout Example



Via connects between two layers

図 10-2. BQ28Z610 Board Layout

Submit Document Feedback

Copyright © 2023 Texas Instruments Incorporated



11 Device and Documentation Support

11.1 サード・パーティ製品に関する免責事項

サード・パーティ製品またはサービスに関するテキサス・インスツルメンツの出版物は、単独またはテキサス・インスツルメンツの製品、サービスと一緒に提供される場合に関係なく、サード・パーティ製品またはサービスの適合性に関する是認、サード・パーティ製品またはサービスの是認の表明を意味するものではありません。

11.2 Documentation Support

- BQ28Z610 Technical Reference Manual (SLUUA65)
- Theory and Implementation of Impedance Track Battery Fuel-Gauging Algorithm Application Report (SLUA364B)

11.3 ドキュメントの更新通知を受け取る方法

ドキュメントの更新についての通知を受け取るには、ti.com のデバイス製品フォルダを開いてください。「更新の通知を受け取る」をクリックして登録すると、変更されたすべての製品情報に関するダイジェストを毎週受け取れます。変更の詳細については、修正されたドキュメントに含まれている改訂履歴をご覧ください。

11.4 静電気放電に関する注意事項



この IC は、ESD によって破損する可能性があります。テキサス・インスツルメンツは、IC を取り扱う際には常に適切な注意を払うことを推奨します。正しい取り扱いおよび設置手順に従わない場合、デバイスを破損するおそれがあります。

ESD による破損は、わずかな性能低下からデバイスの完全な故障まで多岐にわたります。精密な IC の場合、パラメータがわずかに変化するだけで公表されている仕様から外れる可能性があるため、破損が発生しやすくなっています。

11.5 サポート・リソース

TI E2E™ サポート・フォーラムは、エンジニアが検証済みの回答と設計に関するヒントをエキスパートから迅速かつ直接得ることができる場所です。既存の回答を検索したり、独自の質問をしたりすることで、設計で必要な支援を迅速に得ることができます。

リンクされているコンテンツは、該当する貢献者により、現状のまま提供されるものです。これらは TI の仕様を構成するものではなく、必ずしも TI の見解を反映したものではありません。TI の使用条件を参照してください。

11.6 Trademarks

Impedance Track[™] and TI E2E[™] are trademarks of Texas Instruments.

Windows® is a registered trademark of Microsoft.

すべての商標は、それぞれの所有者に帰属します。

11.7 用語集

テキサス・インスツルメンツ用語集 この用語集には、用語や略語の一覧および定義が記載されています。

Mechanical, Packaging, and Orderable Information

The following pages include mechanical, packaging, and orderable information. This information is the most current data available for the designated devices. This data is subject to change without notice and revision of this document. For browser-based versions of this data sheet, refer to the left-hand navigation.

www.ti.com 3-Jun-2021

PACKAGING INFORMATION

Orderable Device	Status	Package Type	Package Drawing	Pins	Package Qty	Eco Plan	Lead finish/ Ball material	MSL Peak Temp	Op Temp (°C)	Device Marking (4/5)	Samples
BQ28Z610DRZR	ACTIVE	SON	DRZ	12	3000	RoHS & Green	NIPDAU	Level-2-260C-1 YEAR	-40 to 85	BQ28 Z610	Samples
BQ28Z610DRZT	ACTIVE	SON	DRZ	12	250	RoHS & Green	NIPDAU	Level-2-260C-1 YEAR	-40 to 85	BQ28 Z610	Samples

(1) The marketing status values are defined as follows:

ACTIVE: Product device recommended for new designs.

LIFEBUY: TI has announced that the device will be discontinued, and a lifetime-buy period is in effect.

NRND: Not recommended for new designs. Device is in production to support existing customers, but TI does not recommend using this part in a new design.

PREVIEW: Device has been announced but is not in production. Samples may or may not be available.

OBSOLETE: TI has discontinued the production of the device.

(2) RoHS: TI defines "RoHS" to mean semiconductor products that are compliant with the current EU RoHS requirements for all 10 RoHS substances, including the requirement that RoHS substance do not exceed 0.1% by weight in homogeneous materials. Where designed to be soldered at high temperatures, "RoHS" products are suitable for use in specified lead-free processes. TI may reference these types of products as "Pb-Free".

RoHS Exempt: TI defines "RoHS Exempt" to mean products that contain lead but are compliant with EU RoHS pursuant to a specific EU RoHS exemption.

Green: TI defines "Green" to mean the content of Chlorine (CI) and Bromine (Br) based flame retardants meet JS709B low halogen requirements of <=1000ppm threshold. Antimony trioxide based flame retardants must also meet the <=1000ppm threshold requirement.

- (3) MSL, Peak Temp. The Moisture Sensitivity Level rating according to the JEDEC industry standard classifications, and peak solder temperature.
- (4) There may be additional marking, which relates to the logo, the lot trace code information, or the environmental category on the device.
- (5) Multiple Device Markings will be inside parentheses. Only one Device Marking contained in parentheses and separated by a "~" will appear on a device. If a line is indented then it is a continuation of the previous line and the two combined represent the entire Device Marking for that device.
- (6) Lead finish/Ball material Orderable Devices may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead finish/Ball material values may wrap to two lines if the finish value exceeds the maximum column width.

Important Information and Disclaimer: The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.



PACKAGE OPTION ADDENDUM


www.ti.com 3-Jun-2021

PACKAGE MATERIALS INFORMATION

www.ti.com 20-Apr-2023

TAPE AND REEL INFORMATION





A0	Dimension designed to accommodate the component width
В0	Dimension designed to accommodate the component length
K0	Dimension designed to accommodate the component thickness
W	Overall width of the carrier tape
P1	Pitch between successive cavity centers


QUADRANT ASSIGNMENTS FOR PIN 1 ORIENTATION IN TAPE



*All dimensions are nominal

Device	Package Type	Package Drawing		SPQ	Reel Diameter (mm)	Reel Width W1 (mm)	A0 (mm)	B0 (mm)	K0 (mm)	P1 (mm)	W (mm)	Pin1 Quadrant
BQ28Z610DRZR	SON	DRZ	12	3000	330.0	12.4	2.8	4.3	1.2	4.0	12.0	Q2
BQ28Z610DRZT	SON	DRZ	12	250	180.0	12.4	2.8	4.3	1.2	4.0	12.0	Q2

www.ti.com 20-Apr-2023




*All dimensions are nominal

Device	Package Type	Package Drawing	Pins SPQ		Length (mm)	Width (mm)	Height (mm)	
BQ28Z610DRZR	SON	DRZ	12	3000	552.0	346.0	36.0	
BQ28Z610DRZT	SON	DRZ	12	250	552.0	185.0	36.0	

PACKAGE MATERIALS INFORMATION

www.ti.com 20-Apr-2023


TUBE



*All dimensions are nominal

Device	Package Name	Package Type Pins		SPQ	L (mm)	W (mm)	T (µm)	B (mm)
BQ28Z610DRZR	DRZ	VSON	12	3000	381.51	4.22	2286	0
BQ28Z610DRZT	DRZ	VSON	12	250	381.51	4.22	2286	0

PLASTIC QUAD FLATPACK- NO LEAD




NOTES:

- All linear dimensions are in millimeters. Any dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.
- 2. This drawing is subject to change without notice.
- 3. The package thermal pad must be soldered to the printed circuit board for optimal thermal and mechanical performance.



PLASTIC QUAD FLATPACK- NO LEAD




NOTES: (continued)

- This package is designed to be soldered to a thermal pad on the board. For more information, see Texas Instruments literature number SLUA271 (www.ti.com/lit/slua271).
- Vias are optional depending on application, refer to device data sheet. If any vias are implemented, refer to their locations shown on this view. It is recommended that vias under paste be filled, plugged or tented.



PLASTIC QUAD FLATPACK- NO LEAD



NOTES: (continued)

6. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.



重要なお知らせと免責事項

TI は、技術データと信頼性データ (データシートを含みます)、設計リソース (リファレンス・デザインを含みます)、アプリケーションや設計に関する各種アドバイス、Web ツール、安全性情報、その他のリソースを、欠陥が存在する可能性のある「現状のまま」提供しており、商品性および特定目的に対する適合性の黙示保証、第三者の知的財産権の非侵害保証を含むいかなる保証も、明示的または黙示的にかかわらず拒否します。

これらのリソースは、TI 製品を使用する設計の経験を積んだ開発者への提供を意図したものです。(1) お客様のアプリケーションに適した TI 製品の選定、(2) お客様のアプリケーションの設計、検証、試験、(3) お客様のアプリケーションに該当する各種規格や、その他のあらゆる安全性、セキュリティ、規制、または他の要件への確実な適合に関する責任を、お客様のみが単独で負うものとします。

上記の各種リソースは、予告なく変更される可能性があります。これらのリソースは、リソースで説明されている TI 製品を使用するアプリケーションの開発の目的でのみ、TI はその使用をお客様に許諾します。これらのリソースに関して、他の目的で複製することや掲載することは禁止されています。TI や第三者の知的財産権のライセンスが付与されている訳ではありません。お客様は、これらのリソースを自身で使用した結果発生するあらゆる申し立て、損害、費用、損失、責任について、TI およびその代理人を完全に補償するものとし、TI は一切の責任を拒否します。

TI の製品は、TI の販売条件、または ti.com やかかる TI 製品の関連資料などのいずれかを通じて提供する適用可能な条項の下で提供されています。TI がこれらのリソースを提供することは、適用される TI の保証または他の保証の放棄の拡大や変更を意味するものではありません。

お客様がいかなる追加条項または代替条項を提案した場合でも、TIはそれらに異議を唱え、拒否します。

郵送先住所:Texas Instruments, Post Office Box 655303, Dallas, Texas 75265 Copyright © 2023, Texas Instruments Incorporated