www.ti.com

SN75185 MULTIPLE RS-232 DRIVERS AND RECEIVERS

SLLS181D-DECEMBER 1994-REVISED JANUARY 2006

FEATURES


- Single Chip With Easy Interface Between UART and Serial-Port Connector of IBM™ PC/AT™ and Compatibles
- Meets or Exceeds the Requirements of TIA/EIA-232-F and ITU v.28 Standards
- Supports Data Rates up to 120 kbit/s
- ESD Protection Meets or Exceeds 10 kV on RS-232 Pins and 3.5 kV on All Other Pins (Human-Body Model)
- Pin-to-Pin Compatible With the SN75C185

DESCRIPTION/ORDERING INFORMATION


The SN75185 combines three drivers and five receivers from the TI SN75188 and SN75189 bipolar quadruple drivers and receivers, respectively. The pinout matches the flow-through design of the SN75C185 to decrease the part count, reduce the board space required, and allow easy interconnection of the UART and serial-port connector of IBM™ PC/AT™ and compatibles. The bipolar circuits and processing of the SN75185 provide a rugged low-cost solution for this function at the expense of quiescent power and external passive components relative to the SN75C185.

The SN75185 complies with the requirements of the TIA/EIA-232-F and ITU v.28 standards. These standards are for data interchange between a host computer and peripheral at signaling rates up to 20 kbit/s. The switching speeds of the SN75185 are fast enough to support rates up to 120 kbit/s with lower capacitive loads (shorter cables). Interoperability at the higher signaling rates cannot be assured unless the designer has design control of the cable and the interface circuits at both ends. For interoperability at signaling rates to 120 kbit/s, use of TIA/EIA-423-B (ITU v.10) and TIA/EIA-422-B (ITU v.11) standards is recommended.

The SN75185 is characterized for operation over the temperature range of 0°C to 70°C.



DB, DW, OR PW PACKAGE (TOP VIEW)





Please be aware that an important notice concerning availability, standard warranty, and use in critical applications of Texas Instruments semiconductor products and disclaimers thereto appears at the end of this data sheet.

IBM, PC/AT are trademarks of IBM Corporation.

SN75185 MULTIPLE RS-232 DRIVERS AND RECEIVERS






ORDERING INFORMATION

T _A	P/	ACKAGE ⁽¹⁾	ORDERABLE PART NUMBER	TOP-SIDE MARKING
	PDIP – N	Tube of 20	SN75185N	SN75185N
	SOIC – DW	Tube of 25	SN75185DW	CNIZE10E
	SOIC - DW	Reel of 2000	SN75185DWR	SN75185
0°C to 70°C	SSOP – DB	Tube of 70	SN75185DB	A185
	330P – DB	Reel of 2000	SN75185DBR	A185
	TSSOP – PW	Tube of 70	SN75185PW	A105
	1350P – PW	Reel of 2000	SN75185PWR	A185


⁽¹⁾ Package drawings, standard packing quantities, thermal data, symbolization, and PCB design guidelines are available at www.ti.com/sc/package.

LOGIC DIAGRAM (POSITIVE LOGIC)






SCHEMATIC OF DRIVERS



Resistor values shown are nominal.

SCHEMATIC (EACH RECEIVER)



Resistor values shown are nominal.

SN75185 **MULTIPLE RS-232 DRIVERS AND RECEIVERS**

SLLS181D-DECEMBER 1994-REVISED JANUARY 2006



Absolute Maximum Ratings(1)

over operating free-air temperature range (unless otherwise noted)

				MIN	MAX	UNIT
V _{CC}	Supply voltage (2)				10	V
V_{DD}	Supply voltage ⁽²⁾				15	V
V _{SS}	Supply voltage ⁽²⁾		-15	V		
	lanut voltage range	Driver		-15	7	V
	Input voltage range	Receiver				V
	Driver output voltage range	,				
	Receiver low-level output current				20	mA
		DB package			70	
Δ	Package thermal impedance (3) (4)	DW package			58	°C/W
θ_{JA}	Fackage mermai impedance (-//-/-/-/-/-/-/-/-/-/-/	N package			69	C/VV
		PW package			83	
TJ	Operating virtual junction temperature				150	°C
		Human-Body Model	RS-232 pins, class 3, A ⁽⁵⁾		10	kV
	Electrostatio discharge	Human-Body Wodel	All pins, class 3, A (6)		3.5	ĸv
	Electrostatic discharge	Maskins Madel	RS-232 pins, class 3, B ⁽⁷⁾		600	V
		Machine Model	All pins, class 3, B ⁽⁵⁾		250	V
T _{stg}	Storage temperature range	-65	150	°C		

⁽¹⁾ Stresses beyond those listed under "absolute maximum ratings" may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated under "recommended operating conditions" is not implied. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability.

All voltages are with respect to the network ground terminal.

RS-232 pins are tested with respect to ground and to each other.

Per MIL-PRF-38535

RS-232 pins are tested with respect to ground.

Maximum power dissipation is a function of $T_J(max)$, θ_{JA} , and T_A . The maximum allowable power dissipation at any allowable ambient temperature is $P_D = (T_J(max) - T_A)/\theta_{JA}$. Operating at the absolute maximum T_J of 150°C can affect reliability. The package thermal impedance is calculated in accordance with JESD 51-7.



SN75185 MULTIPLE RS-232 DRIVERS AND RECEIVERS

SLLS181D-DECEMBER 1994-REVISED JANUARY 2006

Recommended Operating Conditions

			MIN	NOM	MAX	UNIT
V _{CC}	Supply voltage		4.5	5	5.5	V
V_{DD}	7 _{DD} Supply voltage				15	V
V _{SS}	Supply voltage		-7.5	–9	-15	V
V _{IH}	High-level input voltage (drivers only)		1.9			V
V _{IL}	Low-level input voltage (drivers only)				0.8	V
	Lligh lovel output ourset	Drivers			-6	mA
Іон	High-level output current	Receivers			-0.5	IIIA
		Drivers			6	^
I _{OL}	Low-level output current	Receivers			16	mA
T _A	Operating free-air temperature		0		70	°C

Supply Currents

	PARAMETER		TEST C	ONDITIONS		MIN	MAX	UNIT
I _{CC}	Supply current from V _{CC}	All inputs at 5 V,	No load,	V _{CC} = 5 V			30	mA
				V _{DD} = 9 V,	V _{SS} = -9 V		15	
	L. Complex surrout forms V	All inputs at 1.9 V,	No load	V _{DD} = 12 V,	V _{SS} = -12 V		19	
				V _{DD} = 15 V,	V _{SS} = -15 V		25	
I _{DD}	Supply current from V _{DD}			V _{DD} = 9 V,	V _{SS} = -9 V		4.5	mA
		All inputs at 0.8 V,	No load	V _{DD} = 12 V,	V _{SS} = -12 V		5.5	
				V _{DD} = 15 V,	V _{SS} = -15 V		9	
				V _{DD} = 9 V,	V _{SS} = -9 V		-15	
		All inputs at 1.9 V,	No load	V _{DD} = 12 V,	V _{SS} = -12 V		-19	
	0			V _{DD} = 15 V,	V _{SS} = -15 V		-25	4
I _{SS}	Supply current from V _{SS}			V _{DD} = 9 V,	V _{SS} = -9 V		-3.2	mA
		All inputs at 0.8 V,	No load	V _{DD} = 12 V,	V _{SS} = -12 V		-3.2	
				V _{DD} = 15 V,	V _{SS} = -15 V		-3.2	



SLLS181D-DECEMBER 1994-REVISED JANUARY 2006

DRIVER SECTION

Electrical Characteristics

over recommended operating free-air temperature range, V_{DD} = 9 V, V_{SS} = -9 V, V_{CC} = 5 V (unless otherwise noted)

	PARAMETER	•	TEST CONDITIO	NS	MIN	TYP	MAX	UNIT
V _{OH}	High-level output voltage	V _{IL} = 0.8 V,	$R_L = 3 k\Omega$,	See Figure 1	6	7.5		V
V _{OL}	Low-level output voltage (1)	V _{IH} = 1.9 V,	$R_L = 3 k\Omega$,	See Figure 1		-7.5	-6	V
I _{IH}	High-level input current	V _I = 5 V,	See Figure 2				10	μΑ
I _{IL}	Low-level input current	V _I = 0,	See Figure 2				-1.6	mA
I _{OS(H)}	High-level short-circuit output current (2)	V _{IL} = 0.8 V,	$V_{O} = 0$,	See Figure 1	-4.5	-12	-19.5	mA
I _{OS(L)}	Low-level short-circuit output current	V _{IH} = 2 V,	$V_{O} = 0$,	See Figure 1	4.5	12	19.5	mA
r _o	Output resistance (3)	$V_{CC} = V_{DD} = V_{S}$	S = 0,	V _O = -2 V to 2 V	300			Ω

⁽¹⁾ The algebraic convention, in which the more positive (less negative) limit is designated as maximum, is used in this data sheet for logic levels only (e.g., if –10 V is maximum, the typical value is a more negative voltage).

(2) Output short-circuit conditions must maintain the total power dissipation below absolute maximum ratings.

Switching Characteristics

 V_{CC} = 5 V, V_{DD} = 12 V, V_{SS} = -12 V, T_A = 25°C (see Figure 3)

	PARAMETER	TEST C	ONDITIONS	MIN	TYP	MAX	UNIT
t _{PLH}	Propagation delay time, low- to high-level output	$R_L = 3 \text{ k}\Omega \text{ to } 7 \text{ k}\Omega,$	C _L = 15 pF		315	500	ns
t _{PHL}	Propagation delay time, high- to low-level output	$R_L = 3 \text{ k}\Omega \text{ to } 7 \text{ k}\Omega,$	C _L = 15 pF		75	175	ns
	Transition time, low- to high-level output	$R_1 = 3 \text{ k}\Omega \text{ to } 7 \text{ k}\Omega$	C _L = 15 pF		60	100	ns
t _{TLH}	Transition time, low- to high-level output	UF = 2 K25 (0 \ K25	C _L = 2500 pF ⁽¹⁾		1.7	2.5	μs
	Transition time, high- to low-level output	$R_1 = 3 \text{ k}\Omega \text{ to } 7 \text{ k}\Omega$	C _L = 15 pF		40	75	ns
t _{THL}	Transition time, high- to low-level output	nL = 3 K32 to 7 K32	C _L = 2500 pF ⁽²⁾		1.5	2.5	μS

⁽¹⁾ Measured between -3-V and 3-V points of the output waveform (TIA/EIA-232-F conditions); all unused inputs are tied either high or low.

⁽³⁾ Test conditions are those specified by TIA/EIA-232-F and as listed above.

⁽²⁾ Measured between 3-V and -3-V points of the output waveform (TIA/EIA-232-F conditions); all unused inputs are tied either high or low.

SLLS181D-DECEMBER 1994-REVISED JANUARY 2006

RECEIVER SECTION

Electrical Characteristics

over recommended operating conditions (unless otherwise noted)

	PARAMETER	TEST C	ONDITIONS	MIN	TYP (1)	MAX	UNIT
\/	Desitive seins threshold voltage	Coo Figure F	T _A = 25°C	1.75	1.9	2.3	V
V_{T+}	Positive-going threshold voltage	See Figure 5	$T_A = 0$ °C to 70 °C	1.55		2.3	V
V _{T-}	Negative-going threshold voltage		·	0.75	0.97	1.25	٧
V _{hys}	Input hysteresis (V _{T+} – V _{T-})			0.5			V
V	Lligh lavel autout valtage	1 0.5 mA	V _{IH} = 0.75 V	2.6	4	5	V
V _{OH}	High-level output voltage	$I_{OH} = -0.5 \text{ mA}$	Inputs open	2.6			\ \
V _{OL}	Low-level input voltage	I _{OL} = 10 mA,	V _I = 3 V		0.2	0.45	V
	High-level input current	V _I = 25 V,	See Figure 5	3.6		8.3	mA
I _{IH}	nigh-lever input current	$V_I = 3 V$,	See Figure 5	0.43			IIIA
	Low-level output current	$V_{I} = -25 V$,	See Figure 5	-3.6		-8.3	m A
I _{IL}	Low-level output current	V _I = -3 V,	See Figure 5	-0.43			mA
Ios	Short-circuit output current	See Figure 4			-3.4	-12	mA

⁽¹⁾ All typical values are at T_A = 25°C, V_{CC} = 5 V, V_{DD} = 9 V, and V_{SS} = -9 V.

Switching Characteristics

 V_{CC} = 5 V, V_{DD} = 12 V, V_{SS} = -12 V, T_A = 25°C (see Figure 6)

	PARAMETER	TEST CO	ONDITIONS	MIN	TYP	MAX	UNIT
t _{PLH}	Propagation delay time, low- to high-level output	C _L = 50 pF,	$R_L = 5 \text{ k}\Omega$		107	500	ns
t _{PHL}	Propagation delay time, high- to low-level output	C _L = 50 pF,	$R_L = 5 \text{ k}\Omega$		42	150	ns
t _{TLH}	Transition time, low- to high-level output	C _L = 50 pF,	$R_L = 5 \text{ k}\Omega$		175	525	ns
t _{THL}	Transition time, high- to low-level output	C _L = 50 pF,	$R_L = 5 \text{ k}\Omega$		16	60	ns



PARAMETER MEASUREMENT INFORMATION




Figure 1. Driver Test Circuit for $V_{\text{OH}},\,V_{\text{OL}},\,I_{\text{OS(H)}},$ and $I_{\text{OS(L)}}$





Figure 2. Driver Test Circuit for I_{IH} and I_{IL}



- A. C_I includes probe and jig capacitance.
- B. The pulse generator has the following characteristics: t_w = 25 μ s, PRR = 20 kHz, Z_0 = 50 Ω , t_r = t_f < 50 ns.

Figure 3. Driver Test Circuit and Voltage Waveforms




Figure 4. Receiver Test Circuit for Ios





Figure 5. Receiver Test Circuit for V_T, V_{OH}, and V_{OL}



PARAMETER MEASUREMENT INFORMATION (continued)




- A. C_L includes probe and jig capacitance.
- B. The pulse generator has the following characteristics: t_w = 25 μ s, PRR = 20 kHz, Z_O = 50 Ω , t_r = t_f < 50 ns.

Figure 6. Receiver Propagation and Transition Times



TYPICAL CHARACTERISTICS


DRIVER SECTION






SHORT-CIRCUIT OUTPUT CURRENT vs FREE-AIR TEMPERATURE 12 $I_{OS(L)}(V_I = 1.9 V)$ Ios - Short-Circuit Output Current - mA 9 6 3 $V_{DD} = 9 V$ V_{SS} = -9 V 0 V_O = 0 -3 -6 $I_{OS(H)}$ ($V_I = 0.8 V$) -9 0 10 30 40 70 T_A – Free-Air Temperature – $^{\circ}C$

Figure 9.







TYPICAL CHARACTERISTICS

RECEIVER SECTION





Figure 11.



NOTE A: This figure shows the maximum amplitude of a positive-going pulse that, starting from 0 V, will not cause a change in the output level.

Figure 13.




Figure 12.




Figure 14.



APPLICATION INFORMATION

Diodes placed in series with the V_{DD} and V_{SS} leads protect the SN75185 in the fault condition. In the fault condition, the device outputs are shorted to ± 15 V, and the power supplies are at low and provide low-impedance paths to ground (see Figure 15).





Figure 15. Power-Supply Protection to Meet Power-Off Fault Conditions of TIA/EIA-232-F



(1) See Figure 10 to select the correct values for the loading capacitors (C1, C2, and C3), which are required to meet the RS-232 maximum slew-rate requirement of 30 V/μs. The value of the loading capacitors required depends on the line length and desired slew rate, but typically is 330 pF.

Figure 16. Typical Connection

www.ti.com 11-Nov-2025

PACKAGING INFORMATION

Orderable part number	Status	Material type	Package Pins	Package qty Carrier	RoHS	Lead finish/ Ball material	MSL rating/ Peak reflow	Op temp (°C)	Part marking (6)
	(1)	(2)			(5)	(4)	(5)		(0)
SN75185DB	Obsolete	Production	SSOP (DB) 20	-	-	Call TI	Call TI	0 to 70	A185
SN75185DBR	Active	Production	SSOP (DB) 20	2000 LARGE T&R	Yes	NIPDAU	Level-1-260C-UNLIM	0 to 70	A185
SN75185DBR.A	Active	Production	SSOP (DB) 20	2000 LARGE T&R	Yes	NIPDAU	Level-1-260C-UNLIM	0 to 70	A185
SN75185DW	Obsolete	Production	SOIC (DW) 20	-	-	Call TI	Call TI	0 to 70	SN75185
SN75185DWR	Active	Production	SOIC (DW) 20	2000 LARGE T&R	Yes	NIPDAU	Level-1-260C-UNLIM	0 to 70	SN75185
SN75185DWR.A	Active	Production	SOIC (DW) 20	2000 LARGE T&R	Yes	NIPDAU	Level-1-260C-UNLIM	0 to 70	SN75185
SN75185N	Active	Production	PDIP (N) 20	20 TUBE	Yes	NIPDAU	N/A for Pkg Type	0 to 70	SN75185N
SN75185N.A	Active	Production	PDIP (N) 20	20 TUBE	Yes	NIPDAU	N/A for Pkg Type	0 to 70	SN75185N
SN75185PWR	Active	Production	TSSOP (PW) 20	2000 LARGE T&R	Yes	NIPDAU	Level-1-260C-UNLIM	0 to 70	A185
SN75185PWR.A	Active	Production	TSSOP (PW) 20	2000 LARGE T&R	Yes	NIPDAU	Level-1-260C-UNLIM	0 to 70	A185

⁽¹⁾ Status: For more details on status, see our product life cycle.

Multiple part markings will be inside parentheses. Only one part marking contained in parentheses and separated by a "~" will appear on a part. If a line is indented then it is a continuation of the previous line and the two combined represent the entire part marking for that device.

Important Information and Disclaimer: The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative

⁽²⁾ Material type: When designated, preproduction parts are prototypes/experimental devices, and are not yet approved or released for full production. Testing and final process, including without limitation quality assurance, reliability performance testing, and/or process qualification, may not yet be complete, and this item is subject to further changes or possible discontinuation. If available for ordering, purchases will be subject to an additional waiver at checkout, and are intended for early internal evaluation purposes only. These items are sold without warranties of any kind.

⁽³⁾ RoHS values: Yes, No, RoHS Exempt. See the TI RoHS Statement for additional information and value definition.

⁽⁴⁾ Lead finish/Ball material: Parts may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead finish/Ball material values may wrap to two lines if the finish value exceeds the maximum column width.

⁽⁵⁾ **MSL rating/Peak reflow:** The moisture sensitivity level ratings and peak solder (reflow) temperatures. In the event that a part has multiple moisture sensitivity ratings, only the lowest level per JEDEC standards is shown. Refer to the shipping label for the actual reflow temperature that will be used to mount the part to the printed circuit board.

⁽⁶⁾ Part marking: There may be an additional marking, which relates to the logo, the lot trace code information, or the environmental category of the part.



PACKAGE OPTION ADDENDUM

www.ti.com 11-Nov-2025


and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.

PACKAGE MATERIALS INFORMATION

www.ti.com 24-Jul-2025

TAPE AND REEL INFORMATION



TAPE DIMENSIONS KO P1 BO BO Cavity AO

A0	Dimension designed to accommodate the component width
В0	Dimension designed to accommodate the component length
K0	Dimension designed to accommodate the component thickness
W	Overall width of the carrier tape
P1	Pitch between successive cavity centers


QUADRANT ASSIGNMENTS FOR PIN 1 ORIENTATION IN TAPE



*All dimensions are nominal

Device	Package Type	Package Drawing		SPQ	Reel Diameter (mm)	Reel Width W1 (mm)	A0 (mm)	B0 (mm)	K0 (mm)	P1 (mm)	W (mm)	Pin1 Quadrant
SN75185DBR	SSOP	DB	20	2000	330.0	16.4	8.2	7.5	2.5	12.0	16.0	Q1
SN75185DWR	SOIC	DW	20	2000	330.0	24.4	10.8	13.3	2.7	12.0	24.0	Q1
SN75185DWR	SOIC	DW	20	2000	330.0	24.4	10.8	13.3	2.7	12.0	24.0	Q1
SN75185PWR	TSSOP	PW	20	2000	330.0	16.4	6.95	7.0	1.4	8.0	16.0	Q1

www.ti.com 24-Jul-2025



*All dimensions are nominal

Device	Package Type	Package Drawing	Pins	SPQ	Length (mm)	Width (mm)	Height (mm)
SN75185DBR	SSOP	DB	20	2000	353.0	353.0	32.0
SN75185DWR	SOIC	DW	20	2000	356.0	356.0	45.0
SN75185DWR	SOIC	DW	20	2000	367.0	367.0	45.0
SN75185PWR	TSSOP	PW	20	2000	353.0	353.0	32.0

PACKAGE MATERIALS INFORMATION

www.ti.com 24-Jul-2025


TUBE



*All dimensions are nominal

Device	Package Name	Package Type	Pins	SPQ	L (mm)	W (mm)	T (µm)	B (mm)
SN75185N	N	PDIP	20	20	506	13.97	11230	4.32
SN75185N.A	N	PDIP	20	20	506	13.97	11230	4.32






NOTES:

- 1. All linear dimensions are in millimeters. Any dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.

 2. This drawing is subject to change without notice.

 3. This dimension does not include mold flash, protrusions, or gate burrs. Mold flash, protrusions, or gate burrs shall not
- exceed 0.15 mm per side.
- 4. This dimension does not include interlead flash. Interlead flash shall not exceed 0.25 mm per side.
- 5. Reference JEDEC registration MO-153.






NOTES: (continued)

6. Publication IPC-7351 may have alternate designs.

7. Solder mask tolerances between and around signal pads can vary based on board fabrication site.






NOTES: (continued)

- 8. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.
- 9. Board assembly site may have different recommendations for stencil design.








NOTES:

- 1. All linear dimensions are in millimeters. Any dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.

 2. This drawing is subject to change without notice.

 3. This dimension does not include mold flash, protrusions, or gate burrs. Mold flash, protrusions, or gate burrs shall not
- exceed 0.15 mm per side.
- 4. This dimension does not include interlead flash. Interlead flash shall not exceed 0.25 mm per side.
- 5. Reference JEDEC registration MO-150.






NOTES: (continued)

6. Publication IPC-7351 may have alternate designs.

7. Solder mask tolerances between and around signal pads can vary based on board fabrication site.





NOTES: (continued)

- 8. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.
- 9. Board assembly site may have different recommendations for stencil design.



N (R-PDIP-T**)

PLASTIC DUAL-IN-LINE PACKAGE

16 PINS SHOWN




NOTES:

- A. All linear dimensions are in inches (millimeters).
- B. This drawing is subject to change without notice.
- Falls within JEDEC MS-001, except 18 and 20 pin minimum body length (Dim A).
- The 20 pin end lead shoulder width is a vendor option, either half or full width.





SOIC



NOTES:


- 1. All linear dimensions are in millimeters. Dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.

 2. This drawing is subject to change without notice.

 3. This dimension does not include mold flash, protrusions, or gate burrs. Mold flash, protrusions, or gate burrs shall not
- exceed 0.15 mm per side.
- 4. This dimension does not include interlead flash. Interlead flash shall not exceed 0.43 mm per side.
- 5. Reference JEDEC registration MS-013.



SOIC




NOTES: (continued)

6. Publication IPC-7351 may have alternate designs.

7. Solder mask tolerances between and around signal pads can vary based on board fabrication site.



SOIC



NOTES: (continued)

- 8. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.
- 9. Board assembly site may have different recommendations for stencil design.



IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATASHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, regulatory or other requirements.

These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you fully indemnify TI and its representatives against any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to TI's Terms of Sale, TI's General Quality Guidelines, or other applicable terms available either on ti.com or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products. Unless TI explicitly designates a product as custom or customer-specified, TI products are standard, catalog, general purpose devices.

TI objects to and rejects any additional or different terms you may propose.

Copyright © 2025, Texas Instruments Incorporated

Last updated 10/2025