

SNx4AHC14 ヘキサ・シュミット・トリガ・インバータ

1 特長

- JESD 22 を上回る ESD 保護:
 - 2000V、人体モデル (A114-A)
 - 200V、マシン モデル(A115-A)
 - 1000V、デバイス帯電モデル (C101)
- 動作範囲: 2V~5.5V
- 5V で $\pm 8\text{mA}$ の出力駆動能力
- シュミットトリガ入力により入力ノイズ耐性を実現
- 低消費電力: $I_{CC} = 20\mu\text{A}$ (最大値)
- JESD 17 準拠で
250mA 超のラッチアップ性能

2 アプリケーション

- [UPS](#)
- 白物家電
- [コンピュータ周辺機器](#)
- プリンタ
- [AC サーボ・ドライブ](#)
- [デスクトップ・コンピュータ](#)

3 概要


SNx4AHC14 デバイスは、6 つの独立したインバータを備えています。これらのデバイスはブール関数 $Y = \bar{A}$ を実行します。

各回路は、独立したインバータとして機能しますが、シュミット・トリガ動作のため、正方向 (V_{T+}) と負方向 (V_{T-}) の信号に対する入力スレッショルド・レベルが異なります。

製品情報

| 部品番号 | 定格 | パッケージ ⁽¹⁾ |
|-----------|----|----------------------|
| SN54AHC14 | 軍用 | J (CDIP, 14) |
| | | W (CFP, 14) |
| | | FK (LCCC, 20) |
| | | BQA (WQFN, 14) |
| SN74AHC14 | 商用 | D (SOIC, 14) |
| | | DB (SSOP, 14) |
| | | N (PDIP, 14) |
| | | NS (SO, 14) |
| | | PW (TSSOP, 14) |
| | | DGV (TVSOP, 14) |
| | | RGY (VQFN, 14) |
| | | BQA (WQFN, 14) |

(1) 利用可能なすべてのパッケージについては、データシートの末尾にある注文情報を参照してください。



Copyright © 2016, Texas Instruments Incorporated

論理図 (正論理)



Table of Contents

| | | | |
|---|----|--|----|
| 1 特長 | 1 | 7.3 Feature Description..... | 10 |
| 2 アプリケーション | 1 | 7.4 Device Functional Modes..... | 10 |
| 3 概要 | 1 | 8 Application and Implementation | 11 |
| 4 Pin Configuration and Functions | 3 | 8.1 Application Information..... | 11 |
| 5 Specifications | 4 | 8.2 Typical Application..... | 11 |
| 5.1 Absolute Maximum Ratings..... | 4 | 8.3 Power Supply Recommendations..... | 12 |
| 5.2 ESD Ratings..... | 4 | 8.4 Layout..... | 12 |
| 5.3 Recommended Operating Conditions..... | 4 | 9 Device and Documentation Support | 13 |
| 5.4 Thermal Information..... | 5 | 9.1 Documentation Support..... | 13 |
| 5.5 Electrical Characteristics..... | 5 | 9.2 ドキュメントの更新通知を受け取る方法..... | 13 |
| 5.6 Switching Characteristics, $V_{CC} = 3.3\text{ V} \pm 0.3\text{ V}$ | 7 | 9.3 サポート・リソース..... | 13 |
| 5.7 Switching Characteristics, $V_{CC} = 5\text{ V} \pm 0.5\text{ V}$ | 7 | 9.4 Trademarks..... | 13 |
| 5.8 Typical Characteristics..... | 7 | 9.5 静電気放電に関する注意事項..... | 13 |
| 6 Parameter Measurement Information | 8 | 9.6 用語集..... | 13 |
| 7 Detailed Description | 10 | 10 Revision History | 13 |
| 7.1 Overview..... | 10 | 11 Mechanical, Packaging, and Orderable Information | 14 |
| 7.2 Functional Block Diagram..... | 10 | | |

4 Pin Configuration and Functions




Figure 4-1. D, DB, DGV, J, N, NS, PW, or W Package, 14-Pin SOIC, SSOP, TVSOP, CDIP, PDIP, SO, TSSOP, or CFP (Top View)




Figure 4-2. RGY or BQA Package, 14-Pin VQFN or WQFN (Top View)




Figure 4-3. FK Package, 20-Pin LCCC (Top View)

Table 4-1. Pin Functions

| NAME | PIN | | TYPE ⁽¹⁾ | DESCRIPTION |
|-----------------|---|---------------------|---------------------|------------------------|
| | SOIC, SSOP, TVSOP, CDIP, PDIP, SO, TSSOP, CFP, VQFN | LCCC | | |
| 1A | 1 | 2 | I | Channel 1 Input |
| 1Y | 2 | 3 | O | Channel 1 Output |
| 2A | 3 | 4 | I | Channel 2 Input |
| 2Y | 4 | 6 | O | Channel 2 Output |
| 3A | 5 | 8 | I | Channel 3 Input |
| 3Y | 6 | 9 | O | Channel 3 Output |
| 4A | 9 | 13 | I | Channel 4 Input |
| 4Y | 8 | 12 | O | Channel 4 Output |
| 5A | 11 | 16 | I | Channel 5 Input |
| 5Y | 10 | 14 | O | Channel 5 Output |
| 6A | 13 | 19 | I | Channel 6 Input |
| 6Y | 12 | 18 | O | Channel 6 Output |
| GND | 7 | 10 | — | Ground |
| NC | — | 1, 5, 7, 11, 15, 17 | — | No internal connection |
| V _{CC} | 14 | 20 | — | Power supply |

(1) I = input, O = output

5 Specifications

5.1 Absolute Maximum Ratings

over operating free-air temperature range (unless otherwise noted)⁽¹⁾

| | | MIN | MAX | UNIT |
|-------------------------------|---|--|-----------------------|------|
| V _{CC} | Supply voltage | -0.5 | 7 | V |
| V _I ⁽²⁾ | Input voltage | -0.5 | 7 | V |
| V _O ⁽²⁾ | Output voltage | -0.5 | V _{CC} + 0.5 | V |
| I _{IK} | Input clamp current | V _I < 0 | -20 | mA |
| I _{OK} | Output clamp current | V _O < 0 or V _O > V _{CC} | ±20 | mA |
| I _O | Continuous output current | V _O = 0 to V _{CC} | ±25 | mA |
| | Continuous current through V _{CC} or GND | | ±50 | mA |
| T _J | Virtual operating junction temperature | | 150 | °C |
| T _{stg} | Storage temperature | -65 | 150 | °C |

- (1) Stresses beyond those listed under *Absolute Maximum Ratings* may cause permanent damage to the device. These are stress ratings only, which do not imply functional operation of the device at these or any other conditions beyond those indicated under *Recommended Operating Conditions*. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability.
- (2) The input and output voltage ratings may be exceeded if the input and output current ratings are observed.

5.2 ESD Ratings

| | | VALUE | UNIT |
|--------------------|-------------------------|--|-------|
| V _(ESD) | Electrostatic discharge | Human-body model (HBM), per ANSI/ESDA/JEDEC JS-001 ⁽¹⁾ | ±2000 |
| | | Charged-device model (CDM), per JEDEC specification JESD22-C101 ⁽²⁾ | ±1000 |

- (1) JEDEC document JEP155 states that 500-V HBM allows safe manufacturing with a standard ESD control process.
- (2) JEDEC document JEP157 states that 250-V CDM allows safe manufacturing with a standard ESD control process.

5.3 Recommended Operating Conditions

over operating free-air temperature range (unless otherwise noted)⁽¹⁾

| | | MIN | MAX | UNIT |
|-----------------|--------------------------------|---------------------------------|-----------------|------|
| V _{CC} | Supply voltage | 2 | 5.5 | V |
| V _I | Input voltage | 0 | 5.5 | V |
| V _O | Output voltage | 0 | V _{CC} | V |
| I _{OH} | High-level output current | V _{CC} = 2 V | -50 | μA |
| | | V _{CC} = 3.3 V ± 0.3 V | -4 | mA |
| | | V _{CC} = 5 V ± 0.5 V | -8 | |
| I _{OL} | Low-level output current | V _{CC} = 2 V | 50 | μA |
| | | V _{CC} = 3.3 V ± 0.3 V | 4 | mA |
| | | V _{CC} = 5 V ± 0.5 V | 8 | |
| T _A | Operating free-air temperature | SN54AHC14 | -55 | 125 |
| | | SN74AHC14 | -40 | 125 |

- (1) All unused inputs of the device must be held at V_{CC} or GND to ensure proper device operation. See TI application report, [Implications of Slow or Floating CMOS Inputs](#) (SCBA004).

5.4 Thermal Information

| THERMAL METRIC ⁽¹⁾ | | SN74AHC14 | | | | | | | | UNIT |
|-------------------------------|--|-----------|-----------|-------------|----------|---------|------------|------------|------------|------|
| | | D (SOIC) | DB (SSOP) | DGV (TVSOP) | N (PDIP) | NS (SO) | PW (TSSOP) | RGY (VQFN) | BQA (WQFN) | |
| | | 14 PINS | 14 PINS | 14 PINS | 14 PINS | 14 PINS | 14 PINS | 14 PINS | 14 PINS | |
| R _{θJA} | Junction-to-ambient thermal resistance | 124.5 | 137.8 | 141.9 | 61.9 | 94.7 | 147.7 | 87.1 | 88.3 | °C/W |
| R _{θJC(top)} | Junction-to-case (top) thermal resistance | 78.8 | 90 | 61.1 | 49.5 | 52.5 | 77.4 | 92.6 | 90.9 | °C/W |
| R _{θJB} | Junction-to-board thermal resistance | 81 | 98.3 | 71.3 | 41.7 | 53.4 | 90.9 | 62.5 | 56.8 | °C/W |
| ψ _{JT} | Junction-to-top characterization parameter | 37 | 42.7 | 9.7 | 34.7 | 21.3 | 27.2 | 22.8 | 9.9 | °C/W |
| ψ _{JB} | Junction-to-board characterization parameter | 80.6 | 97 | 70.6 | 41.7 | 53.1 | 90.2 | 61.7 | 56.7 | °C/W |
| R _{θJC(bot)} | Junction-to-case (bottom) thermal resistance | N/A | N/A | N/A | N/A | N/A | N/A | 45.1 | 33.4 | °C/W |

(1) For more information about traditional and new thermal metrics, see the [Semiconductor and IC Package Thermal Metrics](#) application report.

5.5 Electrical Characteristics

over operating free-air temperature range (unless otherwise noted)

| PARAMETER | | TEST CONDITIONS | | | MIN | TYP | MAX | UNIT |
|-----------------|--|-------------------------|-----|--|------|-----|------|------|
| V _{T+} | Positive-going input threshold voltage | V _{CC} = 3 V | | | 1.2 | | 2.2 | V |
| | | V _{CC} = 4.5 V | | | 1.75 | | 3.15 | |
| | | V _{CC} = 5.5 V | | | 2.15 | | 3.85 | |
| V _{T-} | Negative-going input threshold voltage | V _{CC} = 3 V | | | 0.9 | | 1.9 | V |
| | | V _{CC} = 4.5 V | | | 1.35 | | 2.75 | |
| | | V _{CC} = 5.5 V | | | 1.65 | | 3.35 | |
| ΔV _T | Hysteresis (V _{T+} – V _{T-}) | V _{CC} = 3 V | | | 0.3 | | 1.2 | V |
| | | V _{CC} = 4.5 V | | | 0.4 | | 1.4 | |
| | | V _{CC} = 5.5 V | | | 0.5 | | 1.6 | |
| V _{OH} | I _{OH} = –50 μA | V _{CC} = 2 V | | | 1.9 | | 2 | V |
| | | V _{CC} = 3 V | | | 2.9 | | 3 | |
| | | V _{CC} = 4.5 V | | | 4.4 | | 4.5 | |
| | I _{OH} = –4 mA, V _{CC} = 3 V | T _A = 25°C | | | 2.58 | | | |
| | | SNx4AHC14 | | | 2.48 | | | |
| | I _{OL} = –8 mA, V _{CC} = 4.5 V | T _A = 25°C | | | 3.94 | | | |
| SNx4AHC14 | | | 3.8 | | | | | |

5.5 Electrical Characteristics (続き)

over operating free-air temperature range (unless otherwise noted)

| PARAMETER | TEST CONDITIONS | MIN | TYP | MAX | UNIT | |
|---------------------------------|---|--|---------------------------------|-------------------|------|------|
| V _{OL} | I _{OH} = 50 μA | V _{CC} = 2 V | | 0.1 | V | |
| | | V _{CC} = 3 V | | 0.1 | | |
| | | V _{CC} = 4.5 V | | 0.1 | | |
| | I _{OH} = 4 mA, V _{CC} = 3 V | T _A = 25°C | | 0.36 | | |
| | | SN54AHC14 | | 0.5 | | |
| | | SN74AHC14 | T _A = -40°C to 85°C | | | 0.44 |
| | | | T _A = -40°C to 125°C | | | 0.5 |
| | I _{OL} = 8 mA, V _{CC} = 4.5 V | T _A = 25°C | | 0.36 | | |
| | | SN54AHC14 | | 0.5 | | |
| | | SN74AHC14 | T _A = -40°C to 85°C | | | 0.44 |
| T _A = -40°C to 125°C | | | | 0.5 | | |
| I _I | V _I = 5.5 V or GND, V _{CC} = 0 V to 5.5 V | T _A = 25°C | | ±0.1 | μA | |
| | | SNx4AHC14 | | ±1 ⁽¹⁾ | | |
| I _{CC} | V _I = V _{CC} or GND, I _O = 0, V _{CC} = 5.5 V | T _A = 25°C | | 1 | μA | |
| | | SNx4AHC14 | | 20 | | |
| C _I | V _I = V _{CC} or GND, V _{CC} = 5 V | T _A = 25°C | 2 | 10 | pF | |
| | | SN74AHC14 | | 10 | | |
| C _{pd} | Power dissipation capacitance No load, f = 1 MHz, V _{CC} = 5 V | | 9 | | pF | |
| NOISE⁽²⁾ | | | | | | |
| V _{OL(P)} | Quiet output, maximum dynamic V _{OL} | V _{CC} = 5 V, C _L = 50 pF, T _A = 25°C | | 0.8 | V | |
| V _{OL(V)} | Quiet output, minimum dynamic V _{OL} | V _{CC} = 5 V, C _L = 50 pF, T _A = 25°C | | -0.4 | V | |
| V _{OH(V)} | Quiet output, minimum dynamic V _{OH} | V _{CC} = 5 V, C _L = 50 pF, T _A = 25°C | | 4.6 | V | |
| V _{IH(D)} | High-level dynamic input voltage | V _{CC} = 5 V, C _L = 50 pF, T _A = 25°C | 3.5 | | V | |
| V _{IL(D)} | Low-level dynamic input voltage | V _{CC} = 5 V, C _L = 50 pF, T _A = 25°C | | 1.5 | V | |

(1) On products compliant to MIL-PRF-38535, this parameter is not production tested at V_{CC} = 0 V.

(2) Characteristics are for surface-mount packages only.

5.6 Switching Characteristics, $V_{CC} = 3.3\text{ V} \pm 0.3\text{ V}$

$V_{CC} = 3.3\text{ V} \pm 0.3\text{ V}$ and over operating free-air temperature range (unless otherwise noted; see [Parameter Measurement Information](#))

| PARAMETER | TEST CONDITIONS | | MIN | TYP | MAX | UNIT |
|-----------|--|--------------------------|--------------------|-----|---------------------|------|
| t_{PLH} | From A (input) to Y (output), $C_L = 15\text{ pF}$ | $T_A = 25^\circ\text{C}$ | 8.3 ⁽¹⁾ | | 12.8 ⁽¹⁾ | ns |
| | | SN54AHC14 | 1 ⁽¹⁾ | | 15 ⁽¹⁾ | |
| | | SN74AHC14 | 1 | | 16 | |
| t_{PHL} | From A (input) to Y (output), $C_L = 15\text{ pF}$ | $T_A = 25^\circ\text{C}$ | 8.3 ⁽¹⁾ | | 12.8 ⁽¹⁾ | ns |
| | | SN54AHC14 | 1 ⁽¹⁾ | | 15 ⁽¹⁾ | |
| | | SN74AHC14 | 1 | | 16 | |
| t_{PLH} | From A (input) to Y (output), $C_L = 50\text{ pF}$ | $T_A = 25^\circ\text{C}$ | 10.8 | | 16.3 | ns |
| | | SN54AHC14 | 1 | | 18.5 | |
| | | SN74AHC14 | 1 | | 19.5 | |
| t_{PHL} | From A (input) to Y (output), $C_L = 50\text{ pF}$ | $T_A = 25^\circ\text{C}$ | 10.8 | | 16.3 | ns |
| | | SN54AHC14 | 1 | | 18.5 | |
| | | SN74AHC14 | 1 | | 19.5 | |

(1) On products compliant to MIL-PRF-38535, this parameter is not production tested.


5.7 Switching Characteristics, $V_{CC} = 5\text{ V} \pm 0.5\text{ V}$

$V_{CC} = 5\text{ V} \pm 0.5\text{ V}$ and over operating free-air temperature range (unless otherwise noted; see [Parameter Measurement Information](#))

| PARAMETER | TEST CONDITIONS | | MIN | TYP | MAX | UNIT |
|-----------|--|--------------------------|--------------------|-----|--------------------|------|
| t_{PLH} | From A (input) to Y (output), $C_L = 15\text{ pF}$ | $T_A = 25^\circ\text{C}$ | 5.5 ⁽¹⁾ | | 8.6 ⁽¹⁾ | ns |
| | | SN54AHC14 | 1 ⁽¹⁾ | | 10 ⁽¹⁾ | |
| | | SN74AHC14 | 1 | | 10 | |
| t_{PHL} | From A (input) to Y (output), $C_L = 15\text{ pF}$ | $T_A = 25^\circ\text{C}$ | 5.5 ⁽¹⁾ | | 8.6 ⁽¹⁾ | ns |
| | | SN54AHC14 | 1 ⁽¹⁾ | | 10 ⁽¹⁾ | |
| | | SN74AHC14 | 1 | | 10 | |
| t_{PLH} | From A (input) to Y (output), $C_L = 50\text{ pF}$ | $T_A = 25^\circ\text{C}$ | 7 | | 10.6 | ns |
| | | SNx4AHC14 | 1 | | 12 | |
| t_{PHL} | From A (input) to Y (output), $C_L = 50\text{ pF}$ | $T_A = 25^\circ\text{C}$ | 7 | | 10.6 | ns |
| | | SNx4AHC14 | 1 | | 12 | |

5.8 Typical Characteristics

$C_L = 50\text{ pF}$ (unless otherwise noted)



5-1. Propagation Delay vs Supply Voltage

6 Parameter Measurement Information




图 6-1. Load Circuit For Totem-Pole Outputs




图 6-2. Load Circuit For 3-State and Open-Drain Outputs

表 6-1. Measurement Information

| TEST | S1 |
|-----------------------|----------|
| t_{PLH} , t_{PHL} | Open |
| t_{PLZ} , t_{PZL} | V_{CC} |
| t_{PHZ} , t_{PZH} | GND |
| Open drain | V_{CC} |




图 6-3. Voltage Waveforms Pulse Duration




图 6-4. Voltage Waveforms Setup and Hold Times





图 6-5. Voltage Waveforms Propagation Delay Times Inverting and Noninverting Outputs



- A. C_L includes probe and jig capacitance.
- B. Waveform 1 is for an output with internal conditions such that the output is low except when disabled by the output control. Waveform 2 is for an output with internal conditions such that the output is high except when disabled by the output control.
- C. All input pulses are supplied by generators having the following characteristics: $PRR \leq 1 \text{ MHz}$, $Z_O = 50 \Omega$, $t_r \leq 3 \text{ ns}$, $t_f \leq 3 \text{ ns}$.
- D. The outputs are measured one at a time with one input transition per measurement.
- E. All parameters and waveforms are not applicable to all devices.

6-6. Voltage Waveforms Enable and Disable Times Low- and High-Level Enabling


7 Detailed Description

7.1 Overview

The SNx4AHC14 Schmitt-Trigger devices contain six independent inverters. They perform the Boolean function $Y = \bar{A}$ in positive logic.

Schmitt-Trigger inputs are designed to provide a minimum separation between positive and negative switching thresholds. This allows for noisy or slow inputs that would cause problems such as oscillation or excessive current draw with normal CMOS inputs.

7.2 Functional Block Diagram



Copyright © 2016, Texas Instruments Incorporated

7.3 Feature Description

The wide operating range of the device allows it to be used in a variety of systems that use different logic levels. The output can drive up to 10 LSTTL loads each. The balanced drive outputs can source or sink 8 mA at 5-V V_{CC} .

7.4 Device Functional Modes

表 7-1 lists the functional modes of the SNx4AHC14.

表 7-1. Function Table

| INPUT A | OUTPUT Y |
|---------|----------|
| H | L |
| L | H |

8 Application and Implementation


注

以下のアプリケーション情報は、TI の製品仕様に含まれるものではなく、TI ではその正確性または完全性を保証いたしません。個々の目的に対する製品の適合性については、お客様の責任で判断していただくこととなります。お客様は自身の設計実装を検証しテストすることで、システムの機能を確認する必要があります。

8.1 Application Information

The SN74AHC14 device is a Schmitt-Trigger input CMOS device that can be used for a multitude of inverting buffer type functions. The application shown here takes advantage of the Schmitt-Trigger inputs to produce a delay for a logic input.

8.2 Typical Application



Copyright © 2016, Texas Instruments Incorporated

図 8-1. Simplified Application Schematic

8.2.1 Design Requirements

This device uses CMOS technology. Take care to avoid bus contention because it can drive currents that would exceed maximum limits. Parallel output drive can create fast edges into light loads so consider routing and load conditions to prevent ringing.


8.2.2 Detailed Design Procedure

This circuit is designed around an RC network that produces a slow input to the second inverter. The RC time constant, τ , is calculated from: $\tau = RC$.

The delay time for this circuit is from $t_{\text{delay}(\text{min})} = -\ln |1 - V_{T+}(\text{min}) / V_{CC}| \tau$ to $t_{\text{delay}(\text{max})} = -\ln |1 - V_{T+}(\text{max}) / V_{CC}| \tau$. It must be noted that the delay is consistent for each device, but because the switching threshold is only ensured between the minimum and maximum value, the output pulse length varies between devices. These values must be calculated by using the minimum and maximum V_{T+} values in the [Electrical Characteristics](#).

The resistor value must be chosen such that the maximum current to and from the SN74AHC14 is 8 mA at 5-V V_{CC} .

8.2.3 Application Curve



8-2. Ideal Capacitor Voltage and Output Voltage With Positive Switching Threshold

8.3 Power Supply Recommendations


The power supply can be any voltage between the minimum and maximum supply voltage rating located in the [Recommended Operating Conditions](#). The V_{CC} terminal must have a good bypass capacitor to prevent power disturbance. TI recommends using a 0.1- μF capacitor on the V_{CC} terminal, and must be placed as close as possible to the pin for best results.

8.4 Layout

8.4.1 Layout Guidelines

When using multiple bit logic devices, inputs must never float. In many cases, functions or parts of functions of digital logic devices are unused, for example, when only two inputs of a triple-input AND gate are used or only three of the four buffer gates are used. Such inputs must not be left unconnected because the undefined voltages at the outside connections result in undefined operational states. All unused inputs of digital logic devices must be connected to a high or low bias to prevent them from floating. The logic level that must be applied to any particular unused input depends on the function of the device. Generally they are tied to GND or V_{CC} , whichever makes more sense or is more convenient. Floating outputs are generally acceptable, unless the part is a transceiver.

8.4.2 Layout Example



8-3. Layout Diagram

9 Device and Documentation Support

9.1 Documentation Support

9.1.1 Related Documentation

For related documentation, see the following:

- Texas Instruments, [Implications of Slow or Floating CMOS Inputs application report](#)

9.2 ドキュメントの更新通知を受け取る方法

ドキュメントの更新についての通知を受け取るには、[ti.com](#) のデバイス製品フォルダを開いてください。「更新の通知を受け取る」をクリックして登録すると、変更されたすべての製品情報に関するダイジェストを毎週受け取れます。変更の詳細については、修正されたドキュメントに含まれている改訂履歴をご覧ください。

9.3 サポート・リソース

[TI E2E™ サポート・フォーラム](#)は、エンジニアが検証済みの回答と設計に関するヒントをエキスパートから迅速かつ直接得ることができる場所です。既存の回答を検索したり、独自の質問をしたりすることで、設計に必要な支援を迅速に得ることができます。

リンクされているコンテンツは、該当する貢献者により、現状のまま提供されるものです。これらは TI の仕様を構成するものではなく、必ずしも TI の見解を反映したものではありません。TI の[使用条件](#)を参照してください。

9.4 Trademarks

TI E2E™ is a trademark of Texas Instruments.

すべての商標は、それぞれの所有者に帰属します。

9.5 静電気放電に関する注意事項



この IC は、ESD によって破損する可能性があります。テキサス・インスツルメンツは、IC を取り扱う際には常に適切な注意を払うことを推奨します。正しい取り扱いおよび設置手順に従わない場合、デバイスを破損するおそれがあります。

ESD による破損は、わずかな性能低下からデバイスの完全な故障まで多岐にわたります。精密な IC の場合、パラメータがわずかに変化するだけで公表されている仕様から外れる可能性があるため、破損が発生しやすくなっています。

9.6 用語集

[テキサス・インスツルメンツ用語集](#) この用語集には、用語や略語の一覧および定義が記載されています。

10 Revision History

資料番号末尾の英字は改訂を表しています。その改訂履歴は英語版に準じています。

| Changes from Revision O (October 2023) to Revision P (February 2024) | Page |
|---|------|
| • Updated R θ JA values: DB = 112.4 to 137.8, RGY = 63.8 to 87.1; Updated DB and RGY packages for R θ JC(top), R θ JB, Ψ JT, Ψ JB, and R θ JC(bot), all values in °C/W..... | 5 |

| Changes from Revision N (June 2023) to Revision O (October 2023) | Page |
|--|------|
| • Deleted machine model..... | 4 |
| • Updated R θ JA values: D = 99.3 to 124.5, PW = 128.8 to 147.7; Updated D and PW packages for R θ JC(top), R θ JB, Ψ JT, Ψ JB, and R θ JC(bot), all values in °C/W..... | 5 |

11 Mechanical, Packaging, and Orderable Information

The following pages include mechanical, packaging, and orderable information. This information is the most current data available for the designated devices. This data is subject to change without notice and revision of this document. For browser-based versions of this data sheet, refer to the left-hand navigation.

PACKAGING INFORMATION

| Orderable part number | Status (1) | Material type (2) | Package Pins | Package qty Carrier | RoHS (3) | Lead finish/ Ball material (4) | MSL rating/ Peak reflow (5) | Op temp (°C) | Part marking (6) |
|---------------------------------|---------------|----------------------|------------------|-----------------------|-------------|--------------------------------------|-----------------------------------|--------------|-------------------------------------|
| 5962-9680201Q2A | Active | Production | LCCC (FK) 20 | 55 TUBE | No | SNPB | N/A for Pkg Type | -55 to 125 | 5962-9680201Q2A SNJ54AHC 14FK |
| 5962-9680201QCA | Active | Production | CDIP (J) 14 | 25 TUBE | No | SNPB | N/A for Pkg Type | -55 to 125 | 5962-9680201QC A SNJ54AHC14J |
| 5962-9680201QDA | NRND | Production | CFP (W) 14 | 25 TUBE | No | SNPB | N/A for Pkg Type | -55 to 125 | 5962-9680201QD A SNJ54AHC14W |
| 5962-9682001QCA | Active | Production | CDIP (J) 14 | 25 TUBE | No | SNPB | N/A for Pkg Type | -55 to 125 | 5962-9682001QC A SNJ54AHC08J |
| 5962-9682001QDA | Active | Production | CFP (W) 14 | 25 TUBE | No | SNPB | N/A for Pkg Type | -55 to 125 | 5962-9682001QD A SNJ54AHC08W |
| SN74AHC14BQAR | Active | Production | WQFN (BQA) 14 | 3000 LARGE T&R | Yes | SN | Level-1-260C-UNLIM | -40 to 125 | AHC14 |
| SN74AHC14BQAR.A | Active | Production | WQFN (BQA) 14 | 3000 LARGE T&R | Yes | SN | Level-1-260C-UNLIM | -40 to 125 | AHC14 |
| SN74AHC14D | Obsolete | Production | SOIC (D) 14 | - | - | Call TI | Call TI | -40 to 125 | AHC14 |
| SN74AHC14DBR | Active | Production | SSOP (DB) 14 | 2000 LARGE T&R | Yes | NIPDAU | Level-1-260C-UNLIM | -40 to 125 | HA14 |
| SN74AHC14DBR.A | Active | Production | SSOP (DB) 14 | 2000 LARGE T&R | Yes | NIPDAU | Level-1-260C-UNLIM | -40 to 125 | HA14 |
| SN74AHC14DGVR | Active | Production | TVSOP (DGV) 14 | 2000 LARGE T&R | Yes | NIPDAU | Level-1-260C-UNLIM | -40 to 125 | HA14 |
| SN74AHC14DGVR.A | Active | Production | TVSOP (DGV) 14 | 2000 LARGE T&R | Yes | NIPDAU | Level-1-260C-UNLIM | -40 to 125 | HA14 |
| SN74AHC14DR | Active | Production | SOIC (D) 14 | 2500 LARGE T&R | Yes | NIPDAU | Level-1-260C-UNLIM | -40 to 125 | AHC14 |
| SN74AHC14DR.A | Active | Production | SOIC (D) 14 | 2500 LARGE T&R | Yes | NIPDAU | Level-1-260C-UNLIM | -40 to 125 | AHC14 |
| SN74AHC14DRE4 | Active | Production | SOIC (D) 14 | 2500 LARGE T&R | Yes | NIPDAU | Level-1-260C-UNLIM | -40 to 125 | AHC14 |
| SN74AHC14DRG3 | Active | Production | SOIC (D) 14 | 2500 LARGE T&R | Yes | SN | Level-1-260C-UNLIM | -40 to 125 | AHC14 |
| SN74AHC14DRG3.A | Active | Production | SOIC (D) 14 | 2500 LARGE T&R | Yes | SN | Level-1-260C-UNLIM | -40 to 125 | AHC14 |
| SN74AHC14DRG4 | Active | Production | SOIC (D) 14 | 2500 LARGE T&R | Yes | NIPDAU | Level-1-260C-UNLIM | -40 to 125 | AHC14 |
| SN74AHC14DRG4.A | Active | Production | SOIC (D) 14 | 2500 LARGE T&R | Yes | NIPDAU | Level-1-260C-UNLIM | -40 to 125 | AHC14 |
| SN74AHC14N | Active | Production | PDIP (N) 14 | 25 TUBE | Yes | NIPDAU | N/A for Pkg Type | -40 to 125 | SN74AHC14N |
| SN74AHC14N.A | Active | Production | PDIP (N) 14 | 25 TUBE | Yes | NIPDAU | N/A for Pkg Type | -40 to 125 | SN74AHC14N |

| Orderable part number | Status (1) | Material type (2) | Package Pins | Package qty Carrier | RoHS (3) | Lead finish/ Ball material (4) | MSL rating/ Peak reflow (5) | Op temp (°C) | Part marking (6) |
|--------------------------------|---------------|----------------------|-----------------|-----------------------|-------------|--------------------------------------|-----------------------------------|--------------|---|
| SN74AHC14NSR | Active | Production | SOP (NS) 14 | 2000 LARGE T&R | Yes | NIPDAU | Level-1-260C-UNLIM | -40 to 125 | AHC14 |
| SN74AHC14NSR.A | Active | Production | SOP (NS) 14 | 2000 LARGE T&R | Yes | NIPDAU | Level-1-260C-UNLIM | -40 to 125 | AHC14 |
| SN74AHC14PW | Obsolete | Production | TSSOP (PW) 14 | - | - | Call TI | Call TI | -40 to 125 | HA14 |
| SN74AHC14PWR | Active | Production | TSSOP (PW) 14 | 2000 LARGE T&R | Yes | NIPDAU SN | Level-1-260C-UNLIM | -40 to 125 | HA14 |
| SN74AHC14PWR.A | Active | Production | TSSOP (PW) 14 | 2000 LARGE T&R | Yes | NIPDAU | Level-1-260C-UNLIM | -40 to 125 | HA14 |
| SN74AHC14PWRG3 | Active | Production | TSSOP (PW) 14 | 2000 LARGE T&R | Yes | SN | Level-1-260C-UNLIM | -40 to 125 | HA14 |
| SN74AHC14PWRG3.A | Active | Production | TSSOP (PW) 14 | 2000 LARGE T&R | Yes | SN | Level-1-260C-UNLIM | -40 to 125 | HA14 |
| SN74AHC14PWRG4 | Active | Production | TSSOP (PW) 14 | 2000 LARGE T&R | Yes | NIPDAU | Level-1-260C-UNLIM | -40 to 125 | HA14 |
| SN74AHC14PWRG4.A | Active | Production | TSSOP (PW) 14 | 2000 LARGE T&R | Yes | NIPDAU | Level-1-260C-UNLIM | -40 to 125 | HA14 |
| SN74AHC14RGYR | Active | Production | VQFN (RGY) 14 | 3000 LARGE T&R | Yes | NIPDAU | Level-1-260C-UNLIM | -40 to 125 | HA14 |
| SN74AHC14RGYR.A | Active | Production | VQFN (RGY) 14 | 3000 LARGE T&R | Yes | NIPDAU | Level-1-260C-UNLIM | -40 to 125 | HA14 |
| SN74AHC14RGYRG4 | Active | Production | VQFN (RGY) 14 | 3000 LARGE T&R | Yes | NIPDAU | Level-1-260C-UNLIM | -40 to 125 | HA14 |
| SN74AHC14RGYRG4.A | Active | Production | VQFN (RGY) 14 | 3000 LARGE T&R | Yes | NIPDAU | Level-1-260C-UNLIM | -40 to 125 | HA14 |
| SNJ54AHC08J | Active | Production | CDIP (J) 14 | 25 TUBE | No | SNPB | N/A for Pkg Type | -55 to 125 | 5962-9682001QC A SNJ54AHC08J |
| SNJ54AHC08W | Active | Production | CFP (W) 14 | 25 TUBE | No | SNPB | N/A for Pkg Type | -55 to 125 | 5962-9682001QD A SNJ54AHC08W |
| SNJ54AHC14FK | Active | Production | LCCC (FK) 20 | 55 TUBE | No | SNPB | N/A for Pkg Type | -55 to 125 | 5962- 9680201Q2A SNJ54AHC 14FK |
| SNJ54AHC14FK.A | Active | Production | LCCC (FK) 20 | 55 TUBE | No | SNPB | N/A for Pkg Type | -55 to 125 | 5962- 9680201Q2A SNJ54AHC 14FK |
| SNJ54AHC14J | Active | Production | CDIP (J) 14 | 25 TUBE | No | SNPB | N/A for Pkg Type | -55 to 125 | 5962-9680201QC A SNJ54AHC14J |
| SNJ54AHC14J.A | Active | Production | CDIP (J) 14 | 25 TUBE | No | SNPB | N/A for Pkg Type | -55 to 125 | 5962-9680201QC A SNJ54AHC14J |

| Orderable part number | Status (1) | Material type (2) | Package Pins | Package qty Carrier | RoHS (3) | Lead finish/ Ball material (4) | MSL rating/ Peak reflow (5) | Op temp (°C) | Part marking (6) |
|-----------------------------|---------------|----------------------|----------------|-----------------------|-------------|--------------------------------------|-----------------------------------|--------------|------------------------------------|
| SNJ54AHC14W | NRND | Production | CFP (W) 14 | 25 TUBE | No | SNPB | N/A for Pkg Type | -55 to 125 | 5962-9680201QD A SNJ54AHC14W |
| SNJ54AHC14W.A | NRND | Production | CFP (W) 14 | 25 TUBE | No | SNPB | N/A for Pkg Type | -55 to 125 | 5962-9680201QD A SNJ54AHC14W |

⁽¹⁾ **Status:** For more details on status, see our [product life cycle](#).

⁽²⁾ **Material type:** When designated, preproduction parts are prototypes/experimental devices, and are not yet approved or released for full production. Testing and final process, including without limitation quality assurance, reliability performance testing, and/or process qualification, may not yet be complete, and this item is subject to further changes or possible discontinuation. If available for ordering, purchases will be subject to an additional waiver at checkout, and are intended for early internal evaluation purposes only. These items are sold without warranties of any kind.

⁽³⁾ **RoHS values:** Yes, No, RoHS Exempt. See the [TI RoHS Statement](#) for additional information and value definition.

⁽⁴⁾ **Lead finish/Ball material:** Parts may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead finish/Ball material values may wrap to two lines if the finish value exceeds the maximum column width.

⁽⁵⁾ **MSL rating/Peak reflow:** The moisture sensitivity level ratings and peak solder (reflow) temperatures. In the event that a part has multiple moisture sensitivity ratings, only the lowest level per JEDEC standards is shown. Refer to the shipping label for the actual reflow temperature that will be used to mount the part to the printed circuit board.

⁽⁶⁾ **Part marking:** There may be an additional marking, which relates to the logo, the lot trace code information, or the environmental category of the part.

Multiple part markings will be inside parentheses. Only one part marking contained in parentheses and separated by a "~" will appear on a part. If a line is indented then it is a continuation of the previous line and the two combined represent the entire part marking for that device.

Important Information and Disclaimer: The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.

OTHER QUALIFIED VERSIONS OF SN54AHC14, SN74AHC14 :

- Catalog : [SN74AHC14](#)
- Military : [SN54AHC14](#)

NOTE: Qualified Version Definitions:

- Catalog - TI's standard catalog product
- Military - QML certified for Military and Defense Applications

TAPE AND REEL INFORMATION

QUADRANT ASSIGNMENTS FOR PIN 1 ORIENTATION IN TAPE


*All dimensions are nominal

| Device | Package Type | Package Drawing | Pins | SPQ | Reel Diameter (mm) | Reel Width W1 (mm) | A0 (mm) | B0 (mm) | K0 (mm) | P1 (mm) | W (mm) | Pin1 Quadrant |
|-----------------|--------------|-----------------|------|------|--------------------|--------------------|---------|---------|---------|---------|--------|---------------|
| SN74AHC14BQAR | WQFN | BQA | 14 | 3000 | 180.0 | 12.4 | 2.8 | 3.3 | 1.1 | 4.0 | 12.0 | Q1 |
| SN74AHC14DBR | SSOP | DB | 14 | 2000 | 330.0 | 16.4 | 8.35 | 6.6 | 2.4 | 12.0 | 16.0 | Q1 |
| SN74AHC14DGVR | TVSOP | DGV | 14 | 2000 | 330.0 | 12.4 | 6.8 | 4.0 | 1.6 | 8.0 | 12.0 | Q1 |
| SN74AHC14DR | SOIC | D | 14 | 2500 | 330.0 | 16.4 | 6.5 | 9.0 | 2.1 | 8.0 | 16.0 | Q1 |
| SN74AHC14DRG3 | SOIC | D | 14 | 2500 | 330.0 | 16.8 | 6.5 | 9.5 | 2.1 | 8.0 | 16.0 | Q1 |
| SN74AHC14DRG4 | SOIC | D | 14 | 2500 | 330.0 | 16.4 | 6.5 | 9.0 | 2.1 | 8.0 | 16.0 | Q1 |
| SN74AHC14NSR | SOP | NS | 14 | 2000 | 330.0 | 16.4 | 8.45 | 10.55 | 2.5 | 12.0 | 16.2 | Q1 |
| SN74AHC14PWR | TSSOP | PW | 14 | 2000 | 330.0 | 12.4 | 6.9 | 5.6 | 1.6 | 8.0 | 12.0 | Q1 |
| SN74AHC14PWR | TSSOP | PW | 14 | 2000 | 330.0 | 12.4 | 6.9 | 5.6 | 1.6 | 8.0 | 12.0 | Q1 |
| SN74AHC14PWRG3 | TSSOP | PW | 14 | 2000 | 330.0 | 12.4 | 6.9 | 5.6 | 1.6 | 8.0 | 12.0 | Q1 |
| SN74AHC14PWRG4 | TSSOP | PW | 14 | 2000 | 330.0 | 12.4 | 6.9 | 5.3 | 1.6 | 8.0 | 12.0 | Q1 |
| SN74AHC14PWRG4 | TSSOP | PW | 14 | 2000 | 330.0 | 12.4 | 6.9 | 5.6 | 1.6 | 8.0 | 12.0 | Q1 |
| SN74AHC14RGYR | VQFN | RGY | 14 | 3000 | 330.0 | 12.4 | 3.75 | 3.75 | 1.15 | 8.0 | 12.0 | Q1 |
| SN74AHC14RGYRG4 | VQFN | RGY | 14 | 3000 | 330.0 | 12.4 | 3.75 | 3.75 | 1.15 | 8.0 | 12.0 | Q1 |

TAPE AND REEL BOX DIMENSIONS



*All dimensions are nominal

| Device | Package Type | Package Drawing | Pins | SPQ | Length (mm) | Width (mm) | Height (mm) |
|-----------------|--------------|-----------------|------|------|-------------|------------|-------------|
| SN74AHC14BQAR | WQFN | BQA | 14 | 3000 | 210.0 | 185.0 | 35.0 |
| SN74AHC14DBR | SSOP | DB | 14 | 2000 | 353.0 | 353.0 | 32.0 |
| SN74AHC14DGVR | TVSOP | DGV | 14 | 2000 | 353.0 | 353.0 | 32.0 |
| SN74AHC14DR | SOIC | D | 14 | 2500 | 353.0 | 353.0 | 32.0 |
| SN74AHC14DRG3 | SOIC | D | 14 | 2500 | 364.0 | 364.0 | 27.0 |
| SN74AHC14DRG4 | SOIC | D | 14 | 2500 | 353.0 | 353.0 | 32.0 |
| SN74AHC14NSR | SOP | NS | 14 | 2000 | 353.0 | 353.0 | 32.0 |
| SN74AHC14PWR | TSSOP | PW | 14 | 2000 | 353.0 | 353.0 | 32.0 |
| SN74AHC14PWR | TSSOP | PW | 14 | 2000 | 353.0 | 353.0 | 32.0 |
| SN74AHC14PWRG3 | TSSOP | PW | 14 | 2000 | 364.0 | 364.0 | 27.0 |
| SN74AHC14PWRG4 | TSSOP | PW | 14 | 2000 | 367.0 | 367.0 | 35.0 |
| SN74AHC14PWRG4 | TSSOP | PW | 14 | 2000 | 353.0 | 353.0 | 32.0 |
| SN74AHC14RGYR | VQFN | RGY | 14 | 3000 | 360.0 | 360.0 | 36.0 |
| SN74AHC14RGYRG4 | VQFN | RGY | 14 | 3000 | 360.0 | 360.0 | 36.0 |

TUBE


*All dimensions are nominal

| Device | Package Name | Package Type | Pins | SPQ | L (mm) | W (mm) | T (μm) | B (mm) |
|-----------------|--------------|--------------|------|-----|--------|--------|--------|--------|
| 5962-9680201Q2A | FK | LCCC | 20 | 55 | 506.98 | 12.06 | 2030 | NA |
| 5962-9680201QDA | W | CFP | 14 | 25 | 506.98 | 26.16 | 6220 | NA |
| 5962-9682001QDA | W | CFP | 14 | 25 | 506.98 | 26.16 | 6220 | NA |
| SN74AHC14N | N | PDIP | 14 | 25 | 506 | 13.97 | 11230 | 4.32 |
| SN74AHC14N | N | PDIP | 14 | 25 | 506 | 13.97 | 11230 | 4.32 |
| SN74AHC14N.A | N | PDIP | 14 | 25 | 506 | 13.97 | 11230 | 4.32 |
| SN74AHC14N.A | N | PDIP | 14 | 25 | 506 | 13.97 | 11230 | 4.32 |
| SNJ54AHC08W | W | CFP | 14 | 25 | 506.98 | 26.16 | 6220 | NA |
| SNJ54AHC14FK | FK | LCCC | 20 | 55 | 506.98 | 12.06 | 2030 | NA |
| SNJ54AHC14FK.A | FK | LCCC | 20 | 55 | 506.98 | 12.06 | 2030 | NA |
| SNJ54AHC14W | W | CFP | 14 | 25 | 506.98 | 26.16 | 6220 | NA |
| SNJ54AHC14W.A | W | CFP | 14 | 25 | 506.98 | 26.16 | 6220 | NA |



D0014A

PACKAGE OUTLINE

SOIC - 1.75 mm max height

SMALL OUTLINE INTEGRATED CIRCUIT



4220718/A 09/2016

NOTES:

1. All linear dimensions are in millimeters. Dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.
2. This drawing is subject to change without notice.
3. This dimension does not include mold flash, protrusions, or gate burrs. Mold flash, protrusions, or gate burrs shall not exceed 0.15 mm, per side.
4. This dimension does not include interlead flash. Interlead flash shall not exceed 0.43 mm, per side.
5. Reference JEDEC registration MS-012, variation AB.

EXAMPLE BOARD LAYOUT

D0014A

SOIC - 1.75 mm max height

SMALL OUTLINE INTEGRATED CIRCUIT



LAND PATTERN EXAMPLE
SCALE:8X



SOLDER MASK DETAILS

4220718/A 09/2016

NOTES: (continued)

- 6. Publication IPC-7351 may have alternate designs.
- 7. Solder mask tolerances between and around signal pads can vary based on board fabrication site.

EXAMPLE STENCIL DESIGN

D0014A

SOIC - 1.75 mm max height

SMALL OUTLINE INTEGRATED CIRCUIT



SOLDER PASTE EXAMPLE
BASED ON 0.125 mm THICK STENCIL
SCALE:8X

4220718/A 09/2016

NOTES: (continued)

8. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.
9. Board assembly site may have different recommendations for stencil design.

GENERIC PACKAGE VIEW


BQA 14


WQFN - 0.8 mm max height

2.5 x 3, 0.5 mm pitch

PLASTIC QUAD FLATPACK - NO LEAD

This image is a representation of the package family, actual package may vary.
Refer to the product data sheet for package details.





4224636/A 11/2018

NOTES:

1. All linear dimensions are in millimeters. Any dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.
2. This drawing is subject to change without notice.
3. The package thermal pad must be soldered to the printed circuit board for optimal thermal and mechanical performance.

EXAMPLE BOARD LAYOUT


WQFN - 0.8 mm max height

BQA0014A

PLASTIC QUAD FLAT PACK-NO LEAD



LAND PATTERN EXAMPLE
EXPOSED METAL SHOWN
SCALE: 20X



4224636/A 11/2018

NOTES: (continued)

4. This package is designed to be soldered to a thermal pad on the board. For more information, see Texas Instruments literature number SLUA271 (www.ti.com/lit/slua271).
5. Vias are optional depending on application, refer to device data sheet. If any vias are implemented, refer to their locations shown on this view. It is recommended that vias under paste be filled, plugged or tented.

EXAMPLE STENCIL DESIGN

BQA0014A

WQFN - 0.8 mm max height

PLASTIC QUAD FLAT PACK-NO LEAD



SOLDER PASTE EXAMPLE
 BASED ON 0.125 mm THICK STENCIL

EXPOSED PAD
 88% PRINTED COVERAGE BY AREA
 SCALE: 20X

4224636/A 11/2018

NOTES: (continued)

- 6. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.

MECHANICAL DATA

NS (R-PDSO-G**)

PLASTIC SMALL-OUTLINE PACKAGE

14-PINS SHOWN



- NOTES:
- A. All linear dimensions are in millimeters.
 - B. This drawing is subject to change without notice.
 - C. Body dimensions do not include mold flash or protrusion, not to exceed 0,15.

W (R-GDFP-F14)

CERAMIC DUAL FLATPACK



- NOTES:
- A. All linear dimensions are in inches (millimeters).
 - B. This drawing is subject to change without notice.
 - C. This package can be hermetically sealed with a ceramic lid using glass frit.
 - D. Index point is provided on cap for terminal identification only.
 - E. Falls within MIL STD 1835 GDFP1-F14

DGV (R-PDSO-G**)

PLASTIC SMALL-OUTLINE


24 PINS SHOWN



4073251/E 08/00

- NOTES: A. All linear dimensions are in millimeters.
 B. This drawing is subject to change without notice.
 C. Body dimensions do not include mold flash or protrusion, not to exceed 0,15 per side.
 D. Falls within JEDEC: 24/48 Pins – MO-153
 14/16/20/56 Pins – MO-194


DB0014A



PACKAGE OUTLINE

SSOP - 2 mm max height

SMALL OUTLINE PACKAGE



NOTES:

1. All linear dimensions are in millimeters. Any dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.
2. This drawing is subject to change without notice.
3. This dimension does not include mold flash, protrusions, or gate burrs. Mold flash, protrusions, or gate burrs shall not exceed 0.15 mm per side.
4. Reference JEDEC registration MO-150.

EXAMPLE BOARD LAYOUT

DB0014A

SSOP - 2 mm max height

SMALL OUTLINE PACKAGE



LAND PATTERN EXAMPLE
EXPOSED METAL SHOWN
SCALE: 10X



4220762/A 05/2024

NOTES: (continued)

- 5. Publication IPC-7351 may have alternate designs.
- 6. Solder mask tolerances between and around signal pads can vary based on board fabrication site.

EXAMPLE STENCIL DESIGN

DB0014A

SSOP - 2 mm max height

SMALL OUTLINE PACKAGE



SOLDER PASTE EXAMPLE
BASED ON 0.125 mm THICK STENCIL
SCALE: 10X

4220762/A 05/2024

NOTES: (continued)

7. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.
8. Board assembly site may have different recommendations for stencil design.

GENERIC PACKAGE VIEW

FK 20

LCCC - 2.03 mm max height

8.89 x 8.89, 1.27 mm pitch

LEADLESS CERAMIC CHIP CARRIER


This image is a representation of the package family, actual package may vary.
Refer to the product data sheet for package details.



4229370VA\

J 14


GENERIC PACKAGE VIEW
CDIP - 5.08 mm max height
CERAMIC DUAL IN LINE PACKAGE



Images above are just a representation of the package family, actual package may vary.
Refer to the product data sheet for package details.

4040083-5/G


J0014A



PACKAGE OUTLINE

CDIP - 5.08 mm max height

CERAMIC DUAL IN LINE PACKAGE



4214771/A 05/2017

NOTES:

1. All controlling linear dimensions are in inches. Dimensions in brackets are in millimeters. Any dimension in brackets or parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.
2. This drawing is subject to change without notice.
3. This package is hermetically sealed with a ceramic lid using glass frit.
4. Index point is provided on cap for terminal identification only and on press ceramic glass frit seal only.
5. Falls within MIL-STD-1835 and GDIP1-T14.

EXAMPLE BOARD LAYOUT


J0014A

CDIP - 5.08 mm max height

CERAMIC DUAL IN LINE PACKAGE



LAND PATTERN EXAMPLE
NON-SOLDER MASK DEFINED
SCALE: 5X



4214771/A 05/2017

N (R-PDIP-T**)

PLASTIC DUAL-IN-LINE PACKAGE

16 PINS SHOWN



- NOTES:
- A. All linear dimensions are in inches (millimeters).
 - B. This drawing is subject to change without notice.
 - Falls within JEDEC MS-001, except 18 and 20 pin minimum body length (Dim A).
 - The 20 pin end lead shoulder width is a vendor option, either half or full width.

PW0014A



PACKAGE OUTLINE
TSSOP - 1.2 mm max height

SMALL OUTLINE PACKAGE



4220202/B 12/2023

NOTES:

1. All linear dimensions are in millimeters. Any dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.
2. This drawing is subject to change without notice.
3. This dimension does not include mold flash, protrusions, or gate burrs. Mold flash, protrusions, or gate burrs shall not exceed 0.15 mm per side.
4. This dimension does not include interlead flash. Interlead flash shall not exceed 0.25 mm per side.
5. Reference JEDEC registration MO-153.

EXAMPLE BOARD LAYOUT


PW0014A

TSSOP - 1.2 mm max height

SMALL OUTLINE PACKAGE



LAND PATTERN EXAMPLE
EXPOSED METAL SHOWN
SCALE: 10X



4220202/B 12/2023

NOTES: (continued)

6. Publication IPC-7351 may have alternate designs.
7. Solder mask tolerances between and around signal pads can vary based on board fabrication site.

EXAMPLE STENCIL DESIGN

PW0014A

TSSOP - 1.2 mm max height

SMALL OUTLINE PACKAGE



SOLDER PASTE EXAMPLE
BASED ON 0.125 mm THICK STENCIL
SCALE: 10X

4220202/B 12/2023

NOTES: (continued)

8. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.
9. Board assembly site may have different recommendations for stencil design.

GENERIC PACKAGE VIEW


RGY 14

VQFN - 1 mm max height

3.5 x 3.5, 0.5 mm pitch


PLASTIC QUAD FLATPACK - NO LEAD

This image is a representation of the package family, actual package may vary.
Refer to the product data sheet for package details.



4231541/A


RGY0014A



PACKAGE OUTLINE

VQFN - 1 mm max height

PLASTIC QUAD FLATPACK - NO LEAD



4219040/A 09/2015

NOTES:


1. All linear dimensions are in millimeters. Any dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.
2. This drawing is subject to change without notice.
3. The package thermal pad must be soldered to the printed circuit board for thermal and mechanical performance.

EXAMPLE BOARD LAYOUT


RGY0014A

VQFN - 1 mm max height

PLASTIC QUAD FLATPACK - NO LEAD



LAND PATTERN EXAMPLE
SCALE:20X



SOLDER MASK DETAILS

4219040/A 09/2015

NOTES: (continued)


4. This package is designed to be soldered to a thermal pad on the board. For more information, see Texas Instruments literature number SLUA271 (www.ti.com/lit/sl原因271).

EXAMPLE STENCIL DESIGN

RGY0014A

VQFN - 1 mm max height

PLASTIC QUAD FLATPACK - NO LEAD



SOLDER PASTE EXAMPLE
BASED ON 0.125 mm THICK STENCIL

EXPOSED PAD
80% PRINTED SOLDER COVERAGE BY AREA
SCALE:20X

4219040/A 09/2015

NOTES: (continued)

5. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.

重要なお知らせと免責事項

TI は、技術データと信頼性データ (データシートを含みます)、設計リソース (リファレンス デザインを含みます)、アプリケーションや設計に関する各種アドバイス、Web ツール、安全性情報、その他のリソースを、欠陥が存在する可能性のある「現状のまま」提供しており、商品性および特定目的に対する適合性の黙示保証、第三者の知的財産権の非侵害保証を含むいかなる保証も、明示的または黙示的にかかわらず拒否します。

これらのリソースは、TI 製品を使用する設計の経験を積んだ開発者への提供を意図したものです。(1) お客様のアプリケーションに適した TI 製品の選定、(2) お客様のアプリケーションの設計、検証、試験、(3) お客様のアプリケーションに該当する各種規格や、その他のあらゆる安全性、セキュリティ、規制、または他の要件への確実な適合に関する責任を、お客様のみが単独で負うものとし、

上記の各種リソースは、予告なく変更される可能性があります。これらのリソースは、リソースで説明されている TI 製品を使用するアプリケーションの開発の目的でのみ、TI はその使用をお客様に許諾します。これらのリソースに関して、他の目的で複製することや掲載することは禁止されています。TI や第三者の知的財産権のライセンスが付与されている訳ではありません。お客様は、これらのリソースを自身で使用した結果発生するあらゆる申し立て、損害、費用、損失、責任について、TI およびその代理人を完全に補償するものとし、TI は一切の責任を拒否します。

TI の製品は、[TI の販売条件](#)、[TI の総合的な品質ガイドライン](#)、[ti.com](#) または TI 製品などに関連して提供される他の適用条件に従い提供されます。TI がこれらのリソースを提供することは、適用される TI の保証または他の保証の放棄の拡大や変更を意味するものではありません。TI がカスタム、またはカスタマー仕様として明示的に指定していない限り、TI の製品は標準的なカタログに掲載される汎用機器です。

お客様がいかなる追加条項または代替条項を提案する場合も、TI はそれらに異議を唱え、拒否します。

Copyright © 2026, Texas Instruments Incorporated

最終更新日 : 2025 年 10 月