




TPSM8282x、TPSM8282xA 1A/2A/3A 高効率降圧コンバータ MicroSiP™ パワー・モジュール、インダクタ内蔵

1 特長

- 高さ 1.1mm の MicroSiP™ パワー・モジュール
- CISPR 11 class B 準拠
- 最大 95% の効率
- 入力電圧範囲: 2.4V~5.5V
- 出力電圧は 0.6V~4V の範囲で可変
- 固定出力電圧を選択可能: 1.2V、1.8V、2.5V、3.3V
- 動作時静止電流: 4μA
- DCS-Control トポロジ
- 軽負荷時の効率を向上させるパワーセーブ・モードを選択可能
- CCM 動作のための強制 PWM を選択可能
- 100% デューティ・サイクル動作による最小のドロップアウト電圧
- ヒカップ短絡保護機能
- 出力放電
- パワー・グッド出力とウィンドウ・コンパレータ
- ソフト・スタートアップ内蔵
- 過熱保護
- PSPICE モデルを提供: [TPSM82821](#)、[TPSM82822](#)、[TPSM82823](#)
- 2.0mm × 2.5mm × 1.1mm の 10 ピン μSiL パッケージ
- トータル・ソリューション・サイズ: 12mm² (固定出力電圧バージョンの場合)

2 アプリケーション

- 光モジュール
- マシン・ビジョン
- 産業用 PC
- PLC
- 有線ネットワーク



1.8V の出力電圧に設定された固定出力アプリケーション

3 概要

TPSM8282x デバイス・ファミリーは、小さいソリューション・サイズと高い効率を実現できるように最適化された 1A/2A/3A 降圧コンバータ MicroSiP™ パワー・モジュールで構成されています。


この電源モジュールには同期整流降圧型コンバータとインダクタが組み込まれているため、設計を簡素化し、外付け部品を減らして、PCB 面積を削減できます。TPSM8282x には 2 種類のバージョンがあります。第 1 のバージョンにはパワーセーブ・モードがあり、自動的にこのモードに移行して、非常に軽い負荷までの範囲で高い効率を維持し、システムのバッテリーでの動作時間を延長します。第 2 のバージョンである TPSM8282xA は、出力リップルを最小限に抑えるため、すべての電流で連続導通モードを維持する強制 PWM で動作します。PWM モードでは、本コンバータは 4MHz の公称スイッチング周波数で動作します。

パワーセーブ・モードでは、4μA (標準値) の静止電流で動作します。このデバイスは DCS-Control トポロジを使用して、非常に優れた負荷過渡性能と、出力電圧の正確なレギュレーションを実現しています。EN および PG ピンはシーケンシング構成をサポートするため、柔軟なシステム設計が可能です。内蔵のソフト・スタートアップにより、入力電源からの突入電流が減少します。過熱保護およびヒカップ短絡保護機能により、堅牢で信頼性の高いソリューションを実現できます。

製品情報

部品番号 ⁽¹⁾	パッケージ	本体サイズ (公称)
TPSM82821xSILR	μSiL (10)	2.0mm × 2.5mm
TPSM82822xSILR		
TPSM82823xSILR		

(1) 利用可能なすべてのパッケージについては、このデータシートの末尾にある注文情報を参照してください。



TPSM82823 の効率 (出力電圧 1.8V)



Table of Contents

1 特長	1	8.3 Feature Description.....	7
2 アプリケーション	1	8.4 Device Functional Modes.....	10
3 概要	1	9 Application and Implementation	11
4 Revision History	2	9.1 Application Information.....	11
5 Device Comparison Table	3	9.2 Typical Applications.....	11
6 Pin Configuration and Functions	3	10 Power Supply Recommendations	42
7 Specifications	4	11 Layout	42
7.1 Absolute Maximum Ratings.....	4	11.1 Layout Guidelines.....	42
7.2 ESD Ratings.....	4	11.2 Layout Example.....	42
7.3 Recommended Operating Conditions.....	4	12 Device and Documentation Support	44
7.4 Thermal Information.....	4	12.1 Device Support.....	44
7.5 Electrical Characteristics.....	5	12.2 Documentation Support.....	44
7.6 Typical Characteristics.....	6	12.3 Receiving Notification of Documentation Updates.....	44
8 Detailed Description	7	12.4 Trademarks.....	44
8.1 Overview.....	7	12.5 Electrostatic Discharge Caution.....	44
8.2 Functional Block Diagram.....	7	12.6 Glossary.....	44

4 Revision History

資料番号末尾の英字は改訂を表しています。その改訂履歴は英語版に準じています。

Changes from Revision E (May 2021) to Revision F (November 2021)	Page
• FPWM デバイスを含むように先頭ページの概要を更新.....	1
• Added FPWM devices.....	3
• Updated セクション 8.3.1 to clarify the addition of the FPWM devices.....	7
• Added application curves for all new FPWM devices.....	14
• Added tape and reel information for FPWM devices.....	45

Changes from Revision D (March 2021) to Revision E (May 2021)	Page
• TPSM82823 をリリース.....	1
• 「特長」の最初の箇条書き項目を更新.....	1
• 「特長」に <i>PSPICE</i> の箇条書き項目を追加.....	1
• 「アプリケーション」を更新.....	1
• Changed name of the first column of the <i>Device Comparison Table</i> to "Orderable Part Number".....	3
• Fixed slight error in the <i>Functional Block Diagram</i>	7
• Added 式 2	7
• Updated 図 9-1 to have an output capacitor option of 1 × 22 μF.....	11
• Expanded 表 9-1 with more choices of capacitors.....	12
• Added EMI measurement plots to show CISPR compliance.....	14
• Added SOA curves for the TPSM82823.....	33
• Added セクション 12.1.2.1	44

5 Device Comparison Table

ORDERABLE PART NUMBER	OUTPUT VOLTAGE	MODE OF OPERATION	OUTPUT CURRENT
TPSM82821SILR	adjustable	Power save mode	1 A
TPSM828211SILR	1.2 V		
TPSM828212SILR	1.8 V		
TPSM828213SILR	2.5 V		
TPSM828214SILR	3.3 V		
TPSM82821ASILR	adjustable	Forced PWM	2 A
TPSM82822SILR	adjustable	Power save mode	
TPSM828221SILR	1.2 V		
TPSM828222SILR	1.8 V		
TPSM828223SILR	2.5 V		
TPSM828224SILR	3.3 V		
TPSM82822ASILR	adjustable	Forced PWM	3 A
TPSM82823SILR	adjustable	Power save mode	
TPSM82823ASILR	adjustable	Forced PWM	

6 Pin Configuration and Functions




图 6-1. μSiL Package (Top View)

表 6-1. Pin Functions

PIN		I/O	DESCRIPTION
NAME	NO.		
EN	3	I	Device enable pin. To enable the device, this pin needs to be pulled high. Pulling this pin low disables the device. Do not leave floating.
FB	8	I	Feedback pin. This pin must be connected to the center of the output voltage resistor divider. For the fixed output voltage devices, connect this pin directly to the output voltage.
GND	9, 10	PWR	Ground pin
PG	4	O	Power-good open-drain output pin with window comparator. The pullup resistor can be connected to voltages up to 5.5 V. If unused, leave it floating.
VIN	1, 2	PWR	Input voltage pin
VOUT	5, 6, 7	PWR	Output voltage pin

7 Specifications

7.1 Absolute Maximum Ratings

Over operating junction temperature range (unless otherwise noted) ⁽¹⁾

		MIN	MAX	UNIT
Pin voltage	VIN, VOUT, FB, EN, PG ⁽²⁾	–0.3	6	V
ISINK_PG	Sink current at PG pin		1	mA
TJ	Operating junction temperature	–40	125	°C
Tstg	Storage temperature	–55	125	°C

(1) Stresses beyond those listed under *Absolute Maximum Ratings* may cause permanent damage to the device. These are stress ratings only, which do not imply functional operation of the device at these or any other conditions beyond those indicated under *Recommended Operating Conditions*. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability.

(2) All voltage values are with respect to the network ground terminal.

7.2 ESD Ratings

			VALUE	UNIT
V(ESD)	Electrostatic discharge	Human body model (HBM), per ANSI/ESDA/JEDEC JS-001, all pins ⁽¹⁾	±2000	V
		Charged device model (CDM), per JEDEC specification JESD22-C101, all pins ⁽²⁾	±1000	

(1) JEDEC document JEP155 states that 500-V HBM allows safe manufacturing with a standard ESD control process.

(2) JEDEC document JEP157 states that 250-V CDM allows safe manufacturing with a standard ESD control process.

7.3 Recommended Operating Conditions

		MIN	MAX	UNIT
VIN	Input voltage	2.4	5.5	V
VOUT	Output voltage range	0.6	4	V
VPG	Pullup resistor voltage		5.5	V
IOUT	Output current range, TPSM82821, TPSM82821A ⁽¹⁾	0	1	A
	Output current range, TPSM82822, TPSM82822A ⁽¹⁾	0	2	
	Output current range, TPSM82823, TPSM82823A ⁽¹⁾	0	3	
TJ	Junction temperature ⁽¹⁾	–40	125	°C

(1) In applications where high power dissipation and high ambient temperatures are present, the maximum output current must be derated to operate the module within its operating temperature range. See [セクション 11.2.1](#).

7.4 Thermal Information

THERMAL METRIC ⁽¹⁾		TPSM8282x		UNIT
		μSiL (JEDEC 51-7)	TPSM8282xEVM-080 TPSM8282xAEVM-127	
		10-PINS		
R _{θJA}	Junction-to-ambient thermal resistance	92.6	64.3	°C/W
R _{θJC(top)}	Junction-to-case (top) thermal resistance	49.6	n/a ⁽²⁾	°C/W
R _{θJB}	Junction-to-board thermal resistance	27.7	n/a ⁽²⁾	°C/W
Ψ _{JT}	Junction-to-top characterization parameter	5.8	4.3	°C/W
Ψ _{JB}	Junction-to-board characterization parameter	26.9	22.4	°C/W

(1) For more information about traditional and new thermal metrics, see the [Semiconductor and IC Package Thermal Metrics](#) application report.

(2) Not applicable to an EVM.

7.5 Electrical Characteristics

$T_J = -40^{\circ}\text{C}$ to 125°C and $V_{IN} = 2.4\text{ V}$ to 5.5 V . Typical values are at $T_J = 25^{\circ}\text{C}$ and $V_{IN} = 5\text{ V}$, unless otherwise noted.

PARAMETER		TEST CONDITIONS	MIN	TYP	MAX	UNIT
SUPPLY						
I_Q	Quiescent current into the VIN	EN = High, no load, device not switching		4	10	μA
I_{SD}	Shutdown current into the VIN	EN = Low, $T_J = -40^{\circ}\text{C}$ to 85°C		0.05	0.5	μA
I_Q	Quiescent current	EN = High, no load, device switching, FPWM devices		8		mA
V_{UVLO}	Undervoltage lockout threshold	V_{IN} falling	2.1	2.2	2.3	V
	Undervoltage lockout hysteresis	V_{IN} rising		160		mV
T_{JSD}	Thermal shutdown threshold	T_J rising		150		$^{\circ}\text{C}$
	Thermal shutdown hysteresis	T_J falling		20		$^{\circ}\text{C}$
LOGIC INTERFACE EN						
V_{IH}	High-level input voltage		1.0			V
V_{IL}	Low-level input voltage				0.4	V
$I_{kg(EN)}$	Input leakage current into EN pin	EN = High		0.01	0.1	μA
SOFT START, POWER GOOD						
t_{SS}	Soft-start time	Time from EN high to 95% of V_{OUT} nominal		1.25		ms
V_{PGTH}	Power-good lower threshold	V_{PG} rising, V_{FB} referenced to V_{FB} nominal	94%	96%	98%	
		V_{PG} falling, V_{FB} referenced to V_{FB} nominal	90%	92%	94%	
	Power-good upper threshold	V_{PG} falling, V_{FB} referenced to V_{FB} nominal	103%	105%	107%	
		V_{PG} rising, V_{FB} referenced to V_{FB} nominal	108%	110%	112%	
$V_{PG,OL}$	Low-level output voltage	$I_{sink} = 1\text{ mA}$			0.4	V
$I_{kg(PG)}$	Input leakage current into PG pin	$V_{PG} = 5\text{ V}$		0.01	0.1	μA
OUTPUT						
V_{OUT}	Output voltage accuracy	TPSM828211, TPSM828221, PWM mode	1.188	1.2	1.212	V
		TPSM828212, TPSM828222, PWM mode	1.782	1.8	1.818	
		TPSM828213, TPSM828223, PWM mode	2.475	2.5	2.525	
		TPSM828214, TPSM828224, PWM mode	3.267	3.3	3.333	
V_{FB}	Feedback regulation voltage	PWM mode	594	600	606	mV
$I_{kg(FB)}$	Feedback input leakage current	$V_{FB} = 0.6\text{ V}$		0.01	0.05	μA
I_{DIS}	Output discharge current	EN = Low, $V_{SW} = 0.4\text{ V}$	75	400		mA
POWER SWITCH						
$R_{DS(on)}$	High-side FET on-resistance			26		$\text{m}\Omega$
	Low-side FET on-resistance			26		$\text{m}\Omega$
R_{DP}	Dropout resistance	TPSM82821, TPSM82821A, 100% mode. $V_{IN} = 2.7\text{ V}$, $T_J = 25^{\circ}\text{C}$		115	145	$\text{m}\Omega$
		TPSM82822, TPSM82822A, 100% mode. $V_{IN} = 2.7\text{ V}$, $T_J = 25^{\circ}\text{C}$		90	120	
		TPSM82823, TPSM82823A, 100% mode. $V_{IN} = 2.7\text{ V}$, $T_J = 25^{\circ}\text{C}$		70	95	
I_{LIMF}	High-side FET switch current limit	TPSM82821A	1.7	2.1	2.4	A
I_{LIMF}	High-side FET switch current limit	TPSM82821	1.75	2.2	2.75	A
		TPSM82822, TPSM82822A	2.7	3.3	3.9	
		TPSM82823, TPSM82823A	3.7	4.3	5.0	
I_{LIM}	Low-side FET negative current limit, DC	TPSM82821A/TPSM82822A/TPSM82823A		-1.6		A
f_{SW}	PWM switching frequency	$I_{OUT} = 1\text{ A}$		4		MHz

7.6 Typical Characteristics




FIG 7-1. TPSM82821/TPSM82821A Dropout Resistance




FIG 7-2. TPSM82822/TPSM82822A Dropout Resistance




FIG 7-3. TPSM82823/TPSM82823A Dropout Resistance




FIG 7-4. Quiescent Current




FIG 7-5. Shutdown Current

8 Detailed Description

8.1 Overview


The TPSM8282x synchronous step-down converter power module is based on DCS-Control (Direct Control with Seamless transition into power save mode). This is an advanced regulation topology that combines the advantages of hysteretic, voltage, and current mode control.

The DCS-Control topology operates in PWM (pulse width modulation) mode for medium to heavy load conditions and in PSM (power save mode) at light load currents. In PWM, the converter operates with its nominal switching frequency of 4 MHz, having a controlled frequency variation over the input voltage range. As the load current decreases, the converter enters power save mode, reducing the switching frequency and minimizing the quiescent current of the IC to achieve high efficiency over the entire load current range. DCS-Control supports both operation modes using a single building block and, therefore, has a seamless transition from PWM to PSM without effects on the output voltage.

The forced PWM versions of this device, the TPSM8282xA, does not enter PSM (power save mode) at light load currents and stays in CCM (continuous conduction mode) regardless of the output current in order to minimize the output ripple.

The TPSM8282x offers excellent DC voltage regulation and load transient regulation, combined with low output voltage ripple, minimizing interference with RF circuits.

8.2 Functional Block Diagram



(1) Inductance value is 0.47 μH in TPSM82821/TPSM82821A, 0.24 μH in TPSM82822/TPSM82822A and 0.24 μH in TPSM82823/TPSM82823A.

8.3 Feature Description

8.3.1 PWM and PSM Operation

The TPSM8282x includes a fixed on-time (t_{ON}) circuitry. This t_{ON} , in steady-state operation in PWM and PSM modes, is estimated as:

$$t_{ON} = 250\text{ns} \times \frac{V_{OUT}}{V_{IN}} \quad (1)$$

In PWM mode, the TPSM8282x operates with pulse width modulation in continuous conduction mode (CCM) with a t_{ON} shown in 式 1 at medium and heavy load currents. A PWM switching frequency of typically 4 MHz is achieved by this t_{ON} circuitry.

To maintain high efficiency at light loads, the device enters power save mode seamlessly when the load current decreases. This happens when the load current becomes smaller than half the ripple current of the inductor. The output current at which this occurs can be approximated with the following equation:

$$I_{OUT(PSM\text{-}entry)} = \frac{V_{IN} \times t_{ON}}{2} \times \frac{1 - \frac{V_{OUT}}{V_{IN}}}{L} \quad (2)$$

In PSM, the converter operates with a reduced switching frequency and with a minimum quiescent current to maintain high efficiency. The on time in PSM is also based on the same t_{ON} circuitry. The switching frequency in PSM is estimated as:

$$f_{PSM} = \frac{2 \times I_{OUT}}{t_{ON}^2 \times \frac{V_{IN}}{V_{OUT}} \times \frac{V_{IN} - V_{OUT}}{L}} \quad (3)$$

In PSM, the output voltage rises slightly above the nominal output voltage in PWM mode. This effect is reduced by increasing the output capacitance.

The forced PWM version of this device, the TPSM8282xA, does not enter PSM (power save mode) at light load currents and stays in CCM (continuous conduction mode) regardless of the output current in order to minimize the output ripple.

8.3.2 Low Dropout Operation (100% Duty Cycle)

The device offers a low input-to-output voltage differential by entering 100% duty cycle mode. In this mode, the high-side MOSFET switch is constantly turned on. This is particularly useful in battery-powered applications to achieve longest operation time by taking full advantage of the whole battery voltage range. The minimum input voltage to maintain a minimum output voltage is given by:

$$V_{IN(min)} = V_{OUT(min)} + I_{OUT} \times R_{DP} \quad (4)$$

where

- R_{DP} = Resistance from V_{IN} to V_{OUT} , which includes the high-side MOSFET on-resistance and DC resistance of the inductor
- $V_{OUT(min)}$ = Minimum output voltage the load can accept

8.3.3 Soft Start-up

After enabling the device, there is a 250-μs delay before switching starts. Then, an internal soft start-up circuitry ramps up the output voltage which reaches nominal output voltage during the start-up time of 1 ms. This avoids excessive inrush current and creates a smooth output voltage rise slope. It also prevents excessive voltage drops of primary cells and rechargeable batteries with high internal impedance.

The device is able to start into a pre-biased output capacitor. It starts with the applied bias voltage and ramps the output voltage to its nominal value.

8.3.4 Switch Current Limit and Hiccup Short Circuit Protection

The switch current limit prevents the device from high inductor current and from drawing excessive current from the battery or input voltage rail. Excessive current can occur with a shorted or saturated inductor or a heavy load or shorted output circuit condition. If the inductor current reaches the threshold of I_{LIMF} , the high-side MOSFET is turned off and the low-side MOSFET remains off while the inductor current flows through its body diode and quickly ramps down.

When this switch current limit is triggered 32 times, the device stops switching. The device then automatically starts a new start-up after a typical delay time of 128 μ s has passed. This is named HICCUP short-circuit protection. The device repeats this mode until the high load condition disappears.

8.3.5 Undervoltage Lockout

To avoid mis-operation of the device at low input voltages, undervoltage lockout is implemented that shuts down the device at voltages lower than V_{UVLO} .

8.3.6 Thermal Shutdown

The device goes into thermal shutdown and stops the power stage switching when the junction temperature exceeds T_{JSD} . When the device temperature falls below the threshold by 20°C, the device returns to normal operation automatically by switching the power stage again.

8.4 Device Functional Modes

8.4.1 Enable and Disable

The device is enabled by setting the EN pin to a logic high. Accordingly, shutdown mode is forced if the EN pin is pulled low with a shutdown current of typically 50 nA. In shutdown mode, the internal power switches and the entire control circuitry are turned off. An internal switch smoothly discharges the output through the VOUT pin in shutdown mode. Do not leave the EN pin floating.

The typical threshold value of the EN pin is 0.89 V for rising input signal, and 0.62 V for falling input signal.

8.4.2 Output Discharge

The purpose of the output discharge function is to ensure a defined down-ramp of the output voltage when the device is disabled and to keep the output voltage close to 0 V. The output discharge is active when the EN pin is set to a logic low and during thermal shutdown. The discharge is not active in UVLO.

8.4.3 Power Good Output

The device has a power good output. The PG pin goes high impedance once the FB pin voltage is above 96% and less than 105% of the nominal voltage, and is driven low once the voltage falls below typically 92% or higher than 110% of the nominal voltage. 表 8-1 shows the typical PG pin logic. The PG pin is an open-drain output and is specified to sink up to 1 mA. The power good output requires a pullup resistor connecting to any voltage rail less than 5.5 V. The PG signal can be used for sequencing of multiple rails by connecting to the EN pin of other converters. If not used, the PG pin can be left floating or connected to GND.

表 8-1. Power Good Pin Logic

DEVICE STATE		PG LOGIC STATUS	
		HIGH IMPEDANCE	LOW
Enabled (EN = High)	$0.576 \text{ V} \leq V_{FB} \leq 0.63 \text{ V}$	√	
	$V_{FB} < 0.552 \text{ V}$ or $V_{FB} > 0.66 \text{ V}$		√
Shutdown (EN = Low)			√
UVLO	$0.7 \text{ V} \leq V_{IN} < V_{UVLO}$		√
Thermal Shutdown	$T_J > T_{JSD}$		√
Power Supply Removal	$V_{IN} < 0.7 \text{ V}$	√	

The PG pin has a 20-μs deglitch time on the falling edge and a 100-μs delay before PG goes high. See 图 8-1.




图 8-1. Power Good Transient and De-glitch Behavior

9 Application and Implementation

Note

以下のアプリケーション情報は、TI の製品仕様に含まれるものではなく、TI ではその正確性または完全性を保証いたしません。個々の目的に対する製品の適合性については、お客様の責任で判断していただくことになります。お客様は自身の設計実装を検証しテストすることで、システムの機能を確認する必要があります。

9.1 Application Information

The TPSM8282x is a synchronous step-down converter power module. The required power inductor is integrated inside the TPSM8282x. The inductance value is 0.47 μH for the TPSM82821 and TPS82821A, 0.24 μH for the TPSM82822, TPSM82822A, TPSM82823 and TPSM82823A with a $\pm 20\%$ tolerance. The TPSM82821/TPSM82821A, TPSM82822/TPSM82822A and TPSM82823/TPSM82823A are pin-to-pin and BOM-to-BOM compatible with each other.

9.2 Typical Applications

9.2.1 1.8-V Output Application




Figure 9-1. Adjustable Output Application Set at 1.8-V Output Voltage




Figure 9-2. Fixed Output Application Set at 1.8-V Output Voltage

9.2.1.1 Design Requirements

The design guidelines provide a component selection to operate the device within the recommended operating conditions.

Table 9-1 lists the components used for [Figure 9-1](#). Table 9-2 lists the components used for [Figure 9-2](#).

表 9-1. List of Components

REFERENCE	DESCRIPTION	MANUFACTURER
C1	Ceramic capacitor, 4.7 µF, 6.3 V, X7R, size (0603), JMK107BB7475MA	Taiyo Yuden
C2	Ceramic capacitor, 2 × 10 µF, 10 V, X7R, size (0603), GRM188Z71A106MA73D	muRata
	Ceramic capacitor, 1 × 22 µF, 6.3 V, X6S, size (0603), JMK107BC6226MA-T	Taiyo Yuden
C3	Ceramic capacitor, 120 pF, 50 V, size (0603), 06035A121JAT2A	AVX
R1	Resistor, 200 kΩ, 1% accuracy	std
R2	Resistor, 100 kΩ, 1% accuracy	std
R3	Resistor, 100 kΩ, 1% accuracy	std

表 9-2. List of Components

REFERENCE	DESCRIPTION	MANUFACTURER
C1	Ceramic capacitor, 4.7 µF, 6.3 V, X7R, size (0603), JMK107BB7475MA	Taiyo Yuden
C2	Ceramic capacitor, 22 µF, 4 V, X5R, size (0402), AMK105EBJ226MV-F	Taiyo Yuden
R3	Resistor, 100 kΩ, 1% accuracy	std

9.2.1.2 Detailed Design Procedure

9.2.1.2.1 Setting the Output Voltage

Choose resistors R1 and R2 to set the output voltage within a range of 0.6 V to 4 V according to [Equation 5](#). To keep the feedback (FB) net robust from noise, set R2 equal to or lower than 100 kΩ to have at least 6 µA of current in the voltage divider. Lower values of FB resistors achieve better noise immunity, and lower light load efficiency, as explained in the [Design Considerations for a Resistive Feedback Divider in a DC/DC Converter Technical Brief](#).

$$R1 = R2 \times \left(\frac{V_{OUT}}{V_{FB}} - 1 \right) = R2 \times \left(\frac{V_{OUT}}{0.6V} - 1 \right) \quad (5)$$

For devices with a fixed output voltage, the FB pin must be connected to VOUT. R1, R2 and C3 are not needed. The fixed output voltage devices have an internal feed forward capacitor.

9.2.1.2.2 Feedforward capacitor

A feedforward capacitor (C3) is required in parallel with R1. [Equation 6](#) calculates the C3 value. For the recommended 100-kΩ value for R2, a 120-pF feedforward capacitor is used.

$$C3 = \frac{12\mu s}{R2} \quad (6)$$

9.2.1.2.3 Input and Output Capacitor Selection

For the best output and input voltage filtering, ceramic capacitors are required. The input capacitor minimizes input voltage ripple, suppresses input voltage spikes, and provides a stable system rail for the device. A 4.7-µF or larger input capacitor is required. The output capacitor value can range from 10 µF up to 47 µF. The recommended typical output capacitor value is 2 × 10-µF or 1 × 22-µF with an X5R or X7R dielectric. Values over 47 µF can degrade the loop stability of the converter. A feedforward capacitor is required for best transient performance.

Ceramic capacitors have a DC-Bias effect, which has a strong influence on the final effective capacitance. Choose the right capacitor carefully in combination with considering its package size and voltage rating. Ensure that the effective input capacitance is at least 3 μF and the effective output capacitance is at least 5 μF .

9.2.1.3 Application Performance Curves

$T_A = 25^\circ\text{C}$, $V_{IN} = 5\text{ V}$, $V_{OUT} = 1.8\text{ V}$, BOM = 表 9-1 unless otherwise noted.

9.2.1.3.1 TPSM82821 Performance Curves




图 9-3. Efficiency




图 9-4. Efficiency




图 9-5. Efficiency




图 9-6. Efficiency




图 9-7. Efficiency




图 9-8. Efficiency




Figure 9-9. Efficiency




Figure 9-10. Efficiency




Figure 9-11. Safe Operating Area




Figure 9-12. Safe Operating Area




Figure 9-13. Safe Operating Area






Figure 9-14. Safe Operating Area




$V_{OUT} = 3.3\text{ V}$ TPSM82821 $R_{\theta JA} = 64.3^{\circ}\text{C/W}$


9-15. Safe Operating Area




9-16. Load Regulation




9-17. Load Regulation




9-18. Load Regulation



9-19. Load Regulation




9-20. Load Regulation



$V_{OUT} = 0.6\text{ V}$

TPSM82821


图 9-21. Line Regulation



$V_{OUT} = 1.2\text{ V}$

TPSM82821


图 9-22. Line Regulation



$V_{OUT} = 1.8\text{ V}$

TPSM82821


图 9-23. Line Regulation



$V_{OUT} = 3.3\text{ V}$

TPSM82821

图 9-24. Line Regulation




$I_{OUT} = 0\text{ A to }1\text{ A}$

Slew Rate = 2 A/μs

TPSM82821

图 9-25. Load Transient




$I_{OUT} = 0.5\text{ A to }1\text{ A}$

Slew Rate = 2 A/μs

TPSM82821


图 9-26. Load Transient



Horizontal - QPK
 Vertical - QPK
 CISPR 11 Group 1 Class B 3m Limit

$R_{LOAD} = 2.2 \Omega$, $V_{IN} = 5.5 \text{ V}$ (battery supply), $V_{OUT} = 1.8 \text{ V}$,
 tested on TPSM82821EVM-080

9-27. TPSM82821 Radiated Emissions



9-28. Power Supply Rejection Ratio (PSRR)

9.2.1.3.2 TPSM82821A Performance Curves




Figure 9-29. Efficiency




Figure 9-30. Efficiency




Figure 9-31. Efficiency




Figure 9-32. Efficiency




Figure 9-33. Efficiency












Figure 9-34. Efficiency


 **9-35. Efficiency**

 **9-36. Efficiency**

 **9-37. Safe Operating Area**

 **9-38. Safe Operating Area**

 **9-39. Safe Operating Area**

 **9-40. Safe Operating Area**




$V_{OUT} = 3.3 \text{ V}$ **TPSM82821A** $R_{\theta JA} = 64.3^{\circ}\text{C/W}$

9-41. Safe Operating Area




$V_{OUT} = 0.6 \text{ V}$ **TPSM82821A**

9-42. Load Regulation




$V_{OUT} = 1.2 \text{ V}$ **TPSM82821A**

9-43. Load Regulation




$V_{OUT} = 1.8 \text{ V}$ **TPSM82821A**

9-44. Load Regulation




$V_{OUT} = 2.5 \text{ V}$ **TPSM82821A**

9-45. Load Regulation




$V_{OUT} = 3.3 \text{ V}$ **TPSM82821A**


9-46. Load Regulation


 $I_{OUT} = 1\text{ A}$

TPSM82821A


9-47. Output Ripple in PWM Mode

 $I_{OUT} = 0\text{ mA to }1\text{ A}$

TPSM82821A


9-48. Load Sweep

 $I_{OUT} = 0\text{ A to }1\text{ A}$

Slew Rate = 2 A/μs


TPSM82821A

9-49. Load Transient

 $I_{OUT} = \text{no load}$

TPSM82821A

9-50. Start-up / Shutdown without Load

 $I_{OUT} = 1\text{ A}$


TPSM82821A

9-51. Start-up / Shutdown with Resistive Load



TPSM82821A

9-52. Short Circuit, HICCUP Protection Entry / Exit


9.2.1.3.3 TPSM82822 Performance Curves




9-53. Efficiency




9-54. Efficiency




9-55. Efficiency




9-56. Efficiency




9-57. Efficiency




9-58. Efficiency




9-59. Efficiency




9-60. Efficiency




9-61. Safe Operating Area




9-62. Safe Operating Area



9-63. Safe Operating Area




9-64. Safe Operating Area




$V_{OUT} = 3.3\text{ V}$ TPSM82822 $R_{\theta JA} = 64.3^{\circ}\text{C/W}$

9-65. Safe Operating Area




$V_{OUT} = 0.6\text{ V}$ TPSM82822

9-66. Load Regulation




$V_{OUT} = 1.2\text{ V}$ TPSM82822

9-67. Load Regulation




$V_{OUT} = 1.8\text{ V}$ TPSM82822

9-68. Load Regulation




$V_{OUT} = 2.5\text{ V}$ TPSM82822

9-69. Load Regulation




$V_{OUT} = 3.3\text{ V}$ TPSM82822

9-70. Load Regulation




$V_{OUT} = 0.6\text{ V}$ TPSM82822

9-71. Line Regulation




$V_{OUT} = 1.2\text{ V}$ TPSM82822

9-72. Line Regulation




$V_{OUT} = 1.8\text{ V}$ TPSM82822

9-73. Line Regulation




$V_{OUT} = 2.5\text{ V}$ TPSM82822

9-74. Line Regulation




$V_{OUT} = 3.3\text{ V}$ TPSM82822

9-75. Line Regulation



$I_{OUT} = 2\text{ A}$ TPSM82822


9-76. Input and Output Ripple in PWM Mode



$I_{OUT} = 25 \text{ mA}$

TPSM82822


9-77. Input and Output Ripple in PSM Mode



$I_{OUT} = 25 \text{ mA to } 2 \text{ A}$

TPSM82822

9-78. Load Sweep




$I_{OUT} = 0 \text{ A to } 2 \text{ A}$

Slew Rate = 2 A/μs

TPSM82822

9-79. Load Transient




$I_{OUT} = 0.5 \text{ A to } 2 \text{ A}$

Slew Rate = 2 A/μs

TPSM82822


9-80. Load Transient



$I_{OUT} = \text{no load}$

TPSM82822


9-81. Start-up / Shutdown without Load



$I_{OUT} = 2 \text{ A}$

TPSM82822

9-82. Start-up / Shutdown with Resistive Load




Time - 500μs/DIV

D052

TPSM82822


9-83. Short Circuit, HICCU Protection Entry / Exit



Horizontal - QPK
 Vertical - QPK
 CISPR 11 Group 1 Class B 3m Limit

$R_{LOAD} = 1 \Omega$, $V_{IN} = 5.5 \text{ V}$ (battery supply), $V_{OUT} = 1.8 \text{ V}$, tested on TPSM82822EVM-080

9-84. TPSM82822 Radiated Emissions



D053

TPSM82822

9-85. Power Supply Rejection Ratio (PSRR)

9.2.1.3.4 TPSM82822A Performance Curves




Figure 9-86. Efficiency




Figure 9-87. Efficiency




Figure 9-88. Efficiency




Figure 9-89. Efficiency




Figure 9-90. Efficiency












Figure 9-91. Efficiency


 **9-92. Efficiency**

 **9-93. Efficiency**

 **9-94. Safe Operating Area**

 **9-95. Safe Operating Area**

 **9-96. Safe Operating Area**

 **9-97. Safe Operating Area**




$V_{OUT} = 3.3\text{ V}$ TPSM82822A $R_{\theta JA} = 64.3^{\circ}\text{C/W}$

9-98. Safe Operating Area




$V_{OUT} = 0.6\text{ V}$ TPSM82822A

9-99. Load Regulation




$V_{OUT} = 1.2\text{ V}$ TPSM82822A

9-100. Load Regulation




$V_{OUT} = 1.8\text{ V}$ TPSM82822A

9-101. Load Regulation




$V_{OUT} = 2.5\text{ V}$ TPSM82822A

9-102. Load Regulation




$V_{OUT} = 3.3\text{ V}$ TPSM82822A


9-103. Load Regulation

 $I_{OUT} = 2\text{ A}$


TPSM82822A

9-104. Output Ripple in PWM Mode $I_{OUT} = 0\text{ mA to }2\text{ A}$


TPSM82822A

9-105. Load Sweep $I_{OUT} = 0\text{ A to }2\text{ A}$ Slew Rate = $2\text{ A}/\mu\text{s}$


TPSM82822A

9-106. Load Transient $I_{OUT} = \text{no load}$

TPSM82822A

9-107. Start-up / Shutdown without Load $I_{OUT} = 2\text{ A}$

TPSM82822A

9-108. Start-up / Shutdown with Resistive Load

TPSM82822A

9-109. Short Circuit, HICCUP Protection Entry / Exit

9.2.1.3.5 TPSM82823 Performance Curves




图 9-110. Efficiency




图 9-111. Efficiency




图 9-112. Efficiency




图 9-113. Efficiency




图 9-114. Efficiency












图 9-115. Efficiency


图 9-116. Efficiency

图 9-117. Efficiency

图 9-118. Safe Operating Area

图 9-119. Safe Operating Area

图 9-120. Safe Operating Area

图 9-121. Safe Operating Area




$V_{OUT} = 3.3 \text{ V}$ TPSM82823 $R_{\theta JA} = 64.3^{\circ}\text{C/W}$

FIG 9-122. Safe Operating Area




$V_{OUT} = 0.6 \text{ V}$ TPSM82823

FIG 9-123. Load Regulation




$V_{OUT} = 1.2 \text{ V}$ TPSM82823

FIG 9-124. Load Regulation




$V_{OUT} = 1.8 \text{ V}$ TPSM82823

FIG 9-125. Load Regulation




$V_{OUT} = 2.5 \text{ V}$ TPSM82823

FIG 9-126. Load Regulation




$V_{OUT} = 3.3 \text{ V}$ TPSM82823


FIG 9-127. Load Regulation

 $I_{OUT} = 3\text{ A}$


TPSM82823

9-128. Output Ripple in PWM Mode $I_{OUT} = 25\text{ mA}$

TPSM82823


9-129. Output Ripple in PSM Mode $I_{OUT} = 25\text{ mA to }3\text{ A}$

TPSM82823

9-130. Load Sweep $I_{OUT} = 0\text{ A to }3\text{ A}$


Slew Rate = 2 A/μs

TPSM82823

9-131. Load Transient $I_{OUT} = 0.5\text{ A to }3\text{ A}$


Slew Rate = 2 A/μs

TPSM82823

9-132. Load Transient $I_{OUT} = \text{no load}$

TPSM82823

9-133. Start-up / Shutdown without Load




D051

$I_{OUT} = 3\text{ A}$

TPSM82823


9-134. Start-up / Shutdown with Resistive Load



D052

TPSM82823

9-135. Short Circuit, HICcup Protection Entry / Exit



$R_{LOAD} = 0.68\ \Omega$, $V_{IN} = 5.5\text{ V}$ (battery supply), $V_{OUT} = 1.8\text{ V}$, tested on TPSM82823EVM-080

9-136. TPSM82823 Radiated Emissions

9.2.1.3.6 TPSM82823A Performance Curves




图 9-137. Efficiency




图 9-138. Efficiency




图 9-139. Efficiency




图 9-140. Efficiency




图 9-141. Efficiency






图 9-142. Efficiency




$V_{IN} = 2.4\text{ V}$ $T_A = 25^\circ\text{C}$ TPSM82823A

图 9-143. Efficiency




$V_{IN} = 2.4\text{ V}$ $T_A = 85^\circ\text{C}$ TPSM82823A

图 9-144. Efficiency




$V_{OUT} = 0.6\text{ V}$ TPSM82823A $R_{\theta JA} = 64.3^\circ\text{C/W}$

图 9-145. Safe Operating Area




$V_{OUT} = 1.2\text{ V}$ TPSM82823A $R_{\theta JA} = 64.3^\circ\text{C/W}$

图 9-146. Safe Operating Area





$V_{OUT} = 1.8\text{ V}$ TPSM82823A $R_{\theta JA} = 64.3^\circ\text{C/W}$


图 9-147. Safe Operating Area





$V_{OUT} = 2.5\text{ V}$ TPSM82823A $R_{\theta JA} = 64.3^\circ\text{C/W}$


图 9-148. Safe Operating Area


 $V_{OUT} = 3.3\text{ V}$ TPSM82823A $R_{\theta JA} = 64.3\text{ }^{\circ}\text{C/W}$
9-149. Safe Operating Area

 $V_{OUT} = 0.6\text{ V}$ TPSM82823A


9-150. Load Regulation

 $V_{OUT} = 1.2\text{ V}$ TPSM82823A

9-151. Load Regulation

 $V_{OUT} = 1.8\text{ V}$ TPSM82823A

9-152. Load Regulation

 $V_{OUT} = 2.5\text{ V}$ TPSM82823A

9-153. Load Regulation

 $V_{OUT} = 3.3\text{ V}$ TPSM82823A


9-154. Load Regulation



$I_{OUT} = 3\text{ A}$

TPSM82823A


9-155. Output Ripple in PWM Mode



$I_{OUT} = 0\text{ mA to }3\text{ A}$

TPSM82823A

9-156. Load Sweep




$I_{OUT} = 0\text{ A to }3\text{ A}$

Slew Rate = $2\text{ A}/\mu\text{s}$

TPSM82823A


9-157. Load Transient



$I_{OUT} = \text{no load}$

TPSM82823A


9-158. Start-up / Shutdown without Load



$I_{OUT} = 3\text{ A}$

TPSM82823A

9-159. Start-up / Shutdown with Resistive Load



TPSM82823A

9-160. Short Circuit, HICUP Protection Entry / Exit

10 Power Supply Recommendations

The devices are designed to operate from an input supply voltage range between 2.4 V and 5.5 V. The average input current of the TPSM8282x/TPSM8282xA is calculated as:

$$I_{IN} = \frac{1}{\eta} \times \frac{V_{OUT} \times I_{OUT}}{V_{IN}} \quad (7)$$

Ensure that the power supply has a sufficient current rating for the application.


11 Layout

11.1 Layout Guidelines


A proper layout is critical for the operation of any switched mode power supply, especially at high switching frequencies. Therefore, the PCB layout of the TPSM8282x/TPSM8282xA demands careful attention to ensure best performance. A poor layout can lead to issues like bad line and load regulation, instability, increased EMI radiation, and noise sensitivity. Refer to the [Five Steps to a Great PCB Layout for a Step-Down Converter Technical Brief](#) for a detailed discussion of general best practices. Specific recommendations for the device are listed below.

- The input capacitor should be placed as close as possible to the VIN and GND pins of the device. This is the most critical component placement. Route the input capacitor directly to the VIN and GND pins avoiding vias.
- Place the output capacitor ground close to the VOUT and GND pins and route it directly avoiding vias.
- Place the FB resistors, R1 and R2, and the feedforward capacitor C_{FF} close to the FB pin to minimize noise pickup.
- The recommended layout is implemented on the EVM and shown in its [TPSM8282xEVM-080 Evaluation Module User's Guide](#)
- The recommended land pattern for the TPSM8282x/TPSM8282xA is shown at the end of this data sheet. For best manufacturing results, it is important to create the pads as solder mask defined (SMD), when some pins (such as VIN, VOUT, and GND) are connected to large copper planes. Using SMD pads keeps each pad the same size and avoids solder pulling the device during reflow.

11.2 Layout Example



☒ 11-1. TPSM8282xx PCB Layout for the Fixed Output Voltage Devices (BOM from Table 9-2)



☒ 11-2. TPSM8282x/TPSM8282xA PCB Layout for the Adjustable Devices (BOM from Table 9-1 with 1 x 22-μF for C2)

11.2.1 Thermal Consideration

The TPSM8282x/TPSM8282xA module temperature must be kept less than the maximum rating of 125°C. The following are three basic approaches for enhancing thermal performance:

- Improve the power dissipation capability of the PCB design.
- Improve the thermal coupling of the component to the PCB.
- Introduce airflow into the system.

To estimate the approximate module temperature of the TPSM8282x/TPSM8282xA, apply the typical efficiency stated in this data sheet to the desired application condition to compute the power dissipation of the module. Then, calculate the module temperature rise by multiplying the power dissipation by its thermal resistance. Using this method to compute the maximum device temperature, the Safe Operating Area (SOA) graphs demonstrate the required derating in maximum output current at high ambient temperatures. For more details on how to use the thermal parameters in real applications, see the application notes: [Thermal Characteristics of Linear and Logic Packages Using JEDEC PCB Designs](#) and [Semiconductor and IC Package Thermal Metrics](#).

12 Device and Documentation Support

12.1 Device Support

12.1.1 Third-Party Products Disclaimer

TI'S PUBLICATION OF INFORMATION REGARDING THIRD-PARTY PRODUCTS OR SERVICES DOES NOT CONSTITUTE AN ENDORSEMENT REGARDING THE SUITABILITY OF SUCH PRODUCTS OR SERVICES OR A WARRANTY, REPRESENTATION OR ENDORSEMENT OF SUCH PRODUCTS OR SERVICES, EITHER ALONE OR IN COMBINATION WITH ANY TI PRODUCT OR SERVICE.

12.1.2 Development Support

12.1.2.1 Models and Simulators

PSpice® for TI is a design and simulation environment that helps evaluate performance of analog circuits. Create subsystem designs and prototype solutions before committing to layout and fabrication, reducing development cost and time to market.

12.2 Documentation Support

12.2.1 Related Documentation

For related documentation see the following:

Texas Instruments, [TPSM82822EVM-080 Evaluation Module](#), SLVUBR5

12.3 Receiving Notification of Documentation Updates

To receive notification of documentation updates, navigate to the device product folder on [ti.com](#). Click on *Subscribe to updates* to register and receive a weekly digest of any product information that has changed. For change details, review the revision history included in any revised document.

12.4 Trademarks

MicroSiP™ are trademarks of TI.

すべての商標は、それぞれの所有者に帰属します。

12.5 Electrostatic Discharge Caution



This integrated circuit can be damaged by ESD. Texas Instruments recommends that all integrated circuits be handled with appropriate precautions. Failure to observe proper handling and installation procedures can cause damage.

ESD damage can range from subtle performance degradation to complete device failure. Precision integrated circuits may be more susceptible to damage because very small parametric changes could cause the device not to meet its published specifications.


12.6 Glossary

[TI Glossary](#) This glossary lists and explains terms, acronyms, and definitions.


Mechanical, Packaging, and Orderable Information

The following pages include mechanical, packaging, and orderable information. This information is the most current data available for the designated devices. This data is subject to change without notice and revision of this document. For browser-based versions of this data sheet, refer to the left-hand navigation.

13.1 Tape and Reel Information




QUADRANT ASSIGNMENTS FOR PIN 1 ORIENTATION IN TAPE




Device	Package Type	Package Drawing	Pins	SPQ	Reel Diameter (mm)	Reel Width W1 (mm)	A0 (mm)	B0 (mm)	K0 (mm)	P1 (mm)	W (mm)	Pin1 Quadrant
TPSM82821SILR	uSiP	SIL	10	3000	330.0	8.4	2.25	2.75	1.25	4.0	8.0	Q1
TPSM82821ASILR	uSiP	SIL	10	3000	330.0	8.4	2.25	2.75	1.25	4.0	8.0	Q1
TPSM828211SILR	uSiP	SIL	10	3000	330.0	8.4	2.25	2.75	1.25	4.0	8.0	Q1
TPSM828212SILR	uSiP	SIL	10	3000	330.0	8.4	2.25	2.75	1.25	4.0	8.0	Q1
TPSM828213SILR	uSiP	SIL	10	3000	330.0	8.4	2.25	2.75	1.25	4.0	8.0	Q1
TPSM828214SILR	uSiP	SIL	10	3000	330.0	8.4	2.25	2.75	1.25	4.0	8.0	Q1
TPSM82822SILR	uSiP	SIL	10	3000	330.0	8.4	2.25	2.75	1.25	4.0	8.0	Q1
TPSM82822ASILR	uSiP	SIL	10	3000	330.0	8.4	2.25	2.75	1.25	4.0	8.0	Q1
TPSM828221SILR	uSiP	SIL	10	3000	330.0	8.4	2.25	2.75	1.25	4.0	8.0	Q1
TPSM828222SILR	uSiP	SIL	10	3000	330.0	8.4	2.25	2.75	1.25	4.0	8.0	Q1
TPSM828223SILR	uSiP	SIL	10	3000	330.0	8.4	2.25	2.75	1.25	4.0	8.0	Q1
TPSM828224SILR	uSiP	SIL	10	3000	330.0	8.4	2.25	2.75	1.25	4.0	8.0	Q1
TPSM82823SILR	uSiP	SIL	10	3000	330.0	8.4	2.25	2.75	1.25	4.0	8.0	Q1
TPSM82823ASILR	uSiP	SIL	10	3000	330.0	8.4	2.25	2.75	1.25	4.0	8.0	Q1

TAPE AND REEL BOX DIMENSIONS



Device	Package Type	Package Drawing	Pins	SPQ	Length (mm)	Width (mm)	Height (mm)
TPSM82821SILR	uSiP	SIL	10	3000	383.0	353.0	58.0
TPSM82821ASILR	uSiP	SIL	10	3000	383.0	353.0	58.0
TPSM828211SILR	uSiP	SIL	10	3000	383.0	353.0	58.0
TPSM828212SILR	uSiP	SIL	10	3000	383.0	353.0	58.0
TPSM828213SILR	uSiP	SIL	10	3000	383.0	353.0	58.0
TPSM828214SILR	uSiP	SIL	10	3000	383.0	353.0	58.0
TPSM82822SILR	uSiP	SIL	10	3000	383.0	353.0	58.0
TPSM82822ASILR	uSiP	SIL	10	3000	383.0	353.0	58.0
TPSM828221SILR	uSiP	SIL	10	3000	383.0	353.0	58.0
TPSM828222SILR	uSiP	SIL	10	3000	383.0	353.0	58.0
TPSM828223SILR	uSiP	SIL	10	3000	383.0	353.0	58.0
TPSM828224SILR	uSiP	SIL	10	3000	383.0	353.0	58.0
TPSM82823SILR	uSiP	SIL	10	3000	383.0	353.0	58.0
TPSM82823ASILR	uSiP	SIL	10	3000	383.0	353.0	58.0




PACKAGE OUTLINE

SIL0010D

uSIP™ - 1.1 mm max height

MICRO SYSTEM IN PACKAGE



4223961/D 09/2019

NOTES:

MicroSiP is a trademark of Texas Instruments


1. All linear dimensions are in millimeters. Any dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.
2. This drawing is subject to change without notice.
3. Pick and place nozzle $\varnothing$ 0.33 mm or smaller recommended.

EXAMPLE BOARD LAYOUT

SIL0010D

uSIP™ - 1.1 mm max height

MICRO SYSTEM IN PACKAGE



NOTES: (continued)


4. For more information, see Texas Instruments literature number SLUA271 (www.ti.com/lit/sluea271).

EXAMPLE STENCIL DESIGN

SIL0010D

uSIP™ - 1.1 mm max height

MICRO SYSTEM IN PACKAGE



SOLDER PASTE EXAMPLE
BASED ON 0.125 mm THICK STENCIL
SCALE:25X

4223961/D 09/2019

NOTES: (continued)

5. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.

PACKAGING INFORMATION

Orderable part number	Status (1)	Material type (2)	Package Pins	Package qty Carrier	RoHS (3)	Lead finish/ Ball material (4)	MSL rating/ Peak reflow (5)	Op temp (°C)	Part marking (6)
TPSM828211SILR	Active	Production	uSiP (SIL) 10	3000 LARGE T&R	-			-40 to 125	GA1
TPSM828211SILR.A	Active	Production	uSiP (SIL) 10	3000 LARGE T&R	-	Call TI	Call TI	-40 to 125	GA1
TPSM828212SILR	Active	Production	uSiP (SIL) 10	3000 LARGE T&R	-			-40 to 125	GA2
TPSM828212SILR.A	Active	Production	uSiP (SIL) 10	3000 LARGE T&R	-	Call TI	Call TI	-40 to 125	GA2
TPSM828213SILR	Active	Production	uSiP (SIL) 10	3000 LARGE T&R	-			-40 to 125	GA3
TPSM828213SILR.A	Active	Production	uSiP (SIL) 10	3000 LARGE T&R	-	Call TI	Call TI	-40 to 125	GA3
TPSM828214SILR	Active	Production	uSiP (SIL) 10	3000 LARGE T&R	-			-40 to 125	GA4
TPSM828214SILR.A	Active	Production	uSiP (SIL) 10	3000 LARGE T&R	-	Call TI	Call TI	-40 to 125	GA4
TPSM82821ASILR	Active	Production	uSiP (SIL) 10	3000 LARGE T&R	-			-40 to 125	L5
TPSM82821ASILR.A	Active	Production	uSiP (SIL) 10	3000 LARGE T&R	-	Call TI	Call TI	-40 to 125	L5
TPSM82821SILR	Active	Production	uSiP (SIL) 10	3000 LARGE T&R	-			-40 to 125	GA
TPSM82821SILR.A	Active	Production	uSiP (SIL) 10	3000 LARGE T&R	-	Call TI	Call TI	-40 to 125	GA
TPSM828221SILR	Active	Production	uSiP (SIL) 10	3000 LARGE T&R	-			-40 to 125	G91
TPSM828221SILR.A	Active	Production	uSiP (SIL) 10	3000 LARGE T&R	-	Call TI	Call TI	-40 to 125	G91
TPSM828222SILR	Active	Production	uSiP (SIL) 10	3000 LARGE T&R	-			-40 to 125	G92
TPSM828222SILR.A	Active	Production	uSiP (SIL) 10	3000 LARGE T&R	-	Call TI	Call TI	-40 to 125	G92
TPSM828223SILR	Active	Production	uSiP (SIL) 10	3000 LARGE T&R	-			-40 to 125	G93
TPSM828223SILR.A	Active	Production	uSiP (SIL) 10	3000 LARGE T&R	-	Call TI	Call TI	-40 to 125	G93
TPSM828224SILR	Active	Production	uSiP (SIL) 10	3000 LARGE T&R	-			-40 to 125	G94
TPSM828224SILR.A	Active	Production	uSiP (SIL) 10	3000 LARGE T&R	-	Call TI	Call TI	-40 to 125	G94
TPSM82822ASILR	Active	Production	uSiP (SIL) 10	3000 LARGE T&R	-			-40 to 125	L6
TPSM82822ASILR.A	Active	Production	uSiP (SIL) 10	3000 LARGE T&R	-	Call TI	Call TI	-40 to 125	L6
TPSM82822SILR	Active	Production	uSiP (SIL) 10	3000 LARGE T&R	-			-40 to 125	G9
TPSM82822SILR.A	Active	Production	uSiP (SIL) 10	3000 LARGE T&R	-	Call TI	Call TI	-40 to 125	G9
TPSM82823ASILR	Active	Production	uSiP (SIL) 10	3000 LARGE T&R	-			-40 to 125	L7
TPSM82823ASILR.A	Active	Production	uSiP (SIL) 10	3000 LARGE T&R	-	Call TI	Call TI	-40 to 125	L7
TPSM82823SILR	Active	Production	uSiP (SIL) 10	3000 LARGE T&R	-			-40 to 125	KM
TPSM82823SILR.A	Active	Production	uSiP (SIL) 10	3000 LARGE T&R	-	Call TI	Call TI	-40 to 125	KM

⁽¹⁾ **Status:** For more details on status, see our [product life cycle](#).

⁽²⁾ **Material type:** When designated, preproduction parts are prototypes/experimental devices, and are not yet approved or released for full production. Testing and final process, including without limitation quality assurance, reliability performance testing, and/or process qualification, may not yet be complete, and this item is subject to further changes or possible discontinuation. If available for ordering, purchases will be subject to an additional waiver at checkout, and are intended for early internal evaluation purposes only. These items are sold without warranties of any kind.

⁽³⁾ **RoHS values:** Yes, No, RoHS Exempt. See the [TI RoHS Statement](#) for additional information and value definition.

⁽⁴⁾ **Lead finish/Ball material:** Parts may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead finish/Ball material values may wrap to two lines if the finish value exceeds the maximum column width.

⁽⁵⁾ **MSL rating/Peak reflow:** The moisture sensitivity level ratings and peak solder (reflow) temperatures. In the event that a part has multiple moisture sensitivity ratings, only the lowest level per JEDEC standards is shown. Refer to the shipping label for the actual reflow temperature that will be used to mount the part to the printed circuit board.

⁽⁶⁾ **Part marking:** There may be an additional marking, which relates to the logo, the lot trace code information, or the environmental category of the part.

Multiple part markings will be inside parentheses. Only one part marking contained in parentheses and separated by a "--" will appear on a part. If a line is indented then it is a continuation of the previous line and the two combined represent the entire part marking for that device.

Important Information and Disclaimer: The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.

重要なお知らせと免責事項

TI は、技術データと信頼性データ (データシートを含みます)、設計リソース (リファレンス デザインを含みます)、アプリケーションや設計に関する各種アドバイス、Web ツール、安全性情報、その他のリソースを、欠陥が存在する可能性のある「現状のまま」提供しており、商品性および特定目的に対する適合性の黙示保証、第三者の知的財産権の非侵害保証を含むいかなる保証も、明示的または黙示的にかかわらず拒否します。

これらのリソースは、TI 製品を使用する設計の経験を積んだ開発者への提供を意図したものです。(1) お客様のアプリケーションに適した TI 製品の選定、(2) お客様のアプリケーションの設計、検証、試験、(3) お客様のアプリケーションに該当する各種規格や、その他のあらゆる安全性、セキュリティ、規制、または他の要件への確実な適合に関する責任を、お客様のみが単独で負うものとし、TI は一切の責任を拒否します。

上記の各種リソースは、予告なく変更される可能性があります。これらのリソースは、リソースで説明されている TI 製品を使用するアプリケーションの開発の目的でのみ、TI はその使用をお客様に許諾します。これらのリソースに関して、他の目的で複製することや掲載することは禁止されています。TI や第三者の知的財産権のライセンスが付与されている訳ではありません。お客様は、これらのリソースを自身で使用した結果発生するあらゆる申し立て、損害、費用、損失、責任について、TI およびその代理人を完全に補償するものとし、TI は一切の責任を拒否します。

TI の製品は、[TI の販売条件](#)、[TI の総合的な品質ガイドライン](#)、[ti.com](https://www.ti.com) または TI 製品などに関連して提供される他の適用条件に従い提供されます。TI がこれらのリソースを提供することは、適用される TI の保証または他の保証の放棄の拡大や変更を意味するものではありません。TI がカスタム、またはカスタマー仕様として明示的に指定していない限り、TI の製品は標準的なカタログに掲載される汎用機器です。

お客様がいかなる追加条項または代替条項を提案する場合も、TI はそれらに異議を唱え、拒否します。

Copyright © 2026, Texas Instruments Incorporated

最終更新日：2025 年 10 月