









TUSB8043

JAJSD85A - JUNE 2017 - REVISED AUGUST 2017

TUSB8043 4ポートUSB 3.1 Gen1ハフ

特長 1

- 4ポートのUSB 3.1 Gen1ハブ
- USB 2.0ハブ機能

Texas

INSTRUMENTS

- Multiple Transaction Translator (MTT)ハブ:4 つのトランザクション・トランスレータ
- トランザクション・トレンスレータごとに2つの非同期 エンドポイント・バッファ
- サポートされるバッテリ充電
 - デバイダ充電ポート(ACP1、ACP2、ACP3)をサ ポート
 - 上流ポートの未接続時に、DCPまたはACPモード の自動移行モードをサポート
 - Galaxy充電をサポート
 - CDPモード(上流ポート接続時)
 - DCPモード(上流ポート未接続時)
 - DCPモードは中国電気通信業界標準YD/T 1591-2009に準拠
- USB 3.1 Gen1またはUSB 2.0複合デバイスとして の動作をサポート
- ポート単位または一括制御のパワー・スイッチン グ、過電流通知入力
- 4つの外部下流ポートと内部USB 2.0専用ポート で、USB HID to I²C機能をサポート
- USB HIDを介したI²C制御用の内部下流ポートで、 ハイ・スピードおよびフル・スピード動作をサ ポートし、上流ポートに対応するスピードを提供
- I²Cの読み出し/書き込みと、100kおよび400k (デ フォルト)でのEEPROMの読み出しに対するベン ダー要求をサポート
- I²Cマスタでクロック・ストレッチングをサポート
- OTP ROM、シリアルEEPROM、または I²C/SMBusスレーブ・インターフェイスで次のカ スタム構成をサポート
 - VIDおよびPID
 - ポートのカスタマイズ
 - メーカーおよび製品文字列(OTP ROMは除く)
 - シリアル番号(OTP ROMは除く)
- ピン選択か、EEPROMまたはI²C/SMBusスレー ブ・インターフェイスを使用したアプリケーショ ン機能選択
- 128ビットのUniversally Unique Identifier (UUID) を提供
- USB 2.0上流ポート経由でオンボードおよびイ ン・システムのEEPROMプログラミングをサポー ト

- 単一クロック入力、24MHzクリスタルまたはオシ レータ
- 下流ポートはUSB 2.0の構成のみ
- 64ピンQFNパッケージ(RGC)
- 2 アプリケーション

コンピュータ・システム、ドッキング・ステーション、モニ タ、セットトップ・ボックス


3 概要

TUSB8043は4ポートのUSB 3.1 Gen1ハブです。上流 ポートでスーパー・スピードUSBおよびハイ・スピード/フ ル・スピード接続を同時に提供し、下流ポートでスーパー・ スピードUSB、ハイ・スピード、フル・スピード、ロー・スピー ド接続を提供します。ハイ・スピード、フル・スピード、ロー・ スピード接続のみをサポートする電子環境に上流ポートが 接続されている場合、スーパー・スピードUSB接続は下流 ポートで無効化されます。

製品情報⁽¹⁾

型番	パッケージ	本体サイズ(公称)
TUSB8043	VQFN (64)	9.00mm×9.00mm

(1) 利用可能なすべてのパッケージについては、このデータシートの末 尾にある注文情報を参照してください。





Χ

TUSB8043

JAJSD85A – JUNE 2017 – REVISED AUGUST 2017

1	特長	
2	アプ	リケーション1
3	概要	[[] 1
4	改訂	「履歴2
5	概要	- (続き)3
6		Configuration and Functions 4
7	Spe	cifications9
	7.1	Absolute Maximum Ratings9
	7.2	ESD Ratings9
	7.3	······································
	7.4	Thermal Information9
	7.5	Electrical Characteristics, 3.3-V I/O 10
	7.6	Timing Requirements, Power-Up 10
	7.7	Hub Input Supply Current 11
8	Deta	ailed Description 12
	8.1	Overview 12
	8.2	Functional Block Diagram 12
	8.3	Feature Description 13
	8.4	Device Functional Modes 20

	8.5	Register Maps	23
9	Appl	ications and Implementation	38
	9.1	Application Information	38
	9.2	Typical Application	38
10	Pow	er Supply Recommendations	47
	10.1	TUSB8043 Power Supply	47
	10.2	Downstream Port Power	47
	10.3	Ground	47
11	Layo	out	48
	11.1	Layout Guidelines	48
	11.2	Layout Examples	49
12	デバ	イスおよびドキュメントのサポート	51
	12.1	ドキュメントの更新通知を受け取る方法	51
	12.2	コミュニティ・リソース	51
	12.3	商標	51
	12.4	静電気放電に関する注意事項	51
	12.5	Glossary	51
13	メカニ	ニカル、パッケージ、および注文情報	51

4 改訂履歴

資料番号末尾の英字は改訂を表しています。その改訂履歴は英語版に準じています。

2017年6月発行のものから更新



www.tij.co.jp



5 概要(続き)

フル・スピード、ロー・スピード接続のみをサポートする電子環境に上流ポートが接続されている場合、スーパー・スピード USBおよびハイ・スピード接続は下流ポートで無効化されます。

TUSB8043は、ポート別または一括制御のパワー・スイッチングと過電流保護を提供し、バッテリ充電アプリケーションをサポートします。

ポート別電力制御のハブでは、USBホストからの要求に応じて各下流ポートへの電力がオン/オフされます。また、過電流を検出した場合には、影響を受ける下流ポートへの電力だけがオフになります。

ー括制御のハブでは、いずれかのポートで電力が必要になると、すべての下流ポートへの給電をオンにします。下流ポート への給電は、すべてのポートが給電を停止できる状態にならない限り、オフになりません。また、一括制御のハブが過電流 イベントを検出すると、すべての下流ポートへの給電がオフになります。

TUSB8043の下流ポートは、Battery Charging Downstream Port (CDP)ハンドシェイクに対応することで、バッテリ充電ア プリケーションにサポートを提供します。また、上流ポートの未接続時にDedicated Charging Port (DCP)をサポートしま す。DCPモードは、USBバッテリ充電、Galaxy充電、中国電気通信業界標準YD/T 1591-2009をサポートするUSBデバイ スに対応します。上流ポートの未接続時、TUSB8043はさらに、デバイダ充電ポート・モード(ACPxモード)と、ACP3から DCPまでの全モード間の自動移行をサポートします。


TUSB8043は、バッテリ充電サポートなどの機能のためにピン・ストラップ構成を提供しており、OTP ROM、I²C EEPROM、またはI²C/SMBusスレーブ・インターフェイスを介した、PID、VID、カスタム・ポート、PHY構成のカスタマイズを サポートしています。また、I²C EEPROMまたはI²C/SMBusスレーブ・インターフェイスを使用する場合、カスタム文字列を サポートします。

TUSB8043は、内部USB HIDからI²Cへのインターフェイスを介して、接続先のEEPROMのプログラミングをサポートします。

このデバイスは64ピンRGCパッケージで提供されます。0℃~70℃の温度範囲での動作向けには商用バージョンで提供されます。



6 Pin Configuration and Functions





TUSB8043 JAJSD85A – JUNE 2017 – REVISED AUGUST 2017

www.ti.com

Pin Functions

PIN					
NAME NO.		I/O	DESCRIPTION		
Clock and Reset Signals	S				
GRSTz	50	I PU	Global power reset. This reset brings all of the TUSB8043 internal registers to their default states. When GRSTz is asserted, the device is completely nonfunctional.		
XI	62	I	Crystal input. This pin is the crystal input for the internal oscillator. The input may alternately be driven by the output of an external oscillator. When using a crystal a $1-M\Omega$ feedback esistor is required between XI and XO.		
хо	61	0	Crystal output. This pin is the crystal output for the internal oscillator. If XI is driven by an external oscillator this pin may be left unconnected. When using a crystal a 1-M Ω feedback resistor is required between XI and XO.		
USB Upstream Signals					
USB_SSTXP_UP	55	0	USB SuperSpeed transmitter differential pair (positive)		
USB_SSTXM_UP	56	0	USB SuperSpeed transmitter differential pair (negative)		
USB_SSRXP_UP	58	I	USB SuperSpeed receiver differential pair (positive)		
USB_SSRXM_UP	59	I	USB SuperSpeed receiver differential pair (negative)		
USB_DP_UP	53	I/O	USB High-speed differential transceiver (positive)		
USB_DM_UP	54	I/O	USB High-speed differential transceiver (negative)		
USB_R1	64	I	Precision resistor reference. A 9.53-k Ω ±1% resistor should be connected between USB_R1 and GND.		
USB_VBUS	48	I	USB upstream port power monitor. The VBUS detection requires a voltage divider. The signal USB_VBUS must be connected to VBUS through a 90.9-K Ω ±1% resistor, and to ground through a 10-k Ω ±1% resistor from the signal to ground.		
USB Downstream Signa	ls	ļ			
USB_SSTXP_DN1	3	0	USB SuperSpeed transmitter differential pair (positive)		
USB_SSTXM_DN1	4	0	USB SuperSpeed transmitter differential pair (negative)		
USB_SSRXP_DN1	6	1	USB SuperSpeed receiver differential pair (positive)		
USB_SSRXM_DN1	7	1	USB SuperSpeed receiver differential pair (negative)		
USB_DP_DN1	1	I/O	USB High-speed differential transceiver (positive)		
USB_DM_DN1	2	I/O	USB High-speed differential transceiver (negative)		
			USB Port 1 Power On Control for Downstream Power/Battery Charging Enable. The pin is used for control of the downstream power switch for Port 1. This pin be left unconnected if power management is not implemented.		
PWRCTL1/BATEN1	36	I/O, PD	In addition, the value of the pin is sampled at the de-assertion of reset to determine the value of the battery charging support for Port 1 as indicated in the Battery Charging Support register:		
			0 = Battery charging not supported		
			1 = Battery charging supported		
			USB Port 1 Over-Current Detection. This pin is typically connected to the over current output of the downstream port power switch for Port 1.		
			0 = An over current event has occurred		
OVERCUR1z	46	I, PU	1 = An over current event has not occurred		
			When GANGED power management is enabled, this pin or one of the other OVERCURz pins must be connected to the over current output of the power switch or circuit which detects the over current conditions. For the case when another OVERCURz pin is used, this pin can be left unconnected.		
USB_SSTXP_DN2	11	0	USB SuperSpeed transmitter differential pair (positive)		
USB_SSTXM_DN2	12	0	USB SuperSpeed transmitter differential pair (negative)		
USB_SSRXP_DN2	14	I	USB SuperSpeed receiver differential pair (positive)		
USB_SSRXM_DN2	15	I	USB SuperSpeed receiver differential pair (negative)		
USB_DP_DN2	9	I/O	USB High-speed differential transceiver (positive)		
USB_DM_DN2	10	I/O	USB High-speed differential transceiver (negative)		
	I				

TUSB8043 JAJSD85A – JUNE 2017 – REVISED AUGUST 2017 TEXAS INSTRUMENTS

www.ti.com

Pin Functions (continued)

PIN			
NAME	NO.	I/O	DESCRIPTION
			USB Port 2 Power On Control for Downstream Power/Battery Charging Enable. The pin is used for control of the downstream power switch for Port 2. This pin be left unconnected if power management is not implemented.
PWRCTL2/BATEN2 35		I/O, PD	In addition, the value of the pin is sampled at the de-assertion of reset to determine the value of the battery charging support for Port 2 as indicated in the Battery Charging Support register:
			0 = Battery charging not supported
			1 = Battery charging supported
			USB Port 2 Over-Current Detection. This pin is typically connected to the over current output of the downstream port power switch for Port 2.
			0 = An over current event has occurred
OVERCUR2z	47	I, PU	1 = An over current event has not occurred
			When GANGED power management is enabled, this pin or one of the other OVERCURz pins must be connected to the over current output of the power switch or circuit which detects the over current conditions. For the case when another OVERCURz pin is used, this pin can be left unconnected.
USB_SSTXP_DN3	19	0	USB SuperSpeed transmitter differential pair (positive)
USB_SSTXM_DN3	20	0	USB SuperSpeed transmitter differential pair (negative)
USB_SSRXP_DN3	22	I	USB SuperSpeed receiver differential pair (positive)
USB_SSRXM_DN3	23	I	USB SuperSpeed receiver differential pair (negative)
USB_DP_DN3	17	I/O	USB High-speed differential transceiver (positive)
USB_DM_DN3	18	I/O	USB High-speed differential transceiver (negative)
			USB Port 3 Power On Control for Downstream Power/Battery Charging Enable. The pin is used for control of the downstream power switch for Port 3. This pin be left unconnected if power management is not implemented.
PWRCTL3/BATEN3	33	I/O, PD	In addition, the value of the pin is sampled at the de-assertion of reset to determine the value of the battery charging support for Port 3 as indicated in the Battery Charging Support register:
			0 = Battery charging not supported
			1 = Battery charging supported
			USB Port 3 Over-Current Detection. This pin is typically connected to the over current output of the downstream port power switch for Port 3.
			0 = An over current event has occurred
OVERCUR3z	44	I, PU	1 = An over current event has not occurred
			When GANGED power management is enabled, this pin or one of the other OVERCURz pins must be connected to the over current output of the power switch or circuit which detects the over current conditions. For the case when another OVERCURz pin is used, this pin can be left unconnected.
USB_SSTXP_DN4	26	0	USB SuperSpeed transmitter differential pair (positive)
USB_SSTXM_DN4	27	0	USB SuperSpeed transmitter differential pair (negative)
USB_SSRXP_DN4	29	I	USB SuperSpeed receiver differential pair (positive)
USB_SSRXM_DN4	30	I	USB SuperSpeed receiver differential pair (negative)
USB_DP_DN4	24	I/O	USB High-speed differential transceiver (positive)
USB_DM_DN4	25	I/O	USB High-speed differential transceiver (negative)
			USB Port 4 Power On Control for Downstream Power/Battery Charging Enable. The pin is used for control of the downstream power switch for Port 4. This pin be left unconnected if power management is not implemented.
PWRCTL4/BATEN4	32	I/O, PD	In addition, the value of the pin is sampled at the de-assertion of reset to determine the value of the battery charging support for Port 4 as indicated in the Battery Charging Support register:
			0 = Battery charging not supported
			1 = Battery charging supported



Pin Functions (continued)

PIN		1/0	DESCRIPTION		
NAME NO.		I/O	DESCRIPTION		
			USB Port 4 Over-Current Detection. This pin is typically connected to the over current output of the downstream port power switch for Port 4.		
			0 = An over current event has occurred		
OVERCUR4z	43	I, PU	1 = An over current event has not occurred		
			When GANGED power management is enabled, this pin or one of the other OVERCURz pins must be connected to the over current output of the power switch or circuit which detects the over current conditions. For the case when another OVERCURz pin is used, this pin can be left unconnected.		
I ² C/SMBUS I ² C Signals					
			I ² C clock/SMBus clock. Function of pin depends on the setting of the SMBUSz input.		
SCL/SMBCLK	38	I/O, PD	When SMBUSz = 1, this pin acts as the serial clock interface for an I^2C EEPROM.		
SCE/SIMIDCER	50	1/O, FD	When SMBUSz = 0, this pin acts as the serial clock interface for an SMBus host.		
			Can be left unconnected if external interface not implemented.		
			I ² C data/SMBus data. Function of pin depends on the setting of the SMBUSz input.		
SDA/SMBDAT	37	I/O, PD	When SMBUSz = 1, this pin acts as the serial data interface for an I^2C EEPROM.		
OD A OWDDA'I	57	1/O, 1 D	When SMBUSz = 0, this pin acts as the serial data interface for an SMBus host.		
			Can be left unconnected if external interface not implemented.		
			$\rm I^2C/SMBus$ mode select/SuperSpeed USB Suspend Status. The value of the pin is sampled at the de-assertion of reset set I^2C or SMBus mode as follows:		
			$1 = I^2 C$ Mode Selected		
SMBUSz/SS_SUSPEND	39	I/O, PU	0 = SMBus Mode Selected		
_			Can be left unconnected if external interface not implemented.		
			After reset, this signal indicates the SuperSpeed USB Suspend status of the upstream port if enabled through the stsOutputEn bit in the Additional Feature Configuration register. When enabled, a value of 1 indicates the connection is suspended.		
Test and Miscellaneous	Signals	1	· · ·		
			Full power management enable/SMBus address bit 1/SuperSpeed USB Connection Status Upstream port.		
			The value of the pin is sampled at the de-assertion of reset to set the power switch control follows:		
			0 = Power switching and over current inputs supported		
			1 = Power switching and over current inputs not supported		
			Full power management is the ability to control power to the downstream ports of the TUSB8043 using PWRCTL[4:1]/BATEN[4:1].		
FULLPWRMGMTz / FULLAUTOz /	40	I/O, PD	If BATENx = 1 on any port, full power management must be enabled so the value of the terminal is sampled at the de-assertion to initialize the value of the FULLAUTOz bit.		
SMBA1/SS_UP	40	<i>"</i> 0,10	When AUTOENz = 0 and FULLAUTOz = 0: all ACP modes are supported.		
			When AUTOENz = 0 and FULLAUTOz = 1:only highest current ACP mode is used in auto mode.		
			When SMBus mode is enabled, this pin sets the value of the SMBus slave address bit 1.		
			Can be left unconnected if full power management and SMBus are not implemented.		
			After reset, this signal indicates the SuperSpeed USB connection status of the upstream port if enabled through the stsOutputEn bit in the Additional Feature Configuration register. When enabled a value of 1 indicates the upstream port is connected to a SuperSpeed USB capable port.		
			Note: Power switching must be supported for battery charging applications.		
			Power Control Polarity.		
PWRCTL_POL	41	I/O, PU	The value of the pin is sampled at the de-assertion of reset to set the polarity of PWRCTL[4:1].		
			0 = PWRCTL polarity is active low		
			1 = PWRCTL polarity is active high		

TUSB8043 JAJSD85A – JUNE 2017 – REVISED AUGUST 2017 TEXAS INSTRUMENTS

www.ti.com

Pin Functions (continued)

PIN		1/0	DESCRIPTION	
NAME	NO.	1/0	DESCRIPTION	
			Ganged operation enable/SMBus Address bit 2/HS Connection Status Upstream Port.	
			The value of the pin is sampled at the de-assertion of reset to set the power switch and over current detection mode as follows:	
			0 = Individual power control supported when power switching is enabled	
			1 = Power control gangs supported when power switching is enabled	
GANGED/SMBA2/ HS_UP	42	I/O, PD	When SMBus mode is enabled using SMBUSz, this pin sets the value of the SMBus slave address bit 2.	
			After reset, this signal indicates the High-speed USB connection status of the upstream port if enabled through the stsOutputEn bit in Additional Feature Configuration register. When enabled, a value of 1 indicates the upstream port is connected to a High-speed USB capable port.	
			Note: Individual power control must be enabled for battery charging applications.	
			Automatic Charge Mode Enable/HS Suspend Status.	
	45	I/O, PU	The value of the pin is sampled at the de-assertion of reset to determine if automatic mode is enabled as follows:	
AUTOENz/			0 = Automatic Mode is enabled on ports that are enabled for battery charging when the hub is unconnected. Please note that CDP is not supported on Port 1 when operating in Automatic mode.	
HS_SUSPEND			1 = Automatic Mode is disabled	
			This value is also used to set the autoEnz bit in the Battery Charging Support Register.	
			After reset, this signal indicates the High-speed USB Suspend status of the upstream port if enabled through the stsOutputEn bit in Additional Feature Configuration register. When enabled, a value of 1 indicates the connection is suspended.	
TEST	49	I, PD	This pin is reserved for factory test. It is suggested to have this pin pulled down to ground on PCB.	
Power and Ground Sign	als			
VDD	5, 8, 13, 21, 28, 31, 51, 57	PWR	1.1-V power rail	
VDD33	16, 34, 52, 63	PWR	3.3-V power rail	
VSS (Thermal Pad)		PWR	Ground. Thermal pad must be connected to ground.	
NC	60		No connect, leave floating	



7 Specifications

7.1 Absolute Maximum Ratings⁽¹⁾

over operating free-air temperature range (unless otherwise noted)

		MIN	MAX	UNIT
	V _{DD} Steady-state supply voltage	-0.3	1.4	V
Supply Voltage Range	V _{DD33} Steady-state supply voltage	-0.3	3.8	V
	USB_SSRXP_UP, USB_SSRXN_UP, USB_SSRXP_DN[4:1], USB_SSRXN_DP[4:1] and USB_VBUS terminals	-0.3	1.4	V
Voltage Range	XI terminals	-0.3	2.45	V
	All other terminals	-0.3	3.8	V
Storage temperature, T _{st}	q	-65	150	°C

(1) Stresses beyond those listed under Absolute Maximum Ratings may cause permanent damage to the device. These are stress ratings only, which do not imply functional operation of the device at these or any other conditions beyond those indicated under Recommended Operating Conditions. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability.

7.2 ESD Ratings

			VALUE	UNIT
		Human body model (HBM), per ANSI/ESDA/JEDEC JS-001 ⁽¹⁾	±2000	
V _(ESD)	Electrostatic discharge	Charged device model (CDM), per JEDEC specification JESD22-C101 $^{\left(2\right) }$	±500	V

(1) JEDEC document JEP155 states that 500-V HBM allows safe manufacturing with a standard ESD control process.

(2) JEDEC document JEP157 states that 250-V CDM allows safe manufacturing with a standard ESD control process.

7.3 Recommended Operating Conditions

over operating free-air temperature range (unless otherwise noted)

			MIN	NOM	MAX	UNIT
VDD ⁽¹⁾	1.1V supply voltage		0.99	1.1	1.26	V
VDD33	3.3V supply voltage		3	3.3	3.6	V
USB_VBUS	Voltage at USB_VBUS PAD		0		1.155	V
T _A	Operating free-air temperature	TUSB8043	0		70	°C
TJ	Operating junction temperature		-40		105	°C

(1) A 1.05-V, 1.1-V, or 1.2-V supply may be used as long as minimum and maximum supply conditions are met.

7.4 Thermal Information

		TUSB8043	
	THERMAL METRIC ⁽¹⁾	RGC	UNIT
		64 PINS	
$R_{\theta JA}$	Junction-to-ambient thermal resistance	26	°C/W
$R_{\theta JCtop}$	Junction-to-case (top) thermal resistance	11.5	°C/W
$R_{\theta JB}$	Junction-to-board thermal resistance	5.3	°C/W
ΨJT	Junction-to-top characterization parameter	0.2	°C/W
ΨJB	Junction-to-board characterization parameter	5.2	°C/W
R _{0JCbot}	Junction-to-case (bottom) thermal resistance	1.0	°C/W

(1) For more information about traditional and new thermal metrics, see the Semiconductor and IC Package Thermal Metrics application report.



7.5 Electrical Characteristics, 3.3-V I/O

over operating free-air temperature range (unless otherwise noted)

	PARAMETER	OPERATION	TEST CONDITIONS	MIN	TYP	MAX	UNIT
VIH	High-level input voltage ⁽¹⁾	VDD33		2		VDD33	V
VIL	Low-level input voltage ⁽¹⁾	VDD33		0		0.8	V
VI	Input voltage			0		VDD33	V
Vo	Output voltage ⁽²⁾			0		VDD33	V
t _t	Input transition time $(t_{rise} and t_{fall})$			0		25	ns
V_{hys}	Input hysteresis ⁽³⁾					0.13 x VDD33	V
V _{OH}	High-level output voltage	VDD33	I _{OH} = -4 mA	2.4			V
V _{OL}	Low-level output voltage	VDD33	$I_{OL} = 4 \text{ mA}$			0.4	V
I _{OZ}	High-impedance, output current ⁽²⁾	VDD33	$V_{I} = 0$ to VDD33			±20	μA
I _{OZP}	High-impedance, output current with internal pullup or pulldown resistor ⁽⁴⁾	VDD33	$V_1 = 0$ to VDD33			±250	μA
I _I	Input current ⁽⁵⁾	VDD33	$V_{I} = 0$ to VDD33			±15	μA
R_{PD}	Internal pull-down resister			13.5	19	27.5	KΩ
R_{PU}	Internal pull-up resistor			14.5	19	25	KΩ

Applies to external inputs and bidirectional buffers. (1)

Applies to external outputs and bidirectional buffers. (2)

(3) Applies to GRSTz.

(4) Applies to pins with internal pullups/pulldowns.

(5) Applies to external input buffers.


7.6 Timing Requirements, Power-Up

PARAMETER	DESCRIPTION	MIN	TYP MAX	UNIT
t _{d1}	VDD33 stable before VDD stable ⁽¹⁾	See ⁽²⁾		ms
t _{d2}	VDD and VDD33 stable before de-assertion of GRSTz	3		ms
t _{su_io}	Setup for MISC inputs ⁽³⁾ sampled at the de-assertion of GRSTz	0.1		μs
t _{hd_io}	Hold for MISC inputs $^{(3)}$ sampled at the de-assertion of GRSTz	0.1		μs
t _{VDD33_RAMP}	VDD33 supply ramp requirements	0.2	100	ms
t _{VDD_RAMP}	VDD supply ramp requirements	0.2	100	ms

(1) An active reset is required if the VDD33 supply is stable before the VDD11 supply. This active Reset shall meet the 3ms power-up delay counting from both power supplies being stable to the de-assertion of GRSTz. There is no power-on relationship between VDD33 and VDD unless GRSTz is only connected to a capacitor to GND. Then VDD must

(2) be stable minimum of 10 µs before the VDD33.

MISC pins sampled at de-assertion of GRSTz: BATEN[4:1], AUTOENz, FULLPWRMGMTz, GANGED, SMBUSz, and PWRCTL_POL. (3)







7.7 Hub Input Supply Current

Typical values measured at $T_{\rm A}$ = 25°C

DADAMETED	VDD33	VDD	
PARAMETER	3.3 V	1.1 V	UNIT
LOW POWER MODES		;	
Power On (after Reset)	3	30	mA
Upstream Disconnect	3	24	mA
Suspend	3	30	mA
ACTIVE MODES (US state / DS State)			
3.0 host / 1 SS Device and Hub in U1 / U2	45	240	mA
3.0 host / 1 SS Device and Hub in U0	45	356	mA
3.0 host / 2 SS Devices and Hub in U1 / U2	45	301	mA
3.0 host / 2 SS Devices and Hub in U0	45	457	mA
3.0 host / 3 SS Devices and Hub in U1 / U2	45	372	mA
3.0 host / 3 SS Devices and Hub in U0	45	563	mA
3.0 host / 4 SS Devices and Hub in U1 / U2	45	440	mA
3.0 host / 4 SS Devices and Hub in U0	45	672	mA
3.0 host / 1 SS Device in U0 and 1 HS Device	84	372	mA
3.0 host / 2 SS Devices in U0 and 2 HS Devices	95	512	mA
2.0 host / HS Device	45	55	mA
2.0 host / 4 HS Devices	76	74	mA




8 Detailed Description

8.1 Overview

The TUSB8043 is a four-port USB 3.1 Gen1 compliant hub. It provides simultaneous SuperSpeed USB and highspeed/full-speed connections on the upstream port and provides SuperSpeed USB, high-speed, full-speed, or low-speed connections on the downstream ports. When the upstream port is connected to an electrical environment that only supports high-speed or full-speed/low-speed connections, SuperSpeed USB connectivity is disabled on the downstream ports. When the upstream port is connected to an electrical environment that only supports full-speed/low-speed connections, SuperSpeed USB and high-speed connectivity are disabled on the downstream ports.

8.2 Functional Block Diagram





8.3 Feature Description

8.3.1 Battery Charging Features

The TUSB8043 provides support for USB Battery Charging (BC1.2) and custom charging. Battery charging support may be enabled on a per port basis through the REG_6h(batEn[3:0]).

USB Battery charging support includes both Charging Downstream Port (CDP) and Dedicated Charging Port (DCP) modes. The DCP mode is compliant with the Chinese Telecommunications Industry Standard YD/T 1591-2009. CDP is enabled when the upstream port has detected valid VBUS, configured, and host sets port power. When the upstream port is not connected and battery charging support is enabled, the TUSB8043 will enable DCP mode.

In addition to USB Battery charging (BC1.2), the TUSB8043 supports custom charging indications: Divider Charging (ACP3, ACP2, ACP1 modes), and Galaxy compatible charging. These custom charging modes are only supported when upstream port is unconnected and AUTOMODE is enabled. When in AUTOMODE and upstream port is disconnected, the port will automatically transition from ACP mode to the DCP mode depending on the portable device connected. The divided mode places a fixed DC voltage on the ports DP and DM signals which allows some devices to identify the capabilities of the charger. The default divider mode indicates support for up to 10W (ACP3). The divider mode can be configured to report a lower-current setting (up to 5 W) through REG_0Ah (HiCurAcpModeEn).

When the upstream port is not connected and battery charging support is enabled for a port, the TUSB8043 drives the port power enable active. If AUTOMODE is disabled, then DCP mode is used. If AUTOMODE is enabled and FullAutoEn bit is cleared (Reg_25h Bit 0), then TUSB8043 will start with highest enabled divider current mode (ACPx). The TUSB8043 will remain in highest current mode as long as a pull-up is not detected on DP pin. If an pull-up is detected on DP pin, then TUSB8043 will drive the port power enable inactive and switch to Galaxy mode, if enabled, or to DCP mode if Galaxy mode is disabled. The TUSB8043 will again drive the port power enable active. The TUSB8043 will remain in Galaxy mode as long as no pull-up is detected on DP pin. If an pull-up is detected on DP pin, then TUSB8043 will drive the port power enable inactive and transition to DCP mode. The TUSB8043 will again drive the port power enable inactive and transition to DCP mode. The TUSB8043 will again drive the port power enable active. In DCP mode, the TUSB8043 will look for a pull-up detected on DP pin or RxVdat. If a pull-up or RxVdat is detected on DP, the TUSB8043 will drive the port power enable inactive and transition back to ACPx mode. This sequence will repeat until upstream port is connected.

When Automatic mode is enabled and full automatic mode (FullAutoEn Reg_25h bit 0) is enabled, TUSB8043 will perform same sequence described in previous paragraph with the addition of attempting all supported ACPx modes before sequencing to Galaxy Mode (if enabled) or DCP mode.

The supported battery charging modes when TUSB8043 configured for SMBus or external EEPROM is detailed in Battery Charging Modes with SMBus/EEPROM Table.

The supported battery charging modes when TUSB8043 configured for I2C but without an external EEPROM is determined by the sampled state of the pins. These modes are detailed in Battery Charging Modes without EEPROM Table.



Feature Description (continued)

Table 1. TUSB8043 Battery Charging Modes with SMBus or I2C EEPROM

batEn[n] Reg_06h Bits 3:0	Upstream VBUS	HiCurAcpMode En Reg_0Ah Bit 4	autoModeEnz Reg_0Ah Bit 1	FullAutoEn Reg_25h Bit 0	Galaxy_Enz Reg_25h Bit 1	Battery Charging Mode Port x (x = n + 1)
0	Don't Care	Don't Care	Don't Care	Don't Care	Don't Care	No Charging support
1	> 4V	Don't Care	Don't Care	Don't Care	Don't Care	CDP
1	< 4V	Don't Care	1	Don't Care	Don't Care	DCP
1	< 4V	0	0	1	1	AUTOMODE enabled. Sequences through all ACPx modes and DCP with the exception of ACP3 Alternate ACP2, ACP1, DCP
1	< 4V	1	0	1	1	AUTOMODE enabled. Sequences through all ACPx modes and DCP. Alternate ACP3, ACP2, ACP1, DCP
1	< 4 V	0	0	0	1	AUTOMODE enabled. Sequences between ACP2 and DCP. Alternate ACP2, DCP
1	< 4V	1	0	0	1	AUTOMODE enabled. Sequences between ACP3 and DCP. Alternate ACP3, DCP
1	< 4V	0	0	1	0	AUTOMODE enabled with Galaxy compatible charging support. Alternate ACP2, ACP1, Galaxy, DCP.
1	< 4V	1	0	1	0	AUTOMODE enabled with Galaxy compatible charging support. Alternate ACP3, ACP2, ACP1, Galaxy, DCP
1	< 4V	0	0	0	0	AUTOMODE enabled with Galaxy compatible charging support. Alternate ACP2, Galaxy, DCP
1	< 4V	1	0	0	0	AUTOMODE enabled with Galaxy compatible charging support. Alternate ACP3, Galaxy, DCP

Table 2. TUSB8043 Battery Charging Modes without EEPROM

BATEN[3:0] pins	Upstream VBUS	AUTOENz pin	FULLAUTO2 pin	Battery Charging Mode Port x (x = n + 1)
0	Don't Care	Don't Care	Don't Care	No Charging support
1	> 4V	Don't Care	Don't Care	CDP
1	< 4V	1	0	DCP
1	< 4V	0	0	AUTOMODE enabled with Galaxy compatible charging support. Sequences through all ACPx modes. Alternate ACP3, ACP2, ACP1, Galaxy, DCP.
1	< 4V	0	1	AUTOMODE enabled with Galaxy compatible charging support. Alternate ACP3, Galaxy, DCP
1	< 4V	1	1	AUTOMODE enabled. Sequences through all ACPx modes. Alternate ACP3, ACP2, ACP1, DCP.



8.3.2 USB Power Management

The TUSB8043 can be configured for power switched applications using either per-port (Full power managed) or ganged power-enable controls and over-current status inputs. When battery charge is enabled, the TUSB8043 will always function in full power managed.

Power switch support is enabled by REG_5h (fullPwrMgmtz) and the per-port or ganged mode is configured by REG_5h(ganged).

The TUSB8043 supports both active high and active low power-enable controls. The PWRCTL[4:1] polarity is configured by REG_Ah(pwrctlPol).

8.3.3 I²C Programming Support Using Internal Hid to I²C Interface

The TUSB8043 I²C programming mode is supported using class-specific requests through the HID interface. The HID's embedded port will be numbered 1 greater than the highest numbered exposed port. The internal HID to I²C function of the TUSB8043 does not have an interrupt OUT endpoint. The TUSB8043 supports *GET REPORT* (*Input*) through the HID interrupt and control endpoints. The *GET REPORT* (*Feature*) and *SET REPORT* (*Output*) occurs through the control endpoint.

COMMAND	bmRequestType	bRequest	wValue	windex	wLength	DATA
Setup field Offset	Offset = 0	Offset = 1	Offset = 2	Offset = 4	Offset = 6	N/A
GET REPORT	A1H	01H	0100H – input 0300H - feature	0000H	Report Length	Report
SET REPORT	21H	09H	0200H – output	0000H	Report Length	Report

Table 3. HID Requests I²C Programming Support

Other HID class specific requests are optional and not supported (SET IDLE, SET PROTOCOL, GET IDLE, GET PROTOCOL) . Also report IDs are not required since all requests are not interleaved.

TUSB8043 JAJSD85A – JUNE 2017 – REVISED AUGUST 2017



8.3.3.1 SET REPORT (Output)

Report length includes overhead bytes (1 byte of opcode, 1 byte of device address and 2 bytes of data length) and must match the number of bytes sent in the data stage or the request will be stalled.

- 1-byte opcode
 - 0x01 read I2C
 - 0x02 write I2C with stop
 - 0x03 write I2C without stop (use to set sub-address prior to read)
- 1-byte I2C slave (7-bit) address
- 2-byte I2C transaction data length
- "length" bytes of Data for a write, but none for a read.

Set Report status stage reports only the status of the receipt and validity of the request, not the status of the I²C transaction. As long as the fields construct a valid request, the status stage will be Acked by a null packet. Otherwise, it will be STALLed. For example, if the report_length is longer than the amount of data sent before the status stage or the wLength is greater than the number of bytes of data sent in the data stage, the status stage will be STALLed. If the number of bytes sent in the data stage is greater than wLength or report_length, the data stage will be STALLED.

Software shall ensure properly formatted commands and data responses. The sum of the start address and wLength shall be less than the total size of the address range of the target device in a properly formatted command. Hardware shall wrap any data addresses above FFFFh and shall discard any data transmitted greater than wLength and return STALL. A STALL will also be returned if opcode is 00h.

The I²C master that performs the I²C reads and writes initiated through USB HID interface supports clock stretching. It operates at 400 kHz by default, but can be configured for 100 kHz through eFuse or register.

If the TUSB8043 is suspended (L2) by the USB host, the USB HID interface must enter suspend, but the I²C master shall remain active while attempting to complete an active I²C write request. An active I²C read request may be aborted if the TUSB8043 enters USB suspend state. Per the USB specification, the USB host should not suspend the HID interface while an I²C read or write is still in progress. The USB HID interface shall refuse requests to enter USB 2.0 sleep mode (L1) while an I²C read or write is in progress.

8.3.3.2 GET REPORT (Feature)

This HID Report will always return a 2-byte constant (0x82FF) which can be used to identify compatible HID devices even if the customer changes the VID/PID.

8.3.3.3 GET REPORT (Input)

A report length of one reports the status byte only. To receive a report with data, the report length must be the length of the data, plus one byte for status and two bytes for the length field.

- 1-byte Status
 - 0 Success
 - 1 Fail timeout (35 ms)
 - 2 Fail Address nak
 - 3 Fail data nak
- 2-byte length
- "length" bytes of Data for a read, but not for a write or a feature report.

A Get Report (input) request is required for both read and write. The interrupt endpoint will NAK until the I²C transaction is complete, so that it can report length, data for a read, and final status.



8.3.4 One Time Programmable (OTP) Configuration

The TUSB8043 allows device configuration through one time programmable non-volatile memory (OTP). The programming of the OTP is supported using vendor-defined USB device requests. For details using the OTP features please contact your TI representative.

Table 4 provides a list features which may be configured using the OTP.

Table 4. OTP Configurable Features

CONFIGURATION REGISTER OFFSET	BIT FIELD	DESCRIPTION
REG_01h	[7:0]	Vendor ID LSB
REG_02h	[7:0]	Vendor ID MSB
REG_03h	[7:0]	Product ID LSB
REG_04h	[7:0]	Product ID MSB
REG_07h	[0]	Port removable configuration for downstream ports 1. OTP configuration is inverse of rmbl[3:0], i.e. 1 = not removable, 0 = removable.
REG_07h	[1]	Port removable configuration for downstream ports 2. OTP configuration is inverse of rmbl[3:0], i.e. 1 = not removable, 0 = removable.
REG_07h	[2]	Port removable configuration for downstream ports 3. OTP configuration is inverse of rmbl[3:0], i.e. 1 = not removable, 0 = removable.
REG_07h	[3]	Port removable configuration for downstream ports 4. OTP configuration is inverse of rmbl[3:0], i.e. 1 = not removable, 0 = removable.
REG_08h	[3:0]	Port used Configured register.
REG_0Ah	[3]	Enable Device Attach Detection
REG_0Ah	[4]	High-current divider mode enable.
REG_0Bh	[0]	USB 2.0 port polarity configuration for downstream ports 1.
REG_0Bh	[1]	USB 2.0 port polarity configuration for downstream ports 2.
REG_0Bh	[2]	USB 2.0 port polarity configuration for downstream ports 3.
REG_0Bh	[3]	USB 2.0 port polarity configuration for downstream ports 4.
REG_25h	[4:0]	Device Configuration Register 3
REG_26h	[3:0]	USB2.0 Only Port Register
REG_F0h	[3:1]	USB power switch power-on delay.

TUSB8043


JAJSD85A-JUNE 2017-REVISED AUGUST 2017



www.ti.com

8.3.5 Clock Generation

The TUSB8043 accepts a crystal input to drive an internal oscillator or an external clock source. If a clock is provided to XI instead of a crystal, XO is left open. Otherwise, if a crystal is used, the connection needs to follow the guidelines below. Since XI and XO are coupled to other leads and supplies on the PCB, it is important to keep them as short as possible and away from any switching leads. It is also recommended to minimize the capacitance between XI and XO. This can be accomplished by shielding C1 and C2 with the clean ground lines.



Copyright © 2016, Texas Instruments Incorporated

Figure 2. TUSB8043 Clock



8.3.6 Crystal Requirements

The crystal must be fundamental mode with load capacitance of 12 pF - 24 pF and frequency stability rating of \pm 100 PPM or better. To ensure proper startup oscillation condition, a maximum crystal equivalent series resistance (ESR) of 50 Ω is recommended. A parallel load capacitor should be used if a crystal source is used. The exact load capacitance value used depends on the crystal vendor. Refer to application note *Selection and Specification for Crystals for Texas Instruments USB2.0 devices* (SLLA122) for details on how to determine the load capacitance value.

8.3.7 Input Clock Requirements

When using an external clock source such as an oscillator, the reference clock should have a ±100 PPM or better frequency stability and have less than 50-ps absolute peak to peak jitter or less than 25-ps peak to peak jitter after applying the USB 3.1 jitter transfer function. XI should be tied to the 1.8-V clock source and XO should be left floating.

8.3.8 Power-Up and Reset

The TUSB8043 does not have specific power sequencing requirements with respect to the core power (VDD) or I/O and analog power (VDD33) as long as GRSTz is held in an asserted state while supplies ramp. The core power (VDD) or I/O power (VDD33) may be powered up for an indefinite period of time while the other is not powered up if all of these constraints are met:

- All maximum ratings and recommended operating conditions are observed.
- All warnings about exposure to maximum rated and recommended conditions are observed, particularly junction temperature. These apply to power transitions as well as normal operation.
- Bus contention while VDD33 is powered up must be limited to 100 hours over the projected life-time of the device.
- Bus contention while VDD33 is powered down may violate the absolute maximum ratings.

A supply bus is powered up when the voltage is within the recommended operating range. It is powered down when it is below that range, either stable or in transition.

A minimum reset duration of 3 ms is required. This is defined as the time when the power supplies are in the recommended operating range to the de-assertion of GRSTz. This can be generated using programmable-delay supervisory device or using an RC circuit. When a RC circuit is used, the external capacitor size chosen must be large enough to meet the 3ms minimum duration requirement. The R of the RC circuit is the internal R_{PU}.



8.4 Device Functional Modes

8.4.1 External Configuration Interface

The TUSB8043 supports a serial interface for configuration register access. The device may be configured by an attached I²C EEPROM or accessed as a slave by an external SMBus master. The external interface is enabled when both the SCL/SMBCLK and SDA/SMBDAT pins are pulled up to 3.3 V at the de-assertion of reset. The mode, I²C master or SMBus slave, is determined by the state of SMBUSz/SS_SUSPEND pin at reset. With the integrated USB HID to I²C master, the I²C interface can also be used to program an external EEPROM or perform updates of an external MCU's firmware.

8.4.2 I²C EEPROM Operation

The TUSB8043 supports a single-master, fast mode (400KHz) connection to a dedicated I²C EEPROM when the I²C interface mode is enabled. In I²C mode, the TUSB8043 reads the contents of the EEPROM at bus address 1010000b using 7-bit addressing starting at address 0. The TUSB8043 will read the entire EEPROM contents using a single burst read transaction. The burst read transaction will end when the address reaches FFh.

If the value of the EEPROM contents at address byte 00h equals 55h, the TUSB8043 loads the configuration registers according to the EEPROM map. If the first byte is not 55h, the TUSB8043 exits the I²C mode and continues execution with the default values in the configuration registers. The hub will not connect on the upstream port until the configuration is completed.

NOTE

The bytes located above offset Ah are optional. The requirement for data in those addresses is dependent on the options configured in the Device Configuration, and Device Configuration 2 registers.

The minimum size I²C EEPROM required is 2Kbit.

For details on I²C operation refer to the UM10204 I²C-bus Specification and User Manual.

8.4.3 Port Configuration

The TUSB8043 port configurations can be selected by registers or efuse. The Port Used Configuration register (USED[3:0]) define how many ports can possibly be reported by the hub. The device removable configuration register (RMBL[3:0]) define if the ports that are reported as used have permanently connected devices or not. The USB 2.0 Only Port register (USB2_ONLY[3:0]) define whether or a used port is reported as part of the USB 2.0 hub or both the USB2.0 and USB3.1 hubs. The USB2_ONLY field will enable the USB2.0 port even if the corresponding USED bit is low. The internal HID port will always be the highest number USB2.0 port. The table below shows examples of the possible combinations.



Device Functional Modes (continued)

USED[3:0]	RMBL[3:0]	USB2_ONLY [3:0]	Reported Port Configuration	Physical to Logical Port mapping
1111	1111	0000	4 Port USB3.1 Hub 5 Port USB2.0 Hub Port 5 is permanently attached HID	Physical1 => Logical Port1 for USB3.1 and USB2.0. Physical2 => Logical Port2 for USB3.1 and USB2.0. Physical3 => Logical Port3 for USB3.1 and USB2.0. Physical4 => Logical Port4 for USB3.1 and USB2.0. Physical5 => Logical Port5 for USB2.0.
1110	1111	0000	3 Port USB3.1 Hub 4 Port USB2.0 Hub Port 4 is permanently attached HID	Physical1 Not used. Physical2 => Logical Port1 for USB3.1 and USB2.0. Physical3 => Logical Port2 for USB3.1 and USB2.0. Physical4 => Logical Port3 for USB3.1 and USB2.0. Physical5 => Logical Port4 for USB 2.0.
1100	0111	0000	2 Port USB 3.1 Hub 3 Port USB2.0 hub with permanently attached device on Port 2 Port 3 is a permanently attached HID	Physical1 Not used. Physical2 Not used. Physical3 => Logical Port1 for USB3.1 and USB2.0. Physical4 => Logical Port2 for USB3.1 and USB2.0. Physical5 => Logical Port3 for USB2.0.
0011	1111	0010	1 Port USB 3.1 Hub 3 Port USB 2.0 Hub Port 3 is a permanently attached HID	Physical1 => Logical Port1 for USB3.1 and USB2.0. Physical2 => Logical Port2 for USB2.0. Physical3 Not Used. Physical4 Not used. Physical5 => Logical Port3 for USB2.0.
1000	1111	0010	1 Port USB 3.1 Hub 3 Port USB 2.0 Hub Port 3 is a permanently attached HID	Physical1 Not used. Physical2 => Logical Port2 for USB2.0. Physical3 Not used Physical4 => Logical Port1 for USB3.1 and USB2.0. Physical5 => Logical Port3 for USB2.0.
1111	1111	1110	1 Port USB 3.1 Hub 5 Port USB 2.0 Hub Port 5 is a permanently attached HID	Physical1 => Logical Port1 for USB3.1 and USB2.0. Physical2 => Logical Port2 for USB2.0. Physical3 => Logical Port3 for USB2.0. Physical4 => Logical Port4 for USB2.0. Physical5 => Logical Port5 for USB2.0.
1010	N/A	0x0x	Invalid combination when USB2_ONLY = 0000, 0001, 0100, or 0101. If invalid combination is used, then physical port 4 will not operate at USB3.1 Gen 1 speeds.	
1011	N/A	0x01	Invalid combination when USB2_ONLY = 0001 or 0101. If invalid combination is used, then physical port 4 will not operate at USB3.1 Gen 1 speeds.	
1110	N/A	010x	Invalid combination when USB2_ONLY = 0100 or 0101. If invalid combination is used, then physical port 4 will not operate at USB3.1 Gen 1 speeds.	
1111	N/A	0101	Invalid combination when USB2_ONLY = 0101. If invalid combination is used, then physical port 4 will not operate at USB3.1 Gen 1 speeds.	

Table 5. TUSB8043 Downstream Port Configuration Examples



8.4.4 SMBus Slave Operation

When the SMBus interface mode is enabled, the TUSB8043 supports read block and write block protocols as a slave-only SMBus device.

The TUSB8043 slave address is 1000 1xyz, where:

- x is the state of GANGED/SMBA2/HS_UP pin at reset,
- y is the state of FULLPWRMGMTz/SMBA1/SS_UP pin at reset, and
- z is the read/write bit; 1 = read access, 0 = write access.

If the TUSB8043 is addressed by a host using an unsupported protocol it will not respond. The TUSB8043 waits indefinitely for configuration by the SMBus host and will not connect on the upstream port until the SMBus host indicates configuration is complete by clearing the CFG_ACTIVE bit.

For details on SMBus requirements, refer to the System Management Bus Specification.



8.5 Register Maps

8.5.1 Configuration Registers

The internal configuration registers are accessed on byte boundaries. The configuration register values are loaded with defaults but can be over-written when the TUSB8043 is in I^2C or SMBus mode.

BYTE ADDRESS	CONTENTS	EEPROM CONFIGURABLE
00h	ROM Signature Register	Yes
01h	Vendor ID LSB	Yes
02h	Vendor ID MSB	Yes
03h	Product ID LSB	Yes
04h	Product ID MSB	Yes
05h	Device Configuration Register	Yes
06h	Battery Charging Support Register	Yes
07h	Device Removable Configuration Register	Yes
08h	Port Used Configuration Register	Yes
09h	Reserved. Must default to 00h.	Yes
0Ah	Device Configuration Register 2	Yes
0Bh	USB 2.0 Port Polarity Control Register	Yes
0Ch-0Fh	Reserved	No
10h-1Fh	UUID Byte [15:0]	No
20h-21h	LangID Byte [1:0]	Yes
22h	Serial Number Length	Yes
23h	Manufacturer String Length	Yes
24h	Product String Length	Yes
25h	Device Configuration Register 3	Yes
26h	USB 2.0 Only Port Register	Yes
27h-2Eh	Reserved	Yes
2Fh	Reserved	No
30h-4Fh	Serial Number String Byte [31:0]	Yes
50h-8Fh	Manufacturer String Byte [63:0]	Yes
90h-CFh	Product String Byte [63:0]	Yes
D0h-D4h	Reserved	Yes ⁽¹⁾
D5h-D7h	Reserved	No
D8h-DCh	Reserved	Yes ⁽¹⁾
DDh-EFh	Reserved	No
F0h	Additional Features Configuration Register	Yes
F1h-F7h	Reserved	No
F8h	SMBus Device Status and Command Register	No
F9h - FFh	Reserved	No

Table 6. TUSB8043 Register Map

TUSB8043

JAJSD85A-JUNE 2017-REVISED AUGUST 2017

www.ti.com

STRUMENTS

EXAS

8.5.2 ROM Signature Register

Bit No. 7 5 3 2 0 6 4 1 Reset State 0 0 0 0 0 0 0 0 Table 7. Bit Descriptions – ROM Signature Register Bit Field Туре Description ROM Signature Register. This register is used by the TUSB8043 in I²C mode to validate the attached EEPROM has been programmed. The romSignature RW first byte of the EEPROM is compared to the mask 55h and if not a 7:0 match, the TUSB8043 aborts the EEPROM load and executes with the register defaults.

Figure 3. Register Offset 0h

8.5.3 Vendor ID LSB Register

Figure 4. Register Offset 1h

Bit No.	7	6	5	4	3	2	1	0
Reset State	0	1	0	1	0	0	0	1

Table 8. Bit Descriptions – Vendor ID LSB Register

Bit	Field	Туре	Description
7:0	vendorldLsb	RO/RW	Vendor ID LSB. Least significant byte of the unique vendor ID assigned by the USB-IF; the default value of this register is 51h representing the LSB of the TI Vendor ID 0451h. The value may be over-written to indicate a customer Vendor ID. Value used for this field will be the non-zero value written by EEPROM/SMBus to both PID and VID. If a zero value is written by EEPROM/SMbus to both PID and VID, then value used for this field will be the non-zero value from OTP. If a zero value is written by OTP, then value used for this field will be 51h.

8.5.4 Vendor ID MSB Register

Figure 5. Register Offset 2h

Bit No.	7	6	5	4	3	2	1	0
Reset State	0	0	0	0	0	1	0	0

Table 9. Bit Descriptions – Vendor ID MSB Register

Bit	Field	Туре	Description
7:0	vendorldMsb	RO/RW	Vendor ID MSB. Most significant byte of the unique vendor ID assigned by the USB-IF; the default value of this register is 04h representing the MSB of the TI Vendor ID 0451h. The value may be over-written to indicate a customer Vendor ID. Value used for this field will be the non-zero value written by EEPROM/SMBus to both PID and VID. If a zero value is written by EEPROM/SMbus to both PID and VID, then value used for this field will be the non-zero value from OTP. If a zero value is written by OTP, then value used for this field will be 04h.



8.5.5 Product ID LSB Register

Bit No.	7	6	5	4	3	2	1	0
Reset State	0	1	0	0	0	0	0	0
		Table 10.	Bit Descrip	tions – Pro	duct ID LSB	Register		
Bit	Field		Туре	Descrip	tion			
7:0	productIdLsb		RO/R'	W Texas Ir the defa SuperSp reported bit wise indicate Value us EEPROI EEPROI will be th	ID LSB. Least si instruments and ro ult value of this r beed product ID a in the USB 2.0 I XORed with 000 a customer prod sed for this field v M/SMBus to both the non-zero value ue used for this f	eported in the Si egister is 40h re assigned by Tex Device descripto 00010b. The val uct ID. will be the non-z h PID and VID. If PID and VID, th e from OTP. If a	uperSpeed Devi presenting the I as Instruments or is the value of lue may be over ero value writter f a zero value is nen value used zero value is w	ce descriptor. LSB of the The value this register -written to h by written by for this field

Figure 6. Register Offset 3h

8.5.6 Product ID MSB Register

Figure 7.	Register	Offset	4h
-----------	----------	--------	----

Bit No.	7	6	5	4	3	2	1	0
Reset State	1	0	0	0	0	0	1	1

Table 11. Bit Descriptions – Product ID MSB Register

Bit	Field	Туре	Description
7:0	productIdMsb	RO/RW	Product ID MSB. Most significant byte of the product ID assigned by Texas Instruments; the default value of this register is 83h representing the MSB of the product ID assigned by Texas Instruments. The value may be over-written to indicate a customer product ID. Value used for this field will be the non-zero value written by EEPROM/SMBus to both PID and VID. If a zero value is written by EEPROM/SMbus to both PID and VID, then value used for this field will be the non-zero value from OTP. If a zero value is written by OTP, then value used for this field will be 83h.

TUSB8043 JAJSD85A – JUNE 2017 – REVISED AUGUST 2017 TEXAS INSTRUMENTS

www.ti.com

8.5.7 Device Configuration Register

Figure 8. Register Offset 5h

Bit No.	7	6	5		4	3	2	1	0		
Reset State	0	0	0		1	Х	Х	0	0		
		Table 12.	Bit Desc	riptions -	- Devic	ce Configurati	on Register				
Bit	Field			Туре	Descri	iption					
7	customStrings			RW	Manufa Length 0 = Th String 1 = Th String Ioaded	n strings enable. T acturer String Len- n, Product String, a e Manufacturer St Length, Product S e Manufacturer St Length, Product S I by EEPROM or v efault value of this	gth, Manufacture and Language ID ring Length, Mar tring, and Langu ring Length, Mar tring, and Langu vritten by SMBus	er String, Produ Dregisters hufacturer Strin lage ID registe hufacturer Strin lage ID registe	ict String ig, Product rs are read only ig, Product		
6	customSernum			RW	serial r 0 = Th registe 1 = Se may be	n serial number en number registers. e Serial Number S ers are read only trial Number String e loaded by EEPR efault value of this	String Length and Length and Ser OM or written by	d Serial Numbe rial Number Str	er String		
5	u1u2Disable			RW	U1 U2 Disable. This bit controls the U1/U2 support. 0 = U1/U2 support is enabled 1 = U1/U2 support is disabled, the TUSB8043 will not initiate or any U1 or U2 requests on any port, upstream or downstream, ur receives or sends a Force_LinkPM_Accept LMP. After receiving sending an FLPMA LMP, it will continue to enable U1 and U2 according to USB 3.1 protocol until it gets a power-on reset or is disconnected on its upstream port. When the TUSB8043 is in I ² C mode, the TUSB8043 loads this b the contents of the EEPROM. When the TUSB8043 is in SMBUS mode, the value may be over written by an SMBus host.						
4	RSVD			RO	Reserv	ved. This bit is res	erved and return	s 1 when read			
3	ganged			RW	the GA 0 = Wh and en 1 = Wh ganged When the cor When	ANGED/SMBA2/H3 hen fullPwrMgmtz habled by the PWF hen fullPwrMgmtz d and enabled by the TUSB8043 is ntents of the EEPf	aded at the de-assertion of reset with the value of $/HS_UP$ pin. tz = 0, each port is individually power switched $//RCTL[4:1]/BATEN[4:1]$ pins tz = 0, the power switch control for all ports is by the PWRCTL[4:1]/BATEN1 pin is is in I ² C mode, the TUSB8043 loads this bit from PROM. is in SMBUS mode, the value may be over-				
2	fullPwrMgmtz			RW	with th 0 = Po 1 = Po When the cor	ower Management e value of the FUI ort power switching ort power switching the TUSB8043 is ntents of the EEPf the TUSB8043 is by an SMBus hos	LPWRMGMTz/S status reporting status reporting in I ² C mode, the ROM. in SMBUS mode	SMBA1/SS_UF is enabled is disabled TUSB8043 loa	? pin. ads this bit from		
1	u1u2TimerOvr			RW	overrid Host se TUSB8	Timer Override. V de the downstream oftware. If softwar 8043 will use the v 8043 will use value	ports U1/U2 time sets value in the alue of FFh. If se	neout values se ne range of 1h	et by USB3.1 - FFh, the		
0	RSVD			RO	Reserv	ved. This field is re	eserved and retu	rns 0 when rea	ıd.		



8.5.8 Battery Charging Support Register

Bit No.	7	6	5	4	3	2	1	0	
Reset State	0	0	0	0	Х	Х	Х	Х	
		Table 13. Bit D	escriptions -	Battery (Charging Sup	port Regist	er		
Bit Field Type Description									
7:4	RSVD		RO	Reserve	d. Read only, retu	urns 0 when rea	ad.		
3:0	batEn[3:0]		RW	downstru 0 = The 1 = The Each bit correspondownstru The defa with the When in	Charger Support. eam port impleme port is not enable port is enabled for corresponds dire onds to downstrea eam port 2. ault value for thes value of PWRCT I2C/SMBus mod M contents or by	ents the chargin ed for battery charg or battery charg ctly to a downs am port 1, and the bits are loade L/BATEN[3:0]. e the bits in this	ng port features. harging support ing support feat tream port, i.e. i batEN1 corresponded at the de-ass is field may be o	features ures batEn0 onds to ertion of reset	

Figure 9. Register Offset 6h

8.5.9 Device Removable Configuration Register

Figure 10. Register Offset 7h

Bit No.	7	6	5	4	3	2	1	0
Reset State	0	0	0	0	Х	Х	Х	Х

Table 14. Bit Descriptions – Device Removable Configuration Register

Bit	Field	Туре	Description
7	customRmbl	RW	Custom Removable. This bit controls the ability to write to the port removable bits, port used bits, and USB2_ONLY bits. 0 = rmbl[3:0], used[3:0], and USB2_ONLY[3:0] are read only and the values are loaded from the OTP ROM 1 = rmbl[3:0], used[3:0], and USB2_ONLY[3:0] are read/write and can be loaded by EEPROM or written by SMBus This bit may be written simultaneously with rmbl[3:0].
6:4	RSVD	RO	Reserved. Read only, returns 0 when read.
3:0	rmbl[3:0]	RO/RW	Removable. The bits in this field indicate whether a device attached to downstream ports 4 through 1 are removable or permanently attached. 0 = The device attached to the port is not removable 1 = The device attached to the port is removable Each bit corresponds directly to a downstream port n + 1, i.e. rmbl0 corresponds to downstream port 1, rmbl1 corresponds to downstream port 2, etc. This field is read only unless the customRmbl bit is set to 1. Otherwise the value of this filed reflects the inverted values of the OTP ROM non_rmb[3:0] field.

8.5.10 Port Used Configuration Register

Figure 11. Register Offset 8h

Bit No.	7	6	5	4	3	2	1	0
Reset State	0	0	0	0	1	1	1	1



Bit	Field	Туре	Description
7:4	RSVD	RO	Reserved. Read only.
3:0	used[3:0]	RO/RW	Used. The bits in this field indicate whether a port is enabled. 0 = The port is not used or disabled 1 = The port is used or enabled Each bit corresponds directly to a downstream port, i.e. used0 corresponds to downstream port 1, used1 corresponds to downstream port 2, etc. All combinations are supported with the exception of both ports 1 and 3 marked as disabled. This field is read only unless the customRmbl bit is set to 1. When the corresponding USB2_ONLY bit is set, the USB2 port will be used and enabled regardless of the bit programmed into this field.

Table 15. Bit Descriptions – Port Used Configuration Register



8.5.11 Device Configuration Register 2

Bit No.	7	6	5	4	3	2	1	0				
Reset State	0	0	Х	1	0	0	0	0				
	Та	able 16. Bit	Description	ns – Device	Configuratio	on Register :	2					
Bit	Field		Туре	Descrip	tion							
7	Reserved		RO	Reserve	Reserved. Read-only, returns 0 when read.							
6	customBCfeatures	5	RW	to write t 0 = The the OTP 1 = The EEPROI	Custom Battery Charging Feature Enable. This bit controls the ability to write to the battery charging feature configuration controls. 0 = The HiCurAcpModeEn is read only and the values are loaded from the OTP ROM. 1 = The HiCurAcpModeEn bit is read/write and can be loaded by EEPROM or written by SMBus. This bit may be written simultaneously with HiCurAcpModeEn.							
5	pwrctlPol		RW	with the 0 = PWF 1 = PWF When th the cont When th	Power enable polarity. This bit is loaded at the de-assertion of reset with the value of the PWRCTL_POL pin. 0 = PWRCTL polarity is active low 1 = PWRCTL polarity is active high When the TUSB8043 is in I ² C mode, the TUSB8043 loads this bit from the contents of the EEPROM. When the TUSB8043 is in SMBUS mode, the value may be over- written by an SMBus host.							
4	HiCurAcpModeEn		RO/R	W Charging for dowr 0 = High 1 = High This bit customE	High-current ACP mode enable. This bit enables the high-current table charging mode when the automatic battery charging mode is enabled for downstream ports. 0 = High current divider mode disabled . High current is ACP2 (default 1 = High current divider mode enabled. High current mode is ACP3 This bit is read only unless the customBCfeatures bit is set to 1. If customBCfeatures is 0, the value of this bit reflects the value of the OTP ROM HiCurAcpModeEn bit.							
3:2	Reserved		RW	Reserve	d							
1	autoModeEnz		RW	with the The auto charging these cc 0 = Auto 1 = Auto mode is NOTE: V mode with	 Automatic Mode Enable. This bit is loaded at the de-assertion o with the value of the AUTOENz/HS_SUSPEND pin. The automatic mode only applies to downstream ports with battic charging enabled when the upstream port is not connected. Und these conditions: 0 = Automatic mode battery charging features are enabled. 1 = Automatic mode is disabled; only Battery Charging DCP and mode is supported. NOTE: When the upstream port is connected, Battery Charging mode will be supported on all ports that are enabled for battery charging support regardless of the value of this bit. 							
0	RSVD		RO	Reserve	d. Read only, re	turns 0 when re	ad.					

Figure 12. Register Offset Ah



8.5.12 USB 2.0 Port Polarity Control Register

Figure 13. Register Offset Bh

Bit No.	7	6	5	4	3	2	1	0		
Reset State	0	0	0	0	0	0	0	0		
	Tab	le 17. Bit De	scriptions	– USB 2.0) Port Polarity	Control Reg	ister			
Bit	Field		Туре	e Des	cription					
7	customPolarity		RW	p[4:(0 = ⁻ from 1 = ⁻ EEP	tom USB 2.0 Polar D]_usb2pol bits. The p[4:0]_usb2pol the OTP ROM. The p[4:0]_usb2pol ROM or written by bit may be written	l bits are read onl l bits are read/wri SMBus.	y and the values te and can be lo	are loaded aded by		
6:5	RSVD		RO	Res	Reserved. Read only, returns 0 when read.					
4	p4_usb2pol		RO/I	RW port. 0 = 1 0 ut, This cust	nstream Port 4 DM JSB 2.0 port polari JSB 2.0 port polari i.e. DM becomes I bit is read only un omPolarity is 0 the 1 p4_usb2pol bit.	ity is as documen ity is swapped fro DP, and DP becor less the customP	ted by the pin ou m that documen nes DM. olarity bit is set t	it ted in the pin o 1. If		
3	p3_usb2pol		RO/I	RW port. 0 = 1 0 ut, This cust	Downstream Port 3 DM/DP Polarity. This controls the polarity of the port. 0 = USB 2.0 port polarity is as documented by the pin out 1 = USB 2.0 port polarity is swapped from that documented in the pin out, i.e. DM becomes DP, and DP becomes DM. This bit is read only unless the customPolarity bit is set to 1. If customPolarity is 0 the value of this bit reflects the value of the OTP ROM p3_usb2pol bit.					
2	p2_usb2pol		RO/I	RW port. 0 = 1 0 ut, This cust	 Downstream Port 2 DM/DP Polarity. This controls the polarity of port. 0 = USB 2.0 port polarity is as documented by the pin out 1 = USB 2.0 port polarity is swapped from that documented in th out, i.e. DM becomes DP, and DP becomes DM. This bit is read only unless the customPolarity bit is set to 1. If customPolarity is 0 the value of this bit reflects the value of the C ROM p2_usb2pol bit. 					
1	p1_usb2pol		ROF	RW port. 0 = 1 0 ut, This cust	 ROM p2_usb2poi bit. Downstream Port 1 DM/DP Polarity. This controls the polarity port. 0 = USB 2.0 port polarity is as documented by the pin out 1 = USB 2.0 port polarity is swapped from that documented in out, i.e. DM becomes DP, and DP becomes DM. This bit is read only unless the customPolarity bit is set to 1.1 customPolarity is 0 the value of this bit reflects the value of the ROM p1_usb2pol bit. 					
0	p0_usb2pol		RO/I	RW 0 = 1 RW out, This cust	ream Port DM/DP JSB 2.0 port polari JSB 2.0 port polari i.e. DM becomes I bit is read only un omPolarity is 0 the 1 p0_usb2pol bit.	ity is as documen ity is swapped fro DP, and DP becor less the customP	ted by the pin ou m that documen mes DM. olarity bit is set t	it ted in the pin o 1. If		



8.5.13 UUID Registers

Figure 14. Register Offset 10h-1Fh

Bit No.	7	6	5	4	3	2	1	0	
Reset State	Х	Х	Х	Х	Х	Х	Х	Х	
		Table 1	8. Bit Descrip	tions – U	UID Byte N R	Register			
Bit	Field Type Description								
7:0	uuidByte[n]		RO	UUID byte N. The UUID returned in the Container ID descriptor. The value of this register is provided by the device and is meets the UUID requirements of Internet Engineering Task Force (IETF) RFC 4122 A UUID URN Namespace.					

8.5.14 Language ID LSB Register

Figure 15. Register Offset 20h

Bit No.	7	6	5	4	3	2	1	0
Reset State	0	0	0	0	1	0	0	1

Table 19. Bit Descriptions – Language ID LSB Register

Bit	Field	Туре	Description
7:0	langIdLsb	RO/RW	Language ID least significant byte. This register contains the value returned in the LSB of the LANGID code in string index 0. The TUSB8043 only supports one language ID. The default value of this register is 09h representing the LSB of the LangID 0409h indicating English United States. When customStrings is 1, this field may be over-written by the contents of an attached EEPROM or by an SMBus host.

8.5.15 Language ID MSB Register

Figure 16. Register Offset 21h

Bit No.	7	6	5	4	3	2	1	0
Reset State	0	0	0	0	0	0	0	0

Table 20. Bit Descriptions – Language ID MSB Register

Bit	Field	Туре	Description
7:0	langldMsb	RO/RW	Language ID most significant byte. This register contains the value returned in the MSB of the LANGID code in string index 0. The TUSB8043 only supports one language ID. The default value of this register is 04h representing the MSB of the LangID 0409h indicating English United States. When customStrings is 1, this field may be over-written by the contents of an attached EEPROM or by an SMBus host.

TEXAS INSTRUMENTS

www.ti.com

8.5.16 Serial Number String Length Register

Bit No.	7	6	5	4	3	2	1	0	
Reset State	0	0	0	1	1	0	0	0	
	Tab	ole 21. Bit Des	scriptions – Se	erial Nu	nber String I	ength Regi	ster		
Bit	Field		Туре	Descrip	otion				
7:6	RSVD RO Reserved. Read only, returns 0 when read.								
5:0	serNumStringLe	n	RO/RW	Serial number string length. The string length in bytes for the serial number string. The default value is 18h indicating that a 24 byte serial number string is supported. The maximum string length is 32 bytes When customSernum is 1, this field may be over-written by the contents of an attached EEPROM or by an SMBus host. When the field is non-zero, a serial number string of serNumbStringLen bytes is returned at string index 1 from the data contained in the Serial Number String registers.					

Figure 17. Register Offset 22h

8.5.17 Manufacturer String Length Register

Figure 18. Register Offset 23h

Bit No.	7	6	5	4	3	2	1	0
Reset State	0	0	0	0	0	0	0	0

Table 22. Bit Descriptions – Manufacturer String Length Register

Bit	Field	Туре	Description
7	RSVD	RO	Reserved. Read only, returns 0 when read.
6:0	mfgStringLen	RO/RW	Manufacturer string length. The string length in bytes for the manufacturer string. The default value is 0, indicating that a manufacturer string is not provided. The maximum string length is 64 bytes. When customStrings is 1, this field may be over-written by the contents of an attached EEPROM or by an SMBus host. When the field is non-zero, a manufacturer string of mfgStringLen bytes is returned at string index 3 from the data contained in the Manufacturer String registers.

8.5.18 Product String Length Register

Figure 19. Register Offset 24h

Bit No.	7	6	5	4	3	2	1	0
Reset State	0	0	0	0	0	0	0	0

Table 23. Bit Descriptions – Product String Length Register

Bit	Field	Туре	Description
7	RSVD	RO	Reserved. Read only, returns 0 when read.
6:0	prodStringLen	RO/RW	Product string length. The string length in bytes for the product string. The default value is 0, indicating that a product string is not provided. The maximum string length is 64 bytes. When customStrings is 1, this field may be over-written by the contents of an attached EEPROM or by an SMBus host. When the field is non-zero, a product string of prodStringLen bytes is returned at string index 3 from the data contained in the Product String registers.



8.5.19 Device Configuration Register 3

Bit No.	7	6	5	4	3	2	1	0		
Reset State	0	0	0	0	0	0	0	0		
		Table 24. Bit	Descriptions	– Device	Configuratio	n Register :	3			
Bit	Field		Туре	Descrip	tion					
7:5	RSVD		RO	Reserve	d. Read only, ret	urns 0 when rea	ad.			
4	USB2.0_only		RW	from rep USB SS the USB This bit	hub reports as 2 porting 5Gbps sup BOS SS device 3.0 hub. is read/write but t and the corresponed.	pport in the wSp capability desc he read value r	eedsSupported riptor. This bit wi eturned is the B	field of the ill also disable oolean OR of		
3	Reserved		RO	Switch to	o reserved					
2	I2C_100k		R/W	USB to eFuse is This bit	kHz. This bit cont I2C requests . Th s used to set the is read/write but t and the correspon ed.	e EEPROM rea rate to 100k. he read value r	ads will occur at eturned is the B	400K unless oolean OR of		
1	Galaxy_Enz		R/W	Disable Galaxy compatible modes. When this field is high, Galax charging compatible mode will not be included in AUTOMODE ch sequence. This bit is read/write but the read value returned is the Boolean C this bit and the corresponding eFuse bit. If either bit is set, this fe is disabled.						
0	FullAutoEn		R/W	Enable all divider battery charging modes. When automode is enable and this bit is set, any DS port enabled for battery charging will atten all divider battery charging modes before DCP, starting with the highest current option. The bit is writable, but the value read back is the Boolean OR of this bit and the corresponding eFuse control. If either bit is set, eFuse or this register, this feature is enabled.						

Figure 20. Register Offset 25h

8.5.20 USB 2.0 Only Port Register

Figure 21. Register Offset 26h

Bit No.	7	6	5	4	3	2	1	0
Reset State	0	0	0	0	0	0	0	0

Table 25. Bit Descriptions – USB 2.0 Only Port Register

Bit	Field Type Description			
7:4	RSVD	RO	Reserved. Read only, returns 0 when read.	
3:0	USB2_ONLY[3:0]	RO/RW	USB 2.0 Only Ports. The bits in this field primarily indicate whether a port is enabled only for USB 2.0 operation. This field is read-only unless customRmbl bit is set. Also, these bits will override the corresponding USED bit. A value of 0 indicates the hub port is enabled for both USB 3.1 and USB 2.0. A value of 1 indicates the hub port is enabled only for USB 2.0 operation.	

8.5.21 Serial Number String Registers

NSTRUMENTS

Texas

TUSB8043 JAJSD85A – JUNE 2017 – REVISED AUGUST 2017

Figure 22. Register Offset 30h-4Fh								
Bit No.	7	6	5	4	3	2	1	0
Reset State	Х	Х	х	х	х	х	х	х

Table 26. Bit Descriptions – Serial Number Registers

Bit	Field	Туре	Description
7:0	serialNumber[n]	RO/RW	Serial Number byte N. The serial number returned in the Serial Number string descriptor at string index 1. The default value of these registers is assigned by TI. When customSernum is 1, these registers may be over-written by EEPROM contents or by an SMBus host.



8.5.22 Manufacturer String Registers

Bit No.	7	6	5	4	3	2	1	0		
Reset State	0	0	0	0	0	0	0	0		
Table 27. Bit Descriptions – Manufacturer String Registers										
Bit	Field		Туре	Descrip	Description					
7:0	mfgStringByte[n]		RW	returned number The pro	cturer string byte d for string index of bytes returned grammed data sh ed by The Unicon 5.0.	3 when mfgStrir d in the string is hould be in UNI	ngLen is greater equal to mfgStr CODE UTF-16L	than 0. The ingLen. E encodings		

Figure 23. Register Offset 50h-8Fh

8.5.23 Product String Registers

Figure 24. Register Offset 90h-CFh

Bit No	. 7	6	5	4	3	2	1	0
Reset St	ate 0	0	0	0	0	0	0	0

Table 28. Bit Descriptions – Product String Byte N Register

Bit	Field	Туре	Description
7:0	prodStringByte[n]	RO/RW	Product string byte N. These registers provide the string values returned for string index 2 when prodStringLen is greater than 0. The number of bytes returned in the string is equal to prodStringLen. The programmed data should be in UNICODE UTF-16LE encodings as defined by The Unicode Standard, Worldwide Character Encoding, Version 5.0.

TUSB8043 JAJSD85A – JUNE 2017 – REVISED AUGUST 2017 Texas Instruments

www.ti.com

8.5.24 Additional Feature Configuration Register

Bit No.	7	6	5	4	3	2	1	0		
Reset State	0	0	0	0	0	0	0	0		
	Table 2	29. Bit Desc	riptions – Ad	ditional F	eature Confi	guration Re	gister			
Bit	Field		Туре	Descrip	otion					
7:5	Reserved		RW	Reserve	ed. This field defa	ults to 3'b000 a	nd must not be	changed.		
4	stsOutputEn		RW	 Status output enable. This field when set enables of the Status output signals, HS_UP, HS_SUSPEND, SS_UP, SS_SUSPEND. 0 = STS outputs are disabled. 1 = STS outputs are enabled. This bit may be loaded by EEPROM or over-written by a SMBUS host. 						
3:1	pwronTime	RW	field set enable o example	On Delay Time. V s the delay time f of PWRCTL when e, when disabling The nominal timin	rom the remova n transitioning b the power on a	al disable of PW attery charging transition from	RCTL to the modes. For			
			TPWR	ON_EN = (pwro	onTime x 1) x	200 ms	(1)			
				This field may be over-written by EEPROM contents or by an SMBus host.						
0	usb3spreadDis		RW	USB3 Spread Spectrum Disable. This bit allows firmware to disable the spread spectrum function of the USB3 phy PLL. 0 = Spread spectrum function is enabled 1= Spread spectrum function is disabled This bit may be loaded by EEPROM or over-written by a SMBUS host.						

Figure 25. Register Offset F0h



8.5.25 SMBus Device Status and Command Register

Figure 26.	Register Offset F8h
------------	---------------------

Bit No.	7	6	5	4	3	2	1	0
Reset State	0	0	0	0	0	0	0	0

Table 30. Bit Descriptions – SMBus Device Status and Command Register

Bit	Field	Туре	Description
7:2	RSVD	RO	Reserved. Read only, returns 0 when read.
1	smbusRst	RSU	SMBus interface reset. This bit loads the registers back to their GRSTz values. Note, that since this bit can only be set when in SMBus mode the cfgActive bit is also reset to 1. When software sets this bit it must reconfigure the registers as necessary. This bit is set by writing a 1 and is cleared by hardware on completion of the reset. A write of 0 has no effect.
0	cfgActive	RCU	Configuration active. This bit indicates that configuration of the TUSB8043 is currently active. The bit is set by hardware when the device enters the I2C or SMBus mode. The TUSB8043 shall not connect on the upstream port while this bit is 1. When in I2C mode, the bit is cleared by hardware when the TUSB8043 exits the I2C mode. When in the SMBus mode, this bit must be cleared by the SMBus host in order to exit the configuration mode and allow the upstream port to connect. The bit is cleared by a writing 1. A write of 0 has no effect.



9 Applications and Implementation

NOTE

Information in the following applications sections is not part of the TI component specification, and TI does not warrant its accuracy or completeness. TI's customers are responsible for determining suitability of components for their purposes. Customers should validate and test their design implementation to confirm system functionality.

9.1 Application Information

The TUSB8043 is a four-port USB 3.1 Gen1 compliant hub. It provides simultaneous SuperSpeed USB and high-speed/full-speed connections on the upstream port and provides SuperSpeed USB, high-speed, full-speed, or low speed connections on the downstream port. The TUSB8043 can be used in any application that needs additional USB compliant ports. For example, a specific notebook may only have two downstream USB ports. By using the TUSB8043, the notebook can increase the downstream port count to five.

9.2 Typical Application

9.2.1 Discrete USB Hub Product

A common application for the TUSB8043 is as a self powered standalone USB hub product. The product is powered by an external 5V DC Power adapter. In this application, using a USB cable TUSB8043 upstream port is plugged into a USB Host controller. The downstream ports of the TUSB8043 are exposed to users for connecting USB hard drives, cameras, flash drives, and so forth.




Figure 27. Discrete USB Hub Product



Typical Application (continued)

9.2.1.1 Design Requirements


DESIGN PARAMETER	EXAMPLE VALUE
VDD Supply	1.1 V
VDD33 Supply	3.3 V
Upstream Port USB Support (SS, HS, FS)	SS, HS, FS
Downstream Port 1 USB Support (SS, HS, FS, LS)	SS, HS, FS, LS
Downstream Port 2 USB Support (SS, HS, FS, LS)	SS, HS, FS, LS
Downstream Port 3 USB Support (SS, HS, FS, LS)	SS, HS, FS, LS
Downstream Port 4 USB Support (SS, HS, FS, LS)	SS, HS, FS, LS
Number of Removable external exposed Downstream Ports	4
Number of Non-Removable external exposed Downstream Ports	0
Full Power Management of Downstream Ports	Yes. (FULLPWRMGMTZ = 0)
Individual Control of Downstream Port Power Switch	Yes. (GANGED = 0)
Power Switch Enable Polarity	Active High. (PWRCTL_POL = 1)
Battery Charge Support for Downstream Port 1	Yes
Battery Charge Support for Downstream Port 2	Yes
Battery Charge Support for Downstream Port 3	Yes
Battery Charge Support for Downstream Port 4	Yes
I2C EEPROM Support	No
24MHz Clock Source	Crystal

Table 31. Design Parameters

9.2.1.2 Detailed Design Procedure

9.2.1.2.1 Upstream Port Implementation

The upstream of the TUSB8043 is connected to a USB3 Type B connector. This particular example has GANGED pin and FULLPWRMGMTZ pin pulled low which results in individual power support each downstream port. The VBUS signal from the USB3 Type B connector is feed through a voltage divider. The purpose of the voltage divider is to make sure the level meets USB_VBUS input requirements






TUSB8043



www.ti.com

9.2.1.2.2 Downstream Port 1 Implementation

The downstream port 1 of the TUSB8043 is connected to a USB3 Type A connector. With BATEN1 pin pulled up, Battery Charge support is enabled for Port 1. If Battery Charge support is not needed, then pull-up resistor on BATEN1 should be uninstalled.




Copyright © 2016, Texas Instruments Incorporated



9.2.1.2.3 Downstream Port 2 Implementation

The downstream port 2 of the TUSB8043 is connected to a USB3 Type A connector. With BATEN2 pin pulled up, Battery Charge support is enabled for Port 2. If Battery Charge support is not needed, then pull-up resistor on BATEN2 should be uninstalled. For ferrite bead used on the VBUS connection, a lower resistance is recommended due to noticeable IR drop during high current charging modes. The isolation between the Type-A connectors shield ground and signal ground pins is not required. Some applications may have better ESD/EMI performance when the grounds are shorted together.




Copyright © 2016, Texas Instruments Incorporated

Figure 30. Downstream Port 2 Implementation



9.2.1.2.4 Downstream Port 3 Implementation

The downstream port3 of the TUSB8043 is connected to a USB3 Type A connector. With BATEN3 pin pulled up, Battery Charge support is enabled for Port 3. If Battery Charge support is not needed, then pull-up resistor on BATEN3 should be uninstalled. For ferrite bead used on the VBUS connection, a lower resistance is recommended due to noticeable IR drop during high current charging modes. The isolation between the Type-A connectors shield ground and signal ground pins is not required. Some applications may have better ESD/EMI performance when the grounds are shorted together.




Copyright © 2016, Texas Instruments Incorporated

Figure 31. Downstream Port 3 Implementation

9.2.1.2.5 Downstream Port 4 Implementation

The downstream port 4 of the TUSB8043 is connected to a USB3 Type A connector. With BATEN4 pin pulled up, Battery Charge support is enabled for Port 4. If Battery Charge support is not needed, then pull-up resistor on BATEN4 should be uninstalled. For ferrite bead used on the VBUS connection, a lower resistance is recommended due to noticeable IR drop during high current charging modes. The isolation between the Type-A connectors shield ground and signal ground pins is not required. Some applications may have better ESD/EMI performance when the grounds are shorted together.



Copyright © 2016, Texas Instruments Incorporated

Figure 32. Downstream Port 4 Implementation

9.2.1.2.6 VBUS Power Switch Implementation

This particular example uses the Texas Instruments TPS2561 Dual Channel Precision Adjustable Current-Limited power switch. For details on this power switch or other power switches available from Texas Instruments, refer to the Texas Instruments website.




Figure 33. VBUS Power Switch Implementation

9.2.1.2.7 Clock, Reset, and Misc

The PWRCTL_POL is left unconnected which results in active high power enable (PWRCTL1, PWRCTL2, PWRCTL3, and PWRCTL4) for a USB VBUS power switch. SMBUSz pin is also left unconnected which will select I2C mode. Both PWRCTL_POL and SMBUSz pins have internal pull-ups. The 1 μ F capacitor on the GRSTN pin can only be used if the VDD11 supply is stable before the VDD33 supply. The depending on the supply ramp of the two supplies the capacitor size may have to be adjusted.






Figure 34. Clock, Reset, and Misc

9.2.1.2.8 TUSB8043 Power Implementation





Figure 35. TUSB8043 Power Implementation




9.2.1.3 Application Curves





JAJSD85A-JUNE 2017-REVISED AUGUST 2017

www.ti.com





10 Power Supply Recommendations

10.1 TUSB8043 Power Supply

 V_{DD} should be implemented as a single power plane, as should V_{DD33} .

- The V_{DD} pins of the TUSB8043 supply 1.1 V (nominal) power to the core of the TUSB8043. This power rail
 can be isolated from all other power rails by a ferrite bead to reduce noise.
- The DC resistance of the ferrite bead on the core power rail can affect the voltage provided to the device due to the high current draw on the power rail. The output of the core voltage regulator may need to be adjusted to account for this or a ferrite bead with low DC resistance (less than 0.05Ω) can be selected.
- The V_{DD33} pins of the TUSB8043 supply 3.3 V power rail to the I/O of the TUSB8043. This power rail can be isolated from all other power rails by a ferrite bead to reduce noise.
- All power rails require a 10 µF capacitor or 1 µF capacitors for stability and noise immunity. These bulk capacitors can be placed anywhere on the power rail. The smaller decoupling capacitors should be placed as close to the TUSB8043 power pins as possible with an optimal grouping of two of differing values per pin.

10.2 Downstream Port Power

- The downstream port power, VBUS, must be supplied by a source capable of supplying 5V and up to 900 mA
 per port. Downstream port power switches can be controlled by the TUSB8043 signals. It is also possible to
 leave the downstream port power always enabled.
- A large bulk low-ESR capacitor of 22 µF or larger is required on each downstream port's VBUS to limit in-rush current.
- The ferrite beads on the VBUS pins of the downstream USB port connections are recommended for both ESD and EMI reasons. A 0.1µF capacitor on the USB connector side of the ferrite provides a low impedance path to ground for fast rise time ESD current that might have coupled onto the VBUS trace from the cable.

10.3 Ground

It is recommended that only one board ground plane be used in the design. This provides the best image plane for signal traces running above the plane. The thermal pad of the TUSB8043 and any of the voltage regulators should be connected to this plane with vias. An earth or chassis ground is implemented only near the USB port connectors on a different plane for EMI and ESD purposes.



11 Layout

11.1 Layout Guidelines

11.1.1 Placement

- 1. 9.53K +/-1% resistor connected to pin USB_R1 should be placed as close as possible to the TUSB8043.
- 2. A 0.1 μ F should be placed as close as possible on each VDD and VDD33 power pin.
- 3. The 100 nF capacitors on the SSTXP and SSTXM nets should be placed close to the USB connector (Type A, Type B, and so forth).
- 4. The ESD and EMI protection devices (if used) should also be placed as close as possible to the USB connector.
- 5. If a crystal is used, it must be placed as close as possible to the TUSB8043 XI and XO pins.
- 6. Place voltage regulators as far away as possible from the TUSB8043, the crystal, and the differential pairs.
- 7. In general, the large bulk capacitors associated with each power rail should be placed as close as possible to the voltage regulators.

11.1.2 Package Specific

- 1. The TUSB8043 package has a 0.5-mm pin pitch.
- 2. The TUSB8043 package has a 6.0-mm x 6.0-mm thermal pad. This thermal pad must be connected to ground through a system of vias.
- 3. All vias under device, except for those connected to thermal pad, should be solder masked to avoid any potential issues with thermal pad layouts.

11.1.3 Differential Pairs

This section describes the layout recommendations for all the TUSB8043 differential pairs: USB_DP_XX, USB_DM_XX, USB_SSTXP_XX, USB_SSTXM_XX, USB_SSRXP_XX, and USB_SSRXM_XX.

- 1. Must be designed with a differential impedance of 90 $\Omega \pm 10\%$.
- 2. In order to minimize cross talk, it is recommended to keep high speed signals away from each other. Each pair should be separated by at least 5 times the signal trace width. Separating with ground as depicted in the layout example will also help minimize cross talk.
- 3. Route all differential pairs on the same layer adjacent to a solid ground plane.
- 4. Do not route differential pairs over any plane split.
- 5. Adding test points will cause impedance discontinuity and will therefore negative impact signal performance. If test points are used, they should be placed in series and symmetrically. They must not be placed in a manner that causes stub on the differential pair.
- 6. Avoid 90 degree turns in trace. The use of bends in differential traces should be kept to a minimum. When bends are used, the number of left and right bends should be as equal as possible and the angle of the bend should be ≥ 135 degrees. This will minimize any length mismatch causes by the bends and therefore minimize the impact bends have on EMI.
- 7. Minimize the trace lengths of the differential pair traces. The maximum recommended trace length for SS differential pair signals and USB 2.0 differential pair signals is eight inches. Longer trace lengths require very careful routing to assure proper signal integrity.
- 8. Match the etch lengths of the differential pair traces (i.e. DP and DM or SSRXP and SSRXM or SSTXP and SSTXM). There should be less than 5 mils difference between a SS differential pair signal and its complement. The USB 2.0 differential pairs should not exceed 50 mils relative trace length difference.
- 9. The etch lengths of the differential pair groups do not need to match (i.e. the length of the SSRX pair to that of the SSTX pair), but all trace lengths should be minimized.
- 10. Minimize the use of vias in the differential pair paths as much as possible. If this is not practical, make sure that the same via type and placement are used for both signals in a pair. Any vias used should be placed as close as possible to the TUSB8043 device.
- 11. To ease routing, the polarity of the SS differential pairs can be swapped. This means that SSTXP can be routed to SSTXM or SSRXM can be routed to SSRXP.



Layout Guidelines (continued)

- 12. To ease routing of the USB2 DP and DM pair, the polarity of these pins can be swapped. If this is done, the appropriate Px_usb2pol register, where x = 0, 1, 2, 3, or 4, must be set.
- 13. Do not place power fuses across the differential pair traces.

11.2 Layout Examples

11.2.1 Upstream Port




Figure 46. Example Routing of Upstream Port



www.tij.co.jp

Layout Examples (continued)

11.2.2 Downstream Port




Figure 47. Example Routing of Downstream Port

The remaining three downstream ports routing can be similar to the example provided.



www.tij.co.jp

12 デバイスおよびドキュメントのサポート

12.1 ドキュメントの更新通知を受け取る方法

ドキュメントの更新についての通知を受け取るには、ti.comのデバイス製品フォルダを開いてください。右上の隅にある「通 知を受け取る」をクリックして登録すると、変更されたすべての製品情報に関するダイジェストを毎週受け取れます。変更の 詳細については、修正されたドキュメントに含まれている改訂履歴をご覧ください。

12.2 コミュニティ・リソース

The following links connect to TI community resources. Linked contents are provided "AS IS" by the respective contributors. They do not constitute TI specifications and do not necessarily reflect TI's views; see TI's Terms of Use.

TI E2E™オンライン・コミュニティ TIのE2E(Engineer-to-Engineer)コミュニティ。エンジニア間の共同作 業を促進するために開設されたものです。e2e.ti.comでは、他のエンジニアに質問し、知識を共有 し、アイディアを検討して、問題解決に役立てることができます。

設計サポート TIの設計サポート 役に立つE2Eフォーラムや、設計サポート・ツールをすばやく見つけることが できます。技術サポート用の連絡先情報も参照できます。

12.3 商標

E2E is a trademark of Texas Instruments. All other trademarks are the property of their respective owners.

12.4 静電気放電に関する注意事項

ے ال

これらのデバイスは、限定的なESD(静電破壊)保護機能を内蔵しています。保存時または取り扱い時は、MOSゲートに対する静電破壊を防止するために、リード線同士をショートさせておくか、デバイスを導電フォームに入れる必要があります。

12.5 Glossary

SLYZ022 — TI Glossary.

This glossary lists and explains terms, acronyms, and definitions.

13 メカニカル、パッケージ、および注文情報

以降のページには、メカニカル、パッケージ、および注文に関する情報が記載されています。これらの情報は、指定のデバイスに対して提供されている最新のデータです。このデータは予告なく変更されることがあり、ドキュメントが改訂される場合もあります。本データシートのブラウザ版を使用されている場合は、画面左側の説明をご覧ください。

RGC0064G




www.tij.co.jp

PACKAGE OUTLINE

VQFN - 1 mm max height

PLASTIC QUAD FLATPACK - NO LEAD



NOTES:

1. All linear dimensions are in millimeters. Any dimensions in parenthesis are for reference only. Dimensioning and tolerancing

per ASME Y14.5M.
This drawing is subject to change without notice.
The package thermal pad must be soldered to the printed circuit board for thermal and mechanical performance.




RGC0064G

www.tij.co.jp

EXAMPLE BOARD LAYOUT

VQFN - 1 mm max height

PLASTIC QUAD FLATPACK - NO LEAD



NOTES: (continued)

 This package is designed to be soldered to a thermal pad on the board. For more information, see Texas Instruments literature number SLUA271 (www.ti.com/lit/slua271).

www.ti.com

RGC0064G




www.tij.co.jp

EXAMPLE STENCIL DESIGN

VQFN - 1 mm max height

PLASTIC QUAD FLATPACK - NO LEAD



NOTES: (continued)

5. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.

www.ti.com



10-Dec-2020

PACKAGING INFORMATION

Orderable Device	Status (1)	Package Type	Package Drawing	Pins	Package Qty	Eco Plan (2)	Lead finish/ Ball material (6)	MSL Peak Temp (3)	Op Temp (°C)	Device Marking (4/5)	Samples
TUSB8043RGCR	ACTIVE	VQFN	RGC	64	2000	RoHS & Green	NIPDAU	Level-3-260C-168 HR	0 to 70	TUSB8043	Samples
TUSB8043RGCT	ACTIVE	VQFN	RGC	64	250	RoHS & Green	NIPDAU	Level-3-260C-168 HR	0 to 70	TUSB8043	Samples

⁽¹⁾ The marketing status values are defined as follows:

ACTIVE: Product device recommended for new designs.

LIFEBUY: TI has announced that the device will be discontinued, and a lifetime-buy period is in effect.

NRND: Not recommended for new designs. Device is in production to support existing customers, but TI does not recommend using this part in a new design.

PREVIEW: Device has been announced but is not in production. Samples may or may not be available.

OBSOLETE: TI has discontinued the production of the device.

⁽²⁾ RoHS: TI defines "RoHS" to mean semiconductor products that are compliant with the current EU RoHS requirements for all 10 RoHS substances, including the requirement that RoHS substance do not exceed 0.1% by weight in homogeneous materials. Where designed to be soldered at high temperatures, "RoHS" products are suitable for use in specified lead-free processes. TI may reference these types of products as "Pb-Free".

RoHS Exempt: TI defines "RoHS Exempt" to mean products that contain lead but are compliant with EU RoHS pursuant to a specific EU RoHS exemption.

Green: TI defines "Green" to mean the content of Chlorine (CI) and Bromine (Br) based flame retardants meet JS709B low halogen requirements of <= 1000ppm threshold. Antimony trioxide based flame retardants must also meet the <= 1000ppm threshold requirement.

⁽³⁾ MSL, Peak Temp. - The Moisture Sensitivity Level rating according to the JEDEC industry standard classifications, and peak solder temperature.

⁽⁴⁾ There may be additional marking, which relates to the logo, the lot trace code information, or the environmental category on the device.

⁽⁵⁾ Multiple Device Markings will be inside parentheses. Only one Device Marking contained in parentheses and separated by a "~" will appear on a device. If a line is indented then it is a continuation of the previous line and the two combined represent the entire Device Marking for that device.

⁽⁶⁾ Lead finish/Ball material - Orderable Devices may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead finish/Ball material values may wrap to two lines if the finish value exceeds the maximum column width.

Important Information and Disclaimer:The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.



PACKAGE OPTION ADDENDUM

10-Dec-2020

PACKAGE MATERIALS INFORMATION

www.ti.com

Texas Instruments

TAPE AND REEL INFORMATION





QUADRANT ASSIGNMENTS FOR PIN 1 ORIENTATION IN TAPE



*All dimensions are nominal												
Device	Package Type	Package Drawing		SPQ	Reel Diameter (mm)	Reel Width W1 (mm)	A0 (mm)	B0 (mm)	K0 (mm)	P1 (mm)	W (mm)	Pin1 Quadrant
TUSB8043RGCR	VQFN	RGC	64	2000	330.0	16.4	9.3	9.3	1.1	12.0	16.0	Q2
TUSB8043RGCT	VQFN	RGC	64	250	180.0	16.4	9.3	9.3	1.1	12.0	16.0	Q2

TEXAS INSTRUMENTS

www.ti.com

PACKAGE MATERIALS INFORMATION

13-Sep-2017



*All dimensions are nominal

Device	Package Type	Package Drawing	Pins	SPQ	Length (mm)	Width (mm)	Height (mm)
TUSB8043RGCR	VQFN	RGC	64	2000	367.0	367.0	38.0
TUSB8043RGCT	VQFN	RGC	64	250	210.0	185.0	35.0

重要なお知らせと免責事項

Ⅱは、技術データと信頼性データ(データシートを含みます)、設計リソース(リファレンス・デザインを含みます)、アプリケーションや設計に関する各種 アドバイス、Web ツール、安全性情報、その他のリソースを、欠陥が存在する可能性のある「現状のまま」提供しており、商品性および特定目的に対す る適合性の黙示保証、第三者の知的財産権の非侵害保証を含むいかなる保証も、明示的または黙示的にかかわらず拒否します。

これらのリソースは、TI 製品を使用する設計の経験を積んだ開発者への提供を意図したものです。(1) お客様のアプリケーションに適した TI 製品の選定、(2) お客様のアプリケーションの設計、検証、試験、(3) お客様のアプリケーションが適用される各種規格や、その他のあらゆる安全性、セキュリ ティ、またはその他の要件を満たしていることを確実にする責任を、お客様のみが単独で負うものとします。上記の各種リソースは、予告なく変更される 可能性があります。これらのリソースは、リソースで説明されている TI 製品を使用するアプリケーションの開発の目的でのみ、TI はその使用をお客様に 許諾します。これらのリソースに関して、他の目的で複製することや掲載することは禁止されています。TI や第三者の知的財産権のライセンスが付与さ れている訳ではありません。お客様は、これらのリソースを自身で使用した結果発生するあらゆる申し立て、損害、費用、損失、責任について、TI および その代理人を完全に補償するものとし、TI は一切の責任を拒否します。

TIの製品は、TIの販売条件(www.tij.co.jp/ja-jp/legal/termsofsale.html)、または ti.com やかかる TI 製品の関連資料などのいずれかを通じて提供 する適用可能な条項の下で提供されています。TI がこれらのリソースを提供することは、適用されるTI の保証または他の保証の放棄の拡大や変更を意 味するものではありません。

Copyright © 2020, Texas Instruments Incorporated

日本語版 日本テキサス・インスツルメンツ株式会社