

## Power Supply Supervisory Circuit

### FEATURES

- Includes Over-Voltage, Under-Voltage, and Current Sensing Circuits
- Internal 1% Accurate Reference
- Programmable Time Delays
- SCR "Crowbar" Drive of 300 mA
- Remote Activation Capability
- Optional Over-Voltage Latch
- Uncommitted Comparator Inputs for Low Voltage Sensing (UC1544 Series Only)

### DESCRIPTION


The monolithic integrated circuits contain all the functions necessary to monitor and control the output of a sophisticated power supply system. Over-voltage (O.V.) sensing with provision to trigger an external SCR "crowbar" shutdown; an undervoltage (U.V.) circuit which can be used to monitor either the output or to sample the input line voltage; and a third op amp/comparator usable for current sensing (C.L.) are all included in this device, together with an independent, accurate reference generator.

Both over- and under-voltage sensing circuits can be externally programmed for minimum time duration of fault before triggering. All functions contain open collector outputs which can be used independently or wire-or'ed together, and although the SCR trigger is directly connected only to the over-voltage sensing circuit, it may be optionally activated by any of the other outputs, or from an external signal. The O.V. circuit also includes an optional latch and external reset capability.

The UC1544/2544/3544 devices have the added versatility of completely uncommitted inputs to the voltage sensing comparators so that levels less than 2.5 V may be monitored by dividing down the internal reference voltage. The current sense circuit may be used with external compensation as a linear amplifier or as a highgain comparator. Although nominally set for zero input offset, a fixed threshold may be added with an external resistor. Instead of current limiting, this circuit may also be used as an additional voltage monitor.

The reference generator circuit is internally trimmed to eliminate the need for external potentiometers and the entire circuit may be powered directly from either the output being monitored or from a separate bias voltage.

### BLOCK DIAGRAM



### NOTE:


For each terminal, first number refers to 1543 series, second to 1544 series.

\*On 1543 series, this function is internally connected to VREF.



Please be aware that an important notice concerning availability, standard warranty, and use in critical applications of Texas Instruments semiconductor products and disclaimers thereto appears at the end of this data sheet.

## Connection Diagrams



## ABSOLUTE MAXIMUM RATINGS<sup>(1)</sup>

over operating free-air temperature range (unless otherwise noted)

|           |                                        | VALUE          | UNIT       |
|-----------|----------------------------------------|----------------|------------|
| $V_{IN}$  | Input supply voltage                   | 40             | V          |
|           | Sense inputs, voltage range            | 0 to $V_{IN}$  |            |
|           | SCR trigger current <sup>(2)</sup>     | -600           | mA         |
|           | Indicator output voltage               | 40             | V          |
|           | Indicator output sink current          | 50             | mA         |
|           | Power dissipation (package limitation) | 1000           | mW         |
| $T_J$     | Operating temperature range            | UC1543, UC1544 | -55 to 125 |
|           |                                        | UC2543, UC2544 | -25 to 85  |
|           |                                        | UC3543, UC3544 | 0 to 70    |
| $T_{stg}$ | Storage temperature range              | -65 to 150     | °C         |

(1) Currents are positive-into, negative-out of the specified terminal.

(2) At higher input voltages, a dissipation limiting resistor,  $R_G$ , is required.

## ELECTRICAL CHARACTERISTICS

Unless otherwise stated, these specifications apply for  $T_A = -55^{\circ}\text{C}$  to  $125^{\circ}\text{C}$  for the UC1543 and UC1544;  $-25^{\circ}\text{C}$  to  $85^{\circ}\text{C}$  for the UC2543 and UC2544; and  $0^{\circ}\text{C}$  to  $70^{\circ}\text{C}$  for the UC3543 and UC3544. Electrical tests are performed with  $V_{IN} = 10\text{ V}$  and 2-k $\Omega$  pull-up resistors on all indicator outputs. All electrical specifications for the UC1544, UC2544, and UC3544 devices are tested with the inverting over-voltage input and the non-inverting under-voltage input externally connected to the 2.5 V reference.  $T_A = T_J$ .

| PARAMETER           |                                                                    | TEST CONDITIONS                                                         | UC1543/UC1544/UC2543/<br>UC2544 |      |      | UC3543/UC3544 |      |      | UNIT   |
|---------------------|--------------------------------------------------------------------|-------------------------------------------------------------------------|---------------------------------|------|------|---------------|------|------|--------|
|                     |                                                                    |                                                                         | MIN                             | TYP  | MAX  | MIN           | TYP  | MAX  |        |
| V <sub>IN</sub>     | Input voltage range                                                | T <sub>J</sub> = 25°C to T <sub>MAX</sub>                               | 4.5                             |      | 40   | 4.5           |      | 40   | V      |
|                     |                                                                    | T <sub>MIN</sub> to T <sub>MAX</sub>                                    | 4.7                             |      | 40   | 4.7           |      | 40   |        |
| I <sub>CC</sub>     | Supply current                                                     | V <sub>IN</sub> = 40 V, output open,<br>T <sub>J</sub> = 25°C           |                                 | 7    | 10   |               | 7    | 10   | mA     |
|                     |                                                                    | T <sub>MIN</sub> ≤ T <sub>J</sub> ≤ T <sub>MAX</sub>                    |                                 |      | 15   |               |      | 15   |        |
| Reference Section   |                                                                    |                                                                         |                                 |      |      |               |      |      |        |
| V <sub>OUT</sub>    | Output voltage                                                     | T <sub>J</sub> = 25°C                                                   | 2.48                            | 2.5  | 2.52 | 2.45          | 2.50 | 2.55 | V      |
|                     |                                                                    | Over temperature range                                                  | 2.45                            |      | 2.55 | 2.40          |      | 2.60 |        |
|                     | Line regulation                                                    | V <sub>IN</sub> = 5 to 30 V                                             |                                 | 1    | 5    |               | 1    | 5    | mV     |
|                     | Load regulation                                                    | I <sub>REF</sub> = 0 to 10 mA                                           |                                 | 1    | 10   |               | 1    | 10   |        |
|                     | Short circuit current                                              | V <sub>REF</sub> = 0                                                    | -10                             | -20  | -40  | -12           | -20  | -40  | mA     |
|                     | Temperature stability                                              |                                                                         |                                 | 50   |      |               | 50   |      | ppm/°C |
| SCR Trigger Section |                                                                    |                                                                         |                                 |      |      |               |      |      |        |
|                     | Peak output current                                                | V <sub>IN</sub> = 5V, R <sub>G</sub> = 0, V <sub>O</sub> = 0            | -100                            | -300 | -600 | -100          | -300 | -600 | mA     |
|                     | Peak output voltage                                                | V <sub>IN</sub> = 15 V, I <sub>O</sub> = -100 mA                        | 12                              | 13   |      | 12            | 13   |      | V      |
|                     | Output OFF voltage                                                 | V <sub>IN</sub> = 40 V                                                  |                                 | 0    | 0.1  |               | 0    | 0.1  |        |
|                     | Remote activate current                                            | R/A Pin = GND                                                           |                                 | -0.4 | -0.8 |               | -0.4 | -0.8 | mA     |
|                     | Remote activate voltage                                            | R/A Pin Open                                                            |                                 | 2    | 6    |               | 2    | 6    | V      |
|                     | Reset current                                                      | Reset = GND, R/A = GND                                                  |                                 | -0.4 | -0.8 |               | -0.4 | -0.8 | mA     |
|                     | Reset voltage                                                      | Reset open, R/A = GND                                                   |                                 | 2    | 6    |               | 2    | 6    | V      |
|                     | Output current rise time                                           | R <sub>L</sub> = 50, T <sub>J</sub> = 25°C, C <sub>D</sub> = 0          |                                 | 400  |      |               | 400  |      | mA/μs  |
|                     | Prop. delay from R/A                                               | R <sub>L</sub> = 50, T <sub>J</sub> = 25°C, C <sub>D</sub> = 0          |                                 | 300  |      |               | 300  |      | ns     |
|                     | Prop. delay from O/V input                                         | R <sub>L</sub> = 50, T <sub>J</sub> = 25°C, C <sub>D</sub> = 0          |                                 | 500  |      |               | 500  |      |        |
| Comparator Section  |                                                                    |                                                                         |                                 |      |      |               |      |      |        |
|                     | Input threshold (Input voltage rising on O.V. and falling on U.V.) | T <sub>J</sub> = 25°C                                                   | 2.45                            | 2.50 | 2.55 | 2.40          | 2.50 | 2.60 | V      |
|                     |                                                                    | Over temperature range                                                  | 2.40                            |      | 2.60 | 2.35          |      | 2.65 |        |
|                     | Input hysteresis                                                   |                                                                         |                                 | 25   |      |               | 25   |      | mV     |
|                     | Input bias current                                                 | Sense input = 0 V                                                       |                                 | -0.3 | -1.0 |               | -0.3 | -1.0 | μA     |
|                     | Delay saturation                                                   |                                                                         |                                 | 0.2  | 0.5  |               | 0.2  | 0.5  | V      |
|                     | Delay high level                                                   |                                                                         |                                 | 6    | 7    |               | 6    | 7    |        |
|                     | Delay charging current                                             | V <sub>O</sub> = 0                                                      | -200                            | -250 | -300 | -200          | -250 | -300 | μA     |
|                     | Indicate saturation                                                | I <sub>L</sub> = 10 mA                                                  |                                 | 0.2  | 0.5  |               | 0.2  | 0.5  | V      |
|                     | Indicate leakage                                                   | V <sub>IND</sub> = 40 V                                                 |                                 | 0.01 | 1.0  |               | 0.01 | 1.0  | μA     |
|                     | Propagation delay                                                  | Input over drive = 200 mV, T <sub>J</sub> = 25°C, C <sub>D</sub> = 0    |                                 | 400  |      |               | 400  |      | ns     |
|                     |                                                                    | Input over drive = 200 mV, T <sub>J</sub> = 25°C, C <sub>D</sub> = 1 μF |                                 | 10   |      |               | 10   |      | ms     |

## ELECTRICAL CHARACTERISTICS (continued)

Unless otherwise stated, these specifications apply for  $T_A = -55^{\circ}\text{C}$  to  $125^{\circ}\text{C}$  for the UC1543 and UC1544;  $-25^{\circ}\text{C}$  to  $85^{\circ}\text{C}$  for the UC2543 and UC2544; and  $0^{\circ}\text{C}$  to  $70^{\circ}\text{C}$  for the UC3543 and UC3544. Electrical tests are performed with  $V_{IN} = 10\text{ V}$  and 2-k $\Omega$  pull-up resistors on all indicator outputs. All electrical specifications for the UC1544, UC2544, and UC3544 devices are tested with the inverting over-voltage input and the non-inverting under-voltage input externally connected to the 2.5 V reference.  $T_A = T_J$ .

| Current Limit Section |                        |                                                                                                                               |    |      |         |    |      |         |               |
|-----------------------|------------------------|-------------------------------------------------------------------------------------------------------------------------------|----|------|---------|----|------|---------|---------------|
|                       | Input voltage range    |                                                                                                                               | 0  |      | VIN -3V | 0  |      | VIN -3V | V             |
|                       | Input Bias Current     | Offset pin open, $V_{CM} = 0$                                                                                                 |    | -0.3 | -1.0    |    | -0.3 | -1.0    | $\mu\text{A}$ |
|                       | Input offset voltage   | Offset pin open, $V_{CM} = 0$                                                                                                 |    | 0    | 10      |    | 0    | 10      | mV            |
|                       |                        | 10k from offset pin to GND                                                                                                    | 80 | 100  | 120     | 80 | 100  | 120     |               |
|                       | CMRR                   | $0 \leq V_{CM} \leq 12\text{ V}$ , $V_{IN} = 15\text{ V}$                                                                     | 60 | 70   |         | 60 | 70   |         |               |
|                       | AVOL                   | Offset pin open, $V_{CM} = 0$<br>$V_i$<br>$R_L = 10\text{ k}\Omega$ to $15\text{ k}\Omega$ ,<br>$V_{OUT} = 1$ to $6\text{ V}$ | 72 | 80   |         | 72 | 80   |         | dB            |
|                       | Output saturation      | $I_L = 10\text{ mA}$                                                                                                          |    | 0.2  | 0.5     |    | 0.2  | 0.5     | V             |
|                       | Output leakage         | $V_{IND} = 40\text{ V}$                                                                                                       |    | 0.01 | 1.0     |    | 0.01 | 1.0     | $\mu\text{A}$ |
|                       | Small signal bandwidth | $A_V = 0\text{ dB}$ , $T_J = 25^{\circ}\text{C}$                                                                              |    | 5    |         |    | 5    |         | MHz           |
|                       | Propagation delay      | $V_{OVERDRIVE} = 100\text{ mV}$ ,<br>$T_J = 25^{\circ}\text{C}$                                                               |    | 200  |         |    | 200  |         | ns            |

## TYPICAL CHARACTERISTICS




Figure 1.








Figure 2.



## APPLICATION INFORMATION

The values for the external components are determined as follows:

$$V_{TH} = \frac{1000}{R1}$$

Current limit input threshold,

$C_S$  is determined by the current loop dynamics

$$I_P \cong \frac{V_{TH}}{R_{SC}} + \frac{V_O}{R_{SC}} \left( \frac{R2}{R2 + R3} \right)$$

Peak current to load,

$$I_{SC} = \frac{V_{TH}}{R_{SC}}$$

Short circuit current,

$$V_{O(low)} = \frac{2.5(R4 + R5 + R6)}{R5 + R6}$$

Low output voltage limit,


$$V_{O(high)} = \frac{2.5(R4 + R5 + R6)}{R6}$$

High output voltage limit,

Voltage sensing delay,  $t_D = 10,000C_d$

$$R_G > \frac{V_{IN} - 5}{0.2}$$

SCR trigger power limiting resistor,



### Figure 7. Typical Application

## APPLICATION INFORMATION (continued)




Figure 8. Sensing Multiple Supply Voltages




Figure 9. Input Line Monitor

## APPLICATION INFORMATION (continued)




Figure 10. Overcurrent Shutdown

## PACKAGING INFORMATION

| Orderable part number          | Status<br>(1) | Material type<br>(2) | Package   Pins | Package qty   Carrier | RoHS<br>(3) | Lead finish/<br>Ball material<br>(4) | MSL rating/<br>Peak reflow<br>(5) | Op temp (°C)    | Part marking<br>(6)            |
|--------------------------------|---------------|----------------------|----------------|-----------------------|-------------|--------------------------------------|-----------------------------------|-----------------|--------------------------------|
| <a href="#">5962-8774001EA</a> | Active        | Production           | CDIP (J)   16  | 25   TUBE             | No          | SNPB                                 | N/A for Pkg Type                  | -55 to 125      | 5962-8774001EA<br>UC1543J/883B |
| <a href="#">5962-8774001FA</a> | Active        | Production           | CFP (W)   16   | 25   TUBE             | No          | SNPB                                 | N/A for Pkg Type                  | See UC1543W883B | 5962-8774001FA<br>UC1543W/883B |
| UC1543J                        | Active        | Production           | CDIP (J)   16  | 25   TUBE             | No          | SNPB                                 | N/A for Pkg Type                  | -55 to 125      | UC1543J                        |
| UC1543J.A                      | Active        | Production           | CDIP (J)   16  | 25   TUBE             | No          | SNPB                                 | N/A for Pkg Type                  | -55 to 125      | UC1543J                        |
| <a href="#">UC1543J883B</a>    | Active        | Production           | CDIP (J)   16  | 25   TUBE             | No          | SNPB                                 | N/A for Pkg Type                  | -55 to 125      | 5962-8774001EA<br>UC1543J/883B |
| UC1543J883B.A                  | Active        | Production           | CDIP (J)   16  | 25   TUBE             | No          | SNPB                                 | N/A for Pkg Type                  | -55 to 125      | 5962-8774001EA<br>UC1543J/883B |
| UC1543L                        | Active        | Production           | LCCC (FK)   20 | 55   TUBE             | No          | SNPB                                 | N/A for Pkg Type                  | -55 to 125      | UC1543L                        |
| UC1543L.A                      | Active        | Production           | LCCC (FK)   20 | 55   TUBE             | No          | SNPB                                 | N/A for Pkg Type                  | -55 to 125      | UC1543L                        |
| <a href="#">UC1543L883B</a>    | Active        | Production           | LCCC (FK)   20 | 55   TUBE             | No          | SNPB                                 | N/A for Pkg Type                  | -55 to 125      | UC1543L/<br>883B               |
| UC1543L883B.A                  | Active        | Production           | LCCC (FK)   20 | 55   TUBE             | No          | SNPB                                 | N/A for Pkg Type                  | -55 to 125      | UC1543L/<br>883B               |
| <a href="#">UC1543W883B</a>    | Active        | Production           | CFP (W)   16   | 25   TUBE             | No          | SNPB                                 | N/A for Pkg Type                  | -               | 5962-8774001FA<br>UC1543W/883B |
| UC1543W883B.A                  | Active        | Production           | CFP (W)   16   | 25   TUBE             | No          | SNPB                                 | N/A for Pkg Type                  | -55 to 125      | 5962-8774001FA<br>UC1543W/883B |
| <a href="#">UC2543DW</a>       | Active        | Production           | SOIC (DW)   16 | 40   TUBE             | Yes         | NIPDAU                               | Level-2-260C-1 YEAR               | -40 to 85       | UC2543DW                       |
| UC2543DW.A                     | Active        | Production           | SOIC (DW)   16 | 40   TUBE             | Yes         | NIPDAU                               | Level-2-260C-1 YEAR               | -40 to 85       | UC2543DW                       |
| UC2543J                        | Active        | Production           | CDIP (J)   16  | 25   TUBE             | No          | SNPB                                 | N/A for Pkg Type                  | -25 to 85       | UC2543J                        |
| UC2543J.A                      | Active        | Production           | CDIP (J)   16  | 25   TUBE             | No          | SNPB                                 | N/A for Pkg Type                  | -25 to 85       | UC2543J                        |
| UC3543J                        | Active        | Production           | CDIP (J)   16  | 25   TUBE             | No          | SNPB                                 | N/A for Pkg Type                  | 0 to 70         | UC3543J                        |
| UC3543J.A                      | Active        | Production           | CDIP (J)   16  | 25   TUBE             | No          | SNPB                                 | N/A for Pkg Type                  | 0 to 70         | UC3543J                        |

<sup>(1)</sup> **Status:** For more details on status, see our [product life cycle](#).

<sup>(2)</sup> **Material type:** When designated, preproduction parts are prototypes/experimental devices, and are not yet approved or released for full production. Testing and final process, including without limitation quality assurance, reliability performance testing, and/or process qualification, may not yet be complete, and this item is subject to further changes or possible discontinuation. If available for ordering, purchases will be subject to an additional waiver at checkout, and are intended for early internal evaluation purposes only. These items are sold without warranties of any kind.

<sup>(3)</sup> **RoHS values:** Yes, No, RoHS Exempt. See the [TI RoHS Statement](#) for additional information and value definition.

<sup>(4)</sup> **Lead finish/Ball material:** Parts may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead finish/Ball material values may wrap to two lines if the finish value exceeds the maximum column width.

<sup>(5)</sup> **MSL rating/Peak reflow:** The moisture sensitivity level ratings and peak solder (reflow) temperatures. In the event that a part has multiple moisture sensitivity ratings, only the lowest level per JEDEC standards is shown. Refer to the shipping label for the actual reflow temperature that will be used to mount the part to the printed circuit board.

<sup>(6)</sup> **Part marking:** There may be an additional marking, which relates to the logo, the lot trace code information, or the environmental category of the part.

Multiple part markings will be inside parentheses. Only one part marking contained in parentheses and separated by a "~" will appear on a part. If a line is indented then it is a continuation of the previous line and the two combined represent the entire part marking for that device.

**Important Information and Disclaimer:** The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.

**OTHER QUALIFIED VERSIONS OF UC2543, UC2543M, UC3543M :**

- Catalog : [UC2543](#)
- Military : [UC2543M](#), [UC1543](#)

**NOTE: Qualified Version Definitions:**

- Catalog - TI's standard catalog product
- Military - QML certified for Military and Defense Applications

## TUBE



\*All dimensions are nominal

| Device         | Package Name | Package Type | Pins | SPQ | L (mm) | W (mm) | T (μm) | B (mm) |
|----------------|--------------|--------------|------|-----|--------|--------|--------|--------|
| 5962-8774001FA | W            | CFP          | 16   | 25  | 506.98 | 26.16  | 6220   | NA     |
| UC1543L        | FK           | LCCC         | 20   | 55  | 506.98 | 12.06  | 2030   | NA     |
| UC1543L.A      | FK           | LCCC         | 20   | 55  | 506.98 | 12.06  | 2030   | NA     |
| UC1543L883B    | FK           | LCCC         | 20   | 55  | 506.98 | 12.06  | 2030   | NA     |
| UC1543L883B.A  | FK           | LCCC         | 20   | 55  | 506.98 | 12.06  | 2030   | NA     |
| UC1543W883B    | W            | CFP          | 16   | 25  | 506.98 | 26.16  | 6220   | NA     |
| UC1543W883B.A  | W            | CFP          | 16   | 25  | 506.98 | 26.16  | 6220   | NA     |
| UC2543DW       | DW           | SOIC         | 16   | 40  | 507    | 12.83  | 5080   | 6.6    |
| UC2543DW.A     | DW           | SOIC         | 16   | 40  | 507    | 12.83  | 5080   | 6.6    |

## GENERIC PACKAGE VIEW


**DW 16**

**SOIC - 2.65 mm max height**


7.5 x 10.3, 1.27 mm pitch

SMALL OUTLINE INTEGRATED CIRCUIT

This image is a representation of the package family, actual package may vary.  
Refer to the product data sheet for package details.



4224780/A




DW0016A

# PACKAGE OUTLINE

## SOIC - 2.65 mm max height

SOIC



4220721/A 07/2016

### NOTES:


1. All linear dimensions are in millimeters. Dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.
2. This drawing is subject to change without notice.
3. This dimension does not include mold flash, protrusions, or gate burrs. Mold flash, protrusions, or gate burrs shall not exceed 0.15 mm, per side.
4. This dimension does not include interlead flash. Interlead flash shall not exceed 0.25 mm, per side.
5. Reference JEDEC registration MS-013.

# EXAMPLE BOARD LAYOUT


DW0016A

SOIC - 2.65 mm max height

SOIC



LAND PATTERN EXAMPLE  
SCALE:7X



SOLDER MASK DETAILS

4220721/A 07/2016

NOTES: (continued)

6. Publication IPC-7351 may have alternate designs.


7. Solder mask tolerances between and around signal pads can vary based on board fabrication site.

## EXAMPLE STENCIL DESIGN

DW0016A

SOIC - 2.65 mm max height

SOIC



SOLDER PASTE EXAMPLE  
BASED ON 0.125 mm THICK STENCIL  
SCALE:7X


4220721/A 07/2016

NOTES: (continued)

8. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.
9. Board assembly site may have different recommendations for stencil design.

W (R-GDFP-F16)

CERAMIC DUAL FLATPACK



- NOTES:
- All linear dimensions are in inches (millimeters).
  - This drawing is subject to change without notice.
  - This package can be hermetically sealed with a ceramic lid using glass frit.
  - Index point is provided on cap for terminal identification only.
  - Falls within MIL STD 1835 GDFP2-F16

## GENERIC PACKAGE VIEW


**FK 20**

**LCCC - 2.03 mm max height**

8.89 x 8.89, 1.27 mm pitch

LEADLESS CERAMIC CHIP CARRIER

This image is a representation of the package family, actual package may vary.  
Refer to the product data sheet for package details.




4229370VA\


J (R-GDIP-T\*\*)

14 LEADS SHOWN

# CERAMIC DUAL IN-LINE PACKAGE



| PINS **<br>DIM | 14                     | 16                     | 18                     | 20                     |
|----------------|------------------------|------------------------|------------------------|------------------------|
| A              | 0.300<br>(7,62)<br>BSC | 0.300<br>(7,62)<br>BSC | 0.300<br>(7,62)<br>BSC | 0.300<br>(7,62)<br>BSC |
| B MAX          | 0.785<br>(19,94)       | .840<br>(21,34)        | 0.960<br>(24,38)       | 1.060<br>(26,92)       |
| B MIN          | —                      | —                      | —                      | —                      |
| C MAX          | 0.300<br>(7,62)        | 0.300<br>(7,62)        | 0.310<br>(7,87)        | 0.300<br>(7,62)        |
| C MIN          | 0.245<br>(6,22)        | 0.245<br>(6,22)        | 0.220<br>(5,59)        | 0.245<br>(6,22)        |



4040083/F 03/03

- NOTES:
- A. All linear dimensions are in inches (millimeters).
  - B. This drawing is subject to change without notice.
  - C. This package is hermetically sealed with a ceramic lid using glass frit.
  - D. Index point is provided on cap for terminal identification only on press ceramic glass frit seal only.
  - E. Falls within MIL STD 1835 GDIP1-T14, GDIP1-T16, GDIP1-T18 and GDIP1-T20.

## IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATASHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, regulatory or other requirements.

These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you fully indemnify TI and its representatives against any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to [TI's Terms of Sale](#), [TI's General Quality Guidelines](#), or other applicable terms available either on [ti.com](#) or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products. Unless TI explicitly designates a product as custom or customer-specified, TI products are standard, catalog, general purpose devices.

TI objects to and rejects any additional or different terms you may propose.

Copyright © 2026, Texas Instruments Incorporated

Last updated 10/2025