

🕳 Order

Now











### DAC38RF82, DAC38RF89

JAJSDO4C - FEBRUARY 2017 - REVISED APRIL 2020

# DAC38RF8x JESD204Bインターフェイス、オンチップPLL、ワイドバン ド補間機能搭載の、デュアル・チャネル、差動出力、14ビット、 9GSPS、RFサンプリングDAC

# 1 特長

- マルチモード動作の 14 ビット分解能、9GSPS の DAC
  - 16 ビット、デュアル・チャネルのデータ・モード
    - 最大入力速度:2.5GSPS
    - 広帯域のデジタル・アップコンバータ
      - 補間: 1、2、4、6、8、10、12、16、18、20、 24x
  - 12 ビット、デュアル・チャネルのデータ・モード
    - 最大入力速度:3.33GSPS
    - 広帯域のデジタル・アップコンバータ
      - 補間: 1、2、24x
  - 8ビット、シングル・チャネルのデータ・モード
     最大入力速度:9GSPS
- JESD204B インターフェイス
  - サブクラス1のマルチチップ同期
  - 最大レーン速度:12.5Gbps
- 差動出力
  - DC カップリングをサポート
  - RF フルスケール出力電力 (2:1 バランの場合):
     2.14GHz で 3dBm
- PLLおよびVCO内蔵、バイパス付き
  - DAC38RF82: f<sub>C(VCO)</sub> = 5.9または8.9GHz
  - DAC38RF89: f<sub>C(VCO)</sub> = 5または7.5GHz
- 電源:-1.8V、1.0V、1.8V
- パッケージ: 10 × 10mm BGA、0.8mm ピッチ、 144 ボール

# 2 アプリケーション

- 任意波形の生成器
- レーダーおよび電子戦
- 通信テスト機器
- DOCSIS 3.0/3.1 用の直接 RF 合成
- マイクロ波バックホール

# 3 概要

DAC38RF82およびDAC38RF89は高性能、広帯域幅の RFサンプリング・デジタル/アナログ・コンバータ(DAC)で、 デュアル・チャネルで3.33GSPSまで、8ビットのシングル・ チャネルで9GSPSまでの入力データに対応できます。こ れらのデバイスは低消費電力のJESD204Bインターフェイ スを持ち、最大8レーンで12.5Gbpsまでのビット速度をサ ポートします。


デュアル・チャネル動作では、入力インターフェイスは12 ビット分解能で3.33GSPS、16ビット分解能で2.5GSPS までのデータ速度に、補間なしで対応できます。2xから 24xまでの補間モードを使用する、複雑なベースバンド送 信機として使用するとき、DAC38RF82または DAC38RF89は16ビット入力分解能で2GHz、12ビット入 力分解能で2.66GHzまでの広い帯域幅の信号を合成で きます。

8ビット・モードでは最大9GSPSのDACサンプル速度での 入力に対応し、0~4.5GHzの広い帯域幅の信号を合成で きます。

### 製品情報<sup>(1)</sup>

型番	パッケージ	本体サイズ(公称)				
DAC38RF82		10.0mm×10.0mm				
DAC38RF89	FCBGA (144)					

(1) 利用可能なすべてのパッケージについては、このデータシートの末 尾にある注文情報を参照してください。





32×6MHz、256QAM の搬送波

# 目次

1	特長	:
2	アプ	リケーション1
3	概要	· 1
4	改訂	'履歴2
5	概要	〔(続き)
6	Dev	ice Comparison Table5
7	Pin	Configuration and Functions 5
8	Spe	cifications8
	8.1	Absolute Maximum Ratings8
	8.2	ESD Ratings8
	8.3	Recommended Operating Conditions
	8.4	Thermal Information9
	8.5	Electrical Characteristics - DC Specifications
	8.6	Electrical Characteristics - Digital Specifications 11
	8.7	Electrical Characteristics - AC Specifications 14
	8.8	PLL/VCO Electrical Characteristics 17
	8.9	Timing Requirements 18
	8.10	Typical Characteristics 19
9	Deta	ailed Description
	9.1	Overview

	ᇔᆕᆓ	
4	改訂履歴	

2

資料番号末尾の英字は改訂を表しています。その改訂履歴は英語版に準じています。

### Revision B (August 2017) から Revision C に変更

•	Changed the tr NOM value from 50 ns To 50 ps in the Anaolog Output of the Timing Requirements table	. 18
•	Changed the t <sub>f</sub> NOM value from 50 ns To 50 ps in the Anaolog Output of the Timing Requirements table	. 18
•	Changed the MPY values in Table 4	. 28
•	Changed The title From: SerDes PLL Modes Selection To: SerDes PLL Multiplier (MPY) Values in in Table 4	. 28
•	Added section: Digital Quadrature Modulator	. 54
•	Added section: Low Power Coarse Resolution Mixing Modes	. 55
•	Added cross reference to MPY values in Table 132	125
•	Changed the enable/disable description for bit [15:13] of Table 134	127

### Revision A (April 2017)から Revision B に変更

۲	a	g	e

Page

•	「 特長」の「補間: 1、2、4、24x」を「補間: 1、2、24x」に変更し、「4」を 削除	1
•	Changed the ALARM pin From: alarm_out_pol To: alm_out_pol in the Pin Functions table	6
•	Changed the Description of pins A3, A4, A7, A6, A9, A10, A12, E12, F11, F7, G6, H5, H7, J6, J11 in the <i>Pin Functions</i> table	6
•	Changed description of TXENABLE pin in the PIN Functions table	7
•	Changed the MAX value of VEE18N rail From: 0.5 V To 0.3 V in the Absolute Maximum Ratings table	8
•	Added "Supply Voltage Range" to the Recommended Operating Conditions table	8
•	Changed DNL typical value From: ±0.5 to ±3 LSB in Electrical Characteristics - DC Specifications table	9
•	Changed INL typical value From: ±1 To: ±4 LSB in Electrical Characteristics - DC Specifications table	9
•	Added "Reference voltage drift" to the Electrical Characteristics - DC Specifications table	9
•	Changed Power Dissipation Test Condition From: MODE 5: dual channel, 8-bit input mode, 2x Interpolation To: MODE 5: dual channel, 8-bit input mode, 1x Interpolation in the <i>Electrical Characteristics - DC Specifications</i>	10
•	Changed the ILOAD values to negative for CMOS interface parameter, low-level output voltage, in the Electrical	



 13.4 商標
 138

 13.5 静電気放電に関する注意事項
 138

 13.6 Glossary
 138

 14 メカニカル、パッケージ、および注文情報
 138





www.tij.co.jp

# DAC38RF82, DAC38RF89

JAJSDO4C - FEBRUARY 2017 - REVISED APRIL 2020

	Characteristics - Digital Specifications table	. 11
•	Added 0 dBFS to the condition statement for the Electrical Characteristics - AC Specifications table	. 14
•	Added MIN and TYP value to maximum DAC sample rate for DAC38RF89 only in the <i>Electrical Characteristics - AC</i> Specifications table	. 14
•	Added NSD values for DAC38RF82 with on-chip PLL enabled to Electrical Characteristics - AC Specifications table	. 16
•	Changed the Isolation values in the TEST CONDITIONS, TYP value From: 74 dBc To: 82 dBc and 56 dBc To 73 dBc in the <i>Electrical Characteristics - AC Specifications</i> table	. 16
•	Added Figure 16	20
•	Added MPY value for 16.5x in the Table 4	28
•	Changed input rate max and fdac max for 6x interpolation mode in Table 9	. 31
•	Changed input data rate From: 6666 MSPS To: 3333 MSPS for LMFSHd=41380, 2x interpolation in Table 9	. 32
•	Changed Table 12, JESD204B frame format for LMFSHd=84111	32
•	Changed Table 14, JESD204B frame format for LMFSHd=44210	33
•	Changed Table 16, JESD204B frame format for LMFSHd = 24410	. 33
•	Changed Table 17, JESD204B frame format for LMFSHd = 44210	. 33
•	Changed Table 18, JESD204B frame format for LMFSHd = 88210	. 34
•	Changed Table 19, JESD204B frame format for LMFSHd = 24410	. 34
•	Changed Table 20, JESD204B frame format for LMFSHd=48410	34
•	Changed Table 21, JESD204B frame format for LMFSHd = 24310	. 34
•	Changed Table 22, JESD204B frame format for LMFSHd = 48310	. 34
•	Changed Table 23, JESD204B frame format for LMFSHd = 81180	35
•	Changed Table 24, JESD204B frame format for LMFSHd = 41380	. 35
•	Changed Table 26, JESD204B frame format for LMFSHd = 41121	. 36
•	Added Table 27, JESD204B frame format for LMFSHd = 41121	. 37
•	Changed Table 38	48
•	Changed register field programming values for LMFSHd=24410, 41380, 41121 and 24310 in the Register Programming for JESD and Interpolation Mode table	53
•	Changed the bit positions of N_M1 register field From: 12-8 To: 4-0 in the Table 42 table	. 54
•	Changed the bit positions of N_M1' (NPRIME_M1) register field From: 4-0 To: 12-0 in the Table 42 table	. 54
•	Changed the description of DAC PLL alarm in Alarm Monitoring	59
•	Changed from BIST_ENA to Reserved in Table 61	79
•	Changed from BIST_ZERO to Reserved in Table 61	79
•	Changed the description of OUTSUM_SEL field in Table 69	85
•	Changed the Description of Bit 11 From "dummy data generation" to "distortion enhancement" in Table 116	115
•	変更 the junction temp and loop filter voltage range for PLL tuning in 図 142	129

# 2017年2月発行のものから更新

•	Corrected the NSD values for -9dBFS in Electrical Characteristics - AC Specifications table	16
•	Added PLL/VCO characteristics table to PLL/VCO Electrical Characteristics	17
•	Added JESD204B clock phase register setting to Table 41	53
•	Removed descriptions for CLKJESD_DIV register from Table 41	53
•	Added JESD204B clock phase register setting to Table 42	53
•	Added information about the DAC output total current for various full scale current settings in DAC Fullscale Output Current	. 61
•	Changed Bit 0 of Table 128 From: Enables the GSM PLL To: Reserved	122
•	Changed Table 130	124
•	Changed description of SERDES_REFCLK_DIV register field in Table 131	125

Page

# DAC38RF82, DAC38RF89

JAJSDO4C – FEBRUARY 2017 – REVISED APRIL 2020

Changed Bit 12:11, 6:5 and 4:2 of Table 134 ...... 127





www.tij.co.jp




# 5 概要(続き)

オプションの低ジッタPLL/VCOにより、低い周波数の基準クロックを使用できるため、DACクロックの生成が簡単になります。DAC38RF82およびDAC38RF89は、「デバイス比較表」に要約されているように、それぞれ異なるVCO周波数範囲に対応しています。

# 6 Device Comparison Table

PART NUMBER ANALOG OUTPUT TYPE		VCO0 CENTER FREQUENCY	VCO1 CENTER FREQUENCY	
DAC38RF82	Differential	5.9 GHz	8.9 GHz	
DAC38RF89	Differential	5 GHz	7.5 GHz	

# 7 Pin Configuration and Functions





# DAC38RF82, DAC38RF89

JAJSDO4C - FEBRUARY 2017 - REVISED APRIL 2020

# **Pin Functions**

PIN					
NO.	NAME	- I/O	DESCRIPTION		
C11, C12, D11, E11, F12, J12, K11, L11,	AGND	-	Analog ground.		
M11, M12 K8	ALARM	0	CMOS output for ALARM condition. Default polarity is active low, but can be changed to active high via RESET_CONFIG alm_out_pol control bit		
G3	AMUX0	0	Analog test pin for SerDes, Lane 0 to Lane 3. Can be left floating.		
F3	AMUX1	0	Analog test pin for SerDes, Lane 4 to Lane 7. Can be left floating.		
C8	ATEST	0	Analog test pin for DAC, references and PLL. Can be left floating.		
A7	CLKTX+	0	Divided output clock, internal 100 $\Omega$ differential termination, self-biased, positive terminal.		
A6	CLKTX-	0	Divided output clock, internal 100 $\Omega$ differential termination, self-biased, positive terminal.		
A10	DACCLK+	1	Device clock, internal 100 $\Omega$ differential termination, self-biased, positive terminal.		
A10	DACCLK-	1	Device clock, internal 100 $\Omega$ differential termination, self-biased, positive terminal.		
A12	DACCLKSE	1	Single ended device clock optional input. Can be left floating if not used, internal 50 $\Omega$ termination.		
A2, B2, C2, D2, D6, E2, E7, F2, F6, G2, G7, H6, J7, K2, L2, L3, L4, L5, M6	DGND	-	Digital ground.		
C10	EXTIO	I/O	Requires a 0.1 µF decoupling capacitor to AGND.		
K7	GPI0	-	Factory use only. User should GND.		
M7	GPI1	-	Factory use only. User should GND.		
L7	GPO0	0	Used for CMOS SYNC0\ signal.		
L6	GPO1	0	Used for CMOS SYNC1\ signal.		
D3	IFORCE	0	Test pin for on chip parametrics. Can be left floating.		
C9	RBIAS	ο	Full-scale output current bias. Change the full-scale output current through DACFS in register DACFS (8.5.72). Expected to be 3.6 k $\Omega$ to GND for 40 mA full scale output.		
K9	RESET	I	Active low input for chip RESET, which resets all the programming registers to their default state. Interna pull-up.		
J1	RX0+	I	CML SerDes interface lane 0 input, positive		
K1	RX0-	I	CML SerDes interface lane 0 input, negative		
M1	RX1+	I	CML SerDes interface lane 1 input, positive		
L1	RX1-	I	CML SerDes interface lane 1 input, negative		
M2	RX2+	I	CML SerDes interface lane 2 input, positive		
M3	RX2-	I	CML SerDes interface lane 2 input, negative		
M5	RX3+	I	CML SerDes interface lane 3 input, positive		
M4	RX3-	I	CML SerDes interface lane 3 input, negative		
H1	RX4+	I	CML SerDes interface lane 4 input, positive		
G1	RX4-	I	CML SerDes interface lane 4 input, negative		
E1	RX5+	I	CML SerDes interface lane 5 input, positive		
F1	RX5-	I	CML SerDes interface lane 5 input, negative		
D1	RX6+	I	CML SerDes interface lane 6 input, positive		
C1	RX6-	I	CML SerDes interface lane 6 input, negative		
A1	RX7+	I	CML SerDes interface lane 7 input, positive		
B1	RX7-	I	CML SerDes interface lane 7 input, negative		
L9	SCLK	I	Serial interface clock. Internal pull-down.		
M8	SDEN	I	Active low serial data enable, always an input to the DAC38RFxx. Internal pull-up.		
M10	M10 SDIO I/O Serial interface data. Bi-directional in 3-pin mode (default) and uni-directional in 3-pin mode (		Serial interface data. Bi-directional in 3-pin mode (default) and uni-directional input 4-pin mode. Internal pull-down.		
M9	SDO	0	Uni-directional serial interface data output in 4-pin mode. The SDO pin is tri-stated in 3-pin interface mode (default).		
L8 SLEEP I Active high asynchronous hardware power-down input. Internal pull-down.		Active high asynchronous hardware power-down input. Internal pull-down.			
C4	SYNC0+	0	Synchronization request to transmitter for JESD204B link 0, LVDS positive output.		
C3	SYNC0-	0	Synchronization request to transmitter for JESD204B link 0, LVDS negative output.		
C7	SYNC1+	0	Synchronization request to transmitter for JESD204B link 1, LVDS positive output.		
C6	SYNC1-	0	Synchronization request to transmitter for JESD204B link 1, LVDS negative output.		



# Pin Functions (continued)

PIN NO. NAME		I/O			
			DESCRIPTION		
A3	SYSREF+	I	LVPECL SYSREF positive input, internal 100 $\Omega$ differential termination, self biased. This positive/negative pair is captured with the rising edge of DACCLKP/N. It is used for multiple DAC synchronization.		
A4	SYSREF-	I	LVPECL SYSREF negative input, self biased, internal 100 $\Omega$ differential termination. (See the SYSREF+ description)		
K4	TCLK	I	JTAG test clock. Internal pull-down		
H4	TDI	I	JTAG test data in. Internal pull-up		
J4	TDO	0	JTAG test data out. Internal pull-up		
КЗ	TESTMODE	-	This pin is used for factory testing. Recommended to connect to ground for normal operation.		
K5	TMS	I	JTAG test mode select. Internal pull-up		
J5	TRST	I	JTAG test reset. Internal pull-up. Must be connected to ground if not used		
K6	TXENABLE	I	Transmit enable active high input. Internal pull-down. This pin is ORed with spi_txenable bit in JESD_FIFO register to enable analog output data transmissio To enable analog output data transmission, pull CMOS TXENABLE pin to high. To disable analog output, pull CMOS TXENABLE pin to low. The DAC output is forced to midscale.		
F11, J11	VDDA1	I	Analog 1 V supply voltage. Must be separated from VDDDIG1 supply for best performance.		
G11, H11	VDDA18	I	Analog 1.8 V supply voltage. (1.8 V)		
D8, E8	VDDPLL1	I	Analog 1 V supply for PLL.		
B9, B10	VDDAPLL18	I	PLL analog supply voltage. (1.8 V)		
D9, E9	VDDAVCO18	I	Analog supply voltage for VCO (1.8 V)		
G9, H9	VDDCLK1	I	Internal clock buffer supply voltage (1 V). It is recommended to isolate this supply from VDDDIG1 and VDDA1.		
G8, H8 VDDL1_1		I	DAC core supply voltage. (1 V)		
G10, H10	VDDL2_1	I	DAC core supply voltage. (1 V)		
A5, B5, C5, D5, D7, E3, E4, E5, E6, F4, F5, G4, G5	VDDDIG1	I	Digital supply voltage. (1 V). It is recommended to isolate this supply from VDDCLK1 and VDDA1.		
F7, H7, G6, J6	VDDE1	I	Digital Encoder supply voltage (1 V). Must be separated from VDDDIG1 supply		
H5	VDDIO18	I	Supply voltage for all digital I/O and CMOS I/O. (1.8 V)		
G12, H12	VDDOUT18	I	DAC output supply. (1.8 V)		
H2, J2	VDDR18	I	Supply voltage for SerDes. (1.8 V)		
B3, B4	VDDS18	I	Supply voltage for LVDS SYNC0+/- and SYNC1+/- (1.8 V)		
H3, J3	VDDT1	I	Supply voltage for SerDes termination. (1 V)		
B6	VDDTX1	I	Supply voltage for divided clock output. (1 V)		
B7	VDDTX18	I	Supply voltage for divided clock output . (1.8 V)		
D10, E10, K10, L10	VEE18N	I	Analog supply voltage. (-1.8 V)		
L12 VOUT1+		0	DAC channel 1 output.		
K12 VOUT1-		0	DAC channel 1 complementary output.		
D12	VOUT2+	0	DAC channel 2 output.		
E12 VOUT2-		0	DAC channel 2 complementary output.		
D4	VSENSE	0	Test pin for on chip parametrics. Can be left floating.		
A8, A11, B8, B11, B12,         VSSCLK         -         Clock ground.					



# 8 Specifications

# 8.1 Absolute Maximum Ratings

over operating free-air temperature range (unless otherwise noted)<sup>(1)</sup>

		MIN	MAX	UNIT
Supply Voltage Range <sup>(2)</sup>	VDDDAC1, VDDDIG1, VDDL1_1, VDDL2_1, VDDCLK1, VDDT1, VDDCLK1, VDDTX1, VDDE1	-0.3	1.3	V
	VDDR18, VDDIO18, VDDS18, VDDAPLL18, VDDAREF18, VDDAOUT18, VDDA18, VDDAVCO18, VDDTX18	-0.3	2.45	V
	VEE18N	-2	0.3	V
Voltage between AGND and DGND		-0.3	0.3	V
	RX[07]+/-	-0.5	VDDDIG1 + 0.5 V	V
	SDEN, SCLK, SDIO, SDO, TXENABLE, ALARM, RESET, SLEEP, TMS, TCLK, TDI, TDO, TRST, TESTMODE, GPI0, GPI1, GPO0, GPO1	-0.5	VDDIO + 0.5 V	V
	CLKOUT+/-	-0.5	VDDTX18 + 0.5 V	V
Pin Voltage Range <sup>(2)</sup>	DACCLK+/-, SYSREF+/-, DACCLKSE	-0.5	VDDCLK1 + 0.5 V	V
	SYNC0+/-, SYNC1+/-	-0.5	VDDS18 + 0.5 V	V
	IOUT1+/-, IOUT2+/-	-0.5	VDDAOUT18 + 0.5 V	V
	RBIAS, EXTIO, ATEST	-0.5	VDDAOUT18 + 0.5 V	V
	IFORCE, VSENSE	-0.5	VDDDIG1 + 0.5 V	V
	AMUX1, AMUX0	-0.5	VDDT1 + 0.5 V	V
Peak input current (any input)			20	mA
Peak total input current (all inputs)		-30		mA
			150	°C
		-40	85	°C
Storage temperature, T <sub>stg</sub>	torage temperature, T <sub>stg</sub>			°C

(1) Stresses beyond those listed under Absolute Maximum Ratings may cause permanent damage to the device. These are stress ratings only, which do not imply functional operation of the device at these or any other conditions beyond those indicated under Recommended Operating Conditions. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability.

(2) Measured with respect to AGND or DGND.

# 8.2 ESD Ratings

			VALUE	UNIT
		Human-body model (HBM), per ANSI/ESDA/JEDEC JS-001 <sup>(1)</sup>	±1000	
V <sub>(ESD)</sub>	Electrostatic discharge	Charged-device model (CDM), per JEDEC specification JESD22-C101 <sup>(2)</sup>	±250	V

(1) JEDEC document JEP155 states that 500-V HBM allows safe manufacturing with a standard ESD control process.

(2) JEDEC document JEP157 states that 250-V CDM allows safe manufacturing with a standard ESD control process.

# 8.3 Recommended Operating Conditions

over operating free-air temperature range (unless otherwise noted)

			MIN	NOM	MAX	UNIT
т	T <sub>J</sub> T <sub>J</sub> Recommended operating temperature Maximum rated operating junction temperature <sup>(1)</sup>				105	°C
IJ			125			°C
T <sub>A</sub>	Recommended free-air temperat	Recommended free-air temperature			85	°C
		VDDA18, VDDAPLL18, VDDS18, VDDIO18, VDDR18, VDDAPLL18, VDDOUT18, VDDAVCO18	1.71	1.8	1.89	
	Supply Voltage Range	VDDDIG1 VDDA1, VDDT1, VDDAPLL1, VDDCLK1, VDDL1_1, VDDL2_1, VDDTX1, VDDE1	0.95	1	1.05	V
		VEE18N	-1.89	-1.8	-1.71	

(1) Prolonged use at this junction temperature may increase the device failure-in-time (FIT) rate

### DAC38RF82, DAC38RF89

JAJSDO4C-FEBRUARY 2017-REVISED APRIL 2020

www.ti.com

**FRUMENTS** 

EXAS

# 8.4 Thermal Information

	(1)	DAC38RF82 DAC38RF89	
	THERMAL METRIC <sup>(1)</sup>	AAV (FCBGA)	UNIT
		144 PINS	
$R_{\thetaJA}$	Junction-to-ambient thermal resistance	25	°C/W
R <sub>0JC(top)</sub>	Junction-to-case (top) thermal resistance	1.0	°C/W
$R_{\theta JB}$	Junction-to-board thermal resistance	7.7	°C/W
ΨJT	Junction-to-top characterization parameter	0.1	°C/W
Ψјв	Junction-to-board characterization parameter	7.7	°C/W
R <sub>0JC(bot)</sub>	Junction-to-case (bottom) thermal resistance	N/A	°C/W

(1) For more information about traditional and new thermal metrics, see the Semiconductor and IC Package Thermal Metrics application report.

# 8.5 Electrical Characteristics - DC Specifications

Typical values at  $T_A = 25^{\circ}$ C, full temperature range is  $T_{MIN} = -40^{\circ}$ C to  $T_{MAX} = 85^{\circ}$ C, nominal supplies, unless otherwise noted.

	PARAMETER	TEST CONDITIONS	MIN	TYP	MAX	UNIT
DC ACCUR	ACY	· · · · · ·				
		8-bit Input Mode	8			
	Digital Input Resolution	12-bit Input Mode	12			bits
		16-bit Input Mode	16			
	DAC Core Resolution		14			bits
	DNL Differential nonlinearity			±3		LSB
	INL Integral nonlinearity			±4		LSB
Analog Out	put					
	Gain Error			±2		%FSR
	Full scale output current		10	30	40	mA
P <sub>(OUTFS)</sub>	Full scale output power	2:1 transformer coupled into 50 $\Omega$ - load. Transformer (TCM2-452X-2+) loss not de- embedded 2.1 GHz output frequency		3		dBm
	Output Compliance Range		1.3		2.3	V
	Output capacitance	Single ended to ground		1.5		pF
	Output resistance	Differential		100		ohms
Reference	Output: EXTIO					
V <sub>REF</sub>	Reference output voltage			0.9		V
	Reference output current			100		nA
	Reference voltage drift			±8		ppm/°C
Power Sup	ply Current and consumption					
	1 V Digital supplies: VDDDIG1			815	1300	mA
	1 V Analog supplies: VDDA1 VDDACLK1 VDDTX1 VDDAPLL1 VDDT1 VDDE1			1144	1250	mA
	1.8 V Supplies: VDDA18 VDDOUT18 VDDAVCO18 VDDAPLL18 VDDR18 VDDIO18 VDDS18 VDDTX18	MODE 1: dual channel, 12-bit input mode, 2x Interpolation, Sin(x)/x enabled, f <sub>DAC</sub> = 6 GHz, CLKTX Disabled		218	270	mA
	-1.8 V Supply: VEE18N			159	180	mA
P <sub>DIS</sub>	Power Dissipation			2638	3360	mW
	1 V Digital supplies: VDDDIG1			798		mA
	1 V Analog supplies: VDDA1 VDDACLK1 VDDTX1 VDDAPLL1 VDDT1 VDDE1			1026		mA
	1.8 V Supplies: VDDA18 VDDOUT18 VDDAVCO18 VDDAPLL18 VDDR18 VDDIO18 VDDS18 VDDTX18	MODE 2: dual channel, 16-bit input mode, 2x Interpolation, Sin(x)/x enabled, f <sub>DAC</sub> = 5 GHz, CLKTX Disabled		222		mA
	-1.8 V Supply: VEE18N			159		mA
P <sub>DIS</sub>	Power Dissipation			2510		mW



# **Electrical Characteristics - DC Specifications (continued)**

Typical values at  $T_A = 25^{\circ}$ C, full temperature range is  $T_{MIN} = -40^{\circ}$ C to  $T_{MAX} = 85^{\circ}$ C, nominal supplies, unless otherwise noted.

	PARAMETER	TEST CONDITIONS	MIN	ТҮР	MAX	UNIT
	1V Digital supplies: VDDDIG1			500		mA
	1 V Analog supplies: VDDA1 VDDACLK1 VDDTX1 VDDAPLL1 VDDT1 VDDE1			751		mA
	1.8 V Supplies: VDDA18 VDDOUT18 VDDAVCO18 VDDAPLL18 VDDR18 VDDIO18 VDDS18 VDDTX18	MODE 3: dual channel, 12-bit input mode, 2x Interpolation, Sin(x)/x enabled, f <sub>DAC</sub> = 3 GHz, CLKTX Disabled		218		mA
	-1.8V Supply: VEE18N			159		mA
P <sub>DIS</sub>	Power Dissipation			1930		mW
	1 V Digital supplies: VDDDIG1			517		mA
	1 V Analog supplies: VDDA1 VDDACLK1 VDDTX1 VDDAPLL1 VDDT1 VDDE1			708		mA
	1.8 V Supplies: VDDA18 VDDOUT18       MODE 4: dual channel, 16-bit input mode, 2x         VDDAVCO18 VDDAPLL18 VDDR18       Interpolation, Sin(x)/x enabled, f <sub>DAC</sub> = 2.5         VDDIO18 VDDS18 VDDTX18       GHz, CLKTX Disabled		222		mA	
	-1.8 V Supply: VEE18N		159		mA	
P <sub>DIS</sub>	Power Dissipation			1911		mW
	1 V Digital supplies: VDDDIG1			624		mA
	1 V Analog supplies: VDDA1 VDDACLK1 VDDTX1 VDDAPLL1 VDDT1 VDDE1			1469		mA
	1.8 V Supplies: VDDA18 VDDOUT18 VDDAVCO18 VDDAPLL18 VDDR18 VDDIO18 VDDS18 VDDTX18	MODE 5: dual channel, 8-bit input mode, 1x Interpolation, Sin(x)/x enabled, f <sub>DAC</sub> = 9 GHz, CLKTX Disabled		218		mA
	-1.8 V Supply: VEE18N			159		mA
P <sub>DIS</sub>	Power Dissipation			2772		mW
	1 V Digital supplies: VDDDIG1			63	568	mA
	1 V Analog supplies: VDDA1 VDDACLK1 VDDTX1 VDDAPLL1 VDDT1 VDDE1			18	105	mA
	1.8 V Supplies: VDDA18 VDDOUT18 VDDAVCO18 VDDAPLL18 VDDR18 VDDIO18 VDDS18 VDDTX18	MODE 6: Power down mode, no clock, DAC in sleep, SerDes in sleep, CLKTX Disabled		47	51	mA
	-1.8 V Supply: VEE18N			23	28	mA
P <sub>DIS</sub>	Power Dissipation			208	815	mW
		f <sub>DAC</sub> = 8847 MSPS, Clock Out Divider Enabled		25		mA
	VDDTX1	f <sub>DAC</sub> = 5898 MSPS, Clock Out Divider Enabled		19		mA
	VDDTX18	Clock Out Enabled		16		mA

# 8.6 Electrical Characteristics - Digital Specifications

Typical values at  $T_A = 25^{\circ}$ C, full temperature range is  $T_{MIN} = -40^{\circ}$ C to  $T_{MAX} = 85^{\circ}$ C, external differential clock mode at 9 GSPS, 12x Interpolation,  $f_{OUT} = 2.14$  GHz,  $I_{(OUTFS)} = 40$  mA, nominal supplies, LMFSHd = 84111, unless otherwise noted.

	PARAMETER	TEST CONDITIONS	MIN	TYP	MAX	UNIT
CML SerD	es Inputs: RX[7:0]+/-					
V <sub>DIFF</sub>	Receiver input amplitude		50		1200	mV
		TERM = 111		600		
		TERM = 001		700		
V <sub>COM</sub>	Input Common Mode Voltage	TERM = 100		0		mV
		TERM = 101		250		
Z <sub>DDIFF</sub>	Internal differential termination		85	100	115	Ω
SerDes	SerDes bit rate		0.78125		12.5	Gbps
Differentia	al Clock Inputs: SYSREF±, DACCLK±	- ·	i			
DACCLK	DACCLK input frequency		0.1		9	GHz
V <sub>COM</sub>	Input common mode voltage			0.5		V
V <sub>I(DPP)</sub>	Differential input peak-to-peak voltage			800	2000	mV
Z <sub>T</sub>	Internal termination			100		Ω
CL	Input capacitance			2		pF
	Duty cycle (DACCLK only		40%		60%	
LVDS Out	put: SYNC0±, SYNC1±					
/ <sub>COM</sub>	Output common mode voltage			1.2		V
ZT	Internal termination			100		Ω
/ <sub>OD</sub>	Differential output voltage swing			500		mV
CML Outp	out: DIVCLKOUT±		H		1	
V <sub>OD</sub>	CML OUTPUT: CLKTX+/-			1300		mV
	erface: SDEN, SCLK, SDIO, SDO, TXENABLE,	ALARM, RESET, SLEEP, TMS, TCLK, TD	I, TDO, TRST, TESTMO	DDE, SYNC	SE1,	
SYNCSE2			0.7			
V <sub>IH</sub>	High-level input voltage		0.7 x VDDIO			V
VIL	Low-level input voltage				0.3 x VDDIO	V
н	High-level input current		-40		40	μA
IL	Low-level input current		-40		40	μA
CI	CMOS input capacitance			2		pF
		I <sub>LOAD</sub> = -100 μA	VDDIO – 0.2			V
V <sub>OH</sub>	High-level output voltage	$I_{LOAD} = -2 \text{ mA}$	0.8 x VDDIO			V
V <sub>OL</sub>	Low-level output voltage	$I_{LOAD} = 100 \ \mu A$			0.2	V
VOL	Low-level output voltage	I <sub>LOAD</sub> = 2 mA			0.5	v
_atency						
		full rate, RATE = "00"		34		
	RX SarDag Digital Dalay	half rate, RATE = "01"		29		UI
	RX SerDes Digital Delay	quarter rate, RATE = "10"		26.5		UI
		eighth rate, RATE = "11"		26.25		
	SerDes output to JED204B elastic buffer input latency			21 -39		JESD clock cycles



# **Electrical Characteristics - Digital Specifications (continued)**

Typical values at  $T_A = 25^{\circ}$ C, full temperature range is  $T_{MIN} = -40^{\circ}$ C to  $T_{MAX} = 85^{\circ}$ C, external differential clock mode at 9 GSPS, 12x Interpolation,  $f_{OUT} = 2.14$  GHz,  $I_{(OUTFS)} = 40$  mA, nominal supplies, LMFSHd = 84111, unless otherwise noted.

PARAMETER	TEST CONDITIONS	MIN	TYP	MAX	UNIT
	LMFSHD = 41121 or 82121, 1x Interpolation		269		
	LMFSHD = 41121 or 82121, 2x Interpolation		417		
	LMFSHD = 41121 or 82121, 4x Interpolation		717		
	LMFSHD = 41380 or 82380, 1x Interpolation		293		
	LMFSHD = 41380 or 82380, 2x Interpolation		465		
	LMFSHD = 81180, 1x Interpolation		289		
	LMFSHD = 82121, 6x Interpolation		269		
	LMFSHD = 82121, 8x Interpolation		1120		
	LMFSHD = 82121, 12x Interpolation		1602		
	LMFSHD = 82121, 16x Interpolation		2091		
	LMFSHD = 42111 or 84111, 6x Interpolation		817		
	LMFSHD = 42111 or 84111, 8x Interpolation		1057		
	LMFSHD = 42111 or 84111, 10x Interpolation		1184		
	LMFSHD = 42111 or 84111, 12x Interpolation		1532		
	LMFSHD = 42111 or 84111, 16x Interpolation		1997		
	LMFSHD = 42111 or 84111, 18x Interpolation		2142		
	LMFSHD = 42111 or 84111, 24x Interpolation		2941		
Digital Latency: JESD Buffer to DAC Output	LMFSHD = 22210 or 44210, 8x Interpolation		1020		DAC clock
Digital Latency. JEOD Duner to DAO Output	LMFSHD = 22210 or 44210, 12x Interpolation		1473		cycles
	LMFSHD = 22210 or 44210, 16x Interpolation		1917		
	LMFSHD = 22210 or 44210, 18x Interpolation		2050		
	LMFSHD = 22210 or 44210, 20x Interpolation		2275		
	LMFSHD = 22210 or 44210, 24x Interpolation		2821		
	LMFSHD = 12410 or 24410, 16x Interpolation		1912		
	LMFSHD = 12410 or 24410, 24x Interpolation		2786		
	LMFSHD = 44210 or 88210, 8x Interpolation		916		
	LMFSHD = 44210 or 88210, 12x Interpolation		1317		
	LMFSHD = 44210 or 88210, 16x Interpolation		1709		
	LMFSHD = 44210 or 88210, 24x Interpolation		2509		
	LMFSHD = 24410 or 48410, 16x Interpolation		1672		
	LMFSHD = 24410 or 48410, 24x Interpolation		1593		



# **Electrical Characteristics - Digital Specifications (continued)**

Typical values at  $T_A = 25^{\circ}$ C, full temperature range is  $T_{MIN} = -40^{\circ}$ C to  $T_{MAX} = 85^{\circ}$ C, external differential clock mode at 9 GSPS, 12x Interpolation,  $f_{OUT} = 2.14$  GHz,  $I_{(OUTFS)} = 40$  mA, nominal supplies, LMFSHd = 84111, unless otherwise noted.

PARAMETER	TEST CONDITIONS	MIN	TYP	MAX	UNIT	
	LMFSHD = 41121 or 82121, 1x Interpolation		13			
	LMFSHD = 41121 or 82121, 2x Interpolation		9			
	LMFSHD = 41121 or 82121, 4x Interpolation		6			
	LMFSHD = 41380 or 82380, 1x Interpolation		15			
	LMFSHD = 41380 or 82380, 2x Interpolation		10			
	LMFSHD = 81180, 1x Interpolation		6			
	LMFSHD = 82121, 6x Interpolation		5			
	LMFSHD = 82121, 8x Interpolation		5			
	LMFSHD = 82121, 12x Interpolation		5			
	LMFSHD = 82121, 16x Interpolation		5			
	LMFSHD = 42111 or 84111, 6x Interpolation		16			
	LMFSHD = 42111 or 84111, 8x Interpolation		16			
	LMFSHD = 42111 or 84111, 10x Interpolation		15			
	LMFSHD = 42111 or 84111, 12x Interpolation		15			
	LMFSHD = 42111 or 84111, 16x Interpolation		13			
	LMFSHD = 42111 or 84111, 18x Interpolation		15			
	LMFSHD = 42111 or 84111, 24x Interpolation		15			
SYSREF TO JESD LMFC RESET	LMFSHD = 22210 or 44210, 8x Interpolation		8		JESD clock	
	LMFSHD = 22210 or 44210, 12x Interpolation		7		cycles	
	LMFSHD = 22210 or 44210, 16x Interpolation		6			
	LMFSHD = 22210 or 44210, 18x Interpolation		7			
	LMFSHD = 22210 or 44210, 20x Interpolation		5			
	LMFSHD = 22210 or 44210, 24x Interpolation		4			
	LMFSHD = 12410 or 24410, 16x Interpolation		9			
	LMFSHD = 12410 or 24410, 24x Interpolation		7			
	LMFSHD = 44210 or 88210, 8x Interpolation		29			
	LMFSHD = 44210 or 88210, 12x Interpolation		27			
	LMFSHD = 44210 or 88210, 16x Interpolation		26			
	LMFSHD = 44210 or 88210, 24x Interpolation		25			
	LMFSHD = 24410 or 48410, 16x Interpolation		8			
	LMFSHD = 24410 or 48410, 24x Interpolation		6			



# 8.7 Electrical Characteristics - AC Specifications

Typical values at  $T_A = 25^{\circ}$ C, full temperature range is  $T_{MIN} = -40^{\circ}$ C to  $T_{MAX} = 85^{\circ}$ C, external differential clock mode at 9 GSPS, 12x Interpolation, 0 dBFS,  $f_{OUT} = 2.14$  GHz,  $I_{(OUTFS)} = 40$  mA, nominal supplies, LMFSHd = 84111, unless otherwise noted.

	PARAMETER	TEST CONDITIONS	MIN	TYP	MAX	UNIT		
Analog C	Dutput							
4	Movimum DAC comple rate	DAC38RF82 only	9			GSPS		
f <sub>DAC</sub>	Maximum DAC sample rate	DAC38RF89 only	8.4	9		6353		
AC Perfo	ormance - CW							
		$f_{CLK} = 6 \text{ GHz}$ , $f_{OUT} = 501 \text{ MHz}$		63				
		$f_{CLK} = 6 \text{ GHz}$ , $f_{OUT} = 951 \text{ MHz}$		62				
		f <sub>CLK</sub> = 6 GHz , f <sub>OUT</sub> = 1851 MHz		58				
		f <sub>CLK</sub> = 6 GHz , f <sub>OUT</sub> = 2651 MHz		57		1		
SFDR	Spurious Free Dynamic Range 0 – f <sub>DAC</sub> /2	$f_{CLK} = 9 \text{ GHz}$ , $f_{OUT} = 501 \text{ MHz}$		62		dBc		
	·DAC/~	f <sub>CLK</sub> = 9 GHz , f <sub>OUT</sub> = 951 MHz		61				
		f <sub>CLK</sub> = 9 GHz , f <sub>OUT</sub> = 1851 MHz		61				
		f <sub>CLK</sub> = 9 GHz , f <sub>OUT</sub> = 2651 MHz		54				
		f <sub>CLK</sub> = 9 GHz , f <sub>OUT</sub> = 3651 MHz		51				
		f <sub>CLK</sub> = 6 GHz , f <sub>OUT</sub> = 501 MHz		97				
		f <sub>CLK</sub> = 6 GHz , f <sub>OUT</sub> = 951 MHz		93				
		f <sub>CLK</sub> = 6 GHz , f <sub>OUT</sub> = 1851 MHz		88				
SFDR		f <sub>CLK</sub> = 6 GHz , f <sub>OUT</sub> = 2651 MHz		77				
	Spurious Free Dynamic Range within 500 MHz f <sub>OUT</sub> ± 250 MHz	f <sub>CLK</sub> = 9 GHz , f <sub>OUT</sub> = 501 MHz		94		dBc		
		f <sub>CLK</sub> = 9 GHz , f <sub>OUT</sub> = 951 MHz		90		]		
		f <sub>CLK</sub> = 9 GHz , f <sub>OUT</sub> = 1851 MHz		85				
		f <sub>CLK</sub> = 9 GHz , f <sub>OUT</sub> = 2651 MHz		82				
		f <sub>CLK</sub> = 9 GHz , f <sub>OUT</sub> = 3651 MHz		79				
		f <sub>CLK</sub> = 6 GHz , f <sub>OUT</sub> = 501 MHz		72				
		f <sub>CLK</sub> = 6 GHz , f <sub>OUT</sub> = 951 MHz		71				
		f <sub>CLK</sub> = 6 GHz , f <sub>OUT</sub> = 1851 MHz		74				
	Spurious Free Dynamic Range	f <sub>CLK</sub> = 6 GHz , f <sub>OUT</sub> = 2651 MHz		71				
SFDR	excluding HD2, HD3 and CMP2 0 –	f <sub>CLK</sub> = 9 GHz , f <sub>OUT</sub> = 501 MHz		69		dBc		
	f <sub>DAC</sub> /2	f <sub>CLK</sub> = 9 GHz , f <sub>OUT</sub> = 951 MHz		69				
		f <sub>CLK</sub> = 9 GHz , f <sub>OUT</sub> = 1851 MHz		72				
		f <sub>CLK</sub> = 9 GHz , f <sub>OUT</sub> = 2651 MHz		71				
		f <sub>CLK</sub> = 9 GHz , f <sub>OUT</sub> = 3651 MHz		67				
		$f_{CLK} = 6 \text{ GHz}$ , $f_{OUT} = 501 \text{ MHz}$		72				
		f <sub>CLK</sub> = 6 GHz , f <sub>OUT</sub> = 951 MHz		65				
		f <sub>CLK</sub> = 6 GHz , f <sub>OUT</sub> = 1851 MHz		57				
		f <sub>CLK</sub> = 6 GHz , f <sub>OUT</sub> = 2651 MHz		57		]		
HD2	2nd Order Harmonic	f <sub>CLK</sub> = 9 GHz , f <sub>OUT</sub> = 501 MHz		71		dBc		
		f <sub>CLK</sub> = 9 GHz , f <sub>OUT</sub> = 951 MHz		65		]		
		f <sub>CLK</sub> = 9 GHz , f <sub>OUT</sub> = 1851 MHz		62		1		
		f <sub>CLK</sub> = 9 GHz , f <sub>OUT</sub> = 2651 MHz		54		1		
		f <sub>CLK</sub> = 9 GHz , f <sub>OUT</sub> = 3651 MHz		51		1		

# **Electrical Characteristics - AC Specifications (continued)**

Typical values at  $T_A = 25^{\circ}$ C, full temperature range is  $T_{MIN} = -40^{\circ}$ C to  $T_{MAX} = 85^{\circ}$ C, external differential clock mode at 9 GSPS, 12x Interpolation, 0 dBFS,  $f_{OUT} = 2.14$  GHz,  $I_{(OUTFS)} = 40$  mA, nominal supplies, LMFSHd = 84111, unless otherwise noted.

	PARAMETER	TEST CONDITIONS	MIN	TYP	MAX	UNIT		
		$f_{CLK} = 6 \text{ GHz}$ , $f_{OUT} = 501 \text{ MHz}$		63				
		$f_{CLK} = 6 \text{ GHz}$ , $f_{OUT} = 951 \text{ MHz}$		62				
		f <sub>CLK</sub> = 6 GHz , f <sub>OUT</sub> = 1851 MHz	71					
		f <sub>CLK</sub> = 6 GHz , f <sub>OUT</sub> = 2651 MHz		69				
HD3	3rd Order Harmonic	f <sub>CLK</sub> = 9 GHz , f <sub>OUT</sub> = 501 MHz		62		dBc		
		f <sub>CLK</sub> = 9 GHz , f <sub>OUT</sub> = 951 MHz		61				
		f <sub>CLK</sub> = 9 GHz , f <sub>OUT</sub> = 1851 MHz		66				
		f <sub>CLK</sub> = 9 GHz , f <sub>OUT</sub> = 2651 MHz		65				
		f <sub>CLK</sub> = 9 GHz , f <sub>OUT</sub> = 3651 MHz		67				
		f <sub>CLK</sub> = 6 GHz , f <sub>OUT</sub> = 501 MHz		85				
		f <sub>CLK</sub> = 6 GHz , f <sub>OUT</sub> = 951 MHz		85				
		f <sub>CLK</sub> = 6 GHz , f <sub>OUT</sub> = 1851 MHz		82				
		f <sub>CLK</sub> = 6 GHz , f <sub>OUT</sub> = 2651 MHz		79		1		
CMP2	Fs/2 clock mixing product (Fs/2 – f <sub>OUT</sub> )	f <sub>CLK</sub> = 9 GHz , f <sub>OUT</sub> = 501 MHz		78		dBc		
		f <sub>CLK</sub> = 9 GHz , f <sub>OUT</sub> = 951 MHz		76				
		f <sub>CLK</sub> = 9 GHz , f <sub>OUT</sub> = 1851 MHz		73				
		f <sub>CLK</sub> = 9 GHz , f <sub>OUT</sub> = 2651 MHz		74		]		
		f <sub>CLK</sub> = 9 GHz , f <sub>OUT</sub> = 3651 MHz		68				
	-	f <sub>CLK</sub> = 6 GHz , f <sub>OUT</sub> = 501 MHz		92				
		f <sub>CLK</sub> = 6 GHz , f <sub>OUT</sub> = 951 MHz		87				
		f <sub>CLK</sub> = 6 GHz , f <sub>OUT</sub> = 1851 MHz		81				
		f <sub>CLK</sub> = 6 GHz , f <sub>OUT</sub> = 2651 MHz		78				
CMP4+	Fs/N (N = 4, 8, 16) clock mixing product $(f_{OUT} \pm Fs/N)$	f <sub>CLK</sub> = 9 GHz , f <sub>OUT</sub> = 501 MHz		95		dBc		
		f <sub>CLK</sub> = 9 GHz , f <sub>OUT</sub> = 951 MHz		89				
		f <sub>CLK</sub> = 9 GHz , f <sub>OUT</sub> = 1851 MHz		84				
		f <sub>CLK</sub> = 9 GHz , f <sub>OUT</sub> = 2651 MHz		79				
		f <sub>CLK</sub> = 9 GHz , f <sub>OUT</sub> = 3651 MHz		74				
		$f_{CLK}$ = 6 GHz , $f_{OUT}$ = 501 $\pm$ 5 MHz, –6 dBFS each tone		80				
		$f_{CLK}$ = 6 GHz , $f_{OUT}$ = 951 $\pm$ 5 MHz, –6 dBFS each tone		76				
		$f_{CLK}$ = 6 GHz , $f_{OUT}$ = 1851 $\pm$ 5 MHz, –6 dBFS each tone		73				
		$f_{CLK}$ = 6 GHz , $f_{OUT}$ = 2651 $\pm$ 5 MHz, –6 dBFS each tone		72				
MD3	Third-order two-tone intermodulation	$f_{CLK}$ = 9 GHz , $f_{OUT}$ = 501 $\pm$ 5 MHz, –6 dBFS each tone		80		dBc		
	distortion	$f_{CLK}$ = 9 GHz , $f_{OUT}$ = 951 $\pm$ 5 MHz, –6 dBFS each tone		75				
		$f_{CLK}$ = 9 GHz , $f_{OUT}$ = 1851 $\pm$ 5 MHz, –6 dBFS each tone		70				
		$f_{CLK}$ = 9 GHz , $f_{OUT}$ = 2651 $\pm$ 5 MHz, –6 dBFS each tone		70				
		$f_{CLK}$ = 9 GHz , $f_{OUT}$ = 3651 $\pm$ 5 MHz, –6 dBFS each tone		68				



# **Electrical Characteristics - AC Specifications (continued)**

Typical values at  $T_A = 25^{\circ}$ C, full temperature range is  $T_{MIN} = -40^{\circ}$ C to  $T_{MAX} = 85^{\circ}$ C, external differential clock mode at 9 GSPS, 12x Interpolation, 0 dBFS,  $f_{OUT} = 2.14$  GHz,  $I_{(OUTFS)} = 40$  mA, nominal supplies, LMFSHd = 84111, unless otherwise noted.

	PARAMETER	TEST CONDITIONS	MIN	TYP	MAX	UNIT
		f <sub>CLK</sub> = 6 GHz , f <sub>OUT</sub> = 501 MHz		-170		
		$f_{CLK} = 6 \text{ GHz}$ , $f_{OUT} = 951 \text{ MHz}$		-163		
		f <sub>CLK</sub> = 6 GHz , f <sub>OUT</sub> = 1851 MHz		-157		
		f <sub>CLK</sub> = 6 GHz , f <sub>OUT</sub> = 2651 MHz		-155		
		f <sub>CLK</sub> = 9 GHz , f <sub>OUT</sub> = 501 MHz		-172		
		f <sub>CLK</sub> = 9 GHz , f <sub>OUT</sub> = 951 MHz		-166		
NSD Noise Spectra offset <sup>(1)</sup>	Noise Spectral Density > 50 MHz	f <sub>CLK</sub> = 9 GHz , f <sub>OUT</sub> = 1851 MHz		-157		
		f <sub>CLK</sub> = 9 GHz , f <sub>OUT</sub> = 2651 MHz		-156		dBFS/Hz
		f <sub>CLK</sub> = 9 GHz , f <sub>OUT</sub> = 3651 MHz		-153		
		f <sub>CLK</sub> = 6 GHz , f <sub>OUT</sub> = 501 MHz, –9 dBFS		-172		
		f <sub>CLK</sub> = 6 GHz , f <sub>OUT</sub> = 951 MHz, –9 dBFS		-164		
		f <sub>CLK</sub> = 6 GHz , f <sub>OUT</sub> = 1851 MHz, –9 dBFS		-162		
		f <sub>CLK</sub> = 9 GHz , f <sub>OUT</sub> = 2651 MHz, –9 dBFS		-162		
		f <sub>CLK</sub> = 9 GHz , f <sub>OUT</sub> = 3651 MHz, –9 dBFS		-159		
		f <sub>CLK</sub> = 5 GHz , f <sub>OUT</sub> = 501 MHz		-172		
		f <sub>CLK</sub> = 5 GHz , f <sub>OUT</sub> = 951 MHz		-166		
		f <sub>CLK</sub> = 5 GHz , f <sub>OUT</sub> = 1851 MHz		-157		
		f <sub>CLK</sub> = 7.5 GHz , f <sub>OUT</sub> = 501 MHz		-173		
		f <sub>CLK</sub> = 7.5 GHz , f <sub>OUT</sub> = 951 MHz		-167		
NSD		f <sub>CLK</sub> = 7.5 GHz , f <sub>OUT</sub> = 1851 MHz		-159		
(on-chip	Noise Spectral Density > 50 MHz offset On-chip PLL enabled	f <sub>CLK</sub> = 7.5 GHz , f <sub>OUT</sub> = 2651 MHz		-155		dBFS/Hz
PLL)		f <sub>CLK</sub> = 7.5 GHz , f <sub>OUT</sub> = 3651 MHz		-151		
		f <sub>CLK</sub> = 5 GHz , f <sub>OUT</sub> = 501 MHz, –9 dBFS		-169		
		f <sub>CLK</sub> = 5 GHz , f <sub>OUT</sub> = 951 MHz, –9 dBFS		-167		
		f <sub>CLK</sub> = 5 GHz , f <sub>OUT</sub> = 1851 MHz, –9 dBFS		-162		
		f <sub>CLK</sub> = 7.5 GHz , f <sub>OUT</sub> = 2651 MHz, –9 dBFS		-162		1
		f <sub>CLK</sub> = 7.5 GHz , f <sub>OUT</sub> = 3651 MHz, –9 dBFS		-157		1
la alatia.	Isolation between DAC A and DAC B	f <sub>OUT</sub> = 1856 MHz		82		-ID -
Isolation	analog output	f <sub>OUT</sub> = 3105 MHz		73		dBc

(1) Also valid for on-chip PLL enabled in DAC38RF82

# 8.8 PLL/VCO Electrical Characteristics

Typical values at  $T_A = 25^{\circ}$ C, full temperature range is  $T_{MIN} = -40^{\circ}$ C to  $T_{MAX} = 85^{\circ}$ C, internal PLL/VCO clock mode, 12x Interpolation,  $f_{OUT} = 1.8$  GHz,  $I_{(OUTFS)} = 40$  mA, nominal supplies, LMFSHd = 84111, unless otherwise noted.

	PARAMETER	TEST CONDITIONS	TEST CONDITIONS DAC38RF82			DAC38RF89			UNIT
			MIN	TYP	MAX	MIN	TYP	MAX	
PLL/VC	0								
f <sub>ref</sub>	Reference clock frequency		100		f <sub>VCO</sub> /4	100		f <sub>VCO</sub> /4	MHz
f <sub>PFD</sub>	Frequency of phase & frequency detector		100		500	100		500	MHz
f <sub>vcoL</sub>	Low VCO operating frequency		5240		6720	4500		5600	MHz
f <sub>vcoH</sub>	High VCO operating frequency		7960		9000	6600		8400	MHz
f <sub>BW</sub>	Loop filter bandwidth			500			500		KHz
Low V	CO Phase Noise		÷						
	600 KHz			-123					
Frequ	1.2 MHz	<sub>vco</sub> = 6 GHz,CP=5, f <sub>PFD</sub> = 500 MHz, measured at output frequency = 1.8 GHz		-132					
ency Offset	1.8 MHz			-135					
	6.0 MHz			-146					dBc/Hz
	600 KHz						-123		
Frequ	1.2 MHz	f <sub>vco</sub> = 5 GHz,CP=5, f <sub>PFD</sub> = 312.5 MHz,					-132		
ency Offset	1.8 MHz	measured at output frequency = 1.8 GHz					-136		
	6.0 MHz						-147		
High V	CO Phase Noise								
	600 kHz			-123					
Frequ	1.2 MHz	f <sub>vco</sub> = 9 GHz, CP=5, f <sub>PFD</sub> = 500 MHz,		-131					
ency Offset	1.8 MHz	measured at output frequency = 1.8 GHz		-135					l
	6.0 MHz			-148					dDo/U-
	600 kHz						-124		dBc/Hz
Frequ	1.2 MHz	f <sub>vco</sub> = 7.5 GHz, CP=5, f <sub>PFD</sub> = 468.75 MHz,					-132		-
ency Offset	1.8 MHz	measured at output frequency = 1.8 GHz					-136		
	6.0 MHz						-148		



# 8.9 Timing Requirements

JAJSDO4C - FEBRUARY 2017 - REVISED APRIL 2020


			MIN	NOM	MAX	UNIT
Digital Inp	ut Timing Specifications					
Timing: S	/SREF+/-					
t <sub>s(SYSREF)</sub>	Setup time, SYSREF+/- valid to rising edge of DACCLK+/-	SYSREF Capture assist disabled		50		ps
t <sub>h(SYSREF)</sub>	Hold time, SYSREF+/- valid after rising edge of DACCLK+/-	SYSREF Capture assist disabled		50		ps
Timing: Se	erial Port				Ľ	
t <sub>s(/SDEN)</sub>	Setup time, SDEN to rising edge of SCL	<		20		ns
t <sub>s(SDIO)</sub>	Setup time, SDIO valid to rising edge of	SCLK		10		ns
t <sub>h(SDIO)</sub>	Hold time, SDIO valid after rising edge of	f SCLK		5		ns
<b>t</b>	Period of SCLK	temperature sensor read		1		μs
t(SCLK)	Fellod of SCER	All other registers	10 5		ns	
t <sub>d(Data)</sub>	Data output delay after falling edge of SC	CLK		25		ns
t <sub>RESET</sub>	Minimum RESET pulse width			25		ns
Analog Ou	Itput					
t <sub>s(DAC)</sub>	Output settling time to 0.1%			1		ns
t <sub>r</sub>	Output rise time 10% to 90%			50		ps
t <sub>f</sub>	Output fall time 90% to 10%			50		ps
Latency						
	RX SerDes AnalogDelay			250		ps
	DAC wake-up time	$I_{OUT}$ current settling to 1% of $I_{OUTFS}$ from deep sleep		90		μs
	DAC sleep time	$I_{OUT}$ current settling to less than 1% of $I_{OUTFS}$ in deep sleep		90		μs



JAJSDO4C-FEBRUARY 2017-REVISED APRIL 2020


www.ti.com

# 8.10 Typical Characteristics






# **Typical Characteristics (continued)**




# **Typical Characteristics (continued)**






# **Typical Characteristics (continued)**





# **Typical Characteristics (continued)**





# 9 Detailed Description

# 9.1 Overview

The DAC38RF82 and DAC38RF89 are high performance, wide bandwidth RF-sampling digital-to-analog (DACs) that are capable of dual channel input data rate up to 3.33 GSPS or single-channel operation with 8-bits up to 9-GSPS. The devices have a low power JESD204B Interface with up to 8 lanes, with a maximum bit rate of 12.5 Gbps. In dual channel operation, the input interface is capable of data rates up to 3.33 GSPS at 12-bits and 2.5 GSPS at 16-bits resolution without interpolation. When used as a complex baseband transmitter with interpolation modes from 2x to 24x, the DAC38RF82 (or DAC38RF89) is capable of synthesizing wideband signals up to 2 GHz bandwidth with 16-bit input resolution and 2.66 GHz bandwidth with 12-bit input resolution. The 8-bit mode allows an input at the full 9 GSPS maximum DAC sample rate and can synthesize wideband signals from 0 to 4.5 GHz. An optional low jitter PLL/VCO simplifies the DAC clock generation by allowing use of a lower frequency reference clock. DAC38RF82 and DAC38RF89 support different VCO frequency ranges, summarized in Device Comparison Table.

# 9.2 Functional Block Diagrams




Figure 25. 12-, 16-Bit Input Mode Block Diagram



# **Functional Block Diagrams (continued)**




Figure 26. 8-Bit Input Mode Block Diagram

Copyright © 2017-2020, Texas Instruments Incorporated



### 9.3 Feature Description

### 9.3.1 SerDes Inputs

The DAC38RF82 (or DAC38RF89) RX [0..7]+/- differential inputs are each internally terminated to a common point via 50  $\Omega$ , as shown in Figure 27.




Figure 27. Serial Lane Input Termination

Common mode termination is via a 50 pF capacitor to GND. The common mode voltage and termination of the differential signal can be controlled in a number of ways to suit a variety of applications via field TERM in register SRDS\_CFG2 (8.5.87), as described in Table 1.

NOTE

AC coupling is recommended for JESD204B compliance.

TERM	EFFECT
000	Reserved
001	Common point set to 0.7 V. This configuration is for AC coupled systems. The transmitter has no effect on the receiver common mode, which is set to optimize the input sensitivity of the receiver. Note: this mode is not compatible with JESD204B.
01x	Reserved
100	Common point set to GND. This configuration is for applications that require a 0 V common mode.
101	Common point set to 0.25 V. This configuration is for applications that require a low common mode.
110	Reserved
111	Common point floating. This configuration is for DC coupled systems in which the common mode voltage is set by the attached transmit link partner to 0 and 0.6 V. Note: this mode is not compatible with JESD204B

### **Table 1. Receiver Termination Selection**

Input data is sampled by the differential sensing amplifier using clocks derived from the clock recovery algorithm. The polarity of RX+ and RX- can be inverted by setting the bit of the corresponding lane in field INVPAIR in register SRDS\_POL (8.5.88) to "1". This can potentially simplify PCB layout and improve signal integrity by avoiding the need to swap over the differential signal traces.

Due to processing effects, the devices in the RX+ and RX- differential sense amplifiers will not be perfectly matched and there will be some offset in switching threshold. The DAC38RF82 (or DAC38RF89) contains circuitry to detect and correct for this offset. This feature can be enabled by setting ENOC in register SRDS\_CFG1 (8.5.86) to "1". It is anticipated that most users will enable this feature.

### 9.3.2 SerDes Rate

The DAC38RF82 (or DAC38RF89) has eight configurable JESD204B serial lanes. The highest speed of each SerDes lane is 12.5 Gbps. Because the primary operating frequency of the SerDes is determined by its reference clock and PLL multiplication factor, there is a limit on the lowest SerDes rate supported. To support lower speed application, each receiver should be configured to operate at half, quarter or eighth of the full rate via field RATE in register SRDS\_CFG2 (8.5.87). Refer to Table 2 for details.

Texas Instruments

www.ti.com

Table	2.	Lane	Rate	Selection

RATE	EFFECT
00	Full rate. Four data samples taken per SerDes PLL output clock cycle.
01	Half rate. Two data samples taken per SerDes PLL output clock cycle.
10	Quarter rate. One data samples taken per SerDes PLL output clock cycle.
11	Eighth rate. One data samples taken every two SerDes PLL output clock cycles.

# 9.3.3 SerDes PLL

The DAC38RF82 (or DAC38RF89) has two integrated PLLs, one PLL is to provide the clocking of DAC, refer to the DAC PLL section; the other PLL is to provide the clocking for the high speed SerDes. The reference frequency of the SerDes PLL can be in the range of 100-800 MHz nominal, and 300-800 MHz optimal. The reference frequency is derived from DACCLK divided down by the value in field SerDes\_REFCLK\_DIV in register SRDS\_CLK\_CFG (8.5.84), as shown in Figure 28. Field SerDes\_CLK\_SEL in register SRDS\_CLK\_CFG (8.5.84) determines if the DACCLK input or DAC PLL output is used as the source of the SerDes PLL reference. If the DACCLK input is used, a pre-divider set by field SerDes\_REFCLK\_PREDIV in register SRDS\_CLK\_CFG (8.5.84) should be used to reduce the frequency of the DACCLK.




Figure 28. Reference Clock of SerDes PLL

During normal operation, the clock generated by PLL is 4-25 times the reference frequency, according to the multiply factor selected via the field MPY] in register SRDS\_PLL\_CFG (8.5.85). In order to select the appropriate multiply factor and reference clock frequency, it is first necessary to determine the required PLL output clock frequency. The relationship between the PLL output clock frequency and the lane rate is determined by field RATE in register SRDS\_CFG2 (8.5.87) is shown in Table 3. Having computed the PLL output frequency, the reference frequency can be obtained by dividing this by the multiply factor specified via MPY.

· · · · · · · · · · · · · · · · · · ·		
RATE	LINE RATE	PLL OUTPUT FREQUENCY
00	x Gbps	0.25x GHz
01	x Gbps	0.5x GHz
10	x Gbps	1x GHz
11	x Gbps	2x GHz

### Table 3. Relationship Between Lane Rate and SerDes PLL Output Frequency

### Table 4. SerDes PLL Multiplier (MPY) Values

MPY	EFFECT
0x10	4x
0x14	5x
0x18	6x
0x20	8x
0x21	8.25x
0x28	10x
0x30	12x
0x32	12.5x
0x3C	15x
0x40	16x
0x42	16.5x
0x50	20x
0x58	22x
0x64	25x
Other codes	Reserved

The wide range of multiply factors combined with the different rate modes means it is often possible to achieve a given line rate from multiple different reference frequencies. The configuration which utilizes the highest reference frequency achievable is always preferable.

The SerDes PLL VCO must be in the nominal range of 1.5625 - 3.125 GHz. It is necessary to adjust the loop filter depending on the operating frequency of the VCO. If the PLL output frequency is below 2.17 GHz, VRANGE in register SRDS\_PLL\_CFG (8.5.84) should be set high.

Performance of the integrated PLL can be optimized according to the jitter characteristics of the reference clock by setting the appropriate loop bandwidth via field LB in register SRDS\_PLL\_CFG (8.5.84). The loop bandwidth is obtained by dividing the reference frequency by BWSCALE, where the BWSCALE is a function of both LB and PLL output frequency as shown in Table 5.

LB	EFFECT	BWSCALE vs PLL OUTPUT FREQUENCY		
		3.125 GHz	2.17 GHz	1.5625 GHz
00	Medium loop bandwidth	13	14	16
01	Ultra high loop bandwidth	7	8	8
10	Low loop bandwidth	21	23	30
11	High loop bandwidth	10	11	14

### Table 5. SerDes PLL Loop Bandwidth Selection


An approximate loop bandwidth of 8 - 30 MHz is suitable and recommended for most systems where the reference clock is via low jitter clock input buffer. For systems where the reference clock is via a low jitter input cell, but of low quality, an approximate loop bandwidth of less than 8 MHz may offer better performance. For systems where the reference clock is cleaned via an ultra-low jitter LC-based cleaner PLL, a high loop bandwidth up to 60 MHz is more appropriate. Note that the use of ultra-high loop bandwidth setting is not recommended for PLL multiply factor of less than 8.



A free running clock output is available when field ENDIVCLK in register SRDS\_PLL\_CFG (8.5.85) is set high. It runs at a fixed divided-by-80 of the PLL output frequency and can be output on the ALARM pin by setting field DTEST to "0001" (lanes 0 - 3) or "0010" (lanes 4 - 7) in register DTEST (8.5.76).

### 9.3.4 SerDes Equalizer

All channels of the DAC38RF82 (or DAC38RF89) incorporate an adaptive equalizer, which can compensate for channel insertion loss by attenuating the low frequency components with respect to the high frequency components of the signal, thereby reducing inter-symbol interference. Figure 29 shows the response of the equalizer, which can be expressed in terms of the amount of low frequency gain and the frequency up to which this gain is applied (i.e., the frequency of the 'zero'). Above the zero frequency, the gain increases at 6 dB/octave until it reaches the high frequency gain.





The equalizer can be configured via fields EQ and EQHLD in register SRDS\_CFG1 (8.5.86). Table 6 and Table 7 summarize the options. When enabled, the receiver equalization logic analyzes data patterns and transition times to determine whether the low frequency gain should be increased or decreased. The decision logic is implemented as a voting algorithm with a relatively long analysis interval. The slow time constant that results reduces the probability of incorrect decisions but allows the equalizer to compensate for the relatively stable response of the channel. The lock time for the adaptive equalizer is data dependent, and so it is not possible to specify a generally applicable absolute limit. However, assuming random data, the maximum lock time will be 6x106 divided by the CDR activity level. For field CDR in register SRDS\_CFG1 (8.5.86) = 110, the activity level is  $1.5 \times 10^6 \text{ UI}$ .

When EQ[2] = 0, finer control of gain boost is available using the EQBOOST IEEE1500 tuning chain field, as shown in Table 6.

E	EQ	EFFECT
	00	No equalization. The equalizer provides a flat response at the maximum gain. This setting may be appropriate if jitter at the receiver occurs predominantly as a result of crosstalk rather than frequency dependent loss.
[1 0]	01	Fully adaptive equalization. The zero position is determined by the selected operating rate, and the low frequency gain of the equalizer is determined algorithmically by analyzing the data patterns and transition positions in the received data. This setting should be used for most applications.
[1-0]	10	Precursor equalization analysis. The data patterns and transition positions in the received data are analyzed to determine whether the transmit link partner is applying more or less precursor equalization than necessary.
	11	Postcursor equalization analysis. The data patterns and transition positions in the received data are analyzed to determine whether the transmit link partner is applying more or less post-cursor equalization than necessary.

### **Table 6. Receiver Equalization Configuration**

### Table 6. Receiver Equalization Configuration (continued)

EQ		EFFECT
	0	Default
[2]	1	Boost. Equalizer gain boosted by 6 dB, with a 20% reduction in bandwidth, and an increase of 5mW power consumption. May improve performance over long links.

### Table 7. Receiver Equalizer Hold

EQHOLD	EFFECT
0	Equalizer adaption enabled. The equalizer adaption and analysis algorithm is enabled. This should be the default state.
1	Equalizer adaption held. The equalizer is held in its current state. Additionally, the adaption and analysis algorithm is reset.

# Table 8. Relationship Between Lane Rate and SerDes PLL Output Frequency

EQBOOST	GAIN BOOST (dB)	BANDWIDTH CHANGE (%)	POWER INCREASE (mW)
00	0	0	0
01	2	-30	0
01	4	10	5
11	6	-20	5

When EQ is set to 010 or 011, the equalizer is reconfigured to provide analytical data about the amount of pre and post cursor equalization respectively present in the received signal. This can in turn be used to adjust the equalization settings of the transmitting link partner, where a suitable mechanism for communicating this data back to the transmitter exists. Status information is provided by setting field DTEST in register DTEST (8.5.76) to "0111" for EQOVER and "0110" for EQUNDER. The procedure is as follows:

- 1. Enable the equalizer by setting fields EQHLD low and EQ to "001" (register SRDS\_CFG1 8.5.86). Allow sufficient time for the equalizer to adapt;
- 2. Set EQHLD to 1 to lock the equalizer and reset the adaption algorithm. This also causes both EQOVER and EQUNDER to become low;
- 3. Wait at least 48 UI, and proportionately longer if the CDR activity is less than 100%, to ensure the 1 on EQHLD is sampled and acted upon;
- 4. Set EQ to "010" or "011", and EQHLD to 0. The equalization characteristics of the received signal are analysed (the equalizer response will continue to be locked);
- 5. Wait at least 150×103 UI to allow time for the analysis to occur, proportionately longer if the CDR activity is less than 100%;
- 6. Examine EQOVER and EQUNDER for results of analysis
  - If EQOVER is high, it indicates the signal is over equalized;
  - If EQUNDER is high, it indicates the signal is under equalized;
- 7. Set EQHLD to 1;
- 8. Repeat items 3-7 if required;
- 9. Set EQ to "001", and EQHLD to 0 to exit analysis mode and return to normal adaptive equalization.

### NOTE

When changing EQ from one non-zero value to another, EQHLD must already be 1. If this is not the case, there is a chance the equalizer could be reset by a transitory input state (i.e., if EQ is momentarily 000). EQHLD can be set to 0 at the same time as EQ is changed.

As the equalizer adaption algorithm is designed to equalize the post cursor, EQOVER or EQUNDER will only be set during post cursor analysis if the amount of post cursor equalization required is more or less than the adaptive equalizer can provide.



### 9.3.5 JESD204B Descrambler

The descrambler is a 16-bit parallel self-synchronous descrambler based on the polynomial 1 + x14 + x15. From the JESD204B specification, the scrambling/descrambling process only occurs on the user data, not on the code group synchronization or the ILA sequence. Each multi-DUC has a separate descrambler that can be enabled independently. The descrambler is enabled by field SCR in the multi-DUC paged register JESD\_N\_HD\_SCR (8.5.49).

### 9.3.6 JESD204B Frame Assembly

The DAC38RF82 (or DAC38RF89) may be programmed as a single or dual DAC device, with one JESD RX block designated for each DAC. The two JESD RX blocks can be programmed to operate as two separate links or as a single link.

The JESD204B defines the following parameters:

- L is the number of lanes
- M is the number of I or Q streams per device (2 = 1 IQ pair, 4 = 2 IQ pairs, 8 = 4 IQ pairs)
- F is the number of octets per frame clock period
- S is the number of samples per frame
- HD is the High-Density bit which controls whether a sample may be divided over more lanes
- N = NPRIME is the number of bits per sample (12 or 16 bits)

Fields K and L are found in multi-DUC paged register JESD\_K\_L (8.5.46), M and S in multi-DUC paged register JESD\_M\_S (8.5.48), and N, NPRIME and HD in multi-DUC paged register JESD\_N\_HD\_SCR (8.5.49).

Table 9 lists the available JESD204B formats, interpolation rates and sample rate limits for the DAC38RF82 (or DAC38RF89). The ranges are limited by the SerDes PLL VCO frequency range, the SerDes PLL reference clock range, the maximum SerDes line rate, and the maximum DAC sample frequency. Table 10 through Table 27 lists the frame formats for each mode. In the frame format tables, i CH (N) [x:y] and q CH (N) [x:y] are bits x through y of the I and Q samples at time N of DUC channel CH. If [x..y] is not listed, the full sample is assumed. For example, i0(0)[15:8] are bits 15 – 8 of the I sample at time 0, and q(1) is the full Q sample at time 1.

L-M-F-S-Hd 1 TX	L-M-F-S-Hd 2 TX	Frame Format	Input Resolution	IQ pairs per DAC	Interp	Input rate max (MSPS)	f <sub>DAC</sub> Max (MSPS)
			16	1	6	1500	9000
00404	NIA	4 TV: Table 40	16	1	8	1125	9000
82121	NA	1 TX: Table 10	16	1	12	750	9000
			16	1	16	max (MSPS)           1500           1125           750           562.5           1250           1125           900           750           562.5           500           375           625           500           375           500           375           500           375           525           500           450           375           312.5	9000
			16	1	6	1250	7500
			16	1	8	1125	9000
			16	1	10	900	9000
42111	84111	1 TX: Table 11 2 TX: Table 12	16	1	12	750	9000
			16	1	16	562.5	9000
			16	1	18	500	9000
			16	1	24	375	9000
			16	1	8	625	5000
			16	1	12	625	7500
22210	44210	1 TX: Table 13	16	1	16	562.5	9000
22210	44210	2 TX: Table 14	16	1	18	500	9000
			16	16 1 20 4	450	9000	
			16	1	24	1125           750           562.5           1250           1125           900           750           562.5           500           375           625           562.5           500           375           625           562.5           500           450           375	9000
10110	24440	1 TX: Table 15	16	1	16	312.5	5000
12410	24410	2 TX: Table 16	16	1	24	312.5	7500

### Table 9. JESD204B Formats for DAC38RF82 and DAC38RF89



Input rate max (MSPS) f<sub>DAC</sub> Max (MSPS) L-M-F-S-Hd L-M-F-S-Hd Input IQ pairs per **Frame Format** Interp 1 TX 2 TX Resolution DAC 1 TX: Table 17 2 TX: Table 18 562.5 312.5 1 TX: Table 19 2 TX: Table 20 312.5 1 TX: Table 21 2 TX: Table 22 NA 1 TX: Table 23 real input 1 TX: Table 24 real input<sup>(1)</sup> 2 TX: Table 25 1 TX: Table 26 real input<sup>(1)</sup> 2 TX: Table 27 

### Table 9. JESD204B Formats for DAC38RF82 and DAC38RF89 (continued)

(1) Can also be used as I-Q pair per 2 DACs. See description in Wideband DUC (wide-DUC)

### Table 10. JESD204B Frame Format for LMFSHd = 82121

# un bits	4	8		
# en bits	5	10		
Nibble	1	2		
lane RX0	i0[15:8]			
lane RX1	i0[7:0]			
lane RX2	i1[15:8]			
lane RX3	i1[7:0]			
lane RX4	q0[15:8]			
lane RX5	q0[7:0]			
lane RX6	q1[15:8]			
lane RX7	q1[7:0]			

### Table 11. JESD204B Frame Format for LMFSHd = 42111

# un bits	4	8	
# en bits	5	10	
Nibble	1	2	
lane RX0	i0[15:8]		
lane RX1	i0[7:0]		
lane RX2	q0[15:8]		
lane RX3	q0[7:0]		

### Table 12. JESD204B Frame Format for LMFSHd = 84111

# un bits	4	8		
# en bits	5	10		
Nibble	1	2		
lane RX0	A-i0[15:8] <sup>(1)</sup>			
lane RX1	A-i0[7:0] <sup>(2)</sup>			

(1) DAC A, I sample 0, MSB byte

(2) DAC A, I sample 0, LSB byte

STRUMENTS

AS

lane RX2	A-q0[15:8]
lane RX3	A-q0[7:0]
lane RX4	B-i0[15:8]
lane RX5	B-i0[7:0]
lane RX6	B-q0[15:8]
lane RX7	B-q0[7:0]

# Table 13. JESD204B Frame Format for LMFSHd = 22210

# un bits	4	8	12	16		
# en bits	5	10	15	20		
Nibble	1	2	3	4		
lane RX0	iO					
lane RX1	q0					

### Table 14. JESD204B Frame Format for LMFSHd = 44210

# un bits	4	8	12	16	
# en bits	5	10	15	20	
Nibble	1	2	3	4	
lane RX0	A-i0 <sup>(1)</sup>				
lane RX1	A-q0				
lane RX2	B-i0				
lane RX3	B-q0				

(1) DAC A, I sample 0

### Table 15. JESD204B Frame Format for LMFSHd = 12410

# un bits	4	8	12	16	20	24	28	32
# en bits	5	10	15	20	25	30	35	40
Nibble	1	2	3	4	5	6	7	8
lane RX0	iO				q	0		

# un bits	4	8	12	16	20	24	28	32
# en bits	5	10	15	20	25	30	35	40
Nibble	1	2	3	4	5	6	7	8
lane RX0	A-i0 <sup>(1)</sup>			A-q0				
lane RX1	B-i0				B-	q0		

(1) DAC A, I sample 0

# Table 17. JESD204B Frame Format for LMFSHd = 44210

# un bits	4	8	12	16	
# en bits	5	10	15	20	
Nibble	1	2	3	4	
lane RX0	A1-i0 <sup>(1)</sup>				
lane RX1	A1-q0 <sup>(2)</sup>				
lane RX2	A2-i0				

DAC A, MultiDUC 1, I sample 0
 DAC A, MultiDUC 2, I sample 0



# Table 17. JESD204B Frame Format for LMFSHd = 44210 (continued)

	lane	RX3

A2-q0

Table	7 10. JLJDZ04L			5210			
# un bits	4	8	12	16			
# en bits	5	10	15	20			
Nibble	1	2	3	4			
lane RX0	A1-i0 <sup>(1)</sup>						
lane RX1	A1-q0						
lane RX2	A2-i0						
lane RX3		A	2-q0				
lane RX4	B1-i0						
lane RX5	B1-q0						
lane RX6	B2-i0						
lane RX7	B1-q0						

Table 18. JESD204B Frame Format for LMFSHd = 88210

(1) DAC A, MultiDUC 1, I sample 0

### Table 19. JESD204B Frame Format for LMFSHd = 24410

# un bits	4	8	12	16	20	24	28	32
# en bits	5	10	15	20	25	30	35	40
Nibble	1	2	3	4	5	6	7	8
lane RX0	A1-i0 <sup>(1)</sup>				A1-q0			
lane RX1	A2-i0				A2	-q0		

(1) DAC A, MultiDUC 1, I sample 0

Table 20. JESD204B Frame Format for LMFSHd = 484 <sup>2</sup>	0
---	---

# un bits	4	8	12	16	20	24	28	32	
# en bits	5	10	15	20	25	30	35	40	
Nibble	1	2	3	4	5	6	7	8	
lane RX0		A1-	i0 <sup>(1)</sup>		A1-q0				
lane RX1		A2	-i0		A2-q0				
lane RX2	B1-i0				B1-q0				
lane RX3	B2-i0				B2-q0				

(1) DAC A, MultiDUC 1, I sample 0

# un bits	4	8	12	16	20	24
# en bits	5	10	15	20	25	30
Nibble	1	2	3	4	5	6
lane RX0	A1-i0 <sup>(1)</sup>			A1-q0		
lane RX1	A2-i0				A2-q0	

(1) DAC A, MultiDUC 1, I sample 0

### Table 22. JESD204B Frame Format for LMFSHd = 48310

# un bits	4	8	12	16	20	24
# en bits	5	10	15	20	25	30

STRUMENTS

EXAS

Nibble	1	2	3	4	5	6	
lane RX0	A1-i0 <sup>(1)</sup>			A1-q0			
lane RX1	A2-i0			A2-q0			
lane RX2	B1-i0			lane RX2 B1-i0 B1-q0			
lane RX3	B2-i0				B2-q0		

### (1) DAC A, MultiDUC 1, I sample 0

# Table 23. JESD204B Frame Format for LMFSHd = 81180

# un bits	4	8			
# en bits	5	10			
Nibble	1	2			
lane RX0		A0 <sup>(1)</sup>			
lane RX1	A1				
lane RX2	A2				
lane RX3	A3				
lane RX4	A4				
lane RX5	A5				
lane RX6	A6				
lane RX7	Α7				

(1) DAC A, sample 0

### Table 24. JESD204B Frame Format for LMFSHd = 41380

# un bits	4	8	12	16	20	24	
# en bits	5	10	15	20	25	30	
Nibble	1	2	3	4	5	6	
lane 0	A-0 <sup>(1)</sup>			A-1			
lane 1	A-2			A-3			
lane 2	A-4			A-5			
lane 3	A-6				A-7		

(1) DAC A, sample 0

### Table 25. JESD204B Frame Format for LMFSHd = 82380

# un bits	4	8	12	16	20	24
# en bits	5	10	15	20	25	30
Nibble	1	2	3	4	5	6
lane 0	i(0)			i(1)		
lane 1	i(2)			i(3)		
lane 2	i(4)			i(5)		
lane 3	i(6)			i(7)		
lane 4		q(0)		q(1)		
lane 5	q(2)			q(3)		
lane 6	q(4)			q(5)		
lane 7	q(6)				q(7)	



# un bits	4	8
# en bits	5	10
Nibble	1	2
lane 0	A-0[15:8] <sup>(1)</sup>	
lane 1	A-0[7:0] <sup>(2)</sup>	
lane 2	A-1[15:8]	
lane 3	A-1[7:0]	

DAC A, sample 0, MSB byte
 DAC A, sample 0, LSB byte

#### Table 27. JESD204B Frame Format for LMFSHd = 82121

# un bits	4	8
# en bits	5	10
Nibble	1	2
lane RX0	A-0[15:8] <sup>(1)</sup>	
lane RX1	A-0[7:0] <sup>(2)</sup>	
lane RX2	A-1[15:8]	
lane RX3	A-1[7:0]	
lane RX4	B-0[15:8]	
lane RX5	B-0[7:0]	
lane RX6	B-1[15:8]	
lane RX7	B-1[7:0]	

DAC A, sample 0, MSB byte
 DAC A, sample 0, LSB byte



## 9.3.7 SYNC Interface

The DAC38RF82 (or DAC38RF89) JESD204B interface has two differential SYNC outputs called SYNC0 and SYNC1 to support one or two links. Alternatively, GPO0 and GPO1 can be used to output SYNC as a singleended CMOS level. Each of the differential or CMOS outputs is enabled by a 2-bit register (fields GPO0\_SEL, GPO1\_SEL, SYNC0B\_SEL, SYNC1B\_SEL in register IO\_CONFIG 8.5.2), with bit 0 enabling multi-DUC1 SYNC and bit 1 enabling multi-DUC2 SYNC. If both are enabled, the SYNC\ signals are OR'ed.

The SYNC signal can be asserted low by the receiver either to make a synchronization request to initialize/reinitialize the link or to report an error to the transmitter. Synchronization requests must have a minimum duration of five frames plus nine octets rounded up to the nearest whole number of frames. To report an error, the SYNC signal is asserted for exactly two frames. The transmitter interprets any negative edge of its SYNC input as an error and any SYNC assertion lasting four frames or longer as a synchronization request. See the following sections in the standard for more details.

- 7.6.3 Errors requiring re-initialization
- 7.6.4 Error reporting via SYNC interface
- 8.4 SYNC signal decoding

## 9.3.8 Single or Dual Link Configuration

The DAC38RF82 (or DAC38RF89) JESD204B interface can be configures with one or two links. The advantage of using two links, one for each DAC, is that one link can be re-established without affecting the other link and DAC.

The configuration for each mode of operation are:

- 1. Dual DAC, dual link
  - a. Program fields OCTETPATH0\_SEL to OCTETPATH7\_SEL in multi-DUC paged registers JESD\_CROSSBAR1 (8.5.57) and JESD\_CROSSBAR2 (8.5.58) so that each multi-DUC will pick data off of the appropriate SerDes lane.
  - b. Appropriate bits in field LANE\_ENA in multi-DUC paged register JESD\_LN\_EN (8.5.45) must be set for each multi-DUC enable the lanes used.
  - c. Field ONE\_DAC\_ONLY in register RESET\_CONFIG (8.5.1) should be '0' (default).
- 2. Dual DAC, single link
  - a. Program OCTETPATH0\_SEL to OCTETPATH7\_SEL in multi-DUC paged registers JESD\_CROSSBAR1 (8.5.57) and JESD\_CROSSBAR2 (8.5.58) so that each multi-DUC will pick data off the appropriate SerDes lane.
  - b. Appropriate bits in field LANE\_ENA in multi-DUC paged register JESD\_LN\_EN (8.5.45) must be set for each multi-DUC enable the lanes used.
  - c. Set field ONE\_LINK\_ONLY to '1' to configure TXENABLE output.
- 3. Single DAC, single link
  - a. Set Field ONE\_DAC\_ONLY in register RESET\_CONFIG (8.5.1) to '1' to gate clocks to unused multi-DUC2 for power savings.
  - b. ONE\_LINK\_ONLY bit does not matter in this case.

### 9.3.9 Multi-Device Synchronization

In many applications, such as multi antenna systems where the various transmit channels information is correlated, it is required that the latency across the link is deterministic and multiple DAC devices are completely synchronized such that their outputs are phase aligned. The DAC38RF82 (or DAC38RF89) achieves the deterministic latency using SYSREF (JESD204B Subclass 1).

SYSREF is generated from the same clock domain as DACCLK. After having resynchronized its local multiframe clock (LMFC) to SYSREF, the DAC will request a link re-initialization via SYNC interface. Processing of the signal on the SYSREF input can be enabled and disabled via the SPI interface.

The SYSREF capture circuit and the timing requirements relative to device clock are described in SYSREF Capture Circuit.



#### 9.3.10 SYSREF Capture Circuit

The JESD204B standard for Device Subclass 1 introduces a SYSREF signal that can be used as a global timing reference to align the phase of the internal local multiframe clock (LMFC) and frame clock across multiple devices. This allows the system to achieve deterministic latency and align data samples across several data converters. The SYSREF signal accomplishes this goal by identifying a device clock edge for each chip that can be used as an alignment reference. In particular, the LMFC and frame clock align to the device clock edge upon which the SYSREF transition from "0" to "1" is sampled. SYSREF may be periodic, one-shot, or "gapped" periodic and its period must be a multiple of the LMFC period.




Figure 30. SYSREF Signal Timing

With high-speed device clocks, the phase of the SYSREF signals relative to the device clock must meet the setup/hold time requirements of each individual device clock. Historically, this has been done by controlling the board-level routing delay and/or employing commercial clock distribution capable of generating device clocks and SYSREF signals with programmable delays and with the option of splitting SYSREF into multiple SYSREFS, each with its own fine-tuned delay. Since the DAC38RF82 (or DAC38RF89) supports device clock frequencies up to 9 GHz, a SYSREF capture circuit is includes in the DAC38RF82 (or DAC38RF89) that allows a relaxation in meeting the device clock setup and hold.

The SYSREF capture circuit provides:

- tolerance to manufacturing and environmental variations in SYSREF phase
- immunity to sampling errors due to setup/hold/meta-stability
- information about phase of SYSREF relative to DAC clock inside the data converter
- software compensation for phase misalignment due to PCB design errors

The concepts behind the SYSREF capture scheme are illustrated in Figure 31.






Figure 31. SYSREF Capture Strategy and Phase Tolerance Windows

To understand Figure 31, to begin with we'll ignore the SYSREF phase tolerance windows in the lower portion of the figure and focus on the blue clock waveform at the top of the figure. This waveform represents the device clock input to a particular DAC chip. The green arrows, labeled "R" and "F", correspond to the rising and falling edges of this clock (ignoring for the moment the additional arrows labeled "ER" and "EF"). While previous devices with lower device clocks captured SYSREF only on the rising edge of the device clock, the new scheme samples SYSREF on the falling edge as well, which provides more flexibility when optimizing the setup and hold time of the SYSREF capture path. Moreover, each time a rising SYSREF edge is captured, the chip remembers the clock phase during which the event occurred, and the system designer can later read back the phase information to observe the SYSREF timing relative to the device clock at the internal capture point. If SYSREF transitions close to the rising or falling clock edge sampling points the capture flop setup and hold time may not be met and the observed phase may be unreliable and subject to meta-stability phenomenon.

To reduce the sensitivity to setup/hold/meta-stability concerns an "early" version of the device clock is generated within the DAC and additional SYSREF samples are taken at the "early falling" and "early rising" edges of the clock (labeled "EF" and "ER", respectively, in Figure 31). The resulting set of four samples is used to narrow down the timing of the rising SYSREF edge to one of four possible clock phases. If the rising SYSREF transition takes place between the "EF" and "F" samples, then SYSREF is said to occur in phase  $\theta$ 1. Similarly, if it takes place between the "F" and "ER" samples, then it is said to occur in phase  $\theta$ 2. If SYSREF transitions between the "ER" and "R" samples, then it is said to occur in phase  $\theta$ 4. As mentioned before, the chip remembers all observed SYSREF phases and the user can later read them back. Since the delay between "early" and "on time" versions of the clock is intentionally chosen to be larger than the setup/hold/meta-stability window, at most one of the four samples can be affected even when the SYSREF transitions right at one of the four sampling points. Thus, the uncertainty in the observed SYSREF timing is limited to adjacent phases, and with twice as many sampling phases the resolution of the timing information is improved by a factor of two.

Referring to the lower portion of Figure 31, the user can now see how this information regarding the observed SYSREF phases is used to devise a reliable SYSREF capture methodology with a high degree of tolerance to manufacturing and environmental variations in SYSREF phase. Based on the SYSREF phases observed for a particular DAC chip during system characterization, the system designer can select one of four so-called "phase tolerance window" options (denoted "00", "01", "10", and "11") to maximize immunity to manufacturing and environmental variations. For example, consider the default phase tolerance window labeled "window=00" in the figure. If, during characterization, the system designer observes (by reading back the recorded phase observations) that the rising SYSREF edge nominally occurs in either  $\theta 1$  or  $\theta 2$  or both (i.e.  $\theta 12$ ) then he would




program that particular DAC chip to use phase tolerance window "00". This mapping is indicated in the figure with the label " $\theta 1|\theta 12|\theta 2$ : window=00". Having programmed the device to use window "00", all future SYSREF events that occur in  $\theta 1$  or  $\theta 2$  would trigger the LMFC and frame clock to be aligned using the following rising clock edge as the alignment reference (as indicated by the red arrow pointing to rising clock edge "R" and labeled "Window=00/01 alignment edge").

The full extent of each phase tolerance window is indicated in the figure using "box and whisker" plots. For the "window=00" example, the "box" portion of the plot indicates that the phase tolerance window is centered on  $\theta$ 12 (to be precise on the boundary between  $\theta$ 1 and  $\theta$ 2) and the "whisker" portion indicates that even if the rising edge of SYSREF occurs as early as the preceding  $\theta$ 4 or as late as the following  $\theta$ 3 it still results in LMFC and frame clock alignment to the same rising clock edge indicated by the red arrow labeled "Window=00/01 alignment edge". When programmed for phase tolerance window "00", the DAC chip is tolerant to variations in the SYSREF timing ranging from a rising SYSREF edge that occurs just after one rising edge of clock to just before the next rising edge of the clock. The qualifying phrases "just after" and "just before" are used here to indicate that the SYSREF transition must occur far enough away from the rising edges of the clock to avoid setup/hold violations and prevent the device from concluding that the SYSREF transition has crossed out off the phase tolerance window when in fact it has not. The tolerance range for window "00" is from rising clock edge to rising clock edge and is indicated in the figure by the green text labeled "tolerance = R $\leftrightarrow$ R".

Following the above example, if characterization reveals SYSREF timing centered on  $\theta$ 23 then phase tolerance window "01" (with tolerance for SYSREF rising edge events from EF to EF) should be chosen. Notice that this option is tolerant even to rising SYSREF edges that occur after the rising device clock edge (i.e. in  $\theta$ 4) and will treat them just as if they had occurred in one of the earlier three phases, aligning to the same rising device clock edge indicated by the red arrow labeled "Window=00/01 Alignment Edge". This allows the system designer to tolerate PCB design errors and/or environmental and manufacturing variations – achieving his intended alignment without having to make physical changes to the board to adjust the SYSREF timing.

Similarly, if characterization indicates that SYSREF timing is centered on  $\theta$ 34 or  $\theta$ 41 then phase tolerance window "10" or "11" can be selected, resulting in tolerance for "F $\leftrightarrow$ F" or "ER $\leftrightarrow$ ER" SYSREF timing, respectively. Note, however, that in these two cases the alignment reference edge is by default taken to be the subsequent rising edge of the device clock. Since this may not be the desired behavior, the DAC38RF82 (or DAC38RF89) allows the user to program in an optional alignment offset of  $\theta$ 1 if the default offset of 0 does not achieve the desired alignment. This feature is illustrated in Figure 32 where the user can see that by setting the alignment offset to -1, phase tolerance windows "10" and "11" can be made to trigger alignment to the earlier rising device clock edge used by windows "00" and "01". Alternatively, the window "00" and "01" alignment edge can be pushed one cycle later by setting their alignment offset to +1.







Several important controls related to SYSREF alignment and capture timing are contained in register SYSR\_CAPTURE (8.5.78). For example, as mentioned before, the device is capable of monitoring the observed phases of the rising SYSREF edge events; however, in order to avoid unwanted noise coupling from the SYSREF circuits into the DAC output, the SYSREF monitoring circuits are disabled by default. Field SYSR\_STATUS\_ENA enables SYSREF status monitoring. Field SYSR\_PHASE\_WDW contains the the phase tolerance window selected for normal operation, which is optimized during characterization. Field SYSR\_ALIGN\_DLY contains the control that allows the system designer to optionally offset the SYSREF alignment event by ±1 device clock cycles. Field SYSR\_STATUS\_ENA enables the SYSREF capture alignment accumulation and will generate alarms when enabled. Writing a "1" to field SYSR\_ALIGN\_SYNC clears the accumulated SYSREF alignment statistics. The SYSREF alignment block can be bypassed completely by field SYSREF\_BYPASS\_ALIGN, in which case SYSREF is latched by the rising edge of DACCLK.

When field SYSR\_STATUS\_ENA is high the device records the phase associated with each SYSREF event for use in characterizing the SYSREF capture timing and selecting an appropriate phase tolerance window. The phase data is available in two forms. First, each of the four phases has a corresponding "sticky" alarm flag indicating which phases have been observed since the last time the register was cleared. In addition, the device also accumulates statistics on the relative number of occurrences of each phase spanning multiple SYSREF events using saturating 8-bit counters. These accumulated real-time SYSREF statistics allow us to account for time-varying effects during characterization such as potential timing differences between the 1st and Nth edges in a "gapped" SYSREF pulse train. The counters are fields PHASE1\_CNT and PHASE2\_CNT in register SYSREF12\_CNT (8.5.10), PHASE3\_CNT and PHASE4\_CNT in register SYSREF34\_CNT (8.5.11), and ALIGN\_TO\_R1\_CNT and ALIGN\_TO\_R3\_CNT in register SYSREF\_ALIGN\_R (8.5.9).

The accumulated SYSREF statistics can be cleared by writing '1' to SYSR\_ALIGN\_SYNC. This sync signal affects only the SYSREF statistics monitors and does not cause a sync of any other portions of the design. Before collecting phase statistics, the user must first enable the SYSREF status monitoring logic by setting the SYSR\_STATUS\_ENA bit. The user must then generate a repeating SYSREF input before using SYSR\_ALIGN\_SYNC to clear the statistic counters. This is necessary to flush invalid data out of the status pipeline.

The "sticky" alarm flags indicating which of the four phases have been observed since the last SYSR\_ALIGN\_SYNC write of '1' are fields ALM\_SYSRPHASE1 to ALM\_SYSRPHASE4 and are contained in the ALM\_SYSREF\_DET register (8.5.6).

### 9.3.11 JESD204B Subclass 0 Support

Some functionality has been implemented to support Subclass 0 operation. Note that programming the SUBCLASSV configuration parameter has no functional impact on the logic. The value programmed for SUBCLASSV is only used in the initial lane alignment (ILA) sequence. The following configuration parameters are used to support Subclass 0 operation:

- Field SYSREF\_MODE in register JESD\_SYSR\_MODE (8.5.56) = 0
- Field DISABLE\_ERR\_RPT in register JESD\_ERR\_OUT (8.5.53) = 1
- Field MIN\_LATENCY\_ENA in register JESD\_MATCH (8.5.50) = 1



## 9.3.12 SerDes Test Modes through Serial Programming

The DAC38RF82 (or DAC38RF89) supports a number of basic pattern generation and verification of SerDes via the serial interface. Three pseudo random bit stream (PRBS) sequences are available, along with an alternating 0/1 pattern and a 20-bit user-defined sequence. The  $2^7 - 1$ ,  $2^{31} - 1$  or  $2^{23} - 1$  sequences implemented can often be found programmed into standard test equipment, such as a Bit Error Rate Tester (BERT). Pattern generation and verification selection is via field TESTPATT in register SRDS\_CFG1 (8.5.86), as shown in Table 28.

### Table 28. SerDes Test Pattern Selection

TESTPATT	EFFECT
000	Test mode disabled.
001	Alternating 0/1 Pattern. An alternating 0/1 pattern with a period of 2 UI.
010	Verify $2^7 - 1$ PRBS. Uses a 7-bit LFSR with feedback polynomial $x^7 + x^6 + 1$ .
011	Verify $2^{23}$ - 1 PRBS. Uses an ITU O.150 conformant 23-bit LFSR with feedback polynomial $x^{23} + x^{18} + 1$ .
100	Verify $2^{31}$ - 1 PRBS. Uses an ITU O.150 conformant 31-bit LFSR with feedback polynomial $x^{31} + x^{28} + 1$ .
101	User-defined 20-bit pattern. Uses the USR PATT IEEE1500 Tuning instruction field to specify the pattern. The default value is 0x66666.
11x	Reserved.

Pattern verification compares the output of the serial to parallel converter with an expected pattern. When there is a mismatch, the TESTFAIL bit is driven high, which can be programmed to come out the ALARM terminal by setting field DTEST in register DTEST (8.5.76) to "0011".

## 9.3.13 SerDes Test Modes through IEEE 1500 Programming

DAC38RF82 (or DAC38RF89) also provide a number of advanced diagnostic capabilities controlled by the IEEE 1500 interface. These are:

- Accumulation of pattern verification errors;
- The ability to map out the width and height of the receive eye, known as Eye Scan;
- Rreal-time monitoring of internal voltages and currents; The SerDes blocks support the following IEEE1500 instructions:

INSTRUCTION	OPCODE	DESCRIPTION
ws_bypass	0x00	Bypass. Selects a 1-bit bypass data register. Use when accessing other macros on the same IEEE1500 scan chain.
ws_cfg	0x35	Configuration. Write protection options for other instructions.
ws_core	0x30	Core. Fields also accessible via dedicated core-side ports.
ws_tuning	0x31	Tuning. Fields for fine tuning macro performance.
ws_debug	0x32	Debug. Fields for advanced control, manufacturing test, silicon characterization and debug.
ws_unshadowed	0x34	Unshadowed. Fields for silicon characterization.
ws_char	0x33	Char. Fields used for eye scan.

#### Table 29. IEEE1500 Instruction for SerDes Receivers

The data for each SerDes instruction is formed by chaining together sub-components called head, body (receiver or transmitter) and tail. DAC38RF82 (or DAC38RF89) uses two SerDes receiver blocks R0 and R1, each of which contains 4 receive lanes (channels), the data for each IEEE1500 instruction is formed by chaining {head, receive lane 0, receive lane 1, receive lane 2, receive lane 3, tail}. A description of bits in head, body and tail for each instruction is given as follows:

### NOTE

All multi-bit signals in each chain are packed with bits reversed e.g. mpy[7:0] in ws\_core head subchain is packed as {retime, enpll, mpy[0:7], vrange, lb[0:1]}. All DATA REGISTER READS from SerDes Block R0 should read 1 bit more than the desired number of bits and discard the first bit received on TDO e.g., to read 40-bit data from R0 block, 41 bits should be read off from TDO and the first bit received should be discarded. Similarly, any data written to SerDes Block R0 Data Registers should be prefixed with an extra 0.

TEXAS INSTRUMENTS

www.ti.com

FIELD	DESCRIPTION	
HEAD (STARTING FROM THE MSB OF CHAIN)		
RETIME	No function.	
CORE_WE	Core chain write enable.	
RECEIVER (FOR EACH LANE 0, 1, 2, 3)		
CORE_WE	Core chain write enable.	
TUNING_WE	Tuning chain write enable.	
DEBUG_WE	Reserved.	
CHAR_WE	Char chain write enable.	
UNSHADOWED_WE	Reserved.	
TAIL (ENDING WITH THE LSB OF CHAIN)		
CORE_WE	Core chain write enable.	
TUNING_WE	Tuning chain write enable.	
DEBUG_WE	Reserved.	
RETIME	No function.	
CHAIN LENGTH = 26 BITS		

## Table 30. ws\_cfg Chain



Table 31.	ws_core	Chain
-----------	---------	-------

FIELD	DESCRIPTION	
HEAD (STARTING FRC	M THE MSB OF CHAIN)	
RETIME	No function.	
ENPLL	PLL enable.	
MPY[7:0]	PLL multiply.	
VRANGE	VCO range.	
ENDIVCLK	Enable DIVCLK output	
LB[1:0]	Loop bandwidth	
RECEIVER (FOR E	ACH LANE 0,1,2,3)	
ENRX	Receiver enable.	
SLEEPRX	Receiver sleep mode.	
BUSWIDTH[2:0]	Bus width.	
RATE[1:0]	Operating rate.	
INVPAIR	Invert polarity.	
TERM[2:0]	Termination.	
ALIGN[1:0]	Symbol alignment.	
LOS[2:0]	Loss of signal enable.	
CDR[2:0]	Clock/data recovery.	
EQ[2:0]	Equalizer.	
EQHLD	Equalizer hold.	
ENOC	Offset compensation.	
LOOPBACK[1:0]	Loopback.	
BSINRXP	Boundary scan initialization.	
BSINRXN	Boundary scan initialization.	
RESERVED	Reserved.	
Testpatt[2:0]	Test pattern selection.	
TESTFAIL	Test failure (real time).	
LOSTDTCT	Loss of signal detected (real time).	
BSRXP	Boundary scan data.	
BSRXP		
OCIP	Boundary scan data.	
EQOVER	Offset compensation in progress.	
	Receiver signal over equalized.	
EQUNDER	Receiver signal under equalized.	
LOSTDTCT	Loss of signal detected (sticky).	
SYNC	Re-alignment done, or aligned comma output (sticky).	
RETIME	No function.	
	H THE LSB CHAIN)	
CLKBYP[1:0]	Clock bypass.	
SLEEPPLL	PLL sleep mode.	
RESERVED	Reserved.	
LOCK	PLL lock (real time).	
BSINITCLK	Boundary scan initialization clock.	
ENBSTX	Enable TX boundary scan.	
ENBSRX	Enable RX boundary scan.	
ENBSPT	RX pulse boundary scan.	
RESERVED	Reserved.	
NEARLOCK	PLL near to lock.	
UNLOCK	PLL lock (sticky).	



Table 31. ws_core Cha	in (continued)
-----------------------	----------------

FIELD	DESCRIPTION
CFG OVR	Configuration over-ride.
RETIME	No function.
CHAIN LENGTH = 196 BITS	

## Table 32. ws\_tuning Chain

FIELD	DESCRIPTION	
HEAD (STARTING FROM THE MSB OF CHAIN)		
RETIME No function.		
RECEIVER (FOR E	ACH LANE 0,1,2,3)	
PATTERRTHR[2:0]	Resync error threshold.	
PATT TIMER	PRBS timer.	
RXDSEL[3:0]	Status select.	
ENCOR	Enable clear-on-read for error counter.	
EQZERO[4:0]	EQZ OVRi Equalizer zero.	
EQZ OVR	Equalizer zero over-ride.	
EQLEVEL[15:0]	EQ OVRi Equalizer gain observe or set.	
EQ OVR	Equalizer over-ride.	
EQBOOST[1:0]	Equalizer gain boost.	
RXASEL[2:0]	Selects amux output.	
TAIL (ENDING WITH THE LSB CHAIN)		
ASEL[3:0]	Selects amux output.	
USR PATT[19:0]	User-defined test pattern.	
RETIME	No function.	
CHAIN LENGTH = 174 BITS		

## Table 33. ws\_char Chain

FIELD	DESCRIPTION	
HEAD (STARTING FROM THE MSB OF CHAIN)		
RETIME	No function.	
RECEIVER (FOR E	ACH LANE 0,1,2,3)	
TESTFAIL	Test failure (sticky).	
ECOUNT[11:0]	Error counter.	
ESWORD[7:0]	Eye scan word masking.	
ES[3:0]	Eye scan.	
ESPO[6:0]	Eye scan phase offset.	
ES BIT SELECT[4:0]	Eye scan compare bit select.	
ESVO[5:0]	Eye scan voltage offset.	
ESVO OVR	Eye scan voltage offset override.	
ESLEN[1:0]	Eye scan run length.	
ESRUN	Eye scan run.	
ESDONE	Eye scan done.	
TAIL (ENDING WITH THE LSB CHAIN)		
RETIME	No function.	
CHAIN LENGTH = 194 BITS		



#### 9.3.14 Error Counter

All receive channels include a 12-bit counter for accumulating pattern verification errors. This counter is accessible via the ECOUNT IEEE1500 Char field. It is an essential part of the eye scan capability (see the *Eye Scan* section).

The counter increments once for every cycle that the TESTFAIL bit is detected. The counter does not increment when at its maximum value (i.e., all 1s). When an IEEE1500 capture is performed, the count value is loaded into the ECOUNT scan elements (so that it can be scanned out), and the counter is then reset, provided NCOR is set high.

ECOUNT can be used to get a measure of the bit error rate. However, as the error rate increases, it becomes less accurate due to limitations of the pattern verification capabilities. Specifically, the pattern verifier checks multiple bits in parallel (as determined by the Rx bus width), and it is not possible to distinguish between 1 or more errors.

### 9.3.15 Eye Scan

All receive channels provide features which facilitate mapping the received data eye or extracting a symbol response. A number of fields accessible via the IEEE1500 Char scan chain allow the required low level data to be gathered. The process of transforming this data into a map of the eye or a symbol response must then be performed externally, typically in software.

The basic principle used is as follows:

- Enable dedicated eye scan input samplers, and generate an error when the value sampled differs from the normal data sample;
- Apply a voltage offset to the dedicated eye scan input samplers, to effectively reduce their sensitivity;
- Apply a phase offset to adjust the point in the eye that the dedicated eye scan data samples are taken;
- Reset the error counter to remove any false errors accumulated as a result of the voltage or phase offset adjustments;
- Run in this state for a period of time, periodically checking to see if any errors have occurred;
- Change voltage and/or phase offset, and repeat.

Alternatively, the algorithm can be configured to optimize the voltage offset at a specified phase offset, over a specified time interval.

Eye scan can be used in both synchronous and asynchronous systems, while receiving normal data traffic. The IEEE1500 Char fields used to directly control eye scan and symbol response extraction are ES, ESWORD, ES BIT SELECT, ESLEN, ESPO, ESVO, ESVO OVR, ESRUN and ESDONE. Eye scan errors are accumulated in ECOUNT.

The required eyescan mode is selected via the ES field, as shown in Table 34. When enabled, only data from the bit position within the 20-bit word specified via ES BIT SELECT is analyzed. In other words, only eye scan errors associated with data output at this bit position will accumulate in ECOUNT. The maximum legal ES BIT SELECT is 10011.

ES[3:0]	EFFECT
0000	Disabled. Eye scan is disabled.
0x01	Compare. Counts mismatches between the normal sample and the eye scan sample if ES[2] = 0, and matches otherwise.
0x10	Compare zeros. As ES = 0x01, but only analyses zeros, and ignores ones.
0x11	Compare ones. As ES = 0x01, but only analyses ones, and ignores zeroes.
0100	Count ones. Increments ECOUNT when the eye scan sample is a 1.
1x00	Average. Adjusts ESVO to the average eye opening over the time interval specified by ESLEN. Analyses zeroes when ES[2] = 0, and ones when ES[2] = 1.
1001 1110	Outer. Adjusts ESVO to the outer eye opening (i.e. lowest voltage zero, highest voltage 1) over the time interval specified by ESLEN. 1001 analyses zeroes, 1110 analyses ones.
1010 1101	Inner. Adjusts ESVO to the inner eye opening (i.e. highest voltage zero, lowest voltage 1) over the time interval specified by ESLEN. 1010 analyses zeroes, 1101 analyses ones.

## Table 34. Eye Scan Mode Selection

STRUMENTS

### Table 34. Eye Scan Mode Selection (continued)

ES[3:0]	EFFECT
1x11	Timed Compare. As $ES = 0.01x$ , but analyses over the time interval specified by ESLEN. Analyses zeroes when $ES[2] = 0$ , and ones when $ES[2] = 1$ .

When ES[3] = 0, the selected analysis runs continuously. However, when ES[3] = 1, only the number of qualified samples specified by ESLed, as shown in Table 35. In this case, analysis is started by writing a 1 to ESRUN (it is not necessary to set it back to 0). When analysis completes, ESDONE is set to 1.

Table 35. Eye Scan Run L	_ength
--------------------------	--------

ESLen	NUMBER OF SAMPLES ANALYZED
00	127
01	1023
10	8095
11	65535

When ESVO OVR = 1, the ESVO field determines the amount of offset voltage that is applied to the eye scan data samplers associated with rxpi and rxni. The amount of offset is variable between 0 and 300 mV in increments of ~10 mV, as shown Table 36. When ES[3] = 1, ESVO OVR must be 0 to allow the optimized voltage offset to be read back via ESVO.

ESVO	OFFSET (mV)	
100000	-310	
111110	-20	
111111	-10	
000000	0	
000001	10	
000010	20	
011111	300	

#### Table 36. Eye Scan Voltage Offset

The phase position of the samplers associated with rxpi and rxni, is controlled to a precision of 1/32UI. When ES is not 00, the phase position can be adjusted forwards or backwards by more than one UI using the ESPO field, as shown in Table 37. In normal use, the range should be limited to  $\pm 0.5$  UI (+15 to -16 phase steps).

Та	ıble 37.	Eye S	Scan	Phase	Offset	

ESPO	OFFSET (1/32 UI)
011111	+63
000001	+1
000000	0
111111	-1
100000	-64



#### 9.3.16 JESD204B Pattern Test

The DAC38RF82 (or DAC38RF89) supports the following test patterns for JESD204B:

- Link layer test pattern by setting field JESD\_TEST\_SEQ in register JESD\_LN\_EN (8.5.45) and monitoring the lane alarms (1 = fail, 0 = pass)
  - Verify repeating /D.21.5/ high frequency pattern for random jitter (RJ)
  - Verify repeating /K.28.5/ mixed frequency pattern for deterministic jitter (DJ)
  - Verify repeating initial lane alignment (ILA) sequence
- RPAT, JSPAT or JTSPAT pattern can be verified using errors counter of 8b/10b errors produced over an amount of time to get an estimate of BER.
- Transport layer test pattern: implements a short transport layer pattern check based on F = 1, 2, 4 or 8. The short test pattern has a duration of one frame period and is repeated continuously for the duration of the test. Each sample has a unique value that can be identified with the position of the sample in the user data format. The sample values are such that correct sample values will never be decoded at the receiver if there is a mismatch between the mapping formats being used at the transmitter and receiver devices. This can generally be accomplished by ensuring there are no repeating sub patterns within the stream of samples being transmitted. Refer to the JESD204B standard section 5.1.6 for more details.

The DAC38RF82 (or DAC38RF89) expects the test samples, in a frame, transmitted by an logic device as per Table 38:

JESD Mode	iO	q0	i1	q1
82121	7CB8, F431	6DA9, E520	n/a	n/a
42111	7CB8	F431	n/a	n/a
22210	7CB8	F431	n/a	n/a
12410	7CB8	F431	n/a	n/a
44210	7CB8	F431	6DA9	E520
24410	7CB8	F431	6DA9	E520
41121	7CB8, F431	n/a	n/a	n/a
81180	7C00, B800, F400, 3100, 6D00, A900, E500, 2000	n/a	n/a	n/a
24310	7CB0	F430	6DA0	E520
41380	7CB0, F430, 6DA0, E520, F870, E960, DA50, CB40	n/a	n/a	n/a

## Table 38. Short Test Patterns

The short test pattern has duration of one frame period and is repeated continuously for the duration of the test. Each sample has a unique value that can be identified with the position of the sample in the user data format. The sample values are such that correct sample values will never be decoded at the receiver if there is a mismatch between the mapping formats being used at the transmitter and receiver devices. This can generally be accomplished by ensuring there are no repeating sub patterns within the stream of samples being transmitted.

Following are the steps required to execute the short test functionality in DAC38RF82 (or DAC38RF89).

- 1. Configure other registers, make sure clocks are up and running.
- 2. Start driving short test patterns
- 3. Clear short test alarm by writing '0' to field ALM\_FROM\_SHORTTEST in register ALM\_SYSREF\_PAP (8.5.67). This is a paged register, one for each Multi-DUC.
- 4. Enable short test by writing a '1' to field SHORTTEST\_ENA in register MULTIDUC\_CFG2 (8.5.14).
- 5. Read the short test alarm from field ALM\_FROM\_SHORTTEST in register ALM\_SYSREF\_PAP (8.5.67). This is a paged register, one for each Multi-DUC


If the alarm read from the register is high, the short test has detected an error.




## 9.3.17 Wideband DUC (wide-DUC)

Each DAC output in the DAC38RF82 ((or DAC38RF89)) can be supported by a wide band digital up-converter (DUC), which is called a wide-DUC. Figure 33 shows the implementation and signal processing features of the wide-DUC which is only available in the 2-TX modes (Table 9). For complex inputs, the in-phase (or I-channel) is path AB of DAC A and the phase of the NCO in this path (7.5.19) must be set to 0 degrees. Similarly, the quadrature phase (or Q-channel) is path AB of DAC B and the phase of the NCO in this path (7.5.19) must be set to 0 degrees. Similarly, the set to 90 degrees. The NCO frequency in both I and Q paths (7.5.20) must be set to the same value. The SPI interface registers for the wide-DUC are addressed through paging, with page 1 supporting the I-channel and page 2 supporting Q-channel configuration of the wide-DUC. Register PAGE\_SET (8.5.8) is used to set the pages. Both pages can be selected at the same time to program both channels of wide-DUC simultaneously.

The output of I and Q channels are added together using the output summation block (Figure 33). Bit 0 and Bit 2 of the register field OUTSUM\_SEL must be set to for this to be accomplished.







#### 9.3.18 Interpolation Block

The DAC38RF82 (or DAC38RF89) provides the optional interpolation of 2x in 12-bit input mode and 2x or 4x in 16-bit input mode. In addition, 1x interpolation can be used in 8, 12 or 16-bit input modes to pass the data directly to the DAC output. The SPI interface registers for the multi-DUCs are addressed through paging, with page 0 supporting the I channel and page 1 supporting the Q channel. Register PAGE\_SET (8.4.8) is used to set the pages. Both pages can be selected at the same time to program both multi-DUCs simultaneously with the same settings.

### 9.3.18.1 Multi-DUC input

Each interpolation block accepts data from up to 8 SerDes lanes. A crossbar switch allows any SerDes lane to be mapped to any other SerDes lane. The crossbar switch is controlled by fields OCTETPATHx\_SEL (x = [0..7]) in Registers JESD\_CROSSBAR1 (8.5.57) and JESD\_CROSSBAR2 (8.5.58).




#### 9.3.18.2 Interpolation Filters

The digital upconverter first increases the sample rate of the IQ signal from the input sample rate to the final DAC sample rate through a series of interpolation filters. Different sets of filters are used to achieve different rates, as shown in Table 39. The interpolation rate is selected by field INTERP in register MULTIDUC\_CFG1 (8.5.13).

FILTERS USED						
Interpolation Rate FIR0 (2x) FIR1 (2x)						
2	x					
4	x	x				

Table 39. FIR filters Used for Different Interpolation Rates


The FIR filter coefficients are shown in Table 40 The FIR filters are design with a passband BW of 0.4 x  $f_{INPUT}$ , a stopband attenuation of 90 dBc and ripple of < 0.001 dB. The composite frequency response for each interpolation factor are shown in *Figure 34to Figure 41*.





#### **DAC38RF82, DAC38RF89**

JAJSDO4C - FEBRUARY 2017 - REVISED APRIL 2020



#### **Table 40. FIR Filter Coefficients**

tap	FIR0	FIR1	LPFIR0_5X	FIR2	LPFIR0_3X	FIR3	LPFIR1_3X	INVSINC
1	6	-12	-6	29	-14	3	25	1
2	0	0	-22	0	-61	0	88	-4
3	-19	84	-51	-214	-125	-25	22	13
4	0	0	-89	0	-95	0	-576	-50
5	47	-336	-117	1209	181	150	-1764	592
6	0	0	-106	2048	681	256	-2263	-50
7	-100	1006	-18	1209	972	150	491	13
8	0	0	171	0	347	0	8139	-4
9	192	-2691	449	-214	-1475	-25	18625	1
10	0	0	745	0	-3519	0	26365	
11	-342	10141	930	29	-3528	3	26365	
12	0	16384	841		707		18625	
13	572	10141	338		9337		8139	
14	0	0	-618		19445		491	
15	-914	-2691	-1892		26299		-2263	
16	0	0	-3147		26299		-1764	



tap	FIR0	FIR1	LPFIR0_5X	FIR2	LPFIR0_3X	FIR3	LPFIR1_3X	INVSINC
17	1409	1006	-3872		19445		-576	
18	0	0	-3500		9337		22	
19	-2119	-336	-1564		707		88	
20	0	0	2121		-3528		25	
21	3152	84	7336		-3519			
22	0	0	13430		-1475			
23	-4729	-12	19426		347			
24	0		24231		972			
25	7420		26904		681			
26	0		26904		181			
27	-13334		24231		-95			
28	0		19426		-125			
29	41527		13430		-61			
30	65536		7336		-14			
31	41527		2121					
32	0		-1564					
33	-13334		-3500					
34	0		-3872					
35	7420		-3147					
36	0		-1892					
37	-4729		-618					
38	0		338					
39	3152		841					
40	0		930					
41	-2119		745					
42	0		449					
43	1409		171					
44	0		-18					
45	-914		-106					
46	0		-117					
47	572		-89					
48	0		-51					
49	-342		-22					
50	0		-6					
51	192							
52	0							
53	-100							
54	0							
55	47							
56	0							
50	-19							
58	-19							
59	6							

NSTRUMENTS

ÈXAS

## 9.3.18.3 JESD204B Modes, Interpolation and Clock phase Programming

Table 41 lists the register field values required for each JESD204B mode interpolation mode and clock phase. The register field addresses are listed in Table 42.

Mod	e					Register	r Field Prog	ramming			
L-M-F-S-Hd 1 TX/2TX	Interp	CLOCK PHASES (1-0)	INTERP (4-0)	CLKJESD _DIV (3-0)	CLKJESD _OUT_DI V (3-0)	L_M1 (4-0)	F_M1 (7-0)	M_M1 (7-0)	S_M1 (4-0)	HD	N_M1/N'_ M1 (4-0)
	6	11	00011	0110	0011		000				
00101/NIA	8	11	00100	0111	0100	00111 0x		0x01	00001	1	01111
	12	11	00110	1010	0110	00111	0x00	UXUT	00001	1	UTTT
	16	11	01000	1011	0111						
6	6	10	00011	0010	0011						
	8	11	00100	0011	0100						
42111/84111	10	11	00101	0101	0101						
	12	11	00110	0110	0110	00011	0x00	0x01	00000	1	01111
	16	11	01000	0111	0111						
	18	11	01001	1001	1000						
	24	11	01100	1010	1010						
_	8	01	00100	0001	0100	00001	0x01	0x01	0x01 00000	0	
	12	10	00110	0010	0110						
	16	11	01000	0011	0111						
22210/44210	18	11	01001	0100	1000						01111
	20	11	01010	0101	1001						
	24	11	01100	0110	1010						
	16	01	01000	0001	0111						
12410/24410	24	10	01100	0010	1010	00000	0x03	0x01	00000	0	01111
	8	01	00100	0001	0100						
	12	10	00110	0010	0110			0x03	00000	0	
44210/88210	16	11	01000	0011	0111	00011	0x01				01111
	24	11	01100	0110	1010						
	16	01	01000	0001	0111						
24410/48410	24	10	01100	0010	1010	00001	0x03	0x03	00000	0	01111
81180/NA	1	11	00000	0011	0001	00111	0x00	0x00	00111	0	00111
41380/82380	1	00	00000	1100	0000	00044	0.00	0.00	00444		04044
	2	00	00001	1101	0001	00011	0x02	0x00	00111	0	01011
	1	01	00000	0000	0000						
41121/ 82121	2	01	000001	0001	0001	00011	0x00	0x00	00001	1	01111
	4	11	00010	0011	0010						
24310/48310	24	11	01100	0011	1010	00001	0x02	0x03	00000	0	01011

## Table 41. Register Programming for JESD and Interpolation Mode

## Table 42. Register Field Addresses for JESD204B Mode, Interpolation and Clock Phase Programming

Register Field Name	Register	Register Address	Bit(s)	Hyperlink
INTERP	MULTIDUC_CFG1	0x0A	12-8	8.5.13
CLKJESD_DIV	CarDan Child	005	15-12	0,5,00
CLKJESD_OUT_DIV	SerDes_CLK	0x25	11-8	- 8.5.28
L_M1	JESD_K_L	0x4C	4-0	8.5.47
F_M1	JESD_RBD_F	0x4B	7-0	8.5.46
M_M1		0×4D	15-8	0 5 40
S_M1	JESD_M_S	0x4D	4-0	- 8.5.48



# Table 42. Register Field Addresses for JESD204B Mode, Interpolation and Clock Phase Programming (continued)

Register Field Name	Register	Register Address	Bit(s)	Hyperlink
HD			6	
N_M1	JESD_N_HD_SCR	0x4E	4-0	8.5.49
N_M1' (NPRIME_M1)			12-8	
JESD_PHASE_MODE	JESD_LN_EN	0x4A	1-0	8.5.45
	All reg	isters are paged!		

## 9.3.18.4 Digital Quadrature Modulator

Each DUC in the DAC38RF8x has digital quadrature modulator (DQM) blocks with independent Numerically Controlled Oscillators (NCO) that converts the complex input signal to a real signal with flexible frequency placement between 0 and  $f_{DAC}/2$ . The NCOs are enabled by fields NCOAB\_ENA and NCOCD\_ENA in register MULTIDUC\_CFG2 (8.5.14). The NCOs have 48-bit frequency registers (FREQ\_NCOAB (8.5.25) and FREQ\_NCOCD (8.5.26)) and 16-bit phase registers (PHASE\_NCOAB (8.5.23) and PHASE\_NCOCD (8.5.24)) that generate the sine and cosine terms for the complex mixing. The NCO block diagram is shown in Figure 42.




Figure 42. NCO Block Diagram

Synchronization of the NCOs occurs by resetting the NCO accumulators to zero. The synchronization source is selected by fields SYNCSEL\_NCOAB and SYNCSEL\_NCOCD in register SYNCSEL1 (8.5.29). The frequency word in the FREQ\_NCOAB and FREQ\_NCOCD registers are added to the accumulators every clock cycle, f<sub>DAC</sub>.

The frequency and phase offset of the NCOs are:

$$f_{NCOAB(or CD)} = \frac{FREQ\_NCOAB(or CD) \times f_{DAC}}{2^{48}}$$
(1)  
$$\delta_{AB(or CD)} = 2\pi \times \frac{PHASE\_NCOAB(or CD)}{2^{16}}$$
(2)

Treating the complex channels as complex vectors of the form I + j Q, the output of the DQM is:

$$Output_{AB} = \{I_{INPUTAB} \times \cos(2\pi f_{NCOAB}t + \delta_{AB}) - Q_{INPUTAB} \times \sin(2\pi f_{NCOAB}t + \delta_{AB})\} \times 2^{(MIXERAB\_GAIN-1)}$$
(3)

$$Output_{CD} = \{I_{INPUTCD} \times \cos(2\pi f_{NCOCD}t + \delta_{CD}) - Q_{INPUTCD} \times \sin(2\pi f_{NCOCD}t + \delta_{CD})\} \times 2^{(MIXERCD\_GAIN-1)}$$
(4)

Where t is the time since the last resetting of the NCO accumulator and the fields MIXERAB\_GAIN and MIXERCD\_GAIN in register MULTIDUC\_CFG2 (8.5.13) are either 0 or 1.

The maximum output amplitude of the DQM occurs if  $I_{IN}(t)$  and  $Q_{IN}(t)$  are simultaneously full scale amplitude and the sine and cosine arguments are equal to an integer multiple of  $\pi/4$ .



With MIXERAB\_GAIN or MIXERCD\_GAIN = 0, the gain through the DQM is sqrt(2)/2 or -3 dB. This loss in signal power is in most cases undesirable, and it is recommended that the gain function be used to increase the signal by 3 dB to compensate. With MIXERAB\_GAIN or MIXERCD\_GAIN = 1, the gain through the DQM is sqrt(2) or +3 dB, which can cause clipping of the signal if  $I_{IN}(t)$  and  $Q_{IN}(t)$  are simultaneously near full scale amplitude and should therefore be used with caution.

## 9.3.18.5 Low Power Coarse Resolution Mixing Modes

In addition to the NCO the DAC38RFxx also has a coarse mixer block capable of shifting the input signal spectrum by the fixed mixing frequencies  $\pm N \ge f_{DAC}/8$ . Using the coarse mixer instead of the full mixers will result in lower power consumption.

Treating the two complex channels as complex vectors of the form I(t) + j Q(t), the outputs of the coarse mixer is equivalent to:

$$Output_{AB} = I_{INPUTAB} \times cos(2\pi f_{CMIX} ABt) - Q_{INPUTAB} \times sin(2\pi f_{CMIX} ABt)$$
(5)

$$Output_{CD} = I_{INPUTCD} \times cos(2\pi f_{CMIX} CD^{t}) - Q_{INPUTCD} \times sin(2\pi f_{CMIX} CD^{t})$$

(6)

Where  $f_{CMIX\_AB}$  and  $f_{CMIX\_CD}$  and the fixed mixing frequency selected by fields CMIX\_AB or CMIX\_CD in register CMIX (8.5.21). The coarse mixer blocks are disabled by setting CMIX\_AB and CMIX\_CD to 0x0.

The NCO and coarse mixers can be enabled simultaneously, although this is not useful in most cases as the full frequency range can be covered by the NCO.

## 9.3.18.6 Inverse Sinc Filter

The DAC38RF82 (or DAC38RF89) has a 9-tap inverse Sinc filter (INVSINC) that runs at the DAC update rate ( $f_{DAC}$ ) that can be used to flatten the frequency response of the sample-and-hold output. The DAC sample-and-hold output sets the output current and holds it constant for one DAC clock cycle until the next sample, resulting in the well known sin(x)/x or Sinc(x) frequency response (Figure 43, red line). The inverse sinc filter response (Figure 43, blue line) has the opposite frequency response from 0 to 0.4 x  $f_{DAC}$ , resulting in the combined response (Figure 43, green line). Between 0 to 0.4 x  $f_{DAC}$ , the inverse sinc filter compensates the sample-and-hold roll-off with less than 0.03 dB error.

The inverse sinc filter has a gain > 1 at all frequencies. Therefore, the signal input to INVSINC must be reduced from full scale to prevent saturation in the filter. The amount of back-off required depends on the signal frequency, and is set such that at the signal frequencies the combination of the input signal and filter response is less than 1 (0 dB). For example, if the signal input to INVSINC is at 0.25 x  $f_{DAC}$ , the response of INVSINC is 0.9 dB, and the signal must be backed off from full scale by 0.9 dB to avoid saturation. The advantage of INVSINC having a positive gain at all frequencies is that the user is then able to optimize the back-off of the signal based on its frequency.

The inverse sinc filters are enabled by field ISFIR\_ENA in register MULTIDUC\_CFG1 (8.5.13).




Figure 43. Composite Magnitude Spectrum for INVSINC



#### DAC38RF82, DAC38RF89 JAJSDO4C – FEBRUARY 2017 – REVISED APRIL 2020

#### www.ti.com

#### 9.3.19 PA Protection Block

The DAC38RFxx incorporates an optional power amplifier protection (PAP) block to monitor when the input signal is two large, for example when an interface error occurs, and reduces the output signal power of the DAC. The PAP block achieves the functionality of reducing the input signal that crosses the threshold through three main sub-blocks. These are PAP trigger generation block, PAP gain state machine and GAIN block.

The PAP block keeps track of the input signal power by maintaining a sliding window accumulation of last N samples. N is selectable to be 32, 64 or 128 based on the setting (Table 43) of fields PAPAB\_SEL\_DLY in register PAP\_CFG\_AB (8.5.35) and PAPCD\_SEL\_DLY in register PAP\_CFG\_CD (8.5.36). The average amplitude of input signal is computed by dividing accumulated value by the number of samples in the delay-line (N). The result is then compared against the threshold in fields PAPAB\_THRESH in register PAP\_CFG\_AB (8.5.35) and PAPCD\_THRESH in register PAP\_CFG\_CD (8.5.36). If the threshold is violated, gain state machine is triggered which generated gain value to ramp down the DAC output signal amplitude. After the input signal returns to normal value, the state machine ramps up the DAC output signal amplitude.

pap_sel_dly[1:0]	# of samples averaged
00	32
01	64
10	128
11	Reserved

#### Table 43. PAP Delay Line Selection

The generation of the PAP trigger as explained as follows:

- The I and Q samples are treated separately either can trigger attenuation
- In dual DUC modes, each IQ pair is treated separately and has a separate gain block
- 8 samples at the input are put through an absolute value circuit (all 2's complement)
- · Next these values are vector summed to get a 12 bit result
- Then 12 bit result is placed into the delay line and summed into the accumulator
- The accumulator is also subtracting out the delayed 12 bit word corresponding to N = 32, N = 64 or N = 128
- Finally the accumulator output is divided down by N and rounded to 13 bits. These 13 bits are compared to the threshold in the SPI registers. A pap\_trig occurs if the threshold is exceeded.

The PAP gain state machine generates the pap gain value to be applied on the output stream to reduce the output signal amplitude. The state machine below is used to control the attenuation of the DAC output and the gaining up of the signal again once the trigger is released.

wait cnt load r=0 pap\_trig=0

wait cnt load r=1

Copyright © 2017, Texas Instruments Incorporated

# pap trig=0 Normal pap trig=1 pap\_gain=1 pap\_trig=1 Attenuate Gain

Figure 44. PAP Gain State Machine

Wait

pap trig=1

The normal operating condition for the PAP block is the NORMAL state in Figure 44. However, when the PAP block detects an error condition it sets the pap\_trig signal to '1' causing a state transition from NORMAL operation to the ATTENUATE state.

In the ATTENUTATE state the data path gain is scaled from 1.0 down to 0.0 by a programmable step amount set by fields PAPAB\_GAIN\_STEP in register PAP\_GAIN\_AB (8.5.31) and PAPCD\_GAIN\_STEP in register PAP GAIN CD (8.5.33). This value is always positive with the decimal place located between the MSB and MSB-1. Unity is equal to "1000000000". Each clock cycle (16 samples) the PAP\_GAIN is stepped down by PAPAB\_GAIN\_STEP and PAPCD\_GAIN\_STEP until the gain is 0.

After PAP GAIN is 0, the state machine moves on to the WAIT state. Here a programmable counter counts clock cycles to allow the condition for the pap\_trig to be fixed. Fields PAPAB\_WAIT in register PAP\_WAIT\_AB (8.5.32) and PAPCD\_WAIT in register PAP\_WAIT\_CD (8.5.34) are used to select the number of clock cycles (samples = 16 x PAPAB\_WAIT or 16 x PAPCD\_WAIT) to wait before moving to the next state. Once the WAIT counter equals zero and pap\_trig='0', the state machine moves on to the GAIN state. If the WAIT equals 0 but pap\_trig still equals '1' then the state machine stays in the WAIT state until pap\_trig ='0'.

## 9.3.20 Gain Block

The GAIN block also has additional output gain control through fields GAINAB in register GAINAB (8.5.39) and GAINCD in register GAINCD (8.5.40). Similar to PAP\_GAIN value, the output gain is always positive with unity when GAINAB or GAINCD = "01000000000".

To reduce the power, the gain block clock has been gated whenever the pap is disabled and GAINAB or GAINCD is set to unity.

## 9.3.21 Output Summation

The OUTSUM block allows addition of samples from each DUC in the multi-DUC. It is also possible to add the output samples from the adjacent multi-DUC. Field OUTSUM SEL in register OUTSUM (8.5.22) controls the summation for each multi-DUC. The functionality of the block can be represented by the following equation:

58



www.ti.com



(7)

#### $OUTSUM_{output} = SAME_{AB} + SAME_{CD} + ADJ_{AB} + ADJ_{CD}$

In order to avoid overflow, rounding operation is performed after the addition to reduce the word size back to 16bits. Exact number of bits rounded depends on the number of channels added. Table 44 shows the description of round after the summation.

# OF CHANNELS ADDED	# OF BITS ROUNDED
0	0, Use bits[15:0] from the result
1	Use bits[16:1] from the result and bit[0] used for rounding
2	Use bits[17:2] from the result and bits[1:0] used for rounding
3	Use bits[18:3] from the result and bit[2:0 used for rounding
4	Use bits[19:4] from the result and bit[3:0] used for rounding

#### Table 44. OUTSUM Scaling and Rounding

### 9.3.22 Output Delay

The signal following output summation can be programmably delayed by 0-15 DACCLK cycles through field OUTPUT\_DELAY in register OUTSUM (8.5.20). The block takes 16 sample words (vec16) from both the A and B paths and shifts the them to 32 sample long delay line.

### 9.3.23 Polarity Inversion

The signal following the output delay can be inverted by a 2's complement conversion allowing the + and - DAC outputs to be swapped by asserting field DAC\_COMPLEMENT in register MULTIDUC\_CFG1 (8.5.13).

#### 9.3.24 Temperature Sensor

The DAC38RF82 (or DAC38RF89) incorporates a temperature sensor block which monitors the die temperature by measuring the voltage across 2 transistors. The voltage is converted to an 8-bit digital word using a successive approximation (SAR) analog to digital conversion process. The result is scaled, limited and formatted as a twos complement value representing the temperature in degrees Celsius.

The sampling is controlled by the serial interface signals SDEN and SCLK. If the temperature sensor is enabled by writing a 0 to field TSENSE\_SLEEP in register SLEEP\_CONFIG (8.5.70), a conversion takes place each time the serial port is written or read. The data is only read and sent out by the digital block when the temperature sensor is read in field TEMPDATA in register TEMP\_PLLVOLT (8.5.7). The conversion uses the first eight clocks of the serial clock as the capture and conversion clock, the data is valid on the falling eighth SCLK. The data is then clocked out of the chip on the rising edge of the ninth SCLK. No other clocks to the chip are necessary for the temperature sensor operation. As a result the temperature sensor is enabled even when the device is in sleep mode.

In order for the process described above to operate properly, the serial port read from register TEMP\_PLLVOLT must be done with an SCLK period of at least 1  $\mu$ s. If this is not satisfied the temperature sensor accuracy is greatly reduced.

### 9.3.25 Alarm Monitoring

The DAC38RF82 (or DAC38RF89) includes a flexible set of alarm monitoring that can be used to alert of a possible malfunction scenario. All the alarm events can be accessed either through the SIP registers and/or through the ALARM output. Once an alarm is set, the corresponding alarm bit must be reset through the serial interface to allow further testing. The set of alarms includes the following conditions:

- JESD alarms
  - Fields ALM\_LANEx\_ERR in registers JESD\_ALM\_Lx (x = 0.7, 8.5.59 to 8.5.66):
    - multiframe alignment\_error. Occurs when multiframe alignment fails
    - frame alignment error. Occurs when multiframe alignment fails
    - link configuration error. Occurs when there is wrong link configuration
    - elastic buffer overflow. Occurs when bad RBD value is used
    - elastic buffer match error. Occurs when the first non-/K/ doesn't match the programmed data
    - code synchronization error



- 8b/10b not-in-table decode error
- 8b/10b disparity error
- Field ALM\_FROM\_SHORTTEST in register ALM\_SYSREF\_PAP (8.5.67): Occurs when the short pattern test fails.
- SerDes alarms
  - Field ALM\_SD\_LOTDET in register ALM\_SD\_DET 8.5.5): Occurs when there are loss of signal detect from SerDes lanes.
  - Fields ALM\_FIFOx\_FLAGS in registers JESD\_ALM\_Lx (x = 0-7, 8.5.59 to 8.5.66):
    - FIFO write error. Occurs if write request and FIFO is full.
    - FIFO write full: Occurs if FIFO is full.
    - FIFO read error. Occurs if read request and FIFO is empty.
    - FIFO read empty: Occurs if FIFO is empty.
  - Field ALM\_SD0\_PLL in register ALM\_SYSREF\_DET (8.5.6): Occurs if the PLL in the SerDes block 0 goes out of lock.
  - Field ALM\_SD1\_PLL in register ALM\_SYSREF\_DET (8.5.6): Occurs if the PLL in the SerDes block 1 goes out of lock.
- SYSREF alarm
  - Field ALM\_SYSREF\_ERR in register ALM\_SYSREF\_PAP (8.5.67): Occurs when the SYSREF is received at an unexpected time. If too many of these occur it will cause the JESD to go into synchronization mode again.
- DAC PLL alarm
  - Field PLL\_LOCK in register ALM\_SYSREF\_DET (8.5.6). This register field is asserted when the PLL is unlocked. When used as an alarm output, a high signal indicates that the PLL is unlocked if the ALM\_OUT\_POL bit in register RESET\_CONFIG is set to 1.
- PAP alarm
  - Field ALM\_PAP in register ALM\_SYSREF\_PAP (8.5.67): Occurs when the average power is above the threshold. While any alarm\_pap is asserted the attenuation for the appropriate data path is applied.

### 9.3.26 Differential Clock Inputs

Figure 45 shows the preferred configuration for driving the DACCLK+/- and SYSREF+/- with a differential ECL/PECL source.





Figure 45. Preferred Clock Input Configuration With a Differential ECL/PECL Clock Source

## 9.3.27 CMOS Digital Inputs

Figure 46 shows a schematic of the equivalent CMOS digital inputs of the DAC38RF82 (or DAC38RF89). SDIO, SCLK, TCLK, <u>SLEEP</u>, TESTMODE and TXENABLE have internal pull-down resistors while SDEN, RESET, TMS, TDI and TRST have internal pull-up resistors. See the *Specifications* table for logic thresholds. The pull-up and pull-down circuitry is approximately equivalent to 10 k $\Omega$ .





Copyright © 2016, Texas Instruments Incorporated

Figure 46. CMOS Digital Equivalent Input

### 9.3.28 DAC Fullscale Output Current

The DAC38RF82 (or DAC38RF89) uses a bandgap reference and control amplifier for biasing the full-scale output current. The DAC full scale output current is set by a combination of the fixed current through the external resistor RBIAS (connected to pin BIASJ) and current from course trim current sources:

The bias current IBIAS through resistor R<sub>BIAS</sub> is defined by the on-chip bandgap reference voltage V<sub>BG</sub> (nominally 0.9 V) and control amplifier. For normal operation, it is recommended that R<sub>BIAS</sub> is set to 3.6 k $\Omega$  for a fixed current through R<sub>BIAS</sub> of 250 µA. This current is scaled 128x internally, giving:

$$I_{RBIAS} = 128 \times \frac{V_{BG}}{R_{BIAS}} = 128 \times \frac{0.9V}{3.6 \ k\Omega} = 32 \ mA$$
(9)

The course trim current sources are configured through SPI register field DACFS in register DACFS (8.5.72), as follows:

From the discussion above, the DAC full scale output current can be configured from 40 mA (DACFS[3:0] = 1111) down to 10 mA (DACFS[3:0] = 0000). In addition to the full scale signal current set by SPI register DACFS (8.5.72), an extra DC bias current is required to set the operating point of the output current sources(Table 45).

DACFS ( 8.5.72)	Signal current (mA)	Total bias current (mA) <sup>(1)</sup>				
0	10	1				
1	12	1				
2	14	2				
3	16	2				
4	18	3				
5	20	3				
6	22	4				
7	24	5				
8	26	5				
9	28	6				
10	30	6				
11	32	7				
12	34	7				
13	36	8				
14	38	8				
15	40	9				

#### Table 45. DAC output current

(1) The bias current per each complementary output is half the total bias current

An external decoupling capacitor C<sub>EXT</sub> of 0.1  $\mu$ F should be connected externally to terminal EXTIO for compensation. The full-scale output current can be adjusted from 40 mA down to 10 mA by varying resistor R<sub>BIAS</sub> From 3.6 k $\Omega$  to 14.4 k $\Omega$ .

## 9.3.29 Current Steering DAC Architecture

The DACs in the DAC38RF82 (or DAC38RF89) consist of a segmented array of NMOS current sources, capable of sinking a full-scale output current up to 40 mA (see Figure 47). Differential current switches direct the current to either one of the complimentary output nodes VOUT1/2+ or VOUT1/2-. Complimentary output currents enable differential operation, thus canceling out common mode noise sources (digital feed-through, on-chip and PCB noise), dc offsets, even order distortion components, and increasing signal output power by a factor of four.



(8)

(10)








Figure 47. Current Steering DAC Architecture for DAC38RF82 (or DAC38RF89)

Referring to Figure 47, the total output current  $I_{OUTFS}$  is fixed, and is switched to either the + or – output by switches S(N):

(11)

Since the output stage is a current sinking architecture, it will denote current into the DAC as + current, and the current flows IOUT+ and IOUT- into terminals VOUT1/2+ and VOUT1/2- respectively. IOUT+ and IOUT- can be expressed as:

$$IOUT_{+} = \frac{IOUT_{FS} \times CODE}{16384}$$
(12)  
$$IOUT_{-} = \frac{IOUT_{FS} \times (16383 - CODE)}{16384}$$
(13)

where CODE is the decimal representation of the 14-bit DAC core data input word. Note the signal path up to the DAC is 16-bits and the 2 LSBs are truncated for the DAC core data input word.

### 9.3.30 DAC Transfer Function

The DAC38RF82 (or DAC38RF89) has a differential output and is terminated internally with a differential  $100-\Omega$  load. The DAC38RF82 (or DAC38RF89) output compliance range is 1.3 to 2.3 V. Note that care should be taken not to exceed the compliance voltages at node VOUT1/2+ and VOUT1/2-, which would lead to increased signal distortion.

Referring again to Figure 47, denote the external impedance as seen by VOUT1/2+ as Zext+ and by VOUT1/2- as Zext-. Note that Zext+ and Zext- should terminate to VDDOUT18 to supply the output current for the DAC. Also, Zext+ and Zext- are ideally identical to maintain the differential balance of the output. The voltage at nodes VOUT1/2+ and VOUT1/2- generated by the current flow through the impedance is

$$VOUT1/2 + = \frac{IOUT + \times (100\Omega + Zext +)}{(100\Omega + Zext + + Zext -)} \times Zext + \frac{IOUT - \times Zext -}{(100\Omega + Zext + + Zext -)} \times Zext +$$
(14)



 $VOUT1/2 - = \frac{IOUT - \times (100\Omega + Zext -)}{(100\Omega + Zext + + Zext -)} \times Zext + \frac{IOUT + \times Zext +}{(100\Omega + Zext + + Zext -)} \times Zext -$ (15)


The DAC38RF82 (or DAC38RF89) can be easily configured to drive a doubly terminated 50- $\Omega$  cable using a properly selected 2:1 RF transformer (Figure 48). Note that the center tap of the primary input of the transformer has to be connected to the VDDOUT18 supply (nominally 1.8 V) to enable a DC current flow into the DAC. The AC load impedance as seen through 2:1 transformer is 100  $\Omega$ , which is split equally into Zext+ = Zext- = 50  $\Omega$ . The DC impedance for the transformer is a short to the center tap of the transformer, which drives the common mode of VOUT1/2+ and VOUT1/2- to 1.8V. To calculate the peak to peak output swing VOUT1/2PP at each node, the equations above simplify to:

$$VOUT1/2_{PP} = VOUT1/2 + |(IOUT_{FS}, IOUT_{-0}) - VOUT1/2 + |(IOUT_{FS}, IOUT_{+0})|$$
(16)

$$VOUT1/2_{PP} = \frac{IOUT_{FS} \times 50\Omega \times 150\Omega}{200\Omega} - \frac{IOUT_{FS} \times 50\Omega \times 50\Omega}{200\Omega} = IOUT_{FS} \times 25\Omega$$
(17)

With  $IOUT_{OUTFS} = 40$  mA, the swing becomes 1 V<sub>PP</sub> at each node. With the common mode at 1.8 V due to the center tap, the voltage at VOUT1/2+ and VOUT1/2- varies between 1.3 and 2.3 V, which is the compliance range of the DAC.

The differential output swing is  $2x \text{ VOUT1/2}_{PP}$ , or  $2 \text{ V}_{PPDIFF}$ . On the load side of the transformer, this reduces to 1.414 V<sub>PP</sub>, for a transferred load power of 7 dBm (assuming no loss).



## Figure 48. Driving a 50-Ω Load Using a 2:1 Impedance Ratio Transformer (DAC38RF82 (or DAC38RF89))

The DAC38RF82 (or DAC38RF89) can also be DC coupled. In this case, the termination voltage can be raised above 1.8 V (for example 2.3 V) so that the common mode for the output pin is nominally 1.8 V.

## 9.4 Device Functional Modes

### 9.4.1 Clocking Modes

The DAC38RF82 (or DAC38RF89) has both a single ended clock input DACCLKSE and a differential clock input DACCLK+/- to clock the device. The clock input is selected by field SEL\_EXTCLK\_DIFFSE in register CLK\_PLL\_CFG (8.5.79). The DAC38RF82 (or DAC38RF89) can be clock directly with a high frequency input clock at the DAC sample rate (PLL Bypass Mode), or an optional on-chip low-jitter phase-locked loop (PLL) can be used to generate the high frequency DAC sample clock internally from a lower frequency reference clock input (PLL Mode).

## 9.4.2 PLL Bypass Mode Programming

In PLL bypass mode a high quality clock is sourced to the DACCLK inputs. This clock is used to directly clock the DAC38RF82 (or DAC38RF89) DAC cores. This mode gives the device best performance and is recommended for extremely demanding applications.

The bypass mode is selected by setting the following:

- 1. Set field PLL\_ENA in register CLK\_PLL\_CFG (8.5.79) to "0" to bypass the PLL circuitry.
- 2. Set field PLL\_SLEEP in register SLEEP\_CONFIG (8.5.70) to "1" to put the PLL and VCO into sleep mode.



## **Device Functional Modes (continued)**

## 9.4.3 Internal PLL/VCO

The DAC38RF82 (or DAC38RF89) has an internal clock generation circuit consisting of a PLL and two selectable VCOs, as shown in Figure 49.




Figure 49. Internal PLL/VCO Block Diagram

DAC38RF82 (or DAC38RF89) each have a low VCO (VCO0) and high VCO (VCO1), but they are tuned to different center frequencies in each device. The VCO frequency ranges for each device are summarized in Electrical Characteristics - Digital Specifications. The VCO is selected through field PLL\_VCOSEL in register PLL\_CONFIG2 (8.5.81), with '0' selecting the low VCO and a '1' the high VCO. The 7 bit VCO tuning code in field PLL\_VCO in register PLL\_CONFIG2 (8.5.81) is used to tune the VCO frequency from the lowest frequency in the range to the highest frequency for the particular VCO used. For the low VCO the center VCO frequency is achieved with PLL\_VCO =  $63_{decimal}$  and for the high VCO the center frequency is achieved with PLL\_VCO =  $63_{decimal}$ .

The supply current, and therefore; the analog signal amplitude in the VCO is controlled using the field PLL\_VCO\_RDAC in register PLL\_CONFIG1 (8.5.80). This control signal should be set  $15_{decimal}$  initially for 18 mA supply current in the VCO and ~1.4 V<sub>PP</sub> single ended oscillation amplitude.

The PLL has no prescaler, so the DAC sample rate is the VCO frequency. In the PLL feedback path a fixed  $\div 4$  frequency divider block receives the VCO output clock and divides its frequency by 4. The maximum operating frequency of the phase-frequency detector (PFD) and charge pump (CP) requires this. The M (feedback) clock divider takes the output clock signal from the fixed  $\div 4$  block and divides it by a programmable ratio set by the 8-bit field in field PLL\_M\_M1 in register PLL\_CONFIG1 (8.5.80). The programmable division ratio range is  $\div 1$  to  $\div 256$ , and is the value of the 8 bit unsigned binary code + 1. Although it is possible to program the M divider to  $\div 1$ ,  $\div 2$  and  $\div 3$ , these values should not be used. As stated previously the PFD and CP have a finite maximum operating frequency, which is the VCO frequency divided by the fixed divider ratio multiplied by the minimum allowable M divider ratio.

PFD\_CP<sub>Fmax</sub> = Fvco / (Fixed\_div x Mdiv<sub>min</sub>)

(18)

The N (reference) divider determines the ratio between the input reference clock frequency and the PFD operating frequency, and is set by the 5-bit field PLL\_N\_M1 in register CLK\_PLL\_CFG (8.5.79). The division ratio range is  $\div$ 1 to  $\div$ 32, and is the value of the 5-bit unsigned binary code + 1.



## **Device Functional Modes (continued)**

The charge pump output current amplitude is set using the 4-bit field PLL\_CP\_ADJ in in register PLL\_CONFIG2 (8.5.81). The current amplitude is simply the digital code multiplied by the unit current amplitude of 100  $\mu$ A. In a nominal condition, with the DAC38RF82 VCO0 running at 5.898 GHz, and with the M divider set to ÷4, the PFD will run at 368.625 MHz, and the change pump current should set to 6<sub>decimal</sub>, which gives 600  $\mu$ A charge pump output current for a good phase margin of 69 degrees. If a higher M ratio (for lower PFD frequencies) are required the charge pump output current must be increased to maintain good loop stability and prevent excessive peaking in the phase noise response. The charge pump output current setting PLL\_CP\_ADJ should be adjusted in relation to the feedback (M) divider ratio PLL\_M\_M1 according to the following table to maintain a constant phase margin of 69 degrees.

М	CP_ADJ
4	6
6	9
8	12
10	15

Similarly for the DAC38RF82 VCO2 running at 8.847 GHz, and with the M divider set to  $\div$ 4, the PFD will run at 552.9375 MHz as shown above. Here the change pump current should set to  $6_{decimal}$ , which gives 600 µA charge pump output current for a good phase margin of 69 degrees.

## 9.4.4 CLKOUT

The DAC38RF82 (or DAC38RF89) has a programmable output clock on CLKTX+/- balls that is a divided version of the internal DAC sample clock, either with or without PLL. Two frequency dividers, either DACCLK/3 or DACCLK/4, are available by programming field CLK\_TX\_DIV4 in register CLK\_OUT (8.5.71). The output swing voltage is programmable from approximately 125 to 1460 mV<sub>PP-DIFF</sub> through field CLK\_TX\_SWING in register CLK OUT (8.5.71).

Field CLK\_TX\_IDLE in register CLK\_OUT (8.5.71) enables an idle state, in which the pins are driven to the proper common-mode levels in order to charge the external AC coupling caps but the clock output is disabled. The output clock circuit can be put to sleep by field CLK\_TX\_SLEEP in register SLEEP\_CONFIG (8.5.70).

### 9.4.5 Serial Peripheral Interface (SPI)

The serial port of the DAC38RF82 (or DAC38RF89) is a flexible serial interface which communicates with industry standard microprocessors and microcontrollers. The interface provides read/write access to all registers used to define the operating modes of DAC38RF82 (or DAC38RF89). It is compatible with most synchronous transfer formats and can be configured as a 3 or 4 terminal interface by SIF4\_ENA in register IO\_CONFIG (8.5.2). In both configurations, SCLK is the serial interface input clock and SDEN is serial interface enable. For 3 terminal configuration, SDIO is a bidirectional terminal for both data in and data out. For 4 terminal configuration, SDIO is bidirectional and SDO is data out only. Data is input into the device with the rising edge of SCLK. Data is output from the device on the falling edge of SCLK.

The SPI registers are reset by writing a 1 to SPI\_RESET in register RESET\_CONFIG (8.5.1).

Each read/write operation is framed by signal <u>SDEN</u> (Serial Data Enable Bar) asserted low. The first frame byte is the instruction cycle which identifies the following data transfer cycle as read or write as well as the 7-bit address to be accessed. Figure 50 indicates the function of each bit in the instruction cycle and is followed by a detailed description of each bit. The data transfer cycle consists of two bytes.

Bit	7 (MSB)	6	5	4	3	2	1	0
Description	R/W	A6	A5	A4	A3	A2	A1	A0

#### Figure 50. Instruction Byte of the Serial Interface

R/W - Identifies the following data transfer cycle as a read or write operation. A high indicates a read operation from DAC38RF82 (or DAC38RF89) and a low indicates a write operation to DAC38RF82 (or DAC38RF89)

A6:A0 - Identifies the address of the register to be accessed during the read or write operation.



Figure 51 shows the serial interface timing diagram for a DAC38RF82 (or DAC38RF89) write operation. SCLK is the serial interface clock input to DAC38RF82 (or DAC38RF89). Serial data enable SDEN is an active low input to DAC38RF82 (or DAC38RF89). SDIO is serial data input. Input data to DAC38RF82 (or DAC38RF89) is clocked on the rising edges of SCLK.






Figure 52 shows the serial interface timing diagram for a DAC38RF82 (or DAC38RF89) read operation. SCLK is the serial interface clock input to DAC38RF82 (or DAC38RF89). Serial data enable SDEN is an active low input to DAC38RF82 (or DAC38RF82). SDIO is serial data input during the instruction cycle. In 3 pin configuration, SDIO is data out from the DAC38RF82 (or DAC38RF89) during the data transfer cycle, while SDO is in a high-impedance state. In 4 pin configuration, both SDIO and SDO are data out from the DAC38RF82 (or DAC38RF89) during the data transfer, SDIO and SDO will output low on the final falling edge of SCLK until the rising edge of SDEN when they will 3-state.




Figure 52. Serial Interface Read Timing Diagram

n the SIF interface there are four types of registers:

## 9.4.5.1 NORMAL (RW)

The NORMAL register type allows data to be written and read from. All 16-bits of the data are registered at the same time. There is no synchronizing with an internal clock thus all register writes are asynchronous with respect to internal clocks. There are three subtypes of NORMAL:

1. AUTOSYNC: A NORMAL register that causes a sync to be generated after the write is finished. These are used when it is desirable to synchronize the block after writing the register or if a single field that spans across multiple registers. For instance, the NCO requires three 16-bit register writes to set the frequency. Upon writing the last of these registers an autosync is generated to deliver the entire field to the NCO block

TEXAS INSTRUMENTS

www.ti.com

at once, rather than in pieces after each individual register write. For a field that spans multiple registers, all non-AUTOSYNC registers for the field must be written first before the actual AUTOSYNC register.

- 2. No RESET Value: These are NORMAL registers, but the reset value cannot be specified. This could be because the register has some read only bits or some internal logic partially controls the bit values.
- 3. READ\_ONLY (R): Registers that can only be read.

## 9.4.5.2 WRITE\_TO\_CLEAR (WOC)

These registers are just like NORMAL registers with one exception. They can be written and read, however, when the internal logic asynchronously sets a bit high in one of these registers, that bit stays high until it is written to '0'. This way interrupts will be captured and stay constant until cleared by the user.

## 9.5 Register Maps

Address	Reset	Acronym	Register Name	Section
		General Configuration Registers (PA	GE_SET[2:0] = 000)	
0x00	0x5803	RESET_CONFIG	Chip Reset and Configuration	8.5.1
0x01	0x1800	IO_CONFIG	IO Configuration	8.5.2
0x02	0xFFFF	ALM_SD_MASK	Lane Signal Detect Alarm Mask	8.5.3
0x03	0xFFFF	ALM_CLK_MASK	Clock Alarms Mask	8.5.4
0x04	0x0000	ALM_SD_DET	SERDES Loss of Signal Detection Alarms	8.5.5
0x05	0x0000	ALM_SYSREF_DET	SYSREF Alignment Circuit Alarms	8.5.6
0x06	variable	TEMP_PLLVOLT	Temperature Sensor and PLL Loop Voltage	8.5.7
0x07-0x08	0x0000	Reserved	Reserved	
0x09	0x0000	PAGE_SET	Page Set	8.5.8
0x0A-0x77	0x0000	Reserved	Reserved	
0x78	0x0000	SYSREF_ALIGN_R	SYSERF Align to r1 and r3 Count	8.5.9
0x79	0x0000	SYSREF12_CNT	SYSREF Phase Count 1 and 2	8.5.10
0x7A	0x0000	SYSREF34_CNT	SYSREF Phase Count 3 and 4	8.5.11
0x7B-0x7E	0x0000	Reserved	Reserved	
0x7F	0x0008	VENDOR_VER	Vendor ID and Chip Version	8.5.12
ulti-DUC Configura	ation Registers (PAGE_	SET[0] = 1 for multi-DUC1, PAGE_SET[1	] = 1 for multi-DUC2)	
0x0A	0x02B0	MULTIDUC_CFG1	Multi-DUC Configuration (PAP, Interpolation)	8.5.13
0x0B	0x0000	Reserved	Reserved	
0x0C	0x2402	MULTIDUC_CFG2	Multi-DUC Configuration (Mixers)	8.5.14
0x0D	0x8300	JESD_FIFO	JESD FIFO Control	8.5.15
0x0E	0x00FF	ALM_MASK1	Alarm Mask 1	8.5.16
0x0F	0x1F83	ALM_MASK2	Alarm Mask 2	8.5.17
0x10	0xFFFF	ALM_MASK3	Alarm Mask 3	8.5.18
0x11	0xFFFF	ALM_MASK4	Alarm Mask 4	8.5.19
0x12	0x0000	JESD_LN_SKEW	JESD Lane Skew	8.5.20
0x13-0x16	0x0000	Reserved	Reserved	
0x17	0x0000	CMIX	CMIX Configuration	8.5.21
0x18	0x0000	Reserved	Reserved	
0x19	0x0000	OUTSUM	Output Summation and Delay	8.5.22
0x1A-0x1B	0x0000	Reserved	Reserved	
0x1C	0x0000	PHASE_NCOAB	Phase offset for AB path NCO	8.5.23
0x1D	0x0000	PHASE_NCOCD	Phase offset for CD path NCO	8.5.24
0x1E-0x20	0x0000	FREQ_NCOAB	Frequency for AB path NCO	8.5.25
0x21-0x23	0x0000	FREQ_NCOCD	Frequency for CD path NCO	8.5.26
0x24	0x0010	SYSREF_CLKDIV	SYSREF Use for Clock Divider	8.5.27
0x25	0x7700	SERDES_CLK	Serdes Clock Control	8.5.28
0x26	0x0000	Reserved	Reserved	

#### Table 47. Register Summary



### DAC38RF82, DAC38RF89 JAJSDO4C – FEBRUARY 2017 – REVISED APRIL 2020

#### www.ti.com

# **Register Maps (continued)**

# Table 47. Register Summary (continued)

Address	Reset	Acronym	Register Name	Section
0x27	0x1144	SYNCSEL1	Sync Source Selection	8.5.29
0x28	0x0000	SYNCSEL2	Sync Source Selection	8.5.30
0x29	0x0000	PAP_GAIN_AB	PAP path AB Gain Attenuation Step	8.5.31
0x2A	0x0000	PAP_WAIT_AB	PAP path AB Wait Time at Gain = 0	8.5.32
0x2B	0x0000	PAP_GAIN_CD	PAP path CD Gain Attenuation Step	8.5.33
0x2C	0x0000	PAP_WAIT_CD	PAP path CD Wait Time at Gain = 0	8.5.34
0x2D	0x1FFF	PAP_CFG_AB	PAP path AB Configuration	8.5.35
0x2E	0x1FFF	PAP_CFG_CD	PAP path CD Configuration	8.5.36
0x2F	0x0000	SPIDAC_TEST1	Configuration for DAC SPI Constant	8.5.37
0x30	0x0000	SPIDAC_TEST2	DAC SPI Constant	8.5.38
0x31	0x0000	Reserved	Reserved	
0x32	0x0800	GAINAB	Gain for path AB	8.5.39
0x33	0x0800	GAINCD	Gain for path CD	8.5.40
0x34-0x40	0x0000	Reserved	Reserved	0.01.10
0x41	0x0000	JESD_ERR_CNT	JESD Error Counter	8.5.41
0x42-0x45	0x0000	Reserved	Reserved	0.0.11
0x46	0x0044	JESD_ID1	JESD ID 1	8.5.42
0x40	0x190A	JESD ID2	JESD ID 2	8.5.43
0x48	0x31C3	JESD_ID3	JESD ID 2 JESD ID 3 and Subclass	8.5.44
0x48 0x49				0.3.44
	0x0000	Reserved	Reserved	0 5 45
0x4A	0x0003	JESD_LN_EN	JESD Lane Enable	8.5.45
0x4B	0x1300	JESD_RBD_F	JESD RBD Buffer and Frame Octets	8.5.46
0x4C	0x1303	JESD_K_L	JESD K and L Parameters	8.5.47
0x4D	0x0100	JESD_M_S	JESD M and S Parameters	8.5.48
0x4E	0x0F4F	JESD_N_HD_SCR	JESD N, HD and SCR Parameters	8.5.49
0x4F	0x1CC1	JESD_MATCH	JESD Character Match and Other	8.5.50
0x50	0x0000	JESD_LINK_CFG	JESD Link Configuration Data	8.5.51
0x51	0x00FF	JESD_SYNC_REQ	JESD Sync Request	8.5.52
0x52	0x00FF	JESD_ERR_OUT	JESD Error Output	8.5.53
0x53	0x0100	JESD_ILA_CFG1	JESD Configuration Value used for ILA Check	8.5.54
0x54	0x8E60	JESD_ILA_CFG2	JESD Configuration Value used for ILA Check	8.5.55
0x55-0x5B	0x0000	Reserved	Reserved	
0x5C	0x0001	JESD_SYSR_MODE	JESD SYSREF Mode	8.5.56
0x5D-0x5E	0x0000	Reserved	Reserved	
0x5F	0x0123	JESD_CROSSBAR1	JESD Crossbar Configuration 1	8.5.57
0x60	0x4567	JESD_CROSSBAR2	JESD Crossbar Configuration 2	8.5.58
0x61-0x63	0x0000	Reserved	Reserved	
0x64	0x0000	JESD_ALM_L0	JESD Alarms for Lane 0	8.5.59
0x65	0x0000	JESD_ ALM_L1	JESD Alarms for Lane 1	8.5.60
0x66	0x0000	JESD_ ALM_L2	JESD Alarms for Lane 2	8.5.61
0x67	0x0000	JESD_ALM_L3	JESD Alarms for Lane 3	8.5.62
0x68	0x0000	JESD_ALM_L4	JESD Alarms for Lane 4	8.5.63
0x69	0x0000	JESD_ALM_L5	JESD Alarms for Lane 5	8.5.64
0x6A	0x0000	JESD_ALM_L6	JESD Alarms for Lane 6	8.5.65
0x6B	0x0000	JESD_ALM_L7	JESD Alarms for Lane 7	8.5.66
0x6C	0x0000	ALM_SYSREF_PAP	SYSREF and PAP Alarms	8.5.67
0x6D	0x0000	ALM_CLKDIV1	Clock Divider Alarms 1	8.5.68
0x6E-0x77	0x0000	Reserved	Reserved	0.0.00



# **Register Maps (continued)**

Address	Reset	Acronym	Register Name	Section
liscellaneous Con	figuration Registers (P	AGE_SET[1:0] = 00, PAGE_SET[2] = 1)		
0x0A	0xFC03	CLK_CONFIG	Clock Configuration	8.5.69
0x0B	0x0022	SLEEP_CONFIG	Sleep Configuration	8.5.70
0x0C	0xA002	CLK_OUT	Divided Output Clock Configuration	8.5.71
0x0D	0xF000	DACFS	DAC Fullscale Current	8.5.72
0x0E-0x0F	0x0000	Reserved	Reserved	
0x10	0x0000	LCMGEN	Internal sysref generator	8.5.73
0x11	0x0000	LCMGEN_DIV	Counter for internal sysref generator	8.5.74
0x12	0x0000	LCMGEN_SPISYSREF	SPI SYSREF for internal sysref generator	8.5.75
0x13-0x1A	0x0000	Reserved	Reserved	
0x1B	0x0000	DTEST	Digital Test Signals	8.5.76
0x1C-0x22	0x0000	Reserved	Reserved	
0x23	0x03F3	SLEEP_CNTL	Sleep Pin Control	8.5.77
0x24	0x1000	SYSR_CAPTURE	SYSREF Capture Circuit Control	8.5.78
0x25-0x30	0x0000	Reserved	Reserved	
0x31	0x0200	CLK_PLL_CFG	Clock Input and PLL Configuration	8.5.79
0x32	0x0308	PLL_CONFIG1	PLL Configuration 1	8.5.80
0x33	0x4018	PLL_CONFIG2	PLL Configuration 2	8.5.81
0x34	0x0000	LVDS_CONFIG	LVDS Output Configuration	8.5.82
0x35	0x0018	PLL_FDIV	Fuse farm clock divider	8.5.83
0x36-0x3A	0x0000	Reserved	Reserved	
0x3B	0x0002	SRDS_CLK_CFG	Serdes Clock Configuration	8.5.84
0x3C	0x8228	SRDS_PLL_CFG	Serdes PLL Configuration	8.5.85
0x3D	0x0088	SRDS_CFG1	Serdes Configuration 1	8.5.86
0x3E	0x0909	SRDS_CFG2	Serdes Configuration 2	8.5.87
0x3F	0x0000	SRDS_POL	Serdes Polarity Control	8.5.88
0x40-0x75	0x0000	Reserved	Reserved	
0x76	0x0000	SYNCBOUT	JESD204B SYNCB Output	8.5.89

## Table 47. Register Summary (continued)



## 9.5.1 Chip Reset and Configuration Register (address = 0x00) [reset = 0x5803]

# Figure 53. Chip Reset and Configuration Register (RESET\_CONFIG)

15	14	13	12	11	10	9	8
0	0	0	0	0	0	0	х
RW							
7	6	5	4	3	2	1	0
0	0	0	0	0	0	0	0
RW							

LEGEND: R/W = Read/Write; R = Read only; -n = value after reset

## Table 48. RESET\_CONFIG Field Descriptions

Bit	Field	Туре	Reset	Description
15	SPI_RESET	RW	0	This will reset all the SPI registers once programmed.
14	ALM_OUT_POL	RW	1	Changes the polarity of the alarm output. 0= active low 1= active high
13	ALM_OUT_ENA	RW	0	Turn on the alarm pin
12	SYSCLK_ENA	RW	1	Turns on the dividers for the SYSCLK to the Fusefarm
11	AUTOLOAD_TRIG	RW	1	Causes a Fuse AUTOLOAD to be executed.
10:7	Reserved	RW	0000	Reserved
6	ONE_DAC_ONLY	RW	0	When set high only the SLICE0 is available.
5	ONE_LINK_ONLY	RW	0	This needs to be set high when a single link setup is being programmed to get the correct TXENABLE signal generation
4:2	Reserved	RW	000	Reserved
1	INIT_SLICE1	RW	1	Puts the multi-DAC2 JESD into initialization state
0	INIT_SLICE0	RW	1	Puts the multi-DAC1 JESD into initialization state

## 9.5.2 IO Configuration Register (address = 0x01) [reset = 0x1800]

# Figure 54. IO Configuration Register (IO\_CONFIG)

15	14	13	12	11	10	9	8
0	0	0	1	1	0	0	x
R/W							
7	6	5	4	3	2	1	0
0	0	0	0	0	0	0	1
R/W							

LEGEND: R/W = Read/Write; R = Read only; -n = value after reset

Bit	Field	Туре	Reset	Description
15:14	GPO0_SEL	RW	00	Selects the JESD SYNC_N signal coming out the GPO0 pin. Both bits can be asserted which does an oring of the SYNC_N signals from each multi-DUC. bit 0 = 1 then multi-DUC1 SYNC_N used bit 1 = 1 then multi-DUC2 SYNC_N is used
13:12	SYNC0B_SEL	RW	01	Selects the JESD SYNC_N signal coming out the SYNC0B pin. Both bits can be asserted which does an oring of the SYNC_N signals from each multi-DUC. bit 0 = 1 then multi-DUC1 SYNC_N used bit 1 = 1 then multi-DUC2 SYNC_N is used
11:10	SYNC1B_SEL	RW	10	Selects the JESD SYNC_N signal coming out the SYNC1B pin. Both bits can be asserted which does an oring of the SYNC_N signals from each multi-DUC. bit 0 = 1 then multi-DUC1 SYNC_N used bit 1 = 1 then multi-DUC2 SYNC_N is used
9:8	GPO1_SEL	RW	00	Selects the JESD SYNC_N signal coming out the GPO1 pin. Both bits can be asserted which does an oring of the SYNC_N signals from each multi-DUC. bit 0 = 1 then multi-DUC1 SYNC_N used bit 1 = 1 then multi-DUC2 SYNC_N is used
7	SPI4_ENA	RW	0	When set to a '1' the chip is in 4 pin SPI interface mode.
6	Reserved	RW	0	Reserved
5:0	ATEST	RW	000000	Select the analog test points: 000000: ATEST is off (ATEST Must be off during normal operation) 000001, 010001, 000110: VSSCLK 000010: VDDPLL1 000101: VDDCLK 000111, 001010, 010000: VDDAPLL18 001011: VDDAVCO18 001101: VDDS18 001101: VDDE1 001111, 111010, 111011, 111100: DGND 010011: VDDTX1 101001, 110001: AGND 101111, 111101, 11111: VDDDIG1 110000: VDDA18

## 9.5.3 Lane Single Detect Alarm Mask Register (address = 0x02) [reset = 0xFFFF]

15	14	13	12	11	10	9	8
0	0	0	0	0	0	0	x
R/W							
7	6	5	4	3	2	1	0
0	0	0	0	0	0	1	0
R/W							

LEGEND: R/W = Read/Write; R = Read only; -n = value after reset

Bit	Field	Туре	Reset	Description
15:0	ALM_SD_MASK	R/W	0xFFFF	Used to mask alarms bit 15 - bit 8 : Reserved bit7 : lane 7 loss of signal detect bit6 : lane 6 loss of signal detect bit5 : lane 5 loss of signal detect bit4 : lane 4 loss of signal detect bit3 : lane 3 loss of signal detect bit2 : lane 2 loss of signal detect bit1 : lane1 loss of signal detect bit0 : lane 0 loss of signal detect

#### 9.5.4 Clock Alarms Mask Register (address = 0x03) [reset = 0xFFFF

#### Figure 56. Clock Alarms Mask Register (ALM\_CLK\_MASK)

15	14	13	12	11	10	9	8
0	0	0	0	0	0	0	x
R/W							
7	6	5	4	3	2	1	0
0	0	0	0	0	0	1	1
R/W							

LEGEND: R/W = Read/Write; R = Read only; -n = value after reset

#### Table 51. ALM\_CLK\_MASK Field Descriptions

Bit	Field	Туре	Reset	Description
15:0	ALM_CLK_MASK	R/W	0xFFFF	Used to mask alarms bit 15 - bit 8 : Reserved bit 7 : alarm_sysrefphase4 bit 6 : alarm_sysrefphase3 bit 5 : alarm_sysrefphase2 bit 4 : alarm_sysrefphase1 bit 3 : alarm_align_to_r3 bit 2 : alarm_align_to_r1 bit 1 : alarm_sd0_pll bit 0 : alarm_sd1_pll

## 9.5.5 SERDES Loss of Signal Detection Alarms Register (address = 0x04) [reset = 0x0000]

# Figure 57. SERDES Loss of Signal Detection Alarms Register (ALM\_SD\_DET)

15	14	13	12	11	10	9	8
0	0	0	0	0	0	0	x
WOC	W0C	WOC	W0C	W0C	W0C	WOC	W0C
7	6	5	4	3	2	1	0
0	0	0	0	0	1	0	0
WOC	W0C						

LEGEND: R/W = Read/Write; R = Read only; W0C = Write 0 to clear bit; -n = value after reset

#### Table 52. ALM\_SD\_DET Field Descriptions

Bit	Field	Туре	Reset	Description
15:8	Reserved	W0C	0x00	Reserved
7:0	ALM_SD_LOSDET	WOC	0x00	Loss of signal detect outputs from the SERDES lanes: bit 7 = lane7 loss of signal bit 6 = lane6 loss of signal bit 5 = lane5 loss of signal bit 4 = lane4 loss of signal bit 3 = lane3 loss of signal bit 2 = lane2 loss of signal bit 1 = lane1 loss of signal bit 0 = lane0 loss of signal



## 9.5.6 SYSREF Alignment Circuit Alarms Register (address = 0x05) [reset = 0x0000]

# Figure 58. SYSREF Alignment Circuit Alarms Register (ALM\_SYSREF\_DET)

15	14	13	12	11	10	9	8
0	0	0	0	0	0	0	x
W0C							
7	6	5	4	3	2	1	0
0	0	0	0	0	1	0	1
WOC	W0C						

LEGEND: R/W = Read/Write; R = Read only; W0C = Write 0 to clear bit; -n = value after reset

#### Table 53. ALM\_SYSREF\_DET Field Descriptions

Bit	Field	Туре	Reset	Description
15:9	Reserved	W0C	0000000	Reserved
8	ALM_SYSRPHASE4	W0C	0	If high the sysrefphase4 state has been observed in the sysrefalign logic at least once since the last sysrefalign sync.
7	ALM_SYSRPHASE3	W0C	0	If high the sysrefphase3 state has been observed in the sysrefalign logic at least once since the last sysrefalign sync.
6	ALM_SYSRPHASE2	W0C	0	If high the sysrefphase2 state has been observed in the sysrefalign logic at least once since the last sysrefalign sync.
5	ALM_SYSRPHASE1	W0C	0	If high the sysrefphase1 state has been observed in the sysrefalign logic at least once since the last sysrefalign sync.
4	ALM_ALIGN_TO_R3	W0C	0	If high the align_to_r3 state has been observed in the sysrefalign logic at least once since the last sysrefalign sync. TI Internal use only.
3	ALM_ALIGN_TO_R1	W0C	0	If high the align_to_r1 state has been observed in the sysrefalign logic at least once since the last sysrefalign sync. TI Internal use only.
2	ALM_SD0_PLL	W0C	0	Driven high if the PLL in the Serdes 0 block goes out of lock. A false alarm is generated at startup when the PLL is locking. User will have to reset this bit after start to monitor accurately.
1	ALM_SD1_PLL	W0C	0	Driven high if the PLL in the Serdes 1 block goes out of lock. A false alarm is generated at startup when the PLL is locking. User will have to reset this bit after start to monitor accurately.
0	PLL_LOCK	W0C	0	Asserted when PLL is unlocked.

## 9.5.7 Temperature Sensor and PLL Loop Voltage Register (address = 0x06) [reset = variable]

## Figure 59. Temperature Sensor and PLL Loop Voltage Register (TEMP\_PLLVOLT)

15	14	13	12	11	10	9	8
0	0	0	0	0	0	0	x
R	R	R	R	R	R	R	R
7	6	5	4	3	2	1	0
0	0	0	0	0	1	1	0
R	R	R	R	R	R	R	R

LEGEND: R/W = Read/Write; R = Read only; -n = value after reset

#### Table 54. TEMP\_PLLVOLT Field Descriptions

Bit	Field	Туре	Reset	Description
15:8	TEMPDATA	R	0x00	8 bits of data from the tempurature sensor
7:5	PLL_LFVOLT	R	0b000	PLL Loop filter voltage
4:0	Reserved	R	0b000	Reserved

## 9.5.8 Page Set Register (address = 0x09) [reset = 0x0000]

#### Figure 60. Page Set Register (PAGE\_SET)

15	14	13	12	11	10	9	8
0	0	0	0	0	0	0	x
R/W							
7	6	5	4	3	2	1	0
0	0	0	0	1	0	0	1
R/W							

LEGEND: R/W = Read/Write; R = Read only; -n = value after reset

## Table 55. PAGE\_SET Field Descriptions

Bit	Field	Туре	Reset	Description
15:0	PAGE_SET	R/W	0x0000	Each bit selects a page that is active. Multiple pages can be selected at the same time. No bits asserted means that MASTER is the only page selected. bit 0 = page0 : multi-DUC1 bit 1 = page1 : multi-DUC2 bit 2 = page2 : DIG_MISC bit 3-15: Reserved



## 9.5.9 SYSREF Align to r1 and r3 Count Register (address = 0x78) [reset = 0x0000]

#### Figure 61. SYSREF Align to r1 and r3 Count Register (SYSREF\_ALIGN\_R)

15	14	13	12	11	10	9	8
0	0	0	0	0	0	0	x
R	R	R	R	R	R	R	R
7	6	5	4	3	2	1	0
0	1	1	1	1	0	0	0
R	R	R	R	R	R	R	R

LEGEND: R/W = Read/Write; R = Read only; -n = value after reset

#### Table 56. SYSREF\_ALIGN\_R Field Descriptions

Bit	Field	Туре	Reset	Description
15:8	ALIGN_TO_R1_CNT	R	0x00	Part of the SYSREF Align block
7:0	ALIGN_TO_R3_CNT	R	0x00	Part of the SYSREF Align block

#### 9.5.10 SYSREF Phase Count 1 and 2 Register (address = 0x79) [reset = 0x0000]

#### Figure 62. SYSREF Phase Count 1 and 2 Register (SYSREF12\_CNT)

15	14	13	12	11	10	9	8
0	0	0	0	0	0	0	х
R	R	R	R	R	R	R	R
7	6	5	4	3	2	1	0
0	1	1	1	1	0	0	1
R	R	R	R	R	R	R	R

LEGEND: R/W = Read/Write; R = Read only; -n = value after reset

#### Table 57. SYSREF12\_CNT Field Descriptions

Bit	Field	Туре	Reset	Description
15:8	PHASE2_CNT	R	0x00	Part of the SYSREF Align block
7:0	PHASE1_CNT	R	0x00	Part of the SYSREF Align block

## 9.5.11 SYSREF Phase Count 3 and 4 Register (address = 0x7A) [reset = 0x0000]

## Figure 63. SYSREF Phase Count 3 and 4 Register (SYSREF34\_CNT)

15	14	13	12	11	10	9	8
0	0	0	0	0	0	0	x
R	R	R	R	R	R	R	R
7	6	5	4	3	2	1	0
0	1	1	1	1	0	1	0
R	R	R	R	R	R	R	R

LEGEND: R/W = Read/Write; R = Read only; -n = value after reset

#### Table 58. SYSREF34\_CNT Field Descriptions

Bit	Field	Туре	Reset	Description
15:8	PHASE4_CNT	R	0x00	Part of the SYSREF Align block
7:0	PHASE3_CNT	R	0x00	Part of the SYSREF Align block

## 9.5.12 Vendor ID and Chip Version Register (address = 0x7F) [reset = 0x0008]]

## Figure 64. Vendor ID and Chip Version Register (VENDOR\_VER)

15	14	13	12	11	10	9	8
0	0	0	0	0	0	0	х
R	R	R	R	R	R	R	R
7	6	5	4	3	2	1	0
0	1	1	1	1	1	1	1
R	R	R	R	R	R	R	R

LEGEND: R/W = Read/Write; R = Read only; -n = value after reset

## Table 59. VENDOR\_VER Field Descriptions

Bit	Field	Туре	Reset	Description
15	AUTOLOAD_DONE	R	0	Asserted when the Fusefarm Autoload sequence is done
14:10	EFC_ERR	R	00000	The error output from the fuse farm.
9:5	Reserved	R	00000	Reserved
4:3	VENDORID	R	01	TI identification
2:0	VERSION	R	001	Bits to determine what version of build for the chip.

# 9.5.13 Multi-DUC Configuration (PAP, Interpolation) Register (address = 0x0A) [reset = 0x02B0]

# Figure 65. Multi-DUC Configuration (PAP, Interolation) Register (MULTIDUC\_CFG1)

15	14	13	12	11	10	9	8
0	0	0	0	0	0	0	x
R/W							
7	6	5	4	3	2	1	0
1	0	0	0	1	0	1	0
R/W							

LEGEND: R/W = Read/Write; R = Read only; -n = value after reset

#### Table 60. MULTIDUC\_CFG1 Field Descriptions

Bit	Field	Туре	Reset	Description
15	DUAL_IQ	R/W	0	When asserted the SLICE uses both IQ paths
14	ISFIR_ENA	R/W	0	Turns on the inverse sync filter for the AB and CD paths when programmed to 1.
13	Not used	R/W	0	Not used
12:8	INTERP	R/W	00010	Determines the interpolation amount. 00000: 1x 00001: 2x 00010: 4x 00011: 6x 00100: 8x 00101: 10x 00110: 12x 01000: 16x 01001: 18x 01001: 18x 01001: 20x 01100: 24x
7	ALM_ZEROS_TXEN	R/W	1	When asserted any alarm that isn't masked will mid-level the DAC output by setting the txenable_from_dig to '0'
6	DAC_COMPLEMENT	R/W	0	When asserted the DAC output will be 2's complemented. This helps with hookup at the board level.
5	ALM_ZEROS_JESD	R/W	1	When asserted any alarm that isn't masked will zero the data coming out of the JESD block.
4	ALM_OUT_ENA	R/W	1	When asserted the output from the selected SLICE will be passed on to the MASTER alarm control if it is also turned on then the alarm will be sent to the pad_alarm pin.
3	PAPA_ENA	R/W	0	Turns on the Power Amp Protection logic for path A.
2	PAPB_ENA	R/W	0	Turns on the Power Amp Protection logic for path B.
1	PAPC_ENA	R/W	0	Turns on the Power Amp Protection logic for path C.
0	PAPD_ENA	R/W	0	Turns on the Power Amp Protection logic for path D.

## 9.5.14 Multi-DUC Configuration (Mixers) Register (address = 0x0C) [reset = 0x2402]

# Figure 66. Multi-DUC Configuration (Mixers) Register (MULTIDUC\_CFG2)

15	14	13	12	11	10	9	8
0	0	0	0	0	1	0	x
R/W							
7	6	5	4	3	2	1	0
0	0	0	0	1	1	0	0
R/W							

LEGEND: R/W = Read/Write; R = Read only; -n = value after reset

## Table 61. MULTIDUC\_CFG2 Field Descriptions

Bit	Field	Туре	Reset	Description
15:14	DAC_BITWIDTH	R/W	0b00	Determines the bit width of the data going to the DAC 00: 14 bits 01: 14 bits 10: 12 bits 11: 11 bits
13	ZERO_INVLD_DATA	R/W	1 When asserted; the data from the JESD block is zeroe mapper to prevent goofy output from the DAC. For test this bit should be desasserted	
12	SHORTTEST_ENA	R/W	0	Turns on the JESD SHORT pattern test (5.1.6.2)
11	Reserved	R/W	0	Reserved
10	Reserved	R/W	1	Reserved
9	MIXERAB_ENA	R/W	0	Turns on the mixer for the A and B streams
8	MIXERCD_ENA	R/W	0	Turns on the mixer for the C and D streams
7	MIXERAB_GAIN	R/W	0	Adds 6dB of gain when asserted
6	MIXERCD_GAIN	R/W	0	Adds 6dB of gain when asserted
5	NCOAB_ENA	R/W	0	When high the full NCO block is turned on.
4	NCOCD_ENA	R/W	0	When high the full NCO block is turned on.
3:2	Reserved	R/W	00	Reserved
1	TWOS	R/W	1	When asserted the chip is expecting 2's complement data is arriving through the JESD; otherwise offset binary is expected
0	Reserved	R/W	0	Reserved

## 9.5.15 JESD FIFO Control Register (address = 0x0D) [reset = 0x1300]

## Figure 67. JESD FIFO Control Register (JESD\_FIFO)

15	14	13	12	11	10	9	8
0	0	0	0	0	0	0	x
R/W							
-	-	-		-	-		10,10
7	6	5	4	3	2	1	0
0	0	0	0	1	1	0	1
R/W							

LEGEND: R/W = Read/Write; R = Read only; -n = value after reset

## Table 62. JESD\_FIFO Field Descriptions

Bit	Field	Туре	Reset	Description
15	FIFO_ZEROS_DATA	R/W	1	When asserted FIFO errors zero the data out of the JESD block. For test purposes this could be turned off to allow test patterns in the FIFO.
14:13	NOT USED	R/W	000	Not Used
12	SRDS_FIFO_ALM_CLR	R/W	0	Set to 1 to clear FIFO errors. Must be set to 0 for proper FIFO operation
11	Not used	R/W	0	Not used
10:8	FIFO_OFFSET	R/W	0000	Used to set the difference between read and write pointers in the JESD FIFO.
7:1	Reserved	R/W	0	Reserved
0	SPI_TXENABLE	R/W	0	When asserted the internal value of txenable = '1'

#### 9.5.16 Alarm Mask 1 Register (address = 0x0E) [reset = 0x00FF]

## Figure 68. Alarm Mask 1 Register (ALM\_MASK1)

15	14	13	12	11	10	9	8
0	0	0	0	0	0	0	x
R/W							
7	6	5	4	3	2	1	0
0	0	0	0	1	1	1	0
R/W							

LEGEND: R/W = Read/Write; R = Read only; -n = value after reset

#### Table 63. ALM\_MASK1 Field Descriptions

Bit	Field	Туре	Reset	Description
15:0	ALM_MASK1	R/W	0x00FF	Each bit is used to mask an alarm. Assertion masks the alarm: bit 15 = mask lane7 lane errors bit 14 = mask lane6 lane errors bit 13 = mask lane5 lane errors bit 12 = mask lane3 lane errors bit 11 = mask lane2 lane errors bit 10 = mask lane2 lane errors bit 9 = mask lane1 lane errors bit 8 = mask lane1 lane errors bit 7 = mask lane6 FIFO flags bit 6 = mask lane6 FIFO flags bit 5 = mask lane4 FIFO flags bit 3 = mask lane4 FIFO flags bit 3 = mask lane4 FIFO flags bit 4 = mask lane4 FIFO flags bit 3 = mask lane4 FIFO flags bit 1 = mask lane4 FIFO flags bit 1 = mask lane4 FIFO flags bit 1 = mask lane4 FIFO flags bit 0 = mask lane0 FIFO flags

## 9.5.17 Alarm Mask 2 Register (address = 0x0F) [reset = 0xFFFF]

# Figure 69. Alarm Mask 2 Register (ALM\_MASK2)

15	14	13	12	11	10	9	8
0	0	0	0	0	0	0	x
R/W							
7	6	5	4	3	2	1	0
0	0	0	0	1	1	1	1
R/W							

LEGEND: R/W = Read/Write; R = Read only; -n = value after reset

#### Table 64. ALM\_MASK2 Field Descriptions

		-	<b>-</b>	
Bit	Field	Туре	Reset	Description
15:0	ALMS_MASK2	R/W	0xFFF	Each bit is used to mask an alarm. Assertion masks the alarm: bit 15 = not used bit 14 = not used bit 13 = not used bit 12 = mask SYSREF errors on link0 bit 11 = mask alarm from JESD shorttest bit 10 = mask alarm from PAPD bit 9 = mask alarm from PAPC bit 8 = mask alarm from PAPB bit 7 = mask alarm from PAPA bit 6 = not used bit 5 = not used bit 4 = not used bit 2 = not used bit 3 = mask alarm_Clkdiv192_eq_zero bit 0 = mask alarm_clkdiv192 eg mult1



## 9.5.18 Alarm Mask 3 Register (address = 0x10) [reset = 0xFFFF]

# Figure 70. Alarm Mask 3 Register (ALM\_MASK3)

15	14	13	12	11	10	9	8
	0	0	0	0	0	0	x
R/W							
7	6	5	4	3	2	1	0
0	0	0	1	0	0	0	0
R/W							

LEGEND: R/W = Read/Write; R = Read only; -n = value after reset

#### Table 65. ALM\_MASK3 Field Descriptions

Bit	Field	Туре	Reset	Description
15:0	ALMS_MASK3	R/W	0xFFF	Each bit is used to mask an alarm. Assertion masks the alarm: bit 15 = mask alarm_clkdiv8_eq_zero bit 14 = mask alarm_clkdiv12_eq_zero bit 13 = mask alarm_clkdiv16_eq_zero bit 12 = mask alarm_clkdiv20_eq_zero bit 11 = mask alarm_clkdiv32_eq_zero bit 9 = mask alarm_clkdiv36_eq_zero bit 8 = mask alarm_clkdiv40_eq_zero bit 7 = mask alarm_clkdiv40_eq_zero bit 6 = mask alarm_clkdiv40_eq_zero bit 5 = mask alarm_clkdiv40_eq_zero bit 5 = mask alarm_clkdiv40_eq_zero bit 5 = mask alarm_clkdiv40_eq_zero bit 4 = mask alarm_clkdiv40_eq_zero bit 3 = mask alarm_clkdiv128_eq_zero bit 3 = mask alarm_clkdiv128_eq_zero bit 1 = mask alarm_clkdiv144_eq_zero bit 0 = mask alarm_clkdiv160 eq zero

## 9.5.19 Alarm Mask 4 Register (address = 0x11) [reset = 0xFFFF]

# Figure 71. Alarm Mask 4 Register (ALM\_MASK4)

15	14	13	12	11	10	9	8
0	0	0	0	0	0	0	х
R/W							
7	6	5	4	3	2	1	0
0	0	0	1	0	0	0	1
R/W							

LEGEND: R/W = Read/Write; R = Read only; -n = value after reset

#### Table 66. ALM\_MASK4 Field Descriptions

Bit	Field	Туре	Reset	Description
15:0	ALMS_MASK4	R/W	0xFFFF	Each bit is used to mask an alarm. Assertion masks the alarm: bit 15 = mask alarm_clkdiv8_eq_mult1 bit 14 = mask alarm_clkdiv12_eq_mult1 bit 13 = mask alarm_clkdiv16_eq_mult1 bit 12 = mask alarm_clkdiv20_eq_mult1 bit 10 = mask alarm_clkdiv32_eq_mult1 bit 9 = mask alarm_clkdiv36_eq_mult1 bit 8 = mask alarm_clkdiv40_eq_mult1 bit 7 = mask alarm_clkdiv40_eq_mult1 bit 6 = mask alarm_clkdiv40_eq_mult1 bit 5 = mask alarm_clkdiv40_eq_mult1 bit 5 = mask alarm_clkdiv40_eq_mult1 bit 5 = mask alarm_clkdiv40_eq_mult1 bit 4 = mask alarm_clkdiv72_eq_mult1 bit 3 = mask alarm_clkdiv128_eq_mult1 bit 2 = mask alarm_clkdiv128_eq_mult1 bit 1 = mask alarm_clkdiv144_eq_mult1 bit 0 = mask alarm_clkdiv160 eq_mult1



## 9.5.20 JESD Lane Skew Register (address = 0x12) [reset = 0x0000]

## Figure 72. JESD Lane Skew Register (JESD\_LN\_SKEW)

15	14	13	12	11	10	9	8
0	0	0	0	0	0	0	x
R	R	R	R	R	R	R	R
7	6	5	4	3	2	1	0
0	0	0	1	0	0	1	0
R	R	R	R	R	R	R	R

LEGEND: R/W = Read/Write; R = Read only; -n = value after reset

#### Table 67. JESD\_LN\_SKEW Field Descriptions

Bit	Field	Туре	Reset	Description
15:5	NOT USED	R	0x0000	Not used
4:0	MEMIN_LANE_SKEW	R	0b00000	Measure of the lane skew for each link only. Bits are READ_ONLY

## 9.5.21 CMIX Configuration Register (address = 0x17) [reset = 0x0000]

## Figure 73. CMIX Configuration Register (CMIX)

15	14	13	12	11	10	9	8
0	0	0	0	0	0	0	x
R/W							
7	6	5	4	3	2	1	0
0	0	0	1	0	1	1	1
R/W							

LEGEND: R/W = Read/Write; R = Read only; -n = value after reset

#### **Table 68. CMIX Field Descriptions**

Bit	Field	Туре	Reset	Description
15:12	CMIX_AB	R/W	0x0	These bits turn on the different coarse mixing options. Combining the different options together can result in every possible n x Fs/8 [n=0->7]. Below is the valid programming table: cmix=(mem_fs8; mem_fs4; mem_fs2; mem_fsm4) 0000 : no mixing 0001 : -fs/4 0010 : fs/4 0100 : fs/4 1000 : fs/8 1100 : 3fs/8 1010 : 5fs/8 1110 : 7fs/8
11:4	Reserved	R/W	00000000 0	Reserved
3:0	CMIX_CD	R/W	0x0	These bits turn on the different coarse mixing options. Combining the different options together can result in every possible n x Fs/8 [n=0->7]. Below is the valid programming table: cmix=(mem_fs8; mem_fs4; mem_fs2; mem_fsm4) 0000 : no mixing 0001 : -fs/4 0010 : fs/2 0100 : fs/8 1100 : 3fs/8 1010 : 5fs/8 1110 : 7fs/8

TEXAS INSTRUMENTS

www.ti.com

## 9.5.22 Output Summation and Delay Register (address = 0x19) [reset = 0x0000]

## Figure 74. Output Summation and Delay Register (OUTSUM)

15	14	13	12	11	10	9	8
0	0	0	0	0	0	0	x
R/W							
7	6	5	4	3	2	1	0
0	0	0	1	1	0	0	1
R/W							

LEGEND: R/W = Read/Write; R = Read only; -n = value after reset

#### Table 69. OUTSUM Field Descriptions

Bit	Field	Туре	Reset	Description
15:12	OUTPUT_DELAY	R/W	0x0	Delays the output to the DAC 0 to 15 clock cycles
11:4	Reserved	R/W	0x00	Reserved
3:0	OUTSUM_SEL	R/W	0x0	Selects the output summing functions. Each bit selects another sample to sum. Multiple bits can be selected. bit 0 = add the path AB sample bit 1 = add the path CD sample bit 2 = add adjacent DAC path AB sample bit 3 = add adjacent DAC path CD sample

#### 9.5.23 NCO Phase Path AB Register (address = 0x1C) [reset = 0x0000]

## Figure 75. NCO Phase Path AB Register (PHASE\_NCOAB)

15	14	13	12	11	10	9	8
0	0	0	0	0	0	0	х
R/W							
7	6	5	4	3	2	1	0
0	0	0	1	1	1	0	0
R/W							

LEGEND: R/W = Read/Write; R = Read only; -n = value after reset

#### Table 70. PHASE\_NCOAB Field Descriptions

Bit	Field	Туре	Reset	Description
15:0	PHASE_NCO1	Auto Sync	0x0000	The phase offset for the FULL NCO1 in the AB datapath.

#### 9.5.24 NCO Phase Path CD Register (address = 0x1D) [reset = 0x0000]

#### Figure 76. NCO Phase Path CD Register (PHASE\_NCOCD)

15	14	13	12	11	10	9	8
0	0	0	0	0	0	0	0
R/W							
7	6	5	4	3	2	1	0
0	0	0	1	1	1	0	1
R/W							

LEGEND: R/W = Read/Write; R = Read only; -n = value after reset

#### Table 71. PHASE\_NCOCD Field Descriptions

Bit	Field	Туре	Reset	Description
15:0	PHASE_NCO12	Auto Sync	0x0000	The phase offset for the FULL NCO2 in the CD datapath.

9.5.25 NCO Frequency Path AB Register (address = 0x1E-0x20) [reset = 0x0000 0000 0000]

15	14	13	12	11	10	9	8
0	0	0	0	0	0	0	x
R/W							
7	6	5	4	3	2	1	0
0	0	0	1	1	1	1	0
R/W							

#### Figure 77. NCO Frequency Path AB Register (FREQ\_NCOAB)

LEGEND: R/W = Read/Write; R = Read only; -n = value after reset

#### Table 72. FREQ\_NCOAB Field Descriptions

Bit	Field	Туре	Reset	Description
47:0	FREQ_NCOAB	R/W	0x0000 0000 0000	NCO frequency word for AB data path.

## 9.5.26 NCO Frequency Path CD Register (address = 0x21-0x23) [reset = 0x0000 0000 0000]

## Figure 78. NCO Frequency Path CD Register (FREQ\_NCOCD)

15	14	13	12	11	10	9	8
0	0	0	0	0	0	0	х
R/W							
7	6	5	4	3	2	1	0
0	0	1	0	0	0	0	1
R/W							

LEGEND: R/W = Read/Write; R = Read only; -n = value after reset

## Table 73. FREQ\_NCOCD Field Descriptions

Bit	Field	Туре	Reset	Description
47:0	FREQ_NCOCD	R/W	0x0000 0000 0000	NCO frequency word for CD data path.

## 9.5.27 SYSREF Use for Clock Divider Register (address = 0x24) [reset = 0x0010]

# Figure 79. SYSREF Use for Clock Divder Register (SYSREF\_CLKDIV)

15	14	13	12	11	10	9	8
0	0	0	0	0	0	0	x
R/W							
7	6	5	4	3	2	1	0
0	0	1	0	0	1	0	0
R/W							

LEGEND: R/W = Read/Write; R = Read only; -n = value after reset

## Table 74. SYSREF\_CLKDIV Field Descriptions

Bit	Field	Туре	Reset	Description
15	Reserved	R/W	0	Reserved
14:12	CDRVSER_SYSREF_DLY	R/W	000	Programmable delay the SYSREF by N dacclk cycles to the CDRV_SER clock dividers. By offsetting the clock to the different multi-DUC blocks, clock mixing could potentially be reduced.
11:7	Not used	R/W	00000	Not used
6:4	SYSREF_MODE	R/W	001	Determines how SYSREF is used to sync the clock dividers in the CDRV_SER block. 000 = Don't use SYSREF pulse 001 = Use all SYSREF pulses 010 = Use only the next SYSREF pulse 011 = Skip one SYSREF pulse then use only the next one 100 = Skip one SYSREF pulse then use all pulses.
3:2	SYSREF_DLY	R/W	00	Delays the SYSREF into the CDRV_SER capture FF through 1 of 4 choices. This allows for extra delay in case the timing of the clock or SYSREF path isn't as good as we think.
1:0	Reserved	R/W	00	Reserved



## 9.5.28 Serdes Clock Control Register (address = 0x25) [reset = 0x7700]

# Figure 80. Serdes Clock Control Register (SERDES\_CLK)

15	14	13	12	11	10	9	8
0	0	0	0	0	0	0	х
R/W							
7	6	5	4	3	2	1	0
0	0	1	0	0	1	0	1
R/W							

LEGEND: R/W = Read/Write; R = Read only; -n = value after reset

Bit	Field	Туре	Reset	Description
15:12	CLKJESD_DIV	R/W	0x7	This controls the selection of the clk_jesd output 0000 = div4 0001 = div8 0010 = div12 0011 = div16 0100 = div18 0101 = div20 0110 = div24 0111 = div36 1010 = div48 1011 = div64 1100 = div5.333 1101 = div10.666 1110 = div21p333
11:8	CLKJESD_OUT_DIV	R/W	0x7	This controls the selection of the clk_jesd_out output 0000 = div8 0001 = div16 0010 = div32 0011 = div48 0100 = div64 0101 = div80 0110 = div96 0111 = div128 1000 = div144 1001 = div160 1010 = div192
7:0	Reserved	R/W	0x0	Reserved

## Table 75. SERDES\_CLK Field Descriptions

TEXAS INSTRUMENTS

www.ti.com

# 9.5.29 Sync Source Control 1 Register (address = 0x27) [reset = 0x1144]

# Figure 81. Sync Source Control 1 Register (SYNCSEL1)

15	14	13	12	11	10	9	8
0	0	0	0	0	0	0	x
R/W							
7	6	5	4	3	2	1	0
0	0	1	0	0	1	1	1
R/W							

LEGEND: R/W = Read/Write; R = Read only; -n = value after reset

#### Table 76. SYNCSEL1 Field Descriptions

Bit	Field	Туре	Reset	Description
15:12	SYNCSEL_MIXERAB	R/W	0x1	Controls the syncing of the double buffered SPI registers for the mixerAB block. These bits are enables so a '1' in the bit place allows the sync to pass to the block. bit 0 = auto-sync from SPI register write bit 1 = sysref bit 2 = sync_out from JESD bit 3 = mem_spi_sync
11:8	SYNCSEL_MIXERCD	R/W	0x1	Controls the syncing of the double buffered SPI registers for the mixerCD block. These bits are enables so a '1' in the bit place allows the sync to pass to the block. bit 0 = auto-sync from SPI register write bit 1 = sysref bit 2 = sync_out from JESD bit 3 = mem_spi_sync
7:4	SYNCSEL_NCOAB	R/W	0x4	Controls the syncing of NCOAB accumulators. These bits are enables so a '1' in the bit place allows the sync to pass to the block. bit 0 = '0' bit 1 = sysref bit 2 = sync_out from JESD bit 3 = mem_spi_sync
3:0	SYNCSEL_NCOCD	R/W	0x4	Controls the syncing of NCOCD accumulators. These bits are enables so a '1' in the bit place allows the sync to pass to the block. bit 0 = '0' bit 1 = sysref bit 2 = sync_out from JESD bit 3 = mem_spi_sync

## 9.5.30 Sync Source Control 2 Register (address = 0x28) [reset = 0x0000]

Figure 82. S	Sync Source	Control 2 Register	(SYNCSEL2)
--------------	-------------	--------------------	------------

15	14	13	12	11	10	9	8
0	0	0	0	0	0	0	x
R/W							
7	6	5	4	3	2	1	0
0	0	1	0	1	0	0	0
R/W							

LEGEND: R/W = Read/Write; R = Read only; -n = value after reset

Bit	Field	Туре	Reset	Description
15:12	Reserved	R/W	0x0	Reserved
11:8	SYNCSEL_PAPAB	R/W	0x0	Select the sync for the PAP A and B. bit 0 = '0' bit 1 = sysref bit 2 = sync_out from JESD bit 3 = mem_spi_sync
7:4	SYNCSEL_PAPCD	R/W	0x0	Select the sync for the PAP C and D. bit 0 = '0' bit 1 = sysref bit 2 = sync_out from JESD bit 3 = mem_spi_sync
3:2	Reserved	R/W	0b00	Reserved
1	SPI_SYNC	R/W	0	This is used to generate the SPI_SYNC signal
0	Reserved	R/W	0	Reserved

## 9.5.31 PAP path AB Gain Attenuation Step Register (address = 0x29) [reset = 0x0000]

#### Figure 83. PAP path AB Gain Attenuation Step Register (PAP\_GAIN\_AB)

15	14	13	12	11	10	9	8
0	0	0	0	0	0	0	x
R/W							
7	6	5	4	3	2	1	0
0	0	1	0	1	0	0	1
R/W							

LEGEND: R/W = Read/Write; R = Read only; -n = value after reset

## Table 78. PAP\_GAIN\_AB Field Descriptions

Bit	Field	Туре	Reset	Description
15:10	NOT USED	RW	000000	Not Used
9:0	PAPAB_GAIN_STEP		0x000	Gain attenuation step

TEXAS INSTRUMENTS

www.ti.com

## 9.5.32 PAP path AB Wait Time Register (address = 0x2A) [reset = 0x0000]

#### Figure 84. PAP path AB Wait Time Register (PAP\_WAIT\_AB)

15	14	13	12	11	10	9	8
0	0	0	0	0	0	0	x
R/W							
7	6	5	4	3	2	1	0
0	0	1	0	1	0	1	0
R/W							

LEGEND: R/W = Read/Write; R = Read only; -n = value after reset

#### Table 79. PAP\_WAIT\_AB Field Descriptions

Bit	Field	Туре	Reset	Description
15:10	Reserved	000000	R/W	Reserved
9:0	PAPAB_WAIT	0x000	R/W	Number of clock cycles to wait after gain = 0

#### 9.5.33 PAP path CD Gain Attenuation Step Register (address = 0x2B) [reset = 0x0000]

#### Figure 85. PAP path CD Gain Attenuation Step Register (PAP\_GAIN\_CD)

15	14	13	12	11	10	9	8
0	0	0	0	0	0	0	х
R/W							
7	6	5	4	3	2	1	0
0	0	0	0	1	0	1	1
R/W							

LEGEND: R/W = Read/Write; R = Read only; -n = value after reset

#### Table 80. PAP\_GAIN\_CD Field Descriptions

Bit	Field	Туре	Reset	Description
15:10	Not Used	R/W	000000	Not Used
9:0	PAPCD_GAIN_STEP	R/W	0x000	Gain attenuation step

#### 9.5.34 PAP Path CD Wait Time Register (address = 0x2C) [reset = 0x0000]

## Figure 86. PAP path CD Wait Time Register (PAP\_WAIT\_CD)

15	14	13	12	11	10	9	8
0	0	0	0	0	0	0	х
R/W							
7	6	5	4	3	2	1	0
0	0	1	0	1	1	0	0
R/W							

LEGEND: R/W = Read/Write; R = Read only; -n = value after reset

#### Table 81. PAP\_WAIT\_CD Field Descriptions

Bit	Field	Туре	Reset	Description
15:10	Reserved	R/W	000000	Reserved
9:0	PAPCD_WAIT	R/W	0x000	Number of clock cycles to wait after gain = 0

## 9.5.35 PAP path AB Configuration Register (address = 0x2D) [reset = 0x0FFF]

15	14	13	12	11	10	9	8
0	0	Reserved	0	0	0	0	x
R/W	R/W	R/W	R/W	R/W	R/W	R/W	R/W
7	6	5	4	3	2	1	0
0	0	1	0	1	1	0	1
R/W	R/W	R/W	R/W	R/W	R/W	R/W	R/W

LEGEND: R/W = Read/Write; R = Read only; -n = value after reset

Table 82.	PAP_		AB	Field	Descriptions
-----------	------	--	----	-------	--------------

Bit	Field	Туре	Reset	Description
15:14	PAPAB_SEL_DLY	R/W	00	Controls the length of the delayline in the PAP AB logic. 00 : N = 32 01 : N = 64 10 : N = 128 11 : Not Valid
13	Reserved	R/W	0	Reserved
12:0	PAPAB_THRESH	R/W	0xFFF	The threshold for the PAP AB trigger.

## 9.5.36 PAP path CD Configuration Register (address = 0x2E) [reset = 0x0FFF]

## Figure 88. PAP path CD Configuration Register (PAP\_CFG\_CD)

15	14	13	12	11	10	9	8
0	0	0	0	0	0	0	х
R/W							
7	6	5	4	3	2	1	0
0	0	1	0	1	1	1	0
R/W							

LEGEND: R/W = Read/Write; R = Read only; -n = value after reset

#### Table 83. PAP\_CFG\_CD Field Descriptions

Bit	Field	Туре	Reset	Description
15:14	PAPCD_SEL_DLY	R/W	00	Controls the length of the delay line in the PAP CD logic. 00 : N = 32 01 : N = 64 10 : N = 128 11 : Not Valid
13	Reserved	R/W	0	Reserved
12:0	PAPCD_THRESH	R/W	0xFFF	The threshold for the PAP CD trigger.

## 9.5.37 DAC SPI Configuration Register (address = 0x2F) [reset = 0x0000]

## Figure 89. DAC SPI Constant 1 Register (SPIDAC\_TEST1)

15	14	13	12	11	10	9	8
0	0	0	0	0	0	0	x
R/W							
7	6	5	4	3	2	1	0
0	0	1	0	1	1	1	1
R/W							

LEGEND: R/W = Read/Write; R = Read only; -n = value after reset

#### Table 84. SPIDAC\_TEST1 Field Descriptions

Bit	Field	Туре	Reset	Description
15:1	Reserved	R/W	0x0000	Reserved
0	SPIDAC_ENA	R/W	0	When asserted the DAC output is set to the value in register SPIDAC. This can be used for trim setting and other static tests.

## 9.5.38 DAC SPI Constant Register (address = 0x30) [reset = 0x0000]

# Figure 90. DAC SPI Constant Register (SPIDAC\_TEST2)

15	14	13	12	11	10	9	8
0	0	0	0	0	0	0	х
R/W							
7	6	5	4	3	2	1	0
0	0	1	1	0	0	0	0
R/W							

LEGEND: R/W = Read/Write; R = Read only; -n = value after reset

#### Table 85. SPIDAC\_TEST2 Field Descriptions

Bit	Field	Туре	Reset	Description
15:0	SPIDAC	R/W	0x0000	This value replaces the data at the output of the JESD so that the DAC value can be controlled

## 9.5.39 Gain for path AB Register (address = 0x32) [reset = 0x0000]

#### Figure 91. Gain for path AB Register (GAINAB)

15	14	13	12	11	10	9	8
0	0	0	0	0	0	0	x
R/W							
7	6	5	4	3	2	1	0
0	0	1	1	0	0	1	0
R/W							

LEGEND: R/W = Read/Write; R = Read only; -n = value after reset

#### Table 86. GAINAB Field Descriptions

Bit	Field	Туре	Reset	Description
15	GAINAB_ENA	R/W	0	Turns on the path AB gain block
14:12	Reserved	R/W	0x0	Reserved
11:0	GAINAB	R/W	0x400	Extra control of gain in the GAINAB block. This allows a fix gain to be added to the signal if needed.

## 9.5.40 Gain for path CD Register (address = 0x33) [reset = 0x0000]

#### Figure 92. Gain for path CD Register (GAINCD)

15	14	13	12	11	10	9	8
0	0	0	0	0	0	0	х
R/W							
7	6	5	4	3	2	1	0
0	0	1	1	0	0	1	1
R/W							

LEGEND: R/W = Read/Write; R = Read only; -n = value after reset

#### **Table 87. GAINCD Field Descriptions**

Bit	Field	Туре	Reset	Description
15	GAINCD_ENA	R/W	0	Turns on the Path CD gain block
14:12	Reserved	R/W	0x0	Reserved
11:0	GAINCD	R/W	0x400	Extra control of gain in the GAINCD block. This allows a fix gain to be added to the signal if needed.

## 9.5.41 JESD Error Counter Register (address = 0x41) [reset = 0x0000]

## Figure 93. JESD Error Counter Register (JESD\_ERR\_CNT)

15	14	13	12	11	10	9	8
0	0	0	0	0	0	0	x
R	R	R	R	R	R	R	R
7	6	5	4	3	2	1	0
0	1	0	0	0	0	0	1
R	R	R	R	R	R	R	R

LEGEND: R/W = Read/Write; R = Read only; -n = value after reset

#### Table 88. JESD\_ERR\_CNT Field Descriptions

Bit	Field	Туре	Reset	Description
15:0	JESD_ERR_CNT	R	0x0000	This is the error count for the JESD link. This is a 16bit value that is not cleared until the JESD synchronization is required or errcnt_clr is programmed to '1'

#### 9.5.42 JESD ID 1 Register (address = 0x46) [reset = 0x0044]

#### Figure 94. JESD ID 1 Register (JESD\_ID1)

15	14	13	12	11	10	9	8
0	0	0	0	0	0	0	х
R	R	R	R	R	R	R	R
7	6	5	4	3	2	1	0
0	1	0	0	0	1	1	0
R	R	R	R	R	R	R	R

LEGEND: R/W = Read/Write; R = Read only; -n = value after reset

#### Table 89. JESD\_ID1 Field Descriptions

Bit	Field	Туре	Reset	Description
15:11	LID0	R/W	00000	JESD ID for lane 0
10:6	LID1	R/W	00001	JESD ID for lane 1
5:1	LID2	R/W	00010	JESD ID for lane 2
0	Reserved	R/W	0	Reserved



## 9.5.43 JESD ID 2 Register (address = 0x47) [reset = 0x190A]

#### Figure 95. JESD ID 2 Register (JESD\_ID2)

15	14	13	12	11	10	9	8
0	0	0	0	0	0	0	0
R	R	R	R	R	R	R	R
7	6	5	4	3	2	1	0
0	1	0	0	0	1	1	1
R	R	R	R	R	R	R	R

LEGEND: R/W = Read/Write; R = Read only; -n = value after reset

#### Table 90. JESD ID 2 Register (JESD\_ID2)

Bit	Field	Туре	Reset	Description
15:11	LID3	R/W	00011	JESD ID for lane 3
10:6	LID4	R/W	00100	JESD ID for lane 4
5:1	LID5	R/W	00101	JESD ID for lane 5
0	Reserved	R/W	0	Reserved

## 9.5.44 JESD ID 3 and Subclass Register (address = 0x48) [reset = 0x31C3]

## Figure 96. JESD ID 3 Register (JESD\_ID3)

15	14	13	12	11	10	9	8
0	0	0	0	0	0	0	х
R/W							
7	6	5	4	3	2	1	0
0	1	0	0	1	0	0	0
R/W							

LEGEND: R/W = Read/Write; R = Read only; -n = value after reset

#### Table 91. JESD\_ID3 Field Descriptions

Bit	Field	Туре	Reset	Description
15:11	LID6	R/W	00110	JESD ID for lane 6
10:6	LID7	R/W	00111	JESD ID for lane 7
5:4	Reserved	R/W	00	Reserved
3:1	SUBCLASSV	R/W	001	Selects the JESD subclass supported. Note: "001" is subclass 1 and "000" is subclass 0 they are the only modes supported; not used for operation but used for configuration. See field MIN_LATENCY_ENA in register JESD_MATCH (9.5.46) for use in subclass0
0	JESDV	R/W	1	Selects the version of JESD support(0=A; 1=B) NOTE: JESD 204B is only supported version.

STRUMENTS

EXAS

## 9.5.45 JESD Lane Enable Register (address = 0x4A) [reset = 0x0003]

# Figure 97. JESD Lane Enable Register (JESD\_LN\_EN)

15	14	13	12	11	10	9	8
0	0	0	0	0	0	0	x
R/W							
7	6	5	4	3	2	1	0
0	1	0	0	1	0	1	0
R/W							

LEGEND: R/W = Read/Write; R = Read only; -n = value after reset

## Table 92. JESD\_LN\_EN Field Descriptions

Bit	Field	Туре	Reset	Description
15:8	LANE_ENA		0x00	Turn on each lane as needed. Signal is active high. bit 15 : lane7 enable bit 14 : lane6 enable bit 13 : lane5 enable bit 12 : lane4 enable bit 11 : lane3 enable bit 10 : lane2 enable bit 9 : lane1 enable bit 8 : lane0 enable
7:6	JESD_TEST_SEQ		00	Set to select and verify link layer test sequences. The error for these sequences comes out the lane alarms bit0. 1= a fail and 0 = pass. 00 : test sequence disabled 01 : verify repeating D.21.5 high frequency pattern for random jitter 10 : verify repeating K.28.5 mixed frequency pattern for deterministic jitter 11 : verify repeating ILA sequence
5:2	Reserved		0x0	Reserved
1:0	1:0 JESD_PHASE_MODE		11	Used to tell the JESD block how many clock phases are being used for lanes. 00 = 1 phase 01 = 2 phases 10 = 4 phases 11 = 8 phases

9.5.46 JESD RBD Buffer and Frame Octets Register (address = 0x4B) [reset = 0x1300]

	IECD DED Buffer and Fram	- Octobe Degister	
Figure 30	. JESD RBD Buffer and Frame	e Ociels Register	

15	14	13	12	11	10	9	8
			0	0	0	0	0
R/W							
7	6	5	4	3	2	1	0
0	1	0	0		0	1	1
R/W							

LEGEND: R/W = Read/Write; R = Read only; -n = value after reset

Table 93. JESD_	RBD_F	Field	Descriptions
-----------------	-------	-------	--------------

Bit	Field	Туре	Reset	Description
15:13	Reserved	R/W	00	Reserved
12:8	RBD	R/W	10011	This controls the amount of elastic buffers being used in the JESD. Larger numbers will mean more latency; but smaller numbers may not hold enough data to capture the input skew. This value must always be ≤ mem_k
7:0	F_M1	R/W	0x00	This is the number of octets in the frame - 1

## 9.5.47 JESD K and L Parameters Register (address = 0x4C) [reset = 0x1303]

## Figure 99. JESD K and L Parameters Register (JESD\_K\_L)

15	14	13	12	11	10	9	8
0	0	0	0	0	0	0	х
R/W							
7	6	5	4	3	2	1	0
0	1	0	0	1	1	0	0
R/W							

LEGEND: R/W = Read/Write; R = Read only; -n = value after reset

#### Table 94. JESD\_K\_L Field Descriptions

Bit	Field	Туре	Reset	Description
15:13	Reserved	R/W	000	Reserved
12:8	K_M1	R/W	10011	The number of frames in a multi-frame - 1. $0 \le k - 1 < 32$
7:5	Reserved	R/W	0	Reserved
4:0	L_M1	R/W	00011	The number of lanes used by the JESD - 1. $0 \le L - 1 < 8$

## 9.5.48 JESD M and S Parameters Register (address = 0x4D) [reset = 0x0100]

## Figure 100. JESD M and S Parameters Register (JESD\_M\_S)

15	14	13	12	11	10	9	8
0	0	0	0	0	0	0	0
R/W							
7	6	5	4	3	2	1	0
0	1	0	0	1	1	0	1
R/W							

LEGEND: R/W = Read/Write; R = Read only; -n = value after reset

#### Table 95. JESD\_M\_S Field Descriptions

Bit	Field	Туре	Reset Description	
15:8	M_M1	R/W	0x01	The number of streams per frame - 1. $0 \le M - 1 < 256$
7:5	Reserved	R/W	000	Reserved
4:0	S_M1	R/W	00000	The number of samples per stream per frame - 1.

## 9.5.49 JESD N, HD and SCR Parameters Register (address = 0x4E) [reset = 0x0F4F]

#### Figure 101. JESD N, HD and SCR Parameters Register (JESD\_N\_HD\_SCR)

15	14	13	12	11	10	9	8
0	0	0	0	0	0	0	0
R/W							
7	6	5	4	3	2	1	0
0	1	0	0	1	1	1	0
R/W							

LEGEND: R/W = Read/Write; R = Read only; -n = value after reset

## Table 96. JESD\_N\_HD\_SCR Field Descriptions

Bit	Field	Туре	Reset	Description
15:13	Reserved	R/W	000	Reserved
12:8	NPRIME_M1	R/W	01111	The number of adjusted bits per sample - 1
7	Reserved	R/W	0	Reserved
6	HD	R/W	1	High density mode. Samples can cross the lane boundary
5	SCR	R/W	0	Turn on the scrambler
4:0	N_M1	R/W	01111	The number of bits per sample - 1

## 9.5.50 JESD Character Match and Other Register (address = 0x4F) [reset = 0x1CC1]

# Figure 102. JESD Character Match and Other Parameters Register (JESD\_MATCH)

15	14	13	12	11	10	9	8
0	0	0	0	0	0	0	x
R/W							
7	6	5	4	3	2	1	0
0	1	0	0	1	1	1	1
R/W							

LEGEND: R/W = Read/Write; R = Read only; -n = value after reset

#### Table 97. JESD\_MATCH Field Descriptions

Bit	Field	Туре	Reset	Description
15:8	MATCH_DATA	R/W	0x1C	The character to match for buffer release. Normally it is a /R/=/K28.0/-0x1C but with these bits the user can program the value.
7	MATCH_SPECIFIC	R/W	1	Match a specific charater to start the JESD buffering when asserted; otherwise the first non-K will start the buffering.
6	MATCH_CTRL	R/W	1	When asserted the match character is a CONTROL character instead of a DATA character.
5	NO_LANE_SYNC	R/W	0	Assert if the TX side does not support lane initialization. This way the RX won't flag errors in the configuration portion of the ILA.
4:2	Not Used	R/W	000	Not Used
1	MIN_LATENCY_ENA	R/W	0	Enable minimum latency when set. This is needed for subclass 0 support.
0	JESD_COMMAALIGN_ENA	R/W	1	When asserted the JESD block SERDES comma align signal will be added with the SERDES ALIGN bit(0) to control when to shut off comma alignment. When this bit is deasserted; then the programmed bit(spi_config62(11)) is the only control.

## 9.5.51 JESD Link Configuration Data Register (address = 0x50) [reset = 0x0000]

## Figure 103. JESD Link Configuration Data Register (JESD\_LINK\_CFG)

15	1.4	10	10	11	10	0	0
10	14	13	12	11	10	9	0
0	0	0	0	0	0	0	Х
R/W							
7	6	5	4	3	2	1	0
0	1	0	1	0	0	0	0
R/W							

LEGEND: R/W = Read/Write; R = Read only; -n = value after reset

#### Table 98. JESD\_Link\_CFG Field Descriptions

Bit	Field	Туре	Reset	Description
15-12	ADJCNT	R/W	0x0	Lane configuration data for link. Reserved by DAC38RF8x except for lane configuration checking.
11	ADJDIR	R/W	0	Lane configuration data for link. Reserved by DAC38RF8x except for lane configuration checking.
10-7	BID	R/W	0x0	Lane configuration data for link. Reserved by DAC38RF8x except for lane configuration checking.
6-2	CF	R/W	00000	Lane configuration data for link. Reserved by DAC38RF8x except for lane configuration checking.
1-0	CS	R/W	00	Lane configuration data for link. Reserved by DAC38RF8x except for lane configuration checking.

#### 9.5.52 JESD Sync Request Register (address = 0x51) [reset = 0x00FF]

#### Figure 104. JESD Sync Request Register (JESD\_SYNC\_REQ)

15	14	13	12	11	10	9	8
0	0	0	0	0	0	0	х
R/W							
7	6	5	4	3	2	1	0
0	1	0	1	0	0	0	1
R/W							

LEGEND: R/W = Read/Write; R = Read only; -n = value after reset

#### Table 99. JESD\_SYNC\_REQ Field Descriptions

Bit	Field	Туре	Reset	Description
15:8	DID	R/W	0x00	Lane configuration
7:0	SYNC_REQUEST	R/W	0xFF	These bits select which errors cause a sync request. Sync requests take priority over the error notification; so if sync request isn't desired; set these bits to a '0'. bit 7 = multi-frame alignment error bit 6 = frame alignment error bit 5 = link configuration error bit 4 = elastic buffer overflow (bad RBD value) bit 3 = elastic buffer end char mismatch (match_ctrl match_data) bit 2 = code synchronization error bit 1 = 8b/10b not-in-table code error bit 0 = 8b/10b disparity error



## 9.5.53 JESD Error Output Register (address = 0x52) [reset = 0x00FF]

## Figure 105. JESD Error Output Register (JESD\_ERR\_OUT)

15	14	13	12	11	10	9	8
0	0	0	0	0	0	0	x
R/W							
7	6	5	4	3	2	1	0
0	1	0	1	0	0	1	0
R/W							

LEGEND: R/W = Read/Write; R = Read only; -n = value after reset

#### Table 100. JESD\_ERR\_OUT Field Descriptions

Bit	Field	Туре	Reset	Description
15:10	Reserved	R/W	000000	Reserved
9	DISABLE_ERR_RPT	R/W	0	Assertion means that errors will not be reported on the sync_n output.
8	PHADJ	R/W	0	Lane configuration
7:0	ERR_ENA	R/W	0xFF	These bits select the errors generated are counted in the err_c for the link. The bits also control what signals are sent out the pad_syncb pin for error notification. bit 7 = multi-frame alignment error bit 6 = frame alignment error bit 5 = link configuration error bit 4 = elastic buffer overflow (bad RBD value) bit 3 = elastic buffer end char mismatch (match_ctrl match_data) bit 2 = code synchronization error bit 1 = 8b/10b not-in-table code error bit 0 = 8b/10b disparity error

## 9.5.54 JESD ILA Check 1 Register (address = 0x53) [reset = 0x0100]

#### Figure 106. JESD ILA Check 1 Register (JESD\_ILA\_CFG1)

15	14	13	12	11	10	9	8
0	0	0	0	0	0	0	х
R/W							
7	6	5	4	3	2	1	0
0	1	0	1	0	0	1	1
R/W							

LEGEND: R/W = Read/Write; R = Read only; -n = value after reset

#### Table 101. JESD\_ILA\_CFG1 Field Descriptions

Bit	Field	Туре	Reset	Description
15:8	ILA_M	R/W	0x01	JESD M-1 configuration value used only for ILA checking; may be set independently of the actual JESD mode
7:0	ILA_F	R/W	0x00	JESD F-1 configuration value used only for ILA checking; may be set independently of the actual JESD mode

#### 9.5.55 JESD ILA Check 2 Register (address = 0x54) [reset = 0x8E60]

15	14	13	12	11	10	9	8
0	0	0	0	0	0	0	x
R/W							
7	6	5	4	3	2	1	0
0	1	0	1	0	1	0	0
R/W							

#### Figure 107. JESD ILA Check 2 Register (JESD\_ILA\_CFG2)

LEGEND: R/W = Read/Write; R = Read only; -n = value after reset

#### Table 102. JESD\_ILA\_CFG2 Field Descriptions

Bit	Field	Туре	Reset	Description
15	ILA_HD	R/W	1	JESD HD configuration value used only for ILA checking; may be set independently of the actual JESD mode
14:10	ILA_L	R/W	00011	JESD L-1 configuration value used only for ILA checking; may be set independently of the actual JESD mode
9:5	ILA_K	R/W	10011	JESD K-1 configuration value used only for ILA checking; may be set independently of the actual JESD mode
4:0	ILA_S	R/W	00000	JESD S-1 configuration value used only for ILA checking; may be set independently of the actual JESD mode

## 9.5.56 JESD SYSREF Mode Register (address = 0x5C) [reset = 0x0001]

## Figure 108. JESD SYSREF Mode Register (JESD\_SYSR\_MODE)

15	14	13	12	11	10	9	8
0	0	0	0	0	0	0	x
R/W							
7	6	5	4	3	2	1	0
0	1	0	1	1	1	0	0
R/W							

LEGEND: R/W = Read/Write; R = Read only; -n = value after reset

#### Table 103. JESD\_SYSR\_MODE Field Descriptions

Bit	Field	Туре	Reset	Description
15:4	Reserved	R/W	0x000	Reserved
3	ERR_CNT_CLR	R/W	0	A transition from 0->1 causes the error_cnt to be cleared
2:0	SYSREF_MODE	R/W	001	Determines how SYSREF is used in the JESD synchronizing block. 000 = Don't use SYSREF pulse 001 = Use all SYSREF pulses 010 = Use only the next SYSREF pulse 011 = Skip one SYSREF pulse then use only the next one 100 = Skip one SYSREF pulse then use all pulses. 101 = skip two SYSREFs and then use one 110 = skip two SYSREFs and then use all

## 9.5.57 JESD Crossbar Configuration 1 Register (address = 0x5F) [reset = 0x0123]

# Figure 109. JESD Crossbar Configuration 1 Register (JESD\_CROSSBAR1)

15	14	13	12	11	10	9	8
Reserved	0	0	0	Reserved	0	0	x
R/W	R/W	R/W	R/W	R/W	R/W	R/W	R/W
7	6	5	4	3	2	1	0
0	1	0	1	1	1	1	1
R/W	R/W	R/W	R/W	R/W	R/W	R/W	R/W

LEGEND: R/W = Read/Write; R = Read only; -n = value after reset

Table 104. JESE	CROSSBAR1	<b>Field Descriptions</b>
-----------------	-----------	---------------------------

Bit	Field	Туре	Reset	Description
15	Reserved	R/W	0	Reserved
14:12	OCTETPATH0_SEL	R/W	000	These bits are used by the cross-bar switch to map any lane to any other lane. The 3 bit term tells the mapper block what lane this particular lane is supposed to be treated as. 000 = treat as lane0 001 = treat as lane1 010 = treat as lane2 011 = treat as lane3 100 = treat as lane4 101 = treat as lane5 110 = treat as lane6 111 = treat as lane7
11	Reserved	R/W	0	Reserved
10:8	OCTETPATH1_SEL	R/W	001	These bits are used by the cross-bar switch to map any lane to any other lane. The 3 bit term tells the mapper block what lane this particular lane is supposed to be treated as. 000 = treat as lane0 001 = treat as lane1 010 = treat as lane2 011 = treat as lane3 100 = treat as lane4 101 = treat as lane5 110 = treat as lane6 111 = treat as lane7
7	Reserved	R/W	0	Reserved
6:4	OCTETPATH2_SEL	R/W	010	These bits are used by the cross-bar switch to map any lane to any other lane. The 3 bit term tells the mapper block what lane this particular lane is supposed to be treated as. 000 = treat as lane0 001 = treat as lane1 010 = treat as lane2 011 = treat as lane3 100 = treat as lane4 101 = treat as lane5 110 = treat as lane6 111 = treat as lane7
3	Reserved	R/W	0	Reserved
2:0	OCTETPATH3_SEL	R/W	011	These bits are used by the cross-bar switch to map any lane to any other lane. The 3 bit term tells the mapper block what lane this particular lane is supposed to be treated as. 000 = treat as lane0 001 = treat as lane1 010 = treat as lane2 011 = treat as lane3 100 = treat as lane4 101 = treat as lane5 110 = treat as lane6 111 = treat as lane7

## 9.5.58 JESD Crossbar Configuration 2 Register (address = 0x60) [reset = 0x4567]

# Figure 110. JESD\_CROSSBAR2 Field DBits to Determine What Version of Build for the chip.escriptions

15	14	13	12	11	10	9	8
0	0	0	0	0	0	0	x
R/W							
7	6	5	4	3	2	1	0
0	1	1	0	0	0	0	1
R/W							

LEGEND: R/W = Read/Write; R = Read only; -n = value after reset

Table 105. JESD_CROSSBAR2 Field Descriptions
--

Bit	Field	Туре	Reset	Description		
15	Reserved	R/W	0	Reserved		
14:12	OCTETPATH4_SEL	R/W	100	These bits are used by the cross-bar switch to map any lane to any other lane. The 3 bit term tells the mapper block what lane this particular lane is supposed to be treated as. 000 = treat as lane0 001 = treat as lane1 010 = treat as lane2 011 = treat as lane3 100 = treat as lane4 101 = treat as lane5 110 = treat as lane6 111 = treat as lane7		
11	Reserved	R/W	0	Reserved		
10:8	OCTETPATH5_SEL	R/W	101	These bits are used by the cross-bar switch to map any lane any other lane. The 3 bit term tells the mapper block what la this particular lane is supposed to be treated as. 000 = treat as lane0 001 = treat as lane1 010 = treat as lane2 011 = treat as lane2 011 = treat as lane3 100 = treat as lane4 101 = treat as lane5 110 = treat as lane6 111 = treat as lane7		
7	Reserved	R/W	0	Reserved		
6:4	OCTETPATH6_SEL	R/W	110	These bits are used by the cross-bar switch to map any lane to any other lane. The 3 bit term tells the mapper block what lane this particular lane is supposed to be treated as. 000 = treat as lane0 001 = treat as lane1 010 = treat as lane2 011 = treat as lane3 100 = treat as lane4 101 = treat as lane5 110 = treat as lane6 111 = treat as lane7		
3	Reserved	R/W	0	Reserved		
2:0	OCTETPATH7_SEL	R/W	111	These bits are used by the cross-bar switch to map any lane to any other lane. The 3 bit term tells the mapper block what lane this particular lane is supposed to be treated as. 000 = treat as lane0 001 = treat as lane1 010 = treat as lane2 011 = treat as lane3 100 = treat as lane4 101 = treat as lane5 110 = treat as lane6 111 = treat as lane7		

## 9.5.59 JESD Alarms for Lane 0 Register (address = 0x64) [reset = 0x0000]

# Figure 111. JESD Alarms for Lane 0 Register (JBits to determine what version of build for the chip.ESD\_ALM\_L0)

15	14	13	12	11	10	9	8
0	0	0	0	0	0	0	х
W0C	W0C	WOC	W0C	W0C	W0C	W0C	W0C
7	6	5	4	3	2	1	0
0	1	1	0	0	1	0	0
W0C							

LEGEND: R/W = Read/Write; R = Read only; W0C = Write 0 to clear bit; -n = value after reset; -n = value after reset

## Table 106. JESD\_ALM\_L0 Field Descriptions

Bit	Field	Туре	Reset	Description
15:8	ALM_LANE0_ERR	W0C	0x00	Lane0 errors: bit 15 = multiframe alignment error bit 14 = frame alignment error bit 13 = link configuration error bit 12 = elastic buffer overflow (bad RBD value) bit 11 = elastic buffer match error. The first non-/K/ doesn't match "match_ctrl" and "match_data" programmed values. bit 10 = code synchronization error bit 9 = 8b/10b not-in-table code error bit 8 = 8b/10b disparity error
7:4	Reserved	W0C	0x0	Reserved
3:0	ALM_FIFO0_FLAGS	WOC	0x0	Lane0 FIFO errors: bit 3 = write_error : High if write request and FIFO is full (NOTE: only released when JESD block is initialize with mem_init_state) bit 2 = write_full : FIFO is FULL bit 1 = read_error : High if read request with empty FIFO (NOTE: only released when JESD block is initialize with mem_init_state) bit 0 = read_empty : FIFO is empty

## 9.5.60 JESD Alarms for Lane 1 Register (address = 0x65 01100101) [reset = 0x0000]

# Figure 112. JESD Alarms for Lane 1 Register (JESD\_ALM\_L1)

15	14	13	12	11	10	9	8
0	0	0	0	0	0	0	x
W0C	WOC	W0C	W0C	WOC	W0C	W0C	W0C
7	6	5	4	3	2	1	0
0	1	1	0	0	1	0	1
WOC	W0C	WOC	WOC	W0C	W0C	W0C	WOC

LEGEND: R/W = Read/Write; R = Read only; W0C = Write 0 to clear bit; -n = value after reset; -n = value after reset

#### Table 107. JESD\_ALM\_L1 Field Descriptions

Bit	Field	Туре	Reset	Description
15:8	ALM_LANE1_ERR	WOC	0x00	Lane1 errors: bit 15 = multiframe alignment error bit 14 = frame alignment error bit 13 = link configuration error bit 12 = elastic buffer overflow (bad RBD value) bit 11 = elastic buffer match error. The first non-/K/ doesn't match "match_ctrl" and "match_data" programmed values. bit 10 = code synchronization error bit 9 = 8b/10b not-in-table code error bit 8 = 8b/10b disparity error
7:4	Reserved	W0C	0x0	Reserved
3:0	ALM_FIFO1_FLAGS	WOC	0x0	Lane1 FIFO errors: bit 3 = write_error : High if write request and FIFO is full (NOTE: only released when JESD block is initialize with mem_init_state) bit 2 = write_full : FIFO is FULL bit 1 = read_error : High if read request with empty FIFO (NOTE: only released when JESD block is initialize with mem_init_state) bit 0 = read_empty : FIFO is empty



### 9.5.61 JESD Alarms for Lane 2 Register (address = 0x66) [reset = 0x0000]

## Figure 113. JESD Alarms for Lane 2 Register (JESD\_ALM\_L2)

15	14	13	12	11	10	9	8
0	0	0	0	0	0	0	x
W0C	WOC						
7	6	5	4	3	2	1	0
0	1	1	0	0	1	1	0
WOC	W0C	W0C	W0C	W0C	W0C	W0C	WOC

LEGEND: R/W = Read/Write; R = Read only; W0C = Write 0 to clear bit; -n = value after reset; -n = value after reset

#### Table 108. JESD\_ALM\_L2 Field Descriptions

Bit	Field	Туре	Reset	Description
15:8	ALM_LANE2_ERR	WOC	0x00	Lane2 errors: bit 15 = multiframe alignment error bit 14 = frame alignment error bit 13 = link configuration error bit 12 = elastic buffer overflow (bad RBD value) bit 11 = elastic buffer match error. The first non-/K/ doesn't match "match_ctrl" and "match_data" programmed values. bit 10 = code synchronization error bit 9 = 8b/10b not-in-table code error bit 8 = 8b/10b disparity error
7:4	Reserved	W0C	0x0	Reserved
3:0	ALM_FIFO2_FLAGS	WOC	0x0	Lane2 FIFO errors: bit 3 = write_error : High if write request and FIFO is full (NOTE: only released when JESD block is initialize with mem_init_state) bit 2 = write_full : FIFO is FULL bit 1 = read_error : High if read request with empty FIFO (NOTE: only released when JESD block is initialize with mem_init_state) bit 0 = read_empty : FIFO is empty

TEXAS INSTRUMENTS

www.ti.com

## 9.5.62 JESD Alarms for Lane 3 Register (address = 0x67) [reset = 0x0000]

## Figure 114. JESD Alarms for Lane 3 Register (JESD\_ALM\_L3)

15	14	13	12	11	10	9	8
0	0	0	0	0	0	0	x
W0C	WOC						
7	6	5	4	3	2	1	0
0	1	1	0	0	1	1	1
WOC	W0C						

LEGEND: R/W = Read/Write; R = Read only; W0C = Write 0 to clear bit; -n = value after reset; -n = value after reset

#### Table 109. JESD\_ALM\_L3 Field Descriptions

Bit	Field	Туре	Reset	Description
15:8	ALM_LANE3_ERR	WOC	0x00	Lane3 errors: bit 15 = multiframe alignment error bit 14 = frame alignment error bit 13 = link configuration error bit 12 = elastic buffer overflow (bad RBD value) bit 11 = elastic buffer match error. The first non-/K/ doesn't match "match_ctrl" and "match_data" programmed values. bit 10 = code synchronization error bit 9 = 8b/10b not-in-table code error bit 8 = 8b/10b disparity error
7:4	Reserved	WOC	0x0	Reserved
3:0	ALM_FIFO3_FLAGS	WOC	0x0	Lane3 FIFO errors: bit 3 = write_error : High if write request and FIFO is full (NOTE: only released when JESD block is initialize with mem_init_state) bit 2 = write_full : FIFO is FULL bit 1 = read_error : High if read request with empty FIFO (NOTE: only released when JESD block is initialize with mem_init_state) bit 0 = read_empty : FIFO is empty



### 9.5.63 JESD Alarms for Lane 4 Register (address = 0x68) [reset = 0x0000]

## Figure 115. JESD Alarms for Lane 4 Register (JESD\_ALM\_L4)

15	14	13	12	11	10	9	8
0	0	0	0	0	0	0	x
WOC	WOC	W0C	W0C	WOC	W0C	W0C	WOC
7	6	5	4	3	2	1	0
0	1	1	0	1	0	0	0
WOC	W0C	W0C	W0C	W0C	W0C	W0C	WOC

LEGEND: R/W = Read/Write; R = Read only; W0C = Write 0 to clear bit; -n = value after reset; -n = value after reset

#### Table 110. JESD\_ALM\_L4 Field Descriptions

Bit	Field	Туре	Reset	Description
15:8	ALM_LANE4_ERR	WOC	0x00	Lane4 errors: bit 15 = multiframe alignment error bit 14 = frame alignment error bit 13 = link configuration error bit 12 = elastic buffer overflow (bad RBD value) bit 11 = elastic buffer match error. The first non-/K/ doesn't match "match_ctrl" and "match_data" programmed values. bit 10 = code synchronization error bit 9 = 8b/10b not-in-table code error bit 8 = 8b/10b disparity error
7:4	Reserved	W0C	0x0	Reserved
3:0	ALM_FIFO4_FLAGS	WOC	0x0	Lane4 FIFO errors: bit 3 = write_error : High if write request and FIFO is full (NOTE: only released when JESD block is initialize with mem_init_state) bit 2 = write_full : FIFO is FULL bit 1 = read_error : High if read request with empty FIFO (NOTE: only released when JESD block is initialize with mem_init_state) bit 0 = read_empty : FIFO is empty

### 9.5.64 JESD Alarms for Lane 5 Register (address = 0x69) [reset = 0x0000]

## Figure 116. 8.4.60 JESD Alarms for Lane 5 Register (address = 0x69) [reset = 0x0000]

15	14	13	12	11	10	9	8
0	0	0	0	0	0	0	x
WOC	WOC	WOC	WOC	W0C	W0C	W0C	WOC
7	6	5	4	3	2	1	0
0	1	1	0	1	0	0	1
WOC	W0C						

LEGEND: R/W = Read/Write; R = Read only; W0C = Write 0 to clear bit; -n = value after reset; -n = value after reset

#### Table 111. JESD\_ALM\_L5 Field Descriptions

Bit	Field	Туре	Reset	Description
15:8	ALM_LANE5_ERR	WOC	0x00	Lane5 errors: bit 15 = multiframe alignment error bit 14 = frame alignment error bit 13 = link configuration error bit 12 = elastic buffer overflow (bad RBD value) bit 11 = elastic buffer match error. The first non-/K/ doesn't match "match_ctrl" and "match_data" programmed values. bit 10 = code synchronization error bit 9 = 8b/10b not-in-table code error bit 8 = 8b/10b disparity error
7:4	Reserved	WOC	0x0	Reserved
3:0	ALM_FIFO5_FLAGS	WOC	0x0	Lane5 FIFO errors: bit 3 = write_error : High if write request and FIFO is full (NOTE: only released when JESD block is initialize with mem_init_state) bit 2 = write_full : FIFO is FULL bit 1 = read_error : High if read request with empty FIFO (NOTE: only released when JESD block is initialize with mem_init_state) bit 0 = read_empty : FIFO is empty



### 9.5.65 JESD Alarms for Lane 6 Register (address = 0x6A [reset = 0x0000]

## Figure 117. JESD Alarms for Lane 6 Register (JESD\_ALM\_L6)

15	14	13	12	11	10	9	8
0	0	0	0	0	0	0	x
WOC	WOC	W0C	W0C	W0C	W0C	W0C	WOC
7	6	5	4	3	2	1	0
0	1	1	0	1	0	1	0
WOC	W0C	W0C	W0C	W0C	W0C	W0C	WOC

LEGEND: R/W = Read/Write; R = Read only; W0C = Write 0 to clear bit; -n = value after reset; -n = value after reset

#### Table 112. JESD\_ALM\_L6 Field Descriptions

Bit	Field	Туре	Reset	Description
15:8	ALM_LANE6_ERR	WOC	0x00	Lane6 errors: bit 15 = multiframe alignment error bit 14 = frame alignment error bit 13 = link configuration error bit 12 = elastic buffer overflow (bad RBD value) bit 11 = elastic buffer match error. The first non-/K/ doesn't match "match_ctrl" and "match_data" programmed values. bit 10 = code synchronization error bit 9 = 8b/10b not-in-table code error bit 8 = 8b/10b disparity error
7:4	Reserved	W0C	0x0	Reserved
3:0	ALM_FIFO6_FLAGS	WOC	0x0	Lane6 FIFO errors: bit 3 = write_error : High if write request and FIFO is full (NOTE: only released when JESD block is initialize with mem_init_state) bit 2 = write_full : FIFO is FULL bit 1 = read_error : High if read request with empty FIFO (NOTE: only released when JESD block is initialize with mem_init_state) bit 0 = read_empty : FIFO is empty

TEXAS INSTRUMENTS

www.ti.com

### 9.5.66 JESD Alarms for Lane 7 Register (address = 0x6B) [reset = 0x0000]

## Figure 118. JESD Alarms for Lane 7 Register (JESD\_ALM\_L7)

15	14	13	12	11	10	9	8
0	0	0	0	0	0	0	x
WOC	WOC	W0C	W0C	W0C	W0C	W0C	W0C
7	6	5	4	3	2	1	0
0	1	1	0	1	0	1	1
W0C	W0C	W0C	WOC	W0C	W0C	W0C	WOC

LEGEND: R/W = Read/Write; R = Read only; W0C = Write 0 to clear bit; -n = value after reset; -n = value after reset

#### Table 113. JESD Alarms for Lane 7 Register (JESD\_ALM\_L7)

Bit	Field	Туре	Reset	Description
15:8	ALM_LANE7_ERR	WOC	0x00	Lane7 errors: bit 15 = multiframe alignment error bit 14 = frame alignment error bit 13 = link configuration error bit 12 = elastic buffer overflow (bad RBD value) bit 11 = elastic buffer match error. The first non-/K/ doesn't match "match_ctrl" and "match_data" programmed values. bit 10 = code synchronization error bit 9 = 8b/10b not-in-table code error bit 8 = 8b/10b disparity error
7:4	Reserved	WOC	0x0	Reserved
3:0	ALM_FIFO7_FLAGS	WOC	0x0	Lane7 FIFO errors: bit 3 = write_error : High if write request and FIFO is full (NOTE: only released when JESD block is initialize with mem_init_state) bit 2 = write_full : FIFO is FULL bit 1 = read_error : High if read request with empty FIFO (NOTE: only released when JESD block is initialize with mem_init_state) bit 0 = read_empty : FIFO is empty

## 9.5.67 SYSREF and PAP Alarms Register (address = 0x6C) [reset = 0x0000]

## Figure 119. SYSREF and PAP Alarms Register (ALM\_SYSREF\_PAP)

15	14	13	12	11	10	9	8
0	0	0	0	0	0	0	x
W0C							
7	6	5	4	3	2	1	0
0	1	1	0	1	1	0	0
WOC	W0C						

LEGEND: R/W = Read/Write; R = Read only; W0C = Write 0 to clear bit; -n = value after reset; -n = value after reset

#### Table 114. ALM\_SYSREF\_PAP Field Descriptions

		—		•
Bit	Field	Туре	Reset	Description
15:13	Reserved	W0C	0	Reserved
12	ALM_SYSREF_ERR	W0C		Alarm caused when the sysref is placed at an incorrect location
11	ALM_FROM_SHORTTEST	W0C		This is the alarm from JESD during the SHORT TEST checking.
10:7	ALM_PAP	WOC	0x0	The alarms from the PAP blocks indicated which PAP was triggered. bit0 = PAPA bit1 = PAPB bit2 = PAPC bit3 = PAPD
6:2	Reserved	W0C	0x0	Reserved
1	ALM_DIV192_ZERO	WOC	0	This is asserted if the clkdiv192 in the CDRV_SER shift register is all zeros.
0	Not Used	W0C	0	Not Used

## 9.5.68 Clock Divider Alarms 1 Register (address = 0x6D) [reset = 0x0000]

## Figure 120. Clock Divider Alarms 1 Register (ALM\_CLKDIV1)

15	14	13	12	11	10	9	8
0	0	0	0	0	0	0	x
W0C							
7	6	5	4	3	2	1	0
0	1	1	0	1	1	0	1
WOC	W0C						

LEGEND: R/W = Read/Write; R = Read only; W0C = Write 0 to clear bit; -n = value after reset; -n = value after reset

#### Table 115. ALM\_CLKDIV1 Field Descriptions

Bit	Field	Туре	Reset	Description
15	ALM_DIV8_ZERO	W0C	0	Asserted if the clkdiv8 in the CDRV_SER shift register is all zeros.
14	ALM_DIV12_ZERO	W0C	0	Asserted if the clkdiv12 in the CDRV_SER shift register is all zeros.
13	ALM_DIV16_ZERO	W0C	0	Asserted if the clkdiv16 in the CDRV_SER shift register is all zeros.
12	ALM_DIV24_ZERO	W0C	0	Asserted if the clkdiv24 in the CDRV_SER shift register is all zeros. (Connected to the div18 port)
11	ALM_DIV20_ZERO	W0C	0	Asserted if the clkdiv20 in the CDRV_SER shift register is all zeros.
10	ALM_DIV32_ZERO	W0C	0	Asserted if the clkdiv32 in the CDRV_SER shift register is all zeros.
9	ALM_DIV36_ZERO	W0C	0	Asserted if the clkdiv36 in the CDRV_SER shift register is all zeros.
8	ALM_DIV40_ZERO	W0C	0	Asserted if the clkdiv40 in the CDRV_SER shift register is all zeros.
7	ALM_DIV48_ZERO	W0C	0	Asserted if the clkdiv48 in the CDRV_SER shift register is all zeros.
6	ALM_DIV64_ZERO	W0C	0	Asserted if the clkdiv64 in the CDRV_SER shift register is all zeros.
5	ALM_DIV72_ZERO	W0C	0	Asserted if the clkdiv72 in the CDRV_SER shift register is all zeros.
4	ALM_DIV80_ZERO	W0C	0	Asserted if the clkdiv80 in the CDRV_SER shift register is all zeros.
3	ALM_DIV96_ZERO	W0C	0	Asserted if the clkdiv96 in the CDRV_SER shift register is all zeros.
2	ALM_DIV128_ZERO	W0C	0	Asserted if the clkdiv128 in the CDRV_SER shift register is all zeros.
1	ALM_DIV144_ZERO	W0C	0	Asserted if the clkdiv144 in the CDRV_SER shift register is all zeros.
0	ALM_DIV160_ZERO	W0C	0	Asserted if the clkdiv160 in the CDRV_SER shift register is all zeros.

## 9.5.69 Clock Configuration Register (address = 0x0A) [reset = 0xF000]

## Figure 121. Clock Configuration Register (CLK\_CONFIG)

15	14	13	12	11	10	9	8
0	0	0	0	0	0	0	x
R/W							
7	6	5	4	3	2	1	0
0	0	0	0	1	0	1	0
R/W							

LEGEND: R/W = Read/Write; R = Read only; -n = value after reset

#### Table 116. CLK\_CONFIG Field Descriptions

Bit	Field	Туре	Reset	Description
15	RCLK_SYNC_ENA	RW	1	When asserted the sysref is used to sync the clock divider in the centralclkdiv. This should be disabled after initial syncing.
14	FRCLK_DIV_ENA	RW	1	When asserted the full rate clock divider that provides the DIV4 phases to the DACs is enabled
13	DACA_FRCLK_ENA	RW	1	When asserted the full rate clock to the DACA block is enabled
12	DACB_FRCLK_ENA	RW	1	When asserted the full rate clock to the DACB block is enabled
11	DACA_DUMDATA	RW	0	Enables distortion enhancement for DACA when set high
10	DACB_DUMDATA	RW	0	Enables distortion enhancement for DACB when set high
9:2	Reserved	RW	0x000	Reserved
1	QRCLOCK_DACA_ENA	RW	1	Turns on the quarter rate clock for DACA when '1'
0	QRCLOCK_DACB_ENA	RW	1	Turns on the quarter rate clock for DACB when '1'

#### 9.5.70 Sleep Configuration Register (address = 0x0B) [reset = 0x0022]

## Figure 122. Clock Configuration Register (SLEEP\_CONFIG)

15	14	13	12	11	10	9	8
0	0	0	0	0	0	0	x
R/W							
7	6	5	4	3	2	1	0
0	0	0	0	1	0	1	1
R/W							

LEGEND: R/W = Read/Write; R = Read only; -n = value after reset

#### Table 117. SLEEP\_CONFIG Field Descriptions

Bit	Field	Туре	Reset	Description
15:9	Reserved	RW	0000000	Reserved
8	VBGR_SLEEP	RW	0	Turns off the 'bandgap-over-R' bias
7	Reserved	RW	0	Reserved
6	TSENSE_SLEEP	RW	0	Turns off the temperature sensor
5	PLL_SLEEP	RW	1	Puts the PLL into sleep mode (FUSE Controlled)
4	CLKRECV_SLEEP	RW	0	When asserted the clock input receiver gets put into sleep mode. This also affects the FIFO_OSTR receiver as well.
3	DACA_SLEEP	RW	0	Puts the DACA into sleep mode
2	DACB_SLEEP	RW	0	Puts the DACB into sleep mode
1	CLK_TX_SLEEP	RW	1	When asserted the PLL TX clock output is in low power mode.
0	Reserved	RW	0	Reserved

## 9.5.71 Divided Output Clock Configuration Register (address = 0x0C) [reset = 0x8000]

## Figure 123. Divided Output Clock Configuration Register (CLK\_OUT)

15	14	13	12	11	10	9	8
0	0	0	0	0	0	0	x
R/W							
7	6	5	4	3	2	1	0
0	0	0	0	1	1	0	0
R/W							

LEGEND: R/W = Read/Write; R = Read only; -n = value after reset

## Table 118. CLK\_OUT Field Descriptions

Bit	Field	Туре	Reset	Description
15	CLK_TX_IDLE	R/W	1	When high puts the CLK_TX circuitry in idle mode during which the CLKTX+ and CLKTX- output pins are driven to the proper common-mode levels in order to charge the external AC coupling caps. When low allows the divided clock to be driven onto the CLKTX+ and CLKTX- output pins.
14:13	CLK_TX_DIVSELECT	R/W	01 Selects either div2, div3 or div 4 output. 00 = divided by 3 01 = divided by 4 10 = divided by 2 11 = not valid	
12	Reserved	R/W	0	Reserved
11:8	CLK_TX_SWING	R/W	0x0	Sets desired swing on CLKTX+ and CLKTX- outputs in mVpp- diff 0x0 125 0x1 232 0x2 337 0x3 440 0x4 540 0x5 639 0x6 736 0x7 831 0x8 924 0x9 1012 0xA 1097 0xB 1178 0xC 1255 0xD 1329 0xE 1398 0xF 1462
7:3	Reserved	R/W	00000	Reserved
2	CLK_TX_FLIP	R/W	0	Flips the polarity of CLKTX
1	TX_SYNC_ENA	R/W	1	Syncs the CLKTX with SYSREF when asserted
0	EXTREF_ENA	R/W	0	Allows the chip to use an external refernce(1) or the internal reference(0)

## 9.5.72 DAC Fullscale Current Register (address = 0x0D) [reset = 0xF000]

## Figure 124. DAC Fullscale Current Register (DACFS)

15	14	13	12	11	10	9	8
0	0	0	0	0	0	0	x
R/W							
7	6	5	4	3	2	1	0
0	0	0	0	1	1	0	1
R/W							

LEGEND: R/W = Read/Write; R = Read only; -n = value after reset

#### Table 119. DACFS Field Descriptions

Bit	Field	Туре	Reset	Description
15:12	DACFS	R/W	0xF	Scales the output current is 16 equal steps from 10-40mA (10mA + 2mA*DACFS)
10:0	Reserved	R/W	0x000	Reserved

#### 9.5.73 Internal SYSREF Generator Register (address = 0x10) [reset = 0x0000]

## Figure 125. Internal SYSREF Register (LCMGEN)

15	14	13	12	11	10	9	8
0	0	0	0	0	0	0	x
R/W							
7	6	5	4	3	2	1	0
0	0	0	0	1	1	0	1
R/W							

LEGEND: R/W = Read/Write; R = Read only; -n = value after reset

#### **Table 120. LCMGEN Field Descriptions**

Bit	Field	Туре	Reset	Description
15:4	Reserved	R/W	0x00	Reserved
3	LCMGEN_ENA	R/W	0	Enables the LCM custom logic
2	LCMGEN_RESET	R/W	0	Reset the LCM custom logic
1	LCMGEN_SPI_SYSREF_ENA	R/W	0	TBD
0	LCM_SYSREF_OUTSEL	R/W	0	Chooses between internal and external SYSREF

## 9.5.74 Counter for Internal SYSREF Generator Register (address = 0x11) [reset = 0x0000]

## Figure 126. Counter for Internal SYSREF Generator Register (LCMGEN\_DIV)

15	14	13	12	11	10	9	8
0	0	0	0	0	0	0	х
R/W							
7	6	5	4	3	2	1	0
0	0	0	0	1	1	0	1
R/W							

LEGEND: R/W = Read/Write; R = Read only; -n = value after reset

### Table 121. LCMGEN\_DIV Field Descriptions

Bit	Field	Туре	Reset	Description
15:0	LCMGEN_DIV	R/W	0x00	Counter setting for the LCMGEN block

## 9.5.75 SPI SYSREF for Internal SYSREF Generator Register (address = 0x12) [reset = 0x0000]

## Figure 127. SPI SYSREF for Internal SYSREF Generator Register (LCMGEN\_SPISYSREF)

15	14	13	12	11	10	9	8
0	0	0	0	0	0	0	x
R/W							
7	6	5	4	3	2	1	0
0	0	0	0	1	1	0	1
R/W							

LEGEND: R/W = Read/Write; R = Read only; -n = value after reset

#### Table 122. LCMGEN\_SPISYSREF Field Descriptions

Bit	Field	Туре	Reset	Description
15:1	Reserved	R/W	0x00	Reserved
0	LCMGEN_SPI_SYSREF	R/W	0	SPI SYSREF for the LCMGEN block

## 9.5.76 Digital Test Signals Register (address = 0x1B) [reset = 0x0000]

## Figure 128. Digital Test Signals Register (DTEST)

15	14	13	12	11	10	9	8
0	0	0	0	0	0	0	х
R/W							
7	6	5	4	3	2	1	0
0	0	0	1	1	0	1	1
R/W							

LEGEND: R/W = Read/Write; R = Read only; -n = value after reset

## Table 123. DTEST Field Descriptions

Bit	Field	Туре	Reset	Description
15	Reserved	R/W	0	Reserved
14:12	DTEST_LANE	R/W	000	Selects the lane to check for the signals selected by field DTEST
11:8	DTEST	R/W	0x0	Allows digital test signals to come out the ALARM pin. 0000 : Test disabled; normal ALARM pin function 0001 : SERDES lanes 0 – 3 PLL clock/80 0010 : SERDES lanes 4 – 7 PLL clock/80 0011 : TESTFAIL (lane selected by field DTEST_LANE) 0100 : SYNC (lane selected by field DTEST_LANE) 0101 : OCIP (lane selected by field DTEST_LANE) 0110 : EQUNDER (lane selected by field DTEST_LANE) 0111 : EQOVER (lane selected by field DTEST_LANE) 0111 : EQOVER (lane selected by field DTEST_LANE) 1000 – 1111 : not used
7:0	Reserved	R/W	0x00	Reserved

#### 9.5.77 Sleep Pin Control Register (address = 0x23) [reset = 0xFFFF]

These fields control the routing of the SLEEP signal to different blocks. Assertion means that the SLEEP signal will be sent to the block. These bits do not override the SPI bits; just the SLEEP signal from the PAD.

#### Figure 129. Sleep Pin Control Register (SLEEP\_CNTL)

15	14	13	12	11	10	9	8
0	0	0	0	0	0	0	x
R/W							
7	6	5	4	3	2	1	0
0	0	1	0	0	0	1	1
R/W							

LEGEND: R/W = Read/Write; R = Read only; -n = value after reset

#### Table 124. SLEEP\_CNTL Field Descriptions

			_	•
Bit	Field	Туре	Reset	Description
15:10	Reserved	R/W	11111	Reserved
9	CLKOUT_SLEEP	R/W	1	Allows the output clock to sleep
8	BG_SLEEP	R/W	1	Allows the band gap to sleep
7	TEMP_SLEEP	R/W	1	Allows the temp sensor to sleep
6	PLL_CP_SLEEP	R/W	1	Allows the PLL charge pump to sleep
5	PLL_SLEEP	R/W	1	Allows the PLL to sleep
4	CLK_RECV_SLEEP	R/W	1	Allows the clock receiver to sleep
3:2	Reserved	R/W	11	Reserved
1	DACB_SLEEP	R/W	1	Allows DACB to sleep
0	DACA_SLEEP	R/W	1	Allows DACA to sleep

## 9.5.78 SYSREF Capture Circuit Control Register (address = 0x24) [reset = 0x1000]

## Figure 130. SYSREF Capture Circuit Control Register (SYSR\_CAPTURE)

15	14	13	12	11	10	9	8
0	0	0	0	0	0	0	x
R/W							
7	6	5	4	3	2	1	0
0	1	0	0	0	1	0	0
R/W							

LEGEND: R/W = Read/Write; R = Read only; -n = value after reset

#### Table 125. SYSR\_CAPTURE Field Descriptions

Bit	Field	Туре	Reset	Description
15:14	SYSR_PHASE_WDW	R/W	00	sysref phase alignment tolerance window Centers sysref capture window as follows: $00 = Centered \text{ on phase } \varphi 12 \text{ (**DEFAULT**)}$ $01 = Centered \text{ on phase } \varphi 23$ $10 = Centered \text{ on phase } \varphi 34$ $11 = Centered \text{ on phase } \varphi 41$
13:12	SYSR_ALIGN_DLY	R/W	01	<ul> <li>sysref alignment offset delay Optional alignment offset that allows system designer to work around hardware (e.g. PCB) alignment errors by letting him specify that the sysref pulse should be treated as occurring one device clock earlier or later than its observed position. Legal settings are as follows:</li> <li>00 = Offset by -1 device clock cycles. Treat sysref as if it were captured 1 cycle earlier.</li> <li>01 = No offset (**DEFAULT**)</li> <li>10 = Offset by +1 device clock cycles. Treat sysref as if it were captured 1 cycle later.</li> <li>11 = Reserved</li> </ul>
11	SYSR_STATUS_ENA	R/W	0	Enable alignment status monitoring Enable logic that generates sysref alignment status information and accumulates statistics that can be read by the user. 0 = Disable sysref alignment status outputs (**DEFAULT**). Used during normal operation. 1 = Enable sysref alignment status outputs. Used when characterizing sysref capture timing.
10:2	Reserved	R/W	0x000	Reserved
1	SYSR_ALIGN_SYNC	R/W	0	Write a '1' to this bit to clear accumulated sysref align statistics
0	SYSR_BYPS_ALIGN	R/W	0	Bypass sysref alignment logic. Bypass the 4x oversampled sysref alignment logic and instead capture the sysref signal using the legacy implementation of a flip-flop clocked directly by the rising edge of the device clock. 0 = Capture sysref using full-featured alignment circuit (**DEFAULT**) 1 = Bypass sysref alignment logic NOTE: When mem_sysref_bypass_align is enabled, the other sysref alignment controls have no effect.

## 9.5.79 Clock Input and PLL Configuration Register (address = 0x31) [reset = 0x0200]

## Figure 131. Clock Input and PLL Configuration Register (CLK\_PLL\_CFG)

15	14	13	12	11	10	9	8
0	0	0	0	0	0	0	x
R/W							
7	6	5	4	3	2	1	0
0	0	1	1	0	0	0	1
R/W							

LEGEND: R/W = Read/Write; R = Read only; -n = value after reset

## Table 126. Clock Input and PLL Configuration Register (CLK\_PLL\_CFG)

Bit	Field	Туре	Reset	Description
15:14	Reserved	R/W	00	Reserved
13	SEL_EXTCLK_DIFFSE	R/W	0	Selects the external differential or single ended clock for DACCLK. 0 = differential 1 = single ended
12	PLL_RESET	R/W	0	When set the M divider; N divider and PFD are held reset
11	PLL_NDIVSYNC_ENA	R/W	0	When asserted; the SYSREF input is used to sync the N dividers of the PLL.
10	PLL_ENA	R/W	0	Enables the PLL output as the DAC clock when set; the clock provided at the DACCLKP/N is used as the PLL reference clock. When cleared; the PLL is bypassed and the clock provided at the DACCLKP/N pins is used as the DAC clock
9	PLL_CP_SLEEP	R/W	1	Must be set to '0' for proper PLL operation. 1 = Charge pump is put to sleep and can be driven by external source through the ATEST pins.
8	Reserved	R/W	0	Reserved
7:3	PLL_N_M1	R/W	00000	Reference clock divider; divide by is N+1
2:0	LOCKDET_ADJ	R/W	000	Adjusts the lock detector sensitivity. Upper bit isn't used: x00 - highest sensitivity x11 - lowest sensitivity

## 9.5.80 PLL Configuration 1 Register (address = 0x32) [reset = 0x0308]

## Figure 132. PLL Configuration 1 Register (PLL\_CONFIG1)

15	14	13	12	11	10	9	8
0	0	0	0	0	0	0	x
R/W							
7	6	5	4	3	2	1	0
0	0	1	1	0	0	1	0
R/W							

LEGEND: R/W = Read/Write; R = Read only; -n = value after reset

#### Table 127. CONFIG1 Field Descriptions

Bit	Field	Туре	Reset	Description
15:8	PLL_M_M1	R/W	0x03	VCO feedback divider; divide by is 4(M+1)
7:4	Reserved	R/W	0x0	Reserved
3:0	PLL_VCO_RDAC	R/W	0x8	Controls the VCO amplitude

#### 9.5.81 PLL Configuration 2 Register (address = 0x33) [reset = 0x4018]

#### Figure 133. PLL Configuration 2 Register (PLL\_CONFIG2)

15	14	13	12	11	10	9	8
0	0	0	0	0	0	0	x
R/W							
7	6	5	4	3	2	1	0
0	0	1	1	0	0	1	1
R/W							

LEGEND: R/W = Read/Write; R = Read only; -n = value after reset

#### Table 128. PLL\_CONFIG2 Field Descriptions

Bit	Field	Туре	Reset	Description
15	PLL_VCOSEL	R/W	0	Selects between two VCOs 0 = 5.9 GHz VCO(2 turn inductor in upper VCO) 1 = 8.9 GHz VCO (1 turn in the lower VCO)
14:8	PLL_VCO	R/W	1000000	VCO frequency range
7:6	Reserved	R/W	000	Reserved
5:2	PLL_CP_ADJ	R/W	0110	Adjusts the charge pump current; 0 to 1.55 mA in 50 $\mu A$ steps. Setting to 0000 will hold the LPF pin at 0 V
1	Reserved	R/W	0	Reserved
0	Reserved	R/W	0	Reserved. Always write 0

## 9.5.82 LVDS Output Configuration Register (address = 0x34) [reset = 0x0000]

## Figure 134. LVDS Output Configuration Register (LVDS\_CONFIG)

15	14	13	12	11	10	9	8
0	0	0	0	0	0	0	x
R/W							
7	6	5	4	3	2	1	0
0	0	1	1	0	1	0	0
R/W							

LEGEND: R/W = Read/Write; R = Read only; -n = value after reset

#### Table 129. LVDS\_CONFIG Field Descriptions

Bit	Field	Туре	Reset	Description
15	LVDS_LOPWRB	R/W	0	LVDS Output current control LSB; allows output current to be scaled from ~2 mA to ~4 mA
14	LVDS_LOPWRA	R/W	0	LVDS Output current control MSB; allows output current to be scaled from ~2 mA to ~4 mA
13	LVDS_LPSEL	R/W	0	SYNC LVDS output on chip termination control; 100 Ω when cleared; 200 ΩOutput current settings for the combination of bits 15:13110 = 4.00 mA010 = 3.50 mA100 = 3.00 mA000 = 2.50 mA - Default current111 = 4.00 mA011 = 3.33 mA101 = 2.66 mA001 = 2.00 mA
12	LVDS_EFUSE_SEL	R/W	0	Enable LVDS bias bandgap reference voltage to the ATEST multiplexer.
11:10	LVDS_TRIM	R/W	00	Adjusts the LVDS 1.2 V reference. LVDS_TRIM_ENA must be set and LVDS_EFUSE_SEL must be cleared for these bits to have any effect. 10 +70 mV 00 -70 mV 01 default 11 -20 mV.
9	LVDS_TRIM_ENA	R/W	0	When set and LVDS_EFUSE_SEL is cleared; the LVDS_TRIM adjustment is enabled. When cleared; the LVDS_TRIM has no effect.
8	LVDS_SYNC0\_PD	R/W	0	The SYNC0 LVDS output is in power down.
7	Reserved	R/W	0	Reserved
6	LVDS_SYNC0\_CM	R/W	0	$\overline{\text{SYNC0}}$ LVDS output common mode is 1.2 V when cleared; 0.9 V when set.
5:0	Reserved	R/W	0x00	Reserved



### 9.5.83 Fuse Farm clock divider Register (address = 0x35) [reset = 0x0018]

## Figure 135. Fuse Farm clock divider Register (PLL\_FDIV)

15	14	13	12	11	10	9	8
0	0	0	0	0	0	0	x
R/W	R/W	R/W	R/W	R/W	R/W	R/W	R/W
7	6	5	4	3	2	1	0
0	0	1	1	1	0	1	1
R/W	R/W	R/1W	R/W	R/W	R/W	R/W	R/W

LEGEND: R/W = Read/Write; R = Read only; -n = value after rese1t

#### Table 130. PLL\_FDIV Field Descriptions

Bit	Field	Туре	Reset	Description
15:8	Reserved	R/W	0	Reserved
7:0	PLL_FDIV	R/W	0x18	Clock divider for the Fuse farm

## 9.5.84 Serdes Clock Configuration Register (address = 0x3B) [reset = 0x0002]

## Figure 136. Serdes Clock Configuration Register (SRDS\_CLK\_CFG)

15	14	13	12	11	10	9	8
0	0	0	0	0	0	0	x
R/W	R/W	R/W	R/W	R/W	R/W	R/W	R/W
7	6	5	4	3	2	1	0
0	0	1	1	1	0	1	1
R/W	R/W	R/1W	R/W	R/W	R/W	R/W	R/W

LEGEND: R/W = Read/Write; R = Read only; -n = value after rese1t

#### Table 131. SRDS\_CLK\_CFG Field Descriptions

Bit	Field	Туре	Reset	Description
15	SERDES_CLK_SEL	R/W	0	Select either the PLL output of the DACCLK from the pad. 0 = DACCLK pad 1 = PLL output
14:11	SERDES_REFCLK_DIV	R/W	0x0	The divide amount for the serdes REFCLK minus 1
10:2	Reserved	R/W	0x000	Reserved
1:0	SERDES_REFCLK_PREDIV	R/W	10	These bits select the pre-divide on the DACCLK input clock before the DACCLK is used in the dividers used in the SERDES PLL REFCLK and the Fusefarm SYSCLK. 00 = if DACCLK input ≤ 2 GHz; prediv is set to div1 01 = if DACCLK input is ≤ 4 GHz and > 2 GHz, prediv is set to div2 10 = if DACCLK input is ≤ 9 GHz and > 4 GHz, prediv is set to div4 11 = Not valid

### 9.5.85 Serdes PLL Configuration Register (address = 0x3C) [reset = 0x8228]

## Figure 137. Serdes PLL Configuration Register (SRDS\_PLL\_CFG)

15	14	13	12	11	10	9	8
0	0	0	0	0	0	0	x
R/W							
7	6	5	4	3	2	1	0
0	0	1	1	1	1	0	0
R/W							

LEGEND: R/W = Read/Write; R = Read only; -n = value after reset

#### Table 132. SRDS\_PLL\_CFG Field Descriptions

Bit	Field	Туре	Reset	Description
15	ENDIVCLK	R/W	1	Enable divided by 5 output clock
14:3	CLKBYP	R/W	00	Serdes clock bypass
12:11	LB	R/W	00	Serdes PLL loop bandwidth
10	SLEEPPLL	R/W	0	Serdes PLL Sleep
9	VRANGE	R/W	1	Serdes PLL loop filter range
8:1	MPY	R/W	00010100	Serdes reference clock multiplication factor Table 4
0	CORRECT	R/W	0	AND'ed with LANE_ENA so it must be set to 1 for correct behavior



## 9.5.86 Serdes Configuration 1 Register (address = 0x3D) [reset = 0x0x0088]

## Figure 138. Serdes Configuration 1 Register (SRDS\_CFG1)

15	14	13	12	11	10	9	8
0	0	0	0	0	0	0	x
R/W							
7	6	5	4	3	2	1	0
0	0	1	1	1	1	0	1
R/W							

LEGEND: R/W = Read/Write; R = Read only; -n = value after reset

#### Table 133. RDS\_CFG1 Field Descriptions

Bit	Field	Туре	Reset	Description
15	Reserved	R/W	0	Reserved
14:12	TESTPATT	R/W	000	Test pattern
11	BSINRXN	R/W	0	Enable boundary scan - pins
10	BSINRXP	R/W	0	Enable boundary scan + pins
9:8	Reserved	R/W	00	Reserved
7	ENOC	R/W	1	Enable Serdes offset compensation
6	EQHLD	R/W	0	Equalizer hold
5:3	EQ	R/W	001	Serdes equalizer
2:0	CDR	R/W	000	Clock data recovery algorithm settings

TEXAS INSTRUMENTS

www.ti.com

## 9.5.87 Serdes Configuration 2 Register (address = 0x3E) [reset = 0x0x0909]

## Figure 139. Serdes Configuration 2 Register (SRDS\_CFG2)

15	14	13	12	11	10	9	8
0	0	0	0	0	0	0	x
R/W							
7	6	5	4	3	2	1	0
0	0	1	1	1	1	1	0
R/W							

LEGEND: R/W = Read/Write; R = Read only; -n = value after reset

Bit	Field	Туре	Reset	Description
15:13	LOS	R/W	000	Enables loss of signal detection. 000 - Disable detection 100 - Enable detection other - reserved
12:11	ALIGN	R/W	01	Enables external or internal symbol alignment 00 : Disabled 01 : Comma alignment 10: Align jog
10:8	TERM	R/W	001	Valid programming: 001 – AC coupling with common mode = 0.7 V 100 – 0 V common mode. 101 – 0.25 V common mode 111 – DC coupling with common mode of 0.6 V. (NOTE: This is not compatible with JESD)
7	Reserved	R/W	0	Reserved
6:5	RATE	R/W	00	Selects full (00), half (01), quarter (10) or eighth (11) rate operation.
4:2	BUSWIDTH	R/W	010	Selects the parallel interface width (16 or 20 bits). 0 : 20 bits 1: 16 bits
1	SLEEPRX	R/W	0	Powers the receiver down into the sleep (fast power up) state when high.
0	Reserved	R/W	1	Reserved

#### Table 134. SRDS\_CFG2 Field Descriptions



## 9.5.88 Serdes Polarity Control Register (address = 0x3F) [reset = 0x0000]

## Figure 140. Serdes Polarity Control Register (SRDS\_POL)

15	14	13	12	11	10	9	8
0	0	0	0	0	0	0	x
R/W							
7	6	5	4	3	2	1	0
0	0	1	1	1	1	1	1
R/W							

LEGEND: R/W = Read/Write; R = Read only; -n = value after reset

#### Table 135. SRDS\_POL Field Descriptions

Bit	Field	Туре	Reset	Description
15:8	Reserved	R/W	0x00	Reserved
7:0	INVPAIR	R/W	0x00	Allows the PN pairs of the different lanes to be inverted. bit 7 = lane7 bit 6 = lane6 bit 5 = lane5 bit 4 = lane4 bit 3 = lane3 bit 2 = lane2 bit 1 = lane1 bit 0 = lane0

## 9.5.89 JESD204B SYNCB OUTPUT Register (address = 0x76) [reset = 0x0000]

### Figure 141. JESD204B SYNCB OUTPUT Register (SYNCBOUT)

15	14	13	12	11	10	9	8
0	0	0	0	0	0	0	x
R/W	R/W	R/W	R/W	R/W	R/W	R/W	R/W
7	6	5	4	3	2	1	0
0	0	1	1	1	0	1	1
R/W	R/W	R/1W	R/W	R/W	R/W	R/W	R/W

LEGEND: R/W = Read/Write; R = Read only; -n = value after reset

#### **Table 136. SYNCBOUT Field Descriptions**

Bit	Field	Туре	Reset	Description
15:2	Reserved	R/W	0x00	Reserved
1	SYNCBOUT1	R/W	0	If the CMOS SYNC outputs are turned on, this bit will show the status of the JESD SYNCB1 signal
0	SYNCBOUT0	R/W	0	If the CMOS SYNC outputs are turned on, this bit will show the status of the JESD SYNCB0 signal




## **10** Application and Implementation

#### 注

Information in the following applications sections is not part of the TI component specification, and TI does not warrant its accuracy or completeness. TI's customers are responsible for determining suitability of components for their purposes. Customers should validate and test their design implementation to confirm system functionality.

#### **10.1** Application Information

#### 10.1.1 Start-up Sequence








#### **10.2 Typical Application**

The block diagram of a typical DOCSIS downstream network is shown in 🛛 143. The physical layer (PHY) of the cable modem termination system (or CMTS) must support normal downstream operating range from 54 MHz to 1002 MHz as well as extended operating range up to 1794 MHz. The high input bandwidth (up to 3.33 GHz) of DAC38RF82 and DAC38RF89 makes these devices suitable for DOCSIS CMTS. Also the integrated high performance PLL simplifies system clocking by eliminating the need to generate and distribute high frequency sampling clock to the DAC. In the following sections, the performance of DAC38RF82 (and DAC38RF89) used to generate DOCSIS 3.0, Annex A, 6 MHz 256-QAM carriers will be described.



#### 図 143. DOCSIS Downstream Network

#### 10.2.1 Design Requirements


Specification	
54 MHz to 1002 MHz	
1	
6 MHz	
256 QAM	
5.3605 Msym/s	
2.4576 GSPS	
>48 dB	
>70 dBc	
	54 MHz to 1002 MHz 1 6 MHz 256 QAM 5.3605 Msym/s 2.4576 GSPS >48 dB

#### 表 137. DOCSIS CMTS Design Features

#### 10.2.2 Detailed Design Procedure

A sample rate of 4.9152 GHz is selected for the DAC. This will make it possible to meet the out of band (up to 3GHz) spurious requirement of 65 dBc by pushing the DAC images to the 2nd Nyquist zone (2.4576 MHz to 4.9152 GHz). Because the input data rate is 2.4576 GSPS, the DAC interpolation is set to 2. To generate the 4.9152 GHz sampling clock for the DAC, a low frequency 409.6 MHz clock is provided to the DAC reference clock input. A detailed block diagram is shown in 🛛 144





#### 図 144. DOCSIS Downstream Network

#### 10.2.3 Calculating the JESD204B SerDes rate

SerDes rate =  $1.25 \times (M/L) \times Baseband data rate \times Number of bits per sample (16)$ 

M is a JESD204B interface parameter that refers to the number of data streams from FPGA to DAC

L is a JESD204B interface parameter that refers to the number of SerDes lanes used to transmit data

1.25 is a factor due to the 8B10B encoding of the baseband data

Example,

if the baseband data rate = 2457.6 MSPS and L-M-F-S-Hd = 4-1-1-2-1 SerDes rate = 1.25 x (1/4) x 2457.6 x 16 = 12.288 Gbps

(19)

### 10.2.4 Calculating valid JESD204B SYSREF Frequency

Valid SYSREF frequencies depend on the following parameters:

- 1. Sample clock frequency
- 2. JESD204B internal clock divider value (CLKJESD\_DIV). This depends on the DAC JESD204B L-M-F-S mode and interpolation
- 3. Number of octets in a frame (F)
- 4. Number of frames in a multi-frame (K)

Maximum SYSREF frequency = (Sample clock frequency/N),

where N =LCM(CLKJESD\_DIV,4 x K x F). N is the Least common multiple of 4 x K x F and CLKJESD\_DIV.

All valid SYSREF frequencies are integer divisors of the maximum SYSREF frequency.

#### Example:

Given sampling clock frequency = 4.9152 GSPS, interpolation =2, DAC Mode=L-M-F-S=4-1-1-2 and K=20:

CLKJESD\_DIV = 8 (CLKJESD\_DIV)

Maximum SYSREF Frequency = 4915.2 MHz/80 = 61.44 MHz

Valid SYSREF Frequencies = 61.44 MHz/n, where n is any positive integer.



#### 10.2.5 Application Curves

Agilent Spectrum Analyzer - ACP									
ef Value -5.00 dBm	E IFGain:Los	Trig: Fre	req: 591.000 e Run		ff g Hold:>	5/5		03:36: lio Std: I lio Devic	
0 dB/div Ref -5.00 dBm			4 dBm -						
5.0 -84.5 dBc -83.9 dBc	-82.7 dBc -	77.4 dBc		-77.4 d	3c - 4	32.7 dBc	-83.7	dBc	-84.3 dBc
5.0									
5.0				_					
5.0 <del>ماريخ من بالمارخ من المارخ من المارخ من الم</del> ارخ and	unaliation		•	in the second		n an finair	i je vrla il		pan 54 MH
Res BW 100 kHz	dBm/6.00 MHz		BW 10 kH	z				Swee	p 134.7 m
			Lo	wer		pper			
Carrier Power	Filter Offset			dBm	dBc	dBm	Filter		
1 -4.421 dBm / 6.000 MHz	OFF 3.3751			-50.79		-51.13	OFF		
	6.3751			-81.78		-81.81	OFF		
	12.001			-87.16		-87.10	OFF		
	18.001			-88.34		-88.13	OFF		
	24.001	MHz 6.000 MH	lz -84.45	-88.87	-84.31	-88.73	OFF		

#### 図 145. ACPR Performance of 6 MHz Single Carrier at 591 MHz



2 146. ACPR performance of 6 MHz Single Carrier at 998 MHz






図 147. Unequalized MER of 6 MHz Single Carrier at 591 MHz




図 148. Unequalized MER of 6 MHz Single Carrier at 998 MHz



## 11 Power Supply Recommendations

Internally, DAC38RF82 (DAC38RF89) comprises a digital subsystem, an analog subsystem, and a clock subsystem. Ideally, the power supply scheme should be partitioned according to these three relatively independent blocks to minimize interactions between them. Most importantly, sensitive analog and clock circuit power supply must be separated from digital switching noise to reduce direct coupling and mixing of switching spurs. 表 138 shows the power supply rails for DAC38RF82 (DAC38RF89) grouped under their respective domains.

Supply rail	Nominal voltage (V)	Domain
VDDIG1	+1.0	
VDDIO18	+1.8	
VDDR18	+1.8	
VDDS18	+1.8	Digital
VDDT1	+1.0	
VDDE1	+1.0	
VDDL1_1	+1.0	
VEE18N	-1.8	
VDDA1	+1.0	Analog
VDDA18	+1.8	Analog
VDDOUT18	+1.8	
VDDPLL1	+1.0	
VDDAPLL18	+1.8	
VDDAVCO18	+1.8	
VDDCLK1	+1.0	Clock
VDDL2_1	+1.0	
VDDTX1	+1.0	
VDDTX18	+1.8	

表 138. Powe	r Supply	Domains
-------------	----------	---------

An example power supply scheme suitable for most applications of DAC38RF82 (DAC38RF89) is shown in 149. It is recommended to use ferrite beads (FB) to isolate the individual rails from each other.




図 149. Power Supply Scheme for DAC38RF82 (DAC38RF89)



### **11.1 Power Supply Sequencing**

There are no power supply sequencing requirements for all the 1-V and 1.8-V power supplies. For the -1.8 V VEE18 rail, it is recommended that this supply is the last to be enabled. Enabling VEE18 (while other supply voltages are disabled) can cause a small negative voltage to be present at the other rails (that is, VDDA1 and VDDDIG1). This small negative voltage can interfere with the startup of some DC-DC converters or LDO connected to the 1 V and 1.8 V input power rails.

## 12 Layout

#### 12.1 Layout Guidelines

- DAC RF output traces
  - Differential 100  $\Omega$  co-planar wave guide for output traces is recommended.
  - Use short RF traces. Place DAC close to edge of PCB to shorten the length of output and clock traces. This helps to minimize PCB loss and coupling
  - Stitch the ground plane with ground vias uniformly along the output trace.
  - Avoid width/spacing differences when entering a landing pad (eg. a balun) by tapering or by redefining width/space rules for the traces
- Power supply planes
  - Ensure sufficient lateral spacing between two power planes (about 3x the thickness of the plane is recommended)
  - Insert ground plane between adjacent power planes where possible




図 150. Example Power Plane Routing

- Bypass Capacitors
  - Use bypass capacitors with in-pad vias and place between the pin and the power plane. Avoid sharing
    ground vias or pads of bypass caps used for different power rails
  - Minimize stubs on bypass capacitors to avoid parasitic inductance



## Layout Guidelines (continued)




図 151. Bypass Capacitors Placed on the Power Supply Pin With In-pad Vias

- High speed SerDes traces
  - Route all SerDes traces straight and minimized sharp curves or serpentines. Route for best signal integrity
  - Some skew between SerDes traces can be tolerated. It is recommended to limit skew between traces to 320ps or less
  - Place ground planes between the SerDes traces for improved isolation




図 152. Layout Example of High Speed SerDes Traces



## 12.2 Layout Example




図 153. Layout Example

## 13 デバイスおよびドキュメントのサポート

## 13.1 関連リンク

次の表に、クイック・アクセス・リンクを示します。カテゴリには、技術資料、サポートおよびコミュニティ・リソース、ツールとソフトウェア、およびサンプル注文またはご購入へのクイック・アクセスが含まれます。

製品	プロダクト・フォルダ	ご注文はこちら	技術資料	ツールとソフトウェア	サポートとコミュニティ
DAC38RF82	ここをクリック	ここをクリック	ここをクリック	ここをクリック	ここをクリック
DAC38RF89	ここをクリック	ここをクリック	ここをクリック	ここをクリック	ここをクリック

#### 表 139. 関連リンク

## 13.2 ドキュメントの更新通知を受け取る方法

ドキュメントの更新についての通知を受け取るには、ti.comのデバイス製品フォルダを開いてください。右上の「アラートを受け取る」をクリックして登録すると、変更されたすべての製品情報に関するダイジェストを毎週受け取れます。変更の詳細については、修正されたドキュメントに含まれている改訂履歴をご覧ください。

## 13.3 サポート・リソース

TI E2E<sup>™</sup> support forums are an engineer's go-to source for fast, verified answers and design help — straight from the experts. Search existing answers or ask your own question to get the quick design help you need.

Linked content is provided "AS IS" by the respective contributors. They do not constitute TI specifications and do not necessarily reflect TI's views; see TI's Terms of Use.

## 13.4 商標

E2E is a trademark of Texas Instruments.

All other trademarks are the property of their respective owners.

## 13.5 静電気放電に関する注意事項



これらのデバイスは、限定的なESD(静電破壊)保護機能を内蔵しています。保存時または取り扱い時は、MOSゲートに対する静電破壊を防止するために、リード線同士をショートさせておくか、デバイスを導電フォームに入れる必要があります。

## 13.6 Glossary

SLYZ022 — TI Glossary.

This glossary lists and explains terms, acronyms, and definitions.

## 14 メカニカル、パッケージ、および注文情報

以降のページには、メカニカル、パッケージ、および注文に関する情報が記載されています。この情報は、そのデバイスについて利用可能な最新のデータです。このデータは予告なく変更されることがあり、ドキュメントが改訂される場合もあります。本データシートのブラウザ版を使用されている場合は、画面左側の説明をご覧ください。



## PACKAGING INFORMATION

Orderable Device	Status	Package Type		Pins	-	Eco Plan	Lead finish/	MSL Peak Temp	Op Temp (°C)	Device Marking	Samples
	(1)		Drawing		Qty	(2)	Ball material	(3)		(4/5)	
							(6)				
DAC38RF82IAAV	ACTIVE	FCCSP	AAV	144	168	RoHS & Green	SNAGCU	Level-3-260C-168 HR	-40 to 85	DAC38RF82I	Samples
DAC38RF82IAAVR	ACTIVE	FCCSP	AAV	144	1000	RoHS & Green	SNAGCU	Level-3-260C-168 HR	-40 to 85	DAC38RF82I	Samples
DAC38RF89IAAV	ACTIVE	FCCSP	AAV	144	168	RoHS & Green	SNAGCU	Level-3-260C-168 HR	-40 to 85	DAC38RF89I	Samples
DAC38RF89IAAVR	ACTIVE	FCCSP	AAV	144	1000	RoHS & Green	SNAGCU	Level-3-260C-168 HR	-40 to 85	DAC38RF89I	Samples

<sup>(1)</sup> The marketing status values are defined as follows:

ACTIVE: Product device recommended for new designs.

**LIFEBUY:** TI has announced that the device will be discontinued, and a lifetime-buy period is in effect.

NRND: Not recommended for new designs. Device is in production to support existing customers, but TI does not recommend using this part in a new design.

PREVIEW: Device has been announced but is not in production. Samples may or may not be available.

**OBSOLETE:** TI has discontinued the production of the device.

<sup>(2)</sup> RoHS: TI defines "RoHS" to mean semiconductor products that are compliant with the current EU RoHS requirements for all 10 RoHS substances, including the requirement that RoHS substance do not exceed 0.1% by weight in homogeneous materials. Where designed to be soldered at high temperatures, "RoHS" products are suitable for use in specified lead-free processes. TI may reference these types of products as "Pb-Free".

**RoHS Exempt:** TI defines "RoHS Exempt" to mean products that contain lead but are compliant with EU RoHS pursuant to a specific EU RoHS exemption.

Green: TI defines "Green" to mean the content of Chlorine (CI) and Bromine (Br) based flame retardants meet JS709B low halogen requirements of <=1000ppm threshold. Antimony trioxide based flame retardants must also meet the <=1000ppm threshold requirement.

<sup>(3)</sup> MSL, Peak Temp. - The Moisture Sensitivity Level rating according to the JEDEC industry standard classifications, and peak solder temperature.

<sup>(4)</sup> There may be additional marking, which relates to the logo, the lot trace code information, or the environmental category on the device.

<sup>(5)</sup> Multiple Device Markings will be inside parentheses. Only one Device Marking contained in parentheses and separated by a "~" will appear on a device. If a line is indented then it is a continuation of the previous line and the two combined represent the entire Device Marking for that device.

<sup>(6)</sup> Lead finish/Ball material - Orderable Devices may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead finish/Ball material values may wrap to two lines if the finish value exceeds the maximum column width.

Important Information and Disclaimer: The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and



continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.



Texas

STRUMENTS

## TAPE AND REEL INFORMATION





#### QUADRANT ASSIGNMENTS FOR PIN 1 ORIENTATION IN TAPE



*All dimensions are nominal												
Device	Package Type	Package Drawing		SPQ	Reel Diameter (mm)	Reel Width W1 (mm)	A0 (mm)	B0 (mm)	K0 (mm)	P1 (mm)	W (mm)	Pin1 Quadrant
DAC38RF82IAAVR	FCCSP	AAV	144	1000	330.0	24.4	10.3	10.3	2.5	16.0	24.0	Q1
DAC38RF89IAAVR	FCCSP	AAV	144	1000	330.0	24.4	10.3	10.3	2.5	16.0	24.0	Q1



# PACKAGE MATERIALS INFORMATION

5-Dec-2023



\*All dimensions are nominal

Device	Package Type	Package Drawing	Pins	SPQ	Length (mm)	Width (mm)	Height (mm)
DAC38RF82IAAVR	FCCSP	AAV	144	1000	350.0	350.0	43.0
DAC38RF89IAAVR	FCCSP	AAV	144	1000	350.0	350.0	43.0


## Texas **INSTRUMENTS**

www.ti.com

## TRAY



PACKAGE MATERIALS INFORMATION



Chamfer on Tray corner indicates Pin 1 orientation of packed units.

*	*All dimensions are nominal												
	Device	Package Name	Package Type	Pins	SPQ	Unit array matrix	Max temperature (°C)	L (mm)	W (mm)	K0 (µm)	P1 (mm)	CL (mm)	CW (mm)
	DAC38RF82IAAV	AAV	FCCSP	144	168	8 X 21	150	315	135.9	7620	14.65	11	11.95
ĺ	DAC38RF89IAAV	AAV	FCCSP	144	168	8 X 21	150	315	135.9	7620	14.65	11	11.95

5-Dec-2023


# AAV0144A



# **PACKAGE OUTLINE**

## FCBGA - 1.91 mm max height

BALL GRID ARRAY



#### NOTES:

- 1. All linear dimensions are in millimeters. Any dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.
- 2. This drawing is subject to change without notice.
- 3. Dimension is measured at the maximum solder ball diameter, parallel to primary datum C.
- 4. Primary datum C and seating plane are defined by the spherical crowns of the solder balls.
- 5. The lids are electrically floating (e.g. not tied to GND).




# **AAV0144A**

# **EXAMPLE BOARD LAYOUT**

## FCBGA - 1.91 mm max height

BALL GRID ARRAY



NOTES: (continued)

6. Final dimensions may vary due to manufacturing tolerance considerations and also routing constraints. For more information, see Texas Instruments literature number SPRU811 (www.ti.com/lit/spru811).




# AAV0144A

# **EXAMPLE STENCIL DESIGN**

## FCBGA - 1.91 mm max height

BALL GRID ARRAY



NOTES. (continued)

7. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release.



#### 重要なお知らせと免責事項

TIは、技術データと信頼性データ (データシートを含みます)、設計リソース (リファレンス・デザインを含みます)、アプリケーションや 設計に関する各種アドバイス、Web ツール、安全性情報、その他のリソースを、欠陥が存在する可能性のある「現状のまま」提供してお り、商品性および特定目的に対する適合性の黙示保証、第三者の知的財産権の非侵害保証を含むいかなる保証も、明示的または黙示的に かかわらず拒否します。

これらのリソースは、TI 製品を使用する設計の経験を積んだ開発者への提供を意図したものです。(1) お客様のアプリケーションに適した TI 製品の選定、(2) お客様のアプリケーションの設計、検証、試験、(3) お客様のアプリケーションに該当する各種規格や、その他のあら ゆる安全性、セキュリティ、規制、または他の要件への確実な適合に関する責任を、お客様のみが単独で負うものとします。

上記の各種リソースは、予告なく変更される可能性があります。これらのリソースは、リソースで説明されている TI 製品を使用するアプ リケーションの開発の目的でのみ、TI はその使用をお客様に許諾します。これらのリソースに関して、他の目的で複製することや掲載す ることは禁止されています。TI や第三者の知的財産権のライセンスが付与されている訳ではありません。お客様は、これらのリソースを 自身で使用した結果発生するあらゆる申し立て、損害、費用、損失、責任について、TI およびその代理人を完全に補償するものとし、TI は一切の責任を拒否します。

TIの製品は、TIの販売条件、または ti.com やかかる TI 製品の関連資料などのいずれかを通じて提供する適用可能な条項の下で提供され ています。TI がこれらのリソースを提供することは、適用される TI の保証または他の保証の放棄の拡大や変更を意味するものではありま せん。

お客様がいかなる追加条項または代替条項を提案した場合でも、TIはそれらに異議を唱え、拒否します。

郵送先住所:Texas Instruments, Post Office Box 655303, Dallas, Texas 75265 Copyright © 2023, Texas Instruments Incorporated