

Application Report SLAA454–June 2010

Headset Detection for TLV320AIC33 and TLV320AIC3101/4/5/6 Family

Hui Li and David K. Wilson

Audio Converters

ABSTRACT

A common feature in most of today's electronic devices – including cell phone, PDAs, notebooks, handheld media players, game systems, etc. – is the provision for connecting to external accessories. The devices therefore include dedicated logic circuitry that can detect not only the presence of an accessory, but also its type.

The TLV320AIC33 and TLV320AIC3101/4/5/6 family includes extensive capability to monitor a headphone, microphone (mic), or headset jack, determine if an audio plug has been inserted, and then detect what type of headset is wired to the plug. This application report mainly discusses the headset detection scheme for two different headset output configurations: pseudo-differential (capacitor-less) output, and ac-coupled output. The content of this document applies to the TLV320AIC33 and TLV320AIC3101/4/5/6 family.

Contents

1	Heads	et Plugs/Connection Diagrams	2
	1.1	Part I: Pseudo-Differential (Capacitor-less) Headset Output Configuration	2
	1.2	Part II: AC-Coupled Stereo Headset Output Configuration - Capacitor Interface	7
2	Refere	nces	12
Append	dix A	Example for a Pseudo-Differential (Capacitor-less) Output Configuration	13
Append	dix B	Example for an AC-Coupled (Capacitor) Output Configuration	14
Append	dix C	Flowchart for Pseudo-Differential (Capacitor-less) Output Configuration	15
Append	dix D	Flowchart for AC-Coupled (Capacitor) Output Configuration	18

List of Figures


1	Different Configurations of 4-Conductor Headset Plug	2
2	Connection Diagrams for Various Headsets	2
3	Device with a Pseudo-Differential (Capacitor-less) Headset Output Connection	3
4	Circuit Diagram of Detection Scheme for Capacitor-less Interface	3
5	Detection Block for Pseudo-Differential (Capacitor-less) Interface	4
6	Device With an AC-Coupled Stereo Headset Output Connection	7
7	Circuit Diagram of Detection Scheme for Capacitor Interface	7
8	Detection Block for AC-Coupled (Capacitor) Interface	8
9	False Detection Due to Overdrawn Current Into Internal Mic	11
10	Flowchart for Insertion Detection and Headset-Type Detection	15
11	Flowchart for Hook Button Press Detection and Headset Removal Detection (With Mic)	16
12	Flowchart for Headset Removal Detection (Without Mic)	17
13	Flowchart for Insertion Detection and Headset-Type Detection	18
14	Flowchart for Hook Button Press Detection and Headset Removal Detection (With Mic)	19
15	Flowchart for Headset Removal Detection (Without Mic)	19
16	Pulse Scheme	20



Headset Plugs/Connection Diagrams

www.ti.com

1 Headset Plugs/Connection Diagrams








Figure 2. Connection Diagrams for Various Headsets

1.1 Part I: Pseudo-Differential (Capacitor-less) Headset Output Configuration

Figure 3 shows one configuration of the device that enables detection and determination of headset type when a pseudo-differential (capacitor-less) stereo headphone output connection is used. Note that for best results, it is recommended to select a MICBIAS value as high as possible, and to program the output driver common-mode level at a 1.35-V or 1.5-V level.






Figure 3. Device with a Pseudo-Differential (Capacitor-less) Headset Output Connection

Figure 4 demonstrates the internal circuitry that implements the detection logic. The detection block circled in red consists of three main components – comparator A, B, and C.




Figure 4. Circuit Diagram of Detection Scheme for Capacitor-less Interface



Headset Plugs/Connection Diagrams

1.1.1 Detection Block, Capacitor-less Interface




Figure 5. Detection Block for Pseudo-Differential (Capacitor-less) Interface



Comparator C is used to detect headset insertion and removal. Headset insertion and removal detection is always active inside device.

MICDET < V2	Insertion detected
MICDET > V2	No insertion

Comparator B is used to detect the type of headset inserted. Headset type detection becomes active only when the headset is inserted and detected.

MICDET > V1	Headset with mic
MICDET < V1	Headset without mic


Comparator B is also used to detect hook button press. However, button press detection becomes active only when headset with mic is detected.

Given headset with mic is already detected:		
MICDET > V1	No button press	
MICDET < V1	Button press detected	

Comparator A is used to differentiate mono headset with mic from stereo headset with mic.

HPROUT > V1	Mono headset with mic
HPROUT < V1	Stereo headset with mic

1.1.2 How to Determine the Comparator Threshold V1 and V2 (Capacitor-less Interface)



V1 = (MICBIAS - ref)
$$\times \frac{3}{46}$$
 + ref
V2 = (MICBIAS - ref) $\times \frac{43}{46}$ + ref

ref = HPCOM MICBIAS varies with detection mode

1.1.3 How Does the Bias Voltage Vary With Detection Mode?

If MICBIAS is turned off or if headset insertion is not detected, then MICBIAS = DVDD If MICBIAS is turned on and if headset insertion is detected, then MICBIA= Mic_bias



Headset Plugs/Connection Diagrams

1.1.4 Detection Sequence – Capacitor-less Interface

- Enable headset detection scheme (Page 0, Reg 13, D7) and set Capacitor-less interface (Page 0, Reg 14, D7 = 0)
- Detect insertion (with headset detection scheme enabled, headset insertion detection is always active inside device)

Insertion detected:

MICDET < (MICBIAS - ref)
$$\times \frac{43}{46}$$
 + ref = (DVDD - ref) $\times \frac{43}{46}$ + ref

No Insertion:

MICDET > (MICBIAS - ref) ×
$$\frac{43}{46}$$
 + ref = (DVDD - ref) × $\frac{43}{46}$ + ref

• Headset type detection (ONLY active when headset is inserted and detected) Headset with mic:

MICDET > (MICBIAS - ref) ×
$$\frac{3}{46}$$
 + ref = (Mic_bias - ref) × $\frac{3}{46}$ + ref

Headset without mic:

MICDET < (MICBIAS - ref)
$$\times \frac{3}{46}$$
 + ref = (Mic_bias - ref) $\times \frac{3}{46}$ + ref

Button press detection (button press detection becomes active ONLY when headset with mic is detected)

No button push:

MICDET > (MICBIAS - ref)
$$\times \frac{3}{46}$$
 + ref = (Mic_bias - ref) $\times \frac{3}{46}$ + ref

Button push detected:

 $MICDET < (MICBIAS - ref) \times \frac{3}{46} + ref = (Mic_bias - ref) \times \frac{3}{46} + ref$

Headset removal detection (With headset detection scheme enabled, removal detection is always active inside device.)

Headset removed:

MICDET < (MICBIAS - ref) ×
$$\frac{43}{46}$$
 + ref = (Mic_bias - ref) × $\frac{43}{46}$ + ref


Insertion detected:

6

MICDET > (MICBIAS - ref) ×
$$\frac{43}{46}$$
 + ref = (Mic_bias - ref) × $\frac{43}{46}$ + ref

Headset Detection for TLV320AIC33 and TLV320AIC3101/4/5/6 Family





1.2 Part II: AC-Coupled Stereo Headset Output Configuration – Capacitor Interface



Figure 7 shows the detection logic implemented by the detection block circled in red. The detection block consists of three main components – comparator A, B, and C.




Figure 7. Circuit Diagram of Detection Scheme for Capacitor Interface



Headset Plugs/Connection Diagrams

1.2.1 Detection Block – Capacitor Interface




Figure 8. Detection Block for AC-Coupled (Capacitor) Interface



Comparator C is used to detect headset insertion and removal. Headset insertion and removal detection is always active inside device.

MICDET < V2	Insertion detected
MICDET > V2	No insertion

Comparator B is used to detect the type of headset inserted. Headset type detection becomes active only when the headset is inserted and detected.

MICDET > V1	Headset with mic
MICDET < V1	Headset without mic


Comparator B is also used to detect hook button press. However button press detection becomes active only when headset with mic is detected.

Given headset with mic is already detected:		
MICDET > V1	No button press	
MICDET < V1	Button press detected	

Comparator A is used to differentiate mono headset with mic from stereo headset with mic.

HPROUT > V1	Mono headset with mic
HPROUT < V1	Stereo headset with mic

1.2.2 How to Determine the Comparator Threshold V1 and V2 – Capacitor Interface



V1 = (MICBIAS - ref)
$$\times \frac{3}{46}$$
 + ref
V2 = (MICBIAS - ref) $\times \frac{43}{46}$ + ref

ref = VSS = 0 V MICBIAS varies with detection mode

1.2.3 How Does the Bias Voltage Change With Detection Mode?

If MICBIAS is turned off or if headset insertion is not detected, then MICBIAS = DVDD If MICBIAS is turned on and if headset insertion is detected, then MICBIAS = Mic_bias



Headset Plugs/Connection Diagrams

1.2.4 Detection Sequence – Capacitor Interface

- Enable headset detection scheme (Page 0, Reg 13, D7) and set AC-coupled interface (page 0, Reg 14, D7 = 1)
- Detect insertion (With headset detection scheme enabled, headset insertion detection is always active inside device.)

Insertion detected:

MICBIAS < (MICBIAS – ref)
$$\times \frac{43}{46}$$
 + ref = DVDD $\times \frac{43}{46}$

No insertion:

MICBIAS > (MICBIAS - ref)
$$\times \frac{43}{46}$$
 + ref = DVDD $\times \frac{43}{46}$

• Headset type detection (only active when headset is inserted and detected) Headset with mic:

MICBIAS > (MICBIAS - ref)
$$\times \frac{3}{46}$$
 + ref = Mic_bias $\times \frac{3}{46}$

Headset without mic:

MICBIAS < (MICBIAS - ref) ×
$$\frac{3}{46}$$
 + ref = Mic_bias × $\frac{3}{46}$

Button press detection (button press detection becomes active only when headset with mic is detected)
 No button push:

MICBIAS > (MICBIAS - ref) ×
$$\frac{3}{46}$$
 + ref = Mic_bias × $\frac{3}{46}$

Button push detected:

MICBIAS < (MICBIAS - ref) × $\frac{3}{46}$ + ref = Mic_bias × $\frac{3}{46}$

Headset removal detection (with headset detection scheme enabled, removal detection is always active inside device.)

Headset removed:

MICBIAS > (MICBIAS - ref) ×
$$\frac{43}{46}$$
 + ref = Mic_bias × $\frac{43}{46}$


Insertion detected:

MICBIAS < (MICBIAS - ref) ×
$$\frac{43}{46}$$
 + ref = Mic_bias × $\frac{43}{46}$

$$\frac{3}{46}$$
 or $\frac{43}{46}$

Note: The ratio above $\begin{pmatrix} 46 \\ -46 \end{pmatrix}$ are determined by the on-chip resistance. A mismatch of on-chip resistance can cause a variation in the ratio by ±10%.








Figure 9. False Detection Due to Overdrawn Current Into Internal Mic

In both capacitor-less and capacitor interface, Reg 14/D6 = 0. Under this condition, bias voltage V_bias adjusts its value based on the detection status:

With Reg14/D6 = 0	
Before detection	V_bias = VDD
After detection	V_bias = Micbias

A portable device like a cell phone not only provides a jack for an external mic, but also has an internal mic embedded inside the device. The TLC320AIC33 and TLC320AIC3101/4/5/6 family device is designed in a way such that it can only accommodate a current flow of no more than 350 μ A into the internal mic. A false detection occurs if the internal mic is drawing more than 350- μ A current. The paragraph below gives a detailed explanation of the false detection.

With Reg14/D6 =0, V_bias is set at VDD when no insertion is detected. That is, switch S1 is switched on when no insertion is detected. Current flow into the Internal mic Ix has to be less than 350 μ A in order to keep V_bias on a level such that V≥V2. With V≥V2, the comparator outputs a logic 0 which indicates no insertion is detected. However, false detection occurs when the internal mic draws more than 350- μ A current. The extra current drawn by the internal mic pulls V_bias down so that V≤V2. With V≤V2, comparator outputs a logic 1 which indicates insertion is detected.

Once this false detection occurs, S1 is switched off and V_bias is set at Micbias instead of VDD. The new bias voltage sets V \geq V2 again and comparator outputs a logic 0 which implies no detection again. The output of comparator therefore switches between 0 and 1 due to the extra current drawn by the internal mic.

To summarize, the current drawn by the internal mic has to be less than 350 μ A in order to avoid false detection. When the current lx is larger than 350 μ A, the comparator generates a false detection even when nothing is actually inserted into the mic jack. A good check in a real application is to double-check the current drawn by the internal mic and make sure that it is under 350 μ A.



References

www.ti.com

2 References

- 1. http://www.india.ti.com/cgi-bin/mstc/twiki/bin/view/DAPIND/AIC33Apps
- TLV320AIC3100, Low Power Stereo CODEC with integrated Mono Class-D Speaker Amplifier data sheet (SLOS545)

.

•

Appendix A Example for a Pseudo-Differential (Capacitor-less) Output Configuration

DVDD = 2 V Mic_bias = 3.3 V Ref = HPRCOM = 1.3 V

- Before insertion, set Bias = DVDD HPCOM = 2.0 V 1.3 V = 0.7 V Insertion detected: Mic_detect < Bias × ⁴³/₄₆ + Ref = 0.7 × ⁴³/₄₆ + 1.3 = 1.95 V No insertion: Mic_detect > Bias × ⁴³/₄₆ + Ref = 0.7 × ⁴³/₄₆ + 1.3 = 1.95 V
 Headset type detection, set Bias = Mic_bias - HPCOM = 3.3 - 1.3 = 2.0 V Headset with Mic: Mic_detect > Bias × ³/₄₆ + Ref = 2.0 × ³/₄₆ + 1.3 = 1.43 V Headset without Mic: Mic_detect < Bias × ³/₄₆ + Ref = 2.0 × ³/₄₆ + 1.3 = 1.43 V
 - 46 46Hook button press detection, set Bias = Mic_bias - HPCOM = 3.3 - 1.3 = 2.0Button press detection is active only when headset with mic has been detected.

No button push: Mic_detect > Bias × $\frac{3}{46}$ + Ref = 2.0 × $\frac{3}{46}$ + 1.3 = 1.43 V

- Button push detected: Mic_detect < Bias × $\frac{3}{46}$ + Ref = 2.0 × $\frac{3}{46}$ + 1.3 = 1.43 V Headset removal detection, set Bias = Mic_bias – HPCOM = 3.3 – 1.3 = 2 V
- Headset removed: Mic_detect > Bias × $\frac{43}{46}$ + Ref = 2.0 × $\frac{43}{46}$ + 1.3 = 3.17 V Insertion detected: Mic_detect < Bias × $\frac{43}{46}$ + Ref = 2.0 × $\frac{43}{46}$ + 1.3 = 3.17 V

Appendix B Example for an AC-Coupled (Capacitor) Output Configuration

DVDD = 2 V Mic_bias = 3.3 V Ref = VSS = 0 V

• Before insertion, set Bias = DVDD = 2 V

Insertion detected: Mic_detect < Bias × $\frac{43}{46}$ + Ref = 2.0 × $\frac{43}{46}$ + 0 = 1.87 V


No insertion: Mic_detect > Bias × $\frac{43}{46}$ + Ref = 2.0 × $\frac{43}{46}$ +0 = 1.87 V

- Headset type detection, set Bias = Mic_bias = 3.3 V Headset with Mic: Mic_detect > Bias × $\frac{3}{46}$ + Ref = $3.3 \times \frac{3}{46}$ + 0 = 0.22 V Headset without Mic: Mic_detect < Bias × $\frac{3}{46}$ + Ref = $3.3 \times \frac{3}{46}$ + 0 = 0.22 V
- Button press detection, set Bias = Mic_bias = 3.3 V Button press detection is active only when headset with mic has been detected. No button push: Mic_detect > Bias × 3/46 + Ref = 3.3 × 3/46 + 0 = 0.22 V Button push detected: Mic_detect < Bias × 3/46 + Ref = 3.3 × 3/46 + 0 = 0.22 V
- Headset removal detection, set Bias = Mic_bias = 3.3 V. Headset removed: Mic_detect > Bias $\times \frac{43}{46}$ + Ref = $3.3 \times \frac{43}{46}$ + 0 = 3.08 V Insertion detected: Mic_detect < Bias $\times \frac{43}{46}$ + Ref = $3.3 \times \frac{43}{46}$ + 0 = 3.08 V

14 Headset Detection for TLV320AIC33 and TLV320AIC3101/4/5/6 Family












Figure 11. Flowchart for Hook Button Press Detection and Headset Removal Detection (With Mic)

If Dvgnd (VGND driver) is on, Micbias is switched on in order to do the hook button press detection and plug removal detection. Power due to Micbias is insignificant as compared to speaker power. If both Dvgnd and Micbias are off, pulse scheme which takes less than 50 μ A is used to complete the detection. Detection is done at the end of high period of pulse.







Figure 12. Flowchart for Headset Removal Detection (Without Mic)

If Dvgnd (VGND driver) is on, Micbias is switched on in order to do the plug removal detection. Power due to Micbias is insignificant as compared to speaker power. If Dvgnd is off, pulse scheme which takes less than 50 µA is used to complete the detection. Detection is done at the end of the high period of the pulse.






Appendix D Flowchart for AC-Coupled (Capacitor) Output Configuration

Figure 13. Flowchart for Insertion Detection and Headset-Type Detection










Figure 15. Flowchart for Headset Removal Detection (Without Mic)

Pulse Scheme



Appendix D




Figure 16. Pulse Scheme

DET_PULSE, which is generated using an internal oscillator, is used for hook button detection. DET_PULSE period is 0.5 ms with high time of 15 μ s.

20 Headset Detection for TLV320AIC33 and TLV320AIC3101/4/5/6 Family

IMPORTANT NOTICE

Texas Instruments Incorporated and its subsidiaries (TI) reserve the right to make corrections, modifications, enhancements, improvements, and other changes to its products and services at any time and to discontinue any product or service without notice. Customers should obtain the latest relevant information before placing orders and should verify that such information is current and complete. All products are sold subject to TI's terms and conditions of sale supplied at the time of order acknowledgment.

TI warrants performance of its hardware products to the specifications applicable at the time of sale in accordance with TI's standard warranty. Testing and other quality control techniques are used to the extent TI deems necessary to support this warranty. Except where mandated by government requirements, testing of all parameters of each product is not necessarily performed.

TI assumes no liability for applications assistance or customer product design. Customers are responsible for their products and applications using TI components. To minimize the risks associated with customer products and applications, customers should provide adequate design and operating safeguards.

TI does not warrant or represent that any license, either express or implied, is granted under any TI patent right, copyright, mask work right, or other TI intellectual property right relating to any combination, machine, or process in which TI products or services are used. Information published by TI regarding third-party products or services does not constitute a license from TI to use such products or services or a warranty or endorsement thereof. Use of such information may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

Reproduction of TI information in TI data books or data sheets is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. Reproduction of this information with alteration is an unfair and deceptive business practice. TI is not responsible or liable for such altered documentation. Information of third parties may be subject to additional restrictions.

Resale of TI products or services with statements different from or beyond the parameters stated by TI for that product or service voids all express and any implied warranties for the associated TI product or service and is an unfair and deceptive business practice. TI is not responsible or liable for any such statements.

TI products are not authorized for use in safety-critical applications (such as life support) where a failure of the TI product would reasonably be expected to cause severe personal injury or death, unless officers of the parties have executed an agreement specifically governing such use. Buyers represent that they have all necessary expertise in the safety and regulatory ramifications of their applications, and acknowledge and agree that they are solely responsible for all legal, regulatory and safety-related requirements concerning their products and any use of TI products in such safety-critical applications, notwithstanding any applications-related information or support that may be provided by TI. Further, Buyers must fully indemnify TI and its representatives against any damages arising out of the use of TI products in such safety-critical applications.

TI products are neither designed nor intended for use in military/aerospace applications or environments unless the TI products are specifically designated by TI as military-grade or "enhanced plastic." Only products designated by TI as military-grade meet military specifications. Buyers acknowledge and agree that any such use of TI products which TI has not designated as military-grade is solely at the Buyer's risk, and that they are solely responsible for compliance with all legal and regulatory requirements in connection with such use.

TI products are neither designed nor intended for use in automotive applications or environments unless the specific TI products are designated by TI as compliant with ISO/TS 16949 requirements. Buyers acknowledge and agree that, if they use any non-designated products in automotive applications, TI will not be responsible for any failure to meet such requirements.

Following are URLs where you can obtain information on other Texas Instruments products and application solutions:

Products		Applications	
Amplifiers	amplifier.ti.com	Audio	www.ti.com/audio
Data Converters	dataconverter.ti.com	Automotive	www.ti.com/automotive
DLP® Products	www.dlp.com	Communications and Telecom	www.ti.com/communications
DSP	dsp.ti.com	Computers and Peripherals	www.ti.com/computers
Clocks and Timers	www.ti.com/clocks	Consumer Electronics	www.ti.com/consumer-apps
Interface	interface.ti.com	Energy	www.ti.com/energy
Logic	logic.ti.com	Industrial	www.ti.com/industrial
Power Mgmt	power.ti.com	Medical	www.ti.com/medical
Microcontrollers	microcontroller.ti.com	Security	www.ti.com/security
RFID	www.ti-rfid.com	Space, Avionics & Defense	www.ti.com/space-avionics-defense
RF/IF and ZigBee® Solutions	www.ti.com/lprf	Video and Imaging	www.ti.com/video
		Wireless	www.ti.com/wireless-apps

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265 Copyright © 2010, Texas Instruments Incorporated