



# SN74AUP1G07 Low-Power Single Buffer/Driver With Open-Drain Outputs

## 1 Features

- Available in the Ultra Small 0.64 mm<sup>2</sup> Package (DPW) with 0.5-mm Pitch
- Low Static-Power Consumption ( $I_{CC} = 0.9 \mu\text{A}$  Maximum)
- Low Dynamic-Power Consumption ( $C_{pd} = 1 \text{ pF}$  Typical at 3.3 V)
- Low Input Capacitance ( $C_i = 1.5 \text{ pF}$  Typical)
- Low Noise – Overshoot and Undershoot <10% of  $V_{CC}$
- $I_{off}$  Supports Live Insertion, Partial-Power-Down Mode, and Back-Drive Protection
- Input Hysteresis Allows Slow Input Transition and Better Switching Noise Immunity at the Input ( $V_{hys} = 250 \text{ mV}$  Typ at 3.3 V)
- Wide Operating  $V_{CC}$  Range of 0.8 V to 3.6 V
- Optimized for 3.3-V Operation
- 3.6-V I/O Tolerant to Support Mixed-Mode Signal Operation
- $t_{pd} = 3.3 \text{ ns}$  Maximum at 3.3 V
- Suitable for Point-to-Point Applications
- Latch-Up Performance Exceeds 100 mA Per JESD 78, Class II
- ESD Performance Tested Per JESD 22
  - 2000-V Human-Body Model (A114-B, Class II)
  - 1000-V Charged-Device Model (C101)

## 2 Applications

- ATCA Solutions
- Active Noise Cancellation (ANC)
- Barcode Scanner
- Blood Pressure Monitor
- CPAP Machine
- Cable Solutions
- DLP 3D Machine Vision, Hyperspectral Imaging, Optical Networking, and Spectroscopy
- E-Book
- Embedded PC
- Field Transmitter: Temperature or Pressure Sensor
- Fingerprint Biometrics
- HVAC: Heating, Ventilating, and Air Conditioning
- Network-Attached Storage (NAS)
- Server Motherboard and PSU
- Software Defined Radio (SDR)
- TV: High-Definition (HDTV), LCD, and Digital
- Video Communications System
- Wireless Data Access Card, Headset, Keyboard, Mouse, and LAN Card
- X-ray: Baggage Scanner, Medical, and Dental

## 3 Description

The SN74AUP1G07 device is a single buffer gate with open drain output that operates from 0.8 V to 3.6 V.

### Device Information<sup>(1)</sup>

| PART NUMBER | PACKAGE    | BODY SIZE (NOM)   |
|-------------|------------|-------------------|
| SN74AUP1G07 | SOT-23 (5) | 2.90 mm × 1.60 mm |
|             | SOT (5)    | 2.00 mm × 1.25 mm |
|             | SOT (5)    | 1.60 mm × 1.20 mm |
|             | USON (6)   | 1.45 mm × 1.00 mm |
|             | X2SON (4)  | 0.80 mm × 0.80 mm |

(1) For all available packages, see the orderable addendum at the end of the data sheet.

## 4 Simplified Schematic



## Table of Contents

|                                                           |          |                                                                  |           |
|-----------------------------------------------------------|----------|------------------------------------------------------------------|-----------|
| <b>1 Features</b> .....                                   | <b>1</b> | Pulse Duration .....                                             | <b>8</b>  |
| <b>2 Applications</b> .....                               | <b>1</b> | 8.2 Enable and Disable Times .....                               | <b>9</b>  |
| <b>3 Description</b> .....                                | <b>1</b> | <b>9 Detailed Description</b> .....                              | <b>10</b> |
| <b>4 Simplified Schematic</b> .....                       | <b>1</b> | 9.1 Overview .....                                               | <b>10</b> |
| <b>5 Revision History</b> .....                           | <b>2</b> | 9.2 Functional Block Diagram .....                               | <b>10</b> |
| <b>6 Pin Configuration and Functions</b> .....            | <b>3</b> | 9.3 Feature Description .....                                    | <b>10</b> |
| <b>7 Specifications</b> .....                             | <b>4</b> | 9.4 Device Functional Modes .....                                | <b>10</b> |
| 7.1 Absolute Maximum Ratings .....                        | <b>4</b> | <b>10 Application and Implementation</b> .....                   | <b>11</b> |
| 7.2 Handling Ratings .....                                | <b>4</b> | 10.1 Application Information .....                               | <b>11</b> |
| 7.3 Recommended Operating Conditions .....                | <b>4</b> | 10.2 Typical Application .....                                   | <b>11</b> |
| 7.4 Thermal Information .....                             | <b>5</b> | <b>11 Power Supply Recommendations</b> .....                     | <b>13</b> |
| 7.5 Electrical Characteristics .....                      | <b>5</b> | <b>12 Layout</b> .....                                           | <b>13</b> |
| 7.6 Switching Characteristics, $C_L = 5\text{ pF}$ .....  | <b>5</b> | 12.1 Layout Guidelines .....                                     | <b>13</b> |
| 7.7 Switching Characteristics, $C_L = 10\text{ pF}$ ..... | <b>6</b> | 12.2 Layout Example .....                                        | <b>13</b> |
| 7.8 Switching Characteristics, $C_L = 15\text{ pF}$ ..... | <b>6</b> | <b>13 Device and Documentation Support</b> .....                 | <b>14</b> |
| 7.9 Switching Characteristics, $C_L = 30\text{ pF}$ ..... | <b>6</b> | 13.1 Trademarks .....                                            | <b>14</b> |
| 7.10 Operating Characteristics .....                      | <b>6</b> | 13.2 Electrostatic Discharge Caution .....                       | <b>14</b> |
| 7.11 Typical Characteristics .....                        | <b>7</b> | 13.3 Glossary .....                                              | <b>14</b> |
| <b>8 Parameter Measurement Information</b> .....          | <b>8</b> | <b>14 Mechanical, Packaging, and Orderable Information</b> ..... | <b>14</b> |
| 8.1 Propagation Delays, Setup and Hold Times, and         |          |                                                                  |           |

## 5 Revision History


NOTE: Page numbers for previous revisions may differ from page numbers in the current version.

| Changes from Revision I (October 2012) to Revision J | Page     |
|------------------------------------------------------|----------|
| • Updated document to new TI data sheet format ..... | <b>1</b> |
| • Removed Ordering Information table .....           | <b>1</b> |
| • Updated $I_{off}$ in Features. ....                | <b>1</b> |
| • Added Applications .....                           | <b>1</b> |
| • Added Handling Ratings table .....                 | <b>4</b> |
| • Added Thermal Information table .....              | <b>5</b> |
| • Added Typical Characteristics .....                | <b>7</b> |

| Changes from Revision H (September 2012) to Revision I | Page     |
|--------------------------------------------------------|----------|
| • Updated DPW package pinout. ....                     | <b>3</b> |

| Changes from Revision F (May 2010) to Revision G      | Page     |
|-------------------------------------------------------|----------|
| • Changed $V_{CC}$ to reflect updated condition ..... | <b>4</b> |

## 6 Pin Configuration and Functions



N.C. – No internal connection.

DNU – Do not use

See mechanical drawings for dimensions.

### Pin Functions

| NAME | PIN           |          |     |     |     | I/O | DESCRIPTION   |
|------|---------------|----------|-----|-----|-----|-----|---------------|
|      | DBV, DCK, DRL | DSF, DRY | YFP | DPW | YZP |     |               |
| NC   | 1             | 1, 5     | —   | 1   | A1  | —   | No Connection |
| A    | 2             | 2        | A1  | 2   | B1  | I   | Input A       |
| GND  | 3             | 3        | B1  | 3   | C1  | —   | Ground Pin    |
| Y    | 4             | 4        | B2  | 4   | C2  | O   | Output Y      |
| VCC  | 5             | 6        | A2  | 5   | A2  | —   | Power Pin     |

## 7 Specifications

### 7.1 Absolute Maximum Ratings<sup>(1)</sup>

over operating free-air temperature range (unless otherwise noted)

|                 |                                                                                             | MIN                | MAX                   | UNIT   |
|-----------------|---------------------------------------------------------------------------------------------|--------------------|-----------------------|--------|
| V <sub>CC</sub> | Supply voltage range                                                                        | –0.5               | 4.6                   | V      |
| V <sub>I</sub>  | Input voltage range <sup>(2)</sup>                                                          | –0.5               | 4.6                   | V      |
| V <sub>O</sub>  | Voltage range applied to any output in the high-impedance or power-off state <sup>(2)</sup> | –0.5               | 4.6                   | V      |
| V <sub>O</sub>  | Voltage range applied to any output in the high or low state <sup>(2)</sup>                 | –0.5               | V <sub>CC</sub> + 0.5 | V      |
| I <sub>IK</sub> | Input clamp current                                                                         | V <sub>I</sub> < 0 |                       | –50 mA |
| I <sub>OK</sub> | Output clamp current                                                                        | V <sub>O</sub> < 0 |                       | –50 mA |
| I <sub>O</sub>  | Continuous output current                                                                   |                    | ±20                   | mA     |
|                 | Continuous current through V <sub>CC</sub> or GND                                           |                    | ±50                   | mA     |

- (1) Stresses beyond those listed under *Absolute Maximum Ratings* may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated under *Recommended Operating Conditions* is not implied. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability.
- (2) The input negative-voltage and output voltage ratings may be exceeded if the input and output current ratings are observed.

### 7.2 Handling Ratings

|                    |                           |                                                                                          | MIN | MAX  | UNIT |
|--------------------|---------------------------|------------------------------------------------------------------------------------------|-----|------|------|
| T <sub>stg</sub>   | Storage temperature range |                                                                                          | −65 | 150  | °C   |
| V <sub>(ESD)</sub> | Electrostatic discharge   | Human body model (HBM), per ANSI/ESDA/JEDEC JS-001, all pins <sup>(1)</sup>              | 0   | 2000 | V    |
|                    |                           | Charged device model (CDM), per JEDEC specification JESD22-C101, all pins <sup>(2)</sup> | 0   | 1000 |      |

- (1) JEDEC document JEP155 states that 500-V HBM allows safe manufacturing with a standard ESD control process.
- (2) JEDEC document JEP157 states that 250-V CDM allows safe manufacturing with a standard ESD control process.

### 7.3 Recommended Operating Conditions

over operating free-air temperature range (unless otherwise noted)<sup>(1)</sup>

|                 |                                    | MIN                               | MAX                    | UNIT |
|-----------------|------------------------------------|-----------------------------------|------------------------|------|
| V <sub>CC</sub> | Supply voltage                     | 0.8                               | 3.6                    | V    |
| V <sub>IH</sub> | High-level input voltage           | V <sub>CC</sub> = 0.8 V           | V <sub>CC</sub>        | V    |
|                 |                                    | V <sub>CC</sub> = 1.0 V to 1.95 V | 0.65 × V <sub>CC</sub> |      |
|                 |                                    | V <sub>CC</sub> = 2.3 V to 2.7 V  | 1.6                    |      |
|                 |                                    | V <sub>CC</sub> = 3 V to 3.6 V    | 2                      |      |
| V <sub>IL</sub> | Low-level input voltage            | V <sub>CC</sub> = 0.8 V           | 0                      | V    |
|                 |                                    | V <sub>CC</sub> = 1.0 V to 1.95 V | 0.35 × V <sub>CC</sub> |      |
|                 |                                    | V <sub>CC</sub> = 2.3 V to 2.7 V  | 0.7                    |      |
|                 |                                    | V <sub>CC</sub> = 3 V to 3.6 V    | 0.9                    |      |
| V <sub>I</sub>  | Input voltage                      | 0                                 | 3.6                    | V    |
| V <sub>O</sub>  | Output voltage                     | 0                                 | 3.6                    | V    |
| I <sub>OL</sub> | Low-level output current           | V <sub>CC</sub> = 0.8 V           | 20                     | mA   |
|                 |                                    | V <sub>CC</sub> = 1.1 V           | 1.1                    |      |
|                 |                                    | V <sub>CC</sub> = 1.4 V           | 1.7                    |      |
|                 |                                    | V <sub>CC</sub> = 1.65 V          | 1.9                    |      |
|                 |                                    | V <sub>CC</sub> = 2.3 V           | 3.1                    |      |
|                 |                                    | V <sub>CC</sub> = 3 V             | 4                      |      |
| Δt/Δv           | Input transition rise or fall rate | V <sub>CC</sub> = 0.8 V to 3.6 V  | 200                    | ns/V |
| T <sub>A</sub>  | Operating free-air temperature     | –40                               | 85                     | °C   |

- (1) All unused inputs of the device must be held at V<sub>CC</sub> or GND to ensure proper device operation. Refer to the TI application report, *Implications of Slow or Floating CMOS Inputs*, literature number [SCBA004](#).

## 7.4 Thermal Information

| THERMAL METRIC <sup>(1)</sup> |                                              | DBV    | DCK    | DPW    | DRL    | DRY    | DSF    | UNIT |
|-------------------------------|----------------------------------------------|--------|--------|--------|--------|--------|--------|------|
|                               |                                              | 5 PINS | 5 PINS | 5 PINS | 5 PINS | 6 PINS | 6 PINS |      |
| $R_{\theta JA}$               | Junction-to-ambient thermal resistance       | 298.6  | 314.4  | 291.8  | 349.7  | 554.9  | 407.1  | °C/W |
| $R_{\theta JC(top)}$          | Junction-to-case (top) thermal resistance    | 240.2  | 128.7  | 224.2  | 120.5  | 385.4  | 232.0  |      |
| $R_{\theta JB}$               | Junction-to-board thermal resistance         | 134.6  | 100.6  | 245.8  | 171.4  | 388.2  | 306.9  |      |
| $\Psi_{JT}$                   | Junction-to-top characterization parameter   | 114.5  | 7.1    | 31.4   | 10.8   | 159.0  | 40.3   |      |
| $\Psi_{JB}$                   | Junction-to-board characterization parameter | 133.9  | 99.8   | 245.6  | 169.4  | 384.1  | 306.0  |      |
| $R_{\theta JC(bot)}$          | Junction-to-case (bottom) thermal resistance | n/a    | n/a    | 195.4  | n/a    | n/a    | n/a    |      |

(1) For more information about traditional and new thermal metrics, see the *IC Package Thermal Metrics* application report, [SPRA953](#).

## 7.5 Electrical Characteristics

over recommended operating free-air temperature range (unless otherwise noted)

| PARAMETER        |         | TEST CONDITIONS                                                  | $V_{CC}$       | $T_A = 25^\circ\text{C}$ |     |                     | $T_A = -40^\circ\text{C}$<br>to $85^\circ\text{C}$ |                     | UNIT          |
|------------------|---------|------------------------------------------------------------------|----------------|--------------------------|-----|---------------------|----------------------------------------------------|---------------------|---------------|
|                  |         |                                                                  |                | MIN                      | TYP | MAX                 | MIN                                                | MAX                 |               |
| $V_{OL}$         |         | $I_{OL} = 20\ \mu\text{A}$                                       | 0.8 V to 3.6 V |                          |     | 0.1                 |                                                    | 0.1                 | V             |
|                  |         | $I_{OL} = 1.1\ \text{mA}$                                        | 1.1 V          |                          |     | $0.3 \times V_{CC}$ |                                                    | $0.3 \times V_{CC}$ |               |
|                  |         | $I_{OL} = 1.7\ \text{mA}$                                        | 1.4 V          |                          |     | 0.31                |                                                    | 0.37                |               |
|                  |         | $I_{OL} = 1.9\ \text{mA}$                                        | 1.65 V         |                          |     | 0.31                |                                                    | 0.35                |               |
|                  |         | $I_{OL} = 2.3\ \text{mA}$                                        | 2.3 V          |                          |     | 0.31                |                                                    | 0.33                |               |
|                  |         | $I_{OL} = 3.1\ \text{mA}$                                        |                |                          |     | 0.44                |                                                    | 0.45                |               |
|                  |         | $I_{OL} = 2.7\ \text{mA}$                                        | 3 V            |                          |     | 0.31                |                                                    | 0.33                |               |
|                  |         | $I_{OL} = 4\ \text{mA}$                                          |                |                          |     | 0.44                |                                                    | 0.45                |               |
| $I_I$            | A input | $V_I = \text{GND to } 3.6\ \text{V}$                             | 0 V to 3.6 V   |                          |     | 0.1                 |                                                    | 0.5                 | $\mu\text{A}$ |
| $I_{off}$        |         | $V_I \text{ or } V_O = 0\ \text{V to } 3.6\ \text{V}$            | 0 V            |                          |     | 0.2                 |                                                    | 0.6                 | $\mu\text{A}$ |
| $\Delta I_{off}$ |         | $V_I \text{ or } V_O = 0\ \text{V to } 3.6\ \text{V}$            | 0 V to 0.2 V   |                          |     | 0.2                 |                                                    | 0.6                 | $\mu\text{A}$ |
| $I_{CC}$         |         | $V_I = \text{GND or } V_{CC} \text{ to } 3.6\ \text{V}, I_O = 0$ | 0.8 V to 3.6 V |                          |     | 0.5                 |                                                    | 0.9                 | $\mu\text{A}$ |
| $\Delta I_{CC}$  |         | $V_I = V_{CC} - 0.6\ \text{V}, I_O = 0$                          | 3.3 V          |                          |     | 40                  |                                                    | 50                  | $\mu\text{A}$ |
| $C_i$            |         | $V_I = V_{CC} \text{ or GND}$                                    | 0 V            |                          | 1.5 |                     |                                                    |                     | pF            |
|                  |         |                                                                  | 3.6 V          |                          | 1.7 |                     |                                                    |                     |               |
| $C_o$            |         | $V_O = \text{GND}$                                               | 0 V            |                          | 1.7 |                     |                                                    |                     | pF            |

## 7.6 Switching Characteristics, $C_L = 5\ \text{pF}$

over recommended operating free-air temperature range (unless otherwise noted) (see [Figure 3](#) and [Figure 4](#))

| PARAMETER | FROM<br>(INPUT) | TO<br>(OUTPUT) | $V_{CC}$                           | $T_A = 25^\circ\text{C}$ |      |     | $T_A = -40^\circ\text{C}$<br>to $85^\circ\text{C}$ |      | UNIT |
|-----------|-----------------|----------------|------------------------------------|--------------------------|------|-----|----------------------------------------------------|------|------|
|           |                 |                |                                    | MIN                      | TYP  | MAX | MIN                                                | MAX  |      |
| $t_{pd}$  | A               | Y              | 0.8 V                              |                          | 12.2 |     |                                                    |      | ns   |
|           |                 |                | $1.2\ \text{V} \pm 0.1\ \text{V}$  | 3.4                      | 5.1  | 7.5 | 1.5                                                | 14.7 |      |
|           |                 |                | $1.5\ \text{V} \pm 0.1\ \text{V}$  | 2.3                      | 3.6  | 5.1 | 1.3                                                | 8.3  |      |
|           |                 |                | $1.8\ \text{V} \pm 0.15\ \text{V}$ | 2.4                      | 3.1  | 4   | 1                                                  | 6.3  |      |
|           |                 |                | $2.5\ \text{V} \pm 0.2\ \text{V}$  | 1.5                      | 2.1  | 2.9 | 0.9                                                | 4.1  |      |
|           |                 |                | $3.3\ \text{V} \pm 0.3\ \text{V}$  | 1.8                      | 2.2  | 2.8 | 1.1                                                | 3.3  |      |

**SN74AUP1G07**

SCES591J – JULY 2004 – REVISED JUNE 2014

[www.ti.com](http://www.ti.com)
**7.7 Switching Characteristics,  $C_L = 10$  pF**

 over recommended operating free-air temperature range (unless otherwise noted) (see [Figure 3](#) and [Figure 4](#))

| PARAMETER | FROM<br>(INPUT) | TO<br>(OUTPUT) | $V_{CC}$           | $T_A = 25^\circ\text{C}$ |     |     | $T_A = -40^\circ\text{C}$<br>to $85^\circ\text{C}$ |      | UNIT |
|-----------|-----------------|----------------|--------------------|--------------------------|-----|-----|----------------------------------------------------|------|------|
|           |                 |                |                    | MIN                      | TYP | MAX | MIN                                                | MAX  |      |
| $t_{pd}$  | A               | Y              | 0.8 V              |                          | 15  |     |                                                    |      | ns   |
|           |                 |                | 1.2 V $\pm$ 0.1 V  | 4                        | 6.2 | 9   | 2.4                                                | 16.2 |      |
|           |                 |                | 1.5 V $\pm$ 0.1 V  | 3.1                      | 4.4 | 6.1 | 2                                                  | 9.4  |      |
|           |                 |                | 1.8 V $\pm$ 0.15 V | 3.3                      | 3.9 | 4.8 | 1.6                                                | 7.1  |      |
|           |                 |                | 2.5 V $\pm$ 0.2 V  | 2.1                      | 2.8 | 3.5 | 1.3                                                | 4.8  |      |
|           |                 |                | 3.3 V $\pm$ 0.3 V  | 2.3                      | 3   | 4   | 1.4                                                | 4.5  |      |

**7.8 Switching Characteristics,  $C_L = 15$  pF**

 over recommended operating free-air temperature range (unless otherwise noted) (see [Figure 3](#) and [Figure 4](#))

| PARAMETER | FROM<br>(INPUT) | TO<br>(OUTPUT) | $V_{CC}$           | $T_A = 25^\circ\text{C}$ |      |      | $T_A = -40^\circ\text{C}$<br>to $85^\circ\text{C}$ |      | UNIT |
|-----------|-----------------|----------------|--------------------|--------------------------|------|------|----------------------------------------------------|------|------|
|           |                 |                |                    | MIN                      | TYP  | MAX  | MIN                                                | MAX  |      |
| $t_{pd}$  | A               | Y              | 0.8 V              |                          | 18.2 |      |                                                    |      | ns   |
|           |                 |                | 1.2 V $\pm$ 0.1 V  | 4.9                      | 7.3  | 10.4 | 3.2                                                | 17.6 |      |
|           |                 |                | 1.5 V $\pm$ 0.1 V  | 3.8                      | 5.2  | 6.8  | 2.6                                                | 10.2 |      |
|           |                 |                | 1.8 V $\pm$ 0.15 V | 3.4                      | 4.8  | 6.7  | 2.2                                                | 7.9  |      |
|           |                 |                | 2.5 V $\pm$ 0.2 V  | 2.4                      | 3.4  | 4.5  | 1.9                                                | 5.3  |      |
|           |                 |                | 3.3 V $\pm$ 0.3 V  | 2.2                      | 3.7  | 5.4  | 1.8                                                | 6.1  |      |

**7.9 Switching Characteristics,  $C_L = 30$  pF**



 over recommended operating free-air temperature range (unless otherwise noted) (see [Figure 3](#) and [Figure 4](#))

| PARAMETER | FROM<br>(INPUT) | TO<br>(OUTPUT) | $V_{CC}$           | $T_A = 25^\circ\text{C}$ |      |      | $T_A = -40^\circ\text{C}$<br>to $85^\circ\text{C}$ |      | UNIT |
|-----------|-----------------|----------------|--------------------|--------------------------|------|------|----------------------------------------------------|------|------|
|           |                 |                |                    | MIN                      | TYP  | MAX  | MIN                                                | MAX  |      |
| $t_{pd}$  | A               | Y              | 0.8 V              |                          | 26.5 |      |                                                    |      | ns   |
|           |                 |                | 1.2 V $\pm$ 0.1 V  | 8.1                      | 10.7 | 14.4 | 4.5                                                | 21.9 |      |
|           |                 |                | 1.5 V $\pm$ 0.1 V  | 6.5                      | 7.7  | 9.4  | 3.8                                                | 13   |      |
|           |                 |                | 1.8 V $\pm$ 0.15 V | 5.8                      | 7.5  | 9.7  | 3.2                                                | 11   |      |
|           |                 |                | 2.5 V $\pm$ 0.2 V  | 4.5                      | 5.4  | 6.7  | 3                                                  | 7.1  |      |
|           |                 |                | 3.3 V $\pm$ 0.3 V  | 3.9                      | 6.3  | 9.7  | 2.8                                                | 10.4 |      |

**7.10 Operating Characteristics**
 $T_A = 25^\circ\text{C}$ 


| PARAMETER |                               | TEST CONDITIONS | $V_{CC}$           | TYP | UNIT |
|-----------|-------------------------------|-----------------|--------------------|-----|------|
| $C_{pd}$  | Power dissipation capacitance | $f = 10$ MHz    | 0.8 V              | 1   | pF   |
|           |                               |                 | 1.2 V $\pm$ 0.1 V  | 1   |      |
|           |                               |                 | 1.5 V $\pm$ 0.1 V  | 1   |      |
|           |                               |                 | 1.8 V $\pm$ 0.15 V | 1   |      |
|           |                               |                 | 2.5 V $\pm$ 0.2 V  | 1   |      |
|           |                               |                 | 3.3 V $\pm$ 0.3 V  | 1   |      |

## 7.11 Typical Characteristics



## 8 Parameter Measurement Information


### 8.1 Propagation Delays, Setup and Hold Times, and Pulse Duration



- NOTES:
- A.  $C_L$  includes probe and jig capacitance.
  - B. All input pulses are supplied by generators having the following characteristics:  $PRR \leq 10 \text{ MHz}$ ,  $Z_O = 50 \Omega$ ,  $t_r/t_f = 3 \text{ ns}$ .
  - C. The outputs are measured one at a time, with one transition per measurement.
  - D.  $t_{PLH}$  and  $t_{PHL}$  are the same as  $t_{pd}$ .
  - E. All parameters and waveforms are not applicable to all devices.

**Figure 3. Load Circuit and Voltage Waveforms**


## 8.2 Enable and Disable Times



LOAD CIRCUIT

| TEST                                   | S1                         |
|----------------------------------------|----------------------------|
| $t_{PLZ}/t_{PZL}$<br>$t_{PHZ}/t_{PZH}$ | 2 $\times$ $V_{CC}$<br>GND |

|              | $V_{CC} = 0.8 \text{ V}$ | $V_{CC} = 1.2 \text{ V}$<br>$\pm 0.1 \text{ V}$ | $V_{CC} = 1.5 \text{ V}$<br>$\pm 0.1 \text{ V}$ | $V_{CC} = 1.8 \text{ V}$<br>$\pm 0.15 \text{ V}$ | $V_{CC} = 2.5 \text{ V}$<br>$\pm 0.2 \text{ V}$ | $V_{CC} = 3.3 \text{ V}$<br>$\pm 0.3 \text{ V}$ |
|--------------|--------------------------|-------------------------------------------------|-------------------------------------------------|--------------------------------------------------|-------------------------------------------------|-------------------------------------------------|
| $C_L$        | 5, 10, 15, 30 pF         | 5, 10, 15, 30 pF                                | 5, 10, 15, 30 pF                                | 5, 10, 15, 30 pF                                 | 5, 10, 15, 30 pF                                | 5, 10, 15, 30 pF                                |
| $V_M$        | $V_{CC}/2$               | $V_{CC}/2$                                      | $V_{CC}/2$                                      | $V_{CC}/2$                                       | $V_{CC}/2$                                      | $V_{CC}/2$                                      |
| $V_I$        | $V_{CC}$                 | $V_{CC}$                                        | $V_{CC}$                                        | $V_{CC}$                                         | $V_{CC}$                                        | $V_{CC}$                                        |
| $V_{\Delta}$ | 0.1 V                    | 0.1 V                                           | 0.1 V                                           | 0.15 V                                           | 0.15 V                                          | 0.3 V                                           |



VOLTAGE WAVEFORMS  
ENABLE AND DISABLE TIMES  
LOW- AND HIGH-LEVEL ENABLING

- NOTES:
- A.  $C_L$  includes probe and jig capacitance.
  - B. Waveform 1 is for an output with internal conditions such that the output is low, except when disabled by the output control. Waveform 2 is for an output with internal conditions such that the output is high, except when disabled by the output control.
  - C. All input pulses are supplied by generators having the following characteristics:  $PRR \leq 10 \text{ MHz}$ ,  $Z_O = 50 \Omega$ ,  $t_r/t_f = 3 \text{ ns}$ .
  - D. The outputs are measured one at a time, with one transition per measurement.
  - E.  $t_{PLZ}$  and  $t_{PHZ}$  are the same as  $t_{dis}$ .
  - F.  $t_{PZL}$  and  $t_{PZH}$  are the same as  $t_{en}$ .
  - G. All parameters and waveforms are not applicable to all devices.

Figure 4. Load Circuit and Voltage Waveforms

## 9 Detailed Description


### 9.1 Overview

The SN74AUP1G07 device is a single buffer gate with open drain output that operates from 0.8 V to 3.6 V. The output of this single buffer/driver is open drain, and can be connected to other open-drain outputs to implement active-low wired-OR or active-high wired-AND functions.

The AUP family of devices has quiescent power consumption less than 1 $\mu$ A and comes in the ultra small DPW package. The DPW package technology is a major breakthrough in IC packaging. Its tiny 0.64 mm square footprint saves significant board space over other package options while still retaining the traditional manufacturing friendly lead pitch of 0.5 mm.

This device is fully specified for partial-power-down applications using I<sub>off</sub>. The I<sub>off</sub> circuitry disables the outputs, preventing damaging current backflow through the device when it is powered down. The I<sub>off</sub> feature also allows for live insertion.

### 9.2 Functional Block Diagram



### 9.3 Feature Description

- Wide operating V<sub>CC</sub> range of 0.8 V to 3.6 V
- 3.6-V I/O tolerant to support down translation
- Input hysteresis allows slow input transition and better switching noise immunity at the input
- I<sub>off</sub> feature allows voltages on the inputs and outputs when V<sub>CC</sub> is 0 V
- Low noise due to slower edge rates

### 9.4 Device Functional Modes

**Table 1. Function Table**


| INPUT<br>A | OUTPUT<br>Y |
|------------|-------------|
| H          | H/Z         |
| L          | L           |

## 10 Application and Implementation

### 10.1 Application Information

The AUP family is TI's premier solution to the industry's low-power needs in battery-powered portable applications. This family ensures a very low static and dynamic power consumption across the entire  $V_{CC}$  range of 0.8 V to 3.6 V, resulting in an increased battery life. This product also maintains excellent signal integrity. It has a small amount of hysteresis built in allowing for slower or noisy input signals. The lowered drive produces slower edges and prevents overshoot and undershoot on the outputs.

### 10.2 Typical Application



**Figure 5. Typical Application Schematic**

#### 10.2.1 Design Requirements



This device uses CMOS technology and has balanced output drive. Care should be taken to avoid bus contention because it can drive currents that would exceed maximum limits.

#### 10.2.2 Detailed Design Procedure

1. Recommended Input conditions
  - Rise time and fall time specs. See  $(\Delta t/\Delta V)$  in [Recommended Operating Conditions](#)
  - Specified high and low levels. See  $(V_{IH}$  and  $V_{IL})$  in [Recommended Operating Conditions](#)
  - Inputs are overvoltage tolerant allowing them to go as high as 3.6 V at any valid  $V_{CC}$
2. Recommend output conditions
  - Load currents should not exceed 20 mA on the output and 50 mA total for the part

## Typical Application (continued)

### 10.2.3 Application Curves



The AUP family of single gate logic makes excellent translators for the new lower voltage microprocessors that typically are powered from 0.8 V to 1.2 V. They can drop the voltage of peripheral drivers and accessories that are still powered by 3.3 V to the new uC power levels.

## 11 Power Supply Recommendations

The power supply can be any voltage between the Min and Max supply voltage rating located in the [Recommended Operating Conditions](#) table.

Each  $V_{CC}$  pin should have a good bypass capacitor to prevent power disturbance. For devices with a single supply, 0.1  $\mu\text{F}$  is recommended; if there are multiple  $V_{CC}$  pins, then 0.01  $\mu\text{F}$  or 0.022  $\mu\text{F}$  is recommended for each power pin. It is acceptable to parallel multiple bypass caps to reject different frequencies of noise. A 0.1  $\mu\text{F}$  and a 1  $\mu\text{F}$  are commonly used in parallel. The bypass capacitor should be installed as close to the power pin as possible for best results.

## 12 Layout

### 12.1 Layout Guidelines

In many cases, functions or parts of functions of digital logic devices are unused, for example, when only two inputs of a triple-input AND gate are used or only 3 of the 4 buffer gates are used. Such input pins should not be left unconnected because the undefined voltages at the outside connections result in undefined operational states. [Figure 8](#) specifies the rules that must be observed under all circumstances. All unused inputs of digital logic devices must be connected to a high or low bias to prevent them from floating. The logic level that should be applied to any particular unused input depends on the function of the device. Generally they will be tied to GND or  $V_{CC}$ , whichever makes more sense or is more convenient. It is generally acceptable to float outputs, unless the part is a transceiver. If the transceiver has an output enable pin, it will disable the output section of the part when asserted. This will not disable the input section of the I/Os, so they cannot float when disabled.

### 12.2 Layout Example




Figure 8. Layout Diagram

## 13 Device and Documentation Support

### 13.1 Trademarks

The  $I_{off}$  feature also allows for live insertion. is a trademark of others. All other trademarks are the property of their respective owners.

### 13.2 Electrostatic Discharge Caution



These devices have limited built-in ESD protection. The leads should be shorted together or the device placed in conductive foam during storage or handling to prevent electrostatic damage to the MOS gates.

### 13.3 Glossary

[SLYZ022](#) — *TI Glossary*.

This glossary lists and explains terms, acronyms, and definitions.

## 14 Mechanical, Packaging, and Orderable Information

The following pages include mechanical, packaging, and orderable information. This information is the most current data available for the designated devices. This data is subject to change without notice and revision of this document. For browser-based versions of this data sheet, refer to the left-hand navigation.

## PACKAGING INFORMATION

| Orderable part number             | Status<br>(1) | Material type<br>(2) | Package   Pins    | Package qty   Carrier | RoHS<br>(3) | Lead finish/<br>Ball material<br>(4) | MSL rating/<br>Peak reflow<br>(5) | Op temp (°C) | Part marking<br>(6)   |
|-----------------------------------|---------------|----------------------|-------------------|-----------------------|-------------|--------------------------------------|-----------------------------------|--------------|-----------------------|
| <a href="#">SN74AUP1G07DBVR</a>   | Active        | Production           | SOT-23 (DBV)   5  | 3000   LARGE T&R      | Yes         | NIPDAU   SN                          | Level-1-260C-UNLIM                | -40 to 85    | (H07F, H07R)          |
| SN74AUP1G07DBVR.B                 | Active        | Production           | SOT-23 (DBV)   5  | 3000   LARGE T&R      | Yes         | SN                                   | Level-1-260C-UNLIM                | -40 to 85    | (H07F, H07R)          |
| SN74AUP1G07DBVRE4                 | Active        | Production           | SOT-23 (DBV)   5  | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 85    | H07F                  |
| <a href="#">SN74AUP1G07DBVRG4</a> | Active        | Production           | SOT-23 (DBV)   5  | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 85    | H07F                  |
| SN74AUP1G07DBVRG4.B               | Active        | Production           | SOT-23 (DBV)   5  | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 85    | H07F                  |
| <a href="#">SN74AUP1G07DBVT</a>   | Active        | Production           | SOT-23 (DBV)   5  | 250   SMALL T&R       | Yes         | NIPDAU   SN                          | Level-1-260C-UNLIM                | -40 to 85    | (H07F, H07R)          |
| SN74AUP1G07DBVT.B                 | Active        | Production           | SOT-23 (DBV)   5  | 250   SMALL T&R       | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 85    | (H07F, H07R)          |
| <a href="#">SN74AUP1G07DCKR</a>   | Active        | Production           | SC70 (DCK)   5    | 3000   LARGE T&R      | Yes         | NIPDAU   SN                          | Level-1-260C-UNLIM                | -40 to 85    | (HV5, HVF, HVK, HV R) |
| SN74AUP1G07DCKR.B                 | Active        | Production           | SC70 (DCK)   5    | 3000   LARGE T&R      | Yes         | SN                                   | Level-1-260C-UNLIM                | -40 to 85    | (HV5, HVF, HVK, HV R) |
| <a href="#">SN74AUP1G07DCKRE4</a> | Active        | Production           | SC70 (DCK)   5    | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 85    | (HV5, HVF, HVK, HV R) |
| SN74AUP1G07DCKRE4.B               | Active        | Production           | SC70 (DCK)   5    | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 85    | (HV5, HVF, HVK, HV R) |
| <a href="#">SN74AUP1G07DCKT</a>   | Active        | Production           | SC70 (DCK)   5    | 250   SMALL T&R       | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 85    | (HV5, HVR)            |
| SN74AUP1G07DCKT.B                 | Active        | Production           | SC70 (DCK)   5    | 250   SMALL T&R       | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 85    | (HV5, HVR)            |
| SN74AUP1G07DCKTG4                 | Active        | Production           | SC70 (DCK)   5    | 250   SMALL T&R       | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 85    | HV5                   |
| SN74AUP1G07DCKTG4.B               | Active        | Production           | SC70 (DCK)   5    | 250   SMALL T&R       | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 85    | HV5                   |
| <a href="#">SN74AUP1G07DPWR</a>   | Active        | Production           | X2SON (DPW)   5   | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 85    | D4                    |
| SN74AUP1G07DPWR.B                 | Active        | Production           | X2SON (DPW)   5   | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 85    | D4                    |
| <a href="#">SN74AUP1G07DRLR</a>   | Active        | Production           | SOT-5X3 (DRL)   5 | 4000   LARGE T&R      | Yes         | NIPDAU   NIPDAUAG                    | Level-1-260C-UNLIM                | -40 to 85    | (HV7, HVR)            |
| SN74AUP1G07DRLR.B                 | Active        | Production           | SOT-5X3 (DRL)   5 | 4000   LARGE T&R      | Yes         | NIPDAUAG                             | Level-1-260C-UNLIM                | -40 to 85    | (HV7, HVR)            |
| <a href="#">SN74AUP1G07DRYR</a>   | Active        | Production           | SON (DRY)   6     | 5000   LARGE T&R      | Yes         | NIPDAU   NIPDAUAG                    | Level-1-260C-UNLIM                | -40 to 85    | HV                    |
| SN74AUP1G07DRYR.B                 | Active        | Production           | SON (DRY)   6     | 5000   LARGE T&R      | Yes         | NIPDAUAG                             | Level-1-260C-UNLIM                | -40 to 85    | HV                    |
| SN74AUP1G07DRYRG4                 | Active        | Production           | SON (DRY)   6     | 5000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 85    | HV                    |
| SN74AUP1G07DRYRG4.B               | Active        | Production           | SON (DRY)   6     | 5000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 85    | HV                    |
| <a href="#">SN74AUP1G07DSF2</a>   | Active        | Production           | SON (DSF)   6     | 5000   LARGE T&R      | Yes         | NIPDAU   NIPDAUAG                    | Level-1-260C-UNLIM                | -40 to 85    | HV                    |
| SN74AUP1G07DSF2.B                 | Active        | Production           | SON (DSF)   6     | 5000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 85    | HV                    |
| <a href="#">SN74AUP1G07DSFR</a>   | Active        | Production           | SON (DSF)   6     | 5000   LARGE T&R      | Yes         | NIPDAU   NIPDAUAG                    | Level-1-260C-UNLIM                | -40 to 85    | HV                    |

| Orderable part number           | Status<br>(1) | Material type<br>(2) | Package   Pins  | Package qty   Carrier | RoHS<br>(3) | Lead finish/<br>Ball material<br>(4) | MSL rating/<br>Peak reflow<br>(5) | Op temp (°C) | Part marking<br>(6) |
|---------------------------------|---------------|----------------------|-----------------|-----------------------|-------------|--------------------------------------|-----------------------------------|--------------|---------------------|
| SN74AUP1G07DSFR.B               | Active        | Production           | SON (DSF)   6   | 5000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 85    | HV                  |
| SN74AUP1G07DSFRG4               | Active        | Production           | SON (DSF)   6   | 5000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 85    | HV                  |
| SN74AUP1G07DSFRG4.B             | Active        | Production           | SON (DSF)   6   | 5000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 85    | HV                  |
| <a href="#">SN74AUP1G07YFPR</a> | Active        | Production           | DSBGA (YFP)   4 | 3000   LARGE T&R      | Yes         | SNAGCU                               | Level-1-260C-UNLIM                | -            | HV<br>N             |
| SN74AUP1G07YFPR.B               | Active        | Production           | DSBGA (YFP)   4 | 3000   LARGE T&R      | Yes         | SNAGCU                               | Level-1-260C-UNLIM                | -40 to 85    | HV<br>N             |
| <a href="#">SN74AUP1G07YZPR</a> | Active        | Production           | DSBGA (YZP)   5 | 3000   LARGE T&R      | Yes         | SNAGCU                               | Level-1-260C-UNLIM                | -40 to 85    | HVN                 |
| SN74AUP1G07YZPR.B               | Active        | Production           | DSBGA (YZP)   5 | 3000   LARGE T&R      | Yes         | SNAGCU                               | Level-1-260C-UNLIM                | -40 to 85    | HVN                 |

<sup>(1)</sup> **Status:** For more details on status, see our [product life cycle](#).

<sup>(2)</sup> **Material type:** When designated, preproduction parts are prototypes/experimental devices, and are not yet approved or released for full production. Testing and final process, including without limitation quality assurance, reliability performance testing, and/or process qualification, may not yet be complete, and this item is subject to further changes or possible discontinuation. If available for ordering, purchases will be subject to an additional waiver at checkout, and are intended for early internal evaluation purposes only. These items are sold without warranties of any kind.

<sup>(3)</sup> **RoHS values:** Yes, No, RoHS Exempt. See the [TI RoHS Statement](#) for additional information and value definition.

<sup>(4)</sup> **Lead finish/Ball material:** Parts may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead finish/Ball material values may wrap to two lines if the finish value exceeds the maximum column width.

<sup>(5)</sup> **MSL rating/Peak reflow:** The moisture sensitivity level ratings and peak solder (reflow) temperatures. In the event that a part has multiple moisture sensitivity ratings, only the lowest level per JEDEC standards is shown. Refer to the shipping label for the actual reflow temperature that will be used to mount the part to the printed circuit board.

<sup>(6)</sup> **Part marking:** There may be an additional marking, which relates to the logo, the lot trace code information, or the environmental category of the part.

Multiple part markings will be inside parentheses. Only one part marking contained in parentheses and separated by a "--" will appear on a part. If a line is indented then it is a continuation of the previous line and the two combined represent the entire part marking for that device.

**Important Information and Disclaimer:** The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.



## TAPE AND REEL INFORMATION



\*All dimensions are nominal

| Device            | Package Type | Package Drawing | Pins | SPQ  | Reel Diameter (mm) | Reel Width W1 (mm) | A0 (mm) | B0 (mm) | K0 (mm) | P1 (mm) | W (mm) | Pin1 Quadrant |
|-------------------|--------------|-----------------|------|------|--------------------|--------------------|---------|---------|---------|---------|--------|---------------|
| SN74AUP1G07DBVR   | SOT-23       | DBV             | 5    | 3000 | 178.0              | 8.4                | 3.2     | 3.2     | 1.4     | 4.0     | 8.0    | Q3            |
| SN74AUP1G07DBVRG4 | SOT-23       | DBV             | 5    | 3000 | 178.0              | 9.0                | 3.23    | 3.17    | 1.37    | 4.0     | 8.0    | Q3            |
| SN74AUP1G07DBVT   | SOT-23       | DBV             | 5    | 250  | 180.0              | 8.4                | 3.2     | 3.2     | 1.4     | 4.0     | 8.0    | Q3            |
| SN74AUP1G07DBVT   | SOT-23       | DBV             | 5    | 250  | 180.0              | 8.4                | 3.2     | 3.2     | 1.4     | 4.0     | 8.0    | Q3            |
| SN74AUP1G07DCKR   | SC70         | DCK             | 5    | 3000 | 180.0              | 8.4                | 2.3     | 2.5     | 1.2     | 4.0     | 8.0    | Q3            |
| SN74AUP1G07DCKR   | SC70         | DCK             | 5    | 3000 | 178.0              | 8.4                | 2.25    | 2.45    | 1.2     | 4.0     | 8.0    | Q3            |
| SN74AUP1G07DCKRE4 | SC70         | DCK             | 5    | 3000 | 178.0              | 9.2                | 2.4     | 2.4     | 1.22    | 4.0     | 8.0    | Q3            |
| SN74AUP1G07DCKRE4 | SC70         | DCK             | 5    | 3000 | 180.0              | 8.4                | 2.47    | 2.3     | 1.25    | 4.0     | 8.0    | Q3            |
| SN74AUP1G07DCKT   | SC70         | DCK             | 5    | 250  | 178.0              | 9.2                | 2.4     | 2.4     | 1.22    | 4.0     | 8.0    | Q3            |
| SN74AUP1G07DCKT   | SC70         | DCK             | 5    | 250  | 180.0              | 8.4                | 2.47    | 2.3     | 1.25    | 4.0     | 8.0    | Q3            |
| SN74AUP1G07DCKTG4 | SC70         | DCK             | 5    | 250  | 178.0              | 9.2                | 2.4     | 2.4     | 1.22    | 4.0     | 8.0    | Q3            |
| SN74AUP1G07DPWR   | X2SON        | DPW             | 5    | 3000 | 178.0              | 8.4                | 0.91    | 0.91    | 0.5     | 2.0     | 8.0    | Q3            |
| SN74AUP1G07DRLR   | SOT-5X3      | DRL             | 5    | 4000 | 180.0              | 8.4                | 1.98    | 1.78    | 0.69    | 4.0     | 8.0    | Q3            |
| SN74AUP1G07DRYR   | SON          | DRY             | 6    | 5000 | 180.0              | 9.5                | 1.15    | 1.6     | 0.75    | 4.0     | 8.0    | Q1            |
| SN74AUP1G07DRYRG4 | SON          | DRY             | 6    | 5000 | 180.0              | 9.5                | 1.15    | 1.6     | 0.75    | 4.0     | 8.0    | Q1            |
| SN74AUP1G07DSF2   | SON          | DSF             | 6    | 5000 | 180.0              | 8.4                | 1.16    | 1.16    | 0.5     | 4.0     | 8.0    | Q3            |

| Device            | Package Type | Package Drawing | Pins | SPQ  | Reel Diameter (mm) | Reel Width W1 (mm) | A0 (mm) | B0 (mm) | K0 (mm) | P1 (mm) | W (mm) | Pin1 Quadrant |
|-------------------|--------------|-----------------|------|------|--------------------|--------------------|---------|---------|---------|---------|--------|---------------|
| SN74AUP1G07DSFR   | SON          | DSF             | 6    | 5000 | 180.0              | 8.4                | 1.16    | 1.16    | 0.5     | 4.0     | 8.0    | Q2            |
| SN74AUP1G07DSFRG4 | SON          | DSF             | 6    | 5000 | 180.0              | 8.4                | 1.16    | 1.16    | 0.5     | 4.0     | 8.0    | Q2            |
| SN74AUP1G07YFPR   | DSBGA        | YFP             | 4    | 3000 | 178.0              | 9.2                | 0.89    | 0.89    | 0.58    | 4.0     | 8.0    | Q1            |
| SN74AUP1G07YZPR   | DSBGA        | YZP             | 5    | 3000 | 178.0              | 9.2                | 1.02    | 1.52    | 0.63    | 4.0     | 8.0    | Q1            |

## TAPE AND REEL BOX DIMENSIONS



\*All dimensions are nominal

| Device            | Package Type | Package Drawing | Pins | SPQ  | Length (mm) | Width (mm) | Height (mm) |
|-------------------|--------------|-----------------|------|------|-------------|------------|-------------|
| SN74AUP1G07DBVR   | SOT-23       | DBV             | 5    | 3000 | 208.0       | 191.0      | 35.0        |
| SN74AUP1G07DBVRG4 | SOT-23       | DBV             | 5    | 3000 | 180.0       | 180.0      | 18.0        |
| SN74AUP1G07DBVT   | SOT-23       | DBV             | 5    | 250  | 210.0       | 185.0      | 35.0        |
| SN74AUP1G07DBVT   | SOT-23       | DBV             | 5    | 250  | 210.0       | 185.0      | 35.0        |
| SN74AUP1G07DCKR   | SC70         | DCK             | 5    | 3000 | 210.0       | 185.0      | 35.0        |
| SN74AUP1G07DCKR   | SC70         | DCK             | 5    | 3000 | 208.0       | 191.0      | 35.0        |
| SN74AUP1G07DCKRE4 | SC70         | DCK             | 5    | 3000 | 180.0       | 180.0      | 18.0        |
| SN74AUP1G07DCKRE4 | SC70         | DCK             | 5    | 3000 | 202.0       | 201.0      | 28.0        |
| SN74AUP1G07DCKT   | SC70         | DCK             | 5    | 250  | 180.0       | 180.0      | 18.0        |
| SN74AUP1G07DCKT   | SC70         | DCK             | 5    | 250  | 202.0       | 201.0      | 28.0        |
| SN74AUP1G07DCKTG4 | SC70         | DCK             | 5    | 250  | 180.0       | 180.0      | 18.0        |
| SN74AUP1G07DPWR   | X2SON        | DPW             | 5    | 3000 | 205.0       | 200.0      | 33.0        |
| SN74AUP1G07DRLR   | SOT-5X3      | DRL             | 5    | 4000 | 202.0       | 201.0      | 28.0        |
| SN74AUP1G07DRYR   | SON          | DRY             | 6    | 5000 | 184.0       | 184.0      | 19.0        |
| SN74AUP1G07DRYRG4 | SON          | DRY             | 6    | 5000 | 184.0       | 184.0      | 19.0        |
| SN74AUP1G07DSF2   | SON          | DSF             | 6    | 5000 | 210.0       | 185.0      | 35.0        |
| SN74AUP1G07DSFR   | SON          | DSF             | 6    | 5000 | 210.0       | 185.0      | 35.0        |
| SN74AUP1G07DSFRG4 | SON          | DSF             | 6    | 5000 | 210.0       | 185.0      | 35.0        |

---

| Device          | Package Type | Package Drawing | Pins | SPQ  | Length (mm) | Width (mm) | Height (mm) |
|-----------------|--------------|-----------------|------|------|-------------|------------|-------------|
| SN74AUP1G07YFPR | DSBGA        | YFP             | 4    | 3000 | 220.0       | 220.0      | 35.0        |
| SN74AUP1G07YZPR | DSBGA        | YZP             | 5    | 3000 | 220.0       | 220.0      | 35.0        |

## GENERIC PACKAGE VIEW

**DPW 5**




**X2SON - 0.4 mm max height**

PLASTIC SMALL OUTLINE - NO LEAD



Images above are just a representation of the package family, actual package may vary.  
Refer to the product data sheet for package details.

4211218-3/D



4223102/D 03/2022


## NOTES:

1. All linear dimensions are in millimeters. Any dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.
2. This drawing is subject to change without notice.
3. The size and shape of this feature may vary.

**DPW0005A**

**X2SON - 0.4 mm max height**

PLASTIC SMALL OUTLINE - NO LEAD



LAND PATTERN EXAMPLE  
SOLDER MASK DEFINED  
SCALE:60X

4223102/D 03/2022

NOTES: (continued)


4. This package is designed to be soldered to a thermal pad on the board. For more information, refer to QFN/SON PCB application note in literature No. SLUA271 ([www.ti.com/lit/slua271](http://www.ti.com/lit/slua271)).

# EXAMPLE STENCIL DESIGN

DPW0005A

X2SON - 0.4 mm max height

PLASTIC SMALL OUTLINE - NO LEAD



SOLDER PASTE EXAMPLE  
BASED ON 0.1 mm THICK STENCIL

EXPOSED PAD 3  
92% PRINTED SOLDER COVERAGE BY AREA UNDER PACKAGE  
SCALE:100X

4223102/D 03/2022

NOTES: (continued)

5. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.



YZP0005



# PACKAGE OUTLINE

DSBGA - 0.5 mm max height

DIE SIZE BALL GRID ARRAY



D: Max = 1.418 mm, Min = 1.358 mm  
E: Max = 0.918 mm, Min = 0.858 mm

4219492/A 05/2017

## NOTES:


1. All linear dimensions are in millimeters. Any dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.
2. This drawing is subject to change without notice.

# EXAMPLE BOARD LAYOUT


YZP0005

DSBGA - 0.5 mm max height

DIE SIZE BALL GRID ARRAY



LAND PATTERN EXAMPLE  
SCALE:40X



SOLDER MASK DETAILS  
NOT TO SCALE

4219492/A 05/2017

NOTES: (continued)


- Final dimensions may vary due to manufacturing tolerance considerations and also routing constraints. For more information, see Texas Instruments literature number SNVA009 ([www.ti.com/lit/snva009](http://www.ti.com/lit/snva009)).

## EXAMPLE STENCIL DESIGN

YZP0005

DSBGA - 0.5 mm max height

DIE SIZE BALL GRID ARRAY



SOLDER PASTE EXAMPLE  
BASED ON 0.1 mm THICK STENCIL  
SCALE:40X

4219492/A 05/2017

NOTES: (continued)

4. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release.




YFP0004



# PACKAGE OUTLINE

DSBGA - 0.5 mm max height

DIE SIZE BALL GRID ARRAY




D: Max = 0.79 mm, Min = 0.73 mm

E: Max = 0.79 mm, Min = 0.73 mm


4223507/A 01/2017

## NOTES:

1. All linear dimensions are in millimeters. Any dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.
2. This drawing is subject to change without notice.



LAND PATTERN EXAMPLE  
EXPOSED METAL SHOWN  
SCALE:50X



SOLDER MASK DETAILS  
NOT TO SCALE

4223507/A 01/2017

NOTES: (continued)


- Final dimensions may vary due to manufacturing tolerance considerations and also routing constraints. For more information, see Texas Instruments literature number SNVA009 ([www.ti.com/lit/snva009](http://www.ti.com/lit/snva009)).

## EXAMPLE STENCIL DESIGN

YFP0004

DSBGA - 0.5 mm max height

DIE SIZE BALL GRID ARRAY



SOLDER PASTE EXAMPLE  
BASED ON 0.1 mm THICK STENCIL  
SCALE:50X

4223507/A 01/2017

NOTES: (continued)

4. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release.




4214834/G 11/2024

## NOTES:

1. All linear dimensions are in millimeters. Any dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.
2. This drawing is subject to change without notice.
3. Reference JEDEC MO-203.
4. Support pin may differ or may not be present.
5. Lead width does not comply with JEDEC.
6. Body dimensions do not include mold flash, protrusions, or gate burrs. Mold flash, protrusions, or gate burrs shall not exceed 0.25mm per side



LAND PATTERN EXAMPLE  
EXPOSED METAL SHOWN  
SCALE:18X



SOLDER MASK DETAILS

4214834/G 11/2024

NOTES: (continued)

7. Publication IPC-7351 may have alternate designs.
8. Solder mask tolerances between and around signal pads can vary based on board fabrication site.



SOLDER PASTE EXAMPLE  
BASED ON 0.125 THICK STENCIL  
SCALE:18X

4214834/G 11/2024

NOTES: (continued)

9. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.
10. Board assembly site may have different recommendations for stencil design.



## SOT-23 - 1.45 mm max height

## SMALL OUTLINE TRANSISTOR




1. All linear dimensions are in millimeters. Any dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.
2. This drawing is subject to change without notice.
3. Reference JEDEC MO-178.
4. Body dimensions do not include mold flash, protrusions, or gate burrs. Mold flash, protrusions, or gate burrs shall not exceed 0.25 mm per side.
5. Support pin may differ or may not be present.


**DBV0005A**

**SOT-23 - 1.45 mm max height**

SMALL OUTLINE TRANSISTOR



LAND PATTERN EXAMPLE  
EXPOSED METAL SHOWN  
SCALE:15X



## SOLDER MASK DETAILS

4214839/K 08/2024

NOTES: (continued)

6. Publication IPC-7351 may have alternate designs.  
7. Solder mask tolerances between and around signal pads can vary based on board fabrication site.

## EXAMPLE STENCIL DESIGN

DBV0005A

SOT-23 - 1.45 mm max height

SMALL OUTLINE TRANSISTOR



SOLDER PASTE EXAMPLE  
BASED ON 0.125 mm THICK STENCIL  
SCALE:15X

4214839/K 08/2024

NOTES: (continued)

8. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.
9. Board assembly site may have different recommendations for stencil design.

## GENERIC PACKAGE VIEW

**DRY 6**

**USON - 0.6 mm max height**

PLASTIC SMALL OUTLINE - NO LEAD



Images above are just a representation of the package family, actual package may vary.  
Refer to the product data sheet for package details.

4207181/G




# EXAMPLE BOARD LAYOUT


DRY0006A

USON - 0.6 mm max height

PLASTIC SMALL OUTLINE - NO LEAD



**LAND PATTERN EXAMPLE**  
1:1 RATIO WITH PKG SOLDER PADS  
EXPOSED METAL SHOWN  
SCALE:40X



**SOLDER MASK DETAILS**

4222894/A 01/2018

NOTES: (continued)


3. For more information, see QFN/SON PCB application report in literature No. SLUA271 ([www.ti.com/lit/sluea271](http://www.ti.com/lit/sluea271)).

## EXAMPLE STENCIL DESIGN

DRY0006A

USON - 0.6 mm max height

PLASTIC SMALL OUTLINE - NO LEAD



SOLDER PASTE EXAMPLE  
BASED ON 0.075 - 0.1 mm THICK STENCIL  
SCALE:40X

4222894/A 01/2018

NOTES: (continued)

4. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.



**DSF0006A**


4220597/B 06/2022

# EXAMPLE BOARD LAYOUT


DSF0006A

X2SON - 0.4 mm max height

PLASTIC SMALL OUTLINE - NO LEAD



LAND PATTERN EXAMPLE  
EXPOSED METAL SHOWN  
SCALE:40X



SOLDER MASK DETAILS

4220597/B 06/2022

NOTES: (continued)


4. For more information, see Texas Instruments literature number SLUA271 ([www.ti.com/lit/slue271](http://www.ti.com/lit/slue271)).

## EXAMPLE STENCIL DESIGN

DSF0006A

X2SON - 0.4 mm max height

PLASTIC SMALL OUTLINE - NO LEAD



SOLDER PASTE EXAMPLE  
BASED ON 0.09 mm THICK STENCIL

PRINTED SOLDER COVERAGE BY AREA UNDER PACKAGE  
SCALE:40X

4220597/B 06/2022

4. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.



**SOT - 0.6 mm max height**

Technical drawing of a 5-pin D-subminiature connector, showing front, side, and end views with dimensions and tolerances.

**Front View:**

- Overall width: 1.5
- Overall height: 1.7
- Pin 1 ID Area: Indicated by a dashed line and label.
- Pin 1: Located at the top left.
- Pin 2: Located below Pin 1.
- Pin 3: Located below Pin 2.
- Pin 4: Located at the bottom right.
- Pin 5: Located at the top right.
- Dimensions: 2X 0.5 (Pin 1 to Pin 2), 2X 1 (Pin 2 to Pin 3), 1.3 (Pin 1 to Pin 4), 1.1 (Pin 2 to Pin 4), 5X 0.3 (Pin 4 to Pin 5), 0.1 (Pin 5 to Pin 4).
- Feature A: Located at the top right corner.
- Feature B: Located at the bottom left corner.
- Feature C: Located at the bottom right corner.
- Feature D: Located at the top left corner.
- Feature E: Located at the bottom center.
- Feature F: Located at the top center.
- Feature G: Located at the bottom right corner.
- Feature H: Located at the top right corner.
- Feature I: Located at the bottom right corner.
- Feature J: Located at the top right corner.
- Feature K: Located at the bottom right corner.
- Feature L: Located at the top right corner.
- Feature M: Located at the bottom right corner.
- Feature N: Located at the top right corner.
- Feature O: Located at the bottom right corner.
- Feature P: Located at the top right corner.
- Feature Q: Located at the bottom right corner.
- Feature R: Located at the top right corner.
- Feature S: Located at the bottom right corner.
- Feature T: Located at the top right corner.
- Feature U: Located at the bottom right corner.
- Feature V: Located at the top right corner.
- Feature W: Located at the bottom right corner.
- Feature X: Located at the top right corner.
- Feature Y: Located at the bottom right corner.
- Feature Z: Located at the top right corner.

**Side View:**

- Overall width: 1.7
- Overall height: 1.5
- Feature A: Located at the top right corner.
- Feature B: Located at the bottom left corner.
- Feature C: Located at the bottom right corner.
- Feature D: Located at the top left corner.
- Feature E: Located at the bottom center.
- Feature F: Located at the top center.
- Feature G: Located at the bottom right corner.
- Feature H: Located at the top right corner.
- Feature I: Located at the bottom right corner.
- Feature J: Located at the top right corner.
- Feature K: Located at the bottom right corner.
- Feature L: Located at the top right corner.
- Feature M: Located at the bottom right corner.
- Feature N: Located at the top right corner.
- Feature O: Located at the bottom right corner.
- Feature P: Located at the top right corner.
- Feature Q: Located at the bottom right corner.
- Feature R: Located at the top right corner.
- Feature S: Located at the bottom right corner.
- Feature T: Located at the top right corner.
- Feature U: Located at the bottom right corner.
- Feature V: Located at the top right corner.
- Feature W: Located at the bottom right corner.
- Feature X: Located at the top right corner.
- Feature Y: Located at the bottom right corner.
- Feature Z: Located at the top right corner.

**End View:**

- Overall width: 0.05 TYP
- Overall height: 0.00
- Feature A: Located at the top right corner.
- Feature B: Located at the bottom left corner.
- Feature C: Located at the bottom right corner.
- Feature D: Located at the top left corner.
- Feature E: Located at the bottom center.
- Feature F: Located at the top center.
- Feature G: Located at the bottom right corner.
- Feature H: Located at the top right corner.
- Feature I: Located at the bottom right corner.
- Feature J: Located at the top right corner.
- Feature K: Located at the bottom right corner.
- Feature L: Located at the top right corner.
- Feature M: Located at the bottom right corner.
- Feature N: Located at the top right corner.
- Feature O: Located at the bottom right corner.
- Feature P: Located at the top right corner.
- Feature Q: Located at the bottom right corner.
- Feature R: Located at the top right corner.
- Feature S: Located at the bottom right corner.
- Feature T: Located at the top right corner.
- Feature U: Located at the bottom right corner.
- Feature V: Located at the top right corner.
- Feature W: Located at the bottom right corner.
- Feature X: Located at the top right corner.
- Feature Y: Located at the bottom right corner.
- Feature Z: Located at the top right corner.

**Notes:**

- NOTE 3: Located near the top right corner.
- 2X 0° - 10°: Located near the top right corner.
- 2X 4° - 15°: Located near the top right corner.
- 0.6 MAX: Located near the top right corner.
- 5X 0.18 / 0.08: Located near the top right corner.
- SEATING PLANE: Located near the top right corner.
- 0.05 C: Located near the top right corner.
- SYMM: Located near the top right corner.
- 5X 0.27 / 0.15: Located near the top right corner.
- 5X 0.4 / 0.2: Located near the top right corner.

**Feature Callouts:**

- A: Located at the top right corner.
- B: Located at the bottom left corner.
- C: Located at the bottom right corner.
- D: Located at the top left corner.
- E: Located at the bottom center.
- F: Located at the top center.
- G: Located at the bottom right corner.
- H: Located at the top right corner.
- I: Located at the bottom right corner.
- J: Located at the top right corner.
- K: Located at the bottom right corner.
- L: Located at the top right corner.
- M: Located at the bottom right corner.
- N: Located at the top right corner.
- O: Located at the bottom right corner.
- P: Located at the top right corner.
- Q: Located at the bottom right corner.
- R: Located at the top right corner.
- S: Located at the bottom right corner.
- T: Located at the top right corner.
- U: Located at the bottom right corner.
- V: Located at the top right corner.
- W: Located at the bottom right corner.
- X: Located at the top right corner.
- Y: Located at the bottom right corner.
- Z: Located at the top right corner.


1. All linear dimensions are in millimeters. Any dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.
2. This drawing is subject to change without notice.
3. This dimension does not include mold flash, protrusions, or gate burrs. Mold flash, protrusions, or gate burrs shall not exceed 0.15 mm per side.
4. Reference JEDEC registration MO-293 Variation UAAD-1

# EXAMPLE BOARD LAYOUT


DRL0005A

SOT - 0.6 mm max height

PLASTIC SMALL OUTLINE



LAND PATTERN EXAMPLE  
SCALE:30X



SOLDERMASK DETAILS

4220753/E 11/2024

NOTES: (continued)


5. Publication IPC-7351 may have alternate designs.
6. Solder mask tolerances between and around signal pads can vary based on board fabrication site.

## EXAMPLE STENCIL DESIGN

DRL0005A

SOT - 0.6 mm max height

PLASTIC SMALL OUTLINE



SOLDER PASTE EXAMPLE  
BASED ON 0.1 mm THICK STENCIL  
SCALE:30X

4220753/E 11/2024

NOTES: (continued)

7. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.
8. Board assembly site may have different recommendations for stencil design.

## IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATASHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, regulatory or other requirements.

These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you fully indemnify TI and its representatives against any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to [TI's Terms of Sale](#), [TI's General Quality Guidelines](#), or other applicable terms available either on [ti.com](https://www.ti.com) or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products. Unless TI explicitly designates a product as custom or customer-specified, TI products are standard, catalog, general purpose devices.

TI objects to and rejects any additional or different terms you may propose.

Copyright © 2026, Texas Instruments Incorporated

Last updated 10/2025