

## 3-V to 5.5-V Multichannel RS-232 Compatible Line Driver and Receiver

### 1 Features

- Operates with 3-V to 5.5-V  $V_{CC}$  supply
- Always-active noninverting receiver output (ROUT2B)
- Low standby current: 1  $\mu$ A typical
- External capacitors:  $4 \times 0.1 \mu$ F
- Accepts 5-V logic input with 3.3-V supply
- Inter-operable with SN65C3238, SN75C3238
- Supports operation from 250 kbit/s to 1 Mbit/s
- RS-232 Bus-pin esd protection exceeds  $\pm 15$  kV using human-body model (HBM)

### 2 Applications

- [Battery-powered systems](#)
- [PDAs](#)
- [Notebooks](#)
- [Laptops](#)
- [Palmtop PCs](#)
- [Hand-held equipment](#)


### 3 Description

The TRSF3243 consists of three line drivers, five line receivers, and a dual charge-pump circuit with  $\pm 15$ -kV ESD protection pin to pin (serial-port connection pins, including GND). This device provides the electrical interface between an asynchronous communication controller and the serial-port connector. The charge pump and four small external capacitors allow operation from a single 3-V to 5.5-V supply. In addition, this device includes an always-active noninverting output (ROUT2B), which allows applications using the ring indicator to transmit data while the device is powered down. The device operates at data signaling rates up to 1 Mbit/s and an increased slew-rate range of 24 V/ $\mu$ s to 150 V/ $\mu$ s.

#### Package Information

| PART NUMBER | PACKAGE <sup>(1)</sup> | BODY SIZE (NOM)           |
|-------------|------------------------|---------------------------|
| TRSF3243    | SSOP (DB)              | 10.20 mm $\times$ 5.30 mm |
|             | SOIC (DW)              | 17.90 mm $\times$ 7.50mm  |
|             | TSSOP (PW)             | 9.70 mm $\times$ 4.40 mm  |

(1) For all available packages, see the orderable addendum at the end of the data sheet.



**Simplified Circuit**



## Table of Contents


|  |          |   |           |
|--|----------|---|-----------|
| <b>1 Features</b> .....                        | <b>1</b> | 6.9 Electrical Characteristics: Auto-Powerdown.....         | <b>7</b>  |
| <b>2 Applications</b> .....                    | <b>1</b> | 6.10 Switching Characteristics: Auto-Powerdown.....         | <b>7</b>  |
| <b>3 Description</b> .....                     | <b>1</b> | <b>Parameter Measurement Information</b> .....              | <b>8</b>  |
| <b>4 Revision History</b> .....                | <b>2</b> | <b>7 Detailed Description</b> .....                         | <b>12</b> |
| <b>5 Pin Configuration and Functions</b> ..... | <b>3</b> | 7.1 Overview.....   | <b>12</b> |
| <b>6 Specifications</b> .....                  | <b>4</b> | 7.2 Device Functional Modes.....                            | <b>12</b> |
| 6.1 Absolute Maximum Ratings.....              | <b>4</b> | <b>8 Device and Documentation Support</b> .....             | <b>14</b> |
| 6.2 Recommended Operating Conditions.....      | <b>4</b> | 8.1 Receiving Notification of Documentation Updates....     | <b>14</b> |
| 6.3 Thermal Information.....                   | <b>4</b> | 8.2 Support Resources.....                                  | <b>14</b> |
| 6.4 Electrical Characteristics.....            | <b>5</b> | 8.3 Trademarks.....   | <b>14</b> |
| 6.5 Electrical Characteristics: Driver.....    | <b>5</b> | 8.4 Electrostatic Discharge Caution.....                    | <b>14</b> |
| 6.6 Switching Characteristics: Driver.....     | <b>6</b> | 8.5 Glossary.....   | <b>14</b> |
| 6.7 Electrical Characteristics: Receiver.....  | <b>6</b> | <b>9 Mechanical, Packaging, and Orderable Information..</b> | <b>14</b> |
| 6.8 Switching Characteristics: Receiver.....   | <b>6</b> |   |           |

## 4 Revision History

NOTE: Page numbers for previous revisions may differ from page numbers in the current version.

| <b>Changes from Revision A (September 2008) to Revision B (October 2022)</b>  | <b>Page</b> |
|---|-------------|
| • Deleted the <i>Ordering Information</i> table.....  | <b>1</b>    |
| • Changed the <i>Package Information</i> table.....   | <b>1</b>    |
| • Added the <i>Simplified Schematic</i> .....   | <b>1</b>    |
| • Added the <i>Pin Configuration and Functions</i> .....  | <b>3</b>    |
| • Added the <i>Thermal Information</i> table.....   | <b>4</b>    |
| • Changed the I <sub>CC</sub> Supply current auto-powerdown disabled MAX value from 1 mA to 1.2 mA in the <i>Electrical Characteristics</i> ..... | <b>5</b>    |
| • Added the <i>Detailed Description</i> section.....  | <b>12</b>   |

## 5 Pin Configuration and Functions



**Figure 5-1. DB, DW, or PW Package, 28 Pin (SSOP, SOIC, TSSOP)  
(Top View)**

**Table 5-1. Pin Functions**

| PIN |                 | TYPE | DESCRIPTION  |
|-----|-----------------|------|--|
| NO. | NAME            |      |  |
| 1   | C2+             | —    | Positive terminal of the voltage-doubler charge-pump capacitor |
| 2   | C2-             | —    | Negative terminal of the voltage-doubler charge-pump capacitor |
| 3   | V-              | —    | Negative charge pump output voltage                            |
| 4   | RIN1            | I    | RS-232 receiver inputs   |
| 5   | RIN2            |      |  |
| 6   | RIN3            |      |  |
| 7   | RIN4            |      |  |
| 8   | RIN5            |      |  |
| 9   | DOUT1           | O    | RS-232 driver outputs  |
| 10  | DOUT2           |      |  |
| 11  | DOUT3           |      |  |
| 12  | DIN3            | I    | Driver inputs  |
| 13  | DIN2            |      |  |
| 14  | DIN1            |      |  |
| 15  | ROUT5           | O    | Receiver outputs   |
| 16  | ROUT4           |      |  |
| 17  | ROUT3           |      |  |
| 18  | ROUT2           |      |  |
| 19  | ROUT1           |      |  |
| 20  | ROUT2B          | —    | Always-active noninverting receiver output;                    |
| 21  | INVALID         | O    | Invalid Output Pin   |
| 22  | FORCEOFF        | I    | Auto Powerdown Control input (Refer to Truth Table)            |
| 23  | FORCEON         | I    | Auto Powerdown Control input (Refer to Truth Table)            |
| 24  | C1-             | —    | Negative terminal of the voltage-doubler charge-pump capacitor |
| 25  | GND             | —    | Ground   |
| 26  | V <sub>CC</sub> | —    | 3-V to 5.5-V supply voltage                                    |
| 27  | V+              | —    | Positive charge pump output voltage                            |
| 28  | C1+             | —    | Positive terminal of the voltage-doubler charge-pump capacitor |

## 6 Specifications

### 6.1 Absolute Maximum Ratings

over operating free-air temperature range (unless otherwise noted) <sup>(1)</sup>

|                  |   |                             | MIN   | MAX  | UNIT |
|------------------|---|-----------------------------|-------|------|------|
| V <sub>CC</sub>  | Supply voltage range <sup>(2)</sup>                 |                             | −0.3  | 6    | V    |
| V+               | Positive-output supply voltage range <sup>(2)</sup> |                             | −0.3  | 7    | V    |
| V−               | Negative-output supply voltage range <sup>(2)</sup> |                             | 0.3   | −7   | V    |
| V+ − V−          | Supply voltage difference <sup>(2)</sup>            |                             |       | 13   | V    |
| V <sub>I</sub>   | Input voltage range                                 | Driver ( FORCEOFF, FORCEON) | −0.3  | 6    | V    |
|                  |   | Receiver                    | −25   | 25   |      |
| V <sub>O</sub>   | Output voltage range                                | Driver                      | −13.2 | 13.2 | V    |
| T <sub>J</sub>   | Operating virtual junction temperature              |                             |       | 150  | °C   |
| T <sub>stg</sub> | Storage temperature range                           |                             | −65   | 150  | °C   |

- (1) Stresses beyond those listed under "absolute maximum ratings" may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated under "recommended operating conditions" is not implied. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability.
- (2) All voltages are with respect to network GND.

### 6.2 Recommended Operating Conditions

see Figure 7-6 <sup>(1)</sup>

|                 |   | MIN                     | NOM                     | MAX | UNIT |
|-----------------|---|-------------------------|-------------------------|-----|------|
| Supply voltage  |   | V <sub>CC</sub> = 3.3 V | 3                       | 3.3 | V    |
|                 |   | V <sub>CC</sub> = 5 V   | 4.5                     | 5   |      |
| V <sub>IH</sub> | Driver and control high-level input voltage | DIN, FORCEOFF, FORCEON  | V <sub>CC</sub> = 3.3 V | 2   | V    |
|                 |   |                         | V <sub>CC</sub> = 5 V   | 2.4 |      |
| V <sub>IL</sub> | Driver and control low-level input voltage  | DIN, FORCEOFF, FORCEON  |                         | 0.8 | V    |
| V <sub>I</sub>  | Driver and control input voltage            | DIN, FORCEOFF, FORCEON  |                         | 0   | V    |
| V <sub>I</sub>  | Receiver input voltage                      |                         |                         | −25 | V    |
| T <sub>A</sub>  | Operating free-air temperature              | TRSF3243I               | −40                     | 85  | °C   |
|                 |   | TRSF3243C               | 0                       | 70  |      |

- (1) Test conditions are C1–C4 = 0.1 μF at V<sub>CC</sub> = 3.3 V ± 0.3 V; C1 = 0.047 μF, C2–C4 = 0.33 μF at V<sub>CC</sub> = 5 V ± 0.5 V.

### 6.3 Thermal Information

| THERMAL METRIC <sup>(1)</sup> |  | TSSOP (PW) | SOIC (DW) | DB (SSOP) | UNIT |
|-------------------------------|--|------------|-----------|-----------|------|
|                               |  | 28 PINS    | 28 PINS   | 28 PINS   |      |
| R <sub>θJA</sub>              | Junction-to-ambient thermal resistance       | 70.3       | 59.0      | 76.1      | °C/W |
| R <sub>θJC(top)</sub>         | Junction-to-case (top) thermal resistance    | 21.0       | 28.8      | 35.8      | °C/W |
| R <sub>θJB</sub>              | Junction-to-board thermal resistance         | 29.2       | 30.3      | 37.4      | °C/W |
| Ψ <sub>JT</sub>               | Junction-to-top characterization parameter   | 1.3        | 7.8       | 7.4       | °C/W |
| Ψ <sub>JB</sub>               | Junction-to-board characterization parameter | 28.8       | 30.0      | 37.0      | °C/W |
| R <sub>θJC(bot)</sub>         | Junction-to-case (bottom) thermal resistance | N/A        | N/A       | N/A       | °C/W |

- (1) For more information about traditional and new thermal metrics, see the [Semiconductor and IC package thermal metrics](#) application report.

## 6.4 Electrical Characteristics

over recommended ranges of supply voltage and operating free-air temperature (unless otherwise noted) (see [Figure 7-6](#)) <sup>(2)</sup>

| PARAMETER       |                       | TEST CONDITIONS         | MIN  | TYP <sup>(1)</sup> | MAX | UNIT |
|-----------------|-----------------------|-------------------------|--|--------------------|-----|------|
| I <sub>I</sub>  | Input leakage current | FORCEOFF, FORCEON       |  | ±0.01              | ±1  | μA   |
| I <sub>CC</sub> | Supply current        | Auto-powerdown disabled | No load,<br>FORCEOFF and FORCEON = V <sub>CC</sub><br>For DB and PW package                                      | 0.3                | 1.2 | mA   |
|                 |                       | Auto-powerdown disabled | No load,<br>FORCEOFF and FORCEON = V <sub>CC</sub><br>For DW package   | 0.3                | 1   | mA   |
|                 |                       | Powered off             | No load, FORCEOFF = GND  | 1                  | 10  | μA   |
|                 |                       | Auto-powerdown enabled  | No load, FORCEOFF = V <sub>CC</sub> ,<br>FORCEON = GND,<br>All RIN are open or grounded,<br>All DIN are grounded | 1                  | 10  |      |

(1) All typical values are at V<sub>CC</sub> = 3.3 V or V<sub>CC</sub> = 5 V, and T<sub>A</sub> = 25°C.

(2) Test conditions are C1–C4 = 0.1 μF at V<sub>CC</sub> = 3.3 V ± 0.3 V; C1 = 0.047 μF, C2–C4 = 0.33 μF at V<sub>CC</sub> = 5 V ± 0.5 V.

## 6.5 Electrical Characteristics: Driver

over recommended ranges of supply voltage and operating free-air temperature (unless otherwise noted) (see [Figure 7-6](#))

| PARAMETER        |   | TEST CONDITIONS <sup>(3)</sup>  | MIN | TYP <sup>(1)</sup> | MAX | UNIT |
|------------------|---|---|-----|--------------------|-----|------|
| V <sub>OH</sub>  | High-level output voltage                   | All DOUT at R <sub>L</sub> = 3 kΩ to GND  | 5   | 5.4                |     | V    |
| V <sub>OL</sub>  | Low-level output voltage                    | All DOUT at R <sub>L</sub> = 3 kΩ to GND  | –5  | –5.4               |     | V    |
| V <sub>O</sub>   | Output voltage (mouse driveability)         | DIN1 = DIN2 = GND, DIN3 = V <sub>CC</sub> , 3-kΩ to GND at DOUT3,<br>DOUT1 = DOUT2 = 2.5 mA | ±5  |                    |     | V    |
| I <sub>IH</sub>  | High-level input current                    | V <sub>I</sub> = V <sub>CC</sub>  |     | ±0.01              | ±1  | μA   |
| I <sub>IL</sub>  | Low-level input current                     | V <sub>I</sub> = GND  |     | ±0.01              | ±1  | μA   |
| I <sub>OS</sub>  | Short-circuit output current <sup>(2)</sup> | V <sub>CC</sub> = 3.6 V, V <sub>O</sub> = 0 V   |     | ±35                | ±60 | mA   |
|                  |   | V <sub>CC</sub> = 5.5 V, V <sub>O</sub> = 0 V   |     | ±35                | ±90 |      |
| r <sub>o</sub>   | Output resistance                           | V <sub>CC</sub> , V+, and V– = 0 V, V <sub>O</sub> = ±2 V                                   | 300 | 10M                |     | Ω    |
| I <sub>off</sub> | Output leakage current                      | FORCEOFF = GND, V <sub>O</sub> = ±12 V, V <sub>CC</sub> = 3 V to 3.6 V                      |     |                    | ±25 | μA   |
|                  |   | V <sub>O</sub> = ±10 V, V <sub>CC</sub> = 4.5 V to 5.5 V                                    |     |                    | ±25 |      |

(1) All typical values are at V<sub>CC</sub> = 3.3 V or V<sub>CC</sub> = 5 V, and T<sub>A</sub> = 25°C.

(2) Short-circuit durations should be controlled to prevent exceeding the device absolute power dissipation ratings, and not more than one output should be shorted at a time.

(3) Test conditions are C1–C4 = 0.1 μF at V<sub>CC</sub> = 3.3 V ± 0.3 V; C1 = 0.047 μF, C2–C4 = 0.33 μF at V<sub>CC</sub> = 5 V ± 0.5 V.

## 6.6 Switching Characteristics: Driver

over recommended ranges of supply voltage and operating free-air temperature (unless otherwise noted) (see [Figure 7-6](#))

| PARAMETER   | TEST CONDITIONS <sup>(3)</sup>   | MIN  | TYP <sup>(1)</sup> | MAX | UNIT       |
|---|--|--|--------------------|-----|------------|
| Maximum data rate<br>(see <a href="#">Figure 7-1</a> )                      | $R_L = 3\text{ k}\Omega$ ,<br>One DOUT switching   | $C_L = 1000\text{ pF}$   | 250                |     | kbit/s     |
|   |  | $C_L = 250\text{ pF}$ , $V_{CC} = 3\text{ V to }4.5\text{ V}$    | 1000               |     |            |
|   |  | $C_L = 1000\text{ pF}$ , $V_{CC} = 4.5\text{ V to }5.5\text{ V}$ | 1000               |     |            |
| $t_{sk(p)}$ Pulse skew <sup>(2)</sup>                                       | $C_L = 150\text{ pF to }2500\text{ pF}$ , $R_L = 3\text{ k}\Omega\text{ to }7\text{ k}\Omega$ , See <a href="#">Figure 7-2</a> |  | 25                 |     | ns         |
| SR(tr) Slew rate,<br>transition region<br>(see <a href="#">Figure 7-1</a> ) | $C_L = 150\text{ pF to }1000\text{ pF}$ , $R_L = 3\text{ k}\Omega\text{ to }7\text{ k}\Omega$ , $V_{CC} = 3.3\text{ V}$        |  | 18                 | 150 | V/ $\mu$ s |

(1) All typical values are at  $V_{CC} = 3.3\text{ V}$  or  $V_{CC} = 5\text{ V}$ , and  $T_A = 25^\circ\text{C}$ .

(2) Pulse skew is defined as  $|t_{PLH} - t_{PHL}|$  of each channel of the same device.

(3) Test conditions are  $C1\text{--}C4 = 0.1\text{ }\mu\text{F}$  at  $V_{CC} = 3.3\text{ V} \pm 0.3\text{ V}$ ;  $C1 = 0.047\text{ }\mu\text{F}$ ,  $C2\text{--}C4 = 0.33\text{ }\mu\text{F}$  at  $V_{CC} = 5\text{ V} \pm 0.5\text{ V}$ .

## 6.7 Electrical Characteristics: Receiver

over recommended ranges of supply voltage and operating free-air temperature (unless otherwise noted) (see [Figure 7-6](#))

| PARAMETER  | TEST CONDITIONS <sup>(2)</sup>             | MIN            | TYP <sup>(1)</sup> | MAX      | UNIT          |
|--|--|----------------|--------------------|----------|---------------|
| $V_{OH}$ High-level output voltage                 | $I_{OH} = -1\text{ mA}$                    | $V_{CC} - 0.6$ | $V_{CC} - 0.1$     |          | V             |
| $V_{OL}$ Low-level output voltage                  | $I_{OL} = 1.6\text{ mA}$                   |                |                    | 0.4      | V             |
| $V_{IT+}$ Positive-going input threshold voltage   | $V_{CC} = 3.3\text{ V}$                    |                | 1.6                | 2.4      | V             |
|  | $V_{CC} = 5\text{ V}$                      |                | 1.9                | 2.4      |               |
| $V_{IT-}$ Negative-going input threshold voltage   | $V_{CC} = 3.3\text{ V}$                    | 0.6            | 1.1                |          | V             |
|  | $V_{CC} = 5\text{ V}$                      | 0.8            | 1.4                |          |               |
| $V_{hys}$ Input hysteresis ( $V_{IT+} - V_{IT-}$ ) |  |                | 0.5                |          | V             |
| $I_{off}$ Output leakage current (except ROUT2B)   | FORCEOFF = 0 V                             |                | $\pm 0.05$         | $\pm 10$ | $\mu\text{A}$ |
| $r_i$ Input resistance                             | $V_I = \pm 3\text{ V to } \pm 25\text{ V}$ | 3              | 5                  | 7        | k $\Omega$    |

(1) All typical values are at  $V_{CC} = 3.3\text{ V}$  or  $V_{CC} = 5\text{ V}$ , and  $T_A = 25^\circ\text{C}$ .

(2) Test conditions are  $C1\text{--}C4 = 0.1\text{ }\mu\text{F}$  at  $V_{CC} = 3.3\text{ V} \pm 0.3\text{ V}$ ;  $C1 = 0.047\text{ }\mu\text{F}$ ,  $C2\text{--}C4 = 0.33\text{ }\mu\text{F}$  at  $V_{CC} = 5\text{ V} \pm 0.5\text{ V}$ .

## 6.8 Switching Characteristics: Receiver

over recommended ranges of supply voltage and operating free-air temperature (unless otherwise noted)

| PARAMETER   | TEST CONDITIONS <sup>(3)</sup>  | TYP <sup>(1)</sup> | UNIT |
|---|---|--------------------|------|
| $t_{PLH}$ Propagation delay time, low- to high-level output | $C_L = 150\text{ pF}$ , See <a href="#">Figure 7-3</a>                            | 150                | ns   |
| $t_{PHL}$ Propagation delay time, high- to low-level output | $C_L = 150\text{ pF}$ , See <a href="#">Figure 7-3</a>                            | 150                | ns   |
| $t_{en}$ Output enable time                                 | $C_L = 150\text{ pF}$ , $R_L = 3\text{ k}\Omega$ , See <a href="#">Figure 7-4</a> | 200                | ns   |
| $t_{dis}$ Output disable time                               | $C_L = 150\text{ pF}$ , $R_L = 3\text{ k}\Omega$ , See <a href="#">Figure 7-4</a> | 200                | ns   |
| $t_{sk(p)}$ Pulse skew <sup>(2)</sup>                       | See <a href="#">Figure 7-3</a>  | 50                 | ns   |

(1) All typical values are at  $V_{CC} = 3.3\text{ V}$  or  $V_{CC} = 5\text{ V}$ , and  $T_A = 25^\circ\text{C}$ .

(2) Pulse skew is defined as  $|t_{PLH} - t_{PHL}|$  of each channel of the same device.

(3) Test conditions are  $C1\text{--}C4 = 0.1\text{ }\mu\text{F}$  at  $V_{CC} = 3.3\text{ V} \pm 0.3\text{ V}$ ;  $C1 = 0.047\text{ }\mu\text{F}$ ,  $C2\text{--}C4 = 0.33\text{ }\mu\text{F}$  at  $V_{CC} = 5\text{ V} \pm 0.5\text{ V}$ .

## 6.9 Electrical Characteristics: Auto-Powerdown

over recommended ranges of supply voltage and operating free-air temperature (unless otherwise noted) (see [Figure 7-5](#))

| PARAMETER               |  | TEST CONDITIONS  | MIN            | MAX | UNIT |
|-------------------------|--|--|----------------|-----|------|
| $V_{T+}(\text{valid})$  | Receiver input threshold for $\overline{\text{INVALID}}$ high-level output voltage | FORCEON = GND, $\overline{\text{FORCEOFF}} = V_{CC}$                             |                | 2.7 | V    |
| $V_{T-}(\text{valid})$  | Receiver input threshold for $\overline{\text{INVALID}}$ high-level output voltage | FORCEON = GND, $\overline{\text{FORCEOFF}} = V_{CC}$                             | –2.7           |     | V    |
| $V_{T}(\text{invalid})$ | Receiver input threshold for $\overline{\text{INVALID}}$ low-level output voltage  | FORCEON = GND, $\overline{\text{FORCEOFF}} = V_{CC}$                             | –0.3           | 0.3 | V    |
| $V_{OH}$                | $\overline{\text{INVALID}}$ high-level output voltage                              | $I_{OH} = -1 \text{ mA}$ , FORCEON = GND, $\overline{\text{FORCEOFF}} = V_{CC}$  | $V_{CC} - 0.6$ |     | V    |
| $V_{OL}$                | $\overline{\text{INVALID}}$ low-level output voltage                               | $I_{OL} = 1.6 \text{ mA}$ , FORCEON = GND, $\overline{\text{FORCEOFF}} = V_{CC}$ |                | 0.4 | V    |


## 6.10 Switching Characteristics: Auto-Powerdown

over recommended ranges of supply voltage and operating free-air temperature (unless otherwise noted) (see [Figure 7-5](#))

| PARAMETER            |   | TYP <sup>(1)</sup> | UNIT |
|----------------------|---|--------------------|------|
| $t_{\text{valid}}$   | Propagation delay time, low- to high-level output | 1                  | μs   |
| $t_{\text{invalid}}$ | Propagation delay time, high- to low-level output | 30                 | μs   |
| $t_{\text{en}}$      | Supply enable time                                | 100                | μs   |


(1) All typical values are at  $V_{CC} = 3.3 \text{ V}$  or  $V_{CC} = 5 \text{ V}$ , and  $T_A = 25^\circ\text{C}$ .

## Parameter Measurement Information




NOTES: A.  $C_L$  includes probe and jig capacitance.  
B. The pulse generator has the following characteristics: PRR = 1 Mbit/s,  $Z_O = 50\ \Omega$ , 50% duty cycle,  $t_r \leq 10\text{ ns}$ ,  $t_f \leq 10\text{ ns}$ .

**Figure 7-1. Driver Slew Rate**



NOTES: A.  $C_L$  includes probe and jig capacitance.  
B. The pulse generator has the following characteristics: PRR = 1 Mbit/s,  $Z_O = 50\ \Omega$ , 50% duty cycle,  $t_r \leq 10\text{ ns}$ ,  $t_f \leq 10\text{ ns}$ .


**Figure 7-2. Driver Pulse Skew**




NOTES: A.  $C_L$  includes probe and jig capacitance.  
B. The pulse generator has the following characteristics:  $Z_O = 50\ \Omega$ , 50% duty cycle,  $t_r \leq 10\text{ ns}$ ,  $t_f \leq 10\text{ ns}$ .

**Figure 7-3. Receiver Propagation Delay Times**








TEST CIRCUIT



VOLTAGE WAVEFORMS

- NOTES: A.  $C_L$  includes probe and jig capacitance.  
B. The pulse generator has the following characteristics:  $Z_O = 50\ \Omega$ , 50% duty cycle,  $t_r \leq 10\text{ ns}$ ,  $t_f \leq 10\text{ ns}$ .  
C.  $t_{PLZ}$  and  $t_{PHZ}$  are the same as  $t_{dis}$ .  
D.  $t_{PZL}$  and  $t_{PZH}$  are the same as  $t_{en}$ .

Figure 7-4. Receiver Enable and Disable Times




† Auto-powerdown disables drivers and reduces supply current to 1  $\mu\text{A}$ .

NOTES: A.  $C_L$  includes probe and jig capacitance.

B. The pulse generator has the following characteristics: PRR = 5 kbit/s,  $Z_O = 50 \Omega$ , 50% duty cycle,  $t_r \leq 10 \text{ ns}$ ,  $t_f \leq 10 \text{ ns}$ .

Figure 7-5.  $\overline{\text{INVALID}}$  Propagation Delay Times and Supply Enabling Time



† C3 can be connected to V<sub>CC</sub> or GND.

NOTE A: Resistor values shown are nominal.

V<sub>CC</sub> vs CAPACITOR VALUES

| V <sub>CC</sub> | C1       | C2, C3, and C4 |
|-----------------|----------|----------------|
| 3.3 V ± 0.3 V   | 0.1 μF   | 0.1 μF         |
| 5 V ± 0.5 V     | 0.047 μF | 0.33 μF        |
| 3 V to 5.5 V    | 0.1 μF   | 0.47 μF        |

Figure 7-6. Typical Operating Circuit and Capacitor Values

## 7 Detailed Description

### 7.1 Overview

Flexible control options for power management are available when the serial port is inactive. The auto-powerdown feature functions when FORCEON is low and FORCEOFF is high. During this mode of operation, if the device does not sense a valid RS-232 signal, the driver outputs are disabled. If FORCEOFF is set low, both drivers and receivers (except ROUT2B) are shut off, and the supply current is reduced to 1  $\mu$ A. Disconnecting the serial port or turning off the peripheral drivers causes the auto-powerdown condition to occur.

Auto-powerdown can be disabled when FORCEON and FORCEOFF are high and should be done when driving a serial mouse. With auto-powerdown enabled, the device is activated automatically when a valid signal is applied to any receiver input. The INVALID output is used to notify the user if an RS-232 signal is present at any receiver input. INVALID is high (valid data) if any receiver input voltage is greater than 2.7 V or less than –2.7 V or has been between –0.3 V and 0.3 V for less than 30  $\mu$ s. INVALID is low (invalid data) if all receiver input voltages are between –0.3 V and 0.3 V for more than 30  $\mu$ s. Refer to Figure 7-5 for receiver input levels.

### 7.2 Device Functional Modes

#### 7.2.1 Function Tables

**EACH DRIVER<sup>(1)</sup>**


| INPUTS |         |          |                           | OUTPUT<br>DOUT | DRIVER STATUS                                 |
|--------|---------|----------|---------------------------|----------------|---|
| DIN    | FORCEON | FORCEOFF | VALID RIN<br>RS-232 LEVEL |                |   |
| X      | X       | L        | X                         | Z              | Powered off                                   |
| L      | H       | H        | X                         | H              | Normal operation with auto-powerdown disabled |
| H      | H       | H        | X                         | L              |   |
| L      | L       | H        | Yes                       | H              | Normal operation with auto-powerdown enabled  |
| H      | L       | H        | Yes                       | L              |   |
| L      | L       | H        | No                        | Z              | Powered off by auto-powerdown feature         |
| H      | L       | H        | No                        | Z              |   |

(1) H = high level, L = low level, X = irrelevant, Z = high impedance

**EACH RECEIVER<sup>(1)</sup>**

| INPUTS |                    |          |                              | OUTPUTS |       |                   | RECEIVER STATUS   |
|--------|--------------------|----------|------------------------------|---------|-------|-------------------|---|
| RIN2   | RIN1,<br>RIN3–RIN5 | FORCEOFF | VALID RIN<br>RS-232<br>LEVEL | ROUT2B  | ROUT2 | ROUT1,<br>ROUT3–5 |   |
| L      | X                  | L        | X                            | L       | Z     | Z                 | Powered off while<br>ROUT2B is active                       |
| H      | X                  | L        | X                            | H       | Z     | Z                 |   |
| L      | L                  | H        | YES                          | L       | H     | H                 | Normal operation with<br>auto-powerdown<br>disabled/enabled |
| L      | H                  | H        | YES                          | L       | L     | L                 |   |
| H      | L                  | H        | YES                          | H       | H     | H                 |   |
| H      | H                  | H        | YES                          | H       | L     | L                 |   |
| Open   | Open               | H        | YES                          | L       | H     | H                 |   |

(1) H = high level, L = low level, X = irrelevant, Z = high impedance (off), Open = input disconnected or connected driver off



**Figure 7-1. LOGIC DIAGRAM (POSITIVE LOGIC)**

## 8 Device and Documentation Support

TI offers an extensive line of development tools. Tools and software to evaluate the performance of the device, generate code, and develop solutions are listed below.

### 8.1 Receiving Notification of Documentation Updates

To receive notification of documentation updates, navigate to the device product folder on [ti.com](http://ti.com). Click on *Subscribe to updates* to register and receive a weekly digest of any product information that has changed. For change details, review the revision history included in any revised document.

### 8.2 Support Resources

[TI E2E™ support forums](#) are an engineer's go-to source for fast, verified answers and design help — straight from the experts. Search existing answers or ask your own question to get the quick design help you need.

Linked content is provided "AS IS" by the respective contributors. They do not constitute TI specifications and do not necessarily reflect TI's views; see TI's [Terms of Use](#).

### 8.3 Trademarks

TI E2E™ is a trademark of Texas Instruments.

All trademarks are the property of their respective owners.

### 8.4 Electrostatic Discharge Caution



This integrated circuit can be damaged by ESD. Texas Instruments recommends that all integrated circuits be handled with appropriate precautions. Failure to observe proper handling and installation procedures can cause damage.

ESD damage can range from subtle performance degradation to complete device failure. Precision integrated circuits may be more susceptible to damage because very small parametric changes could cause the device not to meet its published specifications.

### 8.5 Glossary

[TI Glossary](#) This glossary lists and explains terms, acronyms, and definitions.

## 9 Mechanical, Packaging, and Orderable Information

The following pages include mechanical, packaging, and orderable information. This information is the most current data available for the designated devices. This data is subject to change without notice and revision of this document. For browser-based versions of this data sheet, refer to the left-hand navigation.

## PACKAGING INFORMATION

| Orderable part number        | Status<br>(1) | Material type<br>(2) | Package   Pins  | Package qty   Carrier | RoHS<br>(3) | Lead finish/<br>Ball material<br>(4) | MSL rating/<br>Peak reflow<br>(5) | Op temp (°C) | Part marking<br>(6) |
|------------------------------|---------------|----------------------|-----------------|-----------------------|-------------|--------------------------------------|-----------------------------------|--------------|---------------------|
| <a href="#">TRSF3243IDB</a>  | Active        | Production           | SSOP (DB)   28  | 50   TUBE             | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -            | TRSF3243I           |
| TRSF3243IDB.A                | Active        | Production           | SSOP (DB)   28  | 50   TUBE             | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 85    | TRSF3243I           |
| <a href="#">TRSF3243IPWR</a> | Active        | Production           | TSSOP (PW)   28 | 2000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 85    | RT43I               |
| TRSF3243IPWR.A               | Active        | Production           | TSSOP (PW)   28 | 2000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 85    | RT43I               |

<sup>(1)</sup> **Status:** For more details on status, see our [product life cycle](#).

<sup>(2)</sup> **Material type:** When designated, preproduction parts are prototypes/experimental devices, and are not yet approved or released for full production. Testing and final process, including without limitation quality assurance, reliability performance testing, and/or process qualification, may not yet be complete, and this item is subject to further changes or possible discontinuation. If available for ordering, purchases will be subject to an additional waiver at checkout, and are intended for early internal evaluation purposes only. These items are sold without warranties of any kind.

<sup>(3)</sup> **RoHS values:** Yes, No, RoHS Exempt. See the [TI RoHS Statement](#) for additional information and value definition.

<sup>(4)</sup> **Lead finish/Ball material:** Parts may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead finish/Ball material values may wrap to two lines if the finish value exceeds the maximum column width.

<sup>(5)</sup> **MSL rating/Peak reflow:** The moisture sensitivity level ratings and peak solder (reflow) temperatures. In the event that a part has multiple moisture sensitivity ratings, only the lowest level per JEDEC standards is shown. Refer to the shipping label for the actual reflow temperature that will be used to mount the part to the printed circuit board.

<sup>(6)</sup> **Part marking:** There may be an additional marking, which relates to the logo, the lot trace code information, or the environmental category of the part.

Multiple part markings will be inside parentheses. Only one part marking contained in parentheses and separated by a "~" will appear on a part. If a line is indented then it is a continuation of the previous line and the two combined represent the entire part marking for that device.

**Important Information and Disclaimer:** The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.

## TAPE AND REEL INFORMATION



\*All dimensions are nominal

| Device       | Package Type | Package Drawing | Pins | SPQ  | Reel Diameter (mm) | Reel Width W1 (mm) | A0 (mm) | B0 (mm) | K0 (mm) | P1 (mm) | W (mm) | Pin1 Quadrant |
|--------------|--------------|-----------------|------|------|--------------------|--------------------|---------|---------|---------|---------|--------|---------------|
| TRSF3243IPWR | TSSOP        | PW              | 28   | 2000 | 330.0              | 16.4               | 6.75    | 10.1    | 1.8     | 12.0    | 16.0   | Q1            |



## TAPE AND REEL BOX DIMENSIONS



\*All dimensions are nominal

| Device       | Package Type | Package Drawing | Pins | SPQ  | Length (mm) | Width (mm) | Height (mm) |
|--------------|--------------|-----------------|------|------|-------------|------------|-------------|
| TRSF3243IPWR | TSSOP        | PW              | 28   | 2000 | 353.0       | 353.0      | 32.0        |

## TUBE




\*All dimensions are nominal


| Device        | Package Name | Package Type | Pins | SPQ | L (mm) | W (mm) | T (μm) | B (mm) |
|---------------|--------------|--------------|------|-----|--------|--------|--------|--------|
| TRSF3243IDB   | DB           | SSOP         | 28   | 50  | 530    | 10.5   | 4000   | 4.1    |
| TRSF3243IDB.A | DB           | SSOP         | 28   | 50  | 530    | 10.5   | 4000   | 4.1    |

PW (R-PDSO-G28)

PLASTIC SMALL OUTLINE



4040064-7/G 02/11



4214853/B 03/2018

## NOTES:


1. All linear dimensions are in millimeters. Any dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.
2. This drawing is subject to change without notice.
3. This dimension does not include mold flash, protrusions, or gate burrs. Mold flash, protrusions, or gate burrs shall not exceed 0.15 mm per side.
4. This dimension does not include interlead flash. Interlead flash shall not exceed 0.25 mm per side.
5. Reference JEDEC registration MO-150.

# EXAMPLE BOARD LAYOUT

DB0028A

SSOP - 2 mm max height

SMALL OUTLINE PACKAGE



LAND PATTERN EXAMPLE  
EXPOSED METAL SHOWN  
SCALE: 10X



SOLDER MASK DETAILS

4214853/B 03/2018

NOTES: (continued)

6. Publication IPC-7351 may have alternate designs.


7. Solder mask tolerances between and around signal pads can vary based on board fabrication site.

# EXAMPLE STENCIL DESIGN

DB0028A

SSOP - 2 mm max height

SMALL OUTLINE PACKAGE



SOLDER PASTE EXAMPLE  
BASED ON 0.125 mm THICK STENCIL  
SCALE: 10X

4214853/B 03/2018

NOTES: (continued)

8. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.
9. Board assembly site may have different recommendations for stencil design.

## IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATASHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, regulatory or other requirements.

These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you fully indemnify TI and its representatives against any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to [TI's Terms of Sale](#), [TI's General Quality Guidelines](#), or other applicable terms available either on [ti.com](#) or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products. Unless TI explicitly designates a product as custom or customer-specified, TI products are standard, catalog, general purpose devices.

TI objects to and rejects any additional or different terms you may propose.

Copyright © 2025, Texas Instruments Incorporated

Last updated 10/2025