







CDCDB400 SNAS833A – NOVEMBER 2021 – REVISED MAY 2022

CDCDB400 DB800ZL-Compliant 4-Output Clock Buffer for PCIe Gen 1 to Gen 6

1 Features

- 4 LP-HCSL outputs with programmable integrated 85-Ω (default) or 100-Ω differential output terminations
- 4 hardware output enable (OE#) controls
- Additive phase jitter after PCIE Gen 6 filter: 20 fs, RMS (maximum)
- Additive phase jitter after PCIE Gen 5 filter: 25 fs, RMS (maximum)
- Additive phase jitter after DB2000Q filter: 38 fs, RMS (maximum)
- Supports Common Clock (CC) and Individual Reference (IR) architectures
 - Spread spectrum-compatible
- Output-to-output skew: < 50 ps
- Input-to-output delay: < 3 ns
- Fail-safe input
- Programmable output slew rate control
- 3 selectable SMBus addresses
- 3.3-V core and IO supply voltages
- Hardware-controlled low power mode (PD#)
- Current consumption: 46 mA maximum
- 5-mm × 5-mm, 32-pin VQFN package

2 Applications

- Microserver & tower server
- Storage area network & host bus adapter card
- Network attached storage
- Hardware accelerator
- Rack server
- Communications switch
- Computer on module
- CT & PET scanners
- Rugged PC laptop


3 Description

The CDCDB400 is a 4-output LP-HCSL, DB800ZLcompliant, clock buffer capable of distributing the reference clock for PCIe Gen 1-6, QuickPath Interconnect (QPI), UPI, SAS, and SATA interfaces in CC, SRNS, or SRIS architectures. The SMBus interface and four output enable pins allow the configuration and control of all four outputs individually. The CDCDB400 is a DB800ZL derivative buffer and meets or exceeds the system parameters in the DB800ZL specification. The device also meets or exceeds the parameters in the DB2000Q specification. The CDCDB400 is packaged in a 5-mm × 5-mm, 32-pin VQFN package.

Device Information

PART NUMBER	PACKAGE (1)	BODY SIZE (NOM)
CDCDB400	VQFN (32)	5.00 mm × 5.00 mm

(1) For all available packages, see the orderable addendum at the end of the data sheet.



CDCDB400 System Diagram



Table of Contents

1 Features	1
2 Applications	
3 Description	
4 Revision History	
5 Pin Configuration and Functions	3
6 Specifications	
6.1 Absolute Maximum Ratings	
6.2 ESD Ratings	
6.3 Recommended Operating Conditions	<mark>5</mark>
6.4 Thermal Information	<mark>5</mark>
6.5 Electrical Characteristics	<mark>6</mark>
6.6 Timing Requirements	<mark>8</mark>
6.7 Typical Characteristics	9
7 Parameter Measurement Information	
8 Detailed Description	11
8.1 Overview	11
8.2 Functional Block Diagram	11
8.3 Feature Description	11
8.4 Device Functional Modes	

8.5 Programming	13
8.6 Register Maps	
9 Application and Implementation	
9.1 Application Information	
9.2 Typical Application	19
10 Power Supply Recommendations	21
11 Layout	22
11.1 Layout Guidelines	
11.2 Layout Examples	22
12 Device and Documentation Support	24
12.1 Device Support	24
12.2 Receiving Notification of Documentation Updates	s <mark>24</mark>
12.3 Support Resources	24
12.4 Trademarks	24
12.5 Electrostatic Discharge Caution	24
12.6 Glossary	
13 Mechanical, Packaging, and Orderable	
Information	24

4 Revision History

NOTE: Page numbers for previous revisions may differ from page numbers in the current version.

C	hanges from Revision * (November 2021) to Revision A (May 2022)	Page
•	Changed the data sheet title	1
•	Added PCIe Gen 6 to the data sheet	1
•	Changed the pin description for pin 5	3



5 Pin Configuration and Functions




Figure 5-1. CDCDB400 RHB Package 32-Pin VQFN Top View

Table	5-1.	Pin	Functions	
-------	------	-----	-----------	--

PIN NAME NO.			
		TYPE ⁽²⁾	DESCRIPTION
INPUT CLOCK			
CLKIN_P	3	I	LP-HCSL differential clock input. Typically connected directly to the differential
CLKIN_N	4	I	output of clock source.
OUTPUT CLOCKS			
CK0_P	13	0	LP-HCSL differential clock output of channel 0. Typically connected directly to PCIe
CK0_N	14	0	differential clock input. If unused, the pins can be left no connect.
CK1_P	19	0	LP-HCSL differential clock output of channel 1. Typically connected directly to PCIe
CK1_N	20	0	differential clock input. If unused, the pins can be left no connect.
CK2_P	22	0	LP-HCSL differential clock output of channel 2. Typically connected directly to PCIe
CK2_N	23	0	differential clock input. If unused, the pins can be left no connect.
СК3_Р	27	0	LP-HCSL differential clock output of channel 3. Typically connected directly to PCIe
CK3_N	28	0	differential clock input. If unused, the pins can be left no connect.
MANAGEMENT AN	ID CONTROL ⁽¹⁾		
CKPWRGD_PD#	1	I, S, PD	Clock Power Good and Power Down multi-function input pin with internal 180-kΩ pulldown. Typically connected to GPIO of microcontroller. If unused, the pin can be left no connect. After PWRGD has been asserted high for the first time, the pin becomes a PD# pin and it controls power-down mode: LOW: Power-down mode, all output channels tri-stated. HIGH: Normal operation mode.



Table 5-1. Pin Functions (continued)

PIN		 (2)		
NAME	NO.	TYPE ⁽²⁾	DESCRIPTION	
OE0#	15	I, S, PD	Output Enable for channel 0 with internal $180 \cdot k\Omega$ pulldown, active low. Typically connected to GPIO of microcontroller. If unused, the pin can be left no connect. LOW: enable output channel 0. HIGH: disable output channel 0.	
OE1#	18	I, S, PD	Output Enable for channel 1 with internal 180-k Ω pulldown, active low. Typically connected to GPIO of microcontroller. If unused, the pin can be left no connect. LOW: enable output channel 1. HIGH: disable output channel 1.	
OE2#	24	I, S, PD	Output Enable for channel 2 with internal $180 \cdot k\Omega$ pulldown, active low. Typically connected to GPIO of microcontroller. If unused, the pin can be left no connect. LOW: enable output channel 2. HIGH: disable output channel 2.	
OE3#	26	I, S, PD	Output Enable for channel 3, with internal $180-k\Omega$ pulldown, active low. Typically connected to GPIO of microcontroller. If unused, the pin can be left no connect. LOW: enable output channel 3. HIGH: disable output channel 3.	
SMBUS AND SM	BUS ADDRESS		-	
SADR0	5	I, S, PU / PD	SMBus address strap bit. This is a 3-level input that is decoded in conjunction with pin B8 to set SMBus address. It has internal $180-k\Omega$ pullup / pulldown network biasing to GND when no connect. For a high-level input configuration, the pin should be pulled up to 3.3-V VDD through an external pullup resistor from 1k to 5k with 5% tolerance. For a low-level input configuration input, the pin should be pulled down to ground through an external pulldown resistor from 1k to 5k with 5% tolerance. For a mid-level input configuration, the pin should be pulled down to ground through an external pulldown resistor from 1k to 5k with 5% tolerance. For a mid-level input configuration, the pin should be left floating and not connected to VDD or ground.	
SMBDAT	6	I / O	Data pin of SMBus interface. Typically pulled up to 3.3-V VDD using external pullup resistor. The recommended pullup resistor value is > 8.5k.	
SMBCLK	7	I	Clock pin of SMBus interface. Typically pulled up to 3.3-V VDD using external pullup resistor. The recommended pullup resistor value is > 8.5k.	
SUPPLY VOLTAG	SE AND GROUND		·	
VDDR	2	Р	Power supply input for input clock receiver. Connect to 3.3-V power supply rail with decoupling capacitor to GND. Place a 0.1- μ F capacitor close to each supply pin between power supply and ground.	
VDD	12, 16, 21, 25, 29, 31	Р	3.3-V power supply for output channels and core voltage.	
GND	DAP	G	Ground. Connect ground pad to system ground.	
NO CONNECT				
NC	8, 9, 10, 11, 17, 30	_	Do not connect pins to GND or VDD. Leave floating.	
NC	32	—	Pin may be connected to GND, VDD, or otherwise tied to any potential within the Supply Voltage range stated in the Absolute Maximum Ratings.	

(1) The "#" symbol at the end of a pin name indicates that the active state occurs when the signal is at a low voltage level. When "#" is not present, the signal is active high.

(2) The definitions below define the I/O type for each pin.

- I = Input
- O = Output
- I / O = Input / Output
- PU / PD = Internal 180-kΩ Pullup / Pulldown network biasing to VDD/2
- PD = Internal 180-kΩ Pulldown
- S = Hardware Configuration Pin
- P = Power Supply
- G = Ground



6 Specifications

6.1 Absolute Maximum Ratings

over operating free-air temperature range (unless otherwise noted)⁽¹⁾

		MIN	MAX	UNIT
V _{DD} , V _{DD_R}	Power supply voltage	-0.3	3.6	V
V _{IN}	IO input voltage	-0.3	3.6	V
TJ	Junction temperature		125	°C
T _{stg}	Storage temperature	-65	150	°C

(1) Operation outside the Absolute Maximum Ratings may cause permanent device damage. Absolute Maximum Ratings do not imply functional operation of the device at these or any other conditions beyond those listed under Recommended Operating Conditions. If used outside the Recommended Operating Conditions but within the Absolute Maximum Ratings, the device may not be fully functional, and this may affect device reliability, functionality, performance, and shorten the device lifetime.

6.2 ESD Ratings

			VALUE	UNIT
	Electrostatic discharge	Human body model (HBM), per ANSI/ESDA/JEDEC JS-001, all pins ⁽¹⁾	±3500	V
V _(ESD)	Lieurostario discriarge	Charged device model (CDM), per ANSI/ESDA/ JEDEC JS-002, all pins ⁽²⁾	±1000	V

(1) JEDEC document JEP155 states that 500-V HBM allows safe manufacturing with a standard ESD control process.

(2) JEDEC document JEP157 states that 250-V CDM allows safe manufacturing with a standard ESD control process.

6.3 Recommended Operating Conditions

over operating free-air temperature range (unless otherwise noted)

		MIN	NOM	MAX	UNIT
V _{DD}	IO, Core supply voltage	3	3.3	3.6	V
V _{DD_R}	Input supply voltage	3	3.3	3.6	V
T _A	Ambient temperature	-40		105	°C

6.4 Thermal Information

		CDCDB400	
	THERMAL METRIC ⁽¹⁾	RHB (QFN)	UNIT
		32 PINS	
R _{θJA}	Junction-to-ambient thermal resistance	35.3	°C/W
R _{0JC(top)}	Junction-to-case (top) thermal resistance	27.3	°C/W
R _{θJB}	Junction-to-board thermal resistance	16.2	°C/W
Ψ_{JT}	Junction-to-top characterization parameter	0.6	°C/W
Ψ_{JB}	Junction-to-board characterization parameter	16.2	°C/W
R _{0JC(bot)}	Junction-to-case (bottom) thermal resistance	6.1	°C/W

(1) For more information about traditional and new thermal metrics, see the Semiconductor and IC Package Thermal Metrics application report.

6.5 Electrical Characteristics

VDD, VDD $R = 3.3 V \pm 5 \%$	-40°C ≤ T _Δ ≤ 85°C. Typical value	es are at VDD = VDD_R = 3.3 V, 25°	C (unless otherwise noted)

	PARAMETER	TEST CONDITION		MIN	TYP	MAX	UNIT
CURRENT	CONSUMPTION		I				
		Active mode. CKPWRGD_PD#	= 1			8.5	
I _{DD_R}	Core supply current	Power-down mode. CKPWRGE	D_PD# = 0			2	mA
		All outputs disabled				18	
I _{DD}	IO supply current	All outputs active, 100 MHz (pe	r output)			8.5	mA
		Power-down mode. CKPWRGE	D_PD# = 0			1.5	
CLOCK IN	PUT						
f _{IN}	Input frequency			50	100	250	MHz
V _{IN}	Input voltage swing	Differential voltage between CL CLKIN_N ⁽¹⁾	KIN_P and	200		2300	mV _{Diff-} _{peak}
dV/dt	Input voltage edge rate	20% - 80% of input swing		0.7			V/ns
DV _{CROSS}	Total variation of V _{CROSS}	Total variation across V _{CROSS}			140		mV
DCIN	Input duty cycle			40		60	%
C _{IN}	Input capacitance ⁽²⁾	Differential capacitance betwee and CLKIN_N pins	n CLKIN_P		2.2		pF
CLOCK OL	JTPUT						
f _{OUT}	Output frequency			50	100	250	MHz
C _{OUT}	Output capacitance ⁽¹⁾	Differential capacitance betwee and CKx_N pins	n CKx_P		4		pF
V _{OH}	Output high voltage	O_{12}^{12} where u_{12}^{12} $u_{12}^{$		225		270	
V _{OL}	Output low voltage	Single-ended ^{(2) (3)}		10		150	
V _{HIGH}	Output high voltage	Measured into an AC load as d DB800ZL	efined in	660		850	
V _{LOW}	Output low voltage	Measured into an AC load as d DB800ZL	efined in	-150		150	
V _{MAX}	Output Max voltage	Measured into an AC load as d DB800ZL	efined in			1150	
V _{CROSS}	Crossing point voltage	See ^{(3) (4)}		130		200	mV
V _{CROSSAC}	Crossing point voltage (AC load)	Measured into an AC load as defined in DB800ZL		250		550	
DV _{CROSS}	Total variation of V _{CROSS}	Variation of V _{CROSS} ⁽³⁾ ⁽⁴⁾			35	140	
Vovs	Overshoot voltage	See ⁽³⁾				V _{OH} +75	
V _{ovs(AC)}	Overshoot voltage (AC load)	Measured into an AC load as defined in DB800ZL			V	_{HIGH} +30 0	
V _{uds}	Undershoot voltage	See ⁽³⁾				V _{OL} -75	
V _{uds(AC)}	Undershoot voltage	Measured into an AC load as defined in DB800ZL				V _{LOW} - 300	mV
V _{rb}	Ringback Voltage	Measured into an AC load as defined in DB800ZL and taken from single-ended waveform.	Measured into an AC load as defined in DB800ZL and taken from single- ended waveform.	-0.2		0.2	V



vuu, vuu	_R = 3.3 V ± 5 %, −40°C ≤ $T_A \le 85$ PARAMETER	TEST CONDITIONS		• 3.3 V, 25 C MIN	TYP	MAX	UNIT	
7	Differential impedance (Default setting, 85 Ω)	Measured at V _{OL} /V _{OH}		81	85	89		
Z _{DIFF}	Differential impedance (Output impedance selection bit =1, 100 Ω)	Measured at V _{OL} /V _{OH}		95	100	105	Ω	
Z _{DIFF_CROS}	Differential impedance (Default setting, 85 Ω)	Measured at V _{CROSS}		68	85	102	12	
S	Differential impedance (Output impedance selection bit = 1, 100 Ω)	Measured at V _{CROSS}		80	100	120	20	
t _{EDGE}	Differential edge rate	Measured (±150 mV) around V	CROSS ⁽⁷⁾	2		4	V/ns	
Dt _{EDGE}	Edge rate matching	Measured (±150 mV) V _{CROSS} (7	.)			20	%	
tstable	Power good assertion to stable clock output	CKPWRGD_PD# pin transitions from 0 to 1, f _{IN} = 100 MHz	Measured when positive output reaches 0.2 V			1.8	ms	
t _{DRIVE_PD#}	Power good assertion to outputs driven high	CKPWRGD_PD# pin transitions from 0 to 1, f _{IN} = 100 MHz	Measured when positive output reaches 0.2 V			300	μs	
t _{OE}	Output enable assertion to stable clock output	OEx# pin transitions from 1 to 0			10			
t _{OD}	Output enable de-assertion to no clock output	OEx# pin transitions from 0 to 1			10	CLKIN Periods		
t _{PD}	Power-down assertion to no clock output	CKPWRGD_PD# pin transitions from 1 to 0				3		
t _{DCD}	Duty cycle distortion	Differential; f _{IN} = 100 MHz, f _{IN_E}	_{oc} = 50%	-1		1	%	
t _{DLY}	Propagation delay	See ⁽⁵⁾		0.5		3	ns	
t _{SKEW}	Skew between outputs	See ⁽⁶⁾				50	ps	
t _{DELAY(IN-} OUT)	Input to output delay variation	Input-to-output delay variation a across voltage and temperature		-250		250	ps	
	Additive jitter for DB2000QL	DB2000QL filter, for input of 20 differential swing at 1.5 V/ns	0-mV			0.038		
	Additive jitter for PCIe6.0	PLL BW: 0.5 - 1 MHz; CDR = 10 MHz	Input clock slew rate = 2 V/ns			0.02		
J _{CKx_PCIE}	Additive jitter for PCIe5.0	PCIe5.0 filter				0.025	ps, RMS	
(7)	Additive jitter for PCIe4.0	PLL BW = 2 - 5 MHz; CDR =	Input clock slew rate ≥ 1.8 V/ns			0.06	po, 1 (int	
	Additive jitter for PCIe3.0	10 MHz	Input clock slew rate ≥ 0.6 V/ns			0.1		
J _{СКх}	Additive jitter	f _{IN} = 100 MHz; slew rate ≥ 3 V/r 20 MHz integration bandwidth.	ns; 12 kHz to		100	160	fs, RMS	
NF	Noise floor	f _{IN} = 100 MHz; f _{Offset} ≥ 10 MHz	Input clock slew rate ≥ 3 V/ns		-160	-155	dBc/Hz	
SMBUS IN	TERFACE, OEx#, CKPWRGD_PD#	<u> </u>	I				<u> </u>	
V _{IH}	High level input voltage			2.0			V	
V _{IL}	Low level input voltage					0.8	v	
I _{IH}	Input leakage current	With internal pullup/pulldown	$GND \le V_{IN} \le V_{DD}$	-30		30	μA	

Copyright © 2022 Texas Instruments Incorporated



	PARAMETER	TEST CONDITION	IS	MIN	TYP	MAX	UNIT
IIL	Input leakage current	With internal pullup/pulldown	$ GND \leq V_{IN} $	-30		30	μA
IIH	Input leakage current	Without internal pullup/ pulldown		-5		5	μA
IIL	Input leakage current	Without internal pullup/ pulldown		-5		5	μA
C _{IN}	Input capacitance				4.5		pF
C _{OUT}	Output capacitance				4.5		pF
3-LEVEL	DIGITAL INTERFACE (SADR0)				·		
V _{IH}	High level input voltage			2.3			
V _{IM}	Mid level input voltage			1.25	$V_{DD}/2$	1.725	V
V _{IL}	Low level input voltage					0.85	
I _{IH}	Input leakage current	With internal pullup/pulldown	$V_{IN} = V_{DD}$	-30		30	μA
IIL	Input leakage current	With internal pullup/pulldown	V _{IN} = GND	-30		30	μA
C _{IN}	Input capacitance ⁽¹⁾				4.5		pF

(1) Voltage swing includes overshoot.

(2) Not tested in production. Ensured by design and characterization.

(3) Measured into DC test load.

(4) V_{CROSS} is single-ended voltage when CKx_P = CKx_N with respect to system ground. Only valid on rising edge of CKx, when CKx_P is rising.

(5) Measured from rising edge of CLK_IN to any CKx output.

(6) Measured from rising edge of any $\overline{C}Kx$ output to any other CKx output.

(7) Measured into AC test load.

6.6 Timing Requirements

VDD, VDD_R = $3.3 \text{ V} \pm 5 \%$, $-40^{\circ}\text{C} \le \text{T}_{\text{A}} \le 85^{\circ}\text{C}$. Typical values are at VDD = VDD_R = 3.3 V, 25°C (unless otherwise noted)

			MIN	NOM	MAX	UNIT
SMBUS C	COMPATIBLE INTERFACE TIMING					
f _{SMB}	SMBus operating frequency		10		400	kHz
t _{BUF}	Bus free time between STOP and START		4.7			
t _{HD_STA}	START condition hold time	SMBCLK low after SMBDAT low	4			
t _{SU_STA}	START condition setup time	SMBCLK high before SMBDAT low	4.7			μs
t _{su_sто}	STOP condition setup time		4			
t _{HD_DAT}	SMBDAT hold time		300			ns
t _{SU_DAT}	SMBDAT setup time		250			115
t _{TIMEOUT}	Detect SMBCLK low timeout	In terms of device input clock frequency	1e6			cycles
t _{LOW}	SMBCLK low period		4.7			
t _{HIGH}	SMBCLK high period		4		50	μs
t _F	SMBCLK/SMBDAT fall time ⁽¹⁾				300	20
t _R	SMBCLK/SMBDAT rise time ⁽²⁾				1000	ns

(1) TF = (VIHMIN + 0.15) to (VILMAX - 0.15)

(2) TR = (VILMAX - 0.15) to (VIHMIN + 0.15)



6.7 Typical Characteristics

Figure 6-1 shows both the phase noise of the source as well as the output of the DUT (CDCDB400). It can be seen from the phase noise plot that the DUT has a very low phase noise profile with total jitter of 81.5 fs, rms. If we rms subtract the clock reference noise, the additive jitter of CDCDB400 under typical conditions would be lower than 81.5 fs, rms.




Figure 6-1. CDCDB400 Clock Out (CK0:4) Phase Noise



7 Parameter Measurement Information





Figure 7-1. AC Test Load (Referencing Intel DB2000QL Document)



R1 = 47 Ω and R2 = 147 Ω .






8 Detailed Description

8.1 Overview

The CDCDB400 is a low additive-jitter, low propagation delay clock buffer designed to meet the strict performance requirements for PCIe Gen 1-6, QPI, UPI, SAS, and SATA reference clocks in CC, SRNS, or SRIS architectures. The CDCDB400 allows buffering and replication of a single clock source to up to four individual outputs in the LP-HCSL format. The CDCDB400 also includes status and control registers accessible by an SMBus version 2.0 compliant interface. The device integrates a large amount of external passive components to reduce overall system cost.

8.2 Functional Block Diagram



8.3 Feature Description

8.3.1 Fail-Safe Input

The CDCDB400 is designed to support fail-safe input operation feature. This feature allows the user to drive the device inputs before V_{DD} is applied without damaging the device. Refer to the *Absolute Maximum Ratings* table for more information on the maximum input supported by the device.

8.3.2 Output Enable Control

The CDCDB400 uses SMBus and OE# to control the state of the output channels. The OE# pins control the state of the output with the same number. For example, the OE3# pin controls the state of the CK3 output driver. The SMBus registers may enable or disable the output when the corresponding OE# pin is held low.

8.3.3 SMBus

The CDCDB400 has an SMBus interface that is active only when CKPWRGD_PD# = 1. The SMBus allows individual enable/disable of each output.

When CKPWRGD_PD# = 0, the SMBus pins are placed in a Hi-Z state, but all register settings are retained. The SMBus register values are only retained while V_{DD} remains inside of the recommended operating voltage.



8.3.3.1 SMBus Address Assignment

The SMBus address is assigned by configuring the SADR0 pin which is capable of supporting three levels. This configuration allows the CDCDB400 to assume three different SMBus addresses.

The SMBus address pin is sampled when PWRGD is set to 1. See Table 8-1 for address pin configuration. The address can only be changed by power cycling the device.

	Ŭ U				
SADR0	SMBus ADDRESS : WRITE OPERATION (READ/WRITE=0)	SMBus ADDRESS : READ OPERATION (READ/WRITE=1)			
L	0xD8	0xD9			
М	0xDA	0xDB			
Н	0xDE	0xDF			

Table 8-1. SMBus Address Assignment

8.4 Device Functional Modes

8.4.1 CKPWRGD_PD# Function

The CKPWRGD_PD# pin is used to set two state variables inside of the device: PWRGD and PD#. The PWRGD and PD# variables control which functions of the device are active at any time, as well as the state of the input and output pins.

The PWRGD and PD# states are multiplexed on the CKPWRGD_PD# pin. CKPWRGD_PD# must remain below V_{OL} and not exceed V_{DDR} + 0.3 V until V_{DD} and V_{DDR} are present and within the recommended operating conditions. After CKPWRGD_PD# is set high, a valid CLKIN must be present to use PD#.

The first rising edge of the CKPWRGD_PD# pin sets PWRGD = 1. After PWRGD is set to 1, the CKPWRGD_PD# pin is used to assert PD# mode only. PWRGD variable will only be cleared to 0 with the removal of V_{DD} and V_{DDR} .




Figure 8-1. PWRGD and PD# State Changes



8.4.2 OE[3:0]# and SMBus Output Enables

Each output channel, 0 to 3, can be individually enabled or disabled by a SMBus control register bit, called SMB enable bits. Additionally, each output channel has a dedicated, corresponding, OE[3:0]# hardware pin. The OE[3:0]# pins are asynchronously asserted-low signals that may enable or disable the output.

Refer to Table 8-2 for enabling and disabling outputs through the hardware and software. Note that both the SMB enable bit must be a 1 and the OEx# pin must be an input low voltage 0 for the output channel to be active.

Control Inputs					RDWARE PINS A	CK[3:0]_P/				
CKPWRGD_P D#	PWRGD	PD#		OE[3:0]#	OUT_EN_CLK[3:0]	DRIVE_OP_ST ATE_CTRL	CK[3:0]_N			
0	0	0	Х	Х	X	Х	LOW/LOW			
				Х	0	0	LOW/LOW			
		1	×(1)	X ⁽¹⁾	Ū	1	TRI-STATE			
1			1	1	1			1	x	0
	1			I	^	1	TRI-STATE			
			Running ⁽¹⁾	0	1	Х	Running			
0	0 X ⁽²⁾ X	Х	×	0	LOW/LOW					
0		0	~~/	^	X	1	TRI-STATE			

Table 8-2. OE[3:0]# Functionality

(1) To enter the power-down state, CLKIN must remain active for at least 3 clock cycles after CKPWRGD_PD# transitions from 1 to 0.

(2) To enter the powered-up state with active clock outputs, CLKIN must be active before CKPWRGD_PD# transitions from 0 to 1.

8.4.3 Output Slew Rate Control

The CDCDB400 provides output slew rate control feature which customer can use to compensate for increased output trace length based on their board design. The slew rate of the 4 outputs, CK0 to CK3, can be changed within a given range by a SMBus control register called CAPTRIM. Refer to Table 8-16 for more information.

8.4.4 Output Impedance Control


The integrated termination on the CDCDB400 can be programmed either for 85 Ω or 100 Ω . This flexibility ensures that the customer can use the same device across various applications irrespective of the characteristic board impedance which is typically either 85 Ω or 100 Ω . This termination resistor can be changed for all the outputs as whole using bit 5 of a register called OUTSET. Refer to Table 8-14 for more information.


8.5 Programming

The CDCDB400 uses SMBus to program the states of its four output drivers. See *SMBus* for more information on the SMBus programming, and *Register Maps* for information on the registers.

Table 8-3. Command Code Definition

BIT	DESCRIPTION	
7	e = Block Read or Block Write operation = Byte Read or Byte Write operation	
(6:0)	Register address for Byte operations, or starting register address for Block, operations	







8.6 Register Maps

8.6.1 CDCDB400 Registers

Table 8-4 lists the CDCDB400 registers. All register locations not listed in Table 8-4 should be considered as reserved locations and the register contents should not be modified.

.

Address	Acronym	Register Name	Section	
0h	RCR1	Reserved Control Register 1	Go	
1h	OECR1	Output Enable Control 1 Go		
2h	OECR2	Output Enable Control 2	Go	
3h	OERDBK	Output Enable# Pin Read Back	Go	
4h	RCR2	Reserved Control Register 2	Go	
5h	VDRREVID	Vendor/Revision Identification	Go	
6h	DEVID	Device Identification	Go	
7h	BTRDCNT	Byte Read Count Control	Go	
8h	OUTSET	Output Setting Control	Go	
4Ch	CAPTRIM	Slew Rate Capacitor Cluster 1 & 2	Go	

Complex bit access types are encoded to fit into small table cells. Table 8-5 shows the codes that are used for access types in this section.

····· //					
Access Type	Code	Description			
Read Type					
R	R	Read			
Write Type					
W	W	Write			
Reset or Default	Value				
-n		Value after reset or the default value			

Table 8-5. CDCDB400 Access Type Codes

8.6.1.1 RCR1 Register (Address = 0h) [reset = 47h]

RCR1 is shown in Table 8-6.

Return to the Summary Table.

The RCR1 register contains reserved bits.

Table 8-6. RCR1	Register Field Descriptions
-----------------	------------------------------------

Bit	Field	Туре	Reset	Description
7-4	Reserved	R	4h	Reserved.
3-0	Reserved	R/W	7h	Writing to these bits will not affect the functionality of the device.

8.6.1.2 OECR1 Register (Address = 1h) [reset = FFh]

OECR1 is shown in Table 8-7.

Return to the Summary Table.

The OECR1 register contains bits that enable or disable individual output clock channels [1:0].



Bit	Field	Туре	Reset	Description
7	Reserved	R/W	1h	Writing to this bit will not affect the functionality of the device.
6	Reserved	R/W	1h	Writing to this bit will not affect the functionality of the device.
5	OUT_EN_CLK1	R/W	1h	This bit controls the output enable signal for output channel CK1_P/ CK1_N. 0h = Output Disabled 1h = Output Enabled
4	Reserved	R/W	1h	Writing to this bit will not affect the functionality of the device.
3	Reserved	R/W	1h	Writing to this bit will not affect the functionality of the device.
2	OUT_EN_CLK0	R/W	1h	This bit controls the output enable signal for output channel CK0_P/ CK0_N. 0h = Output Disabled 1h = Output Enabled
1	Reserved	R/W	1h	Writing to this bit will not affect the functionality of the device.
0	Reserved	R/W	1h	Writing to this bit will not affect the functionality of the device.

Table 9.7 OECD1 Desister Field Descriptions

8.6.1.3 OECR2 Register (Address = 2h) [reset = 0Fh]

OECR2 is shown in Table 8-8.

Return to the Summary Table.

The OECR2 register contains bits that enable or disable individual output clock channels [3:2].

	Table 8-8. OECR2 Register Field Descriptions							
Bit	Field	Туре	Reset	Description				
7-4	Reserved	R/W	0h	Writing to these bits will not affect the functionality of the device.				
3	Reserved	R/W	1h	Writing to this bit will not affect the functionality of the device.				
2	OUT_EN_CLK3	R/W	1h	This bit controls the output enable signal for output channel CK3_P/ CK3_N. 0h = Output Disabled 1h = Output Enabled				
1	Reserved	R/W	1h	Writing to this bit will not affect the functionality of the device.				
0	OUT_EN_CLK2	R/W	1h	This bit controls the output enable signal for output channel CK2_P/ CK2_N. 0h = Output Disabled 1h = Output Enabled				

8.6.1.4 OERDBK Register (Address = 3h) [reset = 0h]

OERDBK is shown in Table 8-9.

Return to the Summary Table.

The OERDBK register contains bits that report the current state of the OE[3:0]# input pins.

Bit	Field	Туре	Reset	Description			
7	RB_OEZ3	R	0h	This bit reports the logic level present on the OE3# pin.			
6	RB_OEZ2	R	0h	This bit reports the logic level present on the OE2# pin.			
5-4	Reserved	R	0h	Reserved.			
3	RB_OEZ1	R	0h	This bit reports the logic level present on the OE1# pin.			
2	Reserved	R	0h	Reserved.			

Table 8-9. OERDBK Register Field Descriptions

Table 8-9. OERDBK Register Field Descriptions (continued)

Bit	Field	Туре	Reset	Description
1	RB_OEZ0	R	0h	This bit reports the logic level present on the OE0# pin.
0	Reserved	R	0h	Reserved.

8.6.1.5 RCR2 Register (Address = 4h) [reset = 0h]

RCR2 is shown in Table 8-10.

Return to the Summary Table.

The RCR2 register contains reserved bits.

Table 8-10. RCR2 Register Field Descriptions

Bit	Field	Туре	Reset	Description
7-0	Reserved	R	0h	Reserved.

8.6.1.6 VDRREVID Register (Address = 5h) [reset = 0Ah]

VDRREVID is shown in Table 8-11.

Return to the Summary Table.

The VDRREVID register contains a vendor identification code and silicon revision code.

Table 8-11. VDRREVID Register Field Descriptions

_					
	Bit	Field	Туре	Reset	Description
	7-4	REV_ID	R	0h	Silicon revision code. Silicon revision code bits [3:0] map to register bits [7:4] directly.
	3-0	VENDOR_ID	R	Ah	Vendor identification code. Vendor ID bits [3:0] map to register bits [3:0] directly.

8.6.1.7 DEVID Register (Address = 6h) [reset = E7h]

DEVID is shown in Table 8-12.

Return to the Summary Table.

The DEVID register contains a device identification code.

Table 8-12. DEVID Register Field Descriptions

Bit	Field	Туре	Reset	Description
7-0	DEV_ID	R	E7h	Device ID code.
				Device ID bits[7:0] map to register bits[7:0] directly.



8.6.1.8 BTRDCNT Register (Address = 7h) [reset = 8h]

BTRDCNT is shown in Table 8-13.

Return to the Summary Table.

The BTRDCNT register contains bits [4:0] which configure the number of bytes which will be read back.

Bit	Field	Туре	Reset	Description
7-5	Reserved	R/W	0h	Writing to these bits will not affect the functionality of the device.
4	BYTE_COUNTER	R/W	0h	Writing to this register configures how many bytes will be read back.
3-0	BYTE_COUNTER	R/W	8h	Whiting to this register configures now many bytes will be read back.

8.6.1.9 OUTSET Register (Address = 8h) [reset = 0h]

OUTSET is shown in Table 8-14.

Return to the Summary Table.

Bit5 of the OUTSET register sets the termination for all the outputs while bit4 can be used to set the power-down state for all outputs. The remaining bits for this register are reserved.

Bit	Field	Туре	Reset	Description
7-6	Reserved	R	0h	Reserved.
5	CH_ZOUT_SEL	R/W	0h	Select between 85 Ω (0) and 100 Ω (1) Output impedance
4	d_DRIVE_OP_STATE_CTRL	R/W	Oh	Power-down state of all output clocks. 0: LOW/LOW 1: TRI_STATE
3-0	Reserved	R/W	0h	Register bits can be written to 0. Writing a different value than 0 will affect device functionality.

Table 8-14. OUTSET Register Field Descriptions

8.6.1.10 CAPTRIM Register (Address = 4Ch) [reset = 66h]

CAPTRIM is shown in Table 8-16.

Return to the Summary Table.

Bits [7:4] of the CAPTRIM register is used to control the slew rate for output channel cluster 2. Bits [3:0] control the slew rate for output channel cluster 1. Refer below for cluster identification.

Table 8	Table 8-15. Cluster Identification						
Cluster	luster Outputs						
1	СК1, СК0						
2	СК3, СК2						

Table 8-16. CAPTRIM Register Field Descriptions

Bit	Field	Туре	Reset	Description
7-4	CLUSTER2_CAP_TRIM	R/W	6h	Slew Rate Reduction Cap Trim for Cluster 2 Default value of 6h. 0: minimum F: maximum
3-0	CLUSTER1_CAP_TRIM	R/W	6h	Slew Rate Reduction Cap Trim for Cluster 1. Default value of 6h. 0: minimum F: maximum



9 Application and Implementation

Note

Information in the following applications sections is not part of the TI component specification, and TI does not warrant its accuracy or completeness. TI's customers are responsible for determining suitability of components for their purposes, as well as validating and testing their design implementation to confirm system functionality.

9.1 Application Information

The CDCDB400 is a fanout buffer that supports PCIe generation 4 and PCIe generation 5 REFCLK distribution. The device is used to distribute up to four copies of a typically 100-MHz clock.

9.2 Typical Application

Figure 9-1 shows a CDCDB400 typical application. In this application, a clock generator provides a 100-MHz reference to the CDCDB400 which then distributes that clock to PCIe endpoints. The clock generator may be a discrete clock generator like the CDCI6214 or it may be integrated in a larger component such as a Platform Controller Hub (PCH) or application processor.




Figure 9-1. Typical Application

9.2.1 Design Requirements

Consider a typical server motherboard application which must distribute a 100-MHz PCIe reference clock from the PCH of a processor chipset to multiple endpoints. An example of clock input and output requirements is:

- Clock Input:
 - 100-MHz LP-HCSL
- Clock Output:
 - 2x 100-MHz to processors, LP-HCSL
 - 1x 100-MHz to riser/retimer, LP-HCSL
 - 1x 100-MHz to DDR memory controller, LP-HCSL

9.2.2 Detailed Design Procedure

The following items must be determined before starting design of a CDCDB400 socket:

- Output Enable Control Method
- SMBus address

9.2.2.1 Output Enable Control Method

The device provides an option to either use SMBus programmed registers (software) to control the outputs or by using the hardware OE# pins. When using software to control the outputs, the hardware OE# pins can be left floating as each of these pins have a pulldown to ground. Refer to Table 8-2 and *Register Maps* for more information on programming the register.



When the user wants to control the outputs with the hardware OE# pins, they can connect these pins to a GPIO controller and set the outputs to HIGH/LOW (see Table 5-1). Registers OECR1 (Table 8-7) and OECR2 (Table 8-8) show the OUT_EN_CLK3 to OUT_EN_CLK0 bits used to control the outputs. These register bits are set to 1 by default to ensure that the outputs are "software enabled" and their state is therefore set by hardware OE# pins.


9.2.2.2 SMBus Address

Select a SMBus address from the list of potential addresses in Table 8-1. Place the appropriate pullup or pulldown resistor on the SADR0 pin as indicated in the table. Ensure the SMBus address is not already in use to avoid conflict.

9.2.3 Application Curves

Figure 6-1 in the *Typical Characteristics* section can be used as both an application curve and a typical characteristics plot in this example.

The Figure 9-2 and Figure 9-3 show characterization data for the Output slew rate for various CAPTRIM codes and across temperature. Customers can use these plots as reference for choosing the appropriate output slew rate based on their system requirement.






Figure 9-3. Slew Rate Variation Across Temperature for Different CAPTRIM Code



10 Power Supply Recommendations

High-performance clock buffers are sensitive to noise on the power supply, which can dramatically increase the additive jitter of the buffer. Thus, it is essential to reduce noise from the system power supply, especially when the jitter and phase noise is critical to applications.

Filter capacitors are used to eliminate the low-frequency noise from the power supply, where the bypass capacitors provide the very low impedance path for high-frequency noise and guards the power-supply system against induced fluctuations. These bypass capacitors also provide instantaneous current surges as required by the device and should have low equivalent series resistance (ESR). To properly use the bypass capacitors, place the capacitors very close to the power-supply terminals and lay out with short loops to minimize inductance. TI recommends to insert a ferrite bead between the board power supply and the chip power supply that isolates the high-frequency switching noises generated by the clock buffer. These beads prevent the switching noise from leaking into the board supply. It is imperative to choose an appropriate ferrite bead with very low DC resistance to provide adequate isolation between the board supply and the chip supply, as well as to maintain a voltage at the supply terminals that is greater than the minimum voltage required for proper operation.

Figure 10-1 shows the recommended power supply filtering and decoupling method.




Figure 10-1. Power Supply Decoupling



11 Layout

11.1 Layout Guidelines

The following section provides the layout guidelines to ensure good thermal performance and power supply connections for the CDCDB400.

In *Layout Examples*, the CDCDB400 has $85-\Omega$ differential output impedance LP-HCSL format drivers as per register default settings. All transmission lines connected to CKx pins should be $85-\Omega$ differential impedance, $42.5-\Omega$ single-ended impedance to avoid reflections and increased radiated emissions. If $100-\Omega$ output impedance is enabled, the transmission lines connected to CKx pins should be $100-\Omega$ differential impedance, $50-\Omega$ single-ended impedance. Take care to eliminate or reduce stubs on the transmission lines.

11.2 Layout Examples

Figure 11-1 through Figure 11-3 are printed circuit board (PCB) layout examples that show the application of thermal design practices and a low-inductance ground connection between the device DAP and the PCB.




Figure 11-1. PCB Layout Example for CDCDB400, Top layer




Figure 11-2. PCB Layout Example for CDCDB400, GND Layer




Figure 11-3. PCB Layout Example for CDCDB400, Bottom Layer



12 Device and Documentation Support

12.1 Device Support

12.1.1 TICS Pro

TICS Pro is an offline software tool for EVM programming and also for register map generation to program a device configuration for a specific application. For TICS Pro, go to https://www.ti.com/tool/TICSPRO-SW.

12.2 Receiving Notification of Documentation Updates

To receive notification of documentation updates, navigate to the device product folder on ti.com. Click on *Subscribe to updates* to register and receive a weekly digest of any product information that has changed. For change details, review the revision history included in any revised document.

12.3 Support Resources

TI E2E[™] support forums are an engineer's go-to source for fast, verified answers and design help — straight from the experts. Search existing answers or ask your own question to get the quick design help you need.

Linked content is provided "AS IS" by the respective contributors. They do not constitute TI specifications and do not necessarily reflect TI's views; see TI's Terms of Use.

12.4 Trademarks

TI E2E[™] is a trademark of Texas Instruments. All trademarks are the property of their respective owners.

12.5 Electrostatic Discharge Caution



This integrated circuit can be damaged by ESD. Texas Instruments recommends that all integrated circuits be handled with appropriate precautions. Failure to observe proper handling and installation procedures can cause damage.

ESD damage can range from subtle performance degradation to complete device failure. Precision integrated circuits may be more susceptible to damage because very small parametric changes could cause the device not to meet its published specifications.

12.6 Glossary

TI Glossary This glossary lists and explains terms, acronyms, and definitions.

13 Mechanical, Packaging, and Orderable Information

The following pages include mechanical, packaging, and orderable information. This information is the most current data available for the designated devices. This data is subject to change without notice and revision of this document. For browser-based versions of this data sheet, refer to the left-hand navigation.



PACKAGING INFORMATION

Orderable Device	Status (1)	Package Type	Package Drawing	Pins	Package Qty	Eco Plan (2)	Lead finish/ Ball material (6)	MSL Peak Temp (3)	Op Temp (°C)	Device Marking (4/5)	Samples
CDCDB400RHBR	ACTIVE	VQFN	RHB	32	3000	RoHS & Green	NIPDAU	Level-1-260C-UNLIM	-40 to 105	CDCB400	Samples
CDCDB400RHBT	ACTIVE	VQFN	RHB	32	250	RoHS & Green	NIPDAU	Level-1-260C-UNLIM	-40 to 105	CDCB400	Samples

⁽¹⁾ The marketing status values are defined as follows:

ACTIVE: Product device recommended for new designs.

LIFEBUY: TI has announced that the device will be discontinued, and a lifetime-buy period is in effect.

NRND: Not recommended for new designs. Device is in production to support existing customers, but TI does not recommend using this part in a new design.

PREVIEW: Device has been announced but is not in production. Samples may or may not be available.

OBSOLETE: TI has discontinued the production of the device.

⁽²⁾ RoHS: TI defines "RoHS" to mean semiconductor products that are compliant with the current EU RoHS requirements for all 10 RoHS substances, including the requirement that RoHS substance do not exceed 0.1% by weight in homogeneous materials. Where designed to be soldered at high temperatures, "RoHS" products are suitable for use in specified lead-free processes. TI may reference these types of products as "Pb-Free".

RoHS Exempt: TI defines "RoHS Exempt" to mean products that contain lead but are compliant with EU RoHS pursuant to a specific EU RoHS exemption.

Green: TI defines "Green" to mean the content of Chlorine (CI) and Bromine (Br) based flame retardants meet JS709B low halogen requirements of <=1000ppm threshold. Antimony trioxide based flame retardants must also meet the <=1000ppm threshold requirement.

⁽³⁾ MSL, Peak Temp. - The Moisture Sensitivity Level rating according to the JEDEC industry standard classifications, and peak solder temperature.

⁽⁴⁾ There may be additional marking, which relates to the logo, the lot trace code information, or the environmental category on the device.

⁽⁵⁾ Multiple Device Markings will be inside parentheses. Only one Device Marking contained in parentheses and separated by a "~" will appear on a device. If a line is indented then it is a continuation of the previous line and the two combined represent the entire Device Marking for that device.

⁽⁶⁾ Lead finish/Ball material - Orderable Devices may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead finish/Ball material values may wrap to two lines if the finish value exceeds the maximum column width.

Important Information and Disclaimer: The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.



www.ti.com

PACKAGE OPTION ADDENDUM

10-Apr-2023



Texas

STRUMENTS

TAPE AND REEL INFORMATION





QUADRANT ASSIGNMENTS FOR PIN 1 ORIENTATION IN TAPE



*All dimensions are nominal												
Device	Package Type	Package Drawing		SPQ	Reel Diameter (mm)	Reel Width W1 (mm)	A0 (mm)	B0 (mm)	K0 (mm)	P1 (mm)	W (mm)	Pin1 Quadrant
CDCDB400RHBR	VQFN	RHB	32	3000	330.0	12.4	5.3	5.3	1.1	8.0	12.0	Q2
CDCDB400RHBT	VQFN	RHB	32	250	180.0	12.4	5.3	5.3	1.1	8.0	12.0	Q2



www.ti.com

PACKAGE MATERIALS INFORMATION

3-Jun-2022



*All dimensions are nominal

Device	Package Type	Package Drawing	Pins	SPQ	Length (mm)	Width (mm)	Height (mm)
CDCDB400RHBR	VQFN	RHB	32	3000	367.0	367.0	35.0
CDCDB400RHBT	VQFN	RHB	32	250	210.0	185.0	35.0

RHB 32

5 x 5, 0.5 mm pitch

GENERIC PACKAGE VIEW

VQFN - 1 mm max height

PLASTIC QUAD FLATPACK - NO LEAD



Images above are just a representation of the package family, actual package may vary. Refer to the product data sheet for package details.




RHB0032T



PACKAGE OUTLINE

VQFN - 1 mm max height

PLASTIC QUAD FLATPACK - NO LEAD



NOTES:

- 1. All linear dimensions are in millimeters. Any dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M. 2. This drawing is subject to change without notice.
- 3. The package thermal pad must be soldered to the printed circuit board for thermal and mechanical performance.




RHB0032T

EXAMPLE BOARD LAYOUT

VQFN - 1 mm max height

PLASTIC QUAD FLATPACK - NO LEAD



NOTES: (continued)

 This package is designed to be soldered to a thermal pad on the board. For more information, see Texas Instruments literature number SLUA271 (www.ti.com/lit/slua271).

5. Vias are optional depending on application, refer to device data sheet. If any vias are implemented, refer to their locations shown on this view. It is recommended that vias under paste be filled, plugged or tented.




RHB0032T

EXAMPLE STENCIL DESIGN

VQFN - 1 mm max height

PLASTIC QUAD FLATPACK - NO LEAD



NOTES: (continued)

6. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.



IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATA SHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, regulatory or other requirements.

These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you will fully indemnify TI and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to TI's Terms of Sale or other applicable terms available either on ti.com or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products.

TI objects to and rejects any additional or different terms you may have proposed.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265 Copyright © 2023, Texas Instruments Incorporated