

DS92LV010A

www.ti.com

SNLS007E - MAY 1998-REVISED APRIL 2013

DS92LV010A Bus LVDS 3.3/5.0V Single Transceiver

Check for Samples: DS92LV010A

FEATURES

- Bus LVDS Signaling (BLVDS)
- Designed for Double Termination Applications
- Balanced Output Impedance
- Lite Bus Loading 5pF Typical
- Glitch Free Power Up/Down (Driver Disabled)
- 3.3V or 5.0V Operation
- ±1V Common Mode Range
- ±100mV Receiver Sensitivity
- High Signaling Rate Capability (Above 100 Mbps)
- Low Power CMOS Design
- Product Offered in 8 Lead SOIC Package
- Industrial Temperature Range Operation

DESCRIPTION

The DS92LV010A is one in a series of transceivers designed specifically for the high speed, low power proprietary bus backplane interfaces. The device operates from a single 3.3V or 5.0V power supply and includes one differential line driver and one receiver. To minimize bus loading the driver outputs and receiver inputs are internally connected. The logic interface provides maximum flexibility as 4 separate lines are provided (DIN, DE, RE, and ROUT). The device also features flow through which allows easy PCB routing for short stubs between the bus pins and the connector. The driver has 10 mA drive capability, allowing it to drive heavily loaded backplanes, with impedance as low as 27 Ohms.

The driver translates between TTL levels (singleended) to Low Voltage Differential Signaling levels. This allows for high speed operation, while consuming minimal power with reduced EMI. In addition the differential signaling provides common mode noise rejection of $\pm 1V$.

The receiver threshold is ± 100 mV over a ± 1 V common mode range and translates the low voltage differential levels to standard (CMOS/TTL) levels.

CONNECTION DIAGRAM





Figure 1. SOIC Package See Package Number D0008A

BLOCK DIAGRAM



Please be aware that an important notice concerning availability, standard warranty, and use in critical applications of Texas Instruments semiconductor products and disclaimers thereto appears at the end of this data sheet. All trademarks are the property of their respective owners.

DS92LV010A

SNLS007E - MAY 1998-REVISED APRIL 2013

XAS STRUMENTS

www.ti.com



These devices have limited built-in ESD protection. The leads should be shorted together or the device placed in conductive foam during storage or handling to prevent electrostatic damage to the MOS gates.

ABSOLUTE MAXIMUM RATINGS (1)(2)(3)

Supply Voltage (V _{CC})		6.0V	
Enable Input Voltage (DE, RE)		-0.3V to (V _{CC} + 0.3V)	
Driver Input Voltage (DIN)	Driver Input Voltage (DIN)		
Receiver Output Voltage (R _{OUT})	Receiver Output Voltage (R _{OUT})		
Bus Pin Voltage (DO/RI±)	-0.3V to + 3.9V		
Driver Short Circuit Current	Continuous		
ESD (HBM 1.5 kΩ, 100 pF)		>2.0 kV	
Maximum Package Power Dissipation at 25°C	SOIC	1025 mW	
	Derate SOIC Package	8.2 mW/°C	
Junction Temperature	Junction Temperature		
Storage Temperature Range	−65°C to +150°C		
Lead Temperature (Soldering, 4 sec.)		260°C	

(1) All currents into device pins are positive; all currents out of device pins are negative. All voltages are referenced to device ground except V_{OD} , V_{ID} , V_{TH} and V_{TL} unless otherwise specified.

Absolute Maximum Ratings are these beyond which the safety of the device cannot be ensured. They are not meant to imply that the (2)device should be operated at these limits. The table of "Electrical Characteristics" provides conditions for actual device operation. If Military/Aerospace specified devices are required, please contact the Texas Instruments Sales Office/ Distributors for availability and

(3)specifications.

RECOMMENDED OPERATING CONDITIONS

	Min	Max	Units
Supply Voltage (V _{CC}), or	3.0	3.6	V
Supply Voltage (V _{CC})	4.5	5.5	V
Receiver Input Voltage	0.0	2.9	V
Operating Free Air Temperature	-40	+85	°C



SNLS007E - MAY 1998-REVISED APRIL 2013

www.ti.com

3.3V DC ELECTRICAL CHARACTERISTICS (1)(2)

 T_{A} = -40°C to +85°C unless otherwise noted, V_{CC} = 3.3V \pm 0.3V

	Parameter	Test Conditio	ns	Pin	Min	Тур	Max	Units
V _{OD}	Output Differential Voltage	$R_L = 27\Omega$, See Figure 3		DO+/RI+,	140	250	360	mV
ΔV_{OD}	V _{OD} Magnitude Change	_		DO-/RI-		3	30	mV
V _{OS}	Offset Voltage				1	1.25	1.65	V
ΔV_{OS}	Offset Magnitude Change					5	50	mV
I _{OSD}	Output Short Circuit Current	$V_0 = 0V, DE = V_{CC}$				-12	-20	mA
V _{OH}	Voltage Output High	V _{ID} = +100 mV	I _{OH} = −400 µA	R _{OUT}	2.8	3		V
		Inputs Open			2.8	3		V
		Inputs Shorted			2.8	3		V
		Inputs Terminated, $R_L = 27\Omega$			2.8	3		V
V _{OL}	Voltage Output Low	$I_{OL} = 2.0 \text{ mA}, V_{ID} = -100 \text{ mV}$				0.1	0.4	V
l _{OS}	Output Short Circuit Current	$V_{OUT} = 0V, V_{ID} = +100 \text{ mV}$			-5	-35	-85	mA
V _{TH}	Input Threshold High	DE = 0V		DO+/RI+,			+100	mV
V _{TL}	Input Threshold Low			DO-/RI-	-100			mV
I _{IN}	Input Current	$DE = 0V, V_{IN} = +2.4V, \text{ or } 0V$			-20	±1	+20	μA
		$V_{CC} = 0V, V_{IN} = +2.4V, \text{ or } 0V$			-20	±1	+20	μA
VIH	Minimum Input High Voltage			DIN,	2.0		V _{CC}	V
V _{IL}	Maximum Input Low Voltage			DE,RE	GND		0.8	V
I _{IH}	Input High Current	$V_{IN} = V_{CC} \text{ or } 2.4 V$		_		±1	±10	μA
IIL	Input Low Current	V _{IN} = GND or 0.4V				±1	±10	μA
V _{CL}	Input Diode Clamp Voltage	$I_{CLAMP} = -18 \text{ mA}$			-1.5	-0.8		V
ICCD	Power Supply Current	$DE = \overline{RE} = V_{CC}$, $R_L = 27\Omega$		V _{CC}		13	20	mA
I _{CCR}		$DE = \overline{RE} = 0V$				5	8	mA
I _{CCZ}		$DE = 0V, \overline{RE} = V_{CC}$				3	7.5	mA
I _{CC}		$DE = V_{CC}, \overline{RE} = 0V, R_L = 27\Omega$				16	22	mA
C _{output}	Capacitance @ BUS Pins			DO+/RI+, DO-/RI-		5		pF

All currents into device pins are positive; all currents out of device pins are negative. All voltages are referenced to device ground except (1) V_{OD} , V_{ID} , V_{TH} and V_{TL} unless otherwise specified. All typicals are given for V_{CC} = +3.3V or 5.0 V and T_{A} = +25°C, unless otherwise stated.

(2)

SNLS007E-MAY 1998-REVISED APRIL 2013

5V DC ELECTRICAL CHARACTERISTICS (1)(2)

 $T_A = -40^{\circ}C$ to +85°C unless otherwise noted, $V_{CC} = 5.0V \pm 0.5V$

Parameter		Test Conditions		Pin	Min	Тур	Max	Units
V _{OD}	Output Differential Voltage	$R_L = 27\Omega$, See Figure 3		DO+/RI+,	145	270	390	mV
ΔV_{OD}	V _{OD} Magnitude Change	_		DO-/RI-		3	30	mV
V _{OS}	Offset Voltage				1	1.35	1.65	V
ΔV_{OS}	Offset Magnitude Change					5	50	mV
I _{OSD}	Output Short Circuit Current	$V_{O} = 0V, DE = V_{CC}$				-12	-20	mA
V _{OH}	Voltage Output High	V _{ID} = +100 mV	I _{OH} = -400 μA	R _{OUT}	4.3	5.0		V
		Inputs Open			4.3	5.0		V
		Inputs Shorted			4.3	5.0		V
		Inputs Terminated, $R_L = 27\Omega$	_		4.3	5.0		V
V _{OL}	Voltage Output Low	$I_{OL} = 2.0 \text{ mA}, V_{ID} = -100 \text{ mV}$				0.1	0.4	V
l _{os}	Output Short Circuit Current	V _{OUT} = 0V, V _{ID} = +100 mV			-35	-90	-130	mA
V _{TH}	Input Threshold High	DE = 0V		DO+/RI+,			+100	mV
V _{TL}	Input Threshold Low			DO-/RI-	-100			mV
I _{IN}	Input Current	$DE = 0V, V_{IN} = +2.4V, \text{ or } 0V$			-20	±1	+20	μA
		$V_{CC} = 0V, V_{IN} = +2.4V, \text{ or } 0V$			-20	±1	+20	μA
VIH	Minimum Input High Voltage			DIN, DE,	2.0		V _{CC}	V
V _{IL}	Maximum Input Low Voltage			RE	GND		0.8	V
I _{IH}	Input High Current	$V_{IN} = V_{CC} \text{ or } 2.4 \text{V}$				±1	±10	μA
I _{IL}	Input Low Current	V _{IN} = GND or 0.4V				±1	±10	μA
V _{CL}	Input Diode Clamp Voltage	I _{CLAMP} = −18 mA			-1.5	-0.8		V
ICCD	Power Supply Current	$DE = \overline{RE} = V_{CC}, R_L = 27\Omega$		V _{cc}		17	25	mA
ICCR		$DE = \overline{RE} = 0V$				6	10	mA
I _{CCZ}		$DE = 0V, \overline{RE} = V_{CC}$				3	8	mA
I _{CC}		$DE = V_{CC}, \overline{RE} = 0V, R_L = 27\Omega$				20	25	mA
C _{output}	Capacitance @ BUS Pins			DO+/RI+, DO-/RI-		5		pF

All currents into device pins are positive; all currents out of device pins are negative. All voltages are referenced to device ground except (1) V_{OD} , V_{ID} , V_{TH} and V_{TL} unless otherwise specified. All typicals are given for V_{CC} = +3.3V or 5.0 V and T_{A} = +25°C, unless otherwise stated.

(2)

4 Submit Documentation Feedback



SNLS007E - MAY 1998-REVISED APRIL 2013

www.ti.com

3.3V AC ELECTRICAL CHARACTERISTICS ⁽¹⁾

	Parameter	Parameter Test Conditions		Тур	Max	Units
DIFFER	RENTIAL DRIVER TIMING REQUIR	EMENTS				
t _{PHLD}	Differential Prop. Delay High to Low	$R_L = 27\Omega$, See Figure 4 and Figure 5 $C_L = 10 \text{ pF}$	1.0	3.0	5.0	ns
t _{PLHD}	Differential Prop. Delay Low to High		1.0	2.8	5.0	ns
t _{SKD}	Differential SKEW t _{PHLD} - t _{PLHD}	D 070 Cas Firms Casad Firms 7		0.2	1.0	ns
t _{TLH}	Transition Time Low to High			0.3	2.0	ns
t _{THL}	Transition Time High to Low			0.3	2.0	ns
t _{PHZ}	Disable Time High to Z	$R_L = 27\Omega$, See Figure 6 and Figure 7 $C_L = 10 \text{ pF}$	0.5	4.5	9.0	ns
t _{PLZ}	Disable Time Low to Z		0.5	5.0	10.0	ns
t _{PZH}	Enable Time Z to High		2.0	5.0	7.0	ns
t _{PZL}	Enable Time Z to Low		1.0	4.5	9.0	ns
DIFFER	RENTIAL RECEIVER TIMING REQU	IREMENTS				
t _{PHLD}	Differential Prop. Delay High to Low	See Figure 8 and Figure 9 $C_L = 10 \text{ pF}$	2.5	5.0	12.0	ns
t _{PLHD}	Differential Prop. Delay Low to High		2.5	5.5	10.0	ns
t _{SKD}	Differential SKEW t _{PHLD} - t _{PLHD}			0.5	2.0	ns
t _r	Rise Time			1.5	4.0	ns
t _f	Fall Time			1.5	4.0	ns
t _{PHZ}	Disable Time High to Z	$R_L = 500\Omega$, See Figure 10 and Figure 11	2.0	4.0	6.0	ns
t _{PLZ}	Disable Time Low to Z	$C_{L}^{L} = 10 \text{ pF}^{(2)}$	2.0	5.0	7.0	ns
t _{PZH}	Enable Time Z to High		2.0	7.0	13.0	ns
t _{PZL}	Enable Time Z to Low		2.0	6.0	10.0	ns

(1) Generator waveforms for all tests unless otherwise specified: f = 1MHz, $ZO = 50\Omega$, tr, $tf \le 6.0ns$ (0%–100%) on control pins and $\le 1.0ns$ for RI inputs.

(2) For receiver tri-state delays, the switch is set to V_{CC} for t_{PZL} , and t_{PLZ} and to GND for t_{PZH} , and t_{PHZ} .

SNLS007E - MAY 1998-REVISED APRIL 2013



www.ti.com

5V AC ELECTRICAL CHARACTERISTICS (1)

Т. –	-40°C to	+85°C	Vac -	50V +	0.51/

	Parameter	Test Conditions	Min	Тур	Max	Units
DIFFER	ENTIAL DRIVER TIMING REQUIRE	EMENTS				
t _{PHLD}	Differential Prop. Delay High to Low	R_L = 27 Ω , See Figure 4 and Figure 5 C_L = 10 pF	0.5	2.7	4.5	ns
t _{PLHD}	Differential Prop. Delay Low to High		0.5	2.5	4.5	ns
t _{SKD}	Differential SKEW t _{PHLD} - t _{PLHD}			0.2	1.0	ns
t _{TLH}	Transition Time Low to High			0.3	2.0	ns
t _{THL}	Transition Time High to Low			0.3	2.0	ns
t _{PHZ}	Disable Time High to Z	R_L = 27Ω, See Figure 6 and Figure 7 C_L = 10 pF	0.5	3.0	7.0	ns
t _{PLZ}	Disable Time Low to Z		0.5	5.0	10.0	ns
t _{PZH}	Enable Time Z to High		2.0	4.0	7.0	ns
t _{PZL}	Enable Time Z to Low		1.0	4.0	9.0	ns
DIFFER	ENTIAL RECEIVER TIMING REQU	IREMENTS				
t _{PHLD}	Differential Prop. Delay High to Low	See Figure 8 and Figure 9 $C_L = 10 \text{ pF}$	2.5	5.0	12.0	ns
t _{PLHD}	Differential Prop. Delay Low to High		2.5	4.6	10.0	ns
t _{SKD}	Differential SKEW t _{PHLD} - t _{PLHD}			0.4	2.0	ns
t _r	Rise Time			1.2	2.5	ns
t _f	Fall Time]		1.2	2.5	ns
t _{PHZ}	Disable Time High to Z	$R_L = 500\Omega$, See Figure 10 and Figure 11	2.0	4.0	6.0	ns
t _{PLZ}	Disable Time Low to Z	$C_{L} = 10 \text{ pF}^{(2)}$	2.0	4.0	6.0	ns
t _{PZH}	Enable Time Z to High		2.0	5.0	9.0	ns
t _{PZL}	Enable Time Z to Low		2.0	5.0	7.0	ns

Generator waveforms for all tests unless otherwise specified: f = 1MHz, ZO = 50Ω, tr, tf ≤ 6.0ns (0%-100%) on control pins and ≤ 1.0ns for RI inputs.

(2) For receiver tri-state delays, the switch is set to V_{CC} for t_{PZL} , and t_{PLZ} and to GND for t_{PZH} , and t_{PHZ} .

TEST CIRCUITS AND TIMING WAVEFORMS




Figure 3. Differential Driver DC Test Circuit




Figure 4. Differential Driver Propagation Delay and Transition Time Test Circuit






Figure 5. Differential Driver Propagation Delay and Transition Time Waveforms











SNLS007E - MAY 1998-REVISED APRIL 2013




Figure 8. Receiver Propagation Delay and Transition Time Test Circuit




Figure 9. Receiver Propagation Delay and Transition Time Waveforms




Figure 10. Receiver TRI-STATE Delay Test Circuit




Figure 11. Receiver TRI-STATE Delay Waveforms TRI-STATE Delay Waveforms

TYPICAL BUS APPLICATION CONFIGURATIONS




Figure 12. Bi-Directional Half-Duplex Point-to-Point Applications

8






Figure 13. Multi-Point Bus Applications

DS92LV010A

SNLS007E-MAY 1998-REVISED APRIL 2013

TEXAS INSTRUMENTS

www.ti.com

APPLICATION INFORMATION

There are a few common practices which should be implied when designing PCB for BLVDS signaling. Recommended practices are:

- Use at least 4 layer PCB board (BLVDS signals, ground, power and TTL signals).
- Keep drivers and receivers as close to the (BLVDS port side) connector as possible.
- Bypass each BLVDS device and also use distributed bulk capacitance. Surface mount capacitors placed close to power and ground pins work best. Two or three multi-layer ceramic (MLC) surface mount capacitors (0.1 μ F, and 0.01 μ F in parallel should be used between each V_{CC} and ground. The capacitors should be as close as possible to the V_{CC} pin.
- Use the termination resistor which best matches the differential impedance of your transmission line.
- Leave unused LVDS receiver inputs open (floating)

MODE SELECTED	DE	RE
DRIVER MODE	Н	Н
RECEIVER MODE	L	L
TRI-STATE MODE	L	Н
LOOP BACK MODE	Н	L

Table 1. Functional Table

Table 2. Transmitter Mode⁽¹⁾

INPUTS		OUTI	PUTS
DE	DI	DO+	DO-
Н	L	L	Н
Н	Н	Н	L
Н	2 > & > 0.8	Х	Х
L	Х	Z	Z

(1) L = Low state

H = High state

Table 3. Receiver Mode⁽¹⁾

	INPUTS		
RE	(RI+)-(RI−)	OUTPUT	
L	L (< -100 mV)	L	
L	H (> +100 mV)	Н	
L	100 mV > & > −100 mV	х	
Н	X	Z	

(1) X = High or Low logic state

Z = High impedance state

L = Low state

H = High state

Table 4. Device Pin Descriptions

Pin Name	Pin No.	Input/Output	Description	
DIN	2	I	TTL Driver Input	
DO±/RI±	6, 7	I/O	LVDS Driver Outputs/LVDS Receiver Inputs	
R _{OUT}	3	0	TTL Receiver Output	
RE	5	I	Receiver Enable TTL Input (Active Low)	
DE	1	l	Driver Enable TTL Input (Active High)	
GND	4	NA	Ground	
V _{CC}	8	NA	Power Supply	

TEXAS INSTRUMENTS

www.ti.com

SNLS007E - MAY 1998-REVISED APRIL 2013

Cł	anges from Revision D (April 2013) to Revision E	Page
•	Changed layout of National Data Sheet to TI format	. 10



PACKAGING INFORMATION

Orderable Device		Package Type	Package Drawing	Pins	•	Eco Plan	Lead finish/ Ball material	MSL Peak Temp	Op Temp (°C)	Device Marking	Samples
	(1)		Drawing		Qty	(2)	(6)	(3)		(4/5)	
DS92LV010ATM	LIFEBUY	SOIC	D	8	95	Non-RoHS & Green	Call TI	Level-1-235C-UNLIM	-40 to 85	LV010 ATM	
DS92LV010ATM/NOPB	ACTIVE	SOIC	D	8	95	RoHS & Green	SN	Level-1-260C-UNLIM	-40 to 85	LV010 ATM	Samples
DS92LV010ATMX	LIFEBUY	SOIC	D	8	2500	Non-RoHS & Green	Call TI	Level-1-235C-UNLIM	-40 to 85	LV010 ATM	
DS92LV010ATMX/NOPB	ACTIVE	SOIC	D	8	2500	RoHS & Green	SN	Level-1-260C-UNLIM	-40 to 85	LV010 ATM	Samples

⁽¹⁾ The marketing status values are defined as follows:

ACTIVE: Product device recommended for new designs.

LIFEBUY: TI has announced that the device will be discontinued, and a lifetime-buy period is in effect.

NRND: Not recommended for new designs. Device is in production to support existing customers, but TI does not recommend using this part in a new design.

PREVIEW: Device has been announced but is not in production. Samples may or may not be available.

OBSOLETE: TI has discontinued the production of the device.

⁽²⁾ RoHS: TI defines "RoHS" to mean semiconductor products that are compliant with the current EU RoHS requirements for all 10 RoHS substances, including the requirement that RoHS substance do not exceed 0.1% by weight in homogeneous materials. Where designed to be soldered at high temperatures, "RoHS" products are suitable for use in specified lead-free processes. TI may reference these types of products as "Pb-Free".

RoHS Exempt: TI defines "RoHS Exempt" to mean products that contain lead but are compliant with EU RoHS pursuant to a specific EU RoHS exemption.

Green: TI defines "Green" to mean the content of Chlorine (CI) and Bromine (Br) based flame retardants meet JS709B low halogen requirements of <=1000ppm threshold. Antimony trioxide based flame retardants must also meet the <=1000ppm threshold requirement.

⁽³⁾ MSL, Peak Temp. - The Moisture Sensitivity Level rating according to the JEDEC industry standard classifications, and peak solder temperature.

⁽⁴⁾ There may be additional marking, which relates to the logo, the lot trace code information, or the environmental category on the device.

⁽⁵⁾ Multiple Device Markings will be inside parentheses. Only one Device Marking contained in parentheses and separated by a "~" will appear on a device. If a line is indented then it is a continuation of the previous line and the two combined represent the entire Device Marking for that device.

⁽⁶⁾ Lead finish/Ball material - Orderable Devices may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead finish/Ball material values may wrap to two lines if the finish value exceeds the maximum column width.

Important Information and Disclaimer: The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and



continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.



Texas

STRUMENTS

TAPE AND REEL INFORMATION





QUADRANT ASSIGNMENTS FOR PIN 1 ORIENTATION IN TAPE



*All dimensions are nominal												
Device	-	Package Drawing		SPQ	Reel Diameter (mm)	Reel Width W1 (mm)	A0 (mm)	B0 (mm)	K0 (mm)	P1 (mm)	W (mm)	Pin1 Quadrant
DS92LV010ATMX	SOIC	D	8	2500	330.0	12.4	6.5	5.4	2.0	8.0	12.0	Q1
DS92LV010ATMX/NOPB	SOIC	D	8	2500	330.0	12.4	6.5	5.4	2.0	8.0	12.0	Q1



PACKAGE MATERIALS INFORMATION

9-Aug-2022



*All dimensions are nominal

Device	Package Type	Package Drawing	Pins SPQ		Length (mm)	Width (mm)	Height (mm)	
DS92LV010ATMX	SOIC	D	8	2500	367.0	367.0	35.0	
DS92LV010ATMX/NOPB	SOIC	D	8	2500	367.0	367.0	35.0	

TEXAS INSTRUMENTS

www.ti.com

9-Aug-2022

TUBE



- B - Alignment groove width

*All dimensions are nominal

Device	Package Name	Package Type	Pins	SPQ	L (mm)	W (mm)	Τ (μm)	B (mm)
DS92LV010ATM	D	SOIC	8	95	495	8	4064	3.05
DS92LV010ATM	D	SOIC	8	95	495	8	4064	3.05
DS92LV010ATM/NOPB	D	SOIC	8	95	495	8	4064	3.05

D0008A



PACKAGE OUTLINE

SOIC - 1.75 mm max height

SMALL OUTLINE INTEGRATED CIRCUIT



NOTES:

1. Linear dimensions are in inches [millimeters]. Dimensions in parenthesis are for reference only. Controlling dimensions are in inches. Dimensioning and tolerancing per ASME Y14.5M.

- 2. This drawing is subject to change without notice.
- 3. This dimension does not include mold flash, protrusions, or gate burrs. Mold flash, protrusions, or gate burrs shall not exceed .006 [0.15] per side.
- 4. This dimension does not include interlead flash.
- 5. Reference JEDEC registration MS-012, variation AA.



D0008A

EXAMPLE BOARD LAYOUT

SOIC - 1.75 mm max height

SMALL OUTLINE INTEGRATED CIRCUIT



NOTES: (continued)

6. Publication IPC-7351 may have alternate designs.

7. Solder mask tolerances between and around signal pads can vary based on board fabrication site.



D0008A

EXAMPLE STENCIL DESIGN

SOIC - 1.75 mm max height

SMALL OUTLINE INTEGRATED CIRCUIT



NOTES: (continued)

8. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.

9. Board assembly site may have different recommendations for stencil design.



IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATA SHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, regulatory or other requirements.

These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you will fully indemnify TI and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to TI's Terms of Sale or other applicable terms available either on ti.com or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products.

TI objects to and rejects any additional or different terms you may have proposed.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265 Copyright © 2024, Texas Instruments Incorporated