www.ti.com

# +3.3V Programmable LVDS Transmitter 24-Bit Flat Panel Display (FPD) Link-65 MHz

Check for Samples: DS90CF383B

#### **FEATURES**

- No Special Start-up Sequence Required Between Clock/Data and /PD Pins. Input Signal (Clock and Data) Can be Applied Either Before or After the Device is Powered.
- Support Spread Spectrum Clocking Up to 100KHz Frequency Modulation & Deviations of ±2.5% Center Spread or −5% Down Spread.
- "Input Clock Detection" Feature Will Pull All LVDS Pairs to Logic Low when Input Clock is Missing and When /PD Pin is Logic High.
- 18 to 68 MHz Shift Clock Support
- Best-in-Class Set & Hold Times on TxINPUTs
- Tx Power Consumption < 130 mW (typ) @65MHz Grayscale
- 40% Less Power Dissipation Than BiCMOS Alternatives
- Tx Power-down Mode < 60µW (typ)</li>
- Supports VGA, SVGA, XGA and Dual Pixel SXGA.
- Narrow Cus Reduces Cable Size and Cost
- Up to 1.8 Gbps Throughput
- Up to 227 Megabytes/sec Bandwidth
- 345 mV (typ) Swing LVDS Devices for Low EMI
- PLL Requires No External Components
- Compatible with TIA/EIA-644 LVDS Standard
- Low Profile 56-Lead TSSOP Package
- Improved Replacement for:
  - SN75LVDS83, DS90CF383A

#### **DESCRIPTION**

The DS90CF383B transmitter converts 28 bits of CMOS/TTL data into four LVDS (Low Voltage Differential Signaling) data streams. A phase-locked transmit clock is transmitted in parallel with the data streams over a fifth LVDS link. Every cycle of the transmit clock 28 bits of input data are sampled and transmitted. At a transmit clock frequency of 65 MHz, 24 bits of RGB data and 3 bits of LCD timing and control data (FPLINE, FPFRAME, DRDY) are transmitted at a rate of 455 Mbps per LVDS data channel. Using a 65 MHz clock, the data throughput is 227 Mbytes/sec. The DS90CF383B is fixed as a Falling edge strobe transmitter and will interoperate with a Falling edge strobe Receiver (DS90CF386) without any translation logic.

This chipset is an ideal means to solve EMI and cable size problems associated with wide, high speed TTL interfaces.

松


Please be aware that an important notice concerning availability, standard warranty, and use in critical applications of Texas Instruments semiconductor products and disclaimers thereto appears at the end of this data sheet.

TRI-STATE is a registered trademark of Texas Instruments.

All other trademarks are the property of their respective owners.



#### **Block Diagram**



DS90CF383B See Package Number DGG0056A



These devices have limited built-in ESD protection. The leads should be shorted together or the device placed in conductive foam during storage or handling to prevent electrostatic damage to the MOS gates.

# **Absolute Maximum Ratings** (1)(2)(1)

|  | Value                            | Unit |
|--|----------------------------------|------|
| Supply Voltage (V <sub>CC</sub> )  | -0.3V to +4                      | V    |
| CMOS/TTL Input Voltage   | -0.3V to (V <sub>CC</sub> + 0.3) | V    |
| LVDS Driver Output Voltage   | -0.3V to (V <sub>CC</sub> + 0.3) | V    |
| LVDS Output Short Circuit Duration   | Continuous                       |      |
| Junction Temperature   | +150                             | °C   |
| Storage Temperature  | −65°C to +150                    | °C   |
| Lead Temperature (Soldering, 4 sec)  | +260                             | °C   |
| Maximum Package Power Dissipation Capacity @ 25°C DGG0056A (TSSOP) Package: DS90CF383B | 1.63                             | W    |
| Package Derating:<br>DS90CF383B  | 12.5 mW/°C above<br>+25°C        |      |
| ESD Rating (HBM, 1.5 kΩ, 100 pF)   | 7                                | kV   |
| ESD Rating (EIAJ, 0Ω, 200 pF)  | 500                              | V    |

- (1) If Military/Aerospace specified devices are required, please contact the TI Sales Office/ Distributors for availability and specifications.
- (2) "Absolute Maximum Ratings" are those values beyond which the safety of the device cannot be verified. They are not meant to imply that the device should be operated at these limits. The "Electrical Characteristics" specify conditions for device operation.

# **Recommended Operating Conditions**

|  | Min | Nom | Max | Units   |
|--|-----|-----|-----|---------|
| Supply Voltage (V <sub>CC</sub> )                | 3.0 | 3.3 | 3.6 | V       |
| Operating Free Air Temperature (T <sub>A</sub> ) | -10 | +25 | +70 | °C      |
| Supply Noise Voltage (V <sub>CC</sub> )          |     |     | 200 | $mV_PP$ |
| TxCLKIN frequency                                | 18  |     | 68  | MHz     |

## Electrical Characteristics(1)

Over recommended operating supply and temperature ranges unless otherwise specified.

 Current into device pins is defined as positive. Current out of device pins is defined as negative. Voltages are referenced to ground unless otherwise specified (except V<sub>OD</sub> and ΔV<sub>OD</sub>).



# Electrical Characteristics<sup>(1)</sup> (continued)

Over recommended operating supply and temperature ranges unless otherwise specified

| Symbol          | Parameter   | Condition  | าร                    | Min  | Typ <sup>(2)</sup> | Max             | Units |
|-----------------|---|--|-----------------------|------|--------------------|-----------------|-------|
| CMOS/TT         | L DC SPECIFICATIONS   |  |                       |      |                    |                 |       |
| V <sub>IH</sub> | High Level Input Voltage                                      |  |                       | 2.0  |                    | V <sub>CC</sub> | V     |
| V <sub>IL</sub> | Low Level Input Voltage                                       |  |                       | GND  |                    | 0.8             | V     |
| V <sub>CL</sub> | Input Clamp Voltage   | I <sub>CL</sub> = −18 mA   |                       |      | -0.79              | <b>-</b> 1.5    | V     |
| I <sub>IN</sub> | Input Current   | $V_{IN} = 0.4V$ , 2.5V or $V_{CC}$   |                       |      | +1.8               | +10             | μΑ    |
|                 |   | V <sub>IN</sub> = GND  | -10                   | 0    |                    | μΑ              |       |
| LVDS DC         | SPECIFICATIONS  |  |                       |      |                    |                 | *     |
| V <sub>OD</sub> | Differential Output Voltage                                   | $R_L = 100\Omega$  |                       | 250  | 345                | 450             | mV    |
| $\Delta V_{OD}$ | Change in V <sub>OD</sub> between complimentary output states |  |                       |      |                    | 35              | mV    |
| Vos             | Offset Voltage (3)  |  |                       | 1.13 | 1.25               | 1.38            | V     |
| $\Delta V_{OS}$ | Change in V <sub>OS</sub> between complimentary output states |  |                       |      |                    | 35              | mV    |
| I <sub>OS</sub> | Output Short Circuit Current                                  | $V_{OUT} = 0V, R_L = 100\Omega$  |                       |      | -3.5               | -5              | mA    |
| l <sub>OZ</sub> | Output TRI-STATE® Current                                     | Power Down = 0V,<br>V <sub>OUT</sub> = 0V or V <sub>CC</sub>   |                       |      | ±1                 | ±10             | μA    |
| TRANSM          | ITTER SUPPLY CURRENT  |  |                       |      |                    |                 |       |
| ICCTW           | Transmitter Supply Current                                    | $R_L = 100\Omega$ ,  | f = 25 MHz            |      | 31                 | 45              | mA    |
|                 | Worst Case  | C <sub>L</sub> = 5 pF,<br>Worst Case Pattern   | f = 40 MHz            |      | 37                 | 50              | mA    |
|                 |   | (Figure 1 Figure 4) " Typ " values are given for V $_{\rm CC}$ = 3.6V and T $_{\rm A}$ = +25°C, " Max " values are given for V $_{\rm CC}$ = 3.6V and T $_{\rm A}$ = -10°C | f = 65 MHz            |      | 48                 | 60              | mA    |
| ICCTG           | Transmitter Supply Current                                    | $R_L = 100\Omega$ ,  | f = 25 MHz            |      | 29                 | 40              | mA    |
|                 | 16 Grayscale  | C <sub>L</sub> = 5 pF,<br>16 Grayscale Pattern   | f = 40 MHz            |      | 33                 | 45              | mA    |
|                 |   | (Figure 2 Figure 4) " Typ " values are given for V $_{CC}$ = 3.6V and $T_A$ = +25°C, " Max " values are given for $V_{CC}$ = 3.6V and $T_A$ = -10°C                        | f = 65 MHz            |      | 39                 | 50              | mA    |
| ICCTZ           | Transmitter Supply Current<br>Power Down                      | Power Down = Low<br>Driver Outputs in TRI-STAT<br>Power Down Mode  | ΓE <sup>®</sup> under |      | 17                 | 150             | μА    |

<sup>(2)</sup> Typical values are given for  $V_{CC}$  = 3.3V and T  $_A$  = +25°C unless specified otherwise. (3)  $V_{OS}$  previously referred as  $V_{CM}$ .

# **Recommended Transmitter Input Characteristics**

Over recommended operating supply and temperature ranges unless otherwise specified

| Symbol | Parameter                                     | Min   | Тур  | Max   | Units |
|--------|---|-------|------|-------|-------|
| TCIT   | TxCLK IN Transition Time (Figure 5 )          |       |      | 5     | ns    |
| TCIP   | TxCLK IN Period (Figure 6 )                   | 14.7  | Т    | 50    | ns    |
| TCIH   | TxCLK IN High Time (Figure 6 )                | 0.35T | 0.5T | 0.65T | ns    |
| TCIL   | TxCLK IN Low Time (Figure 6)                  | 0.35T | 0.5T | 0.65T | ns    |
| TXIT   | TxIN, and Power Down pin Transition Time      | 1.5   |      | 6     | ns    |
| TXPD   | Minimum pulse width for Power Down pin signal | 1     |      |       | us    |

Copyright © 2004–2013, Texas Instruments Incorporated



## **Transmitter Switching Characteristics**

Over recommended operating supply and temperature ranges unless otherwise specified

| Symbol | Parameter  |               | Min   | Тур               | Max   | Units |
|--------|--|---------------|-------|-------------------|-------|-------|
| LLHT   | LVDS Low-to-High Transition Time (Figure 4 )   |               |       | 0.75              | 1.4   | ns    |
| LHLT   | LVDS High-to-Low Transition Time (Figure 4 )   |               |       | 0.75              | 1.4   | ns    |
| TPPos0 | Transmitter Output Pulse Position for Bit 0 (Figure 11)(1)   | f = 65        | -0.20 | 0                 | +0.20 | ns    |
| TPPos1 | Transmitter Output Pulse Position for Bit 1  | MHz           | 2.00  | 2.20              | 2.40  | ns    |
| TPPos2 | Transmitter Output Pulse Position for Bit 2  |               | 4.20  | 4.40              | 4.60  | ns    |
| TPPos3 | Transmitter Output Pulse Position for Bit 3  |               | 6.39  | 6.59              | 6.79  | ns    |
| TPPos4 | Transmitter Output Pulse Position for Bit 4  |               | 8.59  | 8.79              | 8.99  | ns    |
| TPPos5 | Transmitter Output Pulse Position for Bit 5  |               | 10.70 | 10.99             | 11.19 | ns    |
| TPPos6 | Transmitter Output Pulse Position for Bit 6  |               | 12.99 | 13.19             | 13.39 | ns    |
| TPPos0 | Transmitter Output Pulse Position for Bit 0 (Figure 11 ) <sup>(1)</sup>  | f = 40        | -0.25 | 0                 | +0.25 | ns    |
| TPPos1 | Transmitter Output Pulse Position for Bit 1  | MHz           | 3.32  | 3.57              | 3.82  | ns    |
| TPPos2 | Transmitter Output Pulse Position for Bit 2  |               | 6.89  | 7.14              | 7.39  | ns    |
| TPPos3 | Transmitter Output Pulse Position for Bit 3  |               | 10.46 | 10.71             | 10.96 | ns    |
| TPPos4 | Transmitter Output Pulse Position for Bit 4  |               | 14.04 | 14.29             | 14.54 | ns    |
| TPPos5 | Transmitter Output Pulse Position for Bit 5  |               | 17.61 | 17.86             | 18.11 | ns    |
| TPPos6 | Transmitter Output Pulse Position for Bit 6  | 21.18         |       | 21.43             | 21.68 | ns    |
| TPPos0 | Transmitter Output Pulse Position for Bit 0 (Figure 11 ) <sup>(1)</sup>  | f = 25        | -0.45 | 0                 | +0.45 | ns    |
| TPPos1 | Transmitter Output Pulse Position for Bit 1  | MHz           | 5.26  | 5.71              | 6.16  | ns    |
| TPPos2 | Transmitter Output Pulse Position for Bit 2  |               | 10.98 | 11.43             | 11.88 | ns    |
| TPPos3 | Transmitter Output Pulse Position for Bit 3  |               | 16.69 | 17.14             | 17.59 | ns    |
| TPPos4 | Transmitter Output Pulse Position for Bit 4  |               | 22.41 | 22.86             | 23.31 | ns    |
| TPPos5 | Transmitter Output Pulse Position for Bit 5  |               | 28.12 | 28.57             | 29.02 | ns    |
| TPPos6 | Transmitter Output Pulse Position for Bit 6  |               | 33.84 | 34.29             | 34.74 | ns    |
| TSTC   | TxIN Setup to TxCLK IN (Figure 6 )   |               | 2.5   |                   |       | ns    |
| THTC   | TxIN Hold to TxCLK IN (Figure 6 )  |               | 0.5   |                   |       | ns    |
| TCCD   | TxCLK IN to TxCLK OUT Delay (Figure 7 ) 50% duty cycle input clock is assumed, $T_A = -10$ °C, and 65MHz for " Min ", $T_A = 70$ °C, and 25MHz for " Max ", $V_{CC} = 3.6$ V |               | 3.011 |                   | 6.062 | ns    |
| SSCG   | Spread Spectrum Clock support; Modulation frequency with a linear profile (2)  | f = 25<br>MHz |       | 100KHz ± 2.5%/-5% |       |       |
|        |  | f = 40<br>MHz |       | 100KHz ± 2.5%/-5% |       |       |
|        |  | f = 65<br>MHz |       | 100KHz ± 2.5%/-5% |       |       |
| TPLLS  | Transmitter Phase Lock Loop Set (Figure 8 )  |               |       |                   | 10    | ms    |
| TPDD   | Transmitter Power Down Delay (Figure 10 )  |               |       |                   | 100   | ns    |

<sup>(1)</sup> The Minimum and Maximum Limits are based on statistical analysis of the device performance over process, voltage, and temperature ranges. This parameter is functionality tested only on Automatic Test Equipment (ATE).

<sup>(2)</sup> Care must be taken to ensure TSTC and THTC are met so input data are sampling correctly. This SSCG parameter only shows the performance of tracking Spread Spectrum Clock applied to TxCLK IN pin, and reflects the result on TxCLKOUT+ and TxCLK- pins.



### **AC Timing Diagrams**





Figure 1. "Worst Case" Test Pattern



The worst case test pattern produces a maximum toggling of digital circuits, LVDS I/O and CMOS/TTL I/O.

The 16 grayscale test pattern tests device power consumption for a "typical" LCD display pattern. The test pattern approximates signal switching needed to produce groups of 16 vertical stripes across the display.

Figure 1 and Figure 2 show a falling edge data strobe (TxCLK IN/RxCLK OUT).

Recommended pin to signal mapping. Customer may choose to define differently.

Figure 2. "16 Grayscale" Test Pattern




Figure 3. DS90CF383B (Transmitter) LVDS Output Load






Figure 4. DS90CF383B (Transmitter) LVDS Transition Times




Figure 5. DS90CF383B (Transmitter) Input Clock Transition Time




Figure 6. DS90CF383B (Transmitter) Setup/Hold and High/Low Times (Falling Edge Strobe)




Figure 7. DS90CF383B (Transmitter) Clock In to Clock Out Delay (Falling Edge Strobe)




Figure 8. DS90CF383B (Transmitter) Phase Lock Loop Set Time






Figure 9. 28 Parallel TTL Data Inputs Mapped to LVDS Outputs




Figure 10. Transmitter Power Down Delay




Figure 11. Transmitter LVDS Output Pulse Position Measurement



## DS90CF383B PIN DESCRIPTIONS — FPD LINK TRANSMITTER

| Pin Name             | I/O | No. | Description   |
|----------------------|-----|-----|---|
| TxIN                 | I   | 28  | TTL level input. This includes: 8 Red, 8 Green, 8 Blue, and 4 control lines—FPLINE, FPFRAME and DRDY (also referred to as HSYNC, VSYNC, Data Enable). |
| TxOUT+               | 0   | 4   | Positive LVDS differential data output.   |
| TxOUT-               | 0   | 4   | Negative LVDS differential data output.   |
| FPSHIFT IN           | I   | 1   | TTL level clock input. The falling edge acts as data strobe. Pin name TxCLK IN.   |
| TxCLK OUT+           | 0   | 1   | Positive LVDS differential clock output.  |
| TxCLK OUT-           | 0   | 1   | Negative LVDS differential clock output.  |
| PWR DOWN             | I   | 1   | TTL level input. Assertion (low input) TRI-STATES the outputs, ensuring low current at power down. See Applications Information.                      |
| V <sub>CC</sub>      | I   | 4   | Power supply pins for TTL inputs.   |
| GND                  | I   | 5   | Ground pins for TTL inputs.   |
| PLL V <sub>CC</sub>  | I   | 1   | Power supply pin for PLL.   |
| PLL GND              | I   | 2   | Ground pins for PLL.  |
| LVDS V <sub>CC</sub> | I   | 1   | Power supply pin for LVDS outputs.  |
| LVDS GND             | I   | 3   | Ground pins for LVDS outputs.   |



#### APPLICATIONS INFORMATION

The DS90CF383B are backward compatible with the DS90C383/DS90CF383, DS90C383A/DS90CF383A and are a pin-for-pin replacement.

This device may also be used as a replacement for the DS90CF583 (5V, 65MHz) and DS90CF581 (5V, 40MHz) FPD-Link Transmitters with certain considerations/modifications:

1. Change 5V power supply to 3.3V. Provide this supply to the  $V_{CC}$ , LVDS  $V_{CC}$  and PLL  $V_{CC}$  of the transmitter.

#### TRANSMITTER INPUT PINS

The DS90CF383B transmitter input and control inputs accept 3.3V LVTTL/LVCMOS levels. They are not 5V tolerant.

#### TRANSMITTER CLOCK CLOCK/DATA SEQUENCING

The DS90CF383B does not require any special requirement for sequencing of the input clock/data and PD (PowerDown) signal. The DS90CF383B offers a more robust input sequencing feature where the input clock/data can be inserted after the release of the PD signal. In the case where the clock/data is stopped and reapplied, such as changing video mode within Graphics Controller, it is not necessary to cycle the PD signal. However, there are in certain cases where the PD may need to be asserted during these mode changes. In cases where the source (Graphics Source) may be supplying an unstable clock or spurious noisy clock output to the LVDS transmitter, the LVDS Transmitter may attempt to lock onto this unstable clock signal but is unable to do so due the instability or quality of the clock source. The PD signal in these cases should then be asserted once a stable clock is applied to the LVDS transmitter. Asserting the PWR DOWN pin will effectively place the device in reset and disable the PLL, enabling the LVDS Transmitter into a power saving standby mode. However, it is still generally a good practice to assert the PWR DOWN pin or reset the LVDS transmitter whenever the clock/data is stopped and reapplied but it is not mandatory for the DS90CF383B.

#### SPREAD SPECTRUM CLOCK SUPPORT

The DS90CF383B can support Spread Spectrum Clocking signal type inputs. The DS90CF383B outputs will accurately track Spread Spectrum Clock/Data inputs with modulation frequencies of up to 100KHz (max.)with either center spread of ±2.5% or down spread -5% deviations.

#### **POWER SOURCES SEQUENCE**

In typical applications, it is recommended to have  $V_{CC}$ , LVDS  $V_{CC}$  and PLL  $V_{CC}$  from the same power source with three separate de-coupling bypass capacitor groups. There is no requirement on which VCC entering the device first.

Product Folder Links: DS90CF383B



## Pin Diagram





Figure 12. DS90CF383B See Package Number DGG0056A

# **Block Diagram**

## **Typical Application**







# **REVISION HISTORY**

| CI | Changes from Revision D (April 2013) to Revision E |    |  |  |  |  |
|----|--|----|--|--|--|--|
| •  | Changed layout of National Data Sheet to TI format | 10 |  |  |  |  |

www.ti.com 28-May-2021

#### PACKAGING INFORMATION

| Orderable Device   | Status | Package Type | Package<br>Drawing | Pins | Package<br>Qty | Eco Plan     | Lead finish/<br>Ball material | MSL Peak Temp       | Op Temp (°C) | Device Marking<br>(4/5) | Samples |
|--------------------|--------|--------------|--------------------|------|----------------|--------------|-------------------------------|---------------------|--------------|-------------------------|---------|
| DS90CF383BMT/NOPB  | ACTIVE | TSSOP        | DGG                | 56   | 34             | RoHS & Green | SN                            | Level-2-260C-1 YEAR | -10 to 70    | DS90CF383BMT            | Samples |
| DS90CF383BMTX/NOPB | ACTIVE | TSSOP        | DGG                | 56   | 1000           | RoHS & Green | SN                            | Level-2-260C-1 YEAR | -10 to 70    | DS90CF383BMT            | Samples |

(1) The marketing status values are defined as follows:

**ACTIVE:** Product device recommended for new designs.

LIFEBUY: TI has announced that the device will be discontinued, and a lifetime-buy period is in effect.

NRND: Not recommended for new designs. Device is in production to support existing customers, but TI does not recommend using this part in a new design.

PREVIEW: Device has been announced but is not in production. Samples may or may not be available.

**OBSOLETE:** TI has discontinued the production of the device.

(2) RoHS: TI defines "RoHS" to mean semiconductor products that are compliant with the current EU RoHS requirements for all 10 RoHS substances, including the requirement that RoHS substance do not exceed 0.1% by weight in homogeneous materials. Where designed to be soldered at high temperatures, "RoHS" products are suitable for use in specified lead-free processes. TI may reference these types of products as "Pb-Free".

RoHS Exempt: TI defines "RoHS Exempt" to mean products that contain lead but are compliant with EU RoHS pursuant to a specific EU RoHS exemption.

Green: TI defines "Green" to mean the content of Chlorine (CI) and Bromine (Br) based flame retardants meet JS709B low halogen requirements of <=1000ppm threshold. Antimony trioxide based flame retardants must also meet the <=1000ppm threshold requirement.

- (3) MSL, Peak Temp. The Moisture Sensitivity Level rating according to the JEDEC industry standard classifications, and peak solder temperature.
- (4) There may be additional marking, which relates to the logo, the lot trace code information, or the environmental category on the device.
- (5) Multiple Device Markings will be inside parentheses. Only one Device Marking contained in parentheses and separated by a "~" will appear on a device. If a line is indented then it is a continuation of the previous line and the two combined represent the entire Device Marking for that device.
- (6) Lead finish/Ball material Orderable Devices may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead finish/Ball material values may wrap to two lines if the finish value exceeds the maximum column width.

**Important Information and Disclaimer:** The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.



# **PACKAGE OPTION ADDENDUM**

www.ti.com 28-May-2021

# **PACKAGE MATERIALS INFORMATION**

www.ti.com 9-Aug-2022

## TAPE AND REEL INFORMATION





|    | Dimension designed to accommodate the component width     |
|----|---|
| В0 | Dimension designed to accommodate the component length    |
| K0 | Dimension designed to accommodate the component thickness |
| W  | Overall width of the carrier tape                         |
| P1 | Pitch between successive cavity centers                   |

#### QUADRANT ASSIGNMENTS FOR PIN 1 ORIENTATION IN TAPE




#### \*All dimensions are nominal

| Device             | Package<br>Type | Package<br>Drawing |    | SPQ  | Reel<br>Diameter<br>(mm) | Reel<br>Width<br>W1 (mm) | A0<br>(mm) | B0<br>(mm) | K0<br>(mm) | P1<br>(mm) | W<br>(mm) | Pin1<br>Quadrant |
|--------------------|-----------------|--------------------|----|------|--------------------------|--------------------------|------------|------------|------------|------------|-----------|------------------|
| DS90CF383BMTX/NOPB | TSSOP           | DGG                | 56 | 1000 | 330.0                    | 24.4                     | 8.6        | 14.5       | 1.8        | 12.0       | 24.0      | Q1               |

# **PACKAGE MATERIALS INFORMATION**

www.ti.com 9-Aug-2022




### \*All dimensions are nominal

| Device             | Package Type | Package Drawing | Pins | SPQ  | Length (mm) | Width (mm) | Height (mm) |  |
|--------------------|--------------|-----------------|------|------|-------------|------------|-------------|--|
| DS90CF383BMTX/NOPB | TSSOP        | DGG             | 56   | 1000 | 367.0       | 367.0      | 45.0        |  |

# **PACKAGE MATERIALS INFORMATION**

www.ti.com 9-Aug-2022

## **TUBE**




#### \*All dimensions are nominal

| Device            | Package Name | Package Type | Pins | SPQ | L (mm) | W (mm) | T (µm) | B (mm) |
|-------------------|--------------|--------------|------|-----|--------|--------|--------|--------|
| DS90CF383BMT/NOPB | DGG          | TSSOP        | 56   | 34  | 495    | 10     | 2540   | 5.79   |



SMALL OUTLINE PACKAGE



#### NOTES:


- 1. All linear dimensions are in millimeters. Any dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.

  2. This drawing is subject to change without notice.

  3. This dimension does not include mold flash, protrusions, or gate burrs. Mold flash, protrusions, or gate burrs shall not
- exceed 0.15 mm per side.
  4. Reference JEDEC registration MO-153.



SMALL OUTLINE PACKAGE




NOTES: (continued)

- 5. Publication IPC-7351 may have alternate designs.
- 6. Solder mask tolerances between and around signal pads can vary based on board fabrication site.



SMALL OUTLINE PACKAGE



NOTES: (continued)

- Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.
- 8. Board assembly site may have different recommendations for stencil design.



## IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATA SHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, regulatory or other requirements.

These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you will fully indemnify TI and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to TI's Terms of Sale or other applicable terms available either on ti.com or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products.

TI objects to and rejects any additional or different terms you may have proposed.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265 Copyright © 2022, Texas Instruments Incorporated