









CC1312R7 SWRS254A - MAY 2021 - REVISED NOVEMBER 2021

CC1312R7 SimpleLink™ High-Performance Sub-1 GHz Wireless MCU

1 Features

Wireless microcontroller

- Powerful 48-MHz Arm® Cortex®-M4F processor
- 704KB flash program memory
- 256KB of ROM for protocols and library functions
- 8KB of cache SRAM
- 144KB of ultra-low leakage SRAM with parity for high-reliability operation
- Dynamic multiprotocol manager (DMM) driver
- Programmable radio includes support for 2-(G)FSK, 4-(G)FSK, MSK, OOK, IEEE 802.15.4 PHY and MAC
- Supports over-the-air upgrade (OTA)

Ultra-low power sensor controller

- Autonomous MCU with 4KB of SRAM
- Sample, store, and process sensor data
- Fast wake-up for low-power operation
- Software defined peripherals; capacitive touch, flow meter, LCD

Low power consumption

- MCU consumption:
 - 2.63 mA active mode, CoreMark
 - 55 μA/MHz running CoreMark
 - 0.8 μA standby mode, RTC, 144KB RAM
 - 0.1 µA shutdown mode, wake-up on pin
- Ultra low-power sensor controller consumption:
 - 25.2 µA in 2 MHz mode
 - 701 µA in 24 MHz mode
- · Radio Consumption:
 - 5.4 mA RX at 868 MHz
 - 24.9 mA TX at +14 dBm at 868 MHz

Wireless protocol support

- Wi-SUN®
- mioty®
- Amazon Sidewalk
- Wireless M-Bus
- SimpleLink™ TI 15.4-stack
- **6LoWPAN**
- Proprietary systems

High performance radio

- -121 dBm for 2.5-kbps long-range mode
- -110 dBm at 50 kbps, 802.15.4, 868 MHz
- Output power up to +14 dBm with temperature compensation

Regulatory compliance

- Suitable for systems targeting compliance with these standards:
 - ETSI EN 300 220 Receiver Cat. 1.5 and 2, EN 303 131, EN 303 204
 - FCC CFR47 Part 15
 - ARIB STD-T108

MCU peripherals

- Digital peripherals can be routed to any GPIO
- Four 32-bit or eight 16-bit general-purpose timers
- 12-bit ADC, 200 kSamples/s, 8 channels
- 8-bit DAC
- Two comparators
- Programmable current source
- Two UART, two SSI, I²C, I²S
- Real-time clock (RTC)
- Integrated temperature and battery monitor

Security enablers

- AES 128- and 256-bit cryptographic accelerator
- ECC and RSA public key hardware accelerator
- SHA2 Accelerator (full suite up to SHA-512)
- True random number generator (TRNG)

Development tools and software

- LP-CC1312R7 Development Kit
- SimpleLink™ CC13xx and CC26xx Software Development Kit (SDK)
- SmartRF™ Studio for simple radio configuration
- Sensor Controller Studio for building low-power sensing applications
- SysConfig system configuration tool

Operating range

- On-chip buck DC/DC converter
- 1.8-V to 3.8-V single supply voltage
- -40 to +105°C

Package

- 7-mm × 7-mm RGZ VQFN48 (30 GPIOs)
- RoHS-compliant package



2 Applications

- · Grid infrastructure
 - Smart Meters electricity meter, water meter, gas meter, and heat cost allocator
 - Grid communications wireless communications
 - EV charging infrastructure AC charging (pile) station
 - Other alternative energy energy harvesting
- Building automation
 - Building security systems motion detector, door and window sensor, glass break detector, panic button, electronic smart lock and IP network camera
 - HVAC systems thermostat, environmental sensor and HVAC controller

- Fire safety smoke and head detector, gas detector and fire alarm control panel
- Retail Automation
 - Retail automation & payment applications
 electronic shelf labels andportable POS terminal
- Personal Electronics
 - RF remote controls
 - Smart Speakers and Smart Displays
 - Gaming and electronic and robotic toys
 - Wearables (non-medical) and smart trackers
- Wireless Modules
 - Wireless third party modules including Wi-SUN[®], Amazon Sidewalk, mioty[®] and multiprotocol
 - Wireless communications modules

3 Description

The SimpleLink™ CC1312R7 device is a multiprotocol Sub-1 GHz wireless microcontroller (MCU) supporting IEEE 802.15.4g, IPv6-enabled smart objects (6LoWPAN), mioty®, Wi-SUN®, proprietary systems, including the TI 15.4-Stack (Sub-1 GHz), and concurrent multiprotocol through a Dynamic Multiprotocol Manager (DMM) driver. The CC1312R7 is based on an Arm® Cortex® M4F main processor and optimized for low-power wireless communication and advanced sensing in grid infrastructure, building automation, retail automation, personal electronics and medical applications.

The CC1312R7 has a software defined radio powered by an Arm® Cortex® M0, which allows support for multiple physical layers and RF standards. The device supports operation in 287 to 351-MHz, 359 to 527-MHz, 861 to 1054-MHz, and 1076 to 1315-MHz frequency bands. PHY and frequency band switching can be done runtime through a dynamic multiprotocol manager (DMM) driver. The CC1312R7 has an efficient built-in PA that supports +14 dBm TX at 24.9 mA current consumption. In RX it has -121 dBm sensitivity and 88 dB blocking ±10 MHz in SimpleLink™ long-range mode with 2.5-kbps data rate.

The CC1312R7 has a low sleep current of 0.9 μ A with RTC and 144KB RAM retention. In addition to the main Cortex® M4F processor, the device also has an autonomous ultra-low power Sensor Controller CPU with fast wake-up capability. As an example, the sensor controller is capable of 1-Hz ADC sampling at 1- μ A system current.

The CC1312R7 has Low SER (Soft Error Rate) FIT (Failure-in-time) for long operational lifetime. Always-on SRAM parity minimizes risk for corruption due to potential radiation events. Consistent with many customers' 10 to 15 years or longer life cycle requirements, TI has a product life cycle policy with a commitment to product longevity and continuity of supply.

The CC1312R7 device is part of the SimpleLink™ MCU platform, which consists of Wi-Fi®, *Bluetooth*® Low Energy, Thread, Zigbee, Wi-SUN®, Amazon Sidewalk, mioty®, Sub-1 GHz MCUs, and host MCUs. CC1312R7 is part of a scalable portfolio with flash sizes from 32KB to 704KB with pin-to-pin compatible package options. The common SimpleLink™CC13xx and CC26xx Software Development Kit (SDK) and SysConfig system configuration tool supports migration between devices in the portfolio. A comprehensive number of software stacks, application examples and SimpleLink™ Academy training sessions are included in the SDK. For more information, visit wireless connectivity.

Device Information

PART NUMBER ⁽¹⁾	PACKAGE	BODY SIZE (NOM)
CC1312R74T0RGZR	VQFN (48)	7.00 mm × 7.00 mm

(1) For the most current part, package, and ordering information for all available devices, see the Package Option Addendum in Section 11, or see the TI website.

Submit Document Feedback



3.1 Functional Block Diagram




Figure 3-1. CC1312R7 Block Diagram



Table of Contents

1 Features1	8 Detailed Description	34
2 Applications2	8.1 Overview	34
3 Description2	8.2 System CPU	34
3.1 Functional Block Diagram3	8.3 Radio (RF Core)	35
4 Revision History4	8.4 Memory	36
5 Device Comparison5		
6 Terminal Configuration and Functions6	8.6 Cryptography	38
6.1 Pin Diagram – RGZ Package (Top View)6	8.7 Timers	39
6.2 Signal Descriptions – RGZ Package7	8.8 Serial Peripherals and I/O	40
6.3 Connections for Unused Pins and Modules8	8.9 Battery and Temperature Monitor	40
7 Specifications9	8.10 µDMA	40
7.1 Absolute Maximum Ratings9		
7.2 ESD Ratings9	8.12 Power Management	41
7.3 Recommended Operating Conditions9	8.13 Clock Systems	42
7.4 Power Supply and Modules10		
7.5 Power Consumption - Power Modes10	9 Application, Implementation, and Layout	43
7.6 Power Consumption - Radio Modes11	9.1 Reference Designs	
7.7 Nonvolatile (Flash) Memory Characteristics 11	9.2 Junction Temperature Calculation	43
7.8 Thermal Resistance Characteristics11	10 Device and Documentation Support	45
7.9 RF Frequency Bands12	10.1 Device Nomenclature	45
7.10 861 MHz to 1054 MHz - Receive (RX)13	10.2 Tools and Software	45
7.11 861 MHz to 1054 MHz - Transmit (TX) 16	10.3 Documentation Support	48
7.12 861 MHz to 1054 MHz - PLL Phase Noise	10.4 Support Resources	48
Wideband Mode17	10.5 Trademarks	48
7.13 861 MHz to 1054 MHz - PLL Phase Noise	10.6 Electrostatic Discharge Caution	49
Narrowband Mode17	10.7 Glossary	49
7.14 Timing and Switching Characteristics17	11 Mechanical, Packaging, and Orderable	
7.15 Peripheral Characteristics22		50
7.16 Typical Characteristics28		

4 Revision History

NOTE: Page numbers for previous revisions may differ from page numbers in the current version.

DATE	REVISION	NOTES	
November 2021	*	Initial Release	



5 Device Comparison

Table 5-1. Device Family Overview

	lable 3-1. De	FLASH	RAM		
DEVICE	RADIO SUPPORT	(KB)	(KB)	GPIO	PACKAGE SIZE
CC1310	Sub-1 GHz Wireless M-Bus	32-128	16-20	10-30	RGZ (7-mm × 7-mm VQFN48) RHB (5 mm × 5 mm VQFN32) RSM (4 mm × 4 mm VQFN32)
CC1312R	Sub-1 GHz Wi-SUN [®] Amazon Sidewalk Wireless M-Bus	352-704	80-144	30	RGZ (7-mm × 7-mm VQFN48)
CC1352P	Multiprotocol Sub-1 GHz Wi-SUN® Amazon Sidewalk Wireless M-Bus Bluetooth 5.2 Low Energy Zigbee Thread 2.4 GHz proprietary FSK-based formats +20-dBm high-power amplifier	352-704	80-144	26	RGZ (7-mm × 7-mm VQFN48)
CC1352R	Multiprotocol Sub-1 GHz Wi-SUN® Wireless M-Bus Bluetooth 5.2 Low Energy Zigbee Thread 2.4 GHz proprietary FSK-based formats	352	80	28	RGZ (7-mm × 7-mm VQFN48)
CC2642R	Bluetooth 5.2 Low Energy 2.4 GHz proprietary FSK-based formats	352	80	31	RGZ (7-mm × 7-mm VQFN48)
CC2642R-Q1	Bluetooth 5.2 Low Energy	352	80	31	RTC (7-mm × 7-mm VQFN48)
CC2652R	Multiprotocol Bluetooth 5.2 Low Energy Zigbee Thread 2.4 GHz proprietary FSK-based formats	352-704	80-144	31	RGZ (7-mm × 7-mm VQFN48)
CC2652RB	Multiprotocol Bluetooth 5.2 Low Energy Zigbee Thread	352	80	31	RGZ (7-mm × 7-mm VQFN48)
CC2652P	Multiprotocol Bluetooth 5.2 Low Energy Zigbee Thread 2.4 GHz proprietary FSK-based formats +19.5-dBm high-power amplifier	352-704	80-144	26	RGZ (7-mm × 7-mm VQFN48)

6 Terminal Configuration and Functions

6.1 Pin Diagram - RGZ Package (Top View)




Figure 6-1. RGZ (7-mm × 7-mm) Pinout, 0.5-mm Pitch (Top View)

The following I/O pins marked in Figure 6-1 in **bold** have high-drive capabilities:

- Pin 10, DIO_5
- Pin 11, DIO 6
- Pin 12, DIO 7
- Pin 24, JTAG_TMSC
- Pin 26, DIO_16
- Pin 27, DIO_17

The following I/O pins marked in Figure 6-1 in *italics* have analog capabilities:

- Pin 36, DIO 23
- Pin 37, DIO_24
- Pin 38, DIO_25
- Pin 39, DIO_26
- Pin 40, DIO_27
- Pin 41, DIO_28Pin 42, DIO_29
- Pin 43, DIO_30

6.2 Signal Descriptions - RGZ Package

Table 6-1. Signal Descriptions - RGZ Package

PIN				iptions – RGZ Package
NAME	NO.	I/O	TYPE	DESCRIPTION
DCDC_SW	33	_	Power	Output from internal DC/DC converter ⁽¹⁾
DCOUPL	23	_	Power	For decoupling of internal 1.27 V regulated digital-supply (2)
DIO_1	6	I/O	Digital	GPIO
DIO_2	7	I/O	Digital	GPIO
DIO_3	8	I/O	Digital	GPIO
DIO_4	9	I/O	Digital	GPIO
DIO_5	10	I/O	Digital	GPIO, high-drive capability
DIO_6	11	I/O	Digital	GPIO, high-drive capability
DIO_7	12	I/O	Digital	GPIO, high-drive capability
DIO_8	14	I/O	Digital	GPIO
DIO_9	15	I/O	Digital	GPIO
DIO_10	16	I/O	Digital	GPIO
DIO_11	17	I/O	Digital	GPIO
DIO_12	18	I/O	Digital	GPIO
DIO_13	19	I/O	Digital	GPIO
DIO_14	20	I/O	Digital	GPIO
DIO_15	21	I/O	Digital	GPIO
DIO_16	26	I/O	Digital	GPIO, JTAG_TDO, high-drive capability
DIO_17	27	I/O	Digital	GPIO, JTAG_TDI, high-drive capability
DIO_18	28	I/O	Digital	GPIO
DIO_19	29	I/O	Digital	GPIO
DIO_20	30	I/O	Digital	GPIO
DIO_21	31	I/O	Digital	GPIO
DIO_22	32	I/O	Digital	GPIO
DIO_23	36	I/O	Digital or Analog	GPIO, analog capability
DIO_24	37	I/O	Digital or Analog	GPIO, analog capability
DIO_25	38	I/O	Digital or Analog	GPIO, analog capability
DIO_26	39	I/O	Digital or Analog	GPIO, analog capability
DIO_27	40	I/O	Digital or Analog	GPIO, analog capability
DIO_28	41	I/O	Digital or Analog	GPIO, analog capability
DIO_29	42	I/O	Digital or Analog	GPIO, analog capability
DIO_30	43	I/O	Digital or Analog	GPIO, analog capability
EGP	_	_	GND	Ground – exposed ground pad ⁽³⁾
JTAG_TMSC	24	I/O	Digital	JTAG TMSC, high-drive capability
JTAG_TCKC	25	ı	Digital	JTAG TCKC
RESET_N	35	I	Digital	Reset, active low. No internal pullup resistor
RF_P	1	_	RF	Positive RF input signal to LNA during RX Positive RF output signal from PA during TX
RF_N	2	_	RF	Negative RF input signal to LNA during RX Negative RF output signal from PA during TX
RX_TX	3	_	RF	Optional bias pin for the RF LNA
VDDR	45	_	Power	Internal supply, must be powered from the internal DC/DC converter or the internal LDO ⁽²⁾ (4) (6)



Table 6-1. Signal Descriptions – RGZ Package (continued)

PIN				
FIN		I/O TYPE		DESCRIPTION
NAME	NO.			
VDDR_RF	48	_	Power	Internal supply, must be powered from the internal DC/DC converter or the internal LDO ⁽²⁾ (5) (6)
VDDS	44	_	Power	1.8-V to 3.8-V main chip supply ⁽¹⁾
VDDS2	13	_	Power	1.8-V to 3.8-V DIO supply ⁽¹⁾
VDDS3	22	_	Power	1.8-V to 3.8-V DIO supply ⁽¹⁾
VDDS_DCDC	34	_	Power	1.8-V to 3.8-V DC/DC converter supply
X48M_N	46	_	Analog	48-MHz crystal oscillator pin 1
X48M_P	47	_	Analog	48-MHz crystal oscillator pin 2
X32K_Q1	4	_	Analog	32-kHz crystal oscillator pin 1
X32K_Q2	5	_	Analog	32-kHz crystal oscillator pin 2

- (1) For more details, see technical reference manual listed in Section 10.3.
- (2) Do not supply external circuitry from this pin.
- (3) EGP is the only ground connection for the device. Good electrical connection to device ground on printed circuit board (PCB) is imperative for proper device operation.
- (4) If internal DC/DC converter is not used, this pin is supplied internally from the main LDO.
- 5) If internal DC/DC converter is not used, this pin must be connected to VDDR for supply from the main LDO.
- (6) Output from internal DC/DC and LDO is trimmed to 1.68 V.

6.3 Connections for Unused Pins and Modules

Table 6-2. Connections for Unused Pins

FUNCTION	SIGNAL NAME	PIN NUMBER	ACCEPTABLE PRACTICE(1)	PREFERRED PRACTICE ⁽¹⁾
GPIO	DIO_n	6–12 14–21 26–32 36–43	NC or GND	NC
32.768-kHz crystal	X32K_Q1	4	NC or GND	NC
32.700-Ki iz Ci ystai	X32K_Q2	5	INC OF GIND	INC
DC/DC converter ⁽²⁾	DCDC_SW	33	NC	NC
	VDDS_DCDC	34	VDDS	VDDS

- (1) NC = No connect
- (2) When the DC/DC converter is not used, the inductor between DCDC_SW and VDDR can be removed. VDDR and VDDR_RF must still be connected and the 22 uF DCDC capacitor must be kept on the VDDR net.

Submit Document Feedback



7 Specifications

7.1 Absolute Maximum Ratings

over operating free-air temperature range (unless otherwise noted)(1) (2)

			MIN	MAX	UNIT
VDDS(3)	Supply voltage		-0.3	4.1	V
	Voltage on any digital pin	(4)	-0.3	VDDS + 0.3, max 4.1	V
	Voltage on crystal oscilla	or pins, X32K_Q1, X32K_Q2, X48M_N and X48M_P	-0.3	VDDR + 0.3, max 2.25	V
		Voltage scaling enabled	-0.3	VDDS	
V _{in}	Voltage on ADC input	Voltage scaling disabled, internal reference	-0.3	1.49	V
		Voltage scaling disabled, VDDS as reference	-0.3	VDDS / 2.9	
	Input level, RF pins (RF_	P and RF_N)		10	
T _{stg}	Storage temperature		-40	150	°C

⁽¹⁾ Stresses beyond those listed under Absolute Maximum Ratings may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated under Recommended Operating Conditions is not implied. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability.

- (2) All voltage values are with respect to ground, unless otherwise noted.
- (3) VDDS DCDC, VDDS2 and VDDS3 must be at the same potential as VDDS.
- (4) Including analog capable DIOs.

7.2 ESD Ratings

				VALUE	UNIT
V	Electrostatic discharge	Human body model (HBM), per ANSI/ESDA/JEDEC JS-001 ⁽¹⁾	All pins	±2000	V
V _{ESD}	Electrostatic discharge	Charged device model (CDM), per ANSI/ESDA/JEDEC JS-002 ⁽²⁾	All pins	±500	V

- (1) JEDEC document JEP155 states that 500-V HBM allows safe manufacturing with a standard ESD control process
- (2) JEDEC document JEP157 states that 250-V CDM allows safe manufacturing with a standard ESD control process

7.3 Recommended Operating Conditions

over operating free-air temperature range (unless otherwise noted)

	,	MIN	MAX	UNIT
Operating ambient temperature ⁽¹⁾ (3)		-40	105	°C
perating junction temperature ^{(1) (3)}		-40	115	°C
Operating supply voltage (VDDS)	Operating supply voltage (VDDS)		3.8	V
Operating supply voltage (VDDS), boost mode	VDDR = 1.95 V +14 dBm RF output power	2.1	3.8	V
Rising supply voltage slew rate		0	100	mV/μs
Falling supply voltage slew rate ⁽²⁾		0	20	mV/μs

- (1) Operation at or near maximum operating temperature for extended durations will result in a reduction in lifetime.
- (2) For small coin-cell batteries, with high worst-case end-of-life equivalent source resistance, a 22-μF VDDS input capacitor must be used to ensure compliance with this slew rate.
- (3) For thermal resistance characteristics refer to Section 7.8.



7.4 Power Supply and Modules

over operating free-air temperature range (unless otherwise noted)

PARAMETER		MIN	TYP	MAX	UNIT
VDDS Power-on-Reset (POR) threshold		1.1	- 1.55		V
VDDS Brown-out Detector (BOD) (1)	Rising threshold		1.77		V
VDDS Brown-out Detector (BOD), before initial boot (2)	Rising threshold		1.70		V
VDDS Brown-out Detector (BOD) (1)	Falling threshold		1.75		V

- (1) For boost mode (VDDR =1.95 V), TI drivers software initialization will trim VDDS BOD limits to maximum (approximately 2.0 V)
- (2) Brown-out Detector is trimmed at initial boot, value is kept until device is reset by a POR reset or the RESET_N pin

7.5 Power Consumption - Power Modes

When measured on the CC1312-R7EM-XD7793 reference design with T_c = 25 °C, V_{DDS} = 3.6 V with DC/DC enabled unless otherwise noted.

	PARAMETER	TEST CONDITIONS	TYP	UNIT
Core Curre	nt Consumption			
	Reset and Shutdown	Reset. RESET_N pin asserted or VDDS below power-on-reset threshold	110	nA
	Reset and Shutdown	Shutdown. No clocks running, no retention	110	IIA
I _{core}		RTC running, CPU, 144KB RAM and (partial) register retention. RCOSC_LF	0.8	μΑ
	Standby without cache retention	RTC running, CPU, 64KB RAM and (partial) register retention. RCOSC_LF	0.7	μΑ
		RTC running, CPU, 144KB RAM and (partial) register retention XOSC_LF	0.9	μΑ
	Standby	RTC running, CPU, 144KB RAM and (partial) register retention. RCOSC_LF	1.9	μΑ
	with cache retention	RTC running, CPU, 144KB RAM and (partial) register retention. XOSC_LF	2.0	μΑ
	Idle	Supply Systems and RAM powered RCOSC_HF	590	μА
	Active	MCU running CoreMark at 48 MHz RCOSC_HF	2.63	mA
Peripheral	Current Consumption			
	Peripheral power domain	Delta current with domain enabled	39	
	Serial power domain	Delta current with domain enabled	2.6	
	RF Core	Delta current with power domain enabled, clock enabled, RF core idle	89	
	μDMA	Delta current with clock enabled, module is idle	57	
	Timers	Delta current with clock enabled, module is idle ⁽³⁾	97	
I _{peri}	I2C	Delta current with clock enabled, module is idle	9.2	μΑ
	I2S	Delta current with clock enabled, module is idle	22	
	SSI	Delta current with clock enabled, module is idle ⁽²⁾	50	
	UART	Delta current with clock enabled, module is idle ⁽¹⁾	110	
	CRYPTO (AES)	Delta current with clock enabled, module is idle	16	
	PKA	Delta current with clock enabled, module is idle	59	
	TRNG	Delta current with clock enabled, module is idle	20	
Sensor Co	ntroller Engine Consumption			
	Active mode	24 MHz, infinite loop	701	
I _{SCE}	Low-power mode	2 MHz, infinite loop	25.2	μA

- (1) Only one UART running
- (2) Only one SSI running
- (3) Only one GPTimer running

7.6 Power Consumption - Radio Modes

When measured on the CC1312-R7EM-XD7793 reference design with T_c = 25 °C, V_{DDS} = 3.6 V with DC/DC enabled unless otherwise noted.

Using boost mode (increasing VDDR up to 1.95 V), will increase system current by 15% (does not apply to TX +14 dBm setting where this current is already included).

Relevant I_{core} and I_{peri} currents are included in below numbers.

PARAMETER	TEST CONDITIONS	TYP	UNIT
Radio receive current, 868 MHz		5.4	mA
Padio transmit current	0 dBm output power setting 868 MHz	8.0	mA
Radio transmit current	+10 dBm output power setting 868 MHz	14.3	mA
Radio transmit current Boost mode	+14 dBm output power setting 868 MHz	24.9	mA

7.7 Nonvolatile (Flash) Memory Characteristics

Over operating free-air temperature range and V_{DDS} = 3.0 V (unless otherwise noted)

PARAMETER	TEST CONDITIONS	MIN	TYP	MAX	UNIT
Flash sector size			8		KB
Supported flash erase cycles before failure, single-bank ^{(1) (5)}		30			k Cycles
Supported flash erase cycles before failure, single sector ⁽²⁾		60			k Cycles
Maximum number of write operations per row before sector erase ⁽³⁾				83	Write Operations
Flash retention	105 °C	11.4			Years at 105 °C
Flash sector erase current	Average delta current		9.5		mA
Flash sector erase time ⁽⁴⁾	Zero cycles		10		ms
Flash sector erase time(**)	30k cycles			4000	ms
Flash write current	Average delta current, 4 bytes at a time		5.2		mA
Flash write time ⁽⁴⁾	4 bytes at a time		21.6		μs

- (1) A full bank erase is counted as a single erase cycle on each sector. If both flash banks are always cycled simultaneously they can be cycled 30K times each. Alternatively, the banks can be cycled a total of 30K times, e.g. the main bank X times and the second bank Y times (X+Y=30K)
- (2) Up to 4 customer-designated sectors can be individually erased an additional 30k times beyond the baseline bank limitation of 30k cycles
- (3) Each wordline is 2048 bits (or 256 bytes) wide. This limitation corresponds to sequential memory writes of 4 (3.1) bytes minimum per write over a whole wordline. If additional writes to the same wordline are required, a sector erase is required once the maximum number of write operations per row is reached.
- (4) This number is dependent on Flash aging and increases over time and erase cycles
- (5) Aborting flash during erase or program modes is not a safe operation.

7.8 Thermal Resistance Characteristics

		PACKAGE	
THERMAL METRIC(1)		RGZ (VQFN)	UNIT
		48 PINS	
$R_{\theta JA}$	Junction-to-ambient thermal resistance	23.7	°C/W ⁽²⁾
R _{0JC(top)}	Junction-to-case (top) thermal resistance	13.0	°C/W ⁽²⁾
$R_{\theta JB}$	Junction-to-board thermal resistance	7.7	°C/W ⁽²⁾
Ψлт	Junction-to-top characterization parameter	0.1	°C/W ⁽²⁾
ΨЈВ	Junction-to-board characterization parameter	7.6	°C/W ⁽²⁾
R _{0JC(bot)}	Junction-to-case (bottom) thermal resistance	1.9	°C/W ⁽²⁾

(1) For more information about traditional and new thermal metrics, see Semiconductor and IC Package Thermal Metrics.



(2) °C/W = degrees Celsius per watt.

7.9 RF Frequency Bands

Over operating free-air temperature range (unless otherwise noted).

PARAMETER	MIN	TYP MAX	UNIT
	1076	1315	
	861	1054	
Frequency bands	431	527	MHz
	359	439	
	287	351	

Submit Document Feedback

7.10 861 MHz to 1054 MHz - Receive (RX)

When Measured on the CC1312-R7EM-XD7793 reference design with T_c = 25 °C, V_{DDS} = 3.0 V with DC/DC enabled unless otherwise noted. All measurements are performed at the antenna input with a combined RX and TX path. All measurements are performed conducted.

PARAMETER	TEST CONDITIONS	MIN	TYP	MAX	UNIT
General Parameters					
Digital channel filter programmable receive bandwidth		4		4000	kHz
Data rate step size			1.5		bps
Spurious emissions 25 MHz to 1 GHz	868 MHz		< -57		dBm
Spurious emissions 1 GHz to 13 GHz	Conducted emissions measured according to ETSI EN 300 220		< -47		dBm
802.15.4, 50 kbps, ±25 kHz deviation, 2-0	GFSK, 100 kHz RX Bandwidth				
Sensitivity	BER = 10 ⁻² , 868 MHz		-110		dBm
Saturation limit	BER = 10 ⁻² , 868 MHz		10		dBm
Selectivity, ±200 kHz	BER = 10 ⁻² , 868 MHz ⁽¹⁾		44		dB
Selectivity, ±400 kHz	BER = 10 ⁻² , 868 MHz ⁽¹⁾		49		dB
Blocking, ±1 MHz	BER = 10 ⁻² , 868 MHz ⁽¹⁾		58		dB
Blocking, ±2 MHz	BER = 10 ⁻² , 868 MHz ⁽¹⁾		62		dB
Blocking, ±5 MHz	BER = 10 ⁻² , 868 MHz ⁽¹⁾		70		dB
Blocking, ±10 MHz	BER = 10^{-2} , 868 MHz ⁽¹⁾		78		dB
Image rejection (image compensation enabled)	BER = 10 ⁻² , 868 MHz ⁽¹⁾		39		dB
RSSI dynamic range	Starting from the sensitivity limit		95		dB
RSSI accuracy	Starting from the sensitivity limit across the given dynamic range		±3		dB
802.15.4, 100 kbps, ±25 kHz deviation, 2	-GFSK, 137 kHz RX Bandwidth				
Sensitivity 100 kbps	868 MHz, 1% PER, 127 byte payload		-103		dBm
Selectivity, ±200 kHz	868 MHz, 1% PER, 127 byte payload. Wanted signal at -96 dBm		38		dB
Selectivity, ±400 kHz	868 MHz, 1% PER, 127 byte payload. Wanted signal at -96 dBm		45		dB
Co-channel rejection	868 MHz, 1% PER, 127 byte payload. Wanted signal at -79 dBm		-9		dB
802.15.4, 200 kbps, ±50 kHz deviation, 2	-GFSK, 311 kHz RX Bandwidth				
Sensitivity	BER = 10 ⁻² , 868 MHz		-103		dBm
Sensitivity	BER = 10 ⁻² , 915 MHz		-103		dBm
Selectivity, ±400 kHz	BER = 10^{-2} , 915 MHz. Wanted signal 3 dB above sensitivity limit.		44		dB
Selectivity, ±800 kHz	BER = 10^{-2} , 915 MHz. Wanted signal 3 dB above sensitivity limit.		49		dB
Blocking, ±2 MHz	BER = 10^{-2} , 915 MHz. Wanted signal 3 dB above sensitivity limit.		57		dB
Blocking, ±10 MHz	BER = 10^{-2} , 915 MHz. Wanted signal 3 dB above sensitivity limit.		69		dB
802.15.4, 500 kbps, ±190 kHz deviation,	2-GFSK, 655 kHz RX Bandwidth				
Sensitivity 500 kbps	916 MHz, 1% PER, 127 byte payload		-95		dBm
Selectivity, ±1 MHz	916 MHz, 1% PER, 127 byte payload. Wanted signal at -88 dBm		35		dB
Selectivity, ±2 MHz	916 MHz, 1% PER, 127 byte payload. Wanted signal at -88 dBm		47		dB
Co-channel rejection	916 MHz, 1% PER, 127 byte payload. Wanted signal at -71 dBm		-9		dB
SimpleLink™ Long Range 2.5 kbps or 5	kbps (20 ksym/s, 2-GFSK, ±5 kHz Deviation, FEC (Half Rate), DSS	S = 1:2 or 1:4,	34 kHz RX Baı	ndwidth	1
Sensitivity	2.5 kbps, BER = 10 ⁻² , 868 MHz	<u> </u>	-121		dBm
Sensitivity	5 kbps, BER = 10 ⁻² , 868 MHz		-119		dBm
Saturation limit	2.5 kbps, BER = 10 ⁻² , 868 MHz		10		dBm
Selectivity, ±100 kHz	2.5 kbps, BER = 10 ⁻² , 868 MHz ⁽¹⁾		49		dB
Selectivity, ±200 kHz	2.5 kbps, BER = 10 ⁻² , 868 MHz ⁽¹⁾		50		dB
Selectivity, ±300 kHz	2.5 kbps, BER = 10 ⁻² , 868 MHz ⁽¹⁾		51		dB
Blocking, ±1 MHz	2.5 kbps, BER = 10 ⁻² , 868 MHz ⁽¹⁾		63		dB
Blocking, ±2 MHz	2.5 kbps, BER = 10 ⁻² , 868 MHz ⁽¹⁾		69		dB
Blocking, ±5 MHz	2.5 kbps, BER = 10 ⁻² , 868 MHz ⁽¹⁾		79		dB
Blocking, ±10 MHz	2.5 kbps, BER = 10 ⁻² , 868 MHz ⁽¹⁾		88		dB
DIOOMING, ± 10 IVII IZ	2.0 KOPS, DEIX = 10 , 000 WILLS		00		ub



7.10 861 MHz to 1054 MHz - Receive (RX) (continued)

When Measured on the CC1312-R7EM-XD7793 reference design with T_c = 25 °C, V_{DDS} = 3.0 V with DC/DC enabled unless otherwise noted. All measurements are performed at the antenna input with a combined RX and TX path. All measurements are performed conducted.

path. All measurements are perform					
PARAMETER	TEST CONDITIONS	MIN	TYP	MAX	UNIT
Image rejection (image compensation enabled)	2.5 kbps, BER = 10 ⁻² , 868 MHz ⁽¹⁾		47		dB
RSSI dynamic range	Starting from the sensitivity limit		108		dB
RSSI accuracy	Starting from the sensitivity limit across the given dynamic range		±3		dB
OOK, 4.8 kbps, 39 kHz RX Bandwidth					
Sensitivity	BER = 10 ⁻² , 868 MHz		-114		dBm
Sensitivity	BER = 10 ⁻² , 915 MHz		-114		dBm
Narrowband, 9.6 kbps ±2.4 kHz deviation,	2-GFSK, 868 MHz, 17.1 kHz RX Bandwidth				
Sensitivity	1% BER		-117		dBm
Adjacent Channel Rejection	1% BER. Wanted signal 3 dB above the ETSI reference sensitivity limit (-104.6 dBm). Interferer ±20 kHz		41		dB
Alternate Channel Rejection	1% BER. Wanted signal 3 dB above the ETSI reference sensitivity limit (-104.6 dBm). Interferer ±40 kHz		42		dB
Blocking, ±1 MHz	1% BER. Wanted signal 3 dB above the ETSI reference sensitivity limit (-104.6 dBm).		65		dB
Blocking, ±2 MHz	1% BER. Wanted signal 3 dB above the ETSI reference sensitivity limit (-104.6 dBm).		69		dB
Blocking, ±10 MHz	1% BER. Wanted signal 3 dB above the ETSI reference sensitivity limit (-104.6 dBm).		85		dB
1 Mbps, ±350 kHz deviation, 2-GFSK, 2.2 M	MHz RX Bandwidth				
Sensitivity	BER = 10 ⁻² , 868 MHz		-97		dBm
Sensitivity	BER = 10 ⁻² , 915 MHz		-97		dBm
Blocking, +2 MHz	BER = 10 ⁻² , 915 MHz. Wanted signal 3 dB above sensitivity limit.		44		dB
Blocking, -2 MHz	BER = 10 ⁻² , 915 MHz. Wanted signal 3 dB above sensitivity limit.		27		dB
Blocking, +10 MHz	BER = 10^{-2} , 915 MHz. Wanted signal 3 dB above sensitivity limit.		59		dB
Blocking, -10 MHz	BER = 10 ⁻² , 915 MHz. Wanted signal 3 dB above sensitivity limit.		54		dB
Wi-SUN, 2-GFSK					
Sensitivity	50 kbps, ±12.5 kHz deviation, 2-GFSK, 866.6 MHz, 68 kHz RX BW, 10% PER, 250 byte payload		-107		dBm
Selectivity, ±100 kHz, 50 kbps, ±12.5 kHz deviation, 2-GFSK, 866.6 MHz	50 kbps, ±12.5 kHz deviation, 2-GFSK, 68 kHz RX Bandwidth, 866.6 MHz, 10% PER, 250 byte payload. Wanted signal 3 dB above sensitivity level		30		dB
Selectivity, ±200 kHz, 50 kbps, ±12.5 kHz deviation, 2-GFSK, 866.6 MHz	50 kbps, ±12.5 kHz deviation, 2-GFSK, 68 kHz RX Bandwidth, 866.6 MHz, 10% PER, 250 byte payload. Wanted signal 3 dB above sensitivity level		36		dB
Sensitivity	50 kbps, ±25 kHz deviation, 2-GFSK, 98 kHz RX Bandwidth, 918.2 MHz, 10% PER, 250 byte payload		-107		dBm
Selectivity, ±200 kHz, 50 kbps, ±25 kHz deviation, 2-GFSK, 918.2 MHz	50 kbps, ±25 kHz deviation, 2-GFSK, 98 kHz RX Bandwidth, 918.2 MHz, 10% PER, 250 byte payload. Wanted signal 3 dB above sensitivity level		34		dB
Selectivity, ±400 kHz, 50 kbps, ±25 kHz deviation, 2-GFSK, 918.2 MHz	50 kbps, ±25 kHz deviation, 2-GFSK, 98 kHz RX Bandwidth, 918.2 MHz, 10% PER, 250 byte payload. Wanted signal 3 dB above sensitivity level		41		dB
Sensitivity	100 kbps, ±25 kHz deviation, 2-GFSK, 866.6 MHz, 135 kHz RX BW, 10% PER, 250 byte payload		-104		dBm
Selectivity, ±200 kHz, 100 kbps, ±25 kHz deviation, 2-GFSK, 866.6 MHz	100 kbps, ±25 kHz deviation, 2-GFSK, 135 kHz RX Bandwidth, 866.6 MHz, 10% PER, 250 byte payload. Wanted signal 3 dB above sensitivity level		37		dB
Selectivity, ±400 kHz, 100 kbps, ±25 kHz deviation, 2-GFSK, 866.6 MHz	100 kbps, ±25 kHz deviation, 2-GFSK, 135 kHz RX Bandwidth, 866.6 MHz, 10% PER, 250 byte payload. Wanted signal 3 dB above sensitivity level		45		dB
	100 kbps, ±50 kHz deviation, 2-GFSK, 920.9 MHz, 196 kHz RX		-102		dBm

Submit Document Feedback

7.10 861 MHz to 1054 MHz - Receive (RX) (continued)

When Measured on the CC1312-R7EM-XD7793 reference design with T_c = 25 °C, V_{DDS} = 3.0 V with DC/DC enabled unless otherwise noted. All measurements are performed at the antenna input with a combined RX and TX path. All measurements are performed conducted.

PARAMETER	TEST CONDITIONS	MIN	TYP	MAX	UNIT
Selectivity, ±400 kHz, 100 kbps, ±50 kHz deviation, 2-GFSK, 920.9 MHz	100 kbps, ±50 kHz deviation, 2-GFSK, 196 kHz RX Bandwidth, 920.9 MHz, 10% PER, 250 byte payload. Wanted signal 3 dB above sensitivity level		40		dB
Selectivity, ±800 kHz, 100 kbps, ±50 kHz deviation, 2-GFSK, 920.9 MHz	100 kbps, ±50 kHz deviation, 2-GFSK, 196 kHz RX Bandwidth, 920.9 MHz, 10% PER, 250 byte payload. Wanted signal 3 dB above sensitivity level		49		dB
Sensitivity	150 kbps, ±37.5 kHz deviation, 2-GFSK, 920.9 MHz, 273 kHz RX BW, 10% PER, 250 byte payload		-99		dBm
Selectivity, ±400 kHz, 150 kbps, ±37.5 kHz deviation, 2-GFSK, 920.9 MHz	150 kbps, ±37.5 kHz deviation, 2-GFSK, 273 kHz RX Bandwidth, 920.9 MHz, 10% PER, 250 byte payload. Wanted signal 3 dB above sensitivity level		41		dB
Selectivity, ±800 kHz, 150 kbps, ±37.5 kHz deviation, 2-GFSK, 920.9 MHz	150 kbps, ±37.5 kHz deviation, 2-GFSK, 273 kHz RX Bandwidth, 920.9 MHz, 10% PER, 250 byte payload. Wanted signal 3 dB above sensitivity level		47		dB
Sensitivity	200 kbps, ±50 kHz deviation, 2-GFSK, 918.4 MHz, 273 kHz RX BW, 10% PER, 250 byte payload		-99		dBm
Selectivity, ±400 kHz, 200 kbps, ±50 kHz deviation, 2-GFSK, 918.4 MHz	200 kbps, ±50 kHz deviation, 2-GFSK, 273 kHz RX Bandwidth, 918.4 MHz, 10% PER, 250 byte payload. Wanted signal 3 dB above sensitivity level		42		dB
Selectivity, ±800 kHz, 200 kbps, ±50 kHz deviation, 2-GFSK, 918.4 MHz	200 kbps, ±50 kHz deviation, 2-GFSK, 273 kHz RX Bandwidth, 918.4 MHz, 10% PER, 250 byte payload. Wanted signal 3 dB above sensitivity level		49		dB
Sensitivity	200 kbps, ±100 kHz deviation, 2-GFSK, 920.8 MHz, 273 kHz RX BW, 10% PER, 250 byte payload		-99		dBm
Selectivity, ±600 kHz, 200 kbps, ±100 kHz deviation, 2-GFSK, 920.8 MHz	200 kbps, ±100 kHz deviation, 2-GFSK, 273 kHz RX Bandwidth, 920.8 MHz,, 10% PER, 250 byte payload. Wanted signal 3 dB above sensitivity level		45		dB
Selectivity, ±1200 kHz, 200 kbps, ±100 kHz deviation, 2-GFSK, 920.8 MHz	200 kbps, ±100 kHz deviation, 2-GFSK, 273 kHz RX Bandwidth, 920.8 MHz,, 10% PER, 250 byte payload. Wanted signal 3 dB above sensitivity level		52		dB
Sensitivity	300 kbps, ±75 kHz deviation, 2-GFSK, 917.6 MHz, 498 kHz RX BW, 10% PER, 250 byte payload		-97		dBm
Selectivity, ±600 kHz, 300 kbps, ±75 kHz deviation, 2-GFSK, 917.6 MHz	300 kbps, ±75 kHz deviation, 2-GFSK, 498 kHz RX Bandwidth, 917.6 MHz., 10% PER, 250 byte payload. Wanted signal 3 dB above sensitivity level		42		dB
Selectivity, ±1200 kHz, 300 kbps, ±75 kHz deviation, 2-GFSK, 917.6 MHz	300 kbps, ±75 kHz deviation, 2-GFSK, 498 kHz RX Bandwidth, 917.6 MHz,, 10% PER, 250 byte payload. Wanted signal 3 dB above sensitivity level		47		dB

⁽¹⁾ Wanted signal 3 dB above the reference sensitivity limit according to ETSI EN 300 220 v. 3.1.1



7.11 861 MHz to 1054 MHz - Transmit (TX)

When measured on the CC1312-R7EM-5XD7793 reference design with T_c = 25 °C, V_{DDS} = 3.0 V with DC/DC enabled using 2-GFSK, 50 kbps, ±25 kHz deviation unless otherwise noted. All measurements are performed at the antenna input with a combined RX and TX path. All measurements are performed conducted. (1)

	PARAMETER	TEST CONDITIONS	MIN TYP MAX	UNIT
General parameters				
Max output power, boost mode		VDDR = 1.95 V Minimum supply voltage (VDDS) for boost mode is 2.1 V 868 MHz and 915 MHz	14	dBm
Max output power		868 MHz and 915 MHz	13	dBm
Output power programmab	ole range	868 MHz and 915 MHz	34	dB
Output power variation ove	er temperature	+10 dBm setting Over recommended temperature operating range	±2	dB
Output power variation ove Boost mode	er temperature	+14 dBm setting Over recommended temperature operating range	±1.5	dB
Spurious emissions and	harmonics			
Spurious emissions 30 MHz to 1 GHz		+14 dBm setting ETSI restricted bands	< -54	dBm
		+14 dBm setting ETSI outside restricted bands	< -36	dBm
	1 GHz to 12.75 GHz (outside ETSI restricted bands)	+14 dBm setting measured in 1 MHz bandwidth (ETSI)	< -30	dBm
Spurious emissions out- of-band, 915 MHz ⁽²⁾	30 MHz to 88 MHz (within FCC restricted bands)	+14 dBm setting	< -56	dBm
	88 MHz to 216 MHz (within FCC restricted bands)	+14 dBm setting	< -52	dBm
	216 MHz to 960 MHz (within FCC restricted bands)	+14 dBm setting	< -50	dBm
	960 MHz to 2390 MHz and above 2483.5 MHz (within FCC restricted band)	+14 dBm setting	<-42	dBm
	1 GHz to 12.75 GHz (outside FCC restricted bands)	+14 dBm setting	< -40	dBm
	Below 710 MHz (ARIB T-108)	+14 dBm setting	< -36	dBm
	710 MHz to 900 MHz (ARIB T-108)	+14 dBm setting	< -55	dBm
Spurious emissions out- of-band, 920.6/928 MHz	900 MHz to 915 MHz (ARIB T-108)	+14 dBm setting	< -55	dBm
(2)	930 MHz to 1000 MHz (ARIB T-108)	+14 dBm setting	< -55	dBm
	1000 MHz to 1215 MHz (ARIB T-108)	+14 dBm setting	< -45	dBm
	Above 1215 MHz (ARIB T-108)	+14 dBm setting	< -30	dBm
	Second harmonic	+14 dBm setting, 868 MHz	< -30	dBm
		+14 dBm setting, 915 MHz	< -30	45111
Harmonics	Third harmonic	+14 dBm setting, 868 MHz	< -30	dBm
		+14 dBm setting, 915 MHz	< -42	
	Fourth harmonic	+14 dBm setting, 868 MHz	< -30	dBm
		+14 dBm setting, 915 MHz	< -30	
	Fifth harmonic	+14 dBm setting, 868 MHz	< -30	dBm
		+14 dBm setting, 915 MHz	< -42	
Adjacent Channel Power	1			
Adjacent channel power, regular 14 dBm PA	Adjacent channel, 20 kHz offset. 9.6 kbps, h=0.5	12.5 dBm setting. 868.3 MHz. 14 kHz channel BW	-23	dBm

7.11 861 MHz to 1054 MHz - Transmit (TX) (continued)

When measured on the CC1312-R7EM-5XD7793 reference design with T_c = 25 °C, V_{DDS} = 3.0 V with DC/DC enabled using 2-GFSK, 50 kbps, ±25 kHz deviation unless otherwise noted. All measurements are performed at the antenna input with a combined RX and TX path. All measurements are performed conducted. (1)

ı	PARAMETER	TEST CONDITIONS	MIN	TYP	MAX	UNIT
Alternate channel power, egular 14 dBm PA	Alternate channel, 40 kHz offset. 9.6 kbps, h=0.5	12.5 dBm setting. 868.3 MHz. 14 kHz channel BW		-29		dBm

- (1) Some combinations of frequency, data rate and modulation format requires use of external crystal load capacitors for regulatory compliance. More details can be found in the device errata.
- (2) Suitable for systems targeting compliance with EN 300 220, EN 303 131, EN 303 204, FCC CFR47 Part 15, ARIB STD-T108.

7.12 861 MHz to 1054 MHz - PLL Phase Noise Wideband Mode

When measured on the CC1312-R7EM-XD7793 reference design with T_c = 25 °C, V_{DDS} = 3.0 V.

PARAMETER	TEST CONDITIONS	MIN	TYP	MAX	UNIT
	±10 kHz offset		- 75		dBc/Hz
	±100 kHz offset		-98		dBc/Hz
	±200 kHz offset		-106		dBc/Hz
Phase noise in the 868- and 915-MHz bands 20 kHz PLL loop bandwidth	±400 kHz offset		-113		dBc/Hz
	±1000 kHz offset		-122		dBc/Hz
	±2000 kHz offset		-129		dBc/Hz
	±10000 kHz offset		-140		dBc/Hz

7.13 861 MHz to 1054 MHz - PLL Phase Noise Narrowband Mode

When measured on the CC1312-R7EM-XD7793 reference design with $T_c = 25$ °C, $V_{DDS} = 3.0$ V.

	3 C 7 BBG							
PARAMETER	TEST CONDITIONS	MIN	TYP	MAX	UNIT			
	±10 kHz offset		- 95		dBc/Hz			
	±100 kHz offset		-94		dBc/Hz			
	±200 kHz offset		– 95		dBc/Hz			
Phase noise in the 868- and 915-MHz bands 150 kHz PLL loop bandwith	±400 kHz offset		-104		dBc/Hz			
100 M 12 12 100 p 2 a 10 10 10 10 10 10 10	±1000 kHz offset		-119		dBc/Hz			
	±2000 kHz offset		-129		dBc/Hz			
	±10000 kHz offset		-140		dBc/Hz			

7.14 Timing and Switching Characteristics

7.14.1 Reset Timing

PARAMETER	MIN	TYP	MAX	UNIT
RESET_N low duration	1			μs

7.14.2 Wakeup Timing

Measured over operating free-air temperature with V_{DDS} = 3.0 V (unless otherwise noted). The times listed here do not include software overhead.

PARAMETER	TEST CONDITIONS	MIN	TYP	MAX	UNIT
MCU, Reset to Active ⁽¹⁾		8	50 - 4000		μs
MCU, Shutdown to Active ⁽¹⁾		8	50 - 4000		μs
MCU, Standby to Active			165		μs
MCU, Active to Standby			39		μs



7.14.2 Wakeup Timing (continued)

Measured over operating free-air temperature with V_{DDS} = 3.0 V (unless otherwise noted). The times listed here do not include software overhead.

PARAMETER	TEST CONDITIONS	MIN	TYP	MAX	UNIT
MCU, Idle to Active			15		μs

(1) The wakeup time is dependent on remaining charge on VDDR capacitor when starting the device, and thus how long the device has been in Reset or Shutdown before starting up again. The wake up time increases with a higher capacitor value.

Submit Document Feedback

7.14.3 Clock Specifications

7.14.3.1 48 MHz Crystal Oscillator (XOSC_HF)

Measured on a Texas Instruments reference design with T_c = 25 °C, V_{DDS} = 3.0 V, unless otherwise noted. (1)

	PARAMETER	MIN	TYP	MAX	UNIT
	Crystal frequency		48		MHz
ESR	Equivalent series resistance 6 pF < C _L ≤ 9 pF		20	60	Ω
ESR	Equivalent series resistance $5 \text{ pF} < C_L \le 6 \text{ pF}$			80	Ω
L _M	Motional inductance, relates to the load capacitance that is used for the crystal (C_L in Farads) $^{(5)}$		< 3 × 10 ⁻²⁵ / C _L ²		Н
CL	Crystal load capacitance ⁽⁴⁾	5	7 ⁽³⁾	9	pF
	Start-up time ⁽²⁾		200		μs

- (1) Probing or otherwise stopping the crystal while the DC/DC converter is enabled may cause permanent damage to the device.
- (2) Start-up time using the TI-provided power driver. Start-up time may increase if driver is not used.
- (3) On-chip default connected capacitance including reference design parasitic capacitance. Connected internal capacitance is changed through software in the Customer Configuration section (CCFG).
- (4) Adjustable load capacitance is integrated into the device. External load capacitors are required for systems targeting compliance with certain regulations. See the device errata for further details.
- (5) The crystal manufacturer's specification must satisfy this requirement for proper operation.

7.14.3.2 48 MHz RC Oscillator (RCOSC_HF)

Measured on a Texas Instruments reference design with T_c = 25 °C, V_{DDS} = 3.0 V, unless otherwise noted.

	MIN	TYP	MAX	UNIT
Frequency		48		MHz
Uncalibrated frequency accuracy		±1		%
Calibrated frequency accuracy ⁽¹⁾		±0.25		%
Start-up time		5		μs

(1) Accuracy relative to the calibration source (XOSC_HF)

7.14.3.3 2 MHz RC Oscillator (RCOSC MF)

Measured on a Texas Instruments reference design with T_c = 25 °C, V_{DDS} = 3.0 V, unless otherwise noted.

	MIN	TYP	MAX	UNIT
Calibrated frequency		2		MHz
Start-up time		5		μs

7.14.3.4 32.768 kHz Crystal Oscillator (XOSC_LF)

Measured on a Texas Instruments reference design with T_c = 25 °C, V_{DDS} = 3.0 V, unless otherwise noted.

		MIN	TYP	MAX	UNIT
	Crystal frequency		32.768		kHz
ESR	Equivalent series resistance		30	100	kΩ
C _L	Crystal load capacitance	6	7 ⁽¹⁾	12	pF

(1) Default load capacitance using TI reference designs including parasitic capacitance. Crystals with different load capacitance may be used.

7.14.3.5 32 kHz RC Oscillator (RCOSC_LF)

Measured on a Texas Instruments reference design with T_c = 25 °C, V_{DDS} = 3.0 V, unless otherwise noted.

		MIN	TYP	MAX	UNIT
Frequency			32.8		kHz
Calibrated RTC variation ⁽¹⁾	Calibrated periodically against XOSC_HF ⁽²⁾		±600 ⁽³⁾		ppm
Temperature coefficient			50		ppm/°C

- (1) When using RCOSC_LF as source for the low frequency system clock (SCLK_LF), the accuracy of the SCLK_LF-derived Real Time Clock (RTC) can be improved by measuring RCOSC_LF relative to XOSC_HF and compensating for the RTC tick speed. This functionality is available through the TI-provided Power driver.
- (2) TI driver software calibrates the RTC every time XOSC_HF is enabled.
- (3) Some device's variation can exceed 1000 ppm. Further calibration will not improve variation.

7.14.4 Synchronous Serial Interface (SSI) Characteristics

7.14.4.1 Synchronous Serial Interface (SSI) Characteristics

over operating free-air temperature range (unless otherwise noted)

PARAMETER NO.	PARAMETER		MIN	TYP	MAX	UNIT
S1	t _{clk_per}	SSICIk cycle time	12		65024	System Clocks (2)
S2 ⁽¹⁾	t _{clk_high}	SSICIk high time		0.5		t _{clk_per}
S3 ⁽¹⁾	t _{clk_low}	SSICIk low time		0.5		t _{clk_per}

- (1) Refer to SSI timing diagrams Figure 7-1, Figure 7-2 and Figure 7-3.
- (2) When using the TI-provided Power driver, the SSI system clock is always 48 MHz.




Figure 7-1. SSI Timing for TI Frame Format (FRF = 01), Single Transfer Timing Measurement




Figure 7-2. SSI Timing for MICROWIRE Frame Format (FRF = 10), Single Transfer




Figure 7-3. SSI Timing for SPI Frame Format (FRF = 00), With SPH = 1

7.14.5 UART

7.14.5.1 UART Characteristics

over operating free-air temperature range (unless otherwise noted)

PARAMETER	MIN	TYP	MAX	UNIT
UART rate			2.89	MBaud



7.15 Peripheral Characteristics

7.15.1 ADC

7.15.1.1 Analog-to-Digital Converter (ADC) Characteristics

 T_c = 25 °C, V_{DDS} = 3.0 V and voltage scaling enabled, unless otherwise noted.⁽¹⁾ Performance numbers require use of offset and gain adjustments in software by TI-provided ADC drivers.

	PARAMETER	TEST CONDITIONS	MIN TY	P MAX	UNIT
	Input voltage range		0	VDDS	V
	Resolution		1	12	Bits
	Sample Rate			200	ksps
	Offset	Internal 4.3 V equivalent reference ⁽²⁾	£	±2	LSB
	Gain error	Internal 4.3 V equivalent reference ⁽²⁾	£	±7	LSB
DNL ⁽⁴⁾	Differential nonlinearity		>-	-1	LSB
NL	Integral nonlinearity		ŧ	±4	LSB
		Internal 4.3 V equivalent reference ⁽²⁾ , 200 kSamples/s, 9.6 kHz input tone	9	.8	
		Internal 4.3 V equivalent reference ⁽²⁾ , 200 kSamples/s, 9.6 kHz input tone, DC/DC enabled	9	.8	
		VDDS as reference, 200 kSamples/s, 9.6 kHz input tone	10	.1	
ENOB	Effective number of bits	Internal reference, voltage scaling disabled, 32 samples average, 200 kSamples/s, 300 Hz input tone	11	.1	Bits
		Internal reference, voltage scaling disabled, 14-bit mode, 200 kSamples/s, 600 Hz input tone ⁽⁵⁾	11	.3	
		Internal reference, voltage scaling disabled, 15-bit mode, 200 kSamples/s, 150 Hz input tone ⁽⁵⁾	11	.6	
	Total harmonic distortion	Internal 4.3 V equivalent reference ⁽²⁾ , 200 kSamples/s, 9.6 kHz input tone	-6	35	
THD		VDDS as reference, 200 kSamples/s, 9.6 kHz input tone	-7	70	dB
		Internal reference, voltage scaling disabled, 32 samples average, 200 kSamples/s, 300 Hz input tone	-7	72	
	Signal-to-noise	Internal 4.3 V equivalent reference ⁽²⁾ , 200 kSamples/s, 9.6 kHz input tone	6	60	
SINAD, SNDR	and	VDDS as reference, 200 kSamples/s, 9.6 kHz input tone	6	33	dB
	distortion ratio	Internal reference, voltage scaling disabled, 32 samples average, 200 kSamples/s, 300 Hz input tone	6	68	
		Internal 4.3 V equivalent reference ⁽²⁾ , 200 kSamples/s, 9.6 kHz input tone	7	70	
SFDR	Spurious-free dynamic range	VDDS as reference, 200 kSamples/s, 9.6 kHz input tone	7	73	dB
		Internal reference, voltage scaling disabled, 32 samples average, 200 kSamples/s, 300 Hz input tone	7	75	
	Conversion time	Serial conversion, time-to-output, 24 MHz clock	Ę	50	Clock Cycles
	Current consumption	Internal 4.3 V equivalent reference ⁽²⁾	0.4	10	mA
	Current consumption	VDDS as reference	0.5	57	mA
	Reference voltage	Equivalent fixed internal reference (input voltage scaling enabled). For best accuracy, the ADC conversion should be initiated through the TI-RTOS API in order to include the gain/ offset compensation factors stored in FCFG1	4.3 ⁽²⁾	(3)	V
	Reference voltage	Fixed internal reference (input voltage scaling disabled). For best accuracy, the ADC conversion should be initiated through the TI-RTOS API in order to include the gain/offset compensation factors stored in FCFG1. This value is derived from the scaled value (4.3 V) as follows: $V_{\text{ref}} = 4.3 \text{ V} \times 1408 \text{ / }4095$	1.4	1 8	V
	Reference voltage	VDDS as reference, input voltage scaling enabled	VDD	s	V
	Reference voltage	VDDS as reference, input voltage scaling disabled	VDDS 2.82		V

Submit Document Feedback

www.ti.com

7.15.1.1 Analog-to-Digital Converter (ADC) Characteristics (continued)

 T_c = 25 °C, V_{DDS} = 3.0 V and voltage scaling enabled, unless otherwise noted.⁽¹⁾

Performance numbers require use of offset and gain adjustments in software by TI-provided ADC drivers.

	PARAMETER	TEST CONDITIONS	MIN	TYP	MAX	UNIT
l.		200 kSamples/s, voltage scaling enabled. Capacitive input, Input impedance depends on sampling frequency and sampling time		>1		ΜΩ

- (1) Using IEEE Std 1241-2010 for terminology and test methods
- (2) Input signal scaled down internally before conversion, as if voltage range was 0 to 4.3 V
- (3) Applied voltage must be within Absolute Maximum Ratings at all times
- (4) No missing codes
- (5) ADC_output = $\Sigma(4^n \text{ samples}) >> n, n = \text{desired extra bits}$

7.15.2 DAC

7.15.2.1 Digital-to-Analog Converter (DAC) Characteristics

 T_c = 25 °C, V_{DDS} = 3.0 V, unless otherwise noted.

	PARAMETER	TEST CONDITIONS	MIN	TYP	MAX	UNIT
Genera	l Parameters					
	Resolution			8		Bits
	Supply voltage	Any load, any V _{REF} , pre-charge OFF, DAC charge-pump ON	1.8		3.8	
V_{DDS}		External Load $^{(4)}$, any V_{REF} , pre-charge OFF, DAC charge-pump OFF	2.0		3.8	V
		Any load, V _{REF} = DCOUPL, pre-charge ON	2.6		3.8	
_	Clock froguency	Buffer ON (recommended for external load)	16		250	kHz
F _{DAC}	Clock frequency	Buffer OFF (internal load)	16		1000	KMZ
	Voltage output settling time	V _{REF} = VDDS, buffer OFF, internal load		13		1/5
	Voltage output settling time	V _{REF} = VDDS, buffer ON, external capacitive load = 20 pF ⁽³⁾		13.8		1 / F _{DAC}
	External capacitive load			20	200	pF
	External resistive load		10			МΩ
	Short circuit current				400	μΑ
	Max output impedance Vref = VDDS, buffer ON, CLK 250	VDDS = 3.8 V, DAC charge-pump OFF		50.8		
		VDDS = 3.0 V, DAC charge-pump ON		51.7		
		VDDS = 3.0 V, DAC charge-pump OFF		53.2		
Z_{MAX}		VDDS = 2.0 V, DAC charge-pump ON		48.7		kΩ
	kHz	VDDS = 2.0 V, DAC charge-pump OFF		70.2		
		VDDS = 1.8 V, DAC charge-pump ON		46.3		
		VDDS = 1.8 V, DAC charge-pump OFF		88.9		
Interna	Load - Continuous Time Com	parator / Low Power Clocked Comparator				
DAII	Differential nonlinearity	V _{REF} = VDDS, load = Continuous Time Comparator or Low Power Clocked Comparator F _{DAC} = 250 kHz		±1		L CD(1)
DNL	Differential nonlinearity	V _{REF} = VDDS, load = Continuous Time Comparator or Low Power Clocked Comparator F _{DAC} = 16 kHz		±1.2		LSB ⁽¹⁾
		V _{REF} = VDDS = 3.8 V		±0.64		
		V _{REF} = VDDS= 3.0 V		±0.81		
	Offset error ⁽²⁾	V _{REF} = VDDS = 1.8 V		±1.27		LSB ⁽¹⁾
	Load = Continuous Time Comparator	V _{REF} = DCOUPL, pre-charge ON		±3.43		rob(,)
	Comparator	V _{REF} = DCOUPL, pre-charge OFF		±2.88		
		V _{REF} = ADCREF		±2.37		



7.15.2.1 Digital-to-Analog Converter (DAC) Characteristics (continued)

T_c = 25 °C, V_{DDS} = 3.0 V, unless otherwise noted.

	PARAMETER	TEST CONDITIONS	MIN TYP	MAX	UNIT
		V _{REF} = VDDS= 3.8 V	±0.78		
		V _{REF} = VDDS = 3.0 V	±0.77		
	Offset error ⁽²⁾ Load = Low Power Clocked	V _{REF} = VDDS= 1.8 V	±3.46		LSB ⁽¹⁾
	Comparator	V _{REF} = DCOUPL, pre-charge ON	±3.44		LOB(1)
		V _{REF} = DCOUPL, pre-charge OFF	±4.70		
		V _{REF} = ADCREF	±4.11		
		V _{REF} = VDDS = 3.8 V	±1.53		
	Max code output voltage variation ⁽²⁾	V _{REF} = VDDS = 3.0 V	±1.71		
		V _{REF} = VDDS= 1.8 V	±2.10		. 00(1)
	Load = Continuous Time	V _{REF} = DCOUPL, pre-charge ON	±6.00		LSB ⁽¹⁾
	Comparator	V _{REF} = DCOUPL, pre-charge OFF	±3.85		
		V _{REF} = ADCREF	±5.84		
		V _{REF} = VDDS= 3.8 V	±2.92		
		V _{REF} =VDDS= 3.0 V	±3.06	;	
	Max code output voltage variation ⁽²⁾	V _{REF} = VDDS= 1.8 V	±3.91		(1)
	variation ⁽²⁾ Load = Low Power Clocked Comparator	V _{REF} = DCOUPL, pre-charge ON	±7.84		LSB ⁽¹⁾
		V _{RFF} = DCOUPL, pre-charge OFF	±4.06		
		V _{REF} = ADCREF	±6.94		
		V _{REF} = VDDS = 3.8 V, code 1	0.03		
		V _{REF} = VDDS = 3.8 V, code 255	3.62	!	
		V _{REF} = VDDS= 3.0 V, code 1	0.02	!	
	Output voltage range ⁽²⁾ Load = Continuous Time Comparator	V _{REF} = VDDS= 3.0 V, code 255	2.86	;	
		V _{REF} = VDDS= 1.8 V, code 1	0.01		
		V _{REF} = VDDS = 1.8 V, code 255	1.71		
		V _{REF} = DCOUPL, pre-charge OFF, code 1	0.01		V
		V _{REF} = DCOUPL, pre-charge OFF, code 255	1.21		
		V _{REF} = DCOUPL, pre-charge ON, code 1	1.27		
		V _{REF} = DCOUPL, pre-charge ON, code 255	2.46		
		V _{REF} = ADCREF, code 1	0.01		
		V _{REF} = ADCREF, code 255	1.41		
		V _{REF} = VDDS = 3.8 V, code 1	0.03		
		V _{REF} = VDDS= 3.8 V, code 255	3.61		
		V _{REF} = VDDS= 3.0 V, code 1	0.02		
		V _{REF} = VDDS= 3.0 V, code 255	2.85		
		V _{REF} = VDDS = 1.8 V, code 1	0.01		
	Output voltage range ⁽²⁾	V _{REF} = VDDS = 1.8 V, code 255	1.71		
	Load = Low Power Clocked	V _{REF} = DCOUPL, pre-charge OFF, code 1	0.01		V
	Comparator	V _{REF} = DCOUPL, pre-charge OFF, code 255	1.21		
		V _{REF} = DCOUPL, pre-charge ON, code 1	1.27		
		V _{REF} = DCOUPL, pre-charge ON, code 255	2.46		
		V _{REF} = DCOOPE, pre-charge ON, code 255	0.01		
		V _{REF} = ADCREF, code 1 V _{REF} = ADCREF, code 255	1.41		
orna	_	* KEF - ADOINET, COUG 200	1.41		
GIIId	ii Loau	V _{REF} = VDDS, F _{DAC} = 250 kHz	. 4		
	Integral poplinggrity		±1		LSB ⁽¹⁾
-	Integral nonlinearity	V _{REF} = DCOUPL, F _{DAC} = 250 kHz		-	LOD(1)
		V_{REF} = ADCREF, F_{DAC} = 250 kHz V_{REF} = VDDS, F_{DAC} = 250 kHz	±1		

www.ti.com

7.15.2.1 Digital-to-Analog Converter (DAC) Characteristics (continued)

T_c = 25 °C. V_{DDS} = 3.0 V. unless otherwise noted

PARAMETER	TEST CONDITIONS	MIN TYP	MAX	UNIT	
	V _{REF} = VDDS= 3.8 V	±0.40			
	V _{REF} = VDDS= 3.0 V	±0.50			
Offset error	V _{REF} = VDDS = 1.8 V	±0.75		LSB ⁽¹⁾	
Oliset error	V _{REF} = DCOUPL, pre-charge ON	±1.55		LOB	
	V _{REF} = DCOUPL, pre-charge OFF	±1.30			
	V _{REF} = ADCREF	±1.10			
	V _{REF} = VDDS= 3.8 V	±1.00			
	V _{REF} = VDDS= 3.0 V	±1.00			
Max code output voltage	V _{REF} = VDDS= 1.8 V	±1.00		LSB ⁽¹⁾	
variation	V _{REF} = DCOUPL, pre-charge ON	±3.45		LSB(1)	
	V _{REF} = DCOUPL, pre-charge OFF	±2.10			
	V _{REF} = ADCREF	±1.90			
	V _{REF} = VDDS = 3.8 V, code 1	0.03			
	V _{REF} = VDDS = 3.8 V, code 255	3.61			
	V _{REF} = VDDS = 3.0 V, code 1	0.02			
	V _{REF} = VDDS= 3.0 V, code 255	2.85			
	V _{REF} = VDDS= 1.8 V, code 1	0.02			
Output voltage range Load = Low Power Clocked	V _{REF} = VDDS = 1.8 V, code 255	1.71		V	
Comparator	V _{REF} = DCOUPL, pre-charge OFF, code 1	0.02		V	
	V _{REF} = DCOUPL, pre-charge OFF, code 255	1.20			
	V _{REF} = DCOUPL, pre-charge ON, code 1	1.27			
	V _{REF} = DCOUPL, pre-charge ON, code 255	2.46			
	V _{REF} = ADCREF, code 1	0.02			
	V _{REF} = ADCREF, code 255	1.42			

¹ LSB (V_{REF} 3.8 V/3.0 V/1.8 V/DCOUPL/ADCREF) = 14.10 mV/11.13 mV/6.68 mV/4.67 mV/5.48 mV

⁽²⁾ Includes comparator offset

⁽³⁾ A load > 20 pF will increases(4) Keysight 34401A Multimeter A load > 20 pF will increases the settling time

7.15.3 Temperature and Battery Monitor

7.15.3.1 Temperature Sensor

Measured on a Texas Instruments reference design with T_c = 25 °C, V_{DDS} = 3.0 V, unless otherwise noted.

PARAMETER	TEST CONDITIONS	MIN	TYP	MAX	UNIT
Resolution			2		°C
Accuracy	-40 °C to 0 °C		±4.0		°C
Accuracy	0 °C to 105 °C		±2.5		°C
Supply voltage coefficient ⁽¹⁾			3.6		°C/V

(1) The temperature sensor is automatically compensated for VDDS variation when using the TI-provided temperature driver.

7.15.3.2 Battery Monitor

Measured on a Texas Instruments reference design with T_c = 25 °C, unless otherwise noted.

PARAMETER	TEST CONDITIONS	MIN	TYP	MAX	UNIT
Resolution			25		mV
Range		1.8		3.8	V
Integral nonlinearity (max)			23		mV
Accuracy	VDDS = 3.0 V		22.5		mV
Offset error			-32		mV
Gain error			-1		%

7.15.4 Comparators

7.15.4.1 Low-Power Clocked Comparator

 $T_c = 25$ °C, $V_{DDS} = 3.0$ V, unless otherwise noted.

PARAMETER	TEST CONDITIONS	MIN	TYP	MAX	UNIT
Input voltage range		0		V _{DDS}	V
Clock frequency			SCLK_LF		
Internal reference voltage ⁽¹⁾	Using internal DAC with VDDS as reference voltage, DAC code = 0 - 255	0.	024 - 2.865		V
Offset	Measured at V _{DDS} / 2, includes error from internal DAC		±5		mV
Decision time	Step from -50 mV to 50 mV		1		Clock Cycle

⁽¹⁾ The comparator can use an internal 8 bits DAC as its reference. The DAC output voltage range depends on the reference voltage selected. See #none#

7.15.4.2 Continuous Time Comparator

 $T_c = 25$ °C, $V_{DDS} = 3.0$ V, unless otherwise noted.

PARAMETER	TEST CONDITIONS	MIN	TYP	MAX	UNIT
Input voltage range ⁽¹⁾		0		V_{DDS}	V
Offset	Measured at V _{DDS} / 2		±5		mV
Decision time	Step from -10 mV to 10 mV		0.70		μs
Current consumption	Internal reference		8.0		μA

(1) The input voltages can be generated externally and connected throughout I/Os or an internal reference voltage can be generated using the DAC

Product Folder Links: CC1312R7

7.15.5 Current Source

7.15.5.1 Programmable Current Source

 T_c = 25 °C, V_{DDS} = 3.0 V, unless otherwise noted.

PARAMETER	TEST CONDITIONS	MIN TYP	MAX	UNIT
Current source programmable output range (logarithmic range)		0.25 - 20		μA
Resolution		0.25		μA

7.15.6 GPIO

7.15.6.1 GPIO DC Characteristics

Measurements CBSed to PG2.1:


PARAMETER	TEST CONDITIONS	MIN TYP	MAX	UNIT
T _A = 25 °C, V _{DDS} = 1.8 V				
GPIO VOH at 8 mA load	IOCURR = 2, high-drive GPIOs only	1.56		V
GPIO VOL at 8 mA load	IOCURR = 2, high-drive GPIOs only	0.24		V
GPIO VOH at 4 mA load	IOCURR = 1	1.59		V
GPIO VOL at 4 mA load	IOCURR = 1	0.21		V
GPIO pullup current	Input mode, pullup enabled, Vpad = 0 V	73		μA
GPIO pulldown current	Input mode, pulldown enabled, Vpad = VDDS	19		μA
GPIO low-to-high input transition, with hysteresis	IH = 1, transition voltage for input read as $0 \rightarrow 1$	1.08		V
GPIO high-to-low input transition, with hysteresis	IH = 1, transition voltage for input read as $1 \rightarrow 0$	0.73		V
GPIO input hysteresis	IH = 1, difference between $0 \rightarrow 1$ and $1 \rightarrow 0$ points	0.35		V
T _A = 25 °C, V _{DDS} = 3.0 V				
GPIO VOH at 8 mA load	IOCURR = 2, high-drive GPIOs only	2.59		V
GPIO VOL at 8 mA load	IOCURR = 2, high-drive GPIOs only	0.42		V
GPIO VOH at 4 mA load	IOCURR = 1	2.63		V
GPIO VOL at 4 mA load	IOCURR = 1	0.40		V
T _A = 25 °C, V _{DDS} = 3.8 V				
GPIO pullup current	Input mode, pullup enabled, Vpad = 0 V	282		μA
GPIO pulldown current	Input mode, pulldown enabled, Vpad = VDDS	110		μA
GPIO low-to-high input transition, with hysteresis	IH = 1, transition voltage for input read as $0 \rightarrow 1$	1.97		V
GPIO high-to-low input transition, with hysteresis	IH = 1, transition voltage for input read as $1 \rightarrow 0$	1.55		V
GPIO input hysteresis	IH = 1, difference between $0 \rightarrow 1$ and $1 \rightarrow 0$ points	0.42		V
T _A = 25 °C				
VIH	Lowest GPIO input voltage reliably interpreted as a High	0.8*V _{DDS}		V
VIL	Highest GPIO input voltage reliably interpreted as a Low		0.2*V _{DDS}	V



7.16 Typical Characteristics

All measurements in this section are done with T_c = 25 °C and V_{DDS} = 3.0 V, unless otherwise noted. See Section 7.3 for device limits. Values exceeding these limits are for reference only.

7.16.1 MCU Current








Figure 7-5. Standby Mode (MCU) Current vs. Temperature

7.16.2 RX Current









Figure 7-7. RX Current vs. Supply Voltage (VDDS) (50 kbps, 868.3 MHz)

7.16.3 TX Current






Figure 7-9. TX Current vs. Supply Voltage (VDDS) (50 kbps; 868.3 MHz)

Table 7-1. Typical TX Current and Output Power


	CC1312R7 at 868 MHz, VDDS	= 3.6 V ⁽¹⁾ (Measured on CC1312-7	REM-XD7793)
txPower	TX Power Setting (SmartRF Studio)	Typical Output Power [dBm]	Typical Current Consumption [mA]
0x013F (2)	14	14.6	25
0xB224	12.5	13.0	18
0x895E	12	12.6	17
0x669A	11	11.6	16
0x3E92	10	10.7	15
0x3EDC	9	9.7	14
0x2CD8	8	9.1	13
0x26D4	7	8.2	12
0x20D1	6	7.2	11
0x1CCE	5	5.9	10
0x16CD	4	5.4	10
0x14CB	3	4.1	9
0x12CA	2	3.3	9
0x12C9	1	2.5	8
0x10C8	0	1.5	8
0x0AC4	-5	-4.6	6
0x0AC2	-10	-10.3	5
0x06C1	-15	-14.8	5
0x04C0	-20	-19.8	4

⁽¹⁾ Internal regulated voltage powers the PA, therefore the output power is not affected by variation in VDDS voltage.

⁽²⁾ Boost mode enabled. VDDR regulated to 1.95 V.



7.16.4 RX Performance



7.16.4 RX Performance (continued)




Figure 7-16. PER vs. Level vs. Frequency (SimpleLink™ Long Range 5 kbps, 868 MHz)






Figure 7-17. Narrowband, 9.6 kbps ±2.4 kHz deviation, 2-GFSK, 868 MHz, 17.1 kHz RX Bandwidth



7.16.5 TX Performance



7.16.6 ADC Performance





8 Detailed Description

8.1 Overview

Section 3.1 shows the core modules of the CC1312R7 device.

8.2 System CPU

The CC1312R7 SimpleLink[™] Wireless MCU contains an Arm[®] Cortex[®]-M4F system CPU, which runs the application and the higher layers of radio protocol stacks.

The system CPU is the foundation of a high-performance, low-cost platform that meets the system requirements of minimal memory implementation, and low-power consumption, while delivering outstanding computational performance and exceptional system response to interrupts.

Its features include the following:

- ARMv7-M architecture optimized for small-footprint embedded applications
- Arm Thumb®-2 mixed 16- and 32-bit instruction set delivers the high performance expected of a 32-bit Arm
 core in a compact memory size
- Fast code execution permits increased sleep mode time
- Deterministic, high-performance interrupt handling for time-critical applications
- Single-cycle multiply instruction and hardware divide
- · Hardware division and fast digital-signal-processing oriented multiply accumulate
- Saturating arithmetic for signal processing
- IEEE 754-compliant single-precision Floating Point Unit (FPU)
- · Memory Protection Unit (MPU) for safety-critical applications
- Full debug with data matching for watchpoint generation
 - Data Watchpoint and Trace Unit (DWT)
 - JTAG Debug Access Port (DAP)
 - Flash Patch and Breakpoint Unit (FPB)
- Trace support reduces the number of pins required for debugging and tracing
 - Instrumentation Trace Macrocell Unit (ITM)
 - Trace Port Interface Unit (TPIU) with asynchronous serial wire output (SWO)
- Optimized for single-cycle flash memory access
- Tightly connected to 8-KB 4-way random replacement cache for minimal active power consumption and wait states
- Ultra-low-power consumption with integrated sleep modes
- 48 MHz operation
- 1.25 DMIPS per MHz

8.3 Radio (RF Core)

The RF Core is a highly flexible and future proof radio module which contains an Arm Cortex-M0 processor that interfaces the analog RF and base-band circuitry, handles data to and from the system CPU side, and assembles the information bits in a given packet structure. The RF core offers a high level, command-based API to the main CPU that configurations and data are passed through. The Arm Cortex-M0 processor is not programmable by customers and is interfaced through the TI-provided RF driver that is included with the SimpleLink Software Development Kit (SDK).

The RF core can autonomously handle the time-critical aspects of the radio protocols, thus offloading the main CPU, which reduces power and leaves more resources for the user application. Several signals are also available to control external circuitry such as RF switches or range extenders autonomously.

The various physical layer radio formats are partly built as a software defined radio where the radio behavior is either defined by radio ROM contents or by non-ROM radio formats delivered in form of firmware patches with the SimpleLink SDKs. This allows the radio platform to be updated for support of future versions of standards even with over-the-air (OTA) updates while still using the same silicon.

Note

Not all combinations of features, frequencies, data rates, and modulation formats described in this chapter are supported. Over time, TI can enable new physical radio formats (PHYs) for the device and provides performance numbers for selected PHYs in the data sheet. Supported radio formats for a specific device, including optimized settings to use with the TI RF driver, are included in the SmartRF Studio tool with performance numbers of selected formats found in Section 7.

8.3.1 Proprietary Radio Formats

The CC1312R7 radio can support a wide range of physical radio formats through a set of hardware peripherals combined with firmware available in the device ROM, covering various customer needs for optimizing towards parameters such as speed or sensitivity. This allows great flexibility in tuning the radio both to work with legacy protocols as well as customizing the behavior for specific application needs.

Table 8-1 gives a simplified overview of features of the various radio formats available in ROM. Other radio formats may be available in the form of radio firmware patches or programs through the Software Development Kit (SDK) and may combine features in a different manner, as well as add other features.

Table	8-1.	Feature	Sup	port
--------------	------	----------------	-----	------

Feature	Main 2-(G)FSK Mode	High Data Rates	Low Data Rates	SimpleLink™ Long Range
Programmable preamble, sync word and CRC	Yes	Yes	Yes	No
Programmable receive bandwidth	Yes	Yes	Yes (down to 4 kHz)	Yes
Data / Symbol rate ⁽³⁾	20 to 1000 kbps	≤ 2 Msps	≤ 100 ksps	≤ 20 ksps
Modulation format	2-(G)FSK	2-(G)FSK 4-(G)FSK	2-(G)FSK 4-(G)FSK	2-(G)FSK
Dual Sync Word	Yes	Yes	No	No
Carrier Sense (1) (2)	Yes	No	No	No
Preamble Detection ⁽²⁾	Yes	Yes	Yes	No
Data Whitening	Yes	Yes	Yes	Yes
Digital RSSI	Yes	Yes	Yes	Yes
CRC filtering	Yes	Yes	Yes	Yes
Direct-sequence spread spectrum (DSSS)	No	No	No	1:2 1:4 1:8
Forward error correction (FEC)	No	No	No	Yes
Link Quality Indicator (LQI)	Yes	Yes	Yes	Yes

⁽¹⁾ Carrier Sense can be used to implement HW-controlled listen-before-talk (LBT) and Clear Channel Assessment (CCA) for compliance with such requirements in regulatory standards. This is available through the CMD PROP CS radio API.

8.4 Memory

The up to 704KB nonvolatile (flash) memory provides storage for code and data. The flash memory is in-system programmable and erasable. The last flash memory sector must contain a Customer Configuration section (CCFG) that is used by boot ROM and TI provided drivers to configure the device. This configuration is done through the ccfg.c source file that is included in all TI provided examples.

The ultra-low leakage system static RAM (SRAM) is split into four 32KB and one 16KB blocks and can be used for both storage of data and execution of code. Retention of SRAM contents in Standby power mode is enabled by default and included in Standby mode power consumption numbers. Parity checking for detection of bit errors in memory is built-in, which reduces chip-level soft errors and thereby increases reliability. System SRAM is always initialized to zeroes upon code execution from boot.

To improve code execution speed and lower power when executing code from nonvolatile memory, a 4-way nonassociative 8-KB cache is enabled by default to cache and prefetch instructions read by the system CPU. The cache can be used as a general-purpose RAM by enabling this feature in the Customer Configuration Area (CCFG).

⁽²⁾ Carrier Sense and Preamble Detection can be used to implement sniff modes where the radio is duty cycled to save power.

⁽³⁾ Data rates are only indicative. Data rates outside this range may also be supported. For some specific combinations of settings, a smaller range might be supported.

www.ti.com

There is a 4KB ultra-low leakage SRAM available for use with the Sensor Controller Engine which is typically used for storing Sensor Controller programs, data and configuration parameters. This RAM is also accessible by the system CPU. The Sensor Controller RAM is not cleared to zeroes between system resets.

The ROM includes a TI-RTOS kernel and low-level drivers, as well as significant parts of selected radio stacks, which frees up flash memory for the application. The ROM also contains a serial (SPI and UART) bootloader that can be used for initial programming of the device.

8.5 Sensor Controller

The Sensor Controller contains circuitry that can be selectively enabled in both Standby and Active power modes. The peripherals in this domain can be controlled by the Sensor Controller Engine, which is a proprietary power-optimized CPU. This CPU can read and monitor sensors or perform other tasks autonomously; thereby significantly reducing power consumption and offloading the system CPU.

The Sensor Controller Engine is user programmable with a simple programming language that has syntax similar to C. This programmability allows for sensor polling and other tasks to be specified as sequential algorithms rather than static configuration of complex peripheral modules, timers, DMA, register programmable state machines, or event routing.

The main advantages are:

- Flexibility data can be read and processed in unlimited manners while still ensuring ultra-low power
- 2 MHz low-power mode enables lowest possible handling of digital sensors
- Dynamic reuse of hardware resources
- 40-bit accumulator supporting multiplication, addition and shift
- Observability and debugging options

Sensor Controller Studio is used to write, test, and debug code for the Sensor Controller. The tool produces C driver source code, which the System CPU application uses to control and exchange data with the Sensor Controller. Typical use cases may be (but are not limited to) the following:

- Read analog sensors using integrated ADC or comparators
- Interface digital sensors using GPIOs, SPI, UART, or I²C (UART and I²C are bit-banged)
- Capacitive sensing
- Waveform generation
- Very low-power pulse counting (flow metering)
- Key scan

The peripherals in the Sensor Controller include the following:

- The low-power clocked comparator can be used to wake the system CPU from any state in which the comparator is active. A configurable internal reference DAC can be used in conjunction with the comparator. The output of the comparator can also be used to trigger an interrupt or the ADC.
- Capacitive sensing functionality is implemented through the use of a constant current source, a time-to-digital converter, and a comparator. The continuous time comparator in this block can also be used as a higheraccuracy alternative to the low-power clocked comparator. The Sensor Controller takes care of baseline tracking, hysteresis, filtering, and other related functions when these modules are used for capacitive
- The ADC is a 12-bit, 200-ksamples/s ADC with eight inputs and a built-in voltage reference. The ADC can be triggered by many different sources including timers, I/O pins, software, and comparators.
- The analog modules can connect to up to eight different GPIOs
- Dedicated SPI master with up to 6 MHz clock speed

The peripherals in the Sensor Controller can also be controlled from the main application processor.

8.6 Cryptography

The CC1312R7 device comes with a wide set of modern cryptography-related hardware accelerators, drastically reducing code footprint and execution time for cryptographic operations. It also has the benefit of being lower power and improves availability and responsiveness of the system because the cryptography operations runs in a background hardware thread.

Together with a large selection of open-source cryptography libraries provided with the Software Development Kit (SDK), this allows for secure and future proof IoT applications to be easily built on top of the platform. The hardware accelerator modules are:

- True Random Number Generator (TRNG) module provides a true, nondeterministic noise source for the
 purpose of generating keys, initialization vectors (IVs), and other random number requirements. The TRNG is
 built on 24 ring oscillators that create unpredictable output to feed a complex nonlinear-combinatorial circuit.
- Secure Hash Algorithm 2 (SHA-2) with support for SHA224, SHA256, SHA384, and SHA512
- Advanced Encryption Standard (AES) with 128 and 256 bit key lengths
- **Public Key Accelerator** Hardware accelerator supporting mathematical operations needed for elliptic curves up to 512 bits and RSA key pair generation up to 1024 bits.

Through use of these modules and the TI provided cryptography drivers, the following capabilities are available for an application or stack:

· Key Agreement Schemes

- Elliptic curve Diffie
 Hellman with static or ephemeral keys (ECDH and ECDHE)
- Elliptic curve Password Authenticated Key Exchange by Juggling (ECJ-PAKE)

Signature Generation

Elliptic curve Diffie-Hellman Digital Signature Algorithm (ECDSA)

Curve Support

- Short Weierstrass form (full hardware support), such as:
 - NIST-P224, NIST-P256, NIST-P384, NIST-P521
 - Brainpool-256R1, Brainpool-384R1, Brainpool-512R1
 - secp256r1
- Montgomery form (hardware support for multiplication), such as:
 - Curve25519

SHA2 based MACs

- HMAC with SHA224, SHA256, SHA384, or SHA512
- Block cipher mode of operation
 - AESCCM
 - AESGCM
 - AESECB
 - AESCBC
 - AESCBC-MAC

True random number generation

Other capabilities, such as RSA encryption and signatures as well as Edwards type of elliptic curves such as Curve1174 or Ed25519, can also be implemented using the provided hardware accelerators but are not part of the TI SimpleLink SDK for the CC1312R7 device.

Submit Document Feedback

8.7 Timers

A large selection of timers are available as part of the CC1312R7 device. These timers are:

Real-Time Clock (RTC)

A 70-bit 3-channel timer running on the 32 kHz low frequency system clock (SCLK_LF). This timer is available in all power modes except Shutdown. The timer can be calibrated to compensate for frequency drift when using the RCOSC_LF as the low frequency system clock. If an external LF clock with frequency different from 32.768 kHz is used, the RTC tick speed can be adjusted to compensate for this. When using TI-RTOS, the RTC is used as the base timer in the operating system and should thus only be accessed through the kernel APIs such as the Clock module. The real time clock can also be read by the Sensor Controller Engine to timestamp sensor data and also has dedicated capture channels. By default, the RTC halts when a debugger halts the device.

General Purpose Timers (GPTIMER)

The four flexible GPTIMERs can be used as either 4× 32 bit timers or 8× 16 bit timers, all running on up to 48 MHz. Each of the 16- or 32-bit timers support a wide range of features such as one-shot or periodic counting, pulse width modulation (PWM), time counting between edges and edge counting. The inputs and outputs of the timer are connected to the device event fabric, which allows the timers to interact with signals such as GPIO inputs, other timers, DMA and ADC. The GPTIMERs are available in Active and Idle power modes.

Sensor Controller Timers

The Sensor Controller contains 3 timers:

AUX Timer 0 and 1 are 16-bit timers with a 2^N prescaler. Timers can either increment on a clock or on each edge of a selected tick source. Both one-shot and periodical timer modes are available.

AUX Timer 2 is a 16-bit timer that can operate at 24 MHz, 2 MHz or 32 kHz independent of the Sensor Controller functionality. There are 4 capture or compare channels, which can be operated in one-shot or periodical modes. The timer can be used to generate events for the Sensor Controller Engine or the ADC, as well as for PWM output or waveform generation.

Radio Timer

A multichannel 32-bit timer running at 4 MHz is available as part of the device radio. The radio timer is typically used as the timing base in wireless network communication using the 32-bit timing word as the network time. The radio timer is synchronized with the RTC by using a dedicated radio API when the device radio is turned on or off. This ensures that for a network stack, the radio timer seems to always be running when the radio is enabled. The radio timer is in most cases used indirectly through the trigger time fields in the radio APIs and should only be used when the accurate 48 MHz high frequency crystal is the source of SCLK_HF.

· Watchdog timer

The watchdog timer is used to regain control if the system operates incorrectly due to software errors. It is typically used to generate an interrupt to and reset of the device for the case where periodic monitoring of the system components and tasks fails to verify proper functionality. The watchdog timer runs on a 1.5 MHz clock rate and cannot be stopped once enabled. The watchdog timer pauses to run in Standby power mode and when a debugger halts the device.

Copyright © 2021 Texas Instruments Incorporated

Submit Document Feedback

8.8 Serial Peripherals and I/O

The SSIs are synchronous serial interfaces that are compatible with SPI, MICROWIRE, and TI's synchronous serial interfaces. The SSIs support both SPI master and slave up to 4 MHz. The SSI modules support configurable phase and polarity.

The UARTs implement universal asynchronous receiver and transmitter functions. They support flexible baudrate generation up to a maximum of 3 Mbps.

The I²S interface is used to handle digital audio and can also be used to interface pulse-density modulation microphones (PDM).

The I²C interface is used to communicate with devices compatible with the I²C standard. The I²C interface can handle 100 kHz and 400 kHz operation, and can serve as both master and slave.

The I/O controller (IOC) controls the digital I/O pins and contains multiplexer circuitry to allow a set of peripherals to be assigned to I/O pins in a flexible manner. All digital I/Os are interrupt and wake-up capable, have a programmable pullup and pulldown function, and can generate an interrupt on a negative or positive edge (configurable). When configured as an output, pins can function as either push-pull or open-drain. Five GPIOs have high-drive capabilities, which are marked in **bold** in Section 6. All digital peripherals can be connected to any digital pin on the device.

For more information, see the CC13x2x7, CC26x2x7 SimpleLink™ Wireless MCU Technical Reference Manual.

8.9 Battery and Temperature Monitor

A combined temperature and battery voltage monitor is available in the CC1312R7 device. The battery and temperature monitor allows an application to continuously monitor on-chip temperature and supply voltage and respond to changes in environmental conditions as needed. The module contains window comparators to interrupt the system CPU when temperature or supply voltage go outside defined windows. These events can also be used to wake up the device from Standby mode through the Always-On (AON) event fabric.

8.10 µDMA

The device includes a direct memory access (μ DMA) controller. The μ DMA controller provides a way to offload data-transfer tasks from the system CPU, thus allowing for more efficient use of the processor and the available bus bandwidth. The μ DMA controller can perform a transfer between memory and peripherals. The μ DMA controller has dedicated channels for each supported on-chip module and can be programmed to automatically perform transfers between peripherals and memory when the peripheral is ready to transfer more data.

Some features of the µDMA controller include the following (this is not an exhaustive list):

- Highly flexible and configurable channel operation of up to 32 channels
- Transfer modes: memory-to-memory, memory-to-peripheral, peripheral-to-memory, and peripheral-to-peripheral
- Data sizes of 8, 16, and 32 bits
- · Ping-pong mode for continuous streaming of data

8.11 Debug

The on-chip debug support is done through a dedicated cJTAG (IEEE 1149.7) or JTAG (IEEE 1149.1) interface. The device boots by default into cJTAG mode and must be reconfigured to use 4-pin JTAG.

Submit Document Feedback

8.12 Power Management

To minimize power consumption, the CC1312R7 supports a number of power modes and power management features (see Table 8-2).

Table 8-2. Power Modes

MODE	SOFT	RESET PIN				
MODE	ACTIVE	IDLE	STANDBY	SHUTDOWN	HELD	
CPU	Active	Off	Off	Off	Off	
Flash	On	Available	Off	Off	Off	
SRAM	On	On	Retention	Off	Off	
Supply System	On	On	Duty Cycled	Off	Off	
Register and CPU retention	Full	Full	Partial	No	No	
SRAM retention	Full	Full	Full	No	No	
48 MHz high-speed clock (SCLK_HF)	XOSC_HF or RCOSC_HF	XOSC_HF or RCOSC_HF	Off	Off	Off	
2 MHz medium-speed clock (SCLK_MF)	RCOSC_MF	RCOSC_MF	Available	Off	Off	
32 kHz low-speed clock (SCLK_LF)	XOSC_LF or RCOSC_LF	XOSC_LF or RCOSC_LF	XOSC_LF or RCOSC_LF	Off	Off	
Peripherals	Available	Available	Off	Off	Off	
Sensor Controller	Available	Available	Available	Off	Off	
Wake-up on RTC	Available	Available	Available	Off	Off	
Wake-up on pin edge	Available	Available	Available	Available	Off	
Wake-up on reset pin	On	On	On	On	On	
Brownout detector (BOD)	On	On	Duty Cycled	Off	Off	
Power-on reset (POR)	On	On	On	Off	Off	
Watchdog timer (WDT)	Available	Available	Paused	Off	Off	

In **Active** mode, the application system CPU is actively executing code. Active mode provides normal operation of the processor and all of the peripherals that are currently enabled. The system clock can be any available clock source (see Table 8-2).

In **Idle** mode, all active peripherals can be clocked, but the Application CPU core and memory are not clocked and no code is executed. Any interrupt event brings the processor back into active mode.

In **Standby** mode, only the always-on (AON) domain is active. An external wake-up event, RTC event, or Sensor Controller event is required to bring the device back to active mode. MCU peripherals with retention do not need to be reconfigured when waking up again, and the CPU continues execution from where it went into standby mode. All GPIOs are latched in standby mode.

In **Shutdown** mode, the device is entirely turned off (including the AON domain and Sensor Controller), and the I/Os are latched with the value they had before entering shutdown mode. A change of state on any I/O pin defined as a *wake from shutdown pin* wakes up the device and functions as a reset trigger. The CPU can differentiate between reset in this way and reset-by-reset pin or power-on reset by reading the reset status register. The only state retained in this mode is the latched I/O state and the flash memory contents.



The Sensor Controller is an autonomous processor that can control the peripherals in the Sensor Controller independently of the system CPU. This means that the system CPU does not have to wake up, for example to perform an ADC sampling or poll a digital sensor over SPI, thus saving both current and wake-up time that would otherwise be wasted. The Sensor Controller Studio tool enables the user to program the Sensor Controller, control its peripherals, and wake up the system CPU as needed. All Sensor Controller peripherals can also be controlled by the system CPU.

Note

The power, RF and clock management for the CC1312R7 device require specific configuration and handling by software for optimized performance. This configuration and handling is implemented in the TI-provided drivers that are part of the SimpleLink™ CC13xx and CC26xx software development kit (SDK). Therefore, TI highly recommends using this software framework for all application development on the device. The complete SDK with TI-RTOS (optional), device drivers, and examples are offered free of charge in source code.

8.13 Clock Systems

The CC1312R7 device has several internal system clocks.

The 48 MHz SCLK_HF is used as the main system (MCU and peripherals) clock. This can be driven by the internal 48 MHz RC Oscillator (RCOSC_HF) or an external 48 MHz crystal (XOSC_HF). Radio operation requires an external 48 MHz crystal.

SCLK_MF is an internal 2 MHz clock that is used by the Sensor Controller in low-power mode and also for internal power management circuitry. The SCLK_MF clock is always driven by the internal 2 MHz RC Oscillator (RCOSC_MF).

SCLK_LF is the 32.768 kHz internal low-frequency system clock. It can be used by the Sensor Controller for ultra-low-power operation and is also used for the RTC and to synchronize the radio timer before or after Standby power mode. SCLK_LF can be driven by the internal 32.8 kHz RC Oscillator (RCOSC_LF), a 32.768 kHz watch-type crystal, or a clock input on any digital IO.

When using a crystal or the internal RC oscillator, the device can output the 32 kHz SCLK_LF signal to other devices, thereby reducing the overall system cost.

8.14 Network Processor

Depending on the product configuration, the CC1312R7 device can function as a wireless network processor (WNP - a device running the wireless protocol stack with the application running on a separate host MCU), or as a system-on-chip (SoC) with the application and protocol stack running on the device's system CPU inside the device.

In the first case, the external host MCU communicates with the device using SPI or UART. In the second case, the application must be written according to the application framework supplied with the wireless protocol stack.

Submit Document Feedback

9 Application, Implementation, and Layout

Note

Information in the following Applications section is not part of the TI component specification, and TI does not warrant its accuracy or completeness. TI's customers are responsible for determining suitability of components for their purposes. Customers should validate and test their design implementation to confirm system functionality.

For general design guidelines and hardware configuration guidelines, refer to CC13xx/CC26xx Hardware Configuration and PCB Design Considerations Application Report.

9.1 Reference Designs

The following reference designs should be followed closely when implementing designs using the CC1312R7 device.

Special attention must be paid to RF component placement, decoupling capacitors and DCDC regulator components, as well as ground connections for all of these.

CC1312-R7EM-XD7793 Design Files

The differential CC1312-R7EM-XD7793 reference design provides schematic, layout and production files for the characterization board used for deriving the performance number found in this document.

LP-CC1312R7 **Design Files** LP-CC1352P7-4 **Design Files**

The CC1312R7 LaunchPad Design Files contain detailed schematics and layouts to build application specific boards using the CC1312R7 device.

Detailed schematics and layouts for the multi-band CC1352P7 LaunchPad evaluation board featuring 2.4 GHz RF matching optimized for 10 dBm operation on the 20 dBm PA output and up to 13 dBm TX power at 433 MHz. For evaluation of 20 dBm operation at 2.4 GHz the BOM can be modified as described in the schematics available in the Design Files.

For CC1312R7, the sub-1 GHz RF circuitry can be used for 433 MHz operation while the 2.4 GHz and 20 dBm RF circuitry can be disregarded.

Sub-1 GHz for LaunchPad™ **Development** Kit and SensorTag

The antenna kit allows real-life testing to identify the optimal antenna for your and 2.4 GHz Antenna Kit application. The antenna kit includes 16 antennas for frequencies from 169 MHz to 2.4 GHz, including:

- PCB antennas
- Helical antennas
- Chip antennas
- Dual-band antennas for 868 MHz and 915 MHz combined with 2.4 GHz

The antenna kit includes a JSC cable to connect to the Wireless MCU LaunchPad Development Kits and SensorTags.

9.2 Junction Temperature Calculation

This section shows the different techniques for calculating the junction temperature under various operating conditions. For more details, see Semiconductor and IC Package Thermal Metrics.

There are three recommended ways to derive the junction temperature from other measured temperatures:

1. From package temperature:

$$T_I = \psi_{\mathsf{IT}} \times P + T_{\mathsf{case}} \tag{1}$$

2. From board temperature:

$$T_I = \psi_{\rm IB} \times P + T_{\rm board} \tag{2}$$

Copyright © 2021 Texas Instruments Incorporated

Submit Document Feedback

3. From ambient temperature:

$$T_{I} = R_{\theta \mid A} \times P + T_{A} \tag{3}$$

P is the power dissipated from the device and can be calculated by multiplying current consumption with supply voltage. Thermal resistance coefficients are found in Section 7.8.

Example:

Using Equation 3, the temperature difference between ambient temperature and junction temperature is calculated. In this example, we assume a simple use case where the radio is transmitting continuously at 10dBm output power. Let us assume the ambient temperature is 105 $^{\circ}$ C and the supply voltage is 3.0 V. To calculate P, we need to look up the current consumption for Tx at 105 $^{\circ}$ C in Figure 7-8. From the plot, we see that the current consumption is 17.1 mA. This means that P is 3.6 V × 14.7 mA = 52.9 mW.

The junction temperature is then calculated as:

$$T_I = 23.4^{\circ} C/_W \times 52.9 mW + T_A = 1.2^{\circ} C + T_A$$
 (4)

As can be seen from the example, the junction temperature is 1.2 °C higher than the ambient temperature when running continuous Tx at 105 °C and, thus, well within the recommended operating conditions of 115 °C.

For various application use cases current consumption for other modules may have to be added to calculate the appropriate power dissipation. For example, the MCU may be running simultaneously as the radio, peripheral modules may be enabled, etc. Typically, the easiest way to find the peak current consumption, and thus the peak power dissipation in the device, is to measure as described in *Measuring CC13xx and CC26xx Current Consumption*.

10 Device and Documentation Support

TI offers an extensive line of development tools. Tools and software to evaluate the performance of the device, generate code, and develop solutions are listed as follows.

10.1 Device Nomenclature

To designate the stages in the product development cycle, TI assigns prefixes to all part numbers and/or date-code. Each device has one of three prefixes/identifications: X, P, or null (no prefix) (for example, XCC1312R7 is in preview; therefore, an X prefix/identification is assigned).

Device development evolutionary flow:

- **X** Experimental device that is not necessarily representative of the final device's electrical specifications and may not use production assembly flow.
- **P** Prototype device that is not necessarily the final silicon die and may not necessarily meet final electrical specifications.

null Production version of the silicon die that is fully qualified.

Production devices have been characterized fully, and the quality and reliability of the device have been demonstrated fully. Tl's standard warranty applies.

Predictions show that prototype devices (X or P) have a greater failure rate than the standard production devices. Texas Instruments recommends that these devices not be used in any production system because their expected end-use failure rate still is undefined. Only qualified production devices are to be used.

TI device nomenclature also includes a suffix with the device family name. This suffix indicates the package type (for example, *RGZ*).

For orderable part numbers of *CC1312R7* devices in the RGZ (7-mm x 7-mm) package type, see the *Package Option Addendum* of this document, the Device Information in Section 3, the TI website (www.ti.com), or contact your TI sales representative.




Figure 10-1. Device Nomenclature

10.2 Tools and Software

The CC1312R7 device is supported by a variety of software and hardware development tools.

Development Kit

CC1312R LaunchPad™ Development Kit

The CC1312R7 LaunchPad[™] Development Kit enables development of high-performance Sub-1 GHz wireless applications that benefit from low-power operation. The kit features the CC1312R7 Sub-1 GHz SimpleLink Wireless MCU. The kit works with the LaunchPad ecosystem, easily enabling additional functionality like sensors, display, and more. The built-



in EnergyTrace[™] software is an energy-based code analysis tool that measures and displays the application's energy profile and helps to optimize it for ultra-low power consumption.

CC1352P7-4 LaunchPad™ Development Kit

The CC1352P7-4 LaunchPad[™] Development Kit enables development of high-performance wireless applications in the 433 MHz and 2.4 GHz frequency bands that benefit from low-power operation. The kit features the CC1352P7 dual-band and multiprotocol SimpleLink Wireless MCU with an integrated High Power Amplifier. The kit works with the LaunchPad ecosystem, easily enabling additional functionality like sensors, display, and more. The built-in EnergyTrace[™] software is an energy-based code analysis tool that measures and displays the application's energy profile and helps to optimize it for ultra-low-power consumption.

The RF configuration of the LaunchPad enables up to +13 dBm output power for 433 MHz and +10 dBm output power for 2.4 GHz. The LaunchPad can also be used as a development kit when evaluating other device family devices such as CC1312R7 for use with 433 MHz frequency bands or CC2652P7 for +10 dBm in the 2.4 GHz band.

Software

SimpleLink™ CC13XX-CC26XX SDK

The SimpleLink CC13xx and CC26xx Software Development Kit (SDK) provides a complete package for the development of wireless applications on the CC13XX / CC26XX family of devices. The SDK includes a comprehensive software package for the CC1312R7 device, including the following protocol stacks:

- Bluetooth Low Energy 4 and 5.2
- Thread (based on OpenThread)
- Zigbee 3.0
- Wi-SUN®
- TI 15.4-Stack an IEEE 802.15.4-based star networking solution for Sub-1 GHz and 2.4 GHz
- Proprietary RF a large set of building blocks for building proprietary RF software
- Multiprotocol support concurrent operation between stacks using the Dynamic Multiprotocol Manager (DMM)

The SimpleLink CC13XX-CC26XX SDK is part of Tl's SimpleLink MCU platform, offering a single development environment that delivers flexible hardware, software and tool options for customers developing wired and wireless applications. For more information about the SimpleLink MCU Platform, visit http://www.ti.com/simplelink.

Submit Document Feedback

Development Tools

Code Composer Studio™ Integrated Development Environment (IDE)

Code Composer Studio is an integrated development environment (IDE) that supports TI's Microcontroller and Embedded Processors portfolio. Code Composer Studio comprises a suite of tools used to develop and debug embedded applications. It includes an optimizing C/C++ compiler, source code editor, project build environment, debugger, profiler, and many other features. The intuitive IDE provides a single user interface taking you through each step of the application development flow. Familiar tools and interfaces allow users to get started faster than ever before. Code Composer Studio combines the advantages of the Eclipse® software framework with advanced embedded debug capabilities from TI resulting in a compelling feature-rich development environment for embedded developers.

CCS has support for all SimpleLink Wireless MCUs and includes support for EnergyTrace[™] software (application energy usage profiling). A real-time object viewer plugin is available for TI-RTOS, part of the SimpleLink SDK.

Code Composer Studio is provided free of charge when used in conjunction with the XDS debuggers included on a LaunchPad Development Kit.

Code Composer Studio™ Cloud IDE

Code Composer Studio (CCS) Cloud is a web-based IDE that allows you to create, edit and build CCS and Energia[™] projects. After you have successfully built your project, you can download and run on your connected LaunchPad. Basic debugging, including features like setting breakpoints and viewing variable values is now supported with CCS Cloud.

IAR Embedded Workbench® for Arm®

IAR Embedded Workbench[®] is a set of development tools for building and debugging embedded system applications using assembler, C and C++. It provides a completely integrated development environment that includes a project manager, editor, and build tools. IAR has support for all SimpleLink Wireless MCUs. It offers broad debugger support, including XDS110, IAR I-jet™ and Segger J-Link™. A real-time object viewer plugin is available for TI-RTOS, part of the SimpleLink SDK. IAR is also supported out-of-the-box on most software examples provided as part of the SimpleLink SDK.

A 30-day evaluation or a 32 KB size-limited version is available through iar.com.

SmartRF™ Studio

SmartRF™ Studio is a Windows® application that can be used to evaluate and configure SimpleLink Wireless MCUs from Texas Instruments. The application will help designers of RF systems to easily evaluate the radio at an early stage in the design process. It is especially useful for generation of configuration register values and for practical testing and debugging of the RF system. SmartRF Studio can be used either as a standalone application or together with applicable evaluation boards or debug probes for the RF device. Features of the SmartRF Studio include:

- · Link tests transmit and receive packets between nodes
- Antenna and radiation tests set the radio in continuous wave TX and RX states
- Export radio configuration code for use with the TI SimpleLink SDK RF driver
- · Custom GPIO configuration for signaling and control of external switches

Sensor Controller Studio

Sensor Controller Studio is used to write, test and debug code for the Sensor Controller peripheral. The tool generates a Sensor Controller Interface driver, which is a set of C source files that are compiled into the System CPU application. These source files also contain the Sensor Controller binary image and allow the System CPU application to control and exchange data with the Sensor Controller. Features of the Sensor Controller Studio include:

- Ready-to-use examples for several common use cases
- Full toolchain with built-in compiler and assembler for programming in a C-like programming language



Provides rapid development by using the integrated sensor controller task testing and debugging functionality, including visualization of sensor data and verification of algorithms

CCS UniFlash

CCS UniFlash is a standalone tool used to program on-chip flash memory on TI MCUs. UniFlash has a GUI, command line, and scripting interface. CCS UniFlash is available free of charge.

10.2.1 SimpleLink™ Microcontroller Platform

The SimpleLink microcontroller platform sets a new standard for developers with the broadest portfolio of wired and wireless Arm® MCUs (System-on-Chip) in a single software development environment. Delivering flexible hardware, software and tool options for your IoT applications. Invest once in the SimpleLink software development kit and use throughout your entire portfolio. Learn more on ti.com/simplelink.

10.3 Documentation Support

To receive notification of documentation updates on data sheets, errata, application notes and similar, navigate to the device product folder on ti.com/product/CC1312R7. In the upper right corner, click on Alert me to register and receive a weekly digest of any product information that has changed. For change details, review the revision history included in any revised document.

The current documentation that describes the MCU, related peripherals, and other technical collateral is listed as follows.

TI Resource Explorer

TI Resource Explorer Software examples, libraries, executables, and documentation are available for your device and development board.

Errata

CC1312R7 Silicon Errata

The silicon errata describes the known exceptions to the functional specifications for each silicon revision of the device and description on how to recognize a device revision.

Application Reports

All application reports for the CC1312R7 device are found on the device product folder at: ti.com/product/ CC1312R7/#tech-docs.

Technical Reference Manual (TRM)

CC13x2x7, CC26x2x7 SimpleLink™ Wireless MCU TRM

The TRM provides a detailed description of all modules and peripherals available in the device family.

10.4 Support Resources

TI E2E[™] support forums are an engineer's go-to source for fast, verified answers and design help — straight from the experts. Search existing answers or ask your own question to get the guick design help you need.

Linked content is provided "AS IS" by the respective contributors. They do not constitute TI specifications and do not necessarily reflect TI's views; see TI's Terms of Use.

10.5 Trademarks

SimpleLink[™], LaunchPad[™], EnergyTrace[™], Code Composer Studio[™], TI E2E[™] are trademarks of Texas Instruments.

I-jet[™] is a trademark of IAR Systems AB.

J-Link[™] is a trademark of SEGGER Microcontroller Systeme GmbH.

www.ti.com

Wi-SUN®, mioty®, are registered trademarks of Wi-SUN Alliance Inc.

Arm Thumb® is a registered trademark of Arm Limited (or its subsidiaries).

Eclipse® is a registered trademark of Eclipse Foundation.

IAR Embedded Workbench® is a registered trademark of IAR Systems AB.

Windows® is a registered trademark of Microsoft Corporation.

All trademarks are the property of their respective owners.

10.6 Electrostatic Discharge Caution



This integrated circuit can be damaged by ESD. Texas Instruments recommends that all integrated circuits be handled with appropriate precautions. Failure to observe proper handling and installation procedures can cause damage.

ESD damage can range from subtle performance degradation to complete device failure. Precision integrated circuits may be more susceptible to damage because very small parametric changes could cause the device not to meet its published specifications.

10.7 Glossary

TI Glossary

This glossary lists and explains terms, acronyms, and definitions.



11 Mechanical, Packaging, and Orderable Information

www.ti.com 6-May-2022

PACKAGING INFORMATION

Orderable Device	Status (1)	Package Type	Package Drawing	Pins	Package Qty	Eco Plan	Lead finish/ Ball material	MSL Peak Temp	Op Temp (°C)	Device Marking (4/5)	Samples
CC1312R74T0RGZR	ACTIVE	VQFN	RGZ	48	2500	RoHS & Green	(6) NIPDAU	Level-3-260C-168 HR	-40 to 105	CC1312 R74	Samples

(1) The marketing status values are defined as follows:

ACTIVE: Product device recommended for new designs.

LIFEBUY: TI has announced that the device will be discontinued, and a lifetime-buy period is in effect.

NRND: Not recommended for new designs. Device is in production to support existing customers, but TI does not recommend using this part in a new design.

PREVIEW: Device has been announced but is not in production. Samples may or may not be available.

OBSOLETE: TI has discontinued the production of the device.

(2) RoHS: TI defines "RoHS" to mean semiconductor products that are compliant with the current EU RoHS requirements for all 10 RoHS substances, including the requirement that RoHS substance do not exceed 0.1% by weight in homogeneous materials. Where designed to be soldered at high temperatures, "RoHS" products are suitable for use in specified lead-free processes. TI may reference these types of products as "Pb-Free".

RoHS Exempt: TI defines "RoHS Exempt" to mean products that contain lead but are compliant with EU RoHS pursuant to a specific EU RoHS exemption.

Green: TI defines "Green" to mean the content of Chlorine (CI) and Bromine (Br) based flame retardants meet JS709B low halogen requirements of <=1000ppm threshold. Antimony trioxide based flame retardants must also meet the <=1000ppm threshold requirement.

- (3) MSL, Peak Temp. The Moisture Sensitivity Level rating according to the JEDEC industry standard classifications, and peak solder temperature.
- (4) There may be additional marking, which relates to the logo, the lot trace code information, or the environmental category on the device.
- (5) Multiple Device Markings will be inside parentheses. Only one Device Marking contained in parentheses and separated by a "~" will appear on a device. If a line is indented then it is a continuation of the previous line and the two combined represent the entire Device Marking for that device.
- (6) Lead finish/Ball material Orderable Devices may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead finish/Ball material values may wrap to two lines if the finish value exceeds the maximum column width.

Important Information and Disclaimer: The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.

PACKAGE MATERIALS INFORMATION

www.ti.com 28-Mar-2023


TAPE AND REEL INFORMATION





A0	Dimension designed to accommodate the component width
В0	Dimension designed to accommodate the component length
K0	Dimension designed to accommodate the component thickness
W	Overall width of the carrier tape
P1	Pitch between successive cavity centers

QUADRANT ASSIGNMENTS FOR PIN 1 ORIENTATION IN TAPE



*All dimensions are nominal

	Device	Package Type	Package Drawing		SPQ	Reel Diameter (mm)	Reel Width W1 (mm)	A0 (mm)	B0 (mm)	K0 (mm)	P1 (mm)	W (mm)	Pin1 Quadrant
١	CC1312R74T0RGZR	VQFN	RGZ	48	2500	330.0	16.4	7.3	7.3	1.1	12.0	16.0	Q2

PACKAGE MATERIALS INFORMATION

www.ti.com 28-Mar-2023



*All dimensions are nominal

Ì	Device Package Type		Package Drawing	Pins	SPQ	Length (mm)	Width (mm)	Height (mm)	
ı	CC1312R74T0RGZR	VQFN	RGZ	48	2500	367.0	367.0	35.0	

7 x 7, 0.5 mm pitch

PLASTIC QUADFLAT PACK- NO LEAD



Images above are just a representation of the package family, actual package may vary. Refer to the product data sheet for package details.

4224671/A



PLASTIC QUADFLAT PACK- NO LEAD



NOTES:

- 1. All linear dimensions are in millimeters. Any dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.
- 2. This drawing is subject to change without notice.
- 3. The package thermal pad must be soldered to the printed circuit board for optimal thermal and mechanical performance.



PLASTIC QUADFLAT PACK- NO LEAD



NOTES: (continued)

- 4. This package is designed to be soldered to a thermal pad on the board. For more information, see Texas Instruments literature number SLUA271 (www.ti.com/lit/slua271).
- 5. Vias are optional depending on application, refer to device data sheet. If any vias are implemented, refer to their locations shown on this view. It is recommended that vias under paste be filled, plugged or tented.



PLASTIC QUADFLAT PACK- NO LEAD



NOTES: (continued)

6. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.



IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATA SHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, regulatory or other requirements.

These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you will fully indemnify TI and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to TI's Terms of Sale or other applicable terms available either on ti.com or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products.

TI objects to and rejects any additional or different terms you may have proposed.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265 Copyright © 2023, Texas Instruments Incorporated