







LSF0102-Q1 SDLS969B - MAY 2018 - REVISED MAY 2023

# LSF0102-Q1 Automotive 2-Channel Auto Bidirectional Multi-Voltage Level Translator

#### 1 Features

- AEC-Q100 qualified for automotive applications
  - Temperature grade 1: –40°C ≤ T<sub>A</sub> ≤ 125°C
  - Device HBM ESD Classification Level 2
  - CDM ESD Classification Level C6
- Provides bidirectional voltage translation with no direction Pin
- Supports open drain and push-pull applications such as I<sup>2</sup>C, SPI, UART, MDIO, SDIO, and GPIO
- Supports up to 100 MHz up translation and greater than 100 MHz down translation at ≤ 30pF cap load and up to 40 MHz up or down translation at 50 pF cap load
- Enables bidirectional voltage level translation between
  - 0.95 V  $\leftrightarrow$  1.8/2.5/3.3/5 V
  - 1.2 V ↔ 1.8/2.5/3.3/5 V
  - $1.8 \text{ V} \leftrightarrow 2.5/3.3/5 \text{ V}$
  - 2.5 V  $\leftrightarrow$  3.3/5 V
  - 3.3 V ↔ 5 V
- Low standby current
- 5 V tolerant I/O ports to support TTL voltage levels
- Low r<sub>on</sub> provides less signal distortion
- High-impedance I/O pins when EN = low
- Flow-through pinout for ease of PCB trace routing
- Latch-up performance exceeds 100 mA per JESD 78, Class II

# 2 Applications

- Infotainment head unit
- **Graphical cluster**
- **ADAS** fusion
- ADAS front camera
- HEV battery management system

# 3 Description


The LSF0102-Q1 device is an auto bidirectional voltage translator that translates among a wide range of supplies without the need for a directional pin. The LSF0102-Q1 supports up to 100 MHz up translation and greater than 100 MHz down translation with capacitive loads ≤ 30 pF. Additionally, the LSF0102-Q1 supports up to 40 MHz up and down translation at 50 pF capacitance load, which enables the LSF0102-Q1 device to support a wide variety of standard interfaces commonly found in automotive applications such as I<sup>2</sup>C, SPI, GPIO, SDIO, UART, and MDIO.

The LSF0102-Q1 device has 5-V tolerant data inputs. This makes the device compatible with TTL voltage levels. Furthermore, the LSF0102-Q1 supports mixedmode voltage translation, allowing the device to up translate and down translate to different supply levels on each channel.

### Package Information<sup>(1)</sup>

PART NUMBER	PACKAGE	BODY SIZE (NOM)				
LSF0102-Q1	DCU (VSSOP, 8)	2.30 mm × 2.00 mm				

For all available packages, see the orderable addendum at the end of the data sheet.



**Functional Block Diagram** 



# **Table of Contents**

1 Features1	7 Parameter Measurement Information	8
2 Applications1	8 Detailed Description	<b>ç</b>
3 Description1	8.1 Overview	
4 Revision History2	8.2 Functional Block Diagram	<b>ç</b>
5 Pin Configuration and Functions3	8.3 Feature Description	9
6 Specifications4	9 Application and Implementation	
6.1 Absolute Maximum Ratings4	9.1 Application Information	12
6.2 ESD Ratings4	9.2 Typical Application	
6.3 Recommended Operating Conditions4	9.3 Power Supply Recommendations	
6.4 Thermal Information4	9.4 Layout	18
6.5 Electrical Characteristics5	10 Device and Documentation Support	
6.6 Switching Characteristics (Translating Down):	10.1 Documentation Support	19
V <sub>CCB</sub> = 3.3 V6	10.2 Receiving Notification of Documentation Updates	
6.7 Switching Characteristics (Translating Down):	10.3 Support Resources	. 19
V <sub>CCB</sub> = 2.5 V6	10.4 Trademarks	. 19
6.8 Switching Characteristics Translating Up): V <sub>CCB</sub>	10.5 Electrostatic Discharge Caution	.19
= 3.3 V6	10.6 Glossary	.19
6.9 Switching Characteristics (Translating Up): V <sub>CCB</sub>	11 Mechanical, Packaging, and Orderable	
= 2.5 V6	Information	. 19
6.10 Typical Characteristics7		

# **4 Revision History**

NOTE: Page numbers for previous revisions may differ from page numbers in the current version.

C	nanges from Revision A (April 2021) to Revision B (May 2023)	Page
•	Updated the Recommended Operating Conditions table to reflect maximum of 5.5 V	4
•	Updated the Thermal Information table	4
•	Changed all Switching Characteristic Test Conditions	6
•	Added the Output Enable section	9
•	Added the Up and Down Translation sections	
•	Changed pull up resistor to bias resistor in Enable, Disable, and Reference Voltage Guidelines section	
•	Added the Bias Circuitry section	13
•	Updated the current values in the table titled Pull-up Resistor Values	13
•	Added image to the Mixed-Mode Voltage Translation section	14
•	Added the Single Supply Translation section	
•	Added section Voltage Translation for Vref_B < Vref_A + 0.8 V	
С	hanges from Revision * (May 2018) to Revision A (April 2021)	Page
•	Updated the numbering format for tables, figures, and cross-references throughout the document	1
•	Updated the Bidirectional Translation section to include inclusive terminology	13



# **5 Pin Configuration and Functions**




Figure 5-1. LSF0102-Q1 DCU Package, 8-Pin VSSOP (Top View)

**Table 5-1. Pin Functions** 

P	'IN	TYPE(1)	DESCRIPTION					
NAME	NO.	I TPE(''	DESCRIPTION					
A1	3	I/O	Input/Output A port for Channel 1					
A2	4	I/O	Input/Output A port for Channel 2					
B1	6	I/O	Input/Output B port for Channel 1					
B2	5	I/O	Input/Output B port for Channel 2					
EN	8	I	I/O enable input; see Figure 9-1 for typical setup. Should be tied directly to $V_{ref\_B}$ to be enabled or pulled LOW to disable all I/O pins.					
GND	1	_	Ground					
Vref_A	2	_	A side reference supply voltage; see Section 9 for setup and supply voltage range.					
Vref_B 7 -		_	B side reference supply voltage. Must be connected to supply through 200 k $\Omega$ ; see Section 9 for setup and supply voltage range.					

<sup>(1)</sup> I = input, O = output



# **6 Specifications**

# **6.1 Absolute Maximum Ratings**

over operating free-air temperature (unless otherwise noted)(1)

		MIN	MAX	UNIT
Input voltage <sup>(2)</sup> , V <sub>I</sub>		-0.5	7	V
Input/output voltage <sup>(2)</sup> , V <sub>I/O</sub>		-0.5	7	V
Continuous channel current			128	mA
Input clamp current, I <sub>IK</sub>	V <sub>I</sub> < 0		-50	mA
Storage temperature range, T <sub>stg</sub>		-65	150	°C
Operating junction temperature, T <sub>J</sub>			150	°C

<sup>(1)</sup> Stresses beyond those listed under Absolute Maximum Ratings may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated under Recommended Operating Conditions is not implied. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability.

# 6.2 ESD Ratings

			VALUE	UNIT
V	Electrostatic discharge	Human-body model (HBM), per AEC Q100-002 <sup>(1)</sup>	±2000	V
V <sub>(ESD)</sub>	Electrostatic discharge	Charged-device model (CDM), per AEC Q100-011	±1000	V

<sup>(1)</sup> AEC Q100-002 indicates that HBM stressing shall be in accordance with the ANSI/ESDA/JEDEC JS-001 specification.

# **6.3 Recommended Operating Conditions**

over operating free-air temperature range (unless otherwise noted)

		MIN	MAX	UNIT
V <sub>I/O</sub>	Input/output voltage		5.5	V
V <sub>ref_A/B/EN</sub>	Reference voltage		5.5	V
I <sub>PASS</sub>	Pass transistor current		64	mA
T <sub>A</sub>	Operating free-air temperature	-40	125	°C

#### 6.4 Thermal Information

		LSF0102-Q1	
	THERMAL METRIC <sup>(1)</sup>	DCU (US8)	UNIT
		8 PINS	
R <sub>θJA</sub>	Junction-to-ambient thermal resistance	279.7	°C/W
R <sub>0</sub> JC(top)	Junction-to-case (top) thermal resistance	129.9	°C/W
$R_{\theta JB}$	Junction-to-board thermal resistance	191.3	°C/W
Ψлт	Junction-to-top characterization parameter	66.3	°C/W
ΨЈВ	Junction-to-board characterization parameter	190.1	°C/W

(1) For more information about traditional and new thermal metrics, see the IC Package Thermal Metrics application report.

Submit Document Feedback

<sup>(2)</sup> The input and input/output negative-voltage ratings may be exceeded if the input and input/output clamp-current ratings are observed.



# **6.5 Electrical Characteristics**

over recommended operating free-air temperature range (unless otherwise noted)

PA	RAMETER	TE	MIN	TYP <sup>(1)</sup>	MAX	UNIT		
V <sub>IK</sub>	Input clamp voltage	$I_I = -18 \text{ mA}, V_{EN} = 0$				-1.2	V	
I <sub>IH</sub>	I/O input high leakage	V <sub>I</sub> = 5 V, V <sub>EN</sub> = 0	$V_{\rm I} = 5 \text{ V}, \text{ V}_{\rm EN} = 0$					
I <sub>CCBA</sub>	V <sub>ref_B</sub> to V <sub>ref_A</sub> leakage	V <sub>ref_B</sub> = V <sub>EN</sub> = 5.5 V, V <sub>ref_</sub>	A = 4.5 V, I <sub>O</sub> = 0, V <sub>I</sub> = V <sub>CC</sub> or GND		1		μΑ	
C <sub>I(ref_A/B/EN)</sub>	Input capacitance	V <sub>I</sub> = 3 V or 0			11		pF	
C <sub>io(off)</sub>	I/O pin off-state capacitance	V <sub>O</sub> = 3 V or 0, V <sub>EN</sub> = 0		4.0	6.0	pF		
C <sub>io(on)</sub>	I/O Pin on-state capacitance	V <sub>O</sub> = 3 V or 0, V <sub>EN</sub> = 3 V			10.5	12.5	pF	
		V <sub>I</sub> = 0, I <sub>O</sub> = 64 mA	$V_{ref\_A} = 3.3 \text{ V}; V_{ref\_B} = V_{EN} = 5 \text{ V}$		8.0			
			$V_{ref\_A} = 1.8 \text{ V}; V_{ref\_B} = V_{EN} = 5 \text{ V}$		9.0		Ω	
			$V_{ref\_A} = 1.0 \text{ V}; V_{ref\_B} = V_{EN} = 5 \text{ V}$		10			
		V = 0 1 = 22 mA	V <sub>ref_A</sub> = 1.8 V; V <sub>ref_B</sub> = V <sub>EN</sub> = 5 V		10		0	
r <sub>on</sub> (2)	On-state resistance	$V_1 = 0$ , $I_0 = 32 \text{ mA}$	$V_{ref\_A} = 2.5 \text{ V}; V_{ref\_B} = V_{EN} = 5 \text{ V}$	1:			Ω	
		V <sub>I</sub> = 1.8 V, I <sub>O</sub> = 15 mA	$V_{ref\_A} = 3.3 \text{ V}; V_{ref\_B} = V_{EN} = 5 \text{ V}$		9.0		Ω	
		V <sub>I</sub> = 1.0 V, I <sub>O</sub> = 10 mA	$V_{ref\_A} = 1.8 \text{ V}; V_{ref\_B} = V_{EN} = 3.3 \text{ V}$		18		Ω	
		V <sub>I</sub> = 0 V, I <sub>O</sub> = 10 mA	$V_{ref\_A} = 1.0 \text{ V}; V_{ref\_B} = V_{EN} = 3.3 \text{ V}$		20		Ω	
		V <sub>I</sub> = 0 V, I <sub>O</sub> = 10 mA	V <sub>ref_A</sub> = 1.0 V; V <sub>ref_B</sub> = V <sub>EN</sub> = 1.8 V		30		Ω	

<sup>(1)</sup> All typical values are at  $T_A = 25$ °C.

<sup>(2)</sup> Measured by the voltage drop between the A and B pins at the indicated current through the switch. On-state resistance is determined by the lowest voltage of the two (A or B) pins.



# 6.6 Switching Characteristics (Translating Down): V<sub>CCB</sub> = 3.3 V

over recommended operating free-air temperature range,  $V_{CCB} = 3.3 \text{ V}$ ,  $V_{CCB} = V_{IH} = V_{ref\_A} + 1$ ,  $V_{IL} = 0$ , and  $V_{M} = 0.5 V_{ref\_A}$  (unless otherwise noted) (see *Parameter Measurement Information*)

PARAMETER	TEST CONDITIONS	C <sub>L</sub> = 50 pF		C <sub>L</sub> = 30 pF			C <sub>L</sub> = 15 pF			UNIT		
PARAMETER	TEST CONDITIONS	MIN	TYP	MAX	MIN	TYP	MAX	MIN	TYP	MAX		
Propagation delay t <sub>PLH</sub> time, low-to-high output	From (input) A or B to (output) B or A		1.1			0.7			0.3		ns	
Propagation delay t <sub>PHL</sub> time, high-to-low output	From (input) A or B to (output) B or A		1.2			0.8			0.4		115	

# 6.7 Switching Characteristics (Translating Down): V<sub>CCB</sub> = 2.5 V

over recommended operating free-air temperature range,  $V_{CCB} = 2.5 \text{ V}$ ,  $V_{CCB} = V_{IH} = V_{ref\_A} + 1$ ,  $V_{IL} = 0$ , and  $V_{M} = 0.5 V_{ref\_A}$  (unless otherwise noted) (see *Parameter Measurement Information*)

	PARAMETER	TEST CONDITIONS	C <sub>L</sub> = 50 pF			C <sub>L</sub> = 30 pF			C <sub>L</sub> = 15 pF			UNIT
	PARAIVIETER	TEST CONDITIONS	MIN	TYP	MAX	MIN	TYP	MAX	MIN	TYP	MAX	UNII
t <sub>PLH</sub>	Propagation delay time, low-to-high output	From (input) A or B to (output) B or A		1.2			0.8			0.35		no
t <sub>PHL</sub>	Propagation delay time, high-to-low output	From (input) A or B to (output) B or A		1.3			1			0.5		ns

# 6.8 Switching Characteristics Translating Up): V<sub>CCB</sub> = 3.3 V

over recommended operating free-air temperature range,  $V_{CCB} = 3.3 \text{ V}$ ,  $V_{CCB} = V_T = V_{ref\_A} + 1$ ,  $V_{ref\_A} = V_{IH}$ ,  $V_{IL} = 0$ ,  $V_M = 0.5V_{ref\_A}$  and  $R_L = 300$  (unless otherwise noted) (see *Parameter Measurement Information*)

	PARAMETER	TEST CONDITIONS	C <sub>L</sub> = 50 pF		C <sub>L</sub> = 30 pF			C <sub>L</sub> = 15 pF			UNIT	
	PARAMETER	TEST CONDITIONS	MIN	TYP	MAX	MIN	TYP	MAX	MIN	TYP	MAX	UNIT
t <sub>PLH</sub>	Propagation delay time, low-to-high output	From (input) A or B to (output) B or A		1			0.8			0.4		ns
t <sub>PHL</sub>	Propagation delay time, high-to-low output	From (input) A or B to (output) B or A		1			0.9			0.4		115


# 6.9 Switching Characteristics (Translating Up): $V_{CCB} = 2.5 \text{ V}$

over recommended operating free-air temperature range,  $V_{CCB} = 2.5 \text{ V}$ ,  $V_{CCB} = V_T = V_{ref\_A} + 1$ ,  $V_{ref\_A} = V_{IH}$ ,  $V_{IL} = 0$ ,  $V_M = 0.5 V_{ref\_A}$  and  $R_L = 300$  (unless otherwise noted) (see *Parameter Measurement Information*)

	PARAMETER	TER TEST CONDITIONS C <sub>L</sub> = 50 pF		C <sub>L</sub> :	= 30 pF		C <sub>L</sub> = 15 pF			UNIT		
	FARAMETER	1E31 CONDITIONS	MIN	TYP	MAX	MIN	TYP	MAX	MIN	TYP	MAX	
t <sub>PLH</sub>	Propagation delay time, low-to-high output	From (input) A or B to (output) B or A		1.1			0.9			0.45		no
t <sub>PHL</sub>	Propagation delay time, high-to-low output	From (input) A or B to (output) B or A		1.3			1.1			0.6		ns

Submit Document Feedback

# **6.10 Typical Characteristics**






## 7 Parameter Measurement Information

The outputs are measured one at a time, with one transition per measurement. All input pulses are supplied by generators that have the following characteristics:

- PRR ≤ 10 MHz
- $Z_{\rm O} = 50 \, \Omega$
- t<sub>r</sub> ≤ 2 ns
- t<sub>f</sub> ≤ 2 ns



A. C<sub>L</sub> includes probe and jig capacitance.

Figure 7-1. Load Circuit

USAGE	SWITCH
Translating Up	S1
Translating Down	S2

Figure 7-2. Translating Up and Down Table




Figure 7-3. Translating Up




Figure 7-4. Translating Down




# 8 Detailed Description

### 8.1 Overview

The LSF0102-Q1 device can be used in level translation applications for interfacing devices or systems operating at different interface voltages. The LSF0102-Q1 device is ideal for use in applications where an open-drain driver is connected to the data I/Os. With appropriate pull-up resistors and layout, the LSF0102-Q1 device can achieve 100 MHz. The LSF0102-Q1 can also be used in applications where a push-pull driver is connected to the data I/Os.

## 8.2 Functional Block Diagram



# 8.3 Feature Description

# 8.3.1 Auto Bidirectional Voltage Translation

The LSF0102-Q1 device is an auto bidirectional voltage level translator that operates from 0.95 to 5.5 V on  $V_{ref\_A}$  and 1.8 to 5.5 V on  $V_{ref\_B}$ . This allows bidirectional voltage translation between 0.95 V and 5.5 V without the need for a direction pin in open-drain or push-pull applications. The LSF0102-Q1 device supports level translation applications with transmission speeds greater than 100 Mbps for open-drain systems using a 250- $\Omega$  pull-up resistor with a 30-pF capacitive load.

### 8.3.2 Output Enable

To enable the I/O pins, the EN input should be tied directly to  $V_{ref\_B}$  during operation and both pins must be pulled up to the HIGH side ( $V_{CCB}$ ) through a bias resistor (typically 200 k $\Omega$ ). To ensure the high impedance state during power-up, power-down, or during operation, the EN pin must be LOW. The EN pin should always be tied directly to the  $V_{ref\_B}$  pin and is recommended to be disabled by an open-drain driver without a pullup resistor. This allows  $V_{ref\_B}$  to regulate the EN input and bias the channels for proper translation. A filter capacitor on  $V_{ref\_B}$  is recommended for a stable supply at the device.






Figure 8-1. EN Pin Tied to V<sub>ref B</sub> Directly and to V<sub>CCB</sub> Through a Pull-Up Resistor

The supply voltage of open drain I/O devices can be completely different from the supplies used for the LSF and has no impact on the operation. For additional details on how to use the enable pin, see the *Using the Enable Pin with the LSF Family video*.

**Table 8-1. EN Pin Function Table** 

INPUT EN <sup>(1)</sup> PIN	Data Port State
Tied directly to V <sub>ref_B</sub>	An = Bn
L	Hi-Z

EN is controlled by V<sub>ref B</sub> logic levels.

## 8.3.3 Device Functional Modes

For each channel (n), when either the An or Bn port is LOW, the switch provides a low impedance path between the An and Bn ports; the corresponding Bn or An port will be pulled LOW. The low R<sub>ON</sub> of the switch allows connections to be made with minimal propagation delay and signal distortion.

Table 8-1 provides a summary of device operation. For additional details on the functional operation of the LSF family of devices, see the *Down Translation with the LSF Family* and *Up Translation with the LSF Family* videos.

**Table 8-2. Device Functionality** 

Signal Direction <sup>(1)</sup>	Input State	Switch State	Functionality
B to A (Down Translation)	B = LOW	ON (Low Impedance)	A-side voltage is pulled low through the switch to the B-side voltage
B to A (Down Translation)	B = HIGH	OFF (High Impedance)	A-side voltage is clamped at V <sub>ref_A</sub> <sup>(2)</sup>
A to D (I in Translation)	A = LOW	ON (Low Impedance)	B-side voltage is pulled low through the switch to the A-side voltage
A to B (Up Translation)	A = HIGH	OFF (High Impedance)	B-side voltage is clamped at $V_{\text{ref\_A}}$ and then pulled up to the $V_{\text{PU}}$ supply voltage

- The downstream channel should not be actively driven through a low impedance driver, or else bus contention may occur.
- (2) The A-side can have a pullup to V<sub>ref\_A</sub> for additional current drive capability or may also be pulled above V<sub>ref\_A</sub> with a pullup resistor. Specifications in the *Recommended Operating Conditions* section should always be followed.

Submit Document Feedback



### 8.3.3.1 Up and Down Translation

### 8.3.3.1.1 Up Translation

When the signal is being driven from A to B and the An port is HIGH, the switch will be OFF and the Bn port will then be driven to a voltage higher than  $V_{ref\_A}$  by the pull-up resistor that is connected to the pull-up supply voltage ( $V_{PU}$ ). This functionality allows seamless translation between higher and lower voltages selected by the user, without the need for directional control. Pull-up resistors are always required on the high side, and pull-ups are only required on the low side, if the low side of the device's output is open drain or its input has a leakage greater than 1  $\mu$ A.




Figure 8-2. Up Translation Example Schematic with Push-Pull and Open Drain Configuration

Up translation with the LSF requires attention to two important factors: maximum data rate and sink current. Maximum data rate is directly related to the rising edge of the output signal. Sink current depends on supply values and the chosen pull-up resistor values. Equation 1 shows the maximum data rate formula and Equation 2 shows the maximum sink current formula, both of which are estimations. A low RC value is needed to reach high speeds, which also require strong drivers. Please see the *Up Translation with the LSF Family* video for estimated data rate and sink current calculations based on circuit components.

$$\frac{1}{3 \times 2R_{B1}C_{B1}} = \frac{1}{6R_{B1}C_{B1}} \left( \frac{bits}{second} \right) \tag{1}$$

$$I_{OL} \cong \frac{V_{CCA}}{R_{A1}} + \frac{V_{CCB}}{R_{B1}} \left( A \right) \tag{2}$$

#### 8.3.3.1.2 Down Translation

When the signal is being driven HIGH from the Bn port to An port, the switch will be OFF, clamping the voltage on the An port to the voltage set by  $V_{ref\_A}$ . A pull-up resistor can be added on either side of the device. There are special circumstances that allow the removal of one or both of the pull-up resistors. If the signal is always going to be down translated from a push-pull transmitter, then the resistor on the B-side can be removed. If the leakage current into the receiver on the A-side is less than 1  $\mu$ A, then the resistor on the A-side can also be removed. This arrangement with no external pull-up resistors can be used when down translating from a push-pull output to a low-leakage input. For an open drain transmitter, the pull-up resistor on the B-side is necessary because an open drain output can't drive high by itself. For a summary of device operation, refer to Section 8.3.3. For additional details on the functional operation of the LSF family of devices, see the *Up Translation with the LSF Family* videos.



# 9 Application and Implementation

#### Note

Information in the following applications sections is not part of the TI component specification, and TI does not warrant its accuracy or completeness. TI's customers are responsible for determining suitability of components for their purposes, as well as validating and testing their design implementation to confirm system functionality.

# 9.1 Application Information

The LSF0102-Q1 device is able to perform voltage translation for open-drain or push-pull interfaces such as I<sup>2</sup>C, SPI, UART, MDIO, SDIO, and GPIO.

### 9.2 Typical Application

#### 9.2.1 Bidirectional Translation




Figure 9-1. Bidirectional Translation to Multiple Voltage Levels

### 9.2.1.1 Design Requirements

#### 9.2.1.1.1 Enable, Disable, and Reference Voltage Guidelines

The LSF0102-Q1 device has an EN input that is used to disable the device by setting EN LOW, which places all I/Os in the high-impedance state. Since LSF family is switch-type voltage translator, the power consumption is very low. It is recommended to always enable LSF0102-Q1 device for bidirectional applications by connecting the EN pin to the  $V_{ref\_B}$  pin, as shown in Figure 9-1. For additional details on setting up the  $V_{ref\_B}$ ,  $V_{ref\_B}$ , and EN pins, see the *Understanding the Bias Circuit for the LSF Family* video.

Table 9-1. Application Op	perating Condition
ETED	MINI

	PARAMETER	MIN	TYP	MAX	UNIT
V <sub>ref_A</sub> (1)	reference voltage (A)	0.95		5.5	V
V <sub>ref_B</sub>	reference voltage (B)	V <sub>ref_A</sub> + 0.8		5.5	V
V <sub>I(EN)</sub>	input voltage on EN pin	V <sub>ref_A</sub> + 0.8	V <sub>ref_B</sub>	5.5	V
V <sub>PU</sub>	pull-up supply voltage	0		V <sub>ref_B</sub>	V

(1)  $V_{ref\ A}$  is required to be the lowest voltage level across all inputs and outputs.

The 200 k $\Omega$ , bias resistor is required to allow  $V_{ref\_B}$  to regulate the EN input. A filter capacitor on  $V_{ref\_B}$  is recommended. Also  $V_{ref\_B}$  and  $V_{I(EN)}$  are recommended to be 1.0 V higher than  $V_{ref\_A}$  for best signal integrity.

#### 9.2.1.1.2 Bias Circuitry

For proper operation,  $V_{CCA}$  must always be at least 0.8 V less than  $V_{CCB}$  ( $V_{CCA}$  + 0.8  $\leq$   $V_{CCB}$ ). The 200 k $\Omega$  bias resistor is required to allow  $V_{ref\_B}$  to regulate the EN input and properly bias the device for translation. A 0.1  $\mu$ F capacitor is recommended for providing a path from  $V_{ref\_B}$  to ground for high frequency noise.  $V_{ref\_B}$  and  $V_{I(EN)}$  are recommended to be 1.0 V higher than  $V_{ref\_A}$  for best signal integrity.

Attempting to drive the EN pin directly with a push-pull output device is a very common design error with the LSF0102-Q1 series of devices. It is also very important to note that current does flow into the A-side voltage supply during normal operation. Not all voltage sources can sink current, so be sure that applicable designs can handle this current. For more design details, see the *Understanding the Bias Circuit for the LSF Family* video.




Figure 9-2. Bias Circuitry Inside the LSF010x-Q1 Device

#### 9.2.1.2 Detailed Design Procedure

#### 9.2.1.2.1 Bidirectional Translation

For the bidirectional clamping configuration (higher voltage to lower voltage or lower voltage to higher voltage), the EN input must be connected to  $V_{ref\_B}$  and both pins pulled to HIGH side  $V_{CCB}$  through a bias resistor (typically 200 k $\Omega$ ), as shown in Figure 9-1. This allows  $V_{ref\_B}$  to regulate the EN input. A filter capacitor on  $V_{ref\_B}$  is recommended. The controller output driver can be push-pull or open-drain (pull-up resistors may be required) and the peripheral device output can be push-pull or open-drain (pull-up resistors are required to pull the Bn outputs to Vpu).

If either output is push-pull, data must be unidirectional or the outputs must be tri-state and be controlled by some direction-control mechanism to prevent HIGH-to-LOW contention in either direction. If both outputs are open-drain, no direction control is needed.

In Figure 9-1, the reference supply voltage  $V_{ref\_A}$  is connected to the processor core power supply voltage.  $V_{ref\_B}$  is connected through a 200 k $\Omega$  resistor to a 3.3 V  $V_{B\_Pullup}$  power supply and  $V_{ref\_A}$  is set to 1.2 V. The output of A1 has a maximum output voltage equal to  $V_{ref\_A}$ , and the bidirectional interface on channel 2 has a maximum output voltage equal to  $V_{PU1}$ .

### 9.2.1.2.2 Pull-Up Resistor Sizing

To maintain an appropriate output low voltage, the pull-up resistor value should limit the current through the pass transistor when it is in the ON state to less than 15 mA. This ensures a pass voltage of 260 mV to 350 mV. To set the current through each pass transistor at 15 mA, the pull-up resistor value can be calculated using the following equation:

$$R_{pu} = \frac{\left(V_{pu} - 0.35\,V\right)}{0.015\,A}\tag{3}$$



The appropriate pull up resistor will depend on the current requirements of the application. Table 9-2 provides resistor values, reference voltages, and currents at 15 mA, 10 mA, and 3 mA. The resistor value shown in the +10% column (or a larger value) should be used to ensure that the pass voltage of the transistor is 350 mV or less. The external driver must be able to sink the total current from the resistors on both sides of the LSF0102-Q1 device at 0.175 V, although the 15 mA applies only to current flowing through the LSF0102-Q1.

V <sub>PU</sub>	8 n	nA	5 r	m <b>A</b>	3 r	nA
▼PU	NOMINAL (Ω)	+10% <sup>(1)</sup> (Ω)	NOMINAL (Ω)	+10% <sup>(1)</sup> (Ω)	NOMINAL (Ω)	+10% <sup>(1)</sup> (Ω)
5 V	581	639	639 930		1550	1705
3.3 V	369	406	590	649	983	1082
2.5 V	269	296	430	473	717	788
1.8 V	181	199	290	319	483	532
1.5 V	144	158	230	253	383	422
1.2 V	106	117	170	187	283	312

Table 9-2. Pull-up Resistor Values

#### 9.2.1.2.3 Application Curve




Figure 9-3. Captured Waveform From Above I<sup>2</sup>C Set-Up (1.8 V to 3.3 V at 2.5 MHz)

#### 9.2.1.2.4 Mixed-Mode Voltage Translation

The supply voltage (V<sub>PU</sub>) for each channel can be individually set with a pull-up resistor. Figure 9-4 shows an example of this mixed-mode multi-voltage translation. For additional details on multi-voltage translation, see the *Multi-voltage Translation with the LSF Family* video.

With the  $V_{ref\_B}$  pulled up to 5 V and  $V_{ref\_A}$  connected to 1.8 V, all channels will be clamped to 1.8 V at which point a pullup can be used to define the high level voltage for a given channel.

- Push-Pull Down Translation (5 V to 1.8 V): Channel 1 is an example of this setup. When B1 is 5 V, A1 is clamped to 1.8 V, and when B1 is LOW, A1 is driven LOW through the switch.
- Push-Pull Up Translation (1.8 V to 5 V): Channel 2 is an example of this setup. When A2 is 1.8 V, the switch is high impedance and the B2 channel is pulled up to 5 V. When A2 is LOW, B2 is driven LOW through the switch.
- Push-Pull Down Translation (3.3 V to 1.8 V): Channels 3 and 4 are examples of this setup. When either B3 or B4 are driven to 3.3 V, A3 or A4 are clamped to 1.8 V, and when either B3 or B4 are LOW, A3 or A4 are driven LOW through the switch.
- Open-Drain Bidirectional Translation (3.3 V ↔ 1.8 V): Channels 5 through 8 are examples of this setup. These channels are for bidirectional operation for I<sup>2</sup>C and MDIO to translate between 1.8 V and 3.3 V with open-drain drivers.

Submit Document Feedback

<sup>(1) +10%</sup> to compensate for V<sub>DD</sub> range and resistor tolerance




Figure 9-4. Multi-Voltage Translation with the LSF010x-Q1

## 9.2.1.2.5 Single Supply Translation

Sometimes, an external device will have an unknown voltage that could be above or below the desired translation voltage, preventing a normal connection of the LSF. Resistors are added on the A side in place of the second supply in this case – this is an example of when LSF single supply operation is utilized, shown in Figure 9-5. In the following figure, a single 3.3 V supply is used to translate between a 3.3 V device and a device that can change between 1.8 V and 5.0 V. R1 and R2 are added in place of the second supply. Note that due to some current coming out of the  $V_{ref}$  A pin, this cannot be treated as a simple voltage divider.






Figure 9-5. Single Supply Translation with 3.3 V Supply

The steps to select the resistor values for R1 and R2 are as follows:

- 1. Select a value for R1. Typically, 1  $M\Omega$  is used to reduce current consumption.
- 2. Plug in values for your system into the following equation. Note that V<sub>ref\_A</sub> is the lowest voltage in the system. V<sub>CCB</sub> is the primary supply and R1 is the selected value from step 1.

$$R_2 = \frac{200(10^3) \times R_1 \times V_{REFA}}{(200(10^3) + R_1)(V_{CCB} - V_{REFA}) - 0.85 \times R_1}$$
(4)

The single supply used must be at least 0.8 V larger than the lowest desired translation voltage. The voltage at  $V_{ref\_A}$  must be selected as the lowest voltage to be used in the system. The LSF evaluation module (LSF-EVM) contains unpopulated pads to place R1 and R2 for single supply operation testing. For an example single supply translation schematic and details, see the *Single Supply Translation with the LSF Family* video.

### 9.2.1.2.6 Voltage Translation for $V_{ref\ B} < V_{ref\ A} + 0.8\ V$

As described in the *Enable, Disable, and Reference Voltage Guidelines* section, it is generally recommended that  $V_{ref\_B} > V_{ref\_A} + 0.8 \text{ V}$ ; however, the device can still operate in the condition where  $V_{ref\_B} < V_{ref\_A} + 0.8 \text{ V}$  as long as additional considerations are made for the design.

**Typical Operation (V**<sub>ref\_B</sub> > V<sub>ref\_A</sub> + 0.8 V): in this scenario, pullup resistors are not required on the A-side for proper down-translation as is shown for channels 1 and 2 of Figure 9-4. The typical operating mode of the device ensures that when down translating from B to A, the A-side I/O ports will clamp at  $V_{ref_A}$  to provide proper voltage translation. For further explanation of device operation, see the *Down Translation with the LSF Family* video.

**Requirements for V**<sub>ref\_B</sub> < **V**<sub>ref\_A</sub> + **0.8 V Operation:** in this scenario, there is not a large enough voltage difference between V<sub>ref\_A</sub> and V<sub>ref\_B</sub> to ensure that the A side I/O ports will be clamped at V<sub>ref\_A</sub>, but rather at a voltage approximately equal to V<sub>ref\_B</sub> - 0.8 V. For example, if V<sub>ref\_B</sub> = 1.8 V and V<sub>ref\_A</sub> = 1.2  $\overline{V}$ , the A-side I/Os will clamp to a voltage around 1.0  $\overline{V}$ . Therefore, to operate in such a condition, the following additional design considerations must be met:

- $V_{ref B}$  must be greater than  $V_{Ref A}$  during operation ( $V_{ref B} > V_{ref A}$ )
- Pullup resistors should be populated on A-side I/O ports to ensure the line will be fully pulled up to the desired voltage.

Figure 9-6 shows an example of this setup, where 1.2 V  $\leftrightarrow$  1.8 V translation is achieved with the LSF0102-Q1. This type of setup also applies for other voltage nodes such as 1.8 V  $\leftrightarrow$  2.5 V, 1.05 V  $\leftrightarrow$  1.5 V, and others as long as the *Recommended Operating Conditions* table is followed.




Figure 9-6. 1.2 V to 1.8 V Level Translation with LSF010x

### 9.3 Power Supply Recommendations

There are no power sequence requirements for the LSF family. Table 9-3 provides the recommended operating voltages for all supply and input pins.

**Table 9-3. Recommended Operating Voltages** 

	PARAMETER	MIN	TYP MAX	UNIT
V <sub>ref_A</sub> (1)	reference voltage (A)	0.95	5.5	V
V <sub>ref_B</sub>	reference voltage (B)	V <sub>ref_A</sub> + 0.8	5.5	V
V <sub>I(EN)</sub>	input voltage on EN pin	V <sub>ref_A</sub> + 0.8	5.5	V
V <sub>PU</sub>	pull-up supply voltage	0	$V_{ref\_B}$	V



# 9.4 Layout

# 9.4.1 Layout Guidelines

Because the LSF0102-Q1 device is a switch-type level translator, the signal integrity is dependent upon the pull-up resistor value and PCB board parasitics. Consider the following recommendations when designing with the LSF0102-Q1.

- Minimize the signal trace length to reduce capacitance
- · Avoid using stubs in the signal path to reduce parasitics.
- Place the LSF0102-Q1 device near the high voltage side.
- · Select the appropriate pull-up resistor that applies to translation levels and driving capability of transmitter.

### 9.4.2 Layout Example




Figure 9-7. Short Trace Layout



Figure 9-8. Device Placement

Submit Document Feedback



# 10 Device and Documentation Support

# **10.1 Documentation Support**

#### 10.1.1 Related Documentation

For related documentation see the following:

- Texas Instruments, TI Logic Minute: Introduction Voltage Level Translation with the LSF Family video
- Texas Instruments, Voltage-Level Translation with the LSF Family application report

## 10.2 Receiving Notification of Documentation Updates

To receive notification of documentation updates, navigate to the device product folder on ti.com. Click on *Subscribe to updates* to register and receive a weekly digest of any product information that has changed. For change details, review the revision history included in any revised document.

# 10.3 Support Resources

TI E2E<sup>™</sup> support forums are an engineer's go-to source for fast, verified answers and design help — straight from the experts. Search existing answers or ask your own question to get the quick design help you need.

Linked content is provided "AS IS" by the respective contributors. They do not constitute TI specifications and do not necessarily reflect TI's views; see TI's Terms of Use.

#### 10.4 Trademarks

TI E2E<sup>™</sup> is a trademark of Texas Instruments.

All trademarks are the property of their respective owners.

# 10.5 Electrostatic Discharge Caution



This integrated circuit can be damaged by ESD. Texas Instruments recommends that all integrated circuits be handled with appropriate precautions. Failure to observe proper handling and installation procedures can cause damage.

ESD damage can range from subtle performance degradation to complete device failure. Precision integrated circuits may be more susceptible to damage because very small parametric changes could cause the device not to meet its published specifications.

## 10.6 Glossary

TI Glossary

This glossary lists and explains terms, acronyms, and definitions.

## 11 Mechanical, Packaging, and Orderable Information

The following pages include mechanical, packaging, and orderable information. This information is the most current data available for the designated devices. This data is subject to change without notice and revision of this document. For browser-based versions of this data sheet, refer to the left-hand navigation.



www.ti.com 28-Feb-2023

#### PACKAGING INFORMATION

Orderable Device	Status	Package Type	Package Drawing	Pins	Package Qty	Eco Plan	Lead finish/ Ball material	MSL Peak Temp	Op Temp (°C)	Device Marking (4/5)	Samples
LSF0102QDCURQ1	ACTIVE	VSSOP	DCU	8	3000	RoHS & Green	NIPDAUAG	Level-2-260C-1 YEAR	-40 to 125	NG2SQ	Samples

(1) The marketing status values are defined as follows:

**ACTIVE:** Product device recommended for new designs.

LIFEBUY: TI has announced that the device will be discontinued, and a lifetime-buy period is in effect.

NRND: Not recommended for new designs. Device is in production to support existing customers, but TI does not recommend using this part in a new design.

PREVIEW: Device has been announced but is not in production. Samples may or may not be available.

**OBSOLETE:** TI has discontinued the production of the device.

(2) RoHS: TI defines "RoHS" to mean semiconductor products that are compliant with the current EU RoHS requirements for all 10 RoHS substances, including the requirement that RoHS substance do not exceed 0.1% by weight in homogeneous materials. Where designed to be soldered at high temperatures, "RoHS" products are suitable for use in specified lead-free processes. TI may reference these types of products as "Pb-Free".

RoHS Exempt: TI defines "RoHS Exempt" to mean products that contain lead but are compliant with EU RoHS pursuant to a specific EU RoHS exemption.

Green: TI defines "Green" to mean the content of Chlorine (CI) and Bromine (Br) based flame retardants meet JS709B low halogen requirements of <=1000ppm threshold. Antimony trioxide based flame retardants must also meet the <=1000ppm threshold requirement.

- (3) MSL, Peak Temp. The Moisture Sensitivity Level rating according to the JEDEC industry standard classifications, and peak solder temperature.
- (4) There may be additional marking, which relates to the logo, the lot trace code information, or the environmental category on the device.
- (5) Multiple Device Markings will be inside parentheses. Only one Device Marking contained in parentheses and separated by a "~" will appear on a device. If a line is indented then it is a continuation of the previous line and the two combined represent the entire Device Marking for that device.
- (6) Lead finish/Ball material Orderable Devices may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead finish/Ball material values may wrap to two lines if the finish value exceeds the maximum column width.

**Important Information and Disclaimer:** The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.

#### OTHER QUALIFIED VERSIONS OF LSF0102-Q1:

# **PACKAGE OPTION ADDENDUM**

www.ti.com 28-Feb-2023

● Catalog : LSF0102

NOTE: Qualified Version Definitions:

• Catalog - TI's standard catalog product

# **PACKAGE MATERIALS INFORMATION**

www.ti.com 10-May-2023

# TAPE AND REEL INFORMATION





A0	Dimension designed to accommodate the component width
В0	Dimension designed to accommodate the component length
K0	Dimension designed to accommodate the component thickness
W	Overall width of the carrier tape
P1	Pitch between successive cavity centers

### QUADRANT ASSIGNMENTS FOR PIN 1 ORIENTATION IN TAPE



#### \*All dimensions are nominal

Device	Package Type	Package Drawing		SPQ	Reel Diameter (mm)	Reel Width W1 (mm)	A0 (mm)	B0 (mm)	K0 (mm)	P1 (mm)	W (mm)	Pin1 Quadrant
LSF0102QDCURQ1	VSSOP	DCU	8	3000	180.0	8.4	2.25	3.35	1.05	4.0	8.0	Q3

# **PACKAGE MATERIALS INFORMATION**

www.ti.com 10-May-2023




## \*All dimensions are nominal

Ì	Device	Package Type	Package Drawing	Pins	SPQ	Length (mm)	Width (mm)	Height (mm)
ı	LSF0102QDCURQ1	VSSOP	DCU	8	3000	213.0	191.0	35.0



SMALL OUTLINE PACKAGE



### NOTES:


- 1. All linear dimensions are in millimeters. Any dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.

  2. This drawing is subject to change without notice.

  3. This dimension does not include mold flash, protrusions, or gate burrs. Mold flash, protrusions, or gate burrs shall not
- exceed 0.15 mm per side.
  4. Reference JEDEC registration MO-187 variation CA.



SMALL OUTLINE PACKAGE



NOTES: (continued)

- 5. Publication IPC-7351 may have alternate designs.
- 6. Solder mask tolerances between and around signal pads can vary based on board fabrication site.



SMALL OUTLINE PACKAGE



NOTES: (continued)

- 7. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.
- 8. Board assembly site may have different recommendations for stencil design.



# IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATA SHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, regulatory or other requirements.

These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you will fully indemnify TI and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to TI's Terms of Sale or other applicable terms available either on ti.com or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products.

TI objects to and rejects any additional or different terms you may have proposed.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265 Copyright © 2023, Texas Instruments Incorporated