









CD74HC14, CD54HC14

SCHS129G - JANUARY 1998 - REVISED MAY 2021

## **CDx4HC14 Hex Inverters with Schmitt-Trigger Inputs**

#### 1 Features

- **Buffered** inputs
- Wide operating voltage range: 2 V to 6 V
- Wide operating temperature range: -55°C to +125°C
- Supports fanout up to 10 LSTTL loads
- Significant power reduction compared to LSTTL logic ICs

## 2 Applications

- Synchronize inverted clock inputs
- Debounce a switch
- Invert a digital signal


## 3 Description

This device contains six independent inverters with Schmitt-trigger inputs. Each gate performs the Boolean function  $Y = \overline{A}$  in positive logic.

#### Device Information<sup>(1)</sup>

PART NUMBER	PACKAGE	BODY SIZE (NOM)							
CD74HC14M	SOIC (14)	8.70 mm × 3.90 mm							
CD74HC14E	PDIP (14)	19.30 mm × 6.40 mm							
CD74HC14PW	TSSOP (14)	5.00 mm × 4.40 mm							
CD54HC14F	CDIP (14)	21.30 mm × 7.60 mm							

For all available packages, see the orderable addendum at the end of the data sheet.



**Functional pinout** 



## **Table of Contents**

1 Features	8.3 Feature Description	8
2 Applications		
3 Description		10
4 Revision History		
5 Pin Configuration and Functions		
Pin Functions		
6 Specifications	11 Layout	13
6.1 Absolute Maximum Ratings		
6.2 ESD Ratings		
6.3 Recommended Operating Conditions4	12 Device and Documentation Support	14
6.4 Thermal Information	12.1 Documentation Support	14
6.5 Electrical Characteristics		
6.6 Switching Characteristics	12.3 Support Resources	14
6.7 Operating Characteristics		
6.8 Typical Characteristics		14
7 Parameter Measurement Information		
8 Detailed Description	13 Mechanical, Packaging, and Orderable	
8.2 Functional Block Diagram	3	


## **4 Revision History**

NOTE: Page numbers for previous revisions may differ from page numbers in the current version.

С	hanges from Revision F (May 2005) to Revision G (June 2020)	Page
•	Updated to new data sheet standards	1
•	Moved the HCT devices to a standalone data sheet (SCHS402)	1
	R <sub>0,JA</sub> increased for the D (86 to 133.6 °C/W) and PW (113 to 151.7 °C/W) packages, and decreased for	
	package (80 to 65.2 °C/W)	5



## **5 Pin Configuration and Functions**



D, N, PW, or J Package 14-Pin SOIC, PDIP, TSSOP, or CDIP Top View

## **Pin Functions**

PIN		1/0	DESCRIPTION
NAME	NO.	- I/O	DESCRIPTION
1A	1	Input	Channel 1, Input A
1Y	2	Output	Channel 1, Output Y
2A	3	Input	Channel 2, Input A
2Y	4	Output	Channel 2, Output Y
3A	5	Input	Channel 3, Input A
3Y	6	Output	Channel 3, Output Y
GND	7	_	Ground
4Y	8	Output	Channel 4, Output Y
4A	9	Input	Channel 4, Input A
5Y	10	Output	Channel 5, Output Y
5A	11	Input	Channel 5, Input A
6Y	12	Output	Channel 6, Output Y
6A	13	Input	Channel 6, Input A
V <sub>CC</sub>	14	_	Positive Supply



## **6 Specifications**

## 6.1 Absolute Maximum Ratings

over operating free-air temperature range (unless otherwise noted)(1)

			MIN	MAX	UNIT
V <sub>CC</sub>	Supply voltage		-0.5	7	V
I <sub>IK</sub>	Input clamp current <sup>(2)</sup>	$V_1 < -0.5 \text{ V or } V_1 > V_{CC} + 0.5 \text{ V}$		±20	mA
I <sub>OK</sub>	Output clamp current <sup>(2)</sup>	$V_{O} < -0.5 \text{ V or } V_{O} > V_{CC} + 0.5 \text{ V}$		±20	mA
Io	Continuous output current	$V_{O} > -0.5 \text{ V or } V_{O} < V_{CC} + 0.5 \text{ V}$		±25	mA
	Continuous current through V <sub>CC</sub> or GND	·		±50	mA
_	Junction temperature <sup>(3)</sup>	Plastic package		150	°C
TJ	Junction temperature(**)	Hermetic package or die		175	
	Lead temperature (soldering 10s)	SOIC - lead tips only		300	°C
T <sub>stg</sub>	Storage temperature		-65	150	°C

<sup>(1)</sup> Stresses beyond those listed under Absolute Maximum Rating may cause permanent damage to the device. These are stress ratings only, which do not imply functional operation of the device at these or any other conditions beyond those indicated under Recommended Operating Condition. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability.

- (2) The input and output voltage ratings may be exceeded if the input and output current ratings are observed.
- (3) Guaranteed by design.

### 6.2 ESD Ratings

			VALUE	UNIT
V	Electrostatic discharge	Human-body model (HBM), per ANSI/ESDA/ JEDEC JS-001 <sup>(1)</sup>	±1500	V
V <sub>(ESD)</sub>	Lieurostatic discriarge	Charged-device model (CDM), per JEDEC specification JESD22-C101 <sup>(2)</sup>	±500	V

- 1) JEDEC document JEP155 states that 500-V HBM allows safe manufacturing with a standard ESD control process.
- (2) JEDEC document JEP157 states that 250-V CDM allows safe manufacturing with a standard ESD control process.

## **6.3 Recommended Operating Conditions**

over operating free-air temperature range (unless otherwise noted)

			MIN	NOM	MAX	UNIT
V <sub>CC</sub>	Supply voltage	·	2	5	6	V
		V <sub>CC</sub> = 2 V	1.5			
V <sub>IH</sub>	High-level input voltage	V <sub>CC</sub> = 4.5 V	3.15			V
		V <sub>CC</sub> = 6 V	4.2			
		V <sub>CC</sub> = 2 V			0.5	
V <sub>IL</sub>	Low-level input voltage	V <sub>CC</sub> = 4.5 V			1.35	V
		V <sub>CC</sub> = 6 V			1.8	
VI	Input voltage	·	0		V <sub>CC</sub>	V
Vo	Output voltage		0		V <sub>CC</sub>	V
		V <sub>CC</sub> = 2 V			1000	
t <sub>t</sub>	Input transition time	V <sub>CC</sub> = 4.5 V			500	ns
		V <sub>CC</sub> = 6 V			400	
T <sub>A</sub>	Operating free-air temperature		-55		125	°C

Submit Document Feedback



## **6.4 Thermal Information**

			CD74HC14					
	THERMAL METRIC(1)	PW (TSSOP)	N (PDIP)	D (SOIC)	UNIT			
		14 PINS	14 PINS	14 PINS				
R <sub>θJA</sub>	Junction-to-ambient thermal resistance	151.7	69.3	133.6	°C/W			
R <sub>0JC(top)</sub>	Junction-to-case (top) thermal resistance	79.4	57.4	89.0	°C/W			
R <sub>θJB</sub>	Junction-to-board thermal resistance	94.7	49.0	89.5	°C/W			
$\Psi_{JT}$	Junction-to-top characterization parameter	25.2	37.4	45.5	°C/W			
$\Psi_{JB}$	Junction-to-board characterization parameter	94.1	48.8	89.1	°C/W			
R <sub>θJC(bot)</sub>	Junction-to-case (bottom) thermal resistance	N/A	N/A	N/A	°C/W			

<sup>(1)</sup> For more information about traditional and new thermal metrics, see the Semiconductor and IC Package Thermal Metrics application report.

## **6.5 Electrical Characteristics**

over operating free-air temperature range; typical values measured at  $T_A$  = 25°C (unless otherwise noted).

							Opera	ting free-	air tem	peratur	e (T <sub>A</sub> )			
F	PARAMETER	TEST CO	NDITIONS	V <sub>cc</sub>		25°C		-40°	C to 85	°C	-55°(	C to 125	°C	UNIT
					MIN	TYP	MAX	MIN	TYP	MAX	MIN	TYP	MAX	
	Positive			2 V	0.7		1.5	0.7		1.5	0.7		1.5	,,
V <sub>T+</sub>	switching			4.5 V	1.7		3.15	1.7		3.15	1.7		3.15	V
	threshold			6 V	2.1		4.2	2.1		4.2	2.1		4.2	
	Negative			2 V	0.3		1.0	0.3		1.0	0.3		1.0	
V <sub>T-</sub>	switching			4.5 V	0.9		2.2	0.9		2.2	0.9		2.2	V
	threshold			6 V	1.2		3.0	1.2		3.0	1.2		3.0	
				2 V	0.2		1.0	0.2		1.0	0.2		1.0	
$\Delta V_T$	Hysteresis (V <sub>T+</sub> - V <sub>T-</sub> )			4.5 V	0.4		1.4	0.4		1.4	0.4		1.4	V
	v 1-7			6 V	0.6		1.6	0.6		1.6	0.6		1.6	
				2 V	1.9			1.9			1.9			
			I <sub>OH</sub> = –20 μΑ	4.5 V	4.4			4.4			4.4			
	High-level	V <sub>I</sub> = V <sub>IH</sub> or	μ, ,	6 V	5.9			5.9			5.9			
V <sub>OH</sub>	output voltage	VIL	I <sub>OH</sub> = -4 mA	4.5 V	3.98			3.84			3.7			V
			I <sub>OH</sub> = -5.2 mA	6 V	5.48			5.34			5.2			
				2 V			0.1			0.1			0.1	
			I <sub>OL</sub> = 20 μΑ	4.5 V			0.1			0.1			0.1	
V <sub>OL</sub>	Low-level output		μ, ,	6 V			0.1			0.1			0.1	V
VOL.	voltage	V <sub>IL</sub>	I <sub>OL</sub> = 4 mA	4.5 V			0.26			0.33			0.4	•
			I <sub>OL</sub> = 5.2 mA	6 V			0.26			0.33			0.4	
Iı	Input leakage current	V <sub>I</sub> = V <sub>CC</sub> or		6 V			±0.1			±1			±1	μΑ
I <sub>CC</sub>	Supply current	V <sub>I</sub> = V <sub>CC</sub> or	I <sub>O</sub> = 0	6 V			2			20			40	μΑ
C <sub>i</sub>	Input capacitance			5 V			10			10			10	pF



## 6.6 Switching Characteristics

over operating free-air temperature range; typical values measured at TA = 25°C (unless otherwise noted).

				TEST	TEST		Operating free-air temperature (T <sub>A</sub> )												
	PARAMETER	FROM	то	CONDITIO	V <sub>cc</sub>		25°C		-40°	C to 8	5°C	-55°0	C to 12	25°C	UNIT				
				NS		MIN	TYP	MAX	MIN	TYP	MAX	MIN	TYP	MAX					
					2 V			135			170			205					
	Propagation dolay	Α	Y C	Υ	Υ	Υ	Y $C_L = 50 \text{ pF}$	C <sub>L</sub> = 50 pF	4.5 V			27			34			41	
t <sub>pd</sub>	Propagation delay				6 V			23			29			35	ns				
		Α	Υ	C <sub>L</sub> = 15 pF	5 V		11												
					2 V			75			95			110					
t <sub>t</sub>	Transition-time		Υ	C <sub>L</sub> = 50 pF	4.5 V			15			19			22	ns				
					6 V			13			16			19					

## **6.7 Operating Characteristics**

over operating free-air temperature range; typical values measured at T<sub>A</sub> = 25°C (unless otherwise noted).

	PARAMETER	TEST CONDITIONS	V <sub>CC</sub>	MIN	TYP MA	X UNIT
C <sub>pd</sub>	Power dissipation capacitance per gate	No load	5 V		20	pF

## **6.8 Typical Characteristics**

 $T_A = 25^{\circ}C$ 




Figure 6-1. Typical output voltage in the high state  $(V_{OH})$ 





Figure 6-2. Typical output voltage in the high state  $(V_{OL})$ 



## 7 Parameter Measurement Information

- Phase relationships between waveforms were chosen arbitrarily. All input pulses are supplied by generators having the following characteristics: PRR  $\leq$  1 MHz,  $Z_O$  = 50  $\Omega$ ,  $t_t$  < 6 ns.
- The outputs are measured one at a time, with one input transition per measurement.




A. C<sub>L</sub>= 50 pF and includes probe and jig capacitance.

Figure 7-1. Load Circuit

A. t<sub>t</sub> is the greater of t<sub>r</sub> and t<sub>f</sub>.

Figure 7-2. Voltage Waveforms Transition Times



The maximum between t<sub>PLH</sub> and t<sub>PHL</sub> is used for t<sub>pd</sub>.

Figure 7-3. Voltage Waveforms Propagation Delays




## **8 Detailed Description**

#### 8.1 Overview

This device contains six independent inverters with Schmitt-trigger inputs. Each gate performs the Boolean function  $Y = \overline{A}$  in positive logic.

## 8.2 Functional Block Diagram



## 8.3 Feature Description

#### 8.3.1 Balanced CMOS Push-Pull Outputs

A balanced output allows the device to sink and source similar currents. The drive capability of this device may create fast edges into light loads so routing and load conditions should be considered to prevent ringing. Additionally, the outputs of this device are capable of driving larger currents than the device can sustain without being damaged. It is important for the output power of the device to be limited to avoid damage due to over-current. The electrical and thermal limits defined in the *Section 6.1* must be followed at all times.

The CD74HC14 can drive a load with a total capacitance less than or equal to the maximum load listed in the Section 6.6 connected to a high-impedance CMOS input while still meeting all of the datasheet specifications. Larger capacitive loads can be applied, however it is not recommended to exceed the provided load value. If larger capacitive loads are required, it is recommended to add a series resistor between the output and the capacitor to limit output current to the values given in the Section 6.1.

### 8.3.2 CMOS Schmitt-Trigger Inputs

Standard CMOS inputs are high impedance and are typically modeled as a resistor from the input to ground in parallel with the input capacitance given in the Section 6.5. The worst case resistance is calculated with the maximum input voltage, given in the Section 6.1, and the maximum input leakage current, given in the Section 6.5, using ohm's law ( $R = V \div I$ ).

The Schmitt-trigger input architecture provides hysteresis as defined by  $\Delta V_T$  in the Section 6.5, which makes this device extremely tolerant to slow or noisy inputs. While the inputs can be driven much slower than standard CMOS inputs, it is still recommended to properly terminate unused inputs. Driving the inputs slowly will also increase dynamic current consumption of the device. For additional information regarding Schmitt-trigger inputs, please see Understanding Schmitt Triggers.



## 8.3.3 Clamp Diode Structure

The inputs and outputs to this device have both positive and negative clamping diodes as depicted in Figure 8-1.

#### **CAUTION**

Voltages beyond the values specified in the Section 6.1 table can cause damage to the device. The recommended input and output voltage ratings may be exceeded if the input and output clamp-current ratings are observed.




Figure 8-1. Electrical Placement of Clamping Diodes for Each Input and Output

## **8.4 Device Functional Modes**

**Table 8-1. Function Table** 

INPUT	OUTPUT
Α	Υ
L	Н
Н	L

## 9 Application and Implementation

#### Note

Information in the following applications sections is not part of the TI component specification, and TI does not warrant its accuracy or completeness. TI's customers are responsible for determining suitability of components for their purposes, as well as validating and testing their design implementation to confirm system functionality.

## 9.1 Application Information

This device can be used to add an additional stage to a counter with an external flip-flop. Because counters use a negative edge trigger, the flip-flop's clock input must be inverted to provide this function. This function only requires one of the six available inverters in the device, so the remaining channels can be used for other applications needing an inverted signal or improved signal integrity. Unused inputs must be terminated at  $V_{CC}$  or GND. Unused outputs can be left floating.

### 9.2 Typical Application




Figure 9-1. Typical application schematic

#### 9.2.1 Design Requirements

#### 9.2.1.1 Power Considerations

Ensure the desired supply voltage is within the range specified in the Section 6.3. The supply voltage sets the device's electrical characteristics as described in the Section 6.5.

The supply must be capable of sourcing current equal to the total current to be sourced by all outputs of the CD74HC14 plus the maximum supply current,  $I_{CC}$ , listed in the *Section 6.5*. The logic device can only source or sink as much current as it is provided at the supply and ground pins, respectively. Be sure not to exceed the maximum total current through GND or  $V_{CC}$  listed in the *Section 6.1*.

Total power consumption can be calculated using the information provided in CMOS Power Consumption and  $C_{pd}$  Calculation.

Thermal increase can be calculated using the information provided in Thermal Characteristics of Standard Linear and Logic (SLL) Packages and Devices.

#### CAUTION

The maximum junction temperature,  $T_J(max)$  listed in the Section 6.1, is an additional limitation to prevent damage to the device. Do not violate any values listed in the Section 6.1. These limits are provided to prevent damage to the device.

#### 9.2.1.2 Input Considerations

Input signals must cross  $V_{t-}(min)$  to be considered a logic LOW, and  $V_{t+}(max)$  to be considered a logic HIGH. Do not exceed the maximum input voltage range found in the Section 6.1.

Unused inputs must be terminated to either  $V_{CC}$  or ground. These can be directly terminated if the input is completely unused, or they can be connected with a pull-up or pull-down resistor if the input is to be used sometimes, but not always. A pull-up resistor is used for a default state of HIGH, and a pull-down resistor is used for a default state of LOW. The resistor size is limited by drive current of the controller, leakage current into the CD74HC14, as specified in the Section 6.5, and the desired input transition rate. A 10-k $\Omega$  resistor value is often used due to these factors.

The CD74HC14 has no input signal transition rate requirements because it has Schmitt-trigger inputs.

Another benefit to having Schmitt-trigger inputs is the ability to reject noise. Noise with a large enough amplitude can still cause issues. To know how much noise is too much, please refer to the  $\Delta V_T$ (min) in the Section 6.5. This hysteresis value will provide the peak-to-peak limit.

Unlike what happens with standard CMOS inputs, Schmitt-trigger inputs can be held at any valid value without causing huge increases in power consumption. The typical additional current caused by holding an input at a value other than V<sub>CC</sub> or ground is plotted in the Section 6.8.

Refer to the Section 8.3 for additional information regarding the inputs for this device.

#### 9.2.1.3 Output Considerations

The positive supply voltage is used to produce the output HIGH voltage. Drawing current from the output will decrease the output voltage as specified by the  $V_{OH}$  specification in the *Section 6.5*. Similarly, the ground voltage is used to produce the output LOW voltage. Sinking current into the output will increase the output voltage as specified by the  $V_{OL}$  specification in the *Section 6.5*.

Unused outputs can be left floating. Do not connect outputs directly to V<sub>CC</sub> or ground.

Refer to Section 8.3 for additional information regarding the outputs for this device.

### 9.2.2 Detailed Design Procedure

- 1. Add a decoupling capacitor from  $V_{CC}$  to GND. The capacitor needs to be placed physically close to the device and electrically close to both the  $V_{CC}$  and GND pins. An example layout is shown in the Section 11.
- 2. Ensure the capacitive load at the output is ≤ 70 pF. This is not a hard limit, however it will ensure optimal performance. This can be accomplished by providing short, appropriately sized traces from the CD74HC14 to the receiving device.
- 3. Ensure the resistive load at the output is larger than  $(V_{CC} / I_O(max)) \Omega$ . This will ensure that the maximum output current from the *Section 6.1* is not violated. Most CMOS inputs have a resistive load measured in megaohms; much larger than the minimum calculated above.
- 4. Thermal issues are rarely a concern for logic gates, however the power consumption and thermal increase can be calculated using the steps provided in the application report, CMOS Power Consumption and Cpd Calculation

#### 9.2.3 Application Curves




Figure 9-2. Typical application timing diagram



## 10 Power Supply Recommendations

The power supply can be any voltage between the minimum and maximum supply voltage rating located in the Section 6.3. Each  $V_{CC}$  terminal should have a bypass capacitor to prevent power disturbance. A 0.1- $\mu$ F capacitor is recommended for this device. It is acceptable to parallel multiple bypass caps to reject different frequencies of noise. The 0.1- $\mu$ F and 1- $\mu$ F capacitors are commonly used in parallel. The bypass capacitor should be installed as close to the power terminal as possible for best results, as shown in Figure 11-1.



## 11 Layout

## 11.1 Layout Guidelines

When using multiple-input and multiple-channel logic devices inputs must not ever be left floating. In many cases, functions or parts of functions of digital logic devices are unused; for example, when only two inputs of a triple-input AND gate are used. Such unused input pins must not be left unconnected because the undefined voltages at the outside connections result in undefined operational states. All unused inputs of digital logic devices must be connected to a logic high or logic low voltage, as defined by the input voltage specifications, to prevent them from floating. The logic level that must be applied to any particular unused input depends on the function of the device. Generally, the inputs are tied to GND or  $V_{CC}$ , whichever makes more sense for the logic function or is more convenient.

#### 11.2 Layout Example




Figure 11-1. Example layout for the CD74HC14



## 12 Device and Documentation Support

## **12.1 Documentation Support**

#### 12.1.1 Related Documentation

For related documentation see the following:

- HCMOS Design Considerations
- CMOS Power Consumption and CPD Calculation
- · Designing with Logic

#### 12.2 Related Links

The table below lists quick access links. Categories include technical documents, support and community resources, tools and software, and quick access to sample or buy.

### 12.3 Support Resources

TI E2E<sup>™</sup> support forums are an engineer's go-to source for fast, verified answers and design help — straight from the experts. Search existing answers or ask your own question to get the quick design help you need.

Linked content is provided "AS IS" by the respective contributors. They do not constitute TI specifications and do not necessarily reflect TI's views; see TI's Terms of Use.

#### 12.4 Trademarks

TI E2E<sup>™</sup> is a trademark of Texas Instruments.

All trademarks are the property of their respective owners.

## 12.5 Electrostatic Discharge Caution



This integrated circuit can be damaged by ESD. Texas Instruments recommends that all integrated circuits be handled with appropriate precautions. Failure to observe proper handling and installation procedures can cause damage.

ESD damage can range from subtle performance degradation to complete device failure. Precision integrated circuits may be more susceptible to damage because very small parametric changes could cause the device not to meet its published specifications.

### 12.6 Glossary

TI Glossary

This glossary lists and explains terms, acronyms, and definitions.

### 13 Mechanical, Packaging, and Orderable Information

The following pages include mechanical, packaging, and orderable information. This information is the most current data available for the designated devices. This data is subject to change without notice and revision of this document. For browser-based versions of this data sheet, refer to the left-hand navigation.

Submit Document Feedback

Copyright © 2021 Texas Instruments Incorporated

www.ti.com 7-Apr-2024

#### PACKAGING INFORMATION

Orderable Device	Status	Package Type	Package Drawing	Pins	Package Qty	Eco Plan	Lead finish/ Ball material	MSL Peak Temp	Op Temp (°C)	Device Marking (4/5)	Samples
							(6)				
CD54HC14F	ACTIVE	CDIP	J	14	25	Non-RoHS & Green	SNPB	N / A for Pkg Type	-55 to 125	CD54HC14F	Samples
CD54HC14F3A	ACTIVE	CDIP	J	14	25	Non-RoHS & Green	SNPB	N / A for Pkg Type	-55 to 125	8409101CA CD54HC14F3A	Samples
CD74HC14E	ACTIVE	PDIP	N	14	25	RoHS & Green	NIPDAU	N / A for Pkg Type	-55 to 125	CD74HC14E	Samples
CD74HC14EE4	ACTIVE	PDIP	N	14	25	RoHS & Green	NIPDAU	N / A for Pkg Type	-55 to 125	CD74HC14E	Samples
CD74HC14M96	ACTIVE	SOIC	D	14	2500	RoHS & Green	NIPDAU   SN	Level-1-260C-UNLIM	-55 to 125	HC14M	Samples
CD74HC14MT	ACTIVE	SOIC	D	14	250	RoHS & Green	NIPDAU	Level-1-260C-UNLIM	-55 to 125	HC14M	Samples
CD74HC14MTG4	ACTIVE	SOIC	D	14	250	RoHS & Green	NIPDAU	Level-1-260C-UNLIM	-55 to 125	HC14M	Samples
CD74HC14PWR	ACTIVE	TSSOP	PW	14	2000	RoHS & Green	NIPDAU   SN	Level-1-260C-UNLIM	-55 to 125	HJ14	Samples

(1) The marketing status values are defined as follows:

**ACTIVE:** Product device recommended for new designs.

LIFEBUY: TI has announced that the device will be discontinued, and a lifetime-buy period is in effect.

NRND: Not recommended for new designs. Device is in production to support existing customers, but TI does not recommend using this part in a new design.

PREVIEW: Device has been announced but is not in production. Samples may or may not be available.

**OBSOLETE:** TI has discontinued the production of the device.

(2) RoHS: TI defines "RoHS" to mean semiconductor products that are compliant with the current EU RoHS requirements for all 10 RoHS substances, including the requirement that RoHS substance do not exceed 0.1% by weight in homogeneous materials. Where designed to be soldered at high temperatures, "RoHS" products are suitable for use in specified lead-free processes. TI may reference these types of products as "Pb-Free".

RoHS Exempt: TI defines "RoHS Exempt" to mean products that contain lead but are compliant with EU RoHS pursuant to a specific EU RoHS exemption.

Green: TI defines "Green" to mean the content of Chlorine (CI) and Bromine (Br) based flame retardants meet JS709B low halogen requirements of <=1000ppm threshold. Antimony trioxide based flame retardants must also meet the <=1000ppm threshold requirement.

<sup>(3)</sup> MSL, Peak Temp. - The Moisture Sensitivity Level rating according to the JEDEC industry standard classifications, and peak solder temperature.

<sup>(4)</sup> There may be additional marking, which relates to the logo, the lot trace code information, or the environmental category on the device.

<sup>(5)</sup> Multiple Device Markings will be inside parentheses. Only one Device Marking contained in parentheses and separated by a "~" will appear on a device. If a line is indented then it is a continuation of the previous line and the two combined represent the entire Device Marking for that device.

## **PACKAGE OPTION ADDENDUM**

www.ti.com 7-Apr-2024

(6) Lead finish/Ball material - Orderable Devices may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead finish/Ball material values may wrap to two lines if the finish value exceeds the maximum column width.

**Important Information and Disclaimer:** The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.

#### OTHER QUALIFIED VERSIONS OF CD54HC14, CD74HC14:

Catalog: CD74HC14

Military: CD54HC14

NOTE: Qualified Version Definitions:

- Catalog TI's standard catalog product
- Military QML certified for Military and Defense Applications

## **PACKAGE MATERIALS INFORMATION**

www.ti.com 6-Apr-2024

## TAPE AND REEL INFORMATION





	•
A0	Dimension designed to accommodate the component width
В0	Dimension designed to accommodate the component length
K0	Dimension designed to accommodate the component thickness
W	Overall width of the carrier tape
P1	Pitch between successive cavity centers

#### QUADRANT ASSIGNMENTS FOR PIN 1 ORIENTATION IN TAPE



#### \*All dimensions are nominal

Device	Package Type	Package Drawing		SPQ	Reel Diameter (mm)	Reel Width W1 (mm)	A0 (mm)	B0 (mm)	K0 (mm)	P1 (mm)	W (mm)	Pin1 Quadrant
CD74HC14M96	SOIC	D	14	2500	330.0	16.4	6.5	9.0	2.1	8.0	16.0	Q1
CD74HC14MT	SOIC	D	14	250	330.0	16.4	6.5	9.0	2.1	8.0	16.0	Q1
CD74HC14PWR	TSSOP	PW	14	2000	330.0	12.4	6.9	5.6	1.6	8.0	12.0	Q1

www.ti.com 6-Apr-2024




### \*All dimensions are nominal

Device	Package Type	Package Drawing	Pins	SPQ	Length (mm)	Width (mm)	Height (mm)	
CD74HC14M96	SOIC	D	14	2500	367.0	367.0	38.0	
CD74HC14MT	SOIC	D	14	250	210.0	185.0	35.0	
CD74HC14PWR	TSSOP	PW	14	2000	356.0	356.0	35.0	

## **PACKAGE MATERIALS INFORMATION**

www.ti.com 6-Apr-2024

## **TUBE**



\*All dimensions are nominal

Device	Package Name	Package Type	Pins	SPQ	L (mm)	W (mm)	T (µm)	B (mm)
CD74HC14E	N	PDIP	14	25	506	13.97	11230	4.32
CD74HC14E	N	PDIP	14	25	506	13.97	11230	4.32
CD74HC14EE4	N	PDIP	14	25	506	13.97	11230	4.32
CD74HC14EE4	N	PDIP	14	25	506	13.97	11230	4.32

CERAMIC DUAL IN LINE PACKAGE



Images above are just a representation of the package family, actual package may vary. Refer to the product data sheet for package details.

4040083-5/G





CERAMIC DUAL IN LINE PACKAGE



- 1. All controlling linear dimensions are in inches. Dimensions in brackets are in millimeters. Any dimension in brackets or parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.
- 2. This drawing is subject to change without notice.
- 3. This package is hermitically sealed with a ceramic lid using glass frit.
- His package is remitted by sealed with a ceramic its using glass mit.
  Index point is provided on cap for terminal identification only and on press ceramic glass frit seal only.
  Falls within MIL-STD-1835 and GDIP1-T14.



CERAMIC DUAL IN LINE PACKAGE



## D (R-PDSO-G14)

## PLASTIC SMALL OUTLINE



- A. All linear dimensions are in inches (millimeters).
- B. This drawing is subject to change without notice.
- Body length does not include mold flash, protrusions, or gate burrs. Mold flash, protrusions, or gate burrs shall not exceed 0.006 (0,15) each side.
- Body width does not include interlead flash. Interlead flash shall not exceed 0.017 (0,43) each side.
- E. Reference JEDEC MS-012 variation AB.



# D (R-PDSO-G14)

## PLASTIC SMALL OUTLINE



- A. All linear dimensions are in millimeters.
- B. This drawing is subject to change without notice.
- C. Publication IPC-7351 is recommended for alternate designs.
- D. Laser cutting apertures with trapezoidal walls and also rounding corners will offer better paste release. Customers should contact their board assembly site for stencil design recommendations. Refer to IPC-7525 for other stencil recommendations.
- E. Customers should contact their board fabrication site for solder mask tolerances between and around signal pads.



PW (R-PDSO-G14)

## PLASTIC SMALL OUTLINE



- A. All linear dimensions are in millimeters. Dimensioning and tolerancing per ASME Y14.5M—1994.
- B. This drawing is subject to change without notice.
  - Sody length does not include mold flash, protrusions, or gate burrs. Mold flash, protrusions, or gate burrs shall not exceed 0,15 each side.
- Body width does not include interlead flash. Interlead flash shall not exceed 0,25 each side.
- E. Falls within JEDEC MO-153



## N (R-PDIP-T\*\*)

## PLASTIC DUAL-IN-LINE PACKAGE

16 PINS SHOWN



- A. All linear dimensions are in inches (millimeters).
- B. This drawing is subject to change without notice.
- Falls within JEDEC MS-001, except 18 and 20 pin minimum body length (Dim A).
- The 20 pin end lead shoulder width is a vendor option, either half or full width.



## IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATA SHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, regulatory or other requirements.

These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you will fully indemnify TI and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to TI's Terms of Sale or other applicable terms available either on ti.com or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products.

TI objects to and rejects any additional or different terms you may have proposed.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265 Copyright © 2024, Texas Instruments Incorporated