

Sample &

Buy



#### DAC128S085

SNAS407H - AUGUST 2007 - REVISED APRIL 2015

## DAC128S085 12-Bit Micro-Power OCTAL Digital-to-Analog Converter With Rail-to-Rail Outputs

Technical

Documents

#### Features 1

- Ensured Monotonicity
- Low Power Operation
- Rail-to-Rail Voltage Output
- **Daisy-Chain Capability**
- Power-on Reset to 0 V
- Simultaneous Output Updating
- Individual Channel Power-Down Capability
- Wide Power Supply Range (2.7 V to 5.5 V)
- Dual Reference Voltages With Range of 0.5 V to V۵
- Operating Temperature Range of -40°C to 125°C
- Smallest Package in the Industry
- **Resolution 12 Bits**
- INL ±8 LSB (Maximum)
- DNL 0.75 / -0.4 LSB (Maximum)
- Settling Time 8.5 µs (Maximum)
- Zero Code Error 15 mV (Maximum)
- Full-Scale Error -0.75 %FSR (Maximum)
- Supply Power
  - 1.95 mW (3 V) / 4.85 mW (5 V) Typical
  - Power Down 0.3 µW (3 V) / 1 µW (5 V) Typical

#### Applications 2

- **Battery-Powered Instruments**
- Digital Gain and Offset Adjustment
- Programmable Voltage and Current Sources
- **Programmable Attenuators**
- Voltage Reference for ADCs
- Sensor Supply Voltage
- **Range Detectors**

### 3 Description

Tools &

Software

The DAC128S085 is a full-featured, general-purpose OCTAL 12-bit voltage-output digital-to-analog converter (DAC) that can operate from a single 2.7-V to 5.5-V supply and consumes 1.95 mW at 3 V and 4.85 mW at 5 V. The DAC128S085 is packaged in a 16-lead WQFN package and a 16-lead TSSOP WQFN package. The package makes the DAC128S085 the smallest OCTAL DAC in its class. The on-chip output amplifiers allow rail-to-rail output swing, and the 3-wire serial interface operates at clock rates up to 40 MHz over the entire supply voltage range. Competitive devices are limited to 25-MHz clock rates at supply voltages in the 2.7-V to 3.6-V range. The serial interface is compatible with standard SPI™, QSPI, MICROWIRE, and DSP interfaces. The DAC128S085 also offers daisy-chain operation, where an unlimited number of DAC128S085s can be updated simultaneously using a single serial interface.

Support &

Community

**.**...


There are two references for the DAC128S085. One reference input serves channels A through D, while the other reference serves channels E through H. Each reference can be set independently between 0.5 V and V<sub>A</sub>, providing the widest possible output dynamic range. The DAC128S085 has a 16-bit input shift register that controls the mode of operation, the power-down condition, and the register/output value of the DAC channels. All eight DAC outputs can be updated simultaneously or individually.

#### Device Information<sup>(1)</sup>

PART NUMBER	PACKAGE	BODY SIZE (NOM)
DAC128S085	TSSOP (16)	5.00 mm × 4.4 mm
	WQFN (16)	4.00 mm × 4.00 mm

(1) For all available packages, see the orderable addendum at the end of the datasheet.

#### **Simplified Schematic**





## **Table of Contents**

8.3 Feature Description	16
8.4 Device Functional Modes	20
8.5 Programming	21
Application and Implementation	22
9.1 Application Information	22
9.2 Typical Application	22
Power Supply Recommendations	23
Layout	23
11.1 Layout Guidelines	23
11.2 Layout Example	24
Device and Documentation Support	25
12.1 Device Support	25
12.2 Documentation Support	26
12.3 Trademarks	26
12.4 Electrostatic Discharge Caution	26
12.5 Glossary	26
Mechanical, Packaging, and Orderable	
Information	26
	<ul> <li>8.4 Device Functional Modes</li></ul>

Copyright © 2007-2015, Texas Instruments Incorporated

## 4 Revision History

8

2

Changes from Revision G (January 2015) to Revision H	Page
Switched WQFN and TSSOP pinouts to their correct titles	
Re-drew TSSOP pinout as a square to better reflect mechanical packaging drawings	
Changes from Revision F (March 2013) to Revision G	Page
<ul> <li>Added Pin Configuration and Functions section, ESD Ratings table, Feature Description section</li> </ul>	on, Device Functional

and Documentation Support section, and Mechanical, Packaging, and Orderable Information section	1
Changes from Revision E (March 2013) to Revision F	Page
Changed layout of National Data Sheet to TI format	23

•	Switched WQFN and TSSOP pinouts to their correct titles Re-drew TSSOP pinout as a square to better reflect mechanical packaging drawings
С	hanges from Revision F (March 2013) to Revision G
•	Added Pin Configuration and Functions section, ESD Ratings table, Feature Description section, Device Functiona

#### 1 Features ..... 1 2 Applications ..... 1 3 Description ..... 1 4 Revision History..... 2 5 Description (continued)...... 3 6 Pin Configuration and Functions ...... 4 7 7.1 Absolute Maximum Ratings ...... 5 7.3 Recommended Operating Conditions ...... 5 7.4 Thermal Information ...... 6

7.7 Typical Characteristics ..... 11

Detailed Description ...... 15 8.2 Functional Block Diagram ..... 15 www.ti.com



## 5 Description (continued)


A power-on reset circuit ensures that the DAC outputs power up to zero volts and remain there until there is a valid write to the device. The power-down feature of the DAC128S085 allows each DAC to be independently powered with three different termination options. With all the DAC channels powered down, power consumption reduces to less than 0.3  $\mu$ W at 3 V and less than 1  $\mu$ W at 5 V. The low power consumption and small packages of the DAC128S085 make it an excellent choice for use in battery-operated equipment.


The DAC128S085 is one of a family of pin-compatible DACs, including the 8-bit DAC088S085 and the 10-bit DAC108S085. All three parts are offered with the same pinout, allowing system designers to select a resolution appropriate for their application without redesigning their printed circuit board. The DAC128S085 operates over the extended industrial temperature range of  $-40^{\circ}$ C to  $125^{\circ}$ C.

TEXAS INSTRUMENTS

www.ti.com

## 6 Pin Configuration and Functions





#### Pin Functions

PIN		PIN TYPE		DESCRIPTION		
NAME	TSSOP NO.	WQFN NO.	ITPE	DESCRIPTION		
D <sub>IN</sub>	1	15	Digital Input	Serial Data Input. Data is clocked into the 16-bit shift register on the falling edges of SCLK after the fall of SYNC.		
D <sub>OUT</sub>	2	16	Digital Output	Serial Data Output. D <sub>OUT</sub> is utilized in daisy chain operation and is connected directly to a D <sub>IN</sub> pin on another DAC128S085. Data is not available at D <sub>OUT</sub> unless SYNC remains low for more than 16 SCLK cycles.		
GND	10	8	Ground	Ground reference for all on-chip circuitry.		
SCLK	16	14	Digital Input	Serial Clock Input. Data is clocked into the input shift register on the falling edges of this pin.		
SYNC	15	13	Digital Input	Frame Synchronization Input. When this pin goes low, data is written into the DAC's input shift register on the <u>falling</u> edges of SCLK. After the 16th falling <u>edge</u> of SCLK, a rising edge of SYNC causes the DAC to be updated. If <u>SYNC</u> is brought high before the 15th falling edge of SCLK, the rising edge of SYNC acts as an interrupt and the write sequence is ignored by the DAC.		
V <sub>A</sub>	7	5	Supply	Power supply input. Must be decoupled to GND.		
V <sub>OUTA</sub>	3	1	Analog Output	Channel A Analog Output Voltage.		
V <sub>OUTB</sub>	4	2	Analog Output	Channel B Analog Output Voltage.		
V <sub>OUTC</sub>	5	3	Analog Output	Channel C Analog Output Voltage.		
V <sub>OUTD</sub>	6	4	Analog Output	Channel D Analog Output Voltage.		
V <sub>OUTE</sub>	14	12	Analog Output	Channel E Analog Output Voltage.		
V <sub>OUTF</sub>	13	11	Analog Output	Channel F Analog Output Voltage.		
V <sub>OUTG</sub>	12	10	Analog Output	Channel G Analog Output Voltage.		
V <sub>OUTH</sub>	11	9	Analog Output	Channel H Analog Output Voltage.		
V <sub>REF1</sub>	8	6	Analog Input	Unbuffered reference voltage shared by Channels A, B, C, and D. Must be decoupled to GND.		
V <sub>REF2</sub>	9	7	Analog Input	Unbuffered reference voltage shared by Channels E, F, G, and H. Must be decoupled to GND.		
PAD (WQFN only)	_	17	Ground	Exposed die attach pad can be connected to ground or left floating. Soldering the pad to the PCB offers optimal thermal performance and enhances package self-alignment during reflow.		

4

Copyright © 2007-2015, Texas Instruments Incorporated



## 7 Specifications

## 7.1 Absolute Maximum Ratings

over operating free-air temperature range (unless otherwise noted)<sup>(1)(2)</sup>

	MIN	MAX	UNIT
Supply Voltage, V <sub>A</sub>		6.5	V
Voltage on any Input Pin	-0.3	6.5	V
Input Current at Any Pin <sup>(3)</sup>		10	mA
Package Input Current <sup>(3)</sup>		30	mA
Power Consumption at $T_A = 25^{\circ}C$		See (4)	
Junction Temperature		150	°C
Storage Temperature, T <sub>stg</sub>	-65	150	°C

(1) Absolute Maximum Ratings indicate limits beyond which damage to the device may occur. Recomended Operating Ratings indicate conditions for which the device is functional, but do not specify specific performance limits. For ensured specifications and test conditions, see Electrical Characteristics. The ensured specifications apply only for the test conditions listed. Some performance characteristics may degrade when the device is not operated under the listed test conditions. Operation of the device beyond the Absolute Maximum Ratings is not recommended.

- (2) All voltages are measured with respect to GND = 0 V, unless otherwise specified.
- (3) When the input voltage at any pin exceeds 5.5 V or is less than GND, the current at that pin should be limited to 10 mA. The 30-mA maximum package input current rating limits the number of pins that can safely exceed the power supplies with an input current of 10 mA to three.
- (4) The absolute maximum junction temperature (T<sub>J</sub>max) for this device is 150°C. The maximum allowable power dissipation is dictated by T<sub>J</sub>max, the junction-to-ambient thermal resistance (R<sub>0JA</sub>), and the ambient temperature (T<sub>A</sub>), and can be calculated using the formula P<sub>D</sub>MAX = (T<sub>J</sub>max T<sub>A</sub>) / R<sub>0JA</sub>. The values for maximum power dissipation will be reached only when the device is operated in a severe fault condition (for example, when input or output pins are driven beyond the operating ratings, or the power supply polarity is reversed). Such conditions should always be avoided.

### 7.2 ESD Ratings

			VALUE	UNIT
		Human body model (HBM), per ANSI/ESDA/JEDEC JS-001 <sup>(1)</sup>	±2500	
V <sub>(ESD)</sub>	Electrostatic discharge	Charged-device model (CDM), per JEDEC specification JESD22-C101 $^{\left( 2\right) }$	±1000	V
		Machine Model	±250	

(1) JEDEC document JEP155 states that 500-V HBM allows safe manufacturing with a standard ESD control process.


(2) JEDEC document JEP157 states that 250-V CDM allows safe manufacturing with a standard ESD control process.

## 7.3 Recommended Operating Conditions

over operating free-air temperature range (unless otherwise noted)

	MIN	MAX	UNIT
Operating Temperature Range		−40 ≤ T <sub>A</sub> ≤ +125	°C
Supply Voltage, V <sub>A</sub>	2.7	5.5	V
Reference Voltage, V <sub>REF1,2</sub>	0.5	V <sub>A</sub>	V
Digital Input Voltage <sup>(1)</sup>	0.0	5.5	V
Output Load	0	1500	pF
SCLK Frequency		40	MHz

(1) The inputs are protected as shown below. Input voltage magnitudes up to 5.5 V, regardless of V<sub>A</sub>, will not cause errors in the conversion result. For example, if V<sub>A</sub> is 3 V, the digital input pins can be driven with a 5-V logic device.



#### DAC128S085

SNAS407H-AUGUST 2007-REVISED APRIL 2015

www.ti.com

STRUMENTS

EXAS

### 7.4 Thermal Information

			DAC128S085		
	THERMAL METRIC <sup>(1)</sup>	PW (TSSOP)	RGH (WQFN)	UNIT	
		16 PINS	16 PINS		
$R_{\theta J A}$	Junction-to-ambient thermal resistance	98	34		
$R_{\thetaJA}$	Junction-to-ambient thermal resistance	31	25		
$R_{\theta JA}$	Junction-to-ambient thermal resistance	43	11	°C/W	
Фјт	Junction-to-top characterization parameter	2	0.2		
$\phi_{JB}$	Junction-to-board characterization parameter	43	11		

(1) For more information about traditional and new thermal metrics, see the IC Package Thermal Metrics application report, SPRA953.

## 7.5 Electrical Characteristics

The following specifications apply for  $V_A = 2.7$  V to 5.5 V,  $V_{REF1} = V_{REF2} = V_A$ ,  $C_L = 200$  pF to GND,  $f_{SCLK} = 30$  MHz, input code range 48 to 4047. All limits are at  $T_A = 25^{\circ}$ C, unless otherwise specified.

	PARAMETER	TEST CONDITIONS	MIN <sup>(1)</sup>	TYP	MAX <sup>(1)</sup>	UNIT
STATIC	PERFORMANCE					
	Resolution	$T_{MIN} \le T_A \le T_{MAX}$	12			Bits
	Monotonicity	$T_{MIN} \le T_A \le T_{MAX}$	12			Bits
INU	late and New Line arity			±2		
INL	Integral Non-Linearity	$T_{MIN} \le T_A \le T_{MAX}$			±8	LSB
				0.15		LSB
	Differential Marchine and	$T_{MIN} \le T_A \le T_{MAX}$			0.75	
DNL	Differential Non-Linearity			-0.09		LSB
		$T_{MIN} \le T_A \le T_{MAX}$	-0.4			
76	Zana Orada Francis	I <sub>OUT</sub> = 0		+5		
ZE	Zero Code Error	$T_{MIN} \le T_A \le T_{MAX}$			15	mV
505		I <sub>OUT</sub> = 0		-0.1%		500
FSE	Full-Scale Error	$T_{MIN} \le T_A \le T_{MAX}$			-0.75%	FSR
05	0.1.5			-0.2%		FSR
GE	Gain Error	$T_{MIN} \le T_A \le T_{MAX}$			-1 %	
ZCED	Zero Code Error Drift			-20		µV/°C
TC GE	Gain Error Tempco			-1		ppm/°C
OUTPUT	CHARACTERISTICS					
	Output Voltage Range	$T_{MIN} \le T_A \le T_{MAX}$	0		V <sub>REF1,2</sub>	V
I <sub>OZ</sub>	High-Impedance Output Leakage Current <sup>(2)</sup>	$T_{MIN} \le T_A \le T_{MAX}$			±1	μΑ
		V <sub>A</sub> = 3 V, I <sub>OUT</sub> = 200 μA		10		mV
700	7 0 1 0 1 1	V <sub>A</sub> = 3 V, I <sub>OUT</sub> = 1 mA		45		mV
ZCO	Zero Code Output	V <sub>A</sub> = 5 V, I <sub>OUT</sub> = 200 μA		8		mV
		V <sub>A</sub> = 5 V, I <sub>OUT</sub> = 1 mA		34		mV
		V <sub>A</sub> = 3 V, I <sub>OUT</sub> = 200 μA		2.984		V
500		V <sub>A</sub> = 3 V, I <sub>OUT</sub> = 1 mA		2.933		V
FSO	Full Scale Output	V <sub>A</sub> = 5 V, I <sub>OUT</sub> = 200 μA		4.987		V
		$V_A = 5 V, I_{OUT} = 1 mA$		4.955		V

(1) Test limits are ensured to TI's AOQL (Average Outgoing Quality Level).

(2) This parameter is ensured by design and/or characterization and is not tested in production.



### **Electrical Characteristics (continued)**

The following specifications apply for  $V_A = 2.7 \text{ V}$  to 5.5 V,  $V_{REF1} = V_{REF2} = V_A$ ,  $C_L = 200 \text{ pF}$  to GND,  $f_{SCLK} = 30 \text{ MHz}$ , input code range 48 to 4047. All limits are at  $T_A = 25^{\circ}$ C, unless otherwise specified.

	PARAMETER	TEST CONDITIONS	MIN <sup>(1)</sup>	ТҮР	MAX <sup>(1)</sup>	UNIT
1	Output Short Circuit Current	$V_A = 3 V, V_{OUT} = 0 V,$ Input Code = FFFh		-50		mA
I <sub>OS</sub>	(source) <sup>(3)</sup>	$V_A = 5 V, V_{OUT} = 0 V,$ Input Code = FFFh		-60		mA
1	Output Short Circuit Current	$V_A = 3 V$ , $V_{OUT} = 3 V$ , Input Code = 000h		50		mA
l <sub>os</sub>	(sink) <sup>(3)</sup>	$V_A = 5 V, V_{OUT} = 5 V,$ Input Code = 000h		70		mA
1-	Continuous Output Current per				10	mA
lo	channel <sup>(2)</sup>	$ \begin{array}{l} T_A = 125^\circ C \\ T_{MIN} \leq T_A \leq T_{MAX} \end{array} $			6.5	mA
0	Maximum I and Canaditanaa	R <sub>L</sub> = ∞		1500		pF
CL	Maximum Load Capacitance	$R_L = 2 k\Omega$		1500		pF
Z <sub>OUT</sub>	DC Output Impedance			8		Ω
	NCE INPUT TERISTICS					
	Input Range Minimum			0.5		V
VREF1,2		$T_{MIN} \le T_A \le T_{MAX}$	2.7			v
VKEF1,2	Input Range Maximum	$T_{MIN} \le T_A \le T_{MAX}$			V <sub>A</sub>	V
	Input Impedance			30		kΩ
LOGIC IN	PUT CHARACTERISTICS					
I <sub>IN</sub>	Input Current <sup>(2)</sup>	$T_{MIN} \le T_A \le T_{MAX}$			±1	μA
		$V_A = 2.7 V$ to 3.6 V		1		V
V	Input Low Voltage	$T_{MIN} \le T_A \le T_{MAX}$			0.6	v
V <sub>IL</sub>	Input Low Voltage	$V_{A} = 4.5 V \text{ to } 5.5 V$		1.1		V
					0.8	v
		$V_A = 2.7 V \text{ to } 3.6 V$		1.4		V
M	Input High Voltage	$T_{MIN} \le T_A \le T_{MAX}$	2.1			v
VIH	Input High Voltage	$V_{A} = 4.5 V \text{ to } 5.5 V$		2		V
		$T_{MIN} \le T_A \le T_{MAX}$	2.4			v
C <sub>IN</sub>	Input Capacitance <sup>(2)</sup>	$T_{MIN} \le T_A \le T_{MAX}$			3	pF

(3) This parameter does not represent a condition which the DAC can sustain continuously. See the continuous output current specification for the maximum DAC output current per channel.

STRUMENTS

EXAS

## **Electrical Characteristics (continued)**

The following specifications apply for  $V_A = 2.7 \text{ V}$  to 5.5 V,  $V_{REF1} = V_{REF2} = V_A$ ,  $C_L = 200 \text{ pF}$  to GND,  $f_{SCLK} = 30 \text{ MHz}$ , input code range 48 to 4047. All limits are at  $T_A = 25^{\circ}$ C, unless otherwise specified.

	PARAMETER	TEST CON	DITIONS	MIN <sup>(1)</sup> TYF	P MAX <sup>(1)</sup>	UNIT	
POWE	R REQUIREMENTS						
V <sub>A</sub>	Supply Voltage Minimum	$T_{MIN} \leq T_{A} \leq T_{MAX}$		2.7		V	
۷A	Supply Voltage Maximum	$T_{MIN} \leq T_{A} \leq T_{MAX}$			5.5	V	
			V <sub>A</sub> = 2.7 V to 3.6 V	460	)	ΠA	
	Normal Supply Current for	f <sub>SCLK</sub> = 30 MHz,	T <sub>MIN</sub> ≤ T <sub>A</sub> ≤ T <sub>MAX</sub>		560	μA	
	supply pin V <sub>A</sub>	output unloaded	V <sub>A</sub> = 4.5 V to 5.5 V	650	)	μA	
					830	-	
N			V <sub>A</sub> = 2.7 V to 3.6 V	99	5	۵	
	Normal Supply Current for	f <sub>SCLK</sub> = 30 MHz,	$\begin{array}{l} T_{MIN} \leq T_A \leq \\ T_{MAX} \end{array}$		130	μA	
	V <sub>REF1</sub> or V <sub>REF2</sub>	output unloaded	V <sub>A</sub> = 4.5 V to 5.5 V	160	)	μA	
					220		
	Static Supply Current for	$f_{SCLK} = 0,$	V <sub>A</sub> = 2.7 V to 3.6 V	370	)	μΑ	
ST	supply pin V <sub>A</sub>	output unloaded	V <sub>A</sub> = 4.5 V to 5.5 V	440	)	μA	
-51	Static Supply Current for	f <sub>SCLK</sub> = 0,	V <sub>A</sub> = 2.7 V to 3.6 V	99	5	μΑ	
	V <sub>REF1</sub> or V <sub>REF2</sub>	output unloaded	V <sub>A</sub> = 4.5 V to 5.5 V	160	)	μA	
			V <sub>A</sub> = 2.7 V to 3.6 V	0.2	2	μA	
		$f_{SCLK} = 30 \text{ MHz},$ SYNC = V <sub>A</sub> and D <sub>IN</sub> = 0V after PD mode loaded			1.5		
			V <sub>A</sub> = 4.5 V to 5.5 V	0.9	5	μΑ	
	Total Power Down Supply		$\begin{array}{l} T_{MIN} \leq T_A \leq \\ T_{MAX} \end{array}$		3		
PD	Current for all PD Modes		V <sub>A</sub> = 2.7 V to 3.6 V	0.1	1	0	
		$f_{SCLK} = 0$ , SYNC = $V_A$ and $D_{IN} = 0V$	$T_{MIN} \le T_A \le T_{MAX}$		1	μΑ	
		after PD mode loaded	V <sub>A</sub> = 4.5 V to 5.5 V	0.2	2		
			$T_{MIN} \le T_A \le T_{MAX}$		2		
			V <sub>A</sub> = 2.7 V to 3.6 V	1.99	5		
		f <sub>SCLK</sub> = 30 MHz	$T_{MIN} \le T_A \le T_{MAX}$		3	mW	
<b>-</b>	Total Power Consumption	output unloaded	V <sub>A</sub> = 4.5 V to 5.5 V	4.85	5	mW	
° <sub>N</sub>	(output unloaded)		$T_{MIN} \le T_A \le T_{MAX}$		7		
		f <sub>SCLK</sub> = 0	V <sub>A</sub> = 2.7 V to 3.6 V	1.68	3	mW	
		output unloaded	V <sub>A</sub> = 4.5 V to 5.5 V	3.80	)	mW	



#### **Electrical Characteristics (continued)**

The following specifications apply for  $V_A = 2.7 \text{ V}$  to 5.5 V,  $V_{REF1} = V_{REF2} = V_A$ ,  $C_L = 200 \text{ pF}$  to GND,  $f_{SCLK} = 30 \text{ MHz}$ , input code range 48 to 4047. All limits are at  $T_A = 25^{\circ}$ C, unless otherwise specified.

	PARAMETER	TEST CON	DITIONS	MIN <sup>(1)</sup>	TYP	MAX <sup>(1)</sup>	UNIT
			V <sub>A</sub> = 2.7 V to 3.6 V		0.6		
			$\begin{array}{l} T_{MIN} \leq T_A \leq \\ T_{MAX} \end{array}$			5.4	μW
			V <sub>A</sub> = 4.5V to 5.5V		2.5		
Р	Total Power Consumption in all PD Modes, (2)		$\begin{array}{l} T_{MIN} \leq T_{A} \leq \\ T_{MAX} \end{array}$			16.5	μW
P <sub>PD</sub>		$f_{SCLK} = 0$ , SYNC = $V_A$ and $D_{IN} = 0V$ after PD mode loaded	V <sub>A</sub> = 2.7 V to 3.6 V		0.3		
			$\begin{array}{l} T_{MIN} \leq T_A \leq \\ T_{MAX} \end{array}$			3.6	μW
			V <sub>A</sub> = 4.5 V to 5.5 V		1		
			$T_{MIN} \le T_A \le T_{MAX}$			11	μW

#### 7.6 AC and Timing Characteristics

The following specifications apply for  $V_A = 2.7$  V to 5.5 V,  $V_{REF1,2} = V_A$ ,  $C_L = 200$  pF to GND,  $f_{SCLK} = 30$  MHz, input code range 48 to 4047. All limits are at  $T_A = 25^{\circ}$ C, unless otherwise specified.

			MIN <sup>(1)</sup>	NOM	MAX <sup>(1)</sup>	UNIT	
4				40		MHz	
f <sub>SCLK</sub>	SCLK Frequency	$T_{MIN} \le T_A \le T_{MAX}$			30	IVITIZ	
t <sub>s</sub>	Output Voltage Settling Time	400h to C00h code change $R_L = 2 k\Omega$ , $C_L = 200 pF$		6		μs	
	· /	$T_{MIN} \le T_A \le T_{MAX}$					
SR	Output Slew Rate			1		V/µs	
GI	Glitch Impulse	Code change from 800h to 7FFh		40		nV-sec	
DF	Digital Feedthrough			0.5		nV-sec	
DC	Digital Crosstalk			0.5		nV-sec	
CROSS	DAC-to-DAC Crosstalk			1		nV-sec	
MBW	Multiplying Bandwidth	V <sub>REF1,2</sub> = 2.5 V ± 2 Vpp		360		kHz	
THD+N	Total Harmonic Distortion Plus Noise	$V_{REF1,2} = 2.5 V \pm 0.5 Vpp$ 100 Hz < f <sub>IN</sub> < 20 kHz		-80		dB	
ONSD	Output Noise Spectral Density	DAC Code = 800 h, 10 kHz		40		nV/sqrt (Hz)	
ON	Output Noise	BW = 30 kHz		14		μV	
		V <sub>A</sub> = 3 V		3		µsec	
t <sub>WU</sub>	Wake-Up Time	V <sub>A</sub> = 5 V	20			µsec	
A //				25			
1/f <sub>SCLK</sub>	SCLK Cycle Time. See Figure 1	$T_{MIN} \le T_A \le T_{MAX}$	33	ns			
				7			
t <sub>CH</sub>	SCLK High time. See Figure 1	$T_{MIN} \le T_A \le T_{MAX}$	10			ns	
				7			
t <sub>CL</sub>	SCLK Low Time. See Figure 1	$T_{MIN} \le T_A \le T_{MAX}$	10	ns			
	SYNC Set-up Time prior to		3 1 / f <sub>SCLK</sub> - 3				
t <sub>SS</sub>	SCLK Falling Edge. See Figure 1	$T_{MIN} \le T_A \le T_{MAX}$	10	ns			

(1) Test limits are ensured to TI's AOQL (Average Outgoing Quality Level).

(2) This parameter is ensured by design and/or characterization and is not tested in production.

Copyright © 2007–2015, Texas Instruments Incorporated

INSTRUMENTS

Texas

## AC and Timing Characteristics (continued)

The following specifications apply for V<sub>A</sub> = 2.7 V to 5.5 V, V<sub>REF1,2</sub> = V<sub>A</sub>, C<sub>L</sub> = 200 pF to GND, f<sub>SCLK</sub> = 30 MHz, input code range 48 to 4047. All limits are at T<sub>A</sub> = 25°C, unless otherwise specified.

			MIN <sup>(1)</sup>	NOM	MAX <sup>(1)</sup>	UNIT	
t <sub>DS</sub>	Data Set-Up Time prior to SCLK		1				
	Falling Edge. See Figure 1	$T_{MIN} \le T_A \le T_{MAX}$	2.5			ns	
t <sub>DH</sub>	Data Hold Time after SCLK Falling Edge. See Figure 1			1			
		$T_{MIN} \le T_A \le T_{MAX}$	2.5			ns	
	SYNC Hold Time after the 16th			0	1 / f <sub>SCLK</sub> - 3		
t <sub>SH</sub>	falling edge of SCLK. See Figure 1	$T_{MIN} \leq T_{A} \leq T_{MAX}$	3			ns	
	OVING Line Time Cas Figure 1			5			
t <sub>SYNC</sub>	SYNC High Time. See Figure 1	$T_{MIN} \le T_A \le T_{MAX}$	15			ns	





Figure 1. Serial Timing Diagram



## 7.7 Typical Characteristics

 $V_{\text{A}}$  = 2.7 V to 5.5 V,  $V_{\text{REF1,2}}$  =  $V_{\text{A}},\,f_{\text{SCLK}}$  = 30 MHz,  $T_{\text{A}}$  = 25°C, unless otherwise stated




DAC128S085 SNAS407H – AUGUST 2007 – REVISED APRIL 2015 TEXAS INSTRUMENTS

www.ti.com


## **Typical Characteristics (continued)**

 $V_A = 2.7$  V to 5.5 V,  $V_{REF1,2} = V_A$ ,  $f_{SCLK} = 30$  MHz,  $T_A = 25^{\circ}$ C, unless otherwise stated






### **Typical Characteristics (continued)**



## **Typical Characteristics (continued)**

 $V_A = 2.7 \text{ V}$  to 5.5 V,  $V_{REF1,2} = V_A$ ,  $f_{SCLK} = 30 \text{ MHz}$ ,  $T_A = 25^{\circ}\text{C}$ , unless otherwise stated






## 8 Detailed Description

#### 8.1 Overview

The DAC128S085 is fabricated on a CMOS process with an architecture that consists of switches and resistor strings followed by an output buffer. The reference voltages are externally applied at  $V_{REF1}$  for DAC channels A through D, and  $V_{REF2}$  for DAC channels E through H.

#### 8.2 Functional Block Diagram



(2)

#### 8.3 Feature Description

#### 8.3.1 DAC Architecture

For simplicity, a single resistor string is shown in Figure 26. This string consists of 4096 equal valued resistors with a switch at each junction of two resistors, plus a switch to ground. The code loaded into the DAC register determines which switch is closed, connecting the proper node to the amplifier. The input coding is straight binary with an ideal output voltage of:

 $V_{OUTA,B,C,D} = V_{REF1} \times (D / 4096)$ 

where

 $V_{OUTE,F,G,H} = V_{REF2} \times (D / 4096)$ 

D can take on any value between 0 and 4095. This configuration ensures that the DAC is monotonic.




Figure 26. DAC Resistor String

Because all eight DAC channels of the DAC128S085 can be controlled independently, each channel consists of a DAC register and a 12-bit DAC. Figure 27 is a simple block diagram of an individual channel in the DAC128S085. Depending on the mode of operation, data written into a DAC register causes the 12-bit DAC output to be updated, or an additional command is required to update the DAC output. Further description of the modes of operation can be found in *Serial Interface*.




Figure 27. Single-Channel Block Diagram



#### Feature Description (continued)

#### 8.3.2 Output Amplifiers

The output amplifiers are rail-to-rail, providing an output voltage range of 0 V to  $V_A$  when the reference is  $V_A$ . All amplifiers, including rail-to-rail types, exhibit a loss of linearity as the output approaches the supply rails (0 V and  $V_A$ , in this case). For this reason, linearity is specified over less than the full output range of the DAC. However, if the reference is less than  $V_A$ , only the lowest codes experience a loss in linearity.

The output amplifiers can drive a load of 2 k $\Omega$  in parallel with 1500 pF to ground or to V<sub>A</sub>. The zero-code and full-scale outputs for given load currents are available in the *Electrical Characteristics*.

#### 8.3.3 Reference Voltage

The DAC128S085 uses dual external references,  $V_{REF1}$  and  $V_{REF2}$ , which are shared by channels A, B, C, D and channels E, F, G, H, respectively. The reference pins are not buffered and have an input impedance of 30 k $\Omega$ . TI recommends driving  $V_{REF1}$  and  $V_{REF2}$  by voltage sources with low output impedance. The reference voltage range is 0.5 V to  $V_A$ , providing the widest possible output dynamic range.

#### 8.3.4 Serial Interface

The three-wire interface is compatible with SPI, QSPI, and MICROWIRE, as well as most DSPs, and operates at clock rates up to 40 MHz. A valid serial frame contains 16 falling edges of SCLK. See Table 1 for information on a write sequence.

A write sequence begins by bringing the SYNC line low. Once SYNC is low, the data on the D<sub>IN</sub> line is clocked into the 16-bit serial input register on the falling edges of SCLK. To avoid mis-clocking data into the shift register, it is critical that SYNC not be brought low on a falling edge of SCLK (see minimum and maximum setup times for SYNC in *AC and Timing Characteristics* and Figure 28). On the 16th falling edge of SCLK, the <u>last data bit</u> is clocked into the register. The write sequence is concluded by bringing the SYNC line high. Once SYNC is high, the programmed function (a change in the DAC channel address, mode of operation, or register contents) is executed. To avoid mis-clocking data into the shift register, it is critical that SYNC be brought high between the 16th and 17th falling edges of SCLK (see minimum and maximum hold times for SYNC in *AC and Timing Characteristics* and Figure 28).




Figure 28. CS Setup and Hold Times

If  $\overline{SYNC}$  is brought high before the 15th falling edge of <u>SCLK</u>, the write sequence is aborted and the data that has been shifted into the input register is discarded. If <u>SYNC</u> is held low beyond the 17th falling edge of SCLK, the serial data presented at D<sub>IN</sub> will begin to be output on D<sub>OUT</sub>. More information on this mode of operation can be found in *Daisy-Chain Operation*. In either case, <u>SYNC</u> must be brought high for the minimum specified time before the next write sequence is initiated with a falling edge of <u>SYNC</u>.

Since the  $D_{IN}$  buffer draws more current when it <u>is high</u>, it should be idled low between write sequences to minimize power consumption. On the other hand, <u>SYNC</u> should be idled high to avoid the activation of daisy chain operation where  $D_{OUT}$  is active.

#### 8.3.5 Daisy-Chain Operation

Daisy-chain operation allows communication with any number of DAC128S085s using a single serial interface. As long as the correct number of data bits are input in a write sequence (multiple of sixteen bits), a rising edge of SYNC will properly update all DACs in the system.



#### Feature Description (continued)

To support multiple devices in a daisy chain configuration, SCLK and  $\overline{SYNC}$  are shared across all DAC128S085s and  $D_{OUT}$  of the first DAC in the chain is connected to  $D_{IN}$  of the second. Figure 29 shows three DAC128S085s connected in daisy chain fashion. Similar to a single channel write sequence, the conversion for a daisy chain operation begins on a falling edge of SYNC and ends on a rising edge of SYNC. A valid write sequence for n devices in a chain requires n times 16 falling edges to shift the entire input data stream through the chain. Daisy chain operation is ensured for a maximum SCLK speed of 30 MHz.




Figure 29. Daisy-Chain Configuration

The serial data output pin,  $D_{OUT}$ , is available on the DAC128S085 to allow daisy-chaining of multiple DAC128S085 devices in a system. In a write sequence,  $D_{OUT}$  remains low for the first 14 falling edges of SCLK before going high on the 15th falling edge. Subsequently, the next 16 falling edges of SCLK will output the first 16 data bits entered into  $D_{IN}$ . Figure 30 shows the timing of 3 DAC128S085s in Figure 29. In this instance, It takes 48 falling edges of SCLK followed by a rising edge of SYNC to load all three DAC128S085s with the appropriate register data. On the rising edge of SYNC, the programmed function is executed in each DAC128S085 simultaneously.

When connecting multiple devices in a daisy-chain configuration, it is important to note that the DAC128S085 will update the  $D_{OUT}$  signal on the falling edge of SCLK, and this will be sampled by the next DAC in the daisy chain on the next falling edge of the clock. Ensure that the timing requirements are met for proper operation. Specifically, pay attention to the data hold time after the SCLK falling ( $t_{DH}$ ) requirement. Improper layout or loading may delay the clock signal between devices. If delayed to the point that data changes prior to meeting the hold time requirement, incorrect data can be sampled. If the clock delay cannot be resolved, an alternative solution is to add a delay between the  $D_{OUT}$  of one device and  $D_{IN}$  of the following device in the daisy chain. This increases the hold time margin and allows for correct sampling. Be aware though, that the tradeoff with this fix is that too much delay eventually impacts the setup time.




Figure 30. Daisy Chain Timing Diagram

#### 8.3.6 DAC Input Data Update Mechanism

The DAC128S085 has two modes of operation, plus a few special command operations. The two modes of operation are Write Register Mode (WRM) and Write Through Mode (WTM). For the rest of this document, these modes will be referred to as WRM and WTM. The special command operations are separate from WRM and WTM because they can be called upon regardless of the current mode of operation. The mode of operation is controlled by the first four bits of the control register, DB15 through DB12. See Table 1 for a detailed summary.



#### Feature Description (continued)

DB[15:12]	DB[11:0]	Description of Mode										
1000	****	WRM: The registers of each DAC Channel can be written to without causing their outputs to change.										
1001	* * * * * * * * * * * * * *	WTM: Writing data to a channel's register causes the DAC output to change.										

#### Table 1. Write Register and Write Through Modes

When the DAC128S085 first powers up, the DAC is in WRM. In WRM, the registers of each individual DAC channel can be written to without updating the DAC outputs. This is accomplished by setting DB15 to 0, specifying the DAC register to be written to in DB[14:12], and entering the new DAC register setting in DB[11:0] (see Table 2). The DAC128S085 remains in WRM until the mode of operation is changed to WTM. The mode of operation is changed from WRM to WTM by setting DB[15:12] to 1001. Once in WTM, writing data to a DAC channel register causes the DAC output to be updated as well. Changing a DAC channel register in WTM is accomplished in the same manner as in WRM. However, in WTM the DAC register and output are updated at the completion of the command (see Table 2). Similarly, the DAC128S085 remains in WTM until the mode of operation is changed to WRM by setting DB[15:12] to 1000.

DB15	DB[14:12]	DB[11:0]	Description of Mode
0	000	D11 D10 D1 D0	WRM: D[11:0] written to ChA's data register only WTM: ChA's output is updated by data in D[11:0]
0	0 0 1	D11 D10 D1 D0	WRM: D[11:0] written to only the data register of ChB WTM: ChB's output is updated by data in D[11:0]
0	010	D11 D10 D1 D0	WRM: D[11:0] written to only the data register of ChC WTM: ChC's output is updated by data in D[11:0]
0	011	D11 D10 D1 D0	WRM: D[11:0] written only the data register of ChD WTM: ChD's output is updated by data in D[11:0]
0	100	D11 D10 D1 D0	WRM: D[11:0] written only the data register of ChE WTM: ChE's output is updated by data in D[11:0]
0	101	D11 D10 D1 D0	WRM: D[11:0] written only the data register of ChF WTM: ChF's output is updated by data in D[11:0]
0	110	D11 D10 D1 D0	WRM: D[11:0] written only the data register of ChG WTM: ChG's output is updated by data in D[11:0]
0	111	D11 D10 D1 D0	WRM: D[11:0] written only the data register of ChH WTM: ChH's output is updated by data in D[11:0]

#### Table 2. Commands Impacted by WRM and WTM

The special command operations can be exercised at any time regardless of the mode of operation. There are three special command operations. The first command is exercised by setting data bits DB[15:12] to 1010. This allows the user to update multiple DAC outputs simultaneously to the values currently loaded in their respective control registers. This command is valuable if the user wants each DAC output to be at a different output voltage, but still have all the DAC outputs changed to their appropriate values simultaneously (see Table 3).

The second special command allows the user to alter the DAC output of channel A with a single write frame. This command is exercised by setting data bits DB[15:12] to 1011 and data bits DB[11:0] to the desired control register value. This command also causes the DAC outputs of the other channels to update to their current control register values. The user may choose to exercise this command to save a write sequence. For example, the user may wish to update several DAC outputs simultaneously, including channel A. To accomplish this task in the minimum number of write frames, the user would alter the control register values of all the DAC channels except channel A while operating in WRM. The last write frame would be used to exercise the special command *Channel A Write Mode*. In addition to updating the control register of channel A and output to a new value, all of the other channels would be updated as well. At the end of this sequence of write frames, the DAC128S085 would still be operating in WRM (see Table 3).

#### TEXAS INSTRUMENTS

#### DAC128S085 SNAS407H-AUGUST 2007-REVISED APRIL 2015

www.ti.com

The third special command allows the user to set all the DAC control registers and outputs to the same level. This command is commonly referred to as "broadcast" mode, as the same data bits are being broadcast to all of the channels simultaneously. This command is exercised by setting data bits DB[15:12] to 1100 and data bits DB[11:0] to the value that the user wishes to broadcast to all the DAC control registers. Once the command is exercised, each DAC output is updated by the new control register value. This command is frequently used to set all the DAC outputs to some known voltage such as 0 V,  $V_{REF}/2$ , or Full Scale. A summary of the commands can be found in Table 3.

DB[15:12]	DB[11:0]	Description of Mode										
1010	X	Update Select: The DAC outputs of the channels selected with a 1 in DB[7:0] are updated simultaneously to the values in their respective control registers.										
1011	1011       D11 D10 D1 D0       Channel A Write: The control register and DAC output updated to the data in DB[11:0]. The outputs of the oth also updated according to their respective control register											
1100	D11 D10 D1 D0	Broadcast: The data in DB[11:0] is written to all channel control registers and DAC output simultaneously.										

#### **Table 3. Special Command Operations**

#### 8.3.7 Power-On Reset

The power-on reset circuit controls the output voltages of the eight DACs during power-up. Upon application of power, the DAC registers are filled with zeros and the output voltages are set to 0 V. The outputs remain at 0 V until a valid write sequence is made.

#### 8.3.8 Transfer Characteristic




Figure 31. Input / Output Transfer Characteristic

#### 8.4 Device Functional Modes

#### 8.4.1 Power-Down Modes

The DAC128S085 has three power-down modes, where different output terminations can be selected (see Table 4). With all channels powered down, the supply current drops to 0.1  $\mu$ A at 3 V and 0.2  $\mu$ A at 5 V. By selecting the channels to be powered down in DB[7:0] with a 1, individual channels can be powered down separately, or multiple channels can be powered down simultaneously. The three different output terminations include high output impedance, 100 k $\Omega$  to ground, and 2.5 k $\Omega$  to ground.



#### **Device Functional Modes (continued)**

The output amplifiers, resistor strings, and other linear circuitry are all shut down in any of the power-down modes. The bias generator, however, is only shut down if all the channels are placed in power-down mode. The contents of the DAC registers are unaffected when in power-down. Therefore, each DAC register maintains its value prior to the DAC128S085 being powered down unless it is changed during the write sequence that instructed it to recover from power down. Minimum power consumption is achieved in the power-down mode with SYNC idled high,  $D_{IN}$  idled low, and SCLK disabled. The time to exit power-down (Wake-Up Time) is typically 3 µsec at 3 V and 20 µsec at 5 V.

DB[15:12]	DB[11:8]	7	6	5	4	3	2	1	0	Output Impedance
1101	ХХХХ	Н	G	F	Е	D	С	В	А	Hi-Z outputs
1110	ХХХХ	Н	G	F	Е	D	С	В	А	100 kΩ outputs
1111	хххх	Н	G	F	Е	D	С	В	А	2.5 kΩ outputs

#### 8.5 Programming

#### 8.5.1 Programming the DAC128S085

This section presents the step-by-step instructions for programming the serial input register.

#### 8.5.1.1 Updating DAC Outputs Simultaneously

When the DAC128S085 is first powered on, the DAC is operating in Write Register Mode (WRM). Operating in WRM allows the user to program the registers of multiple DAC channels without causing the DAC outputs to be updated. For example, below are the steps for setting Channel A to a full scale output, Channel B to threequarters full scale, Channel C to half-scale, Channel D to one-quarter full scale and having all the DAC outputs update simultaneously.

As stated previously, the DAC128S085 powers up in WRM. If the device was previously operating in Write Through Mode (WTM), an extra step to set the DAC into WRM is required. First, the DAC registers must be programmed to the desired values. To set Channel A to an output of full scale, write 0FFF to the control register. This updates the data register for Channel A without updating the output of Channel A. Second, set Channel B to an output of three-quarters full scale by writing 1C00 to the control register. This updates the data register for Channel B and Channel A are not updated, because the DAC is operating in WRM. Third, set Channel C to half scale by writing 2800 to the control register. Fourth, set Channel D to one-quarter full scale by writing 3400 to the control register. Finally, update all four DAC channels simultaneously by writing A00F to the control register. This procedure allows the user to update four channels simultaneously with five steps.

Because Channel A was one of the DACs to be updated, one command step could have been saved by writing to Channel A last. Do this by writing to Channel B, C, and D first, and using the the special command Channel A Write to update the DAC register and output of Channel A. This special command also updates all DAC outputs while updating Channel A. With this sequence of commands, the user can update four channels simultaneously using four steps. A summary of this command can be found in Table 3.

#### 8.5.1.2 Updating DAC Outputs Independently

If the DAC128S085 is currently operating in WRM, change the mode of operation to WTM by writing 9XXX to the control register. Once the DAC is operating in WTM, any DAC channel can be updated in one step. For example, if a design required Channel G to be set to half scale, the user can write 6800 to the control register to update the data register and DAC output of Channel G. Similarly, write 5FFF to the control register to set the output of Channel F to full scale. Channel A is the only channel that has a special command that allows its DAC output to be updated in one command, regardless of the mode of operation. Write BFFF to the control register to set the DAC output of Channel A to full scale in one step.

TEXAS INSTRUMENTS

www.ti.com

### 9 Application and Implementation

#### NOTE

Information in the following applications sections is not part of the TI component specification, and TI does not warrant its accuracy or completeness. TI's customers are responsible for determining suitability of components for their purposes. Customers should validate and test their design implementation to confirm system functionality.

#### 9.1 Application Information

#### 9.1.1 Using References as Power Supplies

While the simplicity of the DAC128S085 implies ease of use, it is important to recognize that the path from the reference input ( $V_{REF1,2}$ ) to the DAC outputs has a zero Power Supply Rejection Ratio (PSRR). Therefore, the user must provide a noise-free supply voltage to  $V_{REF1,2}$ . To utilize the full dynamic range of the DAC128S085, the supply pin ( $V_A$ ) and  $V_{REF1,2}$  can be connected together and share the same supply voltage. Because the DAC128S085 consumes very little power, a reference source can be used as the reference input or the supply voltage. The advantages of using a reference source over a voltage regulator are accuracy and stability. Some low-noise regulators can also be used. Listed below are a few reference and power supply options for the DAC128S085.

#### 9.2 Typical Application

The LM4132, with its ±0.05% accuracy over temperature, is a good choice as a reference source for the DAC128S085. The 4.096-V version is useful for a 0-V to 4.095-V output range. Bypassing the LM4132 voltage input pin with a 4.7-µF capacitor and the voltage output pin with a 4.7-µF capacitor improves stability and reduces output noise. The LM4132 comes in a space-saving 5-pin SOT-23.




Figure 32. The LM4132 as a Power Supply

#### 9.2.1 Design Requirements

There are two references for the DAC128S085. One reference input serves channels A through D, while the other reference serves channels E through H. The 16-bit input shift register of the DAC128S085 controls the mode of operation, the power-down condition, and the register/output value of the DAC channels. All eight DAC outputs can be updated simultaneously or individually.

#### 9.2.2 Detailed Design Procedure

Each reference input pin can be set independently, or the reference pins can be shorted together as shown in Figure 32. Acceptable reference voltages are 0.5 V to  $V_A$ . Utilizing an RC filter on the output to roll off output noise is optional.



## **Typical Application (continued)**

### 9.2.3 Application Curve




Figure 33. Typical Performance

## **10** Power Supply Recommendations

For best performance, the DAC128S085 power supply should be bypassed with at least a 1- $\mu$ F and a 0.1- $\mu$ F capacitor. The 0.1- $\mu$ F capacitor must be placed right at the device supply pin. The 1- $\mu$ F or larger valued capacitor can be a tantalum capacitor, while the 0.1- $\mu$ F capacitor must be a ceramic capacitor with low ESL and low ESR. If a ceramic capacitor with low ESL and low ESR is used for the 1- $\mu$ F value and can be placed right at the supply pin, the 0.1- $\mu$ F capacitor can be eliminated. Capacitors of this nature typically span the same frequency spectrum as the 0.1- $\mu$ F capacitor, and thus eliminate the need for the extra capacitor. The power supply for the DAC128S085 should only be used for analog circuits.

Avoid the crossover of analog and digital signals. This helps minimize the amount of noise from the transitions of the digital signals from coupling onto the sensitive analog signals, such as the reference pins and the DAC outputs.

## 11 Layout

#### 11.1 Layout Guidelines

For best accuracy and minimum noise, the printed circuit board containing the DAC128S085 should have separate analog and digital areas. The areas are defined by the locations of the analog and digital power planes. Both of these planes should be located in the same board layer. A single ground plane is preferred if digital return current does not flow through the analog ground area. Frequently a single ground plane design will utilize a "fencing" technique to prevent the mixing of analog and digital ground current. Separate ground planes should only be utilized when the fencing technique is inadequate. The separate ground planes must be connected in one place, preferably near the DAC128S085. Ensure that digital signals with fast edge rates do not pass over split ground planes. The signals must always have a continuous return path below their traces.

DAC128S085

SNAS407H-AUGUST 2007-REVISED APRIL 2015



www.ti.com

## 11.2 Layout Example




Figure 34. Layout Example



## **12 Device and Documentation Support**

#### 12.1 Device Support

#### 12.1.1 Specification Definitions

- **DIFFERENTIAL NON-LINEARITY (DNL)** is the measure of the maximum deviation from the ideal step size of 1 LSB, which is  $V_{REF} / 4096 = V_A / 4096$ .
- **DAC-to-DAC CROSSTALK** is the glitch impulse transferred to a DAC output in response to a full-scale change in the output of another DAC.
- **DIGITAL CROSSTALK** is the glitch impulse transferred to a DAC output at mid-scale in response to a full-scale change in the input register of another DAC.
- **DIGITAL FEEDTHROUGH** is a measure of the energy injected into the analog output of the DAC from the digital inputs when the DAC outputs are not updated. It is measured with a full-scale code change on the data bus.
- **FULL-SCALE ERROR** is the difference between the actual output voltage with a full scale code (FFFh) loaded into the DAC and the value of V<sub>A</sub> x 4095 / 4096.
- **GAIN ERROR** is the deviation from the ideal slope of the transfer function. It can be calculated from Zero and Full-Scale Errors as GE = FSE ZE, where GE is Gain error, FSE is Full-Scale Error and ZE is Zero Error.
- **GLITCH IMPULSE** is the energy injected into the analog output when the input code to the DAC register changes. It is specified as the area of the glitch in nanovolt-seconds.
- **INTEGRAL NON-LINEARITY (INL)** is a measure of the deviation of each individual code from a straight line through the input to output transfer function. The deviation of any given code from this straight line is measured from the center of that code value. The end point method is used. INL for this product is specified over a limited range, per the Electrical Tables.
- LEAST SIGNIFICANT BIT (LSB) is the bit that has the smallest value or weight of all bits in a word. This value

 $LSB = V_{REF} / 2^n$ 

where

is

 V<sub>REF</sub> is the supply voltage for this product, and n is the DAC resolution in bits, which is 12 for the DAC128S085.

(3)

- **MAXIMUM LOAD CAPACITANCE** is the maximum capacitance that can be driven by the DAC with output stability maintained.
- **MONOTONICITY** is the condition of being monotonic, where the DAC has an output that never decreases when the input code increases.
- **MOST SIGNIFICANT BIT (MSB)** is the bit that has the largest value or weight of all bits in a word. Its value is 1/2 of V<sub>A</sub>.
- **MULTIPLYING BANDWIDTH** is the frequency at which the output amplitude falls 3 dB below the input sine wave on V<sub>REF1,2</sub> with the DAC code at full-scale.
- **NOISE SPECTRAL DENSITY** is the internally generated random noise. It is measured by loading the DAC to mid-scale and measuring the noise at the output.
- **POWER EFFICIENCY** is the ratio of the output current to the total supply current. The output current comes from the power supply. The difference between the supply and output currents is the power consumed by the device without a load.
- **SETTLING TIME** is the time for the output to settle to within 1/2 LSB of the final value after the input code is updated.
- **TOTAL HARMONIC DISTORTION PLUS NOISE (THD+N)** is the ratio of the harmonics plus the noise present at the output of the DACs to the rms level of an ideal sine wave applied to V<sub>REF1,2</sub> with the DAC code at mid-scale.

Copyright © 2007–2015, Texas Instruments Incorporated



## **Device Support (continued)**

**WAKE-UP TIME** is the time for the output to exit power-down mode. This is the time from the rising edge of SYNC to when the output voltage deviates from the power-down voltage of 0 V.

**ZERO CODE ERROR** is the output error, or voltage, present at the DAC output after a code of 000h has been entered.

#### **12.2 Documentation Support**

#### 12.2.1 Related Documentation

LM4132 SOT-23 Precision Low Dropout Voltage Reference, SNVS372

#### 12.3 Trademarks

SPI is a trademark of Motorola, Inc.. All other trademarks are the property of their respective owners.

#### 12.4 Electrostatic Discharge Caution



These devices have limited built-in ESD protection. The leads should be shorted together or the device placed in conductive foam during storage or handling to prevent electrostatic damage to the MOS gates.

#### 12.5 Glossary

SLYZ022 — TI Glossary.

This glossary lists and explains terms, acronyms, and definitions.

## 13 Mechanical, Packaging, and Orderable Information

The following pages include mechanical, packaging, and orderable information. This information is the most current data available for the designated devices. This data is subject to change without notice and revision of this document. For browser-based versions of this data sheet, refer to the left-hand navigation.



## PACKAGING INFORMATION

Orderable Device	Status (1)	Package Type	Package Drawing	Pins	Package Qty	Eco Plan (2)	Lead finish/ Ball material	MSL Peak Temp (3)	Op Temp (°C)	Device Marking (4/5)	Samples
							(6)				
DAC128S085CIMT/NOPB	ACTIVE	TSSOP	PW	16	92	RoHS & Green	SN	Level-1-260C-UNLIM	-40 to 125	X78C	Samples
DAC128S085CIMTX/NOPB	ACTIVE	TSSOP	PW	16	2500	RoHS & Green	SN	Level-1-260C-UNLIM	-40 to 125	X78C	Samples
DAC128S085CISQ/NOPB	ACTIVE	WQFN	RGH	16	1000	RoHS & Green	SN	Level-1-260C-UNLIM	-40 to 125	128S085	Samples
DAC128S085CISQX/NOPB	ACTIVE	WQFN	RGH	16	4500	RoHS & Green	SN	Level-1-260C-UNLIM	-40 to 125	128S085	Samples

<sup>(1)</sup> The marketing status values are defined as follows:

ACTIVE: Product device recommended for new designs.

LIFEBUY: TI has announced that the device will be discontinued, and a lifetime-buy period is in effect.

NRND: Not recommended for new designs. Device is in production to support existing customers, but TI does not recommend using this part in a new design.

**PREVIEW:** Device has been announced but is not in production. Samples may or may not be available.

**OBSOLETE:** TI has discontinued the production of the device.

<sup>(2)</sup> RoHS: TI defines "RoHS" to mean semiconductor products that are compliant with the current EU RoHS requirements for all 10 RoHS substances, including the requirement that RoHS substance do not exceed 0.1% by weight in homogeneous materials. Where designed to be soldered at high temperatures, "RoHS" products are suitable for use in specified lead-free processes. TI may reference these types of products as "Pb-Free".

**RoHS Exempt:** TI defines "RoHS Exempt" to mean products that contain lead but are compliant with EU RoHS pursuant to a specific EU RoHS exemption.

Green: TI defines "Green" to mean the content of Chlorine (CI) and Bromine (Br) based flame retardants meet JS709B low halogen requirements of <=1000ppm threshold. Antimony trioxide based flame retardants must also meet the <=1000ppm threshold requirement.

<sup>(3)</sup> MSL, Peak Temp. - The Moisture Sensitivity Level rating according to the JEDEC industry standard classifications, and peak solder temperature.

<sup>(4)</sup> There may be additional marking, which relates to the logo, the lot trace code information, or the environmental category on the device.

<sup>(5)</sup> Multiple Device Markings will be inside parentheses. Only one Device Marking contained in parentheses and separated by a "~" will appear on a device. If a line is indented then it is a continuation of the previous line and the two combined represent the entire Device Marking for that device.

<sup>(6)</sup> Lead finish/Ball material - Orderable Devices may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead finish/Ball material values may wrap to two lines if the finish value exceeds the maximum column width.

Important Information and Disclaimer: The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and



10-Dec-2020

continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.



Texas

STRUMENTS

## TAPE AND REEL INFORMATION





#### QUADRANT ASSIGNMENTS FOR PIN 1 ORIENTATION IN TAPE




*All dimensions are nominal												
Device	Package Type	Package Drawing		SPQ	Reel Diameter (mm)	Reel Width W1 (mm)	A0 (mm)	B0 (mm)	K0 (mm)	P1 (mm)	W (mm)	Pin1 Quadrant
DAC128S085CIMTX/ NOPB	TSSOP	PW	16	2500	330.0	12.4	6.95	5.6	1.6	8.0	12.0	Q1
DAC128S085CISQ/NOPB	WQFN	RGH	16	1000	178.0	12.4	4.3	4.3	1.3	8.0	12.0	Q1
DAC128S085CISQX/ NOPB	WQFN	RGH	16	4500	330.0	12.4	4.3	4.3	1.3	8.0	12.0	Q1



## PACKAGE MATERIALS INFORMATION

9-Aug-2022



\*All dimensions are nominal


Device	Package Type	Package Drawing	Pins	SPQ	Length (mm)	Width (mm)	Height (mm)
DAC128S085CIMTX/ NOPB	TSSOP	PW	16	2500	367.0	367.0	35.0
DAC128S085CISQ/NOPB	WQFN	RGH	16	1000	210.0	185.0	35.0
DAC128S085CISQX/ NOPB	WQFN	RGH	16	4500	367.0	367.0	35.0

## TEXAS INSTRUMENTS

www.ti.com

9-Aug-2022

## TUBE




## - B - Alignment groove width

\*All dimensions are nominal

Device	Package Name	Package Type	Pins	SPQ	L (mm)	W (mm)	Τ (μm)	B (mm)
DAC128S085CIMT/NOPB	PW	TSSOP	16	92	495	8	2514.6	4.06

## **MECHANICAL DATA**



Complies to JEDEC MO-220 variation WGGD-4.



# **PW0016A**



## **PACKAGE OUTLINE**

## TSSOP - 1.2 mm max height

SMALL OUTLINE PACKAGE



NOTES:

- 1. All linear dimensions are in millimeters. Any dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M. 2. This drawing is subject to change without notice. 3. This dimension does not include mold flash, protrusions, or gate burrs. Mold flash, protrusions, or gate burrs shall not
- exceed 0.15 mm per side.
- 4. This dimension does not include interlead flash. Interlead flash shall not exceed 0.25 mm per side.
- 5. Reference JEDEC registration MO-153.



## PW0016A

# **EXAMPLE BOARD LAYOUT**

## TSSOP - 1.2 mm max height

SMALL OUTLINE PACKAGE



NOTES: (continued)

6. Publication IPC-7351 may have alternate designs.

7. Solder mask tolerances between and around signal pads can vary based on board fabrication site.



## PW0016A

# **EXAMPLE STENCIL DESIGN**

## TSSOP - 1.2 mm max height

SMALL OUTLINE PACKAGE



NOTES: (continued)

9. Board assembly site may have different recommendations for stencil design.



<sup>8.</sup> Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.

## IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATA SHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, regulatory or other requirements.

These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you will fully indemnify TI and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to TI's Terms of Sale or other applicable terms available either on ti.com or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products.

TI objects to and rejects any additional or different terms you may have proposed.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265 Copyright © 2022, Texas Instruments Incorporated