

SNWS009B - MARCH 2003 - REVISED APRIL 2013

# LMX2522/LMX2532 PLLatinum<sup>™</sup> Frequency Synthesizer System with Integrated VCOs

Check for Samples: LMX2522, LMX2532

# **FEATURES**

- Small Size
  - Small 5.0 mm x 5.0 mm x 0.75 mm 28-Pin WQFN Package
- **RF/GPS Synthesizer System** 
  - Integrated RF VCO
  - Integrated GPS VCO
  - Integrated Loop Filter
  - Low Spurious, Low Phase Noise Fractional-N RF PLL Based on 11-bit Delta Sigma Modulator
  - 10 kHz Frequency Resolution
- IF Synthesizer System
  - Integer-N IF PLL
  - Programmable Charge Pump Current Levels
  - Programmable Frequencies
- Supports Various Reference Oscillator Frequencies
  - 19.20/19.68 MHz
- Fast Lock Time: 500 µs
- Low Current Consumption
  - 17 mA at 2.8 V
- 2.7 V to 3.3 V Operation
- **Digital Filtered Lock Detect Output**
- Hardware and Software Power Down Control

# **APPLICATIONS**

- Korean PCS CDMA Systems with GPS
- Korean Cellular CDMA Systems with GPS

## DESCRIPTION

LMX2522 and LMX2532 are highly integrated, high performance, low power frequency synthesizer systems optimized for Korean PCS (K-PCS) with GPS and Korean Cellular (K-Cellular) with GPS, CDMA (1xRTT, IS-95) mobile handsets. Using a proprietary digital phase locked loop technique, LMX2522 and LMX2532 generate very stable, low noise local oscillator signals for up and down conversion in wireless communications devices.

LMX2522 and LMX2532 include a RF voltage controlled oscillator (VCO), a GPS VCO, a loop filter, and a fractional-N RF PLL based on a delta sigma modulator. In concert these blocks form a closed loop RF and GPS synthesizer system. LMX2522 supports the Korean PCS band with GPS and LMX2532 supports the Korean Cellular band with GPS.

LMX2522 and LMX2532 include an Integer-N IF PLL also. For more flexible loop filter designs, the IF PLL includes a 4-level programmable charge pump. Together with an external VCO and loop filter, LMX2522 and LMX2532 make a complete closed loop IF synthesizer system.

Serial data is transferred to the device via a threewire MICROWIRE interface (DATA, LE, CLK).

Operating supply voltage ranges from 2.7 V to 3.3 V. LMX2502 and LMX2512 feature low current consumption: 17 mA at 2.8 V.

LMX2522 and LMX2532 are available in a 28-pin WQFN package.




Please be aware that an important notice concerning availability, standard warranty, and use in critical applications of Texas Instruments semiconductor products and disclaimers thereto appears at the end of this data sheet. PLLatinum is a trademark of Texas Instruments.


All other trademarks are the property of their respective owners.



## Functional Block Diagram



## **Connection Diagram**



NOTE: Analog ground connected through exposed die attached pad.

Figure 1. 28-Pin WQFN (NJB) Package

3

Submit Documentation Feedback

www.ti.com

	PIN DESCRIPTIONS					
Pin Number	Name	I/O	Description			
1	CPout	0	IF PLL charge pump output			
2	NC	—	Do not connect to any node on printed circuit board.			
3	NC	_	Do not connect to any node on printed circuit board.			
4	V <sub>DD</sub>	—	Supply voltage for IF analog circuitry			
5	LE	I	MICROWIRE Latch Enable			
6	CLK	I	MICROWIRE Clock			
7	DATA	I	MICROWIRE Data			
8	V <sub>DD</sub>	_	Supply voltage for VCOs			
9	NC	_	Do not connect to any node on printed circuit board.			
10	NC	—	Do not connect to any node on printed circuit board.			
11	NC	—	Do not connect to any node on printed circuit board.			
12	NC	—	Do not connect to any node on printed circuit board.			
13	V <sub>DD</sub>	—	Supply voltage for VCOs			
14	V <sub>DD</sub>	_	Supply voltage for VCOs output buffer			
15	RFout	0	Buffered VCO output			
16	V <sub>CC</sub>	—	Supply voltage for RF prescaler			
17	V <sub>CC</sub>	_	Supply voltage for charge pump			
18	V <sub>CC</sub>	_	Supply voltage for RF digital circuitry			
19	LD	0	Lock Detect			
20	CE	I	Chip Enable control pin			
21	GND	—	Ground for digital circuitry			
22	OSCin	I	Reference frequency input			
23	V <sub>CC</sub>	_	Supply voltage for reference input buffer			
24	GND	_	Ground for digital circuitry			
25	V <sub>CC</sub>	_	Supply voltage for IF digital circuitry			
26	Fin	I	IF buffer/prescaler input			
27	V <sub>CC</sub>	_	Supply voltage for IF buffer/prescaler			
28	NC	_	Do not connect to any node on printed circuit board.			

# 

# LMX2522, LMX2532

SNWS009B-MARCH 2003-REVISED APRIL 2013



www.ti.com



These devices have limited built-in ESD protection. The leads should be shorted together or the device placed in conductive foam during storage or handling to prevent electrostatic damage to the MOS gates.

## Absolute Maximum Ratings<sup>(1)(2)(3)</sup>

Parameter	Symbol	Ratings	Units
Supply Voltage	V <sub>CC</sub> , V <sub>DD</sub>	-0.3 to 3.6	V
Voltage on any pin	VI	-0. 3 to V <sub>DD</sub> +0.3	V
to GND		-0. 3 to V <sub>CC</sub> +0.3	V
Storage Temperature Range	T <sub>STG</sub>	-65 to 150	°C

(1) Absolute Maximum Ratings indicate limits beyond which damage to the device may occur. Recommended Operating Conditions indicate conditions for which the device is intended to be functional, but do not ensure specific performance limits. For ensured specifications and test conditions, refer to the Electrical Characteristics section. The ensured specifications apply only for the conditions listed.

(2) This device is a high performance RF integrated circuit with an ESD rating < 2 kV and is ESD sensitive. Handling and assembly of this

device should be done at ESD protected work stations.

(3) GND = 0 V.

#### **Recommended Operating Conditions**

Parameter	Symbol	Min	Тур	Мах	Units
Ambient Temperature	T <sub>A</sub>	-30	25	85	°C
Supply Voltage (to GND)	V <sub>CC</sub> , V <sub>DD</sub>	2.7		3.3	V

## **Electrical Characteristics**

 $(V_{CC} = V_{DD} = 2.8 \text{ V}, T_A = 25 \text{ °C}; \text{ unless otherwise noted.})$ 

Symbol	Parameter	Conditions	Min	Тур	Max	Units
ICC PARAM	NETERS	i				
I <sub>CC</sub> + I <sub>DD</sub>	Total Supply Current	OB_CRL [1:0] = 00		17	19	mA
(I <sub>CC</sub> + I <sub>DD)RF</sub>	RF PLL Total Supply Current	OB_CRL [1:0] = 00		16	18	mA
I <sub>PD</sub>	Power Down Current <sup>(1)</sup>	CE = Low or RF_EN = 0 IF_EN = 0			20	μA
REFEREN	CE OSCILLATOR			•	*	*
f <sub>OSCin</sub>	Reference Oscillator Input Frequency	19.20 MHz and 19.68 MHz are supported	19.20		19.68	MHz
V <sub>OSCin</sub>	Reference Oscillator Input sensitivity			0.2	V <sub>CC</sub>	V <sub>P-P</sub>

(1) In power down mode, set DATA, CLK and LE pins to 0 V (GND).

(2) The reference frequency must also be programmed using the OSC\_FREQ control bit. For other reference frequencies, please contact Texas Instruments.



#### www.ti.com

### **Electrical Characteristics (continued)**

(V<sub>CC</sub> = V<sub>DD</sub> = 2.8 V, T<sub>A</sub> = 25 °C; unless otherwise noted.)

Symbol	Parameter		Conditions	Min	Тур	Max	Units
RF VCO	i.						
f <sub>RFout</sub>	Frequency Range (3)	LMX2522LQ1635	RF VCO	1619.62		1649.62	MHz
		LMX2532LQ0967		954.42		979.35	MHz
		LMX2532LQ1065		1052.64		1077.57	MHz
P <sub>RFout</sub>	RF Output Power	OB_CRL [1:0] = 11		-2	1	4	dBm
		OB_CRL [1:0] = 10		-5	-2	1	dBm
		OB_CRL [1:0] = 01		-7	-4	-1	dBm
		OB_CRL [1:0] = 00		-9	-6	-3	dBm
	Lock Time <sup>(4)</sup>	LMX2522LQ1635	30 MHz Band for RF PLL		500	800	μs
		LMX2532LQ0967	25 MHz Band for RF PLL		500	800	μs
		LMX2532LQ1065	25 MHz Band for RF PLL		500	800	μs
	Reference Spurs					-75	dBc
	RMS Phase Error	RF PLL in all band			1.3		degrees
L(f)	Phase Noise	LMX2522LQ1635	@100 kHz offset		-113	-112	dBc/Hz
			@1.25 MHz offset		-138	-136	dBc/Hz
		LMX2532LQ0967	@100 kHz offset		-117	-115	dBc/Hz
			@900 kHz offset		-139	-138	dBc/Hz
		LMX2532LQ1065	@100 kHz offset		-117	-115	dBc/Hz
			@900kHz offset		-139	-138	dBc/Hz
	2nd Harmonic Suppres	sion				-25	dBc
	3rd Harmonic Suppress	sion				-20	dBc
GPS VCO							
f <sub>RFout</sub>	Operating Frequency	LMX2522LQ1635	GPS VCO		1355.04		MHz
		LMX2532LQ0967			1490.04		MHz
		LMX2532LQ1065			1391.82		MHz
PRFout	Output Power		OB_CRL [1:0] = 11	-2	1	4	dBm
			OB_CRL [1:0] = 10	-5	-2	1	dBm
			OB_CRL [1:0] = 01	-7	-4	-1	dBm
			OB_CRL [1:0] = 00	-9	-6	-3	dBm
	Lock Time (4)		From RF to GPS PLL		600	800	μs
	Reference Spurs					-75	dBc
	RMS Phase Error		RF PLL in all band		1.3		degrees
L(f)	Phase Noise		@100 kHz offset		-113	-112	dBc/Hz
			@1.25 MHz offset		-138	-136	dBc/Hz
	2nd Harmonic Suppres	sion				-25	dBc
	3rd Harmonic Suppres	sion				-20	dBc

(3) For other frequency ranges, please contact Texas Instruments.
(4) Lock time is defined as the time difference between the beginning of the frequency transition and the point at which the frequency remains within +/- 1 kHz of the final frequency.



www.ti.com


# **Electrical Characteristics (continued)**

(V<sub>CC</sub> = V<sub>DD</sub> = 2.8 V, T<sub>A</sub> = 25 °C; unless otherwise noted.)

Symbol	Parameter		Conditions	Min	Тур	Max	Units
IF PLL	ł		L				
f <sub>Fin</sub>	Operating Frequency	LMX2522LQ1635	IF_FREQ [1:0] = 10, Default Value		440.76		MHz
		LMX2532LQ0967	IF_FREQ [1:0] = 00, Default Value		170.76		MHz
		LMX2532LQ1065	IF_FREQ [1:0] = 01, Default Value		367.20		MHz
p <sub>Fin</sub>	IF Input Sensitivity			-10		0	dBm
f <sub>ΦIF</sub>	Phase Detector Freque	ncy			120		kHz
I <sub>CPout</sub>	Charge Pump Current		IF_CUR [1:0] = 00		100		μA
			IF_CUR [1:0] = 01		200		μA
			IF_CUR [1:0] = 10		300		μA
			IF_CUR [1:0] = 11		800		μA
DIGITAL I	NTERFACE (DATA, CLK,	LE, LD, CE)			<b>T</b>	<u>.</u>	
V <sub>IH</sub> High-Level Input Voltage		e		0.8 V <sub>DD</sub>		V <sub>DD</sub>	V
				0.8 V <sub>CC</sub>		V <sub>CC</sub>	V
V <sub>IL</sub>	Low-Level Input Voltage			0		0.2 V <sub>DD</sub>	V
				0		$0.2 V_{CC}$	V
I <sub>IH</sub>	High-Level Input Current			-10		10	μA
I <sub>IL</sub>	Low-Level Input Curren	t		-10		10	μA
	Input Capacitance				3		pF
V <sub>OH</sub>	High-Level Output Volta	age		0.9 V <sub>DD</sub>			V
				0.9 V <sub>CC</sub>			V
V <sub>OL</sub>	Low-Level Output Volta	ige				0.1 V <sub>DD</sub>	V
						0.1 V <sub>CC</sub>	V
	Output Capacitance					5	pF
MICROWI	RE INTERFACE TIMING						
t <sub>CS</sub>	Data to Clock Set Up T	ime		50			ns
t <sub>CH</sub>	Data to Clock Hold Tim	e		10			ns
t <sub>CWH</sub>	Clock Pulse Width High	1		50			ns
t <sub>CWL</sub>	Clock Pulse Width Low			50			ns
t <sub>ES</sub>	Clock to Latch Enable S	Set Up Time		50			ns
t <sub>EW</sub>	Latch Enable Pulse Wie	dth		50			ns

(5) Frequencies other that the default value can be programmed using Words R4 and R5. See Programming Description for details.

# Serial Data Input Timing



6



SNWS009B - MARCH 2003 - REVISED APRIL 2013

## **FUNCTIONAL DESCRIPTION**

### **GENERAL DESCRIPTION**

LMX2522/32 is a highly integrated frequency synthesizer system that generates LO signals for PCS, Cellular CDMA and GPS systems. These devices include all of the functional blocks of a PLL, RF VCO, prescaler, RF phase detector, and loop filter. The need for external components is limited to a few passive elements for matching the output impedance and bypass elements for power line stabilization.

In addition to the RF circuitry, the IC also includes IF frequency dividers, and an IF phase detector to complete the IF synthesis with an external VCO and loop filter. Table 4 summarizes the counter values to generate the default IF frequencies.

Using a low spurious fractional-N synthesizer based on a delta sigma modulator, the circuit can support 10 kHz channel spacing for PCS, Cellular CDMA and GPS systems.

The fractional-N synthesizer enables faster lock time, which reduces power consumption and system set-up time. Additionally, the loop filter occupies a smaller area as opposed to the integer-N architecture. This allows the loop filter to be embedded into the circuit, minimizing the external noise coupling and total form factor. The delta sigma architecture delivers very low spurious, which can be a significant problem for other PLL solutions.

The circuit also supports commonly used reference frequencies of 19.20 MHz and 19.68 MHz.

## FREQUENCY GENERATION

#### **RF-PLL Section**

The divide ratio can be calculated using the following equation:

LMX2522 – PCS CDMA:

 $f_{VCO} = \{8 \text{ x RF}_B + RF_A + (RF_FN / f_{OSC}) \text{ x } 10^4\} \text{ x } f_{OSC}$ 

where

• (RF\_A < RF\_B)

LMX2532 - Cellular CDMA:

 $f_{VCO} = \{6 \text{ x RF}_B + RF_A + (RF_FN / f_{OSC}) \text{ x } 10^4\} \text{ x } f_{OSC}$ 

where

- (RF\_A < RF\_B)
- f<sub>VCO</sub>: Output frequency of voltage controlled oscillator (VCO)
- RF\_B: Preset divide ratio of binary 4-bit programmable counter (2 ≤ RF\_B ≤ 15)
- RF\_A: Preset divide ratio of binary 3-bit swallow counter (0 ≤ RF\_A ≤ 7 for LMX2522 or 0 ≤ RF\_A ≤ 5 for LMX2532)
- RF\_FN: Preset numerator of binary 11-bit modulus counter (0 ≤ RF\_FN < 1920 for f<sub>OSC</sub> = 19.20 MHz or 0 ≤ RF\_FN < 1968 for f<sub>OSC</sub> = 19.68 MHz)
- f<sub>OSC</sub>: Reference oscillator frequency

# LMX2522, LMX2532

SNWS009B-MARCH 2003-REVISED APRIL 2013

## **GPS-PLL SECTION**

The divide ratio can be calculated using the following equation:

LMX2522 – PCS CDMA:

 $f_{VCO} = \{6 \text{ x RF}_B + RF_A + (RF_FN / f_{OSC}) \text{ x } 10^4\} \text{ x } f_{OSC}$ 

where

• (RF\_A < RF\_B)

LMX2532 - Cellular CDMA:

 $f_{VCO} = \{8 \text{ x RF}_B + RF_A + (RF_FN / f_{OSC}) \text{ x } 10^4\} \text{ x } f_{OSC}$ 

where

- (RF\_A < RF\_B)
- f<sub>VCO</sub>: Output frequency of voltage controlled oscillator (VCO)
- RF\_B: Preset divide ratio of binary 4-bit programmable counter ( $2 \le RF_B \le 15$ )
- RF\_A: Preset divide ratio of binary 3-bit swallow counter (0 ≤ RF\_A ≤ 5 for LMX2522 or 0 ≤ RF\_A ≤ 7 for LMX2532)
- RF\_FN: Preset numerator of binary 11-bit modulus counter (0 ≤ RF\_FN < 1920 for f<sub>OSC</sub> = 19.20 MHz or 0 ≤ RF\_FN < 1968 for f<sub>OSC</sub> = 19.68 MHz)
- f<sub>OSC</sub>: Reference oscillator frequency

PCS CDMA applications using the LMX2522, if the GPS frequency is 1355.04 MHz, Table 1 provides the proper register settings:

#### Table 1. Settings for GPS (1355.04 MHz) in LMX2522 PCS CDMA application

Reference Frequency	RF_B	RF_A	RF_FN
19.20 MHz	11	4	1104
19.68 MHz	11	2	1680

Cellular CDMA applications using the LMX2532, in which the GPS frequency is 1490.04 MHz, then Table 2 provides the proper register settings:


#### Table 2. Settings for GPS (1490.04 MHz) in LMX2532 Cellular CDMA application

Reference Frequency	RF_B	RF_A	RF_FN
19.20 MHz	9	5	1164
19.68 MHz	9	3	1404

Cellular CDMA applications using the LMX2532, in which the GPS frequency is 1391.82 MHz, then Table 3 provides the proper register settings:

#### Table 3. Settings for GPS (1391.82 MHz) in LMX2532 Cellular CDMA application

Reference Frequency	RF_B	RF_A	RF_FN
19.20 MHz	9	0	942
19.68 MHz	8	6	1422





#### **IF-PLL SECTION**

 $f_{VCO} = \{16 \text{ x IF}_B + IF_A\} \text{ x } f_{OSC} / IF_R$ 

where

- $(IF_A < IF_B)$
- f<sub>VCO</sub>: Output frequency of the voltage controlled oscillator (VCO)
- IF\_B: Preset divide ratio of the binary 9-bit programmable counter ( $1 \le IF_B \le 511$ )
- IF\_A: Preset divide ratio of the binary 4-bit swallow counter ( $0 \le IF_A \le 15$ )
- f<sub>OSC</sub>: Reference oscillator frequency
- IF\_R: Preset divide ratio of the binary 9-bit programmable reference counter ( $2 \le IF_R \le 511$ )

From the above equation, the LMX2522/32 generates the fixed IF frequencies as summarized in Table 4.

Device Type	f <sub>vco</sub> (MHz)	IF_B	IF_A	f <sub>osc</sub> /IF_R (kHz)
LMX2522LQ1635	440.76	229	9	120
LMX2532LQ0967	170.67	88	15	120
LMX2532LQ1065	367.20	191	4	120

#### Table 4. IF Frequencies

## VCO FREQUENCY TUNING

The center frequency of the RF VCO is mainly determined by the resonant frequency of the tank circuit. This tank circuit is implemented on-chip and requires no external inductor. The LMX2522/32 actively tunes the tank circuit to the required frequency with the built-in tracking algorithm.

### BANDWIDTH CONTROL AND FREQUENCY LOCK

During the frequency acquisition period, the loop bandwidth is significantly extended to achieve frequency lock. Once frequency lock occurs, the PLL will return to a steady state condition with the loop bandwidth set to its nominal value. The transition between acquisition and lock modes occurs seamlessly and extremely fast, thereby, meeting the stringent requirements associated with lock time and phase noise. Several controls (BW\_DUR, BW\_CRL and BW\_EN) are used to optimize the lock time performance.

### **SPURIOUS REDUCTION**

To improve the spurious performance of the device one of two types of spurious reduction schemes can be selected:

- A continuous optimization scheme, which tracks the environmental and voltage variations, giving the best spurious performance over changing conditions
- A one time optimization scheme, which sets the internal compensation values only when the PLL goes into a locked state.

The spurious reduction can also be disabled, but it is recommended that the continuous optimization mode be used for normal operation.

## POWER DOWN MODE

The LMX2522 and LMX2532 include a power down mode to reduce the power consumption. The LMX2522/32 enters into the power down mode either by taking the CE pin LOW or by setting the power down bits in Register R1. Table 5 summarizes the power down function. If CE is set LOW, the circuit is powered down regardless of the register values. When CE is HIGH, the IF and RF circuitry are individually powered down by setting the register bits.

CE Pin	RF_EN	IF_EN	RF Circuitry	IF Circuitry
0	X	Х	OFF	OFF
1	0	0	OFF	OFF
1	0	1	OFF	ON
1	1	0	ON	OFF
1	1	1	ON	ON

#### Table 5. Power Down Configuration<sup>(1)</sup>

(1) X = Don't care.

## LOCK DETECT

The LD output can be used to indicate the lock status of the RF PLL. Bit 21 in Register R0 determines the signal that appears on the LD pin. When the RF PLL is not locked, the LD pin remains LOW. After obtaining phase lock, the LD pin will have a logical HIGH level. The output can also be programmed to be ground at all times.

#### Table 6. Lock Detect Modes

LD Bit	Mode
0	Disable (GND)
1	Enable

# Table 7. Lock Detect Logic Table<sup>(1)(2)(3)(4)(5)</sup>

RF PLL Section	LD Output
Locked	HIGH
Not Locked	LOW

(1) LD output becomes low when the phase error is larger than  $t_{W2}$ .

(2) LD output becomes high when the phase error is less than t<sub>W1</sub> for four or more consecutive cycles.

(3) Phase Error is measured on leading edge. Only errors greater than  $t_{W1}$  and  $t_{W2}$  are labeled.

(4) t<sub>W1</sub> and t<sub>W2</sub> are equal to 10 ns.

(5) The lock detect comparison occurs with every  $64^{th}$  cycle of  $f_R$  and  $f_N$ .




Figure 2. Lock Detect Timing Diagram Waveform



SNWS009B-MARCH 2003-REVISED APRIL 2013




Figure 3. Lock Detect Flow Diagram

### **MICROWIRE INTERFACE**

The programmable register set is accessed via the MICROWIRE serial interface. The interface comprises three signal pins: CLK, DATA, and LE. Serial data (DATA) is clocked into the 24-bit shift register on the rising edge of the clock (CLK). The last bits decode the internal control register address. When the Latch Enable (LE) transitions from LOW to HIGH, data stored in the shift registers is loaded into the corresponding control register.



www.ti.com

### **Programming Description**

### CONTROL REGISTER CONTENT MAP

The serial interface has a 24-bit shift register to store the incoming data bits temporarily. The incoming Data is loaded into the shift register from MSB to LSB. The Data is shifted at the rising edge of the Clock signal. When the Latch Enable signal transitions from LOW to HIGH, the data stored in the shift register is transferred to the proper register depending on the address bit settings. The selection of the particular register is determined by the control bits indicated in boldface text.

At initial start-up, the MICROWIRE loading requires 4 default words (registers R3, loaded first, to R0, loaded last). After the device has been initially programmed, the RF VCO frequency can be changed using a single register (R0). If an IF frequency other than the default value for the device is desired the SPI\_DEF bit should be set to 0, the desired values for IF\_A, IF\_B, and IF\_R entered and words R6 to R0 should be sent.

The control register content map describes how the bits within each control register are allocated to the specific control functions.

Register	MSB								SI	HIFT	REG	ISTE	r Bit		CATIO	ON								LSB
	23	22	21	20	19	18	17	16	15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0
R0 (Default)	SPI_ DEF	RF SE L	RF LD	SP UR CR L	RF_ [3:0]				RF_A [2:0]								RF_F [10:0						0	0
R1 (Default)	IF_ FREQ [1:0]		OS C_ FR EQ	1	0	0	0	0	0	0	0	SPL RD1 [1:0]		0	0	1	0	1	OB_ CRI [1:0]	_	RF ĒN	IF_ EN	0	1
R2 (Default)	IF_ CUR[1	:0]	0	0	1	0	0	1	1	1	0	1	1	0	1	0	1	0	0	0	1	0	1	0
R3 (Default)	BW_ DUR [1:0]		BW CRL [1:0]	_	B W_ EN	1	0	1	1	1	1	0	1	0	0	0	1	1	0	VC0 CUI [1:0]	र_	0	1	1
R4	0	0	0	1	0	0	0			_A :0]		IF_B [8:0]								0	1	1	1	
R5	0	0	1	1	0	0	0	0	1	0	IF_R 0 1 1 1 [8:0]							1						
R6	1	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	1	1	1	1	1

## Table 8. Complete Register Map

NOTE: Bold numbers represent the address bits.



#### **R0 REGISTER**

The R0 register address bits (R0 [1:0]) are "00".

The SPI\_DEF bit selects between using the default IF counter values and user programmable values. The use of the default counter values requires that only words R0 to R3 (registers R3, loaded first, to R0, loaded last) be sent after initial power up.

The RF\_LD bit activates the lock detect output of the LD pin (pin 19). The lock detect mode shows the lock status of the RF PLL. The waveform of the lock detect mode is shown in Figure 2, in the Functional Description section on **LOCK DETECT**.

The SPUR\_CRL bit is set to 1 only in the GPS mode with the LMX2532LQ1065 when a 19.68 MHz reference oscillator is used.

The RF N counter consists of the 4-bit programmable counter (RF\_B counter), the 3-bit swallow counter (RF\_A counter) and the 11-bit delta sigma modulator (RF\_FN counter). The equations for calculating the counter values are presented below.

Register	MSB								S	HIFT	REG	ISTE	r Bit		CATI	ON								LSB
	23	22	21	20	19	18	17	16	15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0
										۵	Data F	Field					u							dress ield
R0 (Default)	SPI_ DEF	RF SE L	RF LD	SP UR CR L	RF_ [3:0				RF_ [2:0]								RF_F [10:0						0	0

## Table 9. R0 REGISTER

Name	Functions
SPI_DEF	Default Register Selection 0 = OFF (Use values set in R0 to R6) 1 = ON (Use default values set in R0 to R3)
RF_SEL	<b>RF Select Configuration</b> See Table 10. RF_SEL Configuration below
RF_LD	<b>RF Lock Detect</b> 0 = Hard zero (GND) 1 = Lock detect
SPUR_CRL	<b>Spur Control</b> 1 = LMX2532LQ1065 in GPS mode with 19.68 MHz reference oscillator only 0 = All other options
RF_B [3:0]	<b>RF_B Counter</b> 4-bit programmable counter $2 \le RF_B \le 15$
RF_A [2:0]	RF_A Counter3-bit swallow counter $0 \le RF_A \le 7$ for LMX2522 $0 \le RF_A \le 5$ for LMX2532
RF_FN [10:0]	<b>RF Fractional Numerator Counter</b> 11-bit programmable counter $0 \le RF\_FN < 1920$ for $f_{OSC} = 19.20$ MHz $0 \le RF\_FN < 1968$ for $f_{OSC} = 19.68$ MHz

# LMX2522, LMX2532



#### SNWS009B-MARCH 2003-REVISED APRIL 2013

www.ti.com

Table 10. RF\_SEL Configuration

Device Type	RF_SEL = 0	RF_SEL = 1
LMX2522	GPS	K-PCS
LMX2532	K-Cellular	GPS

#### RF N Counter Setting:

Counter Name	Symbol	Function
Modulus Counter	RF_FN	RF N Divider
Programmable Counter	RF_B	N = Prescaler x RF_B + RF_A + (RF_FN / f <sub>OSC</sub> ) 10 <sup>4</sup>
Swallow Counter	RF_A	

#### Pulse Swallow Function:

 $f = \{Prescaler x RF_B + RF_A + (RF_FN / f_{OSC}) x 10^4\} x f_{OSC} where (RF_A < RF_B)$ 

where

• f<sub>VCO</sub>: Output frequency of voltage controlled oscillator (VCO)

Prescaler Values:

Device Type	RF Prescaler	GPS Prescaler
LMX2522	8	6
LMX2532	6	8

- RF\_B: Preset divide ratio of binary 4-bit programmable counter ( $2 \le RF_B \le 15$ )
- RF\_A: Preset divide ratio of binary 3-bit swallow counter (0 ≤ RF\_A ≤ 7 for prescaler of 8 or 0 ≤ RF\_A ≤ 5 for prescaler of 6)
- RF\_FN: Preset numerator of binary 11-bit modulus counter (0 ≤ RF\_FN < 1920 for f<sub>OSC</sub> = 19.20 MHz; 0 ≤ RF\_FN < 1968 for f<sub>OSC</sub> = 19.68 MHz)
- f<sub>OSC</sub>: Reference oscillator frequency

NOTE: For the use of reference frequencies other than those specified, please contact Texas Instruments.



#### **R1 REGISTER**

The R1 register address bits (R1 [1:0]) are "01".

The IF\_FREQ bits selects the default IF frequency applicable to the specific CDMA system. For the LMX2522 the default IF frequency is 440.76 MHz, and for the LMX2532 the default IF frequencies are 367.20 MHz and 170.76 MHz, depending on variant.

Reference Frequency Selection bit (OSC\_FREQ) selects either 19.20 MHz or 19.68 MHz for the reference oscillator frequency.

The internal spurious reduction scheme is controlled by the SPUR\_RDT [1:0] bits. There are two different spur reduction schemes: a continuous tracking mode and a single optimization mode. The continuous tracking mode will adjust for variations in voltage and temperature. The single optimization mode fixes the internal compensation parameters only when the PLL goes into the locked state. The spur reduction can also be disabled, but it is recommended that the continuous mode be used for normal operation.

The OB\_CRL [1:0] bits determine the power level of the RF output buffer. The power level is set according to the system requirement.

The two bits, RF\_EN and IF\_EN, logically select the active state of the RF/GPS synthesizer system and the IF PLL, respectively. The entire IC can be placed in a power down state by using the CE control pin (pin 20).

Register	MSB								S	HIFT	REG	ISTEF	R BIT	LOC	CATIC	ON							LSB
	23																2	1	1 0				
		Data Field																dress ield					
R1 (Default)	IF_ FREQ [1:0]		OS C_ FR EQ	1	0	0	0	0	0	0	0	SPU RDT [1:0]	_	0	0	1	0	1	OB_ CRL [1:0]	RF ĒN	IF_ EN	0	1

#### Table 11. R1 REGISTER

Name	Functions
IF_FREQ [1:0]	IF Frequency Selection 00 = 170.76 MHz (LMX2532LQ0967) 01 = 367.20 MHz (LMX2532LQ1065) 10 = 440.76 MHz (LMX2522LQ1635)
OSC_FREQ	Reference Frequency Selection 0 = 19.20 MHz 1 = 19.68 MHz
SPUR_RDT [1:0]	Spur Reduction Scheme00 = No spur reduction01 = Not Used10 = Continuous tracking of variation (Recommended)11 = One time optimization
OB_CRL [1:0]	<b>RF Output Power Control</b> 00 = Minimum Output Power         01 =         10 =         11 = Maximum Output Power
RF_EN	RF Enable 0 = RF Off 1 = RF On
IF_EN	IF Enable 0 = IF Off 1 = IF On

# LMX2522, LMX2532



www.ti.com

#### SNWS009B-MARCH 2003-REVISED APRIL 2013

## **R2 REGISTER**

The R2 Register address bits (R2 [1:0]) are "10".

The IF\_CUR [1:0] bits program the IF charge pump current. Considering the external IF VCO and loop filter, the user can select the amount of IF charge pump current to be 100µA, 200µA, 300µA or 800µA.

## Table 12. R2 REGISTER

Register	MSB								S	HIFT	REG	ISTE	r Bit	LOC	ATIC	ON								LSB
	23	22	21	20	19	18	17	16	15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0
		Data Field																dress ield						
R2 (Default)	IF_ CUR[1	IF 0 0 1 0 0 1 1 1 1 1 0 1 1 0 1 0 1														1	0							

Name	Functions
IF_CUR [1:0]	<b>IF Charge Pump Current</b> 00 = 100 μA 01 = 200 μA 10 = 300 μA 11 = 800 μA

Copyright © 2003–2013, Texas Instruments Incorporated



#### **R3 REGISTER**

www.ti.com

The R3 register address bits (R3 [2:0]) are "011".

Register R3 contains the controls for the phase lock bandwidth controls (BW\_DUR, BW\_CRL and BW\_EN). The duration of the digital controller portion of the bandwidth control is set by BW\_DUR [1:0]. The minimum time set with 00 and increasing durations to the maximum value set with 11. BW\_CRL [1:0] sets the phase offset criterion for the bandwidth controller. Once the phase offset between the reference clock and the divided VCO signal are within the set criterion, the bandwidth control stops. The maximum phase offset is set with 00 and decreases to the minimum value set with 11. BW\_EN enables the bandwidth control in the locking state.

The VCO dynamic current is also controlled in register R3 with VCO\_CUR [1:0]. The minimum value corresponds to 00 and increases to a maximum value set at 11.

Register	MSB								S	HIFT	REG	ISTE	r Bit	LOC	CATIO	ON								LSB
	23	22																0						
		Data Field Address Field																						
R3 (Default)	BW_ DUR [1:0]		BW CRI [1:0]		B W_ EN	1	0	1	1	1	1	0	1	0	0	0	1	1	0	VC0 CUI [1:0	R <sup></sup>	0	1	1

Name	Functions
BW_DUR [1:0]	Bandwidth Duration 00 = Minimum value (Recommended) 01 = 10 = 11 = Maximum value
BW_CRL [1:0]	Bandwidth Control 00 = Maximum phase offset (Recommended) 01 = 10 = 11 = Minimum phase offset
BW_EN	Bandwidth Enable 0 = Disable 1 = Enable (Recommended)
VCO_CUR [1:0]	VCO Dynamic Current 00 = Minimum value 01 = 10 = 11 = Maximum value (Recommended)

# LMX2522, LMX2532

SNWS009B-MARCH 2003-REVISED APRIL 2013



www.ti.com

#### **R4 REGISTER**

The R4 register address bits (R3 [3:0]) are "0111".

Register R4 is used to set the IF N counters if the default value is not desired. This register is only active if the SPI\_DEF bit in register R0 is 0.

The IF N counter consists of the 9-bit programmable counter (IF\_B counter) and the 4-bit swallow counter (IF\_A counter). The equations for calculating the counter values are presented below.

#### Table 14. R4 REGISTER

Register	MSB								S	HIFT	REG	ISTE	r Bit		CATIO	ON								LSB
	23	22	21	20	19	18	17	16	15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0
		Data Field Address Field														s								
R4	0	0 0 1 0 0 IF_A IF_B 0 1												1	1	1								

Name	Functions
	IF A Counter 4-bit swallow counter 0 ≤ IF_A ≤ 15
	IF B Counter 9-bit programmable counter 1 ≤ IF_B ≤ 511

#### IF Frequency Setting:

 $f_{VCO} = \{16 \text{ x IF}_B + IF_A\} \text{ x } f_{OSC} / R \text{ where } (IF_A < IF_B)$ 

where

- f<sub>VCO</sub>: Output frequency of IF voltage controlled oscillator (IF VCO)
- IF\_B: Preset divide ratio of binary 9-bit programmable counter ( $1 \le IF_B \le 511$ )
- IF\_A: Preset divide ratio of binary 4-bit swallow counter ( $0 \le IF_A \le 15$ )
- IF\_R: Preset divide ratio of binary 9-bit programmable reference counter ( $2 \le IF_R \le 511$ )
- f<sub>OSC</sub>: Reference oscillator frequency



#### **R5 REGISTER**

www.ti.com

The R5 register address bits (R5 [4:0]) are "01111".

Register R5 is used to set the IF\_R divider if the default value is not desired. This register is only active if the SPI\_DEF bit in register R0 is 0.

Table 15. R5 REGISTER	
-----------------------	--

Register	MSB								S	HIFT	REG	ISTE	r Bit	LOC	CATIO	ON								LSB
	23	22	21	20	19	18	17	16	15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0
		Data Field Address Field																						
R5	0	0	1	1	0	0	0	0	1	0	IF_R 0 1 1 [8:0]									1	1			

Name	Functions
IF_R [8:0]	IF R Counter 9-bit programmable counter 2 ≤ IF_R ≤ 511

#### **R6 REGISTER**

The R6 register address bits (R6 [5:0]) are "011111".

Register R6 is used for internal testing of the device and is not intended for customer use. This register is only active if the SPI\_DEF bit in register R0 is 0.

Register	MSB								S	HIFT	REG	ISTEI	r Bit	LOC	ATIC	N								LSB
	23	3 22 21 20 19 18 17 16 15 14 13 12 11 10 9 8 7 6 5 4 3 2 1 0													0									
	Data Field Address Field																							
R6	1	1 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0												1										

#### Table 16. R6 REGISTER

SNWS009B-MARCH 2003-REVISED APRIL 2013

# **REVISION HISTORY**

Cł	nanges from Revision A (April 2013) to Revision B P	Page
•	Changed layout of National Data Sheet to TI format	. 19



www.ti.com



## PACKAGING INFORMATION

Orderable Device	Status (1)	Package Type	Package Drawing	Pins	Package Qty	Eco Plan (2)	Lead finish/ Ball material	MSL Peak Temp (3)	Op Temp (°C)	Device Marking (4/5)	Samples
							(6)				
LMX2522LQ1635	LIFEBUY	WQFN	NJB	28	1000	Non-RoHS & Green	Call TI	Level-3-260C-168 HR	-30 to 85	25221635	
LMX2522LQ1635/NOPB	ACTIVE	WQFN	NJB	28	1000	RoHS & Green	SN	Level-3-260C-168 HR	-30 to 85	25221635	Samples

<sup>(1)</sup> The marketing status values are defined as follows:

ACTIVE: Product device recommended for new designs.

LIFEBUY: TI has announced that the device will be discontinued, and a lifetime-buy period is in effect.

NRND: Not recommended for new designs. Device is in production to support existing customers, but TI does not recommend using this part in a new design.

**PREVIEW:** Device has been announced but is not in production. Samples may or may not be available.

**OBSOLETE:** TI has discontinued the production of the device.

<sup>(2)</sup> RoHS: TI defines "RoHS" to mean semiconductor products that are compliant with the current EU RoHS requirements for all 10 RoHS substances, including the requirement that RoHS substance do not exceed 0.1% by weight in homogeneous materials. Where designed to be soldered at high temperatures, "RoHS" products are suitable for use in specified lead-free processes. TI may reference these types of products as "Pb-Free".

**RoHS Exempt:** TI defines "RoHS Exempt" to mean products that contain lead but are compliant with EU RoHS pursuant to a specific EU RoHS exemption.

Green: TI defines "Green" to mean the content of Chlorine (CI) and Bromine (Br) based flame retardants meet JS709B low halogen requirements of <=1000ppm threshold. Antimony trioxide based flame retardants must also meet the <=1000ppm threshold requirement.

<sup>(3)</sup> MSL, Peak Temp. - The Moisture Sensitivity Level rating according to the JEDEC industry standard classifications, and peak solder temperature.

<sup>(4)</sup> There may be additional marking, which relates to the logo, the lot trace code information, or the environmental category on the device.

<sup>(5)</sup> Multiple Device Markings will be inside parentheses. Only one Device Marking contained in parentheses and separated by a "~" will appear on a device. If a line is indented then it is a continuation of the previous line and the two combined represent the entire Device Marking for that device.

<sup>(6)</sup> Lead finish/Ball material - Orderable Devices may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead finish/Ball material values may wrap to two lines if the finish value exceeds the maximum column width.

**Important Information and Disclaimer:**The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.



# PACKAGE OPTION ADDENDUM

31-Jan-2024



Texas

STRUMENTS

## TAPE AND REEL INFORMATION





#### QUADRANT ASSIGNMENTS FOR PIN 1 ORIENTATION IN TAPE



*All dimensions are nominal												
Device	Package Type	Package Drawing		SPQ	Reel Diameter (mm)	Reel Width W1 (mm)	A0 (mm)	B0 (mm)	K0 (mm)	P1 (mm)	W (mm)	Pin1 Quadrant
LMX2522LQ1635	WQFN	NJB	28	1000	178.0	12.4	5.3	5.3	1.3	8.0	12.0	Q1
LMX2522LQ1635/NOPB	WQFN	NJB	28	1000	178.0	12.4	5.3	5.3	1.3	8.0	12.0	Q1



# PACKAGE MATERIALS INFORMATION


9-Aug-2022



\*All dimensions are nominal

Device	Package Type	Package Drawing	Pins	SPQ	Length (mm)	Width (mm)	Height (mm)
LMX2522LQ1635	WQFN	NJB	28	1000	208.0	191.0	35.0
LMX2522LQ1635/NOPB	WQFN	NJB	28	1000	208.0	191.0	35.0

# NJB0028A





## IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATA SHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, regulatory or other requirements.

These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you will fully indemnify TI and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to TI's Terms of Sale or other applicable terms available either on ti.com or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products.

TI objects to and rejects any additional or different terms you may have proposed.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265 Copyright © 2024, Texas Instruments Incorporated