





**OPA328, OPA2328** SBOS957D - FEBRUARY 2022 - REVISED DECEMBER 2023

OPAx328 Precision, 40-MHz, 1.0-pA, Low-Noise, RRIO, CMOS Operational Amplifiers With Shutdown

## 1 Features


Texas

INSTRUMENTS

- Precision with zero-crossover distortion:
  - Low offset voltage: 50 µV (maximum)
  - High CMRR: 120 dB
  - Rail-to-rail I/O
- Wide bandwidth: 40 MHz
- Low input bias current: 1 pA (maximum)
- Low noise: 6.1 nV/ $\sqrt{Hz}$  at 10 kHz
- Slew rate: 30 V/µs
- Fast 0.01% settling time: 180 ns •
- Single-supply voltage range: 2.2 V to 5.5 V
- Unity-gain stable

## 2 Applications

- **Optical module**
- Position sensor
- Multiparameter patient monitor
- CT and PET scanner •
- Chemistry and gas analyzer
- Bidirectional 400-V and 800-V to LV
- Merchant network and server PSU •
- String inverter
- Solar power optimizer



**Block Diagram** 

## **3 Description**

single-channel OPA328 and dual-channel The OPA2328 (OPAx328) are a new generation family of precision, low-voltage CMOS operational amplifiers optimized for very low noise and wide bandwidth.

The OPAx328 have a linear input stage with zerocrossover distortion that delivers excellent commonmode rejection ratio (CMRR) of 120 dB (typical) over the full input range. The input common-mode voltage range extends 100 mV beyond the negative and positive supply rails. The output voltage typically swings within 10 mV of the rails.

The OPAx328 also use Texas Instrument's proprietary e-trim<sup>™</sup> operational amplifier technology, enabling a unique combination of ultra-low offset and low input offset drift without the need for any input switching or auto-zero techniques.

Low-noise (6.1 nV/ $\sqrt{Hz}$ ) and high-speed operation (40 MHz, 30 V/µs) make these devices a great choice for driving sampling analog-to-digital converters (ADCs).

The OPAx328 are also a great choice for highimpedance-input, single-supply applications. Low input bias current and low input capacitance allows for high-frequency transimpedance gains at low photocurrent operation (< 1 nA).

Bettee Information					
PART NUMBER	CHANNELS / SHUTDOWN	PACKAGE <sup>(1)</sup>			
OPA328	Single / No	DBV (SOT-23, 5)			
OPA328S <sup>(2)</sup>	Single / Yes	DBV (SOT-23, 6)			
		D (SOIC, 8)			
OPA2328	Dual / No	DGK (VSSOP, 8)			
		DRG (WSON, 8)			
OPA4328 <sup>(2)</sup>	Quad / No	PW (TSSOP, 14)			
	Quad / Yes	RUM (WQFN, 16)			

#### **Device Information**

For more information, see Section 10. (1)

Preview information (not Production Data). (2)





## **Table of Contents**

1 Features	1
2 Applications	1
3 Description	1
4 Pin Configuration and Functions	3
5 Specifications	5
5.1 Absolute Maximum Ratings	5
5.2 ESD Ratings	5
5.3 Recommended Operating Conditions	<mark>5</mark>
5.4 Thermal Information - OPA328	<mark>6</mark>
5.5 Thermal Information - OPA2328	<mark>6</mark>
5.6 Electrical Characteristics	7
5.7 Typical Characteristics	9
6 Detailed Description	15
6.1 Overview	
6.2 Functional Block Diagram	15
6.3 Feature Description	
6.4 Device Functional Modes	16

7 Application and Implementation	17
7.1 Application Information	17
7.2 Typical Applications	
7.3 Power Supply Recommendations	21
7.4 Layout	21
8 Device and Documentation Support	
8.1 Device Support	
8.2 Documentation Support	
8.3 Receiving Notification of Documentation Updates	
8.4 Support Resources	23
8.5 Trademarks	
8.6 Electrostatic Discharge Caution	23
8.7 Glossary	
9 Revision History	
10 Mechanical, Packaging, and Orderable	
Information	24



## **4 Pin Configuration and Functions**




Figure 4-1. OPA328 DBV Package, 5-Pin SOT-23 (Top View)





Figure 4-2. OPA328S DBV Package (Preview) 6-Pin SOT-23 (Top View)

#### Pin Functions: OPA328 and OPA328S

	PIN		TYPE	DESCRIPTION	
NAME	OPA328	OPA328S		DESCRIPTION	
–IN	4	4	Input	Negative (inverting) input	
+IN	3	3	Input	Positive (noninverting) input	
OUT, VOUT	1	1	Output	Output	
SHDN	—	5	Input	Shutdown, active low	
V–	2	2	Power	Negative (lowest) power supply	
V+	5	6	Power	Positive (highest) power supply	







Figure 4-3. OPA2328 D Package, 8-pin SOIC and DGK Package, 8-Pin VSSOP (Top View)


Figure 4-4. OPA2328 DRG Package, 8-Pin WSON (Top View)

#### Pin Functions: OPA2328

PIN		TYPE	DESCRIPTION	
NAME	NO.	ITE	DESCRIPTION	
–IN A	2	Input	Inverting input, channel A	
+IN A	3	Input	Noninverting input, channel A	
–IN B	6	Input	Inverting input, channel B	
+IN B	5	Input	Noninverting input, channel B	
OUT A	1	Output	Output, channel A	
OUT B	7	Output	Output, channel B	
V-	4	Power	Negative (lowest) power supply	
V+	8	Power	Positive (highest) power supply	










Figure 4-6. OPA4328 RUM Package (Preview), 16-Pin WQFN (Top View)

 Table 4-1. Pin Functions: OPA4328

PIN							
NAME	N	0.	TYPE	DESCRIPTION			
NAME	PW (TSSOP)	RUM (WQFN)					
EN AB		6	Input	Enable pin for A and B amplifiers. High = amplifiers A and B are enabled.			
EN CD		7	Input	Enable pin for C and D amplifiers. High = amplifiers C and D are enabled.			
–IN A	2	16	Input	nverting input, channel A			
+IN A	3	1	Input	Noninverting input, channel A			
–IN B	6	4	Input	Inverting input, channel B			
+IN B	5	3	Input	Noninverting input, channel B			
–IN C	9	9	Input	Inverting input, channel C			
+IN C	10	10	Input	Noninverting input, channel C			
–IN D	13	13	Input	Inverting input, channel D			
+IN D	12	12	Input	Noninverting input, channel D			
OUT A	1	15	Output	Output, channel A			
OUT B	7	5	Output	Output, channel B			
OUT C	8	8	Output	Output, channel C			
OUT D	14	14	Output	Output, channel D			
Thermal Pad	_	Thermal Pad	Power	Connect thermal pad to V–			
V-	11	11	Power	Negative (lowest) power supply			
V+	4	2	Power	Positive (highest) power supply			



## **5** Specifications

#### 5.1 Absolute Maximum Ratings

over operating free-air temperature range (unless otherwise noted) (1)

		MIN	MAX	UNIT
Vs	Supply voltage, $V_S = (V+) - (V-)$	-0.3	6	V
	Input voltage, all pins	(V–) – 0.3	(V+) + 0.3	V
	Input current (INA+, INA–, INB+, INB–, INSA/B, OUTSA/B/1/2/3)	-10	10	mA
	Output short-circuit <sup>(2)</sup>	Continuous	Continuous	
T <sub>A</sub>	Operating temperature	-55	150	°C
TJ	Junction temperature	-55	150	°C
T <sub>stg</sub>	Storage temperature	-65	150	°C

(1) Operation outside the Absolute Maximum Ratings may cause permanent device damage. Absolute Maximum Ratings do not imply functional operation of the device at these or any other conditions beyond those listed under Recommended Operating Conditions. If used outside the Recommended Operating Conditions but within the Absolute Maximum Ratings, the device may not be fully functional, and this may affect device reliability, functionality, performance, and shorten the device lifetime.

(2) Short-circuit to ground, one amplifier per package.

### 5.2 ESD Ratings

			VALUE	UNIT
V	Electrostatic discharge	Human-body model (HBM), per ANSI/ESDA/JEDEC JS-001 <sup>(1)</sup>	2000	V
V <sub>(ESD)</sub>	Electrostatic discharge	Charged-device model (CDM), per ANSI/ESDA/JEDEC JS-002 <sup>(2)</sup>	500	v

(1) JEDEC document JEP155 states that 500-V HBM allows safe manufacturing with a standard ESD control process.

(2) JEDEC document JEP157 states that 250-V CDM allows safe manufacturing with a standard ESD control process.

## **5.3 Recommended Operating Conditions**

over operating free-air temperature range (unless otherwise noted)

			MIN	NOM MAX	UNIT
Supply		Single-supply	2.2	5.5	V
Vs	voltage	Dual-supply	±1.1	±2.75	V
T <sub>A</sub>	Specified ten	nperature	-40	125	°C



#### 5.4 Thermal Information - OPA328

		OPA328	
	THERMAL METRIC <sup>(1)</sup>	DBV (SOT-23)	UNIT
		5 PINS	
R <sub>0JA</sub>	Junction-to-ambient thermal resistance	163.2	°C/W
R <sub>0JC(top)</sub>	Junction-to-case (top) thermal resistance	97.6	°C/W
R <sub>θJB</sub>	Junction-to-board thermal resistance	62.8	°C/W
$\Psi_{JT}$	Junction-to-top characterization parameter	40.7	°C/W
Ψ <sub>JB</sub>	Junction-to-board characterization parameter	62.5	°C/W
R <sub>0JC(bot)</sub>	Junction-to-case (bottom) thermal resistance	N/A	°C/W

(1) For more information about traditional and new thermal metrics, see the *Semiconductor and IC Package Thermal Metrics* application report.

### 5.5 Thermal Information - OPA2328

		OPA2328				
	THERMAL METRIC <sup>(1)</sup>	D (SOIC)	DGK (VSSOP)	DRG (WSON)	UNIT	
		8 PINS	8 PINS	8 PINS		
R <sub>0JA</sub>	Junction-to-ambient thermal resistance	123.9	165	50.3	°C/W	
R <sub>0JC(top)</sub>	Junction-to-case (top) thermal resistance	63.1	53	50.2	°C/W	
R <sub>θJB</sub>	Junction-to-board thermal resistance	67.4	87	23.4	°C/W	
$\Psi_{JT}$	Junction-to-top characterization parameter	15.7	4.9	0.8	°C/W	
$\Psi_{JB}$	Junction-to-board characterization parameter	66.6	85	23.4	°C/W	
R <sub>0JC(bot)</sub>	Junction-to-case (bottom) thermal resistance	N/A	N/A	7.3	°C/W	

(1) For more information about traditional and new thermal metrics, see the Semiconductor and IC Package Thermal Metrics application report.



## **5.6 Electrical Characteristics**

at  $T_A = 25^{\circ}$ C,  $V_S = \pm 1.1$  V to  $\pm 2.75$  V ( $V_S = 2.2$  V to 5.5 V),  $R_L = 10$  k $\Omega$  connected to  $V_S$  / 2,  $V_{CM} = V_{OUT} = V_S$  / 2, and min and max specification established from manufacturing final test (unless otherwise noted)

	PARAMETER	TEST CO	ONDITIONS	MIN	TYP	MAX	UNIT	
OFFSET V	OLTAGE							
. <i>(</i>	have the ff and the literation	OPA2328D, DGK, and I	ORG		±3	±50		
V <sub>OS</sub>	Input offset voltage	OPA328DBV			±3	±75	μV	
dV <sub>OS</sub> /dT	Input offset voltage drift	$T_{A} = -40^{\circ}C \text{ to } +125^{\circ}C$	OPA328DBV, OPA2328D, DGK		±0.15	±1	µV/°C	
	input encot renage and		OPA2328DRG		±0.15	±1.5	µ., 0	
	Power-supply rejection	V <sub>S</sub> = ±1.1 V to ±2.75 V			±1	±10		
PSRR	ratio	$V_{\rm S}$ = ±1.1 V to ±2.75 V,	T <sub>A</sub> = -40°C to +125°C		±15	±40	μV/V	
	Channel separation	f = dc			140		dB	
	(dual, quad)	f = 100 kHz			75		uВ	
	SCURRENT							
					±0.2	±1		
I <sub>B</sub>	Input bias current	T <sub>A</sub> = 0°C to 85°C				10	pА	
		$T_{A} = -40^{\circ}C \text{ to } +125^{\circ}C$				100		
					±0.2	±1		
l <sub>os</sub>	Input offset current	$T_A = 0^{\circ}C$ to $85^{\circ}C$				10	pА	
		$T_A = -40^{\circ}C$ to $+125^{\circ}C$				100		
NOISE	1							
	Input voltage noise	f = 0.1 Hz to 10 Hz			3		μV <sub>PP</sub>	
		f = 100 Hz			25			
e <sub>N</sub> Input voltage noise density		f = 1 kHz		9.8		nV/√Hz		
	f = 10 kHz		6.1					
i <sub>N</sub>	Input current noise	f = 10 kHz			0.125		pA/√Hz	
INPUT VO	LTAGE	•						
V <sub>CM</sub>	Common-mode voltage			(V–) – 0.1		(V+) + 0.1	V	
CMRR	Common-mode	(V–) – 0.1 V < V <sub>CM</sub> <		106	120		dB	
CIVIER	rejection ratio	(V+) + 0.1 V	$T_A = -40^{\circ}C \text{ to } +125^{\circ}C$	96	110		uВ	
INPUT CA	PACITANCE	•						
Z <sub>ID</sub>	Differential				1    4		TΩ    pF	
Z <sub>ICM</sub>	Common-mode				1    2		TΩ    pF	
OPEN-LO	OP GAIN	•						
		(V–) + 100 mV < V <sub>O</sub> <		108	132			
		(V+) – 100 mV	$T_{A} = -40^{\circ}C \text{ to } +125^{\circ}C$	96	130			
A <sub>OL</sub>	Open-loop voltage gain	(V–) + 200 mV < V <sub>O</sub> <		106	123		dB	
		(V+) - 200  mV, $R_L = 2 \text{ k}\Omega$	$T_A = -40^{\circ}C \text{ to } +125^{\circ}C$	90				
FREQUEN								
GBW	Gain-bandwidth product	Gain = 100			40		MHz	
SR	Slew rate	4-V step, gain = +1			30		V/µs	
		To 0.1%, 1-V step, gain	= +1		0.1			
ts	Settling time	To 0.01%, 1-V step, gai	n = +1		0.18		μs	
	Overload recovery time	V <sub>IN</sub> × gain > V <sub>S</sub>			0.5		μs	
THD+N	Total harmonic distortion + noise	V <sub>O</sub> = 1 V <sub>RMS</sub> , gain = +1, f = 1 kHz			0.0001		%	

Copyright © 2023 Texas Instruments Incorporated



## 5.6 Electrical Characteristics (continued)


at  $T_A = 25^{\circ}$ C,  $V_S = \pm 1.1$  V to  $\pm 2.75$  V ( $V_S = 2.2$  V to 5.5 V),  $R_L = 10$  k $\Omega$  connected to  $V_S$  / 2,  $V_{CM} = V_{OUT} = V_S$  / 2, and min and max specification established from manufacturing final test (unless otherwise noted)

	PARAMETER	TES	ST CONDITIONS	MIN	TYP	MAX	UNIT	
ουτρυτ	-							
		V - 2 2 V				5		
		V <sub>S</sub> = 2.2 V	$R_L = 2 k\Omega$			15		
			OPA328DBV, OPA2328D, DGK			5		
	Voltage output swing		OPA2328DRG		mV			
	from both rails	V <sub>S</sub> = 5.5 V	R <sub>L</sub> = 2 kΩ, OPA328DBV, OPA2328D, DGK		15			
			$R_L = 2 k\Omega$ , OPA2328DRG			20		
	Chart airquit aurrant	Sinking, V <sub>S</sub> = 5.5 V	1		m۸			
I <sub>SC</sub>	Short-circuit current	Sourcing, V <sub>S</sub> = 5.5	V		55		mA	
C <sub>LOAD</sub>	Capacitive load drive	Gain = +1			28		pF	
R <sub>O</sub>	Open-loop output impedance	f = 10 kHz			55		Ω	
POWER	SUPPLY							
Quiescent current per		I <sub>O</sub> = 0 A			3.8	4.5	mA	
l <sub>Q</sub>	amplifier	$I_0 = 0 \text{ A}, T_A = -40^{\circ}$	°C to +125°C		5.0			
SHUTDO	WN (OPA328SDBV and OF	PA4328RUM)						
I <sub>QSD</sub>	Quiescent current in shutdown	All amplifiers disab	led		30	50	μA	
Z <sub>OFF</sub>	Output impedance in shutdown	All amplifiers disab	led		100    16		GΩ∥pF	
V <sub>IH</sub>	High-level input voltage	Amplifier enabled		(V+) – 0.5			V	
V <sub>IL</sub>	Low-level input voltage	Amplifier disabled				(V–) + 0.5	V	
t <sub>ON</sub>	Output enable time	G = 1, V <sub>OUT</sub> = 0.9 :	× V <sub>S</sub> /2, all amplifiers enabled		10		μs	
t <sub>OFF</sub>	Output disable time	G = 1, V <sub>OUT</sub> = 0.1	× V <sub>S</sub> /2, all amplifiers disabled		3		μs	
	EN pin input leakage current	V <sub>IH</sub> = V+ V <sub>IL</sub> = V-		0.02			μA	
		VIL - V-						




## **5.7 Typical Characteristics**

at T<sub>A</sub> = 25°C, V<sub>S</sub> = 5.5 V, V<sub>CM</sub> = V<sub>OUT</sub> = mid-supply, C<sub>L</sub> = 20 pF, and R<sub>L</sub> = 10 kΩ (unless otherwise noted)






at T<sub>A</sub> = 25°C, V<sub>S</sub> = 5.5 V, V<sub>CM</sub> = V<sub>OUT</sub> = mid-supply, C<sub>L</sub> = 20 pF, and R<sub>L</sub> = 10 kΩ (unless otherwise noted)






at T<sub>A</sub> = 25°C, V<sub>S</sub> = 5.5 V, V<sub>CM</sub> = V<sub>OUT</sub> = mid-supply, C<sub>L</sub> = 20 pF, and R<sub>L</sub> = 10 k $\Omega$  (unless otherwise noted)






at T<sub>A</sub> = 25°C, V<sub>S</sub> = 5.5 V, V<sub>CM</sub> = V<sub>OUT</sub> = mid-supply, C<sub>L</sub> = 20 pF, and R<sub>L</sub> = 10 k $\Omega$  (unless otherwise noted)






at T<sub>A</sub> = 25°C, V<sub>S</sub> = 5.5 V, V<sub>CM</sub> = V<sub>OUT</sub> = mid-supply, C<sub>L</sub> = 20 pF, and R<sub>L</sub> = 10 kΩ (unless otherwise noted)





at  $T_A = 25^{\circ}$ C,  $V_S = 5.5$  V,  $V_{CM} = V_{OUT}$  = mid-supply,  $C_L = 20$  pF, and  $R_L = 10$  k $\Omega$  (unless otherwise noted)






## 6 Detailed Description

### 6.1 Overview

The OPAx328 family features high-speed, precision amplifiers that make this op amp family an excellent choice for driving high-resolution analog-to-digital converters (ADCs). Low output impedance with flat frequency characteristics and zero-crossover distortion circuitry enable high linearity over the full input common-mode range, achieving true rail-to-rail input from a 2.2-V to 5.5-V single supply.

#### 6.2 Functional Block Diagram





#### 6.3 Feature Description

### 6.3.1 Input and ESD Protection

The OPAx328 incorporate internal electrostatic discharge (ESD) protection circuits on all pins. In the case of input and output pins, this protection primarily consists of current-steering diodes connected between the input and power-supply pins. These ESD protection diodes also provide in-circuit input overdrive protection if the current is limited to 10 mA. Many input signals are inherently current-limited to less than 10 mA; therefore, a limiting resistor is not required. Figure 6-1 shows how a series input resistor ( $R_{IN}$ ) can be added to the driven input to limit the input current. The added resistor contributes thermal noise at the amplifier input; therefore, keep this value to a minimum in noise-sensitive applications.





Figure 6-1. Input Current Protection

#### 6.3.2 Rail-to-Rail Input

The OPAx328 feature true rail-to-rail input operation, with supply voltages as low as  $\pm 1.1$  V (2.2 V). The design of the OPAx328 amplifiers includes an internal charge-pump that powers the amplifier input stage with an internal supply rail at approximately 1.6 V greater than the external supply (V<sub>S+</sub>). This internal supply rail allows the single differential input pair to operate and remain very linear over a very-wide input common-mode range. A unique zero-crossover input topology eliminates the input offset transition region typical of many rail-to-rail, complementary-input-stage operational amplifiers. This topology allows the OPAx328 to provide excellent common-mode performance (CMRR > 120 dB, typical) over the entire common-mode input range, which extends 100 mV beyond both power-supply rails. When driving analog-to-digital converters (ADCs), the highly linear V<sub>CM</sub> range of the OPAx328 provides maximum linearity and lowest distortion.

#### 6.3.3 Phase Reversal

The OPAx328 op amps are designed to be immune to phase reversal when the input pins exceed the supply voltages, and thus provide further in-system stability and predictability. Figure 6-2 shows the input voltage exceeding the supply voltage without any phase reversal.



Time (100 µs/div)

Figure 6-2. No Phase Reversal

## 6.4 Device Functional Modes

The OPAx328 operational amplifier is operational when power-supply voltages between 2.2 V to 5.5 V are applied. Devices with an *S* suffix have shutdown capability.



## 7 Application and Implementation

#### Note

Information in the following applications sections is not part of the TI component specification, and TI does not warrant its accuracy or completeness. TI's customers are responsible for determining suitability of components for their purposes, as well as validating and testing their design implementation to confirm system functionality.

#### 7.1 Application Information

The OPAx328 offer outstanding dc and ac performance. These devices operate with up to a 5.5-V power supply, and offer an ultra-low input bias current and a 40-MHz bandwidth. These features make the OPAx328 family of robust operational amplifiers great for both communication and industrial applications.

#### 7.1.1 Capacitive Load and Stability

The OPAx328 are designed for use in high-speed applications for transimpedance amplifiers (TIA) and ADC input-driving amplifiers. As with all op amps, there can be specific instances where the OPAx328 become unstable. The particular op-amp circuit configuration, layout, gain, and output loading are some of the factors to consider when establishing whether an amplifier is stable in operation. An op amp in the unity-gain (1-V/V) buffer configuration driving a capacitive load exhibits a greater tendency to become unstable compared to an amplifier operating at a higher noise gain (see Figure 5-28). The capacitive load, in conjunction with the op-amp output impedance, creates a pole within the loop gain that degrades the phase margin. The degradation of the phase margin increases as the capacitive loading increases. When operating in the unity-gain configuration, the OPAx328 remain stable with a pure capacitive load up to 100 pF.

Figure 7-1 shows one technique to increase the capacitive load drive capability of an amplifier operating in a unity-gain configuration is to insert a small resistor ( $R_S$ ), typically 10  $\Omega$  to 50  $\Omega$ , in series with the output. This resistor significantly reduces the overshoot and ringing associated with large capacitive loads.




Figure 7-1. Improving Capacitive Load Drive

#### 7.2 Typical Applications

#### 7.2.1 Bidirectional Current-Sensing

This single-supply, low-side, bidirectional current-sensing design example detects load currents from -1 A to +1 A. The single-ended output spans from 110 mV to 3.19 V. This design uses the OPAx328 because of the low offset voltage and rail-to-rail input and output. One of the amplifiers is configured as a difference amplifier and the other amplifier provides the reference voltage.

Figure 7-2 shows the schematic.




Figure 7-2. Bidirectional Current-Sensing Schematic

#### 7.2.1.1 Design Requirements

This design example has the following requirements:

- Supply voltage: 3.3 V
- Input: –1 A to +1 A
- Output: 1.65 V ±1.54 V (110 mV to 3.19 V)

#### 7.2.1.2 Detailed Design Procedure

The load current,  $I_{LOAD}$ , flows through the shunt resistor,  $R_{SHUNT}$ , to develop the shunt voltage,  $V_{SHUNT}$ . The shunt voltage is then amplified by the difference amplifier consisting of U1A and  $R_1$  through  $R_4$ . The gain of the difference amplifier is set by the ratio of  $R_4$  to  $R_3$ . To minimize errors, set  $R_2 = R_4$  and  $R_1 = R_3$ . The reference voltage,  $V_{REF}$ , is supplied by buffering a resistor divider using U1B. The transfer function is given by Equation 1.

$$V_{OUT} = V_{SHUNT} \times Gain_{Diff_{Amp}} + V_{REF}$$

where

- $V_{SHUNT} = I_{LOAD} \times R_{SHUNT}$
- Gain<sub>Diff\_Amp</sub> =  $\frac{R_4}{R_3}$

$$V_{\text{REF}} = V_{\text{CC}} \times \left[ \frac{R_6}{R_5 + R_6} \right]$$

There are two types of errors in this design: offset and gain. Gain errors are introduced by the tolerance of the shunt resistor and the ratios of  $R_4$  to  $R_3$  and, similarly,  $R_2$  to  $R_1$ . Offset errors are introduced by the voltage divider ( $R_5$  and  $R_6$ ) and how closely the ratio of  $R_4 / R_3$  matches  $R_2 / R_1$ . The latter value affects the CMRR of the difference amplifier, ultimately translating to an offset error.

The value of  $V_{SHUNT}$  is the ground potential for the system load because  $V_{SHUNT}$  is a low-side measurement. Therefore, a maximum value must be placed on  $V_{SHUNT}$ . In this design, the maximum value for  $V_{SHUNT}$  is set to 100 mV. Equation 2 calculates the maximum value of the shunt resistor given a maximum shunt voltage of 100 mV and maximum load current of 1 A.

$$R_{\text{SHUNT(Max)}} = \frac{V_{\text{SHUNT(Max)}}}{I_{\text{LOAD(Max)}}} = \frac{100 \text{ mV}}{1 \text{ A}} = 100 \text{ m}\Omega$$

(2)

(1)



The tolerance of  $R_{SHUNT}$  is directly proportional to cost. For this design, a shunt resistor with a tolerance of 0.5% is selected. If greater accuracy is required, select a 0.1% resistor or better.

The load current is bidirectional; therefore, the shunt voltage range is -100 mV to +100 mV. This voltage is divided down by R<sub>1</sub> and R<sub>2</sub> before reaching the operational amplifier, U1A. Make sure that the voltage present at the noninverting node of U1A is within the common-mode range of the device. Therefore, use an operational amplifier, such as the OPAx328, that has a common-mode range that extends below the negative supply voltage. Finally, to minimize offset error, the OPAx328 have a typical offset voltage of merely  $\pm 3 \mu V$  ( $\pm 25 \mu V$  maximum).

Given a symmetric load current of -1 A to +1 A, the voltage divider resistors (R<sub>5</sub> and R<sub>6</sub>) must be equal. To be consistent with the shunt resistor, a tolerance of 0.5% is selected. To minimize power consumption,  $10-k\Omega$  resistors are used.

To set the gain of the difference amplifier, the common-mode range and output swing of the OPAx328 must be considered. Equation 3 and Equation 4 depict the typical common-mode range and maximum output swing, respectively, of the OPAx328 given a 3.3-V supply.

$$-100 \text{ mV} < V_{CM} < 3.4 \text{ V}$$
 (3)

$$100 \text{ mV} < V_{OUT} < 3.2 \text{ V}$$
 (4)


The gain of the difference amplifier can now be calculated as shown in Equation 5:

$$Gain_{Diff\_Amp} = \frac{V_{OUT\_Max} - V_{OUT\_Min}}{R_{SHUNT} \times (I_{MAX} - I_{MIN})} = \frac{3.2 \text{ V} - 100 \text{ mV}}{100 \text{ m}\Omega \times [1 \text{ A} - (-1 \text{ A})]} = 15.5 \frac{\text{V}}{\text{V}}$$
(5)

The resistor value selected for  $R_1$  and  $R_3$  is 1 k $\Omega$ . A value of 15.4 k $\Omega$  is selected for  $R_2$  and  $R_4$  because this number is the nearest standard value. Therefore, the calculated gain of the difference amplifier is 15.4 V/V.

The gain error of the circuit primarily depends on  $R_1$  through  $R_4$ . As a result of this dependence, 0.1% resistors are selected. This configuration reduces the likelihood that the design requires a two-point calibration. A simple one-point calibration, if desired, removes the offset errors introduced by the 0.5% resistors.

#### 7.2.1.3 Application Curve





#### 7.2.2 Transimpedance Amplifier

Wide gain bandwidth, low input bias current, low input voltage, and low current noise make the OPAx328 excellent wideband photodiode transimpedance amplifiers. Low-voltage noise is important because photodiode capacitance causes the effective noise gain of the circuit to increase at high frequency.


Copyright © 2023 Texas Instruments Incorporated



Figure 7-4 shows that the key elements to a transimpedance design are the:

- Expected diode capacitance (C<sub>D</sub>), including the parasitic input common-mode voltage and differential-mode input capacitance
- Desired transimpedance gain (R<sub>F</sub>)
- Gain-bandwidth (GBW) = 40 MHz

With these three variables set, the feedback capacitor ( $C_F$ ) value can be set to control the frequency response.  $C_F$  includes the stray capacitance of  $R_F$ , which is 0.2 pF for a typical surface-mount resistor.



NOTE:  $C_F$  is optional to prevent gain peaking, and includes the stray capacitance of  $R_F$ .

#### Figure 7-4. Dual-Supply Transimpedance Amplifier


For an optimized frequency response, use Equation 6 to set the feedback pole:

$$\frac{1}{2\pi R_F C_F} = \sqrt{\frac{GBW}{4\pi R_F C_D}}$$
(6)

Equation 7 calculates the bandwidth:

$$f_{-3dB} = \sqrt{\frac{GBW}{2\pi R_F C_D}} \qquad (Hz)$$

For single-supply applications, the +IN input can be biased with a positive dc voltage to allow the output to reach true zero when the photodiode is not exposed to any light, and respond without the added delay that results from coming out of the negative rail. Figure 7-5 shows this configuration. This bias voltage also appears across the photodiode, providing a reverse bias for faster operation.



NOTE:  $C_F$  is optional to prevent gain peaking, and includes the stray capacitance of  $R_F$ .

## Figure 7-5. Single-Supply Transimpedance Amplifier

For more information, see the Compensate Transimpedance Amplifiers Intuitively application report.



#### 7.3 Power Supply Recommendations

The OPAx328 are specified for operation from 2.2 V to 5.5 V ( $\pm$ 1.1 V to  $\pm$ 2.75 V); many specifications apply from -40°C to +125°C. Parameters that can exhibit significant variance with regard to operating voltage or temperature are presented in *Section* 5.7.

CAUTION

Supply voltages greater than 6 V can permanently damage the device; see Section 5.1.


Place 0.1-µF bypass capacitors close to the power-supply pins to reduce errors coupling in from noisy or high-impedance power supplies. For more detailed information on bypass capacitor placement, see *Section 7.4*.

#### 7.4 Layout

#### 7.4.1 Layout Guidelines

The OPA328 is a wideband amplifier. To realize the full operational performance of this device, use good, high-frequency PCB layout practices. Connect the bypass capacitors between each supply pin and ground, as close to the device as possible. Design the bypass capacitor traces for minimum inductance.

#### 7.4.2 Layout Example






Figure 7-6. Operational Amplifier Board Layout for Noninverting Configuration



## 8 Device and Documentation Support

### 8.1 Device Support

#### 8.1.1 Development Support

#### 8.1.1.1 PSpice<sup>®</sup> for TI

PSpice<sup>®</sup> for TI is a design and simulation environment that helps evaluate performance of analog circuits. Create subsystem designs and prototype solutions before committing to layout and fabrication, reducing development cost and time to market.

#### 8.1.1.2 TINA-TI™ Simulation Software (Free Download)

TINA-TI<sup>™</sup> simulation software is a simple, powerful, and easy-to-use circuit simulation program based on a SPICE engine. TINA-TI simulation software is a free, fully-functional version of the TINA<sup>™</sup> software, preloaded with a library of macromodels, in addition to a range of both passive and active models. TINA-TI simulation software provides all the conventional dc, transient, and frequency domain analysis of SPICE, as well as additional design capabilities.

Available as a free download from the Design tools and simulation web page, TINA-TI simulation software offers extensive post-processing capability that allows users to format results in a variety of ways. Virtual instruments offer the ability to select input waveforms and probe circuit nodes, voltages, and waveforms, creating a dynamic quick-start tool.

#### Note

These files require that either the TINA software or TINA-TI software be installed. Download the free TINA-TI simulation software from the TINA-TI™ software folder.

#### 8.1.1.3 DIP-Adapter-EVM

Speed up your op amp prototyping and testing with the DIP-Adapter-EVM, which provides a fast, easy and inexpensive way to interface with small, surface-mount devices. Connect any supported op amp using the included Samtec terminal strips or wire them directly to existing circuits. The DIP-Adapter-EVM kit supports the following industry-standard packages: D or U (SOIC-8), PW (TSSOP-8), DGK (VSSOP-8), DBV (SOT-23-6, SOT-23-5 and SOT-23-3), DCK (SC70-6 and SC70-5), and DRL (SOT563-6).

#### 8.1.1.4 DIYAMP-EVM

The DIYAMP-EVM is a unique evaluation module (EVM) that provides real-world amplifier circuits, enabling the user to quickly evaluate design concepts and verify simulations. This EVM is available in three industry-standard packages (SC70, SOT23, and SOIC) and 12 popular amplifier configurations, including amplifiers, filters, stability compensation, and comparator configurations for both single and dual supplies.

#### 8.1.1.5 Filter Design Tool

The filter design tool is a simple, powerful, and easy-to-use active filter design program. The filter design tool allows the user to create optimized filter designs using a selection of TI operational amplifiers and passive components from TI's vendor partners.

Available as a web-based tool from the Design tools and simulation web page, the filter design tool allows the user to design, optimize, and simulate complete multistage active filter solutions within minutes.



### 8.2 Documentation Support

#### 8.2.1 Related Documentation

The following documents are recommended as a reference for this device, and available for download at www.ti.com:

- Texas Instruments, Software Pacemaker Detection Design Guide
- Texas Instruments, TIDA-00378 Schematic and Block Diagram
- Texas Instruments, PM2.5/PM10 Particle Sensor Analog Front-End for Air Quality Monitoring Design
- Texas Instruments, QFN/SON PCB Attachment
- Texas Instruments, Quad Flatpack No-Lead Logic Packages
- Texas Instruments, Compensate Transimpedance Amplifiers Intuitively
- Texas Instruments, Noise Analysis of FET Transimpedance Amplifiers
- Texas Instruments, Noise Analysis for High-Speed Op Amps

#### 8.3 Receiving Notification of Documentation Updates

To receive notification of documentation updates, navigate to the device product folder on ti.com. Click on *Notifications* to register and receive a weekly digest of any product information that has changed. For change details, review the revision history included in any revised document.

#### 8.4 Support Resources

TI E2E<sup>™</sup> support forums are an engineer's go-to source for fast, verified answers and design help — straight from the experts. Search existing answers or ask your own question to get the quick design help you need.

Linked content is provided "AS IS" by the respective contributors. They do not constitute TI specifications and do not necessarily reflect TI's views; see TI's Terms of Use.

#### 8.5 Trademarks

e-trim<sup>™</sup>, TINA-TI<sup>™</sup>, and TI E2E<sup>™</sup> are trademarks of Texas Instruments.

TINA<sup>™</sup> is a trademark of DesignSoft, Inc.

PSpice® is a registered trademark of Cadence Design Systems, Inc.

All trademarks are the property of their respective owners.

#### 8.6 Electrostatic Discharge Caution



This integrated circuit can be damaged by ESD. Texas Instruments recommends that all integrated circuits be handled with appropriate precautions. Failure to observe proper handling and installation procedures can cause damage.

ESD damage can range from subtle performance degradation to complete device failure. Precision integrated circuits may be more susceptible to damage because very small parametric changes could cause the device not to meet its published specifications.

#### 8.7 Glossary

TI Glossary This glossary lists and explains terms, acronyms, and definitions.

## **9 Revision History**

NOTE: Page numbers for previous revisions may differ from page numbers in the current version.

С	hanges from Revision C (May 2023) to Revision D (December 2023)	Page
•	Changed OPA2328 D (SOIC, 8) and DRG (WSON, 8) package status from preview to production data (active) and added associated content	1
С	hanges from Revision B (November 2022) to Revision C (May 2023)	Page
	Changed OPA328 DBV/ (SOT-23, 5) package from advanced information (preview) to production data	

#### 

## 10 Mechanical, Packaging, and Orderable Information

The following pages include mechanical, packaging, and orderable information. This information is the most current data available for the designated devices. This data is subject to change without notice and revision of this document. For browser-based versions of this data sheet, refer to the left-hand navigation.



## PACKAGING INFORMATION

Orderable Device	Status	Package Type		Pins	-	Eco Plan	Lead finish/	MSL Peak Temp	Op Temp (°C)	Device Marking	Samples
	(1)		Drawing		Qty	(2)	Ball material	(3)		(4/5)	
OPA2328DGKR	ACTIVE	VSSOP	DGK	8	2500	RoHS & Green	NIPDAU	Level-2-260C-1 YEAR	-40 to 125	2K6S	
	AOTIVE	10001	DOIN	0	2000	Rono & Oreen		ECVCI 2 2000 T TEAK	40 10 120	2100	Samples
OPA2328DGKT	ACTIVE	VSSOP	DGK	8	250	RoHS & Green	NIPDAU	Level-2-260C-1 YEAR	-40 to 125	2K6S	Samples
											1
OPA2328DR	ACTIVE	SOIC	D	8	3000	RoHS & Green	NIPDAU	Level-2-260C-1 YEAR	-40 to 125	2328W	Samples
OPA328DBVR	ACTIVE	SOT-23	DBV	5	3000	RoHS & Green	SN	Level-1-260C-UNLIM	-40 to 125	OP328	Samples
OPA328DBVR	ACTIVE	SOT-23	DBV	5	3000	RoHS & Green	SN	Level-1-260C-UNLIM	-40 to 125	OP328	Samples

<sup>(1)</sup> The marketing status values are defined as follows:

ACTIVE: Product device recommended for new designs.

LIFEBUY: TI has announced that the device will be discontinued, and a lifetime-buy period is in effect.

NRND: Not recommended for new designs. Device is in production to support existing customers, but TI does not recommend using this part in a new design.

PREVIEW: Device has been announced but is not in production. Samples may or may not be available.

**OBSOLETE:** TI has discontinued the production of the device.

<sup>(2)</sup> RoHS: TI defines "RoHS" to mean semiconductor products that are compliant with the current EU RoHS requirements for all 10 RoHS substances, including the requirement that RoHS substance do not exceed 0.1% by weight in homogeneous materials. Where designed to be soldered at high temperatures, "RoHS" products are suitable for use in specified lead-free processes. TI may reference these types of products as "Pb-Free".

**RoHS Exempt:** TI defines "RoHS Exempt" to mean products that contain lead but are compliant with EU RoHS pursuant to a specific EU RoHS exemption.

Green: TI defines "Green" to mean the content of Chlorine (CI) and Bromine (Br) based flame retardants meet JS709B low halogen requirements of <=1000ppm threshold. Antimony trioxide based flame retardants must also meet the <=1000ppm threshold requirement.

<sup>(3)</sup> MSL, Peak Temp. - The Moisture Sensitivity Level rating according to the JEDEC industry standard classifications, and peak solder temperature.

<sup>(4)</sup> There may be additional marking, which relates to the logo, the lot trace code information, or the environmental category on the device.

<sup>(5)</sup> Multiple Device Markings will be inside parentheses. Only one Device Marking contained in parentheses and separated by a "~" will appear on a device. If a line is indented then it is a continuation of the previous line and the two combined represent the entire Device Marking for that device.

<sup>(6)</sup> Lead finish/Ball material - Orderable Devices may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead finish/Ball material values may wrap to two lines if the finish value exceeds the maximum column width.

Important Information and Disclaimer: The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and



www.ti.com

continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.




Texas

STRUMENTS

### TAPE AND REEL INFORMATION





#### QUADRANT ASSIGNMENTS FOR PIN 1 ORIENTATION IN TAPE



*All dimensions are nominal												
Device	Package Type	Package Drawing		SPQ	Reel Diameter (mm)	Reel Width W1 (mm)	A0 (mm)	B0 (mm)	K0 (mm)	P1 (mm)	W (mm)	Pin1 Quadrant
OPA2328DGKR	VSSOP	DGK	8	2500	330.0	12.4	5.3	3.4	1.4	8.0	12.0	Q1
OPA2328DGKT	VSSOP	DGK	8	250	180.0	12.4	5.3	3.4	1.4	8.0	12.0	Q1
OPA2328DR	SOIC	D	8	3000	330.0	12.4	6.4	5.2	2.1	8.0	12.0	Q1



www.ti.com

## PACKAGE MATERIALS INFORMATION

10-Jan-2024



\*All dimensions are nominal

Device	Package Type	Package Drawing	Pins	SPQ	Length (mm)	Width (mm)	Height (mm)
OPA2328DGKR	VSSOP	DGK	8	2500	356.0	356.0	35.0
OPA2328DGKT	VSSOP	DGK	8	250	210.0	185.0	35.0
OPA2328DR	SOIC	D	8	3000	356.0	356.0	35.0

# **DBV0005A**



# **PACKAGE OUTLINE**

## SOT-23 - 1.45 mm max height

SMALL OUTLINE TRANSISTOR



NOTES:

- 1. All linear dimensions are in millimeters. Any dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.
   This drawing is subject to change without notice.
   Reference JEDEC MO-178.

- 4. Body dimensions do not include mold flash, protrusions, or gate burrs. Mold flash, protrusions, or gate burrs shall not exceed 0.25 mm per side.
- 5. Support pin may differ or may not be present.



# **DBV0005A**

# **EXAMPLE BOARD LAYOUT**

## SOT-23 - 1.45 mm max height

SMALL OUTLINE TRANSISTOR



NOTES: (continued)

6. Publication IPC-7351 may have alternate designs.

7. Solder mask tolerances between and around signal pads can vary based on board fabrication site.



## **DBV0005A**

# **EXAMPLE STENCIL DESIGN**

## SOT-23 - 1.45 mm max height

SMALL OUTLINE TRANSISTOR



NOTES: (continued)

8. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.

9. Board assembly site may have different recommendations for stencil design.



# D0008A



## **PACKAGE OUTLINE**

## SOIC - 1.75 mm max height

SMALL OUTLINE INTEGRATED CIRCUIT



#### NOTES:

1. Linear dimensions are in inches [millimeters]. Dimensions in parenthesis are for reference only. Controlling dimensions are in inches. Dimensioning and tolerancing per ASME Y14.5M.

- 2. This drawing is subject to change without notice.
- 3. This dimension does not include mold flash, protrusions, or gate burrs. Mold flash, protrusions, or gate burrs shall not exceed .006 [0.15] per side.
- 4. This dimension does not include interlead flash.
- 5. Reference JEDEC registration MS-012, variation AA.



# D0008A

# **EXAMPLE BOARD LAYOUT**

## SOIC - 1.75 mm max height

SMALL OUTLINE INTEGRATED CIRCUIT



NOTES: (continued)

6. Publication IPC-7351 may have alternate designs.

7. Solder mask tolerances between and around signal pads can vary based on board fabrication site.



## D0008A

# **EXAMPLE STENCIL DESIGN**

## SOIC - 1.75 mm max height

SMALL OUTLINE INTEGRATED CIRCUIT



NOTES: (continued)

8. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.

9. Board assembly site may have different recommendations for stencil design.



DGK (S-PDSO-G8)

PLASTIC SMALL-OUTLINE PACKAGE



NOTES: A. All linear dimensions are in millimeters.

B. This drawing is subject to change without notice.

Body length does not include mold flash, protrusions, or gate burrs. Mold flash, protrusions, or gate burrs shall not exceed 0.15 per end.

- D Body width does not include interlead flash. Interlead flash shall not exceed 0.50 per side.
- E. Falls within JEDEC MO-187 variation AA, except interlead flash.



## IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATA SHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, regulatory or other requirements.

These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you will fully indemnify TI and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to TI's Terms of Sale or other applicable terms available either on ti.com or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products.

TI objects to and rejects any additional or different terms you may have proposed.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265 Copyright © 2024, Texas Instruments Incorporated