SN54HC163 . . . J OR W PACKAGE SN74HC163 . . . D, DB, N, NS, OR PW PACKAGE

(TOP VIEW)

SCLS298D - JANUARY 1996 - REVISED - OCTOBER 2003


- Wide Operating Voltage Range of 2 V to 6 V
- Outputs Can Drive Up To 10 LSTTL Loads
- Low Power Consumption, 80-μA Max I<sub>CC</sub>
- Typical t<sub>pd</sub> = 14 ns
- ±4-mA Output Drive at 5 V
- Low Input Current of 1 μA Max
- Internal Look-Ahead for Fast Counting
- Carry Output for n-Bit Cascading
- Synchronous Counting
- Synchronously Programmable

#### description/ordering information

These synchronous, presettable counters feature an internal carry look-ahead for application in high-speed counting designs. The 'HC163 devices are 4-bit binary counters. Synchronous operation is provided by having all flip-flops clocked simultaneously so that the outputs change coincident with each other when instructed by the count-enable (ENP, ENT) inputs and internal gating. This mode of operation eliminates the output counting spikes normally associated with synchronous (ripple-clock) counters. A buffered clock (CLK) input triggers the four flip-flops on the rising (positive-going) edge of the clock waveform.

|  | • |   |   |
|--|---|---|---|
| CLR<br>CLK<br>A<br>B<br>C<br>C<br>C<br>C<br>C<br>C<br>C<br>C<br>C<br>C<br>C<br>C<br>C<br>C<br>C<br>C<br>C<br>C | 2 | 16<br>15<br>14<br>13<br>12<br>11<br>10<br>9 | V <sub>CC</sub><br>RCO<br>Q <sub>A</sub><br>Q <sub>B</sub><br>Q <sub>C</sub><br>Q <sub>D</sub><br>ENT<br>LOAD |
|  |   |   |   |

SN54HC163 . . . FK PACKAGE (TOP VIEW)



NC - No internal connection

|                | •          |              |                          |                     |
|----------------|------------|--------------|--------------------------|---------------------|
| Τ <sub>Α</sub> | PACKA      | GEŤ          | ORDERABLE<br>PART NUMBER | TOP-SIDE<br>MARKING |
|                | PDIP – N   | Tube of 25   | SN74HC163N               | SN74HC163N          |
|                |            | Tube of 40   | SN74HC163D               |                     |
| −40°C to 85°C  | SOIC – D   | Reel of 2500 | SN74HC163DR              | HC163               |
|                |            | Reel of 250  | SN74HC163DT              |                     |
|                | SOP – NS   | Reel of 2000 | SN74HC163NSR             | HC163               |
|                | SSOP – DB  | Reel of 2000 | SN74HC163DBR             | HC163               |
|                |            | Tube of 90   | SN74HC163PW              |                     |
|                | TSSOP – PW | Reel of 2000 | SN74HC163PWR             | HC163               |
|                |            | Reel of 250  | SN74HC163PWT             |                     |
|                | CDIP – J   | Tube of 25   | SNJ54HC163J              | SNJ54HC163J         |
| –55°C to 125°C | CFP – W    | Tube of 150  | SNJ54HC163W              | SNJ54HC163W         |
| l              | LCCC – FK  | Tube of 55   | SNJ54HC163FK             | SNJ54HC163FK        |

#### **ORDERING INFORMATION**

<sup>†</sup> Package drawings, standard packing quantities, thermal data, symbolization, and PCB design guidelines are available at www.ti.com/sc/package.



Please be aware that an important notice concerning availability, standard warranty, and use in critical applications of Texas Instruments semiconductor products and disclaimers thereto appears at the end of this data sheet.

PRODUCTION DATA information is current as of publication date. Products conform to specifications per the terms of Texas Instruments standard warranty. Production processing does not necessarily include testing of all parameters.



Copyright © 2003, Texas Instruments Incorporated On products compliant to MIL-PRF-38535, all parameters are tested unless otherwise noted. On all other products, production processing does not necessarily include testing of all parameters.

#### SCLS298D - JANUARY 1996 - REVISED - OCTOBER 2003

### description/ordering information (continued)

These counters are fully programmable; that is, they can be preset to any number between 0 and 9 or 15. As presetting is synchronous, setting up a low level at the load input disables the counter and causes the outputs to agree with the setup data after the next clock pulse, regardless of the levels of the enable inputs.


The clear function for the 'HC163 devices is synchronous. A low level at the clear ( $\overline{\text{CLR}}$ ) input sets all four of the flip-flop outputs low after the next low-to-high transition of CLK, regardless of the levels of the enable inputs. This synchronous clear allows the count length to be modified easily by decoding the Q outputs for the maximum count desired. The active-low output of the gate used for decoding is connected to  $\overline{\text{CLR}}$  to synchronously clear the counter to 0000 (LLLL).

The carry look-ahead circuitry provides for cascading counters for n-bit synchronous applications without additional gating. ENP, ENT, and a ripple-carry output (RCO) are instrumental in accomplishing this function. Both ENP and ENT must be high to count, and ENT is fed forward to enable RCO. Enabling RCO produces a high-level pulse while the count is maximum (9 or 15 with  $Q_A$  high). This high-level overflow ripple-carry pulse can be used to enable successive cascaded stages. Transitions at ENP or ENT are allowed, regardless of the level of CLK.

These counters feature a fully independent clock circuit. Changes at control inputs (ENP, ENT, or  $\overline{\text{LOAD}}$ ) that modify the operating mode have no effect on the contents of the counter until clocking occurs. The function of the counter (whether enabled, disabled, loading, or counting) is dictated solely by the conditions meeting the stable setup and hold times.



SCLS298D - JANUARY 1996 - REVISED - OCTOBER 2003



logic diagram (positive logic)


<sup>†</sup> For simplicity, routing of complementary signals LD and CK is not shown on this overall logic diagram. The uses of these signals are shown on the logic diagram of the D/T flip-flops.

Pin numbers shown are for the D, DB, J, N, NS, PW, and W packages.




SCLS298D - JANUARY 1996 - REVISED - OCTOBER 2003

logic symbol, each D/T flip-flop



### logic diagram, each D/T flip-flop (positive logic)



<sup>†</sup> The origins of  $\overline{\text{LD}}$  and  $\overline{\text{CK}}$  are shown in the logic diagram of the overall device.




SCLS298D - JANUARY 1996 - REVISED - OCTOBER 2003

#### typical clear, preset, count, and inhibit sequence

The following sequence is illustrated below:

- 1. Clear outputs to zero (synchronous)
- 2. Preset to binary 12
- 3. Count to 13, 14, 15, 0, 1, and 2
- 4. Inhibit





SCLS298D - JANUARY 1996 - REVISED - OCTOBER 2003

#### absolute maximum ratings over operating free-air temperature range (unless otherwise noted)<sup>†</sup>

| Supply voltage range, $V_{CC}$<br>Input clamp current, $I_{IK}$ ( $V_I < 0$ or $V_I > V_{CC}$ ) (se<br>Output clamp current, $I_{OK}$ ( $V_O < 0$ or $V_O > V_{CC}$<br>Continuous output current, $I_O$ ( $V_O = 0$ to $V_{CC}$ )<br>Continuous current through $V_{CC}$ or GND<br>Package thermal impedance, $\theta_{JA}$ (see Note 2): | ee Note 1)<br>C) (see Note 1)<br>D package<br>DB package<br>N package<br>NS package<br>PW package | ±20 mA<br>±20 mA<br>±25 mA<br>73°C/W<br>82°C/W<br>67°C/W<br>64°C/W<br>108°C/W |
|---|---|---|
| Storage temperature range, T <sub>stg</sub>   |   |   |

<sup>†</sup> Stresses beyond those listed under "absolute maximum ratings" may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated under "recommended operating conditions" is not implied. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability.

NOTES: 1. The input and output voltage ratings may be exceeded if the input and output current ratings are observed.

2. The package thermal impedance is calculated in accordance with JESD 51-7.

#### recommended operating conditions (see Note 3)

|                                  |                                 |                  | SN      | 154HC16 | 63   | SN   | 63  |      |      |
|----------------------------------|---------------------------------|------------------|---------|---------|------|------|-----|------|------|
|                                  |                                 |                  | MIN NON |         | MAX  | MIN  | NOM | MAX  | UNIT |
| VCC                              | Supply voltage                  |                  | 2       | 5       | 6    | 2    | 5   | 6    | V    |
|                                  |                                 | $V_{CC} = 2 V$   | 1.5     |         |      | 1.5  |     |      |      |
| VIH                              | High-level input voltage        | $V_{CC} = 4.5 V$ | 3.15    |         |      | 3.15 |     |      | V    |
|                                  |                                 | $V_{CC} = 6 V$   | 4.2     |         |      | 4.2  |     |      |      |
|                                  |                                 | $V_{CC} = 2 V$   |         |         | 0.5  |      |     | 0.5  |      |
| VIL                              | Low-level input voltage         | $V_{CC} = 4.5 V$ |         |         | 1.35 |      |     | 1.35 | V    |
|                                  |                                 | $V_{CC} = 6 V$   |         |         | 1.8  |      |     | 1.8  |      |
| VI                               | Input voltage                   |                  | 0       |         | VCC  | 0    |     | VCC  | V    |
| VO                               | Output voltage                  |                  | 0       |         | VCC  | 0    |     | VCC  | V    |
|                                  |                                 | $V_{CC} = 2 V$   |         |         | 1000 |      |     | 1000 |      |
| $\Delta t / \Delta v^{\ddagger}$ | Input transition rise/fall time | $V_{CC} = 4.5 V$ |         |         | 500  |      |     | 500  | ns   |
|                                  |                                 | $V_{CC} = 6 V$   |         |         | 400  |      |     | 400  |      |
| Т <sub>А</sub>                   | Operating free-air temperature  |                  | -55     |         | 125  | -40  |     | 85   | °C   |

NOTE 3: All unused inputs of the device must be held at V<sub>CC</sub> or GND to ensure proper device operation. Refer to the TI application report, Implications of Slow or Floating CMOS Inputs, literature number SCBA004.

If this device is used in the threshold region (from V<sub>IL</sub>max = 0.5 V to V<sub>IH</sub>min = 1.5 V), there is a potential to go into the wrong state from induced grounding, causing double clocking. Operating with the inputs at t<sub>t</sub> = 1000 ns and V<sub>CC</sub> = 2 V does not damage the device; however, functionally, the CLK inputs are not ensured while in the shift, count, or toggle operating modes.



SCLS298D - JANUARY 1996 - REVISED - OCTOBER 2003

electrical characteristics over recommended operating free-air temperature range (unless otherwise noted)

|           |                               |                           |            | Т    | A = 25°C | ;    | SN54H | IC163 | SN74H | C163  |      |
|-----------|-------------------------------|---------------------------|------------|------|----------|------|-------|-------|-------|-------|------|
| PARAMETER | TEST CO                       | NDITIONS                  | Vcc        | MIN  | TYP      | MAX  | MIN   | MAX   | MIN   | MAX   | UNIT |
|           |                               |                           | 2 V        | 1.9  | 1.998    |      | 1.9   |       | 1.9   |       |      |
|           |                               | I <sub>OH</sub> = -20 μA  | 4.5 V      | 4.4  | 4.499    |      | 4.4   |       | 4.4   |       |      |
| VOH       | VI = VIH or VIL               |                           | 6 V        | 5.9  | 5.999    |      | 5.9   |       | 5.9   |       | V    |
|           |                               | $I_{OH} = -4 \text{ mA}$  | 4.5 V      | 3.98 | 4.3      |      | 3.7   |       | 3.84  |       |      |
|           |                               | I <sub>OH</sub> = -5.2 mA | 6 V        | 5.48 | 5.8      |      | 5.2   |       | 5.34  |       |      |
|           |                               |                           | 2 V        |      | 0.002    | 0.1  |       | 0.1   |       | 0.1   |      |
|           |                               | I <sub>OL</sub> = 20 μA   | 4.5 V      |      | 0.001    | 0.1  |       | 0.1   |       | 0.1   |      |
| VOL       | VI = VIH or VIL               |                           | 6 V        |      | 0.001    | 0.1  |       | 0.1   |       | 0.1   | V    |
|           |                               | $I_{OL} = 4 \text{ mA}$   | 4.5 V      |      | 0.17     | 0.26 |       | 0.4   |       | 0.33  |      |
|           |                               | I <sub>OL</sub> = 5.2 mA  | 6 V        |      | 0.15     | 0.26 |       | 0.4   |       | 0.33  |      |
| lı        | $V_I = V_{CC} \text{ or } 0$  |                           | 6 V        |      | ±0.1     | ±100 |       | ±1000 |       | ±1000 | nA   |
| ICC       | $V_I = V_{CC} \text{ or } 0,$ | IO = 0                    | 6 V        |      |          | 8    |       | 160   |       | 80    | μΑ   |
| Ci        |                               |                           | 2 V to 6 V |      | 3        | 10   |       | 10    |       | 10    | pF   |

# timing requirements over recommended operating free-air temperature range (unless otherwise noted)

|                 |                                    |                     |       | T <sub>A</sub> = | 25°C | SN54F | IC163 | SN74H | IC163 |      |
|-----------------|------------------------------------|---------------------|-------|------------------|------|-------|-------|-------|-------|------|
|                 |                                    |                     | Vcc   | MIN              | MAX  | MIN   | MAX   | MIN   | MAX   | UNIT |
|                 |                                    |                     | 2 V   |                  | 6    |       | 4.2   |       | 5     |      |
| fclock          | Clock frequency                    |                     | 4.5 V |                  | 31   |       | 21    |       | 25    | MHz  |
|                 |                                    |                     | 6 V   |                  | 36   |       | 25    |       | 29    |      |
|                 |                                    |                     | 2 V   | 80               |      | 120   |       | 100   |       |      |
| tw              | Pulse duration                     | CLK high or low     | 4.5 V | 16               |      | 24    |       | 20    |       | ns   |
|                 |                                    |                     | 6 V   | 14               |      | 20    |       | 17    |       |      |
|                 |                                    |                     | 2 V   | 150              |      | 225   |       | 190   |       |      |
| 1               |                                    | A, B, C, or D       | 4.5 V | 30               |      | 45    |       | 38    |       |      |
|                 |                                    |                     | 6 V   | 26               |      | 38    |       | 32    |       |      |
|                 |                                    |                     | 2 V   | 135              |      | 205   |       | 170   |       |      |
|                 |                                    | LOAD low            | 4.5 V | 27               |      | 41    |       | 34    |       |      |
|                 |                                    |                     | 6 V   | 23               |      | 35    |       | 29    |       |      |
|                 |                                    |                     | 2 V   | 170              |      | 255   |       | 215   |       |      |
| t <sub>su</sub> | Setup time before CLK <sup>↑</sup> | ENP, ENT            | 4.5 V | 34               |      | 51    |       | 43    |       | ns   |
|                 |                                    |                     | 6 V   | 29               |      | 43    |       | 37    |       |      |
|                 |                                    |                     | 2 V   | 160              |      | 240   |       | 200   |       |      |
|                 |                                    | CLR low             | 4.5 V | 32               |      | 48    |       | 40    |       |      |
|                 |                                    |                     | 6 V   | 27               |      | 41    |       | 34    |       |      |
|                 |                                    |                     | 2 V   | 160              |      | 240   |       | 200   |       |      |
|                 |                                    | <b>CLR</b> inactive | 4.5 V | 32               |      | 48    |       | 40    |       |      |
|                 |                                    |                     | 6 V   | 27               |      | 41    |       | 34    |       |      |
|                 |                                    | ÷                   | 2 V   | 0                |      | 0     |       | 0     |       |      |
| <sup>t</sup> h  | Hold time, all synchronous inpu    | ts after CLK↑       | 4.5 V | 0                |      | 0     |       | 0     |       | ns   |
|                 |                                    |                     | 6 V   | 0                |      | 0     |       | 0     |       |      |



SCLS298D – JANUARY 1996 – REVISED – OCTOBER 2003

# switching characteristics over recommended operating free-air temperature range, $C_L = 50 \text{ pF}$ (unless otherwise noted) (see Figure 1)


|                 | FROM    | то       |       | T,  | <b>₄ = 25°C</b> | ;   | SN54H | IC163 | SN74H | C163 |      |
|-----------------|---------|----------|-------|-----|-----------------|-----|-------|-------|-------|------|------|
| PARAMETER       | (INPUT) | (OUTPUT) | VCC   | MIN | TYP             | MAX | MIN   | MAX   | MIN   | MAX  | UNIT |
|                 |         |          | 2 V   | 6   | 14              |     | 4.2   |       | 5     |      |      |
| fmax            |         |          | 4.5 V | 31  | 40              |     | 21    |       | 25    |      | MHz  |
|                 |         |          | 6 V   | 36  | 44              |     | 25    |       | 29    |      |      |
|                 |         |          | 2 V   |     | 83              | 215 |       | 325   |       | 270  |      |
|                 |         | RCO      | 4.5 V |     | 24              | 43  |       | 65    |       | 54   |      |
|                 | CLK     |          | 6 V   |     | 20              | 37  |       | 55    |       | 46   |      |
|                 | CLK     |          | 2 V   |     | 80              | 205 |       | 310   |       | 255  |      |
| <sup>t</sup> pd |         | Any Q    | 4.5 V |     | 25              | 41  |       | 62    |       | 51   | ns   |
|                 |         |          | 6 V   |     | 21              | 35  |       | 53    |       | 43   |      |
|                 |         |          | 2 V   |     | 62              | 195 |       | 295   |       | 245  |      |
|                 | ENT     | RCO      | 4.5 V |     | 17              | 39  |       | 59    |       | 49   |      |
|                 |         |          | 6 V   |     | 14              | 33  |       | 50    |       | 42   |      |
|                 |         |          | 2 V   |     | 38              | 75  |       | 110   |       | 95   |      |
| tt              |         | Any      | 4.5 V |     | 8               | 15  |       | 22    |       | 19   | ns   |
|                 |         |          | 6 V   |     | 6               | 13  |       | 19    |       | 16   |      |

## operating characteristics, $T_A = 25^{\circ}C$

|     | PARAMETER                     | TEST CONDITIONS | TYP | UNIT |
|-----|-------------------------------|-----------------|-----|------|
| Cpd | Power dissipation capacitance | No load         | 60  | pF   |



SCLS298D - JANUARY 1996 - REVISED - OCTOBER 2003



### PARAMETER MEASUREMENT INFORMATION

NOTES: A. CI includes probe and test-fixture capacitance.

- B. Phase relationships between waveforms were chosen arbitrarily. All input pulses are supplied by generators having the following characteristics: PRR  $\leq$  1 MHz, Z<sub>O</sub> = 50  $\Omega$ , t<sub>f</sub> = 6 ns, t<sub>f</sub> = 6 ns.
- C. For clock inputs, fmax is measured when the input duty cycle is 50%.
- D. The outputs are measured one at a time with one input transition per measurement.
- E. tPLH and tPHL are the same as tpd.

#### Figure 1. Load Circuit and Voltage Waveforms



SCLS298D - JANUARY 1996 - REVISED - OCTOBER 2003

### **APPLICATION INFORMATION**


#### n-bit synchronous counters

This application demonstrates how the look-ahead carry circuit can be used to implement a high-speed n-bit counter. The 'HC163 devices count in binary. Virtually any count mode (modulo-N,  $N_1$ -to- $N_2$ ,  $N_1$ -to-maximum) can be used with this fast look-ahead circuit.

The application circuit shown in Figure 2 is not valid for clock frequencies above 18 MHz (at 25°C and 4.5-V  $V_{CC}$ ). The reason for this is that there is a glitch that is produced on the second stage's RCO and every succeeding stage's RCO. This glitch is common to all HC vendors that Texas Instruments has evaluated, in addition to the bipolar equivalents (LS, ALS, AS).



SCLS298D - JANUARY 1996 - REVISED - OCTOBER 2003






SCLS298D - JANUARY 1996 - REVISED - OCTOBER 2003

### **APPLICATION INFORMATION**

#### n-bit synchronous counters (continued)

The glitch on RCO is caused because the propagation delay of the rising edge of  $Q_A$  of the second stage is shorter than the propagation delay of the falling edge of ENT. RCO is the product of ENT,  $Q_A$ ,  $Q_B$ ,  $Q_C$ , and  $Q_D$  (ENT ×  $Q_A × Q_B × Q_C × Q_D$ ). The resulting glitch is about 7–12 ns in duration. Figure 3 shows the condition in which the glitch occurs. For simplicity, only two stages are being considered, but the results can be applied to other stages.  $Q_B$ ,  $Q_C$ , and  $Q_D$  of the first and second stage are at logic one, and  $Q_A$  of both stages are at logic zero (1110 1110) after the first clock pulse. On the rising edge of the second clock pulse,  $Q_A$  and RCO of the first stage go high. On the rising edge of the third clock pulse,  $Q_A$  and RCO of the first stage return to a low level, and  $Q_A$  of the second stage goes to a high level. At this time, the glitch on RCO of the second stage appears because of the race condition inside the chip.





The glitch causes a problem in the next stage (stage three) if the glitch is still present when the next rising clock edge appears (clock pulse 4). To ensure that this does not happen, the clock frequency must be less than the inverse of the sum of the clock-to-RCO propagation delay and the glitch duration ( $t_g$ ). In other words,  $f_{max} = 1/(t_{pd} CLK-to-RCO + t_g)$ . For example, at 25°C at 4.5-V V<sub>CC</sub>, the clock-to-RCO propagation delay is 43 ns and the maximum duration of the glitch is 12 ns. Therefore, the maximum clock frequency that the cascaded counters can use is 18 MHz. The following tables contain the  $f_{clock}$ ,  $t_w$ , and  $f_{max}$  specifications for applications that use more than two 'HC163 devices cascaded together.



SCLS298D - JANUARY 1996 - REVISED - OCTOBER 2003

#### **APPLICATION INFORMATION**

#### n-bit synchronous counters (continued)

# timing requirements over recommended operating free-air temperature range (unless otherwise noted)

|        |                                 |       | T <sub>A</sub> = 25°C |     | SN54HC163 |     | SN74HC163 |     |      |     |  |  |
|--------|---------------------------------|-------|-----------------------|-----|-----------|-----|-----------|-----|------|-----|--|--|
|        |                                 | vcc   | MIN                   | MAX | MIN       | MAX | MIN       | MAX | UNIT |     |  |  |
|        |                                 | 2 V   |                       | 3.6 |           | 2.5 |           | 2.9 |      |     |  |  |
| fclock | Clock frequency                 | 4.5 V |                       | 18  |           | 12  |           | 14  | MHz  |     |  |  |
|        |                                 | 6 V   |                       | 21  |           | 14  |           | 17  |      |     |  |  |
|        | Pulse duration, CLK high or low |       |                       |     | 2 V       | 140 |           | 200 |      | 170 |  |  |
| tw     |                                 | 4.5 V | 28                    |     | 40        |     | 36        |     | ns   |     |  |  |
|        |                                 |       | 24                    |     | 36        |     | 30        |     |      |     |  |  |

# switching characteristics over recommended operating free-air temperature range, $C_L = 50 \text{ pF}$ (unless otherwise noted) (see Note 4)

| ſ | DADAMETER | FROM    | то       |       | T <sub>A</sub> = 25°C |     | SN54HC163 |     | SN74HC163 |     |      |
|---|-----------|---------|----------|-------|-----------------------|-----|-----------|-----|-----------|-----|------|
|   | PARAMETER | (INPUT) | (OUTPUT) | VCC   | MIN                   | MAX | MIN       | MAX | MIN       | MAX | UNIT |
| ſ |           |         |          | 2 V   | 3.6                   |     | 2.5       |     | 2.9       |     |      |
|   | fmax      |         |          | 4.5 V | 18                    |     | 12        |     | 14        |     | MHz  |
|   |           |         |          | 6 V   | 21                    |     | 14        |     | 17        |     |      |

NOTE 4: These limits apply only to applications that use more than two 'HC163 devices cascaded together.

If the 'HC163 devices are used as a single unit, or only two cascaded together, then the maximum clock frequency that the devices can use is not limited because of the glitch. In these situations, the devices can be operated at the maximum specifications.

A glitch can appear on RCO of a single 'HC163 device, depending on the relationship of ENT to CLK. Any application that uses RCO to drive any input, except an ENT of another cascaded 'HC163 device, must take this into consideration.





### **PACKAGING INFORMATION**

| Orderable Device | Status<br>(1) | Package Type | Package<br>Drawing | Pins | Package<br>Qty | Eco Plan<br>(2)     | Lead finish/<br>Ball material<br>(6) | MSL Peak Temp<br>(3) | Op Temp (°C) | Device Marking<br>(4/5)       | Samples |
|------------------|---------------|--------------|--------------------|------|----------------|---------------------|--------------------------------------|----------------------|--------------|-------------------------------|---------|
| 86076012A        | ACTIVE        | LCCC         | FK                 | 20   | 55             | Non-RoHS<br>& Green | SNPB                                 | N / A for Pkg Type   | -55 to 125   | 86076012A<br>SNJ54HC<br>163FK | Samples |
| 8607601EA        | ACTIVE        | CDIP         | J                  | 16   | 25             | Non-RoHS<br>& Green | SNPB                                 | N / A for Pkg Type   | -55 to 125   | 8607601EA<br>SNJ54HC163J      | Samples |
| JM38510/66304BEA | ACTIVE        | CDIP         | J                  | 16   | 25             | Non-RoHS<br>& Green | SNPB                                 | N / A for Pkg Type   | -55 to 125   | JM38510/<br>66304BEA          | Samples |
| M38510/66304BEA  | ACTIVE        | CDIP         | J                  | 16   | 25             | Non-RoHS<br>& Green | SNPB                                 | N / A for Pkg Type   | -55 to 125   | JM38510/<br>66304BEA          | Samples |
| SN54HC163J       | ACTIVE        | CDIP         | J                  | 16   | 25             | Non-RoHS<br>& Green | SNPB                                 | N / A for Pkg Type   | -55 to 125   | SN54HC163J                    | Samples |
| SN74HC163DR      | ACTIVE        | SOIC         | D                  | 16   | 2500           | RoHS & Green        | NIPDAU                               | Level-1-260C-UNLIM   | -40 to 85    | HC163                         | Samples |
| SN74HC163DRE4    | ACTIVE        | SOIC         | D                  | 16   | 2500           | RoHS & Green        | NIPDAU                               | Level-1-260C-UNLIM   | -40 to 85    | HC163                         | Samples |
| SN74HC163N       | ACTIVE        | PDIP         | N                  | 16   | 25             | RoHS & Green        | NIPDAU                               | N / A for Pkg Type   | -40 to 85    | SN74HC163N                    | Samples |
| SN74HC163NE4     | ACTIVE        | PDIP         | N                  | 16   | 25             | RoHS & Green        | NIPDAU                               | N / A for Pkg Type   | -40 to 85    | SN74HC163N                    | Samples |
| SN74HC163NSR     | ACTIVE        | SO           | NS                 | 16   | 2000           | RoHS & Green        | NIPDAU                               | Level-1-260C-UNLIM   | -40 to 85    | HC163                         | Samples |
| SN74HC163PWR     | ACTIVE        | TSSOP        | PW                 | 16   | 2000           | RoHS & Green        | NIPDAU                               | Level-1-260C-UNLIM   | -40 to 85    | HC163                         | Samples |
| SNJ54HC163FK     | ACTIVE        | LCCC         | FK                 | 20   | 55             | Non-RoHS<br>& Green | SNPB                                 | N / A for Pkg Type   | -55 to 125   | 86076012A<br>SNJ54HC<br>163FK | Samples |
| SNJ54HC163J      | ACTIVE        | CDIP         | J                  | 16   | 25             | Non-RoHS<br>& Green | SNPB                                 | N / A for Pkg Type   | -55 to 125   | 8607601EA<br>SNJ54HC163J      | Samples |

<sup>(1)</sup> The marketing status values are defined as follows: **ACTIVE:** Product device recommended for new designs.

LIFEBUY: TI has announced that the device will be discontinued, and a lifetime-buy period is in effect.

**NRND:** Not recommended for new designs. Device is in production to support existing customers, but TI does not recommend using this part in a new design. **PREVIEW:** Device has been announced but is not in production. Samples may or may not be available.

**OBSOLETE:** TI has discontinued the production of the device.



#### www.ti.com

<sup>(2)</sup> RoHS: TI defines "RoHS" to mean semiconductor products that are compliant with the current EU RoHS requirements for all 10 RoHS substances, including the requirement that RoHS substance do not exceed 0.1% by weight in homogeneous materials. Where designed to be soldered at high temperatures, "RoHS" products are suitable for use in specified lead-free processes. TI may reference these types of products as "Pb-Free".

RoHS Exempt: TI defines "RoHS Exempt" to mean products that contain lead but are compliant with EU RoHS pursuant to a specific EU RoHS exemption.

**Green:** TI defines "Green" to mean the content of Chlorine (CI) and Bromine (Br) based flame retardants meet JS709B low halogen requirements of <=1000ppm threshold. Antimony trioxide based flame retardants must also meet the <=1000ppm threshold requirement.

<sup>(3)</sup> MSL, Peak Temp. - The Moisture Sensitivity Level rating according to the JEDEC industry standard classifications, and peak solder temperature.

<sup>(4)</sup> There may be additional marking, which relates to the logo, the lot trace code information, or the environmental category on the device.

(5) Multiple Device Markings will be inside parentheses. Only one Device Marking contained in parentheses and separated by a "~" will appear on a device. If a line is indented then it is a continuation of the previous line and the two combined represent the entire Device Marking for that device.

(6) Lead finish/Ball material - Orderable Devices may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead finish/Ball material values may wrap to two lines if the finish value exceeds the maximum column width.

**Important Information and Disclaimer:**The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.

#### OTHER QUALIFIED VERSIONS OF SN54HC163, SN74HC163 :

• Catalog : SN74HC163

- Automotive : SN74HC163-Q1, SN74HC163-Q1
- Military : SN54HC163

NOTE: Qualified Version Definitions:

- Catalog TI's standard catalog product
- Automotive Q100 devices qualified for high-reliability automotive applications targeting zero defects



Military - QML certified for Military and Defense Applications



Texas

STRUMENTS

### TAPE AND REEL INFORMATION





#### QUADRANT ASSIGNMENTS FOR PIN 1 ORIENTATION IN TAPE



| *All dimensions are nominal |                 |                    |    |      |                          |                          |            |            |            |            |           |                  |
|-----------------------------|-----------------|--------------------|----|------|--------------------------|--------------------------|------------|------------|------------|------------|-----------|------------------|
| Device                      | Package<br>Type | Package<br>Drawing |    | SPQ  | Reel<br>Diameter<br>(mm) | Reel<br>Width<br>W1 (mm) | A0<br>(mm) | B0<br>(mm) | K0<br>(mm) | P1<br>(mm) | W<br>(mm) | Pin1<br>Quadrant |
| SN74HC163DR                 | SOIC            | D                  | 16 | 2500 | 330.0                    | 16.4                     | 6.5        | 10.3       | 2.1        | 8.0        | 16.0      | Q1               |
| SN74HC163NSR                | SO              | NS                 | 16 | 2000 | 330.0                    | 16.4                     | 8.2        | 10.5       | 2.5        | 12.0       | 16.0      | Q1               |
| SN74HC163PWR                | TSSOP           | PW                 | 16 | 2000 | 330.0                    | 12.4                     | 6.9        | 5.6        | 1.6        | 8.0        | 12.0      | Q1               |



www.ti.com

# PACKAGE MATERIALS INFORMATION

16-Apr-2024



\*All dimensions are nominal

| Device       | Package Type | Package Drawing | Pins | SPQ  | Length (mm) | Width (mm) | Height (mm) |
|--------------|--------------|-----------------|------|------|-------------|------------|-------------|
| SN74HC163DR  | SOIC         | D               | 16   | 2500 | 340.5       | 336.1      | 32.0        |
| SN74HC163NSR | SO           | NS              | 16   | 2000 | 356.0       | 356.0      | 35.0        |
| SN74HC163PWR | TSSOP        | PW              | 16   | 2000 | 356.0       | 356.0      | 35.0        |

### TEXAS INSTRUMENTS

www.ti.com

16-Apr-2024

### TUBE



### - B - Alignment groove width

#### \*All dimensions are nominal

| Device       | Package Name | Package Type | Pins | SPQ | L (mm) | W (mm) | Τ (μm) | B (mm) |
|--------------|--------------|--------------|------|-----|--------|--------|--------|--------|
| 86076012A    | FK           | LCCC         | 20   | 55  | 506.98 | 12.06  | 2030   | NA     |
| SN74HC163N   | N            | PDIP         | 16   | 25  | 506    | 13.97  | 11230  | 4.32   |
| SN74HC163N   | N            | PDIP         | 16   | 25  | 506    | 13.97  | 11230  | 4.32   |
| SN74HC163NE4 | N            | PDIP         | 16   | 25  | 506    | 13.97  | 11230  | 4.32   |
| SN74HC163NE4 | N            | PDIP         | 16   | 25  | 506    | 13.97  | 11230  | 4.32   |
| SNJ54HC163FK | FK           | LCCC         | 20   | 55  | 506.98 | 12.06  | 2030   | NA     |

# **NS0016A**



# **PACKAGE OUTLINE**

SOP - 2.00 mm max height

SOP



#### NOTES:

- 1. All linear dimensions are in millimeters. Dimensions in parenthesis are for reference only. Dimensioning and tolerancing
- Per ASME Y14.5M.
  This drawing is subject to change without notice.
  This dimension does not include mold flash, protrusions, or gate burrs. Mold flash, protrusions, or gate burrs shall not exceed 0.15 mm, per side.
- 4. This dimension does not include interlead flash. Interlead flash shall not exceed 0.25 mm, per side.



# NS0016A

# **EXAMPLE BOARD LAYOUT**

### SOP - 2.00 mm max height

SOP



NOTES: (continued)

5. Publication IPC-7351 may have alternate designs.

6. Solder mask tolerances between and around signal pads can vary based on board fabrication site.



# NS0016A

# **EXAMPLE STENCIL DESIGN**

## SOP - 2.00 mm max height

SOP



NOTES: (continued)

7. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.

8. Board assembly site may have different recommendations for stencil design.



D (R-PDSO-G16)

PLASTIC SMALL OUTLINE



NOTES: A. All linear dimensions are in inches (millimeters).

- B. This drawing is subject to change without notice.
- Body length does not include mold flash, protrusions, or gate burrs. Mold flash, protrusions, or gate burrs shall not exceed 0.006 (0,15) each side.
- Body width does not include interlead flash. Interlead flash shall not exceed 0.017 (0,43) each side.
- E. Reference JEDEC MS-012 variation AC.



# **PW0016A**



# **PACKAGE OUTLINE**

# TSSOP - 1.2 mm max height

SMALL OUTLINE PACKAGE



NOTES:

- 1. All linear dimensions are in millimeters. Any dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M. 2. This drawing is subject to change without notice. 3. This dimension does not include mold flash, protrusions, or gate burrs. Mold flash, protrusions, or gate burrs shall not
- exceed 0.15 mm per side.
- 4. This dimension does not include interlead flash. Interlead flash shall not exceed 0.25 mm per side.
- 5. Reference JEDEC registration MO-153.



# PW0016A

# **EXAMPLE BOARD LAYOUT**

# TSSOP - 1.2 mm max height

SMALL OUTLINE PACKAGE



NOTES: (continued)

6. Publication IPC-7351 may have alternate designs.

7. Solder mask tolerances between and around signal pads can vary based on board fabrication site.



# PW0016A

# **EXAMPLE STENCIL DESIGN**

# TSSOP - 1.2 mm max height

SMALL OUTLINE PACKAGE



NOTES: (continued)

9. Board assembly site may have different recommendations for stencil design.



<sup>8.</sup> Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.

### MECHANICAL DATA

#### PLASTIC SMALL-OUTLINE PACKAGE

#### 0,51 0,35 ⊕0,25⊛ 1,27 8 14 0,15 NOM 5,60 8,20 5,00 7,40 $\bigcirc$ Gage Plane ₽ 0,25 7 1 1,05 0,55 0-10 Δ 0,15 0,05 Seating Plane — 2,00 MAX 0,10PINS \*\* 14 16 20 24 DIM 10,50 10,50 12,90 15,30 A MAX A MIN 9,90 9,90 12,30 14,70 4040062/C 03/03

NOTES: A. All linear dimensions are in millimeters.

NS (R-PDSO-G\*\*)

**14-PINS SHOWN** 

- B. This drawing is subject to change without notice.
- C. Body dimensions do not include mold flash or protrusion, not to exceed 0,15.



# FK 20

### 8.89 x 8.89, 1.27 mm pitch

# **GENERIC PACKAGE VIEW**

## LCCC - 2.03 mm max height

LEADLESS CERAMIC CHIP CARRIER

This image is a representation of the package family, actual package may vary. Refer to the product data sheet for package details.





J (R-GDIP-T\*\*) 14 LEADS SHOWN

CERAMIC DUAL IN-LINE PACKAGE



NOTES: A. All linear dimensions are in inches (millimeters).

- B. This drawing is subject to change without notice.
- C. This package is hermetically sealed with a ceramic lid using glass frit.
- D. Index point is provided on cap for terminal identification only on press ceramic glass frit seal only.
- E. Falls within MIL STD 1835 GDIP1-T14, GDIP1-T16, GDIP1-T18 and GDIP1-T20.

# N (R-PDIP-T\*\*)

PLASTIC DUAL-IN-LINE PACKAGE

16 PINS SHOWN



NOTES:

- A. All linear dimensions are in inches (millimeters).B. This drawing is subject to change without notice.
- Falls within JEDEC MS-001, except 18 and 20 pin minimum body length (Dim A).
- $\triangle$  The 20 pin end lead shoulder width is a vendor option, either half or full width.



### IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATA SHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, regulatory or other requirements.

These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you will fully indemnify TI and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to TI's Terms of Sale or other applicable terms available either on ti.com or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products.

TI objects to and rejects any additional or different terms you may have proposed.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265 Copyright © 2024, Texas Instruments Incorporated