







TPS62868, TPS62869 SLVSFS3B – SEPTEMBER 2020 – REVISED JULY 2021

TPS62868x 2.4-V to 5.5-V Input, 4-A/6-A Synchronous Step-Down Converter with I²C Interface in QFN Package

1 Features

Texas

INSTRUMENTS

- 11-mΩ and 10.5-mΩ internal power MOSFETs
- >90% efficiency (0.9-V output)
- DCS-Control topology for fast transient response
- Available output voltage ranges for dynamic voltage scaling (DVS) through I²C
 - Output voltage range from 0.2-V to 0.8375-V with 2.5-mV step size
 - Output voltage range from 0.4-V to 1.675-V with 5-mV step size
 - Output voltage range from 0.8-V to 3.35-V with 10-mV step size
- 1% output voltage accuracy
- 2.4-MHz switching frequency
- · Selection by external resistor
 - Start-up output voltage
 - I²C target address
- Selection by I²C interface
 - Power save mode or forced PWM mode
 - Output discharge
 - Hiccup or latching short-circuit protection
 - Output voltage ramp speed
- Thermal pre-warning and thermal shutdown
- Power good indicator pin option with window comparator
- I²C-compatible interface up to 3.4 Mbps
- Available in 1.5-mm x 2.5-mm x 1.0-mm 9-pin QFN package with 0.5-mm pitch
- Also available in WCSP package: TPS62866, 6-A synchronous step-down converter with I2C interface in 1.05-mm x 1.78-mm WCSP package
- Create a custom design using with TPS62868/9 with the WEBENCH[®] Power Designer



2 Applications

- Core supply for FPGAs, CPUs, ASICs, or video chipsets
- IP network camera
- Solid-state drives
- Optical modules
- LPDDR5 VDDQ rail supply

3 Description

The TPS62868 and TPS62869 devices are highfrequency synchronous step-down converters with I²C interface which provide an efficient, adaptive, and high power-density solution. At medium to heavy loads, the converter operates in PWM mode and automatically enters Power Save Mode operation at light load to maintain high efficiency over the entire load current range. The device can also be forced in PWM mode operation for smallest output voltage ripple. Together with its DCS-Control architecture, excellent load transient performance and tight output voltage accuracy are achieved. Through the I²C interface and a dedicated VID pin, the output voltage is quickly adjusted to adapt the power consumption of the load to the ever-changing performance needs of the application.

Device Information

PART NUMBER	PACKAGE ⁽¹⁾	BODY SIZE (NOM)
TPS62868		15 x 25 x 10 mm
TPS62869	QFN (9)	1.5 X 2.5 X 1.0 11111

(1) For all available packages, see the orderable addendum at the end of the data sheet.





Table of Contents

1 Features	1
2 Applications	1
3 Description	1
4 Revision History	2
5 Device Options	3
6 Pin Configuration and Functions	4
7 Specifications	5
7.1 Absolute Maximum Ratings	5
7.2 ESD Ratings	<mark>5</mark>
7.3 Recommended Operating Conditions	5
7.4 Thermal Information	5
7.5 Electrical Characteristics	7
7.6 I ² C InterfaceTiming Characteristics	8
7.7 Typical Characteristics	11
8 Detailed Description	12
8.1 Overview	12
8.2 Functional Block Diagram	12
8.3 Feature Description	12
8.4 Device Functional Modes	14
8.5 Programming	16

8.6 Register Map	19
9 Application and Implementation	.22
9.1 Application Information	. 22
9.2 Typical Application	. 22
9.3 Typical Application – TPS6286x0A and	
TPS6286x0xC Devices	. 28
10 Power Supply Recommendations	30
11 Layout	.31
11.1 Layout Guidelines	. 31
11.2 Layout Example	. 31
12 Device and Documentation Support	32
12.1 Device Support	. 32
12.2 Documentation Support	. 32
12.3 Support Resources	. 32
12.4 Receiving Notification of Documentation Updates.	.32
12.5 Trademarks	.32
12.6 Glossary	.32
12.7 Electrostatic Discharge Caution	.32
13 Mechanical, Packaging, and Orderable	
Information	. 32

4 Revision History

NOTE: Page numbers for previous revisions may differ from page numbers in the current version.

C	hanges from Revision A (December 2020) to Revision B (July 2021)	Page
•	Globally changed instances of legacy terminology to controller and target where I ² C is mentioned	1
•	Corrected start-up output voltage for TPS6286xxxC device variants in Device Options table	3
•	Changed "VID" to "VSET/VID" in Device Options table	3
•	Added inductor values to Recommended Operating Conditons table	5
•	Corrected number of pins in Thermal Information table	5
•	Added guiescent current specification for TPS6286x0A/C devices in Electrical Characteristics table	7
•	Changed high-level input voltage threshold in <i>Electrical Characteristics table</i>	7
•	Added separate enable delay time parameter for TPS6286x0C device variants	7
•	Added footnote	7
•	Added power-good deglitch block to Functional Block Diagram	12
•	Added 100% Duty Cycle Mode Operation section	13
•	Added section describing the start-up output voltage for TPS6286xxC device variants	14
•	Corrected value of C1 in List of Components table.	22
•	Updated data in <i>Thermal Derating</i> plot for V_{OUT} = 1.675 V	25
•	Added typical application example for TPS6286x0A and TPS6286x0xC device variants	28
•	Changed Layout Example image	31
С	hanges from Revision * (September 2020) to Revision A (December 2020)	Page
•	Changed device status from Advance Information to Production Data	1



5 Device Options

PART NUMBER ⁽¹⁾	FULL OUTPUT VOLTAGE RANGE	START-UP OUTPUT VOLTAGE	DVS STEP SIZE	OUTPUT CURRENT	VSET/VID OR PG PIN
TPS62868 0A RQY	0.2.\/ to 0.8375.\/	0.2 V to 0.575 V, Selectable	2.5 m\/		VSET/VID
TPS62868 00C RQY	0.2 0 10 0.0375 0	0.5 V	2.5 111		PG
TPS62868 1A RQY	0.4.)(to 1.675.)(0.4 V to 1.15 V, Selectable			VSET/VID
TPS6286810CRQY	0.4 V to 1.075 V	0.9 V	5 MV 4 A		PG
TPS62868 2A RQY		0.8 V to 2.3 V, Selectable	10 m)/		VSET/VID
TPS62868 20C RQY	- 0.8 V 10 3.35 V	1.2 V	10 1110		PG
TPS62869 0A RQY	0.2.V.to 0.9275.V	0.2 V to 0.575 V, Selectable	2.5 m\/		VSET/VID
TPS62869 00C RQY	0.2 V 10 0.0375 V	0.5 V	2.5 111		PG
TPS62869 1A RQY	0.4.)(to 1.675.)(0.4 V to 1.15 V, Selectable	E m)/	6.0	VSET/VID
TPS62869 10C RQY	0.4 V to 1.075 V	0.9 V	5 1117	6 A	PG
TPS62869 2A RQY	0.9.\/ to 2.25.\/	0.8 V to 2.3 V, Selectable	10 m\/		VSET/VID
TPS62869 20C RQY	0.0 V 10 3.35 V	1.2 V	10 mV		PG

(1) For all available packages, see the orderable addendum at the end of the data sheet.



6 Pin Configuration and Functions



Figure 6-1. 9-Pin RQY QFN Package (Top View)

Table 6-1. Pin Functions

PIN		DESCRIPTION	
NAME	NO.	DESCRIPTION	
AGND	1	Analog ground pin	
VSET/VID	9	Start-up output voltage and device address selection pin. An external resistor must be connected. After start-up, the pin can be used to select the V_{OUT} registers for the output voltage (Low = V_{OUT} register 1; high = V_{OUT} register 2). See Section 8.4.4. This pin is pulled to GND when the device is in shutdown. The function after start-up depends on the device option. See the Device Options.	
PG	9	Power-good open-drain output pin. The pullup resistor can be connected to voltages up to 5.5 V. If unused, leave it floating. This pin is pulled to GND when the device is in shutdown. The function after start-up depends on the device option. See <i>Section 5</i> .	
VOS	8	Output voltage sense pin. This pin must be directly connected to the output capacitor.	
PGND	2	Power ground pin	
SW	7	Switch pin of the power stage	
VIN	3	Power supply input voltage pin	
EN	4	Device enable pin. To enable the device, this pin needs to be pulled high. Pulling this pin low disables the device. Do not leave floating.	
SDA	5	I ² C serial data pin. Do not leave it floating. Connect it to AGND if not used.	
SCL	6	I ² C serial clock pin. Do not leave it floating. Connect it to AGND if not used.	



7 Specifications

7.1 Absolute Maximum Ratings

Over operating free-air temperature range (unless otherwise noted) (1)

		MIN	MAX	UNIT
	VIN, EN, SDA, SCL, VOS, VSET/VID, VSET/PG	-0.3	6	
Voltage ⁽²⁾	SW (DC)	-0.3	V _{IN} + 0.3	V
	SW (AC, less than 10ns) ⁽³⁾	-2.5	10	
I _{SOURCE_PG}	Source current at VSET/PG		1	mA
I _{SINK_SDA,SCL}	Sink current at SDA, SCL		2	mA
TJ	Junction temperature	-40	150	°C
T _{stg}	Storage temperature	-65	150	°C

(1) Stresses beyond those listed under Absolute Maximum Rating may cause permanent damage to the device. These are stress ratings only, which do not imply functional operation of the device at these or any other conditions beyond those indicated under Recommended Operating Condition. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability.

(2) All voltage values are with respect to network ground terminal.

(3) While switching.

7.2 ESD Ratings

			VALUE	UNIT
V _(ESD) Electrosta	Electrostatic discharge	Human body model (HBM), per ANSI/ESDA/ JEDEC JS-001, all pins ⁽¹⁾	±2000	N
	Lieulostalle discharge	Charged device model (CDM), per JEDEC specification JESD22-C101, all pins ⁽²⁾	±500	V

(1) JEDEC document JEP155 states that 500-V HBM allows safe manufacturing with a standard ESD control process.

(2) JEDEC document JEP157 states that 250-V CDM allows safe manufacturing with a standard ESD control process.

7.3 Recommended Operating Conditions

Over operating junction temperature range (unless otherwise noted)

			MIN	NOM MAX	UNIT	
V _{IN}	Input voltage		2.4	5.5	V	
t _{F_VIN}	Falling transition time at VIN ⁽¹⁾	Falling transition time at VIN ⁽¹⁾		10	mV/µs	
I _{OUT}	Output current, TPS62868 ⁽²⁾		0	4	A	
	Output current, TPS62869 ⁽³⁾		0	6		
		TPS628680x, TPS628690x		110		
L	Output inductor TPS628681x, TPS628682x, TPS628691x, TPS628692x			220	nH	
TJ	Junction temperature		-40	125	°C	

(1) The falling slew rate of V_{IN} should be limited if V_{IN} goes below V_{UVLO} .

(2) Lifetime is reduced when operating continuously at 4-A output current and the junction temperature is higher than 105 °C.

(3) Lifetime is reduced when operating continuously at 6-A output current and the junction temperature is higher than 85 °C.

7.4 Thermal Information

THERMAL METRIC ⁽¹⁾		TPS62868/ T		
		JEDEC 51-7	TPS62869RQYEVM-118	UNIT
		9 PINS	9 PINS	
R _{0JA}	Junction-to-ambient thermal resistance	90.9	60.3	°C/W
$R_{\theta JC(top)}$	Junction-to-case (top) thermal resistance	68.2	n/a ⁽²⁾	°C/W
$R_{\theta JB}$	Junction-to-board thermal resistance	25.0	n/a ⁽²⁾	°C/W

TPS62868, TPS62869 SLVSFS3B – SEPTEMBER 2020 – REVISED JULY 2021



THERMAL METRIC ⁽¹⁾		TPS62868/ TI		
		JEDEC 51-7	TPS62869RQYEVM-118	UNIT
		9 PINS	9 PINS	
Ψ_{JT}	Junction-to-top characterization parameter	1.9	3.3	°C/W
Ψ_{JB}	Junction-to-board characterization parameter	24.7	31.5	°C/W

(1) For more information about traditional and new thermal metrics, see the Semiconductor and IC Package Thermal Metrics application report.

(2) Not applicable to an EVM.



7.5 Electrical Characteristics

 T_J = -40 °C to 125 °C, and V_{IN} = 2.4 V to 5.5 V. Typical values are at T_J = 25 °C and V_{IN} = 5 V, unless otherwise noted.

PARAMETER		र	TEST CONDITIONS	MIN	TYP	MAX	UNIT
SUPPLY			· · · · ·				
IQ	Quiescent current	TPS6286x1A/C, TPS6286x2A/C	EN = High, no load, device not switching		4	10	μA
		TPS6286x0A/C			9	15	
I _{Q_VOS}	Operating quiescent current into VOS pin		EN = High, no load, device not switching, V _{VOS} = 1.8 V		18		μΑ
I _{SD}	Shutdown current		EN = Low, $T_J = -40^{\circ}C$ to $85^{\circ}C$		0.24	1	μA
Vindo	I Indervoltage lockout t	hreshold	V _{IN} rising	2.2	2.3	2.4	V
- 0120			V _{IN} falling	2.1	2.2	2.3	V
T	Thermal warning thres	hold	T _J rising		130		°C
• 300	Thermal warning hyste	resis	T _J falling		20		°C
TICD	Thermal shutdown three	eshold	T _J rising		150		°C
. 12D	Thermal shutdown hys	teresis	T _J falling		20		°C
LOGIC IN	NTERFACE EN, SDA, S	CL					
V _{IH}	High-level input thresh SCL, SDA, VSET/VID	old voltage at EN,		0.84			V
V _{IL}	Low-level input thresho SCL, SDA, VSET/VID	old voltage at EN,				0.4	V
I _{SCL,LKG}	Input leakage current i	nto SCL pin			0.01	0.8	μA
I _{SDA,LKG}	Input leakage current i	nto SDA pin			0.01	0.1	μA
I _{EN,LKG}	Input leakage current i	nto EN pin			0.01	0.1	μA
C _{SCL}	Parasitic capacitance a	at SCL			1		pF
C _{SDA}	Parasitic capacitance a	at SDA			2.4		pF
STARTU	P, POWER GOOD						
t _{Delav}	Enable delay time	TPS6286xA	Time from EN high to device starts switching, R1 = $249k\Omega$	420	700	1100	μs
		TPS6286x0C	Time from EN high to device starts switching	100	350	900	
t _{Ramp}	Output voltage ramp til	ne	Time from device starts switching to power good	0.85	1	1.5	ms
V	Power good lower thre	shold ⁽¹⁾	V _{VOS} referenced to V _{OUT} nominal	85	91	96	%
VPG	Power good upper thre	eshold	V _{VOS} referenced to V _{OUT} nominal	103	111	120	%
t _{PG,DLY}	Power good deglitch de	elay	Rising and falling edges		34		μs
OUTPUT						·	
Vaur			FPWM, no Load, T _J = 0°C to 85°C	-1		1	%
¥001	Output voltage accurat	<i></i>	FPWM, no Load	-2		2	%
I _{VOS,LKG}	Input leakage current in	nto VOS pin	EN = Low, Output discharge disabled, V_{VOS} = 1.8 V, TPS6286x1A/C		0.2	2.5	μΑ
R _{DIS}	Output discharge resis	tor at VOS pin			3.5		Ω
	Load regulation		V _{OUT} = 0.9 V, FPWM		0.04		%/A
POWER	SWITCH						
D	High-side FET on-resis	stance			11		mΩ
TDS(on)	Low-side FET on-resistance				10.5		mΩ
	High aida EET forward	ourront limit	TPS62868	5	5.5	6	Α
			TPS62869	7	7.7	8.5	A
I _{LIM}	Low side EET femurad	ourront limit	TPS62868		4.5		А
			TPS62869		6.5		А
	Low-side FET negative current limit		TPS62868, TPS62869		-3		A



 T_J = -40 °C to 125 °C, and V_{IN} = 2.4 V to 5.5 V. Typical values are at T_J = 25 °C and V_{IN} = 5 V, unless otherwise noted.

PARAMETER		TEST CONDITIONS	MIN	TYP	MAX	UNIT
f _{SW}	PWM switching frequency	I _{OUT} = 1 A, V _{OUT} = 0.9 V		2.4		MHz

(1) TPS6286x0A and TPS6286x00C device variants do not have a lower PG threshold. In these device variants the PG signal is high if the start-up ramp is complete and the output voltage is below the upper PG threshold.

7.6 I²C InterfaceTiming Characteristics

PARAMETER (1) (2)		TEST CONDITIONS	MIN	MAX	UNIT
f _(SCL)	SCL Clock Frequency	Standard mode		100	kHz
f _(SCL)	SCL Clock Frequency	Fast mode		400	kHz
f _(SCL)	SCL Clock Frequency	Fast mode plus		1	MHz
f _(SCL)	SCL Clock Frequency	High-speed mode (write operation), $C_B - 100 \text{ pF}$ max		3.4	MHz
f _(SCL)	SCL Clock Frequency	High-speed mode (read operation), $C_B - 100 \text{ pF}$ max		3.4	MHz
f _(SCL)	SCL Clock Frequency	High-speed mode (write operation), $C_B - 400$ pF max		1.7	MHz
f _(SCL)	SCL Clock Frequency	High-speed mode (read operation), $C_B - 400 \text{ pF}$ max		1.7	MHz
t _{BUF}	Bus Free Time Between a STOP and START Condition	Standard mode	4.7		μs
t _{BUF}	Bus Free Time Between a STOP and START Condition	Fast mode	1.3		μs
t _{BUF}	Bus Free Time Between a STOP and START Condition	Fast mode plus	0.5		μs
t _{HD} , t _{STA}	Hold Time (Repeated) START condition	Standard mode	4		μs
t _{HD} , t _{STA}	Hold Time (Repeated) START condition	Fast mode	600		ns
t _{HD} , t _{STA}	Hold Time (Repeated) START condition	Fast mode plus	260		ns
t _{HD} , t _{STA}	Hold Time (Repeated) START condition	High-speed mode	160		ns
t _{LOW}	LOW Period of the SCL Clock	Standard mode	4.7		μs
t _{LOW}	LOW Period of the SCL Clock	Fast mode	1.3		μs
t _{LOW}	LOW Period of the SCL Clock	Fast mode plus	0.5		μs
t _{LOW}	LOW Period of the SCL Clock	High-speed mode, C _B – 100 pF max	160		ns
t _{LOW}	LOW Period of the SCL Clock	High-speed mode, C _B – 400 pF max	320		ns
t _{HIGH}	HIGH Period of the SCL Clock	Standard mode	4		μs
t _{HIGH}	HIGH Period of the SCL Clock	Fast mode	600		ns
t _{HIGH}	HIGH Period of the SCL Clock	Fast mode plus	260		ns
t _{HIGH}	HIGH Period of the SCL Clock	High-speed mode, C _B – 100 pF max	60		ns
t _{HIGH}	HIGH Period of the SCL Clock	High-speed mode, C _B – 400 pF max	120		ns
t _{SU} , t _{STA}	Setup Time for a Repeated START Condition	Standard mode	4.7		μs
t _{SU} , t _{STA}	Setup Time for a Repeated START Condition	Fast mode	600		ns
t _{SU} , t _{STA}	Setup Time for a Repeated START Condition	Fast mode plus	260		ns
t _{SU} , t _{STA}	Setup Time for a Repeated START Condition	High-speed mode	160		ns
t _{SU} , t _{DAT}	Data Setup Time	Standard mode	250		ns
t _{SU} , t _{DAT}	Data Setup Time	Fast mode	100		ns
t _{SU} , t _{DAT}	Data Setup Time	Fast mode plus	50		ns
t _{SU} , t _{DAT}	Data Setup Time	High-speed mode	10		ns



PARAMETER ⁽¹⁾ ⁽²⁾		TEST CONDITIONS	MIN	MAX	UNIT
t _{HD} , t _{DAT}	Data Hold Time	Standard mode	0	3.45	μs
t _{HD} , t _{DAT}	Data Hold Time	Fast mode	0	0.9	μs
t _{HD} , t _{DAT}	Data Hold Time	Fast mode plus	0		μs
t _{HD} , t _{DAT}	Data Hold Time	High-speed mode, C _B – 100 pF max	0	70	ns
t _{HD} , t _{DAT}	Data Hold Time	High-speed mode, C _B – 400 pF max	0	150	ns
t _{RCL}	Rise Time of SCL Signal	Standard mode		1000	ns
t _{RCL}	Rise Time of SCL Signal	Fast mode	20 + 0.1 C _B	300	ns
t _{RCL}	Rise Time of SCL Signal	Fast mode plus		120	ns
t _{RCL}	Rise Time of SCL Signal	High-speed mode, C _B – 100 pF max	10	40	ns
t _{RCL}	Rise Time of SCL Signal	High-speed mode, C _B – 400 pF max	20	80	ns
t _{RCL1}	Rise Time of SCL Signal After a Repeated START Condition and After an Acknowledge BIT	Standard mode	20 + 0.1 C _B	1000	ns
t _{RCL1}	Rise Time of SCL Signal After a Repeated START Condition and After an Acknowledge BIT	Fast mode	20 + 0.1 C _B	300	ns
t _{RCL1}	Rise Time of SCL Signal After a Repeated START Condition and After an Acknowledge BIT	Fast mode plus		120	ns
t _{RCL1}	Rise Time of SCL Signal After a Repeated START Condition and After an Acknowledge BIT	High-speed mode, C _B – 100 pF max	10	80	ns
t _{RCL1}	Rise Time of SCL Signal After a Repeated START Condition and After an Acknowledge BIT	High-speed mode, C _B – 400 pF max	20	160	ns
t _{FCL}	Fall Time of SCL Signal	Standard mode	20 + 0.1 C _B	300	ns
t _{FCL}	Fall Time of SCL Signal	Fast mode		300	ns
t _{FCL}	Fall Time of SCL Signal	Fast mode plus		120	ns
t _{FCL}	Fall Time of SCL Signal	High-speed mode, C _B – 100 pF max	10	40	ns
t _{FCL}	Fall Time of SCL Signal	High-speed mode, C _B – 400 pF max	20	80	ns
t _{RDA}	Rise Time of SDA Signal	Standard mode		1000	ns
t _{RDA}	Rise Time of SDA Signal	Fast mode	20 + 0.1 C _B	300	ns
t _{RDA}	Rise Time of SDA Signal	Fast mode plus		120	ns
t _{RDA}	Rise Time of SDA Signal	High-speed mode, C _B – 100 pF max	10	80	ns
t _{RDA}	Rise Time of SDA Signal	High-speed mode, $C_B - 400 \text{ pF}$ max	20	160	ns
t _{FDA}	Fall Time of SDA Signal	Standard mode		300	ns
t _{FDA}	Fall Time of SDA Signal	Fast mode	20 + 0.1 C _B	300	ns
t _{FDA}	Fall Time of SDA Signal	Fast mode plus		120	ns
t _{FDA}	Fall Time of SDA Signal	High-speed mode, C _B – 100 pF max	10	80	ns
t _{FDA}	Fall Time of SDA Signal	High-speed mode, C _B – 400 pF max	20	160	ns
t _{SU,} t _{STO}	Setup Time of STOP Condition	Standard mode	4		μs
t _{SU,} t _{STO}	Setup Time of STOP Condition	Fast mode	600		ns
t _{SU,} t _{STO}	Setup Time of STOP Condition	Fast mode plus	260		ns
t _{SU,} t _{STO}	Setup Time of STOP Condition	High-Speed mode	160		ns
CB	Capacitive Load for SDA and SCL	Standard mode		400	pF
C _B	Capacitive Load for SDA and SCL	Fast mode		400	pF
CB	Capacitive Load for SDA and SCL	Fast mode plus		550	pF

Copyright © 2021 Texas Instruments Incorporated

TPS62868, TPS62869

SLVSFS3B - SEPTEMBER 2020 - REVISED JULY 2021



PARAMETER (1) (2)		TEST CONDITIONS		MAX	UNIT
C _B	Capacitive Load for SDA and SCL	High-Speed mode		400	pF

(1)

All values referred to V_{IL} MAX and V_{IH} MIN levels in ELECTRICAL CHARACTERISTICS table. For bus line loads C_B between 100 pF and 400 pF, the timing parameters must be linearly interpolated. (2)



7.7 Typical Characteristics





8 Detailed Description

8.1 Overview

The DCS-Control[™] topology operates in PWM (pulse width modulation) mode for medium to heavy load conditions and in Power Save Mode at light load currents. In PWM mode, the converter operates with its nominal switching frequency of 2.4 MHz, having a controlled frequency variation over the input voltage range. Because DCS-Control supports both operation modes (PWM and PFM) within a single building block, the transition from PWM mode to Power Save Mode is seamless and without effects on the output voltage. The devices offer both excellent DC voltage and superior load transient regulation, combined with very low output voltage ripple.

8.2 Functional Block Diagram



8.3 Feature Description

8.3.1 Power Save Mode

As the load current decreases, the device enters Power Save Mode (PSM) operation. PSM occurs when the inductor current becomes discontinuous, which is when it reaches 0 A during a switching cycle. Power Save Mode is based on a fixed on-time architecture, as shown in Equation 1.

$$t_{ON} = \frac{V_{OUT}}{V_{IN}} \cdot 416 \text{ns}$$

(1)

In Power Save Mode, the output voltage rises slightly above the nominal output voltage. This effect is minimized by increasing the output capacitor or inductor value.



(2)

When V_{IN} decreases to typically 15% above the V_{OUT} , the TPS6286x does not enter Power Save Mode, regardless of the load current. The device maintains output regulation in PWM mode.

8.3.2 Forced PWM Mode

With I²C, set the device in forced PWM (FPWM) mode by the CONTROL register. The device switches at 2.4 MHz, even with a light load. This reduces the output voltage ripple and allows simple filtering of the switching frequency for noise-sensitive applications. Efficiency at light load is lower in FPWM mode.

8.3.3 100% Duty Cycle Mode Operation

There is no limitation for small duty cycles since even at very low duty cycles, the switching frequency is reduced as needed to always ensure a proper regulation.

If the output voltage level comes close to the input voltage, the device enters 100% mode. While the high-side switch is constantly turned on, the low-side switch is switched off. The difference between V_{IN} and V_{OUT} is determined by the voltage drop across the high-side MOSFET and the DC resistance of the inductor. The minimum V_{IN} that is needed to maintain a specific V_{OUT} value is estimated as:

$$V_{\rm IN,MIN} = V_{\rm OUT} + (R_{\rm DS(ON)} + R_{\rm L})I_{\rm OUT,MAX}$$

where

- V_{IN.MIN} is the minimum input voltage to maintain an output voltage
- I_{OUT.MAX} is the maximum output current
- R_{DS(on)} is the high-side FET ON-resistance
- R_L is the inductor ohmic resistance (DCR)

8.3.4 Start-up

After enabling the device, there is an enable delay (t_{Delay}) before the device starts switching. During this period, the device sets the internal reference voltage, and determines the start-up output voltage through the resistor connected to the VSET/VID pin. After t_{delay} , all registers can be read and written by the I²C interface.



Figure 8-1. Start-up Sequence

After the enable delay, an internal soft start-up circuitry ramps up the output voltage with a period of 1 ms (t_{Ramp}) . This avoids excessive inrush current and creates a smooth output voltage rising-slope. It also prevents excessive voltage drops of primary cells and rechargeable batteries with high internal impedance.

The device is able to start into a pre-biased output capacitor. It starts with the applied bias voltage and ramps the output voltage to its nominal value.

8.3.5 Switch Current Limit and HICCUP Short-Circuit Protection

The switch current limit prevents the device from high inductor current and from drawing excessive current from the battery or input voltage rail. Excessive current can occur with a shorted or saturated inductor or a heavy load or shorted output circuit condition. If the inductor current reaches the threshold I_{LIM}, cycle by cycle, the high-side



MOSFET is turned off and the low-side MOSFET is turned on, while the inductor current ramps down to the low-side MOSFET current limit.

When the high-side MOSFET current limit is triggered 32 times, the device stops switching. The device then automatically re-starts, with an internal soft start-up, after a typical delay time of 128 µs has passed. This is named HICCUP short-circuit protection. The device repeats this mode until the high load condition disappears.

The HICCUP is disabled by the CONTROL register bit Enable HICCUP. Disabling HICCUP changes the overcurrent protection to latching protection. The device stops switching after the high-side MOSFET current limit is triggered 32 times. Toggling the EN pin, removing and reapplying the input voltage, or writing to the CONTROL register bit Software Enable Device unlatches the device.

8.3.6 Undervoltage Lockout (UVLO)

To avoid mis-operation of the device at low input voltages, undervoltage lockout (UVLO) is implemented when the input voltage is lower than V_{UVLO} . The device stops switching and the output voltage discharge is active (if enabled through I^2C) when the device is in UVLO. When the input voltage recovers, the device automatically returns to operation with an internal soft start-up. During UVLO, the internal register values are kept.

The UVLO bit in the STATUS Register is set when the input voltage is less than the UVLO falling threshold. When the input voltage is below 1.8 V (typ.), all registers are reset.

8.3.7 Thermal Warning and Shutdown

When the junction temperature goes up to T_{JW} , the device gives a pre-warning indicator in the STATUS register. The device keeps running.

When the junction temperature exceeds T_{JSD} , the device goes into thermal shutdown, stops switching, and activates the output voltage discharge. When the device temperature falls below the threshold by 20°C, the device returns to normal operation automatically with an internal soft start-up. During thermal shutdown, the internal register values are kept.

8.4 Device Functional Modes

8.4.1 Enable and Disable (EN)

The device is enabled by setting the EN pin to a logic High. In shutdown mode (EN = Low), the internal power switches as well as the entire control circuitry are turned off, and all the registers are reset, except for the Enable Output Discharge bit. Do not leave the EN pin floating.

In shutdown mode (EN = Low), all registers cannot be read and written by the I^2C interface.

The typical threshold value of the EN pin is 0.61 V for rising input signals, and 0.51 V for falling input signals.

The device is also enabled or disabled by setting the bit, Software Enable Device in CONTROL register while EN = High. After being disabled/enabled by this bit, the device stops switching and has a new start-up beginning with t_{Ramp} . There is no T_{Delay} time and the registers are not reset.

8.4.2 Output Discharge

An internal MOSFET switch smoothly discharges the output through the VOS pin in shutdown mode (EN = Low or Software Enable Device bit = 0). The output discharge is also active when the device is in thermal shutdown and UVLO.

When the Enable Output Discharge bit is set to 0, the output discharge function is disabled. The input voltage must remain higher than 1 V (typ.) to keep the output discharge function operational and the status of the Enable Output Discharge bit retained. The Enable Output Discharge bit is reset on the rising edge of the EN pin.

8.4.3 Start-Up Output Voltage and I²C Target Address Selection

During the ramp up period (t_{Ramp}), the output voltage ramps to the start-up output voltage first, then ramps up or down to the new value when the value of the output register is changed by I²C interface commands.



8.4.3.1 TPS6286xxA Devices

During the enable delay (t_{Delay}), the start-up output voltage and device I²C target address are set by an external resistor connected to the VSET/VID pin through an internal R2D (resistor to digital) converter. Table 8-1 shows the options.

RESISTOR (E96 SERIES, ±1% ACCURACY) AT VSET/VID	START-UP OUTPUT VOLTAGE (TYP)	I ² C TARGET ADDRESS
249 kΩ	Voltage Factor * 1.15 V	0b1000110 (0x46)
205 kΩ	Voltage Factor * 1.10 V	0b1000101 (0x45)
162 kΩ	Voltage Factor * 1.05 V	0b1000100 (0x44)
133 kΩ	Voltage Factor * 1.00 V	0b1000011 (0x43)
105 kΩ	Voltage Factor * 0.95 V	0b1000010 (0x42)
86.6 kΩ	Voltage Factor * 0.90 V	0b1000001 (0x41)
68.1 kΩ	Voltage Factor * 0.85 V	0b1001000 (0x48)
56.2 kΩ	Voltage Factor * 0.80 V	0b1001001 (0x49)
44.2 kΩ	Voltage Factor * 0.75 V	0b1001010 (0x4A)
36.5 kΩ	Voltage Factor * 0.70 V	0b1001011 (0x4B)
28.7 kΩ	Voltage Factor * 0.65 V	0b1001100 (0x4C)
23.7 kΩ	Voltage Factor * 0.60 V	0b1001101 (0x4D)
18.7 kΩ	Voltage Factor * 0.55 V	0b1001110 (0x4E)
15.4 kΩ	Voltage Factor * 0.50 V	0b1001111 (0x4F)
12.1 kΩ	Voltage Factor * 0.45 V	0b1000000 (0x40)
10 kΩ	Voltage Factor * 0.40 V	0b1000111 (0x47)

Table 8-1. Start-up Output Voltage and I²C Target Address Options

Table 8-2. Device Option Voltage Factors

DEVICE OPTION	VOLTAGE FACTOR
TPS6286x 0 A	0.5
TPS6286x 1 A	1
TPS6286x 2 A	2

The R2D converter has an internal current source which applies current through the external resistor, and an internal ADC which reads back the resulting voltage level. Depending on the level, the correct start-up output voltage and I²C target address are set. Once this R2D conversion is finished, the current source is turned off to avoid current flowing through the external resistor. Ensure that there is no additional current path or capacitance greater than 30 pF from this pin to GND during R2D conversion, otherwise a false value is set.

8.4.3.2 TPS6286xxxC Devices

The start-up output voltage, voltage factor, and I²C target address of the TPS6286xxxC devices are factory-set according to Table 8-3.

Table 8-3. Device Option Start-Up Voltage, Voltage Factor, and I²C Target Address

DEVICE OPTION	VOLTAGE FACTOR	START-UP OUTPUT VOLTAGE	I ² C TARGET ADDRESS
TPS6286x0xC	0.5	0.5 V	
TPS6286x1xC	1	0.9 V	0b1000010 (0x42)
TPS6286x2xC	2	1.2 V	



8.4.4 Select Output Voltage Registers (VID)

After the start-up period ($t_{Startup}$), the output voltage can be selected between two output voltage registers by the VID pin. When VID is pulled low, the output voltage is set by Table 8-6. When VID is pulled high, the output voltage is set by Table 8-7. This is also called dynamic voltage scaling (DVS).

During an output voltage change through I²C or the VSET/VID pin, the device can be set in FPWM by the Enable FPWM Mode during Output Voltage Change bit in CONTROL register. The output voltage change speed is set by the Voltage Ramp Speed bit.

8.4.5 Power Good (PG)

The TPS62868 and TPS62869 families provide device options with the PG pin instead of a VSET/VID pin. Refer to Section 5 to see the according device options.

The PG pin goes high impedance once the output voltage is above 91% and less than 110% of the nominal voltage, and is driven low once the voltage is out of the range. The PG pin is an open-drain output and is specified to sink up to 1 mA. The power good output requires a pullup resistor connecting to any voltage rail less than 5.5 V. The PG signal can be used for sequencing of multiple rails by connecting it to the EN pin of other converters. Leave the PG pin unconnected when not used.

The PG has a deglitch time, before the signal goes high or low, durir	ng normal operation.
---	----------------------

		LOGIC	STATUS
	DEVICE CONDITIONS	HIGH	LOW
Enable	$0.91 \times V_{OUT_NOM} \le V_{VOS} \le 1.11 \times V_{OUT_NOM}$	√	
	V_{VOS} < 0.91 × V_{OUT_NOM} or V_{VOS} > 1.11 × V_{OUT_NOM}		\checkmark
Shutdown	EN = Low		√
Thermal Shutdown	$T_J > T_{JSD}$		\checkmark
UVLO	$1.8 V < V_{IN} < V_{UVLO}$		√
Power Supply Removal	V _{IN} < 1.8 V	undefined	

Table 8-4. PG Pin Logic

8.5 Programming

8.5.1 Serial Interface Description

I2C[™] is a 2-wire serial interface developed by Philips Semiconductor, now NXP Semiconductors. The bus consists of a data line (SDA) and a clock line (SCL) with pullup structures. When the bus is *idle*, both SDA and SCL lines are pulled high. All the I²C-compatible devices connect to the I²C bus through open drain I/O pins, SDA and SCL. A *controller* device, usually a microcontroller or a digital signal processor, controls the bus. The controller is responsible for generating the SCL signal and device addresses. The controller also generates specific conditions that indicate the START and STOP of data transfer. A *target* device receives or transmits data on the bus under control of the controller device, or both.

The device works as a *target* and supports the following data transfer *modes*, as defined in the I²C-Bus Specification: standard mode (100 kbps) and fast mode (400 kbps), fast mode plus (1 Mbps), and high-speed mode (3.4 Mbps). The interface adds flexibility to the power supply solution, enabling most functions to be programmed to new values depending on the instantaneous application requirements. Register contents remain intact as long as the input voltage remains above 1.8 V.

The data transfer protocol for standard and fast modes is exactly the same, therefore, they are referred to as F/S-mode in this document. The protocol for high-speed mode is different from F/S-mode, and it is referred to as HS-mode.

It is recommended that the I²C controller initiates a STOP condition on the I²C bus after the initial power up of SDA and SCL pullup voltages to ensure reset of the I²C engine.



8.5.2 Standard-, Fast-, and Fast-Mode Plus Protocol

The controller initiates data transfer by generating a start condition. The start condition is when a high-to-low transition occurs on the SDA line while SCL is high, as shown in Figure 8-2. All I²C-compatible devices recognize a start condition.



Figure 8-2. START and STOP Conditions

The controller then generates the SCL pulses, and transmits the 7-bit address and the read/write direction bit R/\overline{W} on the SDA line. During all transmissions, the controller ensures that data is valid. A valid data condition requires the SDA line to be stable during the entire high period of the clock pulse (see Figure 8-3). All devices recognize the address sent by the controller and compare it to their internal fixed addresses. Only the target device with a matching address generates an acknowledge (see Figure 8-4) by pulling the SDA line low during the entire high period of the ninth SCL cycle. Upon detecting this acknowledge, the controller knows that communication link with a target has been established.



Figure 8-3. Bit Transfer on the Serial Interface

The controller generates further SCL cycles to either transmit data to the target (R/W bit 0) or receive data from the target (R/W bit 1). In either case, the receiver needs to acknowledge the data sent by the transmitter. So an acknowledge signal can either be generated by the controller or by the target, depending on which one is the receiver. 9-bit valid data sequences consisting of 8-bit data and 1-bit acknowledge can continue as long as necessary.

To signal the end of the data transfer, the controller generates a stop condition by pulling the SDA line from low to high while the SCL line is high (see Figure 8-2). This releases the bus and stops the communication link with the addressed target. All I²C compatible devices must recognize the stop condition. Upon the receipt of a stop condition, all devices know that the bus is released, and they wait for a start condition followed by a matching address.

Attempting to read data from register addresses not listed in this section results in 0x00 being read out.



Figure 8-4. Acknowledge on the I²C Bus



Figure 8-5. Bus Protocol

8.5.3 HS-Mode Protocol

The controller generates a start condition followed by a valid serial byte containing HS controller code 00001XXX. This transmission is made in F/S-mode at no more than 400 kbps. No device is allowed to acknowledge the HS controller code, but all devices must recognize it and switch their internal setting to support 3.4 Mbps operation.

The controller then generates a *repeated start condition* (a repeated start condition has the same timing as the start condition). After this repeated start condition, the protocol is the same as F/S-mode, except that transmission speeds up to 3.4 Mbps are allowed. A stop condition ends the HS-mode and switches all the internal settings of the target devices to support the F/S-mode. Instead of using a stop condition, repeated start conditions must be used to secure the bus in HS-mode.

Attempting to read data from register addresses not listed in this section results in 0x00 being read out.

8.5.4 I²C Update Sequence

The sequence requires a start condition, a valid I²C target address, a register address byte, and a data byte for a single update. After the receipt of each byte, the device acknowledges by pulling the SDA line low during the high period of a single clock pulse. A valid I²C address selects the device. The device performs an update on the falling edge of the acknowledge signal that follows the LSB byte.



	1	7		1	1		8		1		8		1	1		
	S	Target A	ddress	R/W	A	Reg	ister Ad	dress	A		Data		A/A	Р		
				"0" Write	9											
From Controller to Target A = Acknowledge (SDA low) From Target to Controller A = Not acknowledge (SDA high) S = START condition S = START condition Sr = REPEATED START condition P = STOP condition Figure 8-6. "Write" Data Transfer Format in Standard-, Fast, and Fast-Plus Modes																
1	7	7	1 1		8	1	1		8	1	1		8		1	1
S	Target A	Address R	W A	Registe	r Address	А	Sr	Target	Address	R/W	А		Data		A/A	Р
		"O" ⁻	 Vrite							 "1" Read	I					
Fror	m Controller to	Target										/	A = Acknov	wledge (SDA lov	N)

From Target to Controller

A = Not acknowledge (SDA high) S = START condition Sr = REPEATED START condition P = STOP condition

Figure 8-7. "Read" Data Transfer Format in Standard-, Fast, and Fast-Plus Modes



Figure 8-8. Data Transfer Format in HS-Mode

8.5.5 I²C Register Reset

The I²C registers can be reset by:

- Pulling the input voltage below 1.8 V (typ.)
- A high to low transition on EN
- Setting the Reset bit in the CONTROL register. When Reset is set to 1, all registers are reset to the default values and a new start-up is begun immediately. After t_{Delay}, the I²C registers can be programmed again.

8.6 Register Map

REGISTER ADDRESS (HEX)	REGISTER NAME	FACTORY DEFAULT (HEX)	DESCRIPTION						
0x01	V _{OUT} Register 1	0x64	Sets the target output voltage						
0x02	V _{OUT} Register 2	0x64	Sets the target output voltage						
0x03	CONTROL Register	0x6F	Sets miscellaneous configuration bits						
0x05	STATUS Register	0x00	Returns status flags						

Table 8-5, Register Map

8.6.1 Target Address Byte

7	6	5	4	3	2	1	0
1	х	х	х	х	х	х	R/W

The target address byte is the first byte received following the START condition from the controller device. The target addresses can be assigned by an external resistor, see Table 8-1.



8.6.2 Register Address Byte

7	6	5	4	3	2	1	0
0	0	0	0	0	D2	D1	D0

Following the successful acknowledgment of the target address, the bus controller sends a byte to the device, which contains the address of the register to be accessed.

8.6.3 V_{OUT} Register 1

Table 8-6. V_{OUT} Register 1 Description

REGISTER ADDRESS 0X01 READ/WRITE				
BIT	FIELD	VALUE (HEX)	OUTPUT VOLTAGE (TYP)	
7:0	VO1_SET	0x00	Voltage Factor * 400 mV	
		0x01	Voltage Factor * 405 mV	
		0x64	Voltage Factor * 900 mV	
		0xFE	Voltage Factor * 1670 mV	
		0xFF	Voltage Factor * 1675 mV	

8.6.4 V_{OUT} Register 2

Table 8-7. V_{OUT} Register 2 Description

REGISTER ADDRESS	REGISTER ADDRESS 0X02 READ/WRITE				
BIT	FIELD	VALUE (HEX)	OUTPUT VOLTAGE (TYP)		
7:0	VO2_SET	0x00	Voltage Factor * 400 mV		
		0x01	Voltage Factor * 405 mV		
		0x64	Voltage Factor * 900 mV (default value)		
		0xFE	Voltage Factor * 1670 mV		
		0xFF	Voltage Factor * 1675 mV		



8.6.5 CONTROL Register

REGISTER	(EGISTER ADDRESS 0X03 WRITE ONLY				
BIT	FIELD	TYPE	DEFAULT	DESCRIPTION	
7	Reset	R/W	0	1 - Reset all registers to default.	
6	Enable FPWM Mode during Output Voltage Change	R/W	1	0 - Keep the current mode status during output voltage change 1 - Force the device in FPWM during output voltage change.	
5	Software Enable Device	R/W	1	 0 - Disable the device. All registers values are still kept. 1 - Re-enable the device with a new start-up without the t_{Delay} period. 	
4	Enable FPWM Mode	R/W	0	0 - Set the device in power save mode at light loads. 1 - Set the device in forced PWM mode at light loads.	
3	Enable Output Discharge	R/W	1	0 - Disable output discharge. 1 - Enable output discharge.	
2	Enable HICCUP	R/W	1	0 - Disable HICCUP. Enable latching protection. 1 - Enable HICCUP, Disable latching protection.	
0:1	Voltage Ramp Speed	R/W	11	00 - 20mV/μs (0.25 μs/step) 01 - 10 mV/μs (0.5 μs/step) 10 - 5 mV/μs (1 μs/step) 11 - 1 mV/μs (5 μs/step, default)	

Table 8-8. CONTROL Register Description

8.6.6 STATUS Register

Table 8-9. STATUS Register Description

REGISTER ADDRESS 0X05 READ ONLY ⁽¹⁾					
BIT	FIELD	TYPE	DEFAULT	DESCRIPTION	
7:5	Reserved				
4	Thermal Warning	R	0	1: Junction temperature is higher than 130°C.	
3	HICCUP	R	0	1: Device has HICCUP status once.	
2	Reserved				
1	Reserved				
0	UVLO	R	0	1: The input voltage is less than UVLO threshold (falling edge).	

(1) All bit values are latched until the device is reset, or the STATUS register is read. Then, the STATUS register is reset to its default values.



9 Application and Implementation

Note

Information in the following applications sections is not part of the TI component specification, and TI does not warrant its accuracy or completeness. TI's customers are responsible for determining suitability of components for their purposes, as well as validating and testing their design implementation to confirm system functionality.

9.1 Application Information

The following section discusses the design of the external components to complete the power supply design for several input and output voltage options by using typical applications as a reference.

9.2 Typical Application



Figure 9-1. Typical Application

9.2.1 Design Requirements

For this design example, use the parameters listed in Table 9-1 as the input parameters.

DESIGN PARAMETER	EXAMPLE VALUE			
Input voltage	2.4 V to 5.5 V			
Output voltage	0.9 V			
Maximum output current	6 A			

Table 9-1. Design Parameters

Table 9-2 lists the components used for the example.

Table 9-2. List of Components of Table 9-1

REFERENCE	DESCRIPTION	MANUFACTURER ⁽¹⁾
C1	2 × 10 μF, Ceramic capacitor, 6.3 V, X7R, size 0603, CL10B106MQ8NRNC	Samsung Electro- Mechanics
C2	2 × 22 μF, Ceramic capacitor, 6.3 V, X7R, size 0805, GRM21BZ70J226ME44L	Murata
L1	0.22 μH, Power inductor, XAL4020-221ME (12 A, 5.81 mΩ)	Coilcraft
R1	Depending on the start-up output voltage, size 0603	Std

(1) See Third-party Products disclaimer.

9.2.2 Detailed Design Procedure

9.2.2.1 Setting The Output Voltage

The initial output voltage is set by an external resistor connected to the VSET/VID pin, according to Table 8-1. After the soft start-up, the output voltage can be changed in the V_{OUT} Registers. Refer to Table 8-6 and Table 8-7.

9.2.2.2 Output Filter Design

The inductor and the output capacitor together provide a low-pass filter. To simplify this process, Table 9-3 outlines possible inductor and capacitor value combinations for most applications. Checked cells represent combinations that are proven for stability by simulation and lab test. Further combinations should be checked for each individual application.

	NOMINAL C _{OUT} [µF] ⁽³⁾				
	22	2 x 22 or 47	3 x 22	150	
0.24		+ (1)	+	+	

(1) This LC combination is the standard value and recommended for most applications.

(2) Inductor tolerance and current derating is anticipated. The effective inductance can vary by 20% and -30%.

(3) Capacitance tolerance and bias voltage derating is anticipated. The effective capacitance can vary by 20% and -30%.

9.2.2.3 Inductor Selection

The main parameter for the inductor selection is the inductor value and then the saturation current of the inductor. To calculate the maximum inductor current under static load conditions, Equation 3 is given.

$$I_{L,MAX} = I_{OUT,MAX} + \frac{\Delta I_{L}}{2}$$

$$\Delta I_{L} = V_{OUT} \times \frac{1 - \frac{V_{OUT}}{V_{IN}}}{L \times f_{SW}}$$

where

- I_{OUT,MAX} = maximum output current
- ΔI_L = inductor current ripple
- f_{SW} = switching frequency
- L = inductor value

It is recommended to choose a saturation current for the inductor that is approximately 20% to 30% higher than $I_{L,MAX}$. In addition, DC resistance and size must also be taken into account when selecting an appropriate inductor. Table 9-4 lists recommended inductors.

INDUCTANCE [µH]	CURRENT RATING, I _{SAT} [A]	DIMENSIONS [L x W x H mm]	DC RESISTANCE [mΩ]	PART NUMBER		
0.22	18.7	4 x 4 x 2	5.81	Coilcraft, XAL4020-221ME		
0.24	6.6	2 x 1.6 x 1.2	13	Murata, DFE201612E-R24M		

Table 9-4. List of Recommended Inductors

9.2.2.4 Capacitor Selection

The input capacitor is the low-impedance energy source for the converter which helps to provide stable operation. A low-ESR multilayer ceramic capacitor is recommended for best filtering and must be placed between VIN and PGND as close as possible to those pins. For most applications, 8 μ F is a sufficient value for the effective input capacitance, though a larger value reduces input current ripple.

(3)

Copyright © 2021 Texas Instruments Incorporated



The architecture of the device allows the use of tiny ceramic output capacitors with low equivalent series resistance (ESR). These capacitors provide low output voltage ripple and are recommended. To keep its low resistance up to high frequencies and to get narrow capacitance variation with temperature, TI recommends using X7R or X5R dielectrics. The recommended minimum output effective capacitance is 30 μ F; this capacitance can vary over a wide range as outline in the output filter selection table.



9.2.3 Application Curves

 V_{IN} = 5.0 V, V_{OUT} = 0.9 V, T_A = 25°C, BOM = Table 9-2, unless otherwise noted.



SLVSFS3B – SEPTEMBER 2020 – REVISED JULY 2021











9.3 Typical Application – TPS6286x0A and TPS6286x0xC Devices



Figure 9-20. Typical Application

9.3.1 Design Requirements

For this design example, use the parameters listed in Table 9-5 as the input parameters.

DESIGN PARAMETER	EXAMPLE VALUE
Input Voltage Range	2.4 V to 5.5 V
Output Voltage	0.5 V
Maximum Output Current	6 A

Table 9-6 lists the components used in this example.

REFERENCE	DESCRIPTION	MANUFACTURER1
C1	2 × 10 µF Ceramic capacitor, 6.3 V, X7R, size 0603, CL10B106MQ8NRNC	Samsung Electro- Mechanics
C2	3 × 22 µF Ceramic capacitor, 6.3 V, X7R, size 0805, GRM21BZ70J226ME44L	Murata
L1	0.1 µH Power inductor, XEL4020-101ME	Coilcraft
R1	10 kΩ, size 0603	Standard

1. See the Third-Party Products Disclaimer.

9.3.2 Detailed Design Procedure

9.3.2.1 Setting the Output Voltage

The start-up output voltage of the TPS6286900C device is factory-programmed to 0.5 V and therefore no additional external components are needed. After start-up, the output voltage can be changed by using the I^2C interface to program the VOUT Register 1.

9.3.2.2 Output Filter Design

The inductor and output capacitor form a low-pass filter. To simplify the design process, Table 9-7 outlines possible inductor and capacitor combinations for most applications. Checked cells represent combinations that have been proven for stability by simulation and lab testing. Further combinations, not listed in , should be checked for the specific application.

Table 9-7. Matrix of Output Capacitor and Inductor Combinations

NOMINAL L [µH] ⁽²⁾	NOMINAL C _{OUT} [µF] ⁽³⁾								
	22	2 × 22 or 47	3 × 22	150					
0.1		+	+(1)	+					

(1) This LC combination is the standard value and recommended for most applications.



- (2) Inductor tolerance and current derating is anticipated. The effective inductance can vary by 20% and -30%.
- (3) Capacitance tolerance and bias voltage derating is anticipated. The effective capacitance can vary by 20% and -30%.

9.3.2.3 Inductor Selection

Inductor selection for the TPS6286x0A and TPS6286x0xC (0.2-V to 0.8375-V) device variants follows the same procedure as for the other device variants (see Section 9.2.2.3). Table 9-8 lists recommended inductors for the low-voltage device variants.

INDUCTANCE [µH]	CURRENT RATING, I _{SAT} [A]	DIMENSIONS [L × W × H mm]	DC RESISTANCE [mΩ]	PART NUMBER							
0.1	28.5	4 × 4 × 2	2	Coilcraft, XEL4020-101ME							

Table 9-8. List of Recommended Inductors

9.3.2.4 Capacitor Selection

Capacitor selection for the TPS6286x0A and TPS6286x0xC (0.2-V to 0.8375-V) device variants follows the same procedure as for the other device variants (see Section 9.2.2.4).

9.3.3 Application Curves

 V_{IN} = 5.0 V, V_{OUT} = 0.5 V, T_A = 25°C, BOM = Table 9-6, unless otherwise noted.



INSTRUMENTS **TPS62868, TPS62869** SLVSFS3B - SEPTEMBER 2020 - REVISED JULY 2021 www.ti.com 3.0 3.0 2.5 2.5 Switching Frequency (MHz) Switching Frequency (MHz) 2.0 2.0 1.5 1.5 1.0 1.0 0.5 0.5 V_{OUT} = 0.4 V V_{OUT} = 0.6 V V_{OUT} = 0.6 V, FPWM V_{OUT} = 0.6 V, PSM 0.0 0.0 5 4.0 Input Voltage (V) 1 ² ³ ⁴ Output Current (A) 5 6 2.5 3.0 5.0 0 4.5 5.5 3.5 V_{IN} = 5 V I_{OUT} = 1 A Figure 9-25. Switching Frequency Figure 9-26. Switching Frequency

10 Power Supply Recommendations

The device is designed to operate from an input voltage supply range from 2.4 V to 5.5 V. Ensure that the input power supply has a sufficient current rating for the application. The power supply must avoid a fast ramp down. The falling ramp speed must be slower than 10 mV/ μ s, if the input voltage drops below V_{UVLO}.

Texas



11 Layout

11.1 Layout Guidelines

The printed-circuit-board (PCB) layout is an important step to maintain the high performance of the device.

- The input/output capacitors and the inductor must be placed as close as possible to the IC. This keeps the power traces short. Routing these power traces direct and wide results in low trace resistance and low parasitic inductance.
- The low side of the input and output capacitors must be connected properly to the PGND to avoid a GND potential shift.
- The sense traces connected to the VOS pin is a signal trace. Special care must be taken to avoid noise being induced. Keep the trace away from SW.
- Refer to Figure 11-1 for an example of component placement, routing, and thermal design.

11.2 Layout Example



Figure 11-1. Layout Example

11.2.1 Thermal Considerations

Implementation of integrated circuits in low-profile and fine-pitch surface-mount packages typically requires special attention to power dissipation. Many system-dependent issues such as thermal coupling, airflow, added heat sinks and convection surfaces, and the presence of other heat-generating components affect the power dissipation limits of a given component.

Two basic approaches for enhancing thermal performance are improving the power dissipation capability of the PCB design and introducing airflow in the system. For more details on how to use the thermal parameters, see the *Semiconductor and IC Package Thermal Metrics Application Report*.



12 Device and Documentation Support

12.1 Device Support

12.1.1 Third-Party Products Disclaimer

TI'S PUBLICATION OF INFORMATION REGARDING THIRD-PARTY PRODUCTS OR SERVICES DOES NOT CONSTITUTE AN ENDORSEMENT REGARDING THE SUITABILITY OF SUCH PRODUCTS OR SERVICES OR A WARRANTY, REPRESENTATION OR ENDORSEMENT OF SUCH PRODUCTS OR SERVICES, EITHER ALONE OR IN COMBINATION WITH ANY TI PRODUCT OR SERVICE.

12.2 Documentation Support

12.2.1 Related Documentation

For related documentation, see the following:

Texas Instruments, Semiconductor and IC Package Thermal Metrics Application Report

12.3 Support Resources

TI E2E[™] support forums are an engineer's go-to source for fast, verified answers and design help — straight from the experts. Search existing answers or ask your own question to get the quick design help you need.

Linked content is provided "AS IS" by the respective contributors. They do not constitute TI specifications and do not necessarily reflect TI's views; see TI's Terms of Use.

12.4 Receiving Notification of Documentation Updates

To receive notification of documentation updates, navigate to the device product folder on ti.com. Click on *Subscribe to updates* to register and receive a weekly digest of any product information that has changed. For change details, review the revision history included in any revised document.

12.5 Trademarks

DCS-Control[™] is a trademark of TI. I2C[™] is a trademark of NXP Semiconductors. TI E2E[™] is a trademark of Texas Instruments. WEBENCH[®] is a registered trademark of Texas Instruments. All trademarks are the property of their respective owners.

12.6 Glossary

TI Glossary This glossary lists and explains terms, acronyms, and definitions.

12.7 Electrostatic Discharge Caution



This integrated circuit can be damaged by ESD. Texas Instruments recommends that all integrated circuits be handled with appropriate precautions. Failure to observe proper handling and installation procedures can cause damage.

ESD damage can range from subtle performance degradation to complete device failure. Precision integrated circuits may be more susceptible to damage because very small parametric changes could cause the device not to meet its published specifications.

13 Mechanical, Packaging, and Orderable Information

The following pages include mechanical, packaging, and orderable information. This information is the most current data available for the designated devices. This data is subject to change without notice and revision of this document. For browser-based versions of this data sheet, refer to the left-hand navigation.



PACKAGING INFORMATION

Orderable Device	Status	Package Type	Package Drawing	Pins	Package Qty	Eco Plan	Lead finish/ Ball material	MSL Peak Temp	Op Temp (°C)	Device Marking	Samples
	(1)		J			(2)	(6)	(0)		(
TPS6286800CRQYR	ACTIVE	VQFN-HR	RQY	9	3000	RoHS & Green	SN	Level-2-260C-1 YEAR	-40 to 125	2JOH	Samples
TPS628680ARQYR	ACTIVE	VQFN-HR	RQY	9	3000	RoHS & Green	SN	Level-2-260C-1 YEAR	-40 to 125	218H	Samples
TPS6286810CRQYR	ACTIVE	VQFN-HR	RQY	9	3000	RoHS & Green	SN	Level-2-260C-1 YEAR	-40 to 125	2JPH	Samples
TPS628681ARQYR	ACTIVE	VQFN-HR	RQY	9	3000	RoHS & Green	SN	Level-2-260C-1 YEAR	-40 to 125	2ECH	Samples
TPS6286820CRQYR	ACTIVE	VQFN-HR	RQY	9	3000	RoHS & Green	SN	Level-2-260C-1 YEAR	-40 to 125	2JQH	Samples
TPS628682ARQYR	ACTIVE	VQFN-HR	RQY	9	3000	RoHS & Green	SN	Level-2-260C-1 YEAR	-40 to 125	2IAH	Samples
TPS6286900CRQYR	ACTIVE	VQFN-HR	RQY	9	3000	RoHS & Green	SN	Level-2-260C-1 YEAR	-40 to 125	2JRH	Samples
TPS628690ARQYR	ACTIVE	VQFN-HR	RQY	9	3000	RoHS & Green	SN	Level-2-260C-1 YEAR	-40 to 125	2I7H	Samples
TPS6286910CRQYR	ACTIVE	VQFN-HR	RQY	9	3000	RoHS & Green	SN	Level-2-260C-1 YEAR	-40 to 125	2JSH	Samples
TPS628691ARQYR	ACTIVE	VQFN-HR	RQY	9	3000	RoHS & Green	SN	Level-2-260C-1 YEAR	-40 to 125	2EBH	Samples
TPS6286920CRQYR	ACTIVE	VQFN-HR	RQY	9	3000	RoHS & Green	SN	Level-2-260C-1 YEAR	-40 to 125	2JTH	Samples
TPS628692ARQYR	ACTIVE	VQFN-HR	RQY	9	3000	RoHS & Green	SN	Level-2-260C-1 YEAR	-40 to 125	2I9H	Samples

⁽¹⁾ The marketing status values are defined as follows:

ACTIVE: Product device recommended for new designs.

LIFEBUY: TI has announced that the device will be discontinued, and a lifetime-buy period is in effect.

NRND: Not recommended for new designs. Device is in production to support existing customers, but TI does not recommend using this part in a new design.

PREVIEW: Device has been announced but is not in production. Samples may or may not be available.

OBSOLETE: TI has discontinued the production of the device.

⁽²⁾ RoHS: TI defines "RoHS" to mean semiconductor products that are compliant with the current EU RoHS requirements for all 10 RoHS substances, including the requirement that RoHS substance do not exceed 0.1% by weight in homogeneous materials. Where designed to be soldered at high temperatures, "RoHS" products are suitable for use in specified lead-free processes. TI may reference these types of products as "Pb-Free".

RoHS Exempt: TI defines "RoHS Exempt" to mean products that contain lead but are compliant with EU RoHS pursuant to a specific EU RoHS exemption.

Green: TI defines "Green" to mean the content of Chlorine (CI) and Bromine (Br) based flame retardants meet JS709B low halogen requirements of <= 1000ppm threshold. Antimony trioxide based flame retardants must also meet the <= 1000ppm threshold requirement.



www.ti.com

PACKAGE OPTION ADDENDUM

⁽³⁾ MSL, Peak Temp. - The Moisture Sensitivity Level rating according to the JEDEC industry standard classifications, and peak solder temperature.

⁽⁴⁾ There may be additional marking, which relates to the logo, the lot trace code information, or the environmental category on the device.

(5) Multiple Device Markings will be inside parentheses. Only one Device Marking contained in parentheses and separated by a "~" will appear on a device. If a line is indented then it is a continuation of the previous line and the two combined represent the entire Device Marking for that device.

⁽⁶⁾ Lead finish/Ball material - Orderable Devices may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead finish/Ball material values may wrap to two lines if the finish value exceeds the maximum column width.

Important Information and Disclaimer:The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.

PACKAGE MATERIALS INFORMATION

Texas Instruments

www.ti.com

TAPE AND REEL INFORMATION





QUADRANT ASSIGNMENTS FOR PIN 1 ORIENTATION IN TAPE



Device	Package	Package	Pins	SPQ	Reel	Reel	A0	B0	K0	P1	W	Pin1
	Туре	Drawing			Diameter (mm)	Width W1 (mm)	(mm)	(mm)	(mm)	(mm)	(mm)	Quadrant
TPS6286800CRQYR	VQFN- HR	RQY	9	3000	180.0	8.4	1.8	2.8	1.12	4.0	8.0	Q1
TPS628680ARQYR	VQFN- HR	RQY	9	3000	180.0	8.4	1.8	2.8	1.12	4.0	8.0	Q1
TPS6286810CRQYR	VQFN- HR	RQY	9	3000	180.0	8.4	1.8	2.8	1.12	4.0	8.0	Q1
TPS628681ARQYR	VQFN- HR	RQY	9	3000	180.0	8.4	1.8	2.8	1.12	4.0	8.0	Q1
TPS6286820CRQYR	VQFN- HR	RQY	9	3000	180.0	8.4	1.8	2.8	1.12	4.0	8.0	Q1
TPS628682ARQYR	VQFN- HR	RQY	9	3000	180.0	8.4	1.8	2.8	1.12	4.0	8.0	Q1
TPS6286900CRQYR	VQFN- HR	RQY	9	3000	180.0	8.4	1.8	2.8	1.12	4.0	8.0	Q1
TPS628690ARQYR	VQFN- HR	RQY	9	3000	180.0	8.4	1.8	2.8	1.12	4.0	8.0	Q1
TPS6286910CRQYR	VQFN- HR	RQY	9	3000	180.0	8.4	1.8	2.8	1.12	4.0	8.0	Q1
TPS628691ARQYR	VQFN- HR	RQY	9	3000	180.0	8.4	1.8	2.8	1.12	4.0	8.0	Q1
TPS6286920CRQYR	VQFN-	RQY	9	3000	180.0	8.4	1.8	2.8	1.12	4.0	8.0	Q1



www.ti.com

28-Oct-2021

Device	Package Type	Package Drawing	Pins	SPQ	Reel Diameter (mm)	Reel Width W1 (mm)	A0 (mm)	B0 (mm)	K0 (mm)	P1 (mm)	W (mm)	Pin1 Quadrant
	HR											
TPS628692ARQYR	VQFN- HR	RQY	9	3000	180.0	8.4	1.8	2.8	1.12	4.0	8.0	Q1



*All dimensions are nominal

Device	Package Type	Package Drawing	Pins	SPQ	Length (mm)	Width (mm)	Height (mm)
TPS6286800CRQYR	VQFN-HR	RQY	9	3000	210.0	185.0	35.0
TPS628680ARQYR	VQFN-HR	RQY	9	3000	210.0	185.0	35.0
TPS6286810CRQYR	VQFN-HR	RQY	9	3000	210.0	185.0	35.0
TPS628681ARQYR	VQFN-HR	RQY	9	3000	210.0	185.0	35.0
TPS6286820CRQYR	VQFN-HR	RQY	9	3000	210.0	185.0	35.0
TPS628682ARQYR	VQFN-HR	RQY	9	3000	210.0	185.0	35.0
TPS6286900CRQYR	VQFN-HR	RQY	9	3000	210.0	185.0	35.0
TPS628690ARQYR	VQFN-HR	RQY	9	3000	210.0	185.0	35.0
TPS6286910CRQYR	VQFN-HR	RQY	9	3000	210.0	185.0	35.0
TPS628691ARQYR	VQFN-HR	RQY	9	3000	210.0	185.0	35.0
TPS6286920CRQYR	VQFN-HR	RQY	9	3000	210.0	185.0	35.0
TPS628692ARQYR	VQFN-HR	RQY	9	3000	210.0	185.0	35.0

RQY0009A

PACKAGE OUTLINE

VQFN-HR - 1 mm max height

PLASTIC QUAD FLATPACK- NO LEAD



NOTES:

- 1. All linear dimensions are in millimeters. Any dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.
- 2. This drawing is subject to change without notice.



<u>RQY0009A</u>

EXAMPLE BOARD LAYOUT

VQFN-HR - 1 mm max height

PLASTIC QUAD FLATPACK- NO LEAD



NOTES: (continued)

- 3. For more information, see Texas Instruments literature number SLUA271 (www.ti.com/lit/slua271).
- 4. Solder mask tolerances between and around signal pads can vary based on board fabrication site.



RQY0009A

EXAMPLE STENCIL DESIGN

VQFN-HR - 1 mm max height

PLASTIC QUAD FLATPACK- NO LEAD



NOTES: (continued)

5. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.



IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATA SHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, regulatory or other requirements.

These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you will fully indemnify TI and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to TI's Terms of Sale or other applicable terms available either on ti.com or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products.

TI objects to and rejects any additional or different terms you may have proposed.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265 Copyright © 2023, Texas Instruments Incorporated