

TMUX405x-EP Enhanced Product 24V, 8:1, 1-Channel, 4:1, 2-Channel, and 2:1, 3-Channel Multiplexers with 1.8V Logic

1 Features

- VID V62/25616
- EP (Enhanced Product) qualified for high-reliability applications
- Supports defense and aerospace applications:
 - Controlled baseline
 - One fabrication site
 - One assembly and test site
 - Military temperature range: -55°C to $+125^{\circ}\text{C}$ T_A
 - Extended product life cycle
 - Product traceability
- Single supply range: 5V to 24V
- Dual supply range: up to $\pm 12\text{V}$
- Low capacitance: 3pF
- [Bidirectional signal path](#)
- [Rail-to-rail operation](#)
- [1.8V logic compatible](#)
- Break-before-make switching
- ESD protection HBM: 2000V

2 Applications

- Analog multiplexing and demultiplexing
- Battery management systems (BMS)
- HVAC control module
- Telematics
- On-board (OBC) and wireless charging
- Aircraft cockpit display and Flight control units
- Radar and Sonar
- Electronic warfare
- Seeker front end


3 Description

The TMUX405x-EP devices are general purpose complementary metal-oxide semiconductor (CMOS) multiplexers (MUX). The TMUX4051-EP is an 8:1, 1-channel multiplexer, the TMUX4052-EP is a 4:1, 2-channel multiplexer, and the TMUX4053-EP is a 2:1, 3-channel multiplexer. The device works with a single supply (5V to 24V), dual supplies (up to $\pm 12\text{V}$), or asymmetric supplies (such as $V_{DD} = 12\text{V}$, $V_{SS} = -5\text{V}$). The wide supply voltage range allows the TMUX405x-EP to be used in a broad array of applications from battery testers to appliances. The TMUX405x-EP device supports bidirectional analog signals on the source (Sx) and drain (Dx) pins ranging from VSS to VDD. All logic inputs have 1.8V logic compatible thresholds, which is compatible for both TTL and CMOS logic when operating with a valid supply voltage

Package Information

PART NUMBER	PACKAGE	PACKAGE SIZE ⁽¹⁾
TMUX4051-EP	DYY (SOT-23-THIN, 16)	4.2mm × 2mm
TMUX4052-EP	DYY (SOT-23-THIN, 16)	4.2mm × 2mm
TMUX4053-EP	DYY (SOT-23-THIN, 16)	4.2mm × 2mm

(1) For more information, see [Section 11](#).



TMUX405x-EP Block Diagram



Table of Contents

1 Features	1	6.11 Bandwidth.....	18
2 Applications	1	7 Detailed Description	19
3 Description	1	7.1 Overview.....	19
4 Pin Configuration and Functions	3	7.2 Functional Block Diagram.....	19
5 Specifications	6	7.3 Feature Description.....	19
5.1 Absolute Maximum Ratings.....	6	8 Application and Implementation	21
5.2 ESD Ratings.....	6	8.1 Application Information.....	21
5.3 Thermal Information: TMUX405x.....	7	8.2 Typical Application.....	21
5.4 Recommended Operating Conditions.....	7	8.3 Design Requirements.....	22
5.5 Electrical Characteristics.....	8	8.4 Detailed Design Procedure.....	22
5.6 AC Performance Characteristics.....	10	8.5 Application Curves.....	22
5.7 Timing Characteristics.....	11	8.6 Power Supply Recommendations.....	22
6 Parameter Measurement Information	13	8.7 Layout.....	23
6.1 On-Resistance.....	13	9 Device and Documentation Support	24
6.2 Off-Leakage Current.....	13	9.1 Documentation Support.....	24
6.3 On-Leakage Current.....	14	9.2 Receiving Notification of Documentation Updates.....	24
6.4 Transition Time.....	14	9.3 Support Resources.....	24
6.5 Break-Before-Make.....	15	9.4 Trademarks.....	24
6.6 $t_{ON(EN)}$ and $t_{OFF(EN)}$	15	9.5 Electrostatic Discharge Caution.....	24
6.7 Propagation Delay.....	16	9.6 Glossary.....	24
6.8 Charge Injection.....	16	10 Revision History	24
6.9 Off Isolation.....	17	11 Mechanical, Packaging, and Orderable Information	24
6.10 Crosstalk.....	17		

4 Pin Configuration and Functions




Figure 4-1. TMUX4051-EP DYY Package, 16-Pin SOT-23-THIN (Top View)

Pin Functions - TMUX4051-EP

PIN		TYPE ⁽¹⁾	DESCRIPTION ⁽²⁾
NAME	NO.		
S4	1	I/O	Source pin 4. Signal path can be an input or output.
S6	2	I/O	Source pin 6. Signal path can be an input or output.
D	3	I/O	Drain pin (common). Signal path can be an input or output.
S7	4	I/O	Source pin 7. Signal path can be an input or output.
S5	5	I/O	Source pin 5. Signal path can be an input or output.
EN	6	I	Active low logic enable. When this pin is high, all switches are turned off. Section 10 lists how the A[2:0] address inputs determine which switch is turned on when this pin is low.
V _{SS}	7	P	Negative power supply. This pin is the most negative power-supply potential. For reliable operation, connect a decoupling capacitor ranging from 0.1µF to 10µF between V _{SS} and GND.
GND	8	P	Ground (0V) reference
A2	9	I	Address line 2. Section 10 provides information about how A2 controls the switch configuration.
A1	10	I	Address line 1. Section 10 provides information about how A1 controls the switch configuration.
A0	11	I	Address line 0. Section 10 provides information about how A0 controls the switch configuration.
S3	12	I/O	Source pin 3. Signal path can be an input or output.
S0	13	I/O	Source pin 0. Signal path can be an input or output.
S1	14	I/O	Source pin 1. Signal path can be an input or output.
S2	15	I/O	Source pin 2. Signal path can be an input or output.
V _{DD}	16	P	Positive power supply. This pin is the most positive power-supply potential. For reliable operation, connect a decoupling capacitor ranging from 0.1µF to 10µF between V _{DD} and GND.

(1) I = input, O = output, I/O = input and output, P = power.

(2) For what to do with unused pins, refer to [Section 7.3.4](#).




Figure 4-2. TMUX4052-EP DYY Package, 16-Pin SOT-23-THIN (Top View)

Table 4-1. Pin Functions - TMUX4052-EP

PIN		TYPE ⁽¹⁾	DESCRIPTION ⁽²⁾
NAME	NO.		
S0B	1	I/O	Source pin 0 of mux B. Signal path can be an input or output
S2B	2	I/O	Source pin 2 of mux B. Signal path can be an input or output.
DB	3	I/O	Drain pin (common) of mux B. Signal path can be an input or output.
S3B	4	I/O	Source pin 3 of mux B. Signal path can be an input or output.
S1B	5	I/O	Source pin 1 of mux B. Signal path can be an input or output.
EN	6	I	Active low logic enable. When this pin is high, all switches are turned off. Section 10 lists how the A[2:0] address inputs determine which switch is turned on when this pin is low.
V _{SS}	7	P	Negative power supply. This pin is the most negative power-supply potential. For reliable operation, connect a decoupling capacitor ranging from 0.1μF to 10μF between V _{SS} and GND.
GND	8	P	Ground (0V) reference
A1	9	I	Address line 1. Section 10 provides information about how A1 controls the switch configuration.
A0	10	I	Address line 0. Section 10 provides information about how A0 controls the switch configuration.
S3A	11	I	Source pin 3 of mux A. Signal path can be an input or output.
S0A	12	I/O	Source pin 0 of mux A. Signal path can be an input or output.
DA	13	I/O	Drain pin (common) of mux A. Signal path can be an input or output.
S1A	14	I/O	Source pin 1 of mux A. Signal path can be an input or output.
S2A	15	I/O	Source pin 2 of mux A. Signal path can be an input or output.
V _{DD}	16	P	Positive power supply. This pin is the most positive power-supply potential. For reliable operation, connect a decoupling capacitor ranging from 0.1μF to 10μF between V _{DD} and GND.




Figure 4-3. TMUX4053-EP DYY Package, 16-Pin SOT-23-THIN (Top View)

Table 4-2. Pin Functions - TMUX4053-EP

PIN		TYPE ⁽¹⁾	DESCRIPTION ⁽²⁾
NAME	NO.		
S2B	1	I/O	Source pin B of switch 2. Signal path can be an input or output.
S2A	2	I/O	Source pin A of switch 2. Signal path can be an input or output.
S3B	3	I/O	Source pin B of switch 3. Signal path can be an input or output.
D3	4	I/O	Drain pin (common) of switch 3. Signal path can be an input or output.
S3A	5	I/O	Source pin A of switch 3. Signal path can be an input or output.
EN	6	I	Active low logic enable. When this pin is high, all switches are turned off. Section 10 lists how the A[2:0] address inputs determine which switch is turned on when this pin is low.
V _{SS}	7	P	Negative power supply. This pin is the most negative power-supply potential. For reliable operation, connect a decoupling capacitor ranging from 0.1µF to 10µF between V _{SS} and GND.
GND	8	P	Ground (0V) reference
SEL3	9	I	Logic control select pin 3. Section 10 provides controls switch 3 configuration
SEL2	10	I	Logic control select pin 2. Section 10 provides controls switch 2 configuration
SEL1	11	I	Logic control select pin 1. Section 10 provides controls switch 1 configuration
S1A	12	I/O	Source pin A of switch 1. Signal path can be an input or output.
S1B	13	I/O	Source pin B of switch 1. Signal path can be an input or output.
D1	14	I/O	Drain pin (common) of switch 1. Signal path can be an input or output.
D2	15	I/O	Drain pin (common) of switch 2. Signal path can be an input or output.
V _{DD}	16	P	Positive power supply. This pin is the most positive power-supply potential. For reliable operation, connect a decoupling capacitor ranging from 0.1µF to 10µF between V _{DD} and GND.

5 Specifications

5.1 Absolute Maximum Ratings

over operating free-air temperature range (unless otherwise noted)⁽¹⁾⁽³⁾

		MIN	MAX	UNIT
$V_{DD} - V_{SS}$	Supply voltage		28	V
V_{DD}		-0.5	28	V
V_{SS}		-28	0.5	V
V_{SEL} or V_{EN}	Logic control input pin voltage ($\overline{EN}$, Ax, SELx)	-0.5	$V_{DD}+0.5$	V
I_{SEL} or I_{EN}	Logic control input pin current ($\overline{EN}$, Ax, SELx)	-0.5	28	mA
V_S or V_D	Source or drain voltage (Sx, D)	$V_{SS}-0.5$	$V_{DD}+0.5$	V
I_{IK}	Diode clamp current ⁽²⁾	-30	30	mA
I_S or I_D (CONT)	Source or drain continuous current (Sx, D)	-10	10	mA
T_J	Junction temperature		150	°C
T_{stg}	Storage temperature	-65	150	°C

- (1) Operation outside the *Absolute Maximum Ratings* may cause permanent device damage. Absolute maximum ratings do not imply functional operation of the device at these or any other conditions beyond those listed under *Recommended Operating Conditions*. If briefly operating outside the *Recommended Operating Conditions* but within the *Absolute Maximum Ratings*, the device may not sustain damage, but it may not be fully functional. Operating the device in this manner may affect device reliability, functionality, performance, and shorten the device lifetime.
- (2) Pins are diode-clamped to the power-supply rails. Over voltage signals must be voltage and current limited to maximum ratings.
- (3) To avoid drawing excess current from V_{DD} , or into V_{SS} , the voltage drop across the bidirectional switch path (ΔV_{switch}) must not exceed 1.2V (600mV for high temperature).

5.2 ESD Ratings

			VALUE	UNIT
$V_{(ESD)}$	Electrostatic discharge	Human body model (HBM), per ANSI/ESDA/JEDEC JS-001, all pins ⁽¹⁾	±2000	V
		Charged device model (CDM), per ANSI/ESDA/JEDEC JS-002, all pins ⁽²⁾	±500	

- (1) JEDEC document JEP155 states that 500V HBM allows safe manufacturing with a standard ESD control process.
- (2) JEDEC document JEP157 states that 250V CDM allows safe manufacturing with a standard ESD control process.

5.3 Thermal Information: TMUX405x

THERMAL METRIC ⁽¹⁾		TMUX405x-EP	UNIT
		DYY (SOT)	
		16 PINS	
$R_{\theta JA}$	Junction-to-ambient thermal resistance	138.9	°C/W
$R_{\theta JC(top)}$	Junction-to-case (top) thermal resistance	70.3	°C/W
$R_{\theta JB}$	Junction-to-board thermal resistance	69.1	°C/W
Ψ_{JT}	Junction-to-top characterization parameter	5.1	°C/W
Ψ_{JB}	Junction-to-board characterization parameter	69.0	°C/W
$R_{\theta JC(bot)}$	Junction-to-case (bottom) thermal resistance	N/A	°C/W

(1) For more information about traditional and new thermal metrics, see the [Semiconductor and IC Package Thermal Metrics](#) application note.

5.4 Recommended Operating Conditions

over operating free-air temperature range (unless otherwise noted)

		MIN	NOM	MAX	UNIT
$V_{DD} - V_{SS}$ ⁽¹⁾	Power supply voltage differential	5		24	V
V_{DD}	Positive power supply voltage	5		24	V
V_{SS}	Negative power supply voltage	–15		0	V
V_S or V_D	Signal path input/output voltage (source or drain pin) (Sx, D)	V_{SS}		V_{DD}	V
V_{Ax} or V_{EN}	Address or enable pin voltage	0		V_{DD}	V
I_S or $I_D (CONT)$	Source or drain continuous current (Sx, D)	–10		10	mA
T_A	Ambient temperature	–55		125	°C

(1) V_{DD} and V_{SS} can be any value as long as $5V \leq (V_{DD} - V_{SS}) \leq 24V$, and the minimum V_{DD} and V_{SS} are met.

5.5 Electrical Characteristics

Over operating free-air temperature range, Typical at $T_A = 25^\circ\text{C}$ (unless otherwise noted)

PARAMETER	TEST CONDITIONS	V _{DD}	V _{SS}	T _A	MIN	TYP	MAX	UNIT
POWER SUPPLY								
Supply current I _{DD}	Address inputs = 0V, 5V, or V _{DD} EN = 0V	5V	0V	−55°C			60	μA
				25°C	17	60		
				85°C		80		
				125°C		80		
	Address inputs = 0V, 5V, or V _{DD} EN = 0V	10V	0V	−55°C			60	
				25°C	18	60		
				85°C		80		
				125°C		80		
	Address inputs = 0V, 5V, or V _{DD} EN = 0V	24V	0V	−55°C			60	
				25°C	21	60		
				85°C		80		
				125°C		80		
	Address inputs = 0V, 5V, or V _{DD} EN = 0V	5V	−5V	−55°C			60	
				25°C	18	60		
				85°C		80		
				125°C		80		
	Address inputs = 0V, 5V, or V _{DD} EN = 0V	12V	−12V	−55°C			60	
				25°C	20	60		
				85°C		80		
				125°C		80		
Negative supply current I _{SS}	Address inputs = 0V, 5V, or V _{DD} EN = 0V	5V	−5V	−55°C			20	μA
				25°C	6	20		
				85°C		25		
				125°C		25		
	Address inputs = 0V, 5V, or V _{DD} EN = 0V	12V	−12V	−55°C			22	
				25°C	7	22		
				85°C		26		
				125°C		26		
I _{DD} disable	EN = 5V or V _{DD}	All	25°C		8	μA		
			−55°C to 125°C		20			
ANALOG SWITCH								

Over operating free-air temperature range, Typical at $T_A = 25^\circ\text{C}$ (unless otherwise noted)

PARAMETER	TEST CONDITIONS	V _{DD}	V _{SS}	T _A	MIN	TYP	MAX	UNIT
R _{ON} Source to Drain ON-Resistance	V _S = V _{SS} to V _{DD} I _D = −1mA	5V	0V	−55°C			800	Ω
				25°C		75	1050	
				85°C			1200	
				125°C			1300	
	V _S = V _{SS} to V _{DD} I _D = −1mA	10V	0V	−55°C			310	
				25°C		60	400	
				85°C			520	
				125°C			550	
	V _S = V _{SS} to V _{DD} I _D = −1mA	24V	0V	−55°C			200	
				25°C		60	240	
				85°C			300	
				125°C			300	
	V _S = V _{SS} to V _{DD} I _D = −1mA	5V	−5V	−55°C			310	
				25°C		60	400	
				85°C			520	
				125°C			550	
	V _S = V _{SS} to V _{DD} I _D = −1mA	12V	−12V	−55°C			200	
				25°C		60	240	
				85°C			300	
				125°C			300	
ΔR _{ON}	V _S = V _{SS} to V _{DD} I _D = −1mA	All		25°C		2		Ω
R _{ON FLAT}	V _S = V _{SS} to V _{DD} I _D = −1mA	All		25°C		60		Ω
				−55°C to 85°C			150	
				−55°C to 125°C			150	
I _{S(OFF)} I _{D(OFF)}	Switch State is off V _S = V _{SS} / V _{DD} V _D = V _{DD} / V _{SS}	24V	0V	25°C		±0.3	±100	nA
				−55°C to 85°C			±800	
				−55°C to 125°C			±1000	
I _{ON}	Switch State is on V _S = V _D = V _{SS} or V _{DD}	24V	0V	25°C		±0.3	±100	nA
				−55°C to 85°C			±800	
				−55°C to 125°C			±1000	
LOGIC INPUTS (ADDRESS / ENABLE pins)								
V _{IH}	Input High Voltage	All		−55°C to 125°C	1.35		V _{DD}	V
V _{IL}	Input Low Voltage	All		−55°C to 125°C	0		0.8	V
I _{IH} I _{IL} Logic Input Current	V _{LOGIC} = 0V, 5V, or V _{DD}	All		25°C		±0.6		μA
				−55°C to 125°C		−1	1	
C _{IN}		All		25°C		2		pF

5.6 AC Performance Characteristics

Typical at $T_A = 25^\circ\text{C}$ (unless otherwise noted)

PARAMETER	TEST CONDITIONS				T _A = −55°C to 125°C			UNIT
	CONDITION	V _{DD}	V _{SS}	GPN	MIN	TYP	MAX	
CAPACITANCE								
C _{S(OFF)}	V _S = (V _{DD} + V _{SS}) / 2V f = 1MHz	5V	−5V	All	3			pF
		24V	0V		3			
C _{D(OFF)}	V _S = (V _{DD} + V _{SS}) / 2V f = 1MHz	5V	−5V	TMUX4051	11			pF
		24V	0V		9			
		5V	−5V	TMUX4052	6			
		24V	0V		5			
		5V	−5V	TMUX4053	4			
		24V	0V		3			
C _{S(ON)} C _{D(ON)}	V _S = (V _{DD} + V _{SS}) / 2V f = 1MHz	5V	−5V	TMUX4051	13			pF
		24V	0V		11			
		5V	−5V	TMUX4052	8			
		24V	0V		7			
		5V	−5V	TMUX4053	10			
		24V	0V		5			
DYNAMIC CHARACTERISTICS								
Bandwidth (BW) (Sine Wave Input)	V _{BIAS} = (V _{DD} + V _{SS}) / 2V _S = 200mV _{pp} R _L = 50Ω, C _L = 5pF	+5V	−5V	TMUX4051	280			MHz
		24V	0V		430			
		+5V	−5V	TMUX4052	600			
		24V	0V		700			
		+5V	−5V	TMUX4053	750			
		24V	0V		850			
Off Isolation Channel OFF (Sine Wave Input)	V _{BIAS} = (V _{DD} + V _{SS}) / 2V _S = 200mV _{pp} R _L = 50Ω, C _L = 5pF f = 1MHz	+5V	−5V	All	−95			dB
		24V	0V		−95			
Crosstalk (Sine Wave Input)	V _{BIAS} = (V _{DD} + V _{SS}) / 2V _S = 200mV _{pp} R _L = 50Ω, C _L = 5pF f = 1MHz	+5V	−5V	All	−90			dB
		24V	0V		−90			
Charge Injection	V _S = (V _{DD} + V _{SS}) / 2 R _S = 0Ω, C _L = 100pF	+5V	−5V	TMUX4051	6			pC
		24V	0V		2			

5.7 Timing Characteristics

Over operating free-air temperature range, Typical at $T_A = 25^\circ\text{C}$ (unless otherwise noted)

PARAMETER		TEST CONDITIONS				MIN	TYP	MAX	UNIT
		CONDITION	V_{DD}	V_{SS}	T_A				
Prop Delay	Signal Input to Signal Output	$V_S = V_{SS}$ to V_{DD}	5V	0V	25°C		4	20	ns
			10V	0V	25°C		4	20	
			24V	0V	25°C		3	20	
			5V	-5V	25°C		4	20	
			12V	-12V	25°C		3	20	
t_{TRAN}	Address-to-Signal OUT Transition time between inputs	$t_r, t_f = 20\text{ns}$, $C_L = 50\text{pF}$, $R_L = 10\text{k}\Omega$	5V	0V	25°C		105		ns
					-55°C to +125°C			190	
			10V	0V	25°C		100		
					-55°C to +125°C			190	
			24V	0V	25°C		110		
					-55°C to +125°C			230	
			5V	-5V	25°C		100		
					-55°C to +125°C			190	
$t_{ON(EN)}$	Enable-to-Signal OUT Channel turning ON	$t_r, t_f = 20\text{ns}$, $C_L = 50\text{pF}$, $R_L = 10\text{k}\Omega$	5V	0V	25°C		100		ns
					-55°C to +125°C			190	
			10V	0V	25°C		95		
					-55°C to +125°C			190	
			24V	0V	25°C		110		
					-55°C to +125°C			230	
			5V	-5V	25°C		100		
					-55°C to +125°C			190	
$t_{OFF(EN)}$	Enable-to-Signal OUT Channel turning OFF	$t_r, t_f = 20\text{ns}$, $C_L = 50\text{pF}$, $R_L = 10\text{k}\Omega$	5V	0V	25°C		90		ns
					-55°C to +125°C			140	
			10V	0V	25°C		90		
					-55°C to +125°C			140	
			24V	0V	25°C		85		
					-55°C to +125°C			140	
			5V	-5V	25°C		100		
					-55°C to +125°C			160	
			12V	-12V	25°C		90		
					-55°C to +125°C			140	

Over operating free-air temperature range, Typical at $T_A = 25^\circ\text{C}$ (unless otherwise noted)

PARAMETER		TEST CONDITIONS			MIN	TYP	MAX	UNIT
		CONDITION	V_{DD}	V_{SS}				
t_{BBM}		$C_L = 15\text{pF}$, $R_L = 10\text{k}\Omega$	5V	0V	25°C		60	ns
					–55°C to +125°C	1		
			10V	0V	25°C		45	
					–55°C to +125°C	1		
			5V	–5V	25°C		45	
					–55°C to +125°C	1		
			12V	–12V	25°C		55	
					–55°C to +125°C	1		
			24V	0V	25°C		75	
					–55°C to +125°C	1		

6 Parameter Measurement Information

6.1 On-Resistance

The on-resistance of a device is the ohmic resistance between the source (Sx) and drain (D) pins of the device. The on-resistance varies with input voltage and supply voltage. The symbol R_{ON} is used to denote on-resistance. The measurement setup used to measure R_{ON} is shown in the following figure. Figure 6-1 shows how the R_{ON} is computed with $R_{ON} = V / I_{SD}$, and the voltage (V) and current (I_{SD}) are measured using this setup.




Figure 6-1. On-Resistance Measurement Setup

6.2 Off-Leakage Current

There are two types of leakage currents associated with a switch during the off state:

1. Source off-leakage current.
2. Drain off-leakage current.

Source leakage current is defined as the leakage current flowing into or out of the source pin when the switch is off. This current is denoted by the symbol $I_{S(OFF)}$.

Drain leakage current is defined as the leakage current flowing into or out of the drain pin when the switch is off. This current is denoted by the symbol $I_{D(OFF)}$.

Figure 6-2 shows the setup used to measure both off-leakage currents.




Figure 6-2. Off-Leakage Measurement Setup

6.3 On-Leakage Current

Source on-leakage current is defined as the leakage current flowing into or out of the source pin when the switch is on. This current is denoted by the symbol $I_{S(ON)}$.

Drain on-leakage current is defined as the leakage current flowing into or out of the drain pin when the switch is on. This current is denoted by the symbol $I_{D(ON)}$.

Either the source pin or drain pin is left floating during the measurement. Figure 6-3 shows the circuit used for measuring the on-leakage current, denoted by $I_{S(ON)}$ or $I_{D(ON)}$.




Figure 6-3. On-Leakage Measurement Setup

6.4 Transition Time

Transition time is defined as the time taken by the output of the device to rise or fall 10% after the address signal has risen or fallen past the 50% threshold. Figure 6-4 shows the setup used to measure transition time, denoted by the symbol $t_{\text{TRANSITION}}$.




Figure 6-4. Transition-Time Measurement Setup

6.5 Break-Before-Make

Break-before-make delay is a safety feature that prevents two inputs from connecting when the device is switching. The output first breaks from the on-state switch before making the connection with the next on-state switch. The time delay between the *break* and the *make* is known as break-before-make delay. Figure 6-5 shows the setup used to measure break-before-make delay, denoted by the symbol $t_{\text{OPEN(BBM)}}$.




Figure 6-5. Break-Before-Make Delay Measurement Setup

6.6 $t_{\text{ON(EN)}}$ and $t_{\text{OFF(EN)}}$

Turn-on time is defined as the time taken by the output of the device to rise to 10% after the enable has risen past the 50% threshold. The 10% measurement is utilized to provide the timing of the device, system level timing can then account for the time constant added from the load resistance and load capacitance. Figure 6-6 shows the setup used to measure transition time, denoted by the symbol $t_{\text{ON(EN)}}$.

Turn-off time is defined as the time taken by the output of the device to fall to 90% after the enable has fallen past the 50% threshold. The 90% measurement is utilized to provide the timing of the device, system level timing can then account for the time constant added from the load resistance and load capacitance. Figure 6-6 shows the setup used to measure transition time, denoted by the symbol $t_{\text{OFF(EN)}}$.




Figure 6-6. Turn-On and Turn-Off Time Measurement Setup

6.7 Propagation Delay

Propagation delay is defined as the time taken by the output of the device to rise or fall 50% after the input signal has risen or fallen past the 50% threshold. Figure 6-7 shows the setup used to measure propagation delay, denoted by the symbol t_{PD} .




Figure 6-7. Propagation Delay Measurement Setup

6.8 Charge Injection

Any mismatch in capacitance between the NMOS and PMOS transistors results in a charge injected into the drain or source during the falling or rising edge of the gate signal. The amount of charge injected into the source or drain of the device is known as charge injection, and is denoted by the symbol Q_C . Figure 6-8 shows the setup used to measure charge injection from source (Sx) to drain (D).




Figure 6-8. Charge-Injection Measurement Setup

6.9 Off Isolation

Off isolation is defined as the ratio of the signal at the drain pin (D) of the device when a signal is applied to the source pin (S_x) of an off-channel. Figure 6-9 shows the setup used to measure, and the equation to compute off isolation.




Figure 6-9. Off Isolation Measurement Setup

$$\text{Off Isolation} = 20 \times \text{Log} \left(\frac{V_{OUT}}{V_S} \right) \quad (1)$$

6.10 Crosstalk

Crosstalk is defined as the ratio of the signal at the drain pin (D) of a different channel, when a signal is applied at the source pin (S_x) of an on-channel. Figure 6-10 shows the setup used to measure, and the equation used to compute crosstalk.




Figure 6-10. Channel-to-Channel Crosstalk Measurement Setup

$$\text{Channel - to - Channel Crosstalk} = 20 \times \text{Log} \left(\frac{V_{OUT}}{V_S} \right) \quad (2)$$

6.11 Bandwidth

Bandwidth is defined as the range of frequencies that are attenuated by less than 3dB when the input is applied to the source pin (Sx) of an on-channel, and the output is measured at the drain pin (D) of the device. [Figure 6-11](#) shows the setup used to measure bandwidth.




Figure 6-11. Bandwidth Measurement Setup


$$\text{Attenuation} = 20 \times \text{Log} \left(\frac{V_2}{V_1} \right) \quad (3)$$

7 Detailed Description

7.1 Overview

The TMUX4051-EP is an 8:1, single-ended (1-channel) mux, the TMUX4052-EP is a 4:1, differential (2-channel) mux, and the TMUX4053-EP is a 2:1, 3-channel mux. Each channel is turned on or turned off based on the state of the address/select lines and enable pin.

7.2 Functional Block Diagram



7.3 Feature Description

7.3.1 Bidirectional Operation

The TMUX405x-EP device conduct equally well from source (S_x) to drain (D_x) or from drain (D_x) to source (S_x). Each signal path has very similar characteristics in both directions so the signal paths can be used as both multiplexers and demultiplexer to support analog signals.

7.3.2 Rail-to-Rail Operation

The valid signal path input and output voltage for the TMUX405x-EP ranges from V_{SS} to V_{DD} .

7.3.3 1.8V Logic Compatible Inputs

The TMUX405x-EP support 1.8V logic compatible control for all logic control inputs. 1.8V logic level inputs allows the multiplexers to interface with processors that have lower logic I/O rails and eliminates the need for an external voltage translator, which saves both space and BOM cost. For more information on 1.8V logic implementation, refer to [Simplifying Design with 1.8V logic Muxes and Switches](#).

7.3.4 Device Functional Modes

When the $\overline{EN}$ pin of the device is pulled low, one of the switches is closed based on the state of the address or select pins. When the $\overline{EN}$ pin is pulled high, all the switches are in an open state regardless of the state of the address or select pins.

Unused logic control pins must be tied to GND or V_{DD} to be certain that the device does not consume additional current as highlighted in [Implications of Slow or Floating CMOS Inputs](#). Unused signal path inputs (S_x and D_x) must be connected to GND.

7.3.5 Truth Tables

Table 7-1, Table 7-2, and Table 7-3 provides the truth tables.

Table 7-1. TMUX4051-EP Truth Table

EN	A2	A1	A0	Selected Signal Path Connected To Drain (D) Pin
0	0	0	0	S0
0	0	0	1	S1
0	0	1	0	S2
0	0	1	1	S3
0	1	0	0	S4
0	1	0	1	S5
0	1	1	0	S6
0	1	1	1	S7
1	X ⁽¹⁾	X ⁽¹⁾	X ⁽¹⁾	All inputs are unselected (HI-Z)

(1) X denotes *do not care*.

Table 7-2. TMUX4052-EP Truth Table

EN	A1	A0	Selected Signal Path Connected To Drain (DA and DB) Pins
0	0	0	S0A to DA S0B to DB
0	0	1	S1A to DA S1B to DB
0	1	0	S2A to DA S2B to DB
0	1	1	S3A to DA S3B to DB
1	X ⁽¹⁾	X ⁽¹⁾	All inputs are unselected (HI-Z)

(1) X denotes *do not care*.

Table 7-3. TMUX4053-EP Truth Table

EN	SEL1	SEL2	SEL3	Selected Signal Path Connected To Drain Pins
0	0	X	X	S1A to D1
0	1	X	X	S1B to D1
0	X	0	X	S2A to D2
0	X	1	X	S2B to D2
0	X	X	0	S3A to D3
0	X	X	1	S3B to D3
1	X ⁽¹⁾	X ⁽¹⁾	X ⁽¹⁾	All inputs are unselected (HI-Z)

(1) X denotes *do not care*.

The Enable pin, $\overline{\text{EN}}$, of the TMUX405x devices have a weak internal pull-up resistor to put the devices into a disabled state upon power up. The SELx / Address pins (Ax) have weak internal pull-down resistors to put the switch into a defined logic state.

8 Application and Implementation

Note

Information in the following applications sections is not part of the TI component specification, and TI does not warrant its accuracy or completeness. TI's customers are responsible for determining suitability of components for their purposes. Customers should validate and test their design implementation to confirm system functionality.

8.1 Application Information

The TMUX405x-EP offers good system performance across a wide operating supply (5V to 24V, $\pm 12V$). These devices include 1.8V logic compatible control input pins that enable operation in systems with 1.8V I/Os. These features make the TMUX405x-EP multiplexer an good design for many systems as these features can reduce system complexity, board size, and overall system cost.

8.2 Typical Application

One useful application to take advantage of the TMUX405x-EP features is multiplexing various signals into an ADC that is integrated into an MCU. Utilizing an integrated ADC in an MCU allows a system to minimize cost with a potential tradeoff of system performance when compared to an external ADC. The multiplexer allows for multiple inputs or sensors to be monitored with a single ADC pin of the device, which is critical in systems with limited I/Os.




Figure 8-1. Multiplexing Signals to an Integrated ADC with TMUX4051-EP

8.3 Design Requirements

Table 8-1 lists the parameters that must be used for this design example.

Table 8-1. Design Parameters

PARAMETERS	VALUES
Supply (V_{DD})	12V
I/O signal range	0V to V_{DD} (rail-to-rail)
Control logic thresholds	1.8V compatible

8.4 Detailed Design Procedure

The TMUX405x-EP can operate without any external components except for the supply decoupling capacitors. The MCU can control the enable and address pins through GPIOs to toggle between various inputs of the multiplexer. The enable ($\overline{EN}$) pin must be connected to power if the functionality is not required in the system. All inputs being muxed to the ADC of the MCU must fall within the *Recommended Operating Conditions*, including signal range and continuous current. For this design with a supply of 12V, the signal range can be 0V to 12V.

8.5 Application Curves




Figure 8-2. Bandwidth

8.6 Power Supply Recommendations

The TMUX405x-EP operates across a wide supply range of 5V to 24V single supply and up to $\pm 12\text{V}$ dual supply.

Power-supply bypassing improves noise margin and prevents switching noise propagation from the supply pins to other components. Good power-supply decoupling is important to achieve optimum performance. For improved supply noise immunity, use a supply decoupling capacitor ranging from $0.1\mu\text{F}$ to $10\mu\text{F}$ from V_{DD} to ground and V_{SS} to ground. Place the bypass capacitors as close to the power supply pins of the device as possible using low-impedance connections. TI recommends using multi-layer ceramic chip capacitors (MLCCs) that offer low equivalent series resistance (ESR) and inductance (ESL) characteristics for power-supply decoupling purposes. For very sensitive systems or systems in harsh noise environments, avoiding the use of vias for connecting the capacitors to the device pins can offer superior noise immunity. The use of multiple vias in parallel lowers the overall inductance and is beneficial for connections to ground planes.

8.7 Layout

8.7.1 Layout Guidelines

Route high-speed signals using minimal vias and corners, which reduces signal reflections and impedance changes. When a via must be used, increase the clearance size around the via to minimize the capacitance. Each via introduces discontinuities in the transmission line of the signal and increases the chance of picking up interference from the other layers of the board. Be careful when designing test points, through-hole pins are not recommended at high frequencies.

- Decouple the V_{DD} and V_{SS} pins with a 0.1 μF capacitor, placed as close to the pin as possible. Verify that the capacitor voltage rating is sufficient.
- Keep the input lines as short as possible.
- Use a solid ground plane to help reduce electromagnetic interference (EMI) noise pickup.
- Do not run sensitive analog traces in parallel with digital traces. Avoid crossing digital and analog traces if possible, and only make perpendicular crossings when necessary.

8.7.2 Layout Example




Figure 8-3. Layout Example

9 Device and Documentation Support

9.1 Documentation Support

9.1.1 Related Documentation

For related documentation, see the following:

- Texas Instruments, [Simplifying Design with 1.8V logic Muxes and Switches](#) application brief
- Texas Instruments, [QFN/SON PCB Attachment](#) application report
- Texas Instruments, [Quad Flatpack No-Lead Logic Packages](#) application report

9.2 Receiving Notification of Documentation Updates

To receive notification of documentation updates, navigate to the device product folder on [ti.com](https://www.ti.com). Click on *Notifications* to register and receive a weekly digest of any product information that has changed. For change details, review the revision history included in any revised document.

9.3 Support Resources

TI E2E™ support forums are an engineer's go-to source for fast, verified answers and design help — straight from the experts. Search existing answers or ask your own question to get the quick design help you need.

Linked content is provided "AS IS" by the respective contributors. They do not constitute TI specifications and do not necessarily reflect TI's views; see TI's [Terms of Use](#).

9.4 Trademarks

TI E2E™ is a trademark of Texas Instruments.

All trademarks are the property of their respective owners.

9.5 Electrostatic Discharge Caution



This integrated circuit can be damaged by ESD. Texas Instruments recommends that all integrated circuits be handled with appropriate precautions. Failure to observe proper handling and installation procedures can cause damage.

ESD damage can range from subtle performance degradation to complete device failure. Precision integrated circuits may be more susceptible to damage because very small parametric changes could cause the device not to meet its published specifications.

9.6 Glossary

[TI Glossary](#) This glossary lists and explains terms, acronyms, and definitions.

10 Revision History

NOTE: Page numbers for previous revisions may differ from page numbers in the current version.

DATE	REVISION	NOTES
October 2026	*	Initial Release

11 Mechanical, Packaging, and Orderable Information

The following pages include mechanical, packaging, and orderable information. This information is the most current data available for the designated devices. This data is subject to change without notice and revision of this document. For browser-based versions of this data sheet, refer to the left-hand navigation.

PACKAGING INFORMATION

Orderable part number	Status (1)	Material type (2)	Package Pins	Package qty Carrier	RoHS (3)	Lead finish/ Ball material (4)	MSL rating/ Peak reflow (5)	Op temp (°C)	Part marking (6)
TMUX4051MDYYREP	Active	Production	null (null)	3000 LARGE T&R	Yes	NIPDAU	Level-2-260C-1 YEAR	-55 to 125	TMUX4051EP

- (1) **Status:** For more details on status, see our [product life cycle](#).
- (2) **Material type:** When designated, preproduction parts are prototypes/experimental devices, and are not yet approved or released for full production. Testing and final process, including without limitation quality assurance, reliability performance testing, and/or process qualification, may not yet be complete, and this item is subject to further changes or possible discontinuation. If available for ordering, purchases will be subject to an additional waiver at checkout, and are intended for early internal evaluation purposes only. These items are sold without warranties of any kind.
- (3) **RoHS values:** Yes, No, RoHS Exempt. See the [TI RoHS Statement](#) for additional information and value definition.
- (4) **Lead finish/Ball material:** Parts may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead finish/Ball material values may wrap to two lines if the finish value exceeds the maximum column width.
- (5) **MSL rating/Peak reflow:** The moisture sensitivity level ratings and peak solder (reflow) temperatures. In the event that a part has multiple moisture sensitivity ratings, only the lowest level per JEDEC standards is shown. Refer to the shipping label for the actual reflow temperature that will be used to mount the part to the printed circuit board.
- (6) **Part marking:** There may be an additional marking, which relates to the logo, the lot trace code information, or the environmental category of the part.

Multiple part markings will be inside parentheses. Only one part marking contained in parentheses and separated by a "-" will appear on a part. If a line is indented then it is a continuation of the previous line and the two combined represent the entire part marking for that device.

Important Information and Disclaimer:The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.

IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATASHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, regulatory or other requirements.

These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you fully indemnify TI and its representatives against any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to [TI's Terms of Sale](#), [TI's General Quality Guidelines](#), or other applicable terms available either on [ti.com](https://www.ti.com) or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products. Unless TI explicitly designates a product as custom or customer-specified, TI products are standard, catalog, general purpose devices.

TI objects to and rejects any additional or different terms you may propose.

Copyright © 2026, Texas Instruments Incorporated

Last updated 10/2025