

Sample &

Buy



TPS562209, TPS563209

SLVSCM5A-SEPTEMBER 2014-REVISED NOVEMBER 2016

TPS56x209, 4.5V to 17 V Input, 2-A, 3-A Synchronous Step-Down Voltage Regulator in 6 pin SOT-23

Technical

Documents

Features 1

- TPS562209 2A converter with integrated 122-m Ω and 72-m Ω FETs
- TPS563209 3A converter with integrated 68-mΩ and 39-mΩ FETs
- D-CAP2[™] Mode Control for Fast Transient Response
- Input Voltage Range: 4.5 V to 17 V
- Output Voltage Range: 0.76 V to 7 V
- 650 kHz Switching Frequency
- Low Shutdown Current Less than 10µA
- 1% Feedback Voltage Accuracy (25°C)
- Startup from Pre-Biased Output Voltage
- Cycle By Cycle Over-current Limit
- Hiccup-mode Under Voltage Protection
- Non-latch OVP, UVLO and TSD Protections
- Fixed Soft Start : 1.0ms

2 Applications

- **Digital TV Power Supply**
- High Definition Blu-ray Disc[™] Players
- Networking Home Terminal
- Digital Set Top Box (STB)

3 Description

Tools &

Software

The TPS562209 and TPS563209 are simple, easy-touse, 2-A and 3-A synchronous step-down converters in 6 pin SOT-23 package.

Support &

Community

2.2

The devices are optimized to operate with minimum external component counts and also optimized to achieve low standby current.


These switch mode power supply (SMPS) devices employ D-CAP2™ mode control providing a fast transient response and supporting both low equivalent series resistance (ESR) output capacitors such as specialty polymer and ultra-low ESR ceramic capacitors with no external compensation components.

TPS562209 and TPS563209 always operate in continuous conduction mode, which reduces the output ripple voltage in light load compared to discontinous conduction mode. TPS56x209 are available in a 6-pin 1.6 \times 2.9(mm) SOT (DDC) package, and specified from -40°C to 150°C of junction temperature.

Device Information⁽¹⁾

PART NUMBER	PACKAGE	BODY SIZE (NOM)
TPS563209, TPS562209	SOT (6)	1.60 mm × 2.90 mm

(1) For all available packages, see the orderable addendum at the end of the datasheet.



Transient Response




Table of Cont

6.2ESD Ratings46.3Recommended Operating Conditions46.4Thermal Information46.5Electrical Characteristics56.6Typical Characteristics TPS5622096	1	Features 1						
4 Revision History	2	Applications 1						
5Pin Configuration and Functions36Specifications46.1Absolute Maximum Ratings46.2ESD Ratings46.3Recommended Operating Conditions46.4Thermal Information46.5Electrical Characteristics56.6Typical Characteristics TPS5622096	3	Des	cription 1					
6 Specifications	4	Rev	ision History 2					
6.1Absolute Maximum Ratings46.2ESD Ratings46.3Recommended Operating Conditions46.4Thermal Information46.5Electrical Characteristics56.6Typical Characteristics TPS5622096	5	Pin	Configuration and Functions 3					
6.2ESD Ratings46.3Recommended Operating Conditions46.4Thermal Information46.5Electrical Characteristics56.6Typical Characteristics TPS5622096	6	Spe	cifications 4					
6.3Recommended Operating Conditions46.4Thermal Information46.5Electrical Characteristics56.6Typical Characteristics TPS5622096		6.1	Absolute Maximum Ratings 4					
6.4Thermal Information46.5Electrical Characteristics56.6Typical Characteristics TPS5622096		6.2	ESD Ratings 4					
6.5Electrical Characteristics56.6Typical Characteristics TPS5622096		6.3	Recommended Operating Conditions 4					
6.6 Typical Characteristics TPS562209 6		6.4	Thermal Information 4					
		6.5	Electrical Characteristics 5					
6.7 Typical Characteristics TPS5632098		6.6	Typical Characteristics TPS562209 6					
· · · · · · · · · · · · · · · · · · ·		6.7	Typical Characteristics TPS5632098					
7 Detailed Description 10	7	Deta	ailed Description 10					
7.1 Overview 10		7.1	Overview 10					
7.2 Functional Block Diagram 10		7.2	Functional Block Diagram 10					
7.3 Feature Description 11		7.3	Feature Description 11					

4	Revision	History
---	----------	---------

CI	Changes from Original (September 2014) to Revision A				
•	Updated the Pinout image in Pin Configuration and Functions	3			
•	Changed the "Handling Ratings" table to the ESD Ratings table	4			
•	Changed R _{0JB} for TPS562209 From: 57.3 To: 13.4 in Thermal Information	4			
•	The Adaptive On-Time Control and PWM Operation, changed text From: "proportional to the converter input voltage, V_{IN} , and inversely proportional to the output voltage, V_O " To: "inversely proportional to the converter input voltage, V_{IN} , and proportional to the output voltage, V_O "	11			

ter	nts	
	7.4	Device Functional Modes 12
8	App	lication and Implementation 13
	8.1	Application Information 13
	8.2	Typical Applications 13
9	Pow	er Supply Recommendations
10	Lay	out
	10.1	Layout Guidelines 21
	10.2	Layout Example 21
11	Dev	ice and Documentation Support
	11.1	Related Links 22
	11.2	Receiving Notification of Documentation Updates 22
	11.3	Community Resources 22
	11.4	Trademarks 22
	11.5	Electrostatic Discharge Caution 22
	11.6	Glossary 22
12	Mec	hanical, Packaging, and Orderable
		mation


EXAS INSTRUMENTS

www.ti.com

2



5 Pin Configuration and Functions



Pin Functions

PIN DESCRIPTION		DESCRIPTION			
NAME	NO.	DESCRIPTION			
GND	1	round pin Source terminal of low-side power NFET as well as the ground terminal for controller circuit. Connect ensitive VFB to this GND at a single point.			
SW	2	Switch node connection between high-side NFET and low-side NFET.			
VIN	3	nput voltage supply pin. The drain terminal of high-side power NFET.			
VFB	4	onverter feedback input. Connect to output voltage with feedback resistor divider.			
EN	5	nable input control. Active high and must be pulled up to enable the device.			
VBST	6	Supply input for the high-side NFET gate drive circuit. Connect 0.1 µF capacitor between VBST and SW pins.			

TPS562209, TPS563209

SLVSCM5A-SEPTEMBER 2014-REVISED NOVEMBER 2016

6 Specifications

6.1 Absolute Maximum Ratings

 $T_J = -40^{\circ}C$ to 150°C (unless otherwise noted) ⁽¹⁾

		N	IIN	MAX	UNIT
	VIN, EN	-	0.3	19	V
	VBST	-	0.3	25	V
	VBST (10 ns transient)	-	0.3	27.5	V
Input voltage range	VBST (vs SW)	-	0.3	6.5	V
	VFB,	-	0.3	6.5	V
	SW	-	-2	19	V
	SW (10 ns transient)		3.5	21	V
Operating junction ten	nperature, T _J	-	40	150	°C
Storage temperature, T _{stg} -55		150	°C		

(1) Stresses beyond those listed under Absolute Maximum Ratings may cause permanent damage to the device. These are stress ratings only, which do not imply functional operation of the device at these or any other conditions beyond those indicated under Recommended Operating Conditions. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability.

6.2 ESD Ratings

			MIN	MAX	UNIT
V	Electrostatic discharge	Human body model (HBM), per ANSI/ESDA/JEDEC JS-001, all pins ⁽¹⁾		2	kV
V _(ESD)		Charged device model (CDM), per JEDEC specification JESD22-C101, all pins $^{\rm (2)}$		500	V

(1) JEDEC document JEP155 states that 500-V HBM allows safe manufacturing with a standard ESD control process.

(2) JEDEC document JEP157 states that 250-V CDM allows safe manufacturing with a standard ESD control process.

6.3 Recommended Operating Conditions

 $T_J = -40^{\circ}C$ to 150°C (unless otherwise noted)

			MIN	MAX	UNIT
V _{IN}	Supply input voltage	range	4.5	17	V
		VBST	-0.1	23	
		VBST (10 ns transient)	-0.1	26	
		VBST(vs SW)	-0.1	6.0	
VI	Input voltage range	EN	-0.1	17	V
		VFB	-0.1	5.5	
		SW	-1.8	17	
		SW (10 ns transient)	-3.5	20	
T _A	Operating free-air temperature		-40	85	°C

6.4 Thermal Information

	THERMAL METRIC ⁽¹⁾	TPS562209	TPS563209	
		DDC (6	UNIT	
$R_{\theta JA}$	Junction-to-ambient thermal resistance	109.2	87.9	
R _{0JC(top)}	Junction-to-case (top) thermal resistance	44.5	42.2	
$R_{\theta JB}$	Junction-to-board thermal resistance	13.4	13.6	°C/W
ΨJT	Junction-to-top characterization parameter	2.3	1.9	
ΨЈВ	Junction-to-board characterization parameter	60.4	13.3	

(1) For more information about traditional and new thermal metrics, see the IC Package Thermal Metrics application report, SPRA953.

www.ti.com



6.5 Electrical Characteristics

 $T_J = -40^{\circ}C$ to 150°C, VIN = 12V (unless otherwise noted)

	PARAMETER	TEST CONDITIONS	MIN	TYP	MAX	UNIT
SUPPLY	CURRENT					
I _{VIN}	Operating – non-switching supply current	V_{IN} current, $T_A = 25^{\circ}C$, EN = 5V, VFB = 0.8 V		650	900 -	μA μA
IVINSDN	Shutdown supply current	V_{IN} current, $T_A = 25^{\circ}C$, EN = 0 V		3.0	10	μΑ
-	HRESHOLD					•
V _{ENH}	EN high-level input voltage	EN	1.6			V
V _{ENL}	EN low-level input voltage	EN			0.6	V
R _{EN}	EN pin resistance to GND	V _{EN} = 12 V	225	450	900	kΩ
	AGE AND DISCHARGE RESISTANCE	11				
V _{FBTH}	V _{FB} threshold voltage	$T_A = 25^{\circ}C$, $V_O = 1.05$ V, continuous mode operation	758	765	772	mV
I _{VFB}	V _{FB} input current	$V_{FB} = 0.8V, T_A = 25^{\circ}C$		0	±0.1	mA
MOSFET						
		T _A = 25°C, V _{BST} – SW = 5.5 V (TPS562209)		122		
R _{DS(on)h}	High side switch resistance	T _A = 25°C, V _{BST} – SW = 5.5 V (TPS563209)		68		mΩ
D		T _A = 25°C (TPS562209)		72		
R _{DS(on)I}	Low side switch resistance	T _A = 25°C (TPS563209)	39			mΩ
CURREN	TLIMIT					
	Current limit ⁽¹⁾	DC current, VOUT = $1.05V$, L1 = $2.2 \mu H$	2.5	3.2	4.3	٨
l _{ocl}	Current limit "	DC current, VOUT = $1.05V$, L1 = 1.5μ H	3.5	4.2	5.3	A
THERMA	L SHUTDOWN					
-	Thermol shutdown threshold ⁽¹⁾	Shutdown temperature		155		°C
T _{SDN}	Thermal shutdown threshold ⁽¹⁾	Hysteresis		35		
ON-TIME	TIMER CONTROL					
t _{ON}	On time	VIN = 12 V, VO = 1.05 V		150		ns
t _{OFF(MIN)}	Minimum off time	$T_A = 25^{\circ}C, V_{FB} = 0.5 V$		260	310	ns
SOFT ST	ART					
T _{ss}	Soft -start time	Internal soft-start time, $T_A = 25^{\circ}C$	0.7	1.0	1.3	ms
OUTPUT	UNDERVOLTAGE AND OVERVOLTAGE P	ROTECTION				
V _{OVP}	Output OVP threshold	OVP Detect		125%x Vfbth		
V _{UVP}	Output UVP threshold	Hiccup detect		65%xVf bth		
T _{HiccupOn}	Hiccup Power On Time	Relative to soft start time		1		ms
T _{HiccupOff}	Hiccup Power Off Time	Relative to soft start time		7		ms
UVLO						
UVLO	UVLO threshold	Wake up VIN voltage	3.45	3.75	4.05	5 V
UVLU		Hysteresis VIN voltage	0.13	0.32	0.55	v

(1) Not production tested.

TPS562209, TPS563209


SLVSCM5A-SEPTEMBER 2014-REVISED NOVEMBER 2016

Texas Instruments

www.ti.com

6.6 Typical Characteristics TPS562209

V_{IN} = 12V (unless otherwise noted)






TPS562209, TPS563209 SLVSCM5A – SEPTEMBER 2014 – REVISED NOVEMBER 2016

www.ti.com

Typical Characteristics TPS562209 (continued)

V_{IN} = 12V (unless otherwise noted)



TPS562209, TPS563209


SLVSCM5A-SEPTEMBER 2014-REVISED NOVEMBER 2016

Texas Instruments

www.ti.com

6.7 Typical Characteristics TPS563209

 $V_{IN} = 12V$ (unless otherwise noted)






TPS562209, TPS563209 SLVSCM5A – SEPTEMBER 2014 – REVISED NOVEMBER 2016

www.ti.com

Typical Characteristics TPS563209 (continued)

 $V_{IN} = 12V$ (unless otherwise noted)






7 Detailed Description

7.1 Overview

The TPS562209 and TPS563209 are 2-A and 3-A synchronous step-down converters, respectively. The proprietary D-CAP2[™] mode control supports low ESR output capacitors such as specialty polymer capacitors and multi-layer ceramic capacitors without complex external compensation circuits. The fast transient response of D-CAP2[™] mode control can reduce the output capacitance required to meet a specific level of performance.

7.2 Functional Block Diagram



Copyright © 2016, Texas Instruments Incorporated

Figure 19. TPS56x209



TPS562209, TPS563209 SLVSCM5A-SEPTEMBER 2014-REVISED NOVEMBER 2016

7.3 Feature Description

7.3.1 The Adaptive On-Time Control and PWM Operation

The main control loop of the TPS56x209 are adaptive on-time pulse width modulation (PWM) controller that supports a proprietary D-CAP2[™] mode control. The D-CAP2[™] mode control combines adaptive on-time control with an internal compensation circuit for pseudo-fixed frequency and low external component count configuration with both low ESR and ceramic output capacitors. It is stable even with virtually no ripple at the output.

At the beginning of each cycle, the high-side MOSFET is turned on. This MOSFET is turned off after internal one shot timer expires. This one shot duration is set inversely proportional to the converter input voltage, V_{IN}, and proportional to the output voltage, V_O, to maintain a pseudo-fixed frequency over the input voltage range, hence it is called adaptive on-time control. The one-shot timer is reset and the high-side MOSFET is turned on again when the feedback voltage falls below the reference voltage. An internal ramp is added to reference voltage to simulate output ripple, eliminating the need for ESR induced output ripple from D-CAP2[™] mode control.

7.3.2 Soft Start and Pre-Biased Soft Start

The TPS562209 and TPS563209 have an internal 1.0ms soft-start. When the EN pin becomes high, the internal soft-start function begins ramping up the reference voltage to the PWM comparator.

If the output capacitor is pre-biased at startup, the devices initiate switching and start ramping up only after the internal reference voltage becomes greater than the feedback voltage V_{FB} . This scheme ensures that the converters ramp up smoothly into regulation point.

7.3.3 Current Protection

The output over-current limit (OCL) is implemented using a cycle-by-cycle valley detect control circuit. The switch current is monitored during the OFF state by measuring the low-side FET drain to source voltage. This voltage is proportional to the switch current. To improve accuracy, the voltage sensing is temperature compensated. During the on time of the high-side FET switch, the switch current increases at a linear rate determined by Vin, Vout, the on-time and the output inductor value.

During the on time of the low-side FET switch, this current decreases linearly. The average value of the switch current is the load current lout. If the monitored current is above the OCL level, the converter maintains low-side FET on and delays the creation of a new set pulse, even the voltage feedback loop requires one, until the current level becomes OCL level or lower. In subsequent switching cycles, the on-time is set to a fixed value and the current is monitored in the same manner. If the over current condition exists consecutive switching cycles, the internal OCL threshold is set to a lower level, reducing the available output current. When a switching cycle occurs where the switch current is not above the lower OCL threshold, the counter is reset and the OCL threshold is returned to the higher value.

There are some important considerations for this type of over-current protection. The load current is higher than the over-current threshold by one half of the peak-to-peak inductor ripple current. Also, when the current is being limited, the output voltage tends to fall as the demanded load current may be higher than the current available from the converter. This may cause the output voltage to fall. When the VFB voltage falls below the UVP threshold voltage, the UVP comparator detects it. And then, the device will shut down after the UVP delay time (typically 14µs) and re-start after the hiccup time (typically 12ms).

When the over current condition is removed, the output voltage returns to the regulated value.

7.3.4 Over Voltage Protection

TPS562209 and TPS563209 detect over voltage condition by monitoring the feedback voltage (VFB). When the feedback voltage becomes higher than 125% of the target voltage, the OVP comparator output goes high and both the high-side MOSFET and the low-side MOSFET turn off. This function is non-latch operation.

7.3.5 UVLO Protection

Under voltage lock out protection (UVLO) monitors the device input voltage. When the voltage is lower than UVLO threshold voltage, the device is shut off. This protection is non-latching.

Copyright © 2014–2016, Texas Instruments Incorporated



Feature Description (continued)

7.3.6 Thermal Shutdown

The device monitors the temperature of itself. If the temperature exceeds the threshold value (typically 155°C), the device is shut off. This is a non-latch protection.

7.4 Device Functional Modes

7.4.1 Normal Operation

When the input voltage is above the UVLO threshold and the EN voltage is above the enable threshold, the TPS562209 and TPS563209 can operate in their normal switching modes. Normal continuous conduction mode (CCM) occurs when the minimum switch current is above 0 A. In CCM, the TPS562209 and TPS563209 operate at a quasi-fixed frequency of 650 kHz.

7.4.2 Forced CCM Operation

When the TPS562209 and TPS563209 are in the normal CCM operating mode and the switch current falls below 0 A, the TPS562209 and TPS563209 begin operating in forced CCM.

7.4.3 Standby Operation

When the TPS562209 and TPS563209 are operating in either normal CCM or forced CCM, they may be placed in standby by asserting the EN pin low.



8 Application and Implementation

NOTE


Information in the following applications sections is not part of the TI component specification, and TI does not warrant its accuracy or completeness. TI's customers are responsible for determining suitability of components for their purposes. Customers should validate and test their design implementation to confirm system functionality.

8.1 Application Information

The TPS562209 and TPS563209 are typically used as step down converters, which convert a voltage from 4.5V - 17V to a lower voltage. Webench software is available to aid in the design and analysis of circuits

8.2 Typical Applications

8.2.1 TPS562209 4.5-V to 17-V Input, 1.05-V Output Converter



Copyright © 2016, Texas Instruments Incorporated

Figure 20. TPS562209 1.05V/2A Reference Design

8.2.1.1 Design Requirements

To begin the design process, you must know a few application parameters:

Table 1. Design Parameters

PARAMETER	VALUE
Input voltage range	4.5 V to 17 V
Output voltage	1.05 V
Output current	2 A
Output voltage ripple	20 mVpp

8.2.1.2 Detailed Design Procedure

8.2.1.2.1 Output Voltage Resistors Selection

The output voltage is set with a resistor divider from the output node to the VFB pin. It is recommended to use 1% tolerance or better divider resistors. Start by using Equation 1 to calculate V_{OUT}.

To improve efficiency at very light loads consider using larger value resistors, too high of resistance will be more susceptible to noise and voltage errors from the VFB input current will be more noticeable.

$$V_{OUT} = 0.765 \times \left(1 + \frac{R2}{R3}\right)$$

8.2.1.2.2 Output Filter Selection

The LC filter used as the output filter has double pole at:

$$F_{P} = \frac{1}{2\pi \sqrt{L_{OUT} \times C_{OUT}}}$$

(2)

(1)

TEXAS INSTRUMENTS

TPS562209, TPS563209 SLVSCM5A-SEPTEMBER 2014-REVISED NOVEMBER 2016

www.ti.com

At low frequencies, the overall loop gain is set by the output set-point resistor divider network and the internal gain of the device. The low frequency phase is 180 degrees. At the output filter pole frequency, the gain rolls off at a -40 dB per decade rate and the phase drops rapidly. D-CAP2TM introduces a high frequency zero that reduces the gain roll off to -20 dB per decade and increases the phase to 90 degrees one decade above the zero frequency. The inductor and capacitor for the output filter must be selected so that the double pole of Equation 2 is located below the high frequency zero but close enough that the phase boost provided be the high frequency zero provides adequate phase margin for a stable circuit. To meet this requirement use the values recommended in Table 2.

OUTPUT	R2	R3				
VOLTAGE (V)	(kΩ)	(kΩ)	MIN	ТҮР	MAX	C5 + C6 (µF)
1	3.09	10.0	1.5	2.2	4.7	20 - 68
1.05	3.74	10.0	1.5	2.2	4.7	20 - 68
1.2	5.76	10.0	1.5	2.2	4.7	20 - 68
1.5	9.53	10.0	1.5	2.2	4.7	20 - 68
1.8	13.7	10.0	1.5	2.2	4.7	20 - 68
2.5	22.6	10.0	2.2	3.3	4.7	20 - 68
3.3	33.2	10.0	2.2	3.3	4.7	20 - 68
5	54.9	10.0	3.3	4.7	4.7	20 - 68
6.5	75	10.0	3.3	4.7	4.7	20 - 68

Table 2. Recommended Component Values

The inductor peak-to-peak ripple current, peak current and RMS current are calculated using Equation 3, Equation 4 and Equation 5. The inductor saturation current rating must be greater than the calculated peak current and the RMS or heating current rating must be greater than the calculated RMS current.

Use 650 kHz for f_{SW} . Make sure the chosen inductor is rated for the peak current of Equation 4 and the RMS current of Equation 5.

$$Il_{P-P} = \frac{V_{OUT}}{V_{IN(MAX)}} \times \frac{V_{IN(MAX)} - V_{OUT}}{L_O \times f_{SW}}$$
(3)

$$Il_{PEAK} = I_O + \frac{Il_{P-P}}{2}$$
(4)

$$I_{I_O(PMS)} = \sqrt{I_O^2 + \frac{1}{2} Il_{P-P}^2}$$

$$V = 12^{-1}$$
 (5)
or this design example, the calculated neak current is 2.34 A and the calculated PMS current is 2.01 A. The

For this design example, the calculated peak current is 2.34 A and the calculated RMS current is 2.01 A. The inductor used is a TDK CLF7045T-2R2N with a peak current rating of 5.5-A and an RMS current rating of 4.3-A

The capacitor value and ESR determines the amount of output voltage ripple. The TPS562209 is intended for use with ceramic or other low ESR capacitors. Recommended values range from 20μ F to 68μ F. Use Equation 6 to determine the required RMS current rating for the output capacitor.

$$I_{CO(RMS)} = \frac{V_{OUT} \times (V_{IN} - V_{OUT})}{\sqrt{12} \times V_{IN} \times L_O \times f_{SW}}$$
(6)

For this design two TDK C3216X5R0J226M 22 μ F output capacitors are used. The typical ESR is 2 m Ω each. The calculated RMS current is 0.199A and each output capacitor is rated for 4A.

8.2.1.2.3 Input Capacitor Selection

The TPS562209 and TPS563209 require an input decoupling capacitor and a bulk capacitor is needed depending on the application. A ceramic capacitor over 10 μ F is recommended for the decoupling capacitor. An additional 0.1 μ F capacitor (C3) from pin 3 to ground is optional to provide additional high frequency filtering. The capacitor voltage rating needs to be greater than the maximum input voltage.


14 Submit Documentation Feedback



8.2.1.2.4 Bootstrap Capacitor Selection

A 0.1µF ceramic capacitor must be connected between the VBST to SW pin for proper operation. It is recommended to use a ceramic capacitor.

8.2.1.3 Application Curves






TPS562209, TPS563209


SLVSCM5A-SEPTEMBER 2014-REVISED NOVEMBER 2016

www.ti.com





8.2.2 TPS563209 4.5-V to 17-V Input, 1.05-V Output Converter



Copyright © 2016, Texas Instruments Incorporated

Figure 33. TPS563209 1.05V/3A Reference Design

8.2.2.1 Design Requirements

To begin the design process, the user must know a few application parameters:

Table 3. Design Parameters

PARAMETER	VALUE
Input voltage range	4.5 V to 17 V
Output voltage	1.05 V
Output current	3 A
Output voltage ripple	20 mVpp

8.2.2.2 Detailed Design Procedures

The detailed design procedure for TPS563209 is the same as for TPS562209 except for inductor selection.

8.2.2.2.1 Output Filter Selection

OUTPUT	R2	R3		C5 +C6 + C7		
VOLTAGE (V)		(kΩ)	MIN	ТҮР	MAX	(μF)
1	3.09	10.0	1.0	1.5	4.7	20 - 68
1.05	3.74	10.0	1.0	1.5	4.7	20 - 68
1.2	5.76	10.0	1.0	1.5	4.7	20 - 68
1.5	9.53	10.0	1.0	1.5	4.7	20 - 68
1.8	13.7	10.0	1.5	2.2	4.7	20 - 68
2.5	22.6	10.0	1.5	2.2	4.7	20 - 68
3.3	33.2	10.0	1.5	2.2	4.7	20 - 68
5	54.9	10.0	2.2	3.3	4.7	20 - 68
6.5	75	10.0	2.2	3.3	4.7	20 - 68


Table 4. Recommended Component Values

The inductor peak-to-peak ripple current, peak current and RMS current are calculated using Equation 7, Equation 8 and Equation 9. The inductor saturation current rating must be greater than the calculated peak current and the RMS or heating current rating must be greater than the calculated RMS current. Use 650 kHz for f_{SW} .

Use 650 kHz for f_{SW} . Make sure the chosen inductor is rated for the peak current of Equation 8 and the RMS current of Equation 9.


$$Il_{P-P} = \frac{V_{OUT}}{V_{IN(MAX)}} \times \frac{V_{IN(MAX)} - V_{OUT}}{L_O \times f_{SW}}$$

$$Il_{PEAK} = I_O + \frac{Il_{P-P}}{2}$$
(8)



 $I_{CO(RMS)} = \frac{V_{OUT} \times (V_{IN} - V_{OUT})}{\sqrt{12} \times V_{IN} \times L_0 \times f_{SW}}$

For this design three TDK C3216X5R0J226M 22 μ F output capacitors are used. The typical ESR is 2 m Ω each. The calculated RMS current is 0.292A and each output capacitor is rated for 4A.




8.2.2.3 Application Curves

(9)

(10)


www.ti.com



EXAS **ISTRUMENTS**




SLVSCM5A-SEPTEMBER 2014-REVISED NOVEMBER 2016





TPS562209, TPS563209

SLVSCM5A-SEPTEMBER 2014-REVISED NOVEMBER 2016



9 Power Supply Recommendations

The TPS562209 and TPS563209 are designed to operate from input supply voltage in the range of 4.5V to 17V. Buck converters require the input voltage to be higher than the output voltage for proper operation. The maximum recommended operating duty cycle is 65%. Using that criteria, the minimum recommended input voltage is $V_0 / 0.65$.




10 Layout

www.ti.com

10.1 Layout Guidelines

- 1. VIN and GND traces should be as wide as possible to reduce trace impedance. The wide areas are also of advantage from the view point of heat dissipation.
- 2. The input capacitor and output capacitor should be placed as close to the device as possible to minimize trace impedance.
- 3. Provide sufficient vias for the input capacitor and output capacitor.
- 4. Keep the SW trace as physically short and wide as practical to minimize radiated emissions.
- 5. Do not allow switching current to flow under the device.
- 6. A separate VOUT path should be connected to the upper feedback resistor.
- 7. Make a Kelvin connection to the GND pin for the feedback path.
- 8. Voltage feedback loop should be placed away from the high-voltage switching trace, and preferably has ground shield.
- 9. The trace of the VFB node should be as small as possible to avoid noise coupling.
- 10. The GND trace between the output capacitor and the GND pin should be as wide as possible to minimize its trace impedance.



10.2 Layout Example

Figure 46. TPS562209 and TPS563209 Layout

11 Device and Documentation Support

11.1 Related Links

The table below lists quick access links. Categories include technical documents, support and community resources, tools and software, and quick access to sample or buy.

PARTS	PRODUCT FOLDER	SAMPLE & BUY	TECHNICAL DOCUMENTS	TOOLS & SOFTWARE	SUPPORT & COMMUNITY
TPS563209	Click here	Click here	Click here	Click here	Click here
TPS562209	Click here	Click here	Click here	Click here	Click here

Table 5. Related Links

11.2 Receiving Notification of Documentation Updates

To receive notification of documentation updates, navigate to the device product folder on ti.com. In the upper right corner, click on *Alert me* to register and receive a weekly digest of any product information that has changed. For change details, review the revision history included in any revised document.

11.3 Community Resources

The following links connect to TI community resources. Linked contents are provided "AS IS" by the respective contributors. They do not constitute TI specifications and do not necessarily reflect TI's views; see TI's Terms of Use.

TI E2E[™] Online Community *TI's Engineer-to-Engineer (E2E) Community.* Created to foster collaboration among engineers. At e2e.ti.com, you can ask questions, share knowledge, explore ideas and help solve problems with fellow engineers.

Design Support TI's Design Support Quickly find helpful E2E forums along with design support tools and contact information for technical support.

11.4 Trademarks

D-CAP2, E2E are trademarks of Texas Instruments. Blu-ray Disc is a trademark of Blu-ray Disc Association.

11.5 Electrostatic Discharge Caution



These devices have limited built-in ESD protection. The leads should be shorted together or the device placed in conductive foam during storage or handling to prevent electrostatic damage to the MOS gates.

11.6 Glossary

SLYZ022 — TI Glossary.

This glossary lists and explains terms, acronyms, and definitions.

12 Mechanical, Packaging, and Orderable Information

The following pages include mechanical, packaging, and orderable information. This information is the most current data available for the designated devices. This data is subject to change without notice and revision of this document. For browser-based versions of this data sheet, refer to the left-hand navigation.

Copyright © 2014–2016, Texas Instruments Incorporated





PACKAGING INFORMATION

Orderable Device	Status	Package Type	•	Pins	•	Eco Plan	Lead finish/	MSL Peak Temp	Op Temp (°C)	Device Marking	Samples
	(1)		Drawing		Qty	(2)	Ball material	(3)		(4/5)	
							(6)				
TPS562209DDCR	ACTIVE	SOT-23-THIN	DDC	6	3000	RoHS & Green	Call TI SN	Level-1-260C-UNLIM	-40 to 125	209	Samples
TPS562209DDCT	ACTIVE	SOT-23-THIN	DDC	6	250	RoHS & Green	Call TI SN	Level-1-260C-UNLIM	-40 to 125	209	Samples
TPS563209DDCR	ACTIVE	SOT-23-THIN	DDC	6	3000	RoHS & Green	SN	Level-1-260C-UNLIM	-40 to 125	309	Samples
TPS563209DDCT	ACTIVE	SOT-23-THIN	DDC	6	250	RoHS & Green	SN	Level-1-260C-UNLIM	-40 to 125	309	Samples

⁽¹⁾ The marketing status values are defined as follows:

ACTIVE: Product device recommended for new designs.

LIFEBUY: TI has announced that the device will be discontinued, and a lifetime-buy period is in effect.

NRND: Not recommended for new designs. Device is in production to support existing customers, but TI does not recommend using this part in a new design.

PREVIEW: Device has been announced but is not in production. Samples may or may not be available.

OBSOLETE: TI has discontinued the production of the device.

⁽²⁾ RoHS: TI defines "RoHS" to mean semiconductor products that are compliant with the current EU RoHS requirements for all 10 RoHS substances, including the requirement that RoHS substance do not exceed 0.1% by weight in homogeneous materials. Where designed to be soldered at high temperatures, "RoHS" products are suitable for use in specified lead-free processes. TI may reference these types of products as "Pb-Free".

RoHS Exempt: TI defines "RoHS Exempt" to mean products that contain lead but are compliant with EU RoHS pursuant to a specific EU RoHS exemption.

Green: TI defines "Green" to mean the content of Chlorine (CI) and Bromine (Br) based flame retardants meet JS709B low halogen requirements of <=1000ppm threshold. Antimony trioxide based flame retardants must also meet the <=1000ppm threshold requirement.

⁽³⁾ MSL, Peak Temp. - The Moisture Sensitivity Level rating according to the JEDEC industry standard classifications, and peak solder temperature.

⁽⁴⁾ There may be additional marking, which relates to the logo, the lot trace code information, or the environmental category on the device.

⁽⁵⁾ Multiple Device Markings will be inside parentheses. Only one Device Marking contained in parentheses and separated by a "~" will appear on a device. If a line is indented then it is a continuation of the previous line and the two combined represent the entire Device Marking for that device.

⁽⁶⁾ Lead finish/Ball material - Orderable Devices may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead finish/Ball material values may wrap to two lines if the finish value exceeds the maximum column width.

Important Information and Disclaimer: The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and



continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.


In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.

TEXAS

STRUMENTS

TAPE AND REEL INFORMATION





QUADRANT ASSIGNMENTS FOR PIN 1 ORIENTATION IN TAPE



Device	Packago	Package	Dine	SPQ	Reel	Reel	A0	В0	К0	P1	w	Pin1
Device	Туре	Drawing		354	Diameter (mm)		(mm)	(mm)	(mm)	(mm)	(mm)	Quadrant
TPS562209DDCR	SOT-23- THIN	DDC	6	3000	180.0	8.4	3.2	3.2	1.4	4.0	8.0	Q3
TPS562209DDCR	SOT-23- THIN	DDC	6	3000	180.0	8.4	3.2	3.2	1.4	4.0	8.0	Q3
TPS562209DDCT	SOT-23- THIN	DDC	6	250	180.0	8.4	3.2	3.2	1.4	4.0	8.0	Q3
TPS562209DDCT	SOT-23- THIN	DDC	6	250	180.0	8.4	3.2	3.2	1.4	4.0	8.0	Q3
TPS563209DDCR	SOT-23- THIN	DDC	6	3000	180.0	8.4	3.2	3.2	1.4	4.0	8.0	Q3
TPS563209DDCT	SOT-23- THIN	DDC	6	250	180.0	8.4	3.2	3.2	1.4	4.0	8.0	Q3



PACKAGE MATERIALS INFORMATION

26-Mar-2024



All ultrensions are norminal							r.
Device	Package Type	Package Drawing	Pins	SPQ	Length (mm)	Width (mm)	Height (mm)
TPS562209DDCR	SOT-23-THIN	DDC	6	3000	210.0	185.0	35.0
TPS562209DDCR	SOT-23-THIN	DDC	6	3000	210.0	185.0	35.0
TPS562209DDCT	SOT-23-THIN	DDC	6	250	210.0	185.0	35.0
TPS562209DDCT	SOT-23-THIN	DDC	6	250	210.0	185.0	35.0
TPS563209DDCR	SOT-23-THIN	DDC	6	3000	210.0	185.0	35.0
TPS563209DDCT	SOT-23-THIN	DDC	6	250	210.0	185.0	35.0

DDC0006A



PACKAGE OUTLINE

SOT-23 - 1.1 max height

SMALL OUTLINE TRANSISTOR



NOTES:

- All linear dimensions are in millimeters. Any dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.
 This drawing is subject to change without notice.
 Reference JEDEC MO-193.




DDC0006A

EXAMPLE BOARD LAYOUT

SOT-23 - 1.1 max height

SMALL OUTLINE TRANSISTOR



NOTES: (continued)

4. Publication IPC-7351 may have alternate designs.

5. Solder mask tolerances between and around signal pads can vary based on board fabrication site.



DDC0006A

EXAMPLE STENCIL DESIGN

SOT-23 - 1.1 max height

SMALL OUTLINE TRANSISTOR



NOTES: (continued)

6. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations. 7. Board assembly site may have different recommendations for stencil design.



IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATA SHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, regulatory or other requirements.

These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you will fully indemnify TI and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to TI's Terms of Sale or other applicable terms available either on ti.com or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products.

TI objects to and rejects any additional or different terms you may have proposed.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265 Copyright © 2024, Texas Instruments Incorporated