

# DS90CF384A/DS90CF364A +3.3V LVDS Receiver 24-Bit Flat Panel Display (FPD) Link - 65 MHz, +3.3V LVDS Receiver 18-Bit Flat Panel Display (FPD) Link - 65 MHz

Check for Samples: [DS90CF364A](#), [DS90CF384A](#)

## FEATURES

- 20 to 65 MHz Shift Clock Support
- 50% Duty Cycle on Receiver Output Clock
- Best-in-Class Set & Hold Times on RxOUTPUTs
- Rx Power Consumption <142 mW (typ) @65MHz Grayscale
- Rx Power-down Mode <200µW (max)
- ESD Rating >7 kV (HBM), >700V (EIAJ)
- Supports VGA, SVGA, XGA and Dual Pixel SXGA.
- PLL Requires no External Components
- Compatible with TIA/EIA-644 LVDS Standard
- Low Profile 56-lead or 48-lead Packages


## DESCRIPTION

The DS90CF384A receiver converts the four LVDS data streams (Up to 1.8 Gbps throughput or 227 Megabytes/sec bandwidth) back into parallel 28 bits of CMOS/TTL data (24 bits of RGB and 4 bits of Hsync, Vsync, DE and CNTL). Also available is the DS90CF364A that converts the three LVDS data streams (Up to 1.3 Gbps throughput or 170 Megabytes/sec bandwidth) back into parallel 21 bits of CMOS/TTL data (18 bits of RGB and 3 bits of Hsync, Vsync and DE). Both Receivers' outputs are Falling edge strobe. A Rising edge or Falling edge strobe transmitter (DS90C383A/DS90C363A) will interoperate with a Falling edge strobe Receiver without any translation logic.


The DS90CF384A / DS90CF364A devices are enhanced over prior generation receivers and provided a wider data valid time on the receiver output.

This chipset is an ideal means to solve EMI and cable size problems associated with wide, high speed TTL interfaces.

## BLOCK DIAGRAMS



**Figure 1. DS90CF384A  
DGG-56 (TSSOP)**



**Figure 2. DS90CF364A  
DGG-48 (TSSOP)**



Please be aware that an important notice concerning availability, standard warranty, and use in critical applications of Texas Instruments semiconductor products and disclaimers thereto appears at the end of this data sheet.

All trademarks are the property of their respective owners.

**Absolute Maximum Ratings<sup>(1)(2)</sup>**

|                                                      |                                      |                              |
|------------------------------------------------------|--------------------------------------|------------------------------|
| Supply Voltage ( $V_{CC}$ )                          |                                      | -0.3V to +4V                 |
| CMOS/TTL Input Voltage                               |                                      | -0.3V to ( $V_{CC} + 0.3V$ ) |
| CMOS/TTL Output Voltage                              |                                      | -0.3V to ( $V_{CC} + 0.3V$ ) |
| LVDS Receiver Input Voltage                          |                                      | -0.3V to ( $V_{CC} + 0.3V$ ) |
| Junction Temperature                                 |                                      | +150°C                       |
| Storage Temperature                                  |                                      | -65°C to +150°C              |
| Lead Temperature<br>(Soldering, 4 sec)               |                                      | +260°C                       |
| Solder Reflow Temperature (20 sec for FBGA)          |                                      | +220°C                       |
| Maximum Package Power Dissipation<br>Capacity @ 25°C | DGG-56 (TSSOP) Package<br>DS90CF384A | 1.61 W                       |
|                                                      | DGG-48 (TSSOP) Package<br>DS90CF364A | 1.89 W                       |
| Package Derating                                     | DS90CF384AMTD                        | 12.4 mW/°C above +25°C       |
|                                                      | DS90CF364AMTD                        | 15 mW/°C above +25°C         |
| ESD Rating                                           | (HBM, 1.5 k $\Omega$ , 100 pF)       | > 7 kV                       |
|                                                      | (EIAJ, 0 $\Omega$ , 200 pF)          | > 700V                       |

- (1) "Absolute Maximum Ratings" are those values beyond which the safety of the device cannot be verified. They are not meant to imply that the device should be operated at these limits. The tables of "Electrical Characteristics" specify conditions for device operation.
- (2) If Military/Aerospace specified devices are required, please contact the Texas Instruments Sales Office/Distributors for availability and specifications.

**Recommended Operating Conditions**

|                                          | Min | Nom | Max | Units            |
|------------------------------------------|-----|-----|-----|------------------|
| Supply Voltage ( $V_{CC}$ )              | 3.0 | 3.3 | 3.6 | V                |
| Operating Free Air Temperature ( $T_A$ ) | -10 | +25 | +70 | °C               |
| Receiver Input Range                     | 0   |     | 2.4 | V                |
| Supply Noise Voltage ( $V_{CC}$ )        |     |     | 100 | mV <sub>pp</sub> |

**Electrical Characteristics<sup>(1)</sup>**

Over recommended operating supply and temperature ranges unless otherwise specified.

| Symbol                                          | Parameter                    | Conditions                                      | Min | Typ   | Max             | Units |
|-------------------------------------------------|------------------------------|-------------------------------------------------|-----|-------|-----------------|-------|
| CMOS/TTL DC SPECIFICATIONS (For Power Down Pin) |                              |                                                 |     |       |                 |       |
| V <sub>IH</sub>                                 | High Level Input Voltage     |                                                 | 2.0 |       | V <sub>CC</sub> | V     |
| V <sub>IL</sub>                                 | Low Level Input Voltage      |                                                 | GND |       | 0.8             | V     |
| V <sub>CL</sub>                                 | Input Clamp Voltage          | I <sub>CL</sub> = -18 mA                        |     | -0.79 | -1.5            | V     |
| I <sub>IN</sub>                                 | Input Current                | V <sub>IN</sub> = 0.4V, 2.5V or V <sub>CC</sub> |     | +1.8  | +10             | μA    |
|                                                 |                              | V <sub>IN</sub> = GND                           | -10 | 0     |                 | μA    |
| CMOS/TTL DC SPECIFICATIONS                      |                              |                                                 |     |       |                 |       |
| V <sub>OH</sub>                                 | High Level Output Voltage    | I <sub>OH</sub> = -0.4 mA                       | 2.7 | 3.3   |                 | V     |
| V <sub>OL</sub>                                 | Low Level Output Voltage     | I <sub>OL</sub> = 2 mA                          |     | 0.06  | 0.3             | V     |
| I <sub>OS</sub>                                 | Output Short Circuit Current | V <sub>OUT</sub> = 0V                           |     | -60   | -120            | mA    |

- (1) Typical values are given for  $V_{CC} = 3.3V$  and  $T_A = +25C$ .

## Electrical Characteristics<sup>(1)</sup> (continued)

Over recommended operating supply and temperature ranges unless otherwise specified.

| Symbol                                 | Parameter                             | Conditions                                                                         | Min          | Typ | Max  | Units |    |
|----------------------------------------|---------------------------------------|------------------------------------------------------------------------------------|--------------|-----|------|-------|----|
| LVDS RECEIVER DC SPECIFICATIONS        |                                       |                                                                                    |              |     |      |       |    |
| V <sub>TH</sub>                        | Differential Input High Threshold     | V <sub>CM</sub> = +1.2V                                                            |              |     | +100 | mV    |    |
| V <sub>TL</sub>                        | Differential Input Low Threshold      |                                                                                    | -100         |     |      | mV    |    |
| I <sub>IN</sub>                        | Input Current                         | V <sub>IN</sub> = +2.4V, V <sub>CC</sub> = 3.6V                                    |              |     | ±10  | µA    |    |
|                                        |                                       | V <sub>IN</sub> = 0V, V <sub>CC</sub> = 3.6V                                       |              |     | ±10  | µA    |    |
| RECEIVER SUPPLY CURRENT <sup>(2)</sup> |                                       |                                                                                    |              |     |      |       |    |
| ICCRW                                  | Receiver Supply Current Worst Case    | C <sub>L</sub> = 8 pF,<br>Worst Case Pattern,<br>DS90CF384A (Figure 3<br>Figure 6) | f = 32.5 MHz |     | 49   | 65    | mA |
|                                        |                                       |                                                                                    | f = 37.5 MHz |     | 53   | 70    | mA |
|                                        |                                       |                                                                                    | f = 65 MHz   |     | 81   | 105   | mA |
| ICCRW                                  | Receiver Supply Current Worst Case    | C <sub>L</sub> = 8 pF,<br>Worst Case Pattern,<br>DS90CF364A (Figure 3<br>Figure 6) | f = 32.5 MHz |     | 49   | 55    | mA |
|                                        |                                       |                                                                                    | f = 37.5 MHz |     | 53   | 60    | mA |
|                                        |                                       |                                                                                    | f = 65 MHz   |     | 78   | 90    | mA |
| ICCRG                                  | Receiver Supply Current, 16 Grayscale | C <sub>L</sub> = 8 pF,<br>16 Grayscale Pattern,<br>(Figure 4 Figure 5 Figure 6)    | f = 32.5 MHz |     | 28   | 45    | mA |
|                                        |                                       |                                                                                    | f = 37.5 MHz |     | 30   | 47    | mA |
|                                        |                                       |                                                                                    | f = 65 MHz   |     | 43   | 60    | mA |
| ICCRZ                                  | Receiver Supply Current<br>Power Down | Power Down = Low<br>Receiver Outputs Stay Low during<br>Power Down Mode            |              | 10  | 55   | µA    |    |

(2) Current into device pins is defined as positive. Current out of device pins is defined as negative. Voltages are referenced to ground unless otherwise specified (except  $V_{OD}$  and  $\Delta V_{OD}$ ).

## Receiver Switching Characteristics<sup>(1)</sup>

Over recommended operating supply and temperature ranges unless otherwise specified

| Symbol | Parameter                                                       |            | Min   | Typ   | Max   | Units |
|--------|-----------------------------------------------------------------|------------|-------|-------|-------|-------|
| CLHT   | CMOS/TTL Low-to-High Transition Time (Figure 6)                 |            |       | 2     | 5     | ns    |
| CHLT   | CMOS/TTL High-to-Low Transition Time (Figure 6)                 |            |       | 1.8   | 5     | ns    |
| RSPos0 | Receiver Input Strobe Position for Bit 0 (Figure 13, Figure 14) | f = 25 MHz | 1.20  | 1.96  | 2.82  | ns    |
| RSPos1 | Receiver Input Strobe Position for Bit 1                        |            | 6.91  | 7.67  | 8.53  | ns    |
| RSPos2 | Receiver Input Strobe Position for Bit 2                        |            | 12.62 | 13.38 | 14.24 | ns    |
| RSPos3 | Receiver Input Strobe Position for Bit 3                        |            | 18.33 | 19.09 | 19.95 | ns    |
| RSPos4 | Receiver Input Strobe Position for Bit 4                        |            | 24.04 | 24.80 | 25.66 | ns    |
| RSPos5 | Receiver Input Strobe Position for Bit 5                        |            | 29.75 | 30.51 | 31.37 | ns    |
| RSPos6 | Receiver Input Strobe Position for Bit 6                        |            | 35.46 | 36.22 | 37.08 | ns    |
| RSPos0 | Receiver Input Strobe Position for Bit 0 (Figure 13, Figure 14) | f = 65 MHz | 0.7   | 1.1   | 1.4   | ns    |
| RSPos1 | Receiver Input Strobe Position for Bit 1                        |            | 2.9   | 3.3   | 3.6   | ns    |
| RSPos2 | Receiver Input Strobe Position for Bit 2                        |            | 5.1   | 5.5   | 5.8   | ns    |
| RSPos3 | Receiver Input Strobe Position for Bit 3                        |            | 7.3   | 7.7   | 8.0   | ns    |
| RSPos4 | Receiver Input Strobe Position for Bit 4                        |            | 9.5   | 9.9   | 10.2  | ns    |
| RSPos5 | Receiver Input Strobe Position for Bit 5                        |            | 11.7  | 12.1  | 12.4  | ns    |
| RSPos6 | Receiver Input Strobe Position for Bit 6                        |            | 13.9  | 14.3  | 14.6  | ns    |
| RSKM   | RxIN Skew Margin <sup>(2)</sup> (Figure 15)                     | f = 25 MHz | 750   |       |       | ps    |
|        |                                                                 | f = 65 MHz | 500   |       |       | ps    |

(1) Typical values are given for  $V_{CC} = 3.3V$  and  $T_A = +25C$ .

(2) Receiver Skew Margin is defined as the valid data sampling region at the receiver inputs. This margin takes into account the DS90C383B transmitter pulse positions (min and max) and the receiver input setup and hold time (internal data sampling window - RSPos). The RSKM will change when different transmitters are used. This margin allows for LVDS interconnect skew, inter-symbol interference (both dependent on type/length of cable), and clock jitter (less than 250 ps).

## Receiver Switching Characteristics<sup>(1)</sup> (continued)

Over recommended operating supply and temperature ranges unless otherwise specified

| Symbol | Parameter                                                             |            | Min | Typ | Max | Units |
|--------|-----------------------------------------------------------------------|------------|-----|-----|-----|-------|
| RCOP   | RxCLK OUT Period (Figure 7)                                           |            | 15  | T   | 50  | ns    |
| RCOH   | RxCLK OUT High Time (Figure 7)                                        | f = 65 MHz | 5.0 | 7.6 | 9.0 | ns    |
| RCOL   | RxCLK OUT Low Time (Figure 7)                                         |            | 5.0 | 6.3 | 9.0 | ns    |
| RSRC   | RxOUT Setup to RxCLK OUT (Figure 7)                                   |            | 4.5 | 7.3 |     | ns    |
| RHRC   | RxOUT Hold to RxCLK OUT (Figure 7)                                    |            | 4.0 | 6.3 |     | ns    |
| RCCD   | RxCLK IN to RxCLK OUT Delay @ 25°C, V <sub>CC</sub> = 3.3V (Figure 8) |            | 3.5 | 5.0 | 7.5 | ns    |
| RPLLS  | Receiver Phase Lock Loop Set (Figure 9)                               |            |     |     | 10  | ms    |
| RPDD   | Receiver Power Down Delay (Figure 12 )                                |            |     |     | 1   | μs    |

## AC Timing Diagrams






Figure 3. "Worst Case" Test Pattern



- (1) The worst case test pattern produces a maximum toggling of digital circuits, LVDS I/O and CMOS/TTL I/O.
- (2) The 16 grayscale test pattern tests device power consumption for a "typical" LCD display pattern. The test pattern approximates signal switching needed to produce groups of 16 vertical stripes across the display.
- (3) [Figure 3](#) and [Figure 5](#) show a falling edge data strobe (TxCLK IN/RxCLK OUT).
- (4) Recommended pin to signal mapping. Customer may choose to define differently.

**Figure 4. "16 Grayscale" Test Pattern (DS90CF384A)**




- (1) The worst case test pattern produces a maximum toggling of digital circuits, LVDS I/O and CMOS/TTL I/O.
- (2) The 16 grayscale test pattern tests device power consumption for a "typical" LCD display pattern. The test pattern approximates signal switching needed to produce groups of 16 vertical stripes across the display.
- (3) [Figure 3](#) and [Figure 5](#) show a falling edge data strobe (TxCLK IN/RxCLK OUT).
- (4) Recommended pin to signal mapping. Customer may choose to define differently.


**Figure 5. "16 Grayscale" Test Pattern (DS90CF364A)**




**Figure 6. DS90CF384A/DS90CF364A (Receiver) CMOS/TTL Output Load and Transition Times**




**Figure 7. DS90CF384A/DS90CF364A (Receiver) Setup/Hold and High/Low Times**




**Figure 8. DS90CF384A/DS90CF364A (Receiver) Clock In to Clock Out Delay**




**Figure 9. DS90CF384A/DS90CF364A (Receiver) Phase Lock Loop Set Time**




**Figure 10. 28 Parallel TTL Data Inputs Mapped to LVDS Outputs - DS90CF384A**



**Figure 11. 21 Parallel TTL Data Inputs Mapped to LVDS Outputs - DS90CF364A**



**Figure 12. DS90CF384A/DS90CF364A (Receiver) Power Down Delay**



**Figure 13. DS90CF384A (Receiver) LVDS Input Strobe Position**





Figure 14. DS90CF364A (Receiver) LVDS Input Strobe Position



C—Setup and Hold Time (Internal data sampling window) defined by Rspos (receiver input strobe position) min and max

Tppos—Transmitter output pulse position (min and max)

RSKM = Cable Skew (type, length) + Source Clock Jitter (cycle to cycle)<sup>(1)</sup> + ISI (Inter-symbol interference)<sup>(2)</sup>

Cable Skew—typically 10 ps–40 ps per foot, media dependent

Cycle-to-cycle jitter is less than 250 ps at 65 MHz.

ISI is dependent on interconnect length; may be zero.

Figure 15. Receiver LVDS Input Skew Margin


**DS90CF384A PIN DESCRIPTIONS — 56 Lead TSSOP Package — 24-Bit FPD Link Receiver**

| Pin Name             | I/O | No. | Description                                                                                                                                               |
|----------------------|-----|-----|-----------------------------------------------------------------------------------------------------------------------------------------------------------|
| RxIN+                | I   | 4   | Positive LVDS differential data inputs.                                                                                                                   |
| RxIN–                | I   | 4   | Negative LVDS differential data inputs.                                                                                                                   |
| RxOUT                | O   | 28  | TTL level data outputs. This includes: 8 Red, 8 Green, 8 Blue, and 3 control lines—FPLINE, FPFRAME, DRDY (also referred to as HSYNC, VSYNC, Data Enable). |
| RxCLK IN+            | I   | 1   | Positive LVDS differential clock input.                                                                                                                   |
| RxCLK IN–            | I   | 1   | Negative LVDS differential clock input.                                                                                                                   |
| RxCLK OUT            | O   | 1   | TTL level clock output. The falling edge acts as data strobe.                                                                                             |
| PWR DOWN             | I   | 1   | TTL level input. When asserted (low input) the receiver outputs are low.                                                                                  |
| V <sub>CC</sub>      | I   | 4   | Power supply pins for TTL outputs.                                                                                                                        |
| GND                  | I   | 5   | Ground pins for TTL outputs.                                                                                                                              |
| PLL V <sub>CC</sub>  | I   | 1   | Power supply for PLL.                                                                                                                                     |
| PLL GND              | I   | 2   | Ground pin for PLL.                                                                                                                                       |
| LVDS V <sub>CC</sub> | I   | 1   | Power supply pin for LVDS inputs.                                                                                                                         |
| LVDS GND             | I   | 3   | Ground pins for LVDS inputs.                                                                                                                              |


**DS90CF364A PIN DESCRIPTIONS — 48 Lead TSSOP Package — 18-Bit FPD Link Receiver**

| Pin Name             | I/O | No. | Description                                                                                                                                               |
|----------------------|-----|-----|-----------------------------------------------------------------------------------------------------------------------------------------------------------|
| RxIN+                | I   | 3   | Positive LVDS differential data inputs.                                                                                                                   |
| RxIN–                | I   | 3   | Negative LVDS differential data inputs.                                                                                                                   |
| RxOUT                | O   | 21  | TTL level data outputs. This includes: 6 Red, 6 Green, 6 Blue, and 3 control lines—FPLINE, FPFRAME, DRDY (also referred to as HSYNC, VSYNC, Data Enable). |
| RxCLK IN+            | I   | 1   | Positive LVDS differential clock input.                                                                                                                   |
| RxCLK IN–            | I   | 1   | Negative LVDS differential clock input.                                                                                                                   |
| RxCLK OUT            | O   | 1   | TTL level clock output. The falling edge acts as data strobe.                                                                                             |
| PWR DOWN             | I   | 1   | TTL level input. When asserted (low input) the receiver outputs are low.                                                                                  |
| V <sub>CC</sub>      | I   | 4   | Power supply pins for TTL outputs.                                                                                                                        |
| GND                  | I   | 5   | Ground pins for TTL outputs.                                                                                                                              |
| PLL V <sub>CC</sub>  | I   | 1   | Power supply for PLL.                                                                                                                                     |
| PLL GND              | I   | 2   | Ground pin for PLL.                                                                                                                                       |
| LVDS V <sub>CC</sub> | I   | 1   | Power supply pin for LVDS inputs.                                                                                                                         |
| LVDS GND             | I   | 3   | Ground pins for LVDS inputs.                                                                                                                              |

## Pin Diagram for TSSOP Packages



**Figure 16. DS90CF384A  
DGG-56 Package**



**Figure 17. DS90CF364A  
DGG-48 Package**

## REVISION HISTORY

### Changes from Revision H (April 2013) to Revision I

### Page

- Changed layout of National Data Sheet to TI format ..... [12](#)

## PACKAGING INFORMATION

| Orderable part number               | Status<br>(1) | Material type<br>(2) | Package   Pins   | Package qty   Carrier | RoHS<br>(3) | Lead finish/<br>Ball material<br>(4) | MSL rating/<br>Peak reflow<br>(5) | Op temp (°C) | Part marking<br>(6) |
|-------------------------------------|---------------|----------------------|------------------|-----------------------|-------------|--------------------------------------|-----------------------------------|--------------|---------------------|
| <a href="#">DS90CF364AMTD/NOPB</a>  | Active        | Production           | TSSOP (DGG)   48 | 38   TUBE             | Yes         | SN                                   | Level-2-260C-1 YEAR               | -10 to 70    | DS90CF364AMTD<br>>B |
| DS90CF364AMTD/NOPB.B                | Active        | Production           | TSSOP (DGG)   48 | 38   TUBE             | Yes         | SN                                   | Level-2-260C-1 YEAR               | -10 to 70    | DS90CF364AMTD<br>>B |
| <a href="#">DS90CF364AMTDX/NOPB</a> | Active        | Production           | TSSOP (DGG)   48 | 1000   LARGE T&R      | Yes         | SN                                   | Level-2-260C-1 YEAR               | -10 to 70    | DS90CF364AMTD<br>>B |
| <a href="#">DS90CF384AMTD/NOPB</a>  | Active        | Production           | TSSOP (DGG)   56 | 34   TUBE             | Yes         | SN                                   | Level-2-260C-1 YEAR               | -10 to 70    | DS90CF384AMTD<br>>B |
| DS90CF384AMTD/NOPB.B                | Active        | Production           | TSSOP (DGG)   56 | 34   TUBE             | Yes         | SN                                   | Level-2-260C-1 YEAR               | -10 to 70    | DS90CF384AMTD<br>>B |
| <a href="#">DS90CF384AMTDX/NOPB</a> | Active        | Production           | TSSOP (DGG)   56 | 1000   LARGE T&R      | Yes         | SN                                   | Level-2-260C-1 YEAR               | -10 to 70    | DS90CF384AMTD<br>>B |

<sup>(1)</sup> **Status:** For more details on status, see our [product life cycle](#).

<sup>(2)</sup> **Material type:** When designated, preproduction parts are prototypes/experimental devices, and are not yet approved or released for full production. Testing and final process, including without limitation quality assurance, reliability performance testing, and/or process qualification, may not yet be complete, and this item is subject to further changes or possible discontinuation. If available for ordering, purchases will be subject to an additional waiver at checkout, and are intended for early internal evaluation purposes only. These items are sold without warranties of any kind.

<sup>(3)</sup> **RoHS values:** Yes, No, RoHS Exempt. See the [TI RoHS Statement](#) for additional information and value definition.

<sup>(4)</sup> **Lead finish/Ball material:** Parts may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead finish/Ball material values may wrap to two lines if the finish value exceeds the maximum column width.

<sup>(5)</sup> **MSL rating/Peak reflow:** The moisture sensitivity level ratings and peak solder (reflow) temperatures. In the event that a part has multiple moisture sensitivity ratings, only the lowest level per JEDEC standards is shown. Refer to the shipping label for the actual reflow temperature that will be used to mount the part to the printed circuit board.

<sup>(6)</sup> **Part marking:** There may be an additional marking, which relates to the logo, the lot trace code information, or the environmental category of the part.

Multiple part markings will be inside parentheses. Only one part marking contained in parentheses and separated by a "~" will appear on a part. If a line is indented then it is a continuation of the previous line and the two combined represent the entire part marking for that device.

**Important Information and Disclaimer:** The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.

## TAPE AND REEL INFORMATION



\*All dimensions are nominal

| Device               | Package Type | Package Drawing | Pins | SPQ  | Reel Diameter (mm) | Reel Width W1 (mm) | A0 (mm) | B0 (mm) | K0 (mm) | P1 (mm) | W (mm) | Pin1 Quadrant |
|----------------------|--------------|-----------------|------|------|--------------------|--------------------|---------|---------|---------|---------|--------|---------------|
| DS90CF364AMTDX/ NOPB | TSSOP        | DGG             | 48   | 1000 | 330.0              | 24.4               | 8.6     | 13.2    | 1.6     | 12.0    | 24.0   | Q1            |
| DS90CF384AMTDX/ NOPB | TSSOP        | DGG             | 56   | 1000 | 330.0              | 24.4               | 8.6     | 14.5    | 1.8     | 12.0    | 24.0   | Q1            |

## TAPE AND REEL BOX DIMENSIONS



\*All dimensions are nominal

| Device              | Package Type | Package Drawing | Pins | SPQ  | Length (mm) | Width (mm) | Height (mm) |
|---------------------|--------------|-----------------|------|------|-------------|------------|-------------|
| DS90CF364AMTDX/NOPB | TSSOP        | DGG             | 48   | 1000 | 356.0       | 356.0      | 45.0        |
| DS90CF384AMTDX/NOPB | TSSOP        | DGG             | 56   | 1000 | 356.0       | 356.0      | 45.0        |

**TUBE**


\*All dimensions are nominal

| Device                   | Package Name | Package Type | Pins | SPQ | L (mm) | W (mm) | T (μm) | B (mm) |
|--------------------------|--------------|--------------|------|-----|--------|--------|--------|--------|
| DS90CF364AMTD/NOPB       | DGG          | TSSOP        | 48   | 38  | 495    | 10     | 2540   | 5.79   |
| DS90CF364AMTD/<br>NOPB.B | DGG          | TSSOP        | 48   | 38  | 495    | 10     | 2540   | 5.79   |
| DS90CF384AMTD/NOPB       | DGG          | TSSOP        | 56   | 34  | 495    | 10     | 2540   | 5.79   |
| DS90CF384AMTD/<br>NOPB.B | DGG          | TSSOP        | 56   | 34  | 495    | 10     | 2540   | 5.79   |




# EXAMPLE BOARD LAYOUT


DGG0056A

TSSOP - 1.2 mm max height

SMALL OUTLINE PACKAGE



LAND PATTERN EXAMPLE  
SCALE:6X



SOLDER MASK DETAILS

4222167/A 07/2015

NOTES: (continued)


5. Publication IPC-7351 may have alternate designs.
6. Solder mask tolerances between and around signal pads can vary based on board fabrication site.

# EXAMPLE STENCIL DESIGN

DGG0056A

TSSOP - 1.2 mm max height

SMALL OUTLINE PACKAGE





SOLDER PASTE EXAMPLE  
BASED ON 0.125 mm THICK STENCIL  
SCALE:6X

4222167/A 07/2015

NOTES: (continued)

7. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.
8. Board assembly site may have different recommendations for stencil design.



4214859/B 11/2020

## NOTES:


1. All linear dimensions are in millimeters. Any dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.
2. This drawing is subject to change without notice.
3. This dimension does not include mold flash, protrusions, or gate burrs. Mold flash, protrusions, or gate burrs shall not exceed 0.15 mm per side.
4. Reference JEDEC registration MO-153.

# EXAMPLE BOARD LAYOUT


DGG0048A

TSSOP - 1.2 mm max height

SMALL OUTLINE PACKAGE



LAND PATTERN EXAMPLE  
SCALE:6X



SOLDER MASK DETAILS

4214859/B 11/2020

NOTES: (continued)


5. Publication IPC-7351 may have alternate designs.
6. Solder mask tolerances between and around signal pads can vary based on board fabrication site.

## EXAMPLE STENCIL DESIGN

DGG0048A

TSSOP - 1.2 mm max height

SMALL OUTLINE PACKAGE



SOLDER PASTE EXAMPLE  
BASED ON 0.125 mm THICK STENCIL  
SCALE:6X

4214859/B 11/2020


NOTES: (continued)

7. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.
8. Board assembly site may have different recommendations for stencil design.

## DGG (R-PDSO-G\*\*)

## PLASTIC SMALL-OUTLINE PACKAGE

48 PINS SHOWN



- NOTES: A. All linear dimensions are in millimeters.  
 B. This drawing is subject to change without notice.  
 C. Body dimensions do not include mold protrusion not to exceed 0,15.  
 D. Falls within JEDEC MO-153

## IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATASHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, regulatory or other requirements.

These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you fully indemnify TI and its representatives against any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to [TI's Terms of Sale](#), [TI's General Quality Guidelines](#), or other applicable terms available either on [ti.com](#) or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products. Unless TI explicitly designates a product as custom or customer-specified, TI products are standard, catalog, general purpose devices.

TI objects to and rejects any additional or different terms you may propose.

Copyright © 2026, Texas Instruments Incorporated

Last updated 10/2025