

TPD8S009 8-Channel ESD Protection for DisplayPort and HDMI

1 Features

- IEC 61000-4-2 Level 4 ESD Protection
 - $\pm 8\text{kV}$ Contact Discharge
- IEC 61000-4-5 Surge Protection
 - 2.5A ($8/20\mu\text{s}$)
- I/O Capacitance: 0.8pF (Typical)
- Low Leakage Current: 10nA (Typical)
- Supports High-Speed Differential Data Rates (3dB Bandwidth $> 4\text{GHz}$)
- I_{off} Feature
- Industrial Temperature Range: -40°C to $+85^{\circ}\text{C}$
- Easy Straight-Through Routing Package for HDMI and DisplayPort Connectors

2 Applications

- End Equipment
 - Set-Top Boxes
 - Laptops and Desktops
 - Projectors
 - Video Surveillance
- Interfaces
 - DisplayPort 1.1
 - HDMI 1.4
 - DVI

3 Description


The TPD8S009 device is an eight-channel TVS diode array for ESD protection. The TPD8S009 is rated to dissipate contact ESD strikes at the maximum level specified in the IEC 61000-4-2 international standard (Level 4), with $\pm 8\text{kV}$ contact discharge ESD protection. The low capacitance (0.8pF) of this device, coupled with the excellent matching between differential signal pairs enables this device to provide transient voltage suppression circuit protection for high-speed idfferential data rates (3dB bandwidth $> 4\text{GHz}$).

The TPD8S009 is offered in a 8-pin SON package. This package offers easy design and layout, as the package matches exactly with the HDMI and DisplayPort high-speed pinout.

Package Information

PART NUMBER	PACKAGE ⁽¹⁾	BODY SIZE (NOM)
TPD8S009	SON (15)	$2.50\text{mm} \times 6.50\text{mm}$

(1) For all available packages, see the orderable addendum at the end of the data sheet.




Simplified Internal Schematic



Table of Contents

1 Features	1	7 Application and Implementation	8
2 Applications	1	7.1 Application Information.....	8
3 Description	1	7.2 Typical Application.....	8
4 Pin Configuration and Functions	3	8 Power Supply Recommendations	10
Pin Functions.....	3	9 Layout	10
5 Specifications	4	9.1 Layout Guidelines.....	10
5.1 Absolute Maximum Ratings.....	4	9.2 Layout Example.....	10
5.2 ESD Ratings.....	4	10 Device and Documentation Support	11
5.3 Recommended Operating Conditions.....	4	10.1 Third-Party Products Disclaimer.....	11
5.4 Thermal Information.....	4	10.2 Support Resources.....	11
5.5 Electrical Characteristics.....	5	10.3 Trademarks.....	11
5.6 Typical Characteristics.....	5	10.4 Electrostatic Discharge Caution.....	11
6 Detailed Description	6	10.5 Glossary.....	11
6.1 Overview.....	6	11 Revision History	11
6.2 Functional Block Diagram.....	6	12 Mechanical, Packaging, and Orderable	
6.3 Feature Description.....	6	Information	11
6.4 Device Functional Modes.....	7		

4 Pin Configuration and Functions



N.C. – Not internally connected

Figure 4-1. DSM Package 15-Pin SON Top View

Pin Functions

PIN		TYPE	DESCRIPTION
NO.	NAME		
1	D0+	ESD port	High-speed ESD clamp provides ESD protection to the high-speed display port/HDMI differential data lines.
3	D0–		
4	D1+		
6	D1–		
7	D2+		
9	D2–		
10	D3+		
12	D3–		
2	GND	GND	Ground
5			
8			
11			
14	N.C.	No connect	No internal signal connection
13	V _{CC}	Supply	I/O supply
15			

5 Specifications

5.1 Absolute Maximum Ratings

over operating free-air temperature range (unless otherwise noted)⁽¹⁾

		MIN	MAX	UNIT
V _{CC}	Supply voltage	−0.3	6	V
V _{IO}	IO signal voltage	0	V _{CC}	V
T _A	Characterized free-air operating temperature	−40	85	°C
P _{PP}	Peak pulse power (t _p = 8/20μs)		25	W
I _{PP}	Peak pulse current (t _p = 8/20μs)		2.5	A
T _{stg}	Storage temperature	−65	125	°C

- (1) Stresses beyond those listed under *Absolute Maximum Ratings* may cause permanent damage to the device. These are stress ratings only, which do not imply functional operation of the device at these or any other conditions beyond those indicated under *Recommended Operating Conditions*. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability.

5.2 ESD Ratings

		VALUE	UNIT
V _(ESD)	Electrostatic discharge		
	Human-body model (HBM), per ANSI/ESDA/JEDEC JS-001 ⁽¹⁾	±2500	V
	Charged-device model (CDM), per JEDEC specification JESD22-C101 ⁽²⁾	±1000	
	IEC 61000-4-2 Contact Discharge	±8000	
	IEC 61000-4-2 Air-Gap Discharge	±9000	

- (1) JEDEC document JEP155 states that 500V HBM allows safe manufacturing with a standard ESD control process.

- (2) JEDEC document JEP157 states that 250V CDM allows safe manufacturing with a standard ESD control process.

5.3 Recommended Operating Conditions

over operating free-air temperature range (unless otherwise noted)

		MIN	MAX	UNIT
V _{IO}	Input pin voltage	0	V _{CC}	V
T _A	Operating free-air temperature	−40	85	°C

5.4 Thermal Information

THERMAL METRIC ⁽¹⁾		TPD8S009	UNIT
		DSM (SON)	
		15 PINS	
R _{θJA}	Junction-to-ambient thermal resistance	405.4	°C/W
R _{θJC(top)}	Junction-to-case (top) thermal resistance	35.4	°C/W
R _{θJB}	Junction-to-board thermal resistance	284.3	°C/W
ψ _{JT}	Junction-to-top characterization parameter	49.2	°C/W
ψ _{JB}	Junction-to-board characterization parameter	284.3	°C/W
R _{θJC(bot)}	Junction-to-case (bottom) thermal resistance	n/a	°C/W

- (1) For more information about traditional and new thermal metrics, see the [Semiconductor and IC Package Thermal Metrics](#) application report.

5.5 Electrical Characteristics

over operating free-air temperature range (unless otherwise noted)

PARAMETER	TEST CONDITIONS		MIN	TYP	MAX	UNIT
V_{RWM}	Reverse standoff voltage	Any IO pin to ground			5.5	V
V_{BR}	Breakdown voltage	$I_{IO} = 1\text{mA}$ Any IO pin to ground	9			V
I_{IO}	IO port current	$V_{IO} = 3.3\text{V}$, $V_{CC} = 5\text{V}$ Any IO pin		0.01	0.1	μA
I_{off}	Current from IO port to supply pins	$V_{IO} = 3.3\text{V}$, $V_{CC} = 5\text{V}$ Any IO pin		0.01	0.1	μA
V_D	Diode forward voltage	$I_{IO} = 8\text{mA}$ Lower clamp diode	0.6	0.8	0.95	V
R_{DYN}	Dynamic resistance	$I = 1\text{A}$ Any IO pin		1.1		Ω
C_{IO}	IO capacitance	$V_{CC} = 5\text{V}$, $V_{IO} = 2.5\text{V}$ Any IO pin		0.8		pF
I_{CC}	Operating supply current	$V_{IO} = \text{Open}$, $V_{CC} = 5\text{V}$ V_{CC} pin		0.1	1	μA

5.6 Typical Characteristics




Figure 5-1. Insertion Loss vs Frequency




Figure 5-2. Peak Pulse Waveforms




Figure 5-3. IEC Clamping Waveforms (8-kV Contact)




Figure 5-4. Figure 3. IEC Clamping Waveforms (-8-kV Contact)


6 Detailed Description

6.1 Overview

The TPD8S009 is an eight-channel TVS diode array for ESD protection. TPD8S009 is rated to dissipate contact ESD strikes at the maximum level specified in the IEC 61000-4-2 international standard (Level 4), with $\pm 8\text{kV}$ contact discharge ESD protection. The low capacitance (0.8pF) of this device, coupled with the excellent matching between differential signal pairs enables this device to provide transient voltage suppression circuit protection for high-speed differential data rates (3dB bandwidth > 4GHz).

The TPD8S009 offers an optional V_{CC} supply pin which can be connected to system supply plane. There is a blocking diode at the V_{CC} pin to enable the I_{off} feature for the TPD8S009. The TPD8S009 can handle live signal at the signal pins when the V_{CC} pin is connected to 0V. The V_{CC} pin allows all the internal circuit nodes of the TPD8S009 to be at known potential during start-up time. However, connecting the optional V_{CC} pin to board supply plane doesn't affect the system level ESD performance of the TPD8S009.

6.2 Functional Block Diagram



6.3 Feature Description

6.3.1 IEC 61000-4-2 ESD Protection

The I/O pins can withstand ESD events up to $\pm 8\text{kV}$ contact and $\pm 9\text{kV}$ air. An ESD and surge clamp diverts the current to ground.

6.3.2 IEC 61000-4-5 Surge Protection

The I/O pins can withstand surge events up to 2.5A and 25W (8/20 μs waveform). An ESD and surge clamp diverts this current to ground.

6.3.3 I/O Capacitance

The capacitance between each I/O pin to ground is 0.8pF (typical). This device can support data rates up to 3.4Gbps.

6.3.4 Low Leakage Current

The I/O pins feature a low leakage current of 10nA (typical) with an IO bias of 3.3V and V_{CC} bias of 5V.

6.3.5 Supports High-Speed Differential Data Rates

The I/O pins low capacitance of 0.8pF (typical) gives them a typical -3dB bandwidth > 4GHz. This allows the TPD8S009 to protect interfaces with high-speed signals like HDMI 1.4.

6.3.6 I_{off} Feature

The TPD8S009 offers an optional V_{CC} supply pin which can be connected to system supply plane. There is a blocking diode at the V_{CC} pin which makes it so the TPD8S009 can handle live signal at the D+, D- pins when

the V_{CC} pin is connected to 0V. This is the I_{off} feature, which is crucial for HDMI, as a live signal can be put on the IO pins when the system is powered off.

6.3.7 Industrial Temperature Range

This device features an industrial operating range of -40°C to $+85^{\circ}\text{C}$.

6.3.8 Easy Straight Through Routing

The layout of this device makes it simple and easy to add protection to an existing layout. The package offers flow-through routing, requiring minimal modification to an existing layout. Flow-through routing also allows the PCB designer to optimize the signal integrity of any high-speed signals being protected.

6.4 Device Functional Modes

TPD8S009 is a passive-integrated circuit that activates whenever voltages above V_{BR} or below the lower diodes $V_{forward}$ (-0.6V) are present upon the circuit being protected. During ESD events, voltages as high as $\pm 9\text{kV}$ can be directed to ground and V_{CC} through the internal diode network. Once the voltages on the protected lines fall below the trigger voltage of the TPD8S009 (usually within 10's of nano-seconds) the device reverts back to a high-impedance state.

7 Application and Implementation

Note


Information in the following applications sections is not part of the TI component specification, and TI does not warrant its accuracy or completeness. TI's customers are responsible for determining suitability of components for their purposes. Customers should validate and test their design implementation to confirm system functionality.

7.1 Application Information

The TPD8S009 can provide system-level ESD protection to the high-speed differential lines of the HDMI or display ports. The flow-through package offers flexibility for board routing with traces up to 15mm wide. [Figure 7-1](#) shows the board-layout scheme for the four differential pair lines. The special pin configuration of the TPD8S009 matches the HDMI or DisplayPort pin assignments. It allows the differential signal pairs to couple together after they touch the ESD ports (pins 1–3, 4–6, 7–9, and 10–12) of the TPD8S009.

The TPD4E001 is recommended for ESD protection of slow-speed control lines.

7.2 Typical Application



TPD8S009 and TPD4E001 provide complete ESD protection for display or HDMI interface

Figure 7-1. Typical Application

7.2.1 Design Requirements

For this design example, one TPD8S009 devices, and one TPD4E001 are being used in an HDMI 1.4 application. This provides a complete port protection scheme.

Given the HDMI 1.4 application, the following parameters are shown in [Table 7-1](#).

Table 7-1. Design Parameters

DESIGN PARAMETER	VALUE
Signal range on high-speed TMDs pins	0V to 3.6V
Operating Frequency	1.7GHz

7.2.2 Detailed Design Procedure

To begin the design process, some parameters must be decided upon; the designer must know the following:

- Signal range on all the protected lines
- Operating frequency

7.2.2.1 Signal Range on High Speed TMDs Pins

TPD8S009 has 8 identical protection channels for signal lines. The symmetry of the device provides flexibility when selecting which of the 8 I/O channels protect which signal lines. The package is also designed to easily lay out on an HDMI connector, eliminating any tricky routing issues. Any I/O supports a signal range of 0 to 5.5V. Therefore, this device supports the HDMI 1.4 signal swing.

7.2.2.2 Bandwidth on High-Speed TMDs Pins

Each pin of the TPD8S009 has a typical –3dB bandwidth of 4GHz. Therefore, this device can handle HDMI 1.4 data rate of 3.4Gbps with operating frequency of 1.7GHz.

7.2.3 Application Curves




Figure 7-2. Eye Diagram Without TPD8S009 (2.5Gbps Data Rate)




Figure 7-3. Eye Diagram With TPD8S009 (2.5Gbps Data Rate)

8 Power Supply Recommendations


This device is a passive ESD protection device so there is no need to power it. Take care to make sure that the maximum voltage specifications for each pin are not violated.

9 Layout

9.1 Layout Guidelines

- The optimum placement is as close to the connector as possible.
 - EMI during an ESD event can couple from the trace being struck to other nearby unprotected traces, resulting in early system failures.
 - The PCB designer must minimize the possibility of EMI coupling by keeping any unprotected traces away from the protected traces which are between the TVS and the connector.
- Route the protected traces as straight as possible.
- Eliminate any sharp corners on the protected traces between the TVS and the connector by using rounded corners with the largest radii possible.
 - Electric fields tend to build up on corners, increasing EMI coupling.

9.2 Layout Example



Legend

- VIA to 5V Plane
- VIA to GND Plane

Figure 9-1. Typical Layout for HDMI Connector

10 Device and Documentation Support

10.1 Third-Party Products Disclaimer

TI'S PUBLICATION OF INFORMATION REGARDING THIRD-PARTY PRODUCTS OR SERVICES DOES NOT CONSTITUTE AN ENDORSEMENT REGARDING THE SUITABILITY OF SUCH PRODUCTS OR SERVICES OR A WARRANTY, REPRESENTATION OR ENDORSEMENT OF SUCH PRODUCTS OR SERVICES, EITHER ALONE OR IN COMBINATION WITH ANY TI PRODUCT OR SERVICE.

10.2 Support Resources

[TI E2E™ support forums](#) are an engineer's go-to source for fast, verified answers and design help — straight from the experts. Search existing answers or ask your own question to get the quick design help you need.

Linked content is provided "AS IS" by the respective contributors. They do not constitute TI specifications and do not necessarily reflect TI's views; see TI's [Terms of Use](#).

10.3 Trademarks

TI E2E™ is a trademark of Texas Instruments.
All trademarks are the property of their respective owners.

10.4 Electrostatic Discharge Caution



This integrated circuit can be damaged by ESD. Texas Instruments recommends that all integrated circuits be handled with appropriate precautions. Failure to observe proper handling and installation procedures can cause damage.

ESD damage can range from subtle performance degradation to complete device failure. Precision integrated circuits may be more susceptible to damage because very small parametric changes could cause the device not to meet its published specifications.

10.5 Glossary

[TI Glossary](#) This glossary lists and explains terms, acronyms, and definitions.

11 Revision History

NOTE: Page numbers for previous revisions may differ from page numbers in the current version.

Changes from Revision A (February 2015) to Revision B (January 2025)	Page
• Updated device name to TPD8S009.....	6

Changes from Revision * (July 2008) to Revision A (February 2015)	Page
• Added <i>ESD Ratings</i> table, <i>Feature Description</i> section, <i>Device Functional Modes</i> , <i>Application and Implementation</i> section, <i>Power Supply Recommendations</i> section, <i>Layout</i> section, <i>Device and Documentation Support</i> section, and <i>Mechanical, Packaging, and Orderable Information</i> section.....	1
• Deleted <i>Ordering Information</i> table.....	1
• Deleted lead temperature from <i>Absolute Maximum Ratings</i>	4

12 Mechanical, Packaging, and Orderable Information

The following pages include mechanical, packaging, and orderable information. This information is the most current data available for the designated devices. This data is subject to change without notice and revision of this document. For browser-based versions of this data sheet, refer to the left-hand navigation.

PACKAGING INFORMATION

Orderable part number	Status (1)	Material type (2)	Package Pins	Package qty Carrier	RoHS (3)	Lead finish/ Ball material (4)	MSL rating/ Peak reflow (5)	Op temp (°C)	Part marking (6)
TPD8S009DSMR	Active	Production	SON (DSM) 15	3000 LARGE T&R	Yes	NIPDAUAG	Level-1-260C-UNLIM	-40 to 85	PK009
TPD8S009DSMR.B	Active	Production	SON (DSM) 15	3000 LARGE T&R	Yes	NIPDAUAG	Level-1-260C-UNLIM	-40 to 85	PK009

- ⁽¹⁾ **Status:** For more details on status, see our [product life cycle](#).
- ⁽²⁾ **Material type:** When designated, preproduction parts are prototypes/experimental devices, and are not yet approved or released for full production. Testing and final process, including without limitation quality assurance, reliability performance testing, and/or process qualification, may not yet be complete, and this item is subject to further changes or possible discontinuation. If available for ordering, purchases will be subject to an additional waiver at checkout, and are intended for early internal evaluation purposes only. These items are sold without warranties of any kind.
- ⁽³⁾ **RoHS values:** Yes, No, RoHS Exempt. See the [TI RoHS Statement](#) for additional information and value definition.
- ⁽⁴⁾ **Lead finish/Ball material:** Parts may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead finish/Ball material values may wrap to two lines if the finish value exceeds the maximum column width.
- ⁽⁵⁾ **MSL rating/Peak reflow:** The moisture sensitivity level ratings and peak solder (reflow) temperatures. In the event that a part has multiple moisture sensitivity ratings, only the lowest level per JEDEC standards is shown. Refer to the shipping label for the actual reflow temperature that will be used to mount the part to the printed circuit board.
- ⁽⁶⁾ **Part marking:** There may be an additional marking, which relates to the logo, the lot trace code information, or the environmental category of the part.

Multiple part markings will be inside parentheses. Only one part marking contained in parentheses and separated by a "~" will appear on a part. If a line is indented then it is a continuation of the previous line and the two combined represent the entire part marking for that device.

Important Information and Disclaimer:The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.

TAPE AND REEL INFORMATION



*All dimensions are nominal

Device	Package Type	Package Drawing	Pins	SPQ	Reel Diameter (mm)	Reel Width W1 (mm)	A0 (mm)	B0 (mm)	K0 (mm)	P1 (mm)	W (mm)	Pin1 Quadrant
TPD8S009DSMR	SON	DSM	15	3000	180.0	12.4	2.75	6.75	0.95	4.0	12.0	Q1

TAPE AND REEL BOX DIMENSIONS




*All dimensions are nominal

Device	Package Type	Package Drawing	Pins	SPQ	Length (mm)	Width (mm)	Height (mm)
TPD8S009DSMR	SON	DSM	15	3000	200.0	183.0	25.0

DSM (R-PDSO-N15)


PLASTIC SMALL OUTLINE



4208854/A 08/2007

- NOTES:
- A. All linear dimensions are in millimeters. Dimensioning and tolerancing per ASME Y14.5M-1994.
 - B. This drawing is subject to change without notice.
 - C. SON (Small Outline No-Lead) package configuration.
 - Pin 1 identifiers are located on both top and bottom of the package and within the zone indicated. The Pin 1 identifiers are either a molded, marked, or metal feature.


DSM (R-PDSO-N15)



4210120/A 02/09

- NOTES:
- All linear dimensions are in millimeters.
 - This drawing is subject to change without notice.
 - Publication IPC-7351 is recommended for alternate designs.
 - Laser cutting apertures with trapezoidal walls and also rounding corners will offer better paste release. Customers should contact their board assembly site for stencil design recommendations. Refer to IPC 7525 for stencil design considerations.
 - Customers should contact their board fabrication site for minimum solder mask web tolerances between signal pads.

DSM (R-PDSO-N15)



4210120/A 02/09

- NOTES:
- A. All linear dimensions are in millimeters.
 - B. This drawing is subject to change without notice.
 - C. Publication IPC-7351 is recommended for alternate designs.
 - D. Laser cutting apertures with trapezoidal walls and also rounding corners will offer better paste release. Customers should contact their board assembly site for stencil design recommendations. Refer to IPC 7525 for stencil design considerations.
 - E. Customers should contact their board fabrication site for minimum solder mask web tolerances between signal pads.

IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATASHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, regulatory or other requirements.

These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you fully indemnify TI and its representatives against any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to [TI's Terms of Sale](#), [TI's General Quality Guidelines](#), or other applicable terms available either on [ti.com](https://www.ti.com) or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products. Unless TI explicitly designates a product as custom or customer-specified, TI products are standard, catalog, general purpose devices.

TI objects to and rejects any additional or different terms you may propose.

Copyright © 2025, Texas Instruments Incorporated

Last updated 10/2025