







TPS25858-Q1, TPS25859-Q1 SLVSF62B - NOVEMBER 2020 - REVISED SEPTEMBER 2021

# TPS25858-Q1 and TPS25859-Q1 Low EMI Dual 3-A USB Type-C® Charging Ports **Converter With Programmable Current Limit and Thermal Management**

#### 1 Features

- AEC-Q100 qualified for automotive applications:
  - Temperature grade 1: T<sub>A</sub> range –40°C to +125°C
  - HBM ESD classification level H2
  - CDM ESD classification level C5
- Optimized for ultra-low EMI requirements:
  - Meets CISPR25 class 5 standard
  - HotRod<sup>™</sup> package minimizes switch node
  - Spread spectrum reduces peak emissions
- Synchronous buck regulator
  - High efficiency at 400 kHz: 94.5% at  $V_{IN} = 13.5$ V,  $I_{PA BUS} = 3 A$  and  $I_{PB BUS} = 3 A$
  - 18-mΩ/10-mΩ Low R<sub>DS(ON)</sub> buck regulator **MOSFETs**
  - Operating voltage range: 5.5 V to 26 V, withstand 36-V input
  - Adjustable frequency: 200 kHz to 800 kHz
  - FPWM with spread-spectrum dithering
  - Selectable output voltage: 5.1 V, 5.17 V, 5.3 V, 5.4 V
- Internal power path:
  - $-~7\text{-m}\Omega/7\text{-m}\Omega$  low  $R_{DS(ON)}$  internal USB power MOSFETs
  - Programmable current limit for USB ports with high accuracy: ±10% at 3.4 A
  - OUT: 5.1 V, 200-mA supply for auxiliary loads
- Line drop compensation: 90 mV at 2.4-A load
  - PA DM TPS25858-Q1 PA\_CC1 PB\_BUS

Simplified Schematic: TPS25858-Q1

- Compliant to USB-IF standards
  - Type-C rev 1.3
    - 3-A capability advertisement on CC
    - V<sub>BUS</sub> application and discharge
    - V<sub>CONN</sub> source: 200 mA
  - Automatic DCP modes (TPS25858-Q1):
    - Shorted mode per BC1.2 and YD/T 1591 2009
    - 1.2-V mode
    - 2.7-V Divider 3 mode
- Load shedding versus programmable T<sub>△</sub>
- Device T<sub>J</sub> range: -40°C to +150°C
- FAULT flag reports (TPS25859-Q1): USB overcurrent, thermal shutdown
- USB ports ON/OFF control (TPS25859-Q1)

## 2 Applications

- Automotive USB charging ports
- Automotive USB media hubs


## 3 Description

The TPS2585x-Q1 is an integrated USB charging port solution, which includes a synchronous DC/DC converter capable of supplying up to 6.6 A and integrated detection and control for implementing USB Battery Charging 1.2 and Type-C ports.

### Device Information<sup>(1)</sup>

PART NUMBER	PACKAGE	BODY SIZE (NOM)
TPS25858-Q1	VQFN-HR (25)	3.50 mm × 4.50 mm
TPS25859-Q1	VQFN-HR (25)	3.50 mm × 4.50 mm

For detail part numbers for all available different options, see the orderable addendum at the end of the data sheet.



**Efficiency vs Output Current** 



## **Table of Contents**

1 Features	1	10.2 Functional Block Diagram	22
2 Applications		10.3 Feature Description	
3 Description		10.4 Device Functional Modes	
4 Revision History		11 Application and Implementation	40
5 Description (continued)		11.1 Application Information	40
6 Device Comparison Table	4	11.2 Typical Applications	
7 Pin Configuration and Functions		12 Power Supply Recommendations	
8 Specifications		13 Layout	
8.1 Absolute Maximum Ratings		13.1 Layout Guidelines	50
8.2 ESD Ratings		13.2 Layout Example	
8.3 Recommended Operating Conditions	9	13.3 Ground Plane and Thermal Considerations	
8.4 Thermal Information	10	14 Device and Documentation Support	53
8.5 Electrical Characteristics		14.1 Receiving Notification of Documentation Update	
8.6 Timing Requirements		14.2 Support Resources	
8.7 Switching Characteristics	14	14.3 Trademarks	
8.8 Typical Characteristics	15	14.4 Electrostatic Discharge Caution	53
9 Parameter Measurement Information	20	14.5 Glossary	
10 Detailed Description	21	15 Mechanical, Packaging, and Orderable	
10.1 Overview		Information	54

## **4 Revision History**

NOTE: Page numbers for previous revisions may differ from page numbers in the current version.

Changes from Revision A (March 2021) to Revision B (September 2021)	Page
Added TPS25859-Q1 information	1
Changes from Revision * (November 2020) to Revision A (March 2021)	Page
Updated document title	
Added EMI requirements bullet to the <i>Features</i> section	
Added Figure 11-4 to the Application Curves section	45



### 5 Description (continued)

The TPS2585x-Q1 is a family of highly-integrated USB Type-C® charging controller for dual-USB ports application.

The TPS2585x-Q1 integrates a monolithic, synchronous, rectified, step-down, switch-mode converter with internal power MOSFETs and two USB current-limit switches with charging port auto-detection. The TPS2585x-Q1 offers a compact solution that achieves 6.6 A of continuous output current with excellent load and line regulation over a wide input supply range. The synchronous buck regulator operates with peak-current mode control and is internally compensated to simplify the design. A resistor on the FREQ pin sets the switching frequency between 200 kHz and 800 kHz.

The TPS2585x-Q1 integrates standard USB Type-C port controller functionality including Configuration Channel (CC) logic for 3-A and 1.5-A current advertisement. TPS25858-Q1 integrates Battery Charging (Rev. 1.2) to provide the required electrical signatures necessary for non-Type-C, legacy USB devices which use USB data line signaling to determine USB port current sourcing capabilities. TPS25859-Q1 can enable each port individually and can report fault condition for each port. The TPS2585x-Q1 also offers VCONN power that can meet the USB3.1 power requirement. The part is especially suitable for dual-port application due to the high system integration and small footprint.

The TPS2585x-Q1 supports intelligent thermal management. The USB output voltage and Type-C current advertisements can be regulated according to the temperature sensing through the TS pin. The TPS2585x-Q1 must connect a NTC thermistor on the TS pin to monitor the ambient temperature or PCB boar temperature, depending on where the NTC thermistor is put in the USB charging module or PCB board. Select a different NTC thermistor and bottom-side series resistor can change the temperature threshold for load shedding.

The TPS2585x-Q1 have four selectable USB output voltage settings: 5.1 V, 5.17 V, 5.3 V, and 5.4 V. The TPS2585x-Q1 integrates a precision current sense amplifier for cable droop compensation and user-programmable current limit tuning. The cable compensation is only available when the output voltage is set to 5.17 V. The cable compensation voltage is 90 mV at 2.4-A output current. Cable compensation aids portable devices in charging at optimum current and voltage under heavy loads by changing the buck regulator output voltage linearly with load current to counteract the voltage drop due to wire resistance in automotive cabling. The BUS voltage measured at a connected portable device remains approximately constant, regardless of load current, allowing the battery charger of the portable device to work optimally.

The TPS2585x-Q1 provides various safety features for USB charging and system operations, including external negative thermistor monitoring, cycle-by-cycle current limit, hiccup short-circuit protection, undervoltage lockout, BUS overcurrent, OUT overcurrent, and die overtemperature protection.

The device family is available in a 25-pin, 3.5 mm × 4.5 mm QFN package.



## **6 Device Comparison Table**

DEVICE NUMBER	TPS25858-Q1	TPS25859-Q1
Type-C ports number	Dual	Dual
Support Type-C protocol	Yes	Yes
NTC Thermistor Input (TS)	Yes	Yes
USB load switch ON/OFF control	No	Yes
Fault event indication	No	Yes
Thermal warning indication	No	No
External clock synchronization	Yes, range 200 kHz to 800 kHz	Yes, range 200 kHz to 800 kHz
BC1.2 DCP	Yes	No
Apple or Samsung charging scheme	Yes	No
Cable compensation	Yes <sup>(1)</sup>	Yes <sup>(1)</sup>
Selectable output voltage	Yes	Yes
Adjustable output short current limit	Yes	Yes
FPWM/PFM	FPWM	FPWM
DC/DC always ON (EN pull High)	No	Yes
Spread spectrum	Yes	Yes
Package	QFN-25 3.5 mm × 4.5 mm	QFN-25 3.5 mm × 4.5 mm

<sup>(1)</sup> VSET short to GND to set 5.17-V output voltage. Compensation voltage is 90 mV when either USB port A or USB port B output 2.4-A current.



# 7 Pin Configuration and Functions




Figure 7-1. TPS25858-Q1 RPQ Package 25-Pin (QFN) Top View




Figure 7-2. TPS25859-Q1 RPQ Package 25-Pin (QFN) Top View

Table 7-1. Pin Functions for TPS25858-Q1 RPQ Package

and the state of t				
PIN		TYPE (1)	DESCRIPTION	
NAME	NO.	1115=\/	DESCRIPTION	
VSET	1	А	Output Voltage Setting. Short to GND to set the 5.17-V output voltage. Float or pull up to $V_{SENSE}$ to set 5.1-V output voltage. Tie to GND through a 40.2-K $\Omega$ resistor to set 5.3-V output voltage. Tie to GND through a 80.6-K $\Omega$ resistor to set 5.4-V output voltage.	
TS	2	Α	Temperature Sense terminal. Connect the TS input to the NTC thermistor.	
BIAS	3	Р	Input of internal bias supply. Must connect to the SENSE pin directly. Power the internal circuit.	
PA_DP	4	А	D+ data line. Connect to USB Port A connector.	
PA_DM	5	А	D- data line. Connect to USB Port A connector.	
AGND	6	Р	Analog ground terminal. Connect AGND to PGND.	
PA_CC1	7	Α	Connect to Type-C Port A CC1 pin. Analog Input/Output.	
PA_CC2	8	Α	Connect to Type-C Port A CC2 pin. Analog Input/Output.	
ILIM	9	А	Current Limit program. Connect a resistor to set the current limit threshold. Short to GND to set the default 3.55-A current limit.	



## Table 7-1. Pin Functions for TPS25858-Q1 RPQ Package (continued)

PIN	PIN		DESCRIPTION	
NAME	NO.	TYPE (1)	DESCRIPTION	
PA_BUS	10	Р	Port A BUS output.	
SENSE	11	Р	Output Voltage Sensing. External load on this pin is strictly prohibited. Connect to the other side of the external inductor.	
PB_BUS	12	Р	Port B BUS output.	
OUT	13	Р	Output pin. Provide 5.1-V voltage to power external load with max 200-mA capability. The voltage follows the VSET setting.	
PB_CC2	14	Α	Connect to Type-C Port B CC2 pin. Analog Input/Output.	
PB_CC1	15	Α	Connect to Type-C Port B CC1 pin. Analog Input/Output.	
PGND	16, 24, 25	Р	Power Ground terminal. Connected to the source of LS FET internally. Connect to system ground, AGND, and the ground side of the $C_{\text{IN}}$ and $C_{\text{OUT}}$ capacitors. The path to $C_{\text{IN}}$ must be as short as possible.	
PB_DM	17	Α	D- data line. Connect to USB port B connector.	
PB_DP	18	Α	D+ data line. Connect to USB port B connector.	
FREQ/ SYNC	19	Α	Switching Frequency Program and External Clock Input. Connect a resistor from FREQ to GND to set the switching frequency.	
EN/UV	20	А	Enable pin. Precision enable controls the regulator switching action and type-C. Do not float. High = on, Low = off. Can be tied to SENSE directly. Precision enable input allows adjustable UVLO by external resistor divider if tie to IN pin.	
воот	21	Р	Bootstrap capacitor connection. Internally, the BOOT is connected to the cathode of the boost-strap diode. Connect the 0.1-µF bootstrap capacitor from SW to BOOT.	
IN	22	Р	Input power. Connected to external DC supply. Expected range of bypass capacitors is 1 $\mu$ F to 10 $\mu$ F, connect from IN to PGND. Can withstand up to 36 V without damage but operating is suspended if VIN is above the 26-V OVP threshold.	
SW	23	Р	Switching output of the regulator. Internally connected to source of the HS FET and drain of the LS FET. Connect to output inductor.	

(1) A = Analog, P = Power, G = Ground.

### Table 7-2. Pin Functions for TPS25859-Q1 RPQ Package

Table 7-2. Fill Fullictions for 1F325055-Q1 RFQ Fackage				
PIN		TYPE (1)	DESCRIPTION	
NAME	NO.	111 = \	DECORAL FION	
VSET	1	А	Output Voltage Setting. Short to GND to set the 5.17-V output voltage. Float or pull up to $V_{SENSE}$ to set 5.1-V output voltage. Tie to GND through a 40.2-K $\Omega$ resistor to set 5.3-V output voltage. Tie to GND through a 80.6-K $\Omega$ resistor to set 5.4-V output voltage.	
TS	2	Α	Temperature Sense terminal. Connect the TS input to the NTC thermistor.	
BIAS	3	Р	Input of internal bias supply. Must connect to the SENSE pin directly. Power the internal circuit.	
PA_FAULT	4	А	USB Port A Fault Indication. /PA_FAULT indicates overcurrent on PA_BUS or overtemperature conditions. /PA_FAULT is an open drain in normal conditions. Pull /PA_FAULT low during fault conditions.	
PA_EN	5	А	USB Port A Enable pin. To control the USB port A channel load switch ON/OFF. When pull-low, the pin turns off the port A USB power and CC1/2 current and voltage. When pull-high, the pin turns on the port A USB power and CC1/2 current and voltage. Can be tied to SENSE directly to automatically turn on USB port.	
AGND	6	Р	Analog ground terminal. Connect AGND to PGND.	
PA_CC1	7	Α	Connect to Type-C Port A CC1 pin. Analog Input/Output.	
PA_CC2	8	Α	Connect to Type-C Port A CC2 pin. Analog Input/Output.	
ILIM	9	А	Current Limit program. Connect a resistor to set the current limit threshold. Short to GND to set the default 3.55-A current limit.	
PA_BUS	10	Р	Port A BUS output.	
SENSE	11	Р	Output Voltage Sensing, external load on this pin is strictly prohibited. Connect to the other side of the external inductor.	

## Table 7-2. Pin Functions for TPS25859-Q1 RPQ Package (continued)

PIN		<b>7.77</b> (1)	DECODINE SALE	
NAME	NO.	TYPE (1)	DESCRIPTION	
PB_BUS	12	Р	Port B BUS output,	
OUT	13	Р	Output pin. Provide 5.1-V voltage to power external load with max 200-mA capability. The voltage follows the VSET setting.	
PB_CC2	14	Α	Connect to Type-C Port B CC2 pin. Analog Input/Output	
PB_CC1	15	Α	Connect to Type-C Port B CC1 pin. Analog Input/Output	
PGND	16, 24, 25	Р	Power Ground Terminal. Connected to the source of LS FET internally. Connect to system ground, AGND, and the ground side of $C_{\text{IN}}$ and $C_{\text{OUT}}$ capacitors. Path to $C_{\text{IN}}$ must be as short as possible.	
PB_EN	17	А	USB Port B Enable pin. To control the USB port B channel load switch ON/OFF. When pull-low, the pin turns off the port B USB power and CC1/2 current and voltage. When pull-high, the pin turns on the port B USB power and CC1/2 current and voltage. Can be tied to SENSE directly to automatically turn on USB port.	
PB_FAULT	18	Α	USB Port B Fault Indication. /PB_FAULT indicates overcurrent on PB_BUS or overtemperature conditions. /PB_FAULT is an open drain in normal conditions. Pull /PB_FAULT low during fault conditions.	
FREQ/ SYNC	19	А	Switching Frequency Program and External Clock Input. Connect a resistor from FREQ to GND to set the switching frequency.	
EN/UV	20	А	Enable pin. Precision enable controls the regulator switching action and type-C. Do not float. High = on, Low = off. Can be tied to SENSE directly. Precision enable input allows adjustable UVLO by external resistor divider if tie to IN pin.	
воот	21	Р	Bootstrap capacitor connection. Internally, the BOOT is connected to the cathode of the booststrap diode. Connect the 0.1-µF bootstrap capacitor from SW to BOOT.	
IN	22	Р	Input power. Connected to external DC supply. Expected range of bypass capacitors is 1 $\mu$ F to 10 $\mu$ F. Connect from IN to PGND. Withstand up to 36 V without damage but operating is suspended if VIN is above the 26-V OVP threshold.	
SW	23	Р	Switching output of the regulator. Internally connected to source of the HS FET and drain of the LS FET. Connect to output inductor.	

<sup>(1)</sup> A = Analog, P = Power, G = Ground.



## 8 Specifications

## 8.1 Absolute Maximum Ratings

Over the recommended operating junction temperature range of -40 $^{\circ}$ C to +150 $^{\circ}$ C and AGND = PGND (unless otherwise noted)<sup>(1)</sup>

	PARAMETER	MIN	MAX	UNIT	
	IN to PGND	-0.3	40 <sup>(2)</sup>		
	IN to SW	-0.3	35		
	BIAS, SENSE to PGND	-0.3	6		
Input voltage	EN to AGND	-0.3	11	V	
Input voltage	FREQ/SYNC to AGND	-0.3	6	V	
	PA_EN, PB_EN to AGND	-0.3	6		
	VSET, ILIM to AGND	-0.3	6		
	AGND to PGND	-0.3	0.3		
	SW to PGND	-0.3	35		
Output voltage	SW to PGND (less than 10 ns transients)	-3.5	35	V	
Output voltage	BOOT to SW	-0.3	6		
	PA_BUS, PB_BUS, OUT to PGND	-0.3	6		
	CC1, CC2 to AGND	-0.3	6		
Voltago rango	DP, DM to AGND	-0.3	6	V	
Voltage range	TS to AGND	-0.3	6		
	PA_FAULT, PB_FAULT to AGND	-0.3	6	V	
Pin positive sink current, I <sub>SNK</sub>	CC1, CC2 (while applying VCONN)		1	Α	
I/O current	DP to DM in BC1.2 DCP Mode	-35	35	mA	
T <sub>J</sub>	Junction temperature	-40	150	°C	
T <sub>stg</sub>	Storage temperature	-65	150	°C	

<sup>(1)</sup> Stresses beyond those listed under Absolute Maximum Rating may cause permanent damage to the device. These are stress ratings only, which do not imply functional operation of the device at these or any other conditions beyond those indicated under Recommended Operating Condition. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability.

## 8.2 ESD Ratings

				VALUE	UNIT
		Human body model (HBM), per AEC	Q100-002 <sup>(1)</sup>	±2000 <sup>(2)</sup>	
V <sub>(ESD)</sub>	V <sub>(ESD)</sub> Electrostatic discharge	Charged device model (CDM), per	Corner pins	±750 <sup>(3)</sup>	V
		AEC Q100-011	Other pins	±750 <sup>(3)</sup>	

<sup>(1)</sup> AEC Q100-002 indicates that HBM stressing shall be in accordance with the ANSI/ESDA/JEDEC JS-001 specification.

<sup>(2)</sup> VIN rising slew rate below 20V/ms if in 0V to 40V transient, room temperature, max 500uF cap at SENSE

<sup>(2)</sup> The passing level per AEC-Q100 Classification H2.

<sup>(3)</sup> The passing level per AEC-Q100 Classification C5



## 8.3 Recommended Operating Conditions

Over the recommended operating junction temperature range of -40°C to 150°C. Voltages are with respect to GND (unless otherwise noted)

	,		MIN	NOM MAX	UNIT
		IN to PGND	5.5	26	
		EN	0	VSENSE	
VI	Input voltage	TS	0	VSENSE	V
		FREQ/SYNC when driven by external clock	0	3.3	
		PA_EN, PB_EN	0	VSENSE	
V <sub>PU</sub>	Pull up voltage	PA_FAULT, PB_FAULT	0	VSENSE	V
Vo	Output voltage	PA_BUS, PB_BUS, OUT	5	5.5	V
		PA_BUS, PB_BUS	0	3	Α
Io	Output current	OUT	0	0.2	Α
		DP to DM Continuous current in BC1.2 DCP Mode	<b>–15</b>	15	
I <sub>SRC</sub>	Source current	CC1 or CC2 source current when supplying VCONN		250	mA
		R <sub>VSET</sub>	0	100	kΩ
R <sub>EXT</sub>	External resistnace	R <sub>ILIM</sub>	0	100	kΩ
		R <sub>FREQ</sub>	0	100	kΩ
C <sub>EXT</sub>	External capacitance	Своот		0.1	uF
TJ		Operating junction temperature	-40	150	°C



#### 8.4 Thermal Information

		TPS2585x-Q1	
	THERMAL METRIC <sup>(1)</sup> (2)	RPQ (VQFN)	UNIT
		25 PINS	
$R_{\theta JA}$	Junction-to-ambient thermal resistance	37.7	°C/W
R <sub>0JC(top)</sub>	Junction-to-case (top) thermal resistance	17.2	°C/W
R <sub>0JB</sub>	Junction-to-board thermal resistance	8.8	°C/W
$\Psi_{JT}$	Junction-to-top characterization parameter	0.3	°C/W
$\Psi_{JB}$	Junction-to-board characterization parameter	8.8	°C/W
$R_{\theta JC(bot)}$	Junction-to-case (bottom) thermal resistance	20.3	°C/W

<sup>(1)</sup> For more information about traditional and new thermal metrics, see the Semiconductor and IC Package Thermal Metrics application report.

#### 8.5 Electrical Characteristics

Limits apply over the recommended operating junction temperature ( $T_J$ ) range of -40°C to +150°C;  $V_{IN}$  = 13.5 V,  $f_{SW}$  = 400 kHz, VSET short to GND unless otherwise stated. Minimum and maximum limits are specified through test, design or statistical correlation. Typical values represent the most likely parametric norm at  $T_J$  = 25°C, and are provided for reference purposes only.

	PARAMETER	TEST CONDITIONS	MIN	TYP	MAX	UNIT
SUPPLY VOLTA	AGE (IN PIN)					
I <sub>SD</sub>	Shutdown quiescent current; measured at IN pin.	VEN/UV = 0, -40°C ≤ T <sub>J</sub> ≤ 85°C		34	63	uA
IQ	Operating quiescent current (DCDC disable)	V <sub>EN</sub> = V <sub>SENSE</sub> , CCx = open, -40°C ≤ T <sub>J</sub> ≤ 85°C			200	μA
V <sub>OVLO_R</sub>	Voltage on VIN pin when buck regulator stops switching		26.6	27.5	28.4	V
V <sub>OVLO_HYS</sub>	Hysteresis			0.5		V
ENABLE AND U	JVLO (EN/UVLO PIN)					
V <sub>EN/UVLO_R</sub>	Rising threshold for not in External UVLO	V <sub>EN/UV</sub> rising threshold	1.26	1.3	1.34	V
V <sub>EN/UVLO_HYS</sub>	Hysteresis	V <sub>EN/UVLO</sub> falling		100		mV
V <sub>PA/B_EN_H</sub>	PA_EN, PB_EN input level required to turn on PA_BUS and PB_BUS Load Switch (TPS25859-Q1)	V <sub>PA_EN</sub> or V <sub>PB_EN</sub> rising threshold		1.6	1.98	V
V <sub>PA/B_EN_L</sub>	PA_EN, PB_EN input level required to turn off PA_BUS and PB_BUS Load Switch (TPS25859-Q1)	V <sub>PA_EN</sub> or V <sub>PB_EN</sub> falling threshold	0.97	1.5		V
V <sub>EN1/2_HYS</sub>	Hysteresis(TPS25859-Q1)	V <sub>PA_EN</sub> or V <sub>PB_EN</sub> falling threshold		100		mV
BOOTSTRAP						
V <sub>BTST_UVLO</sub>	Bootstrap voltage UVLO threshold			2.2		V
R <sub>BOOT</sub>	Bootstrap pull-up resistence	VSENSE - BOOT = 0.1 V		7.7		Ω
BUCK REGULA	TOR					
I <sub>L-SC-HS</sub>	High-side current limit	BOOT - SW = 5 V	10.2	11.4	12.6	Α
I <sub>L-SC-LS</sub>	Low-side current limit	SENSE = 5 V	8.5	10	11.5	Α
I <sub>L-NEG-LS</sub>	Low-side negative current limit	SENSE = 5 V	-7	-5	-3	Α
I <sub>ZC</sub>	Zero current detector threshold			0.01		Α

Submit Document Feedback

Copyright © 2021 Texas Instruments Incorporated

<sup>(2)</sup> Power rating at a specific ambient temperature T<sub>A</sub> should be determined with a maximum junction temperature of 150 °C.



## 8.5 Electrical Characteristics (continued)

Limits apply over the recommended operating junction temperature ( $T_J$ ) range of -40°C to +150°C;  $V_{IN}$  = 13.5 V,  $f_{SW}$  = 400 kHz, VSET short to GND unless otherwise stated. Minimum and maximum limits are specified through test, design or statistical correlation. Typical values represent the most likely parametric norm at  $T_J$  = 25°C, and are provided for reference

purposes only.

	PARAMETER	TEST CONDITIONS	MIN	TYP	MAX	UNIT
		CC1 or CC2 pulldown resistance = $R_d$ , VSET float or pull up to $V_{SENSE}$ , $T_J$ = $25^{\circ}C$	-1%	5.1	+1%	V
$V_{SENSE}$	BUCK Output voltage	CC1 or CC2 pulldown resistance = R <sub>d</sub> , VSET short to AGND, T <sub>J</sub> =25°C	-1%	5.17	+1%	V
		CC1 or CC2 pulldown resistance = $R_d$ , $R_{VSET}$ =40.2 $K\Omega$ , $T_J$ =25°C	-1%	5.3	+1%	V
		CC1 or CC2 pulldown resistance = $R_d$ , $R_{VSET}$ =80.6 $K\Omega$ , $T_J$ =25°C	-1%	5.4	+1%	V
V <sub>SENSE</sub>	BUCK Output voltage accuracy	CC1 or CC2 pulldown resistance = R <sub>d</sub> , -40°C≤ T <sub>J</sub> ≤150°C	-2		2	%
V <sub>DCDC_UVLO_R</sub>	SENSE input level to enable DCDC switching	V <sub>SENSE</sub> rising, CC1 or CC2 pull down resistance = R <sub>d</sub>	3.85	4	4.15	V
V <sub>DCDC_UVLO_HYS</sub>	Hysteresis	V <sub>SENSE</sub> falling, CC1 or CC2 pull down resistance = R <sub>d</sub>		0.4		V
V <sub>DROP</sub>	Dropout voltage ( V <sub>IN</sub> - V <sub>SENSE</sub> )	V <sub>IN</sub> = V <sub>SENSE</sub> + V <sub>DROP</sub> , V <sub>SENS</sub> = 5.1 V, I <sub>PA_BUS</sub> = 3 A, I <sub>PB_BUS</sub> = 3 A		300		mV
R <sub>DS-ON-HS</sub>	High-side MOSFET ON-resistance	$I_{PA\_BUS} = 3 \text{ A, } I_{PB\_BUS} = 3 \text{ A, BOOT -} $ SW = 5 V, -40°C≤ $T_J$ ≤150°C		18	34	mΩ
R <sub>DS-ON-LS</sub>	Low-side MOSFET ON-resistance	I <sub>PA_BUS</sub> = 3 A, I <sub>PB_BUS</sub> = 3 A, V <sub>SENSE</sub> = 5 V, -40°C≤ T <sub>J</sub> ≤150°C		9.5	18.5	mΩ
POWER SWITCH A	AND CURRENT LIMIT			-		
R <sub>DS-ON_USB</sub>	USB Load Switch MOSFET ON- resistance	I <sub>PA_BUS</sub> = 3 A, I <sub>PB_BUS</sub> = 3 A; -40°C≤T <sub>J</sub> ≤150°C		6.8	11.73	mΩ
R <sub>DS-ON_OUT</sub>	OUT Load Switch MOSFET ON- resistance	I <sub>OUT</sub> = 0.3 A		230		mΩ
R <sub>DS-ON_VCONN</sub>	On-state resistance	T <sub>J</sub> = 25°C, I <sub>CCn</sub> = 0.25 A		410	550	mΩ
R <sub>DS-ON_VCONN</sub>	On-state resistance	-40°C ≤T <sub>J</sub> ≤ 150°C, I <sub>CCn</sub> = 0.25 A		410	740	mΩ
V <sub>USBLS_UVLO_R</sub>	Voltage on SENSE pin that will enable the USB Load Switch		3.95	4.1	4.25	V
V <sub>USBLS_UVLO_HYS</sub>	Hysteresis			200		mV
R <sub>BUS_DCHG</sub>	Discharge resistance for Port A or Port B BUS	Apply 5V on PA_BUS or PB_BUS, CC1 or CC2 = Rd	250	500	750	Ω
V <sub>TH_R_BUS_DCHGb</sub>	Rising threshold voltage for BUS not discharged		670	700	730	mV
V <sub>TH_HYS_BUS_DCHG</sub>	Hysteresis			100		mV
V <sub>BUS_DCHG_BLEED</sub>	BUS bleed resistance	V <sub>Px_BUS</sub> = 4 V, No sink termination on CC lines, Time>t <sub>W_BUS_DCHG</sub>	100	150	200	ΚΩ
		R <sub>ILIM</sub> = 48.7 KΩ	849	1061	1273	mA
		R <sub>ILIM</sub> = 19.1 KΩ	2434	2704	2974	mA
		R <sub>ILIM</sub> = 15.4 KΩ	3018	3354	3689	mA
	BUS output short-circuit secondary	R <sub>ILIM</sub> = 12.4 KΩ	3748	4165	4581	mA
I <sub>OS_HI</sub>	current limit	R <sub>ILIM</sub> = 11.5 KΩ	4040	4490	4938	mA
		R <sub>ILIM</sub> = 9.53 KΩ	4876	5418	5960	mA
		$R_{ILIM} = 0 \Omega(\text{short to GND})$	4828	5680	6532	mA
		R <sub>ILIM</sub> = 11.5 KΩ, T <sub>J</sub> =25°C	4265	4490	4714	mA

### 8.5 Electrical Characteristics (continued)

Limits apply over the recommended operating junction temperature ( $T_J$ ) range of -40°C to +150°C;  $V_{IN}$  = 13.5 V,  $f_{SW}$  = 400 kHz, VSET short to GND unless otherwise stated. Minimum and maximum limits are specified through test, design or statistical correlation. Typical values represent the most likely parametric norm at  $T_J$  = 25°C, and are provided for reference purposes only.

purposes only.	PARAMETER	TEST CONDITIONS	MIN	TYP	MAX	UNIT
		R <sub>ILIM</sub> = 48.7 KΩ	530.4	663	800	mA
		R <sub>ILIM</sub> = 19.1 KΩ	1521	1690	1859	mA
		R <sub>ILIM</sub> = 15.4 KΩ	1886.4	2096	2305.6	mA
		R <sub>ILIM</sub> = 12.4 KΩ	2342.7	2603	2863.3	mA
los_Bus	BUS output short-circuit current limit	R <sub>ILIM</sub> = 11.5 KΩ	2525.4	2806	3086.6	mA
		RILIM = 9.53 KΩ	3047.4	3386	3724.6	mA
		$R_{ILIM} = 0 \Omega(\text{short to GND})$	3017.5	3550	4082.5	mA
		R <sub>ILIM</sub> =11.5 KΩ, T <sub>J</sub> =25°C	2666	2806	2946	mA
I <sub>OS_OUT</sub>	OUT output short-circuit current limit	Short circuit current limit	390	450	495	mA
I <sub>OS_VCONN</sub>	VCONN output short-circuit current limit	Short circuit current limit	240	300	360	mA
CABLE COMP	ENSATION VOLTAGE				'	
V <sub>DROP_COM</sub>	Cable compensation voltage	I <sub>PA_BUS</sub> or I <sub>PB_BUS</sub> = 2.4 A, VSET = GND(set 5.17 V output)	70	90	110	mV
CC CONNECT	MANAGEMENT					
I <sub>SRC_CC_3A</sub>	Sourcing current	CC pin voltage: 0 V ≤ V <sub>CCn</sub> ≤ 2.45 V	304	330	356	μΑ
I <sub>SRC_CC_1.5A</sub>	Sourcing current in thermal management(Temp warm)	CC pin voltage: $0 \text{ V} \le \text{V}_{\text{CCn}} \le 1.5 \text{ V}$ , $\text{T}_{\text{A}} > 85^{\circ}\text{C}$	167	180	194	μΑ
I <sub>SRC_CC_DFLT</sub>	Sourcing current in thermal management(Temp hot)	CC pin voltage: $0 \text{ V} \le \text{V}_{CCn} \le 1.5 \text{ V}$ , $T_A > 85^{\circ}\text{C}$	64	80	105	μΑ
I <sub>REV</sub>	Reverse leakage current	CCx is the CC pin under test, CCy is the other CC pin. CC pin voltage VCCx = 5.5 V, CCy floating, $V_{EN\_UV}$ = 0 V or $V_{SENSE}$ , 0 V $\leq$ $V_{IN}$ $\leq$ 26 V $I_{REV}$ is current into CCx pin		2.75	10	μΑ
V <sub>TH_R</sub>	Rising threshold voltage for VCONN not discharged	CC pin that was providing VCONN in previous SINK state	670	700	730	mV
V <sub>TH_HYS</sub>	Hysteresis			100		mV
FAULT (TPS25	859-Q1)					
V <sub>OL</sub>	PA_FAULT, PB_FAULT Output low voltage	I <sub>SNK_PIN</sub> = 1 mA			250	mV
I <sub>OFF</sub>	PA_FAULT, PB_FAULT Off-state leakage	V <sub>PIN</sub> = 5.5 V			2.2	μΑ
BC 1.2 DOWNS	STREAM CHARGING PORT (TPS25858-C	21)			'	
R <sub>DPM_SHORT</sub>	DP and DM shorting resistance			70	200	Ω
DIVIDER 3 MO	DE (TPS25858-Q1)				'	
V <sub>DP_DIV3</sub>	DP output voltage		2.57	2.7	2.84	V
V <sub>DM_DIV3</sub>	DM output voltage		2.57	2.7	2.84	V
R <sub>DP_DIV3</sub>	DP output impedance	I <sub>DP_IN</sub> = -5 μA	24	30	36	kΩ
R <sub>DM_DIV3</sub>	DM output impedance	I <sub>DM_IN</sub> = -5 μA	24	30	36	kΩ
1.2-V MODE (T	PS25858-Q1)					
V <sub>DP_1.2V</sub>	DP output voltage		1.12	1.2	1.26	V
V <sub>DM_1.2V</sub>	DM output voltage		1.12	1.2	1.26	V
R <sub>DP_1.2V</sub>	DP output impedance	I <sub>DP_IN</sub> = -5 μA	84	100	126	kΩ
R <sub>DM_1.2V</sub>	DM output impedance	I <sub>DM_IN</sub> = -5 μA	84	100	126	kΩ



### 8.5 Electrical Characteristics (continued)

Limits apply over the recommended operating junction temperature ( $T_J$ ) range of -40°C to +150°C;  $V_{IN}$  = 13.5 V,  $f_{SW}$  = 400 kHz, VSET short to GND unless otherwise stated. Minimum and maximum limits are specified through test, design or statistical correlation. Typical values represent the most likely parametric norm at  $T_J$  = 25°C, and are provided for reference purposes only.

	PARAMETER	TEST CONDITIONS	MIN	TYP	MAX	UNIT
FREQ/SYNC TH	RESHOLD					
V <sub>IH_FREQ/SYNC</sub>	FREQ/SYNC high threshold for external clock synchronization	Amplitude of SYNC clock AC signal (measured at FREQ/SYNC pin)	2			V
V <sub>IL_FREQ/SYNC</sub>	FREQ/SYNC low threshold for external clock synchronization	Amplitude of SYNC clock AC signal (measured at FREQ/SYNC pin)			0.8	V
TEMPERATURE	SENSING		•			
V <sub>WARN_HIGH</sub>	Temperature warning threshold rising	As percentage to V <sub>SENSE</sub>	0.475	0.5	0.525	V/V
V <sub>WARN_HYS</sub>	Hysteresis	As percentage to V <sub>SENSE</sub>		0.1		V/V
V <sub>HOT_HIGH</sub>	Temperature Hot assert threshold rising to reduce SENS voltage	As percentage to V <sub>SENSE</sub>	0.618	0.65	0.683	V/V
V <sub>HOT_HYS</sub>	Hysteresis	As percentage to V <sub>SENSE</sub>		0.1		V/V
V <sub>R_VSENS</sub>	V <sub>SENSE</sub> voltage decay when Temperature Hot assert	TS pin voltage rise above 0.65 * V <sub>SENSE</sub>	4.77			V
THERMAL SHU	TDOWN					
<b>T</b>	LISP Load Switch Over Temperature	Shutdown threshold		160		°C
T <sub>LS_SD</sub>	USB Load Switch Over Temperature	Recovery threshold		150		°C
т	Thermal shutdown	Shutdown threshold	16			°C
$T_{SD}$	mermai shutdown	Recovery threshold		154		°C

## 8.6 Timing Requirements

Over the recommended operating junction temperature range of -40 °C to 150 °C (unless otherwise noted)

			MIN	NOM	MAX	UNIT
BUS DISCHA	RGE					
t <sub>DEGA_BUS_DC</sub>	Discharge asserting deglitch		5.6	12.3	21.2	ms
tw_BUS_DCHG	V <sub>BUS</sub> discharge time after sink termination removed from CC lines	V <sub>BUS</sub> = 1 V, time I <sub>SNK_OUT</sub> > 1 mA after sink termination removed from CC lines	170	260	360	ms
POWER SWIT	CH TIMING					
t <sub>IOS_HI_DEG</sub>	Deglitch time for USB power switch current limit enable	USB port enter overcurrent (per ILIM setting)	1.228	2.048	2.867	ms
t <sub>IOS_HI_RST</sub>	MFI OCP reset timing		9.6	16	22.4	ms
t <sub>r_USB</sub>	PA_BUS, PB_BUS voltage rise time	$C_L$ = 1 $\mu F,R_L$ = 100 $\Omega$ (measured from 10% to 90% of final value)		1.67		ms
t <sub>f_USB</sub>	PA_BUS, PB_BUS voltage fall time	$C_L$ = 1 $\mu F,R_L$ = 100 $\Omega$ (measured from 90% to 10% of final value)		0.49		ms
t <sub>on_USB</sub>	PA_BUS, PB_BUS voltage turnon-time	$C_L = 1 \mu F, R_L = 100 \Omega$		2.59		ms
t <sub>off_USB</sub>	PA_BUS, PB_BUS voltage turnoff-time	$C_L = 1 \mu F, R_L = 100 \Omega$		2.07		ms
t <sub>IOS_USB</sub>	PA_BUS, PB_BUS short-circuit response time	$C_L = 1 \mu F, R_L = 1 \Omega$		1		us
t <sub>r_OUT</sub>	OUT voltage rise time	$C_L$ = 1 μF, $R_L$ = 100 $\Omega$ (measured from 10% to 90% of final value)	0.12	0.2	0.28	ms
t <sub>f_OUT</sub>	OUT voltage fall time	$C_L$ = 1 $\mu F, R_L$ = 100 $\Omega$ (measured from 90% to 10% of final value)	0.16	0.22	0.28	ms
t <sub>on_OUT</sub>	OUT voltage turnon-time	$C_L = 1 \mu F, R_L = 100 \Omega$	0.6	1.1	1.65	ms
t <sub>off_OUT</sub>	OUT voltage turnoff-time	$C_L = 1 \mu F, R_L = 100 \Omega$	0.45	0.54	0.62	ms



## 8.6 Timing Requirements (continued)

Over the recommended operating junction temperature range of -40 °C to 150 °C (unless otherwise noted)

			MIN	NOM	MAX	UNIT
t <sub>IOS_OUT</sub>	OUT short-circuit response time	$C_L = 1 \mu F, R_L = 1 \Omega$		1.4	4	us
t <sub>IOS_VCONN</sub>	CC-VCONN short circuit response time	$C_L = 1 \mu F, R_L = 1 \Omega$		1	3.5	μs
t <sub>r_VCONN</sub>	VCONN output voltage rise time	$C_L$ = 1 μF, $R_L$ = 100 $\Omega$ (measured from 10% to 90% of final value); 5.1K $\Omega$ on CC1 and 1K $\Omega$ on CC2	0.2	0.28	0.36	ms
t <sub>f_VCONN</sub>	VCONN output voltage fall time	$C_L$ = 1 μF, $R_L$ = 100 $\Omega$ (measured from 90% to 10% of final value); 5.1K $\Omega$ on CC1 and 1K $\Omega$ on CC2	0.18	0.23	0.28	ms
t <sub>on_VCONN</sub>	VCONN output voltage turnon time	$C_L$ = 1 μF, $R_L$ = 100 $\Omega$ ; 5.1K $\Omega$ on CC1 and 1K $\Omega$ on CC2	0.7	1.2	1.7	ms
t <sub>off_VCONN</sub>	VCONN output voltage turnoff time	$C_L$ = 1 μF, $R_L$ = 100 $\Omega$ ; 5.1K $\Omega$ on CC1 and 1K $\Omega$ on CC2	0.37	0.44	0.51	ms
HICCUP MO	DE					
T <sub>HICP_ON</sub>	OUT, PA_BUS, PB_BUS output hiccup mode ON time	OC, V <sub>OUT</sub> , V <sub>PA_BUS</sub> , V <sub>PB_BUS</sub> drop 10%	2.94	4.1	5.42	ms
T <sub>HICP_OFF</sub>	OUT, PA_BUS, PB_BUS output hiccup mode OFF time	OC, OUT, PA_BUS, PB_BUS connect to GND	367	524	715	ms

## 8.7 Switching Characteristics

Over the recommended operating junction temperature range of -40 °C to 150 °C (unless otherwise noted)

PARAMETER		TEST CONDITIONS	MIN	TYP	MAX	UNIT
SW (SW PIN)						
T <sub>ON_MIN</sub>	Minimum turnon-time			84		ns
T <sub>ON_MAX</sub>	Maximum turnon-time, HS timeout in dropout			6		μs
T <sub>OFF_MIN</sub>	Minimum turnoff time			81		ns
D <sub>max</sub>	Maximum switch duty cycle			98		%
TIMING RESISTO	R AND INTERNAL CLOCK					
f <sub>SW_RANGE</sub>	Switching frequency range using FREQ mode	9 kΩ ≤ R <sub>FREQ</sub> ≤ 99 kΩ	200		800	kHz
f	Out to bin or for more or	$R_{FREQ} = 80.6 \text{ k}\Omega$	228	253	278	kHz
$f_{SW}$	Switching frequency	$R_{FREQ}$ = 49.9 k $\Omega$	360	400	440	kHz
FS <sub>SS</sub>	Frequency span of spread spectrum operation			±6		%
EXTERNAL CLO	CK(SYNC)					
f <sub>FREQ/SYNC</sub>	Switching frequency using external clock on FREQ/SYNC pin		200		800	kHz
T <sub>SYNC_MIN</sub>	Minimum SYNC input pulse width	f <sub>SYNC</sub> = 400kHz, V <sub>FREQ/SYNC</sub> > V <sub>IH_FREQ/SYNC</sub> , V <sub>FREQ/SYNC</sub> < V <sub>IL_FREQ/SYNC</sub>		100		ns
T <sub>LOCK_IN</sub>	PLL lock time			100		μs
t <sub>DEGA_CC_ATT_DETM</sub>	Attach asserting deglitch in the Detached Mode		1.29	2.05	3.05	ms
t <sub>DEGA_CC_DETACH_S</sub>	Detach asserting deglitch for exiting SINK Mode		8.2	12.5	18	ms
t <sub>DEGA_CC_SHORT</sub>	Detach, Rd and Ra asserting deglitch		92	192	339	μs
t <sub>DEGA_CC_LONG</sub>	Long deglitch		103	148	200	ms


Submit Document Feedback

Copyright © 2021 Texas Instruments Incorporated




### 8.8 Typical Characteristics

Unless otherwise specified the following conditions apply:  $V_{IN}$  = 13.5 V,  $f_{SW}$  = 400 kHz, L = 3.3  $\mu$ H,  $C_{SENSE}$  = 141  $\mu$ F,  $C_{PA\_BUS}$  = 1  $\mu$ F,  $C_{PB\_BUS}$  = 1  $\mu$ F,  $T_A$  = 25 °C.





Unless otherwise specified the following conditions apply:  $V_{IN}$  = 13.5 V,  $f_{SW}$  = 400 kHz, L = 3.3  $\mu$ H,  $C_{SENSE}$  = 141  $\mu$ F,  $C_{PA\_BUS}$  = 1  $\mu$ F,  $C_{PB\_BUS}$  = 1  $\mu$ F,  $T_A$  = 25 °C.



Unless otherwise specified the following conditions apply:  $V_{IN}$  = 13.5 V,  $f_{SW}$  = 400 kHz, L = 3.3  $\mu$ H,  $C_{SENSE}$  = 141  $\mu$ F,  $C_{PA\_BUS}$  = 1  $\mu$ F,  $C_{PB\_BUS}$  = 1  $\mu$ F,  $C_{A}$  = 25 °C.




Figure 8-17. USB Power Switch On Resistance vs Junction

**Temperature** 

Figure 8-18. OUT Power Switch On Resistance vs Junction

**Temperature** 

Unless otherwise specified the following conditions apply:  $V_{IN}$  = 13.5 V,  $f_{SW}$  = 400 kHz, L = 3.3  $\mu$ H,  $C_{SENSE}$  = 141  $\mu$ F,  $C_{PA\_BUS}$  = 1  $\mu$ F,  $C_{PB\_BUS}$  = 1  $\mu$ F,  $T_A$  = 25 °C.






Figure 8-19. V<sub>CONN</sub> Power Switch On Resistance vs Junction Temperature



 $R_{FREQ} = 49.9 \text{ k}\Omega$ 

Figure 8-20. Switching Frequency vs Junction Temperature



 $R_{FREQ} = 8.45 \text{ k}\Omega$ 





Figure 8-22. CC Sourcing Current vs Junction Temperature






Figure 8-23. TS Temperature Wam Threshold vs Junction Temperature





Figure 8-24. TS Temperature Hot Threshold vs Junction Temperature




Unless otherwise specified the following conditions apply:  $V_{IN}$  = 13.5 V,  $f_{SW}$  = 400 kHz, L = 3.3  $\mu$ H,  $C_{SENSE}$  = 141  $\mu$ F,  $C_{PA\_BUS}$  = 1  $\mu$ F,  $C_{PB\_BUS}$  = 1  $\mu$ F,  $T_A$  = 25 °C.





## **9 Parameter Measurement Information**





## 10 Detailed Description

#### 10.1 Overview

The TPS2585x-Q1 is a full-featured solution for implementing a compact USB charging port with support for both Type-C and BC1.2 standards. The device contains an efficient buck regulator power source. For dual Type-C ports, the TPS2585x-Q1 is capable of providing up to 6.6 A of output current at 5.17 V (nominal), 3 A for each Type-C port, 200 mA for the OUT pin, and 200 mA for each VCONN power. The TPS2585x-Q1 is an automotive-focused USB charging controller and offers a robust solution, so TI recommends to add adequate protection (TVS3300 equivalent or better but auto qualified) on the IN pin to protect systems from high-power transients or lightning strikes.

System designers can optimize efficiency or solution size through careful selection of switching frequency in the range of 200 KHz–450 KHz with sufficient margin to operate below the AM radio frequency band. The TPS2585x-Q1 protects itself with internal thermal sensing circuits that monitor the operating temperature of the junction and disables operation if the temperature exceeds the thermal shutdown threshold. In high ambient temperature application, the 6.6-A output current capability is not assured. In the TPS2585x-Q1, the buck regulator operates in forced PWM mode, ensuring fixed switching frequency regardless of load current. Spread-spectrum frequency dithering reduces harmonic peaks of the switching frequency, potentially simplifying EMI filter design and easing compliance.


Current sensing through a precision FET current sense amplifier on the USB port enables an accurate, user-programmable overcurrent limit setting, and linear cable compensation to overcome IR losses when powering remote USB ports.

The TPS2585x-Q1 includes a TS input for user-programmable thermal protection using a negative temperature coefficient (NTC) resistor.

The device can support the USB Type-C protocol. The TPS25858-Q1 also supports the legacy Battery Charging Specification Rev 1.2 (BC1.2) DCP mode with an auto-detect feature to charge not only BC1.2-compliant handheld devices, but also popular phones and tablets that incorporate their own propriety charging algorithm. The TPS25859-Q1 can enable each port individually and can report fault condition for each port.



## 10.2 Functional Block Diagram



#### 10.3 Feature Description

#### 10.3.1 Power-Down or Undervoltage Lockout

The device is in low power mode if the IN terminal voltage is less than VUVLO, so the part is considered *dead* and all the terminals are high impedance. Once the IN voltage rises above the VUVLO threshold, the IC enters sleep mode or active mode, depending on the EN/UVLO voltage.

The voltage on the EN/UVLO pin controls the ON/OFF operation of the TPS2585x-Q1. An EN/UVLO pin voltage higher than  $V_{\text{EN/UVLO-H}}$  is required to start the internal regulator and begin monitoring the CCn lines for a valid Type-C connection. The internal USB monitoring circuitry is on when  $V_{\text{IN}}$  is within the operation range and the EN/UVLO threshold is cleared. For TPS25858-Q1, the buck regulator and the USB ports load switch remains OFF until a valid Type-C detection has been made. For TPS25859-Q1, the buck regulator starts to operate, however, the USB ports load switch remains OFF until a valid Type-C detection has been made. This feature ensures the *cold socket* (0 V) USB Type-C  $V_{\text{BUS}}$  requirement is met.

The EN/UVLO pin is an input and cannot be left open or floating. The simplest way to enable the operation of the TPS2585x-Q1 is to connect EN to SENSE. This connection allows self-startup of the TPS2585x-Q1 when  $V_{IN}$  is within the operation range. Note that you cannot connect the EN to IN pin directly for self-startup.

Many applications benefit from the employment of enable dividers,  $R_{ENT}$  and  $R_{ENB}$ , to establish a precision system UVLO level for the TPS2585x-Q1 shown in Figure 10-1. The system UVLO can be used for sequencing, ensuring reliable operation, or supply protection, such as a battery discharge level. To ensure the USB port  $V_{BUS}$  is within the 5-V operating range as required for USB compliance (for the latest USB specifications and requirements, refer to USB.org), TI suggests that the  $R_{ENT}$  and  $R_{ENB}$  resistors be chosen such that the TPS2585x-Q1 enables when  $V_{IN}$  is approximately 6 V. Considering the dropout voltage of the buck regulator and IR losses in the system, 6 V provides adequate margin to maintain  $V_{BUS}$  within USB specifications. If system requirements, such as a warm crank (start) automotive scenario, require operation with  $V_{IN}$  < 6 V, the values of  $R_{ENT}$  and  $R_{ENB}$  can be calculated assuming a lower  $V_{IN}$ . An external logic signal can also be used to drive the EN/UVLO input when a microcontroller is present and it is desirable to enable or disable the USB port remotely for other reasons.




Figure 10-1. System UVLO by Enable Divider

UVLO configuration using external resistors is governed by the following equations:

$$R_{ENT} = \left(\frac{V_{IN(ON)}}{V_{EN/UVLO_{-}H}} - 1\right) \times R_{ENB}$$
(1)

$$V_{IN(OFF)} = V_{IN(ON)} \times \left(1 - \frac{V_{EN/UVLO\_HYS}}{V_{EN/UVLO\_H}}\right)$$
(2)

For example:

 $V_{IN(ON)} = 6 V$ 

 $R_{ENT} = 20 k\Omega$ 



$$R_{ENB} = \left[ \left( V_{EN-VOUT-H} \right) / \left( V_{IN(ON)} - V_{EN} \right) \right] \times R_{ENT}$$
(3)

 $R_{ENB} = 5 k\Omega$ 

Therefore,  $V_{IN(OFF)} = 5.5 \text{ V}$ 

### 10.3.2 Input Overvoltage Protection (OVP) - Continuously Monitored

The operation voltage range of the TPS2585x-Q1 is up to 26 V. If the input source applies an overvoltage, the buck regulator HSFET/LSFET turns off immediately. Thus, the USB ports and OUT pin loses their power as well. Once the overvoltage returns to a normal voltage, the buck regulator continues switching and provides power on the USB ports and OUT pin.

During the overvoltage condition, the internal regulator regulates the SENSE voltage at 5 V, so the SENSE always has power for the internal bias circuit and external NTC pullup reference.

#### 10.3.3 Buck Converter

The following operating description of the TPS2585x-Q1 refers to the *Functional Block Diagram*. The TPS2585x-Q1 integrates a monolithic, synchronous, rectified, step-down, switch-mode converter with internal power MOSFETs and USB current-limit switches with charging ports auto-detection.

The TPS2585x-Q1 offers a compact solution that achieves up to 6.6 A of continuous output current with excellent load and line regulation over a wide input supply range. The TPS2585x-Q1 supplies a regulated output voltage by turning on the high-side (HS) and low-side (LS) NMOS switches with controlled duty cycle. During high-side switch ON time, the SW pin voltage swings up to approximately  $V_{IN}$ . The inductor current  $i_L$  increases with linear slope ( $V_{IN} - V_{OUT}$ ) / L. When the HS switch is turned off by the control logic, the LS switch is turned on after an anti-shoot-through dead time. Inductor current discharges through the LS switch with a slope of  $-V_{OUT}$  / L. The control parameter of a buck converter is defined as Duty Cycle D =  $t_{ON}$  /  $T_{SW}$ , where  $t_{ON}$  is the high-side switch ON time and  $T_{SW}$  is the switching period, shown in Figure 10-2. The regulator control loop maintains a constant output voltage by adjusting the duty cycle D. In an ideal buck converter, where losses are ignored, D is proportional to the output voltage and inversely proportional to the input voltage: D =  $V_{OUT}$  /  $V_{IN}$ .




Figure 10-2. SW Node and Inductor Current Waveforms in Continuous Conduction Mode (CCM)

The TPS2585x-Q1 operates in a fixed-frequency, peak-current-mode control to regulate the output voltage. A voltage feedback loop is used to get accurate DC voltage regulation by adjusting the peak current command based on voltage offset. The peak inductor current is sensed from the high-side switch and compared to the peak current threshold to control the ON time of the high-side switch. The voltage feedback loop is internally compensated, which allows for fewer external components, making it easy to design, and provides stable operation with a reasonable combination of output capacitors. The TPS2585x-Q1 operates in FPWM mode for low output voltage ripple, tight output voltage regulation, and constant switching frequency.

#### 10.3.4 FREQ/SYNC

The switching frequency of the TPS2585x-Q1 can be programmed by the resistor  $R_{FREQ}$  from the FREQ/SYNC pin and AGND pin. To determine the FREQ resistance, for a given switching frequency, use Equation 4:




Figure 10-3. FREQ Set Resistor vs Switching Frequency

The normal method of setting the buck regulator switching frequency is by selecting an appropriate value FREQ resistor, the typical FREQ resistors value are listed in Table 10-1.

Table 10-1. Setting the Switching Frequency with FREQ

FREQ (KΩ)	SWITCHING FREQUENCY (KHz)
80.6	253
49.9	400

The FREQ/SYNC pin can be used to synchronize the internal oscillator to an external clock. The internal oscillator can be synchronized by AC coupling a positive edge into the FREQ/SYNC pin. When using a low impedance signal source, the frequency setting resistor FREQ is connected in parallel with an AC coupling capacitor,  $C_{COUP}$ , to a termination resistor,  $R_{TERM}$  (for example, 50  $\Omega$ ). The two resistors in series provide the default frequency setting resistance when the signal source is turned off. A 10-pF ceramic capacitor can be used for  $C_{COUP}$ . The AC coupled peak-to-peak voltage at the FREQ/SYNC pin must exceed the SYNC amplitude threshold of 1.2 V (typical) to trip the internal synchronization pulse detector, and the minimum SYNC clock HIGH and LOW time must be longer than 100 ns (typical). A 2.5 V or higher amplitude pulse signal coupled through a 1-nF capacitor,  $C_{SYNC}$ , is a good starting point. Figure 10-4 shows the device synchronized to an external system clock. The external clock must be off before start-up to allow proper start-up sequencing.




Figure 10-4. Synchronize to External Clock

The TPS2585x-Q1 switching action can be synchronized to an external clock from 200 KHz to 800 KHz. Note the higher switching frequency results in more power loss on IC, cause the junction temperature and also the board temperature rising, then the device can enter load shedding under high ambient temperature.

#### 10.3.5 Bootstrap Voltage (BOOT)

The TPS2585x-Q1 provides an integrated bootstrap voltage regulator. A small capacitor between the BOOT and SW pins provides the gate drive voltage for the high-side MOSFET. The BOOT capacitor is refreshed when the high-side MOSFET is off and the low-side switch conducts. The recommended value of the BOOT capacitor is 100 nF. A ceramic capacitor with an X7R or X5R grade dielectric with a voltage rating of 10 V or higher is recommended for stable performance over temperature and voltage. The BOOT rail has a UVLO to protect the chip from operation with too little bias, and is typically 2.2 V. If the BOOT capacitor voltage drops below the UVLO threshold, the device initiates a charging sequence using the low-side FET before attempting to turn on the high-side device.

#### 10.3.6 Minimum ON-Time, Minimum OFF-Time

Minimum ON-time,  $T_{ON\_MIN}$ , is the smallest duration of time that the HS switch can be on.  $T_{ON\_MIN}$  is typically 84 ns in the TPS2585x-Q1. Minimum OFF-time,  $T_{OFF\_MIN}$ , is the smallest duration that the HS switch can be off.  $T_{OFF\_MIN}$  is typically 81 ns in the TPS2585x-Q1. In CCM (FPWM) operation,  $T_{ON\_MIN}$  and  $T_{OFF\_MIN}$  limit the voltage conversion range given in a selected switching frequency.

The minimum duty cycle allowed is:

$$D_{MIN} = T_{ON\ MIN} \times f_{SW} \tag{5}$$

And the maximum duty cycle allowed is:

$$D_{MAX} = 1 - T_{OFF MIN} \times f_{SW}$$
 (6)

Given fixed  $T_{ON\_MIN}$  and  $T_{OFF\_MIN}$ , the higher the switching frequency, the narrower the range of the allowed duty cycle.

Given an output voltage, the choice of the switching frequency affects the allowed input voltage range, solution size, and efficiency. The maximum operation supply voltage can be found by:

$$V_{IN\_MAX} = \frac{V_{OUT}}{\left(f_{SW} \times T_{ON\_MIN}\right)}$$
(7)

At lower supply voltage, the switching frequency is limited by  $T_{OFF\_MIN}$ . The minimum  $V_{IN}$  can be approximated by:

$$V_{IN\_MIN} = \frac{V_{OUT}}{\left(1 - f_{SW} \times T_{OFF\_MIN}\right)}$$
(8)

Considering power losses in the system with heavy load operation,  $V_{IN\_MAX}$  is higher than the result calculated in Equation 7.

If minimum ON-time or minimum OFF-time do not support the desired conversion ratio, frequency is reduced, automatically allowing regulation to be maintained during load dump and with very low dropout during cold crank even with high operating-frequency setting.

#### 10.3.7 Internal Compensation

The TPS2585x-Q1 is internally compensated. The internal compensation is designed such that the loop response is stable over the specified operating frequency and output voltage range. The TPS2585x-Q1 is optimized for transient response over the range of 200 kHz  $\leq$  fsw  $\leq$  800 kHz.

#### 10.3.8 Selectable Output Voltage (VSET)

The TPS2585x-Q1 provides four different output voltage options. The voltage can be set by an external resistor across the VSET pin. The normal method of setting the buck output voltage is by selecting an appropriate value VSET resistor as shown in Table 10-2.

Table 10-2. VSET Configuration vs BUS Output Voltage

VSET CONFIGURATION	V <sub>SENSE</sub>
Float or pull up to V <sub>SENSE</sub>	5.1 V
Short to GND	5.17 V
R <sub>VSET</sub> = 40.2 KΩ	5.3 V
R <sub>VSET</sub> = 80.6 KΩ	5.4 V

Note that the VSET has an internal weak 20-µA current source to overdrive the pin to SENSE. If this pin is floated, the voltage on this pin approaches the SENSE voltage, and sets the output voltage to 5.1 V. TI does not recommend to float this pin if there is external noise from the PCB board because the noise interferes with the VSET internal logic block.

#### 10.3.9 Current Limit and Short Circuit Protection

For maximum versatility, the TPS2585x-Q1 includes both a precision, programmable current limit as well cycle-by-cycle current limit to protect the USB port from extreme overload conditions. The R<sub>ILIM</sub> resistor determines the overload threshold on the USB ports in the event ILIM is shorted to ground to set the default USB current limit. The cycle-by-cycle current limit serves as a backup means of protection.

#### 10.3.9.1 USB Switch Programmable Current Limit (ILIM)

Because the TPS2585x-Q1 integrates two USB current-limit switches, it provides adjustable current limit to prevent USB port overheating. the TPS2585x-Q1 engages the Two-level current limit scheme, which has one typical current limit,  $I_{OS\_BUS}$ , and the secondary current limit,  $I_{OS\_HI}$ . The secondary current limit,  $I_{OS\_BUS}$ . The secondary current limit acts as the current limit threshold for a deglitch time,  $t_{IOS\_HI\_DEG}$ , then the USB power switch current limit threshold is set back to  $I_{OS\_BUS}$ . Equation 9 calculates the value of resistor for adjusting the typical current limit.

$$R_{ILIM}(K\Omega) = \frac{32273}{I_{OS\_BUS}(mA)}$$
(9)

This equation assumes an ideal-no variation-external adjusting resistor. To take resistor tolerance into account, first determine the minimum and maximum resistor values based on its tolerance specifications and use these values in the equations. Because of the inverse relationship between the current limit and the adjusting resistor, use the maximum resistor value in the  $I_{OS(min)}$  equation and the minimum resistor value in the  $I_{OS(max)}$  equation. Typical  $R_{ILIM}$  resistor value are listed in Table 10-3.

Table 10-3. Setting the Current Limit with R<sub>ILIM</sub>

R <sub>ILIM</sub> (KΩ)	I <sub>OS_BUS</sub> – Current Limit Threshold (mA)
19.1	1690
15.4	2096
11.5	2806
9.53	3386
Short to GND	3550

For the normal application, it can short the ILIM pin to GND directly, which sets a default 3.55-A current limit with a maximum ±15% variation on each USB port to follow the Type-C specification. The TPS2585x-Q1 provides built-in soft-start circuitry that controls the rising slew rate of the output voltage to limit inrush current and voltage surges.

The secondary current limit,  $I_{OS\_HI}$ , allows the USB port pull out a larger current for a short time during transient overload conditions, which can bring benefits for USB port special overload testing like MFi OCP. In a normal application, once the device is powered on and USB port is not in UVLO, the USB port current limit threshold is overridden by the secondary current limit,  $I_{OS\_HI}$ , so the USB port can output as high as a  $1.6 \times I_{OS\_BUS}$  current for typically 2 ms. After the deglitch time,  $t_{IOS\_HI\_DEG}$ , the current limit threshold is set back to the typical current with  $I_{OS\_BUS}$ . The secondary current limit threshold does not resume until after the  $t_{IOS\_HI\_RST}$  deglitch time, which is typically 16 ms. If there is an inrush current higher than the  $I_{OS\_HI}$  threshold, the current limit is set back to  $I_{OS\_BUS}$  immediately, without waiting for a  $t_{IOS\_HI\_DEG}$ .

The TPS2585x-Q1 responds to overcurrent conditions by limiting output current to I<sub>OS\_BUS</sub> as shown in previous equation. When an overload condition occurs, the device maintains a constant output current and the output voltage reduces accordingly. Three possible overload conditions can occur:

• The first condition is when a short circuit or overload is applied to the USB output when the device is powered up or enabled. There can be inrush current and once it triggers the approximate 8-A threshold, a fast turnoff circuit is activated to turn off the USB power switch within t<sub>IOS\_USB</sub> before the current limit control loop is able to respond (shown in Figure 10-5). After the fast turnoff is triggered, the USB power switch current-sense amplifier is over-driven during this time and momentarily disables the internal N-channel MOSFET to turn off USB port. The current-sense amplifier then recovers and ramps the output current with a soft start. If the USB port is still in overcurrent condition, the short circuit and overload hold the output near zero potential with respect to ground and the power switch ramps the output current to I<sub>OS\_BUS</sub>. If the overcurrent limit condition lasts longer than 4.1 ms, the corresponding USB channel enters hiccup mode with 524 ms of off-time and 4.1 ms of on-time.





Figure 10-5. Response Time to BUS Short-Circuit

• The second condition is the load current increases above I<sub>OS\_BUS</sub> but below the I<sub>OS\_HI</sub> setting. The device allows the USB port to output this large current for t<sub>IOS\_HI\_DEG</sub>, without limiting the USB port current to I<sub>OS\_BUS</sub>. After the t<sub>IOS\_HI\_DEG</sub> deglitch time, the device limits the output current to I<sub>OS\_BUS</sub> and works in a constant current-limit mode. If the load demands a current greater than I<sub>OS\_BUS</sub>, the USB output voltage decreases to I<sub>OS\_BUS</sub> × R<sub>LOAD</sub> for a resistive load, which is shown in Figure 10-6. If the overcurrent limit condition lasts longer than 4.1 ms, the corresponding USB channel enters hiccup mode with 524 ms of off-time and 4.1 ms of on-time. Another USB channel still works normally.



#### Figure 10-6. BUS Overcurrent Protection

• The third condition is the load current increases just over the I<sub>OS\_HI</sub> setting. In this case, the load does not trigger the fast turnoff, the USB power switch current limit threshold is set back to the primary current limit, I<sub>OS\_BUS</sub>, immediately. If the load still demands a current greater than I<sub>OS\_BUS</sub>, the USB output voltage decreases to I<sub>OS\_BUS</sub> × R<sub>LOAD</sub> for a resistive load, which is shown in Figure 10-7. If the overcurrent limit condition lasts longer than 4.1 ms, the corresponding USB channel enters hiccup mode with 524 ms of off-time and 4.1 ms of on-time. Another USB channel still works normally.




Figure 10-7. BUS Overcurrent Protection: Two-Level Current Limit

The TPS2585x-Q1 thermal cycles if an overload condition is present long enough to activate thermal limiting in any of the previously mentioned cases. Thermal limiting turns off the internal NFET and starts when the NFET junction temperature exceeds  $160^{\circ}$ C (typical). The device remains off until the NFET junction temperature cools  $10^{\circ}$ C (typical) and then restarts. This extra thermal protection mechanism can help prevent further junction temperature rise, which can cause the device to turn off due to junction temperature exceeding the main thermal shutdown threshold,  $T_{\rm SD}$ .

### 10.3.9.2 Interlocking for Two-Level USB Switch Current Limit

The TPS2585x-Q1 has two USB ports. Because the secondary current limit, I<sub>OS\_HI</sub>, is 1.6x of the primary current limit, I<sub>OS\_BUS</sub>, if the two USB ports pull out large current at the same time, then the DC-DC regulator is overloaded, and DC-DC regulator output voltage can be crashed. To avoid these potential issues, the TPS2585x-Q1 adopts the interlocking scheme to manage the current limits of the two USB ports.

For interlocking, if one USB port current is beyond the primary current limit threshold,  $I_{OS\_BUS}$ , then another USB port current limit threshold is overridden to the primary current limit,  $I_{OS\_BUS}$ , immediately. With this control scheme, the TPS2585x-Q1 only allows one USB port to output a large current, which can be as high as 1.6x of the primary current limit,  $I_{OS\_BUS}$ , at the same time. Ensure the DC-DC regulator has enough energy to sustain

its output voltage. That means in MFi OCP testing, the DC-DC regulator will support up to 8.4-A output current during the t<sub>IOS\_HI\_DEG</sub> deglitch time, which is 4.8 A for the USB type-C port which under testing, 3 A for another USB type-C port, and maximum 0.6-A total for VCONN and OUT.

### 10.3.9.3 Cycle-by-Cycle Buck Current Limit

There is a buck regulator cycle-by-cycle current limit on both the peak and valley of the inductor current.

High-side MOSFET overcurrent protection is implemented by the nature of the peak current mode control. The HS switch current is sensed when the HS is turned on after a set blanking time. The HS switch current is compared to the output of the Error Amplifier (EA) minus slope compensation every switching cycle. The peak current of HS switch is limited by a clamped maximum peak current threshold, I<sub>HS\_LIMIT</sub>, which is constant. The peak current limit of the high-side switch is not affected by the slope compensation and remains constant over the full duty cycle range.

The current going through LS MOSFET is also sensed and monitored. When the LS switch turns on, the inductor current begins to ramp down. The LS switch does not turn OFF at the end of a switching cycle if its current is above the LS current limit,  $I_{LS\_LIMIT}$ . The LS switch is kept ON so that the inductor current keeps ramping down until the inductor current ramps below the LS current limit,  $I_{LS\_LIMIT}$ . Then, the LS switch is turned OFF and the HS switch is turned on after a dead time. This action is somewhat different than the more typical peak current limit and results in Equation 10 for the maximum load current.

$$I_{OUT\_MAX} = I_{LS\_LIMIT} + \frac{\left(V_{IN} - V_{OUT}\right)}{2 \times f_{SW} \times L} \times \frac{V_{OUT}}{V_{IN}}$$
(10)

#### 10.3.9.4 OUT Current Limit

The TPS2585x-Q1 can provide 200-mA current at the OUT pin to power the auxiliary loads, such as USB HUB, LEDs. The input of the OUT power switch comes from the buck regulator output, so the OUT voltage is same with the SNESE voltage but deduct the OUT  $R_{DS-ON}$  voltage loss.

Because the OUT power is provided by buck regulator, for TPS25858-Q1, the buck regulator is not operating unless Rd is inserted. In normal application, if no USB Type-C cable plug-in, then TPS25858-Q1 OUT voltage is zero. For TPS25859-Q1, the buck regulator operates even though Rd is not inserted, so even if no USB Type-C cable plug-in, the TPS25859-Q1 OUT still has a voltage same with the SENSE voltage.

If the OUT current reaches the current limit level, the OUT pin MOSFET works in a constant current-limit mode. If the overcurrent limit condition lasts longer than 4.1 ms, it enters hiccup mode with 4.1 ms of on-time and 524 ms of off-time.

#### 10.3.10 Cable Compensation

When a load draws current through a long or thin wire, there is an IR drop that reduces the voltage delivered to the load. In the vehicle from the voltage regulator output  $V_{OUT}$  to  $V_{BUS}$  (input voltage of portable device), the total resistance of PCB trace, connector, and cable resistances causes an IR drop at the portable device input, so the charging current of most portable devices is less than their expected maximum charging current. The voltage drop is shown in Figure 10-8.




Figure 10-8. Voltage Drop

To handle this case, the TPS2585x-Q1 has a built-in cable compensation function where the droop compensation linearly increases the voltage at the SENSE pin of the TPS2585x-Q1 as load current increases, to maintain a fairly constant output voltage at the load-side voltage.

For the TPS2585x-Q1, the internal comparator compares the current-sense output voltage of the two current-limit switches and uses the larger current-sense output voltage to compensate for the line drop voltage. The cable compensation amplitude increases linearly as the load current increases. It also has an upper limitation. The cable compensation at output currents greater than 2.4 A is 90 mV and is shown in Figure 10-9. Note the cable compensation only works when you short the VSET to GND. For the other VSET configuration, the cable compensation is not available.




Figure 10-9. Dual Ports Cable Compensation

#### 10.3.11 Thermal Management With Temperature Sensing (TS) and OTSD

The TS input pin allows for user-programmable thermal protection (see the *Electrical Characteristics* for the TS pin thresholds). The TS input pin threshold is ratiometric with  $V_{SENSE}$ . The external resistor divider setting,  $V_{TS}$ , must be connected to the TPS2585x-Q1 SENSE pin to achieve accurate results (refer to the Figure 10-10). When  $V_{TS} = 0.5 \times V_{SENSE}$ , the TPS2585x-Q1 performs the below action:

 If operating with 3-A Type-C advertisement, the Px\_CC1, Px\_CC2 pin automatically reduces advertisement to the 1.5-A level.




Figure 10-10. TS Input

If the overtemperature condition persists, causing  $V_{TS}$  = 0.65 ×  $V_{SENSE}$ , the TPS2585x-Q1 performs the below actions:

- Broadcasts the Default USB Power mode. In Default USB Power, the charging is ideally reduced further per the USB2.0 and USB3.0 specification.
- Buck regulator output voltage at the SENS pin is reduced to 4.77 V.

If the Overtemperature condition persists, causing  $T_J$  to reach the OTSD threshold, then the device thermal shuts down. Figure 10-11 shows the TPS25858-Q1 behavior when the TS pin voltage triggers the Temp Warm and Temp Hot threshold.




Figure 10-11. TPS25858-Q1 Behavior When Trigger Temp Warm and Hot Threshold

The NTC thermistor must be placed near the hottest point on the PCB. In most cases, this is close to the SW node of the TPS2585x-Q1, near the buck inductor.

Tuning the  $V_{NTC}$  threshold levels of  $V_{TEMP\_WARM}$  and  $V_{TEMP\_HOT}$  is achieved by adding  $R_{SER}$ ,  $R_{PARA}$ , or both  $R_{SER}$  and  $R_{PARA}$  in conjunction with  $R_{NTC}$ . Figure 10-12 is an example illustrating how to set the  $V_{TEMP\_WARM}$  threshold between 81°C and 90°C with a  $\Delta T$  between TEMP\_WARM assertion and TEMP\_HOT assertion of 18°C to 29°C. Consult the chosen NTC manufacturer's specification for the value of  $\beta$ . Establishing the desired warning and shutdown thresholds can take some iteration.

Below is NTC spec and resistor value used in Figure 10-2 example.

•  $R_0 = 470 \text{ k}\Omega$ .  $\beta = 4750$ .  $R_{NTC} = R_0 \times \exp \beta \times (1 / T - 1 / T_0)$ .

- R<sub>PARA</sub> = 100 kΩ.
- $R_{SER} = 5.1 \text{ k}\Omega$ .
- $R_B = R_{NTC}$  (at TEMP\_WARM) = 27 k $\Omega$ .




Figure 10-12. V<sub>TS</sub> Threshold Design Examples

#### 10.3.12 Thermal Shutdown

The device has an internal overtemperature shutdown threshold,  $T_{SD}$ , to protect the device from damage and overall safety of the system. When the device temperature exceeds  $T_{SD}$ , the device is turned off when thermal shutdown activates. Once the die temperature falls below 154°C (typical), the device re-initiates the power-up sequence controlled by the internal soft-start circuitry.

#### 10.3.13 USB Enable On and Off Control (TPS25859-Q1)

For the TPS25859-Q1, PA\_EN and PB\_EN are the on/off control input pins for PA\_USB and PB\_USB, respectively. The USB switch is active when Px\_EN is pulled high. Pull the Px\_EN voltage to logic low to shut down the USB switch with an output discharge. Connect Px\_EN to SENSE for automatic start-up, or control them by an external on/off signal from the microcontroller or USB HUB.

#### 10.3.14 FAULT Indication (TPS25859-Q1)

For the TPS25859-Q1, PA\_FAULT and PB\_FAULT are the fault indication pins for PA\_USB and PB\_USB, respectively. FAULT is in an open-drain state during shutdown, start-up, or normal condition. When the USB switch enters hiccup mode, or overtemperature thermal shutdown (OTSD) is triggered, Px\_FAULT is pulled low. FAULT asserts (logic low) on an individual USB switch during an overcurrent or overtemperature condition. Px\_FAULT switches high after the fault condition is removed, and the USB output voltage goes high again.

The device features an active-low, open-drain fault output. Connect a 100-k $\Omega$  pullup resistor from  $\overline{Px}_{FAULT}$  to SENSE or other suitable I/O voltage.  $\overline{Px}_{FAULT}$  can be left open or tied to GND when not used.



Table 10-4 summarizes the conditions that generate a fault and actions taken by the device.

#### Table 10-4. Fault Conditions

EVENT	CONDITION	ACTION				
Overcurrent on Px_BUS	I <sub>Px_BUS</sub> > Programmed I <sub>ILIM</sub>	Px_BUS load switch enter hiccup mode. The fault indicator asserts with a 4.1-ms deglitch and de-asserts with a 16.4-ms deglitch. The fault indicator remains asserted during the Px_BUS overload condition.				
TPS2585x-Q1 overtemperature	$T_J > T_{SD}$	The device immediately disables and asserts fault indicator with no deglitch. The device attempts to power up once the die temperature decreases below the thermal hysteresis threshold as specified.				

#### 10.3.15 USB Specification Overview

All USB ports are capable of providing a 5-V output, making them a convenient power source for operating and charging portable devices. USB specification documents outline specific power requirements to ensure interoperability. In general, a USB 2.0 port host port is required to provide up to 500 mA; a USB 3.0 or USB 3.1 port is required to provide up to 900 mA; ports adhering to the USB Battery Charging 1.2 Specification provide up to 1500 mA; newer Type-C ports can provide up to 3000 mA. Though USB standards governing power requirements exist, some manufacturers of popular portable devices created their own proprietary mechanisms to extend allowed available current beyond the 1500-mA maximum per BC 1.2. While not officially part of the standards maintained by the USB-IF, these proprietary mechanisms are recognized and implemented by manufacturers of USB charging ports.

The TPS2585x-Q1 device supports five of the most-common USB-charging schemes found in popular hand-held media and cellular devices:

- USB Type-C (1.5-A and 3-A advertisement)
- USB Battery Charging Specification BC1.2 DCP mode
- Chinese Telecommunications Industry Standard YD/T 1591-2009
- Divider 3 mode
- 1.2-V mode

#### 10.3.16 USB Type-C® Basics

For a detailed description of the Type-C specification, refer to the USB-IF website to download the latest released version. Some of the basic concepts of the Type-C spec that pertains to understanding the operation of the TPS2585x-Q1 (a DFP device) are described as follows.

USB Type-C removes the need for different plug and receptacle types for host and device functionality. The Type-C receptacle replaces both the Type-A and Type-B receptacles because the Type-C cable is plug-able in either direction between the host and device. A host-to-device logical relationship is maintained by the configuration channel (CC). Optionally, hosts and devices can be either providers or consumers of power when USB PD communication is used to swap roles.

All USB Type-C ports operate in one of following data modes:

- Host mode: the port can only be a host (provider of power).
- Device mode: the port can only be a device (consumer of power).
- Dual-Role mode: the port can be either a host or device.

#### Port types:

- DFP (Downstream Facing Port): Host
- UFP (Upstream Facing Port): Device
- DRP (Dual-Role Port): Host or Device

#### Valid DFP-to-UFP connections:

- Table 10-5 describes valid DFP-to-UFP connections.
- Host-to-Host or Device-to-Device have no functions.

Table 1	0-5.	DFP-to-	UFP	Connections
---------	------	---------	-----	-------------

	HOST-MODE PORT	DEVICE-MODE PORT	DUAL-ROLE PORT
Host-Mode Port	No function	Works	Works
Device-Mode Port	Works	No function	Works
Dual-Role Port	Works	Works	Works <sup>(1)</sup>

<sup>(1)</sup> This can be automatic or manually driven.

#### 10.3.16.1 Configuration Channel

The function of the configuration channel is to detect connections and configure the interface across the USB Type-C cables and connectors.

Functionally, the Configuration Channel (CC) is used to serve the following purposes:

- Detect connect to the USB ports.
- Resolve cable orientation and twist connections to establish USB data bus routing.
- Establish DFP and UFP roles between two connected ports.
- Discover and configure power: USB Type-C current modes or USB Power Delivery.
- Discover and configure optional Alternate and Accessory modes.
- · Enhances flexibility and ease of use.

Typical flow of DFP-to-UFP configuration is shown in Figure 10-13.




Figure 10-13. Flow of DFP-to-UFP Configuration

#### 10.3.16.2 Detecting a Connection

DFPs and DRPs fulfill the role of detecting a valid connection over USB Type-C. Figure 10-14 shows a DFP-to-UFP connection made with a Type-C cable. As shown in Figure 10-14, the detection concept is based on being able to detect terminations in the product that have been attached. A pull-up and pull-down termination model is used. A pull-up termination can be replaced by a current source.

- In the DFP-UFP connection, the DFP monitors both CC pins for a voltage lower than the unterminated voltage.
- An UFP advertises Rd on both its CC pins (CC1 and CC2).
- A powered cable advertises Ra on only one of the CC pins of the plug. Ra is used to inform the source to apply VCONN.
- An analog audio device advertises Ra on both CC pins of the plug, which identifies it as an analog audio device. VCONN is not applied on either CC pin in this case.

Copyright © 2021 Texas Instruments Incorporated






Figure 10-14. DFP-UFP Connection

For USB Type-C solutions, two pins (CC1, CC2) on the connector are used to establish and manage the source-to-sink connection. The general concept for setting up a valid connection between a source and a sink is based on being able to detect terminations residing in the product being attached. To aid in defining the functional behavior of CC, a pull-up (Rp) and pull-down (Rd 5.1 k $\Omega$ ) termination model is used based on a pull-up resistor and pull-down resistor.

Initially, a source exposes independent Rp terminations on its CC1 and CC2 pins, and a sink exposes independent Rd terminations on its CC1 and CC2 pins. The source-to-sink combination of this circuit configuration represents a valid connection. To detect this, the source monitors CC1 and CC2 for a voltage lower than its unterminated voltage. The choice of Rp is a function of the pull-up termination voltage and the detection circuit of the source. This indicates that either a sink, a powered cable, or a sink connected by a powered cable has been attached. Prior to the application of VCONN, a powered cable exposes Ra (typically 1 k $\Omega$ ) on its VCONN pin. Ra represents the load on VCONN plus any resistive elements to ground. In some cable plugs, this can be a pure resistance, and in others, it can simply be the load.

The source must be able to differentiate between the presence of Rd and Ra to know whether there is a sink attached and where to apply VCONN. The source is not required to source VCONN unless Ra is detected. Two special termination combinations on the CC pins as seen by a source are defined for directly attached accessory modes: Ra/Ra for audio adapter accessory mode and Rd/Rd for debug accessory mode.

## 10.3.17 USB Port Operating Modes

## 10.3.17.1 USB Type-C® Mode

The TPS2585x-Q1 is a Type-C controller that supports all Type-C functions in a downstream facing port. The TPS2585x-Q1 is also used to manage current advertisement and protection to a connected UFP and active cable. When V<sub>SENSE</sub> exceeds the undervoltage lockout threshold, the device samples the EN pin. A high level on this pin enables the device and normal operation begins. Having successfully completed its start-up sequence, the device now actively monitors its CC1 and CC2 pins for attachment to a UFP. When a UFP is detected on either the CC1 or CC2 pin the USB power switch turn-ons. If Ra is detected on the other CC pin (not connected to UFP), VCONN is applied to allow current to flow to the CC pin connected to Ra.

## 10.3.17.2 Dedicated Charging Port (DCP) Mode (TPS25858-Q1 Only)

A DCP only provides power and does not support data connection to an upstream port. As shown in the following sections, a DCP is identified by the electrical characteristics of the data lines. The TPS25858-Q1 only emulates one state, DCP-auto state. In the DCP-auto state, the device charge-detection state machine is activated to selectively implement charging schemes involved with the shorted, Divider 3 and 1.2-V modes. The shorted DCP mode complies with BC1.2 and Chinese Telecommunications Industry Standard YD/T 1591-2009,

whereas the Divider 3 and 1.2-V modes are employed to charge devices that do not comply with the BC1.2 DCP standard.

#### 10.3.17.2.1 DCP BC1.2 and YD/T 1591-2009

Both standards specify that the D+ and D- data lines must be connected together with a maximum series impedance of 200  $\Omega$ , as shown in Figure 10-15.




Figure 10-15. DCP Supporting BC1.2 and YD/T 1591-2009

## 10.3.17.2.2 DCP Divider-Charging Scheme

The device supports Divider 3, as shown in Figure 10-16. In the Divider 3 charging scheme, the device applies 2.7 V and 2.7 V to D+ and D- data lines.




Figure 10-16. Divider 3 Mode

#### 10.3.17.2.3 DCP 1.2-V Charging Scheme

The DCP 1.2-V charging scheme is used by some hand-held devices to enable fast charging at 2 A. The TPS25858-Q1 device supports this scheme in DCP-auto state before the device enters BC1.2 shorted mode. To simulate this charging scheme, the D+ and D- lines are shorted and pulled up to 1.2 V for a fixed duration. Then the device moves to DCP shorted mode as defined in the BC1.2 specification and as shown in Figure 10-17.




Figure 10-17. 1.2-V Mode

## 10.3.17.3 DCP Auto Mode (TPS25858-Q1)

The TPS25858-Q1 device integrates an auto-detect state machine that supports all the DCP charging schemes as shown in Figure 10-18. The auto-detect state machine starts in the Divider 3 scheme. If a BC1.2 or YD/T 1591-2009 compliant device is attached, the TPS25858-Q1 device responds by turning the power switch back on without output discharge and operating in 1.2-V mode briefly before entering BC1.2 DCP mode. Then, the auto-detect state machine stays in that mode until the device releases the data line, in which case, the auto-detect state machine goes back to the Divider 3 scheme. When a Divider 3-compliant device is attached, the TPS25858-Q1 device stays in the Divider 3 state.






Figure 10-18. DCP Auto Mode



#### 10.4 Device Functional Modes

#### 10.4.1 Shutdown Mode

The EN pin provides electrical ON and OFF control for the TPS2585x-Q1. When  $V_{EN}$  is below 1.2 V (typical), the device is in shutdown mode. The TPS2585x-Q1 also employs  $V_{IN}$  over voltage lock out protection and  $V_{SENSE}$  under voltage lock out protection. If  $V_{IN}$  voltage is above its respective OVLO level,  $V_{OVLO}$ , or  $V_{SENSE}$  voltage is below its respective UVLO level,  $V_{DCDC}$  UVLO, the DC/DC converter turns off.

#### 10.4.2 Active Mode

The TPS2585x-Q1 is in active mode when  $V_{EN}$  is above the precision enable threshold,  $V_{SENSE}$  is above its respective UVLO levels, and a valid detection has been made on the CC lines. The simplest way to enable the TPS2585x-Q1 is to connect the EN pin to SENSE pin. This connection allows self startup when the input voltage is in the operating range (5.5 V to 26 V) and a UFP detection is made.

In active mode, the TPS25858-Q1 buck regulator does not operate unless Rd is inserted. The TPS25859-Q1 buck regulator operates even though Rd is not inserted. The buck regulator operates with Forced Pulse Width Modulation (FPWM), also referred to as Forced Continuous Conduction Mode (FCCM). This operation ensures the buck regulator switching frequency remains constant under all load conditions. FPWM operation provides low output voltage ripple, tight output voltage regulation, and constant switching frequency. Built-in spread-spectrum modulation aids in distributing spectral energy across a narrow band around the switching frequency programmed by the FREQ/SYNC pin. Under light load conditions, the inductor current is allowed to go negative. A negative current limit of  $I_{L-NEG-LS}$  is imposed to prevent damage to the regulator's low side FET. During operation, the TPS2585x-Q1 synchronizes to any valid clock signal on the FREQ/SYNC input.



## 11 Application and Implementation

#### **Note**

Information in the following applications sections is not part of the TI component specification, and TI does not warrant its accuracy or completeness. TI's customers are responsible for determining suitability of components for their purposes, as well as validating and testing their design implementation to confirm system functionality.

## 11.1 Application Information

The TPS2585x-Q1 is a step down DC-to-DC regulator and USB charge port controller. The TPS2585x-Q1 is typically used in automotive systems to convert a DC voltage from the vehicle battery to 5-V DC with a maximum output current of 6.6 A in dual Type-C ports applications. The TPS2585x-Q1 engages a high efficiency buck converter, letting the device operate at as high as 85°C ambient temperature with full load. The following design procedure can be used to select components for the TPS2585x-Q1.

## 11.2 Typical Applications

The TPS2585x-Q1 only requires a few external components to convert from a wide voltage range supply to a 5-V output to power USB devices. Figure 11-1 shows the TPS25858-Q1 typical application schematic for Dual Type-C charging ports. Figure 11-2 shows the TPS25859-Q1 typical application schematic for Dual Type-C charging ports.




Figure 11-1. TPS25858-Q1 Typical Application Circuit for 400-kHz f<sub>SW</sub>




Figure 11-2. TPS25859-Q1 Typical Application Circuit for 400-kHz f<sub>SW</sub>

As a quick start guide, Table 11-1 provides typical component values for some of the most common configurations. The values given in Table 11-1 are typical. Other values can be used to enhance certain performance criterion as required by the application. The integrated buck regulator of TPS2585x-Q1 is internally compensated and optimized for a reasonable selection of external inductance and capacitance. The external components have to fulfill the needs of the application, but also the stability criteria of the control loop of the device.

Table 11-1. L and C<sub>OUT</sub> Typical Values

f <sub>SW</sub>	V <sub>OUT</sub> WITHOUT CABLE COMPENSATION	L	C <sub>HF</sub> + C <sub>IN</sub>	Своот	RATED C <sub>OUT</sub>	
400 KHZ	5.17 V	3.3 µH	1 × 100 nF + 1 × 47 μF	1 × 100 nF	3 × 47 µF	

- 1. The inductance value is calculated based on maximum  $V_{IN}$  = 18 V.
- 2. All the C<sub>OUT</sub> values are after derating and use low ESR ceramic capacitors.
- 3. The C<sub>OUT</sub> is the buck regulator output capacitors at the SENSE pin.

## 11.2.1 Design Requirements

The detailed design procedure is described based on a design example. For this design example, use the parameters listed in Table 11-2 as the input parameters.

**Table 11-2. Design Example Parameters** 

Input Voltage, V <sub>IN</sub>	13.5-V typical, range from 8 V to 18 V
Output Voltage, V <sub>SENSE</sub>	5.17 V
Maximum Output Current	6.6 A
Switching Frequency f <sub>SW</sub>	400 kHz

#### 11.2.2 Detailed Design Procedure

## 11.2.2.1 Output Voltage Setting

The output voltage of TPS2586x-Q1 is programmed by the VSET pin, and if short VSET to GND, sets the output voltage at 5.17 V and enables the cable compensation function, and the output voltage increases linearly with increasing load current. Refer to Table 10-2 for more details on output voltage setting. Cable compensation can be used to increase the voltage on the SENSE pin linearly with increasing load current. Refer to *List item* for more details on cable compensation setting. If cable compensation is not desired, use a  $0-\Omega$  R<sub>IMON</sub> resistor.

#### 11.2.2.2 Switching Frequency

The recommended switching frequency of the TPS2585x-Q1 is in the range of 250 KHz–400 KHz for high efficiency. Choose  $R_{FREQ}$  = 49.9 k $\Omega$  for 400-KHz operation. To choose a different switching frequency, refer to Table 10-1.

The choice of switching frequency is a compromise between conversion efficiency and overall solution size. Lower switching frequency implies reduced switching losses and usually results in higher system efficiency. However, higher switching frequency allows the use of smaller inductors and output capacitors, and hence, a more compact design. In automotive USB charging applications, it tends to operate at 400 kHz below the AM band. In this example, 400 kHz is chosen.

#### 11.2.2.3 Inductor Selection

The most critical parameters for the inductor are the inductance, saturation current, and the rated current. The inductance is based on the desired peak-to-peak ripple current,  $\Delta i_L$ . Because the ripple current increases with the input voltage, the maximum input voltage is always used to calculate the minimum inductance  $L_{MIN}$ . Use Equation 12 to calculate the minimum value of the output inductor.  $K_{IND}$  is a coefficient that represents the amount of inductor ripple current relative to the maximum output current of the device. A reasonable value of  $K_{IND}$  must be 20% to 40%. Note that when selecting the ripple current for applications with much smaller maximum load than the maximum available from the device, the maximum device current must still be used. During an instantaneous short or overcurrent operation event, the RMS and peak inductor current can be high. The inductor current rating must be higher than the current limit of the device.

$$\Delta i_{L} = \frac{V_{OUT} \times \left(V_{IN\_MAX} - V_{OUT}\right)}{V_{IN\_MAX} \times L \times f_{SW}}$$
(11)

$$L_{MIN} = \frac{V_{IN\_MAX} - V_{OUT}}{I_{OUT} \times K_{IND}} \times \frac{V_{OUT}}{V_{IN\_MAX} \times f_{SW}}$$
(12)

In general, it is preferable to choose lower inductance in switching power supplies because it usually corresponds to faster transient response, smaller DCR, and reduced size for more compact designs. Too low of an inductance can generate too large of an inductor current ripple such that overcurrent protection at the full load can be falsely triggered. It also generates more conduction loss and inductor core loss. Larger inductor current ripple also implies larger output voltage ripple with the same output capacitors. With peak current mode control, it is not recommended to have too small of an inductor current ripple. A larger peak current ripple improves the comparator signal to noise ratio.

For this design example, choose  $K_{IND}$  = 0.3, and find an inductance of approximately 3.58  $\mu$ H. Select the next standard value of 3.3  $\mu$ H.

#### 11.2.2.4 Output Capacitor Selection

The output capacitor or capacitors, C<sub>OUT</sub>, must be chosen with care because it directly affects the steady state output voltage ripple, loop stability, and the voltage overshoot/undershoot during load current transients.

The value of the output capacitor and its ESR, determine the output voltage ripple and load transient performance. The output capacitor is usually limited by the load transient requirements rather than the output voltage ripple if the system requires tight voltage regulation with presence of large current steps and fast slew

rate. When a fast large load increase happens, output capacitors provide the required charge before the inductor current can slew up to the appropriate level. The control loop of the regulator usually needs four or more clock cycles to respond to the output voltage droop. The output capacitance must be large enough to supply the current difference for four clock cycles to maintain the output voltage within the specified range. Table 11-3 can be used to find output capacitors for a few common applications. In this example, good transient performance is desired giving  $3 \times 22$ -µF ceramic as the output capacitor.

**Table 11-3. Selected Output Capacitor** 

FREQUENCY	C <sub>OUT</sub>	SIZE/COST	TRANSIENT PERFORMANCE
400 KHz	3 × 47-μF ceramic	Small size	Good
400 KHz	2 × 47-μF ceramic	Small size	Minimum
400 KHz	$4 \times 22 \mu F + 1 \times 260 \mu F$ , < 50-mΩ electrolytic	Larger size, low cost	Good
400 KHz	1 × 4.7 μF + 2 × 10 μF + 1 × 260 μF, < 50-mΩ electrolytic	Lowest cost	Minimum

### 11.2.2.5 Input Capacitor Selection

The TPS2585x-Q1 device requires a high frequency input decoupling capacitor or capacitors, depending on the application. A high-quality ceramic capacitor type X5R or X7R with sufficient voltage rating is recommended. The ceramic input capacitors provide a low impedance source to the converter in addition to supplying the ripple current and isolating switching noise from other circuits. The typical recommended value for the high frequency decoupling capacitor is 10  $\mu$ F of ceramic capacitance. This must be rated for at least the maximum input voltage that the application requires; preferably twice the maximum input voltage. This capacitance can be increased to help reduce input voltage ripple, maintain the input voltage during load transients, or both. In addition, a small case size 100-nF ceramic capacitor must be used at IN and PGND, immediately adjacent to the converter. This provides a high frequency bypass for the control circuits internal to the device. For this example a 10- $\mu$ F, 50-V, X7R (or better) ceramic capacitor is chosen, and the 100-nF ceramic capacitor must also be rated at 50 V with an X7R or better dielectric.

Additionally, an electrolytic capacitor on the input in parallel with the ceramics can be required, especially if long leads from the automotive battery to the IN pin of the TPS2585x-Q1, cold or warm engine crank requirements, and so forth. The moderate ESR of this capacitor is used to provide damping to the voltage spike due to the lead inductance of the cable or the trace.

#### 11.2.2.6 Bootstrap Capacitor Selection

The TPS2585x-Q1 design requires a bootstrap capacitor ( $C_{BOOT}$ ). The recommended capacitor is 100 nF and rated 16 V or higher. The bootstrap capacitor is located between the SW pin and the BOOT pin. It stores energy that is used to supply the gate drivers for the power MOSFETs. The bootstrap capacitor must be a high-quality ceramic type with an X7R or X5R grade dielectric for temperature stability.

#### 11.2.2.7 Undervoltage Lockout Set-Point

The system undervoltage lockout (UVLO) is adjusted using the external voltage divider network of  $R_{\text{ENT}}$  and  $R_{\text{ENB}}$ . The UVLO has two thresholds, one for power up when the input voltage is rising and one for power down or brownouts when the input voltage is falling. Equation 13 can be used to determine the  $V_{\text{IN}}$  UVLO level.

$$V_{IN\_RISING} = V_{ENH} \times \frac{R_{ENT} + R_{ENB}}{R_{ENB}}$$
(13)

The EN rising threshold ( $V_{ENH}$ ) for the TPS2585x-Q1 is set to be 1.3 V (typical). Choose 10 k $\Omega$  for R<sub>ENB</sub> to minimize input current from the supply. If the desired V<sub>IN</sub> UVLO level is at 6.0 V, then the value of R<sub>ENT</sub> can be calculated using Equation 14:

$$R_{ENT} = \left(\frac{V_{IN\_RISING}}{V_{ENH}} - 1\right) \times R_{ENB}$$
(14)



Equation 14 yields a value of 36.1 k $\Omega$ . The resulting falling UVLO threshold equals 5.5 V and can be calculated by Equation 15, where EN hysteresis (V<sub>EN HYS</sub>) is 0.1 V (typical).

$$V_{IN\_FALLING} = \left(V_{ENH} - V_{EN\_HYS}\right) \times \frac{R_{ENT} + R_{ENB}}{R_{ENB}}$$
(15)

Note that it cannot connect EN to IN pin directly for self-start up. Because the voltage rating of EN pin is 11 V, tying it to VIN directly damages the device. The simplest way to enable the operation of the TPS2585x-Q1 is to connect the EN to  $V_{SENSE}$ . This connection allows the automatic start up when VIN is within the operation range.


## 11.2.2.8 Cable Compensation Set-Point

The TPS2585x-Q1 needs to short the VSET pin to ground to enable the cable compensation. With that setting, the buck regulator increases its output voltage linearly as the load current increases, and the voltage compensation at the currents of the USB ports greater than 2.4 A is 90 mV.




## 11.2.3 Application Curves


Unless otherwise specified the following conditions apply:  $V_{IN}$  = 13.5 V,  $f_{SW}$  = 400 kHz, L = 3.3  $\mu$ H,  $C_{SENSE}$  = 141  $\mu$ F,  $C_{PA\_BUS}$  = 1  $\mu$ F,  $C_{PB\_BUS}$  = 1  $\mu$ F,  $C_{PA\_BUS}$  = 1  $\mu$ F,



















## 12 Power Supply Recommendations

The input supply must be able to withstand the maximum input current and maintain a stable voltage. The resistance of the input supply rail must be low enough that an input current transient does not cause a high enough drop at the TPS2585x-Q1 supply voltage that it causes a false UVLO fault triggering and system reset. If the TPS2585x-Q1 is connected to the input supply through long wires or PCB traces, special care is required to achieve good performance. An additional bulk capacitance can be required in addition to the ceramic input capacitors. The amount of bulk capacitance is not critical, but a 100-µF electrolytic capacitor is a typical choice.

The input voltage must not be allowed to fall below the output voltage. In this scenario, such as a shorted input test, the output capacitors discharge through the internal parasitic diode found between the VIN and SW pins of the device. During this condition, the current can become uncontrolled, possibly causing damage to the device. If this scenario is considered likely, then a Schottky diode between the input supply and the output must be used.

## 13 Layout

## 13.1 Layout Guidelines

The PCB layout of any bulk converter is critical to the optimal performance of the design. Bad PCB layout can disrupt the operation of an otherwise good schematic design. Even if the converter regulates correctly, bad PCB layout can mean the difference between a robust design and one that cannot be mass produced. Furthermore, the EMI performance of the converter is dependent on the PCB layout to a great extent. The following guidelines will help users design a PCB with the best power conversion performance, thermal performance, and minimized generation of unwanted EMI.

- 1. The input bypass capacitor, C<sub>IN</sub>, must be placed as close as possible to the IN and PGND pins. The high frequency ceramic bypass capacitors at the input side provide a primary path for the high di/dt components of the pulsing current. Use a wide VIN plane on a lower layer to connect both of the VIN pairs together to the input supply. Grounding for both the input and output capacitors must consist of localized top-side planes that connect to the PGND pin and PAD.
- 2. Use ground plane in one of the middle layers as noise shielding and heat dissipation path.
- 3. Use wide traces for the  $C_{BOOT}$  capacitor. Place the  $C_{BOOT}$  capacitor as close to the device with short, wide traces to the BOOT and SW pins.
- 4. The SW pin connecting to the inductor must be as short as possible, and just wide enough to carry the load current without excessive heating. Short, thick traces or copper pours (shapes) must be used for a high current conduction path to minimize parasitic resistance. The output capacitors must be placed close to the V<sub>SENSE</sub> end of the inductor and closely grounded to PGND pin and exposed PAD.
- 5. R<sub>ILIM</sub> and R<sub>FREQ</sub> resistors must be placed as close as possible to the ILIM and FREQ pins and connected to AGND. If needed, these components can be placed on the bottom side of the PCB with signals routed through small vias, and the traces need far away from noisy nets like SW, BOOT.
- 6. Make V<sub>IN</sub>, V<sub>SENSE</sub>, and ground bus connections as wide as possible. This action reduces any voltage drops on the input or output paths of the converter and maximizes efficiency.
- 7. Provide enough PCB area for proper heat sinking. Enough copper area must be used to ensure a low  $R_{\theta JA}$ , commensurate with the maximum load current and ambient temperature. Make the top and bottom PCB layers with 2-ounce copper; and no less than 1 ounce. If the PCB design uses multiple copper layers (recommended), thermal vias can also be connected to the inner layer heat-spreading ground planes. Note that the package of this device dissipates heat through all pins. Wide traces must be used for all pins except where noise considerations dictate minimization of area.
- 8. Use an array of heat-sinking vias to connect the exposed pad to the ground plane on the bottom PCB layer. If the PCB has multiple copper layers, these thermal vias can also be connected to inner layer heat-spreading ground planes. Ensure enough copper area is used for heat-sinking to keep the junction temperature below 150°C.
- 9. Keep the CC lines close to the same length. Do not create stubs or test points on the CC lines.



#### 13.2 Layout Example




Figure 13-1. Layout Example

#### 13.3 Ground Plane and Thermal Considerations

TI recommends to use one of the middle layers as a solid ground plane. Ground plane provides shielding for sensitive circuits and traces. It also provides a quiet reference potential for the control circuitry. The AGND and PGND pins must be connected to the ground plane using vias right next to the bypass capacitors. The PGND pin is connected to the source of the internal low-side MOSFET switch, and also connected directly to the grounds of the input and output capacitors. The PGND net contains noise at the switching frequency and can bounce due to load variations. The PGND trace, as well as VIN and SW traces, must be constrained to one side of the ground plane. The other side of the ground plane contains much less noise and must be used for sensitive routes.

TI recommends to provide adequate device heat sinking by using the PAD of the IC as the primary thermal path. Use a minimum  $4 \times 2$  array of 12-mil thermal vias to connect the PAD to the system ground plane heat sink. The vias must be evenly distributed under the PAD. Use as much copper as possible, for system ground plane, on the top and bottom layers for the best heat dissipation. Use a four-layer board with the copper thickness for the four layers, starting from the top of 2 oz / 1 oz / 2 oz. Four layer boards with enough copper thickness provide low current conduction impedance, proper shielding, and lower thermal resistance.

The thermal characteristics of the TPS2585x-Q1 are specified using the parameter  $\theta_{JA}$ , which characterizes the junction temperature of silicon to the ambient temperature in a specific system. Although the value of  $\theta_{JA}$  is dependent on many variables, it still can be used to approximate the operating junction temperature of the device. To obtain an estimate of the device junction temperature, one can use the following relationship:

$$T_{J} = P_{D} \times \theta_{JA} + T_{A} \tag{16}$$

#### where

- T<sub>J</sub> = Junction temperature in °C
- $P_D = V_{IN} \times I_{IN} \times (1 \text{Efficiency}) 1.1 \times I_{OUT}^2 \times \text{DCR}$  in Watt DCR = Inductor DC parasitic resistance in  $\Omega$
- $\theta_{JA}$  = Junction-to-ambient thermal resistance of the device in °C/W
- T<sub>A</sub> = Ambient temperature in °C

The maximum operating junction temperature of the TPS2585x-Q1 is 150°C.  $\theta_{JA}$  is highly related to PCB size and layout, as well as environmental factors such as heat sinking and air flow.



## 14 Device and Documentation Support

## 14.1 Receiving Notification of Documentation Updates

To receive notification of documentation updates, navigate to the device product folder on ti.com. Click on *Subscribe to updates* to register and receive a weekly digest of any product information that has changed. For change details, review the revision history included in any revised document.

## 14.2 Support Resources

TI E2E<sup>™</sup> support forums are an engineer's go-to source for fast, verified answers and design help — straight from the experts. Search existing answers or ask your own question to get the quick design help you need.

Linked content is provided "AS IS" by the respective contributors. They do not constitute TI specifications and do not necessarily reflect TI's views; see TI's Terms of Use.

#### 14.3 Trademarks

HotRod<sup>™</sup> and TI E2E<sup>™</sup> are trademarks of Texas Instruments. USB Type-C<sup>®</sup> is a registered trademark of USB Implementers Forum. All trademarks are the property of their respective owners.

#### 14.4 Electrostatic Discharge Caution



This integrated circuit can be damaged by ESD. Texas Instruments recommends that all integrated circuits be handled with appropriate precautions. Failure to observe proper handling and installation procedures can cause damage.

ESD damage can range from subtle performance degradation to complete device failure. Precision integrated circuits may be more susceptible to damage because very small parametric changes could cause the device not to meet its published specifications.

## 14.5 Glossary

TI Glossary

This glossary lists and explains terms, acronyms, and definitions.



# 15 Mechanical, Packaging, and Orderable Information

The following pages include mechanical, packaging, and orderable information. This information is the most current data available for the designated devices. This data is subject to change without notice and revision of this document. For browser-based versions of this data sheet, refer to the left-hand navigation.

www.ti.com 5-Sep-2024

#### PACKAGING INFORMATION

Orderable Device	Status	Package Type	Package Drawing	Pins	Package Qty	Eco Plan	Lead finish/ Ball material	MSL Peak Temp	Op Temp (°C)	Device Marking (4/5)	Samples
TPS25858QRPQRQ1	ACTIVE	VQFN-HR	RPQ	25	3000	RoHS & Green	NIPDAU   SN	Level-2-260C-1 YEAR	-40 to 125	T25858	Samples
TPS25859QRPQRQ1	ACTIVE	VQFN-HR	RPQ	25	3000	RoHS & Green	NIPDAU   SN	Level-2-260C-1 YEAR	-45 to 125	T25859	Samples

(1) The marketing status values are defined as follows:

**ACTIVE:** Product device recommended for new designs.

LIFEBUY: TI has announced that the device will be discontinued, and a lifetime-buy period is in effect.

NRND: Not recommended for new designs. Device is in production to support existing customers, but TI does not recommend using this part in a new design.

PREVIEW: Device has been announced but is not in production. Samples may or may not be available.

**OBSOLETE:** TI has discontinued the production of the device.

(2) RoHS: TI defines "RoHS" to mean semiconductor products that are compliant with the current EU RoHS requirements for all 10 RoHS substances, including the requirement that RoHS substance do not exceed 0.1% by weight in homogeneous materials. Where designed to be soldered at high temperatures, "RoHS" products are suitable for use in specified lead-free processes. TI may reference these types of products as "Pb-Free".

RoHS Exempt: TI defines "RoHS Exempt" to mean products that contain lead but are compliant with EU RoHS pursuant to a specific EU RoHS exemption.

Green: TI defines "Green" to mean the content of Chlorine (Cl) and Bromine (Br) based flame retardants meet JS709B low halogen requirements of <=1000ppm threshold. Antimony trioxide based flame retardants must also meet the <=1000ppm threshold requirement.

- (3) MSL, Peak Temp. The Moisture Sensitivity Level rating according to the JEDEC industry standard classifications, and peak solder temperature.
- (4) There may be additional marking, which relates to the logo, the lot trace code information, or the environmental category on the device.
- (5) Multiple Device Markings will be inside parentheses. Only one Device Marking contained in parentheses and separated by a "~" will appear on a device. If a line is indented then it is a continuation of the previous line and the two combined represent the entire Device Marking for that device.
- (6) Lead finish/Ball material Orderable Devices may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead finish/Ball material values may wrap to two lines if the finish value exceeds the maximum column width.

**Important Information and Disclaimer:** The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.



# **PACKAGE OPTION ADDENDUM**

www.ti.com 5-Sep-2024

# **PACKAGE MATERIALS INFORMATION**

www.ti.com 3-Nov-2023

## TAPE AND REEL INFORMATION





A0	Dimension designed to accommodate the component width
В0	Dimension designed to accommodate the component length
K0	Dimension designed to accommodate the component thickness
W	Overall width of the carrier tape
P1	Pitch between successive cavity centers

## QUADRANT ASSIGNMENTS FOR PIN 1 ORIENTATION IN TAPE



#### \*All dimensions are nominal

Device	Package Type	Package Drawing		SPQ	Reel Diameter (mm)	Reel Width W1 (mm)	A0 (mm)	B0 (mm)	K0 (mm)	P1 (mm)	W (mm)	Pin1 Quadrant
TPS25858QRPQRQ1	VQFN- HR	RPQ	25	3000	330.0	12.4	3.71	4.71	1.1	8.0	12.0	Q1
TPS25859QRPQRQ1	VQFN- HR	RPQ	25	3000	330.0	12.4	3.71	4.71	1.1	8.0	12.0	Q1

www.ti.com 3-Nov-2023




## \*All dimensions are nominal

Device	Package Type	Package Drawing	Pins	SPQ	Length (mm)	Width (mm)	Height (mm)
TPS25858QRPQRQ1	VQFN-HR	RPQ	25	3000	367.0	367.0	35.0
TPS25859QRPQRQ1	VQFN-HR	RPQ	25	3000	367.0	367.0	35.0



PLASTIC QUAD FLATPACK - NO LEAD




#### NOTES:

- 1. All linear dimensions are in millimeters. Any dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.
  2. This drawing is subject to change without notice.
- 3. The package thermal pad must be soldered to the printed circuit board for thermal and mechanical performance.



PLASTIC QUAD FLATPACK - NO LEAD




NOTES: (continued)

- 4. This package is designed to be soldered to a thermal pad on the board. For more information, see Texas Instruments literature number SLUA271 (www.ti.com/lit/slua271).
- 5. Vias are optional depending on application, refer to device data sheet. If any vias are implemented, refer to their locations shown on this view. It is recommended that vias under paste be filled, plugged or tented.



PLASTIC QUAD FLATPACK - NO LEAD



NOTES: (continued)

6. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.



## IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATA SHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, regulatory or other requirements.

These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you will fully indemnify TI and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to TI's Terms of Sale or other applicable terms available either on ti.com or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products.

TI objects to and rejects any additional or different terms you may have proposed.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265 Copyright © 2024, Texas Instruments Incorporated