

# LM4050-N/-Q1 Precision Micropower Shunt Voltage Reference

## 1 Features

- Small Package: SOT-23
- No Output Capacitor Required
- Tolerates Capacitive Loads
- Fixed Reverse Breakdown Voltages of 2.048V, 2.5V, 4.096V, 5V, 8.192V, and 10V
- Key Specifications (LM4050-N)
  - Output Voltage Tolerance (A Grade, 25°C)  $\pm 0.1\%$  (Maximum)
  - Low Output Noise (10Hz to 10kHz) 41 $\mu$ Vrms (Typical)
  - Wide Operating Current Range 60 $\mu$ A to 15mA
  - Industrial Temperature Range  $-40^{\circ}\text{C}$  to  $85^{\circ}\text{C}$
  - Extended Temperature Range  $-40^{\circ}\text{C}$  to  $125^{\circ}\text{C}$
  - Low Temperature Coefficient 50ppm/ $^{\circ}\text{C}$  (max)
  - LM4050-N-Q1 is AEC-Q100 Grade 1 Qualified and are Manufactured on an Automotive Grade Flow

## 2 Applications

- [Battery-Powered Equipment](#)
- [Data-Acquisition Systems](#)
- [Instrumentation and Test Equipment](#)
- [Process Control](#)
- [Energy Management/Metering](#)
- [Automotive Electronics](#)
- [Precision Audio](#)

## 3 Description

Designed for space-critical applications, the LM4050-N precision voltage reference is available in the sub-miniature (3mm  $\times$  1.3mm) SOT-23 surface-mount package. The LM4050-N design eliminates the need for an external stabilizing capacitor while maintaining stability with any capacitive load, thus making the LM4050-N easy to use. Further reducing design effort is the availability of several fixed reverse breakdown voltages: 2.048V, 2.5V, 4.096V, 5V, 8.192V, and 10V. The minimum operating current increases from 60 $\mu$ A for the LM4050-N-2.0 to 100 $\mu$ A for the LM4050-N-10.0. All versions have a maximum operating current of 15mA.

The LM4050-N utilizes fuse and Zener-zap reverse breakdown voltage trim during wafer sort to make sure that the prime parts have an accuracy of better than  $\pm 0.1\%$  (A grade) at 25°C. Bandgap reference temperature drift curvature correction and low dynamic impedance verify stable reverse breakdown voltage accuracy over a wide range of operating temperatures and currents.


All grades and voltage options of the LM4050-N are available in both an industrial temperature range ( $-40^{\circ}\text{C}$  and  $85^{\circ}\text{C}$ ) and an extended temperature range ( $-40^{\circ}\text{C}$  and  $125^{\circ}\text{C}$ ).

### Device Information

| PART NUMBER | PACKAGE <sup>(1)</sup> | BODY SIZE (NOM) <sup>(2)</sup> |
|-------------|------------------------|--------------------------------|
| LM4050-N    | SOT-23 (3)             | 2.92mm $\times$ 1.30mm         |
| LM4050-N-Q1 |                        |                                |

(1) For all available packages, see the orderable addendum at the end of the data sheet.

(2) The package size (length  $\times$  width) is a nominal value and includes pins, where applicable.




**Shunt Regulator Schematic**



## Table of Contents

|                                                  |           |                                                                  |           |
|--------------------------------------------------|-----------|------------------------------------------------------------------|-----------|
| <b>1 Features</b> .....                          | <b>1</b>  | 7.1 Overview.....                                                | <b>14</b> |
| <b>2 Applications</b> .....                      | <b>1</b>  | 7.2 Functional Block Diagram.....                                | <b>14</b> |
| <b>3 Description</b> .....                       | <b>1</b>  | 7.3 Feature Description.....                                     | <b>14</b> |
| <b>4 Pin Configuration and Functions</b> .....   | <b>3</b>  | 7.4 Device Functional Modes.....                                 | <b>14</b> |
| <b>5 Specifications</b> .....                    | <b>4</b>  | <b>8 Application and Implementation</b> .....                    | <b>15</b> |
| 5.1 Absolute Maximum Ratings.....                | <b>4</b>  | 8.1 Application Information.....                                 | <b>15</b> |
| 5.2 ESD Ratings.....                             | <b>4</b>  | 8.2 Typical Applications.....                                    | <b>16</b> |
| 5.3 Recommended Operating Conditions.....        | <b>5</b>  | 8.3 Power Supply Recommendations.....                            | <b>22</b> |
| 5.4 Thermal Information.....                     | <b>5</b>  | 8.4 Layout.....                                                  | <b>22</b> |
| 5.5 Electrical Characteristics: 2V Option.....   | <b>6</b>  | <b>9 Device and Documentation Support</b> .....                  | <b>23</b> |
| 5.6 Electrical Characteristics: 2.5V Option..... | <b>7</b>  | 9.1 Support Resources.....                                       | <b>23</b> |
| 5.7 Electrical Characteristics: 4.1V Option..... | <b>8</b>  | 9.2 Trademarks.....                                              | <b>23</b> |
| 5.8 Electrical Characteristics: 5V Option.....   | <b>9</b>  | 9.3 Electrostatic Discharge Caution.....                         | <b>23</b> |
| 5.9 Electrical Characteristics: 8.2V Option..... | <b>10</b> | 9.4 Glossary.....                                                | <b>23</b> |
| 5.10 Electrical Characteristics: 10V Option..... | <b>11</b> | <b>10 Revision History</b> .....                                 | <b>23</b> |
| 5.11 Typical Characteristics.....                | <b>12</b> | <b>11 Mechanical, Packaging, and Orderable Information</b> ..... | <b>24</b> |
| <b>6 Parameter Measurement Information</b> ..... | <b>13</b> |                                                                  |           |
| <b>7 Detailed Description</b> .....              | <b>14</b> |                                                                  |           |

## 4 Pin Configuration and Functions



\*This pin must be left floating or connected to pin 2.<sup>(1)</sup>

**Figure 4-1. DBZ Package**  
**3-Pin SOT-23**  
**Top View**

**Table 4-1. Pin Functions**

| PIN     |     | I/O | DESCRIPTION                              |
|---------|-----|-----|------------------------------------------|
| NAME    | NO. |     |                                          |
| Cathode | 1   | I/O | Shunt current and input voltage          |
| Anode   | 2   | O   | Common pin, normally connected to ground |
| NC      | 3   | —   | No internal connection <sup>(1)</sup>    |

- (1) In applications with high electromagnetic interference (for example, when placed near transformers or other electromagnetic sources) or significant high-frequency switching noise, TI recommends to connect this pin to the anode.

## 5 Specifications

### 5.1 Absolute Maximum Ratings

See [\(1\)](#), [\(2\)](#)

|                                                               | MIN | MAX | UNIT |
|---------------------------------------------------------------|-----|-----|------|
| Reverse Current                                               |     | 20  | mA   |
| Forward Current                                               |     | 10  | mA   |
| Power Dissipation ( $T_A = 25^\circ\text{C}$ ) <sup>(1)</sup> |     | 280 | mW   |
| Maximum Junction Temperature <sup>(2)</sup>                   |     | 150 | °C   |
| Storage Temperature                                           | –65 | 150 | °C   |

- (1) Stresses beyond those listed under *Absolute Maximum Ratings* may cause permanent damage to the device. These are stress ratings only, which do not imply functional operation of the device at these or any other conditions beyond those indicated under *Recommended Operating Conditions*. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability.
- (2) If Military/Aerospace specified devices are required, please contact the Texas Instruments Sales Office/ Distributors for availability and specifications.

### 5.2 ESD Ratings

|                                            | VALUE                                                                          | UNIT  |
|--------------------------------------------|--------------------------------------------------------------------------------|-------|
| V <sub>(ESD)</sub> Electrostatic discharge | Human body model (HBM), per ANSI/ESDA/JEDEC JS-001 <sup>(1)</sup>              | ±2000 |
|                                            | Charged device model (CDM), per JEDEC specification JESD22-C101 <sup>(2)</sup> | ±500  |

- (1) JEDEC document JEP155 states that 500V HBM allows safe manufacturing with a standard ESD control process.
- (2) JEDEC document JEP157 states that 250V CDM allows safe manufacturing with a standard ESD control process.

## 5.3 Recommended Operating Conditions

over operating free-air temperature range (unless otherwise noted) <sup>(1)</sup> <sup>(1)</sup>

|                              |                            | MIN | MAX | UNIT |
|------------------------------|----------------------------|-----|-----|------|
| Industrial Temperature Range | Ambient Temperature Range  | –40 | 85  | °C   |
|                              | Junction Temperature Range | –40 | 85  | °C   |
| Extended Temperature Range   | Ambient Temperature Range  | –40 | 125 | °C   |
|                              | Junction Temperature       | –40 | 125 | °C   |

(1) *Recommended Operating Conditions* are conditions under the device is intended to be functional. For specifications and conditions, see *Electrical Characteristics* section.

## 5.4 Thermal Information

| THERMAL METRIC <sup>(1)</sup> |                                              | LM4050-N/-Q1 | UNIT |
|-------------------------------|----------------------------------------------|--------------|------|
|                               |                                              | DBZ (SOT-23) |      |
|                               |                                              | 3 PINS       |      |
| R <sub>θJA</sub>              | Junction-to-ambient thermal resistance       | 287          | °C/W |
| R <sub>θJC(top)</sub>         | Junction-to-case (top) thermal resistance    | 106.6        | °C/W |
| R <sub>θJB</sub>              | Junction-to-board thermal resistance         | 57.7         | °C/W |
| Ψ <sub>JT</sub>               | Junction-to-top characterization parameter   | 5.5          | °C/W |
| Ψ <sub>JB</sub>               | Junction-to-board characterization parameter | 56.4         | °C/W |
| R <sub>θJC(bot)</sub>         | Junction-to-case (bottom) thermal resistance | N/A          | °C/W |

(1) For more information about traditional and new thermal metrics, see the *Semiconductor and IC Package Thermal Metrics* application report, [SPRA953](#).

## 5.5 Electrical Characteristics: 2V Option

All other limits  $T_A = T_J = 25^\circ\text{C}$ . The grades A, B and C designate initial Reverse Breakdown Voltage tolerances of  $\pm 0.1\%$ ,  $\pm 0.2\%$ , and  $0.5\%$  respectively.

| PARAMETER               |                                                                               | TEST CONDITIONS                                                                            |                        | MIN <sup>(4)</sup> | TYP <sup>(3)</sup> | MAX <sup>(4)</sup> | UNIT                       |
|-------------------------|-------------------------------------------------------------------------------|--------------------------------------------------------------------------------------------|------------------------|--------------------|--------------------|--------------------|----------------------------|
| $V_R$                   | Reverse Breakdown Voltage                                                     | $I_R = 100\mu\text{A}$                                                                     |                        |                    | 2.048              |                    | V                          |
|                         | Reverse breakdown voltage tolerance <sup>(5)</sup>                            | $I_R = 100\mu\text{A}$                                                                     | LM4050AIM3, LM4050AEM3 |                    |                    | $\pm 2.048$        | mV                         |
|                         |                                                                               |                                                                                            | LM4050BIM3, LM4050BEM3 |                    |                    | $\pm 4.096$        |                            |
|                         |                                                                               |                                                                                            | LM4050CIM3, LM4050CEM3 |                    |                    | $\pm 10.24$        |                            |
|                         |                                                                               | Industrial temperature range<br>$T_A = T_J = T_{\text{MIN}}$ to $T_{\text{MAX}}$           | LM4050AIM3             |                    |                    | $\pm 9.0112$       |                            |
|                         |                                                                               |                                                                                            | LM4050BIM3             |                    |                    | $\pm 11.4688$      |                            |
|                         |                                                                               |                                                                                            | LM4050CIM3             |                    |                    | $\pm 14.7456$      |                            |
|                         |                                                                               | Extended temperature range<br>$T_A = T_J = T_{\text{MIN}}$ to $T_{\text{MAX}}$             | LM4050AEM3             |                    |                    | $\pm 12.288$       |                            |
|                         |                                                                               |                                                                                            | LM4050BEM3             |                    |                    | $\pm 14.7456$      |                            |
|                         |                                                                               |                                                                                            | LM4050CEM3             |                    |                    | $\pm 17.2032$      |                            |
| $I_{\text{RMIN}}$       | Minimum operating current                                                     | $T_A = T_J = 25^\circ\text{C}$                                                             |                        |                    | 41                 | 60                 | $\mu\text{A}$              |
|                         |                                                                               | $T_A = T_J = T_{\text{MIN}}$ to $T_{\text{MAX}}$                                           |                        |                    |                    | 65                 |                            |
| $\Delta V_R/\Delta T$   | Average reverse breakdown voltage temperature coefficient <sup>(5)</sup>      | $I_R = 10\text{mA}$                                                                        |                        |                    | $\pm 20$           |                    | ppm/ $^\circ\text{C}$      |
|                         |                                                                               | $I_R = 1\text{mA}$                                                                         |                        |                    | $\pm 15$           |                    |                            |
|                         |                                                                               | $I_R = 100\mu\text{A}, T_A = T_J = 25^\circ\text{C}$                                       |                        |                    | $\pm 15$           |                    |                            |
|                         |                                                                               | $I_R = 100\mu\text{A}, T_A = T_J = T_{\text{MIN}}$ to $T_{\text{MAX}}$                     |                        |                    |                    | $\pm 50$           |                            |
| $\Delta V_R/\Delta I_R$ | Reverse breakdown voltage change with operating current change <sup>(6)</sup> | $I_{\text{RMIN}} \leq I_R \leq 1\text{mA}, T_A = T_J = 25^\circ\text{C}$                   |                        |                    | 0.3                | 0.8                | mV                         |
|                         |                                                                               | $I_{\text{RMIN}} \leq I_R \leq 1\text{mA}, T_A = T_J = T_{\text{MIN}}$ to $T_{\text{MAX}}$ |                        |                    |                    | 1.2                |                            |
|                         |                                                                               | $1\text{mA} \leq I_R \leq 15\text{mA}, T_A = T_J = 25^\circ\text{C}$                       |                        |                    | 2.3                | 6                  |                            |
|                         |                                                                               | $1\text{mA} \leq I_R \leq 15\text{mA}, T_A = T_J = T_{\text{MIN}}$ to $T_{\text{MAX}}$     |                        |                    |                    | 8                  |                            |
| $Z_R$                   | Reverse dynamic impedance                                                     | $I_R = 1\text{mA}, f = 120\text{Hz}, I_{\text{AC}} = 0.1 I_R$                              |                        |                    | 0.3                |                    | $\Omega$                   |
| $e_N$                   | Wideband noise                                                                | $I_R = 100\mu\text{A}, 10\text{Hz} \leq f \leq 10\text{kHz}$                               |                        |                    | 34                 |                    | $\mu\text{V}_{\text{rms}}$ |
| $\Delta V_R$            | Reverse breakdown voltage long term stability                                 | $t = 1000 \text{ hrs}, T = 25^\circ\text{C} \pm 0.1^\circ\text{C}, I_R = 100\mu\text{A}$   |                        |                    | 120                |                    | ppm                        |
| $V_{\text{HYST}}$       | Thermal hysteresis <sup>(7)</sup>                                             | $\Delta T = -40^\circ\text{C}$ to $125^\circ\text{C}$                                      |                        |                    | 0.7                |                    | mV                         |

## 5.6 Electrical Characteristics: 2.5V Option

All other limits  $T_A = T_J = 25^\circ\text{C}$ . The grades A, B and C designate initial Reverse Breakdown Voltage tolerances of  $\pm 0.1\%$ ,  $\pm 0.2\%$ , and  $0.5\%$  respectively.

| PARAMETER               |                                                                               | TEST CONDITIONS                                                                            |                        | MIN <sup>(4)</sup> | TYP <sup>(3)</sup> | MAX <sup>(4)</sup> | UNIT                       |
|-------------------------|-------------------------------------------------------------------------------|--------------------------------------------------------------------------------------------|------------------------|--------------------|--------------------|--------------------|----------------------------|
| $V_R$                   | Reverse breakdown voltage                                                     | $I_R = 100\mu\text{A}$                                                                     |                        | 2.500              |                    |                    | V                          |
|                         |                                                                               | $I_R = 100\mu\text{A}$                                                                     | LM4050AIM3, LM4050AEM3 | $\pm 2.5$          |                    |                    | mV                         |
|                         |                                                                               |                                                                                            | LM4050BIM3, LM4050BEM3 | $\pm 5$            |                    |                    |                            |
|                         |                                                                               |                                                                                            | LM4050CIM3, LM4050CEM3 | $\pm 13$           |                    |                    |                            |
|                         | Reverse breakdown voltage tolerance <sup>(5)</sup>                            | Industrial temperature range,<br>$T_A = T_J = T_{\text{MIN}}$ to $T_{\text{MAX}}$          | LM4050AIM3             | $\pm 11$           |                    |                    | mV                         |
|                         |                                                                               |                                                                                            | LM4050BIM3             | $\pm 24$           |                    |                    |                            |
|                         |                                                                               |                                                                                            | LM4050CIM3             | $\pm 21$           |                    |                    |                            |
|                         |                                                                               | Extended temperature range,<br>$T_A = T_J = T_{\text{MIN}}$ to $T_{\text{MAX}}$            | LM4050AEM3             | $\pm 15$           |                    |                    |                            |
|                         |                                                                               |                                                                                            | LM4050BEM3             | $\pm 18$           |                    |                    |                            |
|                         |                                                                               |                                                                                            | LM4050CEM3             | $\pm 25$           |                    |                    |                            |
| $I_{\text{RMIN}}$       | Minimum operating current                                                     | $T_A = T_J = 25^\circ\text{C}$                                                             |                        | 41                 |                    | 60                 | $\mu\text{A}$              |
|                         |                                                                               | $T_A = T_J = T_{\text{MIN}}$ to $T_{\text{MAX}}$                                           |                        |                    |                    | 65                 |                            |
| $\Delta V_R/\Delta T$   | Average reverse breakdown voltage temperature coefficient <sup>(5)</sup>      | $I_R = 10\text{mA}$                                                                        |                        | $\pm 20$           |                    |                    | ppm/ $^\circ\text{C}$      |
|                         |                                                                               | $I_R = 1\text{mA}$                                                                         |                        | $\pm 15$           |                    |                    |                            |
|                         |                                                                               | $I_R = 100\mu\text{A}, T_A = T_J = 25^\circ\text{C}$                                       |                        | $\pm 15$           |                    |                    |                            |
|                         |                                                                               | $I_R = 100\mu\text{A}, T_A = T_J = T_{\text{MIN}}$ to $T_{\text{MAX}}$                     |                        |                    |                    | $\pm 50$           |                            |
| $\Delta V_R/\Delta I_R$ | Reverse breakdown voltage change with operating current change <sup>(6)</sup> | $I_{\text{RMIN}} \leq I_R \leq 1\text{mA}, T_A = T_J = 25^\circ\text{C}$                   |                        | 0.3                |                    | 0.8                | mV                         |
|                         |                                                                               | $I_{\text{RMIN}} \leq I_R \leq 1\text{mA}, T_A = T_J = T_{\text{MIN}}$ to $T_{\text{MAX}}$ |                        |                    |                    | 1.2                |                            |
| $\Delta V_R/\Delta I_R$ | Reverse breakdown voltage change with operating current change <sup>(6)</sup> | $1\text{mA} \leq I_R \leq 15\text{mA}, T_A = T_J = 25^\circ\text{C}$                       |                        | 2.3                |                    | 6                  | mV                         |
|                         |                                                                               | $1\text{mA} \leq I_R \leq 15\text{mA}, T_A = T_J = T_{\text{MIN}}$ to $T_{\text{MAX}}$     |                        |                    |                    | 8                  |                            |
| $Z_R$                   | Reverse dynamic impedance                                                     | $I_R = 1\text{mA}, f = 120\text{Hz}, I_{\text{AC}} = 0.1 I_R$                              |                        | 0.3                |                    |                    | $\Omega$                   |
| $e_N$                   | Wideband noise                                                                | $I_R = 100\mu\text{A}, 10\text{Hz} \leq f \leq 10\text{kHz}$                               |                        | 41                 |                    |                    | $\mu\text{V}_{\text{rms}}$ |
| $\Delta V_R$            | Reverse breakdown voltage long term stability                                 | $t = 1000\text{ hrs}, T = 25^\circ\text{C} \pm 0.1^\circ\text{C}, I_R = 100\mu\text{A}$    |                        | 120                |                    |                    | ppm                        |
| $V_{\text{HYST}}$       | Thermal hysteresis <sup>(7)</sup>                                             | $\Delta T = -40^\circ\text{C}$ to $125^\circ\text{C}$                                      |                        | 07                 |                    |                    | mV                         |

## 5.7 Electrical Characteristics: 4.1V Option

All other limits  $T_A = T_J = 25^\circ\text{C}$ . The grades A, B and C designate initial Reverse Breakdown Voltage tolerances of  $\pm 0.1\%$ ,  $\pm 0.2\%$ , and  $0.5\%$  respectively.

| PARAMETER               |                                                                               | TEST CONDITIONS                                                                                  |                        | MIN | TYP <sup>(3)</sup> | MAX       | UNIT                       |
|-------------------------|-------------------------------------------------------------------------------|--------------------------------------------------------------------------------------------------|------------------------|-----|--------------------|-----------|----------------------------|
| $V_R$                   | Reverse Breakdown Voltage                                                     | $I_R = 100\mu\text{A}$                                                                           |                        |     | 4.096              |           | V                          |
|                         | Reverse Breakdown Voltage Tolerance <sup>(5)</sup>                            | $I_R = 100\mu\text{A}$                                                                           | LM4050AIM3, LM4050AEM3 |     |                    | $\pm 4.1$ | mV                         |
|                         |                                                                               |                                                                                                  | LM4050BIM3, LM4050BEM3 |     |                    | $\pm 8.2$ |                            |
|                         |                                                                               |                                                                                                  | LM4050CIM3, LM4050CEM3 |     |                    | $\pm 21$  |                            |
|                         |                                                                               | Industrial temperature range,<br>$T_A = T_J = T_{\text{MIN}}$ to $T_{\text{MAX}}$                | LM4050AIM3             |     |                    | $\pm 18$  |                            |
|                         |                                                                               |                                                                                                  | LM4050BIM3             |     |                    | $\pm 22$  |                            |
|                         |                                                                               |                                                                                                  | LM4050CIM3             |     |                    | $\pm 34$  |                            |
|                         |                                                                               | Extended temperature range,<br>$T_A = T_J = T_{\text{MIN}}$ to $T_{\text{MAX}}$                  | LM4050AEM3             |     |                    | $\pm 25$  |                            |
|                         |                                                                               |                                                                                                  | LM4050BEM3             |     |                    | $\pm 29$  |                            |
|                         |                                                                               |                                                                                                  | LM4050CEM3             |     |                    | $\pm 41$  |                            |
| $I_{\text{RMIN}}$       | Minimum Operating Current                                                     | $T_A = T_J = 25^\circ\text{C}$                                                                   |                        |     | 52                 | 68        | $\mu\text{A}$              |
|                         |                                                                               | Industrial temperature range,<br>$T_A = T_J = T_{\text{MIN}}$ to $T_{\text{MAX}}$                |                        |     |                    | 73        |                            |
|                         |                                                                               | Extended temperature range,<br>$T_A = T_J = T_{\text{MIN}}$ to $T_{\text{MAX}}$                  |                        |     |                    | 78        |                            |
| $\Delta V_R/\Delta T$   | Average reverse breakdown voltage temperature coefficient <sup>(5)</sup>      | $I_R = 10\text{mA}$                                                                              |                        |     | $\pm 30$           |           | ppm/ $^\circ\text{C}$      |
|                         |                                                                               | $I_R = 1\text{mA}$                                                                               |                        |     | $\pm 20$           |           |                            |
|                         |                                                                               | $I_R = 100\mu\text{A}$ , $T_A = T_J = 25^\circ\text{C}$                                          |                        |     | $\pm 20$           |           |                            |
|                         |                                                                               | $I_R = 100\mu\text{A}$ ,<br>$T_A = T_J = T_{\text{MIN}}$ to $T_{\text{MAX}}$                     |                        |     |                    | $\pm 50$  |                            |
| $\Delta V_R/\Delta I_R$ | Reverse breakdown voltage change with operating current change <sup>(6)</sup> | $I_{\text{RMIN}} \leq I_R \leq 1\text{mA}$ , $T_A = T_J = 25^\circ\text{C}$                      |                        |     | 0.2                | 0.9       | mV                         |
|                         |                                                                               | $I_{\text{RMIN}} \leq I_R \leq 1\text{mA}$ ,<br>$T_A = T_J = T_{\text{MIN}}$ to $T_{\text{MAX}}$ |                        |     |                    | 1.2       |                            |
|                         |                                                                               | $1\text{mA} \leq I_R \leq 15\text{mA}$ , $T_A = T_J = 25^\circ\text{C}$                          |                        |     | 2                  | 7         |                            |
|                         |                                                                               | $1\text{mA} \leq I_R \leq 15\text{mA}$ ,<br>$T_A = T_J = T_{\text{MIN}}$ to $T_{\text{MAX}}$     |                        |     |                    | 10        |                            |
| $Z_R$                   | Reverse dynamic impedance                                                     | $I_R = 1\text{mA}$ , $f = 120\text{Hz}$ , $I_{\text{AC}} = 0.1 I_R$                              |                        |     | 0.5                |           | $\Omega$                   |
| $e_N$                   | Wideband noise                                                                | $I_R = 100\mu\text{A}$ , $10\text{Hz} \leq f \leq 10\text{kHz}$                                  |                        |     | 93                 |           | $\mu\text{V}_{\text{rms}}$ |
| $\Delta V_R$            | Reverse breakdown voltage long term stability                                 | $t = 1000\text{ hrs}$ , $T = 25^\circ\text{C} \pm 0.1^\circ\text{C}$ , $I_R = 100\mu\text{A}$    |                        |     | 120                |           | ppm                        |
| $V_{\text{HYS}}$        | Thermal hysteresis <sup>(7)</sup>                                             | $\Delta T = -40^\circ\text{C}$ to $125^\circ\text{C}$                                            |                        |     | 1.148              |           | mV                         |



## 5.8 Electrical Characteristics: 5V Option

All other limits  $T_A = T_J = 25^\circ\text{C}$ . The grades A, B and C designate initial Reverse Breakdown Voltage tolerances of  $\pm 0.1\%$ ,  $\pm 0.2\%$  and  $0.5\%$  respectively.

| PARAMETER               |                                                                               | TEST CONDITIONS                                                                                 |                        | MIN <sup>(4)</sup> | TYP <sup>(3)</sup> | MAX <sup>(4)</sup> | UNIT                       |
|-------------------------|-------------------------------------------------------------------------------|-------------------------------------------------------------------------------------------------|------------------------|--------------------|--------------------|--------------------|----------------------------|
| $V_R$                   | Reverse Breakdown Voltage                                                     | $I_R = 100\mu\text{A}$                                                                          |                        | 5                  |                    |                    | V                          |
|                         | Reverse Breakdown Voltage Tolerance <sup>(5)</sup>                            | $I_R = 100\mu\text{A}$                                                                          | LM4050AIM3, LM4050AEM3 | $\pm 5$            |                    |                    | mV                         |
|                         |                                                                               |                                                                                                 | LM4050BIM3, LM4050BEM3 | $\pm 10$           |                    |                    |                            |
|                         |                                                                               |                                                                                                 | LM4050CIM3, LM4050CEM3 | $\pm 25$           |                    |                    |                            |
|                         |                                                                               | Industrial Temp. Range<br>$T_A = T_J = T_{\text{MIN}}$ to $T_{\text{MAX}}$                      | LM4050AIM3             | $\pm 22$           |                    |                    |                            |
|                         |                                                                               |                                                                                                 | LM4050BIM3             | $\pm 27$           |                    |                    |                            |
|                         |                                                                               |                                                                                                 | LM4050CIM3             | $\pm 42$           |                    |                    |                            |
|                         |                                                                               | Extended Temp. Range<br>$T_A = T_J = T_{\text{MIN}}$ to $T_{\text{MAX}}$                        | LM4050AEM3             | $\pm 30$           |                    |                    |                            |
|                         |                                                                               |                                                                                                 | LM4050BEM3             | $\pm 35$           |                    |                    |                            |
|                         |                                                                               |                                                                                                 | LM4050CEM3             | $\pm 50$           |                    |                    |                            |
| $I_{\text{RMIN}}$       | Minimum Operating Current                                                     | $T_A = T_J = 25^\circ\text{C}$                                                                  |                        | 56                 |                    | 74                 | $\mu\text{A}$              |
|                         |                                                                               | Industrial Temp. Range<br>$T_A = T_J = T_{\text{MIN}}$ to $T_{\text{MAX}}$                      |                        |                    |                    | 80                 |                            |
|                         |                                                                               | Extended Temp. Range<br>$T_A = T_J = T_{\text{MIN}}$ to $T_{\text{MAX}}$                        |                        |                    |                    | 90                 |                            |
| $\Delta V_R/\Delta T$   | Average Reverse Breakdown Voltage Temperature Coefficient <sup>(5)</sup>      | $I_R = 10\text{mA}$                                                                             |                        | $\pm 30$           |                    |                    | ppm/ $^\circ\text{C}$      |
|                         |                                                                               | $I_R = 1\text{mA}$                                                                              |                        | $\pm 20$           |                    |                    |                            |
|                         |                                                                               | $I_R = 100\mu\text{A}$ , $T_A = T_J = 25^\circ\text{C}$                                         |                        | $\pm 20$           |                    |                    |                            |
|                         |                                                                               | $I_R = 100\mu\text{A}$<br>$T_A = T_J = T_{\text{MIN}}$ to $T_{\text{MAX}}$                      |                        |                    |                    | $\pm 50$           |                            |
| $\Delta V_R/\Delta I_R$ | Reverse Breakdown Voltage Change with Operating Current Change <sup>(6)</sup> | $I_{\text{RMIN}} \leq I_R \leq 1\text{mA}$ , $T_A = T_J = 25^\circ\text{C}$                     |                        | 0.2                |                    | 1                  | mV                         |
|                         |                                                                               | $I_{\text{RMIN}} \leq I_R \leq 1\text{mA}$<br>$T_A = T_J = T_{\text{MIN}}$ to $T_{\text{MAX}}$  |                        |                    |                    | 1.4                |                            |
|                         |                                                                               | $1\text{mA} \leq I_R \leq 15\text{mA}$ , $T_A = T_J = 25^\circ\text{C}$                         |                        | 2                  |                    | 8                  |                            |
|                         |                                                                               | $1\text{mA} \leq I_R \leq 15\text{mA}$<br>$T_A = T_J = T_{\text{MIN}}$ to $T_{\text{MAX}}$      |                        |                    |                    | 12                 |                            |
| $Z_R$                   | Reverse Dynamic Impedance                                                     | $I_R = 1\text{mA}$ , $f = 120\text{Hz}$                                                         |                        | 0.5                |                    |                    | $\Omega$                   |
|                         |                                                                               | $I_{\text{AC}} = 0.1 I_R$                                                                       |                        |                    |                    |                    |                            |
| $e_N$                   | Wideband Noise                                                                | $I_R = 100\mu\text{A}$<br>$10\text{Hz} \leq f \leq 10\text{kHz}$                                |                        | 93                 |                    |                    | $\mu\text{V}_{\text{rms}}$ |
| $\Delta V_R$            | Reverse Breakdown Voltage Long Term Stability                                 | $t = 1000\text{ hrs}$<br>$T = 25^\circ\text{C} \pm 0.1^\circ\text{C}$<br>$I_R = 100\mu\text{A}$ |                        | 120                |                    |                    | ppm                        |
| $V_{\text{HYST}}$       | Thermal Hysteresis <sup>(7)</sup>                                             | $\Delta T = -40^\circ\text{C}$ to $125^\circ\text{C}$                                           |                        | 1.4                |                    |                    | mV                         |

## 5.9 Electrical Characteristics: 8.2V Option

All other limits  $T_A = T_J = 25^\circ\text{C}$ . The grades A, B and C designate initial Reverse Breakdown Voltage tolerances of  $\pm 0.1\%$  and  $\pm 0.2\%$  and  $0.5\%$  respectively.

| PARAMETER               |                                                                               | TEST CONDITIONS                                                                                 |                        | MIN <sup>(4)</sup> | TYP <sup>(3)</sup> | MAX <sup>(4)</sup> | UNIT                       |
|-------------------------|-------------------------------------------------------------------------------|-------------------------------------------------------------------------------------------------|------------------------|--------------------|--------------------|--------------------|----------------------------|
| $V_R$                   | Reverse Breakdown Voltage                                                     | $I_R = 150\mu\text{A}$                                                                          |                        | 8.192              |                    |                    | V                          |
|                         | Reverse Breakdown Voltage Tolerance <sup>(5)</sup>                            | $I_R = 150\mu\text{A}$                                                                          | LM4050AIM3, LM4050AEM3 |                    |                    | $\pm 8.2$          | mV                         |
|                         |                                                                               |                                                                                                 | LM4050BIM3, LM4050BEM3 |                    |                    | $\pm 16$           |                            |
|                         |                                                                               |                                                                                                 | LM4050CIM3, LM4050CEM3 |                    |                    | $\pm 41$           |                            |
|                         |                                                                               | Industrial Temp. Range<br>$T_A = T_J = T_{\text{MIN}}$ to $T_{\text{MAX}}$                      | LM4050AIM3             |                    |                    | $\pm 35$           |                            |
|                         |                                                                               |                                                                                                 | LM4050BIM3             |                    |                    | $\pm 43$           |                            |
|                         |                                                                               |                                                                                                 | LM4050CIM3             |                    |                    | $\pm 68$           |                            |
|                         |                                                                               | Extended Temp. Range<br>$T_A = T_J = T_{\text{MIN}}$ to $T_{\text{MAX}}$                        | LM4050AEM3             |                    |                    | $\pm 49$           |                            |
|                         |                                                                               |                                                                                                 | LM4050BEM3             |                    |                    | $\pm 57$           |                            |
|                         |                                                                               |                                                                                                 | LM4050CEM3             |                    |                    | $\pm 82$           |                            |
| $I_{\text{RMIN}}$       | Minimum Operating Current                                                     | $T_A = T_J = 25^\circ\text{C}$                                                                  |                        |                    | 74                 | 91                 | $\mu\text{A}$              |
|                         |                                                                               | Industrial Temp. Range<br>$T_A = T_J = T_{\text{MIN}}$ to $T_{\text{MAX}}$                      |                        |                    |                    | 95                 |                            |
|                         |                                                                               | Extended Temp. Range<br>$T_A = T_J = T_{\text{MIN}}$ to $T_{\text{MAX}}$                        |                        |                    |                    | 100                |                            |
| $\Delta V_R/\Delta T$   | Average Reverse Breakdown Voltage Temperature Coefficient <sup>(5)</sup>      | $I_R = 10\text{mA}$                                                                             |                        |                    | $\pm 40$           |                    | ppm/ $^\circ\text{C}$      |
|                         |                                                                               | $I_R = 1\text{mA}$                                                                              |                        |                    | $\pm 20$           |                    |                            |
|                         |                                                                               | $I_R = 150\mu\text{A}, T_A = T_J = 25^\circ\text{C}$                                            |                        |                    | $\pm 20$           |                    |                            |
|                         |                                                                               | $I_R = 150\mu\text{A}$<br>$T_A = T_J = T_{\text{MIN}}$ to $T_{\text{MAX}}$                      |                        |                    |                    | $\pm 50$           |                            |
| $\Delta V_R/\Delta I_R$ | Reverse Breakdown Voltage Change with Operating Current Change <sup>(6)</sup> | $I_{\text{RMIN}} \leq I_R \leq 1\text{mA}, T_A = T_J = 25^\circ\text{C}$                        |                        |                    | 0.9                | 3.1                | mV                         |
|                         |                                                                               | $I_{\text{RMIN}} \leq I_R \leq 1\text{mA}$<br>$T_A = T_J = T_{\text{MIN}}$ to $T_{\text{MAX}}$  |                        |                    |                    | 4.6                |                            |
|                         |                                                                               | $1\text{mA} \leq I_R \leq 15\text{mA}, T_A = T_J = 25^\circ\text{C}$                            |                        |                    | 7                  | 10                 |                            |
|                         |                                                                               | $1\text{mA} \leq I_R \leq 15\text{mA}$<br>$T_A = T_J = T_{\text{MIN}}$ to $T_{\text{MAX}}$      |                        |                    |                    | 18                 |                            |
| $Z_R$                   | Reverse Dynamic Impedance                                                     | $I_R = 1\text{mA}, f = 120\text{Hz},$<br>$I_{\text{AC}} = 0.1 I_R$                              |                        |                    | 0.6                |                    | $\Omega$                   |
| $e_N$                   | Wideband Noise                                                                | $I_R = 150\mu\text{A}$<br>$10\text{Hz} \leq f \leq 10\text{kHz}$                                |                        |                    | 150                |                    | $\mu\text{V}_{\text{rms}}$ |
| $\Delta V_R$            | Reverse Breakdown Voltage Long Term Stability                                 | $t = 1000\text{ hrs}$<br>$T = 25^\circ\text{C} \pm 0.1^\circ\text{C}$<br>$I_R = 150\mu\text{A}$ |                        |                    | 120                |                    | ppm                        |
| $V_{\text{HYST}}$       | Thermal Hysteresis <sup>(7)</sup>                                             | $\Delta T = -40^\circ\text{C}$ to $125^\circ\text{C}$                                           |                        |                    | 2.3                |                    | mV                         |


## 5.10 Electrical Characteristics: 10V Option

All other limits  $T_A = T_J = 25^\circ\text{C}$ . The grades A, B and C designate initial Reverse Breakdown Voltage tolerances of  $\pm 0.1\%$  and  $\pm 0.2\%$  and  $0.5\%$  respectively.


| PARAMETER               |                                                                               | TEST CONDITIONS                                                                                 |                        | MIN <sup>(4)</sup> | TYP <sup>(3)</sup> | MAX <sup>(4)</sup> | UNIT                       |
|-------------------------|-------------------------------------------------------------------------------|-------------------------------------------------------------------------------------------------|------------------------|--------------------|--------------------|--------------------|----------------------------|
| $V_R$                   | Reverse Breakdown Voltage                                                     | $I_R = 150\mu\text{A}$                                                                          |                        | 10                 |                    |                    | V                          |
|                         | Reverse Breakdown Voltage Tolerance <sup>(5)</sup>                            | $I_R = 150\mu\text{A}$                                                                          | LM4050AIM3, LM4050AEM3 |                    |                    | $\pm 10$           | mV (max)                   |
|                         |                                                                               |                                                                                                 | LM4050BIM3, LM4050BEM3 |                    |                    | $\pm 20$           |                            |
|                         |                                                                               |                                                                                                 | LM4050CIM3, LM4050CEM3 |                    |                    | $\pm 50$           |                            |
|                         |                                                                               | Industrial Temp. Range<br>$T_A = T_J = T_{\text{MIN}}$ to $T_{\text{MAX}}$                      | LM4050AIM3             |                    |                    | $\pm 43$           |                            |
|                         |                                                                               |                                                                                                 | LM4050BIM3             |                    |                    | $\pm 53$           |                            |
|                         |                                                                               |                                                                                                 | LM4050CIM3             |                    |                    | $\pm 83$           |                            |
|                         |                                                                               | Extended Temp. Range<br>$T_A = T_J = T_{\text{MIN}}$ to $T_{\text{MAX}}$                        | LM4050AEM3             |                    |                    | $\pm 60$           |                            |
|                         |                                                                               |                                                                                                 | LM4050BEM3             |                    |                    | $\pm 70$           |                            |
|                         |                                                                               |                                                                                                 | LM4050CEM3             |                    |                    | $\pm 100$          |                            |
| $I_{\text{RMIN}}$       | Minimum Operating Current                                                     | $T_A = T_J = 25^\circ\text{C}$                                                                  |                        |                    | 80                 | 100                | $\mu\text{A}$              |
|                         |                                                                               | Industrial Temp. Range<br>$T_A = T_J = T_{\text{MIN}}$ to $T_{\text{MAX}}$                      |                        |                    |                    | 103                |                            |
|                         |                                                                               | Extended Temp. Range<br>$T_A = T_J = T_{\text{MIN}}$ to $T_{\text{MAX}}$                        |                        |                    |                    | 110                |                            |
| $\Delta V_R/\Delta T$   | Average Reverse Breakdown Voltage Temperature Coefficient <sup>(5)</sup>      | $I_R = 10\text{mA}$                                                                             |                        |                    | $\pm 40$           |                    | ppm/ $^\circ\text{C}$      |
|                         |                                                                               | $I_R = 1\text{mA}$                                                                              |                        |                    | $\pm 20$           |                    |                            |
|                         |                                                                               | $I_R = 150\mu\text{A}$ , $T_A = T_J = 25^\circ\text{C}$                                         |                        |                    | $\pm 20$           |                    |                            |
|                         |                                                                               | $I_R = 150\mu\text{A}$<br>$T_A = T_J = T_{\text{MIN}}$ to $T_{\text{MAX}}$                      |                        |                    |                    | $\pm 50$           |                            |
| $\Delta V_R/\Delta I_R$ | Reverse Breakdown Voltage Change with Operating Current Change <sup>(6)</sup> | $I_{\text{RMIN}} \leq I_R \leq 1\text{mA}$ , $T_A = T_J = 25^\circ\text{C}$                     |                        |                    | 2.5                | 3.8                | mV                         |
|                         |                                                                               | $I_{\text{RMIN}} \leq I_R \leq 1\text{mA}$<br>$T_A = T_J = T_{\text{MIN}}$ to $T_{\text{MAX}}$  |                        |                    |                    | 6                  |                            |
|                         |                                                                               | $1\text{mA} \leq I_R \leq 15\text{mA}$ , $T_A = T_J = 25^\circ\text{C}$                         |                        |                    | 8                  | 12                 |                            |
|                         |                                                                               | $1\text{mA} \leq I_R \leq 15\text{mA}$<br>$T_A = T_J = T_{\text{MIN}}$ to $T_{\text{MAX}}$      |                        |                    |                    | 23                 |                            |
| $Z_R$                   | Reverse Dynamic Impedance                                                     | $I_R = 1\text{mA}$ , $f = 120\text{Hz}$ ,<br>$I_{\text{AC}} = 0.1 I_R$                          |                        |                    | 0.7                |                    | $\Omega$                   |
| $e_N$                   | Wideband Noise                                                                | $I_R = 150\mu\text{A}$<br>$10\text{Hz} \leq f \leq 10\text{kHz}$                                |                        |                    | 150                |                    | $\mu\text{V}_{\text{rms}}$ |
| $\Delta V_R$            | Reverse Breakdown Voltage Long Term Stability                                 | $t = 1000\text{ hrs}$<br>$T = 25^\circ\text{C} \pm 0.1^\circ\text{C}$<br>$I_R = 150\mu\text{A}$ |                        |                    | 120                |                    | ppm                        |
| $V_{\text{HYST}}$       | Thermal Hysteresis <sup>(7)</sup>                                             | $\Delta T = -40^\circ\text{C}$ to $125^\circ\text{C}$                                           |                        |                    | 2.8                |                    | mV                         |

- The maximum power dissipation must be derated at elevated temperatures and is dictated by  $T_{\text{Jmax}}$  (maximum junction temperature),  $R_{\theta\text{JA}}$  (junction to ambient thermal resistance), and  $T_A$  (ambient temperature). The maximum allowable power dissipation at any temperature is  $\text{PD}_{\text{max}} = (T_{\text{Jmax}} - T_A)/R_{\theta\text{JA}}$  or the number given in the *Absolute Maximum Ratings*, whichever is lower. For the LM4050-N,  $T_{\text{Jmax}} = 150^\circ\text{C}$ , and the typical thermal resistance ( $R_{\theta\text{JA}}$ ), when board mounted, is  $326^\circ\text{C/W}$  for the SOT-23 package.
- High junction temperatures degrade operating lifetimes. Operating lifetime is de-rated for junction temperatures greater than  $125^\circ\text{C}$ .
- Typicals are at  $T_J = 25^\circ\text{C}$  and represent most likely parametric norm.
- Limits are 100% production tested at  $25^\circ\text{C}$ . Limits over temperature are verified through correlation using Statistical Quality Control (SQC) methods. The limits are used to calculate National's AOQL.
- The overtemperature limit for Reverse Breakdown Voltage Tolerance is defined as the room temperature Reverse Breakdown Voltage Tolerance  $\pm[(\Delta V_R/\Delta T)(\text{max}\Delta T)(V_R)]$ . Where,  $\Delta V_R/\Delta T$  is the  $V_R$  temperature coefficient,  $\text{max}\Delta T$  is the maximum difference in temperature from the reference point of  $25^\circ\text{C}$  to  $T_{\text{MIN}}$  or  $T_{\text{MAX}}$ , and  $V_R$  is the reverse breakdown voltage. The total overtemperature tolerance for the different grades in the industrial temperature range where  $\text{max}\Delta T = 65^\circ\text{C}$  is shown below: A-grade:  $\pm 0.425\% = \pm 0.1\% \pm 50\text{ppm}/^\circ\text{C} \times 65^\circ\text{C}$  B-grade:  $\pm 0.525\% = \pm 0.2\% \pm 50\text{ppm}/^\circ\text{C} \times 65^\circ\text{C}$  C-grade:  $\pm 0.825\% = \pm 0.5\% \pm 50\text{ppm}/^\circ\text{C} \times 65^\circ\text{C}$ . Therefore, as an example, the A-grade LM4050-N-2.5 has an overtemperature Reverse Breakdown Voltage tolerance of  $\pm 2.5\text{V} \times 0.425\% = \pm 11\text{mV}$ .
- Load regulation is measured on pulse basis from no load to the specified load current. Output changes due to die temperature change must be taken into account separately.
- Thermal hysteresis is defined as the difference in voltage measured at  $25^\circ\text{C}$  after cycling to temperature  $-40^\circ\text{C}$  and the  $25^\circ\text{C}$  measurement after cycling to temperature  $125^\circ\text{C}$ .


## 5.11 Typical Characteristics




**Figure 5-1. Output Impedance vs Frequency**




**Figure 5-2. Output Impedance vs Frequency**



**Figure 5-3. Reverse Characteristics and Minimum Operating Current**




**Figure 5-4. Noise Voltage vs Frequency**




**Figure 5-5. Thermal Hysteresis**


### 5.11.1 Start-Up Characteristics



**Figure 5-6. Input Voltage Step Response LM4050-N-2.5**




**Figure 5-7. Input Voltage Step Response LM4050-N-5**



**Figure 5-8. Input Voltage Step Response LM4050-N-10**

## 6 Parameter Measurement Information




**Figure 6-1. Test Circuit**

## 7 Detailed Description

### 7.1 Overview

The LM4050-N device is a precision micropower shunt voltage reference. The part comes in 6 different fixed-output voltage options for space-constrained applications, removing the need for feedback resistors. The voltage tolerance accuracies are  $\pm 0.1\%$ ,  $\pm 0.2\%$ , and  $\pm 0.5\%$  for Versions A, B, and C, respectively. The LM4050-N comes in two application versions, Industrial and Extended temperature range, which are operational from  $-40^{\circ}\text{C}$  to  $85^{\circ}\text{C}$  and  $-40^{\circ}\text{C}$  to  $125^{\circ}\text{C}$ , respectively.

### 7.2 Functional Block Diagram



### 7.3 Feature Description

The LM4050-N behaves as a high-precision Zener diode. The voltage is regulated between the cathode and anode which is dependent on the current being supplied to the cathode. This current is needed for the LM4050-N to regulate within the specified limits. Refer to the minimum and maximum operating requirements for the specific voltage option used. The LM4050-N is internally compensated to be stable without the use of an output capacitor. However, if desired, a bypass capacitor can be used.

### 7.4 Device Functional Modes

The LM4050-N can only operate in closed loop due to the fact that the feedback resistors are internal to the device. Additionally, the output voltage cannot be adjusted for the same reason. The output voltage is regulated in a closed loop, provided the  $R_s$  (see [Section 7.2](#)) resistor is sized to deliver the current to the cathode within the limits specified for the fixed-voltage version being used.

## 8 Application and Implementation

### Note

Information in the following applications sections is not part of the TI component specification, and TI does not warrant its accuracy or completeness. TI's customers are responsible for determining suitability of components for their purposes, as well as validating and testing their design implementation to confirm system functionality.

### 8.1 Application Information

The LM4050-N is a precision micropower curvature-corrected bandgap shunt voltage reference. For space critical applications, the LM4050-N is available in the sub-miniature SOT-23 surface-mount package. The LM4050-N has been designed for stable operation without the need of an external capacitor connected between the + pin and the – pin. If, however, a bypass capacitor is used, the LM4050-N remains stable. Reducing design effort is the availability of several fixed reverse breakdown voltages: 2.048V, 2.5V, 4.096V, 5V, 8.192V, and 10V. The minimum operating current increases from 60µA for the LM4050-N-2.0 to 100µA for the LM4050-N-10.0. All versions have a maximum operating current of 15mA.

LM4050-Ns in the SOT-23 packages have a parasitic Schottky diode between pin 2 (–) and pin 3 (Die attach interface contact). Therefore, pin 3 of the SOT-23 package must be left floating or connected to pin 2.

The 4.096V version allows single 5V 12-bit ADCs or DACs to operate with an LSB equal to 1mV. For 12-bit ADCs or DACs that operate on supplies of 10V or greater, the 8.192V version gives 2mV per LSB.

The typical thermal hysteresis specification is defined as the change in 25°C voltage measured after thermal cycling. The device is thermal cycled to temperature –40°C and then measured at 25°C. Next the device is thermal cycled to temperature 125°C and again measured at 25°C. The resulting  $V_{OUT}$  delta shift between the 25°C measurements is thermal hysteresis. Thermal hysteresis is common in precision references and is induced by thermal-mechanical package stress. Changes in environmental storage temperature, operating temperature and board mounting temperature are all factors that can contribute to thermal hysteresis.

In a conventional shunt regulator application ([Figure 8-1](#)), an external series resistor ( $R_S$ ) is connected between the supply voltage and the LM4050-N.  $R_S$  determines the current that flows through the load ( $I_L$ ) and the LM4050-N ( $I_Q$ ). Since load current and supply voltage can vary,  $R_S$  must be small enough to supply at least the maximum  $I_{RMIN}$  (spec. table) to the LM4050-N even when the supply voltage is at the minimum and the load current is at the maximum value. When the supply voltage is at the maximum and  $I_L$  is at the minimum,  $R_S$  must be large enough so that the current flowing through the LM4050-N is less than 15mA.

$R_S$  is determined by the supply voltage, ( $V_S$ ), the load and operating current, ( $I_L$  and  $I_Q$ ), and the LM4050-N's reverse breakdown voltage,  $V_R$ .

$$R_S = \frac{V_S - V_R}{I_L + I_Q} \quad (1)$$

## 8.2 Typical Applications

### 8.2.1 Shunt Regulator




Figure 8-1. Shunt Regulator Schematic

#### 8.2.1.1 Design Requirements

For this design example, use the parameters listed in [Table 8-1](#) as the input parameters.

Table 8-1. Design Parameters

| DESIGN PARAMETER        | VALUE                                                                    |
|-------------------------|--------------------------------------------------------------------------|
| Output Voltage          | 2V, 2.5V, 4.1V, 5V, 8.2V, 10V                                            |
| Minimum Cathode Current | 41μA, 41μA, 52μA, 56μA, 74μA, 80μA (typical) (Respective to Above field) |

#### 8.2.1.2 Detailed Design Procedure

$R_S$  sets the cathode current of the shunt reference. Make sure that this current is greater than the minimum cathode current to maintain regulation and less than the maximum reverse current to prevent overheating of the shunt reference. A suggested good starting value for most designs is from approximately 0.5mA to 1mA.

$$I_{RMIN} < \frac{V_s - V_{out}}{R_s} < 0.015A \quad (2)$$

#### 8.2.1.3 Application Curve





Figure 8-2. Reverse Characteristics and Minimum Operating Current



## 8.2.2 Precision Reference for an Analog-to-Digital Converter



**Figure 8-3. LM4050-N-4.1'S Nominal 4.096 Breakdown Voltage Gives ADC12451 1MV/LSB**

### 8.2.2.1 Design Requirements

For this design example, use the parameters listed in [Table 8-2](#) as the input parameters.

**Table 8-2. Design Parameters**

| DESIGN PARAMETER | VALUE |
|------------------|-------|
| Output Voltage   | 4.1V  |

### 8.2.2.2 Detailed Design Procedure


Set  $I_Q$  to approximately 1mA.

$$R_s = \frac{V_s - V_{out}}{I_Q} \quad (3)$$

where

- $R_s = 900\Omega$ , nearest preferred Value = 909 $\Omega$

### 8.2.3 $V_{OUT}$ Bounded Amplifier



Bounded amplifier reduces saturation-induced delays and can prevent succeeding stage damage. Nominal clamping voltage is  $\pm 11.5\text{V}$  (LM4050-N's reverse breakdown voltage  $+2$  diode  $V_F$ ).

**Figure 8-4. Bounded Amplifier**

#### 8.2.3.1 Design Requirements

The only design requirement is  $V_{OUT}$  bounded to  $\pm 11.5\text{V}$ .

#### 8.2.3.2 Detailed Design Procedure

$$V_{\text{bound}} = 2 \times V_{\text{wd}} + V_{\text{out}} \quad (4)$$

$$V_{\text{fwd}} = 0.7 \text{ V} \quad (5)$$

$$V_{\text{bound}} = (2 \times 0.7 \text{ V}) + 10 \text{ V} \quad (6)$$

Set  $I_Q$  to approximately  $0.6\text{mA}$ .


$$R_s = \frac{V_s + |-V_s| - V_{\text{out}}}{I_Q} \quad (7)$$

$$R_s = \frac{30 \text{ V} - 10 \text{ V}}{0.0006 \text{ A}} \quad (8)$$

where

- $R_s$  (total) =  $33\text{k}\Omega$  (select  $2 \times 15\text{k}\Omega$ )

## 8.2.4 $V_{IN}$ Bounded Amplifier



The bounding voltage is  $\pm 4V$  with the LM4050-N-2.5 (LM4050-N's reverse breakdown voltage + 3 diode  $V_F$ ).

**Figure 8-5. Protecting Op Amp Input**

### 8.2.4.1 Design Requirements

The only design requirement is  $V_{IN}$  bounded to  $\pm 4.6V$ .

### 8.2.4.2 Detailed Design Procedure

$$V_{\text{bound}} = 3 \times V_{\text{wd}} + V_{\text{out}} \quad (9)$$

$$V_{\text{fwd}} = 0.7 \text{ V} \quad (10)$$

$$V_{\text{bound}} = (3 \times 0.7 \text{ V}) + 2.5 \text{ V} \quad (11)$$

Set  $I_Q$  to approximately 0.6mA.


$$R_s = \frac{V_s + |-V_s| - V_{\text{out}}}{I_Q} \quad (12)$$

$$R_s = \frac{10 \text{ V} - 2.5 \text{ V}}{0.0006 \text{ A}} \quad (13)$$

where

- $R_s$  (total) = 12.5kΩ (select  $2 \times 5k\Omega$ )

## 8.2.5 $\pm 4.096$ Precision Reference



**Figure 8-6. Precision  $\pm 4.096$ v Reference**


### 8.2.5.1 Design Requirements

The only design requirement is a positive and negative reference generated from a positive reference,  $\pm 4.096$ V.

### 8.2.5.2 Detailed Design Procedure

Follow the design procedure set in [Section 8.2.2](#).

## 8.2.6 $\pm 1\text{mA}$ Precision Current Sources



$$I_{\text{out}} = \frac{V_{\text{out}}}{R_2}$$

**Figure 8-7. Precision 1 $\mu\text{A}$  to 1mA Current Source ( $\pm$ )**

### 8.2.6.1 Design Requirements

The only design requirement is a dual  $\pm 1\text{mA}$  current source.

### 8.2.6.2 Detailed Design Procedure

Set worse-case cathode current to 0.6mA.

$$V_{\text{out\_opampmax}} = 12 \text{ V} \quad (14)$$

$$R_1 = \frac{V_{\text{out\_opampmax}} - V_{\text{out}}}{I_Q} \quad (15)$$

$$R_1 = \frac{12 \text{ V} - 2.5 \text{ V}}{0.0006 \text{ A}} \quad (16)$$

$$R_1 = 1.583 \times 10^4 \Omega \quad (17)$$

$$I_{\text{out}} = \frac{V_{\text{out}}}{R_2} \quad (18)$$

### 8.3 Power Supply Recommendations


Noise on the power supply input to  $R_S$  can affect output noise performance. Noise performance can be reduced by using an optional bypass capacitor at the input side of  $R_S$  and Ground. TI recommends a 0.1 $\mu$ F ceramic capacitor or higher.

### 8.4 Layout

#### 8.4.1 Layout Guidelines

Place  $R_S$  as close to the cathode as possible. If an input and output capacitor is used, place this as close to the reference as possible.

#### 8.4.2 Layout Example



**Figure 8-8. Layout Recommendation**

## 9 Device and Documentation Support

### 9.1 Support Resources

[TI E2E™ support forums](#) are an engineer's go-to source for fast, verified answers and design help — straight from the experts. Search existing answers or ask your own question to get the quick design help you need.

Linked content is provided "AS IS" by the respective contributors. They do not constitute TI specifications and do not necessarily reflect TI's views; see TI's [Terms of Use](#).

### 9.2 Trademarks

TI E2E™ is a trademark of Texas Instruments.

All trademarks are the property of their respective owners.

### 9.3 Electrostatic Discharge Caution



This integrated circuit can be damaged by ESD. Texas Instruments recommends that all integrated circuits be handled with appropriate precautions. Failure to observe proper handling and installation procedures can cause damage.

ESD damage can range from subtle performance degradation to complete device failure. Precision integrated circuits may be more susceptible to damage because very small parametric changes could cause the device not to meet its published specifications.

### 9.4 Glossary

[TI Glossary](#) This glossary lists and explains terms, acronyms, and definitions.

## 10 Revision History

NOTE: Page numbers for previous revisions may differ from page numbers in the current version.

| <b>Changes from Revision G (September 2015) to Revision H (March 2025)</b>                                       | <b>Page</b>        |
|------------------------------------------------------------------------------------------------------------------|--------------------|
| • Updated the numbering format for tables, figures, and cross-references throughout the document.....            | <a href="#">1</a>  |
| • Updated <i>Applications</i> links.....                                                                         | <a href="#">1</a>  |
| • Added information about high EMI applications.....                                                             | <a href="#">3</a>  |
| • Removed machine model (MM) ESD specification and revised the CDM ESD specification.....                        | <a href="#">4</a>  |
| • Removed industrial temperature range part numbers from extended temperature range row and corrected typos..... | <a href="#">6</a>  |
| • Updated reverse breakdown voltage change with operating current change.....                                    | <a href="#">11</a> |
| • Clarified orderable part number information. ....                                                              | <a href="#">24</a> |

| <b>Changes from Revision F (June 2015) to Revision G (September 2015)</b>                                                                                                                                                                                                                                                                           | <b>Page</b>       |
|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-------------------|
| • Added <i>ESD Ratings</i> table, <i>Feature Description</i> section, <i>Device Functional Modes</i> , <i>Application and Implementation</i> section, <i>Power Supply Recommendations</i> section, <i>Layout</i> section, <i>Device and Documentation Support</i> section, and <i>Mechanical, Packaging, and Orderable Information</i> section..... | <a href="#">1</a> |
| • Removed Vapor Phase and Infrared Lead Temperatures from Abs Max Ratings table. ....                                                                                                                                                                                                                                                               | <a href="#">4</a> |

| <b>Changes from Revision E (April 2013) to Revision F (April 2015)</b>                                                   | <b>Page</b>       |
|--------------------------------------------------------------------------------------------------------------------------|-------------------|
| • Deleted "-25" from (LM4050-N) in Key Specifications title and "A/-Q1B/-Q1C" from Key Specification re: auto grade..... | <a href="#">1</a> |
| • Added Maximum Junction Temperature to Abs Max Ratings table .....                                                      | <a href="#">4</a> |
| • Added table notes to Operating Ratings table to clarify operating and high junction temperature ranges.....            | <a href="#">5</a> |
| • Deleted "-N" from part numbers in EC table "Limits" column headers .....                                               | <a href="#">6</a> |

**Changes from Revision D (April 2013) to Revision E (April 2013)****Page**

- Changed layout of National Data Sheet to TI format.....21

**11 Mechanical, Packaging, and Orderable Information**

The following pages include mechanical, packaging, and orderable information. This information is the most current data available for the designated devices. This data is subject to change without notice and revision of this document. For browser-based versions of this data sheet, refer to the left-hand navigation. Part numbers containing an "X" contain the same electrical properties as those which do not contain an "X".



## PACKAGING INFORMATION

| Orderable part number                | Status<br>(1) | Material type<br>(2) | Package   Pins   | Package qty   Carrier | RoHS<br>(3) | Lead finish/<br>Ball material<br>(4) | MSL rating/<br>Peak reflow<br>(5) | Op temp (°C) | Part marking<br>(6) |
|--------------------------------------|---------------|----------------------|------------------|-----------------------|-------------|--------------------------------------|-----------------------------------|--------------|---------------------|
| <a href="#">LM4050AEM3-10/NOPB</a>   | Active        | Production           | SOT-23 (DBZ)   3 | 3000   SMALL T&R      | Yes         | SN                                   | Level-1-260C-UNLIM                | -40 to 125   | RGA                 |
| LM4050AEM3-10/NOPB.A                 | Active        | Production           | SOT-23 (DBZ)   3 | 3000   SMALL T&R      | Yes         | SN                                   | Level-1-260C-UNLIM                | -40 to 125   | RGA                 |
| LM4050AEM3-10/NOPB.B                 | Active        | Production           | SOT-23 (DBZ)   3 | 3000   SMALL T&R      | Yes         | SN                                   | Level-1-260C-UNLIM                | -40 to 125   | RGA                 |
| LM4050AEM3-2.0/NO.A                  | Active        | Production           | SOT-23 (DBZ)   3 | 3000   LARGE T&R      | Yes         | SN                                   | Level-1-260C-UNLIM                | -40 to 125   | RNA                 |
| <a href="#">LM4050AEM3-2.0/NOPB</a>  | Active        | Production           | SOT-23 (DBZ)   3 | 3000   LARGE T&R      | Yes         | SN                                   | Level-1-260C-UNLIM                | -40 to 125   | RNA                 |
| LM4050AEM3-2.5/NO.A                  | Active        | Production           | SOT-23 (DBZ)   3 | 3000   SMALL T&R      | Yes         | SN                                   | Level-1-260C-UNLIM                | -40 to 125   | RCA                 |
| <a href="#">LM4050AEM3-2.5/NOPB</a>  | Active        | Production           | SOT-23 (DBZ)   3 | 3000   SMALL T&R      | Yes         | SN                                   | Level-1-260C-UNLIM                | -40 to 125   | RCA                 |
| LM4050AEM3-5.0/NO.A                  | Active        | Production           | SOT-23 (DBZ)   3 | 3000   SMALL T&R      | Yes         | SN                                   | Level-1-260C-UNLIM                | -40 to 125   | REA                 |
| <a href="#">LM4050AEM3-5.0/NOPB</a>  | Active        | Production           | SOT-23 (DBZ)   3 | 3000   SMALL T&R      | Yes         | SN                                   | Level-1-260C-UNLIM                | -40 to 125   | REA                 |
| LM4050AEM3-8.2/NO.A                  | Active        | Production           | SOT-23 (DBZ)   3 | 3000   LARGE T&R      | Yes         | SN                                   | Level-1-260C-UNLIM                | -40 to 125   | RFA                 |
| <a href="#">LM4050AEM3-8.2/NOPB</a>  | Active        | Production           | SOT-23 (DBZ)   3 | 3000   LARGE T&R      | Yes         | SN                                   | Level-1-260C-UNLIM                | -40 to 125   | RFA                 |
| LM4050AEM3X-10/NO.A                  | Active        | Production           | SOT-23 (DBZ)   3 | 3000   LARGE T&R      | Yes         | SN                                   | Level-1-260C-UNLIM                | -40 to 125   | RGA                 |
| LM4050AEM3X-10/NO.B                  | Active        | Production           | SOT-23 (DBZ)   3 | 3000   LARGE T&R      | Yes         | SN                                   | Level-1-260C-UNLIM                | -40 to 125   | RGA                 |
| <a href="#">LM4050AEM3X-10/NOPB</a>  | Active        | Production           | SOT-23 (DBZ)   3 | 3000   LARGE T&R      | Yes         | SN                                   | Level-1-260C-UNLIM                | -40 to 125   | RGA                 |
| LM4050AEM3X-2.5/NO.A                 | Active        | Production           | SOT-23 (DBZ)   3 | 3000   LARGE T&R      | Yes         | SN                                   | Level-1-260C-UNLIM                | -40 to 125   | RCA                 |
| <a href="#">LM4050AEM3X-2.5/NOPB</a> | Active        | Production           | SOT-23 (DBZ)   3 | 3000   LARGE T&R      | Yes         | SN                                   | Level-1-260C-UNLIM                | -40 to 125   | RCA                 |
| LM4050AEM3X-5.0/NO.A                 | Active        | Production           | SOT-23 (DBZ)   3 | 3000   LARGE T&R      | Yes         | SN                                   | Level-1-260C-UNLIM                | -40 to 125   | REA                 |
| <a href="#">LM4050AEM3X-5.0/NOPB</a> | Active        | Production           | SOT-23 (DBZ)   3 | 3000   LARGE T&R      | Yes         | SN                                   | Level-1-260C-UNLIM                | -40 to 125   | REA                 |
| <a href="#">LM4050AIM3-10/NOPB</a>   | Active        | Production           | SOT-23 (DBZ)   3 | 3000   LARGE T&R      | Yes         | SN                                   | Level-1-260C-UNLIM                | -40 to 85    | RGA                 |
| LM4050AIM3-10/NOPB.A                 | Active        | Production           | SOT-23 (DBZ)   3 | 3000   LARGE T&R      | Yes         | SN                                   | Level-1-260C-UNLIM                | -40 to 85    | RGA                 |
| LM4050AIM3-10/NOPB.B                 | Active        | Production           | SOT-23 (DBZ)   3 | 3000   LARGE T&R      | Yes         | SN                                   | Level-1-260C-UNLIM                | -40 to 85    | RGA                 |
| LM4050AIM3-2.5/NO.A                  | Active        | Production           | SOT-23 (DBZ)   3 | 3000   SMALL T&R      | Yes         | SN                                   | Level-1-260C-UNLIM                | -40 to 125   | RCA                 |
| <a href="#">LM4050AIM3-2.5/NOPB</a>  | Active        | Production           | SOT-23 (DBZ)   3 | 3000   SMALL T&R      | Yes         | SN                                   | Level-1-260C-UNLIM                | -40 to 85    | RCA                 |
| LM4050AIM3-4.1/NO.A                  | Active        | Production           | SOT-23 (DBZ)   3 | 3000   SMALL T&R      | Yes         | SN                                   | Level-1-260C-UNLIM                | -40 to 125   | RDA                 |
| <a href="#">LM4050AIM3-4.1/NOPB</a>  | Active        | Production           | SOT-23 (DBZ)   3 | 3000   SMALL T&R      | Yes         | SN                                   | Level-1-260C-UNLIM                | -40 to 85    | RDA                 |
| LM4050AIM3-5.0/NO.A                  | Active        | Production           | SOT-23 (DBZ)   3 | 3000   SMALL T&R      | Yes         | SN                                   | Level-1-260C-UNLIM                | -40 to 125   | REA                 |
| <a href="#">LM4050AIM3-5.0/NOPB</a>  | Active        | Production           | SOT-23 (DBZ)   3 | 3000   SMALL T&R      | Yes         | SN                                   | Level-1-260C-UNLIM                | -40 to 85    | REA                 |
| LM4050AIM3X-2.5/NO.A                 | Active        | Production           | SOT-23 (DBZ)   3 | 3000   LARGE T&R      | Yes         | SN                                   | Level-1-260C-UNLIM                | -40 to 125   | RCA                 |
| <a href="#">LM4050AIM3X-2.5/NOPB</a> | Active        | Production           | SOT-23 (DBZ)   3 | 3000   LARGE T&R      | Yes         | SN                                   | Level-1-260C-UNLIM                | -40 to 85    | RCA                 |

| Orderable part number                | Status<br>(1) | Material type<br>(2) | Package   Pins   | Package qty   Carrier | RoHS<br>(3) | Lead finish/<br>Ball material<br>(4) | MSL rating/<br>Peak reflow<br>(5) | Op temp (°C) | Part marking<br>(6) |
|--------------------------------------|---------------|----------------------|------------------|-----------------------|-------------|--------------------------------------|-----------------------------------|--------------|---------------------|
| LM4050AIM3X-4.1/NO.A                 | Active        | Production           | SOT-23 (DBZ)   3 | 3000   LARGE T&R      | Yes         | SN                                   | Level-1-260C-UNLIM                | -40 to 125   | RDA                 |
| <a href="#">LM4050AIM3X-4.1/NOPB</a> | Active        | Production           | SOT-23 (DBZ)   3 | 3000   LARGE T&R      | Yes         | SN                                   | Level-1-260C-UNLIM                | -40 to 85    | RDA                 |
| LM4050AIM3X-5.0/NO.A                 | Active        | Production           | SOT-23 (DBZ)   3 | 3000   LARGE T&R      | Yes         | SN                                   | Level-1-260C-UNLIM                | -40 to 125   | REA                 |
| <a href="#">LM4050AIM3X-5.0/NOPB</a> | Active        | Production           | SOT-23 (DBZ)   3 | 3000   LARGE T&R      | Yes         | SN                                   | Level-1-260C-UNLIM                | -40 to 85    | REA                 |
| <a href="#">LM4050BEM3-10/NOPB</a>   | Active        | Production           | SOT-23 (DBZ)   3 | 3000   SMALL T&R      | Yes         | SN                                   | Level-1-260C-UNLIM                | -40 to 125   | RGB                 |
| LM4050BEM3-10/NOPB.A                 | Active        | Production           | SOT-23 (DBZ)   3 | 3000   SMALL T&R      | Yes         | SN                                   | Level-1-260C-UNLIM                | -40 to 125   | RGB                 |
| LM4050BEM3-10/NOPB.B                 | Active        | Production           | SOT-23 (DBZ)   3 | 3000   SMALL T&R      | Yes         | SN                                   | Level-1-260C-UNLIM                | -40 to 125   | RGB                 |
| LM4050BEM3-2.5/NO.A                  | Active        | Production           | SOT-23 (DBZ)   3 | 3000   SMALL T&R      | Yes         | SN                                   | Level-1-260C-UNLIM                | -40 to 125   | RCB                 |
| <a href="#">LM4050BEM3-2.5/NOPB</a>  | Active        | Production           | SOT-23 (DBZ)   3 | 3000   SMALL T&R      | Yes         | SN                                   | Level-1-260C-UNLIM                | -40 to 125   | RCB                 |
| LM4050BEM3-4.1/NO.A                  | Active        | Production           | SOT-23 (DBZ)   3 | 3000   LARGE T&R      | Yes         | SN                                   | Level-1-260C-UNLIM                | -40 to 125   | RDB                 |
| <a href="#">LM4050BEM3-4.1/NOPB</a>  | Active        | Production           | SOT-23 (DBZ)   3 | 3000   LARGE T&R      | Yes         | SN                                   | Level-1-260C-UNLIM                | -40 to 125   | RDB                 |
| LM4050BEM3-5.0/NO.A                  | Active        | Production           | SOT-23 (DBZ)   3 | 3000   SMALL T&R      | Yes         | SN                                   | Level-1-260C-UNLIM                | -40 to 125   | REB                 |
| <a href="#">LM4050BEM3-5.0/NOPB</a>  | Active        | Production           | SOT-23 (DBZ)   3 | 3000   SMALL T&R      | Yes         | SN                                   | Level-1-260C-UNLIM                | -40 to 125   | REB                 |
| <a href="#">LM4050BEM3-8.2/NOPB</a>  | Active        | Production           | SOT-23 (DBZ)   3 | 3000   LARGE T&R      | Yes         | SN                                   | Level-1-260C-UNLIM                | -40 to 125   | RFB                 |
| LM4050BEM3X-10/NO.A                  | Active        | Production           | SOT-23 (DBZ)   3 | 3000   LARGE T&R      | Yes         | SN                                   | Level-1-260C-UNLIM                | -40 to 125   | RGB                 |
| <a href="#">LM4050BEM3X-10/NOPB</a>  | Active        | Production           | SOT-23 (DBZ)   3 | 3000   LARGE T&R      | Yes         | SN                                   | Level-1-260C-UNLIM                | -40 to 125   | RGB                 |
| LM4050BEM3X-2.5/NO.A                 | Active        | Production           | SOT-23 (DBZ)   3 | 3000   LARGE T&R      | Yes         | SN                                   | Level-1-260C-UNLIM                | -40 to 125   | RCB                 |
| <a href="#">LM4050BEM3X-2.5/NOPB</a> | Active        | Production           | SOT-23 (DBZ)   3 | 3000   LARGE T&R      | Yes         | SN                                   | Level-1-260C-UNLIM                | -40 to 125   | RCB                 |
| LM4050BEM3X-5.0/NO.A                 | Active        | Production           | SOT-23 (DBZ)   3 | 3000   LARGE T&R      | Yes         | SN                                   | Level-1-260C-UNLIM                | -40 to 125   | REB                 |
| <a href="#">LM4050BEM3X-5.0/NOPB</a> | Active        | Production           | SOT-23 (DBZ)   3 | 3000   LARGE T&R      | Yes         | SN                                   | Level-1-260C-UNLIM                | -40 to 125   | REB                 |
| <a href="#">LM4050BIM3-10/NOPB</a>   | Active        | Production           | SOT-23 (DBZ)   3 | 1000   LARGE T&R      | Yes         | SN                                   | Level-1-260C-UNLIM                | -40 to 85    | RGB                 |
| LM4050BIM3-10/NOPB.B                 | Active        | Production           | SOT-23 (DBZ)   3 | 1000   LARGE T&R      | Yes         | SN                                   | Level-1-260C-UNLIM                | -40 to 85    | RGB                 |
| LM4050BIM3-2.5/NO.A                  | Active        | Production           | SOT-23 (DBZ)   3 | 3000   SMALL T&R      | Yes         | SN                                   | Level-1-260C-UNLIM                | -40 to 125   | RCB                 |
| <a href="#">LM4050BIM3-2.5/NOPB</a>  | Active        | Production           | SOT-23 (DBZ)   3 | 3000   SMALL T&R      | Yes         | SN                                   | Level-1-260C-UNLIM                | -40 to 85    | RCB                 |
| LM4050BIM3-4.1/NO.A                  | Active        | Production           | SOT-23 (DBZ)   3 | 3000   SMALL T&R      | Yes         | SN                                   | Level-1-260C-UNLIM                | -40 to 125   | RDB                 |
| <a href="#">LM4050BIM3-4.1/NOPB</a>  | Active        | Production           | SOT-23 (DBZ)   3 | 3000   SMALL T&R      | Yes         | SN                                   | Level-1-260C-UNLIM                | -40 to 85    | RDB                 |
| LM4050BIM3-5.0/NO.A                  | Active        | Production           | SOT-23 (DBZ)   3 | 3000   SMALL T&R      | Yes         | SN                                   | Level-1-260C-UNLIM                | -40 to 125   | REB                 |
| <a href="#">LM4050BIM3-5.0/NOPB</a>  | Active        | Production           | SOT-23 (DBZ)   3 | 3000   SMALL T&R      | Yes         | SN                                   | Level-1-260C-UNLIM                | -40 to 85    | REB                 |
| LM4050BIM3X-2.0/NO.A                 | Active        | Production           | SOT-23 (DBZ)   3 | 3000   LARGE T&R      | Yes         | SN                                   | Level-1-260C-UNLIM                | -40 to 125   | RNB                 |
| <a href="#">LM4050BIM3X-2.0/NOPB</a> | Active        | Production           | SOT-23 (DBZ)   3 | 3000   LARGE T&R      | Yes         | SN                                   | Level-1-260C-UNLIM                | -40 to 85    | RNB                 |
| LM4050BIM3X-2.5/NO.A                 | Active        | Production           | SOT-23 (DBZ)   3 | 3000   LARGE T&R      | Yes         | SN                                   | Level-1-260C-UNLIM                | -40 to 125   | RCB                 |

| Orderable part number                | Status<br>(1) | Material type<br>(2) | Package   Pins   | Package qty   Carrier | RoHS<br>(3) | Lead finish/<br>Ball material<br>(4) | MSL rating/<br>Peak reflow<br>(5) | Op temp (°C) | Part marking<br>(6) |
|--------------------------------------|---------------|----------------------|------------------|-----------------------|-------------|--------------------------------------|-----------------------------------|--------------|---------------------|
| <a href="#">LM4050BIM3X-2.5/NOPB</a> | Active        | Production           | SOT-23 (DBZ)   3 | 3000   LARGE T&R      | Yes         | SN                                   | Level-1-260C-UNLIM                | -40 to 85    | RCB                 |
| <a href="#">LM4050BIM3X-4.1/NO.A</a> | Active        | Production           | SOT-23 (DBZ)   3 | 3000   LARGE T&R      | Yes         | SN                                   | Level-1-260C-UNLIM                | -40 to 125   | RDB                 |
| <a href="#">LM4050BIM3X-4.1/NOPB</a> | Active        | Production           | SOT-23 (DBZ)   3 | 3000   LARGE T&R      | Yes         | SN                                   | Level-1-260C-UNLIM                | -40 to 85    | RDB                 |
| <a href="#">LM4050BIM3X-5.0/NO.A</a> | Active        | Production           | SOT-23 (DBZ)   3 | 3000   LARGE T&R      | Yes         | SN                                   | Level-1-260C-UNLIM                | -40 to 125   | REB                 |
| <a href="#">LM4050BIM3X-5.0/NOPB</a> | Active        | Production           | SOT-23 (DBZ)   3 | 3000   LARGE T&R      | Yes         | SN                                   | Level-1-260C-UNLIM                | -40 to 85    | REB                 |
| <a href="#">LM4050CEM3-10/NOPB</a>   | Active        | Production           | SOT-23 (DBZ)   3 | 1000   LARGE T&R      | Yes         | SN                                   | Level-1-260C-UNLIM                | -            | RGC                 |
| <a href="#">LM4050CEM3-10/NOPB.B</a> | Active        | Production           | SOT-23 (DBZ)   3 | 1000   LARGE T&R      | Yes         | SN                                   | Level-1-260C-UNLIM                | -40 to 125   | RGC                 |
| <a href="#">LM4050CEM3-2.5/NO.A</a>  | Active        | Production           | SOT-23 (DBZ)   3 | 3000   SMALL T&R      | Yes         | SN                                   | Level-1-260C-UNLIM                | -40 to 125   | RCC                 |
| <a href="#">LM4050CEM3-2.5/NOPB</a>  | Active        | Production           | SOT-23 (DBZ)   3 | 3000   SMALL T&R      | Yes         | SN                                   | Level-1-260C-UNLIM                | -40 to 125   | RCC                 |
| <a href="#">LM4050CEM3-5.0/NO.A</a>  | Active        | Production           | SOT-23 (DBZ)   3 | 3000   SMALL T&R      | Yes         | SN                                   | Level-1-260C-UNLIM                | -40 to 125   | REC                 |
| <a href="#">LM4050CEM3-5.0/NOPB</a>  | Active        | Production           | SOT-23 (DBZ)   3 | 3000   SMALL T&R      | Yes         | SN                                   | Level-1-260C-UNLIM                | -            | REC                 |
| <a href="#">LM4050CEM3X-2.5/NO.A</a> | Active        | Production           | SOT-23 (DBZ)   3 | 3000   LARGE T&R      | Yes         | SN                                   | Level-1-260C-UNLIM                | -40 to 125   | RCC                 |
| <a href="#">LM4050CEM3X-2.5/NOPB</a> | Active        | Production           | SOT-23 (DBZ)   3 | 3000   LARGE T&R      | Yes         | SN                                   | Level-1-260C-UNLIM                | -40 to 125   | RCC                 |
| <a href="#">LM4050CEM3X-5.0/NO.A</a> | Active        | Production           | SOT-23 (DBZ)   3 | 3000   LARGE T&R      | Yes         | SN                                   | Level-1-260C-UNLIM                | -40 to 125   | REC                 |
| <a href="#">LM4050CEM3X-5.0/NOPB</a> | Active        | Production           | SOT-23 (DBZ)   3 | 3000   LARGE T&R      | Yes         | SN                                   | Level-1-260C-UNLIM                | -            | REC                 |
| <a href="#">LM4050CIM3-10/NOPB</a>   | Active        | Production           | SOT-23 (DBZ)   3 | 3000   LARGE T&R      | Yes         | SN                                   | Level-1-260C-UNLIM                | -40 to 85    | RGC                 |
| <a href="#">LM4050CIM3-10/NOPB.A</a> | Active        | Production           | SOT-23 (DBZ)   3 | 3000   LARGE T&R      | Yes         | SN                                   | Level-1-260C-UNLIM                | -40 to 85    | RGC                 |
| <a href="#">LM4050CIM3-10/NOPB.B</a> | Active        | Production           | SOT-23 (DBZ)   3 | 3000   LARGE T&R      | Yes         | SN                                   | Level-1-260C-UNLIM                | -40 to 85    | RGC                 |
| <a href="#">LM4050CIM3-2.5/NO.A</a>  | Active        | Production           | SOT-23 (DBZ)   3 | 3000   SMALL T&R      | Yes         | SN                                   | Level-1-260C-UNLIM                | -40 to 125   | RCC                 |
| <a href="#">LM4050CIM3-2.5/NOPB</a>  | Active        | Production           | SOT-23 (DBZ)   3 | 3000   SMALL T&R      | Yes         | SN                                   | Level-1-260C-UNLIM                | -40 to 85    | RCC                 |
| <a href="#">LM4050CIM3-4.1/NO.A</a>  | Active        | Production           | SOT-23 (DBZ)   3 | 3000   SMALL T&R      | Yes         | SN                                   | Level-1-260C-UNLIM                | -40 to 125   | RDC                 |
| <a href="#">LM4050CIM3-4.1/NOPB</a>  | Active        | Production           | SOT-23 (DBZ)   3 | 3000   SMALL T&R      | Yes         | SN                                   | Level-1-260C-UNLIM                | -40 to 85    | RDC                 |
| <a href="#">LM4050CIM3-5.0/NO.A</a>  | Active        | Production           | SOT-23 (DBZ)   3 | 3000   SMALL T&R      | Yes         | SN                                   | Level-1-260C-UNLIM                | -40 to 125   | REC                 |
| <a href="#">LM4050CIM3-5.0/NOPB</a>  | Active        | Production           | SOT-23 (DBZ)   3 | 3000   SMALL T&R      | Yes         | SN                                   | Level-1-260C-UNLIM                | -40 to 85    | REC                 |
| <a href="#">LM4050CIM3X-2.0/NO.A</a> | Active        | Production           | SOT-23 (DBZ)   3 | 3000   LARGE T&R      | Yes         | SN                                   | Level-1-260C-UNLIM                | -40 to 125   | RNC                 |
| <a href="#">LM4050CIM3X-2.0/NOPB</a> | Active        | Production           | SOT-23 (DBZ)   3 | 3000   LARGE T&R      | Yes         | SN                                   | Level-1-260C-UNLIM                | -40 to 85    | RNC                 |
| <a href="#">LM4050CIM3X-2.5/NO.A</a> | Active        | Production           | SOT-23 (DBZ)   3 | 3000   LARGE T&R      | Yes         | SN                                   | Level-1-260C-UNLIM                | -40 to 125   | RCC                 |
| <a href="#">LM4050CIM3X-2.5/NOPB</a> | Active        | Production           | SOT-23 (DBZ)   3 | 3000   LARGE T&R      | Yes         | SN                                   | Level-1-260C-UNLIM                | -40 to 85    | RCC                 |
| <a href="#">LM4050CIM3X-4.1/NO.A</a> | Active        | Production           | SOT-23 (DBZ)   3 | 3000   LARGE T&R      | Yes         | SN                                   | Level-1-260C-UNLIM                | -40 to 125   | RDC                 |
| <a href="#">LM4050CIM3X-4.1/NOPB</a> | Active        | Production           | SOT-23 (DBZ)   3 | 3000   LARGE T&R      | Yes         | SN                                   | Level-1-260C-UNLIM                | -40 to 85    | RDC                 |
| <a href="#">LM4050CIM3X-5.0/NO.A</a> | Active        | Production           | SOT-23 (DBZ)   3 | 3000   LARGE T&R      | Yes         | SN                                   | Level-1-260C-UNLIM                | -40 to 125   | REC                 |

| Orderable part number                | Status<br>(1) | Material type<br>(2) | Package   Pins   | Package qty   Carrier | RoHS<br>(3) | Lead finish/<br>Ball material<br>(4) | MSL rating/<br>Peak reflow<br>(5) | Op temp (°C) | Part marking<br>(6) |
|--------------------------------------|---------------|----------------------|------------------|-----------------------|-------------|--------------------------------------|-----------------------------------|--------------|---------------------|
| <a href="#">LM4050CIM3X-5.0/NOPB</a> | Active        | Production           | SOT-23 (DBZ)   3 | 3000   LARGE T&R      | Yes         | SN                                   | Level-1-260C-UNLIM                | -40 to 85    | REC                 |
| <a href="#">LM4050QAEM3-10/NOPB</a>  | Obsolete      | Production           | SOT-23 (DBZ)   3 | -                     | -           | Call TI                              | Call TI                           | -40 to 125   | RYA                 |
| <a href="#">LM4050QAEM3-2.0/NO.A</a> | Active        | Production           | SOT-23 (DBZ)   3 | 3000   LARGE T&R      | Yes         | SN                                   | Level-1-260C-UNLIM                | -40 to 125   | RSA                 |
| <a href="#">LM4050QAEM3-2.0/NOPB</a> | Active        | Production           | SOT-23 (DBZ)   3 | 3000   LARGE T&R      | Yes         | SN                                   | Level-1-260C-UNLIM                | -40 to 125   | RSA                 |
| <a href="#">LM4050QAEM3-2.5/NO.A</a> | Active        | Production           | SOT-23 (DBZ)   3 | 3000   LARGE T&R      | Yes         | SN                                   | Level-1-260C-UNLIM                | -40 to 125   | RTA                 |
| <a href="#">LM4050QAEM3-2.5/NOPB</a> | Active        | Production           | SOT-23 (DBZ)   3 | 3000   LARGE T&R      | Yes         | SN                                   | Level-1-260C-UNLIM                | -40 to 125   | RTA                 |
| <a href="#">LM4050QAEM3-4.1/NO.A</a> | Active        | Production           | SOT-23 (DBZ)   3 | 3000   LARGE T&R      | Yes         | SN                                   | Level-1-260C-UNLIM                | -40 to 125   | RUA                 |
| <a href="#">LM4050QAEM3-4.1/NOPB</a> | Active        | Production           | SOT-23 (DBZ)   3 | 3000   LARGE T&R      | Yes         | SN                                   | Level-1-260C-UNLIM                | -40 to 125   | RUA                 |
| <a href="#">LM4050QAEM3-5.0/NO.A</a> | Active        | Production           | SOT-23 (DBZ)   3 | 3000   LARGE T&R      | Yes         | SN                                   | Level-1-260C-UNLIM                | -40 to 125   | RVA                 |
| <a href="#">LM4050QAEM3-5.0/NOPB</a> | Active        | Production           | SOT-23 (DBZ)   3 | 3000   LARGE T&R      | Yes         | SN                                   | Level-1-260C-UNLIM                | -40 to 125   | RVA                 |
| <a href="#">LM4050QAEM3X10/NOPB</a>  | Active        | Production           | SOT-23 (DBZ)   3 | 3000   LARGE T&R      | Yes         | SN                                   | Level-1-260C-UNLIM                | -40 to 125   | RYA                 |
| <a href="#">LM4050QAEM3X2.0/NO.A</a> | Active        | Production           | SOT-23 (DBZ)   3 | 3000   LARGE T&R      | Yes         | SN                                   | Level-1-260C-UNLIM                | -40 to 125   | RSA                 |
| <a href="#">LM4050QAEM3X2.0/NOPB</a> | Active        | Production           | SOT-23 (DBZ)   3 | 3000   LARGE T&R      | Yes         | SN                                   | Level-1-260C-UNLIM                | -40 to 125   | RSA                 |
| <a href="#">LM4050QAEM3X2.5/NO.A</a> | Active        | Production           | SOT-23 (DBZ)   3 | 3000   LARGE T&R      | Yes         | SN                                   | Level-1-260C-UNLIM                | -40 to 125   | RTA                 |
| <a href="#">LM4050QAEM3X2.5/NOPB</a> | Active        | Production           | SOT-23 (DBZ)   3 | 3000   LARGE T&R      | Yes         | SN                                   | Level-1-260C-UNLIM                | -40 to 125   | RTA                 |
| <a href="#">LM4050QAEM3X4.1/NO.A</a> | Active        | Production           | SOT-23 (DBZ)   3 | 3000   LARGE T&R      | Yes         | SN                                   | Level-1-260C-UNLIM                | -40 to 125   | RUA                 |
| <a href="#">LM4050QAEM3X4.1/NOPB</a> | Active        | Production           | SOT-23 (DBZ)   3 | 3000   LARGE T&R      | Yes         | SN                                   | Level-1-260C-UNLIM                | -40 to 125   | RUA                 |
| <a href="#">LM4050QAEM3X5.0/NO.A</a> | Active        | Production           | SOT-23 (DBZ)   3 | 3000   LARGE T&R      | Yes         | SN                                   | Level-1-260C-UNLIM                | -40 to 125   | RVA                 |
| <a href="#">LM4050QAEM3X5.0/NOPB</a> | Active        | Production           | SOT-23 (DBZ)   3 | 3000   LARGE T&R      | Yes         | SN                                   | Level-1-260C-UNLIM                | -40 to 125   | RVA                 |
| <a href="#">LM4050QAEM3X8.2/NOPB</a> | Active        | Production           | SOT-23 (DBZ)   3 | 3000   LARGE T&R      | Yes         | SN                                   | Level-1-260C-UNLIM                | -40 to 125   | RXA                 |
| <a href="#">LM4050QAIM3-10/NOPB</a>  | Active        | Production           | SOT-23 (DBZ)   3 | 3000   LARGE T&R      | Yes         | SN                                   | Level-1-260C-UNLIM                | -40 to 85    | RYA                 |
| <a href="#">LM4050QAIM3-2.0/NO.A</a> | Active        | Production           | SOT-23 (DBZ)   3 | 3000   LARGE T&R      | Yes         | SN                                   | Level-1-260C-UNLIM                | -40 to 125   | RSA                 |
| <a href="#">LM4050QAIM3-2.0/NOPB</a> | Active        | Production           | SOT-23 (DBZ)   3 | 3000   LARGE T&R      | Yes         | SN                                   | Level-1-260C-UNLIM                | -40 to 85    | RSA                 |
| <a href="#">LM4050QAIM3-2.5/NO.A</a> | Active        | Production           | SOT-23 (DBZ)   3 | 3000   LARGE T&R      | Yes         | SN                                   | Level-1-260C-UNLIM                | -40 to 125   | RTA                 |
| <a href="#">LM4050QAIM3-2.5/NOPB</a> | Active        | Production           | SOT-23 (DBZ)   3 | 3000   LARGE T&R      | Yes         | SN                                   | Level-1-260C-UNLIM                | -40 to 85    | RTA                 |
| <a href="#">LM4050QAIM3-4.1/NO.A</a> | Active        | Production           | SOT-23 (DBZ)   3 | 3000   LARGE T&R      | Yes         | SN                                   | Level-1-260C-UNLIM                | -40 to 125   | RUA                 |
| <a href="#">LM4050QAIM3-4.1/NOPB</a> | Active        | Production           | SOT-23 (DBZ)   3 | 3000   LARGE T&R      | Yes         | SN                                   | Level-1-260C-UNLIM                | -40 to 85    | RUA                 |
| <a href="#">LM4050QAIM3-8.2/NOPB</a> | Active        | Production           | SOT-23 (DBZ)   3 | 3000   LARGE T&R      | Yes         | SN                                   | Level-1-260C-UNLIM                | -40 to 85    | RXA                 |
| <a href="#">LM4050QAIM3X4.1/NO.A</a> | Active        | Production           | SOT-23 (DBZ)   3 | 3000   LARGE T&R      | Yes         | SN                                   | Level-1-260C-UNLIM                | -40 to 125   | RUA                 |
| <a href="#">LM4050QAIM3X4.1/NOPB</a> | Active        | Production           | SOT-23 (DBZ)   3 | 3000   LARGE T&R      | Yes         | SN                                   | Level-1-260C-UNLIM                | -40 to 85    | RUA                 |
| <a href="#">LM4050QBEM3-10/NOPB</a>  | Obsolete      | Production           | SOT-23 (DBZ)   3 | -                     | -           | Call TI                              | Call TI                           | -40 to 125   | RYB                 |

| Orderable part number                | Status<br>(1) | Material type<br>(2) | Package   Pins   | Package qty   Carrier | RoHS<br>(3) | Lead finish/<br>Ball material<br>(4) | MSL rating/<br>Peak reflow<br>(5) | Op temp (°C) | Part marking<br>(6) |
|--------------------------------------|---------------|----------------------|------------------|-----------------------|-------------|--------------------------------------|-----------------------------------|--------------|---------------------|
| LM4050QBEM3-2.0/NO.A                 | Active        | Production           | SOT-23 (DBZ)   3 | 3000   LARGE T&R      | Yes         | SN                                   | Level-1-260C-UNLIM                | -40 to 125   | RSB                 |
| <a href="#">LM4050QBEM3-2.0/NOPB</a> | Active        | Production           | SOT-23 (DBZ)   3 | 3000   LARGE T&R      | Yes         | SN                                   | Level-1-260C-UNLIM                | -40 to 125   | RSB                 |
| LM4050QBEM3-2.5/NO.A                 | Active        | Production           | SOT-23 (DBZ)   3 | 3000   LARGE T&R      | Yes         | SN                                   | Level-1-260C-UNLIM                | -40 to 125   | RTB                 |
| <a href="#">LM4050QBEM3-2.5/NOPB</a> | Active        | Production           | SOT-23 (DBZ)   3 | 3000   LARGE T&R      | Yes         | SN                                   | Level-1-260C-UNLIM                | -40 to 125   | RTB                 |
| LM4050QBEM3-4.1/NO.A                 | Active        | Production           | SOT-23 (DBZ)   3 | 3000   LARGE T&R      | Yes         | SN                                   | Level-1-260C-UNLIM                | -40 to 125   | RUB                 |
| <a href="#">LM4050QBEM3-4.1/NOPB</a> | Active        | Production           | SOT-23 (DBZ)   3 | 3000   LARGE T&R      | Yes         | SN                                   | Level-1-260C-UNLIM                | -40 to 125   | RUB                 |
| LM4050QBEM3-5.0/NO.A                 | Active        | Production           | SOT-23 (DBZ)   3 | 3000   LARGE T&R      | Yes         | SN                                   | Level-1-260C-UNLIM                | -40 to 125   | RVB                 |
| <a href="#">LM4050QBEM3-5.0/NOPB</a> | Active        | Production           | SOT-23 (DBZ)   3 | 3000   LARGE T&R      | Yes         | SN                                   | Level-1-260C-UNLIM                | -40 to 125   | RVB                 |
| <a href="#">LM4050QBEM3-8.2/NOPB</a> | Obsolete      | Production           | SOT-23 (DBZ)   3 | -                     | -           | Call TI                              | Call TI                           | -40 to 125   | RXB                 |
| <a href="#">LM4050QBEM3X10/NOPB</a>  | Active        | Production           | SOT-23 (DBZ)   3 | 3000   LARGE T&R      | Yes         | SN                                   | Level-1-260C-UNLIM                | -40 to 125   | RYB                 |
| LM4050QBEM3X2.0/NO.A                 | Active        | Production           | SOT-23 (DBZ)   3 | 3000   LARGE T&R      | Yes         | SN                                   | Level-1-260C-UNLIM                | -40 to 125   | RSB                 |
| <a href="#">LM4050QBEM3X2.0/NOPB</a> | Active        | Production           | SOT-23 (DBZ)   3 | 3000   LARGE T&R      | Yes         | SN                                   | Level-1-260C-UNLIM                | -40 to 125   | RSB                 |
| LM4050QBEM3X2.5/NO.A                 | Active        | Production           | SOT-23 (DBZ)   3 | 3000   LARGE T&R      | Yes         | SN                                   | Level-1-260C-UNLIM                | -40 to 125   | RTB                 |
| <a href="#">LM4050QBEM3X2.5/NOPB</a> | Active        | Production           | SOT-23 (DBZ)   3 | 3000   LARGE T&R      | Yes         | SN                                   | Level-1-260C-UNLIM                | -40 to 125   | RTB                 |
| LM4050QBEM3X4.1/NO.A                 | Active        | Production           | SOT-23 (DBZ)   3 | 3000   LARGE T&R      | Yes         | SN                                   | Level-1-260C-UNLIM                | -40 to 125   | RUB                 |
| <a href="#">LM4050QBEM3X4.1/NOPB</a> | Active        | Production           | SOT-23 (DBZ)   3 | 3000   LARGE T&R      | Yes         | SN                                   | Level-1-260C-UNLIM                | -40 to 125   | RUB                 |
| LM4050QBEM3X5.0/NO.A                 | Active        | Production           | SOT-23 (DBZ)   3 | 3000   LARGE T&R      | Yes         | SN                                   | Level-1-260C-UNLIM                | -40 to 125   | RVB                 |
| <a href="#">LM4050QBEM3X5.0/NOPB</a> | Active        | Production           | SOT-23 (DBZ)   3 | 3000   LARGE T&R      | Yes         | SN                                   | Level-1-260C-UNLIM                | -40 to 125   | RVB                 |
| <a href="#">LM4050QBEM3X8.2/NOPB</a> | Active        | Production           | SOT-23 (DBZ)   3 | 3000   LARGE T&R      | Yes         | SN                                   | Level-1-260C-UNLIM                | -40 to 125   | RXB                 |
| <a href="#">LM4050QBIM3-10/NOPB</a>  | Active        | Production           | SOT-23 (DBZ)   3 | 3000   LARGE T&R      | Yes         | SN                                   | Level-1-260C-UNLIM                | -40 to 85    | RYB                 |
| LM4050QBIM3-2.0/NO.A                 | Active        | Production           | SOT-23 (DBZ)   3 | 3000   LARGE T&R      | Yes         | SN                                   | Level-1-260C-UNLIM                | -40 to 125   | RSB                 |
| <a href="#">LM4050QBIM3-2.0/NOPB</a> | Active        | Production           | SOT-23 (DBZ)   3 | 3000   LARGE T&R      | Yes         | SN                                   | Level-1-260C-UNLIM                | -40 to 85    | RSB                 |
| LM4050QBIM3-2.5/NO.A                 | Active        | Production           | SOT-23 (DBZ)   3 | 3000   LARGE T&R      | Yes         | SN                                   | Level-1-260C-UNLIM                | -40 to 125   | RTB                 |
| <a href="#">LM4050QBIM3-2.5/NOPB</a> | Active        | Production           | SOT-23 (DBZ)   3 | 3000   LARGE T&R      | Yes         | SN                                   | Level-1-260C-UNLIM                | -40 to 85    | RTB                 |
| LM4050QBIM3-4.1/NO.A                 | Active        | Production           | SOT-23 (DBZ)   3 | 3000   LARGE T&R      | Yes         | SN                                   | Level-1-260C-UNLIM                | -40 to 125   | RUB                 |
| <a href="#">LM4050QBIM3-4.1/NOPB</a> | Active        | Production           | SOT-23 (DBZ)   3 | 3000   LARGE T&R      | Yes         | SN                                   | Level-1-260C-UNLIM                | -40 to 85    | RUB                 |
| LM4050QBIM3-5.0/NO.A                 | Active        | Production           | SOT-23 (DBZ)   3 | 3000   LARGE T&R      | Yes         | SN                                   | Level-1-260C-UNLIM                | -40 to 125   | RVB                 |
| <a href="#">LM4050QBIM3-5.0/NOPB</a> | Active        | Production           | SOT-23 (DBZ)   3 | 3000   LARGE T&R      | Yes         | SN                                   | Level-1-260C-UNLIM                | -40 to 85    | RVB                 |
| <a href="#">LM4050QBIM3-8.2/NOPB</a> | Active        | Production           | SOT-23 (DBZ)   3 | 3000   LARGE T&R      | Yes         | SN                                   | Level-1-260C-UNLIM                | -40 to 85    | RXB                 |
| <a href="#">LM4050QCEM3-10/NOPB</a>  | Obsolete      | Production           | SOT-23 (DBZ)   3 | -                     | -           | Call TI                              | Call TI                           | -40 to 125   | RYC                 |
| LM4050QCEM3-2.0/NO.A                 | Active        | Production           | SOT-23 (DBZ)   3 | 3000   LARGE T&R      | Yes         | SN                                   | Level-1-260C-UNLIM                | -40 to 125   | RSC                 |



| Orderable part number                | Status<br>(1) | Material type<br>(2) | Package   Pins   | Package qty   Carrier | RoHS<br>(3) | Lead finish/<br>Ball material<br>(4) | MSL rating/<br>Peak reflow<br>(5) | Op temp (°C) | Part marking<br>(6) |
|--------------------------------------|---------------|----------------------|------------------|-----------------------|-------------|--------------------------------------|-----------------------------------|--------------|---------------------|
| <a href="#">LM4050QCEM3-2.0/NOPB</a> | Active        | Production           | SOT-23 (DBZ)   3 | 3000   LARGE T&R      | Yes         | SN                                   | Level-1-260C-UNLIM                | -40 to 125   | RSC                 |
| <a href="#">LM4050QCEM3-2.5/NO.A</a> | Active        | Production           | SOT-23 (DBZ)   3 | 3000   LARGE T&R      | Yes         | SN                                   | Level-1-260C-UNLIM                | -40 to 125   | RTC                 |
| <a href="#">LM4050QCEM3-2.5/NOPB</a> | Active        | Production           | SOT-23 (DBZ)   3 | 3000   LARGE T&R      | Yes         | SN                                   | Level-1-260C-UNLIM                | -40 to 125   | RTC                 |
| <a href="#">LM4050QCEM3-4.1/NO.A</a> | Active        | Production           | SOT-23 (DBZ)   3 | 3000   LARGE T&R      | Yes         | SN                                   | Level-1-260C-UNLIM                | -40 to 125   | RUC                 |
| <a href="#">LM4050QCEM3-4.1/NOPB</a> | Active        | Production           | SOT-23 (DBZ)   3 | 3000   LARGE T&R      | Yes         | SN                                   | Level-1-260C-UNLIM                | -40 to 125   | RUC                 |
| <a href="#">LM4050QCEM3-5.0/NO.A</a> | Active        | Production           | SOT-23 (DBZ)   3 | 3000   LARGE T&R      | Yes         | SN                                   | Level-1-260C-UNLIM                | -40 to 125   | RVC                 |
| <a href="#">LM4050QCEM3-5.0/NO.B</a> | Active        | Production           | SOT-23 (DBZ)   3 | 3000   LARGE T&R      | Yes         | SN                                   | Level-1-260C-UNLIM                | -40 to 125   | RVC                 |
| <a href="#">LM4050QCEM3-5.0/NOPB</a> | Active        | Production           | SOT-23 (DBZ)   3 | 3000   LARGE T&R      | Yes         | SN                                   | Level-1-260C-UNLIM                | -40 to 125   | RVC                 |
| <a href="#">LM4050QCEM3-8.2/NOPB</a> | Obsolete      | Production           | SOT-23 (DBZ)   3 | -                     | -           | Call TI                              | Call TI                           | -40 to 125   | RXC                 |
| <a href="#">LM4050QCEM3X10/NOPB</a>  | Active        | Production           | SOT-23 (DBZ)   3 | 3000   LARGE T&R      | Yes         | SN                                   | Level-1-260C-UNLIM                | -40 to 125   | RYC                 |
| <a href="#">LM4050QCEM3X2.0/NO.A</a> | Active        | Production           | SOT-23 (DBZ)   3 | 3000   LARGE T&R      | Yes         | SN                                   | Level-1-260C-UNLIM                | -40 to 125   | RSC                 |
| <a href="#">LM4050QCEM3X2.0/NOPB</a> | Active        | Production           | SOT-23 (DBZ)   3 | 3000   LARGE T&R      | Yes         | SN                                   | Level-1-260C-UNLIM                | -40 to 125   | RSC                 |
| <a href="#">LM4050QCEM3X2.5/NO.A</a> | Active        | Production           | SOT-23 (DBZ)   3 | 3000   LARGE T&R      | Yes         | SN                                   | Level-1-260C-UNLIM                | -40 to 125   | RTC                 |
| <a href="#">LM4050QCEM3X2.5/NOPB</a> | Active        | Production           | SOT-23 (DBZ)   3 | 3000   LARGE T&R      | Yes         | SN                                   | Level-1-260C-UNLIM                | -40 to 125   | RTC                 |
| <a href="#">LM4050QCEM3X4.1/NO.A</a> | Active        | Production           | SOT-23 (DBZ)   3 | 3000   LARGE T&R      | Yes         | SN                                   | Level-1-260C-UNLIM                | -40 to 125   | RUC                 |
| <a href="#">LM4050QCEM3X4.1/NOPB</a> | Active        | Production           | SOT-23 (DBZ)   3 | 3000   LARGE T&R      | Yes         | SN                                   | Level-1-260C-UNLIM                | -40 to 125   | RUC                 |
| <a href="#">LM4050QCEM3X5.0/NO.A</a> | Active        | Production           | SOT-23 (DBZ)   3 | 3000   LARGE T&R      | Yes         | SN                                   | Level-1-260C-UNLIM                | -40 to 125   | RVC                 |
| <a href="#">LM4050QCEM3X5.0/NOPB</a> | Active        | Production           | SOT-23 (DBZ)   3 | 3000   LARGE T&R      | Yes         | SN                                   | Level-1-260C-UNLIM                | -40 to 125   | RVC                 |
| <a href="#">LM4050QCEM3X8.2/NOPB</a> | Active        | Production           | SOT-23 (DBZ)   3 | 3000   LARGE T&R      | Yes         | SN                                   | Level-1-260C-UNLIM                | -40 to 125   | RXC                 |
| <a href="#">LM4050QCIM3-2.0/NO.A</a> | Active        | Production           | SOT-23 (DBZ)   3 | 3000   LARGE T&R      | Yes         | SN                                   | Level-1-260C-UNLIM                | -40 to 125   | RSC                 |
| <a href="#">LM4050QCIM3-2.0/NO.B</a> | Active        | Production           | SOT-23 (DBZ)   3 | 3000   LARGE T&R      | Yes         | SN                                   | Level-1-260C-UNLIM                | -40 to 125   | RSC                 |
| <a href="#">LM4050QCIM3-2.0/NOPB</a> | Active        | Production           | SOT-23 (DBZ)   3 | 3000   LARGE T&R      | Yes         | SN                                   | Level-1-260C-UNLIM                | -40 to 85    | RSC                 |
| <a href="#">LM4050QCIM3-4.1/NO.A</a> | Active        | Production           | SOT-23 (DBZ)   3 | 3000   LARGE T&R      | Yes         | SN                                   | Level-1-260C-UNLIM                | -40 to 125   | RUC                 |
| <a href="#">LM4050QCIM3-4.1/NOPB</a> | Active        | Production           | SOT-23 (DBZ)   3 | 3000   LARGE T&R      | Yes         | SN                                   | Level-1-260C-UNLIM                | -40 to 85    | RUC                 |
| <a href="#">LM4050QCIM3-5.0/NO.A</a> | Active        | Production           | SOT-23 (DBZ)   3 | 3000   LARGE T&R      | Yes         | SN                                   | Level-1-260C-UNLIM                | -40 to 125   | RVC                 |
| <a href="#">LM4050QCIM3-5.0/NOPB</a> | Active        | Production           | SOT-23 (DBZ)   3 | 3000   LARGE T&R      | Yes         | SN                                   | Level-1-260C-UNLIM                | -40 to 85    | RVC                 |

<sup>(1)</sup> **Status:** For more details on status, see our [product life cycle](#).

<sup>(2)</sup> **Material type:** When designated, preproduction parts are prototypes/experimental devices, and are not yet approved or released for full production. Testing and final process, including without limitation quality assurance, reliability performance testing, and/or process qualification, may not yet be complete, and this item is subject to further changes or possible discontinuation. If available for ordering, purchases will be subject to an additional waiver at checkout, and are intended for early internal evaluation purposes only. These items are sold without warranties of any kind.

<sup>(3)</sup> **RoHS values:** Yes, No, RoHS Exempt. See the [TI RoHS Statement](#) for additional information and value definition.

<sup>(4)</sup> **Lead finish/Ball material:** Parts may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead finish/Ball material values may wrap to two lines if the finish value exceeds the maximum column width.

<sup>(5)</sup> **MSL rating/Peak reflow:** The moisture sensitivity level ratings and peak solder (reflow) temperatures. In the event that a part has multiple moisture sensitivity ratings, only the lowest level per JEDEC standards is shown. Refer to the shipping label for the actual reflow temperature that will be used to mount the part to the printed circuit board.

<sup>(6)</sup> **Part marking:** There may be an additional marking, which relates to the logo, the lot trace code information, or the environmental category of the part.

Multiple part markings will be inside parentheses. Only one part marking contained in parentheses and separated by a "~" will appear on a part. If a line is indented then it is a continuation of the previous line and the two combined represent the entire part marking for that device.

**Important Information and Disclaimer:** The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.


In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.

**OTHER QUALIFIED VERSIONS OF LM4050-N, LM4050-N-Q1 :**

- Catalog : [LM4050-N](#)
- Automotive : [LM4050-N-Q1](#)

NOTE: Qualified Version Definitions:

- Catalog - TI's standard catalog product
- Automotive - Q100 devices qualified for high-reliability automotive applications targeting zero defects

**TAPE AND REEL INFORMATION**


\*All dimensions are nominal

| Device               | Package Type | Package Drawing | Pins | SPQ  | Reel Diameter (mm) | Reel Width W1 (mm) | A0 (mm) | B0 (mm) | K0 (mm) | P1 (mm) | W (mm) | Pin1 Quadrant |
|----------------------|--------------|-----------------|------|------|--------------------|--------------------|---------|---------|---------|---------|--------|---------------|
| LM4050AEM3-10/NOPB   | SOT-23       | DBZ             | 3    | 3000 | 178.0              | 8.4                | 3.3     | 2.9     | 1.22    | 4.0     | 8.0    | Q3            |
| LM4050AEM3-2.0/NOPB  | SOT-23       | DBZ             | 3    | 3000 | 180.0              | 8.4                | 3.2     | 2.85    | 1.3     | 4.0     | 8.0    | Q3            |
| LM4050AEM3-2.0/NOPB  | SOT-23       | DBZ             | 3    | 3000 | 178.0              | 8.4                | 3.3     | 2.9     | 1.22    | 4.0     | 8.0    | Q3            |
| LM4050AEM3-2.5/NOPB  | SOT-23       | DBZ             | 3    | 3000 | 180.0              | 8.4                | 3.2     | 2.85    | 1.3     | 4.0     | 8.0    | Q3            |
| LM4050AEM3-2.5/NOPB  | SOT-23       | DBZ             | 3    | 3000 | 178.0              | 8.4                | 3.3     | 2.9     | 1.22    | 4.0     | 8.0    | Q3            |
| LM4050AEM3-5.0/NOPB  | SOT-23       | DBZ             | 3    | 3000 | 178.0              | 8.4                | 3.3     | 2.9     | 1.22    | 4.0     | 8.0    | Q3            |
| LM4050AEM3-5.0/NOPB  | SOT-23       | DBZ             | 3    | 3000 | 180.0              | 8.4                | 3.2     | 2.85    | 1.3     | 4.0     | 8.0    | Q3            |
| LM4050AEM3-8.2/NOPB  | SOT-23       | DBZ             | 3    | 3000 | 180.0              | 8.4                | 3.2     | 2.85    | 1.3     | 4.0     | 8.0    | Q3            |
| LM4050AEM3-8.2/NOPB  | SOT-23       | DBZ             | 3    | 3000 | 178.0              | 8.4                | 3.3     | 2.9     | 1.22    | 4.0     | 8.0    | Q3            |
| LM4050AEM3X-10/NOPB  | SOT-23       | DBZ             | 3    | 3000 | 180.0              | 8.4                | 3.2     | 2.85    | 1.3     | 4.0     | 8.0    | Q3            |
| LM4050AEM3X-10/NOPB  | SOT-23       | DBZ             | 3    | 3000 | 178.0              | 8.4                | 3.3     | 2.9     | 1.22    | 4.0     | 8.0    | Q3            |
| LM4050AEM3X-2.5/NOPB | SOT-23       | DBZ             | 3    | 3000 | 178.0              | 8.4                | 3.3     | 2.9     | 1.22    | 4.0     | 8.0    | Q3            |
| LM4050AEM3X-2.5/NOPB | SOT-23       | DBZ             | 3    | 3000 | 180.0              | 8.4                | 3.2     | 2.85    | 1.3     | 4.0     | 8.0    | Q3            |
| LM4050AEM3X-5.0/NOPB | SOT-23       | DBZ             | 3    | 3000 | 178.0              | 8.4                | 3.3     | 2.9     | 1.22    | 4.0     | 8.0    | Q3            |
| LM4050AEM3X-5.0/NOPB | SOT-23       | DBZ             | 3    | 3000 | 180.0              | 8.4                | 3.2     | 2.85    | 1.3     | 4.0     | 8.0    | Q3            |
| LM4050AIM3-10/NOPB   | SOT-23       | DBZ             | 3    | 3000 | 180.0              | 8.4                | 3.2     | 2.85    | 1.3     | 4.0     | 8.0    | Q3            |



| Device               | Package Type | Package Drawing | Pins | SPQ  | Reel Diameter (mm) | Reel Width W1 (mm) | A0 (mm) | B0 (mm) | K0 (mm) | P1 (mm) | W (mm) | Pin1 Quadrant |
|----------------------|--------------|-----------------|------|------|--------------------|--------------------|---------|---------|---------|---------|--------|---------------|
| LM4050AIM3-10/NOPB   | SOT-23       | DBZ             | 3    | 3000 | 178.0              | 8.4                | 3.3     | 2.9     | 1.22    | 4.0     | 8.0    | Q3            |
| LM4050AIM3-2.5/NOPB  | SOT-23       | DBZ             | 3    | 3000 | 178.0              | 8.4                | 3.3     | 2.9     | 1.22    | 4.0     | 8.0    | Q3            |
| LM4050AIM3-2.5/NOPB  | SOT-23       | DBZ             | 3    | 3000 | 180.0              | 8.4                | 3.2     | 2.85    | 1.3     | 4.0     | 8.0    | Q3            |
| LM4050AIM3-4.1/NOPB  | SOT-23       | DBZ             | 3    | 3000 | 180.0              | 8.4                | 3.2     | 2.85    | 1.3     | 4.0     | 8.0    | Q3            |
| LM4050AIM3-4.1/NOPB  | SOT-23       | DBZ             | 3    | 3000 | 178.0              | 8.4                | 3.3     | 2.9     | 1.22    | 4.0     | 8.0    | Q3            |
| LM4050AIM3-5.0/NOPB  | SOT-23       | DBZ             | 3    | 3000 | 180.0              | 8.4                | 3.2     | 2.85    | 1.3     | 4.0     | 8.0    | Q3            |
| LM4050AIM3-5.0/NOPB  | SOT-23       | DBZ             | 3    | 3000 | 178.0              | 8.4                | 3.3     | 2.9     | 1.22    | 4.0     | 8.0    | Q3            |
| LM4050AIM3X-2.5/NOPB | SOT-23       | DBZ             | 3    | 3000 | 178.0              | 8.4                | 3.3     | 2.9     | 1.22    | 4.0     | 8.0    | Q3            |
| LM4050AIM3X-2.5/NOPB | SOT-23       | DBZ             | 3    | 3000 | 180.0              | 8.4                | 3.2     | 2.85    | 1.3     | 4.0     | 8.0    | Q3            |
| LM4050AIM3X-4.1/NOPB | SOT-23       | DBZ             | 3    | 3000 | 178.0              | 8.4                | 3.3     | 2.9     | 1.22    | 4.0     | 8.0    | Q3            |
| LM4050AIM3X-4.1/NOPB | SOT-23       | DBZ             | 3    | 3000 | 180.0              | 8.4                | 3.2     | 2.85    | 1.3     | 4.0     | 8.0    | Q3            |
| LM4050AIM3X-5.0/NOPB | SOT-23       | DBZ             | 3    | 3000 | 180.0              | 8.4                | 3.2     | 2.85    | 1.3     | 4.0     | 8.0    | Q3            |
| LM4050AIM3X-5.0/NOPB | SOT-23       | DBZ             | 3    | 3000 | 178.0              | 8.4                | 3.3     | 2.9     | 1.22    | 4.0     | 8.0    | Q3            |
| LM4050BEM3-10/NOPB   | SOT-23       | DBZ             | 3    | 3000 | 178.0              | 8.4                | 3.3     | 2.9     | 1.22    | 4.0     | 8.0    | Q3            |
| LM4050BEM3-10/NOPB   | SOT-23       | DBZ             | 3    | 3000 | 180.0              | 8.4                | 3.2     | 2.85    | 1.3     | 4.0     | 8.0    | Q3            |
| LM4050BEM3-2.5/NOPB  | SOT-23       | DBZ             | 3    | 3000 | 180.0              | 8.4                | 3.2     | 2.85    | 1.3     | 4.0     | 8.0    | Q3            |
| LM4050BEM3-2.5/NOPB  | SOT-23       | DBZ             | 3    | 3000 | 178.0              | 8.4                | 3.3     | 2.9     | 1.22    | 4.0     | 8.0    | Q3            |
| LM4050BEM3-4.1/NOPB  | SOT-23       | DBZ             | 3    | 3000 | 178.0              | 8.4                | 3.3     | 2.9     | 1.22    | 4.0     | 8.0    | Q3            |
| LM4050BEM3-4.1/NOPB  | SOT-23       | DBZ             | 3    | 3000 | 180.0              | 8.4                | 3.2     | 2.85    | 1.3     | 4.0     | 8.0    | Q3            |
| LM4050BEM3-5.0/NOPB  | SOT-23       | DBZ             | 3    | 3000 | 178.0              | 8.4                | 3.3     | 2.9     | 1.22    | 4.0     | 8.0    | Q3            |
| LM4050BEM3-5.0/NOPB  | SOT-23       | DBZ             | 3    | 3000 | 180.0              | 8.4                | 3.2     | 2.85    | 1.3     | 4.0     | 8.0    | Q3            |
| LM4050BEM3-8.2/NOPB  | SOT-23       | DBZ             | 3    | 3000 | 178.0              | 8.4                | 3.3     | 2.9     | 1.22    | 4.0     | 8.0    | Q3            |
| LM4050BEM3X-10/NOPB  | SOT-23       | DBZ             | 3    | 3000 | 178.0              | 8.4                | 3.3     | 2.9     | 1.22    | 4.0     | 8.0    | Q3            |
| LM4050BEM3X-10/NOPB  | SOT-23       | DBZ             | 3    | 3000 | 180.0              | 8.4                | 3.2     | 2.85    | 1.3     | 4.0     | 8.0    | Q3            |
| LM4050BEM3X-2.5/NOPB | SOT-23       | DBZ             | 3    | 3000 | 178.0              | 8.4                | 3.3     | 2.9     | 1.22    | 4.0     | 8.0    | Q3            |
| LM4050BEM3X-2.5/NOPB | SOT-23       | DBZ             | 3    | 3000 | 180.0              | 8.4                | 3.2     | 2.85    | 1.3     | 4.0     | 8.0    | Q3            |
| LM4050BEM3X-5.0/NOPB | SOT-23       | DBZ             | 3    | 3000 | 180.0              | 8.4                | 3.2     | 2.85    | 1.3     | 4.0     | 8.0    | Q3            |
| LM4050BEM3X-5.0/NOPB | SOT-23       | DBZ             | 3    | 3000 | 178.0              | 8.4                | 3.3     | 2.9     | 1.22    | 4.0     | 8.0    | Q3            |
| LM4050BIM3-10/NOPB   | SOT-23       | DBZ             | 3    | 1000 | 178.0              | 8.4                | 3.3     | 2.9     | 1.22    | 4.0     | 8.0    | Q3            |
| LM4050BIM3-2.5/NOPB  | SOT-23       | DBZ             | 3    | 3000 | 180.0              | 8.4                | 3.2     | 2.85    | 1.3     | 4.0     | 8.0    | Q3            |
| LM4050BIM3-2.5/NOPB  | SOT-23       | DBZ             | 3    | 3000 | 178.0              | 8.4                | 3.3     | 2.9     | 1.22    | 4.0     | 8.0    | Q3            |
| LM4050BIM3-4.1/NOPB  | SOT-23       | DBZ             | 3    | 3000 | 180.0              | 8.4                | 3.2     | 2.85    | 1.3     | 4.0     | 8.0    | Q3            |
| LM4050BIM3-4.1/NOPB  | SOT-23       | DBZ             | 3    | 3000 | 178.0              | 8.4                | 3.3     | 2.9     | 1.22    | 4.0     | 8.0    | Q3            |
| LM4050BIM3-5.0/NOPB  | SOT-23       | DBZ             | 3    | 3000 | 178.0              | 8.4                | 3.3     | 2.9     | 1.22    | 4.0     | 8.0    | Q3            |
| LM4050BIM3-5.0/NOPB  | SOT-23       | DBZ             | 3    | 3000 | 180.0              | 8.4                | 3.2     | 2.85    | 1.3     | 4.0     | 8.0    | Q3            |
| LM4050BIM3X-2.0/NOPB | SOT-23       | DBZ             | 3    | 3000 | 180.0              | 8.4                | 3.2     | 2.85    | 1.3     | 4.0     | 8.0    | Q3            |
| LM4050BIM3X-2.0/NOPB | SOT-23       | DBZ             | 3    | 3000 | 178.0              | 8.4                | 3.3     | 2.9     | 1.22    | 4.0     | 8.0    | Q3            |
| LM4050BIM3X-2.5/NOPB | SOT-23       | DBZ             | 3    | 3000 | 178.0              | 8.4                | 3.3     | 2.9     | 1.22    | 4.0     | 8.0    | Q3            |
| LM4050BIM3X-2.5/NOPB | SOT-23       | DBZ             | 3    | 3000 | 180.0              | 8.4                | 3.2     | 2.85    | 1.3     | 4.0     | 8.0    | Q3            |
| LM4050BIM3X-4.1/NOPB | SOT-23       | DBZ             | 3    | 3000 | 180.0              | 8.4                | 3.2     | 2.85    | 1.3     | 4.0     | 8.0    | Q3            |
| LM4050BIM3X-4.1/NOPB | SOT-23       | DBZ             | 3    | 3000 | 178.0              | 8.4                | 3.3     | 2.9     | 1.22    | 4.0     | 8.0    | Q3            |


| Device               | Package Type | Package Drawing | Pins | SPQ  | Reel Diameter (mm) | Reel Width W1 (mm) | A0 (mm) | B0 (mm) | K0 (mm) | P1 (mm) | W (mm) | Pin1 Quadrant |
|----------------------|--------------|-----------------|------|------|--------------------|--------------------|---------|---------|---------|---------|--------|---------------|
| LM4050BIM3X-5.0/NOPB | SOT-23       | DBZ             | 3    | 3000 | 178.0              | 8.4                | 3.3     | 2.9     | 1.22    | 4.0     | 8.0    | Q3            |
| LM4050BIM3X-5.0/NOPB | SOT-23       | DBZ             | 3    | 3000 | 180.0              | 8.4                | 3.2     | 2.85    | 1.3     | 4.0     | 8.0    | Q3            |
| LM4050CEM3-10/NOPB   | SOT-23       | DBZ             | 3    | 1000 | 178.0              | 8.4                | 3.3     | 2.9     | 1.22    | 4.0     | 8.0    | Q3            |
| LM4050CEM3-2.5/NOPB  | SOT-23       | DBZ             | 3    | 3000 | 180.0              | 8.4                | 3.2     | 2.85    | 1.3     | 4.0     | 8.0    | Q3            |
| LM4050CEM3-2.5/NOPB  | SOT-23       | DBZ             | 3    | 3000 | 178.0              | 8.4                | 3.3     | 2.9     | 1.22    | 4.0     | 8.0    | Q3            |
| LM4050CEM3-5.0/NOPB  | SOT-23       | DBZ             | 3    | 3000 | 178.0              | 8.4                | 3.3     | 2.9     | 1.22    | 4.0     | 8.0    | Q3            |
| LM4050CEM3-5.0/NOPB  | SOT-23       | DBZ             | 3    | 3000 | 180.0              | 8.4                | 3.2     | 2.85    | 1.3     | 4.0     | 8.0    | Q3            |
| LM4050CEM3X-2.5/NOPB | SOT-23       | DBZ             | 3    | 3000 | 178.0              | 8.4                | 3.3     | 2.9     | 1.22    | 4.0     | 8.0    | Q3            |
| LM4050CEM3X-2.5/NOPB | SOT-23       | DBZ             | 3    | 3000 | 180.0              | 8.4                | 3.2     | 2.85    | 1.3     | 4.0     | 8.0    | Q3            |
| LM4050CEM3X-5.0/NOPB | SOT-23       | DBZ             | 3    | 3000 | 180.0              | 8.4                | 3.2     | 2.85    | 1.3     | 4.0     | 8.0    | Q3            |
| LM4050CEM3X-5.0/NOPB | SOT-23       | DBZ             | 3    | 3000 | 178.0              | 8.4                | 3.3     | 2.9     | 1.22    | 4.0     | 8.0    | Q3            |
| LM4050CIM3-10/NOPB   | SOT-23       | DBZ             | 3    | 3000 | 180.0              | 8.4                | 3.2     | 2.85    | 1.3     | 4.0     | 8.0    | Q3            |
| LM4050CIM3-10/NOPB   | SOT-23       | DBZ             | 3    | 3000 | 178.0              | 8.4                | 3.3     | 2.9     | 1.22    | 4.0     | 8.0    | Q3            |
| LM4050CIM3-2.5/NOPB  | SOT-23       | DBZ             | 3    | 3000 | 178.0              | 8.4                | 3.3     | 2.9     | 1.22    | 4.0     | 8.0    | Q3            |
| LM4050CIM3-2.5/NOPB  | SOT-23       | DBZ             | 3    | 3000 | 180.0              | 8.4                | 3.2     | 2.85    | 1.3     | 4.0     | 8.0    | Q3            |
| LM4050CIM3-4.1/NOPB  | SOT-23       | DBZ             | 3    | 3000 | 180.0              | 8.4                | 3.2     | 2.85    | 1.3     | 4.0     | 8.0    | Q3            |
| LM4050CIM3-4.1/NOPB  | SOT-23       | DBZ             | 3    | 3000 | 178.0              | 8.4                | 3.3     | 2.9     | 1.22    | 4.0     | 8.0    | Q3            |
| LM4050CIM3-5.0/NOPB  | SOT-23       | DBZ             | 3    | 3000 | 180.0              | 8.4                | 3.2     | 2.85    | 1.3     | 4.0     | 8.0    | Q3            |
| LM4050CIM3-5.0/NOPB  | SOT-23       | DBZ             | 3    | 3000 | 178.0              | 8.4                | 3.3     | 2.9     | 1.22    | 4.0     | 8.0    | Q3            |
| LM4050CIM3X-2.0/NOPB | SOT-23       | DBZ             | 3    | 3000 | 178.0              | 8.4                | 3.3     | 2.9     | 1.22    | 4.0     | 8.0    | Q3            |
| LM4050CIM3X-2.0/NOPB | SOT-23       | DBZ             | 3    | 3000 | 180.0              | 8.4                | 3.2     | 2.85    | 1.3     | 4.0     | 8.0    | Q3            |
| LM4050CIM3X-2.5/NOPB | SOT-23       | DBZ             | 3    | 3000 | 180.0              | 8.4                | 3.2     | 2.85    | 1.3     | 4.0     | 8.0    | Q3            |
| LM4050CIM3X-2.5/NOPB | SOT-23       | DBZ             | 3    | 3000 | 178.0              | 8.4                | 3.3     | 2.9     | 1.22    | 4.0     | 8.0    | Q3            |
| LM4050CIM3X-4.1/NOPB | SOT-23       | DBZ             | 3    | 3000 | 180.0              | 8.4                | 3.2     | 2.85    | 1.3     | 4.0     | 8.0    | Q3            |
| LM4050CIM3X-4.1/NOPB | SOT-23       | DBZ             | 3    | 3000 | 178.0              | 8.4                | 3.3     | 2.9     | 1.22    | 4.0     | 8.0    | Q3            |
| LM4050CIM3X-5.0/NOPB | SOT-23       | DBZ             | 3    | 3000 | 180.0              | 8.4                | 3.2     | 2.85    | 1.3     | 4.0     | 8.0    | Q3            |
| LM4050CIM3X-5.0/NOPB | SOT-23       | DBZ             | 3    | 3000 | 178.0              | 8.4                | 3.3     | 2.9     | 1.22    | 4.0     | 8.0    | Q3            |
| LM4050QAEM3-2.0/NOPB | SOT-23       | DBZ             | 3    | 3000 | 180.0              | 8.4                | 3.2     | 2.85    | 1.3     | 4.0     | 8.0    | Q3            |
| LM4050QAEM3-2.0/NOPB | SOT-23       | DBZ             | 3    | 3000 | 178.0              | 8.4                | 3.3     | 2.9     | 1.22    | 4.0     | 8.0    | Q3            |
| LM4050QAEM3-2.5/NOPB | SOT-23       | DBZ             | 3    | 3000 | 178.0              | 8.4                | 3.3     | 2.9     | 1.22    | 4.0     | 8.0    | Q3            |
| LM4050QAEM3-2.5/NOPB | SOT-23       | DBZ             | 3    | 3000 | 180.0              | 8.4                | 3.2     | 2.85    | 1.3     | 4.0     | 8.0    | Q3            |
| LM4050QAEM3-4.1/NOPB | SOT-23       | DBZ             | 3    | 3000 | 178.0              | 8.4                | 3.3     | 2.9     | 1.22    | 4.0     | 8.0    | Q3            |
| LM4050QAEM3-4.1/NOPB | SOT-23       | DBZ             | 3    | 3000 | 180.0              | 8.4                | 3.2     | 2.85    | 1.3     | 4.0     | 8.0    | Q3            |
| LM4050QAEM3-5.0/NOPB | SOT-23       | DBZ             | 3    | 3000 | 180.0              | 8.4                | 3.2     | 2.85    | 1.3     | 4.0     | 8.0    | Q3            |
| LM4050QAEM3-5.0/NOPB | SOT-23       | DBZ             | 3    | 3000 | 178.0              | 8.4                | 3.3     | 2.9     | 1.22    | 4.0     | 8.0    | Q3            |

| Device                | Package Type | Package Drawing | Pins | SPQ  | Reel Diameter (mm) | Reel Width W1 (mm) | A0 (mm) | B0 (mm) | K0 (mm) | P1 (mm) | W (mm) | Pin1 Quadrant |
|-----------------------|--------------|-----------------|------|------|--------------------|--------------------|---------|---------|---------|---------|--------|---------------|
| LM4050QAEM3X10/ NOPB  | SOT-23       | DBZ             | 3    | 3000 | 178.0              | 8.4                | 3.3     | 2.9     | 1.22    | 4.0     | 8.0    | Q3            |
| LM4050QAEM3X2.0/ NOPB | SOT-23       | DBZ             | 3    | 3000 | 180.0              | 8.4                | 3.2     | 2.85    | 1.3     | 4.0     | 8.0    | Q3            |
| LM4050QAEM3X2.0/ NOPB | SOT-23       | DBZ             | 3    | 3000 | 178.0              | 8.4                | 3.3     | 2.9     | 1.22    | 4.0     | 8.0    | Q3            |
| LM4050QAEM3X2.5/ NOPB | SOT-23       | DBZ             | 3    | 3000 | 178.0              | 8.4                | 3.3     | 2.9     | 1.22    | 4.0     | 8.0    | Q3            |
| LM4050QAEM3X2.5/ NOPB | SOT-23       | DBZ             | 3    | 3000 | 180.0              | 8.4                | 3.2     | 2.85    | 1.3     | 4.0     | 8.0    | Q3            |
| LM4050QAEM3X4.1/ NOPB | SOT-23       | DBZ             | 3    | 3000 | 180.0              | 8.4                | 3.2     | 2.85    | 1.3     | 4.0     | 8.0    | Q3            |
| LM4050QAEM3X4.1/ NOPB | SOT-23       | DBZ             | 3    | 3000 | 178.0              | 8.4                | 3.3     | 2.9     | 1.22    | 4.0     | 8.0    | Q3            |
| LM4050QAEM3X5.0/ NOPB | SOT-23       | DBZ             | 3    | 3000 | 178.0              | 8.4                | 3.3     | 2.9     | 1.22    | 4.0     | 8.0    | Q3            |
| LM4050QAEM3X5.0/ NOPB | SOT-23       | DBZ             | 3    | 3000 | 180.0              | 8.4                | 3.2     | 2.85    | 1.3     | 4.0     | 8.0    | Q3            |
| LM4050QAEM3X8.2/ NOPB | SOT-23       | DBZ             | 3    | 3000 | 178.0              | 8.4                | 3.3     | 2.9     | 1.22    | 4.0     | 8.0    | Q3            |
| LM4050QAIM3-10/NOPB   | SOT-23       | DBZ             | 3    | 3000 | 178.0              | 8.4                | 3.3     | 2.9     | 1.22    | 4.0     | 8.0    | Q3            |
| LM4050QAIM3-2.0/NOPB  | SOT-23       | DBZ             | 3    | 3000 | 180.0              | 8.4                | 3.2     | 2.85    | 1.3     | 4.0     | 8.0    | Q3            |
| LM4050QAIM3-2.0/NOPB  | SOT-23       | DBZ             | 3    | 3000 | 178.0              | 8.4                | 3.3     | 2.9     | 1.22    | 4.0     | 8.0    | Q3            |
| LM4050QAIM3-2.5/NOPB  | SOT-23       | DBZ             | 3    | 3000 | 180.0              | 8.4                | 3.2     | 2.85    | 1.3     | 4.0     | 8.0    | Q3            |
| LM4050QAIM3-2.5/NOPB  | SOT-23       | DBZ             | 3    | 3000 | 178.0              | 8.4                | 3.3     | 2.9     | 1.22    | 4.0     | 8.0    | Q3            |
| LM4050QAIM3-4.1/NOPB  | SOT-23       | DBZ             | 3    | 3000 | 178.0              | 8.4                | 3.3     | 2.9     | 1.22    | 4.0     | 8.0    | Q3            |
| LM4050QAIM3-4.1/NOPB  | SOT-23       | DBZ             | 3    | 3000 | 180.0              | 8.4                | 3.2     | 2.85    | 1.3     | 4.0     | 8.0    | Q3            |
| LM4050QAIM3-8.2/NOPB  | SOT-23       | DBZ             | 3    | 3000 | 178.0              | 8.4                | 3.3     | 2.9     | 1.22    | 4.0     | 8.0    | Q3            |
| LM4050QAIM3X4.1/NOPB  | SOT-23       | DBZ             | 3    | 3000 | 178.0              | 8.4                | 3.3     | 2.9     | 1.22    | 4.0     | 8.0    | Q3            |
| LM4050QAIM3X4.1/NOPB  | SOT-23       | DBZ             | 3    | 3000 | 180.0              | 8.4                | 3.2     | 2.85    | 1.3     | 4.0     | 8.0    | Q3            |
| LM4050QBEM3-2.0/ NOPB | SOT-23       | DBZ             | 3    | 3000 | 178.0              | 8.4                | 3.3     | 2.9     | 1.22    | 4.0     | 8.0    | Q3            |
| LM4050QBEM3-2.0/ NOPB | SOT-23       | DBZ             | 3    | 3000 | 180.0              | 8.4                | 3.2     | 2.85    | 1.3     | 4.0     | 8.0    | Q3            |
| LM4050QBEM3-2.5/ NOPB | SOT-23       | DBZ             | 3    | 3000 | 180.0              | 8.4                | 3.2     | 2.85    | 1.3     | 4.0     | 8.0    | Q3            |
| LM4050QBEM3-2.5/ NOPB | SOT-23       | DBZ             | 3    | 3000 | 178.0              | 8.4                | 3.3     | 2.9     | 1.22    | 4.0     | 8.0    | Q3            |
| LM4050QBEM3-4.1/ NOPB | SOT-23       | DBZ             | 3    | 3000 | 178.0              | 8.4                | 3.3     | 2.9     | 1.22    | 4.0     | 8.0    | Q3            |
| LM4050QBEM3-4.1/ NOPB | SOT-23       | DBZ             | 3    | 3000 | 180.0              | 8.4                | 3.2     | 2.85    | 1.3     | 4.0     | 8.0    | Q3            |
| LM4050QBEM3-5.0/ NOPB | SOT-23       | DBZ             | 3    | 3000 | 180.0              | 8.4                | 3.2     | 2.85    | 1.3     | 4.0     | 8.0    | Q3            |
| LM4050QBEM3-5.0/ NOPB | SOT-23       | DBZ             | 3    | 3000 | 178.0              | 8.4                | 3.3     | 2.9     | 1.22    | 4.0     | 8.0    | Q3            |

| Device                | Package Type | Package Drawing | Pins | SPQ  | Reel Diameter (mm) | Reel Width W1 (mm) | A0 (mm) | B0 (mm) | K0 (mm) | P1 (mm) | W (mm) | Pin1 Quadrant |
|-----------------------|--------------|-----------------|------|------|--------------------|--------------------|---------|---------|---------|---------|--------|---------------|
| LM4050QBEM3X10/ NOPB  | SOT-23       | DBZ             | 3    | 3000 | 178.0              | 8.4                | 3.3     | 2.9     | 1.22    | 4.0     | 8.0    | Q3            |
| LM4050QBEM3X2.0/ NOPB | SOT-23       | DBZ             | 3    | 3000 | 180.0              | 8.4                | 3.2     | 2.85    | 1.3     | 4.0     | 8.0    | Q3            |
| LM4050QBEM3X2.0/ NOPB | SOT-23       | DBZ             | 3    | 3000 | 178.0              | 8.4                | 3.3     | 2.9     | 1.22    | 4.0     | 8.0    | Q3            |
| LM4050QBEM3X2.5/ NOPB | SOT-23       | DBZ             | 3    | 3000 | 180.0              | 8.4                | 3.2     | 2.85    | 1.3     | 4.0     | 8.0    | Q3            |
| LM4050QBEM3X2.5/ NOPB | SOT-23       | DBZ             | 3    | 3000 | 178.0              | 8.4                | 3.3     | 2.9     | 1.22    | 4.0     | 8.0    | Q3            |
| LM4050QBEM3X4.1/ NOPB | SOT-23       | DBZ             | 3    | 3000 | 180.0              | 8.4                | 3.2     | 2.85    | 1.3     | 4.0     | 8.0    | Q3            |
| LM4050QBEM3X4.1/ NOPB | SOT-23       | DBZ             | 3    | 3000 | 178.0              | 8.4                | 3.3     | 2.9     | 1.22    | 4.0     | 8.0    | Q3            |
| LM4050QBEM3X5.0/ NOPB | SOT-23       | DBZ             | 3    | 3000 | 178.0              | 8.4                | 3.3     | 2.9     | 1.22    | 4.0     | 8.0    | Q3            |
| LM4050QBEM3X5.0/ NOPB | SOT-23       | DBZ             | 3    | 3000 | 180.0              | 8.4                | 3.2     | 2.85    | 1.3     | 4.0     | 8.0    | Q3            |
| LM4050QBEM3X8.2/ NOPB | SOT-23       | DBZ             | 3    | 3000 | 178.0              | 8.4                | 3.3     | 2.9     | 1.22    | 4.0     | 8.0    | Q3            |
| LM4050QBIM3-10/NOPB   | SOT-23       | DBZ             | 3    | 3000 | 178.0              | 8.4                | 3.3     | 2.9     | 1.22    | 4.0     | 8.0    | Q3            |
| LM4050QBIM3-2.0/NOPB  | SOT-23       | DBZ             | 3    | 3000 | 178.0              | 8.4                | 3.3     | 2.9     | 1.22    | 4.0     | 8.0    | Q3            |
| LM4050QBIM3-2.0/NOPB  | SOT-23       | DBZ             | 3    | 3000 | 180.0              | 8.4                | 3.2     | 2.85    | 1.3     | 4.0     | 8.0    | Q3            |
| LM4050QBIM3-2.5/NOPB  | SOT-23       | DBZ             | 3    | 3000 | 180.0              | 8.4                | 3.2     | 2.85    | 1.3     | 4.0     | 8.0    | Q3            |
| LM4050QBIM3-2.5/NOPB  | SOT-23       | DBZ             | 3    | 3000 | 178.0              | 8.4                | 3.3     | 2.9     | 1.22    | 4.0     | 8.0    | Q3            |
| LM4050QBIM3-4.1/NOPB  | SOT-23       | DBZ             | 3    | 3000 | 178.0              | 8.4                | 3.3     | 2.9     | 1.22    | 4.0     | 8.0    | Q3            |
| LM4050QBIM3-4.1/NOPB  | SOT-23       | DBZ             | 3    | 3000 | 180.0              | 8.4                | 3.2     | 2.85    | 1.3     | 4.0     | 8.0    | Q3            |
| LM4050QBIM3-5.0/NOPB  | SOT-23       | DBZ             | 3    | 3000 | 180.0              | 8.4                | 3.2     | 2.85    | 1.3     | 4.0     | 8.0    | Q3            |
| LM4050QBIM3-5.0/NOPB  | SOT-23       | DBZ             | 3    | 3000 | 178.0              | 8.4                | 3.3     | 2.9     | 1.22    | 4.0     | 8.0    | Q3            |
| LM4050QBIM3-8.2/NOPB  | SOT-23       | DBZ             | 3    | 3000 | 178.0              | 8.4                | 3.3     | 2.9     | 1.22    | 4.0     | 8.0    | Q3            |
| LM4050QCEM3-2.0/ NOPB | SOT-23       | DBZ             | 3    | 3000 | 178.0              | 8.4                | 3.3     | 2.9     | 1.22    | 4.0     | 8.0    | Q3            |
| LM4050QCEM3-2.0/ NOPB | SOT-23       | DBZ             | 3    | 3000 | 180.0              | 8.4                | 3.2     | 2.85    | 1.3     | 4.0     | 8.0    | Q3            |
| LM4050QCEM3-2.5/ NOPB | SOT-23       | DBZ             | 3    | 3000 | 180.0              | 8.4                | 3.2     | 2.85    | 1.3     | 4.0     | 8.0    | Q3            |
| LM4050QCEM3-2.5/ NOPB | SOT-23       | DBZ             | 3    | 3000 | 178.0              | 8.4                | 3.3     | 2.9     | 1.22    | 4.0     | 8.0    | Q3            |
| LM4050QCEM3-4.1/ NOPB | SOT-23       | DBZ             | 3    | 3000 | 180.0              | 8.4                | 3.2     | 2.85    | 1.3     | 4.0     | 8.0    | Q3            |
| LM4050QCEM3-4.1/ NOPB | SOT-23       | DBZ             | 3    | 3000 | 178.0              | 8.4                | 3.3     | 2.9     | 1.22    | 4.0     | 8.0    | Q3            |
| LM4050QCEM3-5.0/ NOPB | SOT-23       | DBZ             | 3    | 3000 | 178.0              | 8.4                | 3.3     | 2.9     | 1.22    | 4.0     | 8.0    | Q3            |
| LM4050QCEM3-5.0/ NOPB | SOT-23       | DBZ             | 3    | 3000 | 180.0              | 8.4                | 3.2     | 2.85    | 1.3     | 4.0     | 8.0    | Q3            |

| Device                | Package Type | Package Drawing | Pins | SPQ  | Reel Diameter (mm) | Reel Width W1 (mm) | A0 (mm) | B0 (mm) | K0 (mm) | P1 (mm) | W (mm) | Pin1 Quadrant |
|-----------------------|--------------|-----------------|------|------|--------------------|--------------------|---------|---------|---------|---------|--------|---------------|
| LM4050QCEM3X10/ NOPB  | SOT-23       | DBZ             | 3    | 3000 | 178.0              | 8.4                | 3.3     | 2.9     | 1.22    | 4.0     | 8.0    | Q3            |
| LM4050QCEM3X2.0/ NOPB | SOT-23       | DBZ             | 3    | 3000 | 178.0              | 8.4                | 3.3     | 2.9     | 1.22    | 4.0     | 8.0    | Q3            |
| LM4050QCEM3X2.0/ NOPB | SOT-23       | DBZ             | 3    | 3000 | 180.0              | 8.4                | 3.2     | 2.85    | 1.3     | 4.0     | 8.0    | Q3            |
| LM4050QCEM3X2.5/ NOPB | SOT-23       | DBZ             | 3    | 3000 | 180.0              | 8.4                | 3.2     | 2.85    | 1.3     | 4.0     | 8.0    | Q3            |
| LM4050QCEM3X2.5/ NOPB | SOT-23       | DBZ             | 3    | 3000 | 178.0              | 8.4                | 3.3     | 2.9     | 1.22    | 4.0     | 8.0    | Q3            |
| LM4050QCEM3X4.1/ NOPB | SOT-23       | DBZ             | 3    | 3000 | 180.0              | 8.4                | 3.2     | 2.85    | 1.3     | 4.0     | 8.0    | Q3            |
| LM4050QCEM3X4.1/ NOPB | SOT-23       | DBZ             | 3    | 3000 | 178.0              | 8.4                | 3.3     | 2.9     | 1.22    | 4.0     | 8.0    | Q3            |
| LM4050QCEM3X5.0/ NOPB | SOT-23       | DBZ             | 3    | 3000 | 178.0              | 8.4                | 3.3     | 2.9     | 1.22    | 4.0     | 8.0    | Q3            |
| LM4050QCEM3X5.0/ NOPB | SOT-23       | DBZ             | 3    | 3000 | 180.0              | 8.4                | 3.2     | 2.85    | 1.3     | 4.0     | 8.0    | Q3            |
| LM4050QCEM3X8.2/ NOPB | SOT-23       | DBZ             | 3    | 3000 | 178.0              | 8.4                | 3.3     | 2.9     | 1.22    | 4.0     | 8.0    | Q3            |
| LM4050QCIM3-2.0/NOPB  | SOT-23       | DBZ             | 3    | 3000 | 180.0              | 8.4                | 3.2     | 2.85    | 1.3     | 4.0     | 8.0    | Q3            |
| LM4050QCIM3-2.0/NOPB  | SOT-23       | DBZ             | 3    | 3000 | 178.0              | 8.4                | 3.3     | 2.9     | 1.22    | 4.0     | 8.0    | Q3            |
| LM4050QCIM3-4.1/NOPB  | SOT-23       | DBZ             | 3    | 3000 | 178.0              | 8.4                | 3.3     | 2.9     | 1.22    | 4.0     | 8.0    | Q3            |
| LM4050QCIM3-4.1/NOPB  | SOT-23       | DBZ             | 3    | 3000 | 180.0              | 8.4                | 3.2     | 2.85    | 1.3     | 4.0     | 8.0    | Q3            |
| LM4050QCIM3-5.0/NOPB  | SOT-23       | DBZ             | 3    | 3000 | 180.0              | 8.4                | 3.2     | 2.85    | 1.3     | 4.0     | 8.0    | Q3            |
| LM4050QCIM3-5.0/NOPB  | SOT-23       | DBZ             | 3    | 3000 | 178.0              | 8.4                | 3.3     | 2.9     | 1.22    | 4.0     | 8.0    | Q3            |

## TAPE AND REEL BOX DIMENSIONS



\*All dimensions are nominal

| Device               | Package Type | Package Drawing | Pins | SPQ  | Length (mm) | Width (mm) | Height (mm) |
|----------------------|--------------|-----------------|------|------|-------------|------------|-------------|
| LM4050AEM3-10/NOPB   | SOT-23       | DBZ             | 3    | 3000 | 208.0       | 191.0      | 35.0        |
| LM4050AEM3-2.0/NOPB  | SOT-23       | DBZ             | 3    | 3000 | 210.0       | 185.0      | 35.0        |
| LM4050AEM3-2.0/NOPB  | SOT-23       | DBZ             | 3    | 3000 | 208.0       | 191.0      | 35.0        |
| LM4050AEM3-2.5/NOPB  | SOT-23       | DBZ             | 3    | 3000 | 210.0       | 185.0      | 35.0        |
| LM4050AEM3-2.5/NOPB  | SOT-23       | DBZ             | 3    | 3000 | 208.0       | 191.0      | 35.0        |
| LM4050AEM3-5.0/NOPB  | SOT-23       | DBZ             | 3    | 3000 | 208.0       | 191.0      | 35.0        |
| LM4050AEM3-5.0/NOPB  | SOT-23       | DBZ             | 3    | 3000 | 210.0       | 185.0      | 35.0        |
| LM4050AEM3-8.2/NOPB  | SOT-23       | DBZ             | 3    | 3000 | 210.0       | 185.0      | 35.0        |
| LM4050AEM3-8.2/NOPB  | SOT-23       | DBZ             | 3    | 3000 | 208.0       | 191.0      | 35.0        |
| LM4050AEM3X-10/NOPB  | SOT-23       | DBZ             | 3    | 3000 | 210.0       | 185.0      | 35.0        |
| LM4050AEM3X-10/NOPB  | SOT-23       | DBZ             | 3    | 3000 | 208.0       | 191.0      | 35.0        |
| LM4050AEM3X-2.5/NOPB | SOT-23       | DBZ             | 3    | 3000 | 208.0       | 191.0      | 35.0        |
| LM4050AEM3X-2.5/NOPB | SOT-23       | DBZ             | 3    | 3000 | 210.0       | 185.0      | 35.0        |
| LM4050AEM3X-5.0/NOPB | SOT-23       | DBZ             | 3    | 3000 | 208.0       | 191.0      | 35.0        |
| LM4050AEM3X-5.0/NOPB | SOT-23       | DBZ             | 3    | 3000 | 210.0       | 185.0      | 35.0        |
| LM4050AIM3-10/NOPB   | SOT-23       | DBZ             | 3    | 3000 | 210.0       | 185.0      | 35.0        |
| LM4050AIM3-10/NOPB   | SOT-23       | DBZ             | 3    | 3000 | 208.0       | 191.0      | 35.0        |
| LM4050AIM3-2.5/NOPB  | SOT-23       | DBZ             | 3    | 3000 | 208.0       | 191.0      | 35.0        |

| Device               | Package Type | Package Drawing | Pins | SPQ  | Length (mm) | Width (mm) | Height (mm) |
|----------------------|--------------|-----------------|------|------|-------------|------------|-------------|
| LM4050AIM3-2.5/NOPB  | SOT-23       | DBZ             | 3    | 3000 | 210.0       | 185.0      | 35.0        |
| LM4050AIM3-4.1/NOPB  | SOT-23       | DBZ             | 3    | 3000 | 210.0       | 185.0      | 35.0        |
| LM4050AIM3-4.1/NOPB  | SOT-23       | DBZ             | 3    | 3000 | 208.0       | 191.0      | 35.0        |
| LM4050AIM3-5.0/NOPB  | SOT-23       | DBZ             | 3    | 3000 | 210.0       | 185.0      | 35.0        |
| LM4050AIM3-5.0/NOPB  | SOT-23       | DBZ             | 3    | 3000 | 208.0       | 191.0      | 35.0        |
| LM4050AIM3X-2.5/NOPB | SOT-23       | DBZ             | 3    | 3000 | 208.0       | 191.0      | 35.0        |
| LM4050AIM3X-2.5/NOPB | SOT-23       | DBZ             | 3    | 3000 | 210.0       | 185.0      | 35.0        |
| LM4050AIM3X-4.1/NOPB | SOT-23       | DBZ             | 3    | 3000 | 208.0       | 191.0      | 35.0        |
| LM4050AIM3X-4.1/NOPB | SOT-23       | DBZ             | 3    | 3000 | 210.0       | 185.0      | 35.0        |
| LM4050AIM3X-5.0/NOPB | SOT-23       | DBZ             | 3    | 3000 | 210.0       | 185.0      | 35.0        |
| LM4050AIM3X-5.0/NOPB | SOT-23       | DBZ             | 3    | 3000 | 208.0       | 191.0      | 35.0        |
| LM4050BEM3-10/NOPB   | SOT-23       | DBZ             | 3    | 3000 | 208.0       | 191.0      | 35.0        |
| LM4050BEM3-10/NOPB   | SOT-23       | DBZ             | 3    | 3000 | 210.0       | 185.0      | 35.0        |
| LM4050BEM3-2.5/NOPB  | SOT-23       | DBZ             | 3    | 3000 | 210.0       | 185.0      | 35.0        |
| LM4050BEM3-2.5/NOPB  | SOT-23       | DBZ             | 3    | 3000 | 208.0       | 191.0      | 35.0        |
| LM4050BEM3-4.1/NOPB  | SOT-23       | DBZ             | 3    | 3000 | 208.0       | 191.0      | 35.0        |
| LM4050BEM3-4.1/NOPB  | SOT-23       | DBZ             | 3    | 3000 | 210.0       | 185.0      | 35.0        |
| LM4050BEM3-5.0/NOPB  | SOT-23       | DBZ             | 3    | 3000 | 208.0       | 191.0      | 35.0        |
| LM4050BEM3-5.0/NOPB  | SOT-23       | DBZ             | 3    | 3000 | 210.0       | 185.0      | 35.0        |
| LM4050BEM3-8.2/NOPB  | SOT-23       | DBZ             | 3    | 3000 | 208.0       | 191.0      | 35.0        |
| LM4050BEM3X-10/NOPB  | SOT-23       | DBZ             | 3    | 3000 | 208.0       | 191.0      | 35.0        |
| LM4050BEM3X-10/NOPB  | SOT-23       | DBZ             | 3    | 3000 | 210.0       | 185.0      | 35.0        |
| LM4050BEM3X-2.5/NOPB | SOT-23       | DBZ             | 3    | 3000 | 208.0       | 191.0      | 35.0        |
| LM4050BEM3X-2.5/NOPB | SOT-23       | DBZ             | 3    | 3000 | 210.0       | 185.0      | 35.0        |
| LM4050BEM3X-5.0/NOPB | SOT-23       | DBZ             | 3    | 3000 | 210.0       | 185.0      | 35.0        |
| LM4050BEM3X-5.0/NOPB | SOT-23       | DBZ             | 3    | 3000 | 208.0       | 191.0      | 35.0        |
| LM4050BIM3-10/NOPB   | SOT-23       | DBZ             | 3    | 1000 | 208.0       | 191.0      | 35.0        |
| LM4050BIM3-2.5/NOPB  | SOT-23       | DBZ             | 3    | 3000 | 210.0       | 185.0      | 35.0        |
| LM4050BIM3-2.5/NOPB  | SOT-23       | DBZ             | 3    | 3000 | 208.0       | 191.0      | 35.0        |
| LM4050BIM3-4.1/NOPB  | SOT-23       | DBZ             | 3    | 3000 | 210.0       | 185.0      | 35.0        |
| LM4050BIM3-4.1/NOPB  | SOT-23       | DBZ             | 3    | 3000 | 208.0       | 191.0      | 35.0        |
| LM4050BIM3-5.0/NOPB  | SOT-23       | DBZ             | 3    | 3000 | 208.0       | 191.0      | 35.0        |
| LM4050BIM3-5.0/NOPB  | SOT-23       | DBZ             | 3    | 3000 | 210.0       | 185.0      | 35.0        |
| LM4050BIM3X-2.0/NOPB | SOT-23       | DBZ             | 3    | 3000 | 210.0       | 185.0      | 35.0        |
| LM4050BIM3X-2.0/NOPB | SOT-23       | DBZ             | 3    | 3000 | 208.0       | 191.0      | 35.0        |
| LM4050BIM3X-2.5/NOPB | SOT-23       | DBZ             | 3    | 3000 | 208.0       | 191.0      | 35.0        |
| LM4050BIM3X-2.5/NOPB | SOT-23       | DBZ             | 3    | 3000 | 210.0       | 185.0      | 35.0        |
| LM4050BIM3X-4.1/NOPB | SOT-23       | DBZ             | 3    | 3000 | 210.0       | 185.0      | 35.0        |
| LM4050BIM3X-4.1/NOPB | SOT-23       | DBZ             | 3    | 3000 | 208.0       | 191.0      | 35.0        |
| LM4050BIM3X-5.0/NOPB | SOT-23       | DBZ             | 3    | 3000 | 208.0       | 191.0      | 35.0        |
| LM4050BIM3X-5.0/NOPB | SOT-23       | DBZ             | 3    | 3000 | 210.0       | 185.0      | 35.0        |
| LM4050CEM3-10/NOPB   | SOT-23       | DBZ             | 3    | 1000 | 208.0       | 191.0      | 35.0        |
| LM4050CEM3-2.5/NOPB  | SOT-23       | DBZ             | 3    | 3000 | 210.0       | 185.0      | 35.0        |

| Device                   | Package Type | Package Drawing | Pins | SPQ  | Length (mm) | Width (mm) | Height (mm) |
|--------------------------|--------------|-----------------|------|------|-------------|------------|-------------|
| LM4050CEM3-2.5/NOPB      | SOT-23       | DBZ             | 3    | 3000 | 208.0       | 191.0      | 35.0        |
| LM4050CEM3-5.0/NOPB      | SOT-23       | DBZ             | 3    | 3000 | 208.0       | 191.0      | 35.0        |
| LM4050CEM3-5.0/NOPB      | SOT-23       | DBZ             | 3    | 3000 | 210.0       | 185.0      | 35.0        |
| LM4050CEM3X-2.5/NOPB     | SOT-23       | DBZ             | 3    | 3000 | 208.0       | 191.0      | 35.0        |
| LM4050CEM3X-2.5/NOPB     | SOT-23       | DBZ             | 3    | 3000 | 210.0       | 185.0      | 35.0        |
| LM4050CEM3X-5.0/NOPB     | SOT-23       | DBZ             | 3    | 3000 | 210.0       | 185.0      | 35.0        |
| LM4050CEM3X-5.0/NOPB     | SOT-23       | DBZ             | 3    | 3000 | 208.0       | 191.0      | 35.0        |
| LM4050CIM3-10/NOPB       | SOT-23       | DBZ             | 3    | 3000 | 210.0       | 185.0      | 35.0        |
| LM4050CIM3-10/NOPB       | SOT-23       | DBZ             | 3    | 3000 | 208.0       | 191.0      | 35.0        |
| LM4050CIM3-2.5/NOPB      | SOT-23       | DBZ             | 3    | 3000 | 208.0       | 191.0      | 35.0        |
| LM4050CIM3-2.5/NOPB      | SOT-23       | DBZ             | 3    | 3000 | 210.0       | 185.0      | 35.0        |
| LM4050CIM3-4.1/NOPB      | SOT-23       | DBZ             | 3    | 3000 | 210.0       | 185.0      | 35.0        |
| LM4050CIM3-4.1/NOPB      | SOT-23       | DBZ             | 3    | 3000 | 208.0       | 191.0      | 35.0        |
| LM4050CIM3-5.0/NOPB      | SOT-23       | DBZ             | 3    | 3000 | 210.0       | 185.0      | 35.0        |
| LM4050CIM3-5.0/NOPB      | SOT-23       | DBZ             | 3    | 3000 | 208.0       | 191.0      | 35.0        |
| LM4050CIM3X-2.0/NOPB     | SOT-23       | DBZ             | 3    | 3000 | 208.0       | 191.0      | 35.0        |
| LM4050CIM3X-2.0/NOPB     | SOT-23       | DBZ             | 3    | 3000 | 210.0       | 185.0      | 35.0        |
| LM4050CIM3X-2.5/NOPB     | SOT-23       | DBZ             | 3    | 3000 | 210.0       | 185.0      | 35.0        |
| LM4050CIM3X-2.5/NOPB     | SOT-23       | DBZ             | 3    | 3000 | 208.0       | 191.0      | 35.0        |
| LM4050CIM3X-4.1/NOPB     | SOT-23       | DBZ             | 3    | 3000 | 210.0       | 185.0      | 35.0        |
| LM4050CIM3X-4.1/NOPB     | SOT-23       | DBZ             | 3    | 3000 | 208.0       | 191.0      | 35.0        |
| LM4050CIM3X-5.0/NOPB     | SOT-23       | DBZ             | 3    | 3000 | 210.0       | 185.0      | 35.0        |
| LM4050CIM3X-5.0/NOPB     | SOT-23       | DBZ             | 3    | 3000 | 208.0       | 191.0      | 35.0        |
| LM4050QAEM3-2.0/NOPB     | SOT-23       | DBZ             | 3    | 3000 | 210.0       | 185.0      | 35.0        |
| LM4050QAEM3-2.0/NOPB     | SOT-23       | DBZ             | 3    | 3000 | 208.0       | 191.0      | 35.0        |
| LM4050QAEM3-2.5/NOPB     | SOT-23       | DBZ             | 3    | 3000 | 208.0       | 191.0      | 35.0        |
| LM4050QAEM3-2.5/NOPB     | SOT-23       | DBZ             | 3    | 3000 | 210.0       | 185.0      | 35.0        |
| LM4050QAEM3-4.1/NOPB     | SOT-23       | DBZ             | 3    | 3000 | 208.0       | 191.0      | 35.0        |
| LM4050QAEM3-4.1/NOPB     | SOT-23       | DBZ             | 3    | 3000 | 210.0       | 185.0      | 35.0        |
| LM4050QAEM3-5.0/NOPB     | SOT-23       | DBZ             | 3    | 3000 | 210.0       | 185.0      | 35.0        |
| LM4050QAEM3-5.0/NOPB     | SOT-23       | DBZ             | 3    | 3000 | 208.0       | 191.0      | 35.0        |
| LM4050QAEM3X10/NOPB      | SOT-23       | DBZ             | 3    | 3000 | 208.0       | 191.0      | 35.0        |
| LM4050QAEM3X2.0/<br>NOPB | SOT-23       | DBZ             | 3    | 3000 | 210.0       | 185.0      | 35.0        |
| LM4050QAEM3X2.0/<br>NOPB | SOT-23       | DBZ             | 3    | 3000 | 208.0       | 191.0      | 35.0        |
| LM4050QAEM3X2.5/<br>NOPB | SOT-23       | DBZ             | 3    | 3000 | 208.0       | 191.0      | 35.0        |
| LM4050QAEM3X2.5/<br>NOPB | SOT-23       | DBZ             | 3    | 3000 | 210.0       | 185.0      | 35.0        |
| LM4050QAEM3X4.1/<br>NOPB | SOT-23       | DBZ             | 3    | 3000 | 210.0       | 185.0      | 35.0        |
| LM4050QAEM3X4.1/<br>NOPB | SOT-23       | DBZ             | 3    | 3000 | 208.0       | 191.0      | 35.0        |



| Device                   | Package Type | Package Drawing | Pins | SPQ  | Length (mm) | Width (mm) | Height (mm) |
|--------------------------|--------------|-----------------|------|------|-------------|------------|-------------|
| LM4050QAEM3X5.0/<br>NOPB | SOT-23       | DBZ             | 3    | 3000 | 208.0       | 191.0      | 35.0        |
| LM4050QAEM3X5.0/<br>NOPB | SOT-23       | DBZ             | 3    | 3000 | 210.0       | 185.0      | 35.0        |
| LM4050QAEM3X8.2/<br>NOPB | SOT-23       | DBZ             | 3    | 3000 | 208.0       | 191.0      | 35.0        |
| LM4050QAIM3-10/NOPB      | SOT-23       | DBZ             | 3    | 3000 | 208.0       | 191.0      | 35.0        |
| LM4050QAIM3-2.0/NOPB     | SOT-23       | DBZ             | 3    | 3000 | 210.0       | 185.0      | 35.0        |
| LM4050QAIM3-2.0/NOPB     | SOT-23       | DBZ             | 3    | 3000 | 208.0       | 191.0      | 35.0        |
| LM4050QAIM3-2.5/NOPB     | SOT-23       | DBZ             | 3    | 3000 | 210.0       | 185.0      | 35.0        |
| LM4050QAIM3-2.5/NOPB     | SOT-23       | DBZ             | 3    | 3000 | 208.0       | 191.0      | 35.0        |
| LM4050QAIM3-4.1/NOPB     | SOT-23       | DBZ             | 3    | 3000 | 208.0       | 191.0      | 35.0        |
| LM4050QAIM3-4.1/NOPB     | SOT-23       | DBZ             | 3    | 3000 | 210.0       | 185.0      | 35.0        |
| LM4050QAIM3-8.2/NOPB     | SOT-23       | DBZ             | 3    | 3000 | 208.0       | 191.0      | 35.0        |
| LM4050QAIM3X4.1/NOPB     | SOT-23       | DBZ             | 3    | 3000 | 208.0       | 191.0      | 35.0        |
| LM4050QAIM3X4.1/NOPB     | SOT-23       | DBZ             | 3    | 3000 | 210.0       | 185.0      | 35.0        |
| LM4050QBEM3-2.0/NOPB     | SOT-23       | DBZ             | 3    | 3000 | 208.0       | 191.0      | 35.0        |
| LM4050QBEM3-2.0/NOPB     | SOT-23       | DBZ             | 3    | 3000 | 210.0       | 185.0      | 35.0        |
| LM4050QBEM3-2.5/NOPB     | SOT-23       | DBZ             | 3    | 3000 | 210.0       | 185.0      | 35.0        |
| LM4050QBEM3-2.5/NOPB     | SOT-23       | DBZ             | 3    | 3000 | 208.0       | 191.0      | 35.0        |
| LM4050QBEM3-4.1/NOPB     | SOT-23       | DBZ             | 3    | 3000 | 208.0       | 191.0      | 35.0        |
| LM4050QBEM3-4.1/NOPB     | SOT-23       | DBZ             | 3    | 3000 | 210.0       | 185.0      | 35.0        |
| LM4050QBEM3-5.0/NOPB     | SOT-23       | DBZ             | 3    | 3000 | 210.0       | 185.0      | 35.0        |
| LM4050QBEM3-5.0/NOPB     | SOT-23       | DBZ             | 3    | 3000 | 208.0       | 191.0      | 35.0        |
| LM4050QBEM3X10/NOPB      | SOT-23       | DBZ             | 3    | 3000 | 208.0       | 191.0      | 35.0        |
| LM4050QBEM3X2.0/<br>NOPB | SOT-23       | DBZ             | 3    | 3000 | 210.0       | 185.0      | 35.0        |
| LM4050QBEM3X2.0/<br>NOPB | SOT-23       | DBZ             | 3    | 3000 | 208.0       | 191.0      | 35.0        |
| LM4050QBEM3X2.5/<br>NOPB | SOT-23       | DBZ             | 3    | 3000 | 210.0       | 185.0      | 35.0        |
| LM4050QBEM3X2.5/<br>NOPB | SOT-23       | DBZ             | 3    | 3000 | 208.0       | 191.0      | 35.0        |
| LM4050QBEM3X4.1/<br>NOPB | SOT-23       | DBZ             | 3    | 3000 | 210.0       | 185.0      | 35.0        |
| LM4050QBEM3X4.1/<br>NOPB | SOT-23       | DBZ             | 3    | 3000 | 208.0       | 191.0      | 35.0        |
| LM4050QBEM3X5.0/<br>NOPB | SOT-23       | DBZ             | 3    | 3000 | 208.0       | 191.0      | 35.0        |
| LM4050QBEM3X5.0/<br>NOPB | SOT-23       | DBZ             | 3    | 3000 | 210.0       | 185.0      | 35.0        |
| LM4050QBEM3X8.2/<br>NOPB | SOT-23       | DBZ             | 3    | 3000 | 208.0       | 191.0      | 35.0        |
| LM4050QBIM3-10/NOPB      | SOT-23       | DBZ             | 3    | 3000 | 208.0       | 191.0      | 35.0        |
| LM4050QBIM3-2.0/NOPB     | SOT-23       | DBZ             | 3    | 3000 | 208.0       | 191.0      | 35.0        |
| LM4050QBIM3-2.0/NOPB     | SOT-23       | DBZ             | 3    | 3000 | 210.0       | 185.0      | 35.0        |

| Device                   | Package Type | Package Drawing | Pins | SPQ  | Length (mm) | Width (mm) | Height (mm) |
|--------------------------|--------------|-----------------|------|------|-------------|------------|-------------|
| LM4050QBIM3-2.5/NOPB     | SOT-23       | DBZ             | 3    | 3000 | 210.0       | 185.0      | 35.0        |
| LM4050QBIM3-2.5/NOPB     | SOT-23       | DBZ             | 3    | 3000 | 208.0       | 191.0      | 35.0        |
| LM4050QBIM3-4.1/NOPB     | SOT-23       | DBZ             | 3    | 3000 | 208.0       | 191.0      | 35.0        |
| LM4050QBIM3-4.1/NOPB     | SOT-23       | DBZ             | 3    | 3000 | 210.0       | 185.0      | 35.0        |
| LM4050QBIM3-5.0/NOPB     | SOT-23       | DBZ             | 3    | 3000 | 210.0       | 185.0      | 35.0        |
| LM4050QBIM3-5.0/NOPB     | SOT-23       | DBZ             | 3    | 3000 | 208.0       | 191.0      | 35.0        |
| LM4050QBIM3-8.2/NOPB     | SOT-23       | DBZ             | 3    | 3000 | 208.0       | 191.0      | 35.0        |
| LM4050QCEM3-2.0/NOPB     | SOT-23       | DBZ             | 3    | 3000 | 208.0       | 191.0      | 35.0        |
| LM4050QCEM3-2.0/NOPB     | SOT-23       | DBZ             | 3    | 3000 | 210.0       | 185.0      | 35.0        |
| LM4050QCEM3-2.5/NOPB     | SOT-23       | DBZ             | 3    | 3000 | 210.0       | 185.0      | 35.0        |
| LM4050QCEM3-2.5/NOPB     | SOT-23       | DBZ             | 3    | 3000 | 208.0       | 191.0      | 35.0        |
| LM4050QCEM3-4.1/NOPB     | SOT-23       | DBZ             | 3    | 3000 | 210.0       | 185.0      | 35.0        |
| LM4050QCEM3-4.1/NOPB     | SOT-23       | DBZ             | 3    | 3000 | 208.0       | 191.0      | 35.0        |
| LM4050QCEM3-5.0/NOPB     | SOT-23       | DBZ             | 3    | 3000 | 208.0       | 191.0      | 35.0        |
| LM4050QCEM3-5.0/NOPB     | SOT-23       | DBZ             | 3    | 3000 | 210.0       | 185.0      | 35.0        |
| LM4050QCEM3X10/NOPB      | SOT-23       | DBZ             | 3    | 3000 | 208.0       | 191.0      | 35.0        |
| LM4050QCEM3X2.0/<br>NOPB | SOT-23       | DBZ             | 3    | 3000 | 208.0       | 191.0      | 35.0        |
| LM4050QCEM3X2.0/<br>NOPB | SOT-23       | DBZ             | 3    | 3000 | 210.0       | 185.0      | 35.0        |
| LM4050QCEM3X2.5/<br>NOPB | SOT-23       | DBZ             | 3    | 3000 | 210.0       | 185.0      | 35.0        |
| LM4050QCEM3X2.5/<br>NOPB | SOT-23       | DBZ             | 3    | 3000 | 208.0       | 191.0      | 35.0        |
| LM4050QCEM3X4.1/<br>NOPB | SOT-23       | DBZ             | 3    | 3000 | 210.0       | 185.0      | 35.0        |
| LM4050QCEM3X4.1/<br>NOPB | SOT-23       | DBZ             | 3    | 3000 | 208.0       | 191.0      | 35.0        |
| LM4050QCEM3X5.0/<br>NOPB | SOT-23       | DBZ             | 3    | 3000 | 208.0       | 191.0      | 35.0        |
| LM4050QCEM3X5.0/<br>NOPB | SOT-23       | DBZ             | 3    | 3000 | 210.0       | 185.0      | 35.0        |
| LM4050QCEM3X8.2/<br>NOPB | SOT-23       | DBZ             | 3    | 3000 | 208.0       | 191.0      | 35.0        |
| LM4050QCIM3-2.0/NOPB     | SOT-23       | DBZ             | 3    | 3000 | 210.0       | 185.0      | 35.0        |
| LM4050QCIM3-2.0/NOPB     | SOT-23       | DBZ             | 3    | 3000 | 208.0       | 191.0      | 35.0        |
| LM4050QCIM3-4.1/NOPB     | SOT-23       | DBZ             | 3    | 3000 | 208.0       | 191.0      | 35.0        |
| LM4050QCIM3-4.1/NOPB     | SOT-23       | DBZ             | 3    | 3000 | 210.0       | 185.0      | 35.0        |
| LM4050QCIM3-5.0/NOPB     | SOT-23       | DBZ             | 3    | 3000 | 210.0       | 185.0      | 35.0        |
| LM4050QCIM3-5.0/NOPB     | SOT-23       | DBZ             | 3    | 3000 | 208.0       | 191.0      | 35.0        |




# EXAMPLE BOARD LAYOUT



DBZ0003A

SOT-23 - 1.12 mm max height

SMALL OUTLINE TRANSISTOR



LAND PATTERN EXAMPLE  
SCALE:15X



SOLDER MASK DETAILS

4214838/F 08/2024

NOTES: (continued)


5. Publication IPC-7351 may have alternate designs.
6. Solder mask tolerances between and around signal pads can vary based on board fabrication site.

## EXAMPLE STENCIL DESIGN

DBZ0003A

SOT-23 - 1.12 mm max height

SMALL OUTLINE TRANSISTOR



SOLDER PASTE EXAMPLE  
BASED ON 0.125 THICK STENCIL  
SCALE:15X

4214838/F 08/2024

NOTES: (continued)

7. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.
8. Board assembly site may have different recommendations for stencil design.

## IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATASHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, regulatory or other requirements.

These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you fully indemnify TI and its representatives against any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to [TI's Terms of Sale](#), [TI's General Quality Guidelines](#), or other applicable terms available either on [ti.com](https://www.ti.com) or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products. Unless TI explicitly designates a product as custom or customer-specified, TI products are standard, catalog, general purpose devices.

TI objects to and rejects any additional or different terms you may propose.

Copyright © 2026, Texas Instruments Incorporated

Last updated 10/2025