

## LMH664x Low Power, 130 MHz, 75 mA Rail-to-Rail Output Amplifiers

### 1 Features

( $V_S = \pm 5\text{ V}$ ,  $T_A = 25^\circ\text{C}$ ,  $R_L = 2\text{ k}\Omega$ ,  $A_V = +1$ . Typical Values Unless Specified).

- -3 dB BW ( $A_V = +1$ ) 130 MHz
- Supply Voltage Range 2.7 V to 12.8 V
- Slew Rate, ( $A_V = -1$ )  $130\text{V}/\mu\text{s}$ <sup>(1)</sup>
- Supply Current (no load) 2.7 mA/amp
- Output Short Circuit Current +115 mA to 145 mA
- Linear Output Current  $\pm 75\text{ mA}$
- Input Common Mode Volt. 0.5 V Beyond  $V^-$ , 1 V from  $V^+$
- Output Voltage Swing 40 mV from Rails
- Input Voltage Noise (100 kHz)  $17\text{nV}/\sqrt{\text{Hz}}$
- Input Current Noise (100 kHz)  $0.9\text{pA}/\sqrt{\text{Hz}}$
- THD (5MHz,  $R_L = 2\text{ k}\Omega$ ,  $V_O = 2V_{PP}$ ,  $A_V = +2$ ) -62 dBc
- Settling Time 68 ns
- Fully Characterized for 3 V, 5 V, and  $\pm 5\text{ V}$
- Overdrive Recovery 100 ns
- Output Short Circuit Protected<sup>(2)</sup>
- No Output Phase Reversal with CMVR Exceeded

<sup>(1)</sup> Slew rate is the average of the rising and falling slew rates

<sup>(2)</sup> Output short circuit duration is infinite for  $V_S < 6\text{ V}$  at room temperature and below. For  $V_S > 6\text{ V}$ , allowable short circuit duration is 1.5 ms.

### 2 Applications

- Active Filters
- CD/DVD ROM
- ADC Buffer Amp
- Portable Video
- Current Sense Buffer

### 3 Description

The LMH664X family true single supply voltage feedback amplifiers offer high speed (130 MHz), low distortion (-62 dBc), and exceptionally high output current (approximately 75 mA) at low cost and with reduced power consumption when compared against existing devices with similar performance.


Input common mode voltage range extends to 0.5 V below  $V^-$  and 1 V from  $V^+$ . Output voltage range extends to within 40 mV of either supply rail, allowing wide dynamic range especially desirable in low voltage applications. The output stage is capable of approximately 75 mA in order to drive heavy loads. Fast output Slew Rate ( $130\text{ V}/\mu\text{s}$ ) ensures large peak-to-peak output swings can be maintained even at higher speeds, resulting in exceptional full power bandwidth of 40 MHz with a 3 V supply. These characteristics, along with low cost, are ideal features for a multitude of industrial and commercial applications.

#### Device Information<sup>(1)</sup>

| PART NUMBER | PACKAGE    | BODY SIZE (NOM)   |
|-------------|------------|-------------------|
| LMH6642     | SOT-23 (5) | 2.90 mm x 1.60 mm |
|             | SOIC (8)   | 4.90 mm x 3.91 mm |
| LMH6643     | SOIC (8)   | 3.00 mm x 3.00 mm |
|             | VSSOP (8)  |                   |
| LMH6644     | SOIC (14)  | 8.64 mm x 3.91 mm |
|             | TSSOP (14) | 5.00 mm x 4.40 mm |

<sup>(1)</sup> For all available packages, see the orderable addendum at the end of the datasheet.

#### Closed Loop Gain vs. Frequency for Various Supplies



## Table of Contents

|  |           |  |           |
|--|-----------|--|-----------|
| <b>1 Features</b> .....                        | <b>1</b>  | 8.2 Functional Block Diagram .....                               | <b>21</b> |
| <b>2 Applications</b> .....                    | <b>1</b>  | 8.3 Feature Description.....                                     | <b>21</b> |
| <b>3 Description</b> .....                     | <b>1</b>  | 8.4 Device Functional Modes.....                                 | <b>21</b> |
| <b>4 Revision History</b> .....                | <b>2</b>  | <b>9 Application and Implementation</b> .....                    | <b>22</b> |
| <b>5 Description (continued)</b> .....         | <b>3</b>  | 9.1 Application Information.....                                 | <b>22</b> |
| <b>6 Pin Configuration and Functions</b> ..... | <b>4</b>  | 9.2 Typical Application .....                                    | <b>22</b> |
| <b>7 Specifications</b> .....                  | <b>5</b>  | <b>10 Power Supply Recommendations</b> .....                     | <b>24</b> |
| 7.1 Absolute Maximum Ratings .....             | <b>5</b>  | <b>11 Layout</b> .....   | <b>25</b> |
| 7.2 Handling Ratings.....                      | <b>5</b>  | 11.1 Layout Guidelines .....                                     | <b>25</b> |
| 7.3 Recommended Operating Conditions.....      | <b>5</b>  | 11.2 Layout Example .....  | <b>25</b> |
| 7.4 Thermal Information .....                  | <b>5</b>  | <b>12 Device and Documentation Support</b> .....                 | <b>26</b> |
| 7.5 3V Electrical Characteristics .....        | <b>6</b>  | 12.1 Related Links .....   | <b>26</b> |
| 7.6 5V Electrical Characteristics .....        | <b>8</b>  | 12.2 Trademarks .....  | <b>26</b> |
| 7.7 $\pm 5V$ Electrical Characteristics .....  | <b>10</b> | 12.3 Electrostatic Discharge Caution.....                        | <b>26</b> |
| 7.8 Typical Performance Characteristics .....  | <b>12</b> | 12.4 Glossary .....  | <b>26</b> |
| <b>8 Detailed Description</b> .....            | <b>21</b> | <b>13 Mechanical, Packaging, and Orderable Information</b> ..... | <b>26</b> |
| 8.1 Overview .....                             | <b>21</b> |  |           |

## 4 Revision History

NOTE: Page numbers for previous revisions may differ from page numbers in the current version.

| <b>Changes from Revision P (March 2013) to Revision Q</b>  | <b>Page</b> |
|--|-------------|
| • Added, revised, or updated the following sections: Device Information Table, Application and Implementation; Power Supply Recommendations; Device and Documentation Support; Mechanical, Packaging, and Ordering Information ..... | <b>1</b>    |
| • Changed "Junction Temperature Range" to "Operating Temperature Range" .....  | <b>5</b>    |
| • Deleted $T_J = 25^\circ\text{C}$ for Electrical Characteristics tables. ....   | <b>6</b>    |
| • Changed from " $R_L$ " to " $R_f$ " .....  | <b>6</b>    |
| • Deleted $T_J = 25^\circ\text{C}$ for Typical Performance Characteristics .....   | <b>12</b>   |





| <b>Changes from Revision O (March 2013) to Revision P</b>  | <b>Page</b> |
|--|-------------|
| • Changed layout of National Data Sheet to TI format ..... | <b>1</b>    |

## 5 Description (continued)

Careful attention has been paid to ensure device stability under all operating voltages and modes. The result is a very well behaved frequency response characteristic (0.1dB gain flatness up the 12 MHz under 150  $\Omega$  load and  $A_V = +2$ ) with minimal peaking (typically 2dB maximum) for any gain setting and under both heavy and light loads. This along with fast settling time (68ns) and low distortion allows the device to operate well in an ADC buffer as well as high frequency filter applications.

This device family offers professional quality video performance with low DG (0.01%) and DP (0.01°) characteristics. Differential Gain and Differential Phase characteristics are also well maintained under heavy loads (150  $\Omega$ ) and throughout the output voltage range. The LMH664X family is offered in single (LMH6642), dual (LMH6643), and quad (LMH6644) options.

## 6 Pin Configuration and Functions



### Pin Functions

| NAME   | PIN     |       |         |                | I/O | DESCRIPTION             |
|--------|---------|-------|---------|----------------|-----|-------------------------|
|        | LMH6642 |       | LMH6643 | LMH6644        |     |                         |
|        | DBV05A  | D08A  | DGK08A  | D14A and PW14A |     |                         |
| -IN    | 4       | 2     |         |                | I   | Inverting Input         |
| +IN    | 3       | 3     |         |                | I   | Non-inverting Input     |
| -IN A  |         |       | 2       | 2              | I   | ChA Inverting Input     |
| +IN A  |         |       | 3       | 3              | I   | ChA Non-inverting Input |
| -IN B  |         |       | 6       | 6              | I   | ChB Inverting Input     |
| +IN B  |         |       | 5       | 5              | I   | ChB Non-inverting Input |
| -IN C  |         |       |         | 9              | I   | ChC Inverting Input     |
| +IN C  |         |       |         | 10             | I   | ChC Non-inverting Input |
| -IN D  |         |       |         | 13             | I   | ChD Inverting Input     |
| +IN D  |         |       |         | 12             | I   | ChD Non-inverting Input |
| N/C    |         | 1,5,8 |         |                | —   | No connection           |
| OUT A  |         |       | 1       | 1              | O   | ChA Output              |
| OUT B  |         |       | 7       | 7              | O   | ChB Output              |
| OUT C  |         |       |         | 8              | O   | ChC Output              |
| OUT D  |         |       |         | 14             | O   | ChD Output              |
| OUTPUT | 1       | 6     |         |                | O   | Output                  |
| V-     | 2       | 4     | 4       | 11             | I   | Negative Supply         |
| V+     | 5       | 7     | 8       | 4              | I   | Positive Supply         |

## 7 Specifications

### 7.1 Absolute Maximum Ratings<sup>(1)(2)</sup>

over operating free-air temperature range (unless otherwise noted)

|   |  | MIN                                   | MAX  | UNIT |
|---|--|---------------------------------------|--|------|
| V <sub>IN</sub> Differential                      |  |                                       | ±2.5                                       | V    |
| Output Short Circuit Duration                     |  | See <sup>(3)</sup> and <sup>(4)</sup> |  |      |
| Supply Voltage (V <sup>+</sup> - V <sup>-</sup> ) |  |                                       | 13.5                                       | V    |
| Voltage at Input/Output pins                      |  |                                       | V <sup>+</sup> +0.8<br>V <sup>-</sup> -0.8 | V    |
| Input Current                                     |  |                                       | ±10  | mA   |
| Junction Temperature <sup>(5)</sup>               |  |                                       | +150                                       | °C   |
| Soldering Information                             | Infrared or Convection Reflow (20 sec) |                                       | 235  | °C   |
|   | Wave Soldering Lead Temp.(10 sec)      |                                       | 260  | °C   |

- (1) Absolute Maximum Ratings indicate limits beyond which damage to the device may occur. Operating Ratings indicate conditions for which the device is intended to be functional, but specific performance is not ensured. For ensured specifications and the test conditions, see the Electrical Characteristics.
- (2) If Military/Aerospace specified devices are required, please contact the TI Sales Office/Distributors for availability and specifications.
- (3) Applies to both single-supply and split-supply operation. Continuous short circuit operation at elevated ambient temperature can result in exceeding the maximum allowed junction temperature of 150°C.
- (4) Output short circuit duration is infinite for V<sub>S</sub> < 6V at room temperature and below. For V<sub>S</sub> > 6V, allowable short circuit duration is 1.5ms.
- (5) The maximum power dissipation is a function of T<sub>J(MAX)</sub>, R<sub>θJA</sub>, and T<sub>A</sub>. The maximum allowable power dissipation at any ambient temperature is P<sub>D</sub> = (T<sub>J(MAX)</sub> - T<sub>A</sub>) / R<sub>θJA</sub>. All numbers apply for packages soldered directly onto a PC board.

### 7.2 Handling Ratings

|                    |  | MIN  | MAX  | UNIT |
|--------------------|--|--|------|------|
| T <sub>stg</sub>   | Storage temperature range              | -65  | +150 | °C   |
| V <sub>(ESD)</sub> | Electrostatic discharge <sup>(1)</sup> | Human body model (HBM), per ANSI/ESDA/JEDEC JS-001, all pins <sup>(2)</sup>              | 2000 | V    |
|                    |  | Machine model (MM) <sup>(3)</sup>  | 200  |      |
|                    |  | Charged device model (CDM), per JEDEC specification JESD22-C101, all pins <sup>(4)</sup> | 1000 |      |

- (1) Human body model, 1.5 kΩ in series with 100 pF. Machine Model, 0 Ω in series with 200 pF.
- (2) JEDEC document JEP155 states that 2000-V HBM allows safe manufacturing with a standard ESD control process.
- (3) JEDEC document JEP157 states that 200-V MM allows safe manufacturing with a standard ESD control process.
- (4) JEDEC document JEP157 states that 1000-V CDM allows safe manufacturing with a standard ESD control process.

### 7.3 Recommended Operating Conditions<sup>(1)</sup>

over operating free-air temperature range (unless otherwise noted)

|   |  | MIN | MAX  | UNIT |
|---|--|-----|------|------|
| Supply Voltage (V <sup>+</sup> - V <sup>-</sup> ) |  | 2.7 | 12.8 | V    |
| Operating Temperature Range <sup>(2)</sup>        |  | -40 | +85  | °C   |

- (1) Absolute Maximum Ratings indicate limits beyond which damage to the device may occur. Operating Ratings indicate conditions for which the device is intended to be functional, but specific performance is not ensured. For ensured specifications and the test conditions, see the Electrical Characteristics.
- (2) The maximum power dissipation is a function of T<sub>J(MAX)</sub>, R<sub>θJA</sub>, and T<sub>A</sub>. The maximum allowable power dissipation at any ambient temperature is P<sub>D</sub> = (T<sub>J(MAX)</sub> - T<sub>A</sub>) / R<sub>θJA</sub>. All numbers apply for packages soldered directly onto a PC board.

### 7.4 Thermal Information

| THERMAL METRIC <sup>(1)</sup> |   | LMH6642 |        | LMH6643 | LMH6644 |         | UNIT |
|-------------------------------|---|---------|--------|---------|---------|---------|------|
|                               |   | DBV05A  | D08A   | DGK08A  | D14A    | PW14A   |      |
|                               |   | 5 PINS  | 8 PINS | 8 PINS  | 14 PINS | 14 PINS |      |
| R <sub>θJA</sub>              | Junction-to-ambient Thermal Resistance <sup>(2)</sup> | 265     | 190    | 235     | 145     | 155     | °C/W |

- (1) For more information about traditional and new thermal metrics, see the *IC Package Thermal Metrics* application report, [SPRA953](#).
- (2) The maximum power dissipation is a function of T<sub>J(MAX)</sub>, R<sub>θJA</sub>, and T<sub>A</sub>. The maximum allowable power dissipation at any ambient temperature is P<sub>D</sub> = (T<sub>J(MAX)</sub> - T<sub>A</sub>) / R<sub>θJA</sub>. All numbers apply for packages soldered directly onto a PC board.

## 7.5 3V Electrical Characteristics

Unless otherwise specified, all limits ensured for  $V^+ = 3V$ ,  $V^- = 0V$ ,  $V_{CM} = V_O = V^+/2$ ,  $V_{ID}$  (input differential voltage) as noted (where applicable) and  $R_L = 2k\Omega$  to  $V^+/2$ .

| PARAMETER    | TEST CONDITIONS              | AT TEMPERATURE EXTREMES   |     |     | $V^+ = 3V$ , $V^- = 0V$ ,<br>$V_{CM} = V_O = V^+/2$ , $V_{ID}$<br>$R_L = 2k\Omega$ to $V^+/2$ |                    |                    | UNIT             |
|--------------|------------------------------|---|-----|-----|---|--------------------|--------------------|------------------|
|              |                              | MIN   | TYP | MAX | MIN <sup>(1)</sup>  | TYP <sup>(2)</sup> | MAX <sup>(1)</sup> |                  |
| BW           | -3dB BW                      | $A_V = +1$ , $V_{OUT} = 200mV_{PP}$   |     |     | 80  | 115                |                    | MHz              |
|              |                              | $A_V = +2$ , $-1$ , $V_{OUT} = 200mV_{PP}$  |     |     |   | 46                 |                    |                  |
| $BW_{0.1dB}$ | 0.1dB Gain Flatness          | $A_V = +2$ , $R_L = 150\Omega$ to $V^+/2$ ,<br>$R_f = 402\Omega$ , $V_{OUT} = 200mV_{PP}$ |     |     |   | 19                 |                    | MHz              |
| PBW          | Full Power Bandwidth         | $A_V = +1$ , $-1dB$ , $V_{OUT} = 1V_{PP}$   |     |     |   | 40                 |                    | MHz              |
| $e_n$        | Input-Referred Voltage Noise | $f = 100kHz$  |     |     |   | 17                 |                    | $nV/\sqrt{Hz}$   |
|              |                              | $f = 1kHz$  |     |     |   | 48                 |                    |                  |
| $i_n$        | Input-Referred Current Noise | $f = 100kHz$  |     |     |   | 0.90               |                    | $pA/\sqrt{Hz}$   |
|              |                              | $f = 1kHz$  |     |     |   | 3.3                |                    |                  |
| THD          | Total Harmonic Distortion    | $f = 5MHz$ , $V_O = 2V_{PP}$ , $A_V = -1$ ,<br>$R_L = 100\Omega$ to $V^+/2$               |     |     |   | -48                |                    | dBc              |
| DG           | Differential Gain            | $V_{CM} = 1V$ , NTSC, $A_V = +2$<br>$R_L = 150\Omega$ to $V^+/2$                          |     |     |   | 0.17%              |                    |                  |
|              |                              | $R_L = 1k\Omega$ to $V^+/2$   |     |     |   | 0.03%              |                    |                  |
| DP           | Differential Phase           | $V_{CM} = 1V$ , NTSC, $A_V = +2$<br>$R_L = 150\Omega$ to $V^+/2$                          |     |     |   | 0.05               |                    | deg              |
|              |                              | $R_L = 1k\Omega$ to $V^+/2$   |     |     |   | 0.03               |                    |                  |
| CT Rej.      | Cross-Talk Rejection         | $f = 5MHz$ , Receiver:<br>$R_f = R_g = 510\Omega$ , $A_V = +2$                            |     |     |   | 47                 |                    | dB               |
| $T_S$        | Settling Time                | $V_O = 2V_{PP}$ , $\pm 0.1\%$ , 8pF Load,<br>$V_S = 5V$                                   |     |     |   | 68                 |                    | ns               |
| SR           | Slew Rate <sup>(3)</sup>     | $A_V = -1$ , $V_I = 2V_{PP}$  |     |     | 90  | 120                |                    | $V/\mu s$        |
| $V_{OS}$     | Input Offset Voltage         | For LMH6642 and LMH6644   |     |     |   | $\pm 7$            | $\pm 1$ $\pm 5$    | mV               |
|              |                              | For LMH6643   |     |     |   | $\pm 7$            | $\pm 1$ $\pm 3.4$  |                  |
| TC $V_{OS}$  | Input Offset Average Drift   | See <sup>(4)</sup>  |     |     |   | $\pm 5$            |                    | $\mu V/^\circ C$ |
| $I_B$        | Input Bias Current           | See <sup>(5)</sup>  |     |     | -3.25   | -1.50              | -2.60              | $\mu A$          |
| $I_{OS}$     | Input Offset Current         |   |     |     | 1000  | 20                 | 800                | nA               |
| $R_{IN}$     | Common Mode Input Resistance |   |     |     |   | 3                  |                    | M $\Omega$       |

(1) All limits are ensured by testing or statistical analysis.

(2) Typical values represent the most likely parametric norm.

(3) Slew rate is the average of the rising and falling slew rates.

(4) Offset voltage average drift determined by dividing the change in  $V_{OS}$  at temperature extremes by the total temperature change.

(5) Positive current corresponds to current flowing into the device.

### 3V Electrical Characteristics (continued)

Unless otherwise specified, all limits ensured for  $V^+ = 3V$ ,  $V^- = 0V$ ,  $V_{CM} = V_O = V^+/2$ ,  $V_{ID}$  (input differential voltage) as noted (where applicable) and  $R_L = 2k\Omega$  to  $V^+/2$ .

| PARAMETER | TEST CONDITIONS                       | AT TEMPERATURE EXTREMES                                |     |      | $V^+ = 3V$ , $V^- = 0V$ ,<br>$V_{CM} = V_O = V^+/2$ , $V_{ID}$<br>$R_L = 2k\Omega$ to $V^+/2$ |                    |                    | UNIT |
|-----------|---------------------------------------|--|-----|------|---|--------------------|--------------------|------|
|           |                                       | MIN  | TYP | MAX  | MIN <sup>(1)</sup>  | TYP <sup>(2)</sup> | MAX <sup>(1)</sup> |      |
| $C_{IN}$  | Common Mode Input Capacitance         |  |     |      |   | 2                  |                    | pF   |
| CMVR      | Input Common-Mode Voltage Range       | CMRR $\geq$ 50dB                                       |     | -0.1 |   | -0.5               | -0.2               | V    |
| CMRR      | Common Mode Rejection Ratio           | $V_{CM}$ Stepped from 0V to 1.5V                       |     |      |   | 72                 | 95                 | dB   |
| $A_{VOL}$ | Large Signal Voltage Gain             | $V_O = 0.5V$ to $2.5V$<br>$R_L = 2k\Omega$ to $V^+/2$  |     | 75   |   | 80                 | 96                 | dB   |
|           |                                       | $V_O = 0.5V$ to $2.5V$<br>$R_L = 150\Omega$ to $V^+/2$ |     | 70   |   | 74                 | 82                 |      |
| $V_O$     | Output Swing High                     | $R_L = 2k\Omega$ to $V^+/2$ , $V_{ID} = 200mV$         |     |      |   | 2.90               | 2.98               | V    |
|           |                                       | $R_L = 150\Omega$ to $V^+/2$ , $V_{ID} = 200mV$        |     |      |   | 2.80               | 2.93               |      |
| $V_O$     | Output Swing Low                      | $R_L = 2k\Omega$ to $V^+/2$ , $V_{ID} = -200mV$        |     |      |   |                    | 25                 | 75   |
|           |                                       | $R_L = 150\Omega$ to $V^+/2$ , $V_{ID} = -200mV$       |     |      |   |                    | 75                 | 150  |
| $I_{SC}$  | Output Short Circuit Current          | Sourcing to $V^+/2$<br>$V_{ID} = 200mV$ <sup>(6)</sup> |     | 35   |   | 50                 | 95                 | mA   |
|           |                                       | Sinking to $V^+/2$<br>$V_{ID} = -200mV$ <sup>(6)</sup> |     | 40   |   | 55                 | 110                |      |
| $I_{OUT}$ | Output Current                        | $V_{OUT} = 0.5V$ from either supply                    |     |      |   |                    | $\pm 65$           | mA   |
| +PSRR     | Positive Power Supply Rejection Ratio | $V^+ = 3.0V$ to $3.5V$ , $V_{CM} = 1.5V$               |     |      |   | 75                 | 85                 | dB   |
| $I_S$     | Supply Current (per channel)          | No Load  |     |      | 4.50  |                    | 2.70               | 4.00 |

(6) Short circuit test is a momentary test. See [Note 7](#) under 5 V Electrical Characteristics.

## 7.6 5V Electrical Characteristics

Unless otherwise specified, all limits ensured for  $V^+ = 5V$ ,  $V^- = 0V$ ,  $V_{CM} = V_O = V^+/2$ ,  $V_{ID}$  (input differential voltage) as noted (where applicable) and  $R_L = 2k\Omega$  to  $V^+/2$ .

| PARAMETER    | TEST CONDITIONS                 | AT TEMPERATURE EXTREMES  |     |     | $V^+ = 5V, V^- = 0V,$<br>$V_{CM} = V_O = V^+/2, V_{ID}$<br>$R_L = 2k\Omega$ to $V^+/2$ |                    |                    | UNIT             |
|--------------|---------------------------------|--|-----|-----|--|--------------------|--------------------|------------------|
|              |                                 | MIN  | TYP | MAX | MIN <sup>(1)</sup>   | TYP <sup>(2)</sup> | MAX <sup>(1)</sup> |                  |
| BW           | –3dB BW                         | $A_V = +1, V_{OUT} = 200mV_{PP}$   |     |     | 90   | 120                |                    | MHz              |
|              |                                 | $A_V = +2, -1, V_{OUT} = 200mV_{PP}$   |     |     |  | 46                 |                    |                  |
| $BW_{0.1dB}$ | 0.1dB Gain Flatness             | $A_V = +2, R_L = 150\Omega$ to $V^+/2,$<br>$R_f = 402\Omega, V_{OUT} = 200mV_{PP}$ |     |     |  | 15                 |                    | MHz              |
| PBW          | Full Power Bandwidth            | $A_V = +1, -1dB, V_{OUT} = 2V_{PP}$  |     |     |  | 22                 |                    | MHz              |
| $e_n$        | Input-Referred Voltage Noise    | $f = 100kHz$   |     |     |  | 17                 |                    | $nV/\sqrt{Hz}$   |
|              |                                 | $f = 1kHz$   |     |     |  | 48                 |                    |                  |
| $i_n$        | Input-Referred Current Noise    | $f = 100kHz$   |     |     |  | 0.90               |                    | $pA/\sqrt{Hz}$   |
|              |                                 | $f = 1kHz$   |     |     |  | 3.3                |                    |                  |
| THD          | Total Harmonic Distortion       | $f = 5MHz, V_O = 2V_{PP}, A_V = +2$  |     |     |  | –60                |                    | dBc              |
| DG           | Differential Gain               | NTSC, $A_V = +2$<br>$R_L = 150\Omega$ to $V^+/2$                                   |     |     |  | 0.16%              |                    |                  |
|              |                                 | $R_L = 1k\Omega$ to $V^+/2$  |     |     |  | 0.05%              |                    |                  |
| DP           | Differential Phase              | NTSC, $A_V = +2$<br>$R_L = 150\Omega$ to $V^+/2$                                   |     |     |  | 0.05               |                    | deg              |
|              |                                 | $R_L = 1k\Omega$ to $V^+/2$  |     |     |  | 0.01               |                    |                  |
| CT Rej.      | Cross-Talk Rejection            | $f = 5MHz, \text{Receiver:}$<br>$R_f = R_g = 510\Omega, A_V = +2$                  |     |     |  | 47                 |                    | dB               |
| $T_S$        | Settling Time                   | $V_O = 2V_{PP}, \pm 0.1\%, 8pF$ Load   |     |     |  | 68                 |                    | ns               |
| SR           | Slew Rate <sup>(3)</sup>        | $A_V = -1, V_I = 2V_{PP}$  |     |     | 95   | 125                |                    | $V/\mu s$        |
| $V_{OS}$     | Input Offset Voltage            | For LMH6642 and LMH6644  |     |     | $\pm 7$  | $\pm 1$            | $\pm 5$            | mV               |
|              |                                 | For LMH6643  |     |     | $\pm 7$  | $\pm 1$            | $\pm 3.4$          |                  |
| TC $V_{OS}$  | Input Offset Average Drift      | See <sup>(4)</sup>   |     |     |  | $\pm 5$            |                    | $\mu V/^\circ C$ |
| $I_B$        | Input Bias Current              | See <sup>(5)</sup>   |     |     | –3.25  | –1.70              | –2.60              | $\mu A$          |
| $I_{OS}$     | Input Offset Current            |  |     |     | 1000   | 20                 | 800                | nA               |
| $R_{IN}$     | Common Mode Input Resistance    |  |     |     |  | 3                  |                    | M $\Omega$       |
| $C_{IN}$     | Common Mode Input Capacitance   |  |     |     |  | 2                  |                    | pF               |
| CMVR         | Input Common-Mode Voltage Range | CMRR $\geq 50dB$   |     |     | –0.1   | –0.5               | –0.2               | V                |
|              |                                 |  |     |     | 3.6  | 3.8                | 4.0                |                  |
| CMRR         | Common Mode Rejection Ratio     | $V_{CM}$ Stepped from 0V to 3.5V   |     |     |  | 72                 | 95                 | dB               |
| $A_{VOL}$    | Large Signal Voltage Gain       | $V_O = 0.5V$ to $4.50V$<br>$R_L = 2k\Omega$ to $V^+/2$                             |     |     | 82   | 86                 | 98                 | dB               |
|              |                                 | $V_O = 0.5V$ to $4.25V$<br>$R_L = 150\Omega$ to $V^+/2$                            |     |     | 72   | 76                 | 82                 |                  |

(1) All limits are ensured by testing or statistical analysis.

(2) Typical values represent the most likely parametric norm.

(3) Slew rate is the average of the rising and falling slew rates.

(4) Offset voltage average drift determined by dividing the change in  $V_{OS}$  at temperature extremes by the total temperature change.

(5) Positive current corresponds to current flowing into the device.

### 5V Electrical Characteristics (continued)

Unless otherwise specified, all limits ensured for  $V^+ = 5V$ ,  $V^- = 0V$ ,  $V_{CM} = V_O = V^+/2$ ,  $V_{ID}$  (input differential voltage) as noted (where applicable) and  $R_L = 2k\Omega$  to  $V^+/2$ .

| PARAMETER | TEST CONDITIONS                       | AT TEMPERATURE EXTREMES                                   |     |     | $V^+ = 5V$ , $V^- = 0V$ ,<br>$V_{CM} = V_O = V^+/2$ , $V_{ID}$<br>$R_L = 2k\Omega$ to $V^+/2$ |                    |                    | UNIT |    |
|-----------|---------------------------------------|---|-----|-----|---|--------------------|--------------------|------|----|
|           |                                       | MIN   | TYP | MAX | MIN <sup>(1)</sup>  | TYP <sup>(2)</sup> | MAX <sup>(1)</sup> |      |    |
| $V_O$     | Output Swing High                     | $R_L = 2k\Omega$ to $V^+/2$ , $V_{ID} = 200mV$            |     |     |   | 4.90               | 4.98               | V    |    |
|           |                                       | $R_L = 150\Omega$ to $V^+/2$ , $V_{ID} = 200mV$           |     |     |   | 4.65               | 4.90               |      |    |
|           | Output Swing Low                      | $R_L = 2k\Omega$ to $V^+/2$ , $V_{ID} = -200mV$           |     |     |   |                    | 25                 | 100  | mV |
|           |                                       | $R_L = 150\Omega$ to $V^+/2$ , $V_{ID} = -200mV$          |     |     |   |                    | 100                | 150  |    |
| $I_{SC}$  | Output Short Circuit Current          | Sourcing to $V^+/2$<br>$V_{ID} = 200mV$ <sup>(6)(7)</sup> | 40  |     |   | 55                 | 115                | mA   |    |
|           |                                       | Sinking to $V^+/2$<br>$V_{ID} = -200mV$ <sup>(6)(7)</sup> | 55  |     |   | 70                 | 140                |      |    |
| $I_{OUT}$ | Output Current                        | $V_O = 0.5V$ from either supply                           |     |     |   | $\pm 70$           |                    | mA   |    |
| +PSRR     | Positive Power Supply Rejection Ratio | $V^+ = 4.0V$ to $6V$                                      |     |     |   | 79                 | 90                 | dB   |    |
| $I_S$     | Supply Current (per channel)          | No Load   |     |     | 5.00  |                    | 2.70               | 4.25 | mA |

(6) Short circuit test is a momentary test. See [Note 7](#).

(7) Output short circuit duration is infinite for  $V_S < 6V$  at room temperature and below. For  $V_S > 6V$ , allowable short circuit duration is 1.5ms.

## 7.7 ±5V Electrical Characteristics

Unless otherwise specified, all limits ensured for  $V^+ = 5V$ ,  $V^- = -5V$ ,  $V_{CM} = V_O = 0V$ ,  $V_{ID}$  (input differential voltage) as noted (where applicable) and  $R_L = 2k\Omega$  to ground.

| PARAMETER    | TEST CONDITIONS                 | AT TEMPERATURE EXTREMES   |     |     | $V^+ = 5V$ , $V^- = -5V$ ,<br>$V_{CM} = V_O = 0V$ , $V_{ID}$ |                    |                    | UNIT             |
|--------------|---------------------------------|---|-----|-----|--|--------------------|--------------------|------------------|
|              |                                 | MIN   | TYP | MAX | MIN <sup>(1)</sup>   | TYP <sup>(2)</sup> | MAX <sup>(1)</sup> |                  |
| BW           | -3dB BW                         | $A_V = +1$ , $V_{OUT} = 200mV_{PP}$   |     |     | 95   | 130                |                    | MHz              |
|              |                                 | $A_V = +2$ , $-1$ , $V_{OUT} = 200mV_{PP}$  |     |     |  | 46                 |                    |                  |
| $BW_{0.1dB}$ | 0.1dB Gain Flatness             | $A_V = +2$ , $R_L = 150\Omega$ to $V^+/2$ ,<br>$R_f = 806\Omega$ , $V_{OUT} = 200mV_{PP}$ |     |     |  | 12                 |                    | MHz              |
| PBW          | Full Power Bandwidth            | $A_V = +1$ , $-1dB$ , $V_{OUT} = 2V_{PP}$   |     |     |  | 24                 |                    | MHz              |
| $e_n$        | Input-Referred Voltage Noise    | $f = 100kHz$  |     |     |  | 17                 |                    | $nV/\sqrt{Hz}$   |
|              |                                 | $f = 1kHz$  |     |     |  | 48                 |                    |                  |
| $i_n$        | Input-Referred Current Noise    | $f = 100kHz$  |     |     |  | 0.90               |                    | $pA/\sqrt{Hz}$   |
|              |                                 | $f = 1kHz$  |     |     |  | 3.3                |                    |                  |
| THD          | Total Harmonic Distortion       | $f = 5MHz$ , $V_O = 2V_{PP}$ , $A_V = +2$   |     |     |  | -62                |                    | dBc              |
| DG           | Differential Gain               | NTSC, $A_V = +2$<br>$R_L = 150\Omega$ to $V^+/2$  |     |     |  | 0.15%              |                    |                  |
|              |                                 | $R_L = 1k\Omega$ to $V^+/2$   |     |     |  | 0.01%              |                    |                  |
| DP           | Differential Phase              | NTSC, $A_V = +2$<br>$R_L = 150\Omega$ to $V^+/2$  |     |     |  | 0.04               |                    | deg              |
|              |                                 | $R_L = 1k\Omega$ to $V^+/2$   |     |     |  | 0.01               |                    |                  |
| CT Rej.      | Cross-Talk Rejection            | $f = 5MHz$ , Receiver:<br>$R_f = R_g = 510\Omega$ , $A_V = +2$                            |     |     |  | 47                 |                    | dB               |
| $T_S$        | Settling Time                   | $V_O = 2V_{PP}$ , $\pm 0.1\%$ , 8pF Load,<br>$V_S = 5V$                                   |     |     |  | 68                 |                    | ns               |
| SR           | Slew Rate <sup>(3)</sup>        | $A_V = -1$ , $V_I = 2V_{PP}$  |     |     | 100  | 135                |                    | V/ $\mu s$       |
| $V_{OS}$     | Input Offset Voltage            | For LMH6642 and LMH6644   |     |     | $\pm 7$  | $\pm 1$            | $\pm 5$            | mV               |
|              |                                 | For LMH6643   |     |     | $\pm 7$  | $\pm 1$            | $\pm 3.4$          |                  |
| TC $V_{OS}$  | Input Offset Average Drift      | See <sup>(4)</sup>  |     |     |  | $\pm 5$            |                    | $\mu V/^\circ C$ |
| $I_B$        | Input Bias Current              | See <sup>(5)</sup>  |     |     | -3.25  | -1.60              | -2.60              | $\mu A$          |
| $I_{OS}$     | Input Offset Current            |   |     |     | 1000   | 20                 | 800                | nA               |
| $R_{IN}$     | Common Mode Input Resistance    |   |     |     |  | 3                  |                    | M $\Omega$       |
| $C_{IN}$     | Common Mode Input Capacitance   |   |     |     |  | 2                  |                    | pF               |
| CMVR         | Input Common-Mode Voltage Range | CMRR $\geq 50dB$  |     |     | -5.1   | -5.5               | -5.2               | V                |
|              |                                 |   |     |     | 3.6  | 3.8                | 4.0                |                  |
| CMRR         | Common Mode Rejection Ratio     | $V_{CM}$ Stepped from $-5V$ to $3.5V$   |     |     |  | 74                 | 95                 | dB               |

- (1) All limits are ensured by testing or statistical analysis.
- (2) Typical values represent the most likely parametric norm.
- (3) Slew rate is the average of the rising and falling slew rates.
- (4) Offset voltage average drift determined by dividing the change in  $V_{OS}$  at temperature extremes by the total temperature change.
- (5) Positive current corresponds to current flowing into the device.

### ±5V Electrical Characteristics (continued)

Unless otherwise specified, all limits ensured for  $V^+ = 5V$ ,  $V^- = -5V$ ,  $V_{CM} = V_O = 0V$ ,  $V_{ID}$  (input differential voltage) as noted (where applicable) and  $R_L = 2k\Omega$  to ground.

| PARAMETER | TEST CONDITIONS              | AT TEMPERATURE EXTREMES                                  |     |     | $V^+ = 5V$ , $V^- = -5V$ ,<br>$V_{CM} = V_O = 0V$ , $V_{ID}$ |                    |                    | UNIT |
|-----------|------------------------------|--|-----|-----|--|--------------------|--------------------|------|
|           |                              | MIN  | TYP | MAX | MIN <sup>(1)</sup>   | TYP <sup>(2)</sup> | MAX <sup>(1)</sup> |      |
| $A_{VOL}$ | Large Signal Voltage Gain    | $V_O = -4.5V$ to $4.5V$ ,<br>$R_L = 2k\Omega$            | 84  |     |  | 88                 | 96                 | dB   |
|           |                              | $V_O = -4.0V$ to $4.0V$ ,<br>$R_L = 150\Omega$           | 74  |     |  | 78                 | 82                 |      |
| $V_O$     | Output Swing High            | $R_L = 2k\Omega$ , $V_{ID} = 200mV$                      |     |     |  | 4.90               | 4.96               | V    |
|           |                              | $R_L = 150\Omega$ , $V_{ID} = 200mV$                     |     |     |  | 4.65               | 4.80               |      |
|           | Output Swing Low             | $R_L = 2k\Omega$ , $V_{ID} = -200mV$                     |     |     |  | -4.96              | -4.90              | V    |
|           |                              | $R_L = 150\Omega$ , $V_{ID} = -200mV$                    |     |     |  | -4.80              | -4.65              |      |
| $I_{SC}$  | Output Short Circuit Current | Sourcing to Ground<br>$V_{ID} = 200mV$ <sup>(6)(7)</sup> | 35  |     |  | 60                 | 115                | mA   |
|           |                              | Sinking to Ground<br>$V_{ID} = -200mV$ <sup>(6)(7)</sup> | 65  |     |  | 85                 | 145                |      |
| $I_{OUT}$ | Output Current               | $V_O = 0.5V$ from either supply                          |     |     |  | ±75                |                    | mA   |
| PSRR      | Power Supply Rejection Ratio | $(V^+, V^-) = (4.5V, -4.5V)$ to $(5.5V, -5.5V)$          |     |     |  | 78                 | 90                 | dB   |
| $I_S$     | Supply Current (per channel) | No Load  |     |     | 5.50   | 2.70               | 4.50               | mA   |

(6) Short circuit test is a momentary test. See <sup>(7)</sup>.

(7) Output short circuit duration is infinite for  $V_S < 6V$  at room temperature and below. For  $V_S > 6V$ , allowable short circuit duration is 1.5ms.

## 7.8 Typical Performance Characteristics

$V^+ = +5V$ ,  $V^- = -5V$ ,  $R_F = R_L = 2\text{ k}\Omega$ . Unless otherwise specified.




Figure 1. Closed Loop Frequency Response for Various Supplies




Figure 2. Closed Loop Gain vs. Frequency for Various Gain




Figure 3. Closed Loop Gain vs. Frequency for Various Gain




Figure 4. Closed Loop Frequency Response for Various Temperature




Figure 5. Closed Loop Gain vs. Frequency for Various Supplies




Figure 6. Closed Loop Frequency Response for Various Temperature

Typical Performance Characteristics (continued)

$V^+ = +5V$ ,  $V^- = -5V$ ,  $R_F = R_L = 2\text{ k}\Omega$ . Unless otherwise specified.




Figure 7. Large Signal Frequency Response




Figure 8. Closed Loop Small Signal Frequency Response for Various Supplies




Figure 9. Closed Loop Frequency Response for Various Supplies




Figure 10.  $\pm 0.1\text{dB}$  Gain Flatness for Various Supplies




Figure 11.  $V_{\text{OUT}}$  ( $V_{\text{PP}}$ ) for THD < 0.5%




Figure 12.  $V_{\text{OUT}}$  ( $V_{\text{PP}}$ ) for THD < 0.5%

Typical Performance Characteristics (continued)

$V^+ = +5V$ ,  $V^- = -5V$ ,  $R_F = R_L = 2\text{ k}\Omega$ . Unless otherwise specified.




Figure 13.  $V_{OUT}$  ( $V_{PP}$ ) for THD < 0.5%




Figure 14. Open Loop Gain/Phase for Various Temperature




Figure 15. Open Loop Gain/Phase for Various Temperature




Figure 16. HD2 (dBc) vs. Output Swing




Figure 17. HD3 (dBc) vs. Output Swing




Figure 18. HD2 vs. Output Swing

Typical Performance Characteristics (continued)

$V^+ = +5V$ ,  $V^- = -5V$ ,  $R_F = R_L = 2\text{ k}\Omega$ . Unless otherwise specified.




Figure 19. HD3 vs. Output Swing




Figure 20. THD (dBc) vs. Output Swing




Figure 21. Settling Time vs. Input Step Amplitude (Output Slew and Settle Time)




Figure 22. Input Noise vs. Frequency




Figure 23.  $V_{OUT}$  from  $V^+$  vs.  $I_{SOURCE}$




Figure 24.  $V_{OUT}$  from  $V^-$  vs.  $I_{SINK}$

Typical Performance Characteristics (continued)

$V^+ = +5V$ ,  $V^- = -5V$ ,  $R_F = R_L = 2\text{ k}\Omega$ . Unless otherwise specified.




Figure 25.  $V_{OUT}$  from  $V^+$  vs.  $I_{SOURCE}$




Figure 26.  $V_{OUT}$  from  $V^-$  vs.  $I_{SINK}$




Figure 27. Swing vs.  $V_S$




Figure 28. Short Circuit Current (to  $V_S/2$ ) vs.  $V_S$




Figure 29. Output Sinking Saturation Voltage vs.  $I_{OUT}$




Figure 30. Output Sourcing Saturation Voltage vs.  $I_{OUT}$

Typical Performance Characteristics (continued)

$V^+ = +5V$ ,  $V^- = -5V$ ,  $R_F = R_L = 2\text{ k}\Omega$ . Unless otherwise specified.




Figure 31. Closed Loop Output Impedance vs. Frequency  $A_V = +1$




Figure 32. PSRR vs. Frequency




Figure 33. CMRR vs. Frequency




Figure 34. Crosstalk Rejection vs. Frequency (Output to Output)




Figure 35.  $V_{OS}$  vs.  $V_{OUT}$  (Typical Unit)










Figure 36.  $V_{OS}$  vs.  $V_{CM}$  (Typical Unit)

**Typical Performance Characteristics (continued)**
 $V^+ = +5V$ ,  $V^- = -5V$ ,  $R_F = R_L = 2\text{ k}\Omega$ . Unless otherwise specified.

**Figure 37.  $V_{OS}$  vs.  $V_S$  (for 3 Representative Units)**

**Figure 38.  $V_{OS}$  vs.  $V_S$  (for 3 Representative Units)**

**Figure 39.  $V_{OS}$  vs.  $V_S$  (for 3 Representative Units)**

**Figure 40.  $I_B$  vs.  $V_S$** 

**Figure 41.  $I_{OS}$  vs.  $V_S$** 

**Figure 42.  $I_S$  vs.  $V_{CM}$**

Typical Performance Characteristics (continued)

$V^+ = +5V$ ,  $V^- = -5V$ ,  $R_F = R_L = 2\text{ k}\Omega$ . Unless otherwise specified.




Figure 43.  $I_S$  vs.  $V_S$




Figure 44. Small Signal Step Response




Figure 45. Large Signal Step Response




Figure 46. Large Signal Step Response




Figure 47. Small Signal Step Response




Figure 48. Small Signal Step Response

Typical Performance Characteristics (continued)

$V^+ = +5V$ ,  $V^- = -5V$ ,  $R_F = R_L = 2\text{ k}\Omega$ . Unless otherwise specified.




Figure 49. Small Signal Step Response




Figure 50. Small Signal Step Response




Figure 51. Large Signal Step Response




Figure 52. Large Signal Step Response




Figure 53. Large Signal Step Response


## 8 Detailed Description

### 8.1 Overview

The LMH664X family is based on proprietary VIP10 dielectrically isolated bipolar process. This device family architecture features the following:

- Complimentary bipolar devices with exceptionally high  $f_t$  (~8 GHz) even under low supply voltage (2.7 V) and low bias current.
- A class A-B “turn-around” stage with improved noise, offset, and reduced power dissipation compared to similar speed devices (patent pending).
- Common Emitter push-push output stage capable of 75 mA output current (at 0.5 V from the supply rails) while consuming only 2.7 mA of total supply current per channel. This architecture allows output to reach within mV of either supply rail.
- Consistent performance over the entire operating supply voltage range with little variation for the most important specifications (for example, BW, SR,  $I_{OUT}$ , and so forth)
- Significant power saving (~40%) compared to competitive devices on the market with similar performance.

### 8.2 Functional Block Diagram



**Figure 54. Input Equivalent Circuit**

### 8.3 Feature Description

The LMH664X family is a drop-in replacement for the AD805X family of high speed Op Amps in most applications. In addition, the LMH664X will typically save about 40% on power dissipation, due to lower supply current, when compared to competition. All AD805X family’s specified parameters are included in the list of LMH664X ensured specifications in order to ensure equal or better level of performance. However, as in most high performance parts, due to subtleties of applications, it is strongly recommended that the performance of the part to be evaluated is tested under actual operating conditions to ensure full compliance to all specifications.

### 8.4 Device Functional Modes

With 3-V supplies and a common mode input voltage range that extends 0.5 V below  $V^-$ , the LMH664X find applications in low voltage/low power applications. Even with 3-V supplies, the -3dB BW (@  $A_V = +1$ ) is typically 115 MHz with a tested limit of 80 MHz. Production testing guarantees that process variations will not compromise speed. High frequency response is exceptionally stable, confining the typical -3dB BW over the industrial temperature range to  $\pm 2.5\%$ .

As seen in [Typical Performance Characteristics](#), the LMH664X output current capability (~75 mA) is enhanced compared to AD805X. This enhancement increases the output load range, adding to the LMH664X’s versatility. Since LMH664X is capable of high output current, device junction temperature should not to exceed the Absolute Maximum Ratings.

## 9 Application and Implementation

### NOTE

Information in the following applications sections is not part of the TI component specification, and TI does not warrant its accuracy or completeness. TI's customers are responsible for determining suitability of components for their purposes. Customers should validate and test their design implementation to confirm system functionality.


### 9.1 Application Information

This device family was designed to avoid output phase reversal. With input overdrive, the output is kept near supply rail (or as closed to it as mandated by the closed loop gain setting and the input voltage). See [Figure 56](#).

However, if the input voltage range of  $-0.5\text{ V}$  to  $1\text{ V}$  from  $V^+$  is exceeded by more than a diode drop, the internal ESD protection diodes will start to conduct. The current in the diodes should be kept at or below  $10\text{ mA}$ .

Output overdrive recovery time is less than  $100\text{ ns}$  as can be seen in [Figure 57](#).

### 9.2 Typical Application



**Figure 55. Single Supply Photodiode I-V Converter**

#### 9.2.1 Design Requirements

The circuit shown in [Figure 55](#) is used to amplify the current from a photodiode into a voltage output. In this circuit, the emphasis is on achieving high bandwidth and the transimpedance gain setting is kept relatively low. Because of its high slew rate limit and high speed, the LMH664X family lends itself well to such an application. This circuit achieves approximately  $1\text{ V/mA}$  of transimpedance gain and capable of handling up to  $1\text{ mA}_{\text{pp}}$  from the photodiode. Q1, in a common base configuration, isolates the high capacitance of the photodiode ( $C_d$ ) from the Op Amp input in order to maximize speed. Input is AC coupled through C1 to ease biasing and allow single supply operation. With 5-V single supply, the device input/output is shifted to near half supply using a voltage divider from VCC. Note that Q1 collector does not have any voltage swing and the Miller effect is minimized. D1, tied to Q1 base, is for temperature compensation of Q1's bias point. Q1 collector current was set to be large enough to handle the peak-to-peak photodiode excitation and not too large to shift the U1 output too far from mid-supply.

## Typical Application (continued)

### 9.2.1.1 Input and Output Topology

All input / output pins are protected against excessive voltages by ESD diodes connected to  $V^+$  and  $V^-$  rails (see [Figure 54](#)). These diodes start conducting when the input / output pin voltage approaches  $1V_{be}$  beyond  $V^+$  or  $V^-$  to protect against over voltage. These diodes are normally reverse biased. Further protection of the inputs is provided by the two resistors (R in [Figure 54](#)), in conjunction with the string of anti-parallel diodes connected between both bases of the input stage. The combination of these resistors and diodes reduces excessive differential input voltages approaching  $2V_{be}$ . This occurs most commonly when the device is used as a comparator (or with little or no feedback) and the device inputs no longer follow each other. In such a case, the diodes may conduct. As a consequence, input current increases and the differential input voltage is clamped. It is important to make sure that the subsequent current flow through the device input pins does not violate the Absolute Maximum Ratings of the device. To limit the current through this protection circuit, extra series resistors can be placed. Together with the built-in series resistors of several hundred ohms, these external resistors can limit the input current to a safe number (that is, less than 10mA). Be aware that these input series resistors may impact the switching speed of the device and could slow down the device.

### 9.2.1.2 Single Supply, Low Power Photodiode Amplifier

The circuit shown in [Figure 55](#) is used to amplify the current from a photodiode into a voltage output. In this circuit, the emphasis is on achieving high bandwidth and the transimpedance gain setting is kept relatively low. Because of its high slew rate limit and high speed, the LMH664X family lends itself well to such an application.

This circuit achieves approximately 1V/mA of transimpedance gain and capable of handling up to  $1mA_{pp}$  from the photodiode. Q1, in a common base configuration, isolates the high capacitance of the photodiode ( $C_d$ ) from the Op Amp input in order to maximize speed. Input is AC coupled through C1 to ease biasing and allow single supply operation. With 5V single supply, the device input/output is shifted to near half supply using a voltage divider from  $V_{CC}$ . Note that Q1 collector does not have any voltage swing and the Miller effect is minimized. D1, tied to Q1 base, is for temperature compensation of Q1's bias point. Q1 collector current was set to be large enough to handle the peak-to-peak photodiode excitation and not too large to shift the U1 output too far from mid-supply.

No matter how low an  $R_f$  is selected, there is a need for  $C_f$  in order to stabilize the circuit. The reason for this is that the Op Amp input capacitance and Q1 equivalent collector capacitance together ( $C_{IN}$ ) will cause additional phase shift to the signal fed back to the inverting node.  $C_f$  will function as a zero in the feedback path counteracting the effect of the  $C_{IN}$  and acting to stabilize the circuit. By proper selection of  $C_f$  such that the Op Amp open loop gain is equal to the inverse of the feedback factor at that frequency, the response is optimized with a theoretical 45° phase margin.

$$C_F = \sim \text{SQRT} \left[ \frac{C_{IN}}{(2\pi \cdot \text{GBWP} \cdot R_F)} \right]$$

where

- GBWP is the Gain Bandwidth Product of the Op Amp (1)

Optimized as such, the I-V converter will have a theoretical pole,  $f_p$ , at:

$$f_p = \text{SQRT} \left[ \frac{\text{GBWP}}{(2\pi R_F \cdot C_{IN})} \right] \quad (2)$$

With Op Amp input capacitance of 3pF and an estimate for Q1 output capacitance of about 3pF as well,  $C_{IN} = 6$  pF. From the typical performance plots, LMH6642/6643 family GBWP is approximately 57 MHz. Therefore, with  $R_f = 1k$ , from [Equation 1](#) and [Equation 2](#):

$$C_f = \sim 4.1 \text{ pF and } f_p = 39 \text{ MHz} \quad (3)$$

For this example, optimum  $C_f$  was empirically determined to be around 5 pF. This time domain response is shown in [Figure 58](#) below showing about 9 ns rise/fall times, corresponding to about 39 MHz for  $f_p$ . The overall supply current from the +5 V supply is around 5 mA with no load.


## Typical Application (continued)

### 9.2.2 Detailed Design Procedure

No matter how low an  $R_f$  is selected, there is a need for  $C_f$  in order to stabilize the circuit. The reason for this is that the Op Amp input capacitance and Q1 equivalent collector capacitance together ( $C_{IN}$ ) will cause additional phase shift to the signal fed back to the inverting node.  $C_f$  will function as a zero in the feedback path counteracting the effect of the  $C_{IN}$  and acting to stabilize the circuit. By proper selection of  $C_f$  such that the Op Amp open loop gain is equal to the inverse of the feedback factor at that frequency, the response is optimized with a theoretical  $45^\circ$  phase margin where GBWP is the Gain Bandwidth Product of the Op Amp, Optimized as such, the I-V converter will have a theoretical pole,  $f_p$ , at: (2) With Op Amp input capacitance of 3pF and an estimate for Q1 output capacitance of about 3pF as well,  $C_{IN} = 6$  pF. From the typical performance plots, LMH6642/6643 family GBWP is approximately 57 MHz. Therefore, with  $R_f = 1k$ , from Equation 2 and Equation 3 :  $C_f = \sim 4.1$  pF and  $f_p = 39$  MHz.

Single Supply Photodiode I-V Converter For this example, optimum  $C_f$  was empirically determined to be around 5 pF. This time domain response is shown in Figure 58 showing about 9 ns rise/fall times, corresponding to about 39 MHz for  $f_p$ . The overall supply current from the +5 V supply is around 5 mA with no load.

### 9.2.3 Application Curves



## 10 Power Supply Recommendations

The LMH664x device family can operate off a single supply or with dual supplies. The input CM capability of the parts (CMVR) extends all the way down to the  $V_-$  rail to simplify single supply applications. Supplies should be decoupled with low inductance, often ceramic, capacitors to ground less than 0.5 inches from the device pins. The use of ground plane is recommended, and as in most high speed devices, it is advisable to remove ground plane close to device sensitive pins such as the inputs.

## 11 Layout

### 11.1 Layout Guidelines

Generally, a good high frequency layout will keep power supply and ground traces away from the inverting input and output pins. Parasitic capacitances on these nodes to ground will cause frequency response peaking and possible circuit oscillations (see Application Note OA-15, "Frequent Faux Pas in Applying Wideband Current Feedback Amplifiers", [SNOA367](#), for more information). Texas Instruments suggests the following evaluation boards as a guide for high frequency layout and as an aid in device testing and characterization:

**Table 1. Printed Circuit Board Layout And Component Values**

| DEVICE    | PACKAGE      | EVALUATION BOARD PN |
|-----------|--------------|---------------------|
| LMH6642MF | 5-Pin SOT-23 | LMH730216           |
| LMH6642MA | 8-Pin SOIC   | LMH730227           |
| LMH6643MA | 8-Pin SOIC   | LMH730036           |
| LMH6643MM | 8-Pin VSSOP  | LMH730123           |
| LMH6644MA | 14-Pin SOIC  | LMH730231           |
| LMH6644MT | 14-Pin TSSOP | LMH730131           |

Another important parameter in working with high speed/high performance amplifiers, is the component values selection. Choosing external resistors that are large in value will effect the closed loop behavior of the stage because of the interaction of these resistors with parasitic capacitances. These capacitors could be inherent to the device or a by-product of the board layout and component placement. Either way, keeping the resistor values lower, will diminish this interaction to a large extent. On the other hand, choosing very low value resistors could load down nodes and will contribute to higher overall power dissipation.

### 11.2 Layout Example




Figure 59. LMH6642/LMH6643/LMH6644 Layer 1




Figure 60. LMH6642/LMH6643/LMH6644 Layer 2

## 12 Device and Documentation Support

### 12.1 Related Links

The table below lists quick access links. Categories include technical documents, support and community resources, tools and software, and quick access to sample or buy.

Table 2. Related Links

| PARTS   | PRODUCT FOLDER             | SAMPLE & BUY               | TECHNICAL DOCUMENTS        | TOOLS & SOFTWARE           | SUPPORT & COMMUNITY        |
|---------|----------------------------|----------------------------|----------------------------|----------------------------|----------------------------|
| LMH6642 | <a href="#">Click here</a> |
| LMH6643 | <a href="#">Click here</a> |
| LMH6644 | <a href="#">Click here</a> |

### 12.2 Trademarks

All trademarks are the property of their respective owners.

### 12.3 Electrostatic Discharge Caution



These devices have limited built-in ESD protection. The leads should be shorted together or the device placed in conductive foam during storage or handling to prevent electrostatic damage to the MOS gates.

### 12.4 Glossary

[SLYZ022](#) — *TI Glossary*.

This glossary lists and explains terms, acronyms, and definitions.

## 13 Mechanical, Packaging, and Orderable Information

The following pages include mechanical, packaging, and orderable information. This information is the most current data available for the designated devices. This data is subject to change without notice and revision of this document. For browser-based versions of this data sheet, refer to the left-hand navigation.

**PACKAGING INFORMATION**

| Orderable part number           | Status<br>(1) | Material type<br>(2) | Package   Pins   | Package qty   Carrier | RoHS<br>(3) | Lead finish/<br>Ball material<br>(4) | MSL rating/<br>Peak reflow<br>(5) | Op temp (°C) | Part marking<br>(6) |
|---------------------------------|---------------|----------------------|------------------|-----------------------|-------------|--------------------------------------|-----------------------------------|--------------|---------------------|
| <a href="#">LMH6642MA/NOPB</a>  | Active        | Production           | SOIC (D)   8     | 95   TUBE             | Yes         | SN                                   | Level-1-260C-UNLIM                | -40 to 85    | LMH66<br>42MA       |
| LMH6642MA/NOPB.A                | Active        | Production           | SOIC (D)   8     | 95   TUBE             | Yes         | SN                                   | Level-1-260C-UNLIM                | -40 to 85    | LMH66<br>42MA       |
| <a href="#">LMH6642MAX/NOPB</a> | Active        | Production           | SOIC (D)   8     | 2500   LARGE T&R      | Yes         | SN                                   | Level-1-260C-UNLIM                | -40 to 85    | LMH66<br>42MA       |
| LMH6642MAX/NOPB.A               | Active        | Production           | SOIC (D)   8     | 2500   LARGE T&R      | Yes         | SN                                   | Level-1-260C-UNLIM                | -40 to 85    | LMH66<br>42MA       |
| <a href="#">LMH6642MF/NOPB</a>  | Active        | Production           | SOT-23 (DBV)   5 | 1000   SMALL T&R      | Yes         | Call TI   Sn   Nipdau                | Level-1-260C-UNLIM                | -40 to 85    | A64A                |
| LMH6642MF/NOPB.A                | Active        | Production           | SOT-23 (DBV)   5 | 1000   SMALL T&R      | Yes         | Call TI                              | Level-1-260C-UNLIM                | -40 to 85    | A64A                |
| <a href="#">LMH6642MFX/NOPB</a> | Active        | Production           | SOT-23 (DBV)   5 | 3000   LARGE T&R      | Yes         | Call TI   Sn   Nipdau                | Level-1-260C-UNLIM                | -40 to 85    | A64A                |
| LMH6642MFX/NOPB.A               | Active        | Production           | SOT-23 (DBV)   5 | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 85    | A64A                |
| <a href="#">LMH6643MA/NOPB</a>  | Active        | Production           | SOIC (D)   8     | 95   TUBE             | Yes         | SN                                   | Level-1-260C-UNLIM                | -40 to 85    | LMH66<br>43MA       |
| LMH6643MA/NOPB.A                | Active        | Production           | SOIC (D)   8     | 95   TUBE             | Yes         | SN                                   | Level-1-260C-UNLIM                | -40 to 85    | LMH66<br>43MA       |
| <a href="#">LMH6643MAX/NOPB</a> | Active        | Production           | SOIC (D)   8     | 2500   LARGE T&R      | Yes         | SN                                   | Level-1-260C-UNLIM                | -40 to 85    | LMH66<br>43MA       |
| LMH6643MAX/NOPB.A               | Active        | Production           | SOIC (D)   8     | 2500   LARGE T&R      | Yes         | SN                                   | Level-1-260C-UNLIM                | -40 to 85    | LMH66<br>43MA       |
| <a href="#">LMH6643MM/NOPB</a>  | Active        | Production           | VSSOP (DGK)   8  | 1000   SMALL T&R      | Yes         | SN                                   | Level-1-260C-UNLIM                | -40 to 85    | A65A                |
| LMH6643MM/NOPB.A                | Active        | Production           | VSSOP (DGK)   8  | 1000   SMALL T&R      | Yes         | SN                                   | Level-1-260C-UNLIM                | -40 to 85    | A65A                |
| <a href="#">LMH6643MMX/NOPB</a> | Active        | Production           | VSSOP (DGK)   8  | 3500   LARGE T&R      | Yes         | SN                                   | Level-1-260C-UNLIM                | -40 to 85    | A65A                |
| LMH6643MMX/NOPB.A               | Active        | Production           | VSSOP (DGK)   8  | 3500   LARGE T&R      | Yes         | SN                                   | Level-1-260C-UNLIM                | -40 to 85    | A65A                |
| <a href="#">LMH6644MA/NOPB</a>  | Active        | Production           | SOIC (D)   14    | 55   TUBE             | Yes         | SN                                   | Level-1-260C-UNLIM                | -40 to 85    | LMH6644MA           |
| LMH6644MA/NOPB.A                | Active        | Production           | SOIC (D)   14    | 55   TUBE             | Yes         | SN                                   | Level-1-260C-UNLIM                | -40 to 85    | LMH6644MA           |
| <a href="#">LMH6644MAX/NOPB</a> | Active        | Production           | SOIC (D)   14    | 2500   LARGE T&R      | Yes         | SN                                   | Level-1-260C-UNLIM                | -40 to 85    | LMH6644MA           |
| LMH6644MAX/NOPB.A               | Active        | Production           | SOIC (D)   14    | 2500   LARGE T&R      | Yes         | SN                                   | Level-1-260C-UNLIM                | -40 to 85    | LMH6644MA           |
| <a href="#">LMH6644MT/NOPB</a>  | Active        | Production           | TSSOP (PW)   14  | 94   TUBE             | Yes         | NIPDAU   SN                          | Level-1-260C-UNLIM                | -40 to 85    | LMH66<br>44MT       |
| LMH6644MT/NOPB.A                | Active        | Production           | TSSOP (PW)   14  | 94   TUBE             | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 85    | LMH66<br>44MT       |

| Orderable part number           | Status<br>(1) | Material type<br>(2) | Package   Pins  | Package qty   Carrier | RoHS<br>(3) | Lead finish/<br>Ball material<br>(4) | MSL rating/<br>Peak reflow<br>(5) | Op temp (°C) | Part marking<br>(6) |
|---------------------------------|---------------|----------------------|-----------------|-----------------------|-------------|--------------------------------------|-----------------------------------|--------------|---------------------|
| <a href="#">LMH6644MTX/NOPB</a> | Active        | Production           | TSSOP (PW)   14 | 2500   LARGE T&R      | Yes         | NIPDAU   SN                          | Level-1-260C-UNLIM                | -40 to 85    | LMH66<br>44MT       |
| LMH6644MTX/NOPB.A               | Active        | Production           | TSSOP (PW)   14 | 2500   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 85    | LMH66<br>44MT       |

(1) **Status:** For more details on status, see our [product life cycle](#).

(2) **Material type:** When designated, preproduction parts are prototypes/experimental devices, and are not yet approved or released for full production. Testing and final process, including without limitation quality assurance, reliability performance testing, and/or process qualification, may not yet be complete, and this item is subject to further changes or possible discontinuation. If available for ordering, purchases will be subject to an additional waiver at checkout, and are intended for early internal evaluation purposes only. These items are sold without warranties of any kind.

(3) **RoHS values:** Yes, No, RoHS Exempt. See the [TI RoHS Statement](#) for additional information and value definition.

(4) **Lead finish/Ball material:** Parts may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead finish/Ball material values may wrap to two lines if the finish value exceeds the maximum column width.

(5) **MSL rating/Peak reflow:** The moisture sensitivity level ratings and peak solder (reflow) temperatures. In the event that a part has multiple moisture sensitivity ratings, only the lowest level per JEDEC standards is shown. Refer to the shipping label for the actual reflow temperature that will be used to mount the part to the printed circuit board.

(6) **Part marking:** There may be an additional marking, which relates to the logo, the lot trace code information, or the environmental category of the part.

Multiple part markings will be inside parentheses. Only one part marking contained in parentheses and separated by a "-" will appear on a part. If a line is indented then it is a continuation of the previous line and the two combined represent the entire part marking for that device.

**Important Information and Disclaimer:** The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.

**TAPE AND REEL INFORMATION**

**QUADRANT ASSIGNMENTS FOR PIN 1 ORIENTATION IN TAPE**



\*All dimensions are nominal

| Device          | Package Type | Package Drawing | Pins | SPQ  | Reel Diameter (mm) | Reel Width W1 (mm) | A0 (mm) | B0 (mm) | K0 (mm) | P1 (mm) | W (mm) | Pin1 Quadrant |
|-----------------|--------------|-----------------|------|------|--------------------|--------------------|---------|---------|---------|---------|--------|---------------|
| LMH6642MAX/NOPB | SOIC         | D               | 8    | 2500 | 330.0              | 12.4               | 6.5     | 5.4     | 2.0     | 8.0     | 12.0   | Q1            |
| LMH6642MF/NOPB  | SOT-23       | DBV             | 5    | 1000 | 180.0              | 8.4                | 3.2     | 3.2     | 1.4     | 4.0     | 8.0    | Q3            |
| LMH6642MF/NOPB  | SOT-23       | DBV             | 5    | 1000 | 178.0              | 8.4                | 3.2     | 3.2     | 1.4     | 4.0     | 8.0    | Q3            |
| LMH6642MFX/NOPB | SOT-23       | DBV             | 5    | 3000 | 178.0              | 8.4                | 3.2     | 3.2     | 1.4     | 4.0     | 8.0    | Q3            |
| LMH6643MAX/NOPB | SOIC         | D               | 8    | 2500 | 330.0              | 12.4               | 6.5     | 5.4     | 2.0     | 8.0     | 12.0   | Q1            |
| LMH6643MM/NOPB  | VSSOP        | DGK             | 8    | 1000 | 177.8              | 12.4               | 5.3     | 3.4     | 1.4     | 8.0     | 12.0   | Q1            |
| LMH6643MMX/NOPB | VSSOP        | DGK             | 8    | 3500 | 330.0              | 12.4               | 5.3     | 3.4     | 1.4     | 8.0     | 12.0   | Q1            |
| LMH6644MAX/NOPB | SOIC         | D               | 14   | 2500 | 330.0              | 16.4               | 6.5     | 9.35    | 2.3     | 8.0     | 16.0   | Q1            |
| LMH6644MTX/NOPB | TSSOP        | PW              | 14   | 2500 | 330.0              | 12.4               | 6.95    | 5.6     | 1.6     | 8.0     | 12.0   | Q1            |

**TAPE AND REEL BOX DIMENSIONS**


\*All dimensions are nominal

| Device          | Package Type | Package Drawing | Pins | SPQ  | Length (mm) | Width (mm) | Height (mm) |
|-----------------|--------------|-----------------|------|------|-------------|------------|-------------|
| LMH6642MAX/NOPB | SOIC         | D               | 8    | 2500 | 367.0       | 367.0      | 35.0        |
| LMH6642MF/NOPB  | SOT-23       | DBV             | 5    | 1000 | 210.0       | 185.0      | 35.0        |
| LMH6642MF/NOPB  | SOT-23       | DBV             | 5    | 1000 | 208.0       | 191.0      | 35.0        |
| LMH6642MFX/NOPB | SOT-23       | DBV             | 5    | 3000 | 208.0       | 191.0      | 35.0        |
| LMH6643MAX/NOPB | SOIC         | D               | 8    | 2500 | 367.0       | 367.0      | 35.0        |
| LMH6643MM/NOPB  | VSSOP        | DGK             | 8    | 1000 | 208.0       | 191.0      | 35.0        |
| LMH6643MMX/NOPB | VSSOP        | DGK             | 8    | 3500 | 367.0       | 367.0      | 35.0        |
| LMH6644MAX/NOPB | SOIC         | D               | 14   | 2500 | 367.0       | 367.0      | 35.0        |
| LMH6644MTX/NOPB | TSSOP        | PW              | 14   | 2500 | 367.0       | 367.0      | 35.0        |

**TUBE**


\*All dimensions are nominal

| Device           | Package Name | Package Type | Pins | SPQ | L (mm) | W (mm) | T (μm) | B (mm) |
|------------------|--------------|--------------|------|-----|--------|--------|--------|--------|
| LMH6642MA/NOPB   | D            | SOIC         | 8    | 95  | 495    | 8      | 4064   | 3.05   |
| LMH6642MA/NOPB.A | D            | SOIC         | 8    | 95  | 495    | 8      | 4064   | 3.05   |
| LMH6643MA/NOPB   | D            | SOIC         | 8    | 95  | 495    | 8      | 4064   | 3.05   |
| LMH6643MA/NOPB.A | D            | SOIC         | 8    | 95  | 495    | 8      | 4064   | 3.05   |
| LMH6644MA/NOPB   | D            | SOIC         | 14   | 55  | 495    | 8      | 4064   | 3.05   |
| LMH6644MA/NOPB.A | D            | SOIC         | 14   | 55  | 495    | 8      | 4064   | 3.05   |
| LMH6644MT/NOPB   | PW           | TSSOP        | 14   | 94  | 495    | 8      | 2514.6 | 4.06   |
| LMH6644MT/NOPB   | PW           | TSSOP        | 14   | 94  | 530    | 10.2   | 3600   | 3.5    |
| LMH6644MT/NOPB.A | PW           | TSSOP        | 14   | 94  | 495    | 8      | 2514.6 | 4.06   |
| LMH6644MT/NOPB.A | PW           | TSSOP        | 14   | 94  | 530    | 10.2   | 3600   | 3.5    |



# EXAMPLE BOARD LAYOUT

DBV0005A

SOT-23 - 1.45 mm max height

SMALL OUTLINE TRANSISTOR



LAND PATTERN EXAMPLE  
EXPOSED METAL SHOWN  
SCALE:15X



SOLDER MASK DETAILS

4214839/K 08/2024

NOTES: (continued)

- 6. Publication IPC-7351 may have alternate designs.
- 7. Solder mask tolerances between and around signal pads can vary based on board fabrication site.

# EXAMPLE STENCIL DESIGN

DBV0005A

SOT-23 - 1.45 mm max height

SMALL OUTLINE TRANSISTOR



SOLDER PASTE EXAMPLE  
BASED ON 0.125 mm THICK STENCIL  
SCALE:15X

4214839/K 08/2024

NOTES: (continued)

8. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.
9. Board assembly site may have different recommendations for stencil design.


# DGK0008A



# PACKAGE OUTLINE

VSSOP - 1.1 mm max height

SMALL OUTLINE PACKAGE



4214862/A 04/2023

**NOTES:**

PowerPAD is a trademark of Texas Instruments.


1. All linear dimensions are in millimeters. Any dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.
2. This drawing is subject to change without notice.
3. This dimension does not include mold flash, protrusions, or gate burrs. Mold flash, protrusions, or gate burrs shall not exceed 0.15 mm per side.
4. This dimension does not include interlead flash. Interlead flash shall not exceed 0.25 mm per side.
5. Reference JEDEC registration MO-187.

# EXAMPLE BOARD LAYOUT


DGK0008A

™ VSSOP - 1.1 mm max height

SMALL OUTLINE PACKAGE



LAND PATTERN EXAMPLE  
EXPOSED METAL SHOWN  
SCALE: 15X



SOLDER MASK DETAILS

4214862/A 04/2023

NOTES: (continued)


6. Publication IPC-7351 may have alternate designs.
7. Solder mask tolerances between and around signal pads can vary based on board fabrication site.
8. Vias are optional depending on application, refer to device data sheet. If any vias are implemented, refer to their locations shown on this view. It is recommended that vias under paste be filled, plugged or tented.
9. Size of metal pad may vary due to creepage requirement.

# EXAMPLE STENCIL DESIGN

DGK0008A

™ VSSOP - 1.1 mm max height

SMALL OUTLINE PACKAGE



SOLDER PASTE EXAMPLE  
SCALE: 15X

4214862/A 04/2023

NOTES: (continued)

11. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.
12. Board assembly site may have different recommendations for stencil design.


D0014A



# PACKAGE OUTLINE

## SOIC - 1.75 mm max height

SMALL OUTLINE INTEGRATED CIRCUIT



4220718/A 09/2016

NOTES:


1. All linear dimensions are in millimeters. Dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.
2. This drawing is subject to change without notice.
3. This dimension does not include mold flash, protrusions, or gate burrs. Mold flash, protrusions, or gate burrs shall not exceed 0.15 mm, per side.
4. This dimension does not include interlead flash. Interlead flash shall not exceed 0.43 mm, per side.
5. Reference JEDEC registration MS-012, variation AB.

# EXAMPLE BOARD LAYOUT


D0014A

SOIC - 1.75 mm max height

SMALL OUTLINE INTEGRATED CIRCUIT



LAND PATTERN EXAMPLE  
SCALE:8X



SOLDER MASK DETAILS

4220718/A 09/2016

NOTES: (continued)


- 6. Publication IPC-7351 may have alternate designs.
- 7. Solder mask tolerances between and around signal pads can vary based on board fabrication site.

# EXAMPLE STENCIL DESIGN

D0014A

SOIC - 1.75 mm max height

SMALL OUTLINE INTEGRATED CIRCUIT




SOLDER PASTE EXAMPLE  
BASED ON 0.125 mm THICK STENCIL  
SCALE:8X

4220718/A 09/2016

NOTES: (continued)

8. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.
9. Board assembly site may have different recommendations for stencil design.




D0008A

# PACKAGE OUTLINE

SOIC - 1.75 mm max height

SMALL OUTLINE INTEGRATED CIRCUIT



4214825/C 02/2019

### NOTES:


- Linear dimensions are in inches [millimeters]. Dimensions in parenthesis are for reference only. Controlling dimensions are in inches. Dimensioning and tolerancing per ASME Y14.5M.
- This drawing is subject to change without notice.
- This dimension does not include mold flash, protrusions, or gate burrs. Mold flash, protrusions, or gate burrs shall not exceed  $.006$  [0.15] per side.
- This dimension does not include interlead flash.
- Reference JEDEC registration MS-012, variation AA.

# EXAMPLE BOARD LAYOUT


D0008A

SOIC - 1.75 mm max height

SMALL OUTLINE INTEGRATED CIRCUIT



LAND PATTERN EXAMPLE  
EXPOSED METAL SHOWN  
SCALE:8X



SOLDER MASK DETAILS

4214825/C 02/2019

NOTES: (continued)

6. Publication IPC-7351 may have alternate designs.


7. Solder mask tolerances between and around signal pads can vary based on board fabrication site.

# EXAMPLE STENCIL DESIGN

D0008A

SOIC - 1.75 mm max height

SMALL OUTLINE INTEGRATED CIRCUIT





SOLDER PASTE EXAMPLE  
BASED ON .005 INCH [0.125 MM] THICK STENCIL  
SCALE:8X

4214825/C 02/2019

NOTES: (continued)

8. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.
9. Board assembly site may have different recommendations for stencil design.



4220202/B 12/2023

NOTES:


1. All linear dimensions are in millimeters. Any dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.
2. This drawing is subject to change without notice.
3. This dimension does not include mold flash, protrusions, or gate burrs. Mold flash, protrusions, or gate burrs shall not exceed 0.15 mm per side.
4. This dimension does not include interlead flash. Interlead flash shall not exceed 0.25 mm per side.
5. Reference JEDEC registration MO-153.

# EXAMPLE BOARD LAYOUT


PW0014A

TSSOP - 1.2 mm max height

SMALL OUTLINE PACKAGE



LAND PATTERN EXAMPLE  
EXPOSED METAL SHOWN  
SCALE: 10X



4220202/B 12/2023

NOTES: (continued)


- 6. Publication IPC-7351 may have alternate designs.
- 7. Solder mask tolerances between and around signal pads can vary based on board fabrication site.

# EXAMPLE STENCIL DESIGN

PW0014A

TSSOP - 1.2 mm max height

SMALL OUTLINE PACKAGE



SOLDER PASTE EXAMPLE  
BASED ON 0.125 mm THICK STENCIL  
SCALE: 10X

4220202/B 12/2023

NOTES: (continued)

8. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.
9. Board assembly site may have different recommendations for stencil design.

## IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATASHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, regulatory or other requirements.

These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you fully indemnify TI and its representatives against any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to [TI's Terms of Sale](#), [TI's General Quality Guidelines](#), or other applicable terms available either on [ti.com](#) or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products. Unless TI explicitly designates a product as custom or customer-specified, TI products are standard, catalog, general purpose devices.

TI objects to and rejects any additional or different terms you may propose.

Copyright © 2026, Texas Instruments Incorporated

Last updated 10/2025