

## CDx4HCT08 Quadruple 2-Input AND Gates

### 1 Features

- LSTTL input logic compatible
  - $V_{IL(max)} = 0.8V$ ,  $V_{IH(min)} = 2V$
- CMOS input logic compatible
  - $I_I \leq 1\mu A$  at  $V_{OL}$ ,  $V_{OH}$
- Buffered inputs
- 4.5V to 5.5V operation
- Wide operating temperature range:  $-55^{\circ}C$  to  $+125^{\circ}C$
- Supports fanout up to 10 LSTTL loads
- Significant power reduction compared to LSTTL logic ICs

### 2 Applications

- [Combining power good signals](#)
- [Enable digital signals](#)


### 3 Description

This device contains four independent 2-input AND gates. Each gate performs the Boolean function  $Y = A \bullet B$  in positive logic.

#### Device Information

| PART NUMBER | PACKAGE <sup>(1)</sup> | PACKAGE SIZE <sup>(2)</sup> | BODY SIZE <sup>(3)</sup> |
|-------------|------------------------|-----------------------------|--------------------------|
| CDx4HCT08   | D (SOIC, 14)           | 8.65mm × 6mm                | 8.65mm × 3.9mm           |
|             | N (PDIP, 14)           | 19.30mm × 9.4mm             | 19.30mm × 6.35mm         |
|             | J (CDIP, 14)           | 19.56mm × 6.7mm             | 19.56mm × 4.57mm         |

- (1) For more information, see [Mechanical, Packaging, and Orderable Information](#).
- (2) The package size (length × width) is a nominal value and includes pins, where applicable.
- (3) The body size (length × width) is a nominal value and does not include pins.




Functional pinout



## Table of Contents

|                                                  |          |                                                                  |           |
|--------------------------------------------------|----------|------------------------------------------------------------------|-----------|
| <b>1 Features</b> .....                          | <b>1</b> | 7.3 Feature Description.....                                     | <b>8</b>  |
| <b>2 Applications</b> .....                      | <b>1</b> | 7.4 Device Functional Modes.....                                 | <b>9</b>  |
| <b>3 Description</b> .....                       | <b>1</b> | <b>8 Application and Implementation</b> .....                    | <b>10</b> |
| <b>4 Pin Configuration and Functions</b> .....   | <b>3</b> | 8.1 Application Information.....                                 | <b>10</b> |
| <b>5 Specifications</b> .....                    | <b>4</b> | 8.2 Typical Application.....                                     | <b>10</b> |
| 5.1 Absolute Maximum Ratings.....                | <b>4</b> | 8.3 Power Supply Recommendations.....                            | <b>11</b> |
| 5.2 ESD Ratings.....                             | <b>4</b> | 8.4 Layout.....                                                  | <b>12</b> |
| 5.3 Recommended Operating Conditions.....        | <b>4</b> | <b>9 Device and Documentation Support</b> .....                  | <b>13</b> |
| 5.4 Thermal Information.....                     | <b>4</b> | 9.1 Documentation Support.....                                   | <b>13</b> |
| 5.5 Electrical Characteristics.....              | <b>5</b> | 9.2 Receiving Notification of Documentation Updates....          | <b>13</b> |
| 5.6 Switching Characteristics.....               | <b>5</b> | 9.3 Support Resources.....                                       | <b>13</b> |
| 5.7 Operating Characteristics.....               | <b>5</b> | 9.4 Trademarks.....                                              | <b>13</b> |
| 5.8 Typical Characteristics.....                 | <b>6</b> | 9.5 Electrostatic Discharge Caution.....                         | <b>13</b> |
| <b>6 Parameter Measurement Information</b> ..... | <b>7</b> | 9.6 Glossary.....                                                | <b>13</b> |
| <b>7 Detailed Description</b> .....              | <b>8</b> | <b>10 Revision History</b> .....                                 | <b>13</b> |
| 7.1 Overview.....                                | <b>8</b> | <b>11 Mechanical, Packaging, and Orderable Information</b> ..... | <b>13</b> |
| 7.2 Functional Block Diagram.....                | <b>8</b> |                                                                  |           |

## 4 Pin Configuration and Functions



**Figure 4-1. D, N, or J Package 14-Pin SOIC, PDIP, or CDIP Top View**

| PIN             |     | TYPE <sup>(1)</sup> | DESCRIPTION         |
|-----------------|-----|---------------------|---------------------|
| NAME            | NO. |                     |                     |
| 1A              | 1   | Input               | Channel 1, Input A  |
| 1B              | 2   | Input               | Channel 1, Input B  |
| 1Y              | 3   | Output              | Channel 1, Output Y |
| 2A              | 4   | Input               | Channel 2, Input A  |
| 2B              | 5   | Input               | Channel 2, Input B  |
| 2Y              | 6   | Output              | Channel 2, Output Y |
| GND             | 7   | —                   | Ground              |
| 3Y              | 8   | Output              | Channel 3, Output Y |
| 3A              | 9   | Input               | Channel 3, Input A  |
| 3B              | 10  | Input               | Channel 3, Input B  |
| 4Y              | 11  | Output              | Channel 4, Output Y |
| 4A              | 12  | Input               | Channel 4, Input A  |
| 4B              | 13  | Input               | Channel 4, Input B  |
| V <sub>CC</sub> | 14  | —                   | Positive Supply     |

(1) Signal Types: I = Input, O = Output, I/O = Input or Output

## 5 Specifications

### 5.1 Absolute Maximum Ratings

over operating free-air temperature range (unless otherwise noted)<sup>(1)</sup>

|                  |                                                   |                                                                     | MIN  | MAX | UNIT |
|------------------|---------------------------------------------------|---------------------------------------------------------------------|------|-----|------|
| V <sub>CC</sub>  | Supply voltage                                    |                                                                     | –0.5 | 7   | V    |
| I <sub>IK</sub>  | Input clamp current <sup>(2)</sup>                | V <sub>I</sub> < –0.5 V or V <sub>I</sub> > V <sub>CC</sub> + 0.5 V |      | ±20 | mA   |
| I <sub>OK</sub>  | Output clamp current <sup>(2)</sup>               | V <sub>O</sub> < –0.5 V or V <sub>O</sub> > V <sub>CC</sub> + 0.5 V |      | ±20 | mA   |
| I <sub>O</sub>   | Continuous output current                         | V <sub>O</sub> > –0.5 V or V <sub>O</sub> < V <sub>CC</sub> + 0.5 V |      | ±25 | mA   |
|                  | Continuous current through V <sub>CC</sub> or GND |                                                                     |      | ±50 | mA   |
| T <sub>J</sub>   | Junction temperature <sup>(3)</sup>               | Plastic package                                                     |      | 150 | °C   |
|                  |                                                   | Hermetic package or die                                             |      | 175 | °C   |
|                  | Maximum lead temperature (soldering 10s)          | SOIC - lead tips only                                               |      | 300 | °C   |
| T <sub>stg</sub> | Storage temperature                               |                                                                     | –65  | 150 | °C   |

(1) Stresses beyond those listed under *Absolute Maximum Rating* may cause permanent damage to the device. These are stress ratings only, which do not imply functional operation of the device at these or any other conditions beyond those indicated under *Recommended Operating Condition*. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability.

(2) The input and output voltage ratings may be exceeded if the input and output current ratings are observed.

(3) Guaranteed by design.

### 5.2 ESD Ratings

|                    |                         | VALUE                                                                        | UNIT |
|--------------------|-------------------------|------------------------------------------------------------------------------|------|
| V <sub>(ESD)</sub> | Electrostatic discharge | Human body model (HBM), per AEC Q100-002 <sup>(1)</sup>                      | V    |
|                    |                         | HBM ESD Classification Level 2                                               |      |
|                    |                         | Charged device model (CDM), per AEC Q100-011 CDM ESD Classification Level C6 |      |
|                    |                         | ±2000                                                                        |      |
|                    |                         | ±1000                                                                        |      |

(1) AEC Q100-002 indicate that HBM stressing shall be in accordance with the ANSI/ESDA/JEDEC JS-001 specification.

### 5.3 Recommended Operating Conditions

over operating free-air temperature range (unless otherwise noted)

|                 |                                     |                                | MIN | NOM | MAX             | UNIT |
|-----------------|-------------------------------------|--------------------------------|-----|-----|-----------------|------|
| V <sub>CC</sub> | Supply voltage                      |                                | 4.5 |     | 5.5             | V    |
| V <sub>IH</sub> | High-level input voltage            | V <sub>CC</sub> = 4.5 to 5.5 V | 2   |     |                 | V    |
| V <sub>IL</sub> | Low-level input voltage             | V <sub>CC</sub> = 4.5 to 5.5 V |     |     | 0.8             | V    |
| V <sub>I</sub>  | Input voltage                       |                                | 0   |     | V <sub>CC</sub> | V    |
| V <sub>O</sub>  | Output voltage                      |                                | 0   |     | V <sub>CC</sub> | V    |
| Δt/Δv           | Input transition rise and fall rate | V <sub>CC</sub> = 4.5 V        |     |     | 500             | ns   |
|                 |                                     | V <sub>CC</sub> = 5.5 V        |     |     | 400             |      |
| T <sub>A</sub>  | Operating free-air temperature      |                                | –55 |     | 125             | °C   |

### 5.4 Thermal Information

| THERMAL METRIC <sup>(1)</sup> |                                           | CD74HCT08 |          | UNIT |
|-------------------------------|-------------------------------------------|-----------|----------|------|
|                               |                                           | N (PDIP)  | D (SOIC) |      |
|                               |                                           | 14 PINS   | 14 PINS  |      |
| R <sub>θJA</sub>              | Junction-to-ambient thermal resistance    | 103.8     | 138.7    | °C/W |
| R <sub>θJC(top)</sub>         | Junction-to-case (top) thermal resistance | 91.6      | 93.8     | °C/W |

| THERMAL METRIC <sup>(1)</sup> |                                              | CD74HCT08 |          | UNIT |
|-------------------------------|----------------------------------------------|-----------|----------|------|
|                               |                                              | N (PDIP)  | D (SOIC) |      |
|                               |                                              | 14 PINS   | 14 PINS  |      |
| $R_{\theta JB}$               | Junction-to-board thermal resistance         | 83.5      | 94.7     | °C/W |
| $\Psi_{JT}$                   | Junction-to-top characterization parameter   | 71.1      | 49.1     | °C/W |
| $\Psi_{JB}$                   | Junction-to-board characterization parameter | 83.4      | 94.3     | °C/W |
| $R_{\theta JC(bot)}$          | Junction-to-case (bottom) thermal resistance | N/A       | N/A      | °C/W |

(1) For more information about traditional and new thermal metrics, see the [Semiconductor and IC Package Thermal Metrics](#) application report.

## 5.5 Electrical Characteristics

over operating free-air temperature range; typical values measured at  $T_A = 25^\circ\text{C}$  (unless otherwise noted).

| Operating free-air temperature range, typical values measured at T <sub>A</sub> = 25 °C (unless otherwise noted). |                                                   |                                                     |                          |                 |                                                  |     |     |               |     |     |                |     |     |      |
|-------------------------------------------------------------------------------------------------------------------|---------------------------------------------------|-----------------------------------------------------|--------------------------|-----------------|--------------------------------------------------|-----|-----|---------------|-----|-----|----------------|-----|-----|------|
| PARAMETER                                                                                                         |                                                   | TEST CONDITIONS                                     |                          | V <sub>CC</sub> | Operating free-air temperature (T <sub>A</sub> ) |     |     |               |     |     |                |     |     | UNIT |
|                                                                                                                   |                                                   |                                                     |                          |                 | 25°C                                             |     |     | –40°C to 85°C |     |     | –55°C to 125°C |     |     |      |
|                                                                                                                   |                                                   |                                                     |                          |                 | MIN                                              | TYP | MAX | MIN           | TYP | MAX | MIN            | TYP | MAX |      |
| V <sub>OH</sub>                                                                                                   | High-level output voltage                         | V <sub>I</sub> = V <sub>IH</sub> or V <sub>IL</sub> | I <sub>OH</sub> = –20 μA | 4.5 V           | 4.4                                              |     |     | 4.4           |     |     | 4.4            |     |     | V    |
|                                                                                                                   |                                                   |                                                     | I <sub>OH</sub> = –4 mA  | 4.5 V           | 3.98                                             |     |     | 3.84          |     |     | 3.7            |     |     |      |
| V <sub>OL</sub>                                                                                                   | Low-level output voltage                          | V <sub>I</sub> = V <sub>IH</sub> or V <sub>IL</sub> | I <sub>OL</sub> = 20 μA  | 4.5 V           | 0.1                                              |     |     | 0.1           |     |     | 0.1            |     |     | V    |
|                                                                                                                   |                                                   |                                                     | I <sub>OL</sub> = 4 mA   | 4.5 V           | 0.26                                             |     |     | 0.33          |     |     | 0.4            |     |     |      |
| I <sub>I</sub>                                                                                                    | Input leakage current                             | V <sub>I</sub> = V <sub>CC</sub> and GND            | I <sub>O</sub> = 0       | 5.5 V           | ±0.1                                             |     |     | ±1            |     |     | ±1             |     |     | μA   |
| I <sub>CC</sub>                                                                                                   | Supply current                                    | V <sub>I</sub> = V <sub>CC</sub> or GND             | I <sub>O</sub> = 0       | 5.5 V           | 2                                                |     |     | 20            |     |     | 40             |     |     | μA   |
| ΔI <sub>CC</sub><br>(1)                                                                                           | Additional Quiescent Device Current Per Input Pin | V <sub>I</sub> = V <sub>CC</sub> – 2.1              |                          | 4.5 V to 5.5 V  | 100 360                                          |     |     | 450           |     |     | 490            |     |     | μA   |
| C <sub>i</sub>                                                                                                    | Input capacitance                                 |                                                     |                          | 5 V             | 10                                               |     |     | 10            |     |     | 10             |     |     | pF   |

(1) For dual-supply systems theoretical worst case ( $V_I = 2.4\ \text{V}$ ,  $V_{CC} = 5.5\ \text{V}$ ) specification is 1.8 mA.

## 5.6 Switching Characteristics

over operating free-air temperature range; typical values measured at  $T_A = 25^\circ\text{C}$  (unless otherwise noted).

| PARAMETER                         | FROM   | TO | TEST<br>CONDITIO<br>NS | V <sub>CC</sub> | Operating free-air temperature (T <sub>A</sub> ) |     |     |               |     |     |                |     |     | UNIT |
|-----------------------------------|--------|----|------------------------|-----------------|--------------------------------------------------|-----|-----|---------------|-----|-----|----------------|-----|-----|------|
|                                   |        |    |                        |                 | 25°C                                             |     |     | −40°C to 85°C |     |     | −55°C to 125°C |     |     |      |
|                                   |        |    |                        |                 | MIN                                              | TYP | MAX | MIN           | TYP | MAX | MIN            | TYP | MAX |      |
| t <sub>pd</sub> Propagation delay | A or B | Y  | C <sub>L</sub> = 50 pF | 4.5 V           | 25                                               |     |     | 31            |     |     | 38             |     |     | ns   |
|                                   | A or B | Y  | C <sub>L</sub> = 15 pF | 5 V             | 10                                               |     |     |               |     |     |                |     |     |      |
| t <sub>t</sub> Transition-time    |        | Y  | C <sub>L</sub> = 50 pF | 4.5 V           | 15                                               |     |     | 19            |     |     | 22             |     |     | ns   |


## 5.7 Operating Characteristics

over operating free-air temperature range; typical values measured at  $T_A = 25^\circ\text{C}$  (unless otherwise noted).


| PARAMETER                                       | TEST CONDITIONS | $V_{CC}$ | MIN | TYP | MAX | UNIT |
|-------------------------------------------------|-----------------|----------|-----|-----|-----|------|
| $C_{pd}$ Power dissipation capacitance per gate | No load         | 5 V      |     | 51  |     | pF   |

## 5.8 Typical Characteristics

$T_A = 25^\circ\text{C}$




**Figure 5-1. Typical output voltage in the high state ( $V_{OH}$ )**



**Figure 5-2. Typical output voltage in the low state ( $V_{OL}$ )**


## 6 Parameter Measurement Information

- Phase relationships between waveforms were chosen arbitrarily. All input pulses are supplied by generators having the following characteristics:  $PRR \leq 1 \text{ MHz}$ ,  $Z_O = 50 \Omega$ ,  $t_t < 6 \text{ ns}$ .
- The outputs are measured one at a time, with one input transition per measurement.




A.  $C_L = 50 \text{ pF}$  and includes probe and jig capacitance.

**Figure 6-1. Load Circuit**



A.  $t_t$  is the greater of  $t_r$  and  $t_f$ .

**Figure 6-2. Voltage Waveforms Transition Times**



A. The maximum between  $t_{PLH}$  and  $t_{PHL}$  is used for  $t_{pd}$ .


**Figure 6-3. Voltage Waveforms Propagation Delays**

## 7 Detailed Description

### 7.1 Overview

This device contains four independent 2-input AND gates. Each gate performs the Boolean function  $Y = A \bullet B$  in positive logic.

### 7.2 Functional Block Diagram



### 7.3 Feature Description

#### 7.3.1 Balanced CMOS Push-Pull Outputs

A balanced output allows the device to sink and source similar currents. The drive capability of this device may create fast edges into light loads so routing and load conditions should be considered to prevent ringing. Additionally, the outputs of this device are capable of driving larger currents than the device can sustain without being damaged. It is important for the output power of the device to be limited to avoid damage due to over-current. The electrical and thermal limits defined in the [Section 5.1](#) must be followed at all times.

The CD74HCT08 can drive a load with a total capacitance less than or equal to the maximum load listed in the [Section 5.6](#) connected to a high-impedance CMOS input while still meeting all of the datasheet specifications. Larger capacitive loads can be applied, however it is not recommended to exceed the provided load value. If larger capacitive loads are required, it is recommended to add a series resistor between the output and the capacitor to limit output current to the values given in the [Section 5.1](#).

#### 7.3.2 TTL-Compatible CMOS Inputs

TTL-Compatible CMOS inputs are high impedance and are typically modeled as a resistor from the input to ground in parallel with the input capacitance given in the [Section 5.5](#). The worst case resistance is calculated with the maximum input voltage, given in the [Section 5.1](#), and the maximum input leakage current, given in the [Section 5.5](#), using ohm's law ( $R = V \div I$ ).

Signals applied to the inputs need to have fast edge rates, as defined by  $\Delta t/\Delta v$  in the [Section 5.3](#) to avoid excessive current consumption and oscillations. If a slow or noisy input signal is required, a device with a Schmitt-trigger input should be used to condition the input signal prior to the TTL-compatible CMOS input.


TTL-Compatible CMOS inputs have a lower threshold voltage than standard CMOS inputs to allow for compatibility with older bipolar logic devices. See the [Section 5.3](#) for the valid input voltages for the CD74HCT08.

### 7.3.3 Clamp Diode Structure

The inputs and outputs to this device have both positive and negative clamping diodes as depicted in [Figure 7-1](#).

#### CAUTION

Voltages beyond the values specified in the [Section 5.1](#) table can cause damage to the device. The recommended input and output voltage ratings may be exceeded if the input and output clamp-current ratings are observed.



**Figure 7-1. Electrical Placement of Clamping Diodes for Each Input and Output**

## 7.4 Device Functional Modes

**Table 7-1. Function Table**

| INPUTS <sup>(1)</sup> |   | OUTPUT <sup>(2)</sup> |
|-----------------------|---|-----------------------|
| A                     | B | Y                     |
| H                     | H | H                     |
| L                     | X | L                     |
| X                     | L | L                     |

(1) H = High Voltage Level, L = Low Voltage Level, X = Don't Care

(2) H = Driving High, L = Driving Low, Z = High Impedance State

## 8 Application and Implementation

### Note

Information in the following applications sections is not part of the TI component specification, and TI does not warrant its accuracy or completeness. TI's customers are responsible for determining suitability of components for their purposes, as well as validating and testing their design implementation to confirm system functionality.

### 8.1 Application Information

In this application, three 2-input AND gates are combined to produce a 4-input AND gate function as shown in [Figure 8-1](#). The fourth gate can be used for another application in the system, or the inputs can be grounded and the channel left unused.

This device is used to directly control the RESET pin of a motor controller. The controller requires four input signals to all be HIGH before being enabled, and should be disabled in the event that any one signal goes LOW. The 4-input AND gate function combines the four individual reset signals into a single active-low reset signal.

### 8.2 Typical Application




Figure 8-1. Typical application schematic

#### 8.2.1 Design Requirements

##### 8.2.1.1 Power Considerations

Ensure the desired supply voltage is within the range specified in the [Section 5.3](#). The supply voltage sets the device's electrical characteristics as described in the [Section 5.5](#).

The supply must be capable of sourcing current equal to the total current to be sourced by all outputs of the CD74HCT08 plus the maximum supply current,  $I_{CC}$ , listed in the [Section 5.5](#). The logic device can only source or sink as much current as it is provided at the supply and ground pins, respectively. Be sure not to exceed the maximum total current through GND or  $V_{CC}$  listed in the [Section 5.1](#).

Total power consumption can be calculated using the information provided in [CMOS Power Consumption and  \$C\_{pd}\$  Calculation](#).

Thermal increase can be calculated using the information provided in [Thermal Characteristics of Standard Linear and Logic \(SLL\) Packages and Devices](#).

### CAUTION

The maximum junction temperature,  $T_J(\text{max})$  listed in the [Section 5.1](#), is an *additional limitation* to prevent damage to the device. Do not violate any values listed in the [Section 5.1](#). These limits are provided to prevent damage to the device.

### 8.2.1.2 Input Considerations

Unused inputs must be terminated to either  $V_{CC}$  or ground. These can be directly terminated if the input is completely unused, or they can be connected with a pull-up or pull-down resistor if the input is to be used sometimes, but not always. A pull-up resistor is used for a default state of HIGH, and a pull-down resistor is used for a default state of LOW. The resistor size is limited by drive current of the controller, leakage current into the CD74HCT08, as specified in the [Section 5.5](#), and the desired input transition rate. A 10-k $\Omega$  resistor value is often used due to these factors.

Refer to the [Section 7.3](#) for additional information regarding the inputs for this device.

### 8.2.1.3 Output Considerations

The positive supply voltage is used to produce the output HIGH voltage. Drawing current from the output will decrease the output voltage as specified by the  $V_{OH}$  specification in the [Section 5.5](#). Similarly, the ground voltage is used to produce the output LOW voltage. Sinking current into the output will increase the output voltage as specified by the  $V_{OL}$  specification in the [Section 5.5](#).


Unused outputs can be left floating. Do not connect outputs directly to  $V_{CC}$  or ground.

Refer to [Section 7.3](#) for additional information regarding the outputs for this device.

## 8.2.2 Detailed Design Procedure

1. Add a decoupling capacitor from  $V_{CC}$  to GND. The capacitor needs to be placed physically close to the device and electrically close to both the  $V_{CC}$  and GND pins. An example layout is shown in the [Section 8.4](#).
2. Ensure the capacitive load at the output is  $\leq 70$  pF. This is not a hard limit, however it will ensure optimal performance. This can be accomplished by providing short, appropriately sized traces from the CD74HCT08 to the receiving device.
3. Ensure the resistive load at the output is larger than  $(V_{CC} / I_{O(max)}) \Omega$ . This will ensure that the maximum output current from the [Section 5.1](#) is not violated. Most CMOS inputs have a resistive load measured in megaohms; much larger than the minimum calculated above.
4. Thermal issues are rarely a concern for logic gates, however the power consumption and thermal increase can be calculated using the steps provided in the application report, [CMOS Power Consumption and Cpd Calculation](#)

### 8.2.3 Application Curves



**Figure 8-2. Typical application timing diagram**

## 8.3 Power Supply Recommendations

The power supply can be any voltage between the minimum and maximum supply voltage rating located in the [Section 5.3](#). Each  $V_{CC}$  terminal should have a bypass capacitor to prevent power disturbance. A 0.1- $\mu$ F capacitor is recommended for this device. It is acceptable to parallel multiple bypass caps to reject different frequencies of noise. The 0.1- $\mu$ F and 1- $\mu$ F capacitors are commonly used in parallel. The bypass capacitor should be installed as close to the power terminal as possible for best results, as shown in [Figure 8-3](#).

## 8.4 Layout

### 8.4.1 Layout Guidelines

When using multiple-input and multiple-channel logic devices inputs must not ever be left floating. In many cases, functions or parts of functions of digital logic devices are unused; for example, when only two inputs of a triple-input AND gate are used. Such unused input pins must not be left unconnected because the undefined voltages at the outside connections result in undefined operational states. All unused inputs of digital logic devices must be connected to a logic high or logic low voltage, as defined by the input voltage specifications, to prevent them from floating. The logic level that must be applied to any particular unused input depends on the function of the device. Generally, the inputs are tied to GND or  $V_{CC}$ , whichever makes more sense for the logic function or is more convenient.

### 8.4.2 Layout Example




Figure 8-3. Example layout for the CD74HCT08

## 9 Device and Documentation Support

### 9.1 Documentation Support

#### 9.1.1 Related Documentation

For related documentation see the following:

- [HCMOS Design Considerations](#)
- [CMOS Power Consumption and CPD Calculation](#)
- [Designing with Logic](#)

### 9.2 Receiving Notification of Documentation Updates

To receive notification of documentation updates, navigate to the device product folder on [ti.com](https://www.ti.com). Click on *Notifications* to register and receive a weekly digest of any product information that has changed. For change details, review the revision history included in any revised document.

### 9.3 Support Resources

[TI E2E™ support forums](#) are an engineer's go-to source for fast, verified answers and design help — straight from the experts. Search existing answers or ask your own question to get the quick design help you need.

Linked content is provided "AS IS" by the respective contributors. They do not constitute TI specifications and do not necessarily reflect TI's views; see TI's [Terms of Use](#).

### 9.4 Trademarks

TI E2E™ is a trademark of Texas Instruments.  
All trademarks are the property of their respective owners.

### 9.5 Electrostatic Discharge Caution



This integrated circuit can be damaged by ESD. Texas Instruments recommends that all integrated circuits be handled with appropriate precautions. Failure to observe proper handling and installation procedures can cause damage.

ESD damage can range from subtle performance degradation to complete device failure. Precision integrated circuits may be more susceptible to damage because very small parametric changes could cause the device not to meet its published specifications.

### 9.6 Glossary

[TI Glossary](#) This glossary lists and explains terms, acronyms, and definitions.

## 10 Revision History

NOTE: Page numbers for previous revisions may differ from page numbers in the current version.

| Changes from Revision * (August 2019) to Revision A (August 2024)                                                                                            | Page |
|--------------------------------------------------------------------------------------------------------------------------------------------------------------|------|
| • Updated the numbering, formatting, tables, figures, and cross-references throughout the document to reflect modern data sheet standards.....               | 1    |
| • Added package size to <i>Device Information</i> table.....                                                                                                 | 1    |
| • Updated RθJA values: D = 100.1 to 138.7, N = 63.4 to 103.8; Updated D and N packages for RθJC(top), RθJB, ΨJT, ΨJB, and RθJC(bot), all values in °C/W..... | 4    |

## 11 Mechanical, Packaging, and Orderable Information

The following pages include mechanical, packaging, and orderable information. This information is the most current data available for the designated devices. This data is subject to change without notice and revision of this document. For browser-based versions of this data sheet, refer to the left-hand navigation.

## PACKAGING INFORMATION

| Orderable part number          | Status<br>(1) | Material type<br>(2) | Package   Pins | Package qty   Carrier | RoHS<br>(3) | Lead finish/<br>Ball material<br>(4) | MSL rating/<br>Peak reflow<br>(5) | Op temp (°C) | Part marking<br>(6)            |
|--------------------------------|---------------|----------------------|----------------|-----------------------|-------------|--------------------------------------|-----------------------------------|--------------|--------------------------------|
| <a href="#">5962-8688301CA</a> | Active        | Production           | CDIP (J)   14  | 25   TUBE             | No          | SNPB                                 | N/A for Pkg Type                  | -55 to 125   | 5962-8688301CA<br>CD54HCT08F3A |
| <a href="#">CD54HCT08F</a>     | Active        | Production           | CDIP (J)   14  | 25   TUBE             | No          | SNPB                                 | N/A for Pkg Type                  | -55 to 125   | CD54HCT08F                     |
| CD54HCT08F.A                   | Active        | Production           | CDIP (J)   14  | 25   TUBE             | No          | SNPB                                 | N/A for Pkg Type                  | -55 to 125   | CD54HCT08F                     |
| <a href="#">CD54HCT08F3A</a>   | Active        | Production           | CDIP (J)   14  | 25   TUBE             | No          | SNPB                                 | N/A for Pkg Type                  | -55 to 125   | 5962-8688301CA<br>CD54HCT08F3A |
| CD54HCT08F3A.A                 | Active        | Production           | CDIP (J)   14  | 25   TUBE             | No          | SNPB                                 | N/A for Pkg Type                  | -55 to 125   | 5962-8688301CA<br>CD54HCT08F3A |
| <a href="#">CD74HCT08E</a>     | Active        | Production           | PDIP (N)   14  | 25   TUBE             | Yes         | NIPDAU                               | N/A for Pkg Type                  | -55 to 125   | CD74HCT08E                     |
| CD74HCT08E.A                   | Active        | Production           | PDIP (N)   14  | 25   TUBE             | Yes         | NIPDAU                               | N/A for Pkg Type                  | -55 to 125   | CD74HCT08E                     |
| <a href="#">CD74HCT08M</a>     | Obsolete      | Production           | SOIC (D)   14  | -                     | -           | Call TI                              | Call TI                           | -55 to 125   | HCT08M                         |
| <a href="#">CD74HCT08M96</a>   | Active        | Production           | SOIC (D)   14  | 2500   LARGE T&R      | Yes         | NIPDAU   SN                          | Level-1-260C-UNLIM                | -55 to 125   | HCT08M                         |
| CD74HCT08M96.A                 | Active        | Production           | SOIC (D)   14  | 2500   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -55 to 125   | HCT08M                         |

<sup>(1)</sup> **Status:** For more details on status, see our [product life cycle](#).

<sup>(2)</sup> **Material type:** When designated, preproduction parts are prototypes/experimental devices, and are not yet approved or released for full production. Testing and final process, including without limitation quality assurance, reliability performance testing, and/or process qualification, may not yet be complete, and this item is subject to further changes or possible discontinuation. If available for ordering, purchases will be subject to an additional waiver at checkout, and are intended for early internal evaluation purposes only. These items are sold without warranties of any kind.

<sup>(3)</sup> **RoHS values:** Yes, No, RoHS Exempt. See the [TI RoHS Statement](#) for additional information and value definition.

<sup>(4)</sup> **Lead finish/Ball material:** Parts may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead finish/Ball material values may wrap to two lines if the finish value exceeds the maximum column width.

<sup>(5)</sup> **MSL rating/Peak reflow:** The moisture sensitivity level ratings and peak solder (reflow) temperatures. In the event that a part has multiple moisture sensitivity ratings, only the lowest level per JEDEC standards is shown. Refer to the shipping label for the actual reflow temperature that will be used to mount the part to the printed circuit board.

<sup>(6)</sup> **Part marking:** There may be an additional marking, which relates to the logo, the lot trace code information, or the environmental category of the part.

Multiple part markings will be inside parentheses. Only one part marking contained in parentheses and separated by a "~" will appear on a part. If a line is indented then it is a continuation of the previous line and the two combined represent the entire part marking for that device.

**Important Information and Disclaimer:** The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.

**OTHER QUALIFIED VERSIONS OF CD54HCT08, CD74HCT08 :**

- Catalog : [CD74HCT08](#)
- Military : [CD54HCT08](#)

NOTE: Qualified Version Definitions:

- Catalog - TI's standard catalog product
- Military - QML certified for Military and Defense Applications

**D0014A****PACKAGE OUTLINE****SOIC - 1.75 mm max height**

SMALL OUTLINE INTEGRATED CIRCUIT



4220718/A 09/2016


**NOTES:**

1. All linear dimensions are in millimeters. Dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.
2. This drawing is subject to change without notice.
3. This dimension does not include mold flash, protrusions, or gate burrs. Mold flash, protrusions, or gate burrs shall not exceed 0.15 mm, per side.
4. This dimension does not include interlead flash. Interlead flash shall not exceed 0.43 mm, per side.
5. Reference JEDEC registration MS-012, variation AB.



**D0014A**

**SOIC - 1.75 mm max height**

## SMALL OUTLINE INTEGRATED CIRCUIT



LAND PATTERN EXAMPLE  
SCALE:8X



## SOLDER MASK DETAILS

4220718/A 09/2016

NOTES: (continued)

6. Publication IPC-7351 may have alternate designs.

7. Solder mask tolerances between and around signal pads can vary based on board fabrication site.

## EXAMPLE STENCIL DESIGN

D0014A

SOIC - 1.75 mm max height

SMALL OUTLINE INTEGRATED CIRCUIT



SOLDER PASTE EXAMPLE  
BASED ON 0.125 mm THICK STENCIL  
SCALE:8X

4220718/A 09/2016

NOTES: (continued)

8. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.
9. Board assembly site may have different recommendations for stencil design.

**J 14**

## GENERIC PACKAGE VIEW

**CDIP - 5.08 mm max height**

CERAMIC DUAL IN LINE PACKAGE



Images above are just a representation of the package family, actual package may vary.  
Refer to the product data sheet for package details.

4040083-5/G

**J0014A****PACKAGE OUTLINE****CDIP - 5.08 mm max height**

CERAMIC DUAL IN LINE PACKAGE



4214771/A 05/2017

**NOTES:**

1. All controlling linear dimensions are in inches. Dimensions in brackets are in millimeters. Any dimension in brackets or parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.
2. This drawing is subject to change without notice.
3. This package is hermetically sealed with a ceramic lid using glass frit.
4. Index point is provided on cap for terminal identification only and on press ceramic glass frit seal only.
5. Falls within MIL-STD-1835 and GDIP1-T14.

# EXAMPLE BOARD LAYOUT

J0014A

CDIP - 5.08 mm max height

CERAMIC DUAL IN LINE PACKAGE



LAND PATTERN EXAMPLE  
NON-SOLDER MASK DEFINED  
SCALE: 5X



4214771/A 05/2017

N (R-PDIP-T\*\*)

16 PINS SHOWN

## PLASTIC DUAL-IN-LINE PACKAGE



| PINS **<br>DIM      | 14               | 16               | 18               | 20               |
|---------------------|------------------|------------------|------------------|------------------|
| A MAX               | 0.775<br>(19,69) | 0.775<br>(19,69) | 0.920<br>(23,37) | 1.060<br>(26,92) |
| A MIN               | 0.745<br>(18,92) | 0.745<br>(18,92) | 0.850<br>(21,59) | 0.940<br>(23,88) |
| MS-001<br>VARIATION | AA               | BB               | AC               | AD               |



4040049/E 12/2002

NOTES:

- A. All linear dimensions are in inches (millimeters).  
B. This drawing is subject to change without notice.
-  Falls within JEDEC MS-001, except 18 and 20 pin minimum body length (Dim A).  
 The 20 pin end lead shoulder width is a vendor option, either half or full width.

## IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATASHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, regulatory or other requirements.

These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you fully indemnify TI and its representatives against any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to [TI's Terms of Sale](#), [TI's General Quality Guidelines](#), or other applicable terms available either on [ti.com](https://www.ti.com) or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products. Unless TI explicitly designates a product as custom or customer-specified, TI products are standard, catalog, general purpose devices.

TI objects to and rejects any additional or different terms you may propose.

Copyright © 2026, Texas Instruments Incorporated

Last updated 10/2025