

# MC1488, SN55188, SN75188 QUADRUPLE LINE DRIVERS

SLLS094C – SEPTEMBER 1983 – REVISED MAY 2004


- Meet or Exceed the Requirements of ANSI TIA/EIA-232-E and ITU Recommendation V.28
- Current-Limited Output: 10 mA Typical
- Power-Off Output Impedance: 300  $\Omega$  Minimum
- Slew Rate Control by Load Capacitor
- Flexible Supply-Voltage Range
- Input Compatible With Most TTL Circuits

## description/ordering information


The MC1488, SN55188, and SN75188 are monolithic quadruple line drivers designed to interface data terminal equipment with data communications equipment in conformance with ANSI TIA/EIA-232-E, using a diode in series with each supply-voltage terminal as shown under typical applications.

The SN55188 is characterized for operation over the full military temperature range of  $-55^{\circ}\text{C}$  to  $125^{\circ}\text{C}$ . The MC1488 and SN75188 are characterized for operation from  $0^{\circ}\text{C}$  to  $70^{\circ}\text{C}$ .

SN55188 . . . J OR W PACKAGE  
SN75188 . . . D, N, OR NS PACKAGE  
MC1488 . . . N PACKAGE  
(TOP VIEW)



SN55188 . . . FK PACKAGE  
(TOP VIEW)



NC – No internal connection

## ORDERING INFORMATION

| T <sub>A</sub>                                 | PACKAGE <sup>†</sup> |              | ORDERABLE PART NUMBER | TOP-SIDE MARKING |
|------------------------------------------------|----------------------|--------------|-----------------------|------------------|
| 0°C to 70°C                                    | PDIP (N)             | Tube of 25   | MC1488N               | MC1488N          |
|                                                |                      | Tube of 25   | SN75188N              | SN75188N         |
|                                                | SOIC (D)             | Tube of 50   | SN75188D              | SN75188          |
|                                                |                      | Reel of 2500 | SN75188DR             |                  |
|                                                | SOP (NS)             | Reel of 2000 | SN75188NSR            | SN75188          |
| $-55^{\circ}\text{C}$ to $125^{\circ}\text{C}$ | CDIP (J)             | Tube of 25   | SN55188J              | SN55188J         |
|                                                |                      |              | SNJ55188J             | SNJ55188J        |
|                                                | CFP (W)              | Tube of 150  | SNJ55188W             | SNJ55188W        |
|                                                | LCCC (FK)            | Tube of 55   | SNJ55188FK            | SNJ55188FK       |

<sup>†</sup> Package drawings, standard packing quantities, thermal data, symbolization, and PCB design guidelines are available at [www.ti.com/sc/package](http://www.ti.com/sc/package).



Please be aware that an important notice concerning availability, standard warranty, and use in critical applications of Texas Instruments semiconductor products and disclaimers thereto appears at the end of this data sheet.

PRODUCTION DATA information is current as of publication date. Products conform to specifications per the terms of Texas Instruments standard warranty. Production processing does not necessarily include testing of all parameters.

**TEXAS  
INSTRUMENTS**

POST OFFICE BOX 655303 • DALLAS, TEXAS 75265

Copyright © 2004, Texas Instruments Incorporated  
On products compliant to MIL-PRF-38535, all parameters are tested unless otherwise noted. On all other products, production processing does not necessarily include testing of all parameters.

MC1488, SN55188, SN75188  
QUADRUPLE LINE DRIVERS


SLLS094C – SEPTEMBER 1983 – REVISED MAY 2004

FUNCTION TABLE  
(drivers 2–4)

| A | B | Y |
|---|---|---|
| H | H | L |
| L | X | H |
| X | L | H |


H = high level, L = low level,  
X = irrelevant

logic diagram (positive logic)



Positive logic  
 $Y = \overline{A}$  (driver 1)  
 $Y = AB$  or  $\overline{A} + \overline{B}$  (drivers 2 thru 4)

schematic (each driver)



Resistor values shown are nominal.

**absolute maximum ratings over operating free-air temperature (unless otherwise noted)<sup>†</sup>**

|                                                                                       |                              |
|---------------------------------------------------------------------------------------|------------------------------|
| Supply voltage, $V_{CC+}$ at (or below) 25°C free-air temperature (see Notes 1 and 2) | 15 V                         |
| Supply voltage, $V_{CC-}$ at (or below) 25°C free-air temperature (see Notes 1 and 2) | –15 V                        |
| Input voltage, $V_I$                                                                  | –15 V to 7 V                 |
| Output voltage, $V_O$                                                                 | –15 V to 15 V                |
| Continuous total power dissipation (see Note 2)                                       | See Dissipation Rating Table |
| Package thermal impedance, $\theta_{JA}$ (see Notes 3 and 4): D package               | 86°C/W                       |
| N package                                                                             | 80°C/W                       |
| NS package                                                                            | 76°C/W                       |
| Operating virtual junction temperature, $T_J$                                         | 150°C                        |
| Case temperature for 60 seconds, FK package                                           | 260°C                        |
| Lead temperature 1,6 mm (1/16 inch) from case for 60 seconds: J or W package          | 300°C                        |
| Storage temperature range, $T_{Stg}$                                                  | –65°C to 150°C               |

<sup>†</sup> Stresses beyond those listed under “absolute maximum ratings” may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated under “recommended operating conditions” is not implied. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability.

- NOTES:
1. All voltage values are with respect to the network ground terminal.
  2. For operation above 25°C free-air temperature, refer to the maximum supply voltage curve, Figure 6. In the J package, SN55188 chips are alloy mounted.
  3. Maximum power dissipation is a function of  $T_J(\text{max})$ ,  $\theta_{JA}$ , and  $T_A$ . The maximum allowable power dissipation at any allowable ambient temperature is  $P_D = (T_J(\text{max}) - T_A)/\theta_{JA}$ . Selecting the maximum of 150°C can affect reliability.
  4. The package thermal impedance is calculated in accordance with JESD 51-7.

**DISSIPATION RATING TABLE**

| PACKAGE | $T_A \leq 25^\circ\text{C}$<br>POWER RATING | DERATING FACTOR<br>ABOVE $T_A = 25^\circ\text{C}$ | $T_A = 70^\circ\text{C}$<br>POWER RATING | $T_A = 125^\circ\text{C}$<br>POWER RATING |
|---------|---------------------------------------------|---------------------------------------------------|------------------------------------------|-------------------------------------------|
| FK      | 1375 mW                                     | 11.0 mW/°C                                        | 880 mW                                   | 275 mW                                    |
| J       | 1375 mW                                     | 11.0 mW/°C                                        | 880 mW                                   | 275 mW                                    |
| W       | 1000 mW                                     | 8.0 mW/°C                                         | 640 mW                                   | 200 mW                                    |

**recommended operating conditions**

|           |                                | SN55188 |     |     | MC1488, SN75188 |     |     | UNIT |
|-----------|--------------------------------|---------|-----|-----|-----------------|-----|-----|------|
|           |                                | MIN     | NOM | MAX | MIN             | NOM | MAX |      |
| $V_{CC+}$ | Supply voltage                 | 7.5     | 9   | 15  | 7.5             | 9   | 15  | V    |
| $V_{CC-}$ | Supply voltage                 | –7.5    | –9  | –15 | –7.5            | –9  | –15 | V    |
| $V_{IH}$  | High-level input voltage       | 1.9     |     |     | 1.9             |     |     | V    |
| $V_{IL}$  | Low-level input voltage        |         |     | 0.8 |                 |     | 0.8 | V    |
| $T_A$     | Operating free-air temperature | –55     |     | 125 | 0               |     | 70  | °C   |

# MC1488, SN55188, SN75188 QUADRUPLE LINE DRIVERS

SLLS094C – SEPTEMBER 1983 – REVISED MAY 2004

electrical characteristics over operating free-air temperature range,  $V_{CC\pm} = \pm 9\text{ V}$  (unless otherwise noted)

| PARAMETER                                               | TEST CONDITIONS                                                          |                                                           | SN55188 |        |       | MC1488, SN75188 |       |        | UNIT          |
|---------------------------------------------------------|--------------------------------------------------------------------------|-----------------------------------------------------------|---------|--------|-------|-----------------|-------|--------|---------------|
|                                                         |                                                                          |                                                           | MIN     | TYP†   | MAX   | MIN             | TYP†  | MAX    |               |
| $V_{OH}$ High-level output voltage                      | $V_{IL} = 0.8\text{ V}$ ,<br>$R_L = 3\text{ k}\Omega$                    | $V_{CC+} = 9\text{ V}$ ,<br>$V_{CC-} = -9\text{ V}$       | 6       | 7      |       | 6               | 7     |        | V             |
|                                                         |                                                                          | $V_{CC+} = 13.2\text{ V}$ ,<br>$V_{CC-} = -13.2\text{ V}$ | 9       | 10.5   |       | 9               | 10.5  |        |               |
| $V_{OL}$ Low-level output voltage                       | $V_{IH} = 1.9\text{ V}$ ,<br>$R_L = 3\text{ k}\Omega$                    | $V_{CC+} = 9\text{ V}$ ,<br>$V_{CC-} = -9\text{ V}$       |         | -7‡    | -6    |                 | -7    | -6     | V             |
|                                                         |                                                                          | $V_{CC+} = 13.2\text{ V}$ ,<br>$V_{CC-} = -13.2\text{ V}$ |         | -10.5‡ | -9    |                 | -10.5 | -9     |               |
| $I_{IH}$ High-level input current                       | $V_I = 5\text{ V}$                                                       |                                                           |         |        | 10    |                 |       | 10     | $\mu\text{A}$ |
| $I_{IL}$ Low-level input current                        | $V_I = 0$                                                                |                                                           |         | -1     | -1.6  |                 | -1    | -1.6   | mA            |
| $I_{OS(H)}$ Short-circuit output current at high level§ | $V_I = 0.8\text{ V}$                                                     | $V_O = 0$                                                 | -4.6    | -9     | -13.5 | -6              | -9    | -12    | mA            |
| $I_{OS(L)}$ Short-circuit output current at low level§  | $V_I = 1.9\text{ V}$                                                     | $V_O = 0$                                                 | 4.6     | 9      | 13.5  | 6               | 9     | 12     | mA            |
| $r_o$ Output resistance, power off                      | $V_{CC+} = 0$ ,<br>$V_{CC-} = 0$ ,<br>$V_O = -2\text{ V to } 2\text{ V}$ |                                                           | 300     |        |       | 300             |       |        | $\Omega$      |
| $I_{CC+}$ Supply current from $V_{CC+}$                 | $V_{CC+} = 9\text{ V}$ ,<br>No load                                      | All inputs at 1.9 V                                       |         | 15     | 20    |                 | 15    | 20     | mA            |
|                                                         |                                                                          | All inputs at 0.8 V                                       |         | 4.5    | 6     |                 | 4.5   | 6      |               |
|                                                         | $V_{CC+} = 12\text{ V}$ ,<br>No load                                     | All inputs at 1.9 V                                       |         | 19     | 25    |                 | 19    | 25     |               |
|                                                         |                                                                          | All inputs at 0.8 V                                       |         | 5.5    | 7     |                 | 5.5   | 7      |               |
|                                                         | $V_{CC+} = 15\text{ V}$ ,<br>No load, $T_A = 25^\circ\text{C}$           | All inputs at 1.9 V                                       |         | 34     |       |                 | 34    |        |               |
|                                                         |                                                                          | All inputs at 0.8 V                                       |         | 12     |       |                 | 12    |        |               |
| $I_{CC-}$ Supply current from $I_{CC-}$                 | $V_{CC-} = -9\text{ V}$ ,<br>No load                                     | All inputs at 1.9 V                                       |         | -13    | -17   |                 | -13   | -17    | mA            |
|                                                         |                                                                          | All inputs at 0.8 V                                       |         |        | -0.5  |                 |       | -0.015 |               |
|                                                         | $V_{CC-} = -12\text{ V}$ ,<br>No load                                    | All inputs at 1.9 V                                       |         | -18    | -23   |                 | -18   | -23    |               |
|                                                         |                                                                          | All inputs at 0.8 V                                       |         |        | -0.5  |                 |       | -0.015 |               |
|                                                         | $V_{CC-} = -15\text{ V}$ ,<br>No load, $T_A = 25^\circ\text{C}$          | All inputs at 1.9 V                                       |         | -34    |       |                 | -34   |        |               |
|                                                         |                                                                          | All inputs at 0.8 V                                       |         | -2.5   |       |                 | -2.5  |        |               |
| $P_D$ Total power dissipation                           | $V_{CC+} = 9\text{ V}$ ,<br>No load, $V_{CC-} = -9\text{ V}$             |                                                           |         |        | 333   |                 |       | 333    | mW            |
|                                                         | $V_{CC+} = 12\text{ V}$ ,<br>No load, $V_{CC-} = -12\text{ V}$           |                                                           |         |        | 576   |                 |       | 576    |               |

† All typical values are at  $T_A = 25^\circ\text{C}$ .

‡ The algebraic convention, in which the less positive (more negative) limit is designated as minimum, is used in this data sheet for logic voltage levels only, e.g., if  $-6\text{ V}$  is a maximum, the typical value is a more negative voltage.

§ Not more than one output should be shorted at a time.



POST OFFICE BOX 655303 • DALLAS, TEXAS 75265


switching characteristics,  $V_{CC\pm} = \pm 9\text{ V}$ ,  $T_A = 25^\circ\text{C}$

| PARAMETER                                                         | TEST CONDITIONS                                                                            | MIN | TYP | MAX | UNIT          |
|-------------------------------------------------------------------|--------------------------------------------------------------------------------------------|-----|-----|-----|---------------|
| $t_{PLH}$ Propagation delay time, low- to high-level output       | $R_L = 3\text{ k}\Omega$ ,<br>See Figure 1<br>$C_L = 15\text{ pF}$                         |     | 220 | 350 | ns            |
| $t_{PHL}$ Propagation delay time, high- to low-level output       |                                                                                            |     | 100 | 175 | ns            |
| $t_{TLH}$ Transition time, low- to high-level output <sup>†</sup> |                                                                                            |     | 55  | 100 | ns            |
| $t_{THL}$ Transition time, high- to low-level output <sup>†</sup> |                                                                                            |     | 45  | 75  | ns            |
| $t_{TLH}$ Transition time, low- to high-level output <sup>‡</sup> | $R_L = 3\text{ k}\Omega$ to $7\text{ k}\Omega$ ,<br>See Figure 1<br>$C_L = 2500\text{ pF}$ |     | 2.5 |     | $\mu\text{s}$ |
| $t_{THL}$ Transition time, high- to low-level output <sup>‡</sup> |                                                                                            |     | 3.0 |     | $\mu\text{s}$ |

<sup>†</sup> Measured between 10% and 90% points of output waveform

<sup>‡</sup> Measured between 3 V and  $-3\text{ V}$  points on the output waveform (TIA/EIA-232-E conditions)

## PARAMETER MEASUREMENT INFORMATION



- NOTES: A. The pulse generator has the following characteristics:  $t_W = 0.5\text{ }\mu\text{s}$ ,  $\text{PRR} \leq 1\text{ MHz}$ ,  $Z_O = 50\text{ }\Omega$ .  
B.  $C_L$  includes probe and jig capacitance.

Figure 1. Test Circuit and Voltage Waveforms

# TYPICAL CHARACTERISTICS†




Figure 2




Figure 3




Figure 4




Figure 5

† Data for temperatures below 0°C and above 70°C are applicable to SN55188 circuit only.

## THERMAL INFORMATION†




Figure 6

## APPLICATION INFORMATION





Figure 7. Logic Translator Applications



Diodes placed in series with the  $V_{CC+}$  and  $V_{CC-}$  leads protect the SN55188/SN75188 in the fault condition in which the device outputs are shorted to  $\pm 15\text{ V}$ , and the power supplies are at low voltage and provide low-impedance paths to ground.

Figure 8. Power-Supply Protection to Meet  
Power-Off Fault Conditions of  
ANSI TIA/EIA-232-E

**PACKAGING INFORMATION**

| Orderable part number          | Status<br>(1) | Material type<br>(2) | Package   Pins | Package qty   Carrier | RoHS<br>(3) | Lead finish/<br>Ball material<br>(4) | MSL rating/<br>Peak reflow<br>(5) | Op temp (°C) | Part marking<br>(6)                  |
|--------------------------------|---------------|----------------------|----------------|-----------------------|-------------|--------------------------------------|-----------------------------------|--------------|--------------------------------------|
| <a href="#">5962-86889012A</a> | Active        | Production           | LCCC (FK)   20 | 55   TUBE             | No          | SNPB                                 | N/A for Pkg Type                  | -55 to 125   | 5962-<br>86889012A<br>SNJ55<br>188FK |
| <a href="#">5962-8688901CA</a> | Active        | Production           | CDIP (J)   14  | 25   TUBE             | No          | SNPB                                 | N/A for Pkg Type                  | -55 to 125   | 5962-8688901CA<br>SNJ55188J          |
| <a href="#">5962-8688901DA</a> | Active        | Production           | CFP (W)   14   | 25   TUBE             | No          | SNPB                                 | N/A for Pkg Type                  | -55 to 125   | 5962-8688901DA<br>SNJ55188W          |
| <a href="#">MC1488N</a>        | Obsolete      | Production           | PDIP (N)   14  | -                     | -           | Call TI                              | Call TI                           | 0 to 70      | MC1488N                              |
| <a href="#">SN55188J</a>       | Active        | Production           | CDIP (J)   14  | 25   TUBE             | No          | SNPB                                 | N/A for Pkg Type                  | -55 to 125   | SN55188J                             |
| SN55188J.A                     | Active        | Production           | CDIP (J)   14  | 25   TUBE             | No          | SNPB                                 | N/A for Pkg Type                  | -55 to 125   | SN55188J                             |
| <a href="#">SN75188D</a>       | Obsolete      | Production           | SOIC (D)   14  | -                     | -           | Call TI                              | Call TI                           | 0 to 70      | SN75188                              |
| <a href="#">SN75188DR</a>      | Active        | Production           | SOIC (D)   14  | 2500   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | 0 to 70      | SN75188                              |
| SN75188DR.A                    | Active        | Production           | SOIC (D)   14  | 2500   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | 0 to 70      | SN75188                              |
| <a href="#">SN75188N</a>       | Active        | Production           | PDIP (N)   14  | 25   TUBE             | Yes         | NIPDAU                               | N/A for Pkg Type                  | 0 to 70      | SN75188N                             |
| SN75188N.A                     | Active        | Production           | PDIP (N)   14  | 25   TUBE             | Yes         | NIPDAU                               | N/A for Pkg Type                  | 0 to 70      | SN75188N                             |
| <a href="#">SN75188NSR</a>     | Active        | Production           | SOP (NS)   14  | 2000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | 0 to 70      | SN75188                              |
| SN75188NSR.A                   | Active        | Production           | SOP (NS)   14  | 2000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | 0 to 70      | SN75188                              |
| <a href="#">SNJ55188FK</a>     | Active        | Production           | LCCC (FK)   20 | 55   TUBE             | No          | SNPB                                 | N/A for Pkg Type                  | -55 to 125   | 5962-<br>86889012A<br>SNJ55<br>188FK |
| SNJ55188FK.A                   | Active        | Production           | LCCC (FK)   20 | 55   TUBE             | No          | SNPB                                 | N/A for Pkg Type                  | -55 to 125   | 5962-<br>86889012A<br>SNJ55<br>188FK |
| <a href="#">SNJ55188J</a>      | Active        | Production           | CDIP (J)   14  | 25   TUBE             | No          | SNPB                                 | N/A for Pkg Type                  | -55 to 125   | 5962-8688901CA<br>SNJ55188J          |
| SNJ55188J.A                    | Active        | Production           | CDIP (J)   14  | 25   TUBE             | No          | SNPB                                 | N/A for Pkg Type                  | -55 to 125   | 5962-8688901CA<br>SNJ55188J          |
| <a href="#">SNJ55188W</a>      | Active        | Production           | CFP (W)   14   | 25   TUBE             | No          | SNPB                                 | N/A for Pkg Type                  | -55 to 125   | 5962-8688901DA<br>SNJ55188W          |

| Orderable part number | Status<br>(1) | Material type<br>(2) | Package   Pins | Package qty   Carrier | RoHS<br>(3) | Lead finish/<br>Ball material<br>(4) | MSL rating/<br>Peak reflow<br>(5) | Op temp (°C) | Part marking<br>(6)         |
|-----------------------|---------------|----------------------|----------------|-----------------------|-------------|--------------------------------------|-----------------------------------|--------------|-----------------------------|
| SNJ55188W.A           | Active        | Production           | CFP (W)   14   | 25   TUBE             | No          | SNPB                                 | N/A for Pkg Type                  | -55 to 125   | 5962-8688901DA<br>SNJ55188W |

<sup>(1)</sup> **Status:** For more details on status, see our [product life cycle](#).

<sup>(2)</sup> **Material type:** When designated, preproduction parts are prototypes/experimental devices, and are not yet approved or released for full production. Testing and final process, including without limitation quality assurance, reliability performance testing, and/or process qualification, may not yet be complete, and this item is subject to further changes or possible discontinuation. If available for ordering, purchases will be subject to an additional waiver at checkout, and are intended for early internal evaluation purposes only. These items are sold without warranties of any kind.

<sup>(3)</sup> **RoHS values:** Yes, No, RoHS Exempt. See the [TI RoHS Statement](#) for additional information and value definition.

<sup>(4)</sup> **Lead finish/Ball material:** Parts may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead finish/Ball material values may wrap to two lines if the finish value exceeds the maximum column width.

<sup>(5)</sup> **MSL rating/Peak reflow:** The moisture sensitivity level ratings and peak solder (reflow) temperatures. In the event that a part has multiple moisture sensitivity ratings, only the lowest level per JEDEC standards is shown. Refer to the shipping label for the actual reflow temperature that will be used to mount the part to the printed circuit board.

<sup>(6)</sup> **Part marking:** There may be an additional marking, which relates to the logo, the lot trace code information, or the environmental category of the part.

Multiple part markings will be inside parentheses. Only one part marking contained in parentheses and separated by a "-" will appear on a part. If a line is indented then it is a continuation of the previous line and the two combined represent the entire part marking for that device.

**Important Information and Disclaimer:**The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.

## OTHER QUALIFIED VERSIONS OF SN55188, SN75188 :

- Catalog : [SN75188](#)

- Military : [SN55188](#)

NOTE: Qualified Version Definitions:

- Catalog - TI's standard catalog product
- Military - QML certified for Military and Defense Applications

## TAPE AND REEL INFORMATION



\*All dimensions are nominal

| Device     | Package Type | Package Drawing | Pins | SPQ  | Reel Diameter (mm) | Reel Width W1 (mm) | A0 (mm) | B0 (mm) | K0 (mm) | P1 (mm) | W (mm) | Pin1 Quadrant |
|------------|--------------|-----------------|------|------|--------------------|--------------------|---------|---------|---------|---------|--------|---------------|
| SN75188DR  | SOIC         | D               | 14   | 2500 | 330.0              | 16.4               | 6.5     | 9.0     | 2.1     | 8.0     | 16.0   | Q1            |
| SN75188NSR | SOP          | NS              | 14   | 2000 | 330.0              | 16.4               | 8.1     | 10.4    | 2.5     | 12.0    | 16.0   | Q1            |

## TAPE AND REEL BOX DIMENSIONS



\*All dimensions are nominal

| Device     | Package Type | Package Drawing | Pins | SPQ  | Length (mm) | Width (mm) | Height (mm) |
|------------|--------------|-----------------|------|------|-------------|------------|-------------|
| SN75188DR  | SOIC         | D               | 14   | 2500 | 353.0       | 353.0      | 32.0        |
| SN75188NSR | SOP          | NS              | 14   | 2000 | 353.0       | 353.0      | 32.0        |

## TUBE



\*All dimensions are nominal


| Device         | Package Name | Package Type | Pins | SPQ | L (mm) | W (mm) | T (μm) | B (mm) |
|----------------|--------------|--------------|------|-----|--------|--------|--------|--------|
| 5962-86889012A | FK           | LCCC         | 20   | 55  | 506.98 | 12.06  | 2030   | NA     |
| 5962-8688901DA | W            | CFP          | 14   | 25  | 506.98 | 26.16  | 6220   | NA     |
| SN75188N       | N            | PDIP         | 14   | 25  | 506    | 13.97  | 11230  | 4.32   |
| SN75188N       | N            | PDIP         | 14   | 25  | 506    | 13.97  | 11230  | 4.32   |
| SN75188N.A     | N            | PDIP         | 14   | 25  | 506    | 13.97  | 11230  | 4.32   |
| SN75188N.A     | N            | PDIP         | 14   | 25  | 506    | 13.97  | 11230  | 4.32   |
| SNJ55188FK     | FK           | LCCC         | 20   | 55  | 506.98 | 12.06  | 2030   | NA     |
| SNJ55188FK.A   | FK           | LCCC         | 20   | 55  | 506.98 | 12.06  | 2030   | NA     |
| SNJ55188W      | W            | CFP          | 14   | 25  | 506.98 | 26.16  | 6220   | NA     |
| SNJ55188W.A    | W            | CFP          | 14   | 25  | 506.98 | 26.16  | 6220   | NA     |

**D0014A**

## PACKAGE OUTLINE

**SOIC - 1.75 mm max height**

SMALL OUTLINE INTEGRATED CIRCUIT



4220718/A 09/2016

NOTES:

1. All linear dimensions are in millimeters. Dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.
2. This drawing is subject to change without notice.
3. This dimension does not include mold flash, protrusions, or gate burrs. Mold flash, protrusions, or gate burrs shall not exceed 0.15 mm, per side.
4. This dimension does not include interlead flash. Interlead flash shall not exceed 0.43 mm, per side.
5. Reference JEDEC registration MS-012, variation AB.

# EXAMPLE BOARD LAYOUT



D0014A

SOIC - 1.75 mm max height

SMALL OUTLINE INTEGRATED CIRCUIT



LAND PATTERN EXAMPLE  
SCALE:8X



SOLDER MASK DETAILS

4220718/A 09/2016

NOTES: (continued)

6. Publication IPC-7351 may have alternate designs.

7. Solder mask tolerances between and around signal pads can vary based on board fabrication site.

## EXAMPLE STENCIL DESIGN

D0014A

SOIC - 1.75 mm max height

SMALL OUTLINE INTEGRATED CIRCUIT



SOLDER PASTE EXAMPLE  
BASED ON 0.125 mm THICK STENCIL  
SCALE:8X

4220718/A 09/2016

NOTES: (continued)

8. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.
9. Board assembly site may have different recommendations for stencil design.

# MECHANICAL DATA

NS (R-PDSO-G\*\*)

PLASTIC SMALL-OUTLINE PACKAGE

14-PINS SHOWN



- NOTES:
- A. All linear dimensions are in millimeters.
  - B. This drawing is subject to change without notice.
  - C. Body dimensions do not include mold flash or protrusion, not to exceed 0,15.

W (R-GDFP-F14)

CERAMIC DUAL FLATPACK



## NOTES:

- All linear dimensions are in inches (millimeters).
- This drawing is subject to change without notice.
- This package can be hermetically sealed with a ceramic lid using glass frit.
- Index point is provided on cap for terminal identification only.
- Falls within MIL STD 1835 GDFP1-F14

## GENERIC PACKAGE VIEW

**FK 20**

**LCCC - 2.03 mm max height**

8.89 x 8.89, 1.27 mm pitch

LEADLESS CERAMIC CHIP CARRIER

This image is a representation of the package family, actual package may vary.  
Refer to the product data sheet for package details.



4229370VA\

**J 14**

## GENERIC PACKAGE VIEW

**CDIP - 5.08 mm max height**

CERAMIC DUAL IN LINE PACKAGE



Images above are just a representation of the package family, actual package may vary.  
Refer to the product data sheet for package details.

4040083-5/G



**J0014A**

## PACKAGE OUTLINE

**CDIP - 5.08 mm max height**

CERAMIC DUAL IN LINE PACKAGE



4214771/A 05/2017

### NOTES:

1. All controlling linear dimensions are in inches. Dimensions in brackets are in millimeters. Any dimension in brackets or parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.
2. This drawing is subject to change without notice.
3. This package is hermetically sealed with a ceramic lid using glass frit.
4. Index point is provided on cap for terminal identification only and on press ceramic glass frit seal only.
5. Falls within MIL-STD-1835 and GDIP1-T14.

# EXAMPLE BOARD LAYOUT

J0014A

CDIP - 5.08 mm max height

CERAMIC DUAL IN LINE PACKAGE



LAND PATTERN EXAMPLE  
NON-SOLDER MASK DEFINED  
SCALE: 5X



4214771/A 05/2017

## N (R-PDIP-T\*\*)

16 PINS SHOWN

## PLASTIC DUAL-IN-LINE PACKAGE



| PINS **             | 14               | 16               | 18               | 20               |
|---------------------|------------------|------------------|------------------|------------------|
| DIM                 |                  |                  |                  |                  |
| A MAX               | 0.775<br>(19,69) | 0.775<br>(19,69) | 0.920<br>(23,37) | 1.060<br>(26,92) |
| A MIN               | 0.745<br>(18,92) | 0.745<br>(18,92) | 0.850<br>(21,59) | 0.940<br>(23,88) |
| MS-001<br>VARIATION | AA               | BB               | AC               | AD               |



14/18 Pin Only  
20 Pin vendor option

4040049/E 12/2002

- NOTES:
- A. All linear dimensions are in inches (millimeters).
  - B. This drawing is subject to change without notice.
  - Falls within JEDEC MS-001, except 18 and 20 pin minimum body length (Dim A).
  - The 20 pin end lead shoulder width is a vendor option, either half or full width.

## IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATASHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, regulatory or other requirements.

These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you fully indemnify TI and its representatives against any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to [TI's Terms of Sale](#), [TI's General Quality Guidelines](#), or other applicable terms available either on [ti.com](#) or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products. Unless TI explicitly designates a product as custom or customer-specified, TI products are standard, catalog, general purpose devices.

TI objects to and rejects any additional or different terms you may propose.

Copyright © 2026, Texas Instruments Incorporated

Last updated 10/2025