

TLE202xM Excalibur, High-Speed, Low-Power, Precision, Operational Amplifiers

1 Features

- Supply current: 300 μ A, max
- High unity-gain bandwidth: 2MHz
- High slew rate: 0.65V/ μ s
- Supply-current change over military temperature range: 10 μ A at $V_S = \pm 15$ V
- Specified for both 5V single-supply and ± 15 V operation
- Phase-reversal protection
- High open-loop gain: 6.5V/ μ V (136dB)
- Low offset voltage: 100 μ V, max
- Offset voltage drift with time: 0.005 μ V/mo
- Low input bias current: 50nA, max
- Low noise voltage: 19nV/ $\sqrt{\text{Hz}}$

2 Description

The TLE2021xM, TLE2022xM, and TLE2024xM (TLE202xM) devices are precision, high-speed, low-power operational amplifiers using a new Texas Instruments Excalibur process. These devices combine the best features of the OP21, with a highly improved slew rate and unity-gain bandwidth.

The complementary bipolar Excalibur process uses isolated vertical pnp transistors that yield dramatic improvement in unity-gain bandwidth and slew rate over similar devices.

The addition of a bias circuit in conjunction with this process results in extremely stable parameters with both time and temperature. Therefore, a precision device remains a precision device even with changes in temperature and over years of use.

This combination of excellent dc performance with a common-mode input voltage range that includes the negative rail makes these devices an excellent choice for low-level signal conditioning applications in either single-supply or split-supply configurations. In addition, these devices offer phase-reversal protection circuitry that eliminates an unexpected change in output states when one of the inputs is less than the negative supply rail.

A variety of available options includes ceramic DIP and chip-carrier versions for high-density systems applications.


The M-suffix devices are characterized for operation over the full military temperature range of -55°C to $+125^{\circ}\text{C}$.

Device Information

PART NUMBER ⁽¹⁾	CHANNEL COUNT	PACKAGE ⁽²⁾
TLE2021xM	Single	FK (LCCC, 20)
		JG (CDIP, 8)
TLE2022xM	Dual	FK (LCCC, 20)
		JG (CDIP, 8)
TLE2024xM	Quad	FK (LCCC, 20)
		J (CDIP, 14)

(1) See [Section 3](#).

(2) For more information, see [Section 11](#).



Difference Amplifier Circuit With the RES11A



Table of Contents

1 Features	1	5.13 Operating Characteristics TLE2024M, $V_{CC} = 5\text{ V}$	9
2 Description	1	5.14 Electrical Characteristics TLE2024xM, $V_{CC} =$ $\pm 15\text{ V}$	10
3 Device Comparison Tables	2	5.15 Operating Characteristics TLE2024M, $V_{CC} =$ $\pm 15\text{ V}$	10
4 Pin Configuration and Functions	3	5.16 Typical Characteristics.....	11
5 Specifications	4	6 Parameter Measurement Information	23
5.1 Absolute Maximum Ratings.....	4	6.1 Typical Values.....	24
5.2 Dissipation Ratings.....	4	7 Detailed Description	25
5.3 Recommended Operating Conditions.....	4	7.1 Functional Block Diagram.....	25
5.4 Electrical Characteristics TLE2021xM, $V_{CC} = 5\text{ V}$	5	8 Application and Implementation	26
5.5 Operating Characteristics TLE2021M, $V_{CC} = 5\text{ V}$	5	8.1 Application Information.....	26
5.6 Electrical Characteristics TLE2021xM, $V_{CC} =$ $\pm 15\text{ V}$	6	9 Device and Documentation Support	29
5.7 Operating Characteristics TLE2021M, $V_{CC} = \pm 15$ V	6	9.1 Receiving Notification of Documentation Updates....	29
5.8 Electrical Characteristics TLE2022xM, $V_{CC} = 5\text{ V}$	7	9.2 Support Resources.....	29
5.9 Operating Characteristics TLE2022M, $V_{CC} = 5\text{ V}$	7	9.3 Trademarks.....	29
5.10 Electrical Characteristics TLE2022xM, $V_{CC} =$ $\pm 15\text{ V}$	8	9.4 Electrostatic Discharge Caution.....	29
5.11 Operating Characteristics TLE2022M, $V_{CC} =$ $\pm 15\text{ V}$	8	9.5 Glossary.....	29
5.12 Electrical Characteristics TLE2024xM, $V_{CC} = 5\text{ V}$	9	10 Revision History	29
		11 Mechanical, Packaging, and Orderable Information	29

3 Device Comparison Tables

Table 3-1. TLE2021xM Available Options

T_A	PACKAGED DEVICES		
	V_{IOmax} AT 25°C	CHIP CARRIER (FK))	CERAMIC DIP (JG)
–55°C to +125°C	100 μV 500 μV	TLE2021BMFK TLE2021MFK	TLE2021BMJG TLE2021MJG

Table 3-2. TLE2022xM Available Options

T_A	PACKAGED DEVICES		
	V_{IOmax} AT 25°C	CHIP CARRIER (FK))	CERAMIC DIP (JG)
–55°C to +125°C	150 μV 300 μV 500 μV	— TLE2022AMFK TLE2022MFK	TLE2022BMJG TLE2022AMJG TLE2022MJG

Table 3-3. TLE2024xM Available Options

T_A	PACKAGED DEVICES		
	V_{IOmax} AT 25°C	CHIP CARRIER (FK))	CERAMIC DIP (J)
–55°C to +125°C	500 μV 750 μV 1000 μV	TLE2024BMFK TLE2024AMFK TLE2024MFK	TLE2024BMJ TLE2024AMJ TLE2024MJ

4 Pin Configuration and Functions




Figure 4-1. TLE2021xM: JG Package, 8-Pin CDIP (Top View)




Figure 4-2. TLE2022xM: JG Package, 8-Pin CDIP (Top View)




Figure 4-3. TLE2021xM: FK Package, 20-Pin LCCC (Top View)




Figure 4-4. TLE2022xM: FK Package, 20-Pin LCCC (Top View)




Figure 4-5. TLE2024xM: FK Package, 20-Pin LCCC (Top View)




Figure 4-6. TLE2024xM: J Package, 14-Pin CDIP (Top View)

5 Specifications

5.1 Absolute Maximum Ratings

over operating free-air temperature range (unless otherwise noted) ⁽¹⁾

		VALUE	UNIT
Supply voltage, V_{CC+} ⁽²⁾		20	V
Supply voltage, V_{CC-} ⁽²⁾		-20	V
Differential input voltage, V_{ID} ⁽³⁾		± 0.6	V
Input voltage range, V_I (any input) ⁽²⁾		$\pm V_{CC}$	
Input current, I_I (each input)		± 1	mA
Output current, I_O (each output):	TLE2021	± 20	mA
	TLE2022	± 30	
	TLE2024	± 40	
Total current into V_{CC+}		80	mA
Total current out of V_{CC-}		80	mA
Duration of short-circuit current at (or below) 25°C ⁽⁴⁾		Unlimited	
Continuous total power dissipation		See <i>Dissipation Ratings</i>	
Operating free-air temperature range, T_A		-55 to 125	°C
Storage temperature range, T_{stg}		-65 to 150	°C
Case temperature for 60 seconds, T_C : FK package		260	°C
Lead temperature 1,6 mm (1/16 inch) from case for 60 seconds: JG package		300	°C

- (1) Stresses beyond those listed under *Absolute Maximum Ratings* may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated under *Recommended Operating Conditions* is not implied. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability.
- (2) All voltage values, except differential voltages, are with respect to the midpoint between V_{CC+} and V_{CC-} .
- (3) Differential voltages are at $IN+$ with respect to $IN-$. Excessive current flows if a differential input voltage in excess of approximately ± 600 mV is applied between the inputs unless some limiting resistance is used.
- (4) The output is able to be shorted to either supply. Limit temperature, supply voltages, or both to not exceed the maximum dissipation ratings.

5.2 Dissipation Ratings

PACKAGE	$T_A \leq 25^\circ\text{C}$ POWER RATING	DERATING FACTOR ABOVE $T_A = 25^\circ\text{C}$	$T_A = 70^\circ\text{C}$ POWER RATING	$T_A = 85^\circ\text{C}$ POWER RATING	$T_A = 125^\circ\text{C}$ POWER RATING
FK	1375 mW	11.0 mW/°C	880 mW	715 mW	275 mW
J-14	1375 mW	11.0 mW/°C	880 mW	715 mW	275 mW
JG-8	1050 mW	8.4 mW/°C	672 mW	546 mW	210 mW

5.3 Recommended Operating Conditions

over operating free-air temperature range (unless otherwise noted)

		M SUFFIX		UNIT
		MIN	MAX	
Supply voltage, V_{CC}		± 2	± 20	V
Common-mode input voltage, V_{IC}	$V_{CC} = \pm 5$ V	0	3.2	V
	$V_{CC} \pm \pm 15$ V	-15	13.2	
Operating free-air temperature, T_A		-55	125	°C

5.4 Electrical Characteristics TLE2021xM, $V_{CC} = 5\text{ V}$

at specified free-air temperature and $V_{CC} = 5\text{ V}$ (unless otherwise noted)

PARAMETER		TEST CONDITIONS	T_A ⁽¹⁾	TLE2021M			TLE2021BM			UNIT
				MIN	TYP	MAX	MIN	TYP	MAX	
V_{IO}	Input offset voltage	$V_{IC} = 0, R_S = 50\ \Omega$	25°C		120	600		80	200	μV
			Full range			1100			300	
α_{VIO}	Temperature coefficient of input offset voltage		Full range		2			2		$\mu\text{V}/^\circ\text{C}$
	Input offset voltage long-term drift ⁽²⁾		25°C		0.005			0.005		$\mu\text{V}/\text{mo}$
I_{IO}	Input offset current		25°C		0.2	6		0.2	6	nA
			Full range			10			10	
I_{IB}	Input bias current		25°C		25	70		25	70	nA
			Full range			90			90	
V_{ICR}	Common-mode input voltage range	$R_S = 50\ \Omega$	25°C	0 to 3.5	–0.3 to 4		0 to 3.5	–0.3 to 4		V
			Full range	0 to 3.2			0 to 3.2			
V_{OH}	High-level output voltage	$R_L = 10\ \text{k}\Omega$	25°C	4	4.3		4	4.3		V
			Full range	3.8			3.8			
V_{OL}	Low-level output voltage		25°C		0.7	0.8		0.7	0.8	V
			Full range			0.95			0.95	
A_{VD}	Large-signal differential voltage amplification	$V_O = 1.4\text{ V to }4\text{ V}, R_L = 10\ \text{k}\Omega$	25°C	0.3	1.5		0.3	1.5		$\text{V}/\mu\text{V}$
			Full range	0.1			0.1			
CMRR	Common mode rejection ratio	$V_{IC} = V_{ICRmin}, R_S = 50\ \Omega$	25°C	85	110		85	110		dB
			Full range	80			80			
k_{SVR}	Supply-voltage rejection ratio ($\Delta V_{CC}/\Delta V_{IO}$)	$V_{CC} = 5\text{ V to }30\text{ V}$	25°C	105	120		105	120		dB
			Full range	100			100			
I_{CC}	Supply current	$V_O = 2.5\text{ V}, \text{ no load}$	25°C		170	230		170	230	μA
			Full range			230			230	
ΔI_{CC}	Supply-current change over operating temperature range		Full range		9			9		μA

(1) Full range is -55°C to $+125^\circ\text{C}$.

(2) Typical values are based on the input offset voltage shift observed through 168 hours of operating life test at $T_A = 150^\circ\text{C}$ extrapolated to $T_A = 25^\circ\text{C}$ using the Arrhenius equation and assuming an activation energy of 0.96 eV.

5.5 Operating Characteristics TLE2021M, $V_{CC} = 5\text{ V}$

at $T_A = 25^\circ\text{C}$ and $V_{CC} = 5\text{ V}$ (unless otherwise noted)

PARAMETER		TEST CONDITIONS	T_A	M SUFFIX			UNIT
				MIN	TYP	MAX	
SR	Slew rate at unity gain	$V_O = 1\text{ V to }3\text{ V}$, see Figure 6-1	25°C		0.5		$\text{V}/\mu\text{s}$
V_n	Equivalent input noise voltage (see Figure 6-2)	$f = 10\text{ Hz}$	25°C		21		$\text{nV}/\sqrt{\text{Hz}}$
		$f = 1\text{ kHz}$	25°C		17		
$V_{N(PP)}$	Peak-to-peak equivalent input noise voltage	$f = 0.1\text{ Hz to }1\text{ Hz}$	25°C		0.16		μV
		$f = 0.1\text{ Hz to }10\text{ Hz}$	25°C		0.47		
I_n	Equivalent input noise current		25°C		0.9		$\text{pA}/\sqrt{\text{Hz}}$
B_1	Unity-gain bandwidth	See Figure 6-3	25°C		1.2		MHz
Φ_m	Phase margin at unity gain	See Figure 6-3	25°C		42°		

5.6 Electrical Characteristics TLE2021xM, $V_{CC} = \pm 15\text{ V}$

at specified free-air temperature and $V_{CC} = \pm 15\text{ V}$ (unless otherwise noted)

PARAMETER		TEST CONDITIONS	T_A ⁽¹⁾	TLE2021M			TLE2021BM			UNIT
				MIN	TYP	MAX	MIN	TYP	MAX	
V_{IO}	Input offset voltage	$V_{IC} = 0, R_S = 50\ \Omega$	25°C		120	500		40	100	μV
			Full range			1000			200	
α_{VIO}	Temperature coefficient of input offset voltage		Full range		2			2		$\mu\text{V}/^\circ\text{C}$
	Input offset voltage long-term drift ⁽²⁾		25°C		0.006			0.006		$\mu\text{V}/\text{mo}$
I_{IO}	Input offset current		25°C		0.2	6		0.2	6	nA
			Full range			10			10	
I_{IB}	Input bias current		25°C		25	70		25	70	nA
			Full range			90			90	
V_{ICR}	Common-mode input voltage range	$R_S = 50\ \Omega$	25°C	–15 to 13.5	–15.3 to 14		–15 to 13.5	–15.3 to 14		V
			Full range	–15 to 13.2			–15 to 13.2			
V_{OM+}	Maximum positive peak output voltage swing	$R_L = 10\text{ k}\Omega$	25°C	14	14.3		14	14.3		V
			Full range	13.8			13.8			
V_{OM-}	Maximum negative peak output voltage swing		25°C	–13.7	–14.1		–13.7	–14.1		V
			Full range	–13.6			–13.6			
A_{VD}	Large-signal differential voltage amplification	$V_O = \pm 10\text{ V}, R_L = 10\text{ k}\Omega$	25°C	1	6.5		1	6.5		V/ μV
			Full range	0.5			0.5			
$CMRR$	Common mode rejection ratio	$V_{IC} = V_{ICRmin}, R_S = 50\ \Omega$	25°C	100	115		100	115		dB
			Full range	96			96			
k_{SVR}	Supply-voltage rejection ratio ($\Delta V_{CC}/\Delta V_{IO}$)	$V_{CC} = \pm 2.5\text{ V to } \pm 15\text{ V}$	25°C	105	120		105	120		dB
			Full range	100			100			
I_{CC}	Supply current	$V_O = 0, \text{ no load}$	25°C		200	300		200	300	μA
			Full range			300			300	
ΔI_{CC}	Supply-current change over operating temperature range		Full range		10			10		μA

(1) Full range is -55°C to $+125^\circ\text{C}$.

(2) Typical values are based on the input offset voltage shift observed through 168 hours of operating life test at $T_A = 150^\circ\text{C}$ extrapolated to $T_A = 25^\circ\text{C}$ using the Arrhenius equation and assuming an activation energy of 0.96 eV.

5.7 Operating Characteristics TLE2021M, $V_{CC} = \pm 15\text{ V}$

at specified free-air temperature and $V_{CC} = \pm 15\text{ V}$ (unless otherwise noted)

PARAMETER		TEST CONDITIONS	T_A ⁽¹⁾	M SUFFIX			UNIT
				MIN	TYP	MAX	
SR	Slew rate at unity gain	$V_O = 1\text{ V to } 3\text{ V}, \text{ see Figure 6-1}$	25°C	0.45	0.65		V/ μs
			Full range	0.42			
V_n	Equivalent input noise voltage (see Figure 6-2)	$f = 10\text{ Hz}$	25°C		19		nV/ $\sqrt{\text{Hz}}$
		$f = 1\text{ kHz}$	25°C		15		
$V_{N(PP)}$	Peak-to-peak equivalent input noise voltage	$f = 0.1\text{ Hz to } 1\text{ Hz}$	25°C		0.16		μV
		$f = 0.1\text{ Hz to } 10\text{ Hz}$	25°C		0.47		
I_n	Equivalent input noise current		25°C		0.9		pA/ $\sqrt{\text{Hz}}$
B_1	Unity-gain bandwidth	See Figure 6-3	25°C		1.2		MHz
ϕ_m	Phase margin at unity gain	See Figure 6-3	25°C		46°		

(1) Full range is -55°C to $+125^\circ\text{C}$.

5.8 Electrical Characteristics TLE2022xM, $V_{CC} = 5\text{ V}$

at specified free-air temperature and $V_{CC} = 5\text{ V}$ (unless otherwise noted)

PARAMETER		TEST CONDITIONS	T _A ⁽¹⁾	TLE2022M			TLE2022AM			TLE2022BM			UNIT	
				MIN	TYP	MAX	MIN	TYP	MAX	MIN	TYP	MAX		
V _{IO}	Input offset voltage	V _{IC} = 0, R _S = 50 Ω	25°C	600			400			250			μV	
			Full range	800			550			400				
α _{VIO}	Temperature coefficient of input offset voltage		Full range	2			2			2			μV/°C	
	Input offset voltage long-term drift ⁽²⁾		25°C	0.005			0.005			0.005			μV/mo	
I _{IO}	Input offset current		25°C	0.5			6	0.4		6	0.3		6	nA
			Full range	10				10			10			
I _{IB}	Input bias current		25°C	35			70	33		70	30		70	nA
			Full range	90				90			90			
V _{ICR}	Common-mode input voltage range	R _S = 50 Ω	25°C	0 to 3.5	−0.3 to 4		0 to 3.5	−0.3 to 4		0 to 3.5	−0.3 to 4		V	
			Full range	0 to 3.2			0 to 3.2			0 to 3.2				
V _{OH}	High-level output voltage	R _L = 10 kΩ	25°C	4	4.3		4	4.3		4	4.3		V	
			Full range	3.8			3.8		3.8					
V _{OL}	Low-level output voltage		25°C	0.7			0.8	0.7		0.8	0.7		0.8	V
			Full range	0.95			0.95		0.95					
A _{VD}	Large-signal differential voltage amplification	V _O = 1.4 V to 4 V, R _L = 10 kΩ	25°C	0.3	1.5		0.4	1.5		0.5	1.5		V/μV	
			Full range	0.1			0.1		0.1					
CMRR	Common mode rejection ratio	V _{IC} = V _{ICRmin} , R _S = 50 Ω	25°C	85	100		87	102		90	105		dB	
			Full range	80			82		85					
k _{SVR}	Supply-voltage rejection ratio (ΔV _{CC} /ΔV _{IO})	V _{CC} = 5 V to 30 V	25°C	100	115		103	118		105	120		dB	
			Full range	95			98		100					
I _{CC}	Supply current	V _O = 2.5 V, no load	25°C	450			600	450		600	450		600	μA
			Full range	600			600		600					
ΔI _{CC}	Supply-current change over operating temperature range		Full range	37			37		37		37			μA

(1) Full range is -55°C to $+125^\circ\text{C}$.

(2) Typical values are based on the input offset voltage shift observed through 168 hours of operating life test at $T_A = 150^\circ\text{C}$ extrapolated to $T_A = 25^\circ\text{C}$ using the Arrhenius equation and assuming an activation energy of 0.96 eV.

5.9 Operating Characteristics TLE2022M, $V_{CC} = 5\text{ V}$

at $T_A = 25^\circ\text{C}$ and $V_{CC} = 5\text{ V}$ (unless otherwise noted)

PARAMETER		TEST CONDITIONS	T_A	M SUFFIX			UNIT
				MIN	TYP	MAX	
SR	Slew rate at unity gain	$V_O = 1\text{ V to }3\text{ V}$, see Figure 6-1	25°C		0.5		$\text{V}/\mu\text{s}$
V_n	Equivalent input noise voltage (see Figure 6-2)	$f = 10\text{ Hz}$	25°C		21		$\text{nV}/\sqrt{\text{Hz}}$
		$f = 1\text{ kHz}$	25°C		17		
$V_{N(PP)}$	Peak-to-peak equivalent input noise voltage	$f = 0.1\text{ Hz to }1\text{ Hz}$	25°C		0.16		μV
		$f = 0.1\text{ Hz to }10\text{ Hz}$	25°C		0.47		
I_n	Equivalent input noise current		25°C		0.1		$\text{pA}/\sqrt{\text{Hz}}$
B_1	Unity-gain bandwidth	See Figure 6-3	25°C		1.7		MHz
ϕ_m	Phase margin at unity gain	See Figure 6-3	25°C		47°		

5.10 Electrical Characteristics TLE2022xM, $V_{CC} = \pm 15\text{ V}$

at specified free-air temperature and $V_{CC} = \pm 15\text{ V}$ (unless otherwise noted)

PARAMETER		TEST CONDITIONS	T _A ⁽¹⁾	TLE2022M			TLE2022AM			TLE2022BM			UNIT
				MIN	TYP	MAX	MIN	TYP	MAX	MIN	TYP	MAX	
V _{IO}	Input offset voltage	V _{IC} = 0, R _S = 50 Ω	25°C		150	500		120	300		70	150	μV
			Full range			700			450			300	
α _{VIO}	Temperature coefficient of input offset voltage		Full range		2			2			2		μV/°C
	Input offset voltage long-term drift ⁽²⁾		25°C		0.006			0.006			0.006		μV/mo
I _{IO}	Input offset current		25°C		0.5	6		0.4	6		0.3	6	nA
			Full range			10			10			10	
I _{IB}	Input bias current		25°C		35	70		33	70		30	70	nA
			Full range			90			90			90	
V _{ICR}	Common-mode input voltage range	R _S = 50 Ω	25°C	−15 to 13.5	−15.3 to 14		−15 to 13.5	−15.3 to 14		−15 to 13.5	−15.3 to 14	V	
			Full range		−15 to 13.2			−15 to 13.2			−15 to 13.2		
V _{OM+}	Maximum positive peak output voltage swing	R _L = 10 kΩ	25°C	14	14.3		14	14.3		14	14.3	V	
			Full range		13.9			13.9			13.9		
V _{OM−}	Maximum negative peak output voltage swing		25°C	−13.7	−14.1		−13.7	−14.1		−13.7	−14.1	V	
			Full range		−13.6			−13.6			−13.6		
A _{VD}	Large-signal differential voltage amplification	V _O = ±10 V, R _L = 10 kΩ	25°C	0.8	4		1	7		1.5	10	V/μV	
			Full range		0.8			1			1.5		
CMRR	Common mode rejection ratio	V _{IC} = V _{ICRmin} , R _S = 50 Ω	25°C	95	106		97	109		100	112	dB	
			Full range		91			93			96		
k _{SVR}	Supply-voltage rejection ratio (ΔV _{CC} /ΔV _{IO})	V _{CC} = ±2.5 V to ±15 V	25°C	100	115		103	118		105	120	dB	
			Full range		95			98			100		
I _{CC}	Supply current	V _O = 0, no load	25°C		550	700		550	700		550	700	μA
			Full range			700			700			700	
ΔI _{CC}	Supply-current change over operating temperature range		Full range		60			60			60		μA

(1) Full range is -55°C to $+125^\circ\text{C}$.

(2) Typical values are based on the input offset voltage shift observed through 168 hours of operating life test at $T_A = 150^\circ\text{C}$ extrapolated to $T_A = 25^\circ\text{C}$ using the Arrhenius equation and assuming an activation energy of 0.96 eV.

5.11 Operating Characteristics TLE2022M, $V_{CC} = \pm 15\text{ V}$

at specified free-air temperature and $V_{CC} = \pm 15\text{ V}$ (unless otherwise noted)

PARAMETER		TEST CONDITIONS	T_A ⁽¹⁾	M SUFFIX			UNIT
				MIN	TYP	MAX	
SR	Slew rate at unity gain	$V_O = 1\text{ V}$ to 3 V , see Figure 6-1	25°C	0.45	0.65		V/ μs
			Full range	0.4			
V_n	Equivalent input noise voltage (see Figure 6-2)	$f = 10\text{ Hz}$	25°C		19		nV/ $\sqrt{\text{Hz}}$
		$f = 1\text{ kHz}$	25°C		15		
$V_{N(PP)}$	Peak-to-peak equivalent input noise voltage	$f = 0.1\text{ Hz}$ to 1 Hz	25°C		0.16		μV
		$f = 0.1\text{ Hz}$ to 10 Hz	25°C		0.47		
I_n	Equivalent input noise current		25°C		0.1		pA/ $\sqrt{\text{Hz}}$
B_1	Unity-gain bandwidth	See Figure 6-3	25°C		2.8		MHz
ϕ_m	Phase margin at unity gain	See Figure 6-3	25°C		52°		

(1) Full range is -55°C to $+125^\circ\text{C}$.

5.12 Electrical Characteristics TLE2024xM, $V_{CC} = 5\text{ V}$

at specified free-air temperature and $V_{CC} = 5\text{ V}$ (unless otherwise noted)

PARAMETER		TEST CONDITIONS	T _A ⁽¹⁾	TLE2024M			TLE2024AM			TLE2024BM			UNIT
				MIN	TYP	MAX	MIN	TYP	MAX	MIN	TYP	MAX	
V _{IO}	Input offset voltage	V _{IC} = 0, R _S = 50 Ω	25°C	1100			850			600			μV
			Full range	1300			1050			800			
α _{VIO}	Temperature coefficient of input offset voltage		Full range	2			2			2			μV/°C
	Input offset voltage long-term drift ⁽²⁾		25°C	0.005			0.005			0.005			μV/mo
I _{IO}	Input offset current		25°C	0.6 6			0.5 6			0.4 6			nA
			Full range	10			10			10			
I _{IB}	Input bias current		25°C	45 70			40 70			35 70			nA
			Full range	90			90			90			
V _{ICR}	Common-mode input voltage range	R _S = 50 Ω	25°C	0 to 3.5	−0.3 to 4	0 to 3.5	−0.3 to 4	0 to 3.5	−0.3 to 4			V	
			Full range	0 to 3.2			0 to 3.2			0 to 3.2			
V _{OH}	High-level output voltage	R _L = 10 kΩ	25°C	3.9	4.2	3.9	4.2	4	4.3			V	
			Full range	3.7			3.7			3.8			
V _{OL}	Low-level output voltage		25°C	0.7 0.8			0.7 0.8			0.7 0.8			V
			Full range	0.95			0.95			0.95			
A _{VD}	Large-signal differential voltage amplification	V _O = 1.4 V to 4 V, R _L = 10 kΩ	25°C	0.2	1.5	0.3	1.5	0.4	1.5			V/μV	
			Full range	0.1			0.1			0.1			
CMRR	Common mode rejection ratio	V _{IC} = V _{ICRmin} , R _S = 50 Ω	25°C	80	90	82	92	85	95			dB	
			Full range	80			82			85			
k _{SVR}	Supply-voltage rejection ratio (ΔV _{CC} /ΔV _{IO})	V _{CC} = 5 V to 30 V	25°C	98	112	100	115	103	117			dB	
			Full range	93			95			98			
I _{CC}	Supply current	V _O = 2.5 V, no load	25°C	800 1200			800 1200			800 1200			μA
			Full range	1200			1200			1200			
ΔI _{CC}	Supply-current change over operating temperature range		Full range	50			50			50			μA

(1) Full range is -55°C to $+125^\circ\text{C}$.

(2) Typical values are based on the input offset voltage shift observed through 168 hours of operating life test at $T_A = 150^\circ\text{C}$ extrapolated to $T_A = 25^\circ\text{C}$ using the Arrhenius equation and assuming an activation energy of 0.96 eV.

5.13 Operating Characteristics TLE2024M, $V_{CC} = 5\text{ V}$

at $T_A = 25^\circ\text{C}$ and $V_{CC} = 5\text{ V}$ (unless otherwise noted)

PARAMETER		TEST CONDITIONS	T_A	M SUFFIX			UNIT
				MIN	TYP	MAX	
SR	Slew rate at unity gain	$V_O = 1\text{ V to }3\text{ V}$, see Figure 6-1	25°C		0.5		$\text{V}/\mu\text{s}$
V_n	Equivalent input noise voltage (see Figure 6-2)	$f = 10\text{ Hz}$	25°C		21		$\text{nV}/\sqrt{\text{Hz}}$
		$f = 1\text{ kHz}$	25°C		17		
$V_{N(PP)}$	Peak-to-peak equivalent input noise voltage	$f = 0.1\text{ Hz to }1\text{ Hz}$	25°C		0.16		μV
		$f = 0.1\text{ Hz to }10\text{ Hz}$	25°C		0.47		
I_n	Equivalent input noise current		25°C		0.1		$\text{pA}/\sqrt{\text{Hz}}$
B_1	Unity-gain bandwidth	See Figure 6-3	25°C		1.7		MHz
ϕ_m	Phase margin at unity gain	See Figure 6-3	25°C		47°		

5.14 Electrical Characteristics TLE2024xM, $V_{CC} = \pm 15\text{ V}$

at specified free-air temperature and $V_{CC} = \pm 15\text{ V}$ (unless otherwise noted)

PARAMETER		TEST CONDITIONS	T _A ⁽¹⁾	TLE2024M			TLE2024AM			TLE2024BM			UNIT
				MIN	TYP	MAX	MIN	TYP	MAX	MIN	TYP	MAX	
V _{IO}	Input offset voltage	V _{IC} = 0, R _S = 50 Ω	25°C			1000			750			500	μV
			Full range			1200			950			700	
α _{VIO}	Temperature coefficient of input offset voltage		Full range		2			2			2	μV/°C	
	Input offset voltage long-term drift ⁽²⁾		25°C		0.006			0.006			0.006	μV/mo	
I _{IO}	Input offset current		25°C		0.6	6		0.5	6		0.4	6	nA
			Full range			10			10			10	
I _{IB}	Input bias current		25°C		50	70		45	70		40	70	nA
			Full range			90			90			90	
V _{ICR}	Common-mode input voltage range		R _S = 50 Ω	25°C	−15 to 13.5	−15.3 to 14		−15 to 13.5	−15.3 to 14		−15 to 13.5	−15.3 to 14	V
				Full range	−15 to 13.2			−15 to 13.2			−15 to 13.2		
V _{OM+}	Maximum positive peak output voltage swing	R _L = 10 kΩ	25°C	13.8	14.1		13.9	14.2		14	14.3	V	
			Full range	13.7			13.7			13.8			
V _{OM−}	Maximum negative peak output voltage swing		25°C	−13.7	−14.1		−13.7	−14.1		−13.7	−14.1	V	
			Full range	−13.6			−13.6			−13.6			
A _{VD}	Large-signal differential voltage amplification	V _O = ±10 V, R _L = 10 kΩ	25°C	0.4	2		0.8	4		1	7	V/μV	
			Full range	0.4			0.8			1			
CMRR	Common mode rejection ratio	V _{IC} = V _{ICRmin} , R _S = 50 Ω	25°C	92	102		94	105		97	108	dB	
			Full range	88			90			93			
k _{SVR}	Supply-voltage rejection ratio (ΔV _{CC} /ΔV _{IO})	V _{CC} = ±2.5 V to ±15 V	25°C	98	112		100	115		103	117	dB	
			Full range	93			95			98			
I _{CC}	Supply current	V _O = 0, no load	25°C		1050	1400		1050	1400		1050	1400	μA
			Full range			1400			1400			1400	
ΔI _{CC}	Supply-current change over operating temperature range		Full range		85			85			85		μA

(1) Full range is -55°C to $+125^\circ\text{C}$.

(2) Typical values are based on the input offset voltage shift observed through 168 hours of operating life test at $T_A = 150^\circ\text{C}$ extrapolated to $T_A = 25^\circ\text{C}$ using the Arrhenius equation and assuming an activation energy of 0.96 eV.

5.15 Operating Characteristics TLE2024M, $V_{CC} = \pm 15\text{ V}$

at specified free-air temperature and $V_{CC} = \pm 15\text{ V}$ (unless otherwise noted)

PARAMETER		TEST CONDITIONS	T_A ⁽¹⁾	M SUFFIX			UNIT
				MIN	TYP	MAX	
SR	Slew rate at unity gain	$V_O = 1\text{ V}$ to 3 V , see Figure 6-1	25°C	0.45	0.7		V/ μs
			Full range	0.42			
V_n	Equivalent input noise voltage (see Figure 6-2)	$f = 10\text{ Hz}$	25°C		19		nV/ $\sqrt{\text{Hz}}$
		$f = 1\text{ kHz}$	25°C		15		
$V_{N(PP)}$	Peak-to-peak equivalent input noise voltage	$f = 0.1\text{ Hz}$ to 1 Hz	25°C		0.16		μV
		$f = 0.1\text{ Hz}$ to 10 Hz	25°C		0.47		
I_n	Equivalent input noise current		25°C		0.1		pA/ $\sqrt{\text{Hz}}$
B_1	Unity-gain bandwidth	See Figure 6-3	25°C		2.8		MHz
ϕ_m	Phase margin at unity gain	See Figure 6-3	25°C		52°		

(1) Full range is -55°C to $+125^\circ\text{C}$.

5.16 Typical Characteristics

Table 5-1. Table of Graphs

			FIGURE
V_{IO}	Input offset voltage	Distribution	4-1 to 4-3
I_{IB}	Input bias current	vs Common-mode input voltage vs Free-air temperature	4-4 to 4-9
I_I	Input current	vs Differential input voltage	4-10
V_{OM}	Maximum peak output voltage	vs Output current vs Free-air temperature	4-11 to 4-14
V_{OH}	High-level output voltage	vs High-level output current vs Free-air temperature	4-15 to 4-17
V_{OL}	Low-level output voltage	vs Low-level output current vs Free-air temperature	4-18, 4-19
$V_{O(PP)}$	Maximum peak-to-peak output voltage	vs Frequency	4-20, 4-21
A_{VD}	Large-signal differential voltage amplification and phase shift	vs Frequency	4-22
	Large-signal differential voltage amplification	vs Free-air temperature	4-23 to 4-25
I_{OS}	Short-circuit output current	vs Supply voltage vs Free-air temperature	4-26 to 4-33
I_{CC}	Supply current	vs Supply voltage vs Free-air temperature	4-34 to 4-39
CMRR	Common-mode rejection ratio	vs Frequency	4-40 to 4-42
SR	Slew rate	vs Free-air temperature	4-43 to 4-45
	Voltage-follower small-signal pulse response		4-46, 4-47
	Voltage-follower large-signal pulse response		4-48 to 4-53
$V_{N(PP)}$	Peak-to-peak equivalent input noise voltage	0.1Hz to 1Hz 0.1Hz to 10Hz	4-54, 4-55
V_n	Equivalent input noise voltage	vs Frequency	4-56
B_1	Unity-gain bandwidth	vs Supply voltage vs Free-air temperature	4-57 to 4-60
ϕ_m	Phase margin	vs Supply voltage vs Load capacitance vs Free-air temperature	4-61 to 4-66
	Phase shift	vs Frequency	4-22

5.16 Typical Characteristics (continued)




Figure 5-1. Distribution of TLE2021xM Input Offset Voltage




Figure 5-2. Distribution of TLE2022xM Input Offset Voltage




Figure 5-3. Distribution of TLE2024xM Input Offset Voltage




Figure 5-4. TLE2021xM Input Bias Current vs Common-Mode Input Voltage




Figure 5-5. TLE2022xM Input Bias Current vs Common-Mode Input Voltage






Figure 5-6. TLE2024xM Input Bias Current vs Common-Mode Input Voltage

5.16 Typical Characteristics (continued)




Data at high and low temperatures applicable only within rated operating free-air temperature ranges of the various devices

Figure 5-7. TLE2021xM Input Bias Current vs Free-Air Temperature



Data at high and low temperatures applicable only within rated operating free-air temperature ranges of the various devices

Figure 5-8. TLE2022xM Input Bias Current vs Free-Air Temperature



Data at high and low temperatures applicable only within rated operating free-air temperature ranges of the various devices

Figure 5-9. TLE2024xM Input Bias Current vs Free-Air Temperature




Figure 5-10. Input Current vs Differential Input Voltage




Figure 5-11. TLE2021xM Maximum Peak Output Voltage vs Output Current




Figure 5-12. TLE2022xM Maximum Peak Output Voltage vs Output Current

5.16 Typical Characteristics (continued)





Figure 5-13. TLE2024xM Maximum Peak Output Voltage vs Output Current



Data at high and low temperatures applicable only within rated operating free-air temperature ranges of the various devices

Figure 5-14. Maximum Peak Output Voltage vs Free-Air Temperature




Figure 5-15. TLE2021xM High-Level Output Voltage vs High-Level Output Current





Figure 5-16. TLE2022xM and TLE2024xM High-Level Output Voltage vs High-Level Output Current



Data at high and low temperatures applicable only within rated operating free-air temperature ranges of the various devices

Figure 5-17. High-Level Output Voltage vs Free-Air Temperature





Figure 5-18. Low-Level Output Voltage vs Low-Level Output Current

5.16 Typical Characteristics (continued)



Data at high and low temperatures applicable only within rated operating free-air temperature ranges of the various devices

Figure 5-19. Low-Level Output Voltage vs Free-Air Temperature




Figure 5-20. Maximum Peak-to-Peak Output Voltage Vs Frequency




Figure 5-21. Maximum Peak-to-Peak Output Voltage vs Frequency






Figure 5-22. Large-Signal Differential Voltage Amplification and Phase Shift vs Frequency



Data at high and low temperatures applicable only within rated operating free-air temperature ranges of the various devices


Figure 5-23. TLE2021xM Large-Scale Differential Voltage Amplification vs Free-Air Temperature



Data at high and low temperatures applicable only within rated operating free-air temperature ranges of the various devices

Figure 5-24. TLE2022xM Large-Signal Differential Voltage Amplification vs Free-Air Temperature

5.16 Typical Characteristics (continued)



Data at high and low temperatures applicable only within rated operating free-air temperature ranges of the various devices

Figure 5-25. TLE2024xM Large-Scale Differential Voltage Amplification vs Free-Air Temperature




Figure 5-26. TLE2021xM Short-Circuit Output Current vs Supply Voltage




Figure 5-27. TLE2022xM and TLE2024xM Short-Circuit Output Current vs Supply Voltage




Figure 5-28. TLE2021xM Short-Circuit Output Current vs Supply Voltage






Figure 5-29. TLE2022xM and TLE2024xM Short-Circuit Output Current vs Supply Voltage



Data at high and low temperatures applicable only within rated operating free-air temperature ranges of the various devices


Figure 5-30. TLE2021xM Short-Circuit Output Current vs Free-Air Temperature

5.16 Typical Characteristics (continued)




Data at high and low temperatures applicable only within rated operating free-air temperature ranges of the various devices

Figure 5-31. TLE2022xM and TLE2024xM Short-Circuit Output Current vs Free-Air Temperature



Data at high and low temperatures applicable only within rated operating free-air temperature ranges of the various devices

Figure 5-32. TLE2021xM Short-Circuit Output Current vs Free-Air Temperature



Data at high and low temperatures applicable only within rated operating free-air temperature ranges of the various devices

Figure 5-33. TLE2022xM and TLE2024xM Short-Circuit Output Current vs Free-Air Temperature




Figure 5-34. TLE2021xM Supply Current vs Supply Voltage




Figure 5-35. TLE2022xM Supply Current vs Supply Voltage






Figure 5-36. TLE2024xM Supply Current vs Supply Voltage

5.16 Typical Characteristics (continued)




Data at high and low temperatures applicable only within rated operating free-air temperature ranges of the various devices

Figure 5-37. TLE2021xM Supply Current vs Free-Air Temperature



Data at high and low temperatures applicable only within rated operating free-air temperature ranges of the various devices

Figure 5-38. TLE2022xM Supply Current vs Free-Air Temperature



Data at high and low temperatures applicable only within rated operating free-air temperature ranges of the various devices

Figure 5-39. TLE2024xM Supply Current vs Free-Air Temperature




Figure 5-40. TLE2021xM Common-Mode Rejection Ratio vs Frequency




Figure 5-41. TLE2022xM Common-Mode Rejection Ratio vs Frequency






Figure 5-42. TLE2024xM Common-Mode Rejection Ratio vs Frequency

5.16 Typical Characteristics (continued)




Data at high and low temperatures applicable only within rated operating free-air temperature ranges of the various devices

Figure 5-43. TLE2021xM Slew Rate vs Free-Air Temperature



Data at high and low temperatures applicable only within rated operating free-air temperature ranges of the various devices

Figure 5-44. TLE2022xM Slew Rate vs Free-Air Temperature



Data at high and low temperatures applicable only within rated operating free-air temperature ranges of the various devices

Figure 5-45. TLE2024xM Slew Rate vs Free-Air Temperature




Figure 5-46. Voltage-Follower Small-Signal Pulse Response




Figure 5-47. Voltage-Follower Small-Signal Pulse Response




Figure 5-48. TLE2021xM Voltage-Follower Large-Signal Pulse Response

5.16 Typical Characteristics (continued)




Figure 5-49. TLE2022xM Voltage-Follower Large-Signal Pulse Response




Figure 5-50. TLE2024xM Voltage-Follower Large-Scale Pulse Response




Figure 5-51. TLE2021xM Voltage-Follower Large-Signal Pulse Response




Figure 5-52. TLE2022xM Voltage-Follower Large-Signal Pulse Response




Figure 5-53. TLE2024xM Voltage-Follower Large-Signal Pulse Response




Figure 5-54. Peak-to-Peak Equivalent Input Noise Voltage 0.1Hz to 1Hz

5.16 Typical Characteristics (continued)




Figure 5-55. Peak-to-Peak Equivalent Input Noise Voltage 0.1Hz to 10Hz




Figure 5-56. Equivalent Input Noise Voltage vs Frequency




Figure 5-57. TLE2021xM Unity-Gain Bandwidth vs Supply Voltage






Figure 5-58. TLE2022xM and TLE2024xM Unity-Gain Bandwidth vs Supply Voltage



Data at high and low temperatures applicable only within rated operating free-air temperature ranges of the various devices

Figure 5-59. TLE2021xM Unity-Gain Bandwidth vs Free-Air Temperature



Data at high and low temperatures applicable only within rated operating free-air temperature ranges of the various devices

Figure 5-60. TLE2022xM and TLE2024xM Unity-Gain Bandwidth vs Free-Air Temperature

5.16 Typical Characteristics (continued)




Figure 5-61. TLE2021xM Phase Margin vs Supply Voltage




Figure 5-62. TLE2022xM and TLE2024xM Phase Margin vs Supply Voltage




Figure 5-63. TLE2021xM Phase Margin vs Load Capacitance






Figure 5-64. TLE2022xM and TLE2024xM Phase Margin vs Load Capacitance



Data at high and low temperatures applicable only within rated operating free-air temperature ranges of the various devices


Figure 5-65. TLE2021xM Phase Margin vs Free-Air Temperature




Data at high and low temperatures applicable only within rated operating free-air temperature ranges of the various devices

Figure 5-66. TLE2022xM and TLE2024xM Phase Margin vs Free-Air Temperature

6 Parameter Measurement Information




(a) SINGLE SUPPLY




(b) SPLIT SUPPLY

A. C_L includes fixture capacitance.

Figure 6-1. Slew-Rate Test Circuit




(a) SINGLE SUPPLY




(b) SPLIT SUPPLY

Figure 6-2. Noise-Voltage Test Circuit




(a) SINGLE SUPPLY



(b) SPLIT SUPPLY

A. C_L includes fixture capacitance.

Figure 6-3. Unity-Gain Bandwidth and Phase-Margin Test Circuit



A. C_L includes fixture capacitance.

Figure 6-4. Small-Signal Pulse-Response Test Circuit

6.1 Typical Values

Typical values presented in this data sheet represent the median (50% point) of device parametric performance.

7 Detailed Description

7.1 Functional Block Diagram




Figure 7-1. Equivalent Schematic (Each Amplifier)

Table 7-1. Actual Device Component Count

COMPONENT	TLE2021	TLE2022	TLE2024
Transistors	40	80	160
Resistors	7	14	28
Diodes	4	8	16
Capacitors	4	8	16

8 Application and Implementation

Note

Information in the following applications sections is not part of the TI component specification, and TI does not warrant its accuracy or completeness. TI's customers are responsible for determining suitability of components for their purposes, as well as validating and testing their design implementation to confirm system functionality.

8.1 Application Information

8.1.1 Voltage-Follower Applications

The TLE202xM circuitry includes input-protection diodes to limit the voltage across the input transistors; however, no provision is made in the circuit to limit the current if these diodes are forward biased. This condition sometimes occurs when the device is operated in the voltage-follower configuration and driven with a fast, large-signal pulse. Use a feedback resistor to limit the current to a maximum of 1mA to prevent degradation of the device. This feedback resistor forms a pole with the input capacitance of the device. For feedback resistor values greater than 10kΩ, this pole degrades the amplifier phase margin. Figure 8-1 shows that to alleviate this problem, add a capacitor (20pF to 50pF) in parallel with the feedback resistor.




Figure 8-1. Voltage Follower

8.1.2 Input Offset Voltage Null

The TLE202xM series offers external null pins that further reduce the input offset voltage. Figure 8-2 shows how to connect the circuit if this feature is desired. When external null is not needed, leave the null pins disconnected.




Figure 8-2. Input Offset Voltage Null Circuit

8.1.3 Macromodel Information

Macromodel information derived using Microsim Parts™, the model generation software used with PSpice™. The Boyle macromodel¹ (see subcircuit in Figure 8-3, Figure 8-4, and Figure 8-5) are generated using the TLE202x typical electrical and operating characteristics at 25°C. Using this information, output simulations of the following key parameters are generated to a tolerance of 20% (in most cases):

- Maximum positive output voltage swing
- Maximum negative output voltage swing
- Slew rate
- Quiescent power dissipation
- Input bias current
- Open-loop voltage amplification
- Unity-gain frequency
- Common-mode rejection ratio
- Phase margin
- DC output resistance
- AC output resistance
- Short-circuit output current limit




Figure 8-3. Boyle Subcircuit

¹ G. R. Boyle, B. M. Cohn, D. O. Pederson, and J. E. Solomon, "Macromodeling of Integrated Circuit Operational Amplifiers", *IEEE Journal of Solid-State Circuits*, SC-9, 353 (1974).

<pre>.SUBCKT TLE2021 1 2 3 4 5 * c111126.244E ! 12 c26713.4E ! 12 c387010.64E ! 9 cpsr858615.9E ! 9 dcm+8182dx dcm! 8381dx dc553dx de545dx dlp9091dx dln9290dx dp43dx ecmr8499(2 99) 1 egnd990poly(2) (3,0) (4,0) 0 .5 .5 epsr850poly(1) (3,4) ! 60E! 6 2.0E! 6 ense892poly(1) (88,0) 120E ! 6 1 fb799poly(6) vb vc ve vlp vln vpsr 0 547.3E6 + ! 50E7 50E7 50E7 ! 50E7 547E6 ga6011 12 188.5E ! 6 gcm0610 99 335.2E ! 12 gpsr8586(85,86) 100E ! 6 grc1411(4,11) 1.885E ! 4 grc2412(4,12) 1.885E ! 4 gre11310(13,10) 6.82E ! 4 gre21410(14,10) 6.82E ! 4 hlim900vlim 1k</pre>	<pre>hcmr801poly(2) vcm+ vcm ! 0 1E2 1E2 irp34185E ! 6 iee310dc 15.67E ! 6 iio202E ! 9 i18801E ! 21 q1118913 qx q2128014 qx R269100.0E3 rcm 84811K ree109914.76E6 rn18702.55E8 rn2878811.67E3 ro18562 ro279963 vcm+829913.3 vcm! 8399 ! 14.6 vb90dc 0 vc353dc 1.300 ve544dc 1.500 vlim78dc 0 vlp910dc 3.600 vln092dc 3.600 vpsr086dc 0 .model dx d(is=800.0E! 18) .model qx pnp(is=800.0E! 18 bf=270) .ends</pre>
--	---

Figure 8-4. Boyle Macromodel for the TLE2021xM

<pre>.SUBCKT TLE2022 1 2 3 4 5 * c11112 6.814E ! 12 c26720.00E ! 12 dc553 dx de545 dx dlp9091 dx dln9290 dx dp43 dx egnd 990poly(2) (3,0) (4,0) 0 .5 .5 fb799poly(5) vb vc ve vlp vln 0 + 45.47E6 ! 50E6 50E6 50E6 ! 50E6 ga 6011 12 377.9E ! 6 gcm 0610 99 7.84E ! 10 iee310 DC 18.07E ! 6 hlim 900 vlim 1k q1112 13 qx q2121 14 qx r269 100.0E3</pre>	<pre>rc1411 2.842E3 rc2412 2.842E3 ge11310 (10,13) 31.299E ! 3 ge21410 (10,14) 31.299E ! 3 ree1099 11.07E6 ro185 250 ro2799 250 rp34 137.2E3 vb90 dc 0 vc353 dc 1.300 ve544 dc 1.500 vlim78 dc 0 vlp910 dc 3 vln092 dc 3 .model dxd(is=800.0E ! 18) .model qxpnp(is=800.0E ! 18 bf=257.1) .ends</pre>
--	---

Figure 8-5. Boyle Macromodel for the TLE2022xM

9 Device and Documentation Support

TI offers an extensive line of development tools. Tools and software to evaluate the performance of the device, generate code, and develop solutions are listed below.

9.1 Receiving Notification of Documentation Updates

To receive notification of documentation updates, navigate to the device product folder on [ti.com](https://www.ti.com). Click on *Notifications* to register and receive a weekly digest of any product information that has changed. For change details, review the revision history included in any revised document.

9.2 Support Resources

[TI E2E™ support forums](#) are an engineer's go-to source for fast, verified answers and design help — straight from the experts. Search existing answers or ask your own question to get the quick design help you need.

Linked content is provided "AS IS" by the respective contributors. They do not constitute TI specifications and do not necessarily reflect TI's views; see TI's [Terms of Use](#).

9.3 Trademarks

Microsim Parts™ and PSpice™ are trademarks of Cadence Design Systems, Inc..

TI E2E™ is a trademark of Texas Instruments.

All trademarks are the property of their respective owners.

9.4 Electrostatic Discharge Caution



This integrated circuit can be damaged by ESD. Texas Instruments recommends that all integrated circuits be handled with appropriate precautions. Failure to observe proper handling and installation procedures can cause damage.

ESD damage can range from subtle performance degradation to complete device failure. Precision integrated circuits may be more susceptible to damage because very small parametric changes could cause the device not to meet its published specifications.

9.5 Glossary

[TI Glossary](#) This glossary lists and explains terms, acronyms, and definitions.

10 Revision History

NOTE: Page numbers for previous revisions may differ from page numbers in the current version.

Changes from Revision D (November 2010) to Revision E (July 2025)	Page
• Deleted obsolete Y-suffix device and associated content from data sheet.....	1
• Deleted DB and PW packages and associated content from data sheet.....	1
• Moved D, DW, N, and P devices and associated content to SLVSJD7.....	1
• Updated the numbering format for tables, figures, and cross-references throughout the document.....	1
• Added application circuit to <i>Description</i>	1

11 Mechanical, Packaging, and Orderable Information

The following pages include mechanical, packaging, and orderable information. This information is the most current data available for the designated devices. This data is subject to change without notice and revision of this document. For browser-based versions of this data sheet, refer to the left-hand navigation.

PACKAGING INFORMATION

Orderable part number	Status (1)	Material type (2)	Package Pins	Package qty Carrier	RoHS (3)	Lead finish/ Ball material (4)	MSL rating/ Peak reflow (5)	Op temp (°C)	Part marking (6)
5962-9088101MPA	Active	Production	CDIP (JG) 8	50 TUBE	No	SNPB	N/A for Pkg Type	-55 to 125	9088101MPA TLE2021M
5962-9088102M2A	Active	Production	LCCC (FK) 20	55 TUBE	No	SNPB	N/A for Pkg Type	-55 to 125	5962- 9088102M2A TLE2022MFKB
5962-9088102MPA	Active	Production	CDIP (JG) 8	50 TUBE	No	SNPB	N/A for Pkg Type	-55 to 125	9088102MPA TLE2022M
5962-9088103M2A	Active	Production	LCCC (FK) 20	55 TUBE	No	SNPB	N/A for Pkg Type	-55 to 125	5962- 9088103M2A TLE2024MFKB
5962-9088103MCA	Active	Production	CDIP (J) 14	25 TUBE	No	SNPB	N/A for Pkg Type	-55 to 125	5962-9088103MC A TLE2024MJB
5962-9088104Q2A	Active	Production	LCCC (FK) 20	55 TUBE	No	SNPB	N/A for Pkg Type	-55 to 125	5962- 9088104Q2A TLE2021 AMFKB
5962-9088104QPA	Active	Production	CDIP (JG) 8	50 TUBE	No	SNPB	N/A for Pkg Type	-55 to 125	9088104QPA TLE2021AM
5962-9088105Q2A	Active	Production	LCCC (FK) 20	55 TUBE	No	SNPB	N/A for Pkg Type	-55 to 125	5962- 9088105Q2A TLE2022A MFKB
5962-9088105QPA	Active	Production	CDIP (JG) 8	50 TUBE	No	SNPB	N/A for Pkg Type	-55 to 125	9088105QPA TLE2022AM
5962-9088106Q2A	Active	Production	LCCC (FK) 20	55 TUBE	No	SNPB	N/A for Pkg Type	-55 to 125	5962- 9088106Q2A TLE2024A MFKB
5962-9088106QCA	Active	Production	CDIP (J) 14	25 TUBE	No	SNPB	N/A for Pkg Type	-55 to 125	5962-9088106QC A TLE2024AMJB

Orderable part number	Status (1)	Material type (2)	Package Pins	Package qty Carrier	RoHS (3)	Lead finish/ Ball material (4)	MSL rating/ Peak reflow (5)	Op temp (°C)	Part marking (6)
5962-9088107Q2A	Active	Production	LCCC (FK) 20	55 TUBE	No	SNPB	N/A for Pkg Type	-55 to 125	5962- 9088107Q2A TLE2021 BMFKB
5962-9088107QPA	Active	Production	CDIP (JG) 8	50 TUBE	No	SNPB	N/A for Pkg Type	-55 to 125	9088107QPA TLE2021BM
5962-9088108Q2A	Active	Production	LCCC (FK) 20	55 TUBE	No	SNPB	N/A for Pkg Type	-55 to 125	5962- 9088108Q2A TLE2022B MFKB
5962-9088108QPA	Active	Production	CDIP (JG) 8	50 TUBE	No	SNPB	N/A for Pkg Type	-55 to 125	9088108QPA TLE2022BM
5962-9088109Q2A	Active	Production	LCCC (FK) 20	55 TUBE	No	SNPB	N/A for Pkg Type	-55 to 125	5962- 9088109Q2A TLE2024 BMFKB
5962-9088109QCA	Active	Production	CDIP (J) 14	25 TUBE	No	SNPB	N/A for Pkg Type	-55 to 125	5962-9088109QC A TLE2024BMJB
TLE2021AMFKB	Active	Production	LCCC (FK) 20	55 TUBE	No	SNPB	N/A for Pkg Type	-55 to 125	5962- 9088104Q2A TLE2021 AMFKB
TLE2021AMFKB.A	Active	Production	LCCC (FK) 20	55 TUBE	No	SNPB	N/A for Pkg Type	-55 to 125	5962- 9088104Q2A TLE2021 AMFKB
TLE2021AMJGB	Active	Production	CDIP (JG) 8	50 TUBE	No	SNPB	N/A for Pkg Type	-55 to 125	9088104QPA TLE2021AM
TLE2021AMJGB.A	Active	Production	CDIP (JG) 8	50 TUBE	No	SNPB	N/A for Pkg Type	-55 to 125	9088104QPA TLE2021AM
TLE2021BMFKB	Active	Production	LCCC (FK) 20	55 TUBE	No	SNPB	N/A for Pkg Type	-	5962- 9088107Q2A TLE2021 BMFKB

Orderable part number	Status (1)	Material type (2)	Package Pins	Package qty Carrier	RoHS (3)	Lead finish/ Ball material (4)	MSL rating/ Peak reflow (5)	Op temp (°C)	Part marking (6)
TLE2021BMFKB.A	Active	Production	LCCC (FK) 20	55 TUBE	No	SNPB	N/A for Pkg Type	-55 to 125	5962- 9088107Q2A TLE2021 BMFKB
TLE2021BMJG	Active	Production	CDIP (JG) 8	50 TUBE	No	SNPB	N/A for Pkg Type	-55 to 125	TLE2021 BMJG
TLE2021BMJG.A	Active	Production	CDIP (JG) 8	50 TUBE	No	SNPB	N/A for Pkg Type	-55 to 125	TLE2021 BMJG
TLE2021BMJGB	Active	Production	CDIP (JG) 8	50 TUBE	No	SNPB	N/A for Pkg Type	-	9088107QPA TLE2021BM
TLE2021BMJGB.A	Active	Production	CDIP (JG) 8	50 TUBE	No	SNPB	N/A for Pkg Type	-55 to 125	9088107QPA TLE2021BM
TLE2021MJG	Active	Production	CDIP (JG) 8	50 TUBE	No	SNPB	N/A for Pkg Type	-55 to 125	TLE2021MJG
TLE2021MJG.A	Active	Production	CDIP (JG) 8	50 TUBE	No	SNPB	N/A for Pkg Type	-55 to 125	TLE2021MJG
TLE2021MJGB	Active	Production	CDIP (JG) 8	50 TUBE	No	SNPB	N/A for Pkg Type	-55 to 125	9088101MPA TLE2021M
TLE2021MJGB.A	Active	Production	CDIP (JG) 8	50 TUBE	No	SNPB	N/A for Pkg Type	-55 to 125	9088101MPA TLE2021M
TLE2022AMFKB	Active	Production	LCCC (FK) 20	55 TUBE	No	SNPB	N/A for Pkg Type	-55 to 125	5962- 9088105Q2A TLE2022A MFKB
TLE2022AMFKB.A	Active	Production	LCCC (FK) 20	55 TUBE	No	SNPB	N/A for Pkg Type	-55 to 125	5962- 9088105Q2A TLE2022A MFKB
TLE2022AMJGB	Active	Production	CDIP (JG) 8	50 TUBE	No	SNPB	N/A for Pkg Type	-55 to 125	9088105QPA TLE2022AM
TLE2022AMJGB.A	Active	Production	CDIP (JG) 8	50 TUBE	No	SNPB	N/A for Pkg Type	-55 to 125	9088105QPA TLE2022AM
TLE2022BMFKB	Active	Production	LCCC (FK) 20	55 TUBE	No	SNPB	N/A for Pkg Type	-55 to 125	5962- 9088108Q2A TLE2022B MFKB

Orderable part number	Status (1)	Material type (2)	Package Pins	Package qty Carrier	RoHS (3)	Lead finish/ Ball material (4)	MSL rating/ Peak reflow (5)	Op temp (°C)	Part marking (6)
TLE2022BMFKB.A	Active	Production	LCCC (FK) 20	55 TUBE	No	SNPB	N/A for Pkg Type	-55 to 125	5962- 9088108Q2A TLE2022B MFKB
TLE2022BMJGB	Active	Production	CDIP (JG) 8	50 TUBE	No	SNPB	N/A for Pkg Type	-55 to 125	9088108QPA TLE2022BM
TLE2022BMJGB.A	Active	Production	CDIP (JG) 8	50 TUBE	No	SNPB	N/A for Pkg Type	-55 to 125	9088108QPA TLE2022BM
TLE2022MFKB	Active	Production	LCCC (FK) 20	55 TUBE	No	SNPB	N/A for Pkg Type	-55 to 125	5962- 9088102M2A TLE2022MFKB
TLE2022MFKB.A	Active	Production	LCCC (FK) 20	55 TUBE	No	SNPB	N/A for Pkg Type	-55 to 125	5962- 9088102M2A TLE2022MFKB
TLE2022MJG	Active	Production	CDIP (JG) 8	50 TUBE	No	SNPB	N/A for Pkg Type	-55 to 125	TLE2022MJG
TLE2022MJG.A	Active	Production	CDIP (JG) 8	50 TUBE	No	SNPB	N/A for Pkg Type	-55 to 125	TLE2022MJG
TLE2022MJGB	Active	Production	CDIP (JG) 8	50 TUBE	No	SNPB	N/A for Pkg Type	-55 to 125	9088102MPA TLE2022M
TLE2022MJGB.A	Active	Production	CDIP (JG) 8	50 TUBE	No	SNPB	N/A for Pkg Type	-55 to 125	9088102MPA TLE2022M
TLE2024AMFKB	Active	Production	LCCC (FK) 20	55 TUBE	No	SNPB	N/A for Pkg Type	-55 to 125	5962- 9088106Q2A TLE2024A MFKB
TLE2024AMFKB.A	Active	Production	LCCC (FK) 20	55 TUBE	No	SNPB	N/A for Pkg Type	-55 to 125	5962- 9088106Q2A TLE2024A MFKB
TLE2024AMJB	Active	Production	CDIP (J) 14	25 TUBE	No	SNPB	N/A for Pkg Type	-55 to 125	5962-9088106QC A TLE2024AMJB
TLE2024AMJB.A	Active	Production	CDIP (J) 14	25 TUBE	No	SNPB	N/A for Pkg Type	-55 to 125	5962-9088106QC A TLE2024AMJB

Orderable part number	Status (1)	Material type (2)	Package Pins	Package qty Carrier	RoHS (3)	Lead finish/ Ball material (4)	MSL rating/ Peak reflow (5)	Op temp (°C)	Part marking (6)
TLE2024BMFKB	Active	Production	LCCC (FK) 20	55 TUBE	No	SNPB	N/A for Pkg Type	-55 to 125	5962-9088109Q2A TLE2024 BMFKB
TLE2024BMFKB.A	Active	Production	LCCC (FK) 20	55 TUBE	No	SNPB	N/A for Pkg Type	-55 to 125	5962-9088109Q2A TLE2024 BMFKB
TLE2024BMJ	Active	Production	CDIP (J) 14	25 TUBE	No	SNPB	N/A for Pkg Type	-55 to 125	TLE2024BMJ
TLE2024BMJ.A	Active	Production	CDIP (J) 14	25 TUBE	No	SNPB	N/A for Pkg Type	-55 to 125	TLE2024BMJ
TLE2024BMJB	Active	Production	CDIP (J) 14	25 TUBE	No	SNPB	N/A for Pkg Type	-55 to 125	5962-9088109QC A TLE2024BMJB
TLE2024BMJB.A	Active	Production	CDIP (J) 14	25 TUBE	No	SNPB	N/A for Pkg Type	-55 to 125	5962-9088109QC A TLE2024BMJB
TLE2024MFKB	Active	Production	LCCC (FK) 20	55 TUBE	No	SNPB	N/A for Pkg Type	-55 to 125	5962-9088103M2A TLE2024MFKB
TLE2024MFKB.A	Active	Production	LCCC (FK) 20	55 TUBE	No	SNPB	N/A for Pkg Type	-55 to 125	5962-9088103M2A TLE2024MFKB
TLE2024MJB	Active	Production	CDIP (J) 14	25 TUBE	No	SNPB	N/A for Pkg Type	-55 to 125	5962-9088103MC A TLE2024MJB
TLE2024MJB.A	Active	Production	CDIP (J) 14	25 TUBE	No	SNPB	N/A for Pkg Type	-55 to 125	5962-9088103MC A TLE2024MJB

⁽¹⁾ **Status:** For more details on status, see our [product life cycle](#).

⁽²⁾ **Material type:** When designated, preproduction parts are prototypes/experimental devices, and are not yet approved or released for full production. Testing and final process, including without limitation quality assurance, reliability performance testing, and/or process qualification, may not yet be complete, and this item is subject to further changes or possible discontinuation. If available for ordering, purchases will be subject to an additional waiver at checkout, and are intended for early internal evaluation purposes only. These items are sold without warranties of any kind.

⁽³⁾ **RoHS values:** Yes, No, RoHS Exempt. See the [TI RoHS Statement](#) for additional information and value definition.

⁽⁴⁾ **Lead finish/Ball material:** Parts may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead finish/Ball material values may wrap to two lines if the finish value exceeds the maximum column width.

⁽⁵⁾ **MSL rating/Peak reflow:** The moisture sensitivity level ratings and peak solder (reflow) temperatures. In the event that a part has multiple moisture sensitivity ratings, only the lowest level per JEDEC standards is shown. Refer to the shipping label for the actual reflow temperature that will be used to mount the part to the printed circuit board.

⁽⁶⁾ **Part marking:** There may be an additional marking, which relates to the logo, the lot trace code information, or the environmental category of the part.

Multiple part markings will be inside parentheses. Only one part marking contained in parentheses and separated by a "~" will appear on a part. If a line is indented then it is a continuation of the previous line and the two combined represent the entire part marking for that device.

Important Information and Disclaimer: The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.


In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.

OTHER QUALIFIED VERSIONS OF TLE2021AM, TLE2024AM, TLE2024M :

- Catalog : [TLE2021A](#), [TLE2024A](#), [TLE2024](#)
- Automotive : [TLE2021A-Q1](#), [TLE2024-Q1](#)
- Enhanced Product : [TLE2021A-EP](#), [TLE2024A-EP](#), [TLE2024-EP](#)

NOTE: Qualified Version Definitions:

- Catalog - TI's standard catalog product
- Automotive - Q100 devices qualified for high-reliability automotive applications targeting zero defects
- Enhanced Product - Supports Defense, Aerospace and Medical Applications

TUBE


*All dimensions are nominal

Device	Package Name	Package Type	Pins	SPQ	L (mm)	W (mm)	T (μm)	B (mm)
5962-9088102M2A	FK	LCCC	20	55	506.98	12.06	2030	NA
5962-9088103M2A	FK	LCCC	20	55	506.98	12.06	2030	NA
5962-9088104Q2A	FK	LCCC	20	55	506.98	12.06	2030	NA
5962-9088105Q2A	FK	LCCC	20	55	506.98	12.06	2030	NA
5962-9088106Q2A	FK	LCCC	20	55	506.98	12.06	2030	NA
5962-9088107Q2A	FK	LCCC	20	55	506.98	12.06	2030	NA
5962-9088108Q2A	FK	LCCC	20	55	506.98	12.06	2030	NA
5962-9088109Q2A	FK	LCCC	20	55	506.98	12.06	2030	NA
TLE2021AMFKB	FK	LCCC	20	55	506.98	12.06	2030	NA
TLE2021AMFKB.A	FK	LCCC	20	55	506.98	12.06	2030	NA
TLE2021BMFKB	FK	LCCC	20	55	506.98	12.06	2030	NA
TLE2021BMFKB.A	FK	LCCC	20	55	506.98	12.06	2030	NA
TLE2022AMFKB	FK	LCCC	20	55	506.98	12.06	2030	NA
TLE2022AMFKB.A	FK	LCCC	20	55	506.98	12.06	2030	NA
TLE2022BMFKB	FK	LCCC	20	55	506.98	12.06	2030	NA
TLE2022BMFKB.A	FK	LCCC	20	55	506.98	12.06	2030	NA
TLE2022MFKB	FK	LCCC	20	55	506.98	12.06	2030	NA
TLE2022MFKB.A	FK	LCCC	20	55	506.98	12.06	2030	NA
TLE2024AMFKB	FK	LCCC	20	55	506.98	12.06	2030	NA
TLE2024AMFKB.A	FK	LCCC	20	55	506.98	12.06	2030	NA
TLE2024BMFKB	FK	LCCC	20	55	506.98	12.06	2030	NA
TLE2024BMFKB.A	FK	LCCC	20	55	506.98	12.06	2030	NA
TLE2024MFKB	FK	LCCC	20	55	506.98	12.06	2030	NA
TLE2024MFKB.A	FK	LCCC	20	55	506.98	12.06	2030	NA

JG0008A

CDIP - 5.08 mm max height

CERAMIC DUAL IN-LINE PACKAGE




1. All linear dimensions are in millimeters. Any dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.
2. This drawing is subject to change without notice.
3. This package can be hermetically sealed with a ceramic lid using glass frit.
4. Index point is provided on cap for terminal identification.
5. Falls within MIL STD 1835 GDIP1-T8

EXAMPLE BOARD LAYOUT

JG0008A

CDIP - 5.08 mm max height

CERAMIC DUAL IN-LINE PACKAGE



GENERIC PACKAGE VIEW


FK 20

LCCC - 2.03 mm max height

8.89 x 8.89, 1.27 mm pitch

LEADLESS CERAMIC CHIP CARRIER

This image is a representation of the package family, actual package may vary.
Refer to the product data sheet for package details.




4229370VA\

J 14

GENERIC PACKAGE VIEW


CDIP - 5.08 mm max height

CERAMIC DUAL IN LINE PACKAGE




Images above are just a representation of the package family, actual package may vary.
Refer to the product data sheet for package details.

4040083-5/G

J0014A**PACKAGE OUTLINE****CDIP - 5.08 mm max height**

CERAMIC DUAL IN LINE PACKAGE



4214771/A 05/2017

NOTES:

1. All controlling linear dimensions are in inches. Dimensions in brackets are in millimeters. Any dimension in brackets or parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.
2. This drawing is subject to change without notice.
3. This package is hermetically sealed with a ceramic lid using glass frit.
4. Index point is provided on cap for terminal identification only and on press ceramic glass frit seal only.
5. Falls within MIL-STD-1835 and GDIP1-T14.



**TEXAS
INSTRUMENTS**
www.ti.com

IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATASHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, regulatory or other requirements.

These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you fully indemnify TI and its representatives against any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to [TI's Terms of Sale](#), [TI's General Quality Guidelines](#), or other applicable terms available either on [ti.com](#) or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products. Unless TI explicitly designates a product as custom or customer-specified, TI products are standard, catalog, general purpose devices.

TI objects to and rejects any additional or different terms you may propose.

Copyright © 2026, Texas Instruments Incorporated

Last updated 10/2025