

# TLC1078, TLC1078Y, TLC1079, TLC1079Y

## LinCMOS™ $\mu$ POWER PRECISION OPERATIONAL AMPLIFIERS

SLOS179A – FEBRUARY 1997 – REVISED MARCH 2001




- Power Dissipation as Low as 10  $\mu$ W Typ Per Amplifier
- Operates on a Single Silver-Oxide Watch Battery,  $V_{DD} = 1.4$  V Min
- $V_{IO} \dots 450 \mu$ V/850  $\mu$ V Max in DIP and Small-Outline Package (TLC1078/79)
- Input Offset Voltage Drift  $\dots 0.1 \mu$ V/Month Typ, Including the First 30 Days
- High-impedance LinCMOS™ Inputs  
 $I_B = 0.6$  pA Typ
- High Open-Loop Gain  $\dots 800000$  Typ
- Output Drive Capability > 20 mA
- Slew Rate  $\dots 47$  V/ms Typ
- Common-Mode Input Voltage Range Extends Below the Negative Rail
- Output Voltage Range Includes Negative Rail
- On-Chip ESD-Protection Circuitry
- Small-Outline Package Option Also Available in Tape and Reel

### description

The TLC107x operational amplifiers offer ultra-low offset voltage, high gain, 110-kHz bandwidth, 47-V/ms slew rate, and just 150- $\mu$ W power dissipation per amplifier.

With a supply voltage of 1.4 V, common-mode input to the negative rail, and output swing to the negative rail, the TLC107xC is an ideal solution for low-voltage battery-operated systems. The 20-mA output drive capability means that the TLC107x can easily drive small resistive and large capacitive loads when needed, while maintaining ultra-low standby power dissipation.

Since this device is functionally compatible as well as pin compatible with the TLC27L2/4 and TLC27L7/9, the TLC107x easily upgrades existing designs that can benefit from its improved performance.



NC – No internal connection



Please be aware that an important notice concerning availability, standard warranty, and use in critical applications of Texas Instruments semiconductor products and disclaimers thereto appears at the end of this data sheet.

LinCMOS is a trademark of Texas Instruments Incorporated.

PRODUCTION DATA information is current as of publication date. Products conform to specifications per the terms of Texas Instruments standard warranty. Production processing does not necessarily include testing of all parameters.



POST OFFICE BOX 655303 • DALLAS, TEXAS 75265

Copyright © 2001, Texas Instruments Incorporated

**description (continued)**

The TLC107x incorporates internal ESD-protection circuits that will prevent functional failures at voltages up to 2000 V as tested under MIL-PRF-38535, Method 3015.2; however, care should be exercised when handling these devices as exposure to ESD may result in degradation of the device parametric performance. The TLC107x design also inhibits latch-up of the device inputs and outputs even with surge currents as large as 100 mA.


The C-suffix devices are characterized for operation from 0°C to 70°C. The I-suffix devices are characterized for operation from –40°C to 85°C. The M-suffix devices are characterized for operation over the full military temperature range of –55°C to 125°C. The wide range of packaging options includes small-outline and chip-carrier versions for high-density system applications.

**AVAILABLE OPTIONS**

| T <sub>A</sub> | PACKAGED DEVICES                  |                          |                    |                     |                    |                    | CHIP FORM <sup>‡</sup><br>(Y) |
|----------------|-----------------------------------|--------------------------|--------------------|---------------------|--------------------|--------------------|-------------------------------|
|                | SMALL OUTLINE <sup>†</sup><br>(D) | CHIP CARRIER<br>(FK)     | CERAMIC DIP<br>(J) | CERAMIC DIP<br>(JG) | PLASTIC DIP<br>(N) | PLASTIC DIP<br>(P) |                               |
| 0°C to 70°C    | TLC1078CD<br>TLC1079CD            | —                        | —                  | —                   | TLC1079CN          | TLC1078CP          | TLC1078Y<br>TLC1079Y          |
| –40°C to 85°C  | TLC1078ID<br>TLC1079ID            | —                        | —                  | —                   | TLC1079IN          | TLC1078IP          | —                             |
| –55°C to 125°C | TLC1078MD<br>TLC1079MD            | TLC1078MFK<br>TLC1079MFK | TLC1079MJ          | TLC1078MJG          | TLC1079MN          | TLC1078MP          | —                             |


<sup>†</sup> The D package is available taped and reeled. Add the suffix R to the device type (e.g., TLC1078CDR).

<sup>‡</sup> Chip forms are tested 25°C only.

**symbol (each amplifier)**

## TLC1078Y chip information

This chip, when properly assembled, displays characteristics similar to the TLC1078C. Thermal compression or ultrasonic bonding may be used on the doped-aluminum bonding pads. Chips can be mounted with conductive epoxy or a gold-silicon preform.




# TLC1078, TLC1078Y, TLC1079, TLC1079Y

## LinCMOS™ $\mu$ POWER PRECISION OPERATIONAL AMPLIFIERS


SLOS179A – FEBRUARY 1997 – REVISED MARCH 2001

### TLC1079Y chip information

This chip, when properly assembled, display characteristics similar to the TLC1079C. Thermal compression or ultrasonic bonding may be used on the doped-aluminum bonding pads. Chips can be mounted with conductive epoxy or a gold-silicon preform.



equivalent schematic (each amplifier)



| ACTUAL DEVICE COMPONENT COUNT |         |         |
|-------------------------------|---------|---------|
| COMPONENT                     | TLC1078 | TLC1079 |
| Transistors                   | 38      | 76      |
| Resistors                     | 16      | 32      |
| Diodes                        | 12      | 24      |
| Capacitors                    | 2       | 4       |

**absolute maximum ratings over operating free-air temperature range (unless otherwise noted)<sup>†</sup>**

|                                                                               |                                          |
|-------------------------------------------------------------------------------|------------------------------------------|
| Supply voltage, $V_{DD}$ (see Note 1)                                         | 18 V                                     |
| Differential input voltage, $V_{ID}$ (see Note 2)                             | $\pm V_{DD}$                             |
| Input voltage range, $V_I$ (any input)                                        | $-0.3\text{ V to }V_{DD}$                |
| Input current, $I_I$ (each input)                                             | $\pm 5\text{ mA}$                        |
| Output current, $I_O$ (each output)                                           | $\pm 30\text{ mA}$                       |
| Total current into $V_{DD}$ (see Note 3)                                      | 45 mA                                    |
| Duration of short-circuit at (or below) $T_A = 25^\circ\text{C}$ (see Note 3) | unlimited                                |
| Continuous total power dissipation                                            | see Dissipation Rating Table             |
| Operating free-air temperature range, $T_A$ : C suffix                        | $0^\circ\text{C to }70^\circ\text{C}$    |
| I suffix                                                                      | $-40^\circ\text{C to }85^\circ\text{C}$  |
| M suffix                                                                      | $-55^\circ\text{C to }125^\circ\text{C}$ |
| Storage temperature range                                                     | $-65^\circ\text{C to }150^\circ\text{C}$ |
| Case temperature for 60 seconds: FK package                                   | $260^\circ\text{C}$                      |
| Lead temperature 1,6 mm (1/16 inch) from case for 10 seconds: D or P package  | $260^\circ\text{C}$                      |
| Lead temperature 1,6 mm (1/16 inch) from case for 60 seconds: JG package      | $300^\circ\text{C}$                      |

<sup>†</sup> Stresses beyond those listed under "absolute maximum ratings" may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated under "recommended operating conditions" is not implied. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability.

NOTES: 1. All voltage values, except differential voltages, are with respect to network ground.  
2. Differential voltages are at  $IN+$  with respect to  $IN-$ .  
3. The output may be shorted to either supply. Temperature and/or supply voltages must be limited to ensure that the maximum dissipation ratings are not exceeded.

**DISSIPATION RATING TABLE**

| PACKAGE | $T_A \leq 25^\circ\text{C}$<br>POWER RATING | DERATING FACTOR<br>ABOVE $T_A = 25^\circ\text{C}$ | $T_A = 70^\circ\text{C}$<br>POWER RATING | $T_A = 85^\circ\text{C}$<br>POWER RATING | $T_A = 125^\circ\text{C}$<br>POWER RATING |
|---------|---------------------------------------------|---------------------------------------------------|------------------------------------------|------------------------------------------|-------------------------------------------|
| D-8     | 725 mW                                      | $5.8\text{ mW}/^\circ\text{C}$                    | 464 mW                                   | 377 mW                                   | 145 mW                                    |
| D-14    | 950 mW                                      | $7.6\text{ mW}/^\circ\text{C}$                    | 608 mW                                   | 494 mW                                   | 190 mW                                    |
| FK      | 1375 mW                                     | $11.0\text{ mW}/^\circ\text{C}$                   | 880 mW                                   | 715 mW                                   | 275 mW                                    |
| J       | 1375 mW                                     | $11.0\text{ mW}/^\circ\text{C}$                   | 880 mW                                   | 715 mW                                   | 275 mW                                    |
| JG      | 1050 mW                                     | $8.4\text{ mW}/^\circ\text{C}$                    | 672 mW                                   | 546 mW                                   | 210 mW                                    |
| N       | 1150 mW                                     | $9.2\text{ mW}/^\circ\text{C}$                    | 736 mW                                   | 598 mW                                   | 230 mW                                    |
| P       | 1000 mW                                     | $8.0\text{ mW}/^\circ\text{C}$                    | 640 mW                                   | 520 mW                                   | 200 mW                                    |

**recommended operating conditions**

|                                       |                        | C SUFFIX |     | I SUFFIX |     | M SUFFIX |     | UNIT             |
|---------------------------------------|------------------------|----------|-----|----------|-----|----------|-----|------------------|
|                                       |                        | MIN      | MAX | MIN      | MAX | MIN      | MAX |                  |
| Supply voltage, $V_{DD}$              |                        | 1.4      | 16  | 3        | 16  | 4        | 16  | V                |
| Common-mode input voltage, $V_{IC}$   | $V_{DD} = 5\text{ V}$  | -0.2     | 4   | -0.2     | 4   | 0        | 4   | V                |
|                                       | $V_{DD} = 10\text{ V}$ | -0.2     | 9   | -0.2     | 9   | 0        | 9   |                  |
| Operating free-air temperature, $T_A$ |                        | 0        | 70  | -40      | 85  | -55      | 125 | $^\circ\text{C}$ |

**TLC1078, TLC1078Y, TLC1079, TLC1079Y**  
**LinCMOS™  $\mu$ POWER PRECISION**  
**OPERATIONAL AMPLIFIERS**

SLOS179A – FEBRUARY 1997 – REVISED MARCH 2001

**electrical characteristics at specified free-air temperature**

| PARAMETER        |                                                                      | TEST CONDITIONS                                                                                    | T <sub>A</sub> <sup>†</sup> | TLC1078C              |                |                |                        |                |      | UNIT  |
|------------------|----------------------------------------------------------------------|----------------------------------------------------------------------------------------------------|-----------------------------|-----------------------|----------------|----------------|------------------------|----------------|------|-------|
|                  |                                                                      |                                                                                                    |                             | V <sub>DD</sub> = 5 V |                |                | V <sub>DD</sub> = 10 V |                |      |       |
|                  |                                                                      |                                                                                                    |                             | MIN                   | TYP            | MAX            | MIN                    | TYP            | MAX  |       |
| V <sub>IO</sub>  | Input offset voltage                                                 | V <sub>O</sub> = 1.4 V,<br>R <sub>S</sub> = 50 Ω,<br>V <sub>IC</sub> = 0,<br>R <sub>I</sub> = 1 MΩ | 25°C                        |                       | 160            | 450            |                        | 180            | 600  | μV    |
|                  |                                                                      |                                                                                                    | Full range                  |                       |                | 800            |                        |                | 950  |       |
| α <sub>VIO</sub> | Temperature coefficient of input offset voltage                      |                                                                                                    | 25°C to 70°C                |                       | 1.1            |                |                        | 1              |      | μV/°C |
| I <sub>IO</sub>  | Input offset current (see Note 4)                                    | V <sub>O</sub> = V <sub>DD</sub> / 2,<br>V <sub>IC</sub> = V <sub>DD</sub> / 2                     | 25°C                        |                       | 0.1            | 60             |                        | 0.1            | 60   | pA    |
|                  |                                                                      |                                                                                                    | 70°C                        |                       | 7              | 300            |                        | 7              | 300  |       |
| I <sub>IB</sub>  | Input bias current (see Note 4)                                      |                                                                                                    | 25°C                        |                       | 0.6            | 60             |                        | 0.7            | 60   | pA    |
|                  |                                                                      |                                                                                                    | 70°C                        |                       | 40             | 600            |                        | 50             | 600  |       |
| V <sub>ICR</sub> | Common-mode input voltage range (see Note 5)                         |                                                                                                    | 25°C                        | −0.2<br>to 4          | −0.3<br>to 4.2 |                | −0.2<br>to 9           | −0.3<br>to 9.2 | V    |       |
|                  |                                                                      |                                                                                                    | Full range                  | −0.2<br>to 3.5        |                | −0.2<br>to 8.5 |                        | V              |      |       |
| V <sub>OH</sub>  | High-level output voltage                                            | V <sub>ID</sub> = 100 mV,<br>R <sub>L</sub> = 1 MΩ                                                 | 25°C                        | 3.2                   | 4.1            |                | 8.2                    | 8.9            | V    |       |
|                  |                                                                      |                                                                                                    | 0°C                         | 3.2                   | 4.1            |                | 8.2                    | 8.9            |      |       |
|                  |                                                                      |                                                                                                    | 70°C                        | 3.2                   | 4.2            |                | 8.2                    | 8.9            |      |       |
| V <sub>OL</sub>  | Low-level output voltage                                             | V <sub>ID</sub> = −100 mV,<br>I <sub>OL</sub> = 0                                                  | 25°C                        |                       | 0              | 25             |                        | 0              | 25   | mV    |
|                  |                                                                      |                                                                                                    | 0°C                         |                       | 0              | 25             |                        | 0              | 25   |       |
|                  |                                                                      |                                                                                                    | 70°C                        |                       | 0              | 25             |                        | 0              | 25   |       |
| A <sub>VD</sub>  | Large-signal differential voltage amplification                      | R <sub>L</sub> = 1 MΩ,<br>See Note 6                                                               | 25°C                        | 250                   | 525            |                | 500                    | 850            | V/mV |       |
|                  |                                                                      |                                                                                                    | 0°C                         | 250                   | 680            |                | 500                    | 1010           |      |       |
|                  |                                                                      |                                                                                                    | 70°C                        | 200                   | 380            |                | 350                    | 660            |      |       |
| CMRR             | Common-mode rejection ratio                                          | V <sub>IC</sub> = V <sub>ICRmin</sub>                                                              | 25°C                        | 70                    | 95             |                | 75                     | 97             | dB   |       |
|                  |                                                                      |                                                                                                    | 0°C                         | 70                    | 95             |                | 75                     | 97             |      |       |
|                  |                                                                      |                                                                                                    | 70°C                        | 70                    | 95             |                | 75                     | 97             |      |       |
| k <sub>SVR</sub> | Supply-voltage rejection ratio (ΔV <sub>DD</sub> /ΔV <sub>IO</sub> ) | V <sub>O</sub> = 1.4 V                                                                             | 25°C                        | 75                    | 98             |                | 75                     | 98             | dB   |       |
|                  |                                                                      |                                                                                                    | 0°C                         | 75                    | 98             |                | 75                     | 98             |      |       |
|                  |                                                                      |                                                                                                    | 70°C                        | 75                    | 98             |                | 75                     | 98             |      |       |
| I <sub>DD</sub>  | Supply current (two amplifiers)                                      | V <sub>O</sub> = V <sub>DD</sub> / 2,<br>V <sub>IC</sub> = V <sub>DD</sub> / 2,<br>No load         | 25°C                        |                       | 20             | 34             |                        | 29             | 46   | μA    |
|                  |                                                                      |                                                                                                    | 0°C                         |                       | 24             | 42             |                        | 36             | 66   |       |
|                  |                                                                      |                                                                                                    | 70°C                        |                       | 16             | 28             |                        | 22             | 40   |       |

$^\dagger$  Full range is 0°C to 70°C.

NOTES: 4. The typical values of input bias current and input offset current below 5 pA were determined mathematically.

5. This range also applies to each input individually.

6. At  $V_{DD} = 5\text{ V}$ ,  $V_O = 0.25\text{ V}$  to  $2\text{ V}$ ; at  $V_{DD} = 10\text{ V}$ ,  $V_O = 1\text{ V}$  to  $6\text{ V}$ .

# TLC1078, TLC1078Y, TLC1079, TLC1079Y

## LinCMOS™ $\mu$ POWER PRECISION

### OPERATIONAL AMPLIFIERS

SLOS179A – FEBRUARY 1997 – REVISED MARCH 2001

#### electrical characteristics at specified free-air temperature

| PARAMETER        |                                                                      | TEST CONDITIONS                                                                              | T <sub>A</sub> <sup>†</sup> | TLC1079C              |             |             |                        |       |     | UNIT |
|------------------|----------------------------------------------------------------------|----------------------------------------------------------------------------------------------|-----------------------------|-----------------------|-------------|-------------|------------------------|-------|-----|------|
|                  |                                                                      |                                                                                              |                             | V <sub>DD</sub> = 5 V |             |             | V <sub>DD</sub> = 10 V |       |     |      |
|                  |                                                                      |                                                                                              |                             | MIN                   | TYP         | MAX         | MIN                    | TYP   | MAX |      |
| V <sub>IO</sub>  | Input offset voltage                                                 | V <sub>O</sub> = 1.4 V, V <sub>IC</sub> = 0,<br>R <sub>S</sub> = 50 Ω, R <sub>I</sub> = 1 MΩ | 25°C                        | 190                   | 850         | 200         | 1150                   | μV    |     |      |
|                  |                                                                      |                                                                                              | Full range                  | 1200                  |             |             | 1500                   |       |     |      |
| α <sub>VIO</sub> | Temperature coefficient of input offset voltage                      |                                                                                              | 25°C to 70°C                | 1.1                   |             | 1           |                        | μV/°C |     |      |
| I <sub>IO</sub>  | Input offset current (see Note 4)                                    | V <sub>O</sub> = V <sub>DD</sub> / 2,<br>V <sub>IC</sub> = V <sub>DD</sub> / 2               | 25°C                        | 0.1                   | 60          | 0.1         | 60                     | pA    |     |      |
|                  |                                                                      |                                                                                              | 70°C                        | 7                     | 300         | 7           | 300                    |       |     |      |
| I <sub>IB</sub>  | Input bias current (see Note 4)                                      |                                                                                              | 25°C                        | 0.6                   | 60          | 0.7         | 60                     | pA    |     |      |
|                  |                                                                      |                                                                                              | 70°C                        | 40                    | 600         | 50          | 600                    |       |     |      |
| V <sub>ICR</sub> | Common mode input voltage range (see Note 5)                         |                                                                                              | 25°C                        | −0.2 to 4             | −0.3 to 4.2 | −0.2 to 9   | −0.3 to 9.2            | V     |     |      |
|                  |                                                                      |                                                                                              | Full range                  | −0.2 to 3.5           |             | −0.2 to 8.5 |                        | V     |     |      |
| V <sub>OH</sub>  | High-level output voltage                                            | V <sub>ID</sub> = 100 mV,<br>R <sub>L</sub> = 1 MΩ                                           | 25°C                        | 3.2                   | 4.1         | 8.2         | 8.9                    | V     |     |      |
|                  |                                                                      |                                                                                              | 0°C                         | 3.2                   | 4.1         | 8.2         | 8.9                    |       |     |      |
|                  |                                                                      |                                                                                              | 70°C                        | 3.2                   | 4.2         | 8.2         | 8.9                    |       |     |      |
| V <sub>OL</sub>  | Low-level output voltage                                             | V <sub>ID</sub> = −100 mV,<br>I <sub>OL</sub> = 0                                            | 25°C                        | 0                     | 25          | 0           | 25                     | mV    |     |      |
|                  |                                                                      |                                                                                              | 0°C                         | 0                     | 25          | 0           | 25                     |       |     |      |
|                  |                                                                      |                                                                                              | 70°C                        | 0                     | 25          | 0           | 25                     |       |     |      |
| A <sub>VD</sub>  | Large-signal differential voltage amplification                      | R <sub>L</sub> = 1 MΩ, See Note 6                                                            | 25°C                        | 250                   | 525         | 500         | 850                    | V/mV  |     |      |
|                  |                                                                      |                                                                                              | 0°C                         | 250                   | 700         | 500         | 1010                   |       |     |      |
|                  |                                                                      |                                                                                              | 70°C                        | 200                   | 380         | 350         | 660                    |       |     |      |
| CMRR             | Common mode rejection ratio                                          | V <sub>IC</sub> = V <sub>ICRmin</sub>                                                        | 25°C                        | 70                    | 95          | 75          | 97                     | dB    |     |      |
|                  |                                                                      |                                                                                              | 0°C                         | 70                    | 95          | 75          | 97                     |       |     |      |
|                  |                                                                      |                                                                                              | 70°C                        | 70                    | 95          | 75          | 97                     |       |     |      |
| k <sub>SVR</sub> | Supply-voltage rejection ratio (ΔV <sub>DD</sub> /ΔV <sub>IO</sub> ) | V <sub>DD</sub> = 5 V to 10 V,<br>V <sub>O</sub> = 1.4 V                                     | 25°C                        | 75                    | 98          | 75          | 98                     | dB    |     |      |
|                  |                                                                      |                                                                                              | 0°C                         | 75                    | 98          | 75          | 98                     |       |     |      |
|                  |                                                                      |                                                                                              | 70°C                        | 75                    | 98          | 75          | 98                     |       |     |      |
| I <sub>DD</sub>  | Supply current (four amplifiers)                                     | V <sub>O</sub> = V <sub>DD</sub> / 2,<br>V <sub>IC</sub> = V <sub>DD</sub> / 2, No load      | 25°C                        | 40                    | 68          | 57          | 92                     | μA    |     |      |
|                  |                                                                      |                                                                                              | 0°C                         | 48                    | 84          | 72          | 132                    |       |     |      |
|                  |                                                                      |                                                                                              | 70°C                        | 31                    | 56          | 44          | 80                     |       |     |      |

† Full range is 0°C to 70°C.

NOTES: 4. The typical values of input bias current and input offset current below 5 pA were determined mathematically.

5. This range also applies to each input individually.

6. At  $V_{DD} = 5\text{ V}$ ,  $V_O = 0.25\text{ V to }2\text{ V}$ ; at  $V_{DD} = 10\text{ V}$ ,  $V_O = 1\text{ V to }6\text{ V}$ .



**TLC1078, TLC1078Y, TLC1079, TLC1079Y**  
**LinCMOS™  $\mu$ POWER PRECISION**  
**OPERATIONAL AMPLIFIERS**

SLOS179A – FEBRUARY 1997 – REVISED MARCH 2001

**operating characteristics at specified free-air temperature**

| PARAMETER                                     | TEST CONDITIONS                                                                                | T <sub>A</sub> | TLC1078C              |     |     |                        |     |     | UNIT   |
|-----------------------------------------------|------------------------------------------------------------------------------------------------|----------------|-----------------------|-----|-----|------------------------|-----|-----|--------|
|                                               |                                                                                                |                | V <sub>DD</sub> = 5 V |     |     | V <sub>DD</sub> = 10 V |     |     |        |
|                                               |                                                                                                |                | MIN                   | TYP | MAX | MIN                    | TYP | MAX |        |
| SR    Slew rate at unity gain                 | R <sub>L</sub> = 1 MΩ,    C <sub>L</sub> = 20 pF,<br>V <sub>I(PP)</sub> = 1 V,    See Figure 1 | 25°C           | 32                    |     |     | 47                     |     |     | V/ms   |
|                                               |                                                                                                | 0°C            | 35                    |     |     | 51                     |     |     |        |
|                                               |                                                                                                | 70°C           | 27                    |     |     | 38                     |     |     |        |
| V <sub>n</sub> Equivalent input noise voltage | f = 1 kHz,    R <sub>S</sub> = 20 Ω                                                            | 25°C           | 68                    |     |     | 68                     |     |     | nV/√Hz |
| B <sub>1</sub> Unity-gain bandwidth           | C <sub>L</sub> = 20 pF,    See Figure 2                                                        | 25°C           | 85                    |     |     | 110                    |     |     | kHz    |
|                                               |                                                                                                | 0°C            | 100                   |     |     | 125                    |     |     |        |
|                                               |                                                                                                | 70°C           | 65                    |     |     | 90                     |     |     |        |
| φ <sub>m</sub> Phase margin at unity gain     | C <sub>L</sub> = 20 pF,    See Figure 2                                                        | 25°C           | 34°                   |     |     | 38°                    |     |     |        |
|                                               |                                                                                                | 0°C            | 36°                   |     |     | 40°                    |     |     |        |
|                                               |                                                                                                | 70°C           | 30°                   |     |     | 34°                    |     |     |        |

**operating characteristics at specified free-air temperature**

| PARAMETER      |                                | TEST CONDITIONS                                                                       |      | T <sub>A</sub> | TLC1079C              |     |     |                        |     |        | UNIT |
|----------------|--------------------------------|---------------------------------------------------------------------------------------|------|----------------|-----------------------|-----|-----|------------------------|-----|--------|------|
|                |                                |                                                                                       |      |                | V <sub>DD</sub> = 5 V |     |     | V <sub>DD</sub> = 10 V |     |        |      |
|                |                                |                                                                                       |      |                | MIN                   | TYP | MAX | MIN                    | TYP | MAX    |      |
| SR             | Slew rate at unity gain        | R <sub>L</sub> = 1 MΩ, C <sub>L</sub> = 20 pF, V <sub>I(PP)</sub> = 1 V, See Figure 1 | 25°C | 32             |                       |     | 47  |                        |     | V/ms   |      |
|                |                                |                                                                                       | 0°C  | 35             |                       |     | 51  |                        |     |        |      |
|                |                                |                                                                                       | 70°C | 27             |                       |     | 38  |                        |     |        |      |
| V <sub>n</sub> | Equivalent input noise voltage | f = 1 kHz, R <sub>S</sub> = 20 Ω                                                      | 25°C | 68             |                       |     | 68  |                        |     | nV/√Hz |      |
| B <sub>1</sub> | Unity-gain bandwidth           | C <sub>L</sub> = 20 pF, See Figure 2                                                  | 25°C | 85             |                       |     | 110 |                        |     | kHz    |      |
|                |                                |                                                                                       | 0°C  | 100            |                       |     | 125 |                        |     |        |      |
|                |                                |                                                                                       | 70°C | 65             |                       |     | 90  |                        |     |        |      |
| φ <sub>m</sub> | Phase margin at unity gain     | C <sub>L</sub> = 20 pF, See Figure 2                                                  | 25°C | 34°            |                       |     | 38° |                        |     |        |      |
|                |                                |                                                                                       | 0°C  | 36°            |                       |     | 40° |                        |     |        |      |
|                |                                |                                                                                       | 70°C | 30°            |                       |     | 34° |                        |     |        |      |

# TLC1078, TLC1078Y, TLC1079, TLC1079Y

## LinCMOS™ $\mu$ POWER PRECISION

### OPERATIONAL AMPLIFIERS

SLOS179A – FEBRUARY 1997 – REVISED MARCH 2001

#### electrical characteristics at specified free-air temperature

| PARAMETER        |                                                                      | TEST CONDITIONS                                                                                 | T <sub>A</sub> <sup>†</sup> | TLC1078I              |                |      |                        |                |      | UNIT  |
|------------------|----------------------------------------------------------------------|-------------------------------------------------------------------------------------------------|-----------------------------|-----------------------|----------------|------|------------------------|----------------|------|-------|
|                  |                                                                      |                                                                                                 |                             | V <sub>DD</sub> = 5 V |                |      | V <sub>DD</sub> = 10 V |                |      |       |
|                  |                                                                      |                                                                                                 |                             | MIN                   | TYP            | MAX  | MIN                    | TYP            | MAX  |       |
| V <sub>IO</sub>  | Input offset voltage                                                 | V <sub>O</sub> = 1.4 V,<br>R <sub>S</sub> = 50 Ω,<br>V <sub>IC</sub> = 0, R <sub>I</sub> = 1 MΩ | 25°C                        | 160                   |                | 450  | 180                    |                | 600  | μV    |
|                  |                                                                      |                                                                                                 | Full range                  |                       |                | 950  |                        |                | 1100 |       |
| α <sub>VIO</sub> | Temperature coefficient of input offset voltage                      |                                                                                                 | 25°C to 85°C                | 1.1                   |                |      | 1                      |                |      | μV/°C |
| I <sub>IO</sub>  | Input offset current (see Note 4)                                    | V <sub>O</sub> = V <sub>DD</sub> / 2,<br>V <sub>IC</sub> = V <sub>DD</sub> / 2                  | 25°C                        | 0.1                   |                | 60   | 0.1                    |                | 60   | pA    |
|                  |                                                                      |                                                                                                 | 85°C                        | 24                    |                | 1000 | 26                     |                | 1000 |       |
| I <sub>IB</sub>  | Input bias current (see Note 4)                                      |                                                                                                 | 25°C                        | 0.6                   |                | 60   | 0.7                    |                | 60   | pA    |
|                  |                                                                      | 85°C                                                                                            | 200                         |                       | 2000           | 220  |                        | 2000           |      |       |
| V <sub>ICR</sub> | Common-mode input voltage range (see Note 5)                         |                                                                                                 | 25°C                        | −0.2<br>to 4          | −0.3<br>to 4.2 |      | −0.2<br>to 9           | −0.3<br>to 9.2 |      | V     |
|                  |                                                                      |                                                                                                 | Full range                  | −0.2<br>to 3.5        |                |      | −0.2<br>to 8.5         |                |      | V     |
| V <sub>OH</sub>  | High-level output voltage                                            | V <sub>ID</sub> = 100 mV,<br>R <sub>L</sub> = 1 MΩ                                              | 25°C                        | 3.2                   | 4.1            |      | 8.2                    | 8.9            |      | V     |
|                  |                                                                      |                                                                                                 | −40°C                       | 3.2                   | 4.1            |      | 8.2                    | 8.9            |      |       |
|                  |                                                                      |                                                                                                 | 85°C                        | 3.2                   | 4.2            |      | 8.2                    | 8.9            |      |       |
| V <sub>OL</sub>  | Low-level output voltage                                             | V <sub>ID</sub> = −100 mV,<br>I <sub>OL</sub> = 0                                               | 25°C                        | 0                     |                | 25   | 0                      |                | 25   | mV    |
|                  |                                                                      |                                                                                                 | −40°C                       | 0                     |                | 25   | 0                      |                | 25   |       |
|                  |                                                                      |                                                                                                 | 85°C                        | 0                     |                | 25   | 0                      |                | 25   |       |
| A <sub>VD</sub>  | Large-signal differential voltage amplification                      | R <sub>L</sub> = 1 MΩ,<br>See Note 6                                                            | 25°C                        | 250                   | 525            |      | 500                    | 850            |      | V/mV  |
|                  |                                                                      |                                                                                                 | −40°C                       | 250                   | 900            |      | 500                    | 1550           |      |       |
|                  |                                                                      |                                                                                                 | 85°C                        | 150                   | 300            |      | 250                    | 585            |      |       |
| CMRR             | Common-mode rejection ratio                                          | V <sub>IC</sub> = V <sub>ICRmin</sub>                                                           | 25°C                        | 70                    | 95             |      | 75                     | 97             |      | dB    |
|                  |                                                                      |                                                                                                 | −40°C                       | 70                    | 95             |      | 75                     | 97             |      |       |
|                  |                                                                      |                                                                                                 | 85°C                        | 70                    | 95             |      | 75                     | 97             |      |       |
| k <sub>SVR</sub> | Supply-voltage rejection ratio (ΔV <sub>DD</sub> /ΔV <sub>IO</sub> ) | V <sub>O</sub> = 1.4 V                                                                          | 25°C                        | 75                    | 98             |      | 75                     | 98             |      | dB    |
|                  |                                                                      |                                                                                                 | −40°C                       | 75                    | 98             |      | 75                     | 98             |      |       |
|                  |                                                                      |                                                                                                 | 85°C                        | 75                    | 98             |      | 75                     | 98             |      |       |
| I <sub>DD</sub>  | Supply current (two amplifiers)                                      | V <sub>O</sub> = V <sub>DD</sub> / 2,<br>V <sub>IC</sub> = V <sub>DD</sub> / 2,<br>No load      | 25°C                        | 20                    |                | 34   | 29                     |                | 46   | μA    |
|                  |                                                                      |                                                                                                 | −40°C                       | 31                    |                | 54   | 50                     |                | 86   |       |
|                  |                                                                      |                                                                                                 | 85°C                        | 15                    |                | 26   | 20                     |                | 36   |       |

$^\dagger$  Full range is –40°C to 80°C.

NOTES: 4. The typical values of input bias current and input offset current below 5 pA were determined mathematically.

5. This range also applies to each input individually.

6. At  $V_{DD} = 5\text{ V}$ ,  $V_O = 0.25\text{ V}$  to  $2\text{ V}$ ; at  $V_{DD} = 10\text{ V}$ ,  $V_O = 1\text{ V}$  to  $6\text{ V}$ .



**electrical characteristics at specified free-air temperature**

| PARAMETER        |                                                                      | TEST CONDITIONS                                                                           | T <sub>A</sub> <sup>†</sup> | TLC1079I              |             |             |                        |       |     | UNIT |
|------------------|----------------------------------------------------------------------|-------------------------------------------------------------------------------------------|-----------------------------|-----------------------|-------------|-------------|------------------------|-------|-----|------|
|                  |                                                                      |                                                                                           |                             | V <sub>DD</sub> = 5 V |             |             | V <sub>DD</sub> = 10 V |       |     |      |
|                  |                                                                      |                                                                                           |                             | MIN                   | TYP         | MAX         | MIN                    | TYP   | MAX |      |
| V <sub>IO</sub>  | Input offset voltage                                                 | V <sub>O</sub> = 1.4 V, V <sub>IC</sub> = 0, R <sub>S</sub> = 50 Ω, R <sub>I</sub> = 1 MΩ | 25°C                        | 190 850               |             | 200 1150    |                        | μV    |     |      |
|                  |                                                                      |                                                                                           | Full range                  | 1350                  |             | 1650        |                        |       |     |      |
| α <sub>VIO</sub> | Temperature coefficient of input offset voltage                      |                                                                                           | 25°C to 85°C                | 1.1                   |             | 1           |                        | μV/°C |     |      |
| I <sub>IO</sub>  | Input offset current (see Note 4)                                    | V <sub>O</sub> = V <sub>DD</sub> / 2, V <sub>IC</sub> = V <sub>DD</sub> / 2               | 25°C                        | 0.1                   | 60          | 0.1         | 60                     | pA    |     |      |
|                  |                                                                      |                                                                                           | 85°C                        | 24                    | 1000        | 26          | 1000                   |       |     |      |
| I <sub>IB</sub>  | Input bias current (see Note 4)                                      |                                                                                           | 25°C                        | 0.6                   | 60          | 0.7         | 60                     | pA    |     |      |
|                  |                                                                      |                                                                                           | 85°C                        | 200                   | 2000        | 220         | 2000                   |       |     |      |
| V <sub>ICR</sub> | Common-mode input voltage range (see Note 5)                         |                                                                                           | 25°C                        | -0.2 to 4             | -0.3 to 4.2 | -0.2 to 9   | -0.3 to 9.2            | V     |     |      |
|                  |                                                                      |                                                                                           | Full range                  | -0.2 to 3.5           |             | -0.2 to 8.5 |                        | V     |     |      |
| V <sub>OH</sub>  | High-level output voltage                                            | V <sub>ID</sub> = 100 mV, R <sub>L</sub> = 1 MΩ                                           | 25°C                        | 3.2                   | 4.1         | 8.2         | 8.9                    | V     |     |      |
|                  |                                                                      |                                                                                           | -40°C                       | 3.2                   | 4.1         | 8.2         | 8.9                    |       |     |      |
|                  |                                                                      |                                                                                           | 85°C                        | 3.2                   | 4.2         | 8.2         | 8.9                    |       |     |      |
| V <sub>OL</sub>  | Low-level output voltage                                             | V <sub>ID</sub> = -100 mV, I <sub>OL</sub> = 0                                            | 25°C                        | 0                     | 25          | 0           | 25                     | mV    |     |      |
|                  |                                                                      |                                                                                           | -40°C                       | 0                     | 25          | 0           | 25                     |       |     |      |
|                  |                                                                      |                                                                                           | 85°C                        | 0                     | 25          | 0           | 25                     |       |     |      |
| A <sub>VD</sub>  | Large-signal differential voltage amplification                      | R <sub>L</sub> = 1 MΩ, See Note 6                                                         | 25°C                        | 250                   | 525         | 500         | 850                    | V/mV  |     |      |
|                  |                                                                      |                                                                                           | -40°C                       | 250                   | 900         | 500         | 1550                   |       |     |      |
|                  |                                                                      |                                                                                           | 85°C                        | 150                   | 330         | 250         | 585                    |       |     |      |
| CMRR             | Common-mode rejection ratio                                          | V <sub>IC</sub> = V <sub>ICRmin</sub>                                                     | 25°C                        | 70                    | 95          | 75          | 97                     | dB    |     |      |
|                  |                                                                      |                                                                                           | -40°C                       | 70                    | 95          | 75          | 97                     |       |     |      |
|                  |                                                                      |                                                                                           | 85°C                        | 70                    | 95          | 75          | 97                     |       |     |      |
| k <sub>SVR</sub> | Supply-voltage rejection ratio (ΔV <sub>DD</sub> /ΔV <sub>IO</sub> ) | V <sub>DD</sub> = 5 V to 10 V, V <sub>O</sub> = 1.4 V                                     | 25°C                        | 75                    | 98          | 75          | 98                     | dB    |     |      |
|                  |                                                                      |                                                                                           | -40°C                       | 75                    | 98          | 75          | 98                     |       |     |      |
|                  |                                                                      |                                                                                           | 85°C                        | 75                    | 98          | 75          | 98                     |       |     |      |
| I <sub>DD</sub>  | Supply current (four amplifiers)                                     | V <sub>O</sub> = V <sub>DD</sub> / 2, V <sub>IC</sub> = V <sub>DD</sub> / 2, No load      | 25°C                        | 40                    | 68          | 57          | 92                     | μA    |     |      |
|                  |                                                                      |                                                                                           | -40°C                       | 62                    | 108         | 98          | 172                    |       |     |      |
|                  |                                                                      |                                                                                           | 85°C                        | 29                    | 52          | 40          | 72                     |       |     |      |

$^\dagger$  Full range is -40°C to 85°C.

NOTES: 4. The typical values of input bias current and input offset current below 5 pA were determined mathematically.

5. This range also applies to each input individually.

6. At  $V_{DD} = 5\text{ V}$ ,  $V_O = 0.25\text{ V to }2\text{ V}$ ; at  $V_{DD} = 10\text{ V}$ ,  $V_O = 1\text{ V to }6\text{ V}$ .

**TLC1078, TLC1078Y, TLC1079, TLC1079Y**  
**LinCMOS™  $\mu$ POWER PRECISION**  
**OPERATIONAL AMPLIFIERS**

SLOS179A – FEBRUARY 1997 – REVISED MARCH 2001

**operating characteristics at specified free-air temperature**

| PARAMETER                                     | TEST CONDITIONS                                                                                | T <sub>A</sub> | TLC1078I              |     |     |                        |     |     | UNIT   |
|-----------------------------------------------|------------------------------------------------------------------------------------------------|----------------|-----------------------|-----|-----|------------------------|-----|-----|--------|
|                                               |                                                                                                |                | V <sub>DD</sub> = 5 V |     |     | V <sub>DD</sub> = 10 V |     |     |        |
|                                               |                                                                                                |                | MIN                   | TYP | MAX | MIN                    | TYP | MAX |        |
| SR    Slew rate at unity gain                 | R <sub>L</sub> = 1 MΩ,    C <sub>L</sub> = 20 pF,<br>V <sub>I(PP)</sub> = 1 V,    See Figure 1 | 25°C           | 32                    |     |     | 47                     |     |     | V/ms   |
|                                               |                                                                                                | −40°C          | 39                    |     |     | 59                     |     |     |        |
|                                               |                                                                                                | 85°C           | 25                    |     |     | 34                     |     |     |        |
| V <sub>n</sub> Equivalent input noise voltage | f = 1 kHz,    R <sub>S</sub> = 20 Ω                                                            | 25°C           | 68                    |     |     | 68                     |     |     | nV/√Hz |
| B <sub>1</sub> Unity-gain bandwidth           | C <sub>L</sub> = 20 pF,    See Figure 2                                                        | 25°C           | 85                    |     |     | 110                    |     |     | kHz    |
|                                               |                                                                                                | −40°C          | 130                   |     |     | 155                    |     |     |        |
|                                               |                                                                                                | 85°C           | 55                    |     |     | 80                     |     |     |        |
| ϕ <sub>m</sub> Phase margin at unity gain     | C <sub>L</sub> = 20 pF,    See Figure 2                                                        | 25°C           | 34°                   |     |     | 38°                    |     |     |        |
|                                               |                                                                                                | −40°C          | 38°                   |     |     | 40°                    |     |     |        |
|                                               |                                                                                                | 85°C           | 28°                   |     |     | 32°                    |     |     |        |

**operating characteristics at specified free-air temperature**

| PARAMETER                                     | TEST CONDITIONS                                                                                | T <sub>A</sub> | TLC1079I              |     |     |                        |     |     | UNIT   |
|-----------------------------------------------|------------------------------------------------------------------------------------------------|----------------|-----------------------|-----|-----|------------------------|-----|-----|--------|
|                                               |                                                                                                |                | V <sub>DD</sub> = 5 V |     |     | V <sub>DD</sub> = 10 V |     |     |        |
|                                               |                                                                                                |                | MIN                   | TYP | MAX | MIN                    | TYP | MAX |        |
| SR    Slew rate at unity gain                 | R <sub>L</sub> = 1 MΩ,    C <sub>L</sub> = 20 pF,<br>V <sub>I(PP)</sub> = 1 V,    See Figure 1 | 25°C           | 32                    |     |     | 47                     |     |     | V/ms   |
|                                               |                                                                                                | −40°C          | 39                    |     |     | 59                     |     |     |        |
|                                               |                                                                                                | 85°C           | 25                    |     |     | 34                     |     |     |        |
| V <sub>n</sub> Equivalent input noise voltage | f = 1 kHz,    R <sub>S</sub> = 20 Ω                                                            | 25°C           | 68                    |     |     | 68                     |     |     | nV/√Hz |
| B <sub>1</sub> Unity-gain bandwidth           | C <sub>L</sub> = 20 pF,    See Figure 2                                                        | 25°C           | 85                    |     |     | 110                    |     |     | kHz    |
|                                               |                                                                                                | −40°C          | 130                   |     |     | 155                    |     |     |        |
|                                               |                                                                                                | 85°C           | 55                    |     |     | 80                     |     |     |        |
| ϕ <sub>m</sub> Phase margin at unity gain     | C <sub>L</sub> = 20 pF,    See Figure 2                                                        | 25°C           | 34°                   |     |     | 38°                    |     |     |        |
|                                               |                                                                                                | −40°C          | 38°                   |     |     | 42°                    |     |     |        |
|                                               |                                                                                                | 85°C           | 28°                   |     |     | 32°                    |     |     |        |

**TLC1078, TLC1078Y, TLC1079, TLC1079Y**  
**LinCMOS™  $\mu$ POWER PRECISION**  
**OPERATIONAL AMPLIFIERS**

SLOS179A – FEBRUARY 1997 – REVISED MARCH 2001

**electrical characteristics at specified operating free-air temperature**

| PARAMETER        |                                                                      | TEST CONDITIONS                                                                                    | T <sub>A</sub> <sup>†</sup> | TLC1078M              |             |          |                        |             |      | UNIT  |
|------------------|----------------------------------------------------------------------|----------------------------------------------------------------------------------------------------|-----------------------------|-----------------------|-------------|----------|------------------------|-------------|------|-------|
|                  |                                                                      |                                                                                                    |                             | V <sub>DD</sub> = 5 V |             |          | V <sub>DD</sub> = 10 V |             |      |       |
|                  |                                                                      |                                                                                                    |                             | MIN                   | TYP         | MAX      | MIN                    | TYP         | MAX  |       |
| V <sub>IO</sub>  | Input offset voltage                                                 | V <sub>O</sub> = 1.4 V,<br>V <sub>IC</sub> = 0,<br>R <sub>S</sub> = 50 Ω,<br>R <sub>L</sub> = 1 MΩ | 25°C                        |                       | 160         | 450      |                        | 180         | 600  | μV    |
|                  |                                                                      |                                                                                                    | Full range                  |                       |             | 1250     |                        |             | 1400 |       |
| α <sub>VIO</sub> | Temperature coefficient of input offset voltage                      |                                                                                                    | 25°C to 125°C               |                       | 1.4         |          |                        | 1.4         |      | μV/°C |
| I <sub>IO</sub>  | Input offset current (see Note 4)                                    | V <sub>O</sub> = V <sub>DD</sub> / 2,<br>V <sub>IC</sub> = V <sub>DD</sub> / 2                     | 25°C                        |                       | 0.1         | 60       |                        | 0.1         | 60   | pA    |
|                  |                                                                      |                                                                                                    | 125°C                       |                       | 1.4         | 15       |                        | 1.8         | 15   | nA    |
| I <sub>IB</sub>  | Input bias current (see Note 4)                                      |                                                                                                    | 25°C                        |                       | 0.6         | 60       |                        | 0.7         | 60   | pA    |
|                  |                                                                      |                                                                                                    | 125°C                       |                       | 9           | 35       |                        | 10          | 35   | nA    |
| V <sub>ICR</sub> | Common-mode input voltage range (see Note 5)                         |                                                                                                    | 25°C                        | 0 to 4                | −0.3 to 4.2 |          | 0 to 9                 | −0.3 to 9.2 |      | V     |
|                  |                                                                      |                                                                                                    | Full range                  | 0 to 3.5              |             | 0 to 8.5 |                        |             | V    |       |
| V <sub>OH</sub>  | High-level output voltage                                            | V <sub>ID</sub> = 100 mV,<br>R <sub>L</sub> = 1 MΩ                                                 | 25°C                        | 3.2                   | 4.1         |          | 8.2                    | 8.9         |      | V     |
|                  |                                                                      |                                                                                                    | −55°C                       | 3.2                   | 4.1         |          | 8.2                    | 8.8         |      |       |
|                  |                                                                      |                                                                                                    | 125°C                       | 3.2                   | 4.2         |          | 8.2                    | 9           |      |       |
| V <sub>OL</sub>  | Low-level output voltage                                             | V <sub>ID</sub> = −100 mV,<br>I <sub>OL</sub> = 0                                                  | 25°C                        |                       | 0           | 25       |                        | 0           | 25   | mV    |
|                  |                                                                      |                                                                                                    | −55°C                       |                       | 0           | 25       |                        | 0           | 25   |       |
|                  |                                                                      |                                                                                                    | 125°C                       |                       | 0           | 25       |                        | 0           | 25   |       |
| A <sub>VD</sub>  | Large-signal differential voltage amplification                      | R <sub>L</sub> = 1 MΩ ,<br>See Note 6                                                              | 25°C                        | 250                   | 525         |          | 500                    | 850         |      | V/mV  |
|                  |                                                                      |                                                                                                    | −55°C                       | 250                   | 950         |          | 500                    | 1750        |      |       |
|                  |                                                                      |                                                                                                    | 125°C                       | 35                    | 200         |          | 75                     | 380         |      |       |
| CMRR             | Common-mode rejection ratio                                          | V <sub>IC</sub> = V <sub>ICRmin</sub>                                                              | 25°C                        | 70                    | 95          |          | 75                     | 97          |      | dB    |
|                  |                                                                      |                                                                                                    | −55°C                       | 70                    | 95          |          | 75                     | 97          |      |       |
|                  |                                                                      |                                                                                                    | 125°C                       | 70                    | 85          |          | 75                     | 91          |      |       |
| k <sub>SVR</sub> | Supply-voltage rejection ratio (ΔV <sub>DD</sub> /ΔV <sub>IO</sub> ) | V <sub>O</sub> = 1.4 V                                                                             | 25°C                        | 75                    | 98          |          | 75                     | 98          |      | dB    |
|                  |                                                                      |                                                                                                    | −55°C                       | 70                    | 98          |          | 70                     | 98          |      |       |
|                  |                                                                      |                                                                                                    | 125°C                       | 70                    | 98          |          | 70                     | 98          |      |       |
| I <sub>DD</sub>  | Supply current (two amplifiers)                                      | V <sub>O</sub> = V <sub>DD</sub> / 2,<br>V <sub>IC</sub> = V <sub>DD</sub> / 2,<br>No load         | 25°C                        |                       | 20          | 34       |                        | 29          | 46   | μA    |
|                  |                                                                      |                                                                                                    | −55°C                       |                       | 35          | 60       |                        | 56          | 96   |       |
|                  |                                                                      |                                                                                                    | 125°C                       |                       | 14          | 24       |                        | 18          | 30   |       |

$^\dagger$  Full range is –55°C to 125°C.

NOTES: 4. The typical values of input bias current and input offset current below 5 pA were determined mathematically.

5. This range also applies to each input individually.

6. At  $V_{DD} = 5\text{ V}$ ,  $V_O = 0.25\text{ V}$  to  $2\text{ V}$ ; at  $V_{DD} = 10\text{ V}$ ,  $V_O = 1\text{ V}$  to  $6\text{ V}$ .



# TLC1078, TLC1078Y, TLC1079, TLC1079Y

## LinCMOS™ $\mu$ POWER PRECISION

### OPERATIONAL AMPLIFIERS

SLOS179A – FEBRUARY 1997 – REVISED MARCH 2001

#### electrical characteristics at specified free-air temperature

| PARAMETER        |                                                                      | TEST CONDITIONS                                                                              | T <sub>A</sub> <sup>†</sup> | TLC1079M              |             |          |                        |             |      | UNIT  |
|------------------|----------------------------------------------------------------------|----------------------------------------------------------------------------------------------|-----------------------------|-----------------------|-------------|----------|------------------------|-------------|------|-------|
|                  |                                                                      |                                                                                              |                             | V <sub>DD</sub> = 5 V |             |          | V <sub>DD</sub> = 10 V |             |      |       |
|                  |                                                                      |                                                                                              |                             | MIN                   | TYP         | MAX      | MIN                    | TYP         | MAX  |       |
| V <sub>IO</sub>  | Input offset voltage                                                 | V <sub>O</sub> = 1.4 V, V <sub>IC</sub> = 0,<br>R <sub>S</sub> = 50 Ω, R <sub>I</sub> = 1 MΩ | 25°C                        |                       | 190         | 850      |                        | 200         | 1150 | μV    |
|                  |                                                                      |                                                                                              | Full range                  |                       |             | 1600     |                        |             | 1900 |       |
| α <sub>VIO</sub> | Temperature coefficient of input offset voltage                      |                                                                                              | 25°C to 125°C               |                       | 1.4         |          |                        | 1.4         |      | μV/°C |
| I <sub>IO</sub>  | Input offset current (see Note 4)                                    | V <sub>O</sub> = V <sub>DD</sub> / 2,<br>V <sub>IC</sub> = V <sub>DD</sub> / 2               | 25°C                        |                       | 0.1         | 60       |                        | 0.1         | 60   | pA    |
|                  |                                                                      |                                                                                              | 125°C                       |                       | 1.4         | 15       |                        | 1.8         | 15   | nA    |
| I <sub>IB</sub>  | Input bias current (see Note 4)                                      |                                                                                              | 25°C                        |                       | 0.6         | 60       |                        | 0.7         | 60   | pA    |
|                  |                                                                      |                                                                                              | 125°C                       |                       | 9           | 35       |                        | 10          | 35   | nA    |
| V <sub>ICR</sub> | Common mode input voltage range (see Note 5)                         |                                                                                              | 25°C                        | 0 to 4                | –0.3 to 4.2 |          | 0 to 9                 | –0.3 to 9.2 |      | V     |
|                  |                                                                      |                                                                                              | Full range                  | 0 to 3.5              |             | 0 to 8.5 |                        |             | V    |       |
| V <sub>OH</sub>  | High-level output voltage                                            | V <sub>ID</sub> = 100 mV,<br>R <sub>L</sub> = 1 MΩ                                           | 25°C                        | 3.2                   | 4.1         |          | 8.2                    | 8.9         |      | V     |
|                  |                                                                      |                                                                                              | –55°C                       | 3.2                   | 4.1         |          | 8.2                    | 8.9         |      |       |
|                  |                                                                      |                                                                                              | 125°C                       | 3.2                   | 4.2         |          | 8.2                    | 9           |      |       |
| V <sub>OL</sub>  | Low-level output voltage                                             | V <sub>ID</sub> = –100 mV,<br>I <sub>OL</sub> = 0                                            | 25°C                        |                       | 0           | 25       |                        | 0           | 25   | mV    |
|                  |                                                                      |                                                                                              | –55°C                       |                       | 0           | 25       |                        | 0           | 25   |       |
|                  |                                                                      |                                                                                              | 125°C                       |                       | 0           | 25       |                        | 0           | 25   |       |
| A <sub>VD</sub>  | Large-signal differential voltage amplification                      | R <sub>L</sub> = 1 MΩ, See Note 6                                                            | 25°C                        | 250                   | 525         |          | 500                    | 850         |      | V/mV  |
|                  |                                                                      |                                                                                              | –55°C                       | 250                   | 950         |          | 500                    | 1750        |      |       |
|                  |                                                                      |                                                                                              | 125°C                       | 35                    | 200         |          | 75                     | 380         |      |       |
| CMRR             | Common-mode rejection ratio                                          | V <sub>IC</sub> = V <sub>ICRmin</sub>                                                        | 25°C                        | 70                    | 95          |          | 75                     | 97          |      | dB    |
|                  |                                                                      |                                                                                              | –55°C                       | 70                    | 95          |          | 75                     | 97          |      |       |
|                  |                                                                      |                                                                                              | 125°C                       | 70                    | 85          |          | 75                     | 91          |      |       |
| k <sub>SVR</sub> | Supply voltage rejection ratio (ΔV <sub>DD</sub> /ΔV <sub>IO</sub> ) | V <sub>DD</sub> = 5 V to 10 V,<br>V <sub>O</sub> = 1.4 V                                     | 25°C                        | 75                    | 98          |          | 75                     | 98          |      | dB    |
|                  |                                                                      |                                                                                              | –55°C                       | 70                    | 98          |          | 70                     | 98          |      |       |
|                  |                                                                      |                                                                                              | 125°C                       | 70                    | 98          |          | 70                     | 98          |      |       |
| I <sub>DD</sub>  | Supply current (four amplifiers)                                     | V <sub>O</sub> = V <sub>DD</sub> / 2,<br>V <sub>IC</sub> = V <sub>DD</sub> / 2, No load      | 25°C                        |                       | 40          | 68       |                        | 57          | 92   | μA    |
|                  |                                                                      |                                                                                              | –55°C                       |                       | 69          | 120      |                        | 111         | 192  |       |
|                  |                                                                      |                                                                                              | 125°C                       |                       | 27          | 48       |                        | 35          | 60   |       |

† Full range is –55°C to 125°C.

NOTES: 4. The typical values of input bias current and input offset current below 5 pA were determined mathematically.

5. This range also applies to each input individually.

6. At  $V_{DD} = 5\text{ V}$ ,  $V_O = 0.25\text{ V to }2\text{ V}$ ; at  $V_{DD} = 10\text{ V}$ ,  $V_O = 1\text{ V to }6\text{ V}$ .



**TLC1078, TLC1078Y, TLC1079, TLC1079Y**  
**LinCMOS™  $\mu$ POWER PRECISION**  
**OPERATIONAL AMPLIFIERS**

SLOS179A – FEBRUARY 1997 – REVISED MARCH 2001

**operating characteristics at specified free-air temperature**

| PARAMETER                                     | TEST CONDITIONS                                                                                | T <sub>A</sub> | TLC1078M              |     |     |                        |     |     | UNIT   |
|-----------------------------------------------|------------------------------------------------------------------------------------------------|----------------|-----------------------|-----|-----|------------------------|-----|-----|--------|
|                                               |                                                                                                |                | V <sub>DD</sub> = 5 V |     |     | V <sub>DD</sub> = 10 V |     |     |        |
|                                               |                                                                                                |                | MIN                   | TYP | MAX | MIN                    | TYP | MAX |        |
| SR    Slew rate at unity gain                 | R <sub>L</sub> = 1 MΩ,    C <sub>L</sub> = 20 pF,<br>V <sub>I(PP)</sub> = 1 V,    See Figure 1 | 25°C           | 32                    |     |     | 47                     |     |     | V/ms   |
|                                               |                                                                                                | –55°C          | 41                    |     |     | 63                     |     |     |        |
|                                               |                                                                                                | 125°C          | 20                    |     |     | 27                     |     |     |        |
| V <sub>n</sub> Equivalent input noise voltage | f = 1 kHz,    R <sub>S</sub> = 20 Ω                                                            | 25°C           | 68                    |     |     | 68                     |     |     | nV/√Hz |
| B <sub>1</sub> Unity-gain bandwidth           | C <sub>L</sub> = 20 pF,    See Figure 2                                                        | 25°C           | 85                    |     |     | 110                    |     |     | kHz    |
|                                               |                                                                                                | –55°C          | 140                   |     |     | 165                    |     |     |        |
|                                               |                                                                                                | 125°C          | 45                    |     |     | 70                     |     |     |        |
| φ <sub>m</sub> Phase margin at unity gain     | C <sub>L</sub> = 20 pF,    See Figure 2                                                        | 25°C           | 34°                   |     |     | 38°                    |     |     |        |
|                                               |                                                                                                | –55°C          | 39°                   |     |     | 43°                    |     |     |        |
|                                               |                                                                                                | 125°C          | 25°                   |     |     | 29°                    |     |     |        |

**operating characteristics at specified free-air temperature**

| PARAMETER                                     | TEST CONDITIONS                                                                                | T <sub>A</sub> | TLC1079M              |     |     |                        |     |     | UNIT   |
|-----------------------------------------------|------------------------------------------------------------------------------------------------|----------------|-----------------------|-----|-----|------------------------|-----|-----|--------|
|                                               |                                                                                                |                | V <sub>DD</sub> = 5 V |     |     | V <sub>DD</sub> = 10 V |     |     |        |
|                                               |                                                                                                |                | MIN                   | TYP | MAX | MIN                    | TYP | MAX |        |
| SR    Slew rate at unity gain                 | R <sub>L</sub> = 1 MΩ,    C <sub>L</sub> = 20 pF,<br>V <sub>I(PP)</sub> = 1 V,    See Figure 1 | 25°C           | 32                    |     |     | 47                     |     |     | V/ms   |
|                                               |                                                                                                | –55°C          | 41                    |     |     | 63                     |     |     |        |
|                                               |                                                                                                | 125°C          | 20                    |     |     | 27                     |     |     |        |
| V <sub>n</sub> Equivalent input noise voltage | f = 1 kHz,    R <sub>S</sub> = 20 Ω                                                            | 25°C           | 68                    |     |     | 68                     |     |     | nV/√Hz |
| B <sub>1</sub> Unity-gain bandwidth           | C <sub>L</sub> = 20 pF,    See Figure 2                                                        | 25°C           | 85                    |     |     | 110                    |     |     | kHz    |
|                                               |                                                                                                | –55°C          | 140                   |     |     | 165                    |     |     |        |
|                                               |                                                                                                | 125°C          | 45                    |     |     | 70                     |     |     |        |
|                                               |                                                                                                | 25°C           | 34°                   |     |     | 38°                    |     |     |        |
| φ <sub>m</sub> Phase margin at unity gain     | C <sub>L</sub> = 20 pF,    See Figure 2                                                        | –55°C          | 39°                   |     |     | 43°                    |     |     |        |
|                                               |                                                                                                | 125°C          | 25°                   |     |     | 29°                    |     |     |        |




# TLC1078, TLC1078Y, TLC1079, TLC1079Y

## LinCMOS™ $\mu$ POWER PRECISION OPERATIONAL AMPLIFIERS

SLOS179A – FEBRUARY 1997 – REVISED MARCH 2001

### PARAMETER MEASUREMENT INFORMATION



NOTE A:  $C_L$  includes fixture capacitance.

Figure 1. Slew-Rate Test Circuit




Figure 2. Unity-Gain Bandwidth and Phase-Margin Test Circuit

### TYPICAL CHARACTERISTICS

Table of Graphs

|                |                                                 |                                                                                                                         | FIGURE                       |
|----------------|-------------------------------------------------|-------------------------------------------------------------------------------------------------------------------------|------------------------------|
| $\alpha_{VIO}$ | Temperature coefficient of input offset voltage | Distribution                                                                                                            | 3 – 6                        |
| $I_{IB}$       | Input bias current                              | vs Free-air temperature                                                                                                 | 7                            |
| $I_{IO}$       | Input offset current                            | vs Free-air temperature                                                                                                 | 7                            |
| $V_{IC}$       | Common-mode input voltage                       | vs Supply voltage                                                                                                       | 8                            |
| $V_{OH}$       | High-level output voltage                       | vs High-level output current<br>vs Supply voltage<br>vs Free-air temperature                                            | 9, 10<br>11<br>12            |
| $V_{OL}$       | Low-level output voltage                        | vs Common-mode input voltage<br>vs Differential input voltage<br>vs Free-air temperature<br>vs Low-level output current | 13, 14<br>15<br>16<br>17, 18 |
| $A_{VD}$       | Large-signal differential voltage amplification | vs Supply voltage<br>vs Free-air temperature<br>vs Frequency                                                            | 19<br>20<br>21, 22           |
| $V_{OM}$       | Maximum peak output voltage                     | vs Frequency                                                                                                            | 23                           |
| $I_{DD}$       | Supply current                                  | vs Supply voltage<br>vs Free-air temperature                                                                            | 24<br>25                     |
| SR             | Slew rate                                       | vs Supply voltage<br>vs Free-air temperature                                                                            | 26<br>27                     |
|                | Normalized slew rate                            | vs Free-air temperature                                                                                                 | 28                           |
| $V_n$          | Equivalent input noise voltage                  | vs Frequency                                                                                                            | 29                           |
| $B_1$          | Unity-gain bandwidth                            | vs Supply voltage<br>vs Free-air temperature                                                                            | 30<br>31                     |
| $\phi_m$       | Phase margin                                    | vs Supply voltage<br>vs Free-air temperature<br>vs Capacitive load                                                      | 32<br>33<br>34               |
|                | Phase shift                                     | vs Frequency                                                                                                            | 21, 22                       |

## TYPICAL CHARACTERISTICS

DISTRIBUTION OF TLC1078  
 INPUT OFFSET VOLTAGE  
 TEMPERATURE COEFFICIENT




Figure 3

DISTRIBUTION OF TLC1078  
 INPUT OFFSET VOLTAGE  
 TEMPERATURE COEFFICIENT




Figure 4

DISTRIBUTION OF TLC1079  
 INPUT OFFSET VOLTAGE  
 TEMPERATURE COEFFICIENT




Figure 5

DISTRIBUTION OF TLC1079  
 INPUT OFFSET VOLTAGE  
 TEMPERATURE COEFFICIENT






Figure 6

## TYPICAL CHARACTERISTICS




NOTE A: The typical values of input bias current and input offset current below 5 pA were determined mathematically.


**Figure 7**



**Figure 8**



**Figure 9**



**Figure 10**

† Data at high and low temperatures are applicable only within the rated operating free-air temperature ranges of the various devices.

‡ The  $V_{DD} = 3\text{ V}$  curve does not apply to the TLC107xM.

## TYPICAL CHARACTERISTICS




Figure 11




Figure 12




Figure 13




Figure 14

† Data at high and low temperatures are applicable only within the rated operating free-air temperature ranges of the various devices.

## TYPICAL CHARACTERISTICS

LOW-LEVEL OUTPUT VOLTAGE  
vs  
DIFFERENTIAL INPUT VOLTAGE




Figure 15

LOW-LEVEL OUTPUT VOLTAGE†  
vs  
FREE-AIR TEMPERATURE




Figure 16

LOW-LEVEL OUTPUT VOLTAGE  
vs  
LOW-LEVEL OUTPUT CURRENT




Figure 17

LOW-LEVEL OUTPUT VOLTAGE  
vs  
LOW-LEVEL OUTPUT CURRENT




Figure 18

† Data at high and low temperatures are applicable only within the rated operating free-air temperature ranges of the various devices.

## TYPICAL CHARACTERISTICS




Figure 19




Figure 20




Figure 21

† Data at high and low temperatures are applicable only within the rated operating free-air temperature ranges of the various devices.

# TLC1078, TLC1078Y, TLC1079, TLC1079Y

## LinCMOS™ $\mu$ POWER PRECISION

### OPERATIONAL AMPLIFIERS

SLOS179A – FEBRUARY 1997 – REVISED MARCH 2001

#### TYPICAL CHARACTERISTICS

##### LARGE-SIGNAL DIFFERENTIAL VOLTAGE AMPLIFICATION AND PHASE SHIFT VS FREQUENCY




Figure 22

##### MAXIMUM PEAK OUTPUT VOLTAGE VS FREQUENCY




Figure 23

##### SUPPLY CURRENT† VS SUPPLY VOLTAGE




Figure 24

† Data at high and low temperatures are applicable only within the rated operating free-air temperature ranges of the various devices.

## TYPICAL CHARACTERISTICS




Figure 25




Figure 26




Figure 27




Figure 28

<sup>†</sup> Data at high and low temperatures are applicable only within the rated operating free-air temperature ranges of the various devices.

## TYPICAL CHARACTERISTICS




Figure 29




Figure 30




Figure 31






Figure 32

† Data at high and low temperatures are applicable only within the rated operating free-air temperature ranges of the various devices.

## TYPICAL CHARACTERISTICS



**Figure 33**



**Figure 34**

<sup>†</sup> Data at high and low temperatures are applicable only within the rated operating free-air temperature ranges of the various devices.

## PACKAGING INFORMATION

| Orderable part number      | Status<br>(1) | Material type<br>(2) | Package   Pins | Package qty   Carrier | RoHS<br>(3) | Lead finish/<br>Ball material<br>(4) | MSL rating/<br>Peak reflow<br>(5) | Op temp (°C) | Part marking<br>(6) |
|----------------------------|---------------|----------------------|----------------|-----------------------|-------------|--------------------------------------|-----------------------------------|--------------|---------------------|
| <a href="#">TLC1078CD</a>  | Active        | Production           | SOIC (D)   8   | 75   TUBE             | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | 0 to 70      | 1078C               |
| TLC1078CD.A                | Active        | Production           | SOIC (D)   8   | 75   TUBE             | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | 0 to 70      | 1078C               |
| <a href="#">TLC1078CDR</a> | Active        | Production           | SOIC (D)   8   | 2500   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | 0 to 70      | 1078C               |
| TLC1078CDR.A               | Active        | Production           | SOIC (D)   8   | 2500   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | 0 to 70      | 1078C               |
| <a href="#">TLC1078CP</a>  | Active        | Production           | PDIP (P)   8   | 50   TUBE             | Yes         | NIPDAU                               | N/A for Pkg Type                  | 0 to 70      | TLC1078CP           |
| TLC1078CP.A                | Active        | Production           | PDIP (P)   8   | 50   TUBE             | Yes         | NIPDAU                               | N/A for Pkg Type                  | 0 to 70      | TLC1078CP           |
| <a href="#">TLC1078ID</a>  | Active        | Production           | SOIC (D)   8   | 75   TUBE             | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 85    | 1078I               |
| TLC1078ID.A                | Active        | Production           | SOIC (D)   8   | 75   TUBE             | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 85    | 1078I               |
| <a href="#">TLC1078IDR</a> | Active        | Production           | SOIC (D)   8   | 2500   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 85    | 1078I               |
| TLC1078IDR.A               | Active        | Production           | SOIC (D)   8   | 2500   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 85    | 1078I               |
| <a href="#">TLC1078IP</a>  | Active        | Production           | PDIP (P)   8   | 50   TUBE             | Yes         | NIPDAU                               | N/A for Pkg Type                  | -40 to 85    | TLC1078IP           |
| TLC1078IP.A                | Active        | Production           | PDIP (P)   8   | 50   TUBE             | Yes         | NIPDAU                               | N/A for Pkg Type                  | -40 to 85    | TLC1078IP           |
| <a href="#">TLC1079CD</a>  | Active        | Production           | SOIC (D)   14  | 50   TUBE             | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | 0 to 70      | TLC1079C            |
| TLC1079CD.A                | Active        | Production           | SOIC (D)   14  | 50   TUBE             | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | 0 to 70      | TLC1079C            |
| <a href="#">TLC1079CDR</a> | Active        | Production           | SOIC (D)   14  | 2500   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -            | TLC1079C            |
| TLC1079CDR.A               | Active        | Production           | SOIC (D)   14  | 2500   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | 0 to 70      | TLC1079C            |
| <a href="#">TLC1079CN</a>  | Active        | Production           | PDIP (N)   14  | 25   TUBE             | Yes         | NIPDAU                               | N/A for Pkg Type                  | -            | TLC1079CN           |
| TLC1079CN.A                | Active        | Production           | PDIP (N)   14  | 25   TUBE             | Yes         | NIPDAU                               | N/A for Pkg Type                  | 0 to 70      | TLC1079CN           |
| <a href="#">TLC1079ID</a>  | Active        | Production           | SOIC (D)   14  | 50   TUBE             | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -            | TLC1079I            |
| TLC1079ID.A                | Active        | Production           | SOIC (D)   14  | 50   TUBE             | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | 0 to 70      | TLC1079I            |
| <a href="#">TLC1079IDR</a> | Active        | Production           | SOIC (D)   14  | 2500   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -            | TLC1079I            |
| TLC1079IDR.A               | Active        | Production           | SOIC (D)   14  | 2500   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | 0 to 70      | TLC1079I            |
| <a href="#">TLC1079IN</a>  | Active        | Production           | PDIP (N)   14  | 25   TUBE             | Yes         | NIPDAU                               | N/A for Pkg Type                  | -            | TLC1079IN           |
| TLC1079IN.A                | Active        | Production           | PDIP (N)   14  | 25   TUBE             | Yes         | NIPDAU                               | N/A for Pkg Type                  | 0 to 70      | TLC1079IN           |

<sup>(1)</sup> **Status:** For more details on status, see our [product life cycle](#).

<sup>(2)</sup> **Material type:** When designated, preproduction parts are prototypes/experimental devices, and are not yet approved or released for full production. Testing and final process, including without limitation quality assurance, reliability performance testing, and/or process qualification, may not yet be complete, and this item is subject to further changes or possible discontinuation. If available for ordering, purchases will be subject to an additional waiver at checkout, and are intended for early internal evaluation purposes only. These items are sold without warranties of any kind.

<sup>(3)</sup> **RoHS values:** Yes, No, RoHS Exempt. See the [TI RoHS Statement](#) for additional information and value definition.

<sup>(4)</sup> **Lead finish/Ball material:** Parts may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead finish/Ball material values may wrap to two lines if the finish value exceeds the maximum column width.

<sup>(5)</sup> **MSL rating/Peak reflow:** The moisture sensitivity level ratings and peak solder (reflow) temperatures. In the event that a part has multiple moisture sensitivity ratings, only the lowest level per JEDEC standards is shown. Refer to the shipping label for the actual reflow temperature that will be used to mount the part to the printed circuit board.

<sup>(6)</sup> **Part marking:** There may be an additional marking, which relates to the logo, the lot trace code information, or the environmental category of the part.

Multiple part markings will be inside parentheses. Only one part marking contained in parentheses and separated by a "~" will appear on a part. If a line is indented then it is a continuation of the previous line and the two combined represent the entire part marking for that device.

**Important Information and Disclaimer:**The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.

## TAPE AND REEL INFORMATION



\*All dimensions are nominal

| Device     | Package Type | Package Drawing | Pins | SPQ  | Reel Diameter (mm) | Reel Width W1 (mm) | A0 (mm) | B0 (mm) | K0 (mm) | P1 (mm) | W (mm) | Pin1 Quadrant |
|------------|--------------|-----------------|------|------|--------------------|--------------------|---------|---------|---------|---------|--------|---------------|
| TLC1078CDR | SOIC         | D               | 8    | 2500 | 330.0              | 12.4               | 6.4     | 5.2     | 2.1     | 8.0     | 12.0   | Q1            |
| TLC1078IDR | SOIC         | D               | 8    | 2500 | 330.0              | 12.4               | 6.4     | 5.2     | 2.1     | 8.0     | 12.0   | Q1            |
| TLC1079CDR | SOIC         | D               | 14   | 2500 | 330.0              | 16.4               | 6.5     | 9.0     | 2.1     | 8.0     | 16.0   | Q1            |
| TLC1079IDR | SOIC         | D               | 14   | 2500 | 330.0              | 16.4               | 6.5     | 9.0     | 2.1     | 8.0     | 16.0   | Q1            |


## TAPE AND REEL BOX DIMENSIONS



\*All dimensions are nominal

| Device     | Package Type | Package Drawing | Pins | SPQ  | Length (mm) | Width (mm) | Height (mm) |
|------------|--------------|-----------------|------|------|-------------|------------|-------------|
| TLC1078CDR | SOIC         | D               | 8    | 2500 | 353.0       | 353.0      | 32.0        |
| TLC1078IDR | SOIC         | D               | 8    | 2500 | 353.0       | 353.0      | 32.0        |
| TLC1079CDR | SOIC         | D               | 14   | 2500 | 350.0       | 350.0      | 43.0        |
| TLC1079IDR | SOIC         | D               | 14   | 2500 | 350.0       | 350.0      | 43.0        |

## TUBE



\*All dimensions are nominal

| Device      | Package Name | Package Type | Pins | SPQ | L (mm) | W (mm) | T (μm) | B (mm) |
|-------------|--------------|--------------|------|-----|--------|--------|--------|--------|
| TLC1078CD   | D            | SOIC         | 8    | 75  | 507    | 8      | 3940   | 4.32   |
| TLC1078CD   | D            | SOIC         | 8    | 75  | 505.46 | 6.76   | 3810   | 4      |
| TLC1078CD.A | D            | SOIC         | 8    | 75  | 507    | 8      | 3940   | 4.32   |
| TLC1078CD.A | D            | SOIC         | 8    | 75  | 505.46 | 6.76   | 3810   | 4      |
| TLC1078CP   | P            | PDIP         | 8    | 50  | 506    | 13.97  | 11230  | 4.32   |
| TLC1078CP.A | P            | PDIP         | 8    | 50  | 506    | 13.97  | 11230  | 4.32   |
| TLC1078ID   | D            | SOIC         | 8    | 75  | 505.46 | 6.76   | 3810   | 4      |
| TLC1078ID   | D            | SOIC         | 8    | 75  | 507    | 8      | 3940   | 4.32   |
| TLC1078ID.A | D            | SOIC         | 8    | 75  | 505.46 | 6.76   | 3810   | 4      |
| TLC1078ID.A | D            | SOIC         | 8    | 75  | 507    | 8      | 3940   | 4.32   |
| TLC1078IP   | P            | PDIP         | 8    | 50  | 506    | 13.97  | 11230  | 4.32   |
| TLC1078IP.A | P            | PDIP         | 8    | 50  | 506    | 13.97  | 11230  | 4.32   |
| TLC1079CD   | D            | SOIC         | 14   | 50  | 505.46 | 6.76   | 3810   | 4      |
| TLC1079CD.A | D            | SOIC         | 14   | 50  | 505.46 | 6.76   | 3810   | 4      |
| TLC1079CN   | N            | PDIP         | 14   | 25  | 506    | 13.97  | 11230  | 4.32   |
| TLC1079CN.A | N            | PDIP         | 14   | 25  | 506    | 13.97  | 11230  | 4.32   |
| TLC1079ID   | D            | SOIC         | 14   | 50  | 505.46 | 6.76   | 3810   | 4      |
| TLC1079ID.A | D            | SOIC         | 14   | 50  | 505.46 | 6.76   | 3810   | 4      |
| TLC1079IN   | N            | PDIP         | 14   | 25  | 506    | 13.97  | 11230  | 4.32   |
| TLC1079IN.A | N            | PDIP         | 14   | 25  | 506    | 13.97  | 11230  | 4.32   |

**D0014A****PACKAGE OUTLINE****SOIC - 1.75 mm max height**

SMALL OUTLINE INTEGRATED CIRCUIT



4220718/A 09/2016

**NOTES:**

1. All linear dimensions are in millimeters. Dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.
2. This drawing is subject to change without notice.
3. This dimension does not include mold flash, protrusions, or gate burrs. Mold flash, protrusions, or gate burrs shall not exceed 0.15 mm, per side.
4. This dimension does not include interlead flash. Interlead flash shall not exceed 0.43 mm, per side.
5. Reference JEDEC registration MS-012, variation AB.

# EXAMPLE BOARD LAYOUT


D0014A

SOIC - 1.75 mm max height

SMALL OUTLINE INTEGRATED CIRCUIT



LAND PATTERN EXAMPLE  
SCALE:8X



SOLDER MASK DETAILS

4220718/A 09/2016

NOTES: (continued)

6. Publication IPC-7351 may have alternate designs.

7. Solder mask tolerances between and around signal pads can vary based on board fabrication site.

## EXAMPLE STENCIL DESIGN

D0014A

SOIC - 1.75 mm max height

SMALL OUTLINE INTEGRATED CIRCUIT



SOLDER PASTE EXAMPLE  
BASED ON 0.125 mm THICK STENCIL  
SCALE:8X

4220718/A 09/2016

NOTES: (continued)

8. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.
9. Board assembly site may have different recommendations for stencil design.



## PACKAGE OUTLINE

**SOIC - 1.75 mm max height**

SMALL OUTLINE INTEGRATED CIRCUIT



1. Linear dimensions are in inches [millimeters]. Dimensions in parenthesis are for reference only. Controlling dimensions are in inches. Dimensioning and tolerancing per ASME Y14.5M.
2. This drawing is subject to change without notice.
3. This dimension does not include mold flash, protrusions, or gate burrs. Mold flash, protrusions, or gate burrs shall not exceed .006 [0.15] per side.
4. This dimension does not include interlead flash.
5. Reference JEDEC registration MS-012, variation AA.

**D0008A**

**SOIC - 1.75 mm max height**

SMALL OUTLINE INTEGRATED CIRCUIT



LAND PATTERN EXAMPLE  
EXPOSED METAL SHOWN  
SCALE:8X



## SOLDER MASK DETAILS

4214825/C 02/2019

NOTES: (continued)

6. Publication IPC-7351 may have alternate designs.

7. Solder mask tolerances between and around signal pads can vary based on board fabrication site.

## EXAMPLE STENCIL DESIGN

D0008A

SOIC - 1.75 mm max height

SMALL OUTLINE INTEGRATED CIRCUIT



SOLDER PASTE EXAMPLE  
BASED ON .005 INCH [0.125 MM] THICK STENCIL  
SCALE:8X

4214825/C 02/2019

NOTES: (continued)

8. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.
9. Board assembly site may have different recommendations for stencil design.

P (R-PDIP-T8)

PLASTIC DUAL-IN-LINE PACKAGE



- NOTES:
- A. All linear dimensions are in inches (millimeters).
  - B. This drawing is subject to change without notice.
  - C. Falls within JEDEC MS-001 variation BA.


## N (R-PDIP-T\*\*)

16 PINS SHOWN

## PLASTIC DUAL-IN-LINE PACKAGE



| PINS **             | 14               | 16               | 18               | 20               |
|---------------------|------------------|------------------|------------------|------------------|
| DIM                 |                  |                  |                  |                  |
| A MAX               | 0.775<br>(19,69) | 0.775<br>(19,69) | 0.920<br>(23,37) | 1.060<br>(26,92) |
| A MIN               | 0.745<br>(18,92) | 0.745<br>(18,92) | 0.850<br>(21,59) | 0.940<br>(23,88) |
| MS-001<br>VARIATION | AA               | BB               | AC               | AD               |



4040049/E 12/2002

- NOTES:
- A. All linear dimensions are in inches (millimeters).
  - B. This drawing is subject to change without notice.
  - C. Falls within JEDEC MS-001, except 18 and 20 pin minimum body length (Dim A).
  - D. The 20 pin end lead shoulder width is a vendor option, either half or full width.

## IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATASHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, regulatory or other requirements.

These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you fully indemnify TI and its representatives against any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to [TI's Terms of Sale](#), [TI's General Quality Guidelines](#), or other applicable terms available either on [ti.com](https://www.ti.com) or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products. Unless TI explicitly designates a product as custom or customer-specified, TI products are standard, catalog, general purpose devices.

TI objects to and rejects any additional or different terms you may propose.

Copyright © 2026, Texas Instruments Incorporated

Last updated 10/2025