

TLC2274AM-MIL Advanced LinCMOS Rail-to-Rail Operational Amplifier

1 Features

- Output Swing Includes Both Supply Rails
- Low Noise: 9 nV/ $\sqrt{\text{Hz}}$ Typical at $f = 1 \text{ kHz}$
- Low-Input Bias Current: 1-pA Typical
- Fully-Specified for Both Single-Supply and Split-Supply Operation
- Common-Mode Input Voltage Range Includes Negative Rail
- High-Gain Bandwidth: 2.2-MHz Typical
- High Slew Rate: 3.6-V/ μs Typical
- Low Input Offset Voltage: 2.5 mV Maximum at $T_A = 25^\circ\text{C}$
- Macromodel Included
- Performance Upgrades for the TLC272 and TLC274
- Available in Q-Temp Automotive

2 Applications

- White Goods (Refrigerators, Washing Machines)
- Hand-held Monitoring Systems
- Configuration Control and Print Support
- Transducer Interfaces
- Battery-Powered Applications

3 Description

The TLC2274AM-MIL device is a quadruple operational amplifier from Texas Instruments. The device exhibits rail-to-rail output performance for increased dynamic range in single- or split-supply applications. The TLC2274AM-MIL device offers 2 MHz of bandwidth and 3 V/ μs of slew rate for higher-speed applications. The device offers comparable ac performance while having better noise, input offset voltage, and power dissipation than existing CMOS operational amplifiers. The TLC2274AM-MIL device has a noise voltage of 9 nV/ $\sqrt{\text{Hz}}$, two times lower than competitive solutions.

The TLC2274AM-MIL device, exhibiting high input impedance and low noise, is excellent for small-signal conditioning for high-impedance sources such as piezoelectric transducers. Because of the micropower dissipation levels, the device works well in hand-held monitoring and remote-sensing applications. In addition, the rail-to-rail output feature, with single- or split-supplies, makes this device a great choice when interfacing with analog-to-digital converters (ADCs). For precision applications, the TLC2272AM-MIL device is available with a maximum input offset voltage of 950 μV . This device is fully characterized at 5 V and $\pm 5 \text{ V}$.

The TLC2274AM-MIL device also makes a great upgrade to the TLC272 in standard designs, offering increased output dynamic range, lower noise voltage, and lower input offset voltage. This enhanced feature set allows the device to be used in a wider range of applications. For applications that require higher output drive and wider input voltage range, see the TLV2432 and TLV2442 devices.

If the design requires single amplifiers, see the TLV2211, TLV2221 and TLV2231 family. These devices are single rail-to-rail operational amplifiers in the SOT-23 package. Their small size and low power consumption make them ideal for high density, battery-powered equipment.

Device Information⁽¹⁾

| PART NUMBER | PACKAGE | BODY SIZE (NOM) |
|---------------|-----------|--------------------|
| TLC2274AM-MIL | SOIC (14) | 3,91 mm x 8,65 mm |
| | CDIP (14) | 6,67 mm x 19,56 mm |
| | LCCC (20) | 8,89 mm x 8,89 mm |
| | CFP (14) | 6,35 mm x 19,30 mm |

(1) For all available packages, see the orderable addendum at the end of the data sheet.

Maximum Peak-to-Peak Output Voltage vs Supply Voltage







Table of Contents

| | | | |
|---|-----------|--|-----------|
| 1 Features | 1 | 7.3 Feature Description | 19 |
| 2 Applications | 1 | 7.4 Device Functional Modes | 19 |
| 3 Description | 1 | 8 Application and Implementation | 20 |
| 4 Revision History | 2 | 8.1 Application Information | 20 |
| 5 Pin Configuration and Functions | 3 | 8.2 Typical Application | 21 |
| 6 Specifications | 5 | 9 Power Supply Recommendations | 23 |
| 6.1 Absolute Maximum Ratings | 5 | 10 Layout | 24 |
| 6.2 ESD Ratings | 5 | 10.1 Layout Guidelines | 24 |
| 6.3 Recommended Operating Conditions | 5 | 10.2 Layout Example | 24 |
| 6.4 Thermal Information | 5 | 11 Device and Documentation Support | 25 |
| 6.5 Electrical Characteristics $V_{DD} = 5\text{ V}$ | 6 | 11.1 Receiving Notification of Documentation Updates | 25 |
| 6.6 Electrical Characteristics $V_{DD\pm} = \pm 5\text{ V}$ | 8 | 11.2 Community Resources | 25 |
| 6.7 Typical Characteristics | 9 | 11.3 Trademarks | 25 |
| 7 Detailed Description | 19 | 11.4 Electrostatic Discharge Caution | 25 |
| 7.1 Overview | 19 | 11.5 Glossary | 25 |
| 7.2 Functional Block Diagram | 19 | 12 Mechanical, Packaging, and Orderable Information | 25 |

4 Revision History

| DATE | REVISION | NOTE |
|-----------|----------|-----------------|
| June 2017 | * | Initial release |

5 Pin Configuration and Functions



Pin Functions

| NAME | PIN | | I/O | DESCRIPTION |
|-----------------------------------|---------------|---------------------|-----|--------------------------------|
| | NO. | | | |
| | D, J, N, or W | FK | | |
| 1IN+ | 3 | 4 | I | Non-inverting input, Channel 1 |
| 1IN– | 2 | 3 | I | Inverting input, Channel 1 |
| 1OUT | 1 | 2 | O | Output, Channel 1 |
| 2IN+ | 5 | 8 | I | Non-inverting input, Channel 2 |
| 2IN– | 6 | 9 | I | Inverting input, Channel 2 |
| 2OUT | 7 | 10 | O | Output, Channel 2 |
| 3IN+ | 10 | 14 | I | Non-inverting input, Channel 3 |
| 3IN– | 9 | 13 | I | Inverting input, Channel 3 |
| 3OUT | 8 | 12 | O | Output, Channel 3 |
| 4IN+ | 12 | 18 | I | Non-inverting input, Channel 4 |
| 4IN– | 13 | 19 | I | Inverting input, Channel 4 |
| 4OUT | 14 | 20 | O | Output, Channel 4 |
| V _{DD} ⁺ | 4 | 6 | — | Positive (highest) supply |
| V _{DD} [–] | 11 | 16 | — | Negative (lowest) supply |
| V _{DD} [–] /GND | — | — | — | Negative (lowest) supply |
| NC | — | 1, 5, 7, 11, 15, 17 | — | No connection |

6 Specifications

6.1 Absolute Maximum Ratings

over operating ambient temperature range (unless otherwise noted)⁽¹⁾

| | MIN | MAX | UNIT |
|---|-----------------|-----------|------|
| Supply voltage, V_{DD+} ⁽²⁾ | | 8 | V |
| V_{DD-} ⁽²⁾ | -8 | | V |
| Differential input voltage, V_{ID} ⁽³⁾ | | ±16 | V |
| Input voltage, V_I (any input) ⁽²⁾ | $V_{DD-} - 0.3$ | V_{DD+} | V |
| Input current, I_I (any input) | | ±5 | mA |
| Output current, I_O | | ±50 | mA |
| Total current into V_{DD+} | | ±50 | mA |
| Total current out of V_{DD-} | | ±50 | mA |
| Duration of short-circuit current at (or below) 25°C ⁽⁴⁾ | | Unlimited | |
| Operating ambient temperature range, T_A | -55 | 125 | |
| Storage temperature, T_{stg} | -65 | 150 | °C |

- (1) Stresses beyond those listed under *Absolute Maximum Ratings* may cause permanent damage to the device. These are stress ratings only, which do not imply functional operation of the device at these or any other conditions beyond those indicated under *Recommended Operating Conditions*. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability.
- (2) All voltage values, except differential voltages, are with respect to the midpoint between V_{DD+} and V_{DD-} .
- (3) Differential voltages are at IN+ with respect to IN-. Excessive current will flow if input is brought below $V_{DD-} - 0.3$ V.
- (4) The output may be shorted to either supply. Temperature or supply voltages must be limited to ensure that the maximum dissipation rating is not exceeded.

6.2 ESD Ratings

| | | | VALUE | UNIT |
|-------------------------------------|---|-----------------------|-------|------|
| $V_{(ESD)}$ Electrostatic discharge | Human-body model (HBM), per AEC Q100-002 ⁽¹⁾ | Devices in D packages | ±2000 | V |
| | Charged-device model (CDM), per AEC Q100-011 | Devices in D packages | ±1000 | |

- (1) AEC Q100-002 indicates that HBM stressing shall be in accordance with the ANSI/ESDA/JEDEC JS-001 specification.

6.3 Recommended Operating Conditions

| | | MIN | MAX | UNIT |
|-----------|-------------------------------|-----------|-----------------|------|
| $V_{DD±}$ | Supply voltage | ±2.2 | ±8 | V |
| V_I | Input voltage | V_{DD-} | $V_{DD+} - 1.5$ | V |
| V_{IC} | Common-mode input voltage | V_{DD-} | $V_{DD+} - 1.5$ | V |
| T_A | Operating ambient temperature | -55 | 125 | °C |

6.4 Thermal Information

| THERMAL METRIC ⁽¹⁾ | TLC2274AM-MIL | | | | | UNIT |
|--|---------------|----------|-----------|----------|---------|------|
| | D (SOIC) | J (CDIP) | FK (LCCC) | N (PDIP) | W (CFP) | |
| | 14-PIN | 14-PIN | 20-PIN | 14-PIN | 14-PIN | |
| $R_{θJA}$ Junction-to-ambient thermal resistance ⁽²⁾⁽³⁾ | 115.6 | — | — | — | — | °C/W |
| $R_{θJC(top)}$ Junction-to-case (top) thermal resistance ⁽²⁾⁽³⁾ | 61.8 | 16.2 | 18 | — | 121.3 | °C/W |
| $R_{θJB}$ Junction-to-board thermal resistance | 55.9 | — | — | — | — | °C/W |
| $ψ_{JT}$ Junction-to-top characterization parameter | 14.3 | — | — | — | — | °C/W |
| $ψ_{JB}$ Junction-to-board characterization parameter | 55.4 | — | — | — | — | °C/W |
| $R_{θJC(bot)}$ Junction-to-case (bottom) thermal resistance | — | — | — | — | 8.68 | °C/W |

- (1) For more information about traditional and new thermal metrics, see *Semiconductor and IC Package Thermal Metrics*.
- (2) Maximum power dissipation is a function of $T_{J(max)}$, $R_{θJA}$, and T_A . The maximum allowable power dissipation at any allowable ambient temperature is $P_D = (T_{J(max)} - T_A) / R_{θJA}$. Operating at the absolute maximum T_J of 150°C can affect reliability.
- (3) The package thermal impedance is calculated in accordance with JESD 51-7 (plastic) or MIL-STD-883 Method 1012 (ceramic).

6.5 Electrical Characteristics $V_{DD} = 5\text{ V}$

at specified ambient temperature, $V_{DD} = 5\text{ V}$; $T_A = 25^\circ\text{C}$, unless otherwise noted.

| PARAMETER | | TEST CONDITIONS | | MIN | TYP | MAX | UNIT | |
|--|--|---|--|--|-----------|------|------------------------------|------------|
| V_{IO} | Input offset voltage | $V_{IC} = 0\text{ V}$, $V_{DD\pm} = \pm 2.5\text{ V}$, $V_O = 0\text{ V}$, $R_S = 50\ \Omega$ | $T_A = 25^\circ\text{C}$ | | 300 | 950 | μV | |
| | | | $T_A = -55^\circ\text{C}$ to 125°C | | | 1500 | | |
| α_{VIO} | Temperature coefficient of input offset voltage | $V_{IC} = 0\text{ V}$, $V_{DD\pm} = \pm 2.5\text{ V}$, $V_O = 0\text{ V}$, $R_S = 50\ \Omega$ | | | 2 | | $\mu\text{V}/^\circ\text{C}$ | |
| | Input offset voltage long-term drift ⁽¹⁾ | $V_{IC} = 0\text{ V}$, $V_{DD\pm} = \pm 2.5\text{ V}$, $V_O = 0\text{ V}$, $R_S = 50\ \Omega$ | | | 0.002 | | $\mu\text{V}/\text{mo}$ | |
| I_{IO} | Input offset current | $V_{IC} = 0\text{ V}$, $V_{DD\pm} = \pm 2.5\text{ V}$, $V_O = 0\text{ V}$, $R_S = 50\ \Omega$ | $T_A = 25^\circ\text{C}$ | | 0.5 | 60 | pA | |
| | | | $T_A = -55^\circ\text{C}$ to 125°C | | | 800 | | |
| I_{IB} | Input bias current | $V_{IC} = 0\text{ V}$, $V_{DD\pm} = \pm 2.5\text{ V}$, $V_O = 0\text{ V}$, $R_S = 50\ \Omega$ | $T_A = 25^\circ\text{C}$ | | 1 | 60 | pA | |
| | | | $T_A = -55^\circ\text{C}$ to 125°C | | | 800 | | |
| V_{ICR} | Common-mode input voltage | $R_S = 50\ \Omega$; $ V_{IO} \leq 5\text{ mV}$ | $T_A = 25^\circ\text{C}$ | | -0.3 | 2.5 | 4 | V |
| | | | $T_A = -55^\circ\text{C}$ to 125°C | | 0 | 2.5 | 3.5 | |
| V_{OH} | High-level output voltage | | $I_{OH} = -20\ \mu\text{A}$ | | 4.99 | | V | |
| | | | $I_{OH} = -200\ \mu\text{A}$ | $T_A = 25^\circ\text{C}$ | 4.85 | 4.93 | | |
| | | | | $T_A = -55^\circ\text{C}$ to 125°C | 4.85 | | | |
| | | | $I_{OH} = -1\text{ mA}$ | $T_A = 25^\circ\text{C}$ | 4.25 | 4.65 | | |
| $T_A = -55^\circ\text{C}$ to 125°C | 4.25 | | | | | | | |
| V_{OL} | Low-level output voltage | $V_{IC} = 2.5\text{ V}$ | $I_{OL} = 50\ \mu\text{A}$ | $T_A = 25^\circ\text{C}$ | 0.01 | | V | |
| | | | | $T_A = -55^\circ\text{C}$ to 125°C | 0.09 | 0.15 | | |
| | | | $I_{OL} = 500\ \mu\text{A}$ | $T_A = 25^\circ\text{C}$ | | 0.15 | | |
| | | | | $T_A = -55^\circ\text{C}$ to 125°C | 0.9 | 1.5 | | |
| A_{VD} | Large-signal differential voltage amplification | $V_{IC} = 2.5\text{ V}$, $V_O = 1\text{ V}$ to 4 V , $R_L = 10\text{ k}\Omega^{(2)}$ | $T_A = 25^\circ\text{C}$ | | 15 | 35 | V/mV | |
| | | | $T_A = -55^\circ\text{C}$ to 125°C | | 15 | | | |
| | | $V_{IC} = 2.5\text{ V}$, $V_O = 1\text{ V}$ to 4 V , $R_L = 1\text{ M}\Omega^{(2)}$ | | | 175 | | | |
| r_{id} | Differential input resistance | | | | 10^{12} | | Ω | |
| r_i | Common-mode input resistance | | | | 10^{12} | | Ω | |
| c_i | Common-mode input capacitance | $f = 10\text{ kHz}$, P package | | | 8 | | pF | |
| z_o | Closed-loop output impedance | $f = 1\text{ MHz}$, $A_V = 10$ | | | 140 | | Ω | |
| CMRR | Common-mode rejection ratio | $V_{IC} = 0\text{ V}$ to 2.7 V , $V_O = 2.5\text{ V}$, $R_S = 50\ \Omega$ | $T_A = 25^\circ\text{C}$ | | 70 | 75 | dB | |
| | | | $T_A = -55^\circ\text{C}$ to 125°C | | 70 | | | |
| k_{SVR} | Supply-voltage rejection ratio ($\Delta V_{DD} / \Delta V_{IO}$) | $V_{DD} = 4.4\text{ V}$ to 16 V , $V_{IC} = V_{DD} / 2$, no load | $T_A = 25^\circ\text{C}$ | | 80 | 95 | dB | |
| | | | $T_A = -55^\circ\text{C}$ to 125°C | | 80 | | | |
| I_{DD} | Supply current | $V_O = 2.5\text{ V}$, no load | $T_A = 25^\circ\text{C}$ | | 4.4 | 6 | mA | |
| | | | $T_A = -55^\circ\text{C}$ to 125°C | | | 3 | | |
| SR | Slew rate at unity gain | $V_O = 0.5\text{ V}$ to 2.5 V , $R_L = 10\text{ k}\Omega^{(2)}$, $C_L = 100\text{ pF}^{(2)}$ | $T_A = 25^\circ\text{C}$ | | 2.3 | 3.6 | $\text{V}/\mu\text{s}$ | |
| | | | $T_A = -55^\circ\text{C}$ to 125°C | | 1.7 | | | |
| V_n | Equivalent input noise voltage | | $f = 10\text{ Hz}$ | | 50 | | $\text{nV}/\sqrt{\text{Hz}}$ | |
| | | | $f = 1\text{ kHz}$ | | 9 | | | |
| V_{NPP} | Peak-to-peak equivalent input noise voltage | | $f = 0.1\text{ Hz}$ to 1 Hz | | 1 | | μV | |
| | | | $f = 0.1\text{ Hz}$ to 10 Hz | | 1.4 | | | |
| I_n | Equivalent input noise current | | | | 0.6 | | $\text{fA}/\sqrt{\text{Hz}}$ | |
| THD+N | Total harmonic distortion + noise | $V_O = 0.5\text{ V}$ to 2.5 V , $f = 20\text{ kHz}$, $R_L = 10\text{ k}\Omega^{(2)}$ | $A_V = 1$ | | 0.0013% | | | |
| | | | $A_V = 10$ | | 0.004% | | | |
| | | | $A_V = 100$ | | 0.03% | | | |
| | Gain-bandwidth product | $f = 10\text{ kHz}$, $R_L = 10\text{ k}\Omega^{(2)}$, $C_L = 100\text{ pF}^{(2)}$ | | | 2.18 | | MHz | |
| B_{OM} | Maximum output-swing bandwidth | $V_{O(PP)} = 2\text{ V}$, $A_V = 1$, $R_L = 10\text{ k}\Omega^{(2)}$, $C_L = 100\text{ pF}^{(2)}$ | | | 1 | | MHz | |
| t_s | Settling time | $A_V = -1$, $R_L = 10\text{ k}\Omega^{(2)}$, Step = 0.5 V to 2.5 V , $C_L = 100\text{ pF}^{(2)}$ | To 0.1% | | 1.5 | | μs | |
| | | | To 0.01% | | 2.6 | | | |

(1) Typical values are based on the input offset voltage shift observed through 168 hours of operating life test at $T_A = 150^\circ\text{C}$ extrapolated to $T_A = 25^\circ\text{C}$ using the Arrhenius equation and assuming an activation energy of 0.96 eV .

(2) Referenced to 0 V .

Electrical Characteristics $V_{DD} = 5\text{ V}$ (continued)

 at specified ambient temperature, $V_{DD} = 5\text{ V}$; $T_A = 25^\circ\text{C}$, unless otherwise noted.

| PARAMETER | | TEST CONDITIONS | MIN | TYP | MAX | UNIT |
|-----------|----------------------------|---|-----|-----|-----|----------|
| ϕ_m | Phase margin at unity gain | $R_L = 10\text{ k}\Omega^{(2)}$, $C_L = 100\text{ pF}^{(2)}$ | | 50 | | $^\circ$ |
| | Gain margin | $R_L = 10\text{ k}\Omega^{(2)}$, $C_L = 100\text{ pF}^{(2)}$ | | 10 | | dB |

6.6 Electrical Characteristics $V_{DD\pm} = \pm 5\text{ V}$

at specified ambient temperature, $V_{DD\pm} = \pm 5\text{ V}$; $T_A = 25^\circ\text{C}$, unless otherwise noted.

| PARAMETER | | TEST CONDITIONS | | MIN | TYP | MAX | UNIT | |
|--|--|--|--|--|-----------|-------|------------------------------|------------|
| V_{IO} | Input offset voltage | $V_{IC} = 0\text{ V}$, $V_O = 0\text{ V}$, $R_S = 50\ \Omega$ | $T_A = 25^\circ\text{C}$ | | 300 | 950 | μV | |
| | | | $T_A = -55^\circ\text{C}$ to 125°C | | | 1500 | | |
| α_{VIO} | Temperature coefficient of input offset voltage | $V_{IC} = 0\text{ V}$, $V_O = 0\text{ V}$, $R_S = 50\ \Omega$ | | | 2 | | $\mu\text{V}/^\circ\text{C}$ | |
| | Input offset voltage long-term drift | $V_{IC} = 0\text{ V}$, $V_O = 0\text{ V}$, $R_S = 50\ \Omega$ | | | 0.002 | | $\mu\text{V}/\text{mo}$ | |
| I_{IO} | Input offset current | $V_{IC} = 0\text{ V}$, $V_O = 0\text{ V}$, $R_S = 50\ \Omega$ | $T_A = 25^\circ\text{C}$ | | 0.5 | 60 | pA | |
| | | | $T_A = -55^\circ\text{C}$ to 125°C | | | 800 | | |
| I_{IB} | Input bias current | $V_{IC} = 0\text{ V}$, $V_O = 0\text{ V}$, $R_S = 50\ \Omega$ | $T_A = 25^\circ\text{C}$ | | 1 | 60 | pA | |
| | | | $T_A = -55^\circ\text{C}$ to 125°C | | | 800 | | |
| V_{ICR} | Common-mode input voltage | $R_S = 50\ \Omega$; $ V_{IO} \leq 5\text{ mV}$ | $T_A = 25^\circ\text{C}$ | | -5.3 | 0 | 4 | V |
| | | | $T_A = -55^\circ\text{C}$ to 125°C | | -5 | 0 | 3.5 | |
| V_{OM+} | Maximum positive peak output voltage | $V_{IC} = 0\text{ V}$ | $I_O = -20\ \mu\text{A}$ | | 4.99 | | V | |
| | | | $I_O = -200\ \mu\text{A}$ | $T_A = 25^\circ\text{C}$ | 4.85 | 4.93 | | |
| | | | | $T_A = -55^\circ\text{C}$ to 125°C | 4.85 | | | |
| | | | $I_O = -1\text{ mA}$ | $T_A = 25^\circ\text{C}$ | 4.25 | 4.65 | | |
| $T_A = -55^\circ\text{C}$ to 125°C | 4.25 | | | | | | | |
| V_{OM-} | Maximum negative peak output voltage | $V_{IC} = 0\text{ V}$ | $I_O = 50\ \mu\text{A}$ | | -4.99 | | V | |
| | | | $I_O = 500\ \mu\text{A}$ | $T_A = 25^\circ\text{C}$ | -4.85 | -4.91 | | |
| | | | | $T_A = -55^\circ\text{C}$ to 125°C | -4.85 | | | |
| | | | $I_O = 5\text{ mA}$ | $T_A = 25^\circ\text{C}$ | -3.5 | -4.1 | | |
| $T_A = -55^\circ\text{C}$ to 125°C | -3.5 | | | | | | | |
| A_{VD} | Large-signal differential voltage amplification | $V_O = \pm 4\text{ V}$; $R_L = 10\text{ k}\Omega$ | $T_A = 25^\circ\text{C}$ | | 20 | 50 | V/mV | |
| | | | $T_A = -55^\circ\text{C}$ to 125°C | | 20 | | | |
| | | $V_O = \pm 4\text{ V}$; $R_L = 1\text{ M}\Omega$ | | | 300 | | | |
| r_{id} | Differential input resistance | | | | 10^{12} | | Ω | |
| r_i | Common-mode input resistance | | | | 10^{12} | | Ω | |
| c_i | Common-mode input capacitance | $f = 10\text{ kHz}$, P package | | | 8 | | pF | |
| z_o | Closed-loop output impedance | $f = 1\text{ MHz}$, $A_V = 10$ | | | 130 | | Ω | |
| CMRR | Common-mode rejection ratio | $V_{IC} = -5\text{ V}$ to 2.7 V , $V_O = 0\text{ V}$, $R_S = 50\ \Omega$ | $T_A = 25^\circ\text{C}$ | | 75 | 80 | dB | |
| | | | $T_A = -55^\circ\text{C}$ to 125°C | | 75 | | | |
| k_{SVR} | Supply-voltage rejection ratio ($\Delta V_{DD} / \Delta V_{IO}$) | $V_{DD+} = 2.2\text{ V}$ to $\pm 8\text{ V}$, $V_{IC} = 0\text{ V}$, no load | $T_A = 25^\circ\text{C}$ | | 80 | 95 | dB | |
| | | | $T_A = -55^\circ\text{C}$ to 125°C | | 80 | | | |
| I_{DD} | Supply current | $V_O = 0\text{ V}$, no load | $T_A = 25^\circ\text{C}$ | | 4.8 | 6 | mA | |
| | | | $T_A = -55^\circ\text{C}$ to 125°C | | | 6 | | |
| SR | Slew rate at unity gain | $V_O = \pm 2.3\text{ V}$, $R_L = 10\text{ k}\Omega$, $C_L = 100\text{ pF}$ | $T_A = 25^\circ\text{C}$ | | 2.3 | 3.6 | $\text{V}/\mu\text{s}$ | |
| | | | $T_A = -55^\circ\text{C}$ to 125°C | | 1.7 | | | |
| V_n | Equivalent input noise voltage | $f = 10\text{ Hz}$ | | | 50 | | $\text{nV}/\sqrt{\text{Hz}}$ | |
| | | $f = 1\text{ kHz}$ | | | 9 | | | |
| V_{NPP} | Peak-to-peak equivalent input noise voltage | $f = 0.1\text{ Hz}$ to 1 Hz | | | 1 | | μV | |
| | | $f = 0.1\text{ Hz}$ to 10 Hz | | | 1.4 | | | |
| I_n | Equivalent input noise current | | | | 0.6 | | $\text{fA}/\sqrt{\text{Hz}}$ | |
| THD+N | Total harmonic distortion + noise | $V_O = \pm 2.3$, $f = 20\text{ kHz}$, $R_L = 10\text{ k}\Omega$ | $A_V = 1$ | | 0.0011% | | | |
| | | | $A_V = 10$ | | 0.004% | | | |
| | | | $A_V = 100$ | | 0.03% | | | |
| | Gain-bandwidth product | $f = 10\text{ kHz}$, $R_L = 10\text{ k}\Omega$, $C_L = 100\text{ pF}$ | | | 2.25 | | MHz | |
| B_{OM} | Maximum output-swing bandwidth | $V_{O(PP)} = 4.6\text{ V}$, $A_V = 1$, $R_L = 10\text{ k}\Omega$, $C_L = 100\text{ pF}$ | | | 0.54 | | MHz | |
| t_s | Settling time | $A_V = -1$, $R_L = 10\text{ k}\Omega$, Step = -2.3 V to 2.3 V , $C_L = 100\text{ pF}$ | To 0.1% | | 1.5 | | μs | |
| | | | To 0.01% | | 3.2 | | | |
| ϕ_m | Phase margin at unity gain | $R_L = 10\text{ k}\Omega$, $C_L = 100\text{ pF}$ | | | 52 | | $^\circ$ | |
| | | | | | 10 | | | |
| | Gain margin | $R_L = 10\text{ k}\Omega$, $C_L = 100\text{ pF}$ | | | 10 | | dB | |

6.7 Typical Characteristics

Table 1. Table of Graphs

| | | FIGURE⁽¹⁾ | |
|-------------------|--|-------------------------------|---------------------------------------|
| V_{IO} | Input offset voltage | Distribution | 1, 2 |
| | | vs Common-mode voltage | 3, 4 |
| α_{VIO} | Input offset voltage temperature coefficient | Distribution | 5, 6 ⁽²⁾ |
| I_{IB} / I_{IO} | Input bias and input offset current | vs Ambient temperature | 7 ⁽²⁾ |
| V_I | Input voltage | vs Supply voltage | 8 |
| | | vs Ambient temperature | 9 ⁽²⁾ |
| V_{OH} | High-level output voltage | vs High-level output current | 10 ⁽²⁾ |
| V_{OL} | Low-level output voltage | vs Low-level output current | 11, 12 ⁽²⁾ |
| V_{OM+} | Maximum positive peak output voltage | vs Output current | 13 ⁽²⁾ |
| V_{OM-} | Maximum negative peak output voltage | vs Output current | 14 ⁽²⁾ |
| $V_{O(PP)}$ | Maximum peak-to-peak output voltage | vs Frequency | 15 |
| I_{OS} | Short-circuit output current | vs Supply voltage | 16 |
| | | vs Ambient temperature | 17 ⁽²⁾ |
| V_O | Output voltage | vs Differential input voltage | 18, 19 |
| A_{VD} | Large-signal differential voltage amplification | vs Load resistance | 20 |
| | Large-signal differential voltage amplification and phase margin | vs Frequency | 21, 22 |
| | Large-signal differential voltage amplification | vs Ambient temperature | 23 ⁽²⁾ , 24 ⁽²⁾ |
| z_0 | Output impedance | vs Frequency | 25, 26 |
| CMRR | Common-mode rejection ratio | vs Frequency | 27 |
| | | vs Ambient temperature | 28 |
| k_{SVR} | Supply-voltage rejection ratio | vs Frequency | 29, 30 |
| | | vs Ambient temperature | 31 ⁽²⁾ |
| I_{DD} | Supply current | vs Supply voltage | ⁽²⁾ , 32 ⁽²⁾ |
| | | vs Ambient temperature | ⁽²⁾ , 33 ⁽²⁾ |
| SR | Slew rate | vs Load Capacitance | 34 |
| | | vs Ambient temperature | 35 ⁽²⁾ |
| V_O | Inverting large-signal pulse response | | 36, 37 |
| | Voltage-follower large-signal pulse response | | 38, 39 |
| | Inverting small-signal pulse response | | 40, 41 |
| | Voltage-follower small-signal pulse response | | 42, 43 |
| V_n | Equivalent input noise voltage | vs Frequency | 44, 45 |
| | Noise voltage over a 10-second period | | 46 |
| | Integrated noise voltage | vs Frequency | 47 |
| THD+N | Total harmonic distortion + noise | vs Frequency | 48 |
| | Gain-bandwidth product | vs Supply voltage | 49 |
| | | vs Ambient temperature | 50 ⁽²⁾ |
| ϕ_m | Phase margin | vs Load capacitance | 51 |
| | Gain margin | vs Load capacitance | 52 |

(1) For all graphs where $V_{DD} = 5\text{ V}$, all loads are referenced to 2.5 V.

(2) Data at high and low temperatures are applicable only within the rated operating ambient temperature ranges of the various devices.




Figure 1. Distribution of Input Offset Voltage




Figure 2. Distribution of Input Offset Voltage




Figure 3. Input Offset Voltage vs Common-Mode Voltage




Figure 4. Input Offset Voltage vs Common-Mode Voltage




Figure 5. Distribution vs Input-Offset-Voltage Temperature Coefficient




Figure 6. Distribution vs Input-Offset-Voltage Temperature Coefficient




Figure 7. Input Bias and Input Offset Current vs Ambient Temperature




Figure 8. Input Voltage vs Supply Voltage




Figure 9. Input Voltage vs Ambient Temperature




Figure 10. High-Level Output Voltage vs High-Level Output Current




Figure 11. Low-Level Output Voltage vs Low-Level Output Current




Figure 12. Low-Level Output Voltage vs Low-Level Output Current




Figure 13. Maximum Positive Peak Output Voltage vs Output Current




Figure 14. Maximum Negative Peak Output Voltage vs Output Current




Figure 15. Maximum Peak-to-Peak Output Voltage vs Frequency




Figure 16. Short-Circuit Output Current vs Supply Voltage




Figure 17. Short-Circuit Output Current vs Ambient Temperature




Figure 18. Output Voltage vs Differential Input Voltage




Figure 19. Output Voltage vs Differential Input Voltage




Figure 20. Large-Signal Differential Voltage Amplification vs Load Resistance




Figure 21. Large-Signal Differential Voltage Amplification and Phase Margin vs Frequency




Figure 22. Large-Signal Differential Voltage Amplification and Phase Margin vs Frequency




Figure 23. Large-Signal Differential Voltage Amplification vs Ambient Temperature




Figure 24. Large-Signal Differential Voltage Amplification vs Ambient Temperature




Figure 25. Output Impedance vs Frequency




Figure 26. Output Impedance vs Frequency




Figure 27. Common-Mode Rejection Ratio vs Frequency




Figure 28. Common-Mode Rejection Ratio vs Ambient Temperature




Figure 29. Supply-Voltage Rejection Ratio vs Frequency




Figure 30. Supply-Voltage Rejection Ratio vs Frequency




Figure 31. Supply-Voltage Rejection Ratio vs Ambient Temperature




Figure 32. Supply Current vs Supply Voltage




Figure 33. Supply Current vs Ambient Temperature




Figure 34. Slew Rate vs Load Capacitance




Figure 35. Slew Rate vs Ambient Temperature




Figure 36. Inverting Large-Signal Pulse Response




Figure 37. Inverting Large-Signal Pulse Response




Figure 38. Voltage-Follower Large-Signal Pulse Response




Figure 39. Voltage-Follower Large-Signal Pulse Response




Figure 40. Inverting Small-Signal Pulse Response




Figure 41. Inverting Small-Signal Pulse Response




Figure 42. Voltage-Follower Small-Signal Pulse Response




Figure 43. Voltage-Follower Small-Signal Pulse Response




Figure 44. Equivalent Input Noise Voltage vs Frequency




Figure 45. Equivalent Input Noise Voltage vs Frequency




Figure 46. Noise Voltage Over a 10-Second Period




Figure 47. Integrated Noise Voltage vs Frequency




Figure 48. Total Harmonic Distortion + Noise vs Frequency




Figure 49. Gain-Bandwidth Product vs Supply Voltage




Figure 50. Gain-Bandwidth Product vs Ambient Temperature




Figure 51. Phase Margin vs Load Capacitance




Figure 52. Gain Margin vs Load Capacitance

7 Detailed Description

7.1 Overview

The TLC2274AM-MIL device is a rail-to-rail output operational amplifier. The device operates from a 4.4-V to 16-V single supply or ± 2.2 -V to ± 8 -V dual supply, is unity-gain stable, and is suitable for a wide range of general-purpose applications.

7.2 Functional Block Diagram




Table 2. Device Component Count⁽¹⁾

| COMPONENT | COUNT |
|-------------|-------|
| Transistors | 76 |
| Resistors | 52 |
| Diodes | 18 |
| Capacitors | 6 |

(1) Includes both amplifiers and all ESD, bias, and trim circuitry.

7.3 Feature Description

The TLC2274AM-MIL device features 2-MHz bandwidth and voltage noise of $9 \text{ nV}/\sqrt{\text{Hz}}$ with performance rated from 4.4 V to 16 V across a temperature range (-55°C to 125°C). LinMOS suits a wide range of audio, automotive, industrial, and instrumentation applications.

7.4 Device Functional Modes

The TLC2274AM-MIL device is powered on when the supply is connected. The device may operate with single or dual supply, depending on the application. The device is in its full-performance mode once the supply is above the recommended value.

8 Application and Implementation

NOTE

Information in the following applications sections is not part of the TI component specification, and TI does not warrant its accuracy or completeness. TI's customers are responsible for determining suitability of components for their purposes. Customers should validate and test their design implementation to confirm system functionality.

8.1 Application Information

8.1.1 Macromodel Information

Macromodel information provided was derived using MicroSim Parts™, the model generation software used with MicroSim PSpice™. The Boyle macromodel ⁽¹⁾ and subcircuit in Figure 53 were generated using the TLC2274AM-MIL typical electrical and operating characteristics at T_A = 25°C. Using this information, output simulations of the following key parameters can be generated to a tolerance of 20% (in most cases):

- Maximum positive output voltage swing
- Maximum negative output voltage swing
- Slew rate
- Quiescent power dissipation
- Input bias current
- Open-loop voltage amplification
- Unity-gain frequency
- Common-mode rejection ratio
- Phase margin
- DC output resistance
- AC output resistance
- Short-circuit output current limit




Figure 53. Boyle Macromodel and Subcircuit

(1) *Macromodeling of Integrated Circuit Operational Amplifiers*, IEEE Journal of Solid-State Circuits, SC-9, 353 (1974).

8.2 Typical Application

8.2.1 High-Side Current Monitor




Figure 54. Equivalent Schematic (Each Amplifier)

8.2.1.1 Design Requirements

For this design example, use the parameters listed in [Table 3](#) as the input parameters.

Table 3. Design Parameters

| PARAMETER | VALUE |
|-----------------------|--|
| V_{BAT} | Battery voltage 12 V |
| R_{SENSE} | Sense resistor 0.1 Ω |
| I_{LOAD} | Load current 0 A to 10 A |
| Operational amplifier | Set in differential configuration with gain = 10 |

8.2.1.2 Detailed Design Procedure

This circuit is designed for measuring the high-side current in automotive body control modules with a 12-V battery or similar applications. The operational amplifier is set as differential with an external resistor network.

8.2.1.2.1 Differential Amplifier Equations

[Equation 1](#) and [Equation 2](#) are used to calculate V_{OUT} .

$$V_{OUT} = \frac{R_g}{R} \left(\frac{\frac{R}{R_g} - \frac{R_1}{R_2}}{1 + \frac{R_1}{R_2}} \times \frac{V_1 + V_2}{2} + \frac{1 + \frac{1}{2} \left(\frac{R_1}{R_2} + \frac{R}{R_g} \right)}{1 + \frac{R_1}{R_2}} (V_1 - V_2) \right) \quad (1)$$

$$V_{OUT} = \frac{R_g}{R} \left(\frac{\frac{R}{R_g} - \frac{R_1}{R_2}}{1 + \frac{R_1}{R_2}} \times V_{BAT} + \frac{1 + \frac{1}{2} \left(\frac{R_1}{R_2} + \frac{R}{R_g} \right)}{1 + \frac{R_1}{R_2}} \times R_S \times I_{LOAD} \right) \quad (2)$$

In an ideal case $R_1 = R$ and $R_2 = R_g$, and V_{OUT} can then be calculated using [Equation 3](#):

$$V_{OUT} = \frac{R_g}{R} \times R_S \times I_{LOAD} \quad (3)$$

However, as the resistors have tolerances, they cannot be perfectly matched.

$$\begin{aligned}
 R_1 &= R \pm \Delta R_1 \\
 R_2 &= R_2 \pm \Delta R_2 \\
 R &= R \pm \Delta R \\
 R_g &= R_g \pm \Delta R_g \\
 \text{Tol} &= \frac{\Delta R}{R}
 \end{aligned}
 \tag{4}$$

By developing the equations and neglecting the second order, the worst case is when the tolerances add up. This is shown by [Equation 5](#).

$$V_{\text{OUT}} = \pm (4 \text{ Tol}) \frac{R_g}{R + R_g} \times V_{\text{BAT}} + \left(1 \pm 2 \text{ Tol} \left(1 + \frac{2R}{R + R_g} \right) \right) \frac{R_g}{R} \times R_S \times I_{\text{LOAD}}$$

where

- Tol = 0.01 for 1%
 - Tol = 0.001 for 0.1%
- (5)

If the resistors are perfectly matched, then Tol = 0 and V_{OUT} is calculated using [Equation 6](#).

$$V_{\text{OUT}} = \frac{R_g}{R} \times R_S \times I_{\text{LOAD}} \tag{6}$$

The highest error is from the common mode, as shown in [Equation 7](#).

$$4 (\text{Tol}) \frac{R_g}{R + R_g} \times V_{\text{BAT}} \tag{7}$$

Gain of 10, $R_g / R = 10$, and Tol = 1%:

$$\text{Common mode error} = ((4 \times 0.01) / 1.1) \times 12 \text{ V} = 0.436 \text{ V}$$

Gain of 10 and Tol = 0.1%:

$$\text{Common mode error} = 43.6 \text{ mV}$$

The resistors were chosen from 2% batches.

$$R_1 \text{ and } R \text{ 12 k}\Omega$$

$$R_2 \text{ and } R_g \text{ 120 k}\Omega$$

$$\text{Ideal Gain} = 120 / 12 = 10$$

The measured value of the resistors:


$$R_1 = 11.835 \text{ k}\Omega$$

$$R = 11.85 \text{ k}\Omega$$

$$R_2 = 117.92 \text{ k}\Omega$$

$$R_g = 118.07 \text{ k}\Omega$$

8.2.1.3 Application Curves



9 Power Supply Recommendations

Supply voltage for a single supply is from 4.4 V to 16 V, and from ± 2.2 V to ± 8 V for a dual supply. In the high-side sensing application, the supply is connected to a 12-V battery.

10 Layout

10.1 Layout Guidelines

The TLC2274AM-MIL device is a wideband amplifier. To realize the full operational performance of the device, good high-frequency printed-circuit-board (PCB) layout practices are required. Low-loss 0.1- μF bypass capacitors must be connected between each supply pin and ground as close to the device as possible. The bypass capacitor traces should be designed for minimum inductance.

10.2 Layout Example




Figure 57. Layout Example

11 Device and Documentation Support

11.1 Receiving Notification of Documentation Updates

To receive notification of documentation updates, navigate to the device product folder on ti.com. In the upper right corner, click on *Alert me* to register and receive a weekly digest of any product information that has changed. For change details, review the revision history included in any revised document.

11.2 Community Resources

The following links connect to TI community resources. Linked contents are provided "AS IS" by the respective contributors. They do not constitute TI specifications and do not necessarily reflect TI's views; see TI's [Terms of Use](#).

TI E2E™ Online Community *TI's Engineer-to-Engineer (E2E) Community*. Created to foster collaboration among engineers. At e2e.ti.com, you can ask questions, share knowledge, explore ideas and help solve problems with fellow engineers.

Design Support *TI's Design Support* Quickly find helpful E2E forums along with design support tools and contact information for technical support.

11.3 Trademarks

E2E is a trademark of Texas Instruments.
 MicroSim Parts, PSpice are trademarks of MicroSim.
 All other trademarks are the property of their respective owners.

11.4 Electrostatic Discharge Caution



These devices have limited built-in ESD protection. The leads should be shorted together or the device placed in conductive foam during storage or handling to prevent electrostatic damage to the MOS gates.

11.5 Glossary

[SLYZ022](#) — *TI Glossary*.

This glossary lists and explains terms, acronyms, and definitions.

12 Mechanical, Packaging, and Orderable Information

The following pages include mechanical, packaging, and orderable information. This information is the most-current data available for the designated device. This data is subject to change without notice and without revision of this document. For browser-based versions of this data sheet, see the left-hand navigation pane.

PACKAGING INFORMATION

| Orderable Device | Status (1) | Package Type | Package Drawing | Pins | Package Qty | Eco Plan (2) | Lead finish/ Ball material (6) | MSL Peak Temp (3) | Op Temp (°C) | Device Marking (4/5) | Samples |
|------------------|---------------|--------------|-----------------|------|-------------|---------------------|--------------------------------------|----------------------|--------------|---|-------------------------|
| 5962-9318202Q2A | ACTIVE | LCCC | FK | 20 | 55 | Non-RoHS & Green | SNPB | N / A for Pkg Type | -55 to 125 | 5962- 9318202Q2A TLC2274 AMFKB | Samples |
| 5962-9318202QCA | ACTIVE | CDIP | J | 14 | 25 | Non-RoHS & Green | SNPB | N / A for Pkg Type | -55 to 125 | 5962-9318202QC A TLC2274AMJB | Samples |
| 5962-9318202QDA | ACTIVE | CFP | W | 14 | 25 | Non-RoHS & Green | SNPB | N / A for Pkg Type | -55 to 125 | 5962-9318202QD A TLC2274AMWB | Samples |
| TLC2274AMFKB | ACTIVE | LCCC | FK | 20 | 55 | Non-RoHS & Green | SNPB | N / A for Pkg Type | -55 to 125 | 5962- 9318202Q2A TLC2274 AMFKB | Samples |
| TLC2274AMJB | ACTIVE | CDIP | J | 14 | 25 | Non-RoHS & Green | SNPB | N / A for Pkg Type | -55 to 125 | 5962-9318202QC A TLC2274AMJB | Samples |
| TLC2274AMWB | ACTIVE | CFP | W | 14 | 25 | Non-RoHS & Green | SNPB | N / A for Pkg Type | -55 to 125 | 5962-9318202QD A TLC2274AMWB | Samples |

(1) The marketing status values are defined as follows:

ACTIVE: Product device recommended for new designs.

LIFEBUY: TI has announced that the device will be discontinued, and a lifetime-buy period is in effect.

NRND: Not recommended for new designs. Device is in production to support existing customers, but TI does not recommend using this part in a new design.

PREVIEW: Device has been announced but is not in production. Samples may or may not be available.

OBSELETE: TI has discontinued the production of the device.

(2) **RoHS:** TI defines "RoHS" to mean semiconductor products that are compliant with the current EU RoHS requirements for all 10 RoHS substances, including the requirement that RoHS substance do not exceed 0.1% by weight in homogeneous materials. Where designed to be soldered at high temperatures, "RoHS" products are suitable for use in specified lead-free processes. TI may reference these types of products as "Pb-Free".

RoHS Exempt: TI defines "RoHS Exempt" to mean products that contain lead but are compliant with EU RoHS pursuant to a specific EU RoHS exemption.

Green: TI defines "Green" to mean the content of Chlorine (Cl) and Bromine (Br) based flame retardants meet JS709B low halogen requirements of <=1000ppm threshold. Antimony trioxide based flame retardants must also meet the <=1000ppm threshold requirement.

(3) MSL, Peak Temp. - The Moisture Sensitivity Level rating according to the JEDEC industry standard classifications, and peak solder temperature.

(4) There may be additional marking, which relates to the logo, the lot trace code information, or the environmental category on the device.

(5) Multiple Device Markings will be inside parentheses. Only one Device Marking contained in parentheses and separated by a "~" will appear on a device. If a line is indented then it is a continuation of the previous line and the two combined represent the entire Device Marking for that device.

(6) Lead finish/Ball material - Orderable Devices may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead finish/Ball material values may wrap to two lines if the finish value exceeds the maximum column width.

Important Information and Disclaimer:The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.

TUBE


*All dimensions are nominal

| Device | Package Name | Package Type | Pins | SPQ | L (mm) | W (mm) | T (μm) | B (mm) |
|-----------------|--------------|--------------|------|-----|--------|--------|--------|--------|
| 5962-9318202Q2A | FK | LCCC | 20 | 55 | 506.98 | 12.06 | 2030 | NA |
| 5962-9318202QDA | W | CFP | 14 | 25 | 506.98 | 26.16 | 6220 | NA |
| TLC2274AMFKB | FK | LCCC | 20 | 55 | 506.98 | 12.06 | 2030 | NA |
| TLC2274AMWB | W | CFP | 14 | 25 | 506.98 | 26.16 | 6220 | NA |

W (R-GDFP-F14)

CERAMIC DUAL FLATPACK



- NOTES:
- A. All linear dimensions are in inches (millimeters).
 - B. This drawing is subject to change without notice.
 - C. This package can be hermetically sealed with a ceramic lid using glass frit.
 - D. Index point is provided on cap for terminal identification only.
 - E. Falls within MIL STD 1835 GDFP1-F14

GENERIC PACKAGE VIEW

FK 20

LCCC - 2.03 mm max height

8.89 x 8.89, 1.27 mm pitch

LEADLESS CERAMIC CHIP CARRIER

This image is a representation of the package family, actual package may vary.
Refer to the product data sheet for package details.



4229370VA\

J 14

GENERIC PACKAGE VIEW
CDIP - 5.08 mm max height
CERAMIC DUAL IN LINE PACKAGE



Images above are just a representation of the package family, actual package may vary.
Refer to the product data sheet for package details.

4040083-5/G

J0014A



PACKAGE OUTLINE

CDIP - 5.08 mm max height

CERAMIC DUAL IN LINE PACKAGE



4214771/A 05/2017

NOTES:

1. All controlling linear dimensions are in inches. Dimensions in brackets are in millimeters. Any dimension in brackets or parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.
2. This drawing is subject to change without notice.
3. This package is hermetically sealed with a ceramic lid using glass frit.
4. Index point is provided on cap for terminal identification only and on press ceramic glass frit seal only.
5. Falls within MIL-STD-1835 and GDIP1-T14.

EXAMPLE BOARD LAYOUT

J0014A

CDIP - 5.08 mm max height

CERAMIC DUAL IN LINE PACKAGE



LAND PATTERN EXAMPLE
NON-SOLDER MASK DEFINED
SCALE: 5X



4214771/A 05/2017

IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATA SHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, regulatory or other requirements.

These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you will fully indemnify TI and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to [TI's Terms of Sale](#) or other applicable terms available either on [ti.com](https://www.ti.com) or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products.

TI objects to and rejects any additional or different terms you may have proposed.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265
Copyright © 2024, Texas Instruments Incorporated