

SGLS395A-OCTOBER 2008-REVISED SEPTEMBER 2010

DUAL, 250-mA OUTPUT, ULTRA-LOW NOISE, HIGH PSRR, LOW-DROPOUT LINEAR REGULATOR

Check for Samples: TPS71202-EP

FEATURES

- Dual 250-mA High-Performance RF LDOs
- Adjustable Output Voltage (1.2 V to 5.5 V)
- High PSRR: 65 dB at 10 kHz
- Ultra-Low Noise: 32 µVrms
- Fast Start-Up Time: 60 μs
- Stable with 2.2-µF Ceramic Capacitor
- Excellent Load/Line Transient Response
- Very Low Dropout Voltage: 125 mV at 250 mA
- Independent Enable Pins
- Thermal Shutdown and Independent Current
 Limit
- Available in Thermally-Enhanced SON Package: 3 mm × 3 mm × 1 mm

APPLICATIONS

- Cellular and Cordless Phones
- Wireless PDA/Handheld Products
- PCMCIA/Wireless LAN Applications
- Digital Camera/Camcorder/Internet Audio
- DSP/FPGA/ASIC/Controllers and Processors

SUPPORTS DEFENSE, AEROSPACE, AND MEDICAL APPLICATIONS

- Controlled Baseline
- One Assembly/Test Site
- One Fabrication Site
- Available in Military (-55°C/125°C) Temperature Range⁽¹⁾
- Extended Product Life Cycle
- Extended Product-Change Notification

• Product Traceability DESCRIPTION

The TPS71202 low-dropout (LDO) voltage regulator is tailored to noise-sensitive and RF applications. It features dual 250-mA LDOs with ultra-low noise, high power-supply rejection ratio (PSRR), and fast transient and start-up response. Each regulator output is stable with low-cost 2.2-uF ceramic output capacitors and features very low dropout voltages (125 mV typical at 250 mA). The regulator achieves fast start-up times (approximately 60 µs with a 0.001-µF bypass capacitor) while consuming very low quiescent current (300 µÅ typical with both outputs enabled). When the device is placed in standby mode, the supply current is reduced to less than 0.3 µA typical. The regulator exhibits approximately 32 μ Vrms of output voltage noise with V_{OUT} = 2.8 V and a 0.01-µF noise reduction (NR) capacitor. Applications with analog components that are noise-sensitive, such as portable RF electronics, benefit from high PSRR, low noise, and fast line and load transient features. The TPS71202 is offered in a thin 3-mm × 3-mm SON package and is fully specified from -55°C to 125°C (T_J).

(1) Custom temperature ranges available



Please be aware that an important notice concerning availability, standard warranty, and use in critical applications of Texas Instruments semiconductor products and disclaimers thereto appears at the end of this data sheet.

Copyright © 2008–2010, Texas Instruments Incorporated On products compliant to MIL-PRF-38535, all parameters are tested unless otherwise noted. On all other products, production processing does not necessarily include testing of all parameters.

TPS71202-EP

1 Kar

TEXAS INSTRUMENTS


SGLS395A-OCTOBER 2008-REVISED SEPTEMBER 2010

www.ti.com

This integrated circuit can be damaged by ESD. Texas Instruments recommends that all integrated circuits be handled with appropriate precautions. Failure to observe proper handling and installation procedures can cause damage.

ESD damage can range from subtle performance degradation to complete device failure. Precision integrated circuits may be more susceptible to damage because very small parametric changes could cause the device not to meet its published specifications.

DRC PACKAGE 3-mm × 3-mm SON (TOP VIEW)								
IN NC	1	ין וו		EN1 FB1				
OUT1	3	15	I '	EN2				
OUT2 GND	4] [5] I	[[FB2 NR				



ORDERING INFORMATION⁽¹⁾

Tj	PACK	AGE ⁽²⁾	ORDERABLE PART NUMBER	TOP-SIDE MARKING	
–55°C to 125°C	SON-10 - DRC	Reel of 250	TPS71202MDRCTEP	CVQ	

(1) For the most current package and ordering information, see the Package Option Addendum at the end of this document, or see the TI web site at www.ti.com.

(2) Package drawings, thermal data, and symbolization are available at www.ti.com/packaging.

ABSOLUTE MAXIMUM RATINGS

over operating junction temperature range unless otherwise noted⁽¹⁾

V_{IN}	Input voltage range	IN	–0.3 V to 6 V		
V _{EN1} , V _{EN2}	Input voltage range	EN1, EN2	–0.3 V to V _{IN} + 0.3 V		
V _{OUT}	Output voltage range	OUT	-0.3 V to 6 V		
	Peak output current		Internally limited		
	Output short-circuit duration	Indefinite			
	Continuous total power dissipation		See Thermal Information table		
TJ	Junction temperature range		–55°C to 150°C		
	Storage temperature range		-65°C to 150°C		
	Electrostatio discharge action	Human-Body Model (HBM)	2000 V		
ESD	Electrostatic discharge rating	Charged-Device Model (CDM)	500 V		

(1) Stresses beyond those listed under absolute maximum ratings may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated under the Electrical Characteristics is not implied. Exposure to absolute maximum rated conditions for extended periods may affect device reliability.



SGLS395A-OCTOBER 2008-REVISED SEPTEMBER 2010

THERMAL INFORMATION

	THERMAL METRIC ⁽¹⁾⁽²⁾	TPS71202-EP	
		DRC (10 PINS)	UNITS
θ_{JA}	Junction-to-ambient thermal resistance	49.6	
θ_{JCtop}	Junction-to-case (top) thermal resistance	70.0	
θ_{JB}	Junction-to-board thermal resistance	17.8	80 M
ΨJT	Junction-to-top characterization parameter	0.6	°C/W
Ψјв	Junction-to-board characterization parameter	15.2	
θ_{JCbot}	Junction-to-case (bottom) thermal resistance	5.2	

(1) For more information about traditional and new thermal metrics, see the IC Package Thermal Metrics application report, SPRA953. For thermal estimates of this device based on PCB copper area, see the TI PCB Thermal Calculator. (2)

ELECTRICAL CHARACTERISTICS

over operating temperature range ($T_J = -55^{\circ}C$ to +125°C), V_{IN} = highest ($V_{OUT(nom)}$ + 1 V) or 2.7 V (whichever is greater), $I_{OUT} = 1 \text{ mA}$, $V_{EN1, 2} = 1.2 \text{ V}$, $C_{OUT} = 10 \mu\text{F}$, $C_{NR} = 0.01 \mu\text{F}$, and adjustable LDOs are tested at $V_{OUT} = 3.0 \text{ V}$ (unless otherwise noted). Typical values are at $T_J = 25^{\circ}\text{C}$.


	PARAMETER		Т	EST CONDITIONS	MIN	TYP	MAX	UNIT	
V _{IN}	Input voltage range ⁽¹⁾				2.7		5.5	V	
V _{FB}	Internal reference (adjusta	ence (adjustable LDOs)			1.200	1.225	1.250	V	
	Output voltage range (adjustable LDOs)				V _{FB}	5.5	i – V _{DO}	V	
V _{OUT}		Nominal	T _J = +25°C, I	_{OUT} = 0 mA	-1.5		+1.5		
	Accuracy ⁽¹⁾ Over V _{IN} , I _{OUT} , and temperature		V _{OUT} + 1.0 V 0 µA ≤ I _{OUT} ≤	-3	1	+3	%		
ΔV _{OUT} %/ΔV _{IN}	Line regulation ⁽¹⁾	1	V _{OUT} + 1.0 V	$\leq V_{IN} \leq 5.5 V$		0.05		%/V	
ΔV _{OUT} %/ΔI _{OU} τ			0 μA ≤ I _{OUT} ≤	250 mA		0.8		%/mA	
V _{DO}	Dropout voltage ($V_{IN} = V_{OUT(nom)} - 0.1V$)		$I_{OUT1} = I_{OUT2}$		125	315	mV		
I _{CL}	Output current limit		$V_{OUT} = 0.9 \times$	V _{OUT(nom)}	400	600	800	mA	
	Crowned allo comment	One LDO enabled	$I_{OUT} = 1 \text{ mA}$	I _{OUT} = 1 mA (enabled channel)		190	250	٨	
I _{GND}	Ground pin current	Both LDOs enabled	$I_{OUT1} = I_{OUT2}$		300	600	μA		
I _{SHDN}	Shutdown current ⁽²⁾		$V_{EN} \le 0.4 V$,	0 V ≤ V _{IN} ≤ 5.5 V		0.3	2.0	μA	
I _{FB}	FB pin current					0.1	1.50	μA	
M	Output noise voltage,		No C _{NR} , I _{OUT} = 250 mA		80.0) × V _{OUT}		μVrms	
Vn	BW = 10 Hz to 100 kHz		$C_{NR} = 0.01 \ \mu F, \ I_{OUT} = 250 \ mA$		11.8	3 × V _{out}		μνπις	
PSRR	Power-supply rejection ra	tio	f = 100 Hz, I _{OUT} = 250 mA			65		dB	
FORK	(ripple rejection)		f = 10 kHz, I _{OUT} = 250 mA			65		uВ	
t _{STR}	Startup time		V _{OUT} = 2.85	V, $R_L = 30\Omega$, $C_{NR} = 0.001 \ \mu F$		60		μS	
VIH	Enable threshold high (EN	N1, EN2)			1.2		V_{IN}	V	
V _{IL}	Enable threshold low (EN	1, EN2)			0		0.4	V	
I _{EN}	Enable pin current (EN1,	EN2)	$V_{IN} = V_{EN} = 5$	5.5 V	-1		1	μA	
т	Thermal shutdown tempe	raturo	Shutdown	Shutdown Temp increasing		+160		°C	
T _{SD}		aure	Reset Temp decreasing +					-C	
UVLO	Undervoltage lockout thre	shold	V _{IN} rising		2.25		2.65	V	
	Undervoltage lockout hys	teresis	V _{IN} falling			100		mV	

(1)

Minimum $V_{IN} = (V_{OUT} + V_{DO})$ or 2.7 V, whichever is greater. For the adjustable version, this applies only after V_{IN} is applied; then V_{EN} transitions from high to low. (2)



SGLS395A-OCTOBER 2008-REVISED SEPTEMBER 2010






Table 1. TERMINAL FUNCTIONS

TERM	INAL	DECODIDITION
NAME	DRC	DESCRIPTION
IN	1	Unregulated input supply. A small 0.1-µF capacitor should be connected from IN to GND.
GND	5, Pad	Ground
OUT1	3	Output of the regulator. A small 2.2- μ F ceramic capacitor is required from this pin to ground to assure stability.
OUT2	4	Same as OUT1 but for LDO2.
EN1	10	Driving the enable pin (EN) high turns on LDO1. Driving this pin low puts LDO1 into shutdown mode, reducing operating current. The enable pin should be connected to IN if not used.
EN2	8	Same as EN1 but controls LDO2.
FB1	9	Feedback for channel 1
FB2	7	Feedback for channel 2
NR	6	Noise reduction pin; connect an external bypass capacitor to reduce LDO output noise.
NC	2	No connection.

4

TPS71202-EP


www.ti.com


XAS

STRUMENTS


TYPICAL CHARACTERISTICS


For all voltage versions at $T_J = 25^{\circ}$ C, $V_{IN} = V_{OUT(nom)} + 1$ V, $I_{OUT} = 1$ mA, $V_{EN} = 1.2$ V, $C_{OUT} = 2.2 \mu$ F, and $C_{NR} = 0.01 \mu$ F (unless otherwise noted)













SGLS395A-OCTOBER 2008-REVISED SEPTEMBER 2010

Figure 2.

DROPOUT VOLTAGE vs INPUT VOLTAGE (ADJUSTABLE VERSION)



TPS71256 DROPOUT VOLTAGE vs JUNCTION TEMPERATURE



Copyright © 2008–2010, Texas Instruments Incorporated


SGLS395A-OCTOBER 2008-REVISED SEPTEMBER 2010


EXAS ISTRUMENTS

www.ti.com

TYPICAL CHARACTERISTICS (continued)

For all voltage versions at $T_J = 25^{\circ}$ C, $V_{IN} = V_{OUT(nom)} + 1$ V, $I_{OUT} = 1$ mA, $V_{EN} = 1.2$ V, $C_{OUT} = 2.2$ μ F, and $C_{NR} = 0.01$ μ F (unless otherwise noted)





GROUND PIN CURRENT vs JUNCTION TEMPERATURE






Figure 9.



GROUND PIN CURRENT vs JUNCTION TEMPERATURE (DISABLED)









Figure 12.

6



1k

TEXAS INSTRUMENTS

SGLS395A-OCTOBER 2008-REVISED SEPTEMBER 2010

TPS71256

CHANNEL-TO-CHANNEL ISOLATION vs FREQUENCY

www.ti.com

TYPICAL CHARACTERISTICS (continued)

60

50

40

30

20

10

0

Channel Isolation (dB)

For all voltage versions at $T_J = 25^{\circ}$ C, $V_{IN} = V_{OUT(nom)} + 1$ V, $I_{OUT} = 1$ mA, $V_{EN} = 1.2$ V, $C_{OUT} = 2.2$ μ F, and $C_{NR} = 0.01$ μ F (unless otherwise noted)






Figure 13.









0.1 1 10 100 Frequency (Hz) Figure 14. TPS71229


 $I_{OUT1} = 0$ mA to 500 mA Sinusoidal Load


 $C_{OUT1} = C_{OUT2} = 10 \ \mu F$

 $I_{OUT2} = 25 \text{ mA}$










Copyright © 2008–2010, Texas Instruments Incorporated

SGLS395A-OCTOBER 2008-REVISED SEPTEMBER 2010



www.ti.com



8



SGLS395A-OCTOBER 2008-REVISED SEPTEMBER 2010

APPLICATION INFORMATION

The TPS71202 dual low-dropout (LDO) regulator has been optimized for use in noise-sensitive battery-operated equipment. The device features extremely low dropout, high PSRR, ultra-low output noise, and low quiescent current (190 μ A typical per channel). When both outputs are disabled, the supply currents are reduced to less than 2 μ A.

INPUT AND OUTPUT CAPACITOR REQUIREMENTS

A 0.1- μ F or larger ceramic input bypass capacitor, connected between IN and GND and located close to the TPS71202, is required for stability. It improves transient response, noise rejection, and ripple rejection. A higher-value input capacitor may be necessary if large, fast rise-time load transients are anticipated and the device is located several inches from the power source.

TPS71202 requires an output capacitor The connected between the outputs and GND to stabilize control loops. the internal The minimum recommended output capacitor is 2.2 µF. If an output voltage of 1.8 V or less is chosen, the minimum recommended output capacitor is 4.7 µF. Any ceramic capacitor that meets the minimum output capacitor requirements is suitable. Capacitors with higher ESR may be used, provided the ESR is less than 1 Ω .

OUTPUT NOISE

The internal voltage reference is a key source of noise in an LDO regulator. The TPS71202 has an NR pin that is connected to the voltage reference through a 250-k Ω internal resistor. The 250-k Ω internal resistor, in conjunction with an external ceramic bypass capacitor connected to the NR pin, creates a low-pass filter to reduce the voltage reference noise and, therefore, the noise at the regulator output. To achieve a fast startup, the 250-k Ω internal resistor is shorted for 400 μ s after the device is enabled.

Because the primary noise source is the internal voltage reference, the output noise is greater for higher output voltage versions. For the case where no noise reduction capacitor is used, the typical noise (μ Vrms) over 10 Hz to 100 kHz is 80 times the output voltage. If a 0.01- μ F capacitor is used from the NR pin to ground, the noise (μ Vrms) drops to 11.8 times the output voltage.

STARTUP CHARACTERISITCS

To minimize startup overshoot, the TPS71202 initially targets an output voltage that is approximately 80% of the final value. To avoid a delayed startup time, noise reduction capacitors of 0.01 μ F or less are recommended. Larger noise reduction capacitors cause the output to hold at 80% until the voltage on the noise reduction capacitor exceeds 80% of the bandgap voltage. The typical startup time with a 0.001- μ F noise reduction capacitor is 60 μ s. Once one of the output voltages is present, the startup time of the other output is not affected by the noise reduction capacitor.

SGLS395A - OCTOBER 2008 - REVISED SEPTEMBER 2010

PROGRAMMING THE TPS71202 ADJUSTABLE LDO REGULATOR

The output voltage of the TPS71202 dual adjustable regulator is programmed using an external resistor divider, as shown in Figure 24. The output voltage is calculated using Equation 1:

$$V_{OUT} = V_{REF} \times \left(1 + \frac{R1}{R2}\right)$$
(1)

where V_{REF} = 1.225 V (the internal reference voltage).

Resistors R2 and R4 should be chosen for approximately a 40- μ A divider current. Lower value resistors can be used for improved noise performance but consume more power. Higher values should be avoided because leakage current at FB increases the output voltage error. The recommended design procedure is to choose R2 = 30.1 k Ω to set the divider current at 40 μ A, and then calculate R1 using Equation 2:

$$R1 = \left(\frac{V_{OUT}}{V_{REF}} - 1\right) \times R2$$
(2)

To improve the stability and noise performance of the adjustable version, a small compensation capacitor can be placed between OUT and FB.




Figure 24. Adjustable LDO Regulator Programming



For voltages \leq 1.8 V, the value of this capacitor should be 100 pF. For voltages > 1.8 V, the approximate value of this capacitor can be calculated as Equation 3:

$$C1 = \frac{(3 \times 10^5) \times (R1 + R2)}{(R1 \times R2)} \qquad (pF)$$
(3)

The suggested value of this capacitor for several resistor ratios is shown in Figure 24. If this capacitor is not used (such as in a unity-gain configuration) or if an output voltage ≤ 1.8 V is chosen, then the minimum recommended output capacitor is 4.7 μ F instead of 2.2 μ F.

DROPOUT VOLTAGE

The TPS712xx uses a PMOS pass transistor to achieve extremely low dropout. When ($V_{IN} - V_{OUT}$) is less than the dropout voltage (V_{DO}), the PMOS pass device is in its linear region of operation and the input-to-output resistance is the $R_{DS, ON}$ of the PMOS pass element. Dropout voltages at lower currents can be approximated by calculating the effective $R_{DS, ON}$ of the pass element and multiplying that resistance by the load current. $R_{DS, ON}$ of the pass element can be obtained by dividing the dropout voltage by the rated output current.

Output Voltage Programming Guide

V _{OUT}	R1/R3	R2/R4	C1/C2
1.225 V	Short	Open	Open
1.5 V	7.15 kΩ	30.1 kΩ	100 pF
2.5 V	31.6 kΩ	30.1 kΩ	22 pF
3.0 V	43.2 kΩ	30.1 kΩ	15 pF
3.3 V	49.9 kΩ	30.1 kΩ	15 pF
4.75 V	86.6 kΩ	30.1 kΩ	15 pF



SGLS395A - OCTOBER 2008 - REVISED SEPTEMBER 2010

www.ti.com

TRANSIENT RESPONSE

As with any regulator, increasing the size of the output capacitor reduces overshoot/undershoot magnitude but increase duration of the transient response. In the adjustable version, the addition of a capacitor, C_{FB} , from the output to the feedback pin also improves stability and transient response. The transient response of the TPS71202 is enhanced with an active pulldown that engages when the output is overvoltaged. The active pulldown decreases the output recovery time when the load is removed. Figure 13 in the *Typical Characteristics* section shows the output transient response.

SHUTDOWN

Both enable pins are active high and are compatible with standard TTL-CMOS levels. The device is only completely disabled when both EN1 and EN2 are logic low. In this state, the LDO is completely off and the ground pin current drops to approximately 100 nA. With one output disabled, the ground pin current is slightly greater than half the nominal value. When shutdown capability is not required, the enable pins should be connected to the input supply.

INTERNAL CURRENT LIMIT

The TPS71202 internal current limit helps protect the regulator during fault conditions. During current limit, the output sources a fixed amount of current that is largely independent of the output voltage.

The TPS71202 PMOS-pass transistors have a built-in back diode that conducts reverse current when the input voltage drops below the output voltage (that is, during power-down). Current is conducted from the output to the input and is not internally limited. If extended reverse voltage operation is anticipated, external limiting may be appropriate.

THERMAL PROTECTION

Thermal protection disables both outputs when the junction temperature of either channel rises to approximately 160°C, allowing the device to cool. When the junction temperature cools to approximately 140°C, the output circuitry is again

enabled. Depending on power dissipation, thermal resistance, and ambient temperature, the thermal protection circuit may cycle on and off. This limits the dissipation of the regulator, protecting it from damage due to overheating.

Any tendency to activate the thermal protection circuit indicates excessive power dissipation or an inadequate heatsink. For reliable operation, junction temperature should be limited to 125°C maximum. To estimate the margin of safety in a complete design heatsink), increase the (including ambient temperature until the thermal protection is triggered; use worst-case loads and signal conditions. For good reliability, thermal protection should trigger at least 35°C above the maximum expected ambient condition of your application. This produces a worst-case junction temperature of 125°C at the hiahest expected ambient temperature and worst-case load.

The internal protection circuitry of the TPS71202 is designed to protect against overload conditions. It is not intended to replace proper heatsinking. Continuously running the TPS71202 into thermal shutdown degrades device reliability.

POWER DISSIPATION

The ability to remove heat from the die is different for each package type, presenting different considerations in the PCB layout. The PCB area around the device that is free of other components moves the heat from the device to the ambient air. Performance data for a JEDEC high-K board is shown in the *Dissipation Ratings* table. Using heavier copper increases the effectiveness in removing heat from the device. The addition of plated through-holes to heat-dissipating layers also improves the heat-sink effectiveness.

Power dissipation depends on input voltage and load conditions. Power dissipation (P_D) is equal to the product of the output current times the voltage drop across the output pass element (V_{IN} to V_{OUT}):

$$\mathsf{P}_{\mathsf{D}} = (\mathsf{V}_{\mathsf{IN}} - \mathsf{V}_{\mathsf{OUT}}) \times \mathsf{I}_{\mathsf{OUT}} \tag{4}$$

Power dissipation can be minimized by using the lowest possible input voltage necessary to ensure the required output voltage.



10-Dec-2020

PACKAGING INFORMATION

Orderable Device	Status (1)	Package Type	Package Drawing	Pins	Package Qty	Eco Plan (2)	Lead finish/ Ball material (6)	MSL Peak Temp (3)	Op Temp (°C)	Device Marking (4/5)	Samples
TPS71202MDRCTEP	ACTIVE	VSON	DRC	10	250	RoHS & Green	NIPDAU	Level-2-260C-1 YEAR	-55 to 125	CVQ	Samples
V62/08621-01XE	ACTIVE	VSON	DRC	10	250	RoHS & Green	NIPDAU	Level-2-260C-1 YEAR	-55 to 125	CVQ	Samples

⁽¹⁾ The marketing status values are defined as follows:

ACTIVE: Product device recommended for new designs.

LIFEBUY: TI has announced that the device will be discontinued, and a lifetime-buy period is in effect.

NRND: Not recommended for new designs. Device is in production to support existing customers, but TI does not recommend using this part in a new design.

PREVIEW: Device has been announced but is not in production. Samples may or may not be available.

OBSOLETE: TI has discontinued the production of the device.

⁽²⁾ RoHS: TI defines "RoHS" to mean semiconductor products that are compliant with the current EU RoHS requirements for all 10 RoHS substances, including the requirement that RoHS substance do not exceed 0.1% by weight in homogeneous materials. Where designed to be soldered at high temperatures, "RoHS" products are suitable for use in specified lead-free processes. TI may reference these types of products as "Pb-Free".

RoHS Exempt: TI defines "RoHS Exempt" to mean products that contain lead but are compliant with EU RoHS pursuant to a specific EU RoHS exemption.

Green: TI defines "Green" to mean the content of Chlorine (CI) and Bromine (Br) based flame retardants meet JS709B low halogen requirements of <=1000ppm threshold. Antimony trioxide based flame retardants must also meet the <=1000ppm threshold requirement.

⁽³⁾ MSL, Peak Temp. - The Moisture Sensitivity Level rating according to the JEDEC industry standard classifications, and peak solder temperature.

⁽⁴⁾ There may be additional marking, which relates to the logo, the lot trace code information, or the environmental category on the device.

⁽⁵⁾ Multiple Device Markings will be inside parentheses. Only one Device Marking contained in parentheses and separated by a "~" will appear on a device. If a line is indented then it is a continuation of the previous line and the two combined represent the entire Device Marking for that device.

⁽⁶⁾ Lead finish/Ball material - Orderable Devices may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead finish/Ball material values may wrap to two lines if the finish value exceeds the maximum column width.

Important Information and Disclaimer:The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.



PACKAGE OPTION ADDENDUM

10-Dec-2020

PACKAGE MATERIALS INFORMATION

www.ti.com

Texas Instruments

TAPE AND REEL INFORMATION





QUADRANT ASSIGNMENTS FOR PIN 1 ORIENTATION IN TAPE



*All dimensions are nominal	


Device	Package Type	Package Drawing		SPQ	Reel Diameter (mm)	Reel Width W1 (mm)	A0 (mm)	B0 (mm)	K0 (mm)	P1 (mm)	W (mm)	Pin1 Quadrant
TPS71202MDRCTEP	VSON	DRC	10	250	180.0	12.4	3.3	3.3	1.1	8.0	12.0	Q2

TEXAS INSTRUMENTS

www.ti.com

PACKAGE MATERIALS INFORMATION

1-Oct-2014



*All dimensions are nominal

Device	Package Type	Package Drawing	Pins	SPQ	Length (mm)	Width (mm)	Height (mm)
TPS71202MDRCTEP	VSON	DRC	10	250	210.0	185.0	35.0

DRC 10

3 x 3, 0.5 mm pitch

GENERIC PACKAGE VIEW

VSON - 1 mm max height

PLASTIC SMALL OUTLINE - NO LEAD

This image is a representation of the package family, actual package may vary. Refer to the product data sheet for package details.





DRC0010J



PACKAGE OUTLINE

VSON - 1 mm max height

PLASTIC SMALL OUTLINE - NO LEAD



NOTES:

- 1. All linear dimensions are in millimeters. Any dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M. 2. This drawing is subject to change without notice.

3. The package thermal pad must be soldered to the printed circuit board for optimal thermal and mechanical performance.



DRC0010J

EXAMPLE BOARD LAYOUT

VSON - 1 mm max height

PLASTIC SMALL OUTLINE - NO LEAD



NOTES: (continued)

 This package is designed to be soldered to a thermal pad on the board. For more information, see Texas Instruments literature number SLUA271 (www.ti.com/lit/slua271).

5. Vias are optional depending on application, refer to device data sheet. If any vias are implemented, refer to their locations shown on this view. It is recommended that vias under paste be filled, plugged or tented.



DRC0010J

EXAMPLE STENCIL DESIGN

VSON - 1 mm max height

PLASTIC SMALL OUTLINE - NO LEAD



NOTES: (continued)

6. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.



IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATASHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, or other requirements. These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you will fully indemnify TI and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to TI's Terms of Sale (www.ti.com/legal/termsofsale.html) or other applicable terms available either on ti.com or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265 Copyright © 2020, Texas Instruments Incorporated