


# TLV5628C, TLV5628I OCTAL 8-BIT DIGITAL-TO-ANALOG CONVERTERS

SLAS108A – JANUARY 1995 – REVISED NOVEMBER 1995

- Eight 8-Bit Voltage Output DACs
- 3-V Single Supply Operation
- Serial Interface
- High-Impedance Reference Inputs
- Programmable for 1 or 2 Times Output Range
- Simultaneous Update Facility
- Internal Power-On Reset
- Low Power Consumption
- Half-Buffered Output

DW OR N PACKAGE  
(TOP VIEW)



## applications

- Programmable Voltage Sources
- Digitally Controlled Amplifiers/Attenuators
- Mobile Communications
- Automatic Test Equipment
- Process Monitoring and Control
- Signal Synthesis

## description

The TLV5628C and TLV5628I are octal 8-bit voltage output digital-to-analog converters (DACs) with buffered reference inputs (high impedance). The DACs produce an output voltage that varies between one or two times the reference voltages and GND, and the DACs are monotonic. The device is simple to use, running from a single supply of 3 to 3.6 V. A power-on reset function is incorporated to ensure repeatable start-up conditions.

Digital control of the TLV5628C and TLV5628I is over a simple 3-wire serial bus that is CMOS compatible and easily interfaced to all popular microprocessor and microcontroller devices. The 12-bit command word comprises 8 bits of data, 3 DAC select bits and a range bit, the latter allowing selection between the times 1 or times 2 output range. The DAC registers are double buffered, allowing a complete set of new values to be written to the device, then all DAC outputs are updated simultaneously through control of the LDAC terminal. The digital inputs feature Schmitt triggers for high noise immunity.

The 16-terminal small-outline D package allows digital control of analog functions in space-critical applications. The TLV5628C is characterized for operation from 0°C to 70°C. The TLV5628I is characterized for operation from –40°C to 85°C. The TLV5628C and TLV5628I do not require external trimming.

AVAILABLE OPTIONS

| T <sub>A</sub> | PACKAGE            |                 |
|----------------|--------------------|-----------------|
|                | SMALL OUTLINE (DW) | PLASTIC DIP (N) |
| 0°C to 70°C    | TLV5628CDW         | TLV5628CN       |
| –40°C to 85°C  | TLV5628IDW         | TLV5628IN       |



Please be aware that an important notice concerning availability, standard warranty, and use in critical applications of Texas Instruments semiconductor products and disclaimers thereto appears at the end of this data sheet.

PRODUCTION DATA information is current as of publication date. Products conform to specifications per the terms of Texas Instruments standard warranty. Production processing does not necessarily include testing of all parameters.

 **TEXAS  
INSTRUMENTS**

POST OFFICE BOX 655303 • DALLAS, TEXAS 75265


Copyright © 1995, Texas Instruments Incorporated

# TLV5628C, TLV5628I

## OCTAL 8-BIT DIGITAL-TO-ANALOG CONVERTERS

SLAS108A – JANUARY 1995 – REVISED NOVEMBER 1995

### functional block diagram



Terminal Functions

| TERMINAL NAME | NO. | I/O | DESCRIPTION                                              |
|---------------|-----|-----|----------------------------------------------------------|
| CLK           | 5   | I   | Serial-interface clock, data enters on the negative edge |
| DACA          | 2   | O   | DACA analog output                                       |
| DACB          | 1   | O   | DACB analog output                                       |
| DACC          | 16  | O   | DACC analog output                                       |
| DACD          | 15  | O   | DACD analog output                                       |
| DACE          | 7   | O   | DACE analog output                                       |
| DACF          | 8   | O   | DACF analog output                                       |
| DACG          | 9   | O   | DACG analog output                                       |
| DACH          | 10  | O   | DACH analog output                                       |
| DATA          | 4   | I   | Serial-interface digital data input                      |
| GND           | 3   | I   | Ground return and reference terminal                     |
| LDAC          | 13  | I   | DAC-update latch control                                 |
| LOAD          | 12  | I   | Serial-interface load control                            |
| REF1          | 14  | I   | Reference voltage input to DACA                          |
| REF2          | 11  | I   | Reference voltage input to DACB                          |
| VDD           | 6   | I   | Positive supply voltage                                  |

## detailed description

The TLV5628 is implemented using eight resistor-string DACs. The core of each DAC is a single resistor with 256 taps, corresponding to the 256 possible codes listed in Table 1. One end of each resistor string is connected to the GND terminal and the other end is fed from the output of the reference input buffer. Monotonicity is maintained by use of the resistor strings. Linearity depends upon the matching of the resistor elements and upon the performance of the output buffer. Because the inputs are buffered, the DACs always present a high-impedance load to the reference sources. There are two input reference terminals; REF1 is used for DACA through DACD and REF2 is used by DACE through DACH.

Each DAC output is buffered by a configurable-gain output amplifier, which can be programmed to times 1 or times 2 gain.

On power-up, the DACs are reset to CODE 0.

Each output voltage is given by:

$$V_O(\text{DACA}|\text{B}|\text{C}|\text{D}|\text{E}|\text{F}|\text{G}|\text{H}) = \text{REF} \times \frac{\text{CODE}}{256} \times (1 + \text{RNG bit value})$$

where CODE is in the range of 0 to 255 and the range (RNG) bit is a 0 or 1 within the serial-control word.

## data interface

With LOAD high, data is clocked into the DATA terminal on each falling edge of CLK. Once all data bits have been clocked in, LOAD is pulsed low to transfer the data from the serial-input register to the selected DAC as shown in Figure 1. When LDAC is low, the selected DAC output voltage is updated and LOAD goes low. When LDAC is high during serial programming, the new value is stored within the device and can be transferred to the DAC output at a later time by pulsing LDAC low as shown in Figure 2. Data is entered MSB first. Data transfers using two 8 clock cycle periods are shown in Figures 3 and 4.




Figure 1. LOAD-Controlled Update (LDAC = Low)






Figure 2. LDAC-Controlled Update

**TLV5628C, TLV5628I**  
**OCTAL 8-BIT DIGITAL-TO-ANALOG CONVERTERS**

SLAS108A – JANUARY 1995 – REVISED NOVEMBER 1995



**Figure 3. Load Controlled Update Using 8-Bit Serial Word (LDAC = Low)**



**Figure 4. LDAC Controlled Update Using 8-Bit Serial Word**

**data interface (continued)**

Table 2 lists the A2, A1, and A0 bits and the selection of the updated DACs. The RNG bit controls the DAC output range. When RNG = low, the output range is between the applied reference voltage and GND, and when RNG = high, the range is between twice the applied reference voltage and GND.

**Table 1. Ideal Output Transfer**

| D7 | D6 | D5 | D4 | D3 | D2 | D1 | D0 | OUTPUT VOLTAGE                               |
|----|----|----|----|----|----|----|----|----------------------------------------------|
| 0  | 0  | 0  | 0  | 0  | 0  | 0  | 0  | GND                                          |
| 0  | 0  | 0  | 0  | 0  | 0  | 0  | 1  | $(1/256) \times \text{REF} (1+\text{RNG})$   |
| •  | •  | •  | •  | •  | •  | •  | •  | •                                            |
| •  | •  | •  | •  | •  | •  | •  | •  | •                                            |
| 0  | 1  | 1  | 1  | 1  | 1  | 1  | 1  | $(127/256) \times \text{REF} (1+\text{RNG})$ |
| 1  | 0  | 0  | 0  | 0  | 0  | 0  | 0  | $(128/256) \times \text{REF} (1+\text{RNG})$ |
| •  | •  | •  | •  | •  | •  | •  | •  | •                                            |
| •  | •  | •  | •  | •  | •  | •  | •  | •                                            |
| 1  | 1  | 1  | 1  | 1  | 1  | 1  | 1  | $(255/256) \times \text{REF} (1+\text{RNG})$ |

**Table 2. Serial Input Decode**

| A2 | A1 | A0 | DAC UPDATED |
|----|----|----|-------------|
| 0  | 0  | 0  | DACA        |
| 0  | 0  | 1  | DACB        |
| 0  | 1  | 0  | DACC        |
| 0  | 1  | 1  | DACD        |
| 1  | 0  | 0  | DACE        |
| 1  | 0  | 1  | DACF        |
| 1  | 1  | 0  | DACG        |
| 1  | 1  | 1  | DACH        |

# TLV5628C, TLV5628I

## OCTAL 8-BIT DIGITAL-TO-ANALOG CONVERTERS


SLAS108A – JANUARY 1995 – REVISED NOVEMBER 1995

### linearity, offset, and gain error

When an amplifier is operated from a single supply, the voltage offset can still be either positive or negative. With a positive offset, the output voltage changes on the first code change. With a negative offset the output voltage may not change with the first code depending on the magnitude of the offset voltage.

The output amplifier, with a negative voltage offset, attempts to drive the output to a negative voltage. However, since the most negative supply rail is ground, the output cannot drive to a negative voltage.

So when the output offset voltage is negative, the output voltage remains at 0 volts until the input code value produces a sufficient output voltage to overcome the inherent negative offset voltage resulting in the transfer function shown in Figure 5.




**Figure 5. Effect of Negative Offset (Single Supply)**

The negative offset error produces a breakpoint, not a linearity error. The transfer function would follow the dotted line if the output buffer could drive to a negative voltage.

For a DAC, linearity is measured between zero input code (all inputs 0) and full scale code (all inputs 1) after offset and full scale is adjusted out or accounted for in some way. However, single supply operation does not allow for adjustment when the offset is negative due to the breakpoint in the transfer function. The linearity in the unipolar mode is measured between full scale code and the lowest code which produces a positive output voltage.

The code is calculated from the maximum specification for the negative offset.

### equivalent inputs and outputs



# TLV5628C, TLV5628I

## OCTAL 8-BIT DIGITAL-TO-ANALOG CONVERTERS

SLAS108A – JANUARY 1995 – REVISED NOVEMBER 1995

### absolute maximum ratings over operating free-air temperature range (unless otherwise noted)<sup>†</sup>

|                                                              |                                                 |
|--------------------------------------------------------------|-------------------------------------------------|
| Supply voltage ( $V_{DD} - GND$ )                            | 7 V                                             |
| Digital input voltage range, $V_{ID}$                        | $GND - 0.3\text{ V}$ to $V_{DD} + 0.3\text{ V}$ |
| Reference input voltage range                                | $GND - 0.3\text{ V}$ to $V_{DD} + 0.3\text{ V}$ |
| Operating free-air temperature range, $T_A$ : TLV5628C       | 0°C to 70°C                                     |
| TLV5628I                                                     | –40°C to 85°C                                   |
| Storage temperature range, $T_{stg}$                         | –50°C to 150°C                                  |
| Lead temperature 1,6 mm (1/16 inch) from case for 10 seconds | 230°C                                           |

<sup>†</sup> Stresses beyond those listed under “absolute maximum ratings” may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated under “recommended operating conditions” is not implied. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability.

### recommended operating conditions

|                                                                                          |          | MIN                  | NOM | MAX  | UNIT |
|------------------------------------------------------------------------------------------|----------|----------------------|-----|------|------|
| Supply voltage, V <sub>DD</sub>                                                          |          | 2.7                  | 3.3 | 5.25 | V    |
| High-level digital input voltage, V <sub>IH</sub>                                        |          | 0.8 V <sub>DD</sub>  |     |      | V    |
| Low-level digital input voltage, V <sub>IL</sub>                                         |          | 0.8                  |     |      | V    |
| Reference voltage, V <sub>ref</sub> [A B C D E F G H], X1 gain                           |          | V <sub>DD</sub> –1.5 |     |      | V    |
| Load resistance, R <sub>L</sub>                                                          |          | 10                   |     |      | kΩ   |
| Setup time, data input, t <sub>su</sub> (DATA-CLK) (see Figures 1 and 2)                 |          | 50                   |     |      | ns   |
| Valid time, data input valid after CLK↓, t <sub>v</sub> (DATA-CLK) (see Figures 1 and 2) |          | 50                   |     |      | ns   |
| Setup time, CLK eleventh falling edge to LOAD, t <sub>su</sub> (CLK-LOAD) (see Figure 1) |          | 50                   |     |      | ns   |
| Setup time, LOAD↑ to CLK↓, t <sub>su</sub> (LOAD-CLK) (see Figure 1)                     |          | 50                   |     |      | ns   |
| Pulse duration, LOAD, t <sub>w</sub> (LOAD) (see Figure 1)                               |          | 250                  |     |      | ns   |
| Pulse duration, LDAC, t <sub>w</sub> (LDAC) (see Figure 2)                               |          | 250                  |     |      | ns   |
| Setup time, LOAD↑ to LDAC↓, t <sub>su</sub> (LOAD-LDAC) (see Figure 2)                   |          | 0                    |     |      | ns   |
| CLK frequency                                                                            |          | 1                    |     |      | MHz  |
| Operating free-air temperature, T <sub>A</sub>                                           | TLV5628C | 0                    |     | 70   | °C   |
|                                                                                          | TLV5628I | –40                  |     | 85   | °C   |



# TLV5628C, TLV5628I

## OCTAL 8-BIT DIGITAL-TO-ANALOG CONVERTERS

SLAS108A – JANUARY 1995 – REVISED NOVEMBER 1995

**electrical characteristics over recommended operating free-air temperature range,  
V<sub>DD</sub> = 3 V to 3.6 V, V<sub>ref</sub> = 2 V, × 1 gain output range (unless otherwise noted)**

| PARAMETER              |                                          | TEST CONDITIONS                                   | MIN | TYP | MAX  | UNIT  |
|------------------------|------------------------------------------|---------------------------------------------------|-----|-----|------|-------|
| I <sub>IH</sub>        | High-level digital input current         | V <sub>I</sub> = V <sub>DD</sub>                  |     |     | ±10  | μA    |
| I <sub>IL</sub>        | Low-level digital input current          | V <sub>I</sub> = 0 V                              |     |     | ±10  | μA    |
| I <sub>O(sink)</sub>   | Output sink current                      | Each DAC output                                   | 20  |     |      | μA    |
| I <sub>O(source)</sub> | Output source current                    |                                                   | 1   |     |      | mA    |
| C <sub>i</sub>         | Input capacitance                        |                                                   |     | 15  |      | pF    |
|                        | Reference input capacitance              |                                                   |     | 15  |      |       |
| I <sub>DD</sub>        | Supply current                           | V <sub>DD</sub> = 3.3 V                           |     |     | 4    | mA    |
| I <sub>ref</sub>       | Reference input current                  | V <sub>DD</sub> = 3.3 V, V <sub>ref</sub> = 1.5 V |     |     | ±10  | μA    |
| E <sub>L</sub>         | Linearity error (end point corrected)    | V <sub>ref</sub> = 1.25 V, × 2 gain (see Note 1)  |     |     | ±1   | LSB   |
| E <sub>D</sub>         | Differential linearity error             | V <sub>ref</sub> = 1.25 V, × 2 gain (see Note 2)  |     |     | ±0.9 | LSB   |
| E <sub>ZS</sub>        | Zero-scale error                         | V <sub>ref</sub> = 1.25 V, × 2 gain (see Note 3)  | 0   |     | 30   | mV    |
|                        | Zero-scale error temperature coefficient | V <sub>ref</sub> = 1.25 V, × 2 gain (see Note 4)  |     | 10  |      | μV/°C |
| E <sub>FS</sub>        | Full-scale error                         | V <sub>ref</sub> = 1.25 V, × 2 gain (see Note 5)  |     |     | ±60  | mV    |
|                        | Full-scale error temperature coefficient | V <sub>ref</sub> = 1.25 V, × 2 gain (see Note 6)  |     | ±25 |      | μV/°C |
| PSRR                   | Power supply sensitivity                 | See Notes 7 and 8                                 |     | 0.5 |      | mV/V  |

- NOTES: 1. Integral nonlinearity (INL) is the maximum deviation of the output from the line between zero-scale and full scale (excluding the effects of zero code and full-scale errors).
2. Differential nonlinearity (DNL) is the difference between the measured and ideal 1 LSB amplitude change of any two adjacent codes. Monotonic means the output voltage changes in the same direction (or remains constant) as a change in the digital input code.
3. Zero-scale error is the deviation from zero voltage output when the digital input code is zero.
4. Zero-scale error temperature coefficient is given by: ZSETC = [ZSE(T<sub>max</sub>) – ZSE(T<sub>min</sub>)]/V<sub>ref</sub> × 10<sup>6</sup>/(T<sub>max</sub> – T<sub>min</sub>).
5. Full-scale error is the deviation from the ideal full-scale output (V<sub>ref</sub> – 1 LSB) with an output load of 10 kΩ.
6. Full-scale temperature coefficient is given by: FSETC = [FSE(T<sub>max</sub>) – FSE(T<sub>min</sub>)]/V<sub>ref</sub> × 10<sup>6</sup>/(T<sub>max</sub> – T<sub>min</sub>).
7. Zero-scale error rejection ratio (ZSE-RR) is measured by varying the V<sub>DD</sub> voltage from 4.5 V to 5.5 V dc and measuring the effect of this signal on the zero-code output voltage.
8. Full-scale error rejection ratio (FSE-RR) is measured by varying the V<sub>DD</sub> voltage from 3 V to 3.6 V dc and measuring the effect of this signal on the full-scale output voltage.

**operating characteristics over recommended operating free-air temperature range,  
V<sub>DD</sub> = 3 V to 3.6 V, V<sub>ref</sub> = 2 V, × 1 gain output range (unless otherwise noted)**

|                              | TEST CONDITIONS                                                         | MIN | TYP | MAX | UNIT |
|------------------------------|-------------------------------------------------------------------------|-----|-----|-----|------|
| Output slew rate             | C <sub>L</sub> = 100 pF, R <sub>L</sub> = 10 kΩ                         |     | 1   |     | V/μs |
| Output settling time         | To 0.5 LSB, C <sub>L</sub> = 100 pF, R <sub>L</sub> = 10 kΩ, See Note 9 |     | 10  |     | μs   |
| Large-signal bandwidth       | Measured at –3 dB point                                                 |     | 100 |     | kHz  |
| Digital crosstalk            | CLK = 1-MHz square wave measured at DACA-DACH                           |     | –50 |     | dB   |
| Reference feedthrough        | See Note 10                                                             |     | –60 |     | dB   |
| Channel-to-channel isolation | See Note 11                                                             |     | –60 |     | dB   |
| Reference input bandwidth    | See Note 12                                                             |     | 100 |     | kHz  |

- NOTES: 9. Settling time is the time for the output signal to remain within ±0.5 LSB of the final measured value for a digital input code change of 00 hex to FF hex or FF hex to 00 hex. For TLC5628C V<sub>DD</sub> = 5 V, V<sub>ref</sub> = 2 V and range = ×2. For TLC5628I V<sub>DD</sub> = 3 V, V<sub>ref</sub> = 1.25 V and range ×2.
10. Reference feedthrough is measured at any DAC output with an input code = 00 hex with a V<sub>ref</sub> input = 1 V dc + 1 V<sub>pp</sub> at 10 kHz.
11. Channel-to-channel isolation is measured by setting the input code of one DAC to FF hex and the code of all other DACs to 00 hex with V<sub>ref</sub> input = 1 V dc + 1 V<sub>pp</sub> at 10 kHz.
12. Reference bandwidth is a –3 dB bandwidth with an input at V<sub>ref</sub> = 1.25 V dc + 2 V<sub>pp</sub> and with a full-scale digital input code.



## PARAMETER MEASUREMENT INFORMATION





Figure 6. Slewing Settling Time and Linearity Measurements

## TYPICAL CHARACTERISTICS


POSITIVE RISE TIME AND SETTTLING TIME



NOTE A: Rise time = 2.05  $\mu$ s, positive slew rate = 0.96 V/ $\mu$ s, settling time = 4.5  $\mu$ s.

Figure 7

NEGATIVE FALL TIME AND SETTTLING TIME



NOTE B: Fall time = 4.25  $\mu$ s, negative slew rate = 0.46 V/ $\mu$ s, settling time = 8.5  $\mu$ s.

Figure 8

TLV5628C, TLV5628I  
OCTAL 8-BIT DIGITAL-TO-ANALOG CONVERTERS

SLAS108A – JANUARY 1995 – REVISED NOVEMBER 1995

TYPICAL CHARACTERISTICS




Figure 9




Figure 10





Figure 11

## APPLICATION INFORMATION



NOTE A: Resistor R  $\geq$  10 k $\Omega$

**Figure 12. Output Buffering Scheme**

# TLV5628C, TLV5628I

## OCTAL 8-BIT DIGITAL-TO-ANALOG CONVERTERS


SLAS108A – JANUARY 1995 – REVISED NOVEMBER 1995

### MECHANICAL DATA

DW (R-PDSO-G\*\*)

PLASTIC SMALL-OUTLINE PACKAGE

16 PIN SHOWN



- NOTES:
- All linear dimensions are in inches (millimeters).
  - This drawing is subject to change without notice.
  - Body dimensions do not include mold flash or protrusion not to exceed 0.006 (0,15).
  - Falls within JEDEC MS-013

# TLV5628C, TLV5628I

## OCTAL 8-BIT DIGITAL-TO-ANALOG CONVERTERS


SLAS108A – JANUARY 1995 – REVISED NOVEMBER 1995

### MECHANICAL DATA

N (R-PDIP-T\*\*)

PLASTIC DUAL-IN-LINE PACKAGE

16 PIN SHOWN



- NOTES: A. All linear dimensions are in inches (millimeters).  
 B. This drawing is subject to change without notice.  
 C. Falls within JEDEC MS-001 (20-pin package is shorter than MS-001)

## PACKAGING INFORMATION

| Orderable part number       | Status<br>(1) | Material type<br>(2) | Package   Pins | Package qty   Carrier | RoHS<br>(3) | Lead finish/<br>Ball material<br>(4) | MSL rating/<br>Peak reflow<br>(5) | Op temp (°C)    | Part marking<br>(6) |
|-----------------------------|---------------|----------------------|----------------|-----------------------|-------------|--------------------------------------|-----------------------------------|-----------------|---------------------|
| <a href="#">TLV5628CDW</a>  | Active        | Production           | SOIC (DW)   16 | 40   TUBE             | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | 0 to 70         | TLV5628C            |
| TLV5628CDW.A                | Active        | Production           | SOIC (DW)   16 | 40   TUBE             | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | 0 to 70         | TLV5628C            |
| <a href="#">TLV5628CDWR</a> | Active        | Production           | SOIC (DW)   16 | 2000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -               | TLV5628C            |
| TLV5628CDWR.A               | Active        | Production           | SOIC (DW)   16 | 2000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 85       | TLV5628C            |
| <a href="#">TLV5628CN</a>   | Active        | Production           | PDIP (N)   16  | 25   TUBE             | Yes         | NIPDAU                               | N/A for Pkg Type                  | -               | TLV5628CN           |
| TLV5628CN.A                 | Active        | Production           | PDIP (N)   16  | 25   TUBE             | Yes         | NIPDAU                               | N/A for Pkg Type                  | -40 to 85       | TLV5628CN           |
| <a href="#">TLV5628IDW</a>  | Active        | Production           | SOIC (DW)   16 | 40   TUBE             | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 85       | TLV5628I            |
| TLV5628IDW.A                | Active        | Production           | SOIC (DW)   16 | 40   TUBE             | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 85       | TLV5628I            |
| TLV5628IDWG4                | Active        | Production           | SOIC (DW)   16 | 40   TUBE             | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 85       | TLV5628I            |
| <a href="#">TLV5628IDWR</a> | Active        | Production           | SOIC (DW)   16 | 2000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -               | TLV5628I            |
| TLV5628IDWR.A               | Active        | Production           | SOIC (DW)   16 | 2000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 85       | TLV5628I            |
| TLV5628IDWRG4               | Active        | Production           | SOIC (DW)   16 | 2000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | See TLV5628IDWR | TLV5628I            |
| <a href="#">TLV5628IN</a>   | Active        | Production           | PDIP (N)   16  | 25   TUBE             | Yes         | NIPDAU                               | N/A for Pkg Type                  | -               | TLV5628IN           |
| TLV5628IN.A                 | Active        | Production           | PDIP (N)   16  | 25   TUBE             | Yes         | NIPDAU                               | N/A for Pkg Type                  | -40 to 85       | TLV5628IN           |

<sup>(1)</sup> **Status:** For more details on status, see our [product life cycle](#).

<sup>(2)</sup> **Material type:** When designated, preproduction parts are prototypes/experimental devices, and are not yet approved or released for full production. Testing and final process, including without limitation quality assurance, reliability performance testing, and/or process qualification, may not yet be complete, and this item is subject to further changes or possible discontinuation. If available for ordering, purchases will be subject to an additional waiver at checkout, and are intended for early internal evaluation purposes only. These items are sold without warranties of any kind.

<sup>(3)</sup> **RoHS values:** Yes, No, RoHS Exempt. See the [TI RoHS Statement](#) for additional information and value definition.

<sup>(4)</sup> **Lead finish/Ball material:** Parts may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead finish/Ball material values may wrap to two lines if the finish value exceeds the maximum column width.

<sup>(5)</sup> **MSL rating/Peak reflow:** The moisture sensitivity level ratings and peak solder (reflow) temperatures. In the event that a part has multiple moisture sensitivity ratings, only the lowest level per JEDEC standards is shown. Refer to the shipping label for the actual reflow temperature that will be used to mount the part to the printed circuit board.

<sup>(6)</sup> **Part marking:** There may be an additional marking, which relates to the logo, the lot trace code information, or the environmental category of the part.

Multiple part markings will be inside parentheses. Only one part marking contained in parentheses and separated by a "~" will appear on a part. If a line is indented then it is a continuation of the previous line and the two combined represent the entire part marking for that device.

**Important Information and Disclaimer:** The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.

## TAPE AND REEL INFORMATION



\*All dimensions are nominal

| Device      | Package Type | Package Drawing | Pins | SPQ  | Reel Diameter (mm) | Reel Width W1 (mm) | A0 (mm) | B0 (mm) | K0 (mm) | P1 (mm) | W (mm) | Pin1 Quadrant |
|-------------|--------------|-----------------|------|------|--------------------|--------------------|---------|---------|---------|---------|--------|---------------|
| TLV5628CDWR | SOIC         | DW              | 16   | 2000 | 330.0              | 16.4               | 10.75   | 10.7    | 2.7     | 12.0    | 16.0   | Q1            |
| TLV5628IDWR | SOIC         | DW              | 16   | 2000 | 330.0              | 16.4               | 10.75   | 10.7    | 2.7     | 12.0    | 16.0   | Q1            |

## TAPE AND REEL BOX DIMENSIONS



\*All dimensions are nominal

| Device      | Package Type | Package Drawing | Pins | SPQ  | Length (mm) | Width (mm) | Height (mm) |
|-------------|--------------|-----------------|------|------|-------------|------------|-------------|
| TLV5628CDWR | SOIC         | DW              | 16   | 2000 | 350.0       | 350.0      | 43.0        |
| TLV5628IDWR | SOIC         | DW              | 16   | 2000 | 350.0       | 350.0      | 43.0        |

## TUBE



\*All dimensions are nominal

| Device       | Package Name | Package Type | Pins | SPQ | L (mm) | W (mm) | T (μm) | B (mm) |
|--------------|--------------|--------------|------|-----|--------|--------|--------|--------|
| TLV5628CDW   | DW           | SOIC         | 16   | 40  | 506.98 | 12.7   | 4826   | 6.6    |
| TLV5628CDW.A | DW           | SOIC         | 16   | 40  | 506.98 | 12.7   | 4826   | 6.6    |
| TLV5628CN    | N            | PDIP         | 16   | 25  | 506    | 13.97  | 11230  | 4.32   |
| TLV5628CN.A  | N            | PDIP         | 16   | 25  | 506    | 13.97  | 11230  | 4.32   |
| TLV5628IDW   | DW           | SOIC         | 16   | 40  | 506.98 | 12.7   | 4826   | 6.6    |
| TLV5628IDW.A | DW           | SOIC         | 16   | 40  | 506.98 | 12.7   | 4826   | 6.6    |
| TLV5628IDWG4 | DW           | SOIC         | 16   | 40  | 506.98 | 12.7   | 4826   | 6.6    |
| TLV5628IN    | N            | PDIP         | 16   | 25  | 506    | 13.97  | 11230  | 4.32   |
| TLV5628IN.A  | N            | PDIP         | 16   | 25  | 506    | 13.97  | 11230  | 4.32   |

## IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATASHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, regulatory or other requirements.

These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you fully indemnify TI and its representatives against any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to [TI's Terms of Sale](#), [TI's General Quality Guidelines](#), or other applicable terms available either on [ti.com](#) or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products. Unless TI explicitly designates a product as custom or customer-specified, TI products are standard, catalog, general purpose devices.

TI objects to and rejects any additional or different terms you may propose.

Copyright © 2026, Texas Instruments Incorporated

Last updated 10/2025