

# TRS213 5V Multichannel RS-232 Line Driver and Receiver with $\pm 15\text{kV}$ ESD Protection

## 1 Features

- ESD Protection for RS-232 bus pins
  - $\pm 15\text{kV}$  Human-body model (HBM)
- Meets or exceeds the requirements of TIA/EIA-232-F and ITU v.28 standards
- Operates at 5V  $V_{CC}$  supply
- Four drivers and five receivers
- Operates up to 120kbit/s
- Low supply current in shutdown mode: 15 $\mu\text{A}$  typical
- External Capacitors: 4  $\times$  0.1 $\mu\text{F}$
- Designed to be interchangeable with industry standard '213 devices
- Latch-up performance exceeds 100mA per JESD 78, class II

## 2 Applications

- [Battery-powered systems](#)
- [PDAs](#)
- [Notebooks](#)
- [Laptops](#)
- [Palmtop PCs](#)
- [Hand-held equipment](#)

## 3 Description

The TRS213 device consists of four line drivers, five line receivers, and a dual charge-pump circuit with  $\pm 15\text{kV}$  ESD protection pin to pin (serial-port connection pins, including GND). The device meets the requirements of TIA/EIA-232-F and provides the electrical interface between an asynchronous communication controller and the serial-port connector. The charge pump and four small external capacitors allow operation from a single 5V supply. The devices operate at data signaling rates up to 120kbit/s and a maximum of 30V/ $\mu\text{s}$  driver output slew rate.


The TRS213 has an active-low shutdown ( $\overline{\text{SHDN}}$ ) and an active-high enable control (EN). In shutdown mode, the charge pumps are turned off,  $V+$  is pulled down to  $V_{CC}$ ,  $V-$  is pulled to GND, and the transmitter outputs are disabled. This reduces supply current typically to 1 $\mu\text{A}$ . Two receivers of the TRS213 are active during shutdown.

### Package Information

PART NUMBER	PACKAGE <sup>(1)</sup>	PACKAGE SIZE <sup>(2)</sup>
TRS213	DB (SSOP)	10.2 mm x 7.8mm
	DW (SOIC)	17.9mm x 10.3mm

(1) For more information, see [Section 11](#).

(2) The package size (length  $\times$  width) is a nominal value and includes pins, where applicable.




Logic Diagram (Positive Logic)



## Table of Contents

<b>1 Features</b> .....	1	5.10 ESD Protection, Receiver.....	8
<b>2 Applications</b> .....	1	<b>6 Parameter Measurement Information</b> .....	9
<b>3 Description</b> .....	1	<b>7 Functional Modes</b> .....	11
<b>4 Pin Configuration and Functions</b> .....	3	<b>8 Application and Implementation</b> .....	12
<b>5 Specifications</b> .....	5	8.1 Typical Application.....	12
5.1 Absolute Maximum Ratings.....	5	<b>9 Device and Documentation Support</b> .....	13
5.2 Recommended Operating Conditions.....	5	9.1 Receiving Notification of Documentation Updates... 13	
5.3 Thermal Information.....	5	9.2 Support Resources.....	13
5.4 Electrical Characteristics.....	7	9.3 Trademarks.....	13
5.5 Electrical Characteristics, Driver.....	7	9.4 Electrostatic Discharge Caution.....	13
5.6 Switching Characteristics, Driver.....	7	9.5 Glossary.....	13
5.7 ESD Protection, Driver.....	7	<b>10 Revision History</b> .....	13
5.8 Electrical Characteristics, Receiver.....	8	<b>11 Mechanical, Packaging, and Orderable Information</b> .....	13
5.9 Switching Characteristics, Receiver.....	8		

## 4 Pin Configuration and Functions



**Table 4-1. Pin Functions**

PIN		TYPE <sup>(1)</sup>	DESCRIPTION
NAME	NO.		
DOUT3	1	O	RS-232 driver outputs
DOUT1	2	O	RS-232 driver outputs
DOUT2	3	O	RS-232 driver outputs
RIN2	4	I	RS-232 receiver input
ROUT2	5	O	Receiver output
DIN2	6	I	Driver inputs
DIN1	7	I	Driver inputs
ROUT1	8	O	Receiver output
RIN1	9	I	RS-232 receiver input
GND	10	-	Ground
V <sub>CC</sub>	11	-	Supply voltage
C1+	12	-	Positive terminal of the voltage-doubler charge-pump capacitor
V+	13	-	Positive charge pump output voltage
C1-	14	-	Negative terminal of the voltage-doubler charge-pump capacitor
C2+	15	-	Positive terminal of the voltage-doubler charge-pump capacitor
C2-	16	-	Negative terminal of the voltage-doubler charge-pump capacitor
V-	17	-	Negative charge pump output voltage
RIN5	18	I	RS-232 receiver input
ROUT5	19	O	Receiver output
DIN3	20	I	Driver inputs
DIN4	21	I	Driver inputs
ROUT4	22	O	Receiver output
RIN4	23	I	RS-232 receiver input

**Table 4-1. Pin Functions (continued)**

PIN		TYPE <sup>(1)</sup>	DESCRIPTION
NAME	NO.		
EN	24	I	Active high enable
SHDN	25	I	Active low shutdown
ROUT3	26	O	Receiver output
RIN3	27	I	RS-232 receiver input
DOUT4	28	O	RS-232 driver outputs

(1) Signal Types: I = Input, O = Output, I/O = Input or Output.

## 5 Specifications

### 5.1 Absolute Maximum Ratings

over operating free-air temperature range (unless otherwise noted) <sup>(1)</sup>

		MIN	MAX	UNIT	
V <sub>CC</sub>	Supply voltage range	-0.3	6	V	
V+	Positive charge-pump voltage range <sup>(2)</sup>	V <sub>CC</sub> - 0.3	14	V	
V-	Negative charge-pump voltage range <sup>(2)</sup>	0.3	-14	V	
V <sub>I</sub>	Input voltage range	Drivers	V+ + 0.3	V	
		Receivers (DB Package)	±25		
		Receivers (DW Package)	±30	V	
V <sub>O</sub>	Output voltage range	Drivers	V- - 0.3	V+ + 0.3	V
		Receivers	-0.3	V <sub>CC</sub> + 0.3	
DOUT	Short-circuit duration	Continuous			
T <sub>J</sub>	Operating virtual junction temperature	150		°C	
T <sub>stg</sub>	Storage temperature range	-65	150	°C	

- (1) Stresses beyond those listed under "absolute maximum ratings" may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated under "recommended operating conditions" is not implied. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability.
- (2) All voltages are with respect to network GND.

### 5.2 Recommended Operating Conditions

See [Figure 6-4](#), and note <sup>(1)</sup>

			MIN	NOM	MAX	UNIT
Supply voltage			4.5	5	5.5	V
V <sub>IH</sub>	Driver high-level input voltage	DIN	2		V	
	Control high-level input voltage	EN, $\overline{\text{SHDN}}$	2.4			
V <sub>IL</sub>	Driver and control low-level input voltage	DIN, EN, $\overline{\text{SHDN}}$	0.8		V	
V <sub>I</sub>	Driver and control input voltage	DIN, EN, $\overline{\text{SHDN}}$	0	5.5		V
	Receiver input voltage	RIN (DB package)	-25	25		
		RIN (DW package)	-30	30		V
T <sub>A</sub>	Operating free-air temperature	TRS213C	0	70		°C
		TRS213I	-40	85		

- (1) Test conditions are C1-C4 = 0.1µF at V<sub>CC</sub> = 5V ± 0.5V.

### 5.3 Thermal Information

THERMAL METRIC <sup>(1)</sup>		DW (SOIC)	DB (SSOP)	UNIT
		28 PINS	28 PINS	
R <sub>θJA</sub>	Junction-to-ambient thermal resistance	72.3	66.1	°C/W
R <sub>θJC(top)</sub>	Junction-to-case (top) thermal resistance	33.5	33.2	°C/W
R <sub>θJB</sub>	Junction-to-board thermal resistance	37.1	37.0	°C/W
ψ <sub>JT</sub>	Junction-to-top characterization parameter	7.5	4.6	°C/W

### 5.3 Thermal Information (continued)

THERMAL METRIC <sup>(1)</sup>	DW (SOIC)	DB (SSOP)	UNIT
	28 PINS	28 PINS	
$\Psi_{JB}$ Junction-to-board characterization parameter	37.1	36.5	°C/W

- (1) For more information about traditional and new thermal metrics, see the *Semiconductor and IC Package Thermal Metrics* application report, [SPRA953](#).

## 5.4 Electrical Characteristics

over operating free-air temperature range (unless otherwise noted) <sup>(1)</sup>

PARAMETER		TEST CONDITIONS		MIN	TYP <sup>(2)</sup>	MAX	UNIT
I <sub>CC</sub>	Supply current	No load,	See <a href="#">Figure 8-1</a>		14	20	mA
I <sub>SHDN</sub>	Shutdown supply current	T <sub>A</sub> = 25°C,	See <a href="#">Figure 6-1</a>		15	50	μA

- (1) Test conditions are C1–C4 = 0.1μF at V<sub>CC</sub> = 5V ± 0.5V.  
(2) All typical values are at V<sub>CC</sub> = 5V, and T<sub>A</sub> = 25°C.

## 5.5 Electrical Characteristics, Driver

over operating free-air temperature range (unless otherwise noted) (see [Figure 6-4](#), and note <sup>(3)</sup>)

PARAMETER		TEST CONDITIONS		MIN	TYP <sup>(1)</sup>	MAX	UNIT
V <sub>OH</sub>	High-level output voltage	DOUT at R <sub>L</sub> = 3 kΩ to GND		5	9		V
V <sub>OL</sub>	Low-level output voltage	DOUT at R <sub>L</sub> = 3 kΩ to GND		–5	–9		V
I <sub>IH</sub>	Control high-level input current	EN, SHDN = 5V			3	10	μA
I <sub>IL</sub>	Driver low-level input current	DIN = 0V			–15	–200	μA
	Control low-level input current	EN, SHDN = 0V			–3	–10	
I <sub>OS</sub> <sup>(2)</sup>	Short-circuit output current	V <sub>CC</sub> = 5.5V,	V <sub>O</sub> = 0V		±10	±60	mA
r <sub>o</sub>	Output resistance	V <sub>CC</sub> , V+, and V– = 0V,	V <sub>O</sub> = ±2V	300			Ω

- (1) All typical values are at V<sub>CC</sub> = 5V, and T<sub>A</sub> = 25°C.  
(2) Short-circuit durations should be controlled to prevent exceeding the device absolute power dissipation ratings, and not more than one output should be shorted at a time.  
(3) Test conditions are C1–C4 = 0.1μF at V<sub>CC</sub> = 5V ± 0.5V

## 5.6 Switching Characteristics, Driver

over operating free-air temperature range (unless otherwise noted) <sup>(1)</sup>

PARAMETER		TEST CONDITIONS		MIN	TYP <sup>(2)</sup>	MAX	UNIT
	Maximum data rate	C <sub>L</sub> = 50pF to 1000pF, One DO <sub>UT</sub> switching,	R <sub>L</sub> = 3kΩ to 7kΩ, See <a href="#">Figure 6-3</a>	120			kbit/s
t <sub>PLH(D)</sub>	Propagation delay time, low- to high-level output	C <sub>L</sub> = 2500pF, All drivers loaded,	R <sub>L</sub> = 3kΩ, See <a href="#">Figure 6-3</a>		2		μs
t <sub>PHL(D)</sub>	Propagation delay time, high- to low-level output	C <sub>L</sub> = 2500pF, All drivers loaded,	R <sub>L</sub> = 3kΩ, See <a href="#">Figure 6-3</a>		2		μs
t <sub>sk(p)</sub>	Pulse skew <sup>(3)</sup>	C <sub>L</sub> = 150pF to 2500pF, See <a href="#">Figure 6-3</a>	R <sub>L</sub> = 3kΩ to 7kΩ,		300		ns
SR(tr)	Slew rate, transition region (see <a href="#">Figure 6-2</a> )	C <sub>L</sub> = 50pF to 1000pF, V <sub>CC</sub> = 5V	R <sub>L</sub> = 3kΩ to 7kΩ,	3	6	30	V/μs

- (1) Test conditions are C1–C4 = 0.1μF at V<sub>CC</sub> = 5V ± 0.5V.  
(2) All typical values are at V<sub>CC</sub> = 5V, and T<sub>A</sub> = 25°C.  
(3) Pulse skew is defined as (t<sub>PLH</sub> – t<sub>PHL</sub>) of each channel of the same device.

## 5.7 ESD Protection, Driver

over operating free-air temperature range (unless otherwise noted)

PIN	TEST CONDITIONS	TYP	UNIT
DO <sub>UT</sub>	Human-Body Model	±15	kV

### 5.8 Electrical Characteristics, Receiver

over operating free-air temperature range (unless otherwise noted) (see Figure 8-1), and see note<sup>(3)</sup>

PARAMETER		TEST CONDITIONS		MIN	TYP <sup>(1)</sup>	MAX	UNIT
V <sub>OH</sub>	High-level output voltage	I <sub>OH</sub> = -1mA		V <sub>CC</sub> - 0.4			V
V <sub>OL</sub>	Low-level output voltage	I <sub>OH</sub> = 1.6mA				0.4	V
V <sub>IT+</sub>	Positive-going input threshold voltage	V <sub>CC</sub> = 5V, T <sub>A</sub> = 25°C	Active mode		1.7	2.4	V
			Shutdown mode (R4-R5)		1.5	2.4	
V <sub>IT-</sub>	Negative-going input threshold voltage	V <sub>CC</sub> = 5V, T <sub>A</sub> = 25°C	Active mode	0.8	1.2		V
			Shutdown mode (R4-R5)	0.6	1.5		
V <sub>hys</sub> <sup>(2)</sup>	Input hysteresis (V <sub>IT+</sub> , V <sub>IT-</sub> )	V <sub>CC</sub> = 5V			0.5	1	V
r <sub>I</sub>	Input resistance	V <sub>CC</sub> = 5V, T <sub>A</sub> = 25°C		3	5	7	kΩ
	Output leakage current	EN = 0V, 0 ≤ ROUT ≤ V <sub>CC</sub> , R1-R3			±0.05	±10	μA

(1) All typical values are at V<sub>CC</sub> = 5V, and T<sub>A</sub> = 25°C.

(2) No hysteresis in shutdown mode

(3) Test conditions are C1-C4 = 0.1μF at V<sub>CC</sub> = 5V ± 0.5 V.

### 5.9 Switching Characteristics, Receiver

over operating free-air temperature range (unless otherwise noted) <sup>(1)</sup>

PARAMETER		TEST CONDITIONS		MIN	TYP <sup>(2)</sup>	MAX	UNIT
t <sub>PLH(R)</sub>	Propagation delay time, low- to high-level output	C <sub>L</sub> = 150pF, See Figure 6-4	SHDN = V <sub>CC</sub>		0.5	10	μs
			SHDN = 0V, R4-R5		4	40	
t <sub>PHL(R)</sub>	Propagation delay time, high- to low-level output	C <sub>L</sub> = 150pF, See Figure 6-4			0.5	10	μs
t <sub>en</sub>	Output enable time	C <sub>L</sub> = 150pF, See Figure 6-5			600		ns
t <sub>dis</sub>	Output disable time	C <sub>L</sub> = 150pF, See Figure 6-5			200		ns

(1) Test conditions are C1-C4 = 0.1μF at V<sub>CC</sub> = 5V ± 0.5V.

(2) All typical values are at V<sub>CC</sub> = 5V, and T<sub>A</sub> = 25°C.


### 5.10 ESD Protection, Receiver

over operating free-air temperature range (unless otherwise noted)


PIN	TEST CONDITIONS	TYP	UNIT
RIN	Human-Body Model	±15	kV



## 6 Parameter Measurement Information




**Figure 6-1. Shutdown Current Test Circuit**



TEST CIRCUIT


$$SR(tr) = \frac{6\text{ V}}{t_{THL(D)} \text{ or } t_{TLH(D)}}$$




VOLTAGE WAVEFORMS

- NOTES: A.  $C_L$  includes probe and jig capacitance.  
 B. The pulse generator has the following characteristics:  $Z_O = 50\ \Omega$ , 50% duty cycle,  $t_r \leq 10\text{ ns}$ ,  $t_f \leq 10\text{ ns}$ .

Figure 6-2. Driver Slew Rate




TEST CIRCUIT




VOLTAGE WAVEFORMS

- NOTES: A.  $C_L$  includes probe and jig capacitance.  
 B. The pulse generator has the following characteristics:  $Z_O = 50\ \Omega$ , 50% duty cycle,  $t_r \leq 10\text{ ns}$ ,  $t_f \leq 10\text{ ns}$ .

Figure 6-3. Driver Pulse Skew and Propagation Delay Times




TEST CIRCUIT



VOLTAGE WAVEFORMS

- NOTES: A.  $C_L$  includes probe and jig capacitance.  
 B. The pulse generator has the following characteristics:  $Z_O = 50\ \Omega$ , 50% duty cycle,  $t_r \leq 10\text{ ns}$ ,  $t_f \leq 10\text{ ns}$ .

Figure 6-4. Receiver Propagation Delay Times



- NOTES:
- A.  $C_L$  includes probe and jig capacitance.
  - B. The pulse generator has the following characteristics:  $Z_0 = 50\ \Omega$ , 50% duty cycle,  $t_r \leq 10\ \text{ns}$ ,  $t_f \leq 10\ \text{ns}$ .
  - C.  $t_{PLZ}$  and  $t_{PHZ}$  are the same as  $t_{dis}$ .
  - D.  $t_{PZL}$  and  $t_{PZH}$  are the same as  $t_{en}$ .

Figure 6-5. Receiver Enable and Disable Times

## 7 Functional Modes

Table 7-1. Function Table

INPUTS		DRIVER D1–D4	RECEIVER		DEVICE STATUS
SHDN	EN		R1–R3	R4–R5	
L	L	Z	Z	Z	Shutdown
L	H	Z	Z	Active <sup>(1)</sup>	Shutdown
H	L	All active	Z	Z	Normal operation
H	H	All active	Active	Active	Normal operation


(1) See the  $V_{IT+}$  and  $V_{IT-}$  change in the *Electrical Characteristics* table.

## 8 Application and Implementation

### Note

Information in the following applications sections is not part of the TI component specification, and TI does not warrant its accuracy or completeness. TI's customers are responsible for determining suitability of components for their purposes, as well as validating and testing their design implementation to confirm system functionality.

### 8.1 Typical Application



(1) C3 can be connected to V<sub>CC</sub> or GND.

NOTES: A. Resistor values shown are nominal.

B. Nonpolarized ceramic capacitors are acceptable. If polarized tantalum or electrolytic capacitors are used, they should be connected as shown.

**Figure 8-1. Typical Operating Circuit and Capacitor Values**

## 9 Device and Documentation Support

TI offers an extensive line of development tools. Tools and software to evaluate the performance of the device, generate code, and develop solutions are listed below.

### 9.1 Receiving Notification of Documentation Updates

To receive notification of documentation updates, navigate to the device product folder on [ti.com](http://ti.com). Click on *Notifications* to register and receive a weekly digest of any product information that has changed. For change details, review the revision history included in any revised document.

### 9.2 Support Resources

TI E2E™ [support forums](#) are an engineer's go-to source for fast, verified answers and design help — straight from the experts. Search existing answers or ask your own question to get the quick design help you need.

Linked content is provided "AS IS" by the respective contributors. They do not constitute TI specifications and do not necessarily reflect TI's views; see TI's [Terms of Use](#).

### 9.3 Trademarks

TI E2E™ is a trademark of Texas Instruments.  
All trademarks are the property of their respective owners.

### 9.4 Electrostatic Discharge Caution



This integrated circuit can be damaged by ESD. Texas Instruments recommends that all integrated circuits be handled with appropriate precautions. Failure to observe proper handling and installation procedures can cause damage.

ESD damage can range from subtle performance degradation to complete device failure. Precision integrated circuits may be more susceptible to damage because very small parametric changes could cause the device not to meet its published specifications.

### 9.5 Glossary

[TI Glossary](#) This glossary lists and explains terms, acronyms, and definitions.

## 10 Revision History

NOTE: Page numbers for previous revisions may differ from page numbers in the current version.

<b>Changes from Revision * (June 2007) to Revision A (July 2024)</b>	<b>Page</b>
• Changed the numbering format for tables, figures, and cross-references throughout the document.....	1
• Changed the DB package Input voltage range for Receivers from $\pm 30V$ to $\pm 25V$ in the <i>Absolute Maximum Ratings</i> and the <i>Recommended Operating Conditions</i> .....	5

## 11 Mechanical, Packaging, and Orderable Information

The following pages include mechanical, packaging, and orderable information. This information is the most current data available for the designated devices. This data is subject to change without notice and revision of this document. For browser-based versions of this data sheet, refer to the left-hand navigation.

**PACKAGING INFORMATION**

Orderable part number	Status (1)	Material type (2)	Package   Pins	Package qty   Carrier	RoHS (3)	Lead finish/ Ball material (4)	MSL rating/ Peak reflow (5)	Op temp (°C)	Part marking (6)
<a href="#">TRS213CDBR</a>	Obsolete	Production	SSOP (DB)   28	-	-	Call TI	Call TI	0 to 70	TRS213C
<a href="#">TRS213IDB</a>	Obsolete	Production	SSOP (DB)   28	-	-	Call TI	Call TI	-40 to 85	TRS213I
<a href="#">TRS213IDBR</a>	Active	Production	SSOP (DB)   28	2000   LARGE T&R	Yes	NIPDAU	Level-1-260C-UNLIM	-40 to 85	TRS213I
TRS213IDBR.A	Active	Production	SSOP (DB)   28	2000   LARGE T&R	Yes	NIPDAU	Level-1-260C-UNLIM	-40 to 85	TRS213I
TRS213IDBRG4	Active	Production	SSOP (DB)   28	2000   LARGE T&R	Yes	NIPDAU	Level-1-260C-UNLIM	-40 to 85	TRS213I
TRS213IDBRG4.A	Active	Production	SSOP (DB)   28	2000   LARGE T&R	Yes	NIPDAU	Level-1-260C-UNLIM	-40 to 85	TRS213I
<a href="#">TRS213IDWR</a>	Active	Production	SOIC (DW)   28	1000   LARGE T&R	Yes	NIPDAU	Level-1-260C-UNLIM	-40 to 85	TRS213I
TRS213IDWR.A	Active	Production	SOIC (DW)   28	1000   LARGE T&R	Yes	NIPDAU	Level-1-260C-UNLIM	-40 to 85	TRS213I

(1) **Status:** For more details on status, see our [product life cycle](#).

(2) **Material type:** When designated, preproduction parts are prototypes/experimental devices, and are not yet approved or released for full production. Testing and final process, including without limitation quality assurance, reliability performance testing, and/or process qualification, may not yet be complete, and this item is subject to further changes or possible discontinuation. If available for ordering, purchases will be subject to an additional waiver at checkout, and are intended for early internal evaluation purposes only. These items are sold without warranties of any kind.

(3) **RoHS values:** Yes, No, RoHS Exempt. See the [TI RoHS Statement](#) for additional information and value definition.

(4) **Lead finish/Ball material:** Parts may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead finish/Ball material values may wrap to two lines if the finish value exceeds the maximum column width.

(5) **MSL rating/Peak reflow:** The moisture sensitivity level ratings and peak solder (reflow) temperatures. In the event that a part has multiple moisture sensitivity ratings, only the lowest level per JEDEC standards is shown. Refer to the shipping label for the actual reflow temperature that will be used to mount the part to the printed circuit board.

(6) **Part marking:** There may be an additional marking, which relates to the logo, the lot trace code information, or the environmental category of the part.

Multiple part markings will be inside parentheses. Only one part marking contained in parentheses and separated by a "-" will appear on a part. If a line is indented then it is a continuation of the previous line and the two combined represent the entire part marking for that device.

**Important Information and Disclaimer:** The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.

**TAPE AND REEL INFORMATION**

**QUADRANT ASSIGNMENTS FOR PIN 1 ORIENTATION IN TAPE**


\*All dimensions are nominal

Device	Package Type	Package Drawing	Pins	SPQ	Reel Diameter (mm)	Reel Width W1 (mm)	A0 (mm)	B0 (mm)	K0 (mm)	P1 (mm)	W (mm)	Pin1 Quadrant
TRS213IDBR	SSOP	DB	28	2000	330.0	16.4	8.45	10.55	2.5	12.0	16.2	Q1
TRS213IDBRG4	SSOP	DB	28	2000	330.0	16.4	8.45	10.55	2.5	12.0	16.2	Q1
TRS213IDWR	SOIC	DW	28	1000	330.0	32.4	11.35	18.67	3.1	16.0	32.0	Q1




**TAPE AND REEL BOX DIMENSIONS**


\*All dimensions are nominal

Device	Package Type	Package Drawing	Pins	SPQ	Length (mm)	Width (mm)	Height (mm)
TRS213IDBR	SSOP	DB	28	2000	353.0	353.0	32.0
TRS213IDBRG4	SSOP	DB	28	2000	353.0	353.0	32.0
TRS213IDWR	SOIC	DW	28	1000	350.0	350.0	66.0

DW (R-PDSO-G28)

PLASTIC SMALL OUTLINE



- NOTES:
- All linear dimensions are in inches (millimeters). Dimensioning and tolerancing per ASME Y14.5M-1994.
  - This drawing is subject to change without notice.
  - Body dimensions do not include mold flash or protrusion not to exceed 0.006 (0,15).
  - Falls within JEDEC MS-013 variation AE.

# DB0028A



# PACKAGE OUTLINE

## SSOP - 2 mm max height

SMALL OUTLINE PACKAGE



4214853/B 03/2018

### NOTES:


1. All linear dimensions are in millimeters. Any dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.
2. This drawing is subject to change without notice.
3. This dimension does not include mold flash, protrusions, or gate burrs. Mold flash, protrusions, or gate burrs shall not exceed 0.15 mm per side.
4. This dimension does not include interlead flash. Interlead flash shall not exceed 0.25 mm per side.
5. Reference JEDEC registration MO-150.

# EXAMPLE BOARD LAYOUT

DB0028A

SSOP - 2 mm max height

SMALL OUTLINE PACKAGE



LAND PATTERN EXAMPLE  
EXPOSED METAL SHOWN  
SCALE: 10X



4214853/B 03/2018

NOTES: (continued)

- 6. Publication IPC-7351 may have alternate designs.
- 7. Solder mask tolerances between and around signal pads can vary based on board fabrication site.

# EXAMPLE STENCIL DESIGN

DB0028A

SSOP - 2 mm max height

SMALL OUTLINE PACKAGE



NOTES: (continued)

8. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.
9. Board assembly site may have different recommendations for stencil design.

## IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATASHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, regulatory or other requirements.

These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you fully indemnify TI and its representatives against any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to [TI's Terms of Sale](#), [TI's General Quality Guidelines](#), or other applicable terms available either on [ti.com](#) or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products. Unless TI explicitly designates a product as custom or customer-specified, TI products are standard, catalog, general purpose devices.

TI objects to and rejects any additional or different terms you may propose.

Copyright © 2025, Texas Instruments Incorporated

Last updated 10/2025