

# MCF8315D Sensorless Field Oriented Control (FOC) Integrated FET BLDC Driver

## 1 Features

- Three-phase BLDC motor driver with integrated sensorless motor control algorithm
  - Code-free Field Oriented Control (FOC)
  - Speed, current, power and voltage control
  - Forward and reverse windmilling support
  - Configurable power and speed limit
  - Lead angle adjustment for high efficiency
  - Improved acoustic performance with soft-start, soft-stop and dead time compensation
  - Offline motor parameter measurement with Motor Parameter Extraction Tool (MPET)
  - Analog, PWM, freq. or I<sup>2</sup>C based speed input
  - Configurable motor start-up and stop options
  - Flux weakening for high speed operation
  - Anti-voltage surge (AVS) protection
  - Variable monitoring through DACOUT pins
- 4.5 to 35V operating voltage (40V abs max)
- High output current capability: 4A peak
- Low MOSFET on-state resistance
  - RGF: R<sub>DS(ON)</sub>(H+L) at T<sub>J</sub>=25°C: 240mΩ(typ.)
  - RRY: R<sub>DS(ON)</sub>(H+L) at T<sub>J</sub>=25°C: 250mΩ(typ.)
  - PWP: R<sub>DS(ON)</sub>(H+L) at T<sub>J</sub>=25°C: 265mΩ(typ.)
- Low power sleep mode: Refer [Table 6-8](#)
  - 5μA (maximum) at V<sub>VM</sub> = 24V, T<sub>A</sub> = 25°C
- Speed loop accuracy: 3% with internal clock and 1% with external clock reference
- Configurable EEPROM with R/W security to store device configuration
- Does not require external current sense resistors; uses built-in current sensing
- Built-in 3.3V, 20mA LDO regulator
- Built-in 3.3V/5V, 170mA buck regulator
- Dedicated DRVOFF pin to disable (Hi-Z) outputs
- Spread spectrum, PWM dithering and slew rate for EMI reduction
- Suite of integrated protection features
  - Supply under voltage lockout (UVLO)
  - Supply over voltage protection (OVP)
  - Motor lock detection
  - Configurable current limit
  - Thermal warning and shutdown (OTW/TSD)
  - Fault condition indication pin (nFAULT)
  - Optional fault diagnostics over I<sup>2</sup>C interface

## 2 Applications

- [Brushless-DC \(BLDC\) Motor Modules](#)
- [Washer and Dishwashers Pumps](#)
- [Air Purifiers and Humidifier Fans](#)
- [Small Home Appliances](#)
- [Residential and Living Fans](#)

## 3 Description

The MCF8315D provides a single-chip, code-free sensorless FOC device for customers driving speed-controlled 12 to 24V brushless-DC motors (BLDC) or Permanent Magnet Synchronous motor (PMSM) up to 4A peak current. The MCF8315D integrates three ½-bridges with 40V absolute maximum capability and a very low R<sub>DS(ON)</sub> of 240/250/265mΩ (high-side + low-side FETs). MCF8315D integrates power management circuits including a voltage-adjustable buck regulator (3.3V/5V, 170mA) and LDO (3.3V, 20mA) that can be used to power external circuits.

The FOC algorithm configuration can be stored in non-volatile EEPROM, which allows the device to operate stand-alone once the device has been configured. The device receives a speed command through a PWM input, analog voltage, variable frequency square wave, or I<sup>2</sup>C command. There are a large number of protection features integrated into the MCF8315D, is intended to protect the device, motor, and system against fault events.


**Device Information 1**

| PART NUMBER         | PACKAGE     | PACKAGE SIZE (2) |
|---------------------|-------------|------------------|
| MCF8315DVPWPR       | HTSSOP (24) | 7.80mm x 6.40mm  |
| MCF8315DULVPWPR (3) | HTSSOP (24) | 7.80mm x 6.40mm  |
| MCF8315DVRGFR (3)   | VQFN (40)   | 7.00mm x 5.00mm  |
| MCF8315DULVRGFR (3) | VQFN (40)   | 7.00mm x 5.00mm  |
| MCF8315DVRRYR (3)   | WQFN (32)   | 6.00mm x 4.00mm  |
| MCF8315DULVRRYR (3) | WQFN (32)   | 6.00mm x 4.00mm  |

- (1) For all available packages, see the orderable addendum at the end of the data sheet.
- (2) The package size (length × width) is a nominal value and includes pins, where applicable
- (3) Device available for preview only

Documentation for reference:

- Refer [MCF8315D EVM User's Guide](#)
- Refer to the [MCF8315D EVM GUI](#)



**Simplified Schematic**



## Table of Contents

|                                                                               |            |                                                                      |            |
|-------------------------------------------------------------------------------|------------|----------------------------------------------------------------------|------------|
| <b>1 Features</b> .....                                                       | <b>1</b>   | 7.3 Hardware_Configuration Registers.....                            | <b>139</b> |
| <b>2 Applications</b> .....                                                   | <b>1</b>   | 7.4 Internal_Algorithm_Configuration Registers.....                  | <b>153</b> |
| <b>3 Description</b> .....                                                    | <b>1</b>   | <b>8 RAM (Volatile) Register Map</b> .....                           | <b>158</b> |
| <b>4 Pin Configuration and Functions</b> .....                                | <b>3</b>   | 8.1 Fault_Status Registers.....                                      | <b>158</b> |
| <b>5 Specifications</b> .....                                                 | <b>7</b>   | 8.2 System_Status Registers.....                                     | <b>163</b> |
| 5.1 Absolute Maximum Ratings.....                                             | <b>7</b>   | 8.3 Device_Control Registers.....                                    | <b>167</b> |
| 5.2 ESD Ratings.....                                                          | <b>7</b>   | 8.4 Algorithm_Control Registers.....                                 | <b>168</b> |
| 5.3 Recommended Operating Conditions.....                                     | <b>7</b>   | 8.5 Algorithm_Variables Registers.....                               | <b>180</b> |
| 5.4 Thermal Information.....                                                  | <b>8</b>   | <b>9 Application and Implementation</b> .....                        | <b>218</b> |
| 5.5 Electrical Characteristics.....                                           | <b>8</b>   | 9.1 Application Information.....                                     | <b>218</b> |
| 5.6 Characteristics of the SDA and SCL bus for<br>Standard and Fast mode..... | <b>14</b>  | 9.2 Typical Applications.....                                        | <b>218</b> |
| <b>6 Detailed Description</b> .....                                           | <b>16</b>  | 9.3 Power Supply Recommendations.....                                | <b>224</b> |
| 6.1 Overview.....                                                             | <b>16</b>  | 9.4 Layout.....                                                      | <b>225</b> |
| 6.2 Functional Block Diagram.....                                             | <b>17</b>  | <b>10 Device and Documentation Support</b> .....                     | <b>228</b> |
| 6.3 Feature Description.....                                                  | <b>20</b>  | 10.1 Support Resources.....                                          | <b>228</b> |
| 6.4 Device Functional Modes.....                                              | <b>88</b>  | 10.2 Trademarks.....                                                 | <b>228</b> |
| 6.5 External Interface.....                                                   | <b>89</b>  | 10.3 Electrostatic Discharge Caution.....                            | <b>228</b> |
| 6.6 EEPROM access and I <sup>2</sup> C interface.....                         | <b>91</b>  | 10.4 Glossary.....                                                   | <b>228</b> |
| <b>7 EEPROM (Non-Volatile) Register Map</b> .....                             | <b>98</b>  | <b>11 Revision History</b> .....                                     | <b>228</b> |
| 7.1 Algorithm_Configuration Registers.....                                    | <b>98</b>  | <b>12 Mechanical, Packaging, and Orderable<br/>Information</b> ..... | <b>228</b> |
| 7.2 Fault_Configuration Registers.....                                        | <b>129</b> |                                                                      |            |

## 4 Pin Configuration and Functions




Figure 4-1. MCF8315D, 40-Pin VQFN With Exposed Thermal Pad, Top View




Figure 4-2. MCF8315D, 32-Pin WQFN With Exposed Thermal Pad, Top View




Figure 4-3. MCF8315D, 24-Pin HTSSOP With Exposed Thermal Pad, Top View

**Table 4-1. Pin Functions**

| PIN          | 40-pin package | 32-pin package | 24-pin package | TYPE <sup>(1)</sup> | DESCRIPTION                                                                                                                                                                                                                                                                                                                                                                                                        |
|--------------|----------------|----------------|----------------|---------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| NAME         | MCF8315D       | MCF8315D       | MCF8315D       |                     |                                                                                                                                                                                                                                                                                                                                                                                                                    |
| AGND         | 26             | 19             | 16             | GND                 | Device analog ground. Refer <a href="#">Section 9.4.1</a> for connection recommendation.                                                                                                                                                                                                                                                                                                                           |
| ALARM        | 39             | 30             | -              | O                   | Alarm signal: push-pull output. Pulled logic high during fault condition, if enabled.<br>If ALARM pin is not used, leave the pin floating.                                                                                                                                                                                                                                                                         |
| AVDD         | 27             | 20             | 17             | PWR O               | 3.3V internal regulator output. Connect a X7R, 1µF, 10V ceramic capacitor between the AVDD and AGND pins. This regulator can source up to 20mA for external circuits.                                                                                                                                                                                                                                              |
| BRAKE        | 35             | 28             | 24             | I                   | High → Brake the motor<br>Low → Normal motor operation<br>If BRAKE pin is not used, connect to AGND directly.<br>If BRAKE pin is used to brake the motor, use an (optional) external 10kΩ pull-down resistor (to AGND) for better noise rejection.                                                                                                                                                                 |
| CP           | 8              | 7              | 9              | PWR                 | Charge pump output. Connect a X7R, 1µF, 16V ceramic capacitor between the CP and VM pins.                                                                                                                                                                                                                                                                                                                          |
| CPH          | 7              | 6              | 8              | PWR                 | Charge pump switching node. Connect a X7R, 47nF, ceramic capacitor between the CPH and CPL pins. TI recommends a capacitor voltage rating at least twice the normal operating voltage of the device.                                                                                                                                                                                                               |
| CPL          | 6              | 5              | 7              | PWR                 |                                                                                                                                                                                                                                                                                                                                                                                                                    |
| DACOUT1      | 36             | 29             | -              | O                   | DAC output DACOUT1                                                                                                                                                                                                                                                                                                                                                                                                 |
| DACOUT2      | 37             | -              | -              | O                   | DAC output DACOUT2                                                                                                                                                                                                                                                                                                                                                                                                 |
| DACOUT2 /SOX | 38             | -              | -              | O                   | Multi-purpose pin:<br>DAC output when configured as DACOUT2<br>CSA output when configured as SOX                                                                                                                                                                                                                                                                                                                   |
| DGND         | 2              | 1              | 3              | GND                 | Device digital ground. Refer <a href="#">Section 9.4.1</a> for connection recommendation.                                                                                                                                                                                                                                                                                                                          |
| DIR          | 34             | 27             | -              | I                   | Direction of motor spinning;<br>When low, phase driving sequence is OUT A → OUT C → OUT B<br>When high, phase driving sequence is OUT A → OUT B → OUT C<br>If DIR pin is not used, connect to AGND or AVDD directly (depending on phase driving sequence needed).<br>If DIR pin is used for changing motor spin direction, use an (optional) external 10kΩ pulldown resistor (to AGND) for better noise rejection. |
| DRVOFF       | 21             | 18             | 15             | I                   | Coast (Hi-Z) all six MOSFETs as long as DRVOFF is high.<br>If DRVOFF pin is not used, connect to AGND directly.<br>If DRVOFF pin is to be used for instantly coasting (Hi-Z) the MOSFETs, use an external 10kΩ pull-down resistor (to AGND) for better noise rejection.                                                                                                                                            |
| DVDD         | 1              | 32             | 2              | PWR                 | 1.5V internal regulator output. Connect a X7R, 1µF, 6.3V ceramic capacitor between the DVDD and DGND pins.                                                                                                                                                                                                                                                                                                         |
| EXT_CLK      | 33             | 26             | 23             | I                   | External clock reference input in external clock reference mode.                                                                                                                                                                                                                                                                                                                                                   |
| EXT_WD       | 32             | 25             | 22             | I                   | External watchdog input.                                                                                                                                                                                                                                                                                                                                                                                           |
| FB_BK        | 3              | 2              | 4              | PWR I/O             | Feedback for buck regulator output control. Connect to buck regulator output after the inductor/resistor.                                                                                                                                                                                                                                                                                                          |
| FG           | 29             | 22             | 19             | O                   | Motor speed indicator : open-drain output that requires an external pull-up resistor to 1.8V to 5.0V. An optional internal pull-up resistor to AVDD is enabled by setting PULLUP_ENABLE to 1b; no external pull-up resistor should be used when internal pull-up resistor is enabled.                                                                                                                              |
| GND_BK       | 4              | 3              | 5              | GND                 | Buck regulator ground. Refer <a href="#">Section 9.4.1</a> for connection recommendation.                                                                                                                                                                                                                                                                                                                          |
| NC           | 22, 23, 24, 25 | -              | -              | -                   | No connection. Leave these pins floating or connect to Thermal pad for better heat dissipation.                                                                                                                                                                                                                                                                                                                    |

**Table 4-1. Pin Functions (continued)**

| PIN            | 40-pin package | 32-pin package | 24-pin package | TYPE <sup>(1)</sup> | DESCRIPTION                                                                                                                                                                                                                                                                                                             |
|----------------|----------------|----------------|----------------|---------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| NAME           | MCF8315 D      | MCF8315 D      | MCF8315 D      |                     |                                                                                                                                                                                                                                                                                                                         |
| nFAULT         | 40             | 31             | 1              | O                   | Fault indicator. Pulled logic-low during fault condition; open-drain output that requires an external pull-up resistor to 1.8V to 5.0V. An optional internal pull-up resistor to AVDD is enabled by setting PULLUP_ENABLE to 1b; no external pull-up resistor should be used when internal pull-up resistor is enabled. |
| OUTA           | 13, 14         | 11, 12         | 12             | PWR O               | Half-bridge output A                                                                                                                                                                                                                                                                                                    |
| OUTB           | 16, 17         | 13, 14         | 13             | PWR O               | Half-bridge output B                                                                                                                                                                                                                                                                                                    |
| OUTC           | 19, 20         | 15, 16         | 14             | PWR O               | Half-bridge output C                                                                                                                                                                                                                                                                                                    |
| PGND           | 12, 15, 18     | 10, 17         | 11             | GND                 | Device power ground. Refer <a href="#">Section 9.4.1</a> for connection recommendation.                                                                                                                                                                                                                                 |
| SCL            | 31             | 24             | 21             | I                   | I <sup>2</sup> C clock input                                                                                                                                                                                                                                                                                            |
| SDA            | 30             | 23             | 20             | I/O                 | I <sup>2</sup> C data line                                                                                                                                                                                                                                                                                              |
| SPEED/<br>WAKE | 28             | 21             | 18             | I                   | Device speed input; supports analog, PWM or frequency based speed input. The speed pin input can be configured through SPEED_MODE.                                                                                                                                                                                      |
| SW_BK          | 5              | 4              | 6              | PWR                 | Buck switch node. Connect this pin to an inductor or resistor.                                                                                                                                                                                                                                                          |
| VM             | 9, 10, 11      | 8, 9           | 10             | PWR I               | Device and motor power supply. Connect to motor supply voltage; bypass to PGND with one 0.1µF capacitor plus one bulk capacitor. TI recommends a capacitor voltage rating at least twice the normal operating voltage of the device.                                                                                    |
| Thermal pad    |                |                |                | GND                 | Must be connected to AGND.                                                                                                                                                                                                                                                                                              |

(1) I = input, O = output, GND = ground, PWR = power, NC = no connect

## 5 Specifications

### 5.1 Absolute Maximum Ratings

over operating ambient temperature range (unless otherwise noted)<sup>(1)</sup>

|                                                                                | MIN  | MAX                   | UNIT |
|--------------------------------------------------------------------------------|------|-----------------------|------|
| Power supply pin voltage (V <sub>M</sub> )                                     | −0.3 | 40                    | V    |
| Voltage difference between ground pins (GND_BK, DGND, PGND, AGND)              | −0.3 | 0.3                   | V    |
| Charge pump voltage (CPH, CP)                                                  | −0.3 | V <sub>VM</sub> + 6   | V    |
| Charge pump negative switching pin voltage (CPL)                               | −0.3 | V <sub>VM</sub> + 0.3 | V    |
| Switching regulator pin voltage (FB_BK)                                        | −0.3 | 6                     | V    |
| Switching node pin voltage (SW_BK)                                             | −0.3 | V <sub>VM</sub> + 0.3 | V    |
| Analog regulators pin voltage (AVDD)                                           | −0.3 | 4                     | V    |
| Analog regulators pin voltage (DVDD)                                           | −0.3 | 1.7                   | V    |
| Logic pin input voltage (BRAKE, DRVOFF, DIR, EXT_CLK, EXT_WD, SCL, SDA, SPEED) | −0.3 | 6                     | V    |
| Open drain pin output voltage (nFAULT, FG)                                     | −0.3 | 6                     | V    |
| Output pin voltage (OUTA, OUTB, OUTC)                                          | −1   | V <sub>VM</sub> + 1   | V    |
| Ambient temperature, T <sub>A</sub>                                            | −40  | 125                   | °C   |
| Junction temperature, T <sub>J</sub>                                           | −40  | 150                   | °C   |
| Storage temperature, T <sub>stg</sub>                                          | −65  | 150                   | °C   |

- (1) Operation outside the Absolute Maximum Ratings may cause permanent device damage. Absolute Maximum Ratings do not imply functional operation of the device at these or any other conditions beyond those listed under Recommended Operating Conditions. If used outside the Recommended Operating Conditions but within the Absolute Maximum Ratings, the device may not be fully functional, and this may affect device reliability, functionality, performance, and shorten the device lifetime

### 5.2 ESD Ratings

|                         | VALUE                                                                     | UNIT |
|-------------------------|---------------------------------------------------------------------------|------|
| V <sub>(ESD)</sub>      | Human body model (HBM), per ANSI/ESDA/JEDEC JS-001 <sup>(1)</sup>         | V    |
|                         | Charged device model (CDM), per JEDEC specification JS-002 <sup>(2)</sup> |      |
| Electrostatic discharge | ±2000                                                                     |      |
|                         | ±750                                                                      |      |

- (1) JEDEC document JEP155 states that 500-V HBM allows safe manufacturing with a standard ESD control process.  
(2) JEDEC document JEP157 states that 250-V CDM allows safe manufacturing with a standard ESD control process.

### 5.3 Recommended Operating Conditions

over operating ambient temperature range (unless otherwise noted)

|                                 |                                        |                                                      | MIN  | NOM | MAX | UNIT |
|---------------------------------|----------------------------------------|------------------------------------------------------|------|-----|-----|------|
| V <sub>VM</sub>                 | Power supply voltage                   | V <sub>VM</sub>                                      | 4.5  | 24  | 35  | V    |
| I <sub>OUT</sub> <sup>(1)</sup> | Peak output winding current (RGF, RRY) | OUTA, OUTB, OUTC                                     |      |     | 4   | A    |
|                                 | Peak output winding current (PWP)      |                                                      |      |     | 3.5 |      |
| V <sub>IN_LOGIC</sub>           | Logic input voltage                    | BRAKE, DRVOFF, DIR, EXT_CLK, EXT_WD, SPEED, SDA, SCL | −0.1 |     | 5.5 | V    |
| V <sub>OD</sub>                 | Open drain pullup voltage              | nFAULT, FG                                           | −0.1 |     | 5.5 | V    |
| I <sub>OD</sub>                 | Open drain output current capability   | nFAULT, FG                                           |      |     | 5   | mA   |
| T <sub>A</sub>                  | Operating ambient temperature          |                                                      | −40  |     | 125 | °C   |
| T <sub>J</sub>                  | Operating junction temperature         |                                                      | −40  |     | 150 | °C   |

- (1) Power dissipation and thermal limits must be observed

## 5.4 Thermal Information

| THERMAL METRIC <sup>(1)</sup> |                                              | MCF8315D   |            |         | UNIT |
|-------------------------------|----------------------------------------------|------------|------------|---------|------|
|                               |                                              | RGF (VQFN) | RRY (WQFN) | PWP     |      |
|                               |                                              | 40 Pins    | 32 Pins    | 24 Pins |      |
| $R_{\theta JA}$               | Junction-to-ambient thermal resistance       | 28         | 30.7       | 30.5    | °C/W |
| $R_{\theta JC(top)}$          | Junction-to-case (top) thermal resistance    | 16.7       | 18.6       | 23.7    | °C/W |
| $R_{\theta JB}$               | Junction-to-board thermal resistance         | 8.9        | 9.6        | 10.1    | °C/W |
| $\Psi_{JT}$                   | Junction-to-top characterization parameter   | 1.8        | 1.6        | 3.8     | °C/W |
| $\Psi_{JB}$                   | Junction-to-board characterization parameter | 8.9        | 9.6        | 10      | °C/W |
| $R_{\theta JC(bot)}$          | Junction-to-case (bottom) thermal resistance | 3.5        | 3.4        | 4.8     | °C/W |

(1) For more information about traditional and new thermal metrics, see the [Semiconductor and IC Package Thermal Metrics](#) application report.

## 5.5 Electrical Characteristics

$T_J = -40^{\circ}\text{C}$  to  $+150^{\circ}\text{C}$ ,  $V_{VM} = 4.5$  to  $35\text{ V}$  (unless otherwise noted). Typical limits apply for  $T_A = 25^{\circ}\text{C}$ ,  $V_{VM} = 24\text{ V}$

| PARAMETER             |                                | TEST CONDITIONS                                                                                                                                                                                        | MIN   | TYP  | MAX   | UNIT          |
|-----------------------|--------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-------|------|-------|---------------|
| <b>POWER SUPPLIES</b> |                                |                                                                                                                                                                                                        |       |      |       |               |
| $I_{VMQ}$             | VM sleep mode current          | $V_{VM} > 6\text{ V}$ , $V_{SPEED} = 0$ , $T_A = 25^{\circ}\text{C}$                                                                                                                                   |       | 3    | 5     | $\mu\text{A}$ |
|                       |                                | $V_{SPEED} = 0$ , $T_A = 125^{\circ}\text{C}$                                                                                                                                                          |       | 3.5  | 7     | $\mu\text{A}$ |
| $I_{VMS}$             | VM standby mode current        | $V_{VM} \geq 12\text{ V}$ , Standby Mode, DRVOFF = High, $T_A = 25^{\circ}\text{C}$ , $L_{BK} = 47\text{ uH}$ , $C_{BK} = 22\text{ }\mu\text{F}$                                                       |       | 8    | 16    | mA            |
|                       |                                | $V_{VM} \geq 12\text{ V}$ , Standby Mode, DRVOFF = High, $T_A = 25^{\circ}\text{C}$ , $R_{BK} = 22\text{ }\Omega$ , $C_{BK} = 22\text{ }\mu\text{F}$                                                   |       | 25   | 29    | mA            |
|                       |                                | $V_{VM} \geq 12\text{ V}$ , Standby Mode, DRVOFF = High, $L_{BK} = 47\text{ uH}$ , $C_{BK} = 22\text{ }\mu\text{F}$                                                                                    |       | 8    | 16.5  | mA            |
|                       |                                | $V_{VM} \geq 12\text{ V}$ , Standby Mode, DRVOFF = High, $R_{BK} = 22\text{ }\Omega$ , $C_{BK} = 22\text{ }\mu\text{F}$                                                                                |       | 25   | 29    | mA            |
| $I_{VM}$              | VM operating mode current      | $V_{VM} \geq 12\text{ V}$ , $V_{SPEED} > V_{EX\_SL}$ , PWM_FREQ_OUT = 0011b (25 kHz), $T_A = 25^{\circ}\text{C}$ , $L_{BK} = 47\text{ uH}$ , $C_{BK} = 22\text{ }\mu\text{F}$ , No Motor Connected     |       | 11   | 18    | mA            |
|                       |                                | $V_{VM} \geq 12\text{ V}$ , $V_{SPEED} > V_{EX\_SL}$ , PWM_FREQ_OUT = 0011b (25 kHz), $T_A = 25^{\circ}\text{C}$ , $R_{BK} = 22\text{ }\Omega$ , $C_{BK} = 22\text{ }\mu\text{F}$ , No Motor Connected |       | 27   | 31.5  | mA            |
|                       |                                | $V_{VM} \geq 12\text{ V}$ , $V_{SPEED} > V_{EX\_SL}$ , PWM_FREQ_OUT = 0011b (25 kHz), $L_{BK} = 47\text{ uH}$ , $C_{BK} = 22\text{ }\mu\text{F}$ , No Motor Connected                                  |       | 11   | 18    | mA            |
|                       |                                | $V_{VM} \geq 12\text{ V}$ , $V_{SPEED} > V_{EX\_SL}$ , PWM_FREQ_OUT = 0011b (25 kHz), $R_{BK} = 22\text{ }\Omega$ , $C_{BK} = 22\text{ }\mu\text{F}$ , No Motor Connected                              |       | 28   | 32    | mA            |
| $V_{AVDD}$            | Analog regulator voltage       | $0\text{ mA} \leq I_{AVDD} \leq 20\text{ mA}$                                                                                                                                                          | 3.125 | 3.3  | 3.465 | V             |
| $I_{AVDD}$            | External analog regulator load |                                                                                                                                                                                                        |       |      | 20    | mA            |
| $V_{DVDD}$            | Digital regulator voltage      |                                                                                                                                                                                                        | 1.4   | 1.55 | 1.65  | V             |
| $V_{VCP}$             | Charge pump regulator voltage  | VCP with respect to VM                                                                                                                                                                                 | 4.0   | 4.7  | 5.5   | V             |

$T_J = -40^{\circ}\text{C}$  to  $+150^{\circ}\text{C}$ ,  $V_{VM} = 4.5$  to  $35\text{ V}$  (unless otherwise noted). Typical limits apply for  $T_A = 25^{\circ}\text{C}$ ,  $V_{VM} = 24\text{ V}$

| PARAMETER             |                                                                                                           | TEST CONDITIONS                                                                                                                                                                  | MIN                                                | TYP | MAX                 | UNIT |
|-----------------------|-----------------------------------------------------------------------------------------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|----------------------------------------------------|-----|---------------------|------|
| <b>BUCK REGULATOR</b> |                                                                                                           |                                                                                                                                                                                  |                                                    |     |                     |      |
| $V_{BK}$              | Buck regulator average voltage<br>( $L_{BK} = 47\text{ }\mu\text{H}$ , $C_{BK} = 22\text{ }\mu\text{F}$ ) | $V_{VM} > 6\text{ V}$ , $0\text{ mA} \leq I_{BK} \leq 170\text{ mA}$ ,<br>BUCK_SEL = 00b                                                                                         | 3.1                                                | 3.3 | 3.5                 | V    |
|                       |                                                                                                           | $V_{VM} > 6\text{ V}$ , $0\text{ mA} \leq I_{BK} \leq 170\text{ mA}$ ,<br>BUCK_SEL = 01b                                                                                         | 4.6                                                | 5.0 | 5.4                 | V    |
|                       |                                                                                                           | $V_{VM} > 6\text{ V}$ , $0\text{ mA} \leq I_{BK} \leq 170\text{ mA}$ ,<br>BUCK_SEL = 10b                                                                                         | 3.7                                                | 4.0 | 4.3                 | V    |
|                       |                                                                                                           | $V_{VM} > 6.7\text{ V}$ , $0\text{ mA} \leq I_{BK} \leq 170\text{ mA}$ ,<br>BUCK_SEL = 11b                                                                                       | 5.2                                                | 5.7 | 5.8                 | V    |
|                       |                                                                                                           | $V_{VM} < 6.0\text{ V}$ (BUCK_SEL = 00b, 01b,<br>10b, 11b), $0\text{ mA} \leq I_{BK} \leq 170\text{ mA}$                                                                         | $V_{VM} - I_{BK} \cdot (R_{LBK} + 2)$ <sup>1</sup> |     |                     | V    |
| $V_{BK}$              | Buck regulator average voltage<br>( $L_{BK} = 22\text{ }\mu\text{H}$ , $C_{BK} = 22\text{ }\mu\text{F}$ ) | $V_{VM} > 6\text{ V}$ , $0\text{ mA} \leq I_{BK} \leq 20\text{ mA}$ ,<br>BUCK_SEL = 00b                                                                                          | 3.1                                                | 3.3 | 3.5                 | V    |
|                       |                                                                                                           | $V_{VM} > 6\text{ V}$ , $0\text{ mA} \leq I_{BK} \leq 20\text{ mA}$ ,<br>BUCK_SEL = 01b                                                                                          | 4.6                                                | 5.0 | 5.4                 | V    |
|                       |                                                                                                           | $V_{VM} > 6\text{ V}$ , $0\text{ mA} \leq I_{BK} \leq 20\text{ mA}$ ,<br>BUCK_SEL = 10b                                                                                          | 3.7                                                | 4.0 | 4.3                 | V    |
|                       |                                                                                                           | $V_{VM} > 6.7\text{ V}$ , $0\text{ mA} \leq I_{BK} \leq 20\text{ mA}$ ,<br>BUCK_SEL = 11b                                                                                        | 5.2                                                | 5.7 | 5.8                 | V    |
|                       |                                                                                                           | $V_{VM} < 6.0\text{ V}$ (BUCK_SEL = 00b, 01b,<br>10b, 11b), $0\text{ mA} \leq I_{BK} \leq 20\text{ mA}$                                                                          | $V_{VM} - I_{BK} \cdot (R_{LBK} + 2)$ <sup>1</sup> |     |                     | V    |
| $V_{BK}$              | Buck regulator average voltage<br>( $R_{BK} = 22\text{ }\Omega$ , $C_{BK} = 22\text{ }\mu\text{F}$ )      | $V_{VM} > 6\text{ V}$ , $0\text{ mA} \leq I_{BK} \leq 10\text{ mA}$ ,<br>BUCK_SEL = 00b                                                                                          | 3.1                                                | 3.3 | 3.5                 | V    |
|                       |                                                                                                           | $V_{VM} > 6\text{ V}$ , $0\text{ mA} \leq I_{BK} \leq 10\text{ mA}$ ,<br>BUCK_SEL = 01b                                                                                          | 4.6                                                | 5.0 | 5.4                 | V    |
|                       |                                                                                                           | $V_{VM} > 6\text{ V}$ , $0\text{ mA} \leq I_{BK} \leq 10\text{ mA}$ ,<br>BUCK_SEL = 10b                                                                                          | 3.7                                                | 4.0 | 4.3                 | V    |
|                       |                                                                                                           | $V_{VM} > 6.7\text{ V}$ , $0\text{ mA} \leq I_{BK} \leq 10\text{ mA}$ ,<br>BUCK_SEL = 11b                                                                                        | 5.2                                                | 5.7 | 5.8                 | V    |
|                       |                                                                                                           | $V_{VM} < 6.0\text{ V}$ (BUCK_SEL = 00b, 01b,<br>10b, 11b), $0\text{ mA} \leq I_{BK} \leq 10\text{ mA}$                                                                          | $V_{VM} - I_{BK} \cdot (R_{BK} + 2)$               |     |                     | V    |
| $V_{BK\_RIP}$         | Buck regulator ripple voltage                                                                             | $V_{VM} > 6\text{ V}$ , $0\text{ mA} \leq I_{BK} \leq 170\text{ mA}$ , Buck<br>regulator with inductor, $L_{BK} = 47\text{ }\mu\text{H}$ , $C_{BK}$<br>= $22\text{ }\mu\text{F}$ | -100                                               |     | 100                 | mV   |
|                       |                                                                                                           | $V_{VM} > 6\text{ V}$ , $0\text{ mA} \leq I_{BK} \leq 20\text{ mA}$ , Buck<br>regulator with inductor, $L_{BK} = 22\text{ }\mu\text{H}$ , $C_{BK}$<br>= $22\text{ }\mu\text{F}$  | -100                                               |     | 100                 | mV   |
|                       |                                                                                                           | $V_{VM} > 6\text{ V}$ , $0\text{ mA} \leq I_{BK} \leq 10\text{ mA}$ , Buck<br>regulator with resistor; $R_{BK} = 22\text{ }\Omega$ , $C_{BK}$<br>= $22\text{ }\mu\text{F}$       | -100                                               |     | 100                 | mV   |
| $I_{BK}$              | External buck regulator load                                                                              | $L_{BK} = 47\text{ }\mu\text{H}$ , $C_{BK} = 22\text{ }\mu\text{F}$ ,<br>BUCK_PS_DIS = 1b                                                                                        |                                                    |     | 170                 | mA   |
|                       |                                                                                                           | $L_{BK} = 47\text{ }\mu\text{H}$ , $C_{BK} = 22\text{ }\mu\text{F}$ ,<br>BUCK_PS_DIS = 0b                                                                                        |                                                    |     | 170 –<br>$I_{AVDD}$ | mA   |
|                       |                                                                                                           | $L_{BK} = 22\text{ }\mu\text{H}$ , $C_{BK} = 22\text{ }\mu\text{F}$ ,<br>BUCK_PS_DIS = 1b                                                                                        |                                                    |     | 20                  | mA   |
|                       |                                                                                                           | $L_{BK} = 22\text{ }\mu\text{H}$ , $C_{BK} = 22\text{ }\mu\text{F}$ ,<br>BUCK_PS_DIS = 0b                                                                                        |                                                    |     | 20 –<br>$I_{AVDD}$  | mA   |
|                       |                                                                                                           | $R_{BK} = 22\text{ }\Omega$ , $C_{BK} = 22\text{ }\mu\text{F}$ ,<br>BUCK_PS_DIS = 1b                                                                                             |                                                    |     | 10                  | mA   |
|                       |                                                                                                           | $R_{BK} = 22\text{ }\Omega$ , $C_{BK} = 22\text{ }\mu\text{F}$ ,<br>BUCK_PS_DIS = 0b                                                                                             |                                                    |     | 10 –<br>$I_{AVDD}$  | mA   |

$T_J = -40^{\circ}\text{C}$  to  $+150^{\circ}\text{C}$ ,  $V_{VM} = 4.5$  to  $35\text{ V}$  (unless otherwise noted). Typical limits apply for  $T_A = 25^{\circ}\text{C}$ ,  $V_{VM} = 24\text{ V}$

| PARAMETER                 |                                                                       | TEST CONDITIONS                                                        | MIN  | TYP | MAX  | UNIT |
|---------------------------|-----------------------------------------------------------------------|------------------------------------------------------------------------|------|-----|------|------|
| f <sub>SW_BK</sub>        | Buck regulator switching frequency                                    | Regulation Mode                                                        | 20   |     | 535  | kHz  |
|                           |                                                                       | Linear Mode                                                            | 20   |     | 535  | kHz  |
| V <sub>BK_UVLO</sub>      | Buck regulator undervoltage lockout                                   | V <sub>BK</sub> rising, BUCK_SEL = 00b                                 | 2.7  | 2.8 | 2.95 | V    |
|                           |                                                                       | V <sub>BK</sub> falling, BUCK_SEL = 00b                                | 2.5  | 2.6 | 2.7  | V    |
|                           |                                                                       | V <sub>BK</sub> rising, BUCK_SEL = 01b                                 | 4.3  | 4.4 | 4.55 | V    |
|                           |                                                                       | V <sub>BK</sub> falling, BUCK_SEL = 01b                                | 4.1  | 4.2 | 4.42 | V    |
|                           |                                                                       | V <sub>BK</sub> rising, BUCK_SEL = 10b                                 | 2.7  | 2.8 | 2.95 | V    |
|                           |                                                                       | V <sub>BK</sub> falling, BUCK_SEL = 10b                                | 2.5  | 2.6 | 2.7  | V    |
|                           |                                                                       | V <sub>BK</sub> rising, BUCK_SEL = 11b                                 | 4.3  | 4.4 | 4.55 | V    |
|                           |                                                                       | V <sub>BK</sub> falling, BUCK_SEL = 11b                                | 4.1  | 4.2 | 4.42 | V    |
| V <sub>BK_UVLO_HYS</sub>  | Buck regulator undervoltage lockout hysteresis                        | Rising to falling threshold, BUCK_SEL = 00b                            | 90   | 200 | 400  | mV   |
|                           |                                                                       | Rising to falling threshold, BUCK_SEL = 01b                            | 70   | 200 | 400  | mV   |
|                           |                                                                       | Rising to falling threshold, BUCK_SEL = 10b                            | 90   | 200 | 400  | mV   |
|                           |                                                                       | Rising to falling threshold, BUCK_SEL = 11b                            | 70   | 200 | 400  | mV   |
| I <sub>BK_CL</sub>        | Buck regulator current limit threshold                                | BUCK_CL = 0b                                                           | 360  | 600 | 910  | mA   |
|                           |                                                                       | BUCK_CL = 1b                                                           | 80   | 150 | 250  | mA   |
| I <sub>BK_OCP</sub>       | Buck regulator over current protection trip point                     |                                                                        | 2    | 3   | 4    | A    |
| t <sub>BK_RETRY</sub>     | Over current protection retry time                                    |                                                                        | 0.7  | 1   | 1.3  | ms   |
| DRIVER OUTPUTS            |                                                                       |                                                                        |      |     |      |      |
| R <sub>DS(ON)</sub> (RGF) | Total MOSFET on resistance (High-side + Low-side)                     | V <sub>VM</sub> > 6 V, I <sub>OUT</sub> = 1 A, T <sub>A</sub> = 25°C   |      | 240 | 260  | mΩ   |
|                           |                                                                       | V <sub>VM</sub> < 6 V, I <sub>OUT</sub> = 1 A, T <sub>A</sub> = 25°C   |      | 250 | 270  | mΩ   |
|                           |                                                                       | V <sub>VM</sub> > 6 V, I <sub>OUT</sub> = 1 A, T <sub>A</sub> = 150°C  |      | 360 | 400  | mΩ   |
|                           |                                                                       | V <sub>VM</sub> < 6 V, I <sub>OUT</sub> = 1 A, T <sub>A</sub> = 150°C  |      | 370 | 415  | mΩ   |
| R <sub>DS(ON)</sub> (RRY) | Total MOSFET on resistance (High-side + Low-side)                     | V <sub>VM</sub> > 6 V, I <sub>OUT</sub> = 1 A, T <sub>A</sub> = 25°C   |      | 250 | 270  | mΩ   |
|                           |                                                                       | V <sub>VM</sub> < 6 V, I <sub>OUT</sub> = 1 A, T <sub>A</sub> = 25°C   |      | 260 | 280  | mΩ   |
|                           |                                                                       | V <sub>VM</sub> > 6 V, I <sub>OUT</sub> = 1 A, T <sub>J</sub> = 150 °C |      | 375 | 415  | mΩ   |
|                           |                                                                       | V <sub>VM</sub> < 6 V, I <sub>OUT</sub> = 1 A, T <sub>J</sub> = 150 °C |      | 385 | 425  | mΩ   |
| R <sub>DS(ON)</sub> (PWP) | Total MOSFET on resistance (High-side + Low-side)                     | V <sub>VM</sub> > 6 V, I <sub>OUT</sub> = 1 A, T <sub>A</sub> = 25°C   |      | 265 | 280  | mΩ   |
|                           |                                                                       | V <sub>VM</sub> < 6 V, I <sub>OUT</sub> = 1 A, T <sub>A</sub> = 25°C   |      | 275 | 290  | mΩ   |
|                           |                                                                       | V <sub>VM</sub> > 6 V, I <sub>OUT</sub> = 1 A, T <sub>A</sub> = 150°C  |      | 390 | 430  | mΩ   |
|                           |                                                                       | V <sub>VM</sub> < 6 V, I <sub>OUT</sub> = 1 A, T <sub>A</sub> = 150°C  |      | 400 | 440  | mΩ   |
| SR                        | Phase pin slew rate switching low to high (Rising from 20 % to 80 %)  | V <sub>VM</sub> = 24 V, SLEW_RATE = 10b                                | 80   | 125 | 210  | V/μs |
|                           |                                                                       | V <sub>VM</sub> = 24 V, SLEW_RATE = 11b                                | 130  | 200 | 315  | V/μs |
| SR                        | Phase pin slew rate switching high to low (Falling from 80 % to 20 %) | V <sub>VM</sub> = 24 V, SLEW_RATE = 10b                                | 80   | 125 | 235  | V/μs |
|                           |                                                                       | V <sub>VM</sub> = 24 V, SLEW_RATE = 11b                                | 130  | 200 | 345  | V/μs |
| t <sub>DEAD</sub>         | Output dead time (high to low / low to high)                          | V <sub>VM</sub> = 24 V, SR = 125 V/μs                                  |      | 650 | 850  | ns   |
|                           |                                                                       | V <sub>VM</sub> = 24 V, SR = 200 V/μs                                  |      | 500 | 550  | ns   |
| SPEED INPUT - PWM MODE    |                                                                       |                                                                        |      |     |      |      |
| f <sub>PWM</sub>          | PWM input frequency                                                   |                                                                        | 0.01 |     | 100  | kHz  |

$T_J = -40^{\circ}\text{C}$  to  $+150^{\circ}\text{C}$ ,  $V_{VM} = 4.5$  to  $35\text{ V}$  (unless otherwise noted). Typical limits apply for  $T_A = 25^{\circ}\text{C}$ ,  $V_{VM} = 24\text{ V}$

| PARAMETER                    |                                                                       | TEST CONDITIONS                                                                                                               | MIN   | TYP  | MAX   | UNIT |
|------------------------------|-----------------------------------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------|-------|------|-------|------|
| Res <sub>PWM</sub>           | PWM input resolution                                                  | f <sub>PWM</sub> = 0.01 to 0.35 kHz                                                                                           | 11    | 12   | 13    | bits |
|                              |                                                                       | f <sub>PWM</sub> = 0.35 to 2 kHz                                                                                              | 11    | 13   | 14    | bits |
|                              |                                                                       | f <sub>PWM</sub> = 2 to 3.5 kHz                                                                                               | 11    | 11.5 | 12    | bits |
|                              |                                                                       | f <sub>PWM</sub> = 3.5 to 7 kHz                                                                                               | 12    | 13   | 13.5  | bits |
|                              |                                                                       | f <sub>PWM</sub> = 7 to 14 kHz                                                                                                | 11    | 12   | 12.5  | bits |
|                              |                                                                       | f <sub>PWM</sub> = 14 to 29.2 kHz                                                                                             | 10    | 11.5 | 12    | bits |
|                              |                                                                       | f <sub>PWM</sub> = 29.3 to 60 kHz                                                                                             | 9     | 10.5 | 11    | bits |
|                              |                                                                       | f <sub>PWM</sub> = 60 to 100 kHz                                                                                              | 8     | 9    | 10    | bits |
| SPEED INPUT - ANALOG MODE    |                                                                       |                                                                                                                               |       |      |       |      |
| V <sub>ANA_FS</sub>          | Analog full-speed voltage                                             |                                                                                                                               | 2.95  | 3    | 3.05  | V    |
| V <sub>ANA_RES</sub>         | Analog voltage resolution                                             |                                                                                                                               | 732   |      |       | μV   |
| SPEED INPUT - FREQUENCY MODE |                                                                       |                                                                                                                               |       |      |       |      |
| f <sub>PWM_FREQ</sub>        | PWM input frequency range                                             | Duty cycle = 50%                                                                                                              | 3     |      | 32767 | Hz   |
| SLEEP MODE                   |                                                                       |                                                                                                                               |       |      |       |      |
| V <sub>EN_SL</sub>           | Analog voltage to enter sleep mode                                    | SPEED_MODE = 00b (analog mode)                                                                                                |       |      | 40    | mV   |
| V <sub>EX_SL</sub>           | Analog voltage to exit sleep mode                                     | SPEED_MODE = 00b (analog mode)                                                                                                | 2.2   |      |       | V    |
| t <sub>DET_ANA</sub>         | Time needed to detect wake up signal on SPEED pin                     | SPEED_MODE= 00b (analog mode)<br>V <sub>SPEED</sub> > V <sub>EX_SL</sub>                                                      | 0.5   | 1    | 1.5   | μs   |
| t <sub>WAKE</sub>            | Wakeup time from sleep state                                          | V <sub>SPEED</sub> > V <sub>EX_SL</sub> to DVDD voltage available, SPEED_MODE = 00b (analog mode)                             |       | 3    | 5     | ms   |
| t <sub>EX_SL_DR_A NA</sub>   | Time taken to drive motor after wake-up from sleep state (MCF8315D)   | SPEED_MODE = 00b (analog mode), DVDD voltage available to first output PWM pulse, ISD detection disabled                      |       |      | 30    | ms   |
| t <sub>EX_SL_DR_A NA</sub>   | Time taken to drive motor after wake-up from sleep state (MCF8315DUL) | SPEED_MODE = 00b (analog mode), DVDD voltage available to first output PWM pulse, ISD detection disabled                      |       |      | 180   | ms   |
| t <sub>DET_PWM</sub>         | Time needed to detect wake up signal on SPEED pin                     | SPEED_MODE = 01b (PWM mode) or 11b (Frequency mode), V <sub>SPEED</sub> > V <sub>IH</sub>                                     | 0.5   | 1    | 1.5   | μs   |
| t <sub>WAKE_PWM</sub>        | Wakeup time from sleep state                                          | V <sub>SPEED</sub> > V <sub>IH</sub> to DVDD voltage available, SPEED_MODE = 01b (PWM mode) or 11b (Frequency mode)           |       | 3    | 5     | ms   |
| t <sub>EX_SL_DR_P WM</sub>   | Time taken to drive motor after wake-up from sleep state (MCF8315D)   | SPEED_MODE = 01b (PWM mode) or 11b (Frequency mode), DVDD voltage available to first output PWM pulse, ISD detection disabled |       |      | 30    | ms   |
| t <sub>EX_SL_DR_P WM</sub>   | Time taken to drive motor after wake-up from sleep state (MCF8315DUL) | SPEED_MODE = 01b (PWM mode) or 11b (Frequency mode), DVDD voltage available to first output PWM pulse, ISD detection disabled |       |      | 180   | ms   |
| t <sub>DET_SL_ANA</sub>      | Time needed to detect sleep command, analog mode                      | SPEED_MODE = 00b (analog mode)<br>V <sub>SPEED</sub> < V <sub>EN_SL</sub> , SLEEP_ENTRY_TIME = 00b                            | 0.035 | 0.05 | 0.065 | ms   |
|                              |                                                                       | SPEED_MODE = 00b (analog mode)<br>V <sub>SPEED</sub> < V <sub>EN_SL</sub> , SLEEP_ENTRY_TIME = 00b or 01b                     | 0.14  | 0.2  | 0.26  | ms   |
|                              |                                                                       | SPEED_MODE = 00b (analog mode)<br>V <sub>SPEED</sub> < V <sub>EN_SL</sub> , SLEEP_ENTRY_TIME = 10b                            | 14    | 20   | 26    | ms   |
|                              |                                                                       | SPEED_MODE = 00b (analog mode)<br>V <sub>SPEED</sub> < V <sub>EN_SL</sub> , SLEEP_ENTRY_TIME = 11b                            | 140   | 200  | 260   | ms   |

$T_J = -40^{\circ}\text{C}$  to  $+150^{\circ}\text{C}$ ,  $V_{VM} = 4.5$  to  $35\text{ V}$  (unless otherwise noted). Typical limits apply for  $T_A = 25^{\circ}\text{C}$ ,  $V_{VM} = 24\text{ V}$

| PARAMETER                                                      |                                                                   | TEST CONDITIONS                                                                                                                                                                           | MIN   | TYP  | MAX                          | UNIT          |
|----------------------------------------------------------------|-------------------------------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-------|------|------------------------------|---------------|
| $t_{\text{DET\_SL\_PWM}}$                                      | Time needed to detect sleep command, PWM or frequency mode        | SPEED_MODE = 01b (PWM mode) or 11b (Frequency mode), $V_{\text{SPEED}} < V_{\text{IL}}$ , SLEEP_ENTRY_TIME = 00b                                                                          | 0.035 | 0.05 | 0.065                        | ms            |
|                                                                |                                                                   | SPEED_MODE = 01b (PWM mode) or 11b (Frequency mode), $V_{\text{SPEED}} < V_{\text{IL}}$ , SLEEP_ENTRY_TIME = 01b                                                                          | 0.14  | 0.2  | 0.26                         | ms            |
|                                                                |                                                                   | SPEED_MODE = 01b (PWM mode) or 11b (Frequency mode), $V_{\text{SPEED}} < V_{\text{IL}}$ , SLEEP_ENTRY_TIME = 10b                                                                          | 14    | 20   | 26                           | ms            |
|                                                                |                                                                   | SPEED_MODE = 01b (PWM mode) or 11b (Frequency mode), $V_{\text{SPEED}} < V_{\text{IL}}$ , SLEEP_ENTRY_TIME = 11b                                                                          | 140   | 200  | 260                          | ms            |
| $t_{\text{EN\_SL}}$                                            | Time needed to stop driving motor after detecting sleep command   | SPEED < $V_{\text{EN\_SL}}$ (analog mode) or $V_{\text{SPEED}} < V_{\text{IL}}$ (PWM mode or Frequency mode) or $V_{\text{SPEED}} < V_{\text{IL}}$ and DIGITAL_SPEED_CTRL = 0b (I2C mode) |       | 1    | 2                            | ms            |
| <b>STANDBY MODE</b>                                            |                                                                   |                                                                                                                                                                                           |       |      |                              |               |
| $t_{\text{EX\_SB\_DR\_ANA}}$                                   | Time taken to drive motor after exiting standby mode, analog mode | SPEED_MODE = 00b (analog mode), $V_{\text{SPEED}} > V_{\text{EX\_SB}}$ , ISD detection disabled                                                                                           |       |      | 6                            | ms            |
| $t_{\text{EX\_SB\_DR\_PWM}}$                                   | Time taken to drive motor after exiting standby mode, PWM mode    | SPEED_MODE = 01b (PWM mode) $V_{\text{SPEED}} > V_{\text{IH}}$ , ISD detection disabled                                                                                                   |       |      | 6                            | ms            |
| $t_{\text{DET\_SB\_ANA}}$                                      | Time needed to detect standby command, analog mode                | SPEED_MODE = 00b (analog mode), $V_{\text{SPEED}} < V_{\text{EN\_SB}}$                                                                                                                    | 0.5   | 1    | 2                            | ms            |
| $t_{\text{DET\_SB\_PWM}}$                                      | Time needed to detect standby command, PWM or frequency mode      | SPEED_MODE = 01b (PWM mode) or SPEED_MODE = 11b (Freq mode), $V_{\text{SPEED}} < V_{\text{IL}}$ , SLEEP_ENTRY_TIME = 00b                                                                  | 0.035 | 0.05 | 0.065                        | ms            |
|                                                                |                                                                   | SPEED_MODE = 01b (PWM mode) or SPEED_MODE = 11b (Freq mode), $V_{\text{SPEED}} < V_{\text{IL}}$ , SLEEP_ENTRY_TIME = 01b                                                                  | 0.14  | 0.2  | 0.26                         | ms            |
|                                                                |                                                                   | SPEED_MODE = 01b (PWM mode) or SPEED_MODE = 11b (Freq mode), $V_{\text{SPEED}} < V_{\text{IL}}$ , SLEEP_ENTRY_TIME = 10b                                                                  | 14    | 20   | 26                           | ms            |
|                                                                |                                                                   | SPEED_MODE = 01b (PWM mode) or SPEED_MODE = 11b (Freq mode), $V_{\text{SPEED}} < V_{\text{IL}}$ , SLEEP_ENTRY_TIME = 11b                                                                  | 140   | 200  | 260                          | ms            |
| $t_{\text{DET\_SB\_DIG}}$                                      | Time needed to detect standby mode, I2C mode                      | SPEED_MODE = 10b (I2C mode), DIGITAL_SPEED_CTRL = 0b                                                                                                                                      |       | 1    | 2                            | ms            |
| $t_{\text{EN\_SB}}$                                            | Time needed to stop driving motor after detecting standby command | All reference input modes                                                                                                                                                                 |       | 1    | 2                            | ms            |
| <b>LOGIC-LEVEL INPUTS (BRAKE, DIR, EXT_CLK, EXT_WD, SPEED)</b> |                                                                   |                                                                                                                                                                                           |       |      |                              |               |
| $V_{\text{IL}}$                                                | Input logic low voltage                                           | AVDD = 3 to 3.6 V                                                                                                                                                                         |       |      | $0.25 \cdot V_{\text{AVDD}}$ | V             |
| $V_{\text{IH}}$                                                | Input logic high voltage                                          | AVDD = 3 to 3.6 V                                                                                                                                                                         |       |      | $0.65 \cdot V_{\text{AVDD}}$ | V             |
| $V_{\text{HYS}}$                                               | Input hysteresis                                                  |                                                                                                                                                                                           | 50    | 500  | 800                          | mV            |
| $I_{\text{IL}}$                                                | Input logic low current                                           | AVDD = 3 to 3.6 V                                                                                                                                                                         | -0.15 |      | 0.15                         | $\mu\text{A}$ |

$T_J = -40^{\circ}\text{C}$  to  $+150^{\circ}\text{C}$ ,  $V_{VM} = 4.5$  to  $35\text{ V}$  (unless otherwise noted). Typical limits apply for  $T_A = 25^{\circ}\text{C}$ ,  $V_{VM} = 24\text{ V}$

| PARAMETER                         |                                                                            | TEST CONDITIONS                         | MIN              | TYP          | MAX              | UNIT   |
|-----------------------------------|----------------------------------------------------------------------------|-----------------------------------------|------------------|--------------|------------------|--------|
| I <sub>IH</sub>                   | Input logic high current                                                   | AVDD = 3 to 3.6 V                       | -0.3             |              | 0                | μA     |
| R <sub>PD_SPEED</sub>             | Input pulldown resistance                                                  | SPEED pin To GND                        | 0.6              | 1            | 1.4              | MΩ     |
| OPEN-DRAIN OUTPUTS (nFAULT, FG)   |                                                                            |                                         |                  |              |                  |        |
| V <sub>OL</sub>                   | Output logic low voltage                                                   | I <sub>OD</sub> = -5 mA                 |                  |              | 0.4              | V      |
| I <sub>OZ</sub>                   | Output logic high current                                                  | V <sub>OD</sub> = 3.3 V                 | 0                |              | 0.5              | μA     |
| I <sup>2</sup> C Serial Interface |                                                                            |                                         |                  |              |                  |        |
| V <sub>I2C_L</sub>                | Input logic low voltage                                                    |                                         | -0.5             | 0.3*AVD<br>D |                  | V      |
| V <sub>I2C_H</sub>                | Input logic high voltage                                                   |                                         | 0.7*AVD<br>D     |              | 5.5              | V      |
| V <sub>I2C_HYS</sub>              | Hysteresis                                                                 |                                         | 0.05*AV<br>DD    |              |                  | V      |
| V <sub>I2C_OL</sub>               | Output logic low voltage                                                   | Open-drain at 2mA sink current          | 0                |              | 0.4              | V      |
| I <sub>I2C_OL</sub>               | Output logic low current                                                   | V <sub>I2C_OL</sub> = 0.6V              |                  |              | 6                | mA     |
| I <sub>I2C_IL</sub>               | Input current on SDA and SCL                                               |                                         | -10 <sup>2</sup> |              | 10 <sup>2</sup>  | μA     |
| C <sub>i</sub>                    | Capacitance for SDA and SCL                                                |                                         |                  |              | 10               | pF     |
| t <sub>of</sub>                   | Output fall time from V <sub>I2C_H</sub> (min) to V <sub>I2C_L</sub> (max) | Standard Mode                           |                  |              | 250 <sup>3</sup> | ns     |
|                                   |                                                                            | Fast Mode                               |                  |              | 250 <sup>3</sup> | ns     |
| t <sub>SP</sub>                   | Pulse width of spikes that must be suppressed by the input filter          | Fast Mode                               | 0                |              | 50 <sup>4</sup>  | ns     |
| OSCILLATOR                        |                                                                            |                                         |                  |              |                  |        |
| f <sub>OSCREF</sub>               | External clock reference                                                   | EXT_CLK_CONFIG = 000b                   |                  | 8            |                  | kHz    |
|                                   |                                                                            | EXT_CLK_CONFIG = 001b                   |                  | 16           |                  | kHz    |
|                                   |                                                                            | EXT_CLK_CONFIG = 010b                   |                  | 32           |                  | kHz    |
|                                   |                                                                            | EXT_CLK_CONFIG = 011b                   |                  | 64           |                  | kHz    |
|                                   |                                                                            | EXT_CLK_CONFIG = 100b                   |                  | 128          |                  | kHz    |
|                                   |                                                                            | EXT_CLK_CONFIG = 101b                   |                  | 256          |                  | kHz    |
|                                   |                                                                            | EXT_CLK_CONFIG = 110b                   |                  | 512          |                  | kHz    |
|                                   |                                                                            | EXT_CLK_CONFIG = 111b                   |                  | 1024         |                  | kHz    |
| EEPROM                            |                                                                            |                                         |                  |              |                  |        |
| EE <sub>Prog</sub>                | Programming voltage                                                        |                                         | 1.35             | 1.5          | 1.65             | V      |
| EE <sub>RET</sub>                 | Retention                                                                  | T <sub>A</sub> = 25 °C                  |                  | 100          |                  | Years  |
|                                   |                                                                            | T <sub>J</sub> = -40 to 150 °C          | 10               |              |                  | Years  |
| EE <sub>END</sub>                 | Endurance                                                                  | T <sub>J</sub> = -40 to 150 °C          | 1000             |              |                  | Cycles |
|                                   |                                                                            | T <sub>J</sub> = -40 to 85 °C           | 20000            |              |                  | Cycles |
| PROTECTION CIRCUITS               |                                                                            |                                         |                  |              |                  |        |
| V <sub>UVLO</sub>                 | Supply under voltage lockout (UVLO)                                        | VM rising                               | 4.3              | 4.4          | 4.51             | V      |
|                                   |                                                                            | VM falling                              | 4.1              | 4.2          | 4.32             | V      |
| V <sub>UVLO_HYS</sub>             | Supply under voltage lockout hysteresis                                    | Rising to falling threshold             | 90               | 200          | 350              | mV     |
| t <sub>UVLO</sub>                 | Supply under voltage deglitch time                                         |                                         | 3                | 5            | 7                | μs     |
| V <sub>OVP</sub>                  | Supply over voltage protection (OVP) threshold                             | Supply rising, OVP_EN = 1, OVP_SEL = 0  | 32.5             | 34           | 35               | V      |
|                                   |                                                                            | Supply falling, OVP_EN = 1, OVP_SEL = 0 | 31.8             | 33           | 34.3             | V      |
|                                   |                                                                            | Supply rising, OVP_EN = 1, OVP_SEL = 1  | 20               | 22           | 23               | V      |
|                                   |                                                                            | Supply falling, OVP_EN = 1, OVP_SEL = 1 | 19               | 21           | 22               | V      |

$T_J = -40^{\circ}\text{C}$  to  $+150^{\circ}\text{C}$ ,  $V_{VM} = 4.5$  to  $35\text{ V}$  (unless otherwise noted). Typical limits apply for  $T_A = 25^{\circ}\text{C}$ ,  $V_{VM} = 24\text{ V}$

| PARAMETER            |                                                   | TEST CONDITIONS                             | MIN  | TYP  | MAX  | UNIT               |
|----------------------|---------------------------------------------------|---------------------------------------------|------|------|------|--------------------|
| $V_{OVP\_HYS}$       | Supply over voltage protection hysteresis         | Rising to falling threshold, $OVP\_SEL = 1$ | 0.9  | 1    | 1.15 | V                  |
|                      |                                                   | Rising to falling threshold, $OVP\_SEL = 0$ | 0.7  | 0.8  | 0.9  | V                  |
| $t_{OVP}$            | Supply over voltage deglitch time                 |                                             | 2.5  | 5    | 7    | $\mu\text{s}$      |
| $V_{CPUV}$           | Charge pump under voltage lockout (above VM)      | Supply rising                               | 2.25 | 2.5  | 2.75 | V                  |
|                      |                                                   | Supply falling                              | 2.2  | 2.4  | 2.6  | V                  |
| $V_{CPUV\_HYS}$      | Charge pump UVLO hysteresis                       | Rising to falling threshold                 | 65   | 100  | 150  | mV                 |
| $V_{AVDD\_UV}$       | Analog regulator (AVDD) under voltage lockout     | Supply rising                               | 2.7  | 2.85 | 3    | V                  |
|                      |                                                   | Supply falling                              | 2.48 | 2.65 | 2.8  | V                  |
| $V_{AVDD\_UV\_HYS}$  | Analog regulator under voltage lockout hysteresis | Rising to falling threshold                 | 180  | 200  | 240  | mV                 |
| $I_{OCP}$            | Over current protection trip point                | $OCP\_LVL = 0b$                             | 5.5  | 9    | 12   | A                  |
|                      |                                                   | $OCP\_LVL = 1b$                             | 9    | 13   | 18   | A                  |
| $t_{OCP}$            | Over current protection deglitch time             | $OCP\_DEG = 00b$                            | 0.02 | 0.2  | 0.4  | $\mu\text{s}$      |
|                      |                                                   | $OCP\_DEG = 01b$                            | 0.2  | 0.6  | 1.2  | $\mu\text{s}$      |
|                      |                                                   | $OCP\_DEG = 10b$                            | 0.5  | 1.2  | 1.8  | $\mu\text{s}$      |
|                      |                                                   | $OCP\_DEG = 11b$                            | 0.9  | 1.6  | 2.5  | $\mu\text{s}$      |
| $t_{RETRY}$          | Over current protection retry time                |                                             | 425  | 500  | 575  | ms                 |
| $T_{OTW}$            | Thermal warning temperature                       | Die temperature ( $T_J$ )                   | 135  | 145  | 155  | $^{\circ}\text{C}$ |
| $T_{OTW\_HYS}$       | Thermal warning hysteresis                        | Die temperature ( $T_J$ )                   | 15   | 20   | 30   | $^{\circ}\text{C}$ |
| $T_{TSD\_BUCK}$      | Thermal shutdown temperature (Buck)               | Die temperature ( $T_J$ )                   | 170  | 180  | 190  | $^{\circ}\text{C}$ |
| $T_{TSD\_BUCK\_HYS}$ | Thermal shutdown hysteresis (Buck)                | Die temperature ( $T_J$ )                   | 15   | 20   | 30   | $^{\circ}\text{C}$ |
| $T_{TSD}$            | Thermal shutdown temperature (FET)                | Die temperature ( $T_J$ )                   | 165  | 175  | 185  | $^{\circ}\text{C}$ |
| $T_{TSD\_HYS}$       | Thermal shutdown hysteresis (FET)                 | Die temperature ( $T_J$ )                   | 15   | 20   | 30   | $^{\circ}\text{C}$ |

- (1)  $R_{LBK}$  is resistance of inductor  $L_{BK}$ .
- (2) If AVDD is switched off, I/O pins must not obstruct the SDA and SCL lines.
- (3) The maximum  $t_f$  for the SDA and SCL bus lines (300 ns) is longer than the specified maximum  $t_{of}$  for the output stages (250 ns). This allows series protection resistors ( $R_s$ ) to be connected between the SDA/SCL pins and the SDA/SCL bus lines without exceeding the maximum specified  $t_f$ .
- (4) Input filters on the SDA and SCL inputs suppress noise spikes of less than 50 ns.

## 5.6 Characteristics of the SDA and SCL bus for Standard and Fast mode

over operating free-air temperature range (unless otherwise noted)

| PARAMETER            |                                                                                                      | TEST CONDITIONS                                       | MIN              | NOM | MAX            | UNIT          |
|----------------------|------------------------------------------------------------------------------------------------------|-------------------------------------------------------|------------------|-----|----------------|---------------|
| <b>Standard-mode</b> |                                                                                                      |                                                       |                  |     |                |               |
| $f_{SCL}$            | SCL clock frequency                                                                                  |                                                       | 0                |     | 100            | kHz           |
| $t_{HD\_STA}$        | Hold time (repeated) START condition                                                                 | After this period, the first clock pulse is generated | 4                |     |                | $\mu\text{s}$ |
| $t_{LOW}$            | LOW period of the SCL clock                                                                          |                                                       | 4.7              |     |                | $\mu\text{s}$ |
| $t_{HIGH}$           | HIGH period of the SCL clock                                                                         |                                                       | 4                |     |                | $\mu\text{s}$ |
| $t_{SU\_STA}$        | Set-up time for a repeated START condition                                                           |                                                       | 4.7              |     |                | $\mu\text{s}$ |
| $t_{HD\_DAT}$        | Data hold time <sup>(2)</sup>                                                                        | I2C bus devices                                       | 0 <sup>(3)</sup> |     | <sup>(4)</sup> | $\mu\text{s}$ |
| $t_{SU\_DAT}$        | Data set-up time                                                                                     |                                                       | 250              |     |                | ns            |
| $t_r$                | Rise time for both SDA and SCL signals                                                               |                                                       |                  |     | 1000           | ns            |
| $t_f$                | Fall time of both SDA and SCL signals <sup>(3)</sup><br><sup>(6)</sup> <sup>(7)</sup> <sup>(8)</sup> |                                                       |                  |     | 300            | ns            |
| $t_{SU\_STO}$        | Set-up time for STOP condition                                                                       |                                                       | 4                |     |                | $\mu\text{s}$ |

over operating free-air temperature range (unless otherwise noted)

| PARAMETER        |                                                                                                      | TEST CONDITIONS                                       | MIN                     | NOM | MAX                 | UNIT    |
|------------------|------------------------------------------------------------------------------------------------------|-------------------------------------------------------|-------------------------|-----|---------------------|---------|
| $t_{BUF}$        | Bus free time between STOP and START condition                                                       |                                                       | 4.7                     |     |                     | $\mu s$ |
| $C_b$            | Capacitive load for each bus line <sup>(9)</sup>                                                     |                                                       |                         |     | 400                 | pF      |
| $t_{VD\_DAT}$    | Data valid time <sup>(10)</sup>                                                                      |                                                       |                         |     | 3.45 <sup>(4)</sup> | $\mu s$ |
| $t_{VD\_ACK}$    | Data valid acknowledge time <sup>(11)</sup>                                                          |                                                       |                         |     | 3.45 <sup>(4)</sup> | $\mu s$ |
| $V_{nL}$         | Noise margin at the LOW level                                                                        | For each connected device (including hysteresis)      | 0.1*AVD<br>D            |     |                     | V       |
| $V_{nh}$         | Noise margin at the HIGHlevel                                                                        | For each connected device (including hysteresis)      | 0.2*AVD<br>D            |     |                     | V       |
| <b>Fast-mode</b> |                                                                                                      |                                                       |                         |     |                     |         |
| $f_{SCL}$        | SCL clock frequency                                                                                  |                                                       | 0                       |     | 400                 | KHz     |
| $t_{HD\_STA}$    | Hold time (repeated) START condition                                                                 | After this period, the first clock pulse is generated | 0.6                     |     |                     | $\mu s$ |
| $t_{LOW}$        | LOW period of the SCL clock                                                                          |                                                       | 1.3                     |     |                     | $\mu s$ |
| $t_{HIGH}$       | HIGH period of the SCL clock                                                                         |                                                       | 0.6                     |     |                     | $\mu s$ |
| $t_{SU\_STA}$    | Set-up time for a repeated START condition                                                           |                                                       | 0.6                     |     |                     | $\mu s$ |
| $t_{HD\_DAT}$    | Data hold time <sup>(2)</sup>                                                                        |                                                       | 0 <sup>(3)</sup>        |     | <sup>(4)</sup>      | $\mu s$ |
| $t_{SU\_DAT}$    | Data set-up time                                                                                     |                                                       | 100 <sup>(5)</sup>      |     |                     | ns      |
| $t_r$            | Rise time for both SDA and SCL signals                                                               |                                                       | 20                      |     | 300                 | ns      |
| $t_f$            | Fall time of both SDA and SCL signals <sup>(3)</sup><br><sup>(6)</sup> <sup>(7)</sup> <sup>(8)</sup> |                                                       | 20 x<br>(AVDD/<br>5.5V) |     | 300                 | ns      |
| $t_{SU\_STO}$    | Set-up time for STOP condition                                                                       |                                                       | 0.6                     |     |                     | $\mu s$ |
| $t_{BUF}$        | Bus free time between STOP and START condition                                                       |                                                       | 1.3                     |     |                     | $\mu s$ |
| $C_b$            | Capacitive load for each bus line <sup>(9)</sup>                                                     |                                                       |                         |     | 400                 | pF      |
| $t_{VD\_DAT}$    | Data valid time <sup>(10)</sup>                                                                      |                                                       |                         |     | 0.9 <sup>(4)</sup>  | $\mu s$ |
| $t_{VD\_ACK}$    | Data valid acknowledge time <sup>(11)</sup>                                                          |                                                       |                         |     | 0.9 <sup>(4)</sup>  | $\mu s$ |
| $V_{nL}$         | Noise margin at the LOW level                                                                        | For each connected device (including hysteresis)      | 0.1*AVD<br>D            |     |                     | V       |
| $V_{nh}$         | Noise margin at the HIGHlevel                                                                        | For each connected device (including hysteresis)      | 0.2*AVD<br>D            |     |                     | V       |

- (1) All values referred to  $V_{IH(min)}$  (0.3V<sub>DD</sub>) and  $V_{IL(max)}$  levels
- (2)  $t_{HD\_DAT}$  is the data hold time that is measured from the falling edge of SCL, applies to data in transmission and the acknowledge.
- (3) A device must internally provide a hold time of at least 300 ns for the SDA signal (with respect to the  $V_{IH(min)}$  of the SCL signal) to bridge the undefined region of the falling edge of SCL.
- (4) The maximum  $t_{HD\_DAT}$  could be 3.45  $\mu s$  and .9  $\mu s$  for Standard-mode and Fast-mode, but must be less than the maximum of  $t_{VD\_DAT}$  or  $t_{VD\_ACK}$  by a transition time. This maximum must only be met if the device does not stretch the LOW period ( $t_{LOW}$ ) of the SCL signal. If the clock stretched the SCL, the data must be valid by the set-up time before it releases the clock.
- (5) A Fast-mode I2C-bus device can be used in a Standard-mode I2C-bus system, but the requirement  $t_{SU\_DAT}$  250 ns must then be met. This will automatically be the case if the device does not stretch the LOW period of the SCL signal. If such a device does stretch the LOW period of the SCL signal, it must output the next data bit to the SDA line  $t_{r(max)} + t_{SU\_DAT} = 1000 + 250 = 1250$  ns (according to the Standard-mode I2C-bus specification) before the SCL line is released. Also the acknowledge timing must meet this set-up time.
- (6) If mixed with HS-mode devices, faster fall times according to Table 10 are allowed.
- (7) The maximum  $t_f$  for the SDA and SCL bus lines is specified at 300 ns. The maximum fall time for the SDA output stage  $t_f$  is specified at 250 ns. This allows series protection resistors to be connected in between the SDA and the SCL pins and the SDA/SCL bus lines without exceeding the maximum specified  $t_f$ .
- (8) In Fast-mode Plus, fall time is specified the same for both output stage and bus timing. If series resistors are used, designers should allow for this when considering bus timing.
- (9) The maximum bus capacitance allowable may vary from the value depending on the actual operating voltage and frequency of the application.
- (10)  $t_{VD\_DAT}$  = time for data signal from SCL LOW to SDA output (HIGH or LOW, depending on which one is worse).
- (11)  $t_{VD\_ACK}$  = time for Acknowledgement signal from SCL LOW to SDA output (HIGH or LOW, depending on which one is worse).

## 6 Detailed Description

### 6.1 Overview

The MCF8315D provides a single-chip, code-free sensorless FOC solution for customers driving speed-controlled 12 to 24V brushless-DC motors requiring up to 4A peak phase currents.

The MCF8315D integrates three  $\frac{1}{2}$ -bridges with 40V absolute maximum capability and a low  $R_{DS(ON)}$  of 240m $\Omega$ (RGF)/250m $\Omega$ (RRY)/265m $\Omega$ (PWP) (high-side + low-side) to enable high power drive capability. Current is sensed using an integrated current sensing circuit which eliminates the need for external sense resistors. Power management features of an adjustable buck regulator and LDO generate the necessary voltage rails for the device and can also be used to power external circuits.

MCF8315D implements sensorless FOC, so an external microcontroller is not required to spin the brushless DC motor. The algorithm is implemented in a fixed-function state machine, so no coding is needed. The algorithm is highly configurable through register settings ranging from motor start-up behavior to closed-loop operation. Register settings can be stored in non-volatile EEPROM, which allows the device to operate stand-alone once it has been configured. The device receives a speed command through a PWM input, analog voltage, frequency input, or I<sup>2</sup>C command.

In-built protection features include power-supply under voltage lockout (UVLO), charge-pump under voltage lockout (CPUV), over current protection (OCP), AVDD under voltage lockout (AVDD\_UV), buck regulator UVLO, motor lock detection and over temperature warning and shutdown (OTW and TSD). Fault events are indicated by the nFAULT pin with detailed fault information available in the registers.

The MCF8315D device is available in three packages:

1. RGF: 40-pin, 7x5mm, 0.5mm pin pitch VQFN with a height of 1mm
2. RRY: 32-pin, 6x4mm, 0.5mm pin pitch WQFN with a height of 0.8mm
3. PWP: 24-pin, 7.8x6.4mm, 0.65mm pin pitch HTSSOP with a height of 1.2mm

## 6.2 Functional Block Diagram




Figure 6-1. MCF8315D (PWP) Functional Block Diagram




Figure 6-2. MCF8315D (RGF) Functional Block Diagram




**Figure 6-3. MCF8315D (RRY) Functional Block Diagram**

## 6.3 Feature Description

### 6.3.1 Output Stage

The MCF8315D consists of integrated 240mΩ/250mΩ/265mΩ (combined high-side and low-side FETs' on-state resistance) NMOS FETs connected in a three-phase bridge configuration. A doubler charge pump provides the proper gate-bias voltage to the high-side NMOS FETs across a wide operating voltage range in addition to providing 100% duty-cycle support. An internal linear regulator provides the gate-bias voltage for the low-side MOSFETs.

### 6.3.2 Device Interface

The MCF8315D supports I<sup>2</sup>C interface to provide end application design with adequate flexibility. MCF8315D allows controlling the motor operation and system through BRAKE, DRVOFF, DIR, EXT\_CLK, EXT\_WD and SPEED/WAKE pins. MCF8315D also provides different signals for monitoring system variables, speed, fault and phase current feedback through DACOUT1, DACOUT2, FG, nFAULT and SOX pins.

#### 6.3.2.1 Interface - Control and Monitoring

##### Motor Control Signals

- SPEED/WAKE pin is used to control the motor speed and to wake up MCF8315D from sleep. SPEED pin can be configured to accept PWM, frequency or analog input signals. It is also used to enter and exit from sleep and standby mode (see [Table 6-8](#)).
- When BRAKE pin is driven 'High', MCF8315D enters brake state. Brake state can be configured to either low side brake (see [Low-Side Braking](#)) or align brake (see [Section 6.3.22](#)) through BRAKE\_PIN\_MODE. MCF8315D decreases output speed to value defined by BRAKE\_SPEED\_THRESHOLD before entering brake state. As long as BRAKE is driven 'High', MCF8315D stays in brake state. Brake pin input can be overwritten by configuring BRAKE\_INPUT over the I<sup>2</sup>C interface.
- The DIR pin decides the direction of motor spin; when driven 'High', the sequence is OUT A → OUT B → OUT C, and when driven 'Low', the sequence is OUT A → OUT C → OUT B. DIR pin input can be overwritten by configuring DIR\_INPUT over the I<sup>2</sup>C interface.
- When DRVOFF pin is driven 'High', MCF8315D stops driving the motor by turning OFF (Hi-Z) all MOSFETs (coast state) - this could be accompanied by faults like no motor or abnormal BEMF. When DRVOFF is driven 'Low', MCF8315D returns to normal state of operation, as if it was restarting the motor (see [DRVOFF Functionality](#)). DRVOFF does not cause the device to go to sleep or standby mode; the digital core is still active. Entry and exit from sleep or standby condition is controlled by SPEED pin.

##### External Oscillator and Watchdog Signals

- EXT\_CLK pin can be used to provide an external clock reference (see [External Clock Source](#)).
- EXT\_WD pin can be used to provide an external watchdog signal (see [External Watchdog](#)).

##### Output Signals

- DACOUT1 outputs internal variable defined by address in register DACOUT1\_VAR\_ADDR. DACOUT1 is refreshed every 100μs (see [DAC outputs](#)).
- DACOUT2 outputs internal variable defined by address in register DACOUT2\_VAR\_ADDR. DACOUT2 is refreshed every 100μs (see [DAC outputs](#)).
- FG pin provides pulses which are proportional to motor speed (see [FG Configuration](#)).
- nFAULT (active low) pin provides fault status in device or motor operation.
- ALARM pin, when enabled using ALARM\_PIN\_EN, provides fault status in device or motor operation as an active high signal. When ALARM pin is enabled, report only faults are reported only on ALARM pin (as logic high) and not reported on nFAULT pin (as logic low). When ALARM pin is enabled, actionable faults are reported on ALARM pin (as logic high) as well as on nFAULT pin (as logic low). When ALARM pin is disabled, it is in Hi-Z state and all faults (actionable and report only) are reported on nFAULT as logic low. ALARM pin should be left floating when unused/disabled.
- SOX pin provides the output of one of the current sense amplifiers.

### Note

1. Internal pull-up resistor (to AVDD) for both FG and nFAULT pins can be enabled by configuring PULLUP\_ENABLE to 1b. Any change to this bit needs to be written to EEPROM followed by a power recycle to take effect. When PULLUP\_ENABLE is set to 1b, no external pull-up resistor should be provided.
2. DIR and BRAKE pins each have an internal pull-down resistor of 100kΩ. When these pins are used, an additional pull-down resistor of 10kΩ may be added externally for additional noise immunity.
3. SPEED pin has an internal pull-down resistor of 1MΩ. In analog speed input mode, a suitable R-C filter can be added externally for reducing noise. In PWM speed input mode, SPEED\_PIN\_GLITCH\_FILTER can be appropriately configured for glitch rejection.

### 6.3.2.2 I<sup>2</sup>C Interface

The MCF8315D supports an I<sup>2</sup>C serial communication interface that allows an external controller to send and receive data. This I<sup>2</sup>C interface lets the external controller to configure the EEPROM and read detailed fault and motor state information. The pull-down strength of the I<sup>2</sup>C pins can be configured using SLEW\_RATE\_I2C\_PINS. The I<sup>2</sup>C bus is a two-wire interface using the SCL and SDA pins which are described as follows :

- The SCL pin is the clock signal input.
- The SDA pin is the data input and output.

### 6.3.3 Step-Down Mixed-Mode Buck Regulator

The MCF8315D has an integrated mixed-mode buck regulator to supply regulated 3.3V or 5V power for an external controller or system voltage rail. Additionally, the buck output can also be configured to 4V or 5.7V for supporting the extra headroom for an external LDO for generating a 3.3V or 5V supplies. The output voltage of the buck is set by BUCK\_SEL.

The buck regulator has a low quiescent current of ~1-2mA during light loads to prolong battery life. The device improves performance during line and load transients by implementing a pulse-frequency current-mode control scheme which requires less output capacitance and simplifies frequency compensation design.

**Table 6-1. Recommended settings for Buck Regulator**

| Buck Mode       | Buck output voltage | AVDD power sequencing            | Max output current from AVDD (I <sub>AVDD_MAX</sub> ) | Max output current from Buck (I <sub>BK_MAX</sub> ) | Buck current limit   |
|-----------------|---------------------|----------------------------------|-------------------------------------------------------|-----------------------------------------------------|----------------------|
| Inductor - 47μH | 3.3V or 4V          | Not supported (BUCK_PS_DIS = 1b) | 20mA                                                  | 170mA                                               | 600mA (BUCK_CL = 0b) |
| Inductor - 47μH | 5V or 5.7V          | Supported (BUCK_PS_DIS = 0b)     | 20mA                                                  | 170mA - I <sub>AVDD</sub>                           | 600mA (BUCK_CL = 0b) |
| Inductor - 22μH | 3.3V or 4V          | Not supported (BUCK_PS_DIS = 1b) | 20mA                                                  | 20mA                                                | 150mA (BUCK_CL = 1b) |
| Inductor - 22μH | 5V or 5.7V          | Supported (BUCK_PS_DIS = 0b)     | 20mA                                                  | 20mA - I <sub>AVDD</sub>                            | 150mA (BUCK_CL = 1b) |
| Resistor - 22Ω  | 3.3V or 4V          | Not supported (BUCK_PS_DIS = 1b) | 20mA                                                  | 10mA                                                | 150mA (BUCK_CL = 1b) |
| Resistor - 22Ω  | 5V or 5.7V          | Supported (BUCK_PS_DIS = 0b)     | 20mA                                                  | 10mA - I <sub>AVDD</sub>                            | 150mA (BUCK_CL = 1b) |

#### 6.3.3.1 Buck in Inductor Mode

The buck regulator in MCF8315D is primarily designed to support low inductance of 47μH and 22μH. A 47μH inductor allows the buck regulator to operate up to 170mA load current support, whereas applications requiring current up to 20mA can use a 22μH inductor which reduces component size.

Figure 6-4 shows the connection of buck regulator in inductor mode.




**Figure 6-4. Buck (Inductor Mode)**

### 6.3.3.2 Buck in Resistor mode

If the external load requirement is less than 10mA, the inductor can be replaced with a resistor. In resistor mode the power is dissipated across the external resistor and the efficiency is lower than buck in inductor mode.

Figure 6-5 shows the connection of buck in resistor mode.




**Figure 6-5. Buck (Resistor Mode)**

### 6.3.3.3 Buck Regulator with External LDO

The buck regulator also supports the voltage requirement to supply an external LDO to generate standard 3.3V or 5V output rail with higher accuracies. The buck output voltage should be configured to 4V or 5.7V to provide extra headroom to support the external LDO for generating 3.3V or 5V rail as shown in Figure 6-6. This allows for a lower-voltage LDO design to save cost and better thermal management due to low drop-out voltage.




**Figure 6-6. Buck Regulator with External LDO**

#### 6.3.3.4 AVDD Power Sequencing from Buck Regulator

The AVDD LDO has an option of using the power supply from mixed mode buck regulator to reduce the device power dissipation. The power sequencing mode allows on-the-fly changeover of AVDD LDO input from DC mains (VM) to buck output ( $V_{BK}$ ) as shown in Figure 6-7. This sequencing can be configured through the BUCK\_PS\_DIS bit. Power sequencing is supported only when buck output voltage is set to 5V or 5.7V.




**Figure 6-7. AVDD Power Sequencing from Mixed Mode Buck Regulator**

### 6.3.3.5 Mixed Mode Buck Operation and Control

The buck regulator implements a pulse frequency modulation (PFM) architecture with peak current mode control. The output voltage of the buck regulator is compared with the internal reference voltage ( $V_{BK\_REF}$ ) which is internally generated depending on the buck output voltage setting (BUCK\_SEL) which constitutes an outer voltage control loop. Depending on the comparator output going high ( $V_{BK} < V_{BK\_REF}$ ) or low ( $V_{BK} > V_{BK\_REF}$ ), the high-side power FET of the buck turns on and off respectively. An independent current control loop monitors the current in high-side power FET ( $I_{BK}$ ) and turns off the high-side FET when the current becomes higher than the buck current limit ( $I_{BK\_CL}$  set by BUCK\_CL) - this implements a current limit control for the buck regulator. Figure 6-8 shows the architecture of the buck and various control/protection loops.




**Figure 6-8. Buck Operation and Control Loops**

### 6.3.4 AVDD Linear Voltage Regulator

A 3.3V linear regulator is integrated into MCF8315D and is available for use by external circuitry. This AVDD LDO regulator is used for powering up the internal circuitry of the device and additionally, this regulator can also provide the supply voltage for a low-power MCU or other external circuitry supporting up to 20mA. The output of the AVDD regulator should be bypassed near the AVDD pin with an X5R or X7R, 1- $\mu$ F, 6.3V ceramic capacitor routed directly back to the adjacent AGND ground pin.

The AVDD nominal, no-load output voltage is 3.3V.




**Figure 6-9. AVDD Linear Regulator Block Diagram**

Use [Equation 1](#) to calculate the power dissipated in the device by the AVDD linear regulator with VM as supply (BUCK\_PS\_DIS = 1b)

$$P = (V_{VM} - V_{AVDD}) \times I_{AVDD} \quad (1)$$

For example, at a  $V_{VM}$  of 24V, drawing 20mA out of AVDD results in power dissipation as shown in [Equation 2](#).

$$P = (24 \text{ V} - 3.3 \text{ V}) \times 20 \text{ mA} = 414 \text{ mW} \quad (2)$$

Use [Equation 3](#) to calculate the power dissipated in the device by the AVDD linear regulator with buck output as supply (BUCK\_PS\_DIS = 0b)

$$P = (V_{FB\_BK} - V_{AVDD}) \times I_{AVDD} \quad (3)$$

### 6.3.5 Charge Pump

Since the output stages use N-channel FETs, the device requires a gate-drive voltage higher than the VM power supply to turn-on the high-side FETs. The MCF8315D integrates a charge-pump circuit that generates a voltage above the VM supply for this purpose.

The charge pump requires two external capacitors ( $C_{CP}$ ,  $C_{FLY}$ ) for operation. See [Figure 6-10](#) and [Section 4](#) for details on these capacitors (value, connection, and so forth).




**Figure 6-10. Charge Pump**

### 6.3.6 Slew Rate Control

An adjustable gate-drive current control is provided for the output stage MOSFETs to achieve configurable slew rate for EMI mitigation. The MOSFET VDS slew rate is a critical factor for optimizing conducted and radiated emissions, total energy and duration of diode recovery spikes and switching voltage transients related to parasitic elements of the PCB. This slew rate is predominantly determined by the control of the internal MOSFET gate current as shown in [Figure 6-11](#).




**Figure 6-11. Slew Rate Circuit Implementation**

The slew rate of each half-bridge can be adjusted through SLEW\_RATE. The slew rate can be configured as either 125V/μs or 200V/μs. The slew rate is calculated by the rise-time and fall-time of the voltage on the OUTx pin as shown in [Figure 6-12](#).




**Figure 6-12. Slew Rate Timings**

### 6.3.7 Cross Conduction (Dead Time)

The device is fully protected against any cross conduction of MOSFETs - during the switching of high-side and low-side MOSFETs, MCF8315D avoids shoot-through events by inserting a dead time ( $t_{dead}$ ). This is implemented by sensing the gate-source voltage (VGS) of the high-side and low-side MOSFETs and ensuring that VGS of high-side MOSFET has dropped below turn-off level before switching on the low-side MOSFET of same half-bridge (or vice-versa) as shown in Figure 6-13 and Figure 6-14. The VGS of the high-side and low-side MOSFETs (VGS\_HS and VGS\_LS) shown in Figure 6-14 are internal signals.




**Figure 6-13. Cross Conduction Protection**




Figure 6-14. Dead Time

### 6.3.8 Motor Control Input Sources

The MCF8315D provides four ways of controlling the motor :

1. **SPEED Control:** In speed control mode, the speed of the motor is controlled using a closed loop PI control according to the input reference.
2. **POWER Control:** In power control mode, the DC input power of the inverter power stage is controlled using a closed loop PI control according to the input reference.
3. **CURRENT Control:** In current control mode, the torque generating current (iq) is controlled using a closed loop PI control according to the input reference.
4. **VOLTAGE Control:** In voltage control mode, the voltage applied to the motor is controlled according to the input reference.

The MCF8315D provides four sources of the reference input for motor control as listed below. The reference input source is configured by SPEED\_MODE.

- PWM input on SPEED/WAKE pin by varying duty cycle of input signal
- Frequency input on SPEED/WAKE pin by varying frequency of input signal
- Analog input on SPEED/WAKE pin by varying amplitude of input signal
- Over I<sup>2</sup>C by configuring DIGITAL\_SPEED\_CTRL register




**Figure 6-15. Multiplexing the Reference Input Command**

The signal path from REF (SPEED/WAKE) pin input (or I<sup>2</sup>C based speed input) to output reference (SPEED\_REF or POWER\_REF or CURRENT\_REF or VOLTAGE\_REF) shown in [Figure 6-15](#).

#### 6.3.8.1 Analog-Mode Motor Control

Analog input based motor control can be configured by setting SPEED\_MODE to 00b. In this mode, the duty command (DUTY\_CMD) varies with the analog voltage input on the SPEED pin ( $V_{\text{SPEED}}$ ). When  $0 \leq V_{\text{SPEED}} \leq V_{\text{EN\_SB}}$ , DUTY\_CMD is set to zero. When  $V_{\text{EX\_SB}} \leq V_{\text{SPEED}} \leq V_{\text{ANA\_FS}}$ , DUTY\_CMD varies linearly with  $V_{\text{SPEED}}$  as shown in [Figure 6-16](#).  $V_{\text{EX\_SB}}$  and  $V_{\text{EN\_SB}}$  are the standby entry and exit thresholds - refer [Section 6.4.1.2](#) for more information on  $V_{\text{EX\_SB}}$  and  $V_{\text{EN\_SB}}$ . When  $V_{\text{SPEED}} > V_{\text{ANA\_FS}}$ , DUTY\_CMD is clamped to 100%.




**Figure 6-16. Analog-Mode Motor Control**

### 6.3.8.2 PWM-Mode Motor Control

PWM based motor control can be configured by setting SPEED\_MODE to 01b. In this mode, the PWM duty cycle applied to the SPEED pin can be varied from 0 to 100% and duty command (DUTY\_CMD) varies linearly with the applied PWM duty cycle. When  $0 \leq \text{Duty}_{\text{SPEED}} \leq \text{Duty}_{\text{EN\_SB}}$ , DUTY\_CMD is set to zero. When  $\text{Duty}_{\text{EX\_SB}} \leq \text{Duty}_{\text{SPEED}} \leq 100\%$ , DUTY\_CMD varies linearly with  $\text{Duty}_{\text{SPEED}}$  as shown in Figure 6-17.  $\text{Duty}_{\text{EX\_SB}}$  and  $\text{Duty}_{\text{EN\_SB}}$  are the standby entry and exit thresholds - refer Section 6.4.1.2 for more information on  $\text{Duty}_{\text{EX\_SB}}$  and  $\text{Duty}_{\text{EN\_SB}}$ . The frequency of the PWM input signal applied to the SPEED pin is defined as  $f_{\text{PWM}}$  and the range for this frequency can be configured through SPEED\_RANGE\_SEL.

#### Note

1.  $f_{\text{PWM}}$  is the frequency of the PWM signal the device can accept at SPEED pin to control motor speed. It does not correspond to the PWM output frequency that is applied to the motor phases. The PWM output frequency can be configured through PWM\_FREQ\_OUT (see Section 6.3.17).
2. SLEEP\_ENTRY\_TIME should be set longer than the off time in PWM signal ( $V_{\text{SPEED}} < V_{\text{IL}}$ ) at lowest duty input. For example, if  $f_{\text{PWM}}$  is 10 kHz and lowest duty input is 2%, SLEEP\_ENTRY\_TIME should be more than 98  $\mu\text{s}$  to ensure there is no unintended sleep/standby entry.




Figure 6-17. PWM-Mode Motor Control

#### 6.3.8.3 I<sup>2</sup>C-based Motor Control

I<sup>2</sup>C based serial interface can be used for motor control by setting SPEED\_MODE to 10b. In this mode, the control command can be written directly into DIGITAL\_SPEED\_CTRL register. The SPEED pin can be used to control the sleep entry and exit - if SPEED pin input is set to a value lower than  $V_{EN\_SL}$  after DIGITAL\_SPEED\_CTRL register has been set to 0b for a time longer than SLEEP\_ENTRY\_TIME, MCF8315D enters sleep state. When SPEED pin  $> V_{EX\_SL}$ , MCF8315D exits sleep state and motor is controlled through DIGITAL\_SPEED\_CTRL register. If  $0 \leq \text{DIGITAL\_SPEED\_CTRL} \leq \text{DIGITAL\_SPEED\_CTRL}_{EN\_SB}$  and SPEED pin  $> V_{EX\_SL}$ , MCF8315D is in standby state. The relationship between DUTY\_CMD and DIGITAL\_SPEED\_CTRL register is shown in Figure 6-18. Refer Section 6.4.1.2 for more information on DIGITAL\_SPEED\_CTRL<sub>EN\\_SB</sub>, EX\_SB and DIGITAL\_SPEED\_CTRL<sub>EN\\_SB</sub>, EN\_SB.




**Figure 6-18. I2C Mode Speed Control**

#### 6.3.8.4 Frequency-Mode Motor Control

Frequency based motor control is configured by setting SPEED\_MODE to 11b. In this mode, duty command varies linearly as a function of the frequency of the square wave input at SPEED/WAKE pin. When  $0 \leq \text{Freq}_{\text{SPEED}} \leq \text{Freq}_{\text{EN\_SB}}$ , DUTY\_CMD is set to zero. When  $\text{Freq}_{\text{EX\_SB}} \leq \text{Freq}_{\text{SPEED}} \leq \text{INPUT\_MAXIMUM\_FREQ}$ , DUTY\_CMD varies linearly with  $\text{Freq}_{\text{SPEED}}$  as shown in Figure 6-19.  $\text{Freq}_{\text{EX\_SB}}$  and  $\text{Freq}_{\text{EN\_SB}}$  are the standby entry and exit thresholds - refer Section 6.4.1.2 for more information on  $\text{Freq}_{\text{EX\_SB}}$  and  $\text{Freq}_{\text{EN\_SB}}$ . Input frequency greater than INPUT\_MAXIMUM\_FREQ clamps the DUTY\_CMD to 100%.




Figure 6-19. Frequency Mode Speed Control

#### 6.3.8.5 Input Reference Profiles

MCF8315D supports three different kinds of input reference profiles (linear, step, forward-reverse) to enable a variety of end-user applications. The different profiles can be configured through REF\_PROFILE\_CONFIG and the input reference can be a speed, power, current or voltage command as configured by INPUT\_REFERENCE\_MODE.

In speed reference mode, the profiler output REF\_X corresponds to percentage of MAX\_SPEED as shown in Equation 4. In power reference mode, the profiler output REF\_X corresponds to percentage of MAX\_POWER as shown in Equation 5. In current reference mode, the profiler output REF\_X corresponds to percentage of ILIMIT as shown in Equation 6. In voltage reference mode, REF\_X corresponds to the modulation index applied to the motor.

$$\text{SPEED\_REF (Hz)} = (\text{REF\_X}/255) \times \text{MAX\_SPEED (Hz)} \quad (4)$$

$$\text{POWER\_REF (W)} = (\text{REF\_X}/255) \times \text{MAX\_POWER (W)} \quad (5)$$

$$\text{CURRENT\_REF (A)} = (\text{REF\_X}/255) \times \text{ILIMIT (A)} \quad (6)$$

When REF\_PROFILE\_CONFIG is set to 00b, the input reference is set by the duty command (DUTY\_CMD) as explained in Section 6.3.8.5.5.

##### 6.3.8.5.1 Linear Control Profiles

#### Note

For all three profiles (linear, step, forward/reverse),

- When MCF8315D is configured as a sleep device, a zero input reference (0V in analog mode, 0% duty in PWM mode, DIGITAL\_SPEED\_CTRL = 0b in I<sup>2</sup>C mode or 0Hz in frequency mode) will stop the motor.
- When MCF8315D is configured as a standby device, a zero input reference will result in motor operating at reference level (speed, power, current or voltage) set by REF\_OFF1.




**Figure 6-20. Linear Control Profiles**

Linear control profiles can be configured by setting REF\_PROFILE\_CONFIG to 01b. Linear profiles feature input control references which change linearly between REF\_CLAMP1 and REF\_CLAMP2 with different slopes which can be set by configuring DUTY\_x and REF\_x combination.

- DUTY\_OFF1 configures the duty command below which the reference will be REF\_OFF1.
- DUTY\_OFF1 and DUTY\_ON1 configures a hysteresis around reference control input REF\_CLAMP1 and REF\_OFF1 as shown in [Figure 6-20](#).
- DUTY\_CLAMP1 configures the duty command till which reference will be constant with a value REF\_CLAMP1. DUTY\_CLAMP1 can be placed anywhere between DUTY\_OFF1 and DUTY\_A.
- DUTY\_A configures the duty command for reference REF\_A. The reference changes from REF\_CLAMP1 to REF\_A linearly between DUTY\_CLAMP1 and DUTY\_A. DUTY\_A to DUTY\_E has to be in the same order as shown in [Figure 6-20](#).
- DUTY\_B configures the duty command for reference REF\_B. The reference changes linearly between DUTY\_A and DUTY\_B.
- DUTY\_C configures the duty command for reference REF\_C. The reference changes linearly between DUTY\_B and DUTY\_C.
- DUTY\_D configures the duty command for reference REF\_D. The reference changes linearly between DUTY\_C and DUTY\_D.
- DUTY\_E configures the duty command for reference REF\_E. The reference changes linearly between DUTY\_D and DUTY\_E.
- DUTY\_CLAMP2 configures the duty command above which the reference will be constant at REF\_CLAMP2. REF\_CLAMP2 configures this constant reference between DUTY\_CLAMP2 and DUTY\_OFF2. The reference changes linearly between DUTY\_E and DUTY\_CLAMP2. DUTY\_CLAMP2 can be placed anywhere between DUTY\_E and DUTY\_OFF2.

- DUTY\_OFF2 and DUTY\_ON2 configures a hysteresis around reference control input REF\_CLAMP2 and REF\_OFF2 as shown in [Figure 6-20](#).
- DUTY\_OFF2 configures the duty command above which the reference will change from REF\_CLAMP2 to REF\_OFF2.

#### 6.3.8.5.2 Staircase Control Profiles




**Figure 6-21. Staircase Control Profiles**

Staircase control profiles can be configured by setting REF\_PROFILE\_CONFIG to 10b. Staircase profiles feature input control reference changes in steps between REF\_CLAMP1 and REF\_CLAMP2, by configuring DUTY\_x and REF\_x.

- DUTY\_OFF1 configures the duty command below which the reference will be REF\_OFF1.
- DUTY\_OFF1 and DUTY\_ON1 configures a hysteresis around reference control input REF\_CLAMP1 and REF\_OFF1 as shown in [Figure 6-21](#).
- DUTY\_CLAMP1 configures the duty command till which reference will be constant. REF\_CLAMP1 configures this constant reference between DUTY\_OFF1 and DUTY\_CLAMP1. DUTY\_CLAMP1 can be placed anywhere between DUTY\_OFF1 and DUTY\_A.
- DUTY\_A configures the duty command for reference REF\_A. There is a step change in reference from REF\_CLAMP1 to REF\_A at DUTY\_CLAMP1. DUTY\_A to DUTY\_E has to be in the same order as shown in [Figure 6-21](#).
- DUTY\_B configures the duty command for reference REF\_B. There is a step change in reference from REF\_A to REF\_B at DUTY\_A.
- DUTY\_C configures the duty command for reference REF\_C. There is a step change in reference from REF\_B to REF\_C at DUTY\_B.
- DUTY\_D configures the duty command for reference REF\_D. There is a step change in reference from REF\_C to REF\_D at DUTY\_C.

- DUTY\_E configures the duty command for reference REF\_E. There is a step change in reference from REF\_D to REF\_E at DUTY\_D.
- DUTY\_CLAMP2 configures the duty command above which the reference will be constant at REF\_CLAMP2. REF\_CLAMP2 configures this constant reference between DUTY\_CLAMP2 and DUTY\_OFF2. There is a step change in reference from REF\_E to REF\_CLAMP2 at DUTY\_E. DUTY\_CLAMP2 can be placed anywhere between DUTY\_E and DUTY\_OFF2.
- DUTY\_OFF2 and DUTY\_ON2 configures a hysteresis around reference control input REF\_CLAMP2 and REF\_OFF2 as shown in [Figure 6-21](#).
- DUTY\_OFF2 configures the duty command above which the reference will change from REF\_CLAMP2 to REF\_OFF2.
- DUTY\_HYS configures the hysteresis during every step change at DUTY\_CLAMP1, DUTY\_A to DUTY\_E.

### 6.3.8.5.3 Forward-Reverse Profiles




**Figure 6-22. Forward Reverse Control Profiles**

Forward-Reverse control profiles can be configured by setting REF\_PROFILE\_CONFIG to 11b. Forward-Reverse profiles feature direction change through adjusting the duty command. DUTY\_C configures duty command at which the direction will be changed. The Forward-Reverse speed profile can be used to eliminate the separate signal used to control the motor direction.

---

**Note**

The direction change functionality through DIR pin and DIR\_INPUT bits are disabled in forward reverse profile mode.

---

- DUTY\_OFF1 configures the duty command below which the reference will be REF\_OFF1.
- DUTY\_OFF1 and DUTY\_ON1 configures a hysteresis around reference control input REF\_CLAMP1 and REF\_OFF1 as shown in [Figure 6-22](#).
- DUTY\_CLAMP1 configures the duty command till which reference will be constant. REF\_CLAMP1 configures this constant reference between DUTY\_OFF1 and DUTY\_CLAMP1. DUTY\_CLAMP1 can be placed anywhere between DUTY\_OFF1 and DUTY\_A.
- DUTY\_A configures the duty command for reference REF\_A. The reference changes linearly between DUTY\_CLAMP1 and DUTY\_A. DUTY\_A to DUTY\_E has to be in the same order as shown in [Figure 6-22](#).
- DUTY\_B configures the duty command above which MCF8315D will be in off state. The reference remains constant at REF\_A between DUTY\_A and DUTY\_B.
- DUTY\_C configures the duty command at which the direction is changed
- DUTY\_D configures the duty command above which the MCF8315D will be in running state in the reverse direction. REF\_D configures constant reference between DUTY\_D and DUTY\_E.
- DUTY\_E configures the duty command above which reference changes linearly between DUTY\_E and DUTY\_CLAMP2.
- DUTY\_CLAMP2 configures the duty command above which the reference will be constant at REF\_CLAMP2. REF\_CLAMP2 configures this constant reference between DUTY\_CLAMP2 and DUTY\_OFF2. DUTY\_CLAMP2 can be placed anywhere between DUTY\_E and DUTY\_OFF2.
- DUTY\_OFF2 and DUTY\_ON2 configures a hysteresis around reference control input REF\_CLAMP2 and REF\_OFF2 as shown in [Figure 6-22](#).
- DUTY\_OFF2 configures the duty command above which the reference changes in the reverse direction from REF\_CLAMP2 to REF\_OFF2.
- DUTY\_HYS configures the hysteresis during step change at DUTY\_B and DUTY\_D.

#### **6.3.8.5.4 Multi-Reference Mode Operation**

---

**Note**

The multi-reference (mixed) mode operation is available only when REF\_PROFILE\_CONFIG is set 01b (linear profile) or 10b (staircase profile).

---

MCF8315D provides the option of multi-reference mode operation when VOLTAGE\_MODE\_CONFIG is set to 01b or 10b. When VOLTAGE\_MODE\_CONFIG is set to 01b, MCF8315D operates in speed, current or power reference mode till DUTY\_CMD reaches DUTY\_C and then switches to voltage reference mode from DUTY\_C till 100% duty command as shown in [Figure 6-23](#).




**Figure 6-23. Multi-Reference Mode Operation (when VOLTAGE\_MODE\_CONFIG = 01b)**

Conversely, MCF8315D operates in voltage reference mode till DUTY\_C and then switches to speed, current or power reference from DUTY\_C till 100% duty command when VOLTAGE\_MODE\_CONFIG is set to 10b as shown in Figure 6-24.




**Figure 6-24. Multi-Reference Mode Operation (when VOLTAGE\_MODE\_CONFIG = 10b)**

#### 6.3.8.5.5 Input Reference Transfer Function without Profiler

The input reference can be a speed, power, current or voltage command as configured by INPUT\_REFERENCE\_MODE.

### Note

- In this mode, if MIN\_DUTY < REF\_CLAMP1, the minimum reference is set by REF\_CLAMP1 and not MIN\_DUTY. For example, if MIN\_DUTY is set to 1% and REF\_CLAMP1 set to 5%, the minimum reference is REF\_CLAMP1 x MAX\_REFERENCE. MAX\_REFERENCE can be MAX\_SPEED, MAX\_POWER, ILIMIT or 100% depending on input reference mode.
- Set MIN\_DUTY > REF\_CLAMP1 for using MIN\_DUTY to set the minimum reference.

### Speed Reference Transfer Function




**Figure 6-25. Speed Reference Transfer Function**

Figure 6-25 shows the relationship between DUTY\_CMD and SPEED\_REF. MAX\_SPEED sets the SPEED\_REF at DUTY\_CMD of 100%. MIN\_DUTY sets the minimum SPEED\_REF (MIN\_DUTY x MAX\_SPEED). If MAX\_SPEED is set to 0-Hz, SPEED\_REF is clamped to zero (irrespective of DUTY\_CMD) and motor is in stopped state.

### Power Reference Transfer Function




**Figure 6-26. Power Reference Transfer Function**

Figure 6-26 shows the relationship between DUTY\_CMD and POWER\_REF. MAX\_POWER sets the POWER\_REF at DUTY\_CMD of 100%. MIN\_DUTY sets the minimum POWER\_REF (MIN\_DUTY x

MAX\_POWER). If MAX\_POWER is set to 0-W, POWER\_REF is clamped to zero (irrespective of DUTY\_CMD) and motor is in stopped state.

### Voltage Reference Transfer Function




**Figure 6-27. Voltage Reference Transfer Function**

In voltage reference mode, the phase voltage applied to motor is proportional to the DUTY\_CMD (from MIN\_DUTY to 100%) as shown in Figure 6-27. For DUTY\_CMD less than MIN\_DUTY, the applied voltage to motor is clamped to zero.

### Current Input Transfer Function




**Figure 6-28. Current Reference Transfer Function**

Figure 6-28 shows the relationship between DUTY\_CMD and CURRENT\_REF. ILIMIT sets the CURRENT\_REF at DUTY\_CMD of 100%. MIN\_DUTY sets the minimum CURRENT\_REF (MIN\_DUTY x ILIMIT).

#### 6.3.9 Starting the Motor Under Different Initial Conditions

The motor can be in one of three states when MCF8315D begins the start-up process. The motor may be stationary, spinning in the forward direction, or spinning in the reverse direction. The MCF8315D includes a number of features to allow for reliable motor start-up under all of these conditions. Figure 6-29 shows the motor start-up flow for each of the three initial motor states.




**Figure 6-29. Starting the motor under different initial conditions**

**Note**

"Forward" means "spinning in the same direction as the commanded direction", and "Reverse" means "spinning in the opposite direction as the commanded direction".

#### 6.3.9.1 Case 1 – Motor is Stationary

If the motor is stationary, the commutation must be initialized to be in phase with the position of the motor. The MCF8315D provides various options to initialize the commutation logic to the motor position and reliably start the motor.

- The align and double align techniques force the motor into alignment by applying a voltage across particular motor phases to force the motor to rotate in alignment with this phase.
- Initial position detect (IPD) determines the position of the motor based on the deterministic inductance variation, which is often present in BLDC motors.
- The slow first cycle method starts the motor by applying a low frequency cycle to align the rotor position to the applied commutation by the end of one electrical rotation.

MCF8315D also provides a configurable brake option to ensure the motor is stationary before initiating one of the above start-up methods. Device enters open loop acceleration after going through the configured start-up method.

#### 6.3.9.2 Case 2 – Motor is Spinning in the Forward Direction

If the motor is spinning forward (same direction as the commanded direction) with sufficient speed (BEMF), the MCF8315D resynchronizes with the spinning motor and continues commutation by going directly to closed loop operation. If the motor speed is too low for closed loop operation, MCF8315D enters open loop operation to accelerate the motor till it reaches sufficient speed to enter closed loop operation. By resynchronizing to the spinning motor, the user achieves the fastest possible start-up time for this initial condition. This resynchronization feature can be enabled or disabled through RESYNC\_EN. If resynchronization is disabled, the MCF8315D can be configured to wait for the motor to coast to a stop and/or apply a brake. After the motor has stopped spinning, the motor start-up sequence proceeds as in Case 1, considering the motor is stationary.

#### 6.3.9.3 Case 3 – Motor is Spinning in the Reverse Direction

If the motor is spinning in the reverse direction (the opposite direction as the commanded direction), the MCF8315D provides several methods to change the direction and drive the motor to the target speed reference in the commanded direction.

The reverse drive method allows the motor to be driven so that it decelerates through zero speed.

If reverse drive is not enabled, then the MCF8315D can be configured to wait for the motor to coast to a stop and/or apply a brake. After the motor has stopped spinning, the motor start-up sequence proceeds as in Case 1, considering the motor is stationary.

---

#### Note

Take care when using the reverse drive or brake feature to ensure that the current is limited to an acceptable level and that the supply voltage does not surge as a result of energy being returned to the power supply.

---

### 6.3.10 Motor Start Sequence (MSS)

Figure 6-30 shows the motor-start sequence implemented in the MCF8315D device.




**Figure 6-30. Motor Start Sequence**




**Figure 6-31. Brake Routine**

**Power-On State**

This is the initial state of the Motor Start Sequence (MSS) when MCF8315D is powered on. In this state, MCF8315D configures the peripherals, initializes the algorithm parameters from EEPROM and prepares for driving the motor.

**Sleep/Standby**

In this state, SPEED\_REF is set to zero and MCF8315D is either in sleep or standby mode depending on DEV\_MODE and SPEED/WAKE pin voltage.

**SPEED\_REF > 0 Judgement**

When SPEED\_REF is set to greater than zero, MCF8315D exits the sleep/standby state and proceeds to ISD\_EN judgement. As long as SPEED\_REF is set to zero, MCF8315D stays in sleep/standby state.

**Direction Change Command Judgement**

When a direction change command is received, MCF8315D proceeds to DIR\_CHANGE\_MODE judgement.

**DIR\_CHANGE\_MODE Judgement**

If DIR\_CHANGE\_MODE is set to 0b, MCF8315D initiates direction change by proceeding to ISD\_EN judgement. Instead, if DIR\_CHANGE\_MODE is set to 1b, MCF8315D initiates direction change by proceeding to Speed > OPN\_CL\_HANDOFF\_THR judgement.

**ISD\_EN Judgement**

MCF8315D checks to see if the initial speed detect (ISD) function is enabled (ISD\_EN = 1b). If ISD is enabled, MSS proceeds to the BEMF < STAT\_DETECT\_THR judgement. Instead, if ISD is disabled, the MSS proceeds directly to the BRAKE\_EN judgement.

**BEMF < STAT\_DETECT\_THR Judgement**

ISD determines the initial condition (speed, angle, direction of spin) of the motor (see [Section 6.3.10.1](#)). If motor is deemed to be stationary (BEMF < STAT\_DETECT\_THR), the MSS proceeds to BRAKE\_EN judgement. If the motor is not stationary, MSS proceeds to verify the direction of spin.

**Direction of spin Judgement**

The MSS determines whether the motor is spinning in the forward or the reverse direction. If the motor is spinning in the forward direction, the

|                                                                             |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                        |
|-----------------------------------------------------------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
|                                                                             | MCF8315D proceeds to the RESYNC_EN judgement. If the motor is spinning in the reverse direction, the MSS proceeds to the RVS_DR_EN judgement.                                                                                                                                                                                                                                                                                                                                                                          |
| <b>RESYNC_EN Judgement</b>                                                  | If RESYNC_EN is set to 1b, MCF8315D proceeds to Speed > Open to Closed Loop Handoff (Resync) judgement. If RESYNC_EN is set to 0b, MSS proceeds to HIZ_EN judgement.                                                                                                                                                                                                                                                                                                                                                   |
| <b>Speed &gt; FW_DRV_RESYN_THR Judgement</b>                                | If motor speed > FW_DRV_RESYN_THR, MCF8315D uses the speed and position information from the ISD to transition to the closed loop state (see <a href="#">Section 6.3.10.2</a> ) directly. If motor speed < FW_DRV_RESYN_THR, MCF8315D transitions to open loop state.                                                                                                                                                                                                                                                  |
| <b>RVS_DR_EN Judgement</b>                                                  | The MSS checks to see if the reverse drive function is enabled (RVS_DR_EN = 1b). If it is enabled, the MSS transitions to check speed of the motor in reverse direction. If the reverse drive function is not enabled (RVS_DR_EN = 0b), the MSS advances to the HIZ_EN judgement.                                                                                                                                                                                                                                      |
| <b>Speed &gt; OPN_CL_HANDOFF_THR Judgement</b>                              | The MSS checks to see if the reverse speed is high enough for MCF8315D to decelerate in closed loop. Till the speed (in reverse direction) is above OL_CL_HANDOFF_THR, MSS stays in closed loop deceleration. If speed is below OPN_CL_HANDOFF_THR, then the MSS transitions to open loop deceleration.                                                                                                                                                                                                                |
| <b>Reverse Closed Loop, Open Loop Deceleration and Zero Speed Crossover</b> | The MCF8315D resynchronizes in the reverse direction, decelerates the motor in closed loop till motor speed falls below the handoff threshold. (see <a href="#">Reverse Drive</a> ). When motor speed in reverse direction is too low, the MCF8315D switches to open-loop, decelerates the motor in open-loop, crosses zero speed, and accelerates in the forward direction in open-loop before entering closed loop operation after motor speed is sufficiently high.                                                 |
| <b>HIZ_EN Judgement</b>                                                     | The MSS checks to determine whether the coast (Hi-Z) function is enabled (HIZ_EN = 1b). If the coast function is enabled (HIZ_EN = 1b), the MSS advances to the coast routine. If the coast function is disabled (HIZ_EN = 0b), the MSS advances to the BRAKE_EN judgement.                                                                                                                                                                                                                                            |
| <b>Coast (Hi-Z) Routine</b>                                                 | The device coasts the motor by turning OFF all six MOSFETs for a certain time configured by HIZ_TIME.                                                                                                                                                                                                                                                                                                                                                                                                                  |
| <b>BRAKE_EN Judgement</b>                                                   | The MSS checks to determine whether the brake function is enabled (BRAKE_EN = 1b). If the brake function is enabled (BRAKE_EN = 1b), the MSS advances to the brake routine. If the brake function is disabled (BRAKE_EN = 0b), the MSS advances to the motor start-up state (see <a href="#">Section 6.3.10.4</a> ).                                                                                                                                                                                                   |
| <b>Brake Routine</b>                                                        | MCF8315D implements either a time based brake (duration configured by BRK_TIME) or a current based brake (brake applied till phase currents < BRK_CURR_THR for BRAKE_CURRENT_PERSIST) based on BRK_CONFIG. Current based brake has a timeout to ensure brake state ends in case phase currents do not drop below BRK_CURR_THR within BRK_TIME. Time based brake can be applied either using high-side or low-side MOSFETs based on BRK_MODE configuration. Current based brake is applied using low-side MOSFETs only. |
| <b>Closed Loop State</b>                                                    | In this state, the MCF8315D drives the motor with sensorless FOC based on rotor angle estimation.                                                                                                                                                                                                                                                                                                                                                                                                                      |

#### 6.3.10.1 Initial Speed Detect (ISD)

The ISD function is used to identify the initial condition of the motor and is enabled by setting ISD\_EN to 1b. The initial speed, position and direction is determined by sensing the three phase voltages. ISD can be disabled by setting ISD\_EN to 0b. If the function is disabled (ISD\_EN set to 0b), the MCF8315D does not perform the initial speed detect function and proceeds to check if the brake routine (BRAKE\_EN) is enabled.

### 6.3.10.2 Motor Resynchronization

The motor resynchronization function works when the ISD and resynchronization functions are both enabled and the device determines that the initial state of the motor is spinning in the forward direction (same direction as the commanded direction). The speed and position information measured during ISD are used to initialize the drive state of the MCF8315D, which can transition directly into closed loop (or open loop if motor speed is not sufficient for closed loop operation) state without needing to stop the motor. In the MCF8315D, motor resynchronization can be enabled/disabled through RESYNC\_EN bit. If motor resynchronization is disabled, the device proceeds to check if the motor coast (Hi-Z) routine is enabled.

### 6.3.10.3 Reverse Drive

The MCF8315D uses the reverse drive function to change the direction of the motor rotation when ISD\_EN and RVS\_DR\_EN are both set to 1b and the ISD determines the motor spin direction to be opposite to that of the commanded direction. Reverse drive includes synchronizing with the motor speed in the reverse direction, reverse decelerating the motor through zero speed, changing direction, and accelerating in open loop in forward (or commanded) direction until the device transitions into closed loop in forward direction (see [Figure 6-32](#)). MCF8315D provides the option of using the forward direction parameters or a separate set of reverse drive parameters by configuring REV\_DRV\_CONFIG.




**Figure 6-32. Reverse Drive Function**

#### 6.3.10.3.1 Reverse Drive Tuning

MCF8315D provides the option of tuning the open to closed loop handoff threshold, open loop acceleration (and deceleration) rates and open loop current limit in reverse drive to values different to those used in forward drive operation; the reverse drive specific parameters can be used by setting REV\_DRV\_CONFIG to 1b. If REV\_DRV\_CONFIG is set to 0b, MCF8315D uses the equivalent parameters configured for forward drive operation during the reverse drive operation too.

The speed at which motor would enter the open loop in reverse direction can be configured using REV\_DRV\_HANDOFF\_THR. For a smooth transition without jerks or loss of synchronism, user can configure an appropriate current limit when the motor is spinning in open loop during speed reversal using REV\_DRV\_OPEN\_LOOP\_CURRENT. The open loop acceleration rates for the forward direction during speed reversal are defined using REV\_DRV\_OPEN\_LOOP\_ACCEL\_A1 and REV\_DRV\_OPEN\_LOOP\_ACCEL\_A2. The reverse drive open loop deceleration rate, when the motor is decelerating in the opposite direction

to zero speed, can be configured as a percentage of reverse drive open loop acceleration using REV\_DRV\_OPEN\_LOOP\_DEC.

#### **6.3.10.4 Motor Start-up**

There are different options available for motor start-up from a stationary position and these options can be configured by MTR\_STARTUP. In align and double align mode, the motor is aligned to a known position by injecting a DC current. In IPD mode, the rotor position is estimated by applying 6 different high-frequency pulses. In slow first cycle mode, the motor is started by applying a low frequency cycle.

##### **6.3.10.4.1 Align**

Align is enabled by configuring MTR\_STARTUP to 00b. The MCF8315D aligns the motor by injecting a DC current through a particular phase pattern for a certain time configured by ALIGN\_TIME. The phase pattern during align is generated based on ALIGN\_ANGLE. In the MCF8315D, the current limit during align is configured through ALIGN\_OR\_SLOW\_CURRENT\_ILIMIT.

A fast change in the phase current may result in a sudden change in the driving torque and this could result in acoustic noise. To avoid this, the MCF8315D ramps up the current from 0 to the current limit at a configurable ramp rate set by ALIGN\_SLOW\_RAMP\_RATE. At the end of align routine, the motor will be aligned at the known position.

##### **6.3.10.4.2 Double Align**

Double align is enabled by configuring MTR\_STARTUP to 01b. Single align is not reliable when the initial position of the rotor is 180° out of phase with the applied phase pattern. In this case, it is possible to have start-up failures using single align. In order to improve the reliability of align based start-up, the MCF8315D provides the option of double align start-up. In double align start-up, MCF8315D uses a phase pattern for the second align that is 90° ahead of the first align phase pattern. In double align, relevant parameters like align time, current limit, ramp rate are the same as in the case of single align - two different phase patterns are applied in succession with the same parameters to ensure that the motor will be aligned to a known position irrespective of initial rotor position.

##### **6.3.10.4.3 Initial Position Detection (IPD)**

Initial Position Detection (IPD) can be enabled by configuring MTR\_STARTUP to 10b. In IPD, inductive sense method is used to determine the initial position of the motor using the spatial variation in the motor inductance.

Align or double align may result in the motor spinning in the reverse direction before starting open loop acceleration. IPD can be used in such applications where reverse rotation of the motor is unacceptable. IPD does not wait for the motor to align with the commutation and therefore can allow for a faster motor start-up sequence. IPD works well when the inductance of the motor varies as a function of position. IPD works by pulsing current in to the motor and hence can generate acoustics which must be taken into account when determining the best start-up method for a particular application.

##### **6.3.10.4.3.1 IPD Operation**

IPD operates by sequentially applying six different phase patterns according to the following sequence: BC-> CB-> AB-> BA-> CA-> AC (see [Figure 6-33](#)). When the current reaches the threshold configured by IPD\_CURR\_THR, the MCF8315D stops driving the particular phase pattern and measures the time taken to reach the current threshold from when the particular phase pattern was applied. Thus, the time taken to reach IPD\_CURR\_THR is measured for all six phase patterns - this time varies as a function of the inductance in the motor windings. The state with the shortest time represents the state with the minimum inductance. The minimum inductance is because of the alignment of the north pole of the motor with this particular driving state.




Figure 6-33. IPD Function

#### 6.3.10.4.3.2 IPD Release Mode

Two modes are available for configuring the way the MCF8315D stops driving the motor when the current threshold is reached. The recirculate (or brake) mode is selected if `IPD_RLS_MODE = 0b`. In this configuration, the low-side (LSC) MOSFET remains ON to allow the current to recirculate between the MOSFET (LSC) and body diode (LSA) (see Figure 6-34). Hi-Z mode is selected if `IPD_RLS_MODE = 1b`. In Hi-Z mode, both the high-side (HSA) and low-side (LSC) MOSFETs are turned OFF and the current recirculates through the body diodes back to the power supply (see Figure 6-35).

In the Hi-Z mode, the phase current has a faster settle-down time, but that can result in a voltage increase on  $V_M$ . The user must manage this with an appropriate selection of either a clamp circuit or by providing sufficient capacitance between  $V_M$  and PGND to absorb the energy. If the voltage surge cannot be contained or if it is unacceptable for the application, recirculate mode must be used. When using the recirculate mode, select the `IPD_CLK_FREQ` appropriately to give the current in the motor windings enough time to decay to 0-A before the next IPD phase pattern is applied.




Figure 6-34. IPD Release Mode - Brake (0b)




**Figure 6-35. IPD Release Mode - Tristate (1b)**

#### 6.3.10.4.3 IPD Advance Angle

After the initial position is detected, the MCF8315D begins driving the motor in open loop at an angle specified by IPD\_ADV\_ANGLE.

Advancing the drive angle anywhere from 0° to 180° results in positive torque. Advancing the drive angle by 90° results in maximum initial torque. Applying maximum initial torque could result in uneven acceleration to the rotor. Select the IPD\_ADV\_ANGLE to allow for smooth acceleration in the application (see [Figure 6-36](#)).




**Figure 6-36. IPD Advance Angle**

#### 6.3.10.4.4 Slow First Cycle Startup

Slow First Cycle start-up is enabled by configuring MTR\_STARTUP to 11b. In slow first cycle start-up, the MCF8315D starts motor commutation at a frequency defined by SLOW\_FIRST\_CYCLE\_FREQ. The frequency configured is used only for first cycle, and then the motor commutation follows acceleration profile configured by open loop acceleration coefficients A1 and A2. The slow first cycle frequency has to be configured to be slow enough to allow motor to synchronize with the commutation sequence. This mode is useful when fast startup is desired as it significantly reduces the align time.

#### 6.3.10.4.5 Open Loop

Upon completing the motor position initialization with either align, double align, IPD or slow first cycle, the MCF8315D begins to accelerate the motor in open loop. In MCF8315D, the current limit in open loop is set by OL\_ILIMIT and the speed is increased using this current. In open loop, the control PI loops for  $I_q$  and  $I_d$  actively control the currents. The angle during open loop is provided from the ramp generator as shown in [Figure 6-37](#).




**Figure 6-37. Open Loop**

The function of the open-loop operation is to drive the motor to a speed at which the motor generates sufficient BEMF to allow the back-EMF observer to accurately detect the position of the rotor. The motor is accelerated in open loop and speed at any given time is determined by Equation 7. In MCF8315D, open loop acceleration coefficients, A1 and A2 are configured through OL\_ACC\_A1 and OL\_ACC\_A2 respectively.

$$\text{Speed}(t) = A1 * t + 0.5 * A2 * t^2 \quad (7)$$

#### 6.3.10.4.6 Transition from Open to Closed Loop

Once the motor has reached a sufficient speed for the back-EMF observer to estimate the angle and speed of the motor, the MCF8315D transitions into closed loop state. This handoff speed is automatically determined based on the measured back-EMF and motor speed. Users also have an option to manually set the handoff speed by configuring OPN\_CL\_HANDOFF\_THR and setting AUTO\_HANDOFF\_EN to 0b. In order to have smooth transition and avoid speed transients, the theta error ( $\theta_{\text{gen}} - \theta_{\text{est}}$ ) is decreased linearly after transition. The ramp rate of theta error reduction can be configured using THETA\_ERROR\_RAMP\_RATE. If the current limit set during the open loop is high and if it is not reduced before transition to closed loop, the motor speed may momentarily rise to higher values than SPEED\_REF after transition into closed loop. In order to avoid such speed variations, configure the IQ\_RAMP\_EN to 1b, so that  $i_{q\_ref}$  decreases prior to transition into closed loop. However if the final speed reference (SPEED\_REF) is more than two times the open loop to closed loop hand off speed (OPN\_CL\_HANDOFF\_THR), then  $i_{q\_ref}$  is not decreased independent of the IQ\_RAMP\_EN setting, to enable faster motor acceleration.

After hand off to closed loop at a sufficient speed, there could be still some theta error, as the estimators may not be fully aligned. A slow acceleration can be used after the open loop to closed loop transition, ensuring that the theta error reduces to zero. The slow acceleration can be configured using CL\_SLOW\_ACC.

Figure 6-38 shows the control sequence in open to closed loop transition. The current  $i_{q\_ref}$  reduces to a lower value in current decay region, if IQ\_RAMP\_EN is set to 1b. If IQ\_RAMP\_EN is set to 0b, then the current decay region will not be present in the transition sequence.





**Figure 6-38. Control Sequence in Open to Closed Loop Transition**



### 6.3.11 Closed Loop Operation

The MCF8315D drives the motor using Field Oriented Control (FOC) as shown in Figure 6-40. In closed loop operation, the motor angle ( $\theta_{est}$ ) and speed (SPEED\_EST) are estimated using the back-EMF observer. The speed, power or current regulation is achieved using PI control loops.




**Figure 6-40. Closed Loop FOC Control**

#### 6.3.11.1 Closed Loop Acceleration/Deceleration Slew Rate

During closed loop acceleration/deceleration, MCF8315D provides the option of configuring the slew rate of the reference input. This allows for a linear change in reference input (speed or power or current or modulation index) even when there is a step change in reference input (from Analog, PWM, Frequency or I<sup>2</sup>C) as seen in Figure 6-41. This slew rate can be configured so as to prevent sudden changes in the torque applied to the motor which could result in acoustic noise. The closed loop acceleration/deceleration slew rate parameter, **CL\_ACC/CL\_DEC**, sets the slew rate of the reference during acceleration and deceleration respectively.




**Figure 6-41. Closed Loop Acceleration/Deceleration Slew Rate**

### 6.3.11.2 Speed PI Control

The integrated speed control loop helps maintain a constant speed over varying operating conditions. The  $K_p$  and  $K_i$  coefficients are configured through SPD\_LOOP\_KP and SPD\_LOOP\_KI. The output of the speed loop is used to generate the current reference for torque control ( $I_{q\_ref}$ ). The output of the speed loop is limited to implement a current limit. The current limit is set by configuring ILIMIT. When output of the speed loop saturates, the integrator is disabled to prevent integral wind-up.

SPEED\_REF\_SLEW is derived from the duty command input, speed profiles and closed loop acceleration/deceleration rates configured by the user and SPEED\_EST is the estimated speed from the back-EMF observer.




**Figure 6-42. Speed PI Control**

### 6.3.11.3 Current PI Control

The MCF8315D has two PI controllers, one each for  $I_d$  and  $I_q$  to control flux and torque separately.  $K_p$  and  $K_i$  coefficients are the same for both PI controllers and are configured through CURR\_LOOP\_KP and CURR\_LOOP\_KI. The outputs of the current control loops are used to generate voltage signals  $V_d$  and  $V_q$  to be

applied to the motor. The outputs of the current loops are clamped to supply voltage  $V_M$ .  $I_d$  current PI loop is executed first and output of  $I_d$  current PI loop  $V_d$  is checked for saturation. When the output of the current loop saturates, the integration is disabled to prevent integral wind-up.




**Figure 6-43.  $I_d$  Current PI Control**




**Figure 6-44.  $I_q$  Current PI Control**

#### 6.3.11.4 Power Control Mode

MCF8315D provides an option of regulating the (input DC) power instead of motor speed for a closed loop power control. Input power regulation (instead of motor speed) mode is selected by setting INPUT\_REFERENCE\_MODE to 01b. The maximum power that MCF8315D can draw from the DC input supply is set by MAX\_POWER. The  $K_p$  and  $K_i$  coefficients for power loop are configured through SPD\_LOOP\_KP and SPD\_LOOP\_KI.

$$POWER REF(W) = DUTY CMD \times Maximum Power (W) \quad (8)$$




**Figure 6-45. Closed Loop Power Control**

### 6.3.11.5 Current (Torque) Control Mode

MCF8315D provides the option of controlling the motor q- and d-axis currents directly by setting INPUT\_REFERENCE\_MODE to 10b. In this mode, the q- and d-axis current references,  $I_{q\_ref}$  and  $I_{d\_ref}$  is directly set by the duty cycle input, DUTY\_CMD, ILIMIT and LEAD\_ANGLE instead of the speed PI loop output as shown in Figure 6-40. Thus, this mode enables torque control through setting ILIMIT and hence can be used for torque mode operation.

### 6.3.11.6 Modulation Index Control

MCF8315D provides voltage control mode, selected by setting INPUT\_REFERENCE\_MODE to 11b. The closed loop speed control, power control and current control ( $i_q$  and  $i_d$ ) are disabled in this mode. The applied  $V_q$  and  $V_d$  are controlled directly using the user defined modulation index reference voltage (VOLTAGE REF) and the lead angle setting. The VOLTAGE REF varies from MIN\_DUTY to 100%.




**Figure 6-46. Open Loop Voltage Control**

### Note

MCF8315D does not support recirculation stop mode during modulation index control mode.

### 6.3.11.7 Overmodulation

MCF8315D provides an overmodulation option to operate the motor at a higher speed at the same VM voltage by increasing the applied fundamental phase voltage by suitably modifying the applied PWM pattern - the higher fundamental phase voltage is accompanied by an increase in higher order harmonics. This feature can be enabled by setting OVERMODULATION\_ENABLE to 1b.

### 6.3.11.8 Motor Speed Limit

MCF8315D provides the option of limiting the motor speed to a user configured limit. When SPEED\_LIMIT\_ENABLE is set to 1b, irrespective of the input reference mode (current, power or voltage) and operating conditions like (VM, load), MCF8315D limits the motor speed to MAX\_SPEED by restricting the input DC power, motor phase current or voltage (depending on input reference mode). When speed limit is active

(motor speed limited at MAX\_SPEED), the acceleration/deceleration rate is set by CL\_SLOW\_ACC instead of CL\_ACC/CL\_DEC to minimize chattering around the MAX\_SPEED value. When the speed limit condition becomes inactive (motor speed < MAX\_SPEED), acceleration/deceleration rate reverts to CL\_ACC/CL\_DEC.

#### 6.3.11.9 Input DC Power Limit

MCF8315D provides the option of limiting the power that the motor driver can draw from the input DC source (VM). When BUS\_POWER\_LIMIT\_ENABLE is set to 1b, irrespective of the input reference mode (speed, current or voltage) and operating conditions like (VM, load), MCF8315D limits the input DC power to MAX\_POWER by restricting the motor speed, current or voltage (depending on input reference mode). When power limit is active (input DC power limited at MAX\_POWER), the acceleration/deceleration rate is set by CL\_SLOW\_ACC instead of CL\_ACC/CL\_DEC to minimize chattering around the MAX\_POWER value. When the power limit condition becomes inactive (input DC power < MAX\_POWER), acceleration/deceleration rate reverts to CL\_ACC/CL\_DEC.

#### 6.3.12 Flux Weakening Control

PMSM motors can be operated not only in the constant torque region below the base speed (rated speed) but also in the constant power region above the base speed, but the base speed can be varied according to current and voltage limitation. MCF8315D provides a flux weakening control, to increase the motor speed beyond the rated speed. The flux weakening can be enabled by setting FLUX\_WEAK\_EN to 1b. The flux weakening control uses a PI control loop as shown in , to create the  $I_{d\_ref}$ . Kp and Ki coefficients for flux weakening loop are configured through FLUX\_WEAK\_KP and FLUX\_WEAK\_KI.

User can configure the modulation index reference,  $V_{s\_ref}$  (shown in [Figure 6-47](#)) below that the flux weakening is not active and  $I_{d\_FW}$  is set to zero. The configuration is available in the bits FLUX\_WEAK\_REF.

$$V_{s\_ref} = \sqrt{V_{q\_ref}^2 + V_{d\_ref}^2} \quad (9)$$




Figure 6-47. Flux Weakening Control

### 6.3.13 Motor Parameters

The MCF8315D uses the motor resistance, motor inductance and motor back-EMF constant to estimate motor position when operating in closed loop. The MCF8315D has the capability of measuring these motor parameters in the offline state (see [Motor Parameter Extraction Tool \(MPET\)](#)). Offline measurement of parameters, when enabled, takes place before normal motor operation. The user can also disable the offline measurement and configure motor parameters through EEPROM. This feature of offline motor parameter measurement is useful to account for motor to motor variation during manufacturing.

#### 6.3.13.1 Motor Resistance

For a wye-connected motor, the motor phase resistance refers to the resistance from the phase output to the center tap,  $R_{PH}$  (denoted as  $R_{PH}$  in [Figure 6-48](#)). For a delta-connected motor, the motor phase resistance refers to the equivalent phase to center tap in the wye configuration in [Figure 6-48](#).




Figure 6-48. Motor Resistance

For both the delta-connected and the wye-connected motor, the easy way to get the equivalent  $R_{PH}$  is to measure the resistance between two phase terminals ( $R_{PH\_PH}$ ), and then divide this value by two,  $R_{PH} = \frac{1}{2}$

$R_{PH\_PH}$ . In wye-connected motor, if user has access to center tap (CT),  $R_{PH}$  can also be measured between center tap (CT) and phase terminal.

Configure the motor resistance ( $R_{PH}$ ) to a nearest value from [Table 6-2](#).

**Table 6-2. Motor Resistance Look-Up Table**


| MOTOR_RES (HEX) | $R_{PH}$ ( $\Omega$ )                                                          | MOTOR_RES (HEX) | $R_{PH}$ ( $\Omega$ ) | MOTOR_RES (HEX) | $R_{PH}$ ( $\Omega$ ) | MOTOR_RES (HEX) | $R_{PH}$ ( $\Omega$ ) |
|-----------------|--------------------------------------------------------------------------------|-----------------|-----------------------|-----------------|-----------------------|-----------------|-----------------------|
| 0x00            | Self Measurement (see <a href="#">Motor Parameter Extraction Tool (MPET)</a> ) | 0x40            | 0.145                 | 0x80            | 0.465                 | 0xC0            | 2.1                   |
| 0x01            | 0.006                                                                          | 0x41            | 0.150                 | 0x81            | 0.470                 | 0xC1            | 2.2                   |
| 0x02            | 0.007                                                                          | 0x42            | 0.155                 | 0x82            | 0.475                 | 0xC2            | 2.3                   |
| 0x03            | 0.008                                                                          | 0x43            | 0.160                 | 0x83            | 0.480                 | 0xC3            | 2.4                   |
| 0x04            | 0.009                                                                          | 0x44            | 0.165                 | 0x84            | 0.485                 | 0xC4            | 2.5                   |
| 0x05            | 0.010                                                                          | 0x45            | 0.170                 | 0x85            | 0.490                 | 0xC5            | 2.6                   |
| 0x06            | 0.011                                                                          | 0x46            | 0.175                 | 0x86            | 0.495                 | 0xC6            | 2.7                   |
| 0x07            | 0.012                                                                          | 0x47            | 0.180                 | 0x87            | 0.50                  | 0xC7            | 2.8                   |
| 0x08            | 0.013                                                                          | 0x48            | 0.185                 | 0x88            | 0.51                  | 0xC8            | 2.9                   |
| 0x09            | 0.014                                                                          | 0x49            | 0.190                 | 0x89            | 0.52                  | 0xC9            | 3.0                   |
| 0x0A            | 0.015                                                                          | 0x4A            | 0.195                 | 0x8A            | 0.53                  | 0xCA            | 3.2                   |
| 0x0B            | 0.016                                                                          | 0x4B            | 0.200                 | 0x8B            | 0.54                  | 0xCB            | 3.4                   |
| 0x0C            | 0.017                                                                          | 0x4C            | 0.205                 | 0x8C            | 0.55                  | 0xCC            | 3.6                   |
| 0x0D            | 0.018                                                                          | 0x4D            | 0.210                 | 0x8D            | 0.56                  | 0xCD            | 3.8                   |
| 0x0E            | 0.019                                                                          | 0x4E            | 0.215                 | 0x8E            | 0.57                  | 0xCE            | 4.0                   |
| 0x0F            | 0.020                                                                          | 0x4F            | 0.220                 | 0x8F            | 0.58                  | 0xCF            | 4.2                   |
| 0x10            | 0.022                                                                          | 0x50            | 0.225                 | 0x90            | 0.59                  | 0xD0            | 4.4                   |
| 0x11            | 0.024                                                                          | 0x51            | 0.230                 | 0x91            | 0.60                  | 0xD1            | 4.6                   |
| 0x12            | 0.026                                                                          | 0x52            | 0.235                 | 0x92            | 0.61                  | 0xD2            | 4.8                   |
| 0x13            | 0.028                                                                          | 0x53            | 0.240                 | 0x93            | 0.62                  | 0xD3            | 5.0                   |
| 0x14            | 0.030                                                                          | 0x54            | 0.245                 | 0x94            | 0.63                  | 0xD4            | 5.2                   |
| 0x15            | 0.032                                                                          | 0x55            | 0.250                 | 0x95            | 0.64                  | 0xD5            | 5.4                   |
| 0x16            | 0.034                                                                          | 0x56            | 0.255                 | 0x96            | 0.65                  | 0xD6            | 5.6                   |
| 0x17            | 0.036                                                                          | 0x57            | 0.260                 | 0x97            | 0.66                  | 0xD7            | 5.8                   |
| 0x18            | 0.038                                                                          | 0x58            | 0.265                 | 0x98            | 0.67                  | 0xD8            | 6.0                   |
| 0x19            | 0.040                                                                          | 0x59            | 0.270                 | 0x99            | 0.68                  | 0xD9            | 6.2                   |
| 0x1A            | 0.042                                                                          | 0x5A            | 0.275                 | 0x9A            | 0.69                  | 0xDA            | 6.4                   |
| 0x1B            | 0.044                                                                          | 0x5B            | 0.280                 | 0x9B            | 0.70                  | 0xDB            | 6.6                   |
| 0x1C            | 0.046                                                                          | 0x5C            | 0.285                 | 0x9C            | 0.72                  | 0xDC            | 6.8                   |
| 0x1D            | 0.048                                                                          | 0x5D            | 0.290                 | 0x9D            | 0.74                  | 0xDD            | 7.0                   |
| 0x1E            | 0.050                                                                          | 0x5E            | 0.295                 | 0x9E            | 0.76                  | 0xDE            | 7.2                   |
| 0x1F            | 0.052                                                                          | 0x5F            | 0.300                 | 0x9F            | 0.78                  | 0xDF            | 7.4                   |
| 0x20            | 0.054                                                                          | 0x60            | 0.305                 | 0xA0            | 0.80                  | 0xE0            | 7.6                   |
| 0x21            | 0.056                                                                          | 0x61            | 0.310                 | 0xA1            | 0.82                  | 0xE1            | 7.8                   |
| 0x22            | 0.058                                                                          | 0x62            | 0.315                 | 0xA2            | 0.84                  | 0xE2            | 8.0                   |
| 0x23            | 0.060                                                                          | 0x63            | 0.320                 | 0xA3            | 0.86                  | 0xE3            | 8.2                   |
| 0x24            | 0.062                                                                          | 0x64            | 0.325                 | 0xA4            | 0.88                  | 0xE4            | 8.4                   |

**Table 6-2. Motor Resistance Look-Up Table (continued)**

| MOTOR_RES (HEX) | R <sub>PH</sub> (Ω) | MOTOR_RES (HEX) | R <sub>PH</sub> (Ω) | MOTOR_RES (HEX) | R <sub>PH</sub> (Ω) | MOTOR_RES (HEX) | R <sub>PH</sub> (Ω) |
|-----------------|---------------------|-----------------|---------------------|-----------------|---------------------|-----------------|---------------------|
| 0x25            | 0.064               | 0x65            | 0.330               | 0xA5            | 0.90                | 0xE5            | 8.6                 |
| 0x26            | 0.066               | 0x66            | 0.335               | 0xA6            | 0.92                | 0xE6            | 8.8                 |
| 0x27            | 0.068               | 0x67            | 0.340               | 0xA7            | 0.94                | 0xE7            | 9                   |
| 0x28            | 0.070               | 0x68            | 0.345               | 0xA8            | 0.96                | 0xE8            | 9.2                 |
| 0x29            | 0.072               | 0x69            | 0.350               | 0xA9            | 0.98                | 0xE9            | 9.4                 |
| 0x2A            | 0.074               | 0x6A            | 0.355               | 0xAA            | 1.00                | 0xEA            | 9.6                 |
| 0x2B            | 0.076               | 0x6B            | 0.360               | 0xAB            | 1.05                | 0xEB            | 9.8                 |
| 0x2C            | 0.078               | 0x6C            | 0.365               | 0xAC            | 1.10                | 0xEC            | 10.0                |
| 0x2D            | 0.080               | 0x6D            | 0.370               | 0xAD            | 1.15                | 0xED            | 10.5                |
| 0x2E            | 0.082               | 0x6E            | 0.375               | 0xAE            | 1.20                | 0xEE            | 11.0                |
| 0x2F            | 0.084               | 0x6F            | 0.380               | 0xAF            | 1.25                | 0xEF            | 11.5                |
| 0x30            | 0.086               | 0x70            | 0.385               | 0xB0            | 1.30                | 0xF0            | 12.0                |
| 0x31            | 0.088               | 0x71            | 0.390               | 0xB1            | 1.35                | 0xF1            | 12.5                |
| 0x32            | 0.090               | 0x72            | 0.395               | 0xB2            | 1.40                | 0xF2            | 13.0                |
| 0x33            | 0.092               | 0x73            | 0.400               | 0xB3            | 1.45                | 0xF3            | 13.5                |
| 0x34            | 0.094               | 0x74            | 0.405               | 0xB4            | 1.50                | 0xF4            | 14.0                |
| 0x35            | 0.096               | 0x75            | 0.410               | 0xB5            | 1.55                | 0xF5            | 14.5                |
| 0x36            | 0.098               | 0x76            | 0.415               | 0xB6            | 1.60                | 0xF6            | 15.0                |
| 0x37            | 0.100               | 0x77            | 0.420               | 0xB7            | 1.65                | 0xF7            | 15.5                |
| 0x38            | 0.105               | 0x78            | 0.425               | 0xB8            | 1.70                | 0xF8            | 16.0                |
| 0x39            | 0.110               | 0x79            | 0.430               | 0xB9            | 1.75                | 0xF9            | 16.5                |
| 0x3A            | 0.115               | 0x7A            | 0.435               | 0xBA            | 1.80                | 0xFA            | 17.0                |
| 0x3B            | 0.120               | 0x7B            | 0.440               | 0xBB            | 1.85                | 0xFB            | 17.5                |
| 0x3C            | 0.125               | 0x7C            | 0.445               | 0xBC            | 1.90                | 0xFC            | 18.0                |
| 0x3D            | 0.130               | 0x7D            | 0.450               | 0xBD            | 1.95                | 0xFD            | 18.5                |
| 0x3E            | 0.135               | 0x7E            | 0.455               | 0xBE            | 2.00                | 0xFE            | 19.0                |
| 0x3F            | 0.140               | 0x7F            | 0.460               | 0xBF            | 2.05                | 0xFF            | 20.0                |

**6.3.13.2 Motor Inductance**

For a wye-connected motor, the motor phase inductance refers to the inductance from the phase output to the center tap,  $L_{PH}$  (denoted as  $L_{PH}$  in Figure 6-49). For a delta-connected motor, the motor phase inductance refers to the equivalent phase to center tap in the wye configuration in Figure 6-49.

**Figure 6-49. Motor Inductance**

For both the delta-connected motor and the wye-connected motor, the easy way to get the equivalent  $L_{PH}$  is to measure the inductance between two phase terminals ( $L_{PH\_PH}$ ), and then divide this value by two,  $L_{PH} = \frac{1}{2} L_{PH\_PH}$ . In wye-connected motor, if user has access to center tap (CT),  $L_{PH}$  can also be measured between center tap (CT) and phase terminal.

Configure the motor inductance ( $L_{PH}$ ) to a nearest value from [Table 6-3](#).

**Table 6-3. Motor Inductance Look-Up Table**

| MOTOR_IND (HEX) | L <sub>PH</sub> (mH)                                                           | MOTOR_IND (HEX) | L <sub>PH</sub> (mH) | MOTOR_IND (HEX) | L <sub>PH</sub> (mH) | MOTOR_IND (HEX) | L <sub>PH</sub> (mH) |
|-----------------|--------------------------------------------------------------------------------|-----------------|----------------------|-----------------|----------------------|-----------------|----------------------|
| 0x00            | Self Measurement (see <a href="#">Motor Parameter Extraction Tool (MPET)</a> ) | 0x40            | 0.145                | 0x80            | 0.465                | 0xC0            | 2.1                  |
| 0x01            | 0.006                                                                          | 0x41            | 0.150                | 0x81            | 0.470                | 0xC1            | 2.2                  |
| 0x02            | 0.007                                                                          | 0x42            | 0.155                | 0x82            | 0.475                | 0xC2            | 2.3                  |
| 0x03            | 0.008                                                                          | 0x43            | 0.160                | 0x83            | 0.480                | 0xC3            | 2.4                  |
| 0x04            | 0.009                                                                          | 0x44            | 0.165                | 0x84            | 0.485                | 0xC4            | 2.5                  |
| 0x05            | 0.010                                                                          | 0x45            | 0.170                | 0x85            | 0.490                | 0xC5            | 2.6                  |
| 0x06            | 0.011                                                                          | 0x46            | 0.175                | 0x86            | 0.495                | 0xC6            | 2.7                  |
| 0x07            | 0.012                                                                          | 0x47            | 0.180                | 0x87            | 0.50                 | 0xC7            | 2.8                  |
| 0x08            | 0.013                                                                          | 0x48            | 0.185                | 0x88            | 0.51                 | 0xC8            | 2.9                  |
| 0x09            | 0.014                                                                          | 0x49            | 0.190                | 0x89            | 0.52                 | 0xC9            | 3.0                  |
| 0x0A            | 0.015                                                                          | 0x4A            | 0.195                | 0x8A            | 0.53                 | 0xCA            | 3.2                  |
| 0x0B            | 0.016                                                                          | 0x4B            | 0.200                | 0x8B            | 0.54                 | 0xCB            | 3.4                  |
| 0x0C            | 0.017                                                                          | 0x4C            | 0.205                | 0x8C            | 0.55                 | 0xCC            | 3.6                  |
| 0x0D            | 0.018                                                                          | 0x4D            | 0.210                | 0x8D            | 0.56                 | 0xCD            | 3.8                  |
| 0x0E            | 0.019                                                                          | 0x4E            | 0.215                | 0x8E            | 0.57                 | 0xCE            | 4.0                  |
| 0x0F            | 0.020                                                                          | 0x4F            | 0.220                | 0x8F            | 0.58                 | 0xCF            | 4.2                  |
| 0x10            | 0.022                                                                          | 0x50            | 0.225                | 0x90            | 0.59                 | 0xD0            | 4.4                  |
| 0x11            | 0.024                                                                          | 0x51            | 0.230                | 0x91            | 0.60                 | 0xD1            | 4.6                  |
| 0x12            | 0.026                                                                          | 0x52            | 0.235                | 0x92            | 0.61                 | 0xD2            | 4.8                  |
| 0x13            | 0.028                                                                          | 0x53            | 0.240                | 0x93            | 0.62                 | 0xD3            | 5.0                  |
| 0x14            | 0.030                                                                          | 0x54            | 0.245                | 0x94            | 0.63                 | 0xD4            | 5.2                  |
| 0x15            | 0.032                                                                          | 0x55            | 0.250                | 0x95            | 0.64                 | 0xD5            | 5.4                  |
| 0x16            | 0.034                                                                          | 0x56            | 0.255                | 0x96            | 0.65                 | 0xD6            | 5.6                  |
| 0x17            | 0.036                                                                          | 0x57            | 0.260                | 0x97            | 0.66                 | 0xD7            | 5.8                  |
| 0x18            | 0.038                                                                          | 0x58            | 0.265                | 0x98            | 0.67                 | 0xD8            | 6.0                  |
| 0x19            | 0.040                                                                          | 0x59            | 0.270                | 0x99            | 0.68                 | 0xD9            | 6.2                  |
| 0x1A            | 0.042                                                                          | 0x5A            | 0.275                | 0x9A            | 0.69                 | 0xDA            | 6.4                  |
| 0x1B            | 0.044                                                                          | 0x5B            | 0.280                | 0x9B            | 0.70                 | 0xDB            | 6.6                  |
| 0x1C            | 0.046                                                                          | 0x5C            | 0.285                | 0x9C            | 0.72                 | 0xDC            | 6.8                  |
| 0x1D            | 0.048                                                                          | 0x5D            | 0.290                | 0x9D            | 0.74                 | 0xDD            | 7.0                  |
| 0x1E            | 0.050                                                                          | 0x5E            | 0.295                | 0x9E            | 0.76                 | 0xDE            | 7.2                  |
| 0x1F            | 0.052                                                                          | 0x5F            | 0.300                | 0x9F            | 0.78                 | 0xDF            | 7.4                  |
| 0x20            | 0.054                                                                          | 0x60            | 0.305                | 0xA0            | 0.80                 | 0xE0            | 7.6                  |
| 0x21            | 0.056                                                                          | 0x61            | 0.310                | 0xA1            | 0.82                 | 0xE1            | 7.8                  |
| 0x22            | 0.058                                                                          | 0x62            | 0.315                | 0xA2            | 0.84                 | 0xE2            | 8.0                  |
| 0x23            | 0.060                                                                          | 0x63            | 0.320                | 0xA3            | 0.86                 | 0xE3            | 8.2                  |
| 0x24            | 0.062                                                                          | 0x64            | 0.325                | 0xA4            | 0.88                 | 0xE4            | 8.4                  |
| 0x25            | 0.064                                                                          | 0x65            | 0.330                | 0xA5            | 0.90                 | 0xE5            | 8.6                  |
| 0x26            | 0.066                                                                          | 0x66            | 0.335                | 0xA6            | 0.92                 | 0xE6            | 8.8                  |
| 0x27            | 0.068                                                                          | 0x67            | 0.340                | 0xA7            | 0.94                 | 0xE7            | 9                    |
| 0x28            | 0.070                                                                          | 0x68            | 0.345                | 0xA8            | 0.96                 | 0xE8            | 9.2                  |

**Table 6-3. Motor Inductance Look-Up Table (continued)**

| MOTOR_IND (HEX) | L <sub>PH</sub> (mH) | MOTOR_IND (HEX) | L <sub>PH</sub> (mH) | MOTOR_IND (HEX) | L <sub>PH</sub> (mH) | MOTOR_IND (HEX) | L <sub>PH</sub> (mH) |
|-----------------|----------------------|-----------------|----------------------|-----------------|----------------------|-----------------|----------------------|
| 0x29            | 0.072                | 0x69            | 0.350                | 0xA9            | 0.98                 | 0xE9            | 9.4                  |
| 0x2A            | 0.074                | 0x6A            | 0.355                | 0xAA            | 1.00                 | 0xEA            | 9.6                  |
| 0x2B            | 0.076                | 0x6B            | 0.360                | 0xAB            | 1.05                 | 0xEB            | 9.8                  |
| 0x2C            | 0.078                | 0x6C            | 0.365                | 0xAC            | 1.10                 | 0xEC            | 10.0                 |
| 0x2D            | 0.080                | 0x6D            | 0.370                | 0xAD            | 1.15                 | 0xED            | 10.5                 |
| 0x2E            | 0.082                | 0x6E            | 0.375                | 0xAE            | 1.20                 | 0xEE            | 11.0                 |
| 0x2F            | 0.084                | 0x6F            | 0.380                | 0xAF            | 1.25                 | 0xEF            | 11.5                 |
| 0x30            | 0.086                | 0x70            | 0.385                | 0xB0            | 1.30                 | 0xF0            | 12.0                 |
| 0x31            | 0.088                | 0x71            | 0.390                | 0xB1            | 1.35                 | 0xF1            | 12.5                 |
| 0x32            | 0.090                | 0x72            | 0.395                | 0xB2            | 1.40                 | 0xF2            | 13.0                 |
| 0x33            | 0.092                | 0x73            | 0.400                | 0xB3            | 1.45                 | 0xF3            | 13.5                 |
| 0x34            | 0.094                | 0x74            | 0.405                | 0xB4            | 1.50                 | 0xF4            | 14.0                 |
| 0x35            | 0.096                | 0x75            | 0.410                | 0xB5            | 1.55                 | 0xF5            | 14.5                 |
| 0x36            | 0.098                | 0x76            | 0.415                | 0xB6            | 1.60                 | 0xF6            | 15.0                 |
| 0x37            | 0.100                | 0x77            | 0.420                | 0xB7            | 1.65                 | 0xF7            | 15.5                 |
| 0x38            | 0.105                | 0x78            | 0.425                | 0xB8            | 1.70                 | 0xF8            | 16.0                 |
| 0x39            | 0.110                | 0x79            | 0.430                | 0xB9            | 1.75                 | 0xF9            | 16.5                 |
| 0x3A            | 0.115                | 0x7A            | 0.435                | 0xBA            | 1.80                 | 0xFA            | 17.0                 |
| 0x3B            | 0.120                | 0x7B            | 0.440                | 0xBB            | 1.85                 | 0xFB            | 17.5                 |
| 0x3C            | 0.125                | 0x7C            | 0.445                | 0xBC            | 1.90                 | 0xFC            | 18.0                 |
| 0x3D            | 0.130                | 0x7D            | 0.450                | 0xBD            | 1.95                 | 0xFD            | 18.5                 |
| 0x3E            | 0.135                | 0x7E            | 0.455                | 0xBE            | 2.00                 | 0xFE            | 19.0                 |
| 0x3F            | 0.140                | 0x7F            | 0.460                | 0xBF            | 2.05                 | 0xFF            | 20.0                 |

### 6.3.13.3 Motor Back-EMF constant

The back-EMF constant describes the motor phase-to-neutral back-EMF voltage as a function of the motor speed. For a wye-connected motor, the motor BEMF constant refers to the BEMF as a function of time from the phase output to the center tap,  $K_{t_{PH\_N}}$  (denoted as  $K_{t_{PH\_N}}$  in [Figure 6-50](#)). For a delta-connected motor, the motor BEMF constant refers to the equivalent phase to center tap in the wye configuration in [Figure 6-50](#).




**Figure 6-50. Motor back-EMF constant**

For both the delta-connected motor and the wye-connected motor, the easy way to get the equivalent  $Kt_{PH\_N}$  is to measure the peak value of BEMF on scope for one electrical cycle between two phase terminals ( $E_{PH}$ ), and then multiply by time duration of one electrical cycle and in order to convert from phase-to-phase to phase-to-neutral divide by  $\sqrt{3}$  as shown in Equation 10.

$$Kt_{PH\_N} = \frac{1}{\sqrt{3}} \times E_{PH} \times t_E \quad (10)$$

Configure the motor BEMF constant ( $Kt_{PH\_N}$ ) to a nearest value from Table 6-4.

**Table 6-4. Motor BEMF constant Look-Up Table**

| MOTOR_BEMF_CONST (HEX) | $Kt_{PH\_N}$ (mV/Hz)                                          | MOTOR_BEMF_CONST (HEX) | $Kt_{PH\_N}$ (mV/Hz) | MOTOR_BEMF_CONST (HEX) | $Kt_{PH\_N}$ (mV/Hz) | MOTOR_BEMF_CONST (HEX) | $Kt_{PH\_N}$ (mV/Hz) |
|------------------------|---------------------------------------------------------------|------------------------|----------------------|------------------------|----------------------|------------------------|----------------------|
| 0x00                   | Self Measurement (see Motor Parameter Extraction Tool (MPET)) | 0x40                   | 14.5                 | 0x80                   | 46.5                 | 0xC0                   | 210                  |
| 0x01                   | 0.6                                                           | 0x41                   | 15.0                 | 0x81                   | 47.0                 | 0xC1                   | 220                  |
| 0x02                   | 0.7                                                           | 0x42                   | 15.5                 | 0x82                   | 47.5                 | 0xC2                   | 230                  |
| 0x03                   | 0.8                                                           | 0x43                   | 16.0                 | 0x83                   | 48.0                 | 0xC3                   | 240                  |
| 0x04                   | 0.9                                                           | 0x44                   | 16.5                 | 0x84                   | 48.5                 | 0xC4                   | 250                  |
| 0x05                   | 1.0                                                           | 0x45                   | 17.0                 | 0x85                   | 49.0                 | 0xC5                   | 260                  |
| 0x06                   | 1.1                                                           | 0x46                   | 17.5                 | 0x86                   | 49.5                 | 0xC6                   | 270                  |
| 0x07                   | 1.2                                                           | 0x47                   | 18.0                 | 0x87                   | 50.0                 | 0xC7                   | 280                  |
| 0x08                   | 1.3                                                           | 0x48                   | 18.5                 | 0x88                   | 51                   | 0xC8                   | 290                  |
| 0x09                   | 1.4                                                           | 0x49                   | 19.0                 | 0x89                   | 52                   | 0xC9                   | 300                  |
| 0x0A                   | 1.5                                                           | 0x4A                   | 19.5                 | 0x8A                   | 53                   | 0xCA                   | 320                  |
| 0x0B                   | 1.6                                                           | 0x4B                   | 20.0                 | 0x8B                   | 54                   | 0xCB                   | 340                  |
| 0x0C                   | 1.7                                                           | 0x4C                   | 20.5                 | 0x8C                   | 55                   | 0xCC                   | 360                  |
| 0x0D                   | 1.8                                                           | 0x4D                   | 21.0                 | 0x8D                   | 56                   | 0xCD                   | 380                  |
| 0x0E                   | 1.9                                                           | 0x4E                   | 21.5                 | 0x8E                   | 57                   | 0xCE                   | 400                  |
| 0x0F                   | 2.0                                                           | 0x4F                   | 22.0                 | 0x8F                   | 58                   | 0xCF                   | 420                  |

**Table 6-4. Motor BEMF constant Look-Up Table (continued)**

| MOTOR_BEMF_<br>CONST (HEX) | Kt <sub>PH_N</sub><br>(mV/Hz) | MOTOR_BEMF_<br>CONST (HEX) | Kt <sub>PH_N</sub><br>(mV/Hz) | MOTOR_BEMF_<br>CONST (HEX) | Kt <sub>PH_N</sub><br>(mV/Hz) | MOTOR_BEMF_<br>CONST (HEX) | Kt <sub>PH_N</sub><br>(mV/Hz) |
|----------------------------|-------------------------------|----------------------------|-------------------------------|----------------------------|-------------------------------|----------------------------|-------------------------------|
| 0x10                       | 2.2                           | 0x50                       | 22.5                          | 0x90                       | 59                            | 0xD0                       | 440                           |
| 0x11                       | 2.4                           | 0x51                       | 23.0                          | 0x91                       | 60                            | 0xD1                       | 460                           |
| 0x12                       | 2.6                           | 0x52                       | 23.5                          | 0x92                       | 61                            | 0xD2                       | 480                           |
| 0x13                       | 2.8                           | 0x53                       | 24.0                          | 0x93                       | 62                            | 0xD3                       | 500                           |
| 0x14                       | 3.0                           | 0x54                       | 24.5                          | 0x94                       | 63                            | 0xD4                       | 520                           |
| 0x15                       | 3.2                           | 0x55                       | 25.0                          | 0x95                       | 64                            | 0xD5                       | 540                           |
| 0x16                       | 3.4                           | 0x56                       | 25.5                          | 0x96                       | 65                            | 0xD6                       | 560                           |
| 0x17                       | 3.6                           | 0x57                       | 26.0                          | 0x97                       | 66                            | 0xD7                       | 580                           |
| 0x18                       | 3.8                           | 0x58                       | 26.5                          | 0x98                       | 67                            | 0xD8                       | 600                           |
| 0x19                       | 4.0                           | 0x59                       | 27.0                          | 0x99                       | 68                            | 0xD9                       | 620                           |
| 0x1A                       | 4.2                           | 0x5A                       | 27.5                          | 0x9A                       | 69                            | 0xDA                       | 640                           |
| 0x1B                       | 4.4                           | 0x5B                       | 28.0                          | 0x9B                       | 70                            | 0xDB                       | 660                           |
| 0x1C                       | 4.6                           | 0x5C                       | 28.5                          | 0x9C                       | 72                            | 0xDC                       | 680                           |
| 0x1D                       | 4.8                           | 0x5D                       | 29.0                          | 0x9D                       | 74                            | 0xDD                       | 700                           |
| 0x1E                       | 5.0                           | 0x5E                       | 29.5                          | 0x9E                       | 76                            | 0xDE                       | 720                           |
| 0x1F                       | 5.2                           | 0x5F                       | 30.0                          | 0x9F                       | 78                            | 0xDF                       | 740                           |
| 0x20                       | 5.4                           | 0x60                       | 30.5                          | 0xA0                       | 80                            | 0xE0                       | 760                           |
| 0x21                       | 5.6                           | 0x61                       | 31.0                          | 0xA1                       | 82                            | 0xE1                       | 780                           |
| 0x22                       | 5.8                           | 0x62                       | 31.5                          | 0xA2                       | 84                            | 0xE2                       | 800                           |
| 0x23                       | 6.0                           | 0x63                       | 32.0                          | 0xA3                       | 86                            | 0xE3                       | 820                           |
| 0x24                       | 6.2                           | 0x64                       | 32.5                          | 0xA4                       | 88                            | 0xE4                       | 840                           |
| 0x25                       | 6.4                           | 0x65                       | 33.0                          | 0xA5                       | 90                            | 0xE5                       | 860                           |
| 0x26                       | 6.6                           | 0x66                       | 33.5                          | 0xA6                       | 92                            | 0xE6                       | 880                           |
| 0x27                       | 6.8                           | 0x67                       | 34.0                          | 0xA7                       | 94                            | 0xE7                       | 900                           |
| 0x28                       | 7.0                           | 0x68                       | 34.5                          | 0xA8                       | 96                            | 0xE8                       | 920                           |
| 0x29                       | 7.2                           | 0x69                       | 35.0                          | 0xA9                       | 98                            | 0xE9                       | 940                           |
| 0x2A                       | 7.4                           | 0x6A                       | 35.5                          | 0xAA                       | 100                           | 0xEA                       | 960                           |
| 0x2B                       | 7.6                           | 0x6B                       | 36.0                          | 0xAB                       | 105                           | 0xEB                       | 980                           |
| 0x2C                       | 7.8                           | 0x6C                       | 36.5                          | 0xAC                       | 110                           | 0xEC                       | 1000                          |
| 0x2D                       | 8.0                           | 0x6D                       | 37.0                          | 0xAD                       | 115                           | 0xED                       | 1050                          |
| 0x2E                       | 8.2                           | 0x6E                       | 37.5                          | 0xAE                       | 120                           | 0xEE                       | 1100                          |
| 0x2F                       | 8.4                           | 0x6F                       | 38.0                          | 0xAF                       | 125                           | 0xEF                       | 1150                          |
| 0x30                       | 8.6                           | 0x70                       | 38.5                          | 0xB0                       | 130                           | 0xF0                       | 1200                          |
| 0x31                       | 8.8                           | 0x71                       | 39.0                          | 0xB1                       | 135                           | 0xF1                       | 1250                          |
| 0x32                       | 9.0                           | 0x72                       | 39.5                          | 0xB2                       | 140                           | 0xF2                       | 1300                          |
| 0x33                       | 9.2                           | 0x73                       | 40.0                          | 0xB3                       | 145                           | 0xF3                       | 1350                          |
| 0x34                       | 9.4                           | 0x74                       | 40.5                          | 0xB4                       | 150                           | 0xF4                       | 1400                          |
| 0x35                       | 9.6                           | 0x75                       | 41.0                          | 0xB5                       | 155                           | 0xF5                       | 1450                          |
| 0x36                       | 9.8                           | 0x76                       | 41.5                          | 0xB6                       | 160                           | 0xF6                       | 1500                          |
| 0x37                       | 10.0                          | 0x77                       | 42.0                          | 0xB7                       | 165                           | 0xF7                       | 1550                          |
| 0x38                       | 10.5                          | 0x78                       | 42.5                          | 0xB8                       | 170                           | 0xF8                       | 1600                          |
| 0x39                       | 11.0                          | 0x79                       | 43.0                          | 0xB9                       | 175                           | 0xF9                       | 1650                          |
| 0x3A                       | 11.5                          | 0x7A                       | 43.5                          | 0xBA                       | 180                           | 0xFA                       | 1700                          |
| 0x3B                       | 12.0                          | 0x7B                       | 44.0                          | 0xBB                       | 185                           | 0xFB                       | 1750                          |


**Table 6-4. Motor BEMF constant Look-Up Table (continued)**

| MOTOR_BEMF_CONST (HEX) | Kt <sub>PH_N</sub> (mV/Hz) | MOTOR_BEMF_CONST (HEX) | Kt <sub>PH_N</sub> (mV/Hz) | MOTOR_BEMF_CONST (HEX) | Kt <sub>PH_N</sub> (mV/Hz) | MOTOR_BEMF_CONST (HEX) | Kt <sub>PH_N</sub> (mV/Hz) |
|------------------------|----------------------------|------------------------|----------------------------|------------------------|----------------------------|------------------------|----------------------------|
| 0x3C                   | 12.5                       | 0x7C                   | 44.5                       | 0xBC                   | 190                        | 0xFC                   | 1800                       |
| 0x3D                   | 13.0                       | 0x7D                   | 45.0                       | 0xBD                   | 195                        | 0xFD                   | 1850                       |
| 0x3E                   | 13.5                       | 0x7E                   | 45.5                       | 0xBE                   | 200                        | 0xFE                   | 1900                       |
| 0x3F                   | 14.0                       | 0x7F                   | 46.0                       | 0xBF                   | 205                        | 0xFF                   | 2000                       |

### 6.3.14 Motor Parameter Extraction Tool (MPET)

The MCF8315D uses motor winding resistance, motor winding inductance and Back-EMF constant to estimate motor position in closed loop operation. The MCF8315D has capability of automatically measuring motor parameters in offline state, rather than having the user enter the values themselves. The MPET routine measures motor winding resistance, inductance, back EMF constant and mechanical load inertia and frictional coefficients. Offline measurement of parameters takes place before normal motor operation. TI recommends to estimate the motor parameters before motor startup to minimize the impact caused due to possible parameter variations.

Figure 6-51 shows the sequence of operation in the MPET routine. The MPET routine is entered when either the MPET\_CMD bit is set to 1b or a non-zero target speed is set. The MPET routine consists of four steps namely, IPD, Open Loop Acceleration, Current Ramp Down and Coasting. Each one of these steps are executed if the condition shown below the step evaluates to TRUE; if the condition evaluates to FALSE, the algorithm bypasses that particular step and moves on to the next step in the sequence. Once all the 4 steps are completed (or bypassed), the algorithm exits the MPET routine. If target speed is set to a non-zero value, the algorithm begins the start-up and acceleration sequence (to target speed reference) once MPET routine is exited.

**Figure 6-51. MPET Sequence**

TI proprietary MPET routine includes following sequence of operation.

- **IPD:** The MPET routine starts with IPD, if the user enables motor winding resistance or inductance measurement by setting MPET\_R = 1b and MPET\_L = 1b or if the user defines MOTOR\_RES = 0 or MOTOR\_IND = 0. The IPD during MPET is configured using the normal motor operation IPD configuration parameters. The IPD current limit and the repeat number is configured using IPD\_CURR\_THR and IPD\_REPEAT. The IPD timer over flow or the IPD current decay time more than three times the current ramp up time can result in MPET\_IPD\_FAULT.
- **Open loop Acceleration:**

After IPD, the MPET routine runs align and then open loop acceleration if the back-EMF constant or mechanical parameter measurement are enabled by setting MPET\_KE = 1b and MPET\_MECH = 1b. The MPET routine incorporates the sequences for mechanical parameter measurement, if the speed loop PI constants are defined as zero, even if MPET\_MECH = 0b. This routine uses normal motor operation open loop configuration parameters. The speed slew rate is set by OL\_ACC\_A1 and OL\_ACC\_A2, current reference is set by OL\_ILIMIT and speed reference is set by OPN\_CL\_HANDOFF\_THR.

- **Current Ramp Down:** After open loop acceleration, if the mechanical parameter measurement is enabled, then the MPET routine optimizes the motor current to lower value sufficient to support the load. If mechanical parameter measurement is disabled (MPET\_MECH = 0b, or non-zero speed loop PI parameters) then the MPET will not have the current ramp down sequence.
- **Coasting:** MPET routine completes the sequence by allowing the motor to coast by enabling Hi-Z. The motor back EMF and indicative values of mechanical parameters are measured during the motor coasting period. If the motor back EMF is lower than the threshold defined in STAT\_DETECT\_THR, the MPET\_BEMF\_FAULT is generated.

#### Note

User can exit the MPET routine at any time by writing 0b to MPET\_CMD bit and by making target speed as zero.

### Selecting the parameters from EEPROM or MPET

The MPET estimated values are available in the MTR\_PARAMS Register. Setting the MPET\_WRITE\_SHADOW bit to 1, writes the MPET estimated values to the shadow/RAM registers and the user-configured (from EEPROM) values in MOTOR\_RES, MOTOR\_IND, MOTOR\_BEMF\_CONST, CURR\_LOOP\_KP, CURR\_LOOP\_KI, SPD\_LOOP\_KP and SPD\_LOOP\_KI shadow/RAM registers will be overwritten by the estimated values from MPET. If any of the shadow/RAM registers are initialized to zero (from EEPROM registers), the MPET estimated values are used for those registers independent of the MPET\_WRITE\_SHADOW setting. The MPET calculates the current loop KP and KI by using the measured resistance and inductance. The MPET does an estimation of the mechanical parameters including the inertia and frictional coefficient at the shaft (includes both motor and shaft coupled load). These values are used to set an initial values speed loop KP and KI. The estimated speed loop KP and KI setting can be used as an initial setting only and TI recommends to tune these parameters on application by the user based on the performance requirement.

#### 6.3.15 Anti-Voltage Surge (AVS)

When a motor is driven, energy is transferred from the power supply into the motor. Some of this energy is stored in the form of inductive and mechanical energy. If the speed command suddenly drops such that the BEMF voltage generated by the motor is greater than the voltage that is applied to the motor, then the mechanical energy of the motor is returned to the power supply and the  $V_M$  voltage surges. The AVS feature works to prevent this voltage surge on  $V_M$  and can be enabled by setting AVS\_EN to 1b. AVS can be disabled by setting AVS\_EN to 0b. When AVS is disabled, the deceleration rate is configured through CL\_DEC.

#### 6.3.16 Active Braking

Decelerating the motor quickly requires the motor mechanical energy to be extracted from the rotor in a fast and controlled manner. However, the supply voltage (VM) increases if the motor mechanical energy is returned to the power supply during the deceleration process. MCF8315D is capable of decelerating the motor quickly without pumping energy back into the supply voltage by using a novel technique called active braking. ACTIVE\_BRAKE\_EN should be set to 1b to enable active braking and prevent DC bus voltage (VM) spike during fast motor deceleration. Active braking can also be used during reverse drive (see [Reverse Drive](#)) or motor stop (see [Active Spin-Down](#)) to reduce the motor speed quickly without DC bus voltage (VM) spike.

The maximum limit on the current sourced from the DC bus ( $i_{dc\_ref}$ ) during active braking can be configured using ACTIVE\_BRAKE\_CURRENT\_LIMIT. The D-axis current reference ( $i_{d\_ref}$ ) is generated from the error between DC bus current limit ( $i_{dc\_ref}$ ) and the estimated DC bus current ( $i_{dc}$ ) using a PI controller as shown in [Figure 6-52](#). The gain constants of PI controller can be configured using ACTIVE\_BRAKE\_KP and ACTIVE\_BRAKE\_KI. During active braking, the DC bus current limit ( $i_{dc\_ref}$ ) starts from zero and linearly increases to ACTIVE\_BRAKE\_CURRENT\_LIMIT with current slew rate as defined by ACTIVE\_BRAKE\_BUS\_CURRENT\_SLEW\_RATE.




**Figure 6-52. Active Braking Current Control Loop for  $i_{d\_ref}$**

ACTIVE\_BRAKE\_SPEED\_DELTA\_LIMIT\_ENTRY sets the minimum difference between the initial and target speed above which active braking will be entered. For example, consider ACTIVE\_BRAKE\_SPEED\_DELTA\_LIMIT\_ENTRY is set to 10%; if the initial speed is 100% and target speed is set to 95%, MCF8315D uses AVS instead of active braking to reach 95% speed since the difference in commanded speed change (5%) is less than ACTIVE\_BRAKE\_SPEED\_DELTA\_LIMIT\_ENTRY (10%).

ACTIVE\_BRAKE\_SPEED\_DELTA\_LIMIT\_EXIT sets the difference between the current and target speed below which active braking will be exited. For example, consider ACTIVE\_BRAKE\_SPEED\_DELTA\_LIMIT\_EXIT is set to 5%; if the initial motor speed is 100% and target speed is set to 10%, MCF8315D uses active braking to reduce the motor speed to 15%; upon reaching 15% speed, MCF8315D exits active braking and uses AVS to decelerate the motor speed to 10%.

ACTIVE\_BRAKE\_MOD\_INDEX\_LIMIT sets the modulation index below which active braking will be used. For example, consider ACTIVE\_BRAKE\_MOD\_INDEX\_LIMIT is set to 50%, ACTIVE\_BRAKE\_SPEED\_DELTA\_LIMIT\_ENTRY is set to 5%, ACTIVE\_BRAKE\_SPEED\_DELTA\_LIMIT\_EXIT is set to 2.5%. If the initial motor speed is at 70% (corresponding modulation index is 90%) and target speed is 40% (corresponding modulation index is 60%), MCF8315D uses AVS to decelerate the motor till target speed of 40% since the modulation index (60%) corresponding to final speed is higher than ACTIVE\_BRAKE\_MOD\_INDEX\_LIMIT of 50%. In the same case, if final speed command is 10% (corresponding modulation index is 30%), MCF8315D uses AVS till 30% speed (corresponding modulation index is 50%), switches to active braking from 30% to 15% speed (final speed of 10% + ACTIVE\_BRAKE\_SPEED\_DELTA\_LIMIT\_EXIT of 5%) and uses AVS again from 15% to 10% speed to complete the active braking. TI recommends starting active braking tuning with ACTIVE\_BRAKE\_MOD\_INDEX\_LIMIT set to 100%; if there is a DC bus voltage (VM) spike observed during active braking, reduce ACTIVE\_BRAKE\_MOD\_INDEX\_LIMIT in steps so as to eliminate this voltage spike. If ACTIVE\_BRAKE\_MOD\_INDEX\_LIMIT is set to 0%, MCF8315D decelerates in AVS (even when ACTIVE\_BRAKE\_EN is set to 1b) in the forward direction; in reverse direction (during direction change), ACTIVE\_BRAKE\_MOD\_INDEX\_LIMIT is not applicable and therefore MCF8315D decelerates in active braking.

#### Note

1. ACTIVE\_BRAKE\_SPEED\_DELTA\_LIMIT\_ENTRY, ACTIVE\_BRAKE\_SPEED\_DELTA\_LIMIT\_EXIT and ACTIVE\_BRAKE\_MOD\_INDEX\_LIMIT are applicable only during deceleration in forward direction and not used during direction change.
2. ACTIVE\_BRAKE\_SPEED\_DELTA\_LIMIT\_ENTRY should be set higher than ACTIVE\_BRAKE\_SPEED\_DELTA\_LIMIT\_EXIT for active braking operation.
3. During active (or closed loop) braking,  $i_{q\_ref}$  is clamped to -ILIMIT. This ( $i_{q\_ref}$  being clamped to -ILIMIT) may result in the speed PI loop getting saturated and SPEED\_LOOP\_SATURATION bit getting set to 1b during deceleration. This bit is automatically set to 0b once the deceleration is completed and the speed PI loop is out of saturation. Hence, speed loop saturation fault should be ignored during deceleration.
4. Active braking is available only in speed control mode.
5. Active braking is not available (even when ACTIVE\_BRAKE\_EN = 1b) when (bus) power limit feature (BUS\_POWER\_LIMIT\_ENABLE = 1b) is enabled.

### 6.3.17 Output PWM Switching Frequency

MCF8315D provides the option to configure the output PWM switching frequency of the MOSFETs through PWM\_FREQ\_OUT. PWM\_FREQ\_OUT has range of 10-60 kHz. In order to select optimal output PWM switching

frequency, user has to make tradeoff between the current ripple and the switching losses. Generally, motors having lower L/R ratio require higher PWM switching frequency to reduce current ripple.

### 6.3.18 PWM Dithering

MCF8315D provides the option of PWM dithering to reduce the EMI generated by MOSFET switching - when enabled, the PWM switching frequency is varied continuously (within a user configured frequency range) around the PWM\_FREQ\_OUT setting to spread the EMI energy across the frequency spectrum and reduce the EMI peak values. The user configured frequency range for PWM dithering is set by PWM\_DITHER\_DEPTH; setting PWM\_DITHER\_DEPTH to 0x0 disables PWM dithering. PWM\_DITHER\_DEPTH provides  $\pm 5\%$ ,  $\pm 7.5\%$  and  $\pm 10\%$  frequency spread options. When PWM\_FREQ\_OUT is set to 25kHz and PWM\_DITHER\_DEPTH is set to  $\pm 10\%$ , the PWM switching frequency applied to the MOSFETs continuously varies between 22.5kHz (25kHz-10%) and 27.5kHz (25kHz+10%), thereby reducing the EMI peaks at multiples of 25kHz. PWM dithering is available in two modes - random or triangular (configured by PWM\_DITHER\_MODE). In random dithering, the PWM switching frequency is continuously varied randomly within the range set by PWM\_FREQ\_OUT and PWM\_DITHER\_DEPTH. In triangular dithering, the PWM switching frequency is varied at user configured slew rate (configured by PWM\_DITHER\_STEP) as shown in Figure 6-53.




**Figure 6-53. Triangular PWM Dithering**

The PWM switching frequency slew rate (PWM\_DITHER\_SLEW in Figure 6-53) is set as shown in Equation 11.

$$PWM\_DITHER\_SLEW \text{ (kHz/s)} = PWM\_DITHER\_STEP * SLEW\_SCALING \text{ FACTOR} \quad (11)$$

SLEW\_SCALING FACTOR varies with PWM switching frequency as listed in Table 6-5.

**Table 6-5. SLEW\_SCALING FACTOR vs PWM switching frequency**

| PWM switching frequency (kHz) | SLEW_SCALING FACTOR |
|-------------------------------|---------------------|
| 10                            | 1                   |
| 15                            | 2.25                |
| 20                            | 2                   |
| 25                            | 3.125               |
| 30                            | 4.5                 |
| 35                            | 3.0625              |
| 40                            | 4                   |
| 45                            | 5.0625              |
| 50                            | 6.25                |
| 55                            | 7.5625              |
| 60                            | 9                   |

### 6.3.19 PWM Modulation Schemes

The MCF8315D supports two different modulation schemes, namely, continuous and discontinuous space vector PWM modulation schemes. In continuous PWM modulation, all the three phases switch all the time as per the defined switching frequency. In discontinuous PWM modulation, one of the phases is clamped to ground for 120° electrical period, and the other two phases are pulse width modulated. The modulation scheme is configured using PWM\_MODE. Figure 6-54 shows the modulated average phase voltages for different modulation schemes.




**Figure 6-54. Continuous and Discontinuous PWM Modulation Phase Voltages**

Continuous modulation helps in reducing current ripple for motors having low inductance but it results in higher switching losses because all three phases are switching. Discontinuous modulation has lower switching losses due to only two phases switching at a time, but higher current ripple.

### 6.3.20 Dead Time Compensation

Dead time is inserted between the switching instants of high-side and low-side MOSFETs in a half-bridge leg to avoid shoot-through condition. Due to dead time insertion, the expected voltage and applied voltage at the phase node differ based on the phase current direction. The phase node voltage distortion introduces undesired distortion in the phase current causing audible noise. MCF8315D integrates a proprietary dead time compensation technique to remove this phase current distortion and greatly reduce the audible noise, thereby significantly improving the acoustic performance of the FOC in MCF8315D. This dead time compensation can be enabled or disabled by configuring DEADTIME\_COMP\_EN. Even when DEADTIME\_COMP\_EN is set to 1b (compensation enabled), dead time compensation is disabled when motor electrical frequency exceeds 108Hz and re-enabled when motor electrical frequency drops below 102Hz.

### 6.3.21 Motor Stop Options

The MCF8315D provides different options for stopping the motor which can be configured by MTR\_STOP.

#### 6.3.21.1 Coast (Hi-Z) Mode

Coast (Hi-Z) mode is configured by setting MTR\_STOP to 000b. When motor stop command is received, the MCF8315D will transition into a high impedance (Hi-Z) state by turning off all MOSFETs. When the MCF8315D transitions from driving the motor into a Hi-Z state, the inductive current in the motor windings continues to flow and the energy returns to the power supply through the body diodes in the MOSFET output stage (see example Figure 6-55).




**Figure 6-55. Coast (Hi-Z) Mode**

In this example, current is applied to the motor through the high-side phase-A MOSFET (HSA), high-side phase-B MOSFET (HSB) and returned through the low-side phase-C MOSFET (LSC). When motor stop command is received all 6 MOSFETs transition to Hi-Z state and the inductive energy returns to supply through body diodes of MOSFETs LSA, LSB and HSC.

### 6.3.21.2 Recirculation Mode

Recirculation mode is configured by setting MTR\_STOP to 001b. In order to prevent the inductive energy from returning to DC input supply during motor stop, the MCF8315D allows current to circulate within the MOSFETs by selectively turning OFF some of the active (ON) MOSFETs for a certain time (auto calculated recirculation time to allow the inductive current to decay to zero) before transitioning into Hi-Z by turning OFF the remaining MOSFETs.

Depending on the phase voltage pattern at the time of receiving the stop command, either low-side (see [Figure 6-56](#)) or high-side recirculation (see [Figure 6-57](#)) will be used to stop the motor without sending the inductive energy back to the DC input supply.




**Figure 6-56. Low-Side Recirculation**




**Figure 6-57. High-Side Recirculation**

**Note**

Recirculation stop will not be available when the motor is in open loop state or active braking state or during flux weakening or when lead angle is non-zero; in such cases, the motor stop mode is set by LOW\_SPEED\_RECIRC\_BRAKE\_EN.

### 6.3.21.3 Low-Side Braking

Low-side braking mode is configured by setting MTR\_STOP to 010b. When a motor stop command is received, the output speed is reduced to a value defined by BRAKE\_SPEED\_THRESHOLD prior to turning all low-side MOSFETs ON (see example [Figure 6-58](#)) for a time configured by MTR\_STOP\_BRK\_TIME. If the motor speed is below BRAKE\_SPEED\_THRESHOLD prior to receiving stop command, then the MCF8315D transitions directly into the brake state. After applying the brake for MTR\_STOP\_BRK\_TIME, the MCF8315D transitions into the Hi-Z state by turning OFF all MOSFETs.




**Figure 6-58. Low-Side Braking**

The MCF8315D can also enter low-side braking through BRAKE pin input. When BRAKE pin is pulled to HIGH state, the output speed is reduced to a value defined by BRAKE\_SPEED\_THRESHOLD prior to turning all low-side MOSFETs ON. In this case, MCF8315D stays in low-side brake state till BRAKE pin changes to LOW state.

### 6.3.21.4 High-Side Braking

High-side braking mode is configured by setting MTR\_STOP to 011b. When a motor stop command is received, the output speed is reduced to a value defined by BRAKE\_SPEED\_THRESHOLD prior to turning all high-side MOSFETs ON (see example [Figure 6-59](#)) for a time configured by MTR\_STOP\_BRK\_TIME. If the motor speed is below BRAKE\_SPEED\_THRESHOLD prior to receiving stop command, then the MCF8315D transitions directly into the brake state. After applying the brake for MTR\_STOP\_BRK\_TIME, the MCF8315D transitions into Hi-Z state by turning OFF all MOSFETs.




Figure 6-59. High-Side Braking

#### 6.3.21.5 Active Spin-Down

Active spin down mode is configured by setting MTR\_STOP to 100b. When a motor stop command is received, the MCF8315D reduces SPEED\_REF to ACT\_SPIN\_THR and then transitions to Hi-Z state by turning all MOSFETs OFF. The advantage of this mode is that by reducing SPEED\_REF, the motor is decelerated to lower speed thereby reducing the phase currents before entering Hi-Z. Now, when the motor transitions into Hi-Z state, the energy transfer to the power supply is reduced. The threshold ACT\_SPIN\_THR needs to be configured high enough for MCF8315D to not lose synchronization with the motor.

#### 6.3.22 Align Braking

##### Note

Align braking is available only when BRAKE\_PIN\_MODE is set to 1b.

Align braking is used to stop the motor at a user configured angle when a brake command is received either through a logic High signal on the BRAKE pin or by setting BRAKE\_INPUT to 01b. In this mode, on receiving the brake command, MCF8315D reduces the motor speed to a value defined by BRAKE\_SPEED\_THRESHOLD before bringing the motor to an "aligned stop" by continuously injecting a DC current through a particular phase pattern. The phase pattern during align brake is generated based on the angle at which align needs to be performed - this angle can be configured either as the last commutation angle when BRAKE\_SPEED\_THRESHOLD is reached (ALIGN\_BRAKE\_ANGLE\_SEL = 0b) or set directly using ALIGN\_ANGLE (when ALIGN\_BRAKE\_ANGLE\_SEL = 1b). The current limit during align braking is configured through ALIGN\_OR\_SLOW\_CURRENT\_ILIMIT.

#### 6.3.23 FG Configuration

The MCF8315D provides information about the motor speed through the Frequency Generate (FG) pin. In MCF8315D, the FG pin output is configured through FG\_CONFIG. When FG\_CONFIG is configured to 0b, the FG output is active as long as the MCF8315D is driving the motor. When FG\_CONFIG is configured to 1b, the MCF8315D provides an FG output until the motor back-EMF falls below FG\_BEMF\_THR.

##### 6.3.23.1 FG Output Frequency

The FG output frequency can be configured by FG\_DIV. Many applications require the FG output to provide a pulse for every mechanical rotation of the motor. Different FG\_DIV configurations can accomplish this for 2-pole up to 30-pole motors. FG\_DIV = 0000b provides an FG pulse every 120° (electrical) for backward compatibility with legacy 3-Hall sensed solutions.

Figure 6-60 shows the FG output when MCF8315D has been configured to provide FG pulses every 120° (elec.), once every electrical cycle (2 poles), once every two electrical cycle (4 poles), once every three electrical cycles (6 poles), once every four electrical cycles (8 poles), and so on.




**Figure 6-60. FG Frequency Divider**

#### 6.3.23.2 FG during Open and Closed Loop States

During closed loop operation, the driving speed (FG output frequency) and the actual motor speed are synchronized. During open-loop operation, however, FG may not reflect the actual motor speed.

The MCF8315D provides three options for controlling the FG output during open loop, as shown in [Figure 6-61](#). The selection of these options is configured through FG\_SEL.

If FG\_SEL is set to,

- 00b: When in open loop, the FG output is based on the driving frequency.
- 01b: When in open loop, the FG output will be driven high.
- 10b: The FG output will reflect the driving frequency during open loop operation in the first motor start-up cycle after power-on, sleep/standby; FG will be held high during open loop operation in subsequent start-up cycles.




**Figure 6-61. FG Behavior During Open Loop**

### 6.3.23.3 FG during Fault and Idle States

MCF8315D provides the option of configuring FG output during fault and idle (motor stopped due to zero speed command) states. FG output during fault state is configured by FG\_FAULT\_CONFIG and FG output during idle state is configured by FG\_IDLE\_CONFIG - FG can be configured as a low or high signal during fault and can also be configured as a low or high signal during idle state. This allows the use of FG signal to uniquely determine the motor operating condition (fault, idle, spinning). For example, FG output during fault can be configured as a low signal and FG output during idle state can be configured as a high signal and FG during motor spinning can be configured to be at mechanical speed - a low FG output indicates MCF8315D encountered a fault condition, a high FG output indicates motor is in idle state and a FG signal at 50% duty indicates motor spinning at a speed equal to FG frequency.

### Note

Motor is considered to be in stationary/idle state when back-EMF sensed at OUTx is less than STAT\_DETECT\_THR. STAT\_DETECT\_THR should be set sufficiently high to avoid spurious FG toggles due to noise in OUTx pins when motor is in stationary/idle state.

## 6.3.24 Protections

The MCF8315D is protected from a host of fault events including motor lock, VM undervoltage, AVDD undervoltage, buck undervoltage, charge pump undervoltage, overtemperature and overcurrent events. [Table 6-6](#) summarizes the response, recovery modes, power stage status, reporting mechanism for different faults.

### Note

1. Actionable faults (latched or retry) are always reported on nFAULT pin (as logic low).
2. Actionable faults (latched or retry) are reported on ALARM pin (as logic high) when ALARM\_PIN\_EN is set to 1b.
3. Report only faults are reported on nFAULT (as logic low) only when ALARM\_PIN\_EN is set to 0b. When ALARM\_PIN\_EN is set to 1b, report only faults are reported only on ALARM pin (as logic high) while nFAULT stays high (external or internal pull-up).
4. Priority order for multi-fault scenarios is latched > slower retry time fault > faster retry time fault > report only fault. For example, if a latched and retry fault happen simultaneously, the device stays latched in fault mode until user issues clear fault command by writing 1b to CLR\_FLT. If two retry faults with different retry times happen simultaneously, the device retries only after the longer (slower) retry time lapses.
5. Recovery refers only to state of FETs (Hi-Z or active) after the fault condition is removed. Automatic indicates that the device automatically recovers (and FETs are active) when retry time lapses after the fault condition is removed. Latched indicates that the device waits for clearing of fault condition (by writing 1b to CLR\_FLT bit) to make the FETs active again.
6. Actionable (latched or retry) faults can take up to 200-ms after fault response (FETs in Hi-Z) to be reported on nFAULT pin (as logic low), ALARM pin (as logic high) and fault status registers.
7. Latched faults can take up to 200-ms after CLR\_FLT command is issued (over I<sup>2</sup>C) to be cleared.
8. The fault state is latched when the cumulative number of automatic retry attempts (AUTO\_RETRY\_TIMES ≠ 000b) for all faults configured in automatic retry mode is reached. In this case, it is necessary to write 1b to CLR\_FLT\_RETRY\_COUNT bit when writing 1b to CLR\_FLT bit in ALGO\_CTRL1 register to reset the retry counter to zero while clearing the latched fault state.

**Table 6-6. Fault Action and Response**

| FAULT                                   | CONDITION                           | CONFIGURATION  | REPORT                                             | FETs        | DIGITAL         | RECOVERY                                         |
|-----------------------------------------|-------------------------------------|----------------|----------------------------------------------------|-------------|-----------------|--------------------------------------------------|
| VM undervoltage                         | $V_{VM} < V_{UVLO}$ (falling)       | —              | —                                                  | Hi-Z        | Disabled        | Automatic:<br>$V_{VM} > V_{UVLO}$ (rising)       |
| AVDD undervoltage                       | $V_{AVDD} < V_{AVDD\_UV}$ (falling) | —              | —                                                  | Hi-Z        | Disabled        | Automatic:<br>$V_{AVDD} > V_{AVDD\_UV}$ (rising) |
| Buck undervoltage<br>(BUCK_UV)          | $V_{FB\_BK} < V_{BK\_UV}$ (falling) | —              | —                                                  | Active/Hi-Z | Active/Disabled | Automatic:<br>$V_{FB\_BK} > V_{BK\_UV}$ (rising) |
| Charge pump<br>undervoltage<br>(VCP_UV) | $V_{CP} < V_{CPUV}$ (falling)       | —              | nFAULT and<br>GATE_DRIVER_FAULT_STATUS<br>register | Hi-Z        | Active          | Automatic:<br>$V_{VCP} > V_{CPUV}$ (rising)      |
| Over Voltage<br>Protection<br>(OVP)     | $V_{VM} > V_{OVP}$ (rising)         | OVP_EN = 0b    | None                                               | Active      | Active          | No action                                        |
|                                         |                                     | OVP_EN = 1b    | nFAULT and<br>GATE_DRIVER_FAULT_STATUS<br>register | Hi-Z        | Active          | Automatic:<br>$V_{VM} < V_{OVP}$ (falling)       |
| Over Current<br>Protection<br>(OCP)     | $I_{PHASE} > I_{OCP}$               | OCP_MODE = 00b | nFAULT and<br>GATE_DRIVER_FAULT_STATUS<br>register | Hi-Z        | Active          | Latched:<br>CLR_FLT                              |
|                                         |                                     | OCP_MODE = 01b | nFAULT and<br>GATE_DRIVER_FAULT_STATUS<br>register | Hi-Z        | Active          | Retry:<br>t <sub>RETRY</sub>                     |

**Table 6-6. Fault Action and Response (continued)**

| FAULT                                                 | CONDITION                                                | CONFIGURATION              | REPORT                                      | FETs             | DIGITAL  | RECOVERY                |
|-------------------------------------------------------|----------------------------------------------------------|----------------------------|---------------------------------------------|------------------|----------|-------------------------|
| Buck Overcurrent Protection (BUCK_OCP)                | $I_{BK} > I_{BK\_OCP}$                                   | —                          | —                                           | Hi-Z             | Disabled | Automatic               |
| Motor Lock (MTR_LCK)                                  | Motor lock: Abnormal Speed; No Motor Lock; Abnormal BEMF | MTR_LCK_MODE = 000b        | nFAULT and CONTROLLER_FAULT_STATUS register | Hi-Z             | Active   | Latched: CLR_FLT        |
|                                                       |                                                          | MTR_LCK_MODE = 001b        | nFAULT and CONTROLLER_FAULT_STATUS register | Low- side brake  | Active   | Latched: CLR_FLT        |
|                                                       |                                                          | MTR_LCK_MODE = 010b        | nFAULT and CONTROLLER_FAULT_STATUS register | High- side brake | Active   | Latched: CLR_FLT        |
|                                                       |                                                          | MTR_LCK_MODE = 011b        | nFAULT and CONTROLLER_FAULT_STATUS register | Hi-Z             | Active   | Retry: $t_{LCK\_RETRY}$ |
|                                                       |                                                          | MTR_LCK_MODE = 100b        | nFAULT and CONTROLLER_FAULT_STATUS register | Low- side brake  | Active   | Retry: $t_{LCK\_RETRY}$ |
|                                                       |                                                          | MTR_LCK_MODE = 101b        | nFAULT and CONTROLLER_FAULT_STATUS register | High- side brake | Active   | Retry: $t_{LCK\_RETRY}$ |
|                                                       |                                                          | MTR_LCK_MODE = 110b        | nFAULT and CONTROLLER_FAULT_STATUS register | Active           | Active   | No action               |
|                                                       |                                                          | MTR_LCK_MODE = 111b        | None                                        | Active           | Active   | No action               |
| Hardware Lock-Detection Current Limit (HW_LOCK_LIMIT) | $V_{SOX} > HW\_LOCK\_ILIMIT$                             | HW_LOCK_ILIMIT_MODE = 000b | nFAULT and CONTROLLER_FAULT_STATUS register | Hi-Z             | Active   | Latched: CLR_FLT        |
|                                                       |                                                          | HW_LOCK_ILIMIT_MODE = 001b | nFAULT and CONTROLLER_FAULT_STATUS register | Low-side brake   | Active   | Latched: CLR_FLT        |
|                                                       |                                                          | HW_LOCK_ILIMIT_MODE = 010b | nFAULT and CONTROLLER_FAULT_STATUS register | High-side brake  | Active   | Latched: CLR_FLT        |
|                                                       |                                                          | HW_LOCK_ILIMIT_MODE = 011b | nFAULT and CONTROLLER_FAULT_STATUS register | Hi-Z             | Active   | Retry: $t_{LCK\_RETRY}$ |
|                                                       |                                                          | HW_LOCK_ILIMIT_MODE = 100b | nFAULT and CONTROLLER_FAULT_STATUS register | Low-side brake   | Active   | Retry: $t_{LCK\_RETRY}$ |
|                                                       |                                                          | HW_LOCK_ILIMIT_MODE = 101b | nFAULT and CONTROLLER_FAULT_STATUS register | High-side brake  | Active   | Retry: $t_{LCK\_RETRY}$ |
|                                                       |                                                          | HW_LOCK_ILIMIT_MODE = 110b | nFAULT and CONTROLLER_FAULT_STATUS register | Active           | Active   | No action               |
|                                                       |                                                          | HW_LOCK_ILIMIT_MODE = 111b | None                                        | Active           | Active   | No action               |

**Table 6-6. Fault Action and Response (continued)**

| FAULT                                              | CONDITION                                                                                                                 | CONFIGURATION             | REPORT                                      | FETs            | DIGITAL | RECOVERY                                                        |
|----------------------------------------------------|---------------------------------------------------------------------------------------------------------------------------|---------------------------|---------------------------------------------|-----------------|---------|-----------------------------------------------------------------|
| Software Lock-Detection Current Limit (LOCK_LIMIT) | $V_{SOX} > LOCK\_LIMIT$                                                                                                   | LOCK_ILIMIT_MODE = 000b   | nFAULT and CONTROLLER_FAULT_STATUS register | Hi-Z            | Active  | Latched: CLR_FLT                                                |
|                                                    |                                                                                                                           | LOCK_ILIMIT_MODE = 001b   | nFAULT and CONTROLLER_FAULT_STATUS register | Low-side brake  | Active  | Latched: CLR_FLT                                                |
|                                                    |                                                                                                                           | LOCK_ILIMIT_MODE = 010b   | nFAULT and CONTROLLER_FAULT_STATUS register | High-side brake | Active  | Latched: CLR_FLT                                                |
|                                                    |                                                                                                                           | LOCK_ILIMIT_MODE = 011b   | nFAULT and CONTROLLER_FAULT_STATUS register | Hi-Z            | Active  | Retry: $t_{LCK\_RETRY}$                                         |
|                                                    |                                                                                                                           | LOCK_ILIMIT_MODE = 100b   | nFAULT and CONTROLLER_FAULT_STATUS register | Low-side brake  | Active  | Retry: $t_{LCK\_RETRY}$                                         |
|                                                    |                                                                                                                           | LOCK_ILIMIT_MODE = 101b   | nFAULT and CONTROLLER_FAULT_STATUS register | High-side brake | Active  | Retry: $t_{LCK\_RETRY}$                                         |
|                                                    |                                                                                                                           | LOCK_ILIMIT_MODE = 110b   | nFAULT and CONTROLLER_FAULT_STATUS register | Active          | Active  | No action                                                       |
|                                                    |                                                                                                                           | LOCK_ILIMIT_MODE = 111b   | None                                        | Active          | Active  | No action                                                       |
| IPD Timeout Fault (IPD_T1_FAULT and IPD_T2_FAULT)  | IPD TIME > 500ms (approx.), during IPD current ramp up or ramp down                                                       | IPD_TIMEOUT_FAULT_EN = 0b | —                                           | Active          | Active  | No action                                                       |
|                                                    |                                                                                                                           | IPD_TIMEOUT_FAULT_EN = 1b | nFAULT and CONTROLLER_FAULT_STATUS register | Hi-Z            | Active  | Retry: $t_{LCK\_RETRY}$                                         |
| IPD Frequency Fault (IPD_FREQ_FAULT)               | IPD pulse before the current decay in previous IPD pulse                                                                  | IPD_FREQ_FAULT_EN = 0b    | —                                           | Active          | Active  | No action                                                       |
|                                                    |                                                                                                                           | IPD_FREQ_FAULT_EN = 1b    | nFAULT and CONTROLLER_FAULT_STATUS register | Hi-Z            | Active  | Retry: $t_{LCK\_RETRY}$                                         |
| MPET IPD Fault (MPET_IPD_FAULT)                    | Same as IPD Timeout Fault during MPET R, L measurement                                                                    | —                         | nFAULT and CONTROLLER_FAULT_STATUS register | Hi-Z            | Active  | Latched: CLR_FLT                                                |
| MPET Back-EMF Fault (MPET_BEMF_FAULT)              | Motor Back EMF < STAT_DETECT_THR during MPET Ke and mechanical parameters measurement                                     | —                         | nFAULT and CONTROLLER_FAULT_STATUS register | Hi-Z            | Active  | Latched: CLR_FLT                                                |
| Maximum VM (overvoltage) fault                     | $V_{VM} > MAX\_VM\_MOTOR$ , if MAX_VM_MOTOR ≠ 000b                                                                        | MAX_VM_MODE = 0b          | nFAULT and CONTROLLER_FAULT_STATUS register | Hi-Z            | Active  | Latched: CLR_FLT                                                |
|                                                    |                                                                                                                           | MAX_VM_MODE = 1b          | nFAULT and CONTROLLER_FAULT_STATUS register | Hi-Z            | Active  | Automatic: ( $V_{VM} < MAX\_VM\_MOTOR - VOLTAGE\_HYSTERESIS$ )V |
| Minimum VM (undervoltage) fault                    | $V_{VM} < MIN\_VM\_MOTOR$ , if MIN_VM_MOTOR ≠ 000b                                                                        | MIN_VM_MODE = 0b          | nFAULT and CONTROLLER_FAULT_STATUS register | Hi-Z            | Active  | Latched: CLR_FLT                                                |
|                                                    |                                                                                                                           | MIN_VM_MODE = 1b          | nFAULT and CONTROLLER_FAULT_STATUS register | Hi-Z            | Active  | Automatic: ( $V_{VM} > MIN\_VM\_MOTOR + VOLTAGE\_HYSTERESIS$ )V |
| External Watchdog                                  | Watchdog tickle does not arrive before configured time interval when EXT_WDT_EN = 1b. Refer <a href="#">Section 6.5.5</a> | EXT_WDT_FAULT_MODE = 0b   | nFAULT and CONTROLLER_FAULT_STATUS register | Active          | Active  | No action                                                       |
|                                                    |                                                                                                                           | EXT_WDT_FAULT_MODE = 1b   | nFAULT and CONTROLLER_FAULT_STATUS register | Hi-Z            | Active  | Latched: CLR_FLT                                                |

**Table 6-6. Fault Action and Response (continued)**

| FAULT                          | CONDITION                                                                              | CONFIGURATION                | REPORT                                       | FETs                                              | DIGITAL | RECOVERY                                                                      |
|--------------------------------|----------------------------------------------------------------------------------------|------------------------------|----------------------------------------------|---------------------------------------------------|---------|-------------------------------------------------------------------------------|
| Current Loop Saturation        | Indication of current loop saturation due to lower $V_{VM}$                            | SATURATION_FLAGS_E<br>N = 1b | nFAULT and CONTROLLER_FAULT_STATUS register  | Active; motor speed may not reach speed reference | Active  | Automatic: motor will reach reference operating point upon exiting saturation |
| Speed Loop Saturation          | Indication of speed loop saturation due to lower $V_{VM}$ , lower ILIMIT setting etc., | SATURATION_FLAGS_E<br>N = 1b | nFAULT and CONTROLLER_FAULT_STATUS register  | Active; motor speed may not reach speed reference | Active  | Automatic: motor will reach reference operating point upon exiting saturation |
| Thermal warning (OTW)          | $T_J > T_{OTW}$                                                                        | OTW_REP = 0b                 | —                                            | Active                                            | Active  | No action                                                                     |
|                                |                                                                                        | OTW_REP = 1b                 | nFAULT and GATE_DRIVER_FAULT_STATUS register | Active                                            | Active  | No action                                                                     |
| FET thermal shutdown (TSD_FET) | $T_J > T_{TSD\_FET}$                                                                   | —                            | nFAULT and GATE_DRIVER_FAULT_STATUS register | Hi-Z                                              | Active  | Automatic:<br>$T_J < T_{TSD\_FET} - T_{TSD\_FET\_HYS}$                        |

### 6.3.24.1 VM Supply Undervoltage Lockout

If at any time the input supply voltage on the VM pin falls lower than the  $V_{UVLO}$  threshold (VM UVLO falling threshold), all the integrated FETs, driver charge-pump and digital logic are disabled as shown in Figure 6-62. MCF8315D goes into reset state whenever VM UVLO event occurs.




**Figure 6-62. VM Supply Undervoltage Lockout**

### 6.3.24.2 AVDD Undervoltage Lockout (AVDD\_UV)

If at any time the voltage on the AVDD pin falls lower than the  $V_{AVDD\_UV}$  threshold, all the integrated FETs, driver charge-pump and digital logic controller are disabled. Since internal circuitry in MCF8315D is powered through the AVDD regulator, MCF8315D goes into reset state whenever AVDD UV event occurs.

### 6.3.24.3 BUCK Under Voltage Lockout (BUCK\_UV)

If at any time the voltage on the FB\_BK pin falls lower than the  $V_{BK\_UVLO}$  threshold, a buck UV fault is recognized - MCF8315D continues to attempt regulating the FB\_BK voltage to set value. Since internal circuitry in MCF8315D is powered through the buck regulator, MCF8315D may go into reset state if FB\_BK voltage drops low enough to trigger UV on the internal circuits.

### 6.3.24.4 VCP Charge Pump Undervoltage Lockout (CPUV)

If at any time the voltage on the VCP pin (charge pump) falls lower than the  $V_{CPUV}$  threshold, all the integrated FETs are disabled and the nFAULT pin is driven low. The DRIVER\_FAULT and VCP\_UV bits are set to 1b in the status registers. Normal operation resumes (driver operation and the nFAULT pin is released) when the VCP undervoltage condition clears. The VCP\_UV bit stays set until cleared through the CLR\_FLT bit.

### 6.3.24.5 Overvoltage Protection (OVP)

If at any time input supply voltage on the VM pins rises higher than  $V_{OVP}$ , all the integrated FETs are disabled and the nFAULT pin is driven low. The DRIVER\_FAULT and OVP bits are set to 1b in the status registers. Normal operation resumes (driver operation and the nFAULT pin is released) when the OVP condition clears. The OVP bit stays set until cleared through the CLR\_FLT bit. Setting the OVP\_EN to 0b disables this protection feature.

The OVP threshold can be set to 22-V or 34-V based on the OVP\_SEL bit.




Figure 6-63. Over Voltage Protection

#### 6.3.24.6 Overcurrent Protection (OCP)

MOSFET overcurrent event is sensed by monitoring the current flowing through the FETs. If the current across a FET exceeds the  $I_{OCP}$  threshold for longer than the deglitch time  $t_{OCP}$ , an OCP event is recognized and action is taken according to OCP\_MODE. The  $I_{OCP}$  threshold is set through the OCP\_LVL,  $t_{OCP}$  is set through OCP\_DEG and the OCP\_MODE can be configured in two different modes: latched shutdown and automatic retry.

##### 6.3.24.6.1 OCP Latched Shutdown (OCP\_MODE = 00b)

When an OCP event happens in this mode, all MOSFETs are disabled and the nFAULT pin is driven low. The DRIVER\_FAULT, OCP and corresponding FET's OCP bits are set to 1b in the status registers. Normal operation resumes (driver operation and the nFAULT pin is released) when the OCP condition clears and a clear fault command is issued through the CLR\_FLT bit.




Figure 6-64. Overcurrent Protection - Latched Shutdown Mode

##### 6.3.24.6.2 OCP Automatic Retry (OCP\_MODE = 01b)

When an OCP event happens in this mode, all the FETs are disabled and the nFAULT pin is driven low. The DRIVER\_FAULT, OCP and corresponding FET's OCP bits are set to 1b in the fault status registers.

Normal operation resumes automatically (gate driver operation and the nFAULT pin is released) after the  $t_{\text{RETRY}}$  (TRETRY) time elapses. The DRIVER\_FAULT bit is reset to 0b after the  $t_{\text{RETRY}}$  period expires. The OCP and corresponding FET's OCP bits are set to 1b until cleared through the CLR\_FLT bit.




**Figure 6-65. Overcurrent Protection - Automatic Retry Mode**

#### 6.3.24.7 Buck Overcurrent Protection

The buck overcurrent event is sensed by monitoring the current flowing through high-side MOSFET of the buck regulator. If the current through the high-side MOSFET exceeds the  $I_{\text{BK\_OCP}}$  threshold for a time longer than the deglitch time ( $t_{\text{OCP}}$ ), a buck OCP event is recognized and the buck regulator MOSFETs are disabled (Hi-Z). MCF8315D goes into reset state whenever buck OCP event occurs, since the internal circuitry in MCF8315D is powered from the buck regulator output.

#### 6.3.24.8 Hardware Lock Detection Current Limit (HW\_LOCK\_ILIMIT)

The hardware lock detection current limit function provides a configurable threshold for limiting the current to prevent damage to the system. The MCF8315D continuously monitors motor phase currents using comparators. If at any time, any phase current exceeds HW\_LOCK\_ILIMIT threshold for a time longer than  $t_{\text{HW\_LOCK\_ILIMIT}}$ , a HW\_LOCK\_ILIMIT event is recognized and action is taken according to the HW\_LOCK\_ILIMIT\_MODE. The current threshold is set by HW\_LOCK\_ILIMIT and the deglitch time,  $t_{\text{HW\_LOCK\_ILIMIT}}$  is set by HW\_LOCK\_ILIMIT\_DEG. HW\_LOCK\_ILIMIT\_MODE can be set in four different modes: HW\_LOCK\_ILIMIT latched shutdown, HW\_LOCK\_ILIMIT automatic retry, HW\_LOCK\_ILIMIT report only, and HW\_LOCK\_ILIMIT disabled.

##### 6.3.24.8.1 HW\_LOCK\_ILIMIT Latched Shutdown

When a HW\_LOCK\_ILIMIT event happens in this mode, the status of MOSFET will be configured by HW\_LOCK\_ILIMIT\_MODE and nFAULT is driven low. Status of MOSFETs during HW\_LOCK\_ILIMIT:

- HW\_LOCK\_ILIMIT\_MODE = 000b: All MOSFETs are turned OFF.
- HW\_LOCK\_ILIMIT\_MODE = 001b: All low-side MOSFETs are turned ON.
- HW\_LOCK\_ILIMIT\_MODE = 010b: All high-side MOSFETs are turned ON.

The CONTROLLER\_FAULT and HW\_LOCK\_ILIMIT bits are set to 1b in the fault status registers. Normal operation resumes (gate driver operation and the nFAULT pin is released) when the HW\_LOCK\_ILIMIT condition clears and a clear fault command is issued through the CLR\_FLT bit.

#### 6.3.24.8.2 HW\_LOCK\_ILIMIT Automatic Recovery

When a HW\_LOCK\_ILIMIT event happens in this mode, the status of MOSFET will be configured by HW\_LOCK\_ILIMIT\_MODE and nFAULT is driven low. Status of MOSFET during HW\_LOCK\_ILIMIT:

- HW\_LOCK\_ILIMIT\_MODE = 011b: All MOSFETs are turned OFF.
- HW\_LOCK\_ILIMIT\_MODE = 100b: All low-side MOSFETs are turned ON
- HW\_LOCK\_ILIMIT\_MODE = 101b: All high-side MOSFETs are turned ON

The CONTROLLER\_FAULT and HW\_LOCK\_ILIMIT bits are set to 1b in the fault status registers. Normal operation resumes automatically (gate driver operation and the nFAULT pin is released) after the  $t_{LCK\_RETRY}$  (configured by LCK\_RETRY) time lapses. The CONTROLLER\_FAULT and HW\_LOCK\_ILIMIT bits are reset to 0b after the  $t_{LCK\_RETRY}$  period expires.

#### 6.3.24.8.3 HW\_LOCK\_ILIMIT Report Only

No protective action is taken when a HW\_LOCK\_ILIMIT event happens in this mode (HW\_LOCK\_ILIMIT\_MODE = 110b). The hardware lock detection current limit event is reported by setting the CONTROLLER\_FAULT and HW\_LOCK\_ILIMIT bits to 1b in the fault status registers. The gate drivers continue to operate. The external controller manages this condition by acting appropriately. The reporting clears when the HW\_LOCK\_ILIMIT condition clears and a clear fault command is issued through the CLR\_FLT bit.

#### 6.3.24.8.4 HW\_LOCK\_ILIMIT Disabled

No action is taken when a HW\_LOCK\_ILIMIT event happens in this mode (HW\_LOCK\_ILIMIT\_MODE = 111b).

#### 6.3.24.9 Lock Detection Current Limit (LOCK\_ILIMIT)

The lock detection current limit function provides a configurable threshold for limiting the current to prevent damage to the system. The MCF8315D continuously monitors the motor phase currents through the ADC. If at any time, any phase current exceeds LOCK\_ILIMIT for a time longer than  $t_{LCK\_ILIMIT}$ , a LOCK\_ILIMIT event is recognized and action is taken according to LOCK\_ILIMIT\_MODE. The current threshold is set by LOCK\_ILIMIT and the deglitch time,  $t_{LCK\_ILIMIT}$  is set by LOCK\_ILIMIT\_DEG. LOCK\_ILIMIT\_MODE can be set in four different modes: LOCK\_ILIMIT latched shutdown, LOCK\_ILIMIT automatic retry, LOCK\_ILIMIT report only and LOCK\_ILIMIT disabled.

##### 6.3.24.9.1 LOCK\_ILIMIT Latched Shutdown

When a LOCK\_ILIMIT event happens in this mode, the status of MOSFETs will be configured by LOCK\_ILIMIT\_MODE and nFAULT is driven low. Status of MOSFETs during LOCK\_ILIMIT:

- LOCK\_ILIMIT\_MODE = 000b: All MOSFETs are turned OFF.
- LOCK\_ILIMIT\_MODE = 001b: All low-side MOSFETs are turned ON.
- LOCK\_ILIMIT\_MODE = 010b: All high-side MOSFETs are turned ON.

The CONTROLLER\_FAULT and LOCK\_ILIMIT bits are set to 1b in the fault status registers. Normal operation resumes (gate driver operation and the nFAULT pin is released) when the LOCK\_ILIMIT condition clears and a clear fault command is issued through the CLR\_FLT bit.

##### 6.3.24.9.2 LOCK\_ILIMIT Automatic Recovery

When a LOCK\_ILIMIT event happens in this mode, the status of MOSFETs will be configured by LOCK\_ILIMIT\_MODE and nFAULT is driven low. Status of MOSFETs during LOCK\_ILIMIT:

- LOCK\_ILIMIT\_MODE = 011b: All MOSFETs are turned OFF.
- LOCK\_ILIMIT\_MODE = 100b: All low-side MOSFETs are turned ON
- LOCK\_ILIMIT\_MODE = 101b: All high-side MOSFETs are turned ON

The CONTROLLER\_FAULT and LOCK\_ILIMIT bits are set to 1b in the fault status registers. Normal operation resumes automatically (gate driver operation and the nFAULT pin is released) after the  $t_{LCK\_RETRY}$  (configured by LCK\_RETRY) time lapses. The CONTROLLER\_FAULT and LOCK\_ILIMIT bits are reset to 0b after the  $t_{LCK\_RETRY}$  period expires.

#### 6.3.24.9.3 LOCK\_ILIMIT Report Only

No protective action is taken when a LOCK\_ILIMIT event happens in this mode (LOCK\_ILIMIT\_MODE = 110b). The lock detection current limit event is reported by setting the CONTROLLER\_FAULT and LOCK\_ILIMIT bits to 1b in the fault status registers. The gate drivers continue to operate. The external controller manages this condition by acting appropriately. The reporting clears when the LOCK\_ILIMIT condition clears and a clear fault command is issued through the CLR\_FLT bit.

#### 6.3.24.9.4 LOCK\_ILIMIT Disabled

No action is taken when a LOCK\_ILIMIT event happens in this mode (LOCK\_ILIMIT\_MODE = 111b).

### 6.3.24.10 Motor Lock Detection

The MCF8315D provides different lock detect mechanisms to determine if the motor is in a locked state. Multiple detection mechanisms work together to ensure the lock condition is detected quickly and reliably. In addition to detecting if there is a locked motor condition, the MCF8315D can also identify and take action if there is no motor connected to the system. Each of the lock detect mechanisms and the no-motor detection can be disabled by their respective register bits (LOCK1/2/3\_EN).

#### 6.3.24.10.1 Lock 1: Abnormal Speed (ABN\_SPEED)

MCF8315D monitors the speed continuously and at any time the speed exceeds LOCK\_ABN\_SPEED, an ABN\_SPEED lock event is recognized and action is taken according to the MTR\_LCK\_MODE. The threshold is set through the LOCK\_ABN\_SPEED register. ABN\_SPEED lock can be enabled/disabled by LOCK1\_EN.

#### 6.3.24.10.2 Lock 2: Abnormal BEMF (ABN\_BEMF)

MCF8315D estimates back-EMF in order to run motor optimally in closed loop. This estimated back-EMF is compared against the expected back-EMF calculated using the estimated speed and the BEMF constant. Whenever motor is stalled the estimated back-EMF is inaccurate due to lower back-EMF at low speed. When the difference between estimated and expected back-EMF exceeds ABNORMAL\_BEMF\_THR for ABNORMAL\_BEMF\_PERSISTENT\_TIME, an abnormal BEMF fault is triggered and action is taken according to the MTR\_LCK\_MODE.

ABN\_BEMF lock can be enabled/disabled by LOCK2\_EN.

#### 6.3.24.10.3 Lock3: No-Motor Fault (NO\_MTR)

The MCF8315D continuously monitors phase currents on all three phases; if any phase current stays below NO\_MTR\_THR for 500ms, a NO\_MTR event is recognized. The response to the NO\_MTR event is configured through MTR\_LCK\_MODE. NO\_MTR lock can be enabled/disabled by LOCK3\_EN.

---

#### Note

- No motor fault is disabled when motor speed is < 2Hz.
  - No motor fault is unavailable (even when enabled) during motor start-up (IPD or align or double align) state - it is available (when enabled) in open and closed loop states
  - No motor fault detection during closed loop can be disabled by setting NO\_MTR\_FLT\_CLOSEDLOOP\_DIS to 1b.
- 

### 6.3.24.11 Motor Lock (MTR\_LCK)

The MCF8315D continuously checks for different motor lock conditions (see [Motor Lock Detection](#)) during motor operation. When one of the enabled lock condition happens, a MTR\_LCK event is recognized and action is taken according to the MTR\_LCK\_MODE.

All locks can be enabled or disabled individually and retry times can be configured through LCK\_RETRY. MTR\_LCK\_MODE bit can operate in four different modes: MTR\_LCK latched shutdown, MTR\_LCK automatic retry, MTR\_LCK report only and MTR\_LCK disabled.

#### 6.3.24.11.1 MTR\_LCK Latched Shutdown

When a MTR\_LCK event happens in this mode, the status of MOSFETs will be configured by MTR\_LCK\_MODE and nFAULT is driven low. Status of MOSFETs during MTR\_LCK:

- MTR\_LCK\_MODE = 000b: All MOSFETs are turned OFF.
- MTR\_LCK\_MODE = 001b: All low-side MOSFETs are turned ON.
- MTR\_LCK\_MODE = 010b: All high-side MOSFETs are turned ON.

The CONTROLLER\_FAULT, MTR\_LCK and respective motor lock condition bits are set to 1b in the fault status registers. Normal operation resumes (gate driver operation and the nFAULT pin is released) when the MTR\_LCK condition clears and a clear fault command is issued through the CLR\_FLT bit.

#### 6.3.24.11.2 MTR\_LCK Automatic Recovery

When a MTR\_LCK event happens in this mode, the status of MOSFETs will be configured by MTR\_LCK\_MODE and nFAULT is driven low. Status of MOSFETs during MTR\_LCK:

- MTR\_LCK\_MODE = 011b: All MOSFETs are turned OFF.
- MTR\_LCK\_MODE = 100b: All low-side MOSFETs are turned ON.
- MTR\_LCK\_MODE = 101b: All high-side MOSFETs are turned ON.

The CONTROLLER\_FAULT, MTR\_LCK and respective motor lock condition bits are set to 1b in the fault status registers. Normal operation resumes automatically (gate driver operation and the nFAULT pin is released) after the  $t_{LCK\_RETRY}$  (configured by LCK\_RETRY) time lapses. The CONTROLLER\_FAULT, MTR\_LCK and respective motor lock condition bits are reset to 0b after the  $t_{LCK\_RETRY}$  period expires.

#### 6.3.24.11.3 MTR\_LCK Report Only

No protective action is taken when a MTR\_LCK event happens in this mode (MTR\_LCK\_MODE = 110b). The motor lock event is reported by setting the CONTROLLER\_FAULT, MTR\_LCK and respective motor lock condition bits to 1b in the fault status registers. The gate drivers continue to operate. The external controller manages this condition by acting appropriately. The reporting clears when the MTR\_LCK condition clears and a clear fault command is issued through the CLR\_FLT bit.

#### 6.3.24.11.4 MTR\_LCK Disabled

No action is taken when a MTR\_LCK event happens in this mode (MTR\_LCK\_MODE = 111b).

#### 6.3.24.12 EEPROM Fault

MCF8315D provides an EEPROM fault detection feature to prevent device operation when there is EEPROM data mismatch due to an interrupted EEPROM write (UVLO during EEPROM write), EEPROM aging etc., MCF8315D implements a CRC and parity check whenever an EEPROM read command is issued - if there is a CRC or parity mismatch, an EEPROM fault is recognized and action taken according to EEP\_FAULT\_MODE. If EEP\_FAULT\_MODE is set to 0b, nFAULT is pulled low, the FETs are in Hi-Z and the CONTROLLER\_FAULT and EEPROM\_ERR\_STATUS bits are set to 1b until the fault condition is cleared by writing 1b to CLR\_FLT. If EEP\_FAULT\_MODE is set to 1b, this fault is reported on nFAULT pin and CONTROLLER\_FAULT, EEPROM\_ERR\_STATUS bits are set to 1b but the device operation (FETs) continues normally. The fault reporting can be cleared (nFAULT pin is released, CONTROLLER\_FAULT, EEPROM\_ERR\_STATUS set to 0b) by writing 1b to CLR\_FLT.

#### Note

- An EEPROM read command is internally issued by the device at every power-up/wake-up to load the configurations from EEPROM into the shadow/RAM registers.
- A successful EEPROM write can fix EEPROM data mismatch. When an EEPROM write is successfully completed, MCF8315D automatically updates the internal CRC for the new EEPROM values - this updated CRC will be used during subsequent EEPROM read commands to check for EEPROM data mismatch.
- An EEPROM write can happen even when the device is in fault state.

#### 6.3.24.13 I<sup>2</sup>C CRC Fault

MCF8315D provides I<sup>2</sup>C CRC fault detection feature to detect errors in an I<sup>2</sup>C transaction. MCF8315D implements a CRC check on the entire I<sup>2</sup>C packet when I<sup>2</sup>C CRC is enabled - if there is a CRC mismatch, an I<sup>2</sup>C CRC fault is recognized and action taken according to CRC\_ERR\_MODE. If CRC\_ERR\_MODE is set to 0b, nFAULT is pulled low, the FETs are in Hi-Z and the CONTROLLER\_FAULT and I2C\_CRC\_FAULT\_STATUS bits are set to 1b until the fault condition is cleared by writing 1b to CLR\_FLT. If EEP\_FAULT\_MODE is set to 1b, this fault is reported on nFAULT pin and CONTROLLER\_FAULT, I2C\_CRC\_FAULT\_STATUS bits are set to 1b but the device operation (FETs) continues normally. The fault reporting can be cleared (nFAULT pin is released, CONTROLLER\_FAULT, I2C\_CRC\_FAULT\_STATUS set to 0b) by writing 1b to CLR\_FLT.

#### 6.3.24.14 Minimum VM (Undervoltage) Protection

MCF8315D provides a configurable VM undervoltage protection. The VM level at which MCF8315D triggers the undervoltage fault is set by MIN\_VM\_MOTOR and the fault response to VM undervoltage is set by MIN\_VM\_MODE. If MIN\_VM\_MODE is set to 0b, VM undervoltage fault (at MIN\_VM\_MOTOR) is latched and the FETs are in Hi-Z until the fault condition is cleared by writing 1b to CLR\_FLT bit. If MIN\_VM\_MODE is set to 1b, VM undervoltage fault (at MIN\_VM\_MOTOR) automatically clears and the device starts motor operation once VM > (MIN\_VM\_MOTOR + VOLTAGE\_HYSTERESIS).

#### 6.3.24.15 Maximum VM (Overvoltage) Protection

MCF8315D provides a configurable VM overvoltage protection. The VM level at which MCF8315D triggers the overvoltage fault is set by MAX\_VM\_MOTOR and the fault response to VM overvoltage is set by MAX\_VM\_MODE. If MAX\_VM\_MODE is set to 0b, VM overvoltage fault (at MAX\_VM\_MOTOR) is latched and the FETs are in Hi-Z until the fault condition is cleared by writing 1b to CLR\_FLT bit. If MAX\_VM\_MODE is set to 1b, VM overvoltage fault (at MAX\_VM\_MOTOR) automatically clears and the device starts motor operation once VM < (MAX\_VM\_MOTOR - VOLTAGE\_HYSTERESIS).

#### 6.3.24.16 MPET Faults

An error during resistance and inductance measurement is reported using MPET\_IPD\_FAULT. The MPET\_IPD\_FAULT gets triggered when the IPD timer overflows due to unsuccessful attempt to ramp up the current to the threshold value, same as explained in [Section 6.3.24.17](#). The fault typically gets triggered when there is no motor connected to MCF8315D or when the MPET IPD current threshold is set high for motors with high resistance.

An error during BEMF constant measurement is reported using MPET\_BEMF\_FAULT. This fault gets triggered when the measured back EMF is less than the threshold set in STAT\_DETECT\_THR. One example of such fault scenario can be the motor stall while running in open loop due to incorrect open loop configuration used.

#### 6.3.24.17 IPD Faults

The MCF8315D uses 12-bit timers to estimate the time during the current ramp up and ramp down during IPD, when the motor start-up is configured as IPD (MTR\_STARTUP is set to 10b). During IPD, the algorithm checks for a successful current ramp-up to IPD\_CURR\_THR, starting with an IPD clock of 10MHz; if unsuccessful (timer overflow before current reaches IPD\_CURR\_THR), IPD is repeated with lower frequency clocks of 1MHz, 100kHz, and 10kHz sequentially. If the IPD timer overflows (current does not reach IPD\_CURR\_THR) with all the four clock frequencies, then the IPD\_T1\_FAULT gets triggered. Similarly the algorithm checks for a successful current decay to zero during IPD current ramp down using all the mentioned IPD clock frequencies. If the IPD timer overflows (current does not ramp down to zero) in all the four attempts, then the IPD\_T2\_FAULT gets triggered. The user can enable IPD timeout (IPD timer overflow) by setting IPD\_TIMEOUT\_FAULT\_EN to 1b.

IPD gives incorrect results if the next IPD pulse is commanded before the complete decay of current due to present IPD pulse. The MCF8315D can generate a fault called IPD\_FREQ\_FAULT during such a scenario by setting IPD\_FREQ\_FAULT\_EN to 1b. The IPD\_FREQ\_FAULT maybe triggered if the IPD frequency is too high for the IPD current limit and the IPD release mode or if the motor inductance is too high for the IPD frequency, IPD current limit and IPD release mode.

On the occurrence of any IPD fault, MCF8315D stops the IPD based start-up process and FETs are in Hi-Z. MCF8315D automatically retries IPD based start-up after  $t_{LCK\_RETRY}$  elapses.

#### **6.3.24.18 FET Thermal Warning (OTW)**

If the FET temperature exceeds the FET thermal warning limit ( $T_{OTW}$ ), nFAULT is pulled low and the OT and OTW bits in the gate driver status register are set to 1b. The reporting of OTW (on nFAULT and status bits) can be enabled by setting OTW\_REP to 1b. The device performs no additional action and continues to function. The nFAULT pin is pulled low and OTW bit remains set until cleared through the CLR\_FLT bit and the die temperature is lower than thermal warning limit. ( $T_{OTW} - T_{OTW\_HYS}$ ).

#### **6.3.24.19 FET Thermal Shutdown (TSD\_FET)**

If the FET temperature exceeds the FET thermal shutdown limit ( $T_{TSD\_FET}$ ), all the FETs are disabled, the charge pump is shut down, and the nFAULT pin is driven low. In addition, the DRIVER\_FAULT, OT and OTS bit in the status register are set to 1b. Normal operation resumes (driver operation and the nFAULT pin is released) when the die temperature decreases below the hysteresis point of the thermal shutdown limit ( $T_{TSD\_FET} - T_{TSD\_FET\_HYS}$ ). The OTS bit stays latched high indicating that a thermal event occurred until a clear fault command is issued through the CLR\_FLT bit. This protection feature cannot be disabled.

---

#### **Note**

If die temperature increases to  $T_{TSD\_BUCK}$ , MCF8315D will undergo a reset and all fault status bits in this case will be reset to 0b.

---

## 6.4 Device Functional Modes

### 6.4.1 Functional Modes

#### 6.4.1.1 Sleep Mode

In sleep mode, the MOSFETs, sense amplifiers, buck regulator, charge pump, AVDD LDO regulator and the I<sup>2</sup>C bus are disabled. The device can be configured to enter sleep (instead of standby) mode by configuring DEV\_MODE to 1b. SPEED pin and I<sup>2</sup>C speed command determine entry and exit from sleep state as described in [Table 6-8](#).

#### 6.4.1.2 Standby Mode

The device can be configured to operate as a standby device by setting DEV\_MODE to 0b. In standby mode, the charge pump, AVDD LDO, buck regulator and I<sup>2</sup>C bus are active while the motor is in stopped state waiting for a suitable non-zero speed command. SPEED pin (analog, PWM or frequency based speed input) or I<sup>2</sup>C speed command (I<sup>2</sup>C based speed input) determines entry and exit from standby state as described in [Table 6-8](#).

The thresholds for entering and exiting standby mode in different input modes are as follows,

**Table 6-7. Standby Mode Entry/Exit Thresholds**

| Input Source (SPEED_MODE) | Standby entry/exit thresholds             | REF_PROFILE_CONFIG = 00b                                                   | REF_PROFILE_CONFIG ≠ 00b |
|---------------------------|-------------------------------------------|----------------------------------------------------------------------------|--------------------------|
| Analog (00b)              | V <sub>EN_SB</sub>                        | 1% x V <sub>ANA_FS</sub>                                                   | 1% x V <sub>ANA_FS</sub> |
|                           | V <sub>EX_SB</sub>                        | 5% x V <sub>ANA_FS</sub>                                                   | 5% x V <sub>ANA_FS</sub> |
| PWM (01b)                 | Duty <sub>EX_SB/EN_SB</sub>               | Maximum of (1%, DUTY_HYS)                                                  | 0%                       |
| I <sup>2</sup> C (10b)    | DIGITAL_SPEED_CTRL <sub>EX_SB/EN_SB</sub> | Maximum of (1%, DUTY_HYS) x 32767                                          | 0                        |
| Frequency (11b)           | Freq <sub>EX_SB/EN_SB</sub>               | Maximum of (1%, DUTY_HYS) x INPUT_MAXIMUM_FREQ (subject to minimum of 3Hz) | < 3Hz                    |

**Table 6-8. Conditions to Enter or Exit Sleep/Standby Modes**

| SPEED COMMAND MODE | ENTER STANDBY CONDITION                                  | EXIT FROM STANDBY CONDITION                              | ENTER SLEEP CONDITION                                                                         | EXIT FROM SLEEP CONDITION                                        |
|--------------------|----------------------------------------------------------|----------------------------------------------------------|-----------------------------------------------------------------------------------------------|------------------------------------------------------------------|
| Analog             | V <sub>SPEED</sub> < V <sub>EN_SB</sub>                  | V <sub>SPEED</sub> > V <sub>EX_SB</sub>                  | V <sub>SPEED</sub> < V <sub>EN_SL</sub> for t <sub>DET_SL_ANA</sub>                           | V <sub>SPEED</sub> > V <sub>EX_SL</sub> for t <sub>DET_ANA</sub> |
| PWM                | Duty <sub>SPEED</sub> < Duty <sub>EN_SB</sub>            | Duty <sub>SPEED</sub> > Duty <sub>EX_SB</sub>            | V <sub>SPEED</sub> < V <sub>IL</sub> for t <sub>DET_SL_PWM</sub>                              | V <sub>SPEED</sub> > V <sub>IH</sub> for t <sub>DET_PWM</sub>    |
| I <sup>2</sup> C   | DIGITAL_SPEED_CTRL < DIGITAL_SPEED_CTRL <sub>EN_SB</sub> | DIGITAL_SPEED_CTRL > DIGITAL_SPEED_CTRL <sub>EX_SB</sub> | DIGITAL_SPEED_CTRL is set to 0b for SLEEP_ENTRY_TIME and V <sub>SPEED</sub> < V <sub>IL</sub> | V <sub>SPEED</sub> > V <sub>IH</sub> for t <sub>DET_PWM</sub>    |
| Frequency          | Freq <sub>SPEED</sub> < Freq <sub>EN_SB</sub>            | Freq <sub>SPEED</sub> > Freq <sub>EX_SB</sub>            | V <sub>SPEED</sub> < V <sub>IL</sub> for t <sub>DET_SL_PWM</sub>                              | V <sub>SPEED</sub> > V <sub>IH</sub> for t <sub>DET_PWM</sub>    |

#### Note

V<sub>SPEED</sub> : SPEED pin input voltage, Duty<sub>SPEED</sub> : SPEED pin input PWM duty, Freq<sub>SPEED</sub> : SPEED pin input frequency

#### 6.4.1.3 Fault Reset (CLR\_FLT)

In the case of latched faults, the device goes into a partial shutdown state to help protect the power MOSFETs and system. When the fault condition clears, the device can go to the operating state again by setting the CLR\_FLT to 1b.

## 6.5 External Interface

### 6.5.1 DRVOFF Functionality

When DRVOFF pin is driven high, all six MOSFETs are put in Hi-Z state, irrespective of speed command. If motor speed command is non-zero when DRVOFF is driven high, device may encounter a fault like no motor or abnormal BEMF. Whenever DRVOFF is driven high, it should be held high for a minimum of 10s for safe operation.

### 6.5.2 DAC outputs

MCF8315D has two 12-bit DACs which output analog voltage equivalent of digital variables on the DACOUT1 and DACOUT2 pins. The maximum DAC output voltage is 3-V. Signals available on DACOUT pins are useful in tracking internal variables in real-time and can be used for tuning speed controller or motor acceleration time. The address for variables to be tracked on DACOUT1 and DACOUT2 are configured using DACOUT1\_VAR\_ADDR and DACOUT2\_VAR\_ADDR respectively. DACOUT1 is available on pin 36 and DACOUT2 can be configured on pin 38 by setting DAC\_SOx\_SEL to 00b. DACOUT2 is also available on pin 37. DAC\_ENABLE should be configured to 1b for pins 36, 37 to function as DAC outputs.

### 6.5.3 Current Sense Output

MCF8315D can provide the built-in current sense amplifiers' output on the SOX pin. SOX output is available on pin 38 and can be configured by DAC\_SOx\_SEL.

### 6.5.4 Oscillator Source

MCF8315D has a built-in oscillator that is used as the clock source for all digital peripherals and timing measurements. Default configuration for MCF8315D is to use the internal oscillator and it is sufficient to drive the motor without need for any external crystal or clock sources.

In case MCF8315D does not meet accuracy requirements of timing measurement or speed loop, then MCF8315D has an option to support an external clock reference.

In order to improve EMI performance, MCF8315D provides the option of modulating the clock frequency by enabling Spread Spectrum Modulation (SSM) through SPREAD\_SPECTRUM\_MODULATION\_DIS.

#### 6.5.4.1 External Clock Source

Speed loop accuracy of MCF8315D over the operating temperature range can be improved by providing a more accurate clock reference on EXT\_CLK pin as shown in [Figure 6-66](#). EXT\_CLK will be used to calibrate the internal clock oscillator - this will help match the accuracy of the internal clock oscillator to that of the external clock. External clock source can be selected by setting EXT\_CLK\_EN to 1b. The external clock source frequency can be configured through EXT\_CLK\_CONFIG.




**Figure 6-66. External Clock Reference**

#### Note

External clock is optional and can be used when higher clock accuracy is needed. MCF8315D will always power up using the internal oscillator in all modes.

### 6.5.5 External Watchdog

MCF8315D provides an external watchdog feature - EXT\_WDT\_EN bit should be set to 1b to enable the external watchdog. When this feature is enabled, the device waits for a tickle (low to high transition in EXT\_WD pin, WATCHDOG\_TICKLE set to 1b in I<sup>2</sup>C mode) from the external watchdog input for a configured time interval; if the time interval between two consecutive tickles is higher than the configured time, a watchdog fault is triggered. The watchdog fault response can be configured using EXT\_WDT\_FAULT\_MODE either as a report only fault or as a latched fault with MOSFETs in Hi-Z state. The latched fault can be cleared by writing 1b to CLR\_FLT. When a watchdog timeout occurs, WATCHDOG\_FAULT bit is set to 1b. In case, the next tickle arrives before the configured time interval elapses, the watchdog timer is reset and it begins to wait for the next tickle. This can be used to continuously monitor the health of an external MCU (which is the external watchdog input) and put the MCF8315D MOSFETs in Hi-Z, in case the external MCU is in a fault/hang state.

The external watchdog input is selected using EXT\_WDT\_INPUT\_MODE and can either be the EXT\_WD pin or the I<sup>2</sup>C interface. The time interval between two tickles to trigger a watchdog fault is configured by EXT\_WDT\_CONFIG; there are 4 time settings - 100, 200, 500 and 1000ms for the EXT\_WD pin based watchdog and 4 time settings - 1, 2, 5 and 10s for the I<sup>2</sup>C based watchdog.

---

#### Note

Watchdog should be disabled by setting EXT\_WDT\_EN to 0b before changing EXT\_WDT\_CONFIG configuration.

---

## 6.6 EEPROM access and I<sup>2</sup>C interface

### 6.6.1 EEPROM Access

MCF8315D has 1024 bits (16 rows of 64 bits each) of EEPROM, which are used to store the motor configuration parameters. Erase operations are row-wise (all 64 bits are erased in a single erase operation), but 32-bit write and read operations are supported. EEPROM can be written and read using the I<sup>2</sup>C serial interface but erase cannot be performed using I<sup>2</sup>C serial interface. The shadow/RAM registers corresponding to the EEPROM are located at addresses 0x000080-0x0000AE.

---

#### Note

MCF8315D allows EEPROM write and read operations only when the motor is not spinning.

---

#### 6.6.1.1 EEPROM Write

---

#### Note

- EEPROM write should be issued only when device is in idle or fault state (motor not driven by device). VM should be  $\geq 6V$  throughout the EEPROM write process to ensure that all power rails (AVDD, FB\_BK and DVDD) stay within datasheet specifications and EEPROM write is never interrupted due to any UVLO condition.
  - TI does not recommend writing to EEPROM during every power-up/wake-up due to aging/write cycle limitations on number of EEPROM writes (20000 write cycles at  $T_J = 85^\circ C$ ). Repetitive register settings change can be done at shadow/RAM registers (0x000080-0x0000AE); only default configurations need to be written to EEPROM (at first power-up)
- 

In MCF8315D, EEPROM write procedure is as follows,

1. Write register 0x000080 (ISD\_CONFIG) with ISD and reverse drive configuration like resync enable, reverse drive enable, stationary detect threshold, reverse drive handoff threshold etc.
2. Write register 0x000082 (REV\_DRIVE\_CONFIG) with reverse drive and active brake configuration like reverse drive open loop acceleration, active brake current limit, Kp, Ki values etc.
3. Write register 0x000084 (MOTOR\_STARTUP1) with motor start-up configuration like start-up method, IPD parameters, align parameters etc.
4. Write register 0x000086 (MOTOR\_STARTUP2) with motor start-up configuration like open loop acceleration, open loop current limit, first cycle frequency etc.
5. Write register 0x000088 (CLOSED\_LOOP1) with motor control configuration like closed loop acceleration, overmodulation enable, PWM frequency, FG signal parameters etc.
6. Write register 0x00008A (CLOSED\_LOOP2) with motor control configuration like motor winding resistance and inductance, motor stop options, brake speed threshold etc.
7. Write register 0x00008C (CLOSED\_LOOP3) with motor control configuration like motor BEMF constant, current loop Kp, Ki etc.
8. Write register 0x00008E (CLOSED\_LOOP4) with motor control configuration like speed loop Kp, Ki and maximum speed.
9. Write register 0x000090 (FAULT\_CONFIG1) with fault control configuration software and hardware current limits, lock current limit and actions, retry times etc.
10. Write register 0x000092 (FAULT\_CONFIG2) with fault control configuration like hardware current limit actions, OV, UV limits and actions, abnormal speed level, no motor threshold etc.
11. Write registers 0x000094 – 0x00009E (SPEED\_PROFILES1-6) with speed profile configuration like profile type, duty cycle, speed clamp level, duty cycle clamp level etc.
12. Write register 0x0000A0 (INT\_ALGO\_1) with miscellaneous configuration like ISD run time and timeout, MPET parameters etc.
13. Write register 0x0000A2 (INT\_ALGO\_2) with miscellaneous configuration like additional MPET parameters, IPD high resolution enable, active brake current slew rate, closed loop slow acceleration etc.
14. Write registers 0x0000A4 (PIN\_CONFIG1) with pin configuration for speed input mode (analog or PWM), BRAKE pin mode etc.

15. Write registers 0x0000A6 and 0x0000A8 (DEVICE\_CONFIG1 and DEVICE\_CONFIG2) with device configuration like DAC/SOX, I<sup>2</sup>C target address, dynamic CSA gain enable, dynamic voltage gain enable, clock source select, speed range select etc.
16. Write register 0x0000AA (PERI\_CONFIG1) with peripheral configuration like dead time, bus current limit, DIR input, SSM enable etc.
17. Write registers 0x0000AC and 0x0000AE (GD\_CONFIG1 and GD\_CONFIG2) with gate driver configuration like slew rate, CSA gain, OCP level, mode, OVP enable, level, buck voltage level, buck current limit etc.
18. Write 0x8A500000 into register 0x0000EA to write the shadow/RAM register (0x000080-0x0000AE) values into the EEPROM.
19. Wait for 750ms for the EEPROM write operation to complete.
20. After 750ms, read 0x0000EA register to ensure it has been reset to 0x0. This confirms that the EEPROM write process has been completed successfully.

Steps 1-17 can be selectively executed based on registers/parameters that need to be modified. After all shadow/RAM registers have been updated with the required values, steps 18-20 should be executed to write the contents of the shadow/RAM registers into the EEPROM.

#### 6.6.1.2 EEPROM Read

In MCF8315D, EEPROM read procedure is as follows,

1. Write 0x40000000 into register 0x0000EA to read the EEPROM data into the shadow/RAM registers (0x000080-0x0000AE).
2. Wait for 100ms for the EEPROM read operation to complete.
3. Read the shadow/RAM register values, one or two registers at a time, using the I<sup>2</sup>C read command as explained in [Section 6.6.2](#). Shadow/RAM register addresses are in the range of 0x000080-0x0000AE. Register address increases in steps of 2 for 32-bit read operation (since each address is a 16-bit location).

#### 6.6.1.3 EEPROM Security

MCF8315D provides configurable read and write protection to EEPROM registers. The level of protection can be configured using EEPROM\_LOCK\_MODE as per following list,

- 00b : EEPROM read and write are allowed without a passcode
- 01b : EEPROM read and write need a valid passcode
- 10b : EEPROM read needs a valid passcode; EEPROM write is locked permanently
- 11b : EEPROM read and write are locked permanently

Passcode is a 15-bit field in the EEPROM denoted by EEPROM\_LOCK\_KEY in the DEVICE\_CONFIG1 register. EEPROM\_LOCK\_KEY is write accessible (when EEPROM\_LOCK\_MODE is set to 00b or 01b) but not read accessible.

When passcode based read/write protection is enabled (EEPROM\_LOCK\_MODE set to 01b or 10b), user has to write the passcode set in EEPROM\_LOCK\_KEY to USER\_EEPROM\_KEY bitfield in 0xF8 register after every power-up/wake-up before sending the first EEPROM read/write transaction over I<sup>2</sup>C. One valid passcode write after power-up/wake-up is sufficient for all subsequent EEPROM read/write transactions as long as there is no power reset, sleep mode entry, digital reset or incorrect passcode write. If an invalid passcode is written, the subsequent EEPROM read/write transactions are rejected - MCF8315D does not respond to the read/write requests. The read/write protection is applicable to EEPROM as well as the corresponding shadow/RAM locations. The EEPROM\_LOCK\_MODE as well as the passcode are part of the EEPROM registers and hence same level of read/write protection applies to these bit fields as configured by EEPROM\_LOCK\_MODE.

#### 6.6.2 I<sup>2</sup>C Serial Interface

MCF8315D interfaces with an external MCU over an I<sup>2</sup>C serial interface. MCF8315D is an I<sup>2</sup>C target to be interfaced with a controller. External MCU can use this interface to read/write from/to any non-reserved register in MCF8315D.

### Note

For reliable communication, a 100-μs delay should be used between every byte transferred over the I<sup>2</sup>C bus.

#### 6.6.2.1 I<sup>2</sup>C Data Word

The I<sup>2</sup>C data word format is shown in [Table 6-9](#).

**Table 6-9. I<sup>2</sup>C Data Word Format**

| TARGET_ID | R/W | CONTROL WORD | DATA                | CRC-8   |
|-----------|-----|--------------|---------------------|---------|
| A6 - A0   | W0  | CW23 - CW0   | D15 / D31/ D63 - D0 | C7 - C0 |

**Target ID and R/W Bit:** The first byte includes the 7-bit I<sup>2</sup>C target ID, followed by the read/write command bit. Every packet in MCF8315D the communication protocol starts with writing a 24-bit control word and hence the R/W bit is always 0.

**24-bit Control Word:** The Target Address is followed by a 24-bit control bit. The control word format is shown in [Table 6-10](#).

**Table 6-10. 24-bit Control Word Format**

| OP_R/W | CRC_EN | DLEN       | MEM_SEC     | MEM_PAGE    | MEM_ADDR   |
|--------|--------|------------|-------------|-------------|------------|
| CW23   | CW22   | CW21- CW20 | CW19 - CW16 | CW15 - CW12 | CW11 - CW0 |

Each field in the control word is explained in detail below.

**OP\_R/W – Read/Write:** R/W bit gives information on whether this is a read (1b) operation or write (0b) operation. For write operation, MCF8315D will expect data bytes to be sent after the 24-bit control word. For read operation, MCF8315D will expect an I<sup>2</sup>C read request with repeated start or normal start after the 24-bit control word.

**CRC\_EN – Cyclic Redundancy Check(CRC) Enable:** MCF8315D supports CRC to verify the data integrity. This bit controls whether the CRC feature is enabled or not.

**DLEN – Data Length:** DLEN field determines the length of the data that will be sent by external MCU to MCF8315D. MCF8315D protocol supports three data lengths: 16-bit, 32-bit and 64-bit.

**Table 6-11. Data Length Configuration**

| DLEN Value | Data Length |
|------------|-------------|
| 00b        | 16-bit      |
| 01b        | 32-bit      |
| 10b        | 64-bit      |
| 11b        | Reserved    |

**MEM\_SEC – Memory Section:** Each memory location in MCF8315D is addressed using three separate entities in the control word – Memory Section, Memory Page, Memory Address. Memory Section is a 4-bit field which denotes the memory section to which the memory location belongs like RAM, ROM etc.

**MEM\_PAGE – Memory Page:** Memory page is a 4-bit field which denotes the memory page to which the memory location belongs.

**MEM\_ADDR – Memory Address:** Memory address is the last 12-bits of the address. The complete 22-bit address is constructed internally by MCF8315D using all three fields – Memory Section, Memory Page, Memory Address. For memory locations 0x000000-0x000800, memory section is 0x0, memory page is 0x0 and memory address is the lowest 12 bits(0x000 for 0x000000, 0x080 for 0x000080 and 0x800 for 0x000800). All relevant memory locations (EEPROM and RAM variables) have MEM\_SEC and MEM\_PAGE values both corresponding to 0x0. All other MEM\_SEC, MEM\_PAGE values are reserved and not for external use.

**Data Bytes:** For a write operation to MCF8315D, the 24-bit control word is followed by data bytes. The DLEN field in the control word should correspond with the number of bytes sent in this section. In case of mismatch between number of data bytes and DLEN, the write operation is discarded.

**CRC Byte:** If the CRC feature is enabled in the control word, CRC byte has to be sent at the end of a write transaction. Refer to [Section 6.6.2.6](#) for detailed information on CRC byte calculation.

### 6.6.2.2 I<sup>2</sup>C Write Transaction

MCF8315D write transaction over I<sup>2</sup>C involves the following sequence (see [Figure 6-67](#)).

1. I<sup>2</sup>C start condition.
2. Start is followed by the I<sup>2</sup>C target ID byte, made up of 7-bit target ID along with the R/W bit set to 0b. ACK in yellow box indicates that MCF8315D has processed the received target ID which has matched with its I<sup>2</sup>C target ID and therefore will proceed with this transaction. If target ID received does not match with the I<sup>2</sup>C ID of MCF8315D, then the transaction is ignored. and no ACK is sent by MCF8315D.
3. The target ID byte is followed by the 24-bit control word sent one byte at a time. Bit 23 in the control word is 0b as it is a write transaction. ACK in blue boxes correspond to acknowledgements sent by MCF8315D to the controller that the previous byte (of control word) has been received and next byte can be sent.
4. The 24-bit control word is then followed by the data bytes. The number of data bytes sent by the controller depends on the DLEN field in the control word.
  - a. While sending data bytes, the LSB byte is sent first. Refer to [Section 6.6.2.4](#) for more details.
  - b. 16-bit/32-bit write – The data sent is written to the address mentioned in control word.
  - c. 64-bit Write – 64-bit is treated as two successive 32-bit writes. The address mentioned in control word is taken as Addr\_1. Addr\_2 is internally calculated by MCF8315D by incrementing Addr\_1 by 0x2. A total of 8 data bytes are sent. The first 4 bytes (sent in LSB first) are written to Addr\_1 and the next 4 bytes are written to Addr\_2.
  - d. ACK in blue boxes (after every data byte) correspond to the acknowledgement sent by MCF8315D to the controller that the previous data byte has been received and next data byte can be sent.
5. If CRC is enabled, the packet ends with a CRC byte. CRC is calculated for the entire packet (Target ID + W bit, Control Word, Data Bytes). MCF8315D will send an ACK on receiving the CRC byte.
6. I<sup>2</sup>C Stop condition from the controller to terminate the transaction.




**Figure 6-67. I<sup>2</sup>C Write Transaction Sequence**

### 6.6.2.3 I<sup>2</sup>C Read Transaction

MCF8315D read transaction over I<sup>2</sup>C involves the following sequence (see [Figure 6-68](#)).

1. I<sup>2</sup>C Start condition from the controller to initiate the transaction.
2. Start is followed by the I<sup>2</sup>C target ID byte, made up of 7-bit target ID along with the R/W bit set to 0b. ACK (in yellow box) indicates that MCF8315D has processed the received target ID which has matched with its I<sup>2</sup>C target ID and therefore will proceed with this transaction. If target ID received does not match with the I<sup>2</sup>C ID of MCF8315D, then the transaction is ignored and no ACK is sent by MCF8315D.

3. The target ID byte is followed by the 24-bit control word sent one byte at a time. Bit 23 in the control word is set to 1b as it is a read transaction. ACK (in blue boxes) correspond to acknowledgements sent by MCF8315D to the controller that the previous byte (of control word) has been received and next byte can be sent.
4. The control word is followed by a Repeated Start (RS, start without a preceding stop) or normal Start (P followed by S) to initiate the data (to be read back) transfer from MCF8315D to I<sup>2</sup>C controller. RS or S is followed by the 7-bit target ID along with R/W bit set to 1b to initiate the read transaction. MCF8315D sends an ACK (in grey box after RS) to the controller to acknowledge the receipt of read transaction request.
5. Post acknowledgement of read transaction request, MCF8315D sends the data bytes on SDA one byte at a time. The number of data bytes sent by MCF8315D depends on the DLEN field in the control word.
  - a. While sending data bytes, the LSB byte is sent first. Refer the examples in [Section 6.6.2.4](#) for more details.
  - b. 16-bit/32-bit Read – The data from the address mentioned in control word is sent back to the controller.
  - c. 64-bit Read – 64-bit is treated as two successive 32-bit reads. The address mentioned in control word is taken as Addr\_1. Addr\_2 is internally calculated by MCF8315D by incrementing Addr\_1 by 0x2. A total of 8 data bytes are sent by MCF8315D. The first 4 bytes (sent in LSB first) are read from Addr\_1 and the next 4 bytes are read from Addr\_2.
  - d. ACK in orange boxes correspond to acknowledgements sent by the controller to MCF8315D that the previous byte has been received and next byte can be sent.
6. If CRC is enabled in the control word, then MCF8315D sends an additional CRC byte at the end. Controller has to read the CRC byte and then send the last ACK (in orange). CRC is calculated for the entire packet (Target ID + W bit, Control Word, Target ID + R bit, Data Bytes).
7. I<sup>2</sup>C Stop condition from the controller to terminate the transaction.




**Figure 6-68. I<sup>2</sup>C Read Transaction Sequence**

#### 6.6.2.4 I<sup>2</sup>C Communication Protocol Packet Examples

All values used in this example section are in hex format. I<sup>2</sup>C target ID used in the examples is 0x60.

**Example for 32-bit Write Operation:** Address – 0x00000080, Data – 0x1234ABCD, CRC Byte – 0x45 (Sample value; does not match with the actual CRC calculation)

**Table 6-12. Example for 32-bit Write Operation Packet**

| Start Byte |                        | Control Word 0 |        |           |           | Control Word 1 |           |           | Control Word 2 | Data Bytes |       |       |       | CRC      |
|------------|------------------------|----------------|--------|-----------|-----------|----------------|-----------|-----------|----------------|------------|-------|-------|-------|----------|
| Target ID  | I <sup>2</sup> C Write | OP_R/W         | CRC_EN | DLEN      | MEM_SEC   | MEM_P_AGE      | MEM_A_DDR | MEM_A_DDR |                | DB0        | DB1   | DB2   | DB3   | CRC Byte |
| A6-A0      | W0                     | CW23           | CW22   | CW21-CW20 | CW19-CW16 | CW15-CW12      | CW11-CW8  | CW7-CW0   |                | D7-D0      | D7-D0 | D7-D0 | D7-D0 | C7-C0    |
| 0x60       | 0x0                    | 0x0            | 0x1    | 0x1       | 0x0       | 0x0            | 0x0       | 0x80      |                | 0xCD       | 0xAB  | 0x34  | 0x12  | 0x45     |
| 0xC0       |                        | 0x50           |        |           |           | 0x00           |           | 0x80      |                | 0xCD       | 0xAB  | 0x34  | 0x12  | 0x45     |

**Example for 64-bit Write Operation:** Address - 0x00000080, Data Address 0x00000080 - Data 0x01234567, Data Address 0x00000082 – Data 0x89ABCDEF, CRC Byte – 0x45 (Sample value; does not match with the actual CRC calculation)

**Table 6-13. Example for 64-bit Write Operation Packet**

| Start Byte |                        | Control Word 0 |        |           |           | Control Word 1 |          | Control Word 2 | Data Bytes        | CRC      |
|------------|------------------------|----------------|--------|-----------|-----------|----------------|----------|----------------|-------------------|----------|
| Target ID  | I <sup>2</sup> C Write | OP_R/W         | CRC_EN | DLEN      | MEM_SEC   | MEM_PAGE       | MEM_ADDR | MEM_ADDR       | DB0 - DB7         | CRC Byte |
| A6-A0      | W0                     | CW23           | CW22   | CW21-CW20 | CW19-CW16 | CW15-CW12      | CW11-CW8 | CW7-CW0        | [D7-D0] x 8       | C7-C0    |
| 0x60       | 0x0                    | 0x0            | 0x1    | 0x2       | 0x0       | 0x0            | 0x0      | 0x80           | 0x67452301EFCDA89 | 0x45     |
| 0xC0       |                        | 0x60           |        |           |           | 0x00           |          | 0x80           | 0x67452301EFCDA89 | 0x45     |

**Example for 32-bit Read Operation:** Address – 0x00000080, Data – 0x1234ABCD, CRC Byte – 0x56 (Sample value; does not match with the actual CRC calculation)

**Table 6-14. Example for 32-bit Read Operation Packet**

| Start Byte |                        | Control Word 0 |        |           |           | Control Word 1 |          | Control Word 2 | Start Byte |                       | Byte 0 | Byte 1 | Byte 2 | Byte 3 | Byte 4   |
|------------|------------------------|----------------|--------|-----------|-----------|----------------|----------|----------------|------------|-----------------------|--------|--------|--------|--------|----------|
| Target ID  | I <sup>2</sup> C Write | R/W            | CRC_EN | DLEN      | MEM_SEC   | MEM_PAGE       | MEM_ADDR | MEM_ADDR       | Target ID  | I <sup>2</sup> C Read | DB0    | DB1    | DB2    | DB3    | CRC Byte |
| A6-A0      | W0                     | CW23           | CW22   | CW21-CW20 | CW19-CW16 | CW15-CW12      | CW11-CW8 | CW7-CW0        | A6-A0      | W0                    | D7-D0  | D7-D0  | D7-D0  | D7-D0  | C7-C0    |
| 0x60       | 0x0                    | 0x1            | 0x1    | 0x1       | 0x0       | 0x0            | 0x0      | 0x80           | 0x60       | 0x1                   | 0xCD   | 0xAB   | 0x34   | 0x12   | 0x56     |
| 0xC0       |                        | 0xD0           |        |           |           | 0x00           |          | 0x80           | 0xC1       |                       | 0xCD   | 0xAB   | 0x34   | 0x12   | 0x56     |

#### 6.6.2.5 I<sup>2</sup>C Clock Stretching

The I<sup>2</sup>C peripheral in MCF8315D implements clock stretching under certain conditions when there are pending I<sup>2</sup>C interrupts waiting to be processed. During clock stretching, MCF8315D pulls SCL low and the I<sup>2</sup>C bus is unavailable for use by other devices. The following is a list of conditions under which clock stretching can occur:

- Start interrupt pending:** There are two scenarios when a start interrupt can result in clock stretching,
  - When target ID is a match, I<sup>2</sup>C peripheral in MCF8315D raises a start interrupt request. Until this start interrupt request is processed, clock is stretched. Upon processing this request, clock is released and an ACK (marked in yellow or grey in [Figure 6-67](#) and [Figure 6-68](#)) is sent to the controller for continuing with the transaction.
  - If Start (followed by target ID match) for a new transaction is received when a receive interrupt from previous transaction is yet to be processed, clock is stretched until both the receive interrupt and start interrupt are processed in chronological order. This process ensures that previous transaction is executed correctly before initiating the next transaction.
- Receive interrupt pending:** When a receive interrupt is waiting to be processed and the receive register is full which occurs when two successive bytes (data or control) have been received by MCF8315D (separated by one ACK shown as blue boxes in [Figure 6-67](#) and [Figure 6-68](#)) without the receive interrupt generated by the first byte being processed. Upon receive of second byte, clock is stretched until receive interrupt generated by the first byte is processed.
- Transmit buffer is empty:** In case of a transmit interrupt pending (to send data back to controller), if the transmit buffer is waiting to be populated with data to be read back to the controller, clock stretching is done until the transmit buffer is populated with requested data. After the buffer is populated, clock is released and data is sent to controller.

#### Note

I<sup>2</sup>C clock stretching is timed out after 5 ms by MCF8315D to allow I<sup>2</sup>C bus access for other devices on the same bus.

#### 6.6.2.6 CRC Byte Calculation

An 8-bit CCIT polynomial ( $x^8 + x^2 + x + 1$ ) and CRC initial value 0xFF is used for CRC computation.

**CRC Calculation in Write Operation:** When the external MCU writes to MCF8315D, if the CRC is enabled, the external MCU has to compute an 8-bit CRC byte and add the CRC byte at the end of the data. MCF8315D will compute CRC using the same polynomial internally and if there is a mismatch, the write request is discarded. Input data for CRC calculation by external MCU for write operation are listed below:

1. Target ID + write bit.
2. Control word – 3 bytes
3. Data bytes – 2/4/8 bytes

**CRC Calculation in Read Operation:** When the external MCU reads from MCF8315D, if the CRC is enabled, MCF8315D sends the CRC byte at the end of the data. The CRC computation in read operation involves the start byte, control words sent by external MCU along with data bytes sent by MCF8315D. Input data for CRC calculation by external MCU to verify the data sent by MCF8315D are listed below :

1. Target ID + write bit
2. Control word – 3 bytes
3. Target ID + read bit
4. Data bytes – 2/4/8 bytes

## 7 EEPROM (Non-Volatile) Register Map

### 7.1 Algorithm\_Configuration Registers

Table 7-1 lists the memory-mapped registers for the Algorithm\_Configuration registers. All register offset addresses not listed in Table 7-1 should be considered as reserved locations and the register contents should not be modified.

**Table 7-1. ALGORITHM\_CONFIGURATION Registers**

| Offset | Acronym          | Register Name                    | Section                        |
|--------|------------------|----------------------------------|--------------------------------|
| 80h    | ISD_CONFIG       | ISD Configuration                | <a href="#">Section 7.1.1</a>  |
| 82h    | REV_DRIVE_CONFIG | Reverse Drive Configuration      | <a href="#">Section 7.1.2</a>  |
| 84h    | MOTOR_STARTUP1   | Motor Startup Configuration1     | <a href="#">Section 7.1.3</a>  |
| 86h    | MOTOR_STARTUP2   | Motor Startup Configuration2     | <a href="#">Section 7.1.4</a>  |
| 88h    | CLOSED_LOOP1     | Close Loop Configuration1        | <a href="#">Section 7.1.5</a>  |
| 8Ah    | CLOSED_LOOP2     | Close Loop Configuration2        | <a href="#">Section 7.1.6</a>  |
| 8Ch    | CLOSED_LOOP3     | Close Loop Configuration3        | <a href="#">Section 7.1.7</a>  |
| 8Eh    | CLOSED_LOOP4     | Close Loop Configuration4        | <a href="#">Section 7.1.8</a>  |
| 94h    | REF_PROFILES1    | Reference Profile Configuration1 | <a href="#">Section 7.1.9</a>  |
| 96h    | REF_PROFILES2    | Reference Profile Configuration2 | <a href="#">Section 7.1.10</a> |
| 98h    | REF_PROFILES3    | Reference Profile Configuration3 | <a href="#">Section 7.1.11</a> |
| 9Ah    | REF_PROFILES4    | Reference Profile Configuration4 | <a href="#">Section 7.1.12</a> |
| 9Ch    | REF_PROFILES5    | Reference Profile Configuration5 | <a href="#">Section 7.1.13</a> |
| 9Eh    | REF_PROFILES6    | Reference Profile Configuration6 | <a href="#">Section 7.1.14</a> |

Complex bit access types are encoded to fit into small table cells. Table 7-2 shows the codes that are used for access types in this section.

**Table 7-2. Algorithm\_Configuration Access Type Codes**

| Access Type            | Code | Description                            |
|------------------------|------|----------------------------------------|
| Read Type              |      |                                        |
| R                      | R    | Read                                   |
| Write Type             |      |                                        |
| W                      | W    | Write                                  |
| Reset or Default Value |      |                                        |
| -n                     |      | Value after reset or the default value |

### 7.1.1 ISD\_CONFIG Register (Offset = 80h) [Reset = 00000000h]

ISD\_CONFIG is shown in [Figure 7-1](#) and described in [Table 7-3](#).

Return to the [Summary Table](#).

Register to configure initial speed detect settings

**Figure 7-1. ISD\_CONFIG Register**

|                  |        |                     |            |              |           |                           |                 |
|------------------|--------|---------------------|------------|--------------|-----------|---------------------------|-----------------|
| 31               | 30     | 29                  | 28         | 27           | 26        | 25                        | 24              |
| PARITY           | ISD_EN | BRAKE_EN            | HIZ_EN     | RVS_DR_EN    | RESYNC_EN | FW_DRV_RESYN_THR          |                 |
| R/W-0h           | R/W-0h | R/W-0h              | R/W-0h     | R/W-0h       | R/W-0h    | R/W-0h                    |                 |
| 23               | 22     | 21                  | 20         | 19           | 18        | 17                        | 16              |
| FW_DRV_RESYN_THR |        | BRK_MODE            | BRK_CONFIG | BRK_CURR_THR |           |                           | BRK_TIME        |
| R/W-0h           |        | R/W-0h              | R/W-0h     | R/W-0h       |           |                           | R/W-0h          |
| 15               | 14     | 13                  | 12         | 11           | 10        | 9                         | 8               |
| BRK_TIME         |        |                     | HIZ_TIME   |              |           |                           | STAT_DETECT_THR |
| R/W-0h           |        |                     | R/W-0h     |              |           |                           | R/W-0h          |
| 7                | 6      | 5                   | 4          | 3            | 2         | 1                         | 0               |
| STAT_DETECT_THR  |        | REV_DRV_HANDOFF_THR |            |              |           | REV_DRV_OPEN_LOOP_CURRENT |                 |
| R/W-0h           |        | R/W-0h              |            |              |           | R/W-0h                    |                 |

**Table 7-3. ISD\_CONFIG Register Field Descriptions**

| Bit | Field     | Type | Reset | Description                                             |
|-----|-----------|------|-------|---------------------------------------------------------|
| 31  | PARITY    | R/W  | 0h    | Parity bit                                              |
| 30  | ISD_EN    | R/W  | 0h    | ISD enable<br>0h = Disable<br>1h = Enable               |
| 29  | BRAKE_EN  | R/W  | 0h    | ISD brake enable<br>0h = Disable<br>1h = Enable         |
| 28  | HIZ_EN    | R/W  | 0h    | ISD Hi-Z enable<br>0h = Disable<br>1h = Enable          |
| 27  | RVS_DR_EN | R/W  | 0h    | Reverse drive enable<br>0h = Disable<br>1h = Enable     |
| 26  | RESYNC_EN | R/W  | 0h    | Resynchronization enable<br>0h = Disable<br>1h = Enable |

**Table 7-3. ISD\_CONFIG Register Field Descriptions (continued)**

| Bit   | Field            | Type | Reset | Description                                                                                                                                                                                                                                                                                                                                  |
|-------|------------------|------|-------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| 25-22 | FW_DRV_RESYN_THR | R/W  | 0h    | Minimum speed threshold to resynchronize to close loop (% of MAX_SPEED)<br><br>0h = 5%<br>1h = 10%<br>2h = 15%<br>3h = 20%<br>4h = 25%<br>5h = 30%<br>6h = 35%<br>7h = 40%<br>8h = 45%<br>9h = 50%<br>Ah = Not Applicable<br>Bh = Not Applicable<br>Ch = Not Applicable<br>Dh = Not Applicable<br>Eh = Not Applicable<br>Fh = Not Applicable |
| 21    | BRK_MODE         | R/W  | 0h    | Brake mode<br><br>0h = All three high side FETs turned ON<br>1h = All three low side FETs turned ON                                                                                                                                                                                                                                          |
| 20    | BRK_CONFIG       | R/W  | 0h    | Brake configuration<br><br>0h = Brake time is used to come out of Brake state<br>1h = Brake current threshold and Brake time is used to come out of Brake state                                                                                                                                                                              |
| 19-17 | BRK_CURR_THR     | R/W  | 0h    | Brake current threshold<br><br>0h = 0.062 A<br>1h = 0.125 A<br>2h = 0.187 A<br>3h = 0.312 A<br>4h = 0.625 A<br>5h = 1.25 A<br>6h = Not Applicable<br>7h = Not Applicable                                                                                                                                                                     |

**Table 7-3. ISD\_CONFIG Register Field Descriptions (continued)**

| Bit   | Field           | Type | Reset | Description                                                                                                                                                                                                                              |
|-------|-----------------|------|-------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| 16-13 | BRK_TIME        | R/W  | 0h    | Brake time<br><br>0h = 10 ms<br>1h = 50 ms<br>2h = 100 ms<br>3h = 200 ms<br>4h = 300 ms<br>5h = 400 ms<br>6h = 500 ms<br>7h = 750 ms<br>8h = 1 s<br>9h = 2 s<br>Ah = 3 s<br>Bh = 4 s<br>Ch = 5 s<br>Dh = 7.5 s<br>Eh = 10 s<br>Fh = 15 s |
| 12-9  | HIZ_TIME        | R/W  | 0h    | Hi-Z time<br><br>0h = 10 ms<br>1h = 50 ms<br>2h = 100 ms<br>3h = 200 ms<br>4h = 300 ms<br>5h = 400 ms<br>6h = 500 ms<br>7h = 750 ms<br>8h = 1 s<br>9h = 2 s<br>Ah = 3 s<br>Bh = 4 s<br>Ch = 5 s<br>Dh = 7.5 s<br>Eh = 10 s<br>Fh = 15 s  |
| 8-6   | STAT_DETECT_THR | R/W  | 0h    | BEMF threshold to detect if motor is stationary<br><br>0h = 50 mV<br>1h = 75 mV<br>2h = 100 mV<br>3h = 250 mV<br>4h = 500 mV<br>5h = 750 mV<br>6h = 1000 mV<br>7h = 1500 mV                                                              |

**Table 7-3. ISD\_CONFIG Register Field Descriptions (continued)**

| Bit | Field                     | Type | Reset | Description                                                                                                                                                                                                                                                                                                                                         |
|-----|---------------------------|------|-------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| 5-2 | REV_DRV_HANDOFF_THR       | R/W  | 0h    | Speed threshold used to transition to open loop during reverse drive (% of MAX_SPEED)<br><br>0h = 2.5%<br>1h = 5%<br>2h = 7.5%<br>3h = 10%<br>4h = 12.5%<br>5h = 15%<br>6h = 20%<br>7h = 25%<br>8h = 30%<br>9h = 40%<br>Ah = 50%<br>Bh = Not Applicable<br>Ch = Not Applicable<br>Dh = Not Applicable<br>Eh = Not Applicable<br>Fh = Not Applicable |
| 1-0 | REV_DRV_OPEN_LOOP_CURRENT | R/W  | 0h    | Open loop current limit during reverse drive<br><br>0h = 0.937 A<br>1h = 1.562 A<br>2h = 2.187 A<br>3h = 3.125 A                                                                                                                                                                                                                                    |

### 7.1.2 REV\_DRIVE\_CONFIG Register (Offset = 82h) [Reset = 00000000h]

REV\_DRIVE\_CONFIG is shown in [Figure 7-2](#) and described in [Table 7-4](#).

Return to the [Summary Table](#).

Register to configure reverse drive settings

**Figure 7-2. REV\_DRIVE\_CONFIG Register**

|                                    |                            |        |    |    |                            |                 |    |
|------------------------------------|----------------------------|--------|----|----|----------------------------|-----------------|----|
| 31                                 | 30                         | 29     | 28 | 27 | 26                         | 25              | 24 |
| PARITY                             | REV_DRV_OPEN_LOOP_ACCEL_A1 |        |    |    | REV_DRV_OPEN_LOOP_ACCEL_A2 |                 |    |
| R/W-0h                             |                            | R/W-0h |    |    |                            | R/W-0h          |    |
| 23                                 | 22                         | 21     | 20 | 19 | 18                         | 17              | 16 |
| REV_DRV_OP<br>EN_LOOP_AC<br>CEL_A2 | ACTIVE_BRAKE_CURRENT_LIMIT |        |    |    | ACTIVE_BRAKE_KP            |                 |    |
| R/W-0h                             |                            | R/W-0h |    |    |                            | R/W-0h          |    |
| 15                                 | 14                         | 13     | 12 | 11 | 10                         | 9               | 8  |
| ACTIVE_BRAKE_KP                    |                            |        |    |    |                            | ACTIVE_BRAKE_KI |    |
| R/W-0h                             |                            |        |    |    |                            | R/W-0h          |    |
| 7                                  | 6                          | 5      | 4  | 3  | 2                          | 1               | 0  |
| ACTIVE_BRAKE_KI                    |                            |        |    |    |                            |                 |    |
| R/W-0h                             |                            |        |    |    |                            |                 |    |

**Table 7-4. REV\_DRIVE\_CONFIG Register Field Descriptions**

| Bit   | Field                      | Type | Reset | Description                                                                                                                                                                                                                                                                                                                                |
|-------|----------------------------|------|-------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| 31    | PARITY                     | R/W  | 0h    | Parity bit                                                                                                                                                                                                                                                                                                                                 |
| 30-27 | REV_DRV_OPEN_LOOP_ACCEL_A1 | R/W  | 0h    | Open loop acceleration coefficient A1 during reverse drive<br><br>0h = 0.1 Hz/s<br>1h = 0.5 Hz/s<br>2h = 1 Hz/s<br>3h = 2.5 Hz/s<br>4h = 5 Hz/s<br>5h = 10 Hz/s<br>6h = 25 Hz/s<br>7h = 50 Hz/s<br>8h = 75 Hz/s<br>9h = 100 Hz/s<br>Ah = 250 Hz/s<br>Bh = 500 Hz/s<br>Ch = 750 Hz/s<br>Dh = 1000 Hz/s<br>Eh = 5000 Hz/s<br>Fh = 10000 Hz/s |

**Table 7-4. REV\_DRIVE\_CONFIG Register Field Descriptions (continued)**

| Bit   | Field                      | Type | Reset | Description                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                |
|-------|----------------------------|------|-------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| 26-23 | REV_DRV_OPEN_LOOP_ACCEL_A2 | R/W  | 0h    | Open loop acceleration coefficient A2 during reverse drive<br><br>0h = 0.0 Hz/s <sup>2</sup><br>1h = 0.5 Hz/s <sup>2</sup><br>2h = 1 Hz/s <sup>2</sup><br>3h = 2.5 Hz/s <sup>2</sup><br>4h = 5 Hz/s <sup>2</sup><br>5h = 10 Hz/s <sup>2</sup><br>6h = 25 Hz/s <sup>2</sup><br>7h = 50 Hz/s <sup>2</sup><br>8h = 75 Hz/s <sup>2</sup><br>9h = 100 Hz/s <sup>2</sup><br>Ah = 250 Hz/s <sup>2</sup><br>Bh = 500 Hz/s <sup>2</sup><br>Ch = 750 Hz/s <sup>2</sup><br>Dh = 1000 Hz/s <sup>2</sup><br>Eh = 5000 Hz/s <sup>2</sup><br>Fh = 10000 Hz/s <sup>2</sup> |
| 22-20 | ACTIVE_BRAKE_CURRENT_LIMIT | R/W  | 0h    | Bus current limit during active braking<br><br>0h = 0.312 A<br>1h = 0.625 A<br>2h = 1.25 A<br>3h = 1.875 A<br>4h = 2.5 A<br>5h = 3.125 A<br>6h = 3.75 A<br>7h = Not Applicable                                                                                                                                                                                                                                                                                                                                                                             |
| 19-10 | ACTIVE_BRAKE_KP            | R/W  | 0h    | 10-bit value for active braking loop Kp. $K_p = \text{ACTIVE\_BRAKE\_KP} / 2^7$                                                                                                                                                                                                                                                                                                                                                                                                                                                                            |
| 9-0   | ACTIVE_BRAKE_KI            | R/W  | 0h    | 10-bit value for active braking loop Ki. $K_i = \text{ACTIVE\_BRAKE\_KI} / 2^9$                                                                                                                                                                                                                                                                                                                                                                                                                                                                            |

### 7.1.3 MOTOR\_STARTUP1 Register (Offset = 84h) [Reset = 00000000h]

MOTOR\_STARTUP1 is shown in [Figure 7-3](#) and described in [Table 7-5](#).

Return to the [Summary Table](#).

Register to configure motor startup settings<sup>1</sup>

**Figure 7-3. MOTOR\_STARTUP1 Register**

|               |             |              |                              |          |            |                 |                |
|---------------|-------------|--------------|------------------------------|----------|------------|-----------------|----------------|
| 31            | 30          | 29           | 28                           | 27       | 26         | 25              | 24             |
| PARITY        | MTR_STARTUP |              | ALIGN_SLOW_RAMP_RATE         |          |            | ALIGN_TIME      |                |
| R/W-0h        | R/W-0h      |              | R/W-0h                       |          |            | R/W-0h          |                |
| 23            | 22          | 21           | 20                           | 19       | 18         | 17              | 16             |
| ALIGN_TIME    |             |              | ALIGN_OR_SLOW_CURRENT_ILIMIT |          |            |                 | IPD_CLK_FREQ   |
| R/W-0h        |             |              | R/W-0h                       |          |            |                 | R/W-0h         |
| 15            | 14          | 13           | 12                           | 11       | 10         | 9               | 8              |
| IPD_CLK_FREQ  |             | IPD_CURR_THR |                              |          |            |                 | IPD_RLS_MODE   |
| R/W-0h        |             | R/W-0h       |                              |          |            |                 | R/W-0h         |
| 7             | 6           | 5            | 4                            | 3        | 2          | 1               | 0              |
| IPD_ADV_ANGLE |             | IPD_REPEAT   |                              | RESERVED | IQ_RAMP_EN | ACTIVE_BRAKE_EN | REV_DRV_CONFIG |
| R/W-0h        |             | R/W-0h       |                              | R-0h     | R/W-0h     | R/W-0h          | R/W-0h         |

**Table 7-5. MOTOR\_STARTUP1 Register Field Descriptions**

| Bit   | Field                | Type | Reset | Description                                                                                                                                                                                                                                                                                                             |
|-------|----------------------|------|-------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| 31    | PARITY               | R/W  | 0h    | Parity bit                                                                                                                                                                                                                                                                                                              |
| 30-29 | MTR_STARTUP          | R/W  | 0h    | Motor start-up method<br>0h = Align<br>1h = Double Align<br>2h = IPD<br>3h = Slow first cycle                                                                                                                                                                                                                           |
| 28-25 | ALIGN_SLOW_RAMP_RATE | R/W  | 0h    | Align, slow first cycle and open loop current ramp rate<br>0h = 0.1 A/s<br>1h = 1 A/s<br>2h = 5 A/s<br>3h = 10 A/s<br>4h = 15 A/s<br>5h = 25 A/s<br>6h = 50 A/s<br>7h = 100 A/s<br>8h = 150 A/s<br>9h = 200 A/s<br>Ah = 250 A/s<br>Bh = 500 A/s<br>Ch = 1000 A/s<br>Dh = 2000 A/s<br>Eh = 5000 A/s<br>Fh = No Limit A/s |

**Table 7-5. MOTOR\_STARTUP1 Register Field Descriptions (continued)**

| Bit   | Field                        | Type | Reset | Description                                                                                                                                                                                                                                                                                                       |
|-------|------------------------------|------|-------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| 24-21 | ALIGN_TIME                   | R/W  | 0h    | Align time<br>0h = 10 ms<br>1h = 50 ms<br>2h = 100 ms<br>3h = 200 ms<br>4h = 300 ms<br>5h = 400 ms<br>6h = 500 ms<br>7h = 750 ms<br>8h = 1 s<br>9h = 1.5 s<br>Ah = 2 s<br>Bh = 3 s<br>Ch = 4 s<br>Dh = 5 s<br>Eh = 7.5 s<br>Fh = 10 s                                                                             |
| 20-17 | ALIGN_OR_SLOW_CURRENT_ILIMIT | R/W  | 0h    | Align or slow first cycle current limit<br>0h = 0.078 A<br>1h = 0.156 A<br>2h = 0.312 A<br>3h = 0.625 A<br>4h = 0.937 A<br>5h = 1.25 A<br>6h = 1.562 A<br>7h = 1.875 A<br>8h = 2.187 A<br>9h = 2.5 A<br>Ah = 2.812 A<br>Bh = 3.125 A<br>Ch = 3.437 A<br>Dh = 3.75 A<br>Eh = Not Applicable<br>Fh = Not Applicable |
| 16-14 | IPD_CLK_FREQ                 | R/W  | 0h    | IPD clock frequency<br>0h = 50 Hz<br>1h = 100 Hz<br>2h = 250 Hz<br>3h = 500 Hz<br>4h = 1000 Hz<br>5h = 2000 Hz<br>6h = 5000 Hz<br>7h = 10000 Hz                                                                                                                                                                   |

**Table 7-5. MOTOR\_STARTUP1 Register Field Descriptions (continued)**

| Bit  | Field         | Type | Reset | Description                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                  |
|------|---------------|------|-------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| 13-9 | IPD_CURR_THR  | R/W  | 0h    | IPD current threshold<br><br>0h = 0.156 A<br>1h = 0.312 A<br>2h = 0.468 A<br>3h = 0.625 A<br>4h = 0.781 A<br>5h = 0.937 A<br>6h = 1.25 A<br>7h = 1.562 A<br>8h = 1.875 A<br>9h = 2.291 A<br>Ah = 2.5 A<br>Bh = 2.916 A<br>Ch = 3.125 A<br>Dh = 3.333 A<br>Eh = 3.75 A<br>Fh = Not Applicable<br>10h = Not Applicable<br>11h = Not Applicable<br>12h = Not Applicable<br>13h = Not Applicable<br>14h = Not Applicable<br>15h = Not Applicable<br>16h = Not Applicable<br>17h = Not Applicable<br>18h = Not Applicable<br>19h = Not Applicable<br>1Ah = Not Applicable<br>1Bh = Not Applicable<br>1Ch = Not Applicable<br>1Dh = Not Applicable<br>1Eh = Not Applicable<br>1Fh = Not Applicable |
| 8    | IPD_RLS_MODE  | R/W  | 0h    | IPD release mode<br><br>0h = Brake<br>1h = Tristate                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                          |
| 7-6  | IPD_ADV_ANGLE | R/W  | 0h    | IPD advance angle<br><br>0h = 0°<br>1h = 30°<br>2h = 60°<br>3h = 90°                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                         |

**Table 7-5. MOTOR\_STARTUP1 Register Field Descriptions (continued)**

| Bit | Field           | Type | Reset | Description                                                                                                                                                                              |
|-----|-----------------|------|-------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| 5-4 | IPD_REPEAT      | R/W  | 0h    | Number of times IPD is executed<br><br>0h = 1 time<br>1h = 2 times<br>2h = 3 times<br>3h = 4 times                                                                                       |
| 3   | RESERVED        | R    | 0h    | Reserved                                                                                                                                                                                 |
| 2   | IQ_RAMP_EN      | R/W  | 0h    | Iq reference ramp down during transition from open loop to closed loop<br><br>0h = Disable Iq ramp down<br>1h = Enable Iq ramp down                                                      |
| 1   | ACTIVE_BRAKE_EN | R/W  | 0h    | Enable active braking<br><br>0h = Disable Active Brake<br>1h = Enable Active Brake                                                                                                       |
| 0   | REV_DRV_CONFIG  | R/W  | 0h    | Choose between forward and reverse drive setting for reverse drive<br><br>0h = Open loop current, A1, A2 based on forward drive<br>1h = Open loop current, A1, A2 based on reverse drive |

### 7.1.4 MOTOR\_STARTUP2 Register (Offset = 86h) [Reset = 00000000h]

MOTOR\_STARTUP2 is shown in [Figure 7-4](#) and described in [Table 7-6](#).

Return to the [Summary Table](#).

Register to configure motor startup settings2

**Figure 7-4. MOTOR\_STARTUP2 Register**

|                     |           |        |             |                      |                       |                    |    |
|---------------------|-----------|--------|-------------|----------------------|-----------------------|--------------------|----|
| 31                  | 30        | 29     | 28          | 27                   | 26                    | 25                 | 24 |
| PARITY              | OL_ILIMIT |        |             |                      | OL_ACC_A1             |                    |    |
| R/W-0h              |           | R/W-0h |             |                      |                       | R/W-0h             |    |
| 23                  | 22        | 21     | 20          | 19                   | 18                    | 17                 | 16 |
| OL_ACC_A1           | OL_ACC_A2 |        |             |                      | AUTO_HANDOFF_EN       | OPN_CL_HANDOFF_THR |    |
| R/W-0h              |           | R/W-0h |             |                      |                       | R/W-0h             |    |
| 15                  | 14        | 13     | 12          | 11                   | 10                    | 9                  | 8  |
| OPN_CL_HANDOFF_THR  |           |        | ALIGN_ANGLE |                      |                       |                    |    |
| R/W-0h              |           |        | R/W-0h      |                      |                       |                    |    |
| 7                   | 6         | 5      | 4           | 3                    | 2                     | 1                  | 0  |
| SLOW_FIRST_CYC_FREQ |           |        |             | FIRST_CYCLE_FREQ_SEL | THETA_ERROR_RAMP_RATE |                    |    |
| R/W-0h              |           |        |             | R/W-0h               | R/W-0h                |                    |    |

**Table 7-6. MOTOR\_STARTUP2 Register Field Descriptions**

| Bit   | Field     | Type | Reset | Description                                                                                                                                                                                                                                                                                           |
|-------|-----------|------|-------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| 31    | PARITY    | R/W  | 0h    | Parity bit                                                                                                                                                                                                                                                                                            |
| 30-27 | OL_ILIMIT | R/W  | 0h    | Open loop current limit<br><br>0h = 0.078 A<br>1h = 0.156 A<br>2h = 0.312 A<br>3h = 0.625 A<br>4h = 0.937 A<br>5h = 1.25 A<br>6h = 1.562 A<br>7h = 1.875 A<br>8h = 2.187 A<br>9h = 2.5 A<br>Ah = 2.812 A<br>Bh = 3.125 A<br>Ch = 3.437 A<br>Dh = 3.75 A<br>Eh = Not Applicable<br>Fh = Not Applicable |

**Table 7-6. MOTOR\_STARTUP2 Register Field Descriptions (continued)**

| Bit   | Field           | Type | Reset | Description                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                           |
|-------|-----------------|------|-------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| 26-23 | OL_ACC_A1       | R/W  | 0h    | Open loop acceleration coefficient A1<br><br>0h = 0.1 Hz/s<br>1h = 0.5 Hz/s<br>2h = 1 Hz/s<br>3h = 2.5 Hz/s<br>4h = 5 Hz/s<br>5h = 10 Hz/s<br>6h = 25 Hz/s<br>7h = 50 Hz/s<br>8h = 75 Hz/s<br>9h = 100 Hz/s<br>Ah = 250 Hz/s<br>Bh = 500 Hz/s<br>Ch = 750 Hz/s<br>Dh = 1000 Hz/s<br>Eh = 5000 Hz/s<br>Fh = 10000 Hz/s                                                                                                                                                                                                                 |
| 22-19 | OL_ACC_A2       | R/W  | 0h    | Open loop acceleration coefficient A2<br><br>0h = 0.0 Hz/s <sup>2</sup><br>1h = 0.5 Hz/s <sup>2</sup><br>2h = 1 Hz/s <sup>2</sup><br>3h = 2.5 Hz/s <sup>2</sup><br>4h = 5 Hz/s <sup>2</sup><br>5h = 10 Hz/s <sup>2</sup><br>6h = 25 Hz/s <sup>2</sup><br>7h = 50 Hz/s <sup>2</sup><br>8h = 75 Hz/s <sup>2</sup><br>9h = 100 Hz/s <sup>2</sup><br>Ah = 250 Hz/s <sup>2</sup><br>Bh = 500 Hz/s <sup>2</sup><br>Ch = 750 Hz/s <sup>2</sup><br>Dh = 1000 Hz/s <sup>2</sup><br>Eh = 5000 Hz/s <sup>2</sup><br>Fh = 10000 Hz/s <sup>2</sup> |
| 18    | AUTO_HANDOFF_EN | R/W  | 0h    | Auto handoff enable<br><br>0h = Disable Auto Handoff (and use OPN_CL_HANDOFF_THR)<br>1h = Enable Auto Handoff                                                                                                                                                                                                                                                                                                                                                                                                                         |

**Table 7-6. MOTOR\_STARTUP2 Register Field Descriptions (continued)**

| Bit   | Field              | Type | Reset | Description                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                      |
|-------|--------------------|------|-------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| 17-13 | OPN_CL_HANDOFF_THR | R/W  | 0h    | <p>Open to closed loop handoff threshold (% of MAX_SPEED)</p> <p>0h = 1%</p> <p>1h = 2%</p> <p>2h = 3%</p> <p>3h = 4%</p> <p>4h = 5%</p> <p>5h = 6%</p> <p>6h = 7%</p> <p>7h = 8%</p> <p>8h = 9%</p> <p>9h = 10%</p> <p>Ah = 11%</p> <p>Bh = 12%</p> <p>Ch = 13%</p> <p>Dh = 14%</p> <p>Eh = 15%</p> <p>Fh = 16%</p> <p>10h = 17%</p> <p>11h = 18%</p> <p>12h = 19%</p> <p>13h = 20%</p> <p>14h = 22.5%</p> <p>15h = 25%</p> <p>16h = 27.5%</p> <p>17h = 30%</p> <p>18h = 32.5%</p> <p>19h = 35%</p> <p>1Ah = 37.5%</p> <p>1Bh = 40%</p> <p>1Ch = 42.5%</p> <p>1Dh = 45%</p> <p>1Eh = 47.5%</p> <p>1Fh = 50%</p> |

**Table 7-6. MOTOR\_STARTUP2 Register Field Descriptions (continued)**

| Bit  | Field       | Type | Reset | Description                                                                                                                                                                                                                                                                                                                                                                                                                                                                     |
|------|-------------|------|-------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| 12-8 | ALIGN_ANGLE | R/W  | 0h    | Align angle<br>0h = 0°<br>1h = 10°<br>2h = 20°<br>3h = 30°<br>4h = 45°<br>5h = 60°<br>6h = 70°<br>7h = 80°<br>8h = 90°<br>9h = 110°<br>Ah = 120°<br>Bh = 135°<br>Ch = 150°<br>Dh = 160°<br>Eh = 170°<br>Fh = 180°<br>10h = 190°<br>11h = 210°<br>12h = 225°<br>13h = 240°<br>14h = 250°<br>15h = 260°<br>16h = 270°<br>17h = 280°<br>18h = 290°<br>19h = 315°<br>1Ah = 330°<br>1Bh = 340°<br>1Ch = 350°<br>1Dh = Not Applicable<br>1Eh = Not Applicable<br>1Fh = Not Applicable |

**Table 7-6. MOTOR\_STARTUP2 Register Field Descriptions (continued)**

| Bit | Field                 | Type | Reset | Description                                                                                                                                                                                                                                                                       |
|-----|-----------------------|------|-------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| 7-4 | SLOW_FIRST_CYC_FREQ   | R/W  | 0h    | Frequency of first cycle in open loop start-up (% of MAX_SPEED)<br><br>0h = 0.1%<br>1h = 0.3%<br>2h = 0.5%<br>3h = 0.7%<br>4h = 1.0%<br>5h = 1.5%<br>6h = 2.0%<br>7h = 2.5%<br>8h = 3.0%<br>9h = 4.0%<br>Ah = 5.0%<br>Bh = 7.5%<br>Ch = 10.0%<br>Dh = 15%<br>Eh = 20%<br>Fh = 25% |
| 3   | FIRST_CYCLE_FREQ_SEL  | R/W  | 0h    | First cycle frequency in open loop for align, double align and IPD start-up<br><br>0h = 0 Hz<br>1h = Defined by SLOW_FIRST_CYC_FREQ                                                                                                                                               |
| 2-0 | THETA_ERROR_RAMP_RATE | R/W  | 0h    | Ramp rate for reducing difference between estimated theta and open loop theta<br><br>0h = 0.01 deg/ms<br>1h = 0.05 deg/ms<br>2h = 0.1 deg/ms<br>3h = 0.15 deg/ms<br>4h = 0.2 deg/ms<br>5h = 0.5 deg/ms<br>6h = 1 deg/ms<br>7h = 2 deg/ms                                          |

### 7.1.5 CLOSED\_LOOP1 Register (Offset = 88h) [Reset = 00000000h]

CLOSED\_LOOP1 is shown in [Figure 7-5](#) and described in [Table 7-7](#).

Return to the [Summary Table](#).

Register to configure close loop settings1

**Figure 7-5. CLOSED\_LOOP1 Register**

| 31           | 30                    | 29     | 28 | 27           | 26               | 25       | 24                        |
|--------------|-----------------------|--------|----|--------------|------------------|----------|---------------------------|
| PARITY       | OVERMODULATION_ENABLE | CL_ACC |    |              |                  | RESERVED |                           |
| R/W-0h       | R/W-0h                | R/W-0h |    |              |                  | R-0h     |                           |
| 23           | 22                    | 21     | 20 | 19           | 18               | 17       | 16                        |
| CL_DEC       |                       |        |    | PWM_FREQ_OUT |                  |          |                           |
| R/W-0h       |                       |        |    | R/W-0h       |                  |          |                           |
| 15           | 14                    | 13     | 12 | 11           | 10               | 9        | 8                         |
| PWM_FREQ_OUT | PWM_MODE              | FG_SEL |    | FG_DIV       |                  |          |                           |
| R/W-0h       | R/W-0h                | R/W-0h |    | R/W-0h       |                  |          |                           |
| 7            | 6                     | 5      | 4  | 3            | 2                | 1        | 0                         |
| FG_CONFIG    | FG_BEMF_THR           |        |    | AVS_EN       | DEADTIME_COMP_EN | RESERVED | LOW_SPEED_RECIRC_BRAKE_EN |
| R/W-0h       | R/W-0h                |        |    | R/W-0h       | R/W-0h           | R-0h     | R/W-0h                    |

**Table 7-7. CLOSED\_LOOP1 Register Field Descriptions**

| Bit | Field                 | Type | Reset | Description                                                                        |
|-----|-----------------------|------|-------|------------------------------------------------------------------------------------|
| 31  | PARITY                | R/W  | 0h    | Parity bit                                                                         |
| 30  | OVERMODULATION_ENABLE | R/W  | 0h    | Enable overmodulation<br>0h = Disable overmodulation<br>1h = Enable overmodulation |

**Table 7-7. CLOSED\_LOOP1 Register Field Descriptions (continued)**

| Bit   | Field    | Type | Reset | Description                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                        |
|-------|----------|------|-------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| 29-25 | CL_ACC   | R/W  | 0h    | <p>Closed loop acceleration (Speed mode: Hz/s Power mode: deciWatts/s Torque mode: centiA/s duty cycle mode: milliUnit/s)<br/>deciWatt: 0.1W centiA: 0.01A milliUnit: 0.001%</p> <p>0h = 0.5<br/>1h = 1<br/>2h = 2.5<br/>3h = 5<br/>4h = 7.5<br/>5h = 10<br/>6h = 20<br/>7h = 40<br/>8h = 60<br/>9h = 80<br/>Ah = 100<br/>Bh = 200<br/>Ch = 300<br/>Dh = 400<br/>Eh = 500<br/>Fh = 600<br/>10h = 700<br/>11h = 800<br/>12h = 900<br/>13h = 1000<br/>14h = 2000<br/>15h = 4000<br/>16h = 6000<br/>17h = 8000<br/>18h = 10000<br/>19h = 20000<br/>1Ah = 30000<br/>1Bh = 40000<br/>1Ch = 50000<br/>1Dh = 60000<br/>1Eh = 70000<br/>1Fh = No limit</p> |
| 24    | RESERVED | R    | 0h    | Reserved                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                           |

**Table 7-7. CLOSED\_LOOP1 Register Field Descriptions (continued)**

| Bit   | Field  | Type | Reset | Description                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                      |
|-------|--------|------|-------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| 23-19 | CL_DEC | R/W  | 0h    | <p>Closed loop deceleration (Speed mode: Hz/s Power mode: deciWatts/s Torque mode: centiA/s duty cycle mode: milliUnit/s) If AVS is enabled in speed or power mode, the current is clamped to 0 only if negative iqRef is set by outer PI (speed/power) loop deciWatt: 0.1W centiA: 0.01A milliUnit: 0.001%</p> <p>0h = 0.5<br/> 1h = 1<br/> 2h = 2.5<br/> 3h = 5<br/> 4h = 7.5<br/> 5h = 10<br/> 6h = 20<br/> 7h = 40<br/> 8h = 60<br/> 9h = 80<br/> Ah = 100<br/> Bh = 200<br/> Ch = 300<br/> Dh = 400<br/> Eh = 500<br/> Fh = 600<br/> 10h = 700<br/> 11h = 800<br/> 12h = 900<br/> 13h = 1000<br/> 14h = 2000<br/> 15h = 4000<br/> 16h = 6000<br/> 17h = 8000<br/> 18h = 10000<br/> 19h = 20000<br/> 1Ah = 30000<br/> 1Bh = 40000<br/> 1Ch = 50000<br/> 1Dh = 60000<br/> 1Eh = 70000<br/> 1Fh = No limit</p> |

**Table 7-7. CLOSED\_LOOP1 Register Field Descriptions (continued)**

| Bit   | Field        | Type | Reset | Description                                                                                                                                                                                                                                                                                                              |
|-------|--------------|------|-------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| 18-15 | PWM_FREQ_OUT | R/W  | 0h    | PWM output frequency<br>0h = 10 kHz<br>1h = 15 kHz<br>2h = 20 kHz<br>3h = 25 kHz<br>4h = 30 kHz<br>5h = 35 kHz<br>6h = 40 kHz<br>7h = 45 kHz<br>8h = 50 kHz<br>9h = 55 kHz<br>Ah = 60 kHz<br>Bh = Not Applicable<br>Ch = Not Applicable<br>Dh = Not Applicable<br>Eh = Not Applicable<br>Fh = Not Applicable             |
| 14    | PWM_MODE     | R/W  | 0h    | PWM modulation<br>0h = Continuous Space Vector Modulation<br>1h = Discontinuous Space Vector Modulation                                                                                                                                                                                                                  |
| 13-12 | FG_SEL       | R/W  | 0h    | FG select<br>0h = Output FG in ISD, open loop and closed loop<br>1h = Output FG in only closed loop<br>2h = Output FG in open loop for the first try.<br>3h = Not Applicable                                                                                                                                             |
| 11-8  | FG_DIV       | R/W  | 0h    | FG division factor<br>0h = 3x electrical speed<br>1h = Divide by 1 (2-pole motor mechanical speed)<br>2h = Divide by 2 (4-pole motor mechanical speed)<br>3h = Divide by 3 (6-pole motor mechanical speed)<br>4h = Divide by 4 (8-pole motor mechanical speed) ...<br>Fh = Divide by 15 (30-pole motor mechanical speed) |
| 7     | FG_CONFIG    | R/W  | 0h    | FG output configuration. BEMF threshold defined by FG_BEMF_THR<br>0h = FG active as long as motor is driven<br>1h = FG active till BEMF drops below BEMF threshold                                                                                                                                                       |

**Table 7-7. CLOSED\_LOOP1 Register Field Descriptions (continued)**

| Bit | Field                         | Type | Reset | Description                                                                                                                                                                   |
|-----|-------------------------------|------|-------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| 6-4 | FG_BEMF_THR                   | R/W  | 0h    | FG output BEMF threshold<br><br>0h = +/- 1mV<br>1h = +/- 2mV<br>2h = +/- 5mV<br>3h = +/- 10mV<br>4h = +/- 20mV<br>5h = +/- 30mV<br>6h = Not Applicable<br>7h = Not Applicable |
| 3   | AVS_EN                        | R/W  | 0h    | AVS enable<br><br>0h = Disable<br>1h = Enable                                                                                                                                 |
| 2   | DEADTIME_COMP_EN              | R/W  | 0h    | Deadtime compensation enable<br><br>0h = Disable<br>1h = Enable                                                                                                               |
| 1   | RESERVED                      | R    | 0h    | Reserved                                                                                                                                                                      |
| 0   | LOW_SPEED_RECIRC_B<br>RAKE_EN | R/W  | 0h    | Stop mode applied when stop mode is recirculation brake and motor in align or open loop state<br><br>0h = Hi-z<br>1h = Low Side Brake                                         |

### 7.1.6 CLOSED\_LOOP2 Register (Offset = 8Ah) [Reset = 00000000h]

CLOSED\_LOOP2 is shown in [Figure 7-6](#) and described in [Table 7-8](#).

Return to the [Summary Table](#).

Register to configure close loop settings2

**Figure 7-6. CLOSED\_LOOP2 Register**

|              |          |    |    |                       |    |    |    |
|--------------|----------|----|----|-----------------------|----|----|----|
| 31           | 30       | 29 | 28 | 27                    | 26 | 25 | 24 |
| PARITY       | MTR_STOP |    |    | MTR_STOP_BRK_TIME     |    |    |    |
| R/W-0h       | R/W-0h   |    |    | R/W-0h                |    |    |    |
| 23           | 22       | 21 | 20 | 19                    | 18 | 17 | 16 |
| ACT_SPIN_THR |          |    |    | BRAKE_SPEED_THRESHOLD |    |    |    |
| R/W-0h       |          |    |    | R/W-0h                |    |    |    |
| 15           | 14       | 13 | 12 | 11                    | 10 | 9  | 8  |
| MOTOR_RES    |          |    |    |                       |    |    |    |
| R/W-0h       |          |    |    |                       |    |    |    |
| 7            | 6        | 5  | 4  | 3                     | 2  | 1  | 0  |
| MOTOR_IND    |          |    |    |                       |    |    |    |
| R/W-0h       |          |    |    |                       |    |    |    |

**Table 7-8. CLOSED\_LOOP2 Register Field Descriptions**

| Bit   | Field    | Type | Reset | Description                                                                                                                                                                                              |
|-------|----------|------|-------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| 31    | PARITY   | R/W  | 0h    | Parity bit                                                                                                                                                                                               |
| 30-28 | MTR_STOP | R/W  | 0h    | Motor stop mode<br>0h = Hi-z<br>1h = Recirculation Stop<br>2h = Low side braking<br>3h = High side braking<br>4h = Active spin down<br>5h = Not Applicable<br>6h = Not Applicable<br>7h = Not Applicable |

**Table 7-8. CLOSED\_LOOP2 Register Field Descriptions (continued)**

| Bit   | Field             | Type | Reset | Description                                                                                                                                                                                                                                                                |
|-------|-------------------|------|-------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| 27-24 | MTR_STOP_BRK_TIME | R/W  | 0h    | Brake time during motor stop<br><br>0h = 1 ms<br>1h = 1 ms<br>2h = 1 ms<br>3h = 1 ms<br>4h = 1 ms<br>5h = 5 ms<br>6h = 10 ms<br>7h = 50 ms<br>8h = 100 ms<br>9h = 250 ms<br>Ah = 500 ms<br>Bh = 1000 ms<br>Ch = 2500 ms<br>Dh = 5000 ms<br>Eh = 10000 ms<br>Fh = 15000 ms  |
| 23-20 | ACT_SPIN_THR      | R/W  | 0h    | Speed threshold for active spin down (% of MAX_SPEED)<br><br>0h = 100 %<br>1h = 90 %<br>2h = 80 %<br>3h = 70 %<br>4h = 60 %<br>5h = 50 %<br>6h = 45 %<br>7h = 40 %<br>8h = 35 %<br>9h = 30 %<br>Ah = 25 %<br>Bh = 20 %<br>Ch = 15 %<br>Dh = 10 %<br>Eh = 5 %<br>Fh = 2.5 % |

**Table 7-8. CLOSED\_LOOP2 Register Field Descriptions (continued)**

| Bit   | Field                     | Type | Reset | Description                                                                                                                                                                                                                                                                                                                                |
|-------|---------------------------|------|-------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| 19-16 | BRAKE_SPEED_THRES<br>HOLD | R/W  | 0h    | Speed threshold for BRAKE pin and Motor stop (Low side Braking or High Side Braking or Align Braking) (% of MAX_SPEED)<br><br>0h = 100 %<br>1h = 90 %<br>2h = 80 %<br>3h = 70 %<br>4h = 60%<br>5h = 50 %<br>6h = 45 %<br>7h = 40 %<br>8h = 35 %<br>9h = 30 %<br>Ah = 25 %<br>Bh = 20 %<br>Ch = 15 %<br>Dh = 10 %<br>Eh = 5 %<br>Fh = 2.5 % |
| 15-8  | MOTOR_RES                 | R/W  | 0h    | 8-bit values for motor phase resistance. See Table 6-2 for values of phase resistance                                                                                                                                                                                                                                                      |
| 7-0   | MOTOR_IND                 | R/W  | 0h    | 8-bit values for motor phase inductance. See Table 6-3 for values of phase inductance                                                                                                                                                                                                                                                      |

### 7.1.7 CLOSED\_LOOP3 Register (Offset = 8Ch) [Reset = 00000000h]

CLOSED\_LOOP3 is shown in [Figure 7-7](#) and described in [Table 7-9](#).

Return to the [Summary Table](#).

Register to configure close loop settings3

**Figure 7-7. CLOSED\_LOOP3 Register**

|                  |                  |    |    |              |             |    |    |
|------------------|------------------|----|----|--------------|-------------|----|----|
| 31               | 30               | 29 | 28 | 27           | 26          | 25 | 24 |
| PARITY           | MOTOR_BEMF_CONST |    |    |              |             |    |    |
| R/W-0h           | R/W-0h           |    |    |              |             |    |    |
| 23               | 22               | 21 | 20 | 19           | 18          | 17 | 16 |
| MOTOR_BEMF_CONST | CURR_LOOP_KP     |    |    |              |             |    |    |
| R/W-0h           | R/W-0h           |    |    |              |             |    |    |
| 15               | 14               | 13 | 12 | 11           | 10          | 9  | 8  |
| CURR_LOOP_KP     |                  |    |    | CURR_LOOP_KI |             |    |    |
| R/W-0h           |                  |    |    | R/W-0h       |             |    |    |
| 7                | 6                | 5  | 4  | 3            | 2           | 1  | 0  |
| CURR_LOOP_KI     |                  |    |    |              | SPD_LOOP_KP |    |    |
| R/W-0h           |                  |    |    |              | R/W-0h      |    |    |

**Table 7-9. CLOSED\_LOOP3 Register Field Descriptions**

| Bit   | Field            | Type | Reset | Description                                                                                                                                                            |
|-------|------------------|------|-------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| 31    | PARITY           | R/W  | 0h    | Parity bit                                                                                                                                                             |
| 30-23 | MOTOR_BEMF_CONST | R/W  | 0h    | 8-bit values for motor BEMF Constant. See Table 6-4 for values of BEMF constant                                                                                        |
| 22-13 | CURR_LOOP_KP     | R/W  | 0h    | 10-bit value for current Iq and Id loop Kp. Kp = 8LSB of CURR_LOOP_KP / 10 <sup>2</sup> MSB of CURR_LOOP_KP. Set to 0 for auto calculation of current Kp and Ki        |
| 12-3  | CURR_LOOP_KI     | R/W  | 0h    | 10-bit value for current Iq and Id loop Ki. Ki = 1000 * 8LSB of CURR_LOOP_KI / 10 <sup>2</sup> MSB of CURR_LOOP_KI. Set to 0 for auto calculation of current Kp and Ki |
| 2-0   | SPD_LOOP_KP      | R/W  | 0h    | 3 MSB bits for speed loop Kp. Kp = 0.01 * 8LSB of SPD_LOOP_KP / 10 <sup>2</sup> MSB of SPD_LOOP_KP                                                                     |

### 7.1.8 CLOSED\_LOOP4 Register (Offset = 8Eh) [Reset = 00000000h]

CLOSED\_LOOP4 is shown in [Figure 7-8](#) and described in [Table 7-10](#).

Return to the [Summary Table](#).

Register to configure close loop settings4

**Figure 7-8. CLOSED\_LOOP4 Register**

|             |             |           |    |        |    |    |    |
|-------------|-------------|-----------|----|--------|----|----|----|
| 31          | 30          | 29        | 28 | 27     | 26 | 25 | 24 |
| PARITY      | SPD_LOOP_KP |           |    |        |    |    |    |
| R/W-0h      |             |           |    | R/W-0h |    |    |    |
| 23          | 22          | 21        | 20 | 19     | 18 | 17 | 16 |
| SPD_LOOP_KI |             |           |    |        |    |    |    |
| R/W-0h      |             |           |    |        |    |    |    |
| 15          | 14          | 13        | 12 | 11     | 10 | 9  | 8  |
| SPD_LOOP_KI |             | MAX_SPEED |    |        |    |    |    |
| R/W-0h      |             |           |    | R/W-0h |    |    |    |
| 7           | 6           | 5         | 4  | 3      | 2  | 1  | 0  |
| MAX_SPEED   |             |           |    |        |    |    |    |
| R/W-0h      |             |           |    |        |    |    |    |

**Table 7-10. CLOSED\_LOOP4 Register Field Descriptions**

| Bit   | Field       | Type | Reset | Description                                                                                                                                                                                                                           |
|-------|-------------|------|-------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| 31    | PARITY      | R/W  | 0h    | Parity bit                                                                                                                                                                                                                            |
| 30-24 | SPD_LOOP_KP | R/W  | 0h    | 7 LSB bits for speed loop Kp. $K_p = 0.01 * 8\text{LSB of SPD\_LOOP\_KP} / 10^2\text{MSB of SPD\_LOOP\_KP}$                                                                                                                           |
| 23-14 | SPD_LOOP_KI | R/W  | 0h    | 10 bit value for speed loop Ki. $K_i = 0.1 * 8\text{LSB of SPD\_LOOP\_KI} / 10^2\text{MSB of SPD\_LOOP\_KI}$                                                                                                                          |
| 13-0  | MAX_SPEED   | R/W  | 0h    | 14-bit value for setting maximum motor speed in electrical Hz. Maximum motor electrical speed (Hz): $\{\text{MAX\_SPEED}/6\}$ For example: if MAX_SPEED is 0x2710, then maximum motor speed (Hz) = $10000(0x2710)/6 = 1666\text{ Hz}$ |

### 7.1.9 REF\_PROFILES1 Register (Offset = 94h) [Reset = 00000000h]

REF\_PROFILES1 is shown in [Figure 7-9](#) and described in [Table 7-11](#).

Return to the [Summary Table](#).

Register to configure Reference profile1

**Figure 7-9. REF\_PROFILES1 Register**

|             |                    |    |             |          |    |    |    |
|-------------|--------------------|----|-------------|----------|----|----|----|
| 31          | 30                 | 29 | 28          | 27       | 26 | 25 | 24 |
| PARITY      | REF_PROFILE_CONFIG |    |             | DUTY_ON1 |    |    |    |
| R/W-0h      | R/W-0h             |    |             | R/W-0h   |    |    |    |
| 23          | 22                 | 21 | 20          | 19       | 18 | 17 | 16 |
| DUTY_ON1    |                    |    | DUTY_OFF1   |          |    |    |    |
| R/W-0h      |                    |    | R/W-0h      |          |    |    |    |
| 15          | 14                 | 13 | 12          | 11       | 10 | 9  | 8  |
| DUTY_OFF1   |                    |    | DUTY_CLAMP1 |          |    |    |    |
| R/W-0h      |                    |    | R/W-0h      |          |    |    |    |
| 7           | 6                  | 5  | 4           | 3        | 2  | 1  | 0  |
| DUTY_CLAMP1 |                    |    | DUTY_A      |          |    |    |    |
| R/W-0h      |                    |    | R/W-0h      |          |    |    |    |

**Table 7-11. REF\_PROFILES1 Register Field Descriptions**

| Bit   | Field              | Type | Reset | Description                                                                                                                                      |
|-------|--------------------|------|-------|--------------------------------------------------------------------------------------------------------------------------------------------------|
| 31    | PARITY             | R/W  | 0h    | Parity bit                                                                                                                                       |
| 30-29 | REF_PROFILE_CONFIG | R/W  | 0h    | Configuration for reference profiles<br>0h = Reference/Equation<br>1h = Linear Profile<br>2h = Staircase Profile<br>3h = Forward-Reverse Profile |
| 28-21 | DUTY_ON1           | R/W  | 0h    | Turn-on duty cycle (%) = $\{(DUTY\_ON1/256)*100\}$                                                                                               |
| 20-13 | DUTY_OFF1          | R/W  | 0h    | Turn-off duty cycle (%) = $\{(DUTY\_OFF1/256)*100\}$                                                                                             |
| 12-5  | DUTY_CLAMP1        | R/W  | 0h    | Duty cycle for clamping speed (%) = $\{(DUTY\_CLAMP1/256)*100\}$                                                                                 |
| 4-0   | DUTY_A             | R/W  | 0h    | 5 MSB bits for duty cycle A                                                                                                                      |

### 7.1.10 REF\_PROFILES2 Register (Offset = 96h) [Reset = 00000000h]

REF\_PROFILES2 is shown in [Figure 7-10](#) and described in [Table 7-12](#).

Return to the [Summary Table](#).

Register to configure Reference profile2

**Figure 7-10. REF\_PROFILES2 Register**

|        |        |    |    |        |        |    |    |
|--------|--------|----|----|--------|--------|----|----|
| 31     | 30     | 29 | 28 | 27     | 26     | 25 | 24 |
| PARITY | DUTY_A |    |    |        | DUTY_B |    |    |
| R/W-0h | R/W-0h |    |    |        | R/W-0h |    |    |
| 23     | 22     | 21 | 20 | 19     | 18     | 17 | 16 |
| DUTY_B |        |    |    | DUTY_C |        |    |    |
| R/W-0h |        |    |    | R/W-0h |        |    |    |
| 15     | 14     | 13 | 12 | 11     | 10     | 9  | 8  |
| DUTY_C |        |    |    | DUTY_D |        |    |    |
| R/W-0h |        |    |    | R/W-0h |        |    |    |
| 7      | 6      | 5  | 4  | 3      | 2      | 1  | 0  |
| DUTY_D |        |    |    | DUTY_E |        |    |    |
| R/W-0h |        |    |    | R/W-0h |        |    |    |

**Table 7-12. REF\_PROFILES2 Register Field Descriptions**

| Bit   | Field  | Type | Reset | Description                                                            |
|-------|--------|------|-------|------------------------------------------------------------------------|
| 31    | PARITY | R/W  | 0h    | Parity bit                                                             |
| 30-28 | DUTY_A | R/W  | 0h    | 3 LSB bits for duty cycle A Duty cycle A (%) = $\{(DUTY\_A/256)*100\}$ |
| 27-20 | DUTY_B | R/W  | 0h    | Duty cycle B (%) = $\{(DUTY\_B/256)*100\}$                             |
| 19-12 | DUTY_C | R/W  | 0h    | Duty cycle C (%) = $\{(DUTY\_C/256)*100\}$                             |
| 11-4  | DUTY_D | R/W  | 0h    | Duty cycle D (%) = $\{(DUTY\_D/256)*100\}$                             |
| 3-0   | DUTY_E | R/W  | 0h    | 4 MSB bits for Duty cycle E                                            |

### 7.1.11 REF\_PROFILES3 Register (Offset = 98h) [Reset = 00000000h]

REF\_PROFILES3 is shown in [Figure 7-11](#) and described in [Table 7-13](#).

Return to the [Summary Table](#).

Register to configure Reference profile3

**Figure 7-11. REF\_PROFILES3 Register**

|             |        |    |    |    |             |    |          |
|-------------|--------|----|----|----|-------------|----|----------|
| 31          | 30     | 29 | 28 | 27 | 26          | 25 | 24       |
| PARITY      | DUTY_E |    |    |    | DUTY_ON2    |    |          |
| R/W-0h      | R/W-0h |    |    |    | R/W-0h      |    |          |
| 23          | 22     | 21 | 20 | 19 | 18          | 17 | 16       |
| DUTY_ON2    |        |    |    |    | DUTY_OFF2   |    |          |
| R/W-0h      |        |    |    |    | R/W-0h      |    |          |
| 15          | 14     | 13 | 12 | 11 | 10          | 9  | 8        |
| DUTY_OFF2   |        |    |    |    | DUTY_CLAMP2 |    |          |
| R/W-0h      |        |    |    |    | R/W-0h      |    |          |
| 7           | 6      | 5  | 4  | 3  | 2           | 1  | 0        |
| DUTY_CLAMP2 |        |    |    |    | DUTY_HYS    |    | RESERVED |
| R/W-0h      |        |    |    |    | R/W-0h      |    | R-0h     |

**Table 7-13. REF\_PROFILES3 Register Field Descriptions**

| Bit   | Field       | Type | Reset | Description                                                                              |
|-------|-------------|------|-------|------------------------------------------------------------------------------------------|
| 31    | PARITY      | R/W  | 0h    | Parity bit                                                                               |
| 30-27 | DUTY_E      | R/W  | 0h    | 4 LSB bits for Duty cycle E Duty cycle E (%) = $\{(DUTY\_E/256)*100\}$                   |
| 26-19 | DUTY_ON2    | R/W  | 0h    | Turn-on duty cycle (%) = $\{(DUTY\_ON2/256)*100\}$                                       |
| 18-11 | DUTY_OFF2   | R/W  | 0h    | Turn-off duty cycle (%) = $\{(DUTY\_OFF2/256)*100\}$                                     |
| 10-3  | DUTY_CLAMP2 | R/W  | 0h    | Duty cycle for clamping speed (%) = $\{(DUTY\_CLAMP1/256)*100\}$                         |
| 2-1   | DUTY_HYS    | R/W  | 0h    | Duty hysteresis for speed reference mode<br><br>0h = 0%<br>1h = 1%<br>2h = 2%<br>3h = 3% |
| 0     | RESERVED    | R    | 0h    | Reserved                                                                                 |

### 7.1.12 REF\_PROFILES4 Register (Offset = 9Ah) [Reset = 00000000h]

REF\_PROFILES4 is shown in [Figure 7-12](#) and described in [Table 7-14](#).

Return to the [Summary Table](#).

Register to configure Reference profile4

**Figure 7-12. REF\_PROFILES4 Register**

|            |            |    |    |    |    |    |    |
|------------|------------|----|----|----|----|----|----|
| 31         | 30         | 29 | 28 | 27 | 26 | 25 | 24 |
| PARITY     | REF_OFF1   |    |    |    |    |    |    |
| R/W-0h     |            |    |    |    |    |    |    |
| 23         | 22         | 21 | 20 | 19 | 18 | 17 | 16 |
| REF_OFF1   | REF_CLAMP1 |    |    |    |    |    |    |
| R/W-0h     |            |    |    |    |    |    |    |
| 15         | 14         | 13 | 12 | 11 | 10 | 9  | 8  |
| REF_CLAMP1 | REF_A      |    |    |    |    |    |    |
| R/W-0h     |            |    |    |    |    |    |    |
| 7          | 6          | 5  | 4  | 3  | 2  | 1  | 0  |
| REF_A      | REF_B      |    |    |    |    |    |    |
| R/W-0h     |            |    |    |    |    |    |    |

**Table 7-14. REF\_PROFILES4 Register Field Descriptions**

| Bit   | Field      | Type | Reset | Description                                                             |
|-------|------------|------|-------|-------------------------------------------------------------------------|
| 31    | PARITY     | R/W  | 0h    | Parity bit                                                              |
| 30-23 | REF_OFF1   | R/W  | 0h    | Turn off reference (% of Maximum Reference) = $\{(REF\_OFF1/256)*100\}$ |
| 22-15 | REF_CLAMP1 | R/W  | 0h    | Clamp Ref 1 (% of Maximum Reference) = $\{(REF\_CLAMP1/256)*100\}$      |
| 14-7  | REF_A      | R/W  | 0h    | Ref A (% of Maximum Reference) = $\{(REF\_A/256)*100\}$                 |
| 6-0   | REF_B      | R/W  | 0h    | 7 MSB of REF_B configuration                                            |

### 7.1.13 REF\_PROFILES5 Register (Offset = 9Ch) [Reset = 00000000h]

REF\_PROFILES5 is shown in [Figure 7-13](#) and described in [Table 7-15](#).

Return to the [Summary Table](#).

Register to configure Reference profile5

**Figure 7-13. REF\_PROFILES5 Register**

|        |        |          |    |                     |    |                     |          |
|--------|--------|----------|----|---------------------|----|---------------------|----------|
| 31     | 30     | 29       | 28 | 27                  | 26 | 25                  | 24       |
| PARITY | REF_B  | REF_C    |    |                     |    |                     |          |
| R/W-0h | R/W-0h | R/W-0h   |    |                     |    |                     |          |
| 23     | 22     | 21       | 20 | 19                  | 18 | 17                  | 16       |
| REF_C  |        | REF_D    |    |                     |    |                     |          |
| R/W-0h |        | R/W-0h   |    |                     |    |                     |          |
| 15     | 14     | 13       | 12 | 11                  | 10 | 9                   | 8        |
| REF_D  |        | REF_E    |    |                     |    |                     |          |
| R/W-0h |        | R/W-0h   |    |                     |    |                     |          |
| 7      | 6      | 5        | 4  | 3                   | 2  | 1                   | 0        |
| REF_E  |        | MIN_DUTY |    | VOLTAGE_MODE_CONFIG |    | DUTY_COMMAND_FILTER | RESERVED |
| R/W-0h |        | R/W-0h   |    | R/W-0h              |    | R/W-0h              | R-0h     |

**Table 7-15. REF\_PROFILES5 Register Field Descriptions**

| Bit   | Field               | Type | Reset | Description                                                                                                                                                                                                                                                                                                                                                                                |
|-------|---------------------|------|-------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| 31    | PARITY              | R/W  | 0h    | Parity bit                                                                                                                                                                                                                                                                                                                                                                                 |
| 30    | REF_B               | R/W  | 0h    | 1 LSB of REF_B configuration. Ref B(% of Maximum Reference) = $\{(REF\_B/256)*100\}$                                                                                                                                                                                                                                                                                                       |
| 29-22 | REF_C               | R/W  | 0h    | Ref C (% of Maximum Reference) = $\{(REF\_C/256)*100\}$                                                                                                                                                                                                                                                                                                                                    |
| 21-14 | REF_D               | R/W  | 0h    | Ref D (% of Maximum Reference) = $\{(REF\_D/256)*100\}$                                                                                                                                                                                                                                                                                                                                    |
| 13-6  | REF_E               | R/W  | 0h    | Ref E(% of Maximum Reference) = $\{(REF\_E/256)*100\}$                                                                                                                                                                                                                                                                                                                                     |
| 5-4   | MIN_DUTY            | R/W  | 0h    | Minimum input duty to start driving the motor<br><br>0h = 1 %<br>1h = 3 %<br>2h = 5 %<br>3h = 10 %                                                                                                                                                                                                                                                                                         |
| 3-2   | VOLTAGE_MODE_CONFIG | R/W  | 0h    | Voltage mode configuration for reference profiles<br><br>0h = User defined reference modes throughout the duty range<br>1h = Voltage mode if input duty > DUTY_C + DUTY_HYST;<br>configured reference mode if input duty < DUTY_C - DUTY_HYST<br>2h = configured reference mode if input duty > DUTY_C + DUTY_HYST; voltage mode if input duty < DUTY_C - DUTY_HYST<br>3h = Not Applicable |
| 1     | DUTY_COMMAND_FILTER | R/W  | 0h    | Speed pin input filter<br><br>0h = Filter on Speed pin is disabled<br>1h = Filter on Speed pin is enabled (0.4%)                                                                                                                                                                                                                                                                           |
| 0     | RESERVED            | R    | 0h    | Reserved                                                                                                                                                                                                                                                                                                                                                                                   |

#### 7.1.14 REF\_PROFILES6 Register (Offset = 9Eh) [Reset = 00000000h]

REF\_PROFILES6 is shown in [Figure 7-14](#) and described in [Table 7-16](#).

Return to the [Summary Table](#).

Register to configure Reference profile6

**Figure 7-14. REF\_PROFILES6 Register**

|            |            |    |    |        |    |    |    |
|------------|------------|----|----|--------|----|----|----|
| 31         | 30         | 29 | 28 | 27     | 26 | 25 | 24 |
| PARITY     | REF_OFF2   |    |    |        |    |    |    |
| R/W-0h     |            |    |    | R/W-0h |    |    |    |
| 23         | 22         | 21 | 20 | 19     | 18 | 17 | 16 |
| REF_OFF2   | REF_CLAMP2 |    |    |        |    |    |    |
| R/W-0h     |            |    |    | R/W-0h |    |    |    |
| 15         | 14         | 13 | 12 | 11     | 10 | 9  | 8  |
| REF_CLAMP2 | RESERVED   |    |    |        |    |    |    |
| R/W-0h     |            |    |    | R-0h   |    |    |    |
| 7          | 6          | 5  | 4  | 3      | 2  | 1  | 0  |
| RESERVED   |            |    |    |        |    |    |    |
| R-0h       |            |    |    |        |    |    |    |

**Table 7-16. REF\_PROFILES6 Register Field Descriptions**

| Bit   | Field      | Type | Reset | Description                                                               |
|-------|------------|------|-------|---------------------------------------------------------------------------|
| 31    | PARITY     | R/W  | 0h    | Parity bit                                                                |
| 30-23 | REF_OFF2   | R/W  | 0h    | Turn off Ref (% of Maximum Reference) = $\{(\text{REF\_OFF2}/256)*100\}$  |
| 22-15 | REF_CLAMP2 | R/W  | 0h    | Clamp Ref 2 (% of Maximum Reference) = $\{(\text{REF\_CLAMP2}/256)*100\}$ |
| 14-0  | RESERVED   | R    | 0h    | Reserved                                                                  |

## 7.2 Fault\_Configuration Registers

[Table 7-17](#) lists the memory-mapped registers for the Fault\_Configuration registers. All register offset addresses not listed in [Table 7-17](#) should be considered as reserved locations and the register contents should not be modified.

**Table 7-17. FAULT\_CONFIGURATION Registers**

| Offset | Acronym       | Register Name        | Section                       |
|--------|---------------|----------------------|-------------------------------|
| 90h    | FAULT_CONFIG1 | Fault Configuration1 | <a href="#">Section 7.2.1</a> |
| 92h    | FAULT_CONFIG2 | Fault Configuration2 | <a href="#">Section 7.2.2</a> |

Complex bit access types are encoded to fit into small table cells. [Table 7-18](#) shows the codes that are used for access types in this section.

**Table 7-18. Fault\_Configuration Access Type Codes**

| Access Type            | Code | Description |
|------------------------|------|-------------|
| Read Type              |      |             |
| R                      | R    | Read        |
| Write Type             |      |             |
| W                      | W    | Write       |
| Reset or Default Value |      |             |

**Table 7-18. Fault\_Configuration Access Type Codes  
(continued)**

| Access Type | Code | Description                            |
|-------------|------|----------------------------------------|
| -n          |      | Value after reset or the default value |

## 7.2.1 FAULT\_CONFIG1 Register (Offset = 90h) [Reset = 00000000h]

FAULT\_CONFIG1 is shown in [Figure 7-15](#) and described in [Table 7-19](#).

Return to the [Summary Table](#).

Register to configure fault settings1

**Figure 7-15. FAULT\_CONFIG1 Register**

|                      |                  |              |    |    |                          |                       |                         |
|----------------------|------------------|--------------|----|----|--------------------------|-----------------------|-------------------------|
| 31                   | 30               | 29           | 28 | 27 | 26                       | 25                    | 24                      |
| PARITY               | ILIMIT           |              |    |    | HW_LOCK_ILIMIT           |                       |                         |
| R/W-0h               | R/W-0h           |              |    |    | R/W-0h                   |                       |                         |
| 23                   | 22               | 21           | 20 | 19 | 18                       | 17                    | 16                      |
| HW_LOCK_ILI<br>MIT   | LOCK_ILIMIT      |              |    |    | EEP_FAULT_M<br>ODE       | LOCK_ILIMIT_MODE      |                         |
| R/W-0h               | R/W-0h           |              |    |    | R/W-0h                   | R/W-0h                |                         |
| 15                   | 14               | 13           | 12 | 11 | 10                       | 9                     | 8                       |
| LOCK_ILIMIT_<br>MODE | LOCK_ILIMIT_DEG  |              |    |    | LCK_RETRY                |                       |                         |
| R/W-0h               | R/W-0h           |              |    |    | R/W-0h                   |                       |                         |
| 7                    | 6                | 5            | 4  | 3  | 2                        | 1                     | 0                       |
| LCK_RETRY            | CRC_ERR_MO<br>DE | MTR_LCK_MODE |    |    | IPD_TIMEOUT<br>_FAULT_EN | IPD_FREQ_FA<br>ULT_EN | SATURATION_<br>FLAGS_EN |
| R/W-0h               | R/W-0h           | R/W-0h       |    |    | R/W-0h                   | R/W-0h                | R/W-0h                  |

**Table 7-19. FAULT\_CONFIG1 Register Field Descriptions**

| Bit   | Field  | Type | Reset | Description                                                                                                                                                                                                                                                                                                                                        |
|-------|--------|------|-------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| 31    | PARITY | R/W  | 0h    | Parity bit                                                                                                                                                                                                                                                                                                                                         |
| 30-27 | ILIMIT | R/W  | 0h    | Current limit for Iq axis (torque) current reference in closed loop<br><br>0h = 0.078 A<br>1h = 0.156 A<br>2h = 0.312 A<br>3h = 0.625 A<br>4h = 0.937 A<br>5h = 1.250 A<br>6h = 1.562 A<br>7h = 1.875 A<br>8h = 2.187 A<br>9h = 2.5 A<br>Ah = 2.812 A<br>Bh = 3.125 A<br>Ch = 3.437 A<br>Dh = 3.75 A<br>Eh = Not Applicable<br>Fh = Not Applicable |

**Table 7-19. FAULT\_CONFIG1 Register Field Descriptions (continued)**

| Bit   | Field          | Type | Reset | Description                                                                                                                                                                                                                                                                                                                      |
|-------|----------------|------|-------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| 26-23 | HW_LOCK_ILIMIT | R/W  | 0h    | Comparator based lock detection current threshold<br><br>0h = 0.078 A<br>1h = 0.156 A<br>2h = 0.312 A<br>3h = 0.625 A<br>4h = 0.937 A<br>5h = 1.250 A<br>6h = 1.562 A<br>7h = 1.875 A<br>8h = 2.187 A<br>9h = 2.5 A<br>Ah = 2.812 A<br>Bh = 3.125 A<br>Ch = 3.437 A<br>Dh = 3.75 A<br>Eh = Not Applicable<br>Fh = Not Applicable |
| 22-19 | LOCK_ILIMIT    | R/W  | 0h    | ADC based lock detection current threshold<br><br>0h = 0.078 A<br>1h = 0.156 A<br>2h = 0.312 A<br>3h = 0.625 A<br>4h = 0.937 A<br>5h = 1.250 A<br>6h = 1.562 A<br>7h = 1.875 A<br>8h = 2.187 A<br>9h = 2.5 A<br>Ah = 2.812 A<br>Bh = 3.125 A<br>Ch = 3.437 A<br>Dh = 3.75 A<br>Eh = Not Applicable<br>Fh = Not Applicable        |
| 18    | EEP_FAULT_MODE | R/W  | 0h    | Fault response type for EEPROM fault<br><br>0h = Latched Fault<br>1h = Report only fault                                                                                                                                                                                                                                         |

**Table 7-19. FAULT\_CONFIG1 Register Field Descriptions (continued)**

| Bit   | Field            | Type | Reset | Description                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                     |
|-------|------------------|------|-------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| 17-15 | LOCK_ILIMIT_MODE | R/W  | 0h    | <p>Lock current limit mode</p> <p>0h = Ilimit lock detection causes latched fault; nFAULT active; Gate driver is tristated</p> <p>1h = Ilimit lock detection causes latched fault; nFAULT active; Gate driver is in low side brake mode (All low side FETs are turned ON)</p> <p>2h = Ilimit lock detection causes latched fault; nFAULT active; Gate driver is in high side brake mode (All high side FETs are turned ON)</p> <p>3h = Fault automatically cleared after LCK_RETRY time. Number of retries limited to AUTO_RETRY_TIMES. If number of retries exceed AUTO_RETRY_TIMES, fault is latched; Gate driver is tristated; nFAULT active</p> <p>4h = Fault automatically cleared for AUTO_RETRY_TIMES after LCK_RETRY time; Gate driver is in low side brake mode (All low side FETs are turned ON); nFAULT active</p> <p>5h = Fault automatically cleared after LCK_RETRY time. Number of retries limited to AUTO_RETRY_TIMES. If number of retries exceed AUTO_RETRY_TIMES, fault is latched; Gate driver is in high side brake mode (All high side FETs are turned ON); nFAULT active</p> <p>6h = Ilimit lock detection current limit is in report only but no action is taken; nFAULT active</p> <p>7h = ILIMIT LOCK is disabled</p> |
| 14-11 | LOCK_ILIMIT_DEG  | R/W  | 0h    | <p>Lock current limit detection deglitch time</p> <p>0h = No deglitch</p> <p>1h = 0.1 ms</p> <p>2h = 0.2 ms</p> <p>3h = 0.5 ms</p> <p>4h = 1 ms</p> <p>5h = 2.5 ms</p> <p>6h = 5 ms</p> <p>7h = 7.5 ms</p> <p>8h = 10 ms</p> <p>9h = 25 ms</p> <p>Ah = 50 ms</p> <p>Bh = 75 ms</p> <p>Ch = 100 ms</p> <p>Dh = 200 ms</p> <p>Eh = 500 ms</p> <p>Fh = 1000 ms</p>                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                 |

**Table 7-19. FAULT\_CONFIG1 Register Field Descriptions (continued)**

| Bit  | Field        | Type | Reset | Description                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                  |
|------|--------------|------|-------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| 10-7 | LCK_RETRY    | R/W  | 0h    | Lock detection retry time<br><br>0h = 300 ms<br>1h = 500 ms<br>2h = 1 s<br>3h = 2 s<br>4h = 3 s<br>5h = 4 s<br>6h = 5 s<br>7h = 6 s<br>8h = 7 s<br>9h = 8 s<br>Ah = 9 s<br>Bh = 10 s<br>Ch = 11 s<br>Dh = 12 s<br>Eh = 13 s<br>Fh = 14 s                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                     |
| 6    | CRC_ERR_MODE | R/W  | 0h    | CRC (in I2C communication) error mode<br><br>0h = CRC error on I2C causes latched fault; nFAULT active;<br>Gate driver is tristated<br>1h = CRC error on I2C causes report only but no action is taken;<br>nFAULT is active                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                  |
| 5-3  | MTR_LCK_MODE | R/W  | 0h    | Motor lock mode<br><br>0h = Motor lock detection causes latched fault; nFAULT active;<br>Gate driver is tristated<br>1h = Motor lock detection causes latched fault; nFAULT active;<br>Gate driver is in low side brake mode (All low side FETs are turned ON)<br>2h = Motor lock detection causes latched fault; nFAULT active;<br>Gate driver is in high side brake mode (All high side FETs are turned ON)<br>3h = Fault automatically cleared after LCK_RETRY time.<br>Number of retries limited to AUTO_RETRY_TIMES. If number of retries exceed AUTO_RETRY_TIMES, fault is latched; Gate driver is tristated; nFAULT active<br>4h = Fault automatically cleared for AUTO_RETRY_TIMES after LCK_RETRY time; Gate driver is in low side brake mode (All low side FETs are turned ON); nFAULT active<br>5h = Fault automatically cleared after LCK_RETRY time.<br>Number of retries limited to AUTO_RETRY_TIMES. If number of retries exceed AUTO_RETRY_TIMES, fault is latched; Gate driver is in high side brake mode (All high side FETs are turned ON); nFAULT active<br>6h = Motor lock detection current limit is in report only but no action is taken; nFAULT active<br>7h = MTR LOCK is disabled |

**Table 7-19. FAULT\_CONFIG1 Register Field Descriptions (continued)**

| Bit | Field                | Type | Reset | Description                                                                                    |
|-----|----------------------|------|-------|------------------------------------------------------------------------------------------------|
| 2   | IPD_TIMEOUT_FAULT_EN | R/W  | 0h    | IPD timeout fault enable<br><br>0h = Disable<br>1h = Enable                                    |
| 1   | IPD_FREQ_FAULT_EN    | R/W  | 0h    | IPD frequency fault enable<br><br>0h = Disable<br>1h = Enable                                  |
| 0   | SATURATION_FLAGS_EN  | R/W  | 0h    | Enable indication of current loop and speed loop saturation<br><br>0h = Disable<br>1h = Enable |

## 7.2.2 FAULT\_CONFIG2 Register (Offset = 92h) [Reset = 00000000h]

FAULT\_CONFIG2 is shown in [Figure 7-16](#) and described in [Table 7-20](#).

Return to the [Summary Table](#).

Register to configure fault settings2

**Figure 7-16. FAULT\_CONFIG2 Register**

| 31                 | 30           | 29         | 28                 | 27             | 26                  | 25                | 24 |
|--------------------|--------------|------------|--------------------|----------------|---------------------|-------------------|----|
| PARITY             | LOCK1_EN     | LOCK2_EN   | LOCK3_EN           | LOCK_ABN_SPEED |                     | ABNORMAL_BEMF_THR |    |
| R/W-0h             | R/W-0h       | R/W-0h     | R/W-0h             | R/W-0h         |                     | R/W-0h            |    |
| 23                 | 22           | 21         | 20                 | 19             | 18                  | 17                | 16 |
| ABNORMAL_BEMF_THR  |              | NO_MTR_THR |                    |                | HW_LOCK_ILIMIT_MODE |                   |    |
| R/W-0h             |              | R/W-0h     |                    |                | R/W-0h              |                   |    |
| 15                 | 14           | 13         | 12                 | 11             | 10                  | 9                 | 8  |
| HW_LOCK_ILIMIT_DEG |              |            | VOLTAGE_HYSTERESIS |                | MIN_VM_MOTOR        |                   |    |
| R/W-0h             |              |            | R/W-0h             |                | R/W-0h              |                   |    |
| 7                  | 6            | 5          | 4                  | 3              | 2                   | 1                 | 0  |
| MIN_VM_MODE        | MAX_VM_MOTOR |            |                    | MAX_VM_MODE    | AUTO_RETRY_TIMES    |                   |    |
| R/W-0h             | R/W-0h       |            |                    | R/W-0h         | R/W-0h              |                   |    |

**Table 7-20. FAULT\_CONFIG2 Register Field Descriptions**

| Bit   | Field          | Type | Reset | Description                                                                                                                                            |
|-------|----------------|------|-------|--------------------------------------------------------------------------------------------------------------------------------------------------------|
| 31    | PARITY         | R/W  | 0h    | Parity bit                                                                                                                                             |
| 30    | LOCK1_EN       | R/W  | 0h    | Lock 1 (Abnormal Speed) Enable<br>0h = Disable<br>1h = Enable                                                                                          |
| 29    | LOCK2_EN       | R/W  | 0h    | Lock 2 (Abnormal BEMF) Enable<br>0h = Disable<br>1h = Enable                                                                                           |
| 28    | LOCK3_EN       | R/W  | 0h    | Lock 3 (No Motor) Enable<br>0h = Disable<br>1h = Enable                                                                                                |
| 27-25 | LOCK_ABN_SPEED | R/W  | 0h    | Abnormal speed lock threshold (% of MAX_SPEED)<br>0h = 130%<br>1h = 140%<br>2h = 150%<br>3h = 160%<br>4h = 170%<br>5h = 180%<br>6h = 190%<br>7h = 200% |

**Table 7-20. FAULT\_CONFIG2 Register Field Descriptions (continued)**

| Bit   | Field               | Type | Reset | Description                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                           |
|-------|---------------------|------|-------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| 24-22 | ABNORMAL_BEMF_THR   | R/W  | 0h    | <p>Abnormal BEMF lock threshold (% of expected BEMF)</p> <p>0h = 40%</p> <p>1h = 45%</p> <p>2h = 50%</p> <p>3h = 55%</p> <p>4h = 60%</p> <p>5h = 65%</p> <p>6h = 67.5%</p> <p>7h = 70%</p>                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                            |
| 21-19 | NO_MTR_THR          | R/W  | 0h    | <p>No motor lock threshold</p> <p>0h = 0.023 A</p> <p>1h = 0.046 A</p> <p>2h = 0.062A</p> <p>3h = 0.078 A</p> <p>4h = 0.156 A</p> <p>5h = 0.312 A</p> <p>6h = 0.468 A</p> <p>7h = 0.625 A</p>                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                         |
| 18-16 | HW_LOCK_ILIMIT_MODE | R/W  | 0h    | <p>Hardware lock current limit mode</p> <p>0h = Hardware llimit lock detection causes latched fault; nFAULT active; Gate driver is tristated</p> <p>1h = Hardware llimit lock detection causes latched fault; nFAULT active; Gate driver is in low side brake mode (All low side FETs are turned ON)</p> <p>2h = Hardware llimit lock detection causes latched fault; nFAULT active; Gate driver is in high side brake mode (All high side FETs are turned ON)</p> <p>3h = Fault automatically cleared after LCK_RETRY time. Number of retries limited to AUTO_RETRY_TIMES. If number of retries exceed AUTO_RETRY_TIMES, fault is latched; Gate driver is tristated; nFAULT active</p> <p>4h = Fault automatically cleared for AUTO_RETRY_TIMES after LCK_RETRY time; Gate driver is in low side brake mode (All low side FETs are turned ON); nFAULT active</p> <p>5h = Fault automatically cleared after LCK_RETRY time. Number of retries limited to AUTO_RETRY_TIMES. If number of retries exceed AUTO_RETRY_TIMES, fault is latched; Gate driver is in high side brake mode (All high side FETs are turned ON); nFAULT active</p> <p>6h = Hardware llimit lock detection current limit is in report only but no action is taken; nFAULT active</p> <p>7h = HARDWARE ILIMIT LOCK is disabled</p> |

**Table 7-20. FAULT\_CONFIG2 Register Field Descriptions (continued)**

| Bit   | Field              | Type | Reset | Description                                                                                                                                                                                                |
|-------|--------------------|------|-------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| 15-13 | HW_LOCK_ILIMIT_DEG | R/W  | 0h    | Hardware lock current limit detection deglitch time<br><br>0h = No deglitch<br>1h = 1 $\mu$ s<br>2h = 2 $\mu$ s<br>3h = 3 $\mu$ s<br>4h = 4 $\mu$ s<br>5h = 5 $\mu$ s<br>6h = 6 $\mu$ s<br>7h = 7 $\mu$ s  |
| 12-11 | VOLTAGE_HYSTERESIS | R/W  | 0h    | Hysteresis for controller overvoltage and undervoltage faults. Fault triggered at threshold, cleared at threshold $\pm$ hysteresis (+ for UV, - for OV).<br><br>0h = 0.5V<br>1h = 1V<br>2h = 2V<br>3h = 3V |
| 10-8  | MIN_VM_MOTOR       | R/W  | 0h    | Controller under voltage fault threshold - minimum DC bus voltage for running motor<br><br>0h = No Limit<br>1h = 6 V<br>2h = 7 V<br>3h = 8 V<br>4h = 10 V<br>5h = 14 V<br>6h = 16 V<br>7h = 18 V           |
| 7     | MIN_VM_MODE        | R/W  | 0h    | DC bus (controller) undervoltage fault recovery mode<br><br>0h = Latch on Undervoltage<br>1h = Automatic clear if voltage in bounds                                                                        |
| 6-4   | MAX_VM_MOTOR       | R/W  | 0h    | Controller over voltage fault threshold - maximum DC bus voltage for running motor<br><br>0h = No Limit<br>1h = 18 V<br>2h = 20 V<br>3h = 22 V<br>4h = 28 V<br>5h = 30 V<br>6h = 32 V<br>7h = 34 V         |
| 3     | MAX_VM_MODE        | R/W  | 0h    | DC bus (controller) overvoltage fault recovery mode<br><br>0h = Latch on Overvoltage<br>1h = Automatic clear if voltage in bounds                                                                          |

**Table 7-20. FAULT\_CONFIG2 Register Field Descriptions (continued)**

| Bit | Field            | Type | Reset | Description                                                                                                                      |
|-----|------------------|------|-------|----------------------------------------------------------------------------------------------------------------------------------|
| 2-0 | AUTO_RETRY_TIMES | R/W  | 0h    | Number of automatic retry attempts<br><br>0h = No Limit<br>1h = 2<br>2h = 3<br>3h = 5<br>4h = 7<br>5h = 10<br>6h = 15<br>7h = 20 |

### 7.3 Hardware\_Configuration Registers

Table 7-21 lists the memory-mapped registers for the Hardware\_Configuration registers. All register offset addresses not listed in Table 7-21 should be considered as reserved locations and the register contents should not be modified.

**Table 7-21. HARDWARE\_CONFIGURATION Registers**

| Offset | Acronym        | Register Name              | Section                       |
|--------|----------------|----------------------------|-------------------------------|
| A4h    | PIN_CONFIG     | Hardware Pin Configuration | <a href="#">Section 7.3.1</a> |
| A6h    | DEVICE_CONFIG1 | Device configuration1      | <a href="#">Section 7.3.2</a> |
| A8h    | DEVICE_CONFIG2 | Device configuration2      | <a href="#">Section 7.3.3</a> |
| AAh    | PERI_CONFIG1   | Peripheral Configuration1  | <a href="#">Section 7.3.4</a> |
| ACh    | GD_CONFIG1     | Gate Driver Configuration1 | <a href="#">Section 7.3.5</a> |
| A Eh   | GD_CONFIG2     | Gate Driver Configuration2 | <a href="#">Section 7.3.6</a> |

Complex bit access types are encoded to fit into small table cells. Table 7-22 shows the codes that are used for access types in this section.

**Table 7-22. Hardware\_Configuration Access Type Codes**

| Access Type            | Code | Description                            |
|------------------------|------|----------------------------------------|
| Read Type              |      |                                        |
| R                      | R    | Read                                   |
| Write Type             |      |                                        |
| W                      | W    | Write                                  |
| Reset or Default Value |      |                                        |
| -n                     |      | Value after reset or the default value |

### 7.3.1 PIN\_CONFIG Register (Offset = A4h) [Reset = 00000000h]

PIN\_CONFIG is shown in [Figure 7-17](#) and described in [Table 7-23](#).

Return to the [Summary Table](#).

Register to configure hardware pins

**Figure 7-17. PIN\_CONFIG Register**

|                 |                 |                 |                       |             |            |    |    |
|-----------------|-----------------|-----------------|-----------------------|-------------|------------|----|----|
| 31              | 30              | 29              | 28                    | 27          | 26         | 25 | 24 |
| PARITY          | PWM_DITHER_STEP | VDC_FILTER      | LEAD_ANGLE            |             |            |    |    |
| R/W-0h          | R/W-0h          | R/W-0h          | R/W-0h                |             |            |    |    |
| 23              | 22              | 21              | 20                    | 19          | 18         | 17 | 16 |
| LEAD_ANGLE      | MAX_POWER       |                 |                       |             |            |    |    |
| R/W-0h          | R/W-0h          |                 |                       |             |            |    |    |
| 15              | 14              | 13              | 12                    | 11          | 10         | 9  | 8  |
| MAX_POWER       | FG_IDLE_CONFIG  | FG_FAULT_CONFIG |                       |             |            |    |    |
| R/W-0h          | R/W-0h          | R/W-0h          |                       |             |            |    |    |
| 7               | 6               | 5               | 4                     | 3           | 2          | 1  | 0  |
| FG_FAULT_CONFIG | ALARM_PIN_EN    | BRAKE_PIN_MODE  | ALIGN_BRAKE_ANGLE_SEL | BRAKE_INPUT | SPEED_MODE |    |    |
| R/W-0h          | R/W-0h          | R/W-0h          | R/W-0h                | R/W-0h      | R/W-0h     |    |    |

**Table 7-23. PIN\_CONFIG Register Field Descriptions**

| Bit   | Field           | Type | Reset | Description                                                                                                                                                                                            |
|-------|-----------------|------|-------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| 31    | PARITY          | R/W  | 0h    | Parity bit                                                                                                                                                                                             |
| 30-29 | PWM_DITHER_STEP | R/W  | 0h    | PWM dither slew rate<br>0h = 1<br>1h = 2<br>2h = 5<br>3h = 10                                                                                                                                          |
| 28-27 | VDC_FILTER      | R/W  | 0h    | Vdc(VM) filter coefficient<br>0h = Disable<br>1h = Enable with default filter cut-off frequency<br>2h = Enable with filter cut-off frequency 100Hz<br>3h = Enable with filter cut-off frequency 1000Hz |

**Table 7-23. PIN\_CONFIG Register Field Descriptions (continued)**

| Bit   | Field          | Type | Reset | Description                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                               |
|-------|----------------|------|-------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| 26-22 | LEAD_ANGLE     | R/W  | 0h    | <p>Lead angle. In voltage mode, positive value indicates the applied voltage is leading the BEMF, negative value indicates applied voltage is lagging the BEMF. In other modes, positive means negative id reference, negative means positive id reference</p> <p>0h = 0 deg<br/> 1h = 3 deg<br/> 2h = 6 deg<br/> 3h = 9 deg<br/> 4h = 12 deg<br/> 5h = 15 deg<br/> 6h = 18 deg<br/> 7h = 21 deg<br/> 8h = 24 deg<br/> 9h = 27 deg<br/> Ah = 30 deg<br/> Bh = 33 deg<br/> Ch = 36 deg<br/> Dh = 39 deg<br/> Eh = 42 deg<br/> Fh = 45 deg<br/> 10h = -48 deg<br/> 11h = -45 deg<br/> 12h = -42 deg<br/> 13h = -39 deg<br/> 14h = -36 deg<br/> 15h = -33 deg<br/> 16h = -30 deg<br/> 17h = -27 deg<br/> 18h = -24 deg<br/> 19h = -21 deg<br/> 1Ah = -18 deg<br/> 1Bh = -15 deg<br/> 1Ch = -12 deg<br/> 1Dh = -9 deg<br/> 1Eh = -6 deg<br/> 1Fh = -3 deg</p> |
| 21-11 | MAX_POWER      | R/W  | 0h    | Maximum power for power loop or power limit. Max power in Watts = $(MAX\_POWER / 2^{11}) * 100$                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                           |
| 10-9  | FG_IDLE_CONFIG | R/W  | 0h    | <p>FG configuration during motor stopped/idle state</p> <p>0h = FG continues and end state depends on FG_CONFIG and last state before motor stops<br/> 1h = FG is pulled High<br/> 2h = FG is pulled Low<br/> 3h = FG is pulled High</p>                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                  |

**Table 7-23. PIN\_CONFIG Register Field Descriptions (continued)**

| Bit | Field                 | Type | Reset | Description                                                                                                                                                                                                                                              |
|-----|-----------------------|------|-------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| 8-7 | FG_FAULT_CONFIG       | R/W  | 0h    | FG configuration during fault state. BEMF threshold defined by FG_BEMF_THR if FG_CONFIG 1<br><br>0h = Use last FG signal when motor was driven<br>1h = FG is pulled High<br>2h = FG is pulled Low<br>3h = FG active till BEMF drops below BEMF threshold |
| 6   | ALARM_PIN_EN          | R/W  | 0h    | Enable Alarm pin<br><br>0h = Disable<br>1h = Enable                                                                                                                                                                                                      |
| 5   | BRAKE_PIN_MODE        | R/W  | 0h    | Brake pin mode<br><br>0h = Low side Brake<br>1h = Align Brake                                                                                                                                                                                            |
| 4   | ALIGN_BRAKE_ANGLE_SEL | R/W  | 0h    | Select align brake angle<br><br>0h = Use last commutation angle before entering align braking<br>1h = Use ALIGN_ANGLE configuration for align braking                                                                                                    |
| 3-2 | BRAKE_INPUT           | R/W  | 0h    | Brake pin override<br><br>0h = Hardware Pin BRAKE<br>1h = Override pin and brake / align according to BRAKE_PIN_MODE<br>2h = Override pin and do not brake / align<br>3h = Hardware Pin BRAKE                                                            |
| 1-0 | SPEED_MODE            | R/W  | 0h    | Configure motor control input source<br><br>0h = Controlled by analog voltage on SPEED pin<br>1h = Controlled by duty cycle (PWM) on SPEED pin<br>2h = Controlled by DIGITAL_SPEED_CTRL value (I2C)<br>3h = Controlled by frequency on SPEED pin         |

### 7.3.2 DEVICE\_CONFIG1 Register (Offset = A6h) [Reset = 00000000h]

DEVICE\_CONFIG1 is shown in [Figure 7-18](#) and described in [Table 7-24](#).

Return to the [Summary Table](#).

Register to configure device

**Figure 7-18. DEVICE\_CONFIG1 Register**

|                 |          |             |                    |                 |      |          |    |
|-----------------|----------|-------------|--------------------|-----------------|------|----------|----|
| 31              | 30       | 29          | 28                 | 27              | 26   | 25       | 24 |
| PARITY          | RESERVED | DAC_SOx_SEL | PWM_DITHER_MODE    | I2C_TARGET_ADDR |      |          |    |
| R/W-0h          | R-0h     | R/W-0h      | R/W-0h             | R/W-0h          |      |          |    |
| 23              | 22       | 21          | 20                 | 19              | 18   | 17       | 16 |
| I2C_TARGET_ADDR |          |             |                    | EEPROM_LOCK_KEY |      |          |    |
|                 |          | R/W-0h      |                    |                 | W-0h |          |    |
| 15              | 14       | 13          | 12                 | 11              | 10   | 9        | 8  |
| EEPROM_LOCK_KEY |          |             |                    |                 |      |          |    |
|                 |          |             |                    |                 |      |          |    |
| 7               | 6        | 5           | 4                  | 3               | 2    | 1        | 0  |
| EEPROM_LOCK_KEY |          |             | SLEW_RATE_I2C_PINS | PULLUP_ENABLE   |      | BUS_VOLT |    |
|                 |          | W-0h        | R/W-0h             | R/W-0h          |      | R/W-0h   |    |

**Table 7-24. DEVICE\_CONFIG1 Register Field Descriptions**

| Bit   | Field              | Type | Reset | Description                                                                                               |
|-------|--------------------|------|-------|-----------------------------------------------------------------------------------------------------------|
| 31    | PARITY             | R/W  | 0h    | Parity bit                                                                                                |
| 30    | RESERVED           | R    | 0h    | Reserved                                                                                                  |
| 29-28 | DAC_SOx_SEL        | R/W  | 0h    | Select between DACOUT2 and SOx channels<br>0h = DACOUT2<br>1h = SOA<br>2h = SOB<br>3h = SOC               |
| 27    | PWM_DITHER_MODE    | R/W  | 0h    | PWM dither mode<br>0h = Triangular Mode<br>1h = Random Mode                                               |
| 26-20 | I2C_TARGET_ADDR    | R/W  | 0h    | I2C target address                                                                                        |
| 19-5  | EEPROM_LOCK_KEY    | W    | 0h    | EEPROM lock/unlock key when EEPROM R/W protection is enabled. This bitfield will always read 0 when read. |
| 4-3   | SLEW_RATE_I2C_PINS | R/W  | 0h    | Slew rate control for I2C pins<br>0h = 4.8 mA<br>1h = 3.9 mA<br>2h = 1.86 mA<br>3h = 30.8 mA              |
| 2     | PULLUP_ENABLE      | R/W  | 0h    | Internal pull-up enable for nFAULT and FG pins<br>0h = Disable<br>1h = Enable                             |

**Table 7-24. DEVICE\_CONFIG1 Register Field Descriptions (continued)**

| Bit | Field    | Type | Reset | Description                                                                                            |
|-----|----------|------|-------|--------------------------------------------------------------------------------------------------------|
| 1-0 | BUS_VOLT | R/W  | 0h    | Maximum DC bus voltage configuration<br><br>0h = 15 V<br>1h = 30 V<br>2h = 40 V<br>3h = Not Applicable |

### 7.3.3 DEVICE\_CONFIG2 Register (Offset = A8h) [Reset = 00000000h]

DEVICE\_CONFIG2 is shown in [Figure 7-19](#) and described in [Table 7-25](#).

Return to the [Summary Table](#).

Register to configure device

**Figure 7-19. DEVICE\_CONFIG2 Register**

|                    |                     |                         |                |                  |                    |                    |    |
|--------------------|---------------------|-------------------------|----------------|------------------|--------------------|--------------------|----|
| 31                 | 30                  | 29                      | 28             | 27               | 26                 | 25                 | 24 |
| PARITY             | INPUT_MAXIMUM_FREQ  |                         |                |                  |                    |                    |    |
| R/W-0h             | R/W-0h              |                         |                |                  |                    |                    |    |
| 23                 | 22                  | 21                      | 20             | 19               | 18                 | 17                 | 16 |
| INPUT_MAXIMUM_FREQ |                     |                         |                |                  |                    |                    |    |
| R/W-0h             |                     |                         |                |                  |                    |                    |    |
| 15                 | 14                  | 13                      | 12             | 11               | 10                 | 9                  | 8  |
| SLEEP_ENTRY_TIME   | DYNAMIC_CSA_GAIN_EN | DYNAMIC_VOLTAGE_GAIN_EN | DEV_MODE       | PWM_DITHER_DEPTH |                    | EXT_CLK_EN         |    |
| R/W-0h             | R/W-0h              | R/W-0h                  | R/W-0h         | R/W-0h           |                    | R/W-0h             |    |
| 7                  | 6                   | 5                       | 4              | 3                | 2                  | 1                  | 0  |
| EXT_CLK_CONFIG     |                     | EXT_WDT_EN              | EXT_WDT_CONFIG |                  | EXT_WDT_INPUT_MODE | EXT_WDT_FAULT_MODE |    |
| R/W-0h             |                     | R/W-0h                  | R/W-0h         |                  | R/W-0h             | R/W-0h             |    |

**Table 7-25. DEVICE\_CONFIG2 Register Field Descriptions**

| Bit   | Field                   | Type | Reset | Description                                                                                                                                                                                                                                                                                                                                                      |
|-------|-------------------------|------|-------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| 31    | PARITY                  | R/W  | 0h    | Parity bit                                                                                                                                                                                                                                                                                                                                                       |
| 30-16 | INPUT_MAXIMUM_FREQ      | R/W  | 0h    | Input frequency on speed pin for input reference mode as "controlled by frequency of SPEED pin" that corresponds to 100% duty cycle. Duty cycle = Input frequency / INPUT_MAXIMUM_FREQ                                                                                                                                                                           |
| 15-14 | SLEEP_ENTRY_TIME        | R/W  | 0h    | Device enters sleep mode when input source (SPEED_MODE) is held at or below the sleep entry threshold for SLEEP_ENTRY_TIME<br>0h = Sleep Entry when SPEED pin remains low for 50 µs<br>1h = Sleep Entry when SPEED pin remains low for 200 µs<br>2h = Sleep Entry when SPEED pin remains low for 20 ms<br>3h = Sleep Entry when SPEED pin remains low for 200 ms |
| 13    | DYNAMIC_CSA_GAIN_EN     | R/W  | 0h    | Adjust CSA gain automatically for optimal current resolution at all current levels<br>0h = Disable<br>1h = Enable                                                                                                                                                                                                                                                |
| 12    | DYNAMIC_VOLTAGE_GAIN_EN | R/W  | 0h    | Adjust voltage gain automatically for optimal voltage resolution at all voltage levels<br>0h = Disable<br>1h = Enable                                                                                                                                                                                                                                            |
| 11    | DEV_MODE                | R/W  | 0h    | Device mode select<br>0h = Standby Mode<br>1h = Sleep Mode                                                                                                                                                                                                                                                                                                       |

**Table 7-25. DEVICE\_CONFIG2 Register Field Descriptions (continued)**

| Bit  | Field              | Type | Reset | Description                                                                                                                                                            |
|------|--------------------|------|-------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| 10-9 | PWM_DITHER_DEPTH   | R/W  | 0h    | PWM dither depth<br><br>0h = PWM dither disabled<br>1h = 5%<br>2h = 7.5%<br>3h = 10%                                                                                   |
| 8    | EXT_CLK_EN         | R/W  | 0h    | Enable external clock mode<br><br>0h = Disable<br>1h = Enable                                                                                                          |
| 7-5  | EXT_CLK_CONFIG     | R/W  | 0h    | External clock frequency configuration<br><br>0h = 8 kHz<br>1h = 16 kHz<br>2h = 32 kHz<br>3h = 64 kHz<br>4h = 128 kHz<br>5h = 256 kHz<br>6h = 512 kHz<br>7h = 1024 kHz |
| 4    | EXT_WDT_EN         | R/W  | 0h    | Enable external watchdog<br><br>0h = Disable<br>1h = Enable                                                                                                            |
| 3-2  | EXT_WDT_CONFIG     | R/W  | 0h    | Time between watchdog tickles (GPIO/I2C)<br><br>0h = 100ms/1s<br>1h = 200ms/2s<br>2h = 500ms/5s<br>3h = 1000ms/10s                                                     |
| 1    | EXT_WDT_INPUT_MODE | R/W  | 0h    | External watchdog input source<br><br>0h = Watchdog tickle over I2C<br>1h = Watchdog tickle over GPIO                                                                  |
| 0    | EXT_WDT_FAULT_MODE | R/W  | 0h    | External watchdog fault mode<br><br>0h = Report only<br>1h = Latch with MOSFETs in Hi-Z                                                                                |

### 7.3.4 PERI\_CONFIG1 Register (Offset = AAh) [Reset = 00000000h]

PERI\_CONFIG1 is shown in [Figure 7-20](#) and described in [Table 7-26](#).

Return to the [Summary Table](#).

Register to peripheral1

**Figure 7-20. PERI\_CONFIG1 Register**

| 31                                   | 30                             | 29                     | 28                           | 27                            | 26              | 25                 | 24                                   |
|--------------------------------------|--------------------------------|------------------------|------------------------------|-------------------------------|-----------------|--------------------|--------------------------------------|
| PARITY                               | SPREAD_SPECTRUM_MODULATION_DIS | RESERVED               | NO_MTR_FLT_CLOSEDLOOP_DIS    | ABNORMAL_BEMF_PERSISTENT_TIME |                 | FLUX_WEAK_REF      |                                      |
| R/W-0h                               | R/W-0h                         | R-0h                   | R/W-0h                       | R/W-0h                        |                 | R/W-0h             |                                      |
| 23                                   | 22                             | 21                     | 20                           | 19                            | 18              | 17                 | 16                                   |
| INPUT_REFERENCE_WINDOW               |                                | BUS_POWER_LIMIT_ENABLE | DIR_INPUT                    |                               | DIR_CHANGE_MODE | SPEED_LIMIT_ENABLE | ACTIVE_BRAKE_SPEED_DELTA_LIMIT_ENTRY |
| R/W-0h                               |                                | R/W-0h                 | R/W-0h                       |                               | R/W-0h          | R/W-0h             | R/W-0h                               |
| 15                                   | 14                             | 13                     | 12                           | 11                            | 10              | 9                  | 8                                    |
| ACTIVE_BRAKE_SPEED_DELTA_LIMIT_ENTRY |                                |                        | ACTIVE_BRAKE_MOD_INDEX_LIMIT |                               |                 | SPEED_RANGE_SEL    | INPUT_REFERENCE_MODE                 |
| R/W-0h                               |                                |                        | R/W-0h                       |                               |                 | R/W-0h             | R/W-0h                               |
| 7                                    | 6                              | 5                      | 4                            | 3                             | 2               | 1                  | 0                                    |
| INPUT_REFERENCE_MODE                 | EEPROM_LOCK_MODE               |                        |                              |                               |                 |                    | RESERVED                             |
| R/W-0h                               | R/W-0h                         |                        |                              |                               |                 |                    | R-0h                                 |

**Table 7-26. PERI\_CONFIG1 Register Field Descriptions**

| Bit   | Field                          | Type | Reset | Description                                                                                                                                                    |
|-------|--------------------------------|------|-------|----------------------------------------------------------------------------------------------------------------------------------------------------------------|
| 31    | PARITY                         | R/W  | 0h    | Parity bit                                                                                                                                                     |
| 30    | SPREAD_SPECTRUM_MODULATION_DIS | R/W  | 0h    | Disable Spread Spectrum Modulation (SSM)<br><br>0h = SSM is Enabled<br>1h = SSM is Disabled                                                                    |
| 29    | RESERVED                       | R    | 0h    | Reserved                                                                                                                                                       |
| 28    | NO_MTR_FLT_CLOSEDLOOP_DIS      | R/W  | 0h    | Disable No Motor fault in closed loop<br><br>0h = Enable no motor fault in closed loop if LOCK2_EN is set to 0x1<br>1h = Disable No Motor fault in closed loop |
| 27-26 | ABNORMAL_BEMF_PERSISTENT_TIME  | R/W  | 0h    | Deglitch time for Abnormal BEMF fault detection<br><br>0h = 2 electrical cycles<br>1h = 500 ms<br>2h = 1000 ms<br>3h = 2000 ms                                 |
| 25-24 | FLUX_WEAK_REF                  | R/W  | 0h    | Reference for flux weakening controller<br><br>0h = 70%<br>1h = 80%<br>2h = 90%<br>3h = 95%                                                                    |

**Table 7-26. PERI\_CONFIG1 Register Field Descriptions (continued)**

| Bit   | Field                                | Type | Reset | Description                                                                                                                                                                                                                                                                                                |
|-------|--------------------------------------|------|-------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| 23-22 | INPUT_REFERENCE_WINDOW               | R/W  | 0h    | Disables all control loops when output reaches within the window<br><br>0h = Reference window disabled<br>1h = Reference window of 5%<br>2h = Reference window of 10%<br>3h = Reference window of 15%                                                                                                      |
| 21    | BUS_POWER_LIMIT_ENABLE               | R/W  | 0h    | Enable bus power limit. Limits input DC bus power to MAX_POWER in all input reference modes except power mode<br><br>0h = Disable power limit<br>1h = Enable power limit                                                                                                                                   |
| 20-19 | DIR_INPUT                            | R/W  | 0h    | DIR pin override<br><br>0h = Hardware Pin DIR<br>1h = Override DIR pin with clockwise rotation OUTA-OUTB-OUTC<br>2h = Override DIR pin with counter clockwise rotation OUTA-OUTC-OUTB<br>3h = Hardware Pin DIR                                                                                             |
| 18    | DIR_CHANGE_MODE                      | R/W  | 0h    | Response to change of DIR pin status<br><br>0h = Follow motor stop options and ISD routine on detecting DIR change<br>1h = Change the direction through Reverse Drive while continuously driving the motor                                                                                                 |
| 17    | SPEED_LIMIT_ENABLE                   | R/W  | 0h    | Enable motor speed limit. Limits motor speed to MAX_SPEED in all input reference modes except speed mode<br><br>0h = Disable speed limit<br>1h = Enable speed limit                                                                                                                                        |
| 16-13 | ACTIVE_BRAKE_SPEED_DELTA_LIMIT_ENTRY | R/W  | 0h    | Difference between final speed and present speed below which active braking will be applied<br><br>0h = Not Applicable<br>1h = 5%<br>2h = 10%<br>3h = 15%<br>4h = 20%<br>5h = 25%<br>6h = 30%<br>7h = 35%<br>8h = 40%<br>9h = 45%<br>Ah = 50%<br>Bh = 60%<br>Ch = 70%<br>Dh = 80%<br>Eh = 90%<br>Fh = 100% |

**Table 7-26. PERI\_CONFIG1 Register Field Descriptions (continued)**

| Bit   | Field                        | Type | Reset | Description                                                                                                                                                                                                                                                                                                                                          |
|-------|------------------------------|------|-------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| 12-10 | ACTIVE_BRAKE_MOD_INDEX_LIMIT | R/W  | 0h    | Modulation index limit below which active braking will be applied<br><br>0h = 0%<br>1h = 40%<br>2h = 50%<br>3h = 60%<br>4h = 70%<br>5h = 80%<br>6h = 90%<br>7h = 100%                                                                                                                                                                                |
| 9     | SPEED_RANGE_SEL              | R/W  | 0h    | Frequency range selection for PWM duty mode reference input<br><br>0h = 325Hz to 100kHz<br>1h = 10Hz to 325Hz                                                                                                                                                                                                                                        |
| 8-7   | INPUT_REFERENCE_MODE         | R/W  | 0h    | Input reference mode used for close loop operation<br><br>0h = Control speed (Input is speed reference, scaled to MAX_SPEED)<br>1h = Control power (Input is power reference, scaled to MAX_POWER)<br>2h = Control Torque (Input is current reference, scaled to ILIMIT)<br>3h = Control Modulation Index (Input is modulation index scaled to 100%) |
| 6-5   | EEPROM_LOCK_MODE             | R/W  | 0h    | EEPROM lock mode<br><br>0h = EEPROM read and write allowed without a passcode<br>1h = EEPROM read and write need a valid passcode<br>2h = EEPROM read needs a valid passcode, write is locked permanently<br>3h = EEPROM read and write is locked permanently                                                                                        |
| 4-0   | RESERVED                     | R    | 0h    | Reserved                                                                                                                                                                                                                                                                                                                                             |

### 7.3.5 GD\_CONFIG1 Register (Offset = ACh) [Reset = 00000000h]

GD\_CONFIG1 is shown in [Figure 7-21](#) and described in [Table 7-27](#).

Return to the [Summary Table](#).

Register to configure gated driver settings1

**Figure 7-21. GD\_CONFIG1 Register**

|          |          |          |          |           |          |          |         |
|----------|----------|----------|----------|-----------|----------|----------|---------|
| 31       | 30       | 29       | 28       | 27        | 26       | 25       | 24      |
| PARITY   | RESERVED |          | RESERVED | SLEW_RATE |          | RESERVED |         |
| R/W-0h   | R-0h     |          | R-0h     | R/W-0h    |          | R-0h     |         |
| 23       | 22       | 21       | 20       | 19        | 18       | 17       | 16      |
| RESERVED | RESERVED | RESERVED | RESERVED | OVP_SEL   | OVP_EN   | RESERVED | OTW_REP |
| R-0h     | R-0h     | R-0h     | R-0h     | R/W-0h    | R/W-0h   | R-0h     | R/W-0h  |
| 15       | 14       | 13       | 12       | 11        | 10       | 9        | 8       |
| RESERVED | RESERVED | OCP_DEG  |          | RESERVED  | OCP_LVL  | OCP_MODE |         |
| R-0h     | R-0h     | R/W-0h   |          | R-0h      | R/W-0h   | R/W-0h   |         |
| 7        | 6        | 5        | 4        | 3         | 2        | 1        | 0       |
| RESERVED | RESERVED | RESERVED | RESERVED | RESERVED  | RESERVED | CSA_GAIN |         |
| R-0h     | R-0h     | R-0h     | R-0h     | R-0h      | R-0h     | R/W-0h   |         |

**Table 7-27. GD\_CONFIG1 Register Field Descriptions**

| Bit   | Field     | Type | Reset | Description                                                                                                                                    |
|-------|-----------|------|-------|------------------------------------------------------------------------------------------------------------------------------------------------|
| 31    | PARITY    | R/W  | 0h    | Parity bit                                                                                                                                     |
| 30-29 | RESERVED  | R    | 0h    | Reserved                                                                                                                                       |
| 28    | RESERVED  | R    | 0h    | Reserved                                                                                                                                       |
| 27-26 | SLEW_RATE | R/W  | 0h    | Slew rate<br>0h = Not Applicable<br>1h = Not Applicable<br>2h = Slew rate is 125 V/μs<br>3h = Slew rate is 200 V/μs                            |
| 25-24 | RESERVED  | R    | 0h    | Reserved                                                                                                                                       |
| 23    | RESERVED  | R    | 0h    | Reserved                                                                                                                                       |
| 22    | RESERVED  | R    | 0h    | Reserved                                                                                                                                       |
| 21    | RESERVED  | R    | 0h    | Reserved                                                                                                                                       |
| 20    | RESERVED  | R    | 0h    | Reserved                                                                                                                                       |
| 19    | OVP_SEL   | R/W  | 0h    | Overvoltage level<br>0h = VM overvoltage level is 34-V<br>1h = VM overvoltage level is 22-V                                                    |
| 18    | OVP_EN    | R/W  | 0h    | Enable overvoltage<br>0h = Overvoltage protection is disabled<br>1h = Overvoltage protection is enabled                                        |
| 17    | RESERVED  | R    | 0h    | Reserved                                                                                                                                       |
| 16    | OTW_REP   | R/W  | 0h    | Overtemperature warning reporting<br>0h = Over temperature warning reporting is disabled<br>1h = Over temperature warning reporting is enabled |
| 15    | RESERVED  | R    | 0h    | Reserved                                                                                                                                       |

**Table 7-27. GD\_CONFIG1 Register Field Descriptions (continued)**

| Bit   | Field    | Type | Reset | Description                                                                                                                                                                                 |
|-------|----------|------|-------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| 14    | RESERVED | R    | 0h    | Reserved                                                                                                                                                                                    |
| 13-12 | OCP_DEG  | R/W  | 0h    | OCP deglitch time<br>0h = OCP deglitch time is 0.2 $\mu$ s<br>1h = OCP deglitch time is 0.6 $\mu$ s<br>2h = OCP deglitch time is 1.2 $\mu$ s<br>3h = OCP deglitch time is 1.6 $\mu$ s       |
| 11    | RESERVED | R    | 0h    | Reserved                                                                                                                                                                                    |
| 10    | OCP_LVL  | R/W  | 0h    | Overcurrent level<br>0h = OCP level is 9 A (Typical)<br>1h = OCP level is 13 A (Typical)                                                                                                    |
| 9-8   | OCP_MODE | R/W  | 0h    | OCP fault mode<br>0h = Overcurrent causes a latched fault<br>1h = Overcurrent causes an automatic retry after 500ms<br>2h = Not Applicable<br>3h = Not Applicable                           |
| 7     | RESERVED | R    | 0h    | Reserved                                                                                                                                                                                    |
| 6     | RESERVED | R    | 0h    | Reserved                                                                                                                                                                                    |
| 5     | RESERVED | R    | 0h    | Reserved                                                                                                                                                                                    |
| 4     | RESERVED | R    | 0h    | Reserved                                                                                                                                                                                    |
| 3     | RESERVED | R    | 0h    | Reserved                                                                                                                                                                                    |
| 2     | RESERVED | R    | 0h    | Reserved                                                                                                                                                                                    |
| 1-0   | CSA_GAIN | R/W  | 0h    | Current sense amplifier's gain (used only if DYNAMIC_CSA_GAIN_EN = 0x0)<br>0h = CSA gain is 0.24 V/A<br>1h = CSA gain is 0.48 V/A<br>2h = CSA gain is 0.96 V/A<br>3h = CSA gain is 1.92 V/A |

### 7.3.6 GD\_CONFIG2 Register (Offset = AEh) [Reset = 00000000h]

GD\_CONFIG2 is shown in [Figure 7-22](#) and described in [Table 7-28](#).

Return to the [Summary Table](#).

Register to configure gated driver settings2

**Figure 7-22. GD\_CONFIG2 Register**

|          |          |          |          |             |    |          |             |
|----------|----------|----------|----------|-------------|----|----------|-------------|
| 31       | 30       | 29       | 28       | 27          | 26 | 25       | 24          |
| PARITY   | RESERVED | RESERVED |          |             |    | RESERVED | BUCK_PS_DIS |
| R/W-0h   | R-0h     | R-0h     |          |             |    | R-0h     | R/W-0h      |
| 23       | 22       | 21       | 20       | 19          | 18 | 17       | 16          |
| BUCK_CL  | BUCK_SEL |          | BUCK_DIS | MIN_ON_TIME |    |          | RESERVED    |
| R/W-0h   | R/W-0h   |          | R/W-0h   | R/W-0h      |    |          | R-0h        |
| 15       | 14       | 13       | 12       | 11          | 10 | 9        | 8           |
| RESERVED |          |          | RESERVED |             |    |          |             |
| R-0h     |          |          | R-0h     |             |    |          |             |
| 7        | 6        | 5        | 4        | 3           | 2  | 1        | 0           |
| RESERVED |          |          |          |             |    |          |             |
| R-0h     |          |          |          |             |    |          |             |

**Table 7-28. GD\_CONFIG2 Register Field Descriptions**

| Bit   | Field       | Type | Reset | Description                                                                                                                                 |
|-------|-------------|------|-------|---------------------------------------------------------------------------------------------------------------------------------------------|
| 31    | PARITY      | R/W  | 0h    | Parity bit                                                                                                                                  |
| 30    | RESERVED    | R    | 0h    | Reserved                                                                                                                                    |
| 29-26 | RESERVED    | R    | 0h    | Reserved                                                                                                                                    |
| 25    | RESERVED    | R    | 0h    | Reserved                                                                                                                                    |
| 24    | BUCK_PS_DIS | R/W  | 0h    | Buck power sequencing disable<br>0h = Buck power sequencing is enabled<br>1h = Buck power sequencing is disabled                            |
| 23    | BUCK_CL     | R/W  | 0h    | Buck current limit<br>0h = Buck regulator current limit is set to 600 mA<br>1h = Buck regulator current limit is set to 150 mA              |
| 22-21 | BUCK_SEL    | R/W  | 0h    | Buck output voltage<br>0h = Buck voltage is 3.3 V<br>1h = Buck voltage is 5.0 V<br>2h = Buck voltage is 4.0 V<br>3h = Buck voltage is 5.7 V |
| 20    | BUCK_DIS    | R/W  | 0h    | Buck disable<br>0h = Buck regulator is enabled<br>1h = Buck regulator is disabled                                                           |

**Table 7-28. GD\_CONFIG2 Register Field Descriptions (continued)**

| Bit   | Field       | Type | Reset | Description                                                                                                                                                                                                          |
|-------|-------------|------|-------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| 19-17 | MIN_ON_TIME | R/W  | 0h    | Minimum ON time for low side MOSFET<br><br>0h = 0 $\mu$ s<br>1h = Automatic based on slew rate<br>2h = 0.5 $\mu$ s<br>3h = 0.75 $\mu$ s<br>4h = 1 $\mu$ s<br>5h = 1.25 $\mu$ s<br>6h = 1.5 $\mu$ s<br>7h = 2 $\mu$ s |
| 16-13 | RESERVED    | R    | 0h    | Reserved                                                                                                                                                                                                             |
| 12-0  | RESERVED    | R    | 0h    | Reserved                                                                                                                                                                                                             |

## 7.4 Internal\_Algorithm\_Configuration Registers

Table 7-29 lists the memory-mapped registers for the Internal\_Algorithm\_Configuration registers. All register offset addresses not listed in Table 7-29 should be considered as reserved locations and the register contents should not be modified.

**Table 7-29. INTERNAL\_ALGORITHM\_CONFIGURATION Registers**

| Offset | Acronym    | Register Name                     | Section                       |
|--------|------------|-----------------------------------|-------------------------------|
| A0h    | INT_ALGO_1 | Internal Algorithm Configuration1 | <a href="#">Section 7.4.1</a> |
| A2h    | INT_ALGO_2 | Internal Algorithm Configuration2 | <a href="#">Section 7.4.2</a> |

Complex bit access types are encoded to fit into small table cells. Table 7-30 shows the codes that are used for access types in this section.

**Table 7-30. Internal\_Algorithm\_Configuration  
Access Type Codes**

| Access Type            | Code | Description                            |
|------------------------|------|----------------------------------------|
| Read Type              |      |                                        |
| R                      | R    | Read                                   |
| Write Type             |      |                                        |
| W                      | W    | Write                                  |
| Reset or Default Value |      |                                        |
| -n                     |      | Value after reset or the default value |

### 7.4.1 INT\_ALGO\_1 Register (Offset = A0h) [Reset = 00000000h]

INT\_ALGO\_1 is shown in [Figure 7-23](#) and described in [Table 7-31](#).

Return to the [Summary Table](#).

Register to configure internal algorithm parameters<sup>1</sup>

**Figure 7-23. INT\_ALGO\_1 Register**

|                       |                                      |                         |                       |               |                       |    |    |
|-----------------------|--------------------------------------|-------------------------|-----------------------|---------------|-----------------------|----|----|
| 31                    | 30                                   | 29                      | 28                    | 27            | 26                    | 25 | 24 |
| PARITY                | ACTIVE_BRAKE_SPEED__DELTA_LIMIT_EXIT | SPEED_PIN_GLITCH_FILTER | FAST_ISD_EN           | ISD_STOP_TIME |                       |    |    |
| R/W-0h                | R/W-0h                               | R/W-0h                  | R/W-0h                | R/W-0h        | R/W-0h                |    |    |
| 23                    | 22                                   | 21                      | 20                    | 19            | 18                    | 17 | 16 |
| ISD_RUN_TIME          | ISD_TIMEOUT                          | AUTO_HANDOFF_MIN_BEMF   | BRAKE_CURRENT_PERSIST |               |                       |    |    |
| R/W-0h                | R/W-0h                               | R/W-0h                  | R/W-0h                | R/W-0h        | R/W-0h                |    |    |
| 15                    | 14                                   | 13                      | 12                    | 11            | 10                    | 9  | 8  |
| BRAKE_CURRENT_PERSIST | RESERVED                             |                         |                       |               |                       |    |    |
| R/W-0h                | R-0h                                 |                         |                       |               |                       |    |    |
| 7                     | 6                                    | 5                       | 4                     | 3             | 2                     | 1  | 0  |
| RESERVED              |                                      |                         |                       |               | REV_DRV_OPEN_LOOP_DEC |    |    |
| R-0h                  |                                      |                         |                       |               | R/W-0h                |    |    |

**Table 7-31. INT\_ALGO\_1 Register Field Descriptions**

| Bit   | Field                                | Type | Reset | Description                                                                                                                                      |
|-------|--------------------------------------|------|-------|--------------------------------------------------------------------------------------------------------------------------------------------------|
| 31    | PARITY                               | R/W  | 0h    | Parity bit                                                                                                                                       |
| 30-29 | ACTIVE_BRAKE_SPEED__DELTA_LIMIT_EXIT | R/W  | 0h    | Difference between final speed and present speed below which active braking will be stopped<br><br>0h = 2.5%<br>1h = 5%<br>2h = 7.5%<br>3h = 10% |
| 28-27 | SPEED_PIN_GLITCH_FILTER              | R/W  | 0h    | Glitch filter applied on speed pin input<br><br>0h = No Glitch Filter<br>1h = 0.2 $\mu$ s<br>2h = 0.5 $\mu$ s<br>3h = 1.0 $\mu$ s                |
| 26    | FAST_ISD_EN                          | R/W  | 0h    | Enable fast speed detection during ISD<br><br>0h = Disable fast ISD<br>1h = Enable fast ISD                                                      |
| 25-24 | ISD_STOP_TIME                        | R/W  | 0h    | Persistence time for declaring motor is in stopped state during ISD<br><br>0h = 1 ms<br>1h = 5 ms<br>2h = 50 ms<br>3h = 100 ms                   |

**Table 7-31. INT\_ALGO\_1 Register Field Descriptions (continued)**

| Bit   | Field                 | Type | Reset | Description                                                                                                                                                                                     |
|-------|-----------------------|------|-------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| 23-22 | ISD_RUN_TIME          | R/W  | 0h    | Persistence time for declaring motor is in running state during ISD<br><br>0h = 1 ms<br>1h = 5 ms<br>2h = 50 ms<br>3h = 100 ms                                                                  |
| 21-20 | ISD_TIMEOUT           | R/W  | 0h    | Timeout in case ISD is unable to reliably detect speed or direction<br><br>0h = 500ms<br>1h = 750 ms<br>2h = 1000 ms<br>3h = 2000 ms                                                            |
| 19-17 | AUTO_HANDOFF_MIN_BEMF | R/W  | 0h    | Minimum BEMF for handoff. Applicable when auto handoff is enabled.<br><br>0h = 0 mV<br>1h = 50 mV<br>2h = 100 mV<br>3h = 250 mV<br>4h = 500 mV<br>5h = 1000 mV<br>6h = 1250 mV<br>7h = 1500 mV  |
| 16-15 | BRAKE_CURRENT_PERSIST | R/W  | 0h    | Persistence time for current below threshold during current based ISD brake<br><br>0h = 50 ms<br>1h = 100 ms<br>2h = 250 ms<br>3h = 500 ms                                                      |
| 14-3  | RESERVED              | R    | 0h    | Reserved                                                                                                                                                                                        |
| 2-0   | REV_DRV_OPEN_LOOP_DEC | R/W  | 0h    | % of open loop acceleration to be applied during open loop deceleration in reverse drive<br><br>0h = 50%<br>1h = 60%<br>2h = 70%<br>3h = 80%<br>4h = 90%<br>5h = 100%<br>6h = 125%<br>7h = 150% |

### 7.4.2 INT\_ALGO\_2 Register (Offset = A2h) [Reset = 00000000h]

INT\_ALGO\_2 is shown in [Figure 7-24](#) and described in [Table 7-32](#).

Return to the [Summary Table](#).

Register to configure internal algorithm parameters2

**Figure 7-24. INT\_ALGO\_2 Register**

|              |              |                                    |              |        |                        |                               |                        |
|--------------|--------------|------------------------------------|--------------|--------|------------------------|-------------------------------|------------------------|
| 31           | 30           | 29                                 | 28           | 27     | 26                     | 25                            | 24                     |
| PARITY       | FLUX_WEAK_KP |                                    |              |        |                        |                               |                        |
| R/W-0h       |              |                                    |              | R/W-0h |                        |                               |                        |
| 23           | 22           | 21                                 | 20           | 19     | 18                     | 17                            | 16                     |
| FLUX_WEAK_KP |              |                                    | FLUX_WEAK_KI |        |                        |                               |                        |
| R/W-0h       |              |                                    |              | R/W-0h |                        |                               |                        |
| 15           | 14           | 13                                 | 12           | 11     | 10                     | 9                             | 8                      |
| FLUX_WEAK_KI |              |                                    |              |        | FLUX_WEAK_ENABLE       | CL_SLOW_ACC                   |                        |
| R/W-0h       |              |                                    |              | R/W-0h |                        | R/W-0h                        |                        |
| 7            | 6            | 5                                  | 4            | 3      | 2                      | 1                             | 0                      |
| CL_SLOW_ACC  |              | ACTIVE_BRAKE_BUS_CURRENT_SLEW_RATE |              |        | ISD_BEMF_FILTER_ENABLE | CIRCULAR_CURRENT_LIMIT_ENABLE | IPD_HIGH_RESOLUTION_EN |
| R/W-0h       |              | R/W-0h                             |              |        | R/W-0h                 | R/W-0h                        | R/W-0h                 |

**Table 7-32. INT\_ALGO\_2 Register Field Descriptions**

| Bit   | Field            | Type | Reset | Description                                                                                                                       |
|-------|------------------|------|-------|-----------------------------------------------------------------------------------------------------------------------------------|
| 31    | PARITY           | R/W  | 0h    | Parity bit                                                                                                                        |
| 30-21 | FLUX_WEAK_KP     | R/W  | 0h    | 10-bit value for flux weakening loop Kp. $K_p = 8\text{LSB of } 0.1 * \text{FLUX\_WEAK\_KP} / 10^2\text{MSB of FLUX\_WEAK\_KP}$ . |
| 20-11 | FLUX_WEAK_KI     | R/W  | 0h    | 10-bit value for current $I_q$ and $I_d$ loop Ki. $K_i = 10 * 8\text{LSB of FLUX\_WEAK\_KI} / 10^2\text{MSB of FLUX\_WEAK\_KI}$ . |
| 10    | FLUX_WEAK_ENABLE | R/W  | 0h    | Enable flux weakening<br>0h = Flux Weakening is disabled<br>1h = Flux Weakening is enabled                                        |

**Table 7-32. INT\_ALGO\_2 Register Field Descriptions (continued)**

| Bit | Field                              | Type | Reset | Description                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                               |
|-----|------------------------------------|------|-------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| 9-6 | CL_SLOW_ACC                        | R/W  | 0h    | <p>Close loop acceleration when estimator is not yet fully aligned (only in speed mode) and acceleration/deacceleration during power/speed limit (Speed mode: Hz/s Power mode: deciWatts/s Torque mode: centiA/s duty cycle mode: milliUnit/s) deciWatt: 0.1W centiA: 0.01A milliUnit: 0.001%</p> <p>0h = 0.1 Hz/s<br/>1h = 1 Hz/s<br/>2h = 2 Hz/s<br/>3h = 3 Hz/s<br/>4h = 5 Hz/s<br/>5h = 10 Hz/s<br/>6h = 20 Hz/s<br/>7h = 30 Hz/s<br/>8h = 40 Hz/s<br/>9h = 50 Hz/s<br/>Ah = 100 Hz/s<br/>Bh = 200 Hz/s<br/>Ch = 500 Hz/s<br/>Dh = 750 Hz/s<br/>Eh = 1000 Hz/s<br/>Fh = 2000 Hz/s</p> |
| 5-3 | ACTIVE_BRAKE_BUS_CURRENT_SLEW_RATE | R/W  | 0h    | <p>Bus current slew rate during active braking</p> <p>0h = 10 A/s<br/>1h = 50 A/s<br/>2h = 100 A/s<br/>3h = 250 A/s<br/>4h = 500 A/s<br/>5h = 1000 A/s<br/>6h = 5000 A/s<br/>7h = No Limit A/s</p>                                                                                                                                                                                                                                                                                                                                                                                        |
| 2   | ISD_BEMF_FILT_ENABLE               | R/W  | 0h    | <p>Enable BEMF filter during ISD.</p> <p>0h = Disable<br/>1h = Enable</p>                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                 |
| 1   | CIRCULAR_CURRENT_LIMIT_ENABLE      | R/W  | 0h    | <p>Configuration for ILIMIT vs. peak phase current</p> <p>0h = Circular current limit is disabled: ILIMIT * sqrt(2) can be peak phase current<br/>1h = Circular current limit is enabled: ILIMIT is peak phase current</p>                                                                                                                                                                                                                                                                                                                                                                |
| 0   | IPD_HIGH_RESOLUTION_EN             | R/W  | 0h    | <p>IPD high resolution enable</p> <p>0h = Disable<br/>1h = Enable</p>                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                     |

## 8 RAM (Volatile) Register Map

### 8.1 Fault\_Status Registers

[Table 8-1](#) lists the memory-mapped registers for the Fault\_Status registers. All register offset addresses not listed in [Table 8-1](#) should be considered as reserved locations and the register contents should not be modified.

**Table 8-1. FAULT\_STATUS Registers**

| Offset | Acronym                  | Register Name         | Section                       |
|--------|--------------------------|-----------------------|-------------------------------|
| E0h    | GATE_DRIVER_FAULT_STATUS | Fault Status Register | <a href="#">Section 8.1.1</a> |
| E2h    | CONTROLLER_FAULT_STATUS  | Fault Status Register | <a href="#">Section 8.1.2</a> |
| 32Ch   | EEPROM_FAULT_STATUS      |                       | <a href="#">Section 8.1.3</a> |

Complex bit access types are encoded to fit into small table cells. [Table 8-2](#) shows the codes that are used for access types in this section.

**Table 8-2. Fault\_Status Access Type Codes**

| Access Type            | Code | Description                            |
|------------------------|------|----------------------------------------|
| Read Type              |      |                                        |
| R                      | R    | Read                                   |
| Reset or Default Value |      |                                        |
| -n                     |      | Value after reset or the default value |

### 8.1.1 GATE\_DRIVER\_FAULT\_STATUS Register (Offset = E0h) [Reset = 00000000h]

GATE\_DRIVER\_FAULT\_STATUS is shown in [Figure 8-1](#) and described in [Table 8-3](#).

Return to the [Summary Table](#).

Status of various gate driver faults

**Figure 8-1. GATE\_DRIVER\_FAULT\_STATUS Register**

|              |          |          |         |          |          |          |          |
|--------------|----------|----------|---------|----------|----------|----------|----------|
| 31           | 30       | 29       | 28      | 27       | 26       | 25       | 24       |
| DRIVER_FAULT | RESERVED | RESERVED | OCP     | RESERVED | OVP      | RESERVED | RESERVED |
| R-0h         | R-0h     | R-0h     | R-0h    | R-0h     | R-0h     | R-0h     | R-0h     |
| 23           | 22       | 21       | 20      | 19       | 18       | 17       | 16       |
| OTW          | OTS      | OCP_HC   | OCP_LC  | OCP_HB   | OCP_LB   | OCP_HA   | OCP_LA   |
| R-0h         | R-0h     | R-0h     | R-0h    | R-0h     | R-0h     | R-0h     | R-0h     |
| 15           | 14       | 13       | 12      | 11       | 10       | 9        | 8        |
| RESERVED     | RESERVED | BUCK_OCP | BUCK_UV | VCP_UV   | RESERVED | RESERVED | RESERVED |
| R-0h         | R-0h     | R-0h     | R-0h    | R-0h     | R-0h     | R-0h     | R-0h     |
| 7            | 6        | 5        | 4       | 3        | 2        | 1        | 0        |
| RESERVED     |          |          |         |          |          |          |          |
| R-0h         |          |          |         |          |          |          |          |

**Table 8-3. GATE\_DRIVER\_FAULT\_STATUS Register Field Descriptions**

| Bit | Field        | Type | Reset | Description                                                                                                                                                         |
|-----|--------------|------|-------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| 31  | DRIVER_FAULT | R    | 0h    | Logic OR of gate driver fault status bits                                                                                                                           |
| 30  | RESERVED     | R    | 0h    | Reserved                                                                                                                                                            |
| 29  | RESERVED     | R    | 0h    | Reserved                                                                                                                                                            |
| 28  | OCP          | R    | 0h    | Over current protection status<br>0h = No overcurrent condition is detected<br>1h = Overcurrent condition is detected                                               |
| 27  | RESERVED     | R    | 0h    | Reserved                                                                                                                                                            |
| 26  | OVP          | R    | 0h    | Supply (VM) overvoltage protection status<br>0h = No overvoltage condition is detected on VM<br>1h = Overvoltage condition is detected on VM                        |
| 25  | RESERVED     | R    | 0h    | Reserved                                                                                                                                                            |
| 24  | RESERVED     | R    | 0h    | Reserved                                                                                                                                                            |
| 23  | OTW          | R    | 0h    | Overtemperature warning status<br>0h = No overtemperature warning is detected<br>1h = Overtemperature warning is detected                                           |
| 22  | OTS          | R    | 0h    | Overtemperature shutdown status<br>0h = No overtemperature shutdown is detected<br>1h = Overtemperature shutdown is detected                                        |
| 21  | OCP_HC       | R    | 0h    | Overcurrent status on high-side switch of OUTC<br>0h = No overcurrent detected on high-side switch of OUTC<br>1h = Overcurrent detected on high-side switch of OUTC |

**Table 8-3. GATE\_DRIVER\_FAULT\_STATUS Register Field Descriptions (continued)**

| Bit | Field    | Type | Reset | Description                                                                                                                                                         |
|-----|----------|------|-------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| 20  | OCP_LC   | R    | 0h    | Overcurrent status on low-side switch of OUTC<br>0h = No overcurrent detected on low-side switch of OUTC<br>1h = Overcurrent detected on low-side switch of OUTC    |
| 19  | OCP_HB   | R    | 0h    | Overcurrent status on high-side switch of OUTB<br>0h = No overcurrent detected on high-side switch of OUTB<br>1h = Overcurrent detected on high-side switch of OUTB |
| 18  | OCP_LB   | R    | 0h    | Overcurrent status on low-side switch of OUTB<br>0h = No overcurrent detected on low-side switch of OUTB<br>1h = Overcurrent detected on low-side switch of OUTB    |
| 17  | OCP_HA   | R    | 0h    | Overcurrent status on high-side switch of OUTA<br>0h = No overcurrent detected on high-side switch of OUTA<br>1h = Overcurrent detected on high-side switch of OUTA |
| 16  | OCP_LA   | R    | 0h    | Overcurrent status on low-side switch of OUTA<br>0h = No overcurrent detected on low-side switch of OUTA<br>1h = Overcurrent detected on low-side switch of OUTA    |
| 15  | RESERVED | R    | 0h    | Reserved                                                                                                                                                            |
| 14  | RESERVED | R    | 0h    | Reserved                                                                                                                                                            |
| 13  | BUCK_OCP | R    | 0h    | Buck regulator overcurrent status<br>0h = No buck regulator overcurrent is detected<br>1h = Buck regulator overcurrent is detected                                  |
| 12  | BUCK_UV  | R    | 0h    | Buck regulator undervoltage status<br>0h = No buck regulator undervoltage is detected<br>1h = Buck regulator undervoltage is detected                               |
| 11  | VCP_UV   | R    | 0h    | Charge pump undervoltage status<br>0h = No charge pump undervoltage is detected<br>1h = Charge pump undervoltage is detected                                        |
| 10  | RESERVED | R    | 0h    | Reserved                                                                                                                                                            |
| 9   | RESERVED | R    | 0h    | Reserved                                                                                                                                                            |
| 8   | RESERVED | R    | 0h    | Reserved                                                                                                                                                            |
| 7-0 | RESERVED | R    | 0h    | Reserved                                                                                                                                                            |

### 8.1.2 CONTROLLER\_FAULT\_STATUS Register (Offset = E2h) [Reset = 00000000h]

CONTROLLER\_FAULT\_STATUS is shown in [Figure 8-2](#) and described in [Table 8-4](#).

Return to the [Summary Table](#).

Status of various controller faults

**Figure 8-2. CONTROLLER\_FAULT\_STATUS Register**

| 31                    | 30                      | 29                   | 28                         | 27                    | 26                     | 25                | 24               |
|-----------------------|-------------------------|----------------------|----------------------------|-----------------------|------------------------|-------------------|------------------|
| CONTROLLER_FAULT      | RESERVED                | IPD_FREQ_FAULT       | IPD_T1_FAULT               | IPD_T2_FAULT          | RESERVED               | MPET_IPD_FAULT    | MPET_BEMF_FAULT  |
| R-0h                  | R-0h                    | R-0h                 | R-0h                       | R-0h                  | R-0h                   | R-0h              | R-0h             |
| 23                    | 22                      | 21                   | 20                         | 19                    | 18                     | 17                | 16               |
| ABN_SPEED             | ABN_BEMF                | NO_MTR               | MTR_LCK                    | LOCK_LIMIT            | HW_LOCK_LIMIT          | MTR_UNDER_VOLTAGE | MTR_OVER_VOLTAGE |
| R-0h                  | R-0h                    | R-0h                 | R-0h                       | R-0h                  | R-0h                   | R-0h              | R-0h             |
| 15                    | 14                      | 13                   | 12                         | 11                    | 10                     | 9                 | 8                |
| SPEED_LOOP_SATURATION | CURRENT_LOOP_SATURATION | MAX_SPEED_SATURATION | BUS_POWER_LIMIT_SATURATION | EEPROM_WRITE_LOCK_SET | EEPROM_READ_LOCK_SET   | RESERVED          |                  |
| R-0h                  | R-0h                    | R-0h                 | R-0h                       | R-0h                  | R-0h                   | R-0h              |                  |
| 7                     | 6                       | 5                    | 4                          | 3                     | 2                      | 1                 | 0                |
| RESERVED              | I2C_CRC_FAULT_STATUS    | EEPROM_ERROR_STATUS  | BOOT_STL_FAULT             | WATCHDOG_FAULT        | CPU_RESET_FAULT_STATUS | WWDT_FAULT_STATUS | RESERVED         |
| R-0h                  | R-0h                    | R-0h                 | R-0h                       | R-0h                  | R-0h                   | R-0h              | R-0h             |

**Table 8-4. CONTROLLER\_FAULT\_STATUS Register Field Descriptions**

| Bit | Field                   | Type | Reset | Description                                                                       |
|-----|-------------------------|------|-------|-----------------------------------------------------------------------------------|
| 31  | CONTROLLER_FAULT        | R    | 0h    | Logic OR of controller fault status bits                                          |
| 30  | RESERVED                | R    | 0h    | Reserved                                                                          |
| 29  | IPD_FREQ_FAULT          | R    | 0h    | IPD frequency fault status                                                        |
| 28  | IPD_T1_FAULT            | R    | 0h    | IPD T1 fault status                                                               |
| 27  | IPD_T2_FAULT            | R    | 0h    | IPD T2 fault status                                                               |
| 26  | RESERVED                | R    | 0h    | Reserved                                                                          |
| 25  | MPET_IPD_FAULT          | R    | 0h    | Indicates error during MPET resistance and inductance measurement                 |
| 24  | MPET_BEMF_FAULT         | R    | 0h    | Indicates error during MPET BEMF constant measurement                             |
| 23  | ABN_SPEED               | R    | 0h    | Indicates Abnormal speed motor lock condition                                     |
| 22  | ABN_BEMF                | R    | 0h    | Indicates Abnormal BEMF motor lock condition                                      |
| 21  | NO_MTR                  | R    | 0h    | Indicates No Motor (loss of phase) fault                                          |
| 20  | MTR_LCK                 | R    | 0h    | Indicates when one of the motor lock (abnormal BEMF/speed, no motor) is triggered |
| 19  | LOCK_LIMIT              | R    | 0h    | Indicates lock current limit fault                                                |
| 18  | HW_LOCK_LIMIT           | R    | 0h    | Indicates hardware lock current limit fault                                       |
| 17  | MTR_UNDER_VOLTAGE       | R    | 0h    | Indicates configurable under voltage fault on VM                                  |
| 16  | MTR_OVER_VOLTAGE        | R    | 0h    | Indicates configurable over voltage fault on VM                                   |
| 15  | SPEED_LOOP_SATURATION   | R    | 0h    | Indicates speed loop saturation                                                   |
| 14  | CURRENT_LOOP_SATURATION | R    | 0h    | Indicates current loop saturation                                                 |

**Table 8-4. CONTROLLER\_FAULT\_STATUS Register Field Descriptions (continued)**

| Bit | Field                          | Type | Reset | Description                                                              |
|-----|--------------------------------|------|-------|--------------------------------------------------------------------------|
| 13  | MAX_SPEED_SATURATI<br>ON       | R    | 0h    | Indicates maximum speed limit saturation                                 |
| 12  | BUS_POWER_LIMIT_SA<br>TURATION | R    | 0h    | Indicates maximum (input DC bus) power limit saturation                  |
| 11  | EEPROM_WRITE_LOCK<br>_SET      | R    | 0h    | Indicates EEPROM write lock is set                                       |
| 10  | EEPROM_READ_LOCK_<br>SET       | R    | 0h    | Indicates EEPROM read lock is set                                        |
| 9-8 | RESERVED                       | R    | 0h    | Reserved                                                                 |
| 7   | RESERVED                       | R    | 0h    | Reserved                                                                 |
| 6   | I2C_CRC_FAULT_STATU<br>S       | R    | 0h    | Indicates CRC fault in I2C packet                                        |
| 5   | EEPROM_ERR_STATUS              | R    | 0h    | Indicates error in EEPROM                                                |
| 4   | BOOT_STL_FAULT                 | R    | 0h    | Indicates self test fault during boot-up (applicable to MCF8315DUL only) |
| 3   | WATCHDOG_FAULT                 | R    | 0h    | Indicates watchdog timeout fault                                         |
| 2   | CPU_RESET_FAULT_ST<br>ATUS     | R    | 0h    | Indicates unexpected CPU reset fault (applicable to MCF8315DUL only)     |
| 1   | WWDT_FAULT_STATUS              | R    | 0h    | Indicates windowed watchdog reset fault (applicable to MCF8315DUL only)  |
| 0   | RESERVED                       | R    | 0h    | Reserved                                                                 |

### 8.1.3 EEPROM\_FAULT\_STATUS Register (Offset = 32Ch) [Reset = 0000h]

EEPROM\_FAULT\_STATUS is shown in [Figure 8-3](#) and described in [Table 8-5](#).

Return to the [Summary Table](#).

**Figure 8-3. EEPROM\_FAULT\_STATUS Register**

|          |    |    |                    |          |                       |          |          |
|----------|----|----|--------------------|----------|-----------------------|----------|----------|
| 15       | 14 | 13 | 12                 | 11       | 10                    | 9        | 8        |
| RESERVED |    |    |                    |          |                       |          |          |
| R-0h     |    |    |                    |          |                       |          |          |
| 7        | 6  | 5  | 4                  | 3        | 2                     | 1        | 0        |
| RESERVED |    |    | EEPROM_CRC_FLT_STS | RESERVED | EEPROM_PARITY_FLT_STS | RESERVED | RESERVED |
| R-0h     |    |    | R-0h               | R-0h     | R-0h                  | R-0h     | R-0h     |

**Table 8-5. EEPROM\_FAULT\_STATUS Register Field Descriptions**

| Bit  | Field                 | Type | Reset | Description                                                                                                                                          |
|------|-----------------------|------|-------|------------------------------------------------------------------------------------------------------------------------------------------------------|
| 15-5 | RESERVED              | R    | 0h    | Reserved                                                                                                                                             |
| 4    | EEPROM_CRC_FLT_STS    | R    | 0h    | EEPROM CRC error fault status<br>0h = EEPROM CRC Error fault condition is not detected<br>1h = EEPROM CRC Error fault condition is detected          |
| 3    | RESERVED              | R    | 0h    | Reserved                                                                                                                                             |
| 2    | EEPROM_PARITY_FLT_STS | R    | 0h    | EEPROM parity error fault status<br>0h = EEPROM Parity error fault condition is not detected<br>1h = EEPROM Parity error fault condition is detected |
| 1    | RESERVED              | R    | 0h    | Reserved                                                                                                                                             |
| 0    | RESERVED              | R    | 0h    | Reserved                                                                                                                                             |

## 8.2 System\_Status Registers

[Table 8-6](#) lists the memory-mapped registers for the System\_Status registers. All register offset addresses not listed in [Table 8-6](#) should be considered as reserved locations and the register contents should not be modified.

**Table 8-6. SYSTEM\_STATUS Registers**

| Offset | Acronym          | Register Name          | Section                       |
|--------|------------------|------------------------|-------------------------------|
| E4h    | ALGO_STATUS      | System Status Register | <a href="#">Section 8.2.1</a> |
| E6h    | MTR_PARAMS       | System Status Register | <a href="#">Section 8.2.2</a> |
| E8h    | ALGO_STATUS_MPET | System Status Register | <a href="#">Section 8.2.3</a> |

Complex bit access types are encoded to fit into small table cells. [Table 8-7](#) shows the codes that are used for access types in this section.

**Table 8-7. System\_Status Access Type Codes**

| Access Type            | Code | Description                            |
|------------------------|------|----------------------------------------|
| Read Type              |      |                                        |
| R                      | R    | Read                                   |
| Reset or Default Value |      |                                        |
| -n                     |      | Value after reset or the default value |

### 8.2.1 ALGO\_STATUS Register (Offset = E4h) [Reset = 00000000h]

ALGO\_STATUS is shown in [Figure 8-4](#) and described in [Table 8-8](#).

Return to the [Summary Table](#).

Status of various system and algorithm parameters

**Figure 8-4. ALGO\_STATUS Register**

|          |    |    |    |          |                 |          |    |
|----------|----|----|----|----------|-----------------|----------|----|
| 31       | 30 | 29 | 28 | 27       | 26              | 25       | 24 |
| VOLT_MAG |    |    |    |          |                 |          |    |
| R-0h     |    |    |    |          |                 |          |    |
| 23       | 22 | 21 | 20 | 19       | 18              | 17       | 16 |
| VOLT_MAG |    |    |    |          |                 |          |    |
| R-0h     |    |    |    |          |                 |          |    |
| 15       | 14 | 13 | 12 | 11       | 10              | 9        | 8  |
| DUTY_CMD |    |    |    |          |                 |          |    |
| R-0h     |    |    |    |          |                 |          |    |
| 7        | 6  | 5  | 4  | 3        | 2               | 1        | 0  |
| DUTY_CMD |    |    |    | RESERVED | SYS_ENABLE_FLAG | RESERVED |    |
| R-0h     |    |    |    | R-0h     | R-0h            | R-0h     |    |

**Table 8-8. ALGO\_STATUS Register Field Descriptions**

| Bit   | Field           | Type | Reset | Description                                                                                                        |
|-------|-----------------|------|-------|--------------------------------------------------------------------------------------------------------------------|
| 31-16 | VOLT_MAG        | R    | 0h    | 16-bit value indicating applied modulation index. Modulation index applied = $(VOLT\_MAG * 100 / 32768)\%$         |
| 15-4  | DUTY_CMD        | R    | 0h    | 12-bit value indicating input duty command in PWM/Analog/Freq mode $DUTY\_CMD (\%) = (DUTY\_CMD / 4095 * 100)\%$ . |
| 3     | RESERVED        | R    | 0h    | Reserved                                                                                                           |
| 2     | SYS_ENABLE_FLAG | R    | 0h    | 1 indicates GUI can control the register 0 indicates GUI is still copying default parameters from shadow memory    |
| 1-0   | RESERVED        | R    | 0h    | Reserved                                                                                                           |

## 8.2.2 MTR\_PARAMS Register (Offset = E6h) [Reset = 00000000h]

MTR\_PARAMS is shown in [Figure 8-5](#) and described in [Table 8-9](#).

Return to the [Summary Table](#).

Status of various motor parameters

**Figure 8-5. MTR\_PARAMS Register**

|         |    |    |    |    |    |    |    |                  |    |    |    |    |    |    |    |
|---------|----|----|----|----|----|----|----|------------------|----|----|----|----|----|----|----|
| 31      | 30 | 29 | 28 | 27 | 26 | 25 | 24 | 23               | 22 | 21 | 20 | 19 | 18 | 17 | 16 |
| MOTOR_R |    |    |    |    |    |    |    | MOTOR_BEMF_CONST |    |    |    |    |    |    |    |
| R-0h    |    |    |    |    |    |    |    | R-0h             |    |    |    |    |    |    |    |
| 15      | 14 | 13 | 12 | 11 | 10 | 9  | 8  | 7                | 6  | 5  | 4  | 3  | 2  | 1  | 0  |
| MOTOR_L |    |    |    |    |    |    |    | RESERVED         |    |    |    |    |    |    |    |
| R-0h    |    |    |    |    |    |    |    | R-0h             |    |    |    |    |    |    |    |

**Table 8-9. MTR\_PARAMS Register Field Descriptions**

| Bit   | Field            | Type | Reset | Description                                           |
|-------|------------------|------|-------|-------------------------------------------------------|
| 31-24 | MOTOR_R          | R    | 0h    | 8-bit value indicating MPET measured motor resistance |
| 23-16 | MOTOR_BEMF_CONST | R    | 0h    | 8-bit value indicating MPET measured BEMF constant    |
| 15-8  | MOTOR_L          | R    | 0h    | 8-bit value indicating MPET measured motor inductance |
| 7-0   | RESERVED         | R    | 0h    | Reserved                                              |

### 8.2.3 ALGO\_STATUS\_MPET Register (Offset = E8h) [Reset = 00000000h]

ALGO\_STATUS\_MPET is shown in [Figure 8-6](#) and described in [Table 8-10](#).

Return to the [Summary Table](#).

Status of various MPET parameters

**Figure 8-6. ALGO\_STATUS\_MPET Register**

|                   |                   |                    |                      |               |    |    |    |
|-------------------|-------------------|--------------------|----------------------|---------------|----|----|----|
| 31                | 30                | 29                 | 28                   | 27            | 26 | 25 | 24 |
| MPET_R_STAT<br>US | MPET_L_STAT<br>US | MPET_KE_STA<br>TUS | MPET_MECH_<br>STATUS | MPET_PWM_FREQ |    |    |    |
| R-0h              | R-0h              | R-0h               | R-0h                 | R-0h          |    |    |    |
| 23                | 22                | 21                 | 20                   | 19            | 18 | 17 | 16 |
| RESERVED          |                   |                    |                      |               |    |    |    |
| R-0h              |                   |                    |                      |               |    |    |    |
| 15                | 14                | 13                 | 12                   | 11            | 10 | 9  | 8  |
| RESERVED          |                   |                    |                      |               |    |    |    |
| R-0h              |                   |                    |                      |               |    |    |    |
| 7                 | 6                 | 5                  | 4                    | 3             | 2  | 1  | 0  |
| RESERVED          |                   |                    |                      |               |    |    |    |
| R-0h              |                   |                    |                      |               |    |    |    |

**Table 8-10. ALGO\_STATUS\_MPET Register Field Descriptions**

| Bit | Field            | Type | Reset | Description                                                                                                                                                                                                                                                                                                                     |
|-----|------------------|------|-------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| 31  | MPET_R_STATUS    | R    | 0h    | Indicates status of resistance measurement<br><br>0h = Measurement of motor resistance during MPET routine is not completed if resistance measurement is initiated during MPET<br>1h = Measurement of motor resistance during MPET routine is completed                                                                         |
| 30  | MPET_L_STATUS    | R    | 0h    | Indicates status of inductance measurement<br><br>0h = Measurement of motor inductance during MPET routine is not completed if inductance measurement is initiated during MPET<br>1h = Measurement of motor inductance during MPET routine is completed                                                                         |
| 29  | MPET_KE_STATUS   | R    | 0h    | Indicates status of BEMF constant measurement<br><br>0h = Measurement of motor BEMF constant during MPET routine is not completed if BEMF constant measurement is initiated during MPET<br>1h = Measurement of motor BEMF constant during MPET routine is completed                                                             |
| 28  | MPET_MECH_STATUS | R    | 0h    | Indicates status of mechanical parameter measurement<br><br>0h = Auto Calculation of Speed loop Kp, Ki values during MPET routine is not completed if mechanical parameters measurement(speed loop kp,ki values) is initiated during MPET<br>1h = Auto Calculation of Speed loop Kp, Ki values during MPET routine is completed |

**Table 8-10. ALGO\_STATUS\_MPET Register Field Descriptions (continued)**

| Bit   | Field         | Type | Reset | Description                                                                                                                               |
|-------|---------------|------|-------|-------------------------------------------------------------------------------------------------------------------------------------------|
| 27-24 | MPET_PWM_FREQ | R    | 0h    | 4-bit value indicating MPET recommended PWM switching frequency based on electrical time constant. Follows same enum list as PWM_FREQ_OUT |
| 23-0  | RESERVED      | R    | 0h    | Reserved                                                                                                                                  |

### 8.3 Device\_Control Registers

[Table 8-11](#) lists the memory-mapped registers for the Device\_Control registers. All register offset addresses not listed in [Table 8-11](#) should be considered as reserved locations and the register contents should not be modified.

**Table 8-11. DEVICE\_CONTROL Registers**

| Offset | Acronym    | Register Name           | Section                       |
|--------|------------|-------------------------|-------------------------------|
| EAh    | ALGO_CTRL1 | Device Control Register | <a href="#">Section 8.3.1</a> |

Complex bit access types are encoded to fit into small table cells. [Table 8-12](#) shows the codes that are used for access types in this section.

**Table 8-12. Device\_Control Access Type Codes**

| Access Type            | Code | Description                            |
|------------------------|------|----------------------------------------|
| Read Type              |      |                                        |
| R                      | R    | Read                                   |
| Write Type             |      |                                        |
| W                      | W    | Write                                  |
| Reset or Default Value |      |                                        |
| -n                     |      | Value after reset or the default value |

### 8.3.1 ALGO\_CTRL1 Register (Offset = EAh) [Reset = 00000000h]

ALGO\_CTRL1 is shown in [Figure 8-7](#) and described in [Table 8-13](#).

Return to the [Summary Table](#).

Control settings

**Figure 8-7. ALGO\_CTRL1 Register**

| 31                      | 30          | 29      | 28                  | 27                      | 26              | 25      | 24       |
|-------------------------|-------------|---------|---------------------|-------------------------|-----------------|---------|----------|
| EEPROM_WRT              | EEPROM_READ | CLR_FLT | CLR_FLT_RETRY_COUNT | EEPROM_WRITE_ACCESS_KEY |                 |         |          |
| R/W-0h                  | R/W-0h      | W-0h    | W-0h                | W-0h                    |                 |         |          |
| 23                      | 22          | 21      | 20                  | 19                      | 18              | 17      | 16       |
| EEPROM_WRITE_ACCESS_KEY |             |         |                     | FORCED_ALIGN_ANGLE      |                 |         |          |
| W-0h                    |             |         |                     | W-0h                    |                 |         |          |
| 15                      | 14          | 13      | 12                  | 11                      | 10              | 9       | 8        |
| FORCED_ALIGN_ANGLE      |             |         |                     |                         | WATCHDOG_TICKLE | STL_CMD | STL_KEY  |
| W-0h                    |             |         |                     |                         | R/W-0h          | R/W-0h  | R/W-0h   |
| 7                       | 6           | 5       | 4                   | 3                       | 2               | 1       | 0        |
| STL_KEY                 |             |         |                     |                         |                 |         | RESERVED |
| R/W-0h                  |             |         |                     |                         |                 |         | R-0h     |

**Table 8-13. ALGO\_CTRL1 Register Field Descriptions**

| Bit   | Field                   | Type | Reset | Description                                                                                                                                                                                                                                                                                                                                                                                     |
|-------|-------------------------|------|-------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| 31    | EEPROM_WRT              | R/W  | 0h    | Write the configuration from RAM/shadow to EEPROM                                                                                                                                                                                                                                                                                                                                               |
| 30    | EEPROM_READ             | R/W  | 0h    | Read the default configuration from EEPROM to RAM/shadow                                                                                                                                                                                                                                                                                                                                        |
| 29    | CLR_FLT                 | W    | 0h    | Clears all faults                                                                                                                                                                                                                                                                                                                                                                               |
| 28    | CLR_FLT_RETRY_COUNT     | W    | 0h    | Clears automatic fault retry count                                                                                                                                                                                                                                                                                                                                                              |
| 27-20 | EEPROM_WRITE_ACCESS_KEY | W    | 0h    | EEPROM write access key (0xA5)                                                                                                                                                                                                                                                                                                                                                                  |
| 19-11 | FORCED_ALIGN_ANGLE      | W    | 0h    | 9-bit value (in degrees) used during forced align state (applicable when FORCE_ALIGN_EN = 0x1) For example if FORCED_ALIGN_ANGLE value is 225 degrees then angle applied during Forced Align will be 225 degrees, similarly if FORCED_ALIGN_ANGLE value is 395 degrees then angle applied during Forced Align will be 395%360 which is 35 degrees Angle applied = (FORCED_ALIGN_ANGLE % 360)deg |
| 10    | WATCHDOG_TICKLE         | R/W  | 0h    | RAM bit to tickle watchdog in I2C mode. 0x1 should be written to this bit by external controller every EXT_WDT_CFG. Device will reset this bit to 0x0.                                                                                                                                                                                                                                          |
| 9     | STL_CMD                 | R/W  | 0h    | Command to initiate self test (applicable to MCF8315DUL only)                                                                                                                                                                                                                                                                                                                                   |
| 8-1   | STL_KEY                 | R/W  | 0h    | Key(0xBE) to initiate self test on demand (applicable to MCF8315DUL only)                                                                                                                                                                                                                                                                                                                       |
| 0     | RESERVED                | R    | 0h    | Reserved                                                                                                                                                                                                                                                                                                                                                                                        |

## 8.4 Algorithm\_Control Registers

[Table 8-14](#) lists the memory-mapped registers for the Algorithm\_Control registers. All register offset addresses not listed in [Table 8-14](#) should be considered as reserved locations and the register contents should not be modified.

**Table 8-14. ALGORITHM\_CONTROL Registers**

| Offset | Acronym         | Register Name                    | Section                       |
|--------|-----------------|----------------------------------|-------------------------------|
| ECh    | ALGO_DEBUG1     | Algorithm Control Register       | <a href="#">Section 8.4.1</a> |
| EEh    | ALGO_DEBUG2     | Algorithm Control Register       | <a href="#">Section 8.4.2</a> |
| F0h    | CURRENT_PI      | Current PI Controller used       | <a href="#">Section 8.4.3</a> |
| F2h    | SPEED_PI        | Speed PI controller used         | <a href="#">Section 8.4.4</a> |
| F4h    | DAC_1           | DAC1 Control Register            | <a href="#">Section 8.4.5</a> |
| F6h    | DAC_2           | DAC2 Control Register            | <a href="#">Section 8.4.6</a> |
| F8h    | EEPROM_SECURITY | EEPROM Security Control Register | <a href="#">Section 8.4.7</a> |

Complex bit access types are encoded to fit into small table cells. [Table 8-15](#) shows the codes that are used for access types in this section.

**Table 8-15. Algorithm\_Control Access Type Codes**

| Access Type            | Code | Description                            |
|------------------------|------|----------------------------------------|
| Read Type              |      |                                        |
| R                      | R    | Read                                   |
| Write Type             |      |                                        |
| W                      | W    | Write                                  |
| Reset or Default Value |      |                                        |
| -n                     |      | Value after reset or the default value |

### 8.4.1 ALGO\_DEBUG1 Register (Offset = ECh) [Reset = 00000000h]

ALGO\_DEBUG1 is shown in [Figure 8-8](#) and described in [Table 8-16](#).

Return to the [Summary Table](#).

Algorithm control register for debug

**Figure 8-8. ALGO\_DEBUG1 Register**

|                    |                |                           |              |              |                           |          |    |
|--------------------|----------------|---------------------------|--------------|--------------|---------------------------|----------|----|
| 31                 | 30             | 29                        | 28           | 27           | 26                        | 25       | 24 |
| OVERRIDE           |                | DIGITAL_SPEED_CTRL        |              |              |                           |          |    |
| W-0h               |                | W-0h                      |              |              |                           |          |    |
| 23                 | 22             | 21                        | 20           | 19           | 18                        | 17       | 16 |
| DIGITAL_SPEED_CTRL |                |                           |              |              |                           |          |    |
| W-0h               |                |                           |              |              |                           |          |    |
| 15                 | 14             | 13                        | 12           | 11           | 10                        | 9        | 8  |
| CLOSED_LOOP_DIS    | FORCE_ALIGN_EN | FORCE_SLOW_FIRST_CYCLE_EN | FORCE_IPD_EN | FORCE_ISD_EN | FORCE_ALIGN_ANGLE_SRC_SEL | RESERVED |    |
| W-0h               | W-0h           | W-0h                      | W-0h         | W-0h         | W-0h                      | R-0h     |    |
| 7                  | 6              | 5                         | 4            | 3            | 2                         | 1        | 0  |
| RESERVED           |                |                           |              |              |                           |          |    |
| R-0h               |                |                           |              |              |                           |          |    |

**Table 8-16. ALGO\_DEBUG1 Register Field Descriptions**

| Bit   | Field                     | Type | Reset | Description                                                                                                                                                                                                                                                     |
|-------|---------------------------|------|-------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| 31    | OVERRIDE                  | W    | 0h    | Use to control the reference input mode. If OVERRIDE = 0x1, speed command can be written by the user through I2C interface irrespective of SPEED_MODE setting.<br><br>0h = SPEED_CMD using Analog/PWM/Frequency mode<br>1h = SPEED_CMD using DIGITAL_SPEED_CTRL |
| 30-16 | DIGITAL_SPEED_CTRL        | W    | 0h    | Reference input when OVERRIDE is set 0x1 or SPEED_MODE is set to 0x2. Reference input = (DIGITAL_SPEED_CTRL/32768 *100)%                                                                                                                                        |
| 15    | CLOSED_LOOP_DIS           | W    | 0h    | Use to disable closed loop operation<br><br>0h = Enable closed Loop<br>1h = Disable closed loop, motor commutation in open loop                                                                                                                                 |
| 14    | FORCE_ALIGN_EN            | W    | 0h    | Enable force align state<br><br>0h = Disable force align state<br>1h = Enable force align state, device stays in align state if MTR_STARTUP is selected as ALIGN or DOUBLE ALIGN                                                                                |
| 13    | FORCE_SLOW_FIRST_CYCLE_EN | W    | 0h    | Enable force slow first cycle<br><br>0h = Disable force slow first Cycle state<br>1h = Enable force slow first cycle state, device stays in slow first cycle state if MTR_STARTUP is selected as SLOW FIRST CYCLE                                               |
| 12    | FORCE_IPD_EN              | W    | 0h    | Enable force IPD<br><br>0h = Disable force IPD state<br>1h = Enable force IPD state, device stays in IPD state if MTR_STARTUP is selected as IPD                                                                                                                |

**Table 8-16. ALGO\_DEBUG1 Register Field Descriptions (continued)**

| Bit | Field                     | Type | Reset | Description                                                                                                                                  |
|-----|---------------------------|------|-------|----------------------------------------------------------------------------------------------------------------------------------------------|
| 11  | FORCE_ISD_EN              | W    | 0h    | Enable force ISD<br><br>0h = Disable force ISD state<br>1h = Enable force ISD state, device stays in ISD state if ISD_EN is set              |
| 10  | FORCE_ALIGN_ANGLE_SRC_SEL | W    | 0h    | Select force align angle source<br><br>0h = Force align angle defined by ALIGN_ANGLE<br>1h = Force align angle defined by FORCED_ALIGN_ANGLE |
| 9-0 | RESERVED                  | R    | 0h    | Reserved                                                                                                                                     |

### 8.4.2 ALGO\_DEBUG2 Register (Offset = EEh) [Reset = 00000000h]

ALGO\_DEBUG2 is shown in [Figure 8-9](#) and described in [Table 8-17](#).

Return to the [Summary Table](#).

Algorithm control register for debug

**Figure 8-9. ALGO\_DEBUG2 Register**

|                           |                               |    |        |                           |                  |                           |                   |
|---------------------------|-------------------------------|----|--------|---------------------------|------------------|---------------------------|-------------------|
| 31                        | 30                            | 29 | 28     | 27                        | 26               | 25                        | 24                |
| RESERVED                  | FORCE_RECIRCULATE_STOP_SECTOR |    |        | FORCE_RECIRCULATE_STOP_EN | CURRENT_LOOP_DIS | FORCE_VD_CURRENT_LOOP_DIS |                   |
| R-0h                      | W-0h                          |    |        | W-0h                      | W-0h             | W-0h                      |                   |
| 23                        | 22                            | 21 | 20     | 19                        | 18               | 17                        | 16                |
| FORCE_VD_CURRENT_LOOP_DIS |                               |    |        |                           |                  |                           |                   |
| W-0h                      |                               |    |        |                           |                  |                           |                   |
| 15                        | 14                            | 13 | 12     | 11                        | 10               | 9                         | 8                 |
| FORCE_VQ_CURRENT_LOOP_DIS |                               |    |        |                           |                  |                           |                   |
| W-0h                      |                               |    |        |                           |                  |                           |                   |
| 7                         | 6                             | 5  | 4      | 3                         | 2                | 1                         | 0                 |
| FORCE_VQ_CURRENT_LOOP_DIS | MPET_CMD                      |    | MPET_R | MPET_L                    | MPET_KE          | MPET_MECH                 | MPET_WRITE_SHADOW |
| W-0h                      | W-0h                          |    | W-0h   | W-0h                      | W-0h             | W-0h                      | W-0h              |

**Table 8-17. ALGO\_DEBUG2 Register Field Descriptions**

| Bit   | Field                         | Type | Reset | Description                                                                                                                                                                                                                                                                              |
|-------|-------------------------------|------|-------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| 31    | RESERVED                      | R    | 0h    | Reserved                                                                                                                                                                                                                                                                                 |
| 30-28 | FORCE_RECIRCULATE_STOP_SECTOR | W    | 0h    | Select the specific sector for recirculation stop if FORCE_RECIRCULATE_STOP_EN is set to 0x1<br>0h = The last sector before stop condition<br>1h = Sector1<br>2h = Sector2<br>3h = Sector3<br>4h = Sector4<br>5h = Sector5<br>6h = Sector6<br>7h = The last sector before stop condition |
| 27    | FORCE_RECIRCULATE_STOP_EN     | W    | 0h    | Enable force recirculate stop<br>0h = Enable force recirculate stop<br>1h = Disable force recirculate stop                                                                                                                                                                               |
| 26    | CURRENT_LOOP_DIS              | W    | 0h    | Use to control the FORCE_VD_CURRENT_LOOP_DIS and FORCE_VQ_CURRENT_LOOP_DIS. If CURRENT_LOOP_DIS = 0x1, Current loop and speed loop are disabled<br>0h = Enable current loop<br>1h = Disable current loop                                                                                 |

**Table 8-17. ALGO\_DEBUG2 Register Field Descriptions (continued)**

| Bit   | Field                     | Type | Reset | Description                                                                                                                                                                                                                                                                                                                                             |
|-------|---------------------------|------|-------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| 25-16 | FORCE_VD_CURRENT_LOOP_DIS | W    | 0h    | Sets Vd when current loop speed loop are disabled If CURRENT_LOOP_DIS = 0b1, then Vd is control using FORCE_VD_CURRENT_LOOP_DIS<br>$mdRef = (FORCE\_VD\_CURRENT\_LOOP\_DIS / 500)$<br>if FORCE_VD_CURRENT_LOOP_DIS < 500<br>$(FORCE\_VD\_CURRENT\_LOOP\_DIS - 1024) / 500$ if<br>FORCE_VD_CURRENT_LOOP_DIS > 512 Valid values: 0 to 500 and 512 to 1000 |
| 15-6  | FORCE_VQ_CURRENT_LOOP_DIS | W    | 0h    | Sets Vq when current loop speed loop are disabled If CURRENT_LOOP_DIS = 0b1, then Vq is control using FORCE_VQ_CURRENT_LOOP_DIS<br>$mqRef = (FORCE\_VQ\_CURRENT\_LOOP\_DIS / 500)$<br>if FORCE_VQ_CURRENT_LOOP_DIS < 500<br>$(FORCE\_VQ\_CURRENT\_LOOP\_DIS - 1024) / 500$ if<br>FORCE_VQ_CURRENT_LOOP_DIS > 512 Valid values: 0 to 500 and 512 to 1000 |
| 5     | MPET_CMD                  | W    | 0h    | Initiates motor parameter measurement (MPET) routine when set to 0x1                                                                                                                                                                                                                                                                                    |
| 4     | MPET_R                    | W    | 0h    | Enables motor resistance measurement during motor parameter measurement routine<br><br>0h = Disables Motor Resistance measurement during motor parameter measurement routine<br>1h = Enable Motor Resistance measurement during motor parameter measurement routine                                                                                     |
| 3     | MPET_L                    | W    | 0h    | Enables motor inductance measurement during motor parameter measurement routine<br><br>0h = Disables Motor Inductance measurement during motor parameter measurement routine<br>1h = Enable Motor Inductance measurement during motor parameter measurement routine                                                                                     |
| 2     | MPET_KE                   | W    | 0h    | Enables motor BEMF constant measurement during motor parameter measurement routine<br><br>0h = Disables Motor BEMF constant measurement during motor parameter measurement routine<br>1h = Enable Motor BEMF constant measurement during motor parameter measurement routine                                                                            |
| 1     | MPET_MECH                 | W    | 0h    | Enables motor mechanical parameter measurement during motor parameter measurement routine<br><br>0h = Disables Motor mechanical parameter measurement during motor parameter measurement routine<br>1h = Enable Motor mechanical parameter measurement during motor parameter measurement routine                                                       |
| 0     | MPET_WRITE_SHADOW         | W    | 0h    | Write measured parameters to shadow register when set to 0x1                                                                                                                                                                                                                                                                                            |

### 8.4.3 CURRENT\_PI Register (Offset = F0h) [Reset = 00000000h]

CURRENT\_PI is shown in [Figure 8-10](#) and described in [Table 8-18](#).

Return to the [Summary Table](#).

Current PI controller used

**Figure 8-10. CURRENT\_PI Register**

| 31              | 30 | 29 | 28 | 27 | 26 | 25 | 24 | 23 | 22 | 21 | 20 | 19 | 18 | 17 | 16 | 15              | 14 | 13 | 12 | 11 | 10 | 9 | 8 | 7 | 6 | 5 | 4 | 3 | 2 | 1 | 0 |
|-----------------|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|-----------------|----|----|----|----|----|---|---|---|---|---|---|---|---|---|---|
| CURRENT_LOOP_KI |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    | CURRENT_LOOP_KP |    |    |    |    |    |   |   |   |   |   |   |   |   |   |   |
| R-0h            |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    | R-0h            |    |    |    |    |    |   |   |   |   |   |   |   |   |   |   |

**Table 8-18. CURRENT\_PI Register Field Descriptions**

| Bit   | Field           | Type | Reset | Description                                                   |
|-------|-----------------|------|-------|---------------------------------------------------------------|
| 31-16 | CURRENT_LOOP_KI | R    | 0h    | 10 bit value for current loop Ki Same Scaling as CURR_LOOP_KI |
| 15-0  | CURRENT_LOOP_KP | R    | 0h    | 10 bit value for current loop Kp Same Scaling as CURR_LOOP_KP |

#### 8.4.4 SPEED\_PI Register (Offset = F2h) [Reset = 00000000h]

SPEED\_PI is shown in [Figure 8-11](#) and described in [Table 8-19](#).

Return to the [Summary Table](#).

Speed PI controller used

**Figure 8-11. SPEED\_PI Register**

|               |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |               |    |    |    |    |    |   |   |   |   |   |   |   |   |   |   |
|---------------|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|---------------|----|----|----|----|----|---|---|---|---|---|---|---|---|---|---|
| 31            | 30 | 29 | 28 | 27 | 26 | 25 | 24 | 23 | 22 | 21 | 20 | 19 | 18 | 17 | 16 | 15            | 14 | 13 | 12 | 11 | 10 | 9 | 8 | 7 | 6 | 5 | 4 | 3 | 2 | 1 | 0 |
| SPEED_LOOP_KI |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    | SPEED_LOOP_KP |    |    |    |    |    |   |   |   |   |   |   |   |   |   |   |
| R-0h          |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    | R-0h          |    |    |    |    |    |   |   |   |   |   |   |   |   |   |   |

**Table 8-19. SPEED\_PI Register Field Descriptions**

| Bit   | Field         | Type | Reset | Description                                                |
|-------|---------------|------|-------|------------------------------------------------------------|
| 31-16 | SPEED_LOOP_KI | R    | 0h    | 10 bit value for Speed loop Ki Same Scaling as SPD_LOOP_KI |
| 15-0  | SPEED_LOOP_KP | R    | 0h    | 10 bit value for Speed loop Kp Same Scaling as SPD_LOOP_KP |

### 8.4.5 DAC\_1 Register (Offset = F4h) [Reset = 00110000h]

DAC\_1 is shown in [Figure 8-12](#) and described in [Table 8-20](#).

Return to the [Summary Table](#).

DAC1 Control Register

**Figure 8-12. DAC\_1 Register**

|                  |    |    |                      |                  |    |                 |    |
|------------------|----|----|----------------------|------------------|----|-----------------|----|
| 31               | 30 | 29 | 28                   | 27               | 26 | 25              | 24 |
| RESERVED         |    |    |                      |                  |    |                 |    |
| R-0h             |    |    |                      |                  |    |                 |    |
| 23               | 22 | 21 | 20                   | 19               | 18 | 17              | 16 |
| RESERVED         |    |    | DACOUT1_ENUM_SCALING |                  |    | DACOUT1_SCALING |    |
| R-0h             |    |    | W-8h                 |                  |    | W-8h            |    |
| 15               | 14 | 13 | 12                   | 11               | 10 | 9               | 8  |
| DACOUT1_SCALING  |    |    | DACOUT1_UNIPOLAR     | DACOUT1_VAR_ADDR |    |                 |    |
| W-8h             |    |    | W-0h                 | R/W-0h           |    |                 |    |
| 7                | 6  | 5  | 4                    | 3                | 2  | 1               | 0  |
| DACOUT1_VAR_ADDR |    |    |                      |                  |    |                 |    |
| R/W-0h           |    |    |                      |                  |    |                 |    |

**Table 8-20. DAC\_1 Register Field Descriptions**

| Bit   | Field                | Type | Reset | Description                                                                                                                                                                                                                               |
|-------|----------------------|------|-------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| 31-21 | RESERVED             | R    | 0h    | Reserved                                                                                                                                                                                                                                  |
| 20-17 | DACOUT1_ENUM_SCALING | W    | 8h    | Multiplication Factor for DACOUT1 Algorithm Variable extracted from the address contained in DACOUT1_VAR_ADDR multiplied with $2^{\text{DACOUT1\_ENUM\_SCALING}}$ . DACOUT1_ENUM_SCALING comes into effect only if DACOUT1_SCALING is 0x0 |

**Table 8-20. DAC\_1 Register Field Descriptions (continued)**

| Bit   | Field            | Type | Reset | Description                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                             |
|-------|------------------|------|-------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| 16-13 | DACOUT1_SCALING  | W    | 8h    | <p>Scaling factor for DACOUT1 Algorithm Variable extracted from the address contained in DACOUT1_VAR_ADDR scaled with DACOUT1_SCALING. Actual voltage depends on DACOUT1_UNIPOLAR. If DACOUT1_UNIPOLAR = 0x1, Actual Value= ((DAC Voltage*Base Value) )/((3* DACOUT1_SCALING)) If DACOUT1_UNIPOLAR = 0x0, Actual Value= (((DAC Voltage-1.5)*Base Value) )/((1.5* DACOUT1_SCALING)) Base Current is 6.25/8 A, Base Speed is MAX_SPEED in Hz, Base Voltage for DC Bus Voltage is 60V, Base voltage for phase voltages is 60V/Sqrt(3) Note: For currents recommended DACOUT1_SCALING is 2/8, for Voltages 8/8 and for Speed 7/8</p> <p>0h = Treated s Enum with max value being 31</p> <p>1h = 1 / 8</p> <p>2h = 2 / 8</p> <p>3h = 3 / 8</p> <p>4h = 4 / 8</p> <p>5h = 5 / 8</p> <p>6h = 6 / 8</p> <p>7h = 7 / 8</p> <p>8h = 8 / 8</p> <p>9h = 9 / 8</p> <p>Ah = 10 / 8</p> <p>Bh = 11 / 8</p> <p>Ch = 12 / 8</p> <p>Dh = 13 / 8</p> <p>Eh = 14 / 8</p> <p>Fh = 15 / 8</p> |
| 12    | DACOUT1_UNIPOLAR | W    | 0h    | <p>Configures output of DACOUT1 If DACOUT1_UNIPOLAR = 0x1, Actual Value= ((DAC1 Voltage*Base Value) )/((3* DACOUT1_SCALING)) If DACOUT1_UNIPOLAR = 0x0, Actual Value= (((DAC2 Voltage-1.5)*Base Value) )/((1.5* DACOUT1_SCALING)) Base Current is 6.25/8 A, Base Speed is MAX_SPEED in Hz, Base Voltage for DC Bus Voltage is 60V, Base voltage for phase voltages is 60V/Sqrt(3)</p> <p>0h = Bipolar (Offset of 1.5 V)</p> <p>1h = Unipolar (No Offset)</p>                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                            |
| 11-0  | DACOUT1_VAR_ADDR | R/W  | 0h    | 12-bit address of variable to be monitored on DACOUT1                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                   |

### 8.4.6 DAC\_2 Register (Offset = F6h) [Reset = 00XX0000h]

DAC\_2 is shown in [Figure 8-13](#) and described in [Table 8-21](#).

Return to the [Summary Table](#).

DAC2 Control Register

**Figure 8-13. DAC\_2 Register**

|                     |                      |                  |    |    |                 |    |    |
|---------------------|----------------------|------------------|----|----|-----------------|----|----|
| 31                  | 30                   | 29               | 28 | 27 | 26              | 25 | 24 |
| RESERVED            |                      |                  |    |    |                 |    |    |
| R-0h                |                      |                  |    |    |                 |    |    |
| 23                  | 22                   | 21               | 20 | 19 | 18              | 17 | 16 |
| RESERVED            | DACOUT2_ENUM_SCALING |                  |    |    | DACOUT2_SCALING |    |    |
| R-0h                | W-Xh                 |                  |    |    | W-8h            |    |    |
| 15                  | 14                   | 13               | 12 | 11 | 10              | 9  | 8  |
| DACOUT2_SC<br>ALING | DACOUT2_UNI<br>POLAR | DACOUT2_VAR_ADDR |    |    |                 |    |    |
| W-8h                | W-0h                 | R/W-0h           |    |    |                 |    |    |
| 7                   | 6                    | 5                | 4  | 3  | 2               | 1  | 0  |
| DACOUT2_VAR_ADDR    |                      |                  |    |    |                 |    |    |
| R/W-0h              |                      |                  |    |    |                 |    |    |

**Table 8-21. DAC\_2 Register Field Descriptions**

| Bit   | Field                | Type | Reset | Description                                                                                                                                                                                                                               |
|-------|----------------------|------|-------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| 31-23 | RESERVED             | R    | 0h    | Reserved                                                                                                                                                                                                                                  |
| 22-19 | DACOUT2_ENUM_SCALING | W    | Xh    | Multiplication Factor for DACOUT2 Algorithm Variable extracted from the address contained in DACOUT2_VAR_ADDR multiplied with $2^{\text{DACOUT2\_ENUM\_SCALING}}$ . DACOUT2_ENUM_SCALING comes into effect only if DACOUT2_SCALING is 0x0 |

**Table 8-21. DAC\_2 Register Field Descriptions (continued)**

| Bit   | Field            | Type | Reset | Description                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                           |
|-------|------------------|------|-------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| 18-15 | DACOUT2_SCALING  | W    | 8h    | <p>Scaling factor for DACOUT2 Algorithm Variable extracted from the address contained in DACOUT2_VAR_ADDR scaled with DACOUT2_SCALING. Actual voltage depends on DACOUT2_UNIPOLAR. If DACOUT2_UNIPOLAR = 0x1, Actual Value= ((DAC2 Voltage*Base Value) )/((3* DACOUT2_SCALING)) If DACOUT2_UNIPOLAR = 0x0, Actual Value= (((DAC2 Voltage-1.5)*Base Value) )/((1.5* DACOUT2_SCALING)) Base Current is 6.25/8 A, Base Speed is MAX_SPEED in Hz, Base Voltage for DC Bus Voltage is 60V, Base voltage for phase voltages is 60V/Sqrt(3) Note: For currents recommended DACOUT1_SCALING is 2/8, for Voltages 8/8 and for Speed information 7/8</p> <p>0h = Treated s Enum with max value being 31</p> <p>1h = 1 / 8</p> <p>2h = 2 / 8</p> <p>3h = 3 / 8</p> <p>4h = 4 / 8</p> <p>5h = 5 / 8</p> <p>6h = 6 / 8</p> <p>7h = 7 / 8</p> <p>8h = 8 / 8</p> <p>9h = 9 / 8</p> <p>Ah = 10 / 8</p> <p>Bh = 11 / 8</p> <p>Ch = 12 / 8</p> <p>Dh = 13 / 8</p> <p>Eh = 14 / 8</p> <p>Fh = 15 / 8</p> |
| 14    | DACOUT2_UNIPOLAR | W    | 0h    | <p>Configures output of DACOUT2 If DACOUT2_UNIPOLAR = 0x1, Actual Value= ((DAC2 Voltage*Base Value) )/((3* DACOUT2_SCALING)) If DACOUT2_UNIPOLAR = 0x0, Actual Value= (((DAC2 Voltage-1.5)*Base Value) )/((1.5* DACOUT2_SCALING)) Base Current is 6.25/8 A, Base Speed is MAX_SPEED in Hz, Base Voltage for DC Bus Voltage is 60V, Base voltage for phase voltages is 60V/Sqrt(3) Note: For currents recommended DACOUT1_SCALING is 2/8, for Voltages 8/8 and for Speed information 7/8</p> <p>0h = Bipolar (Offset of 1.5 V)</p> <p>1h = Unipolar (No Offset)</p>                                                                                                                                                                                                                                                                                                                                                                                                                    |
| 13-0  | DACOUT2_VAR_ADDR | R/W  | 0h    | 14-bit address of variable to be monitored on DACOUT2                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                 |

### 8.4.7 EEPROM\_SECURITY Register (Offset = F8h) [Reset = 0000h]

EEPROM\_SECURITY is shown in [Figure 8-14](#) and described in [Table 8-22](#).

Return to the [Summary Table](#).

EEPROM Security Control Register

**Figure 8-14. EEPROM\_SECURITY Register**

|                 |    |                 |    |    |    |   |   |
|-----------------|----|-----------------|----|----|----|---|---|
| 15              | 14 | 13              | 12 | 11 | 10 | 9 | 8 |
| RESERVED        |    | USER_EEPROM_KEY |    |    |    |   |   |
| R-0h            |    | R/W-0h          |    |    |    |   |   |
| 7               | 6  | 5               | 4  | 3  | 2  | 1 | 0 |
| USER_EEPROM_KEY |    |                 |    |    |    |   |   |
| R/W-0h          |    |                 |    |    |    |   |   |

**Table 8-22. EEPROM\_SECURITY Register Field Descriptions**

| Bit  | Field           | Type | Reset | Description                                                                                                           |
|------|-----------------|------|-------|-----------------------------------------------------------------------------------------------------------------------|
| 15   | RESERVED        | R    | 0h    | Reserved                                                                                                              |
| 14-0 | USER_EEPROM_KEY | R/W  | 0h    | User input key to unlock EEPROM for read/writes. Value in EEPROM_LOCK_KEY should be written here for unlocking EEPROM |

## 8.5 Algorithm\_Variables Registers

[Table 8-23](#) lists the memory-mapped registers for the Algorithm\_Variables registers. All register offset addresses not listed in [Table 8-23](#) should be considered as reserved locations and the register contents should not be modified.

**Table 8-23. ALGORITHM\_VARIABLES Registers**

| Offset | Acronym               | Register Name                        | Section                        |
|--------|-----------------------|--------------------------------------|--------------------------------|
| 18Eh   | ALGORITHM_STATE       | Current Algorithm State Register     | <a href="#">Section 8.5.1</a>  |
| 194h   | FG_SPEED_FDBK         | FG Speed Feedback Register           | <a href="#">Section 8.5.2</a>  |
| 400h   | VBETA                 | VBETA Voltage Register               | <a href="#">Section 8.5.3</a>  |
| 40Ch   | BUS_CURRENT           | Calculated DC Bus Current Register   | <a href="#">Section 8.5.4</a>  |
| 444h   | PHASE_CURRENT_A       | Measured Current on Phase A Register | <a href="#">Section 8.5.5</a>  |
| 446h   | PHASE_CURRENT_B       | Measured Current on Phase B Register | <a href="#">Section 8.5.6</a>  |
| 448h   | PHASE_CURRENT_C       | Measured Current on Phase C Register | <a href="#">Section 8.5.7</a>  |
| 46Ch   | CSA_GAIN_FEEDBACK     | CSA Gain Register                    | <a href="#">Section 8.5.8</a>  |
| 477h   | VOLTAGE_GAIN_FEEDBACK | Voltage Gain Register                | <a href="#">Section 8.5.9</a>  |
| 47Ch   | VM_VOLTAGE            | VM Voltage Register                  | <a href="#">Section 8.5.10</a> |
| 484h   | PHASE_VOLTAGE_VA      | Phase A Voltage Register             | <a href="#">Section 8.5.11</a> |
| 486h   | PHASE_VOLTAGE_VB      | Phase B Voltage Register             | <a href="#">Section 8.5.12</a> |
| 488h   | PHASE_VOLTAGE_VC      | Phase C Voltage Register             | <a href="#">Section 8.5.13</a> |
| 4BCh   | SIN_COMMUTATION_ANGLE | Sine of Commutation Angle            | <a href="#">Section 8.5.14</a> |
| 4BEh   | COS_COMMUTATION_ANGLE | Cosine of Commutation Angle          | <a href="#">Section 8.5.15</a> |
| 4DCh   | IALPHA                | IALPHA Current Register              | <a href="#">Section 8.5.16</a> |
| 4DEh   | IBETA                 | IBETA Current Register               | <a href="#">Section 8.5.17</a> |
| 4E0h   | VALPHA                | VALPHA Voltage Register              | <a href="#">Section 8.5.18</a> |
| 4ECh   | ID                    | Measured d-axis Current Register     | <a href="#">Section 8.5.19</a> |
| 4EEh   | IQ                    | Measured q-axis Current Register     | <a href="#">Section 8.5.20</a> |
| 4F0h   | VD                    | VD Voltage Register                  | <a href="#">Section 8.5.21</a> |

**Table 8-23. ALGORITHM\_VARIABLES Registers (continued)**

| Offset | Acronym               | Register Name                       | Section                        |
|--------|-----------------------|-------------------------------------|--------------------------------|
| 4F2h   | VQ                    | VQ Voltage Register                 | <a href="#">Section 8.5.22</a> |
| 52Ah   | IQ_REF_ROTOR_ALIGN    | Align Current Reference             | <a href="#">Section 8.5.23</a> |
| 540h   | SPEED_REF_OPEN_LOOP   | Open Loop Speed Register            | <a href="#">Section 8.5.24</a> |
| 550h   | IQ_REF_OPEN_LOOP      | Open Loop Current Reference         | <a href="#">Section 8.5.25</a> |
| 5D2h   | SPEED_REF_CLOSED_LOOP | Speed Reference Register            | <a href="#">Section 8.5.26</a> |
| 612h   | ID_REF_CLOSED_LOOP    | Reference for Current Loop Register | <a href="#">Section 8.5.27</a> |
| 614h   | IQ_REF_CLOSED_LOOP    | Reference for Current Loop Register | <a href="#">Section 8.5.28</a> |
| 6AEh   | ISD_STATE             | ISD State Register                  | <a href="#">Section 8.5.29</a> |
| 6B8h   | ISD_SPEED             | ISD Speed Register                  | <a href="#">Section 8.5.30</a> |
| 6EAh   | IPD_STATE             | IPD State Register                  | <a href="#">Section 8.5.31</a> |
| 72Eh   | IPD_ANGLE             | Calculated IPD Angle Register       | <a href="#">Section 8.5.32</a> |
| 772h   | ED                    | Estimated BEMF EQ Register          | <a href="#">Section 8.5.33</a> |
| 774h   | EQ                    | Estimated BEMF ED Register          | <a href="#">Section 8.5.34</a> |
| 782h   | SPEED_FDBK            | Speed Feedback Register             | <a href="#">Section 8.5.35</a> |
| 786h   | THETA_EST             | Estimated rotor Position Register   | <a href="#">Section 8.5.36</a> |

Complex bit access types are encoded to fit into small table cells. [Table 8-24](#) shows the codes that are used for access types in this section.

**Table 8-24. Algorithm\_Variables Access Type Codes**

| Access Type            | Code | Description                            |
|------------------------|------|----------------------------------------|
| Read Type              |      |                                        |
| R                      | R    | Read                                   |
| Reset or Default Value |      |                                        |
| -n                     |      | Value after reset or the default value |

### 8.5.1 ALGORITHM\_STATE Register (Offset = 18Eh) [Reset = 0000h]

ALGORITHM\_STATE is shown in [Figure 8-15](#) and described in [Table 8-25](#).

Return to the [Summary Table](#).

Current Algorithm State Register

**Figure 8-15. ALGORITHM\_STATE Register**

|                 |    |    |    |    |    |   |   |
|-----------------|----|----|----|----|----|---|---|
| 15              | 14 | 13 | 12 | 11 | 10 | 9 | 8 |
| ALGORITHM_STATE |    |    |    |    |    |   |   |
| R-0h            |    |    |    |    |    |   |   |
| 7               | 6  | 5  | 4  | 3  | 2  | 1 | 0 |
| ALGORITHM_STATE |    |    |    |    |    |   |   |
| R-0h            |    |    |    |    |    |   |   |

**Table 8-25. ALGORITHM\_STATE Register Field Descriptions**

| Bit  | Field           | Type | Reset | Description                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                      |
|------|-----------------|------|-------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| 15-0 | ALGORITHM_STATE | R    | 0h    | 16-bit value indicating current state of device<br><br>0h = MOTOR_IDLE<br>1h = MOTOR_ISD<br>2h = MOTOR_TRISTATE<br>3h = MOTOR_BRAKE_ON_START<br>4h = MOTOR_IPD<br>5h = MOTOR_SLOW_FIRST_CYCLE<br>6h = MOTOR_ALIGN<br>7h = MOTOR_OPEN_LOOP<br>8h = MOTOR_CLOSED_LOOP_UNALIGNED<br>9h = MOTOR_CLOSED_LOOP_ALIGNED<br>Ah = MOTOR_CLOSED_LOOP_ACTIVE BRAKING<br>Bh = MOTOR_SOFT_STOP<br>Ch = MOTOR_RECIRCULATE_STOP<br>Dh = MOTOR_BRAKE_ON_STOP<br>Eh = MOTOR_FAULT<br>Fh = MOTOR_MPET_MOTOR_STOP_CHECK<br>10h = MOTOR_MPET_MOTOR_STOP_WAIT<br>11h = MOTOR_MPET_MOTOR_BRAKE<br>12h = MOTOR_MPET_ALGORITHM_PARAMETERS_INIT<br>13h = MOTOR_MPET_RL_MEASURE<br>14h = MOTOR_MPET_KE_MEASURE<br>15h = MOTOR_MPET_STALL_CURRENT_MEASURE<br>16h = MOTOR_MPET_TORQUE_MODE<br>17h = MOTOR_MPET_DONE<br>18h = MOTOR_MPET_FAULT |

### 8.5.2 FG\_SPEED\_FDBK Register (Offset = 194h) [Reset = 00000000h]

FG\_SPEED\_FDBK is shown in [Figure 8-16](#) and described in [Table 8-26](#).

Return to the [Summary Table](#).

Speed Feedback from FG

**Figure 8-16. FG\_SPEED\_FDBK Register**

|               |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |   |   |   |   |   |   |   |   |   |   |
|---------------|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|---|---|---|---|---|---|---|---|---|---|
| 31            | 30 | 29 | 28 | 27 | 26 | 25 | 24 | 23 | 22 | 21 | 20 | 19 | 18 | 17 | 16 | 15 | 14 | 13 | 12 | 11 | 10 | 9 | 8 | 7 | 6 | 5 | 4 | 3 | 2 | 1 | 0 |
| FG_SPEED_FDBK |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |   |   |   |   |   |   |   |   |   |   |
| R-0h          |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |   |   |   |   |   |   |   |   |   |   |

**Table 8-26. FG\_SPEED\_FDBK Register Field Descriptions**

| Bit  | Field         | Type | Reset | Description                                                                                                                                                                   |
|------|---------------|------|-------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| 31-0 | FG_SPEED_FDBK | R    | 0h    | 32-bit value indicating absolute (unsigned) value of estimated motor speed based on FG Estimated Motor Speed (in Hz) = (FG_SPEED_FDBK / 2 <sup>27</sup> ) * MAX_SPEED (in Hz) |

### 8.5.3 VBETA Register (Offset = 400h) [Reset = 00000000h]

VBETA is shown in [Figure 8-17](#) and described in [Table 8-27](#).

Return to the [Summary Table](#).

VBETA Voltage Register

**Figure 8-17. VBETA Register**

|       |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |   |   |   |   |   |   |   |   |   |   |
|-------|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|---|---|---|---|---|---|---|---|---|---|
| 31    | 30 | 29 | 28 | 27 | 26 | 25 | 24 | 23 | 22 | 21 | 20 | 19 | 18 | 17 | 16 | 15 | 14 | 13 | 12 | 11 | 10 | 9 | 8 | 7 | 6 | 5 | 4 | 3 | 2 | 1 | 0 |
| VBETA |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |   |   |   |   |   |   |   |   |   |   |
| R-0h  |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |   |   |   |   |   |   |   |   |   |   |

**Table 8-27. VBETA Register Field Descriptions**

| Bit  | Field | Type | Reset | Description                                                                                                                                                                             |
|------|-------|------|-------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| 31-0 | VBETA | R    | 0h    | 32-bit signed value indicating applied phase voltage in alpha-beta domain. Negative value represented in two's complement. VBeta (in Volts) = (VBETA / 2 <sup>27</sup> ) * 60 / sqrt(3) |

#### 8.5.4 BUS\_CURRENT Register (Offset = 40Ch) [Reset = 00000000h]

BUS\_CURRENT is shown in [Figure 8-18](#) and described in [Table 8-28](#).

Return to the [Summary Table](#).

Calculated Supply Current Register

**Figure 8-18. BUS\_CURRENT Register**

|             |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |   |   |   |   |   |   |   |   |   |   |
|-------------|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|---|---|---|---|---|---|---|---|---|---|
| 31          | 30 | 29 | 28 | 27 | 26 | 25 | 24 | 23 | 22 | 21 | 20 | 19 | 18 | 17 | 16 | 15 | 14 | 13 | 12 | 11 | 10 | 9 | 8 | 7 | 6 | 5 | 4 | 3 | 2 | 1 | 0 |
| BUS_CURRENT |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |   |   |   |   |   |   |   |   |   |   |
| R-0h        |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |   |   |   |   |   |   |   |   |   |   |

**Table 8-28. BUS\_CURRENT Register Field Descriptions**

| Bit  | Field       | Type | Reset | Description                                                                                                                                                         |
|------|-------------|------|-------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| 31-0 | BUS_CURRENT | R    | 0h    | 32-bit signed value indicating DC bus current. Negative value represented in two's complement. DC bus Current (in Amps) = $(\text{BUS\_CURRENT} / 2^{27}) * 6.25/8$ |

### 8.5.5 PHASE\_CURRENT\_A Register (Offset = 444h) [Reset = 00000000h]

PHASE\_CURRENT\_A is shown in [Figure 8-19](#) and described in [Table 8-29](#).

Return to the [Summary Table](#).

Measured current on Phase A Register

**Figure 8-19. PHASE\_CURRENT\_A Register**

|                 |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |   |   |   |   |   |   |   |   |   |   |
|-----------------|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|---|---|---|---|---|---|---|---|---|---|
| 31              | 30 | 29 | 28 | 27 | 26 | 25 | 24 | 23 | 22 | 21 | 20 | 19 | 18 | 17 | 16 | 15 | 14 | 13 | 12 | 11 | 10 | 9 | 8 | 7 | 6 | 5 | 4 | 3 | 2 | 1 | 0 |
| PHASE_CURRENT_A |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |   |   |   |   |   |   |   |   |   |   |
| R-0h            |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |   |   |   |   |   |   |   |   |   |   |

**Table 8-29. PHASE\_CURRENT\_A Register Field Descriptions**

| Bit  | Field           | Type | Reset | Description                                                                                                                                                                                   |
|------|-----------------|------|-------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| 31-0 | PHASE_CURRENT_A | R    | 0h    | 32-bit signed value indicating measured continuous Phase A current. Negative value represented in two's complement. Phase A current (in Amps) = (PHASE_CURRENT_A / 2 <sup>27</sup> ) * 6.25/8 |

### 8.5.6 PHASE\_CURRENT\_B Register (Offset = 446h) [Reset = 00000000h]

PHASE\_CURRENT\_B is shown in [Figure 8-20](#) and described in [Table 8-30](#).

Return to the [Summary Table](#).

Measured current on Phase B Register

**Figure 8-20. PHASE\_CURRENT\_B Register**

|                 |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |   |   |   |   |   |   |   |   |   |   |
|-----------------|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|---|---|---|---|---|---|---|---|---|---|
| 31              | 30 | 29 | 28 | 27 | 26 | 25 | 24 | 23 | 22 | 21 | 20 | 19 | 18 | 17 | 16 | 15 | 14 | 13 | 12 | 11 | 10 | 9 | 8 | 7 | 6 | 5 | 4 | 3 | 2 | 1 | 0 |
| PHASE_CURRENT_B |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |   |   |   |   |   |   |   |   |   |   |
| R-0h            |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |   |   |   |   |   |   |   |   |   |   |

**Table 8-30. PHASE\_CURRENT\_B Register Field Descriptions**

| Bit  | Field           | Type | Reset | Description                                                                                                                                                                                   |
|------|-----------------|------|-------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| 31-0 | PHASE_CURRENT_B | R    | 0h    | 32-bit signed value indicating measured continuous Phase B current. Negative value represented in two's complement. Phase B current (in Amps) = (PHASE_CURRENT_B / 2 <sup>27</sup> ) * 6.25/8 |

### 8.5.7 PHASE\_CURRENT\_C Register (Offset = 448h) [Reset = 00000000h]

PHASE\_CURRENT\_C is shown in [Figure 8-21](#) and described in [Table 8-31](#).

Return to the [Summary Table](#).

Measured current on Phase C Register

**Figure 8-21. PHASE\_CURRENT\_C Register**

|                 |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |   |   |   |   |   |   |   |   |   |   |
|-----------------|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|---|---|---|---|---|---|---|---|---|---|
| 31              | 30 | 29 | 28 | 27 | 26 | 25 | 24 | 23 | 22 | 21 | 20 | 19 | 18 | 17 | 16 | 15 | 14 | 13 | 12 | 11 | 10 | 9 | 8 | 7 | 6 | 5 | 4 | 3 | 2 | 1 | 0 |
| PHASE_CURRENT_C |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |   |   |   |   |   |   |   |   |   |   |
| R-0h            |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |   |   |   |   |   |   |   |   |   |   |

**Table 8-31. PHASE\_CURRENT\_C Register Field Descriptions**

| Bit  | Field           | Type | Reset | Description                                                                                                                                                                                   |
|------|-----------------|------|-------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| 31-0 | PHASE_CURRENT_C | R    | 0h    | 32-bit signed value indicating measured continuous Phase C current. Negative value represented in two's complement. Phase C current (in Amps) = (PHASE_CURRENT_C / 2 <sup>27</sup> ) * 6.25/8 |

### 8.5.8 CSA\_GAIN\_FEEDBACK Register (Offset = 46Ch) [Reset = 0000h]

CSA\_GAIN\_FEEDBACK is shown in [Figure 8-22](#) and described in [Table 8-32](#).

Return to the [Summary Table](#).

VM Voltage Register

**Figure 8-22. CSA\_GAIN\_FEEDBACK Register**

|                   |    |    |    |    |    |   |   |
|-------------------|----|----|----|----|----|---|---|
| 15                | 14 | 13 | 12 | 11 | 10 | 9 | 8 |
| CSA_GAIN_FEEDBACK |    |    |    |    |    |   |   |
| R-0h              |    |    |    |    |    |   |   |
| 7                 | 6  | 5  | 4  | 3  | 2  | 1 | 0 |
| CSA_GAIN_FEEDBACK |    |    |    |    |    |   |   |
| R-0h              |    |    |    |    |    |   |   |

**Table 8-32. CSA\_GAIN\_FEEDBACK Register Field Descriptions**

| Bit  | Field             | Type | Reset | Description                                                                                                                                                                |
|------|-------------------|------|-------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| 15-0 | CSA_GAIN_FEEDBACK | R    | 0h    | 16-bit value indicating current sense gain. MIN_CSA_GAIN = 0.24V/A<br><br>0h = MIN_CSA_GAIN * 8<br>1h = MIN_CSA_GAIN * 4<br>2h = MIN_CSA_GAIN * 2<br>3h = MIN_CSA_GAIN * 1 |

### 8.5.9 VOLTAGE\_GAIN\_FEEDBACK Register (Offset = 477h) [Reset = 0000h]

VOLTAGE\_GAIN\_FEEDBACK is shown in [Figure 8-23](#) and described in [Table 8-33](#).

Return to the [Summary Table](#).

Voltage Gain Register

**Figure 8-23. VOLTAGE\_GAIN\_FEEDBACK Register**

|                       |    |    |    |    |    |   |   |
|-----------------------|----|----|----|----|----|---|---|
| 15                    | 14 | 13 | 12 | 11 | 10 | 9 | 8 |
| VOLTAGE_GAIN_FEEDBACK |    |    |    |    |    |   |   |
| R-0h                  |    |    |    |    |    |   |   |
| 7                     | 6  | 5  | 4  | 3  | 2  | 1 | 0 |
| VOLTAGE_GAIN_FEEDBACK |    |    |    |    |    |   |   |
| R-0h                  |    |    |    |    |    |   |   |

**Table 8-33. VOLTAGE\_GAIN\_FEEDBACK Register Field Descriptions**

| Bit  | Field                 | Type | Reset | Description                                                              |
|------|-----------------------|------|-------|--------------------------------------------------------------------------|
| 15-0 | VOLTAGE_GAIN_FEEDBACK | R    | 0h    | 16-bit value indicating voltage gain<br>0h = 40V<br>1h = 30V<br>2h = 15V |

### 8.5.10 VM\_VOLTAGE Register (Offset = 47Ch) [Reset = 00000000h]

VM\_VOLTAGE is shown in [Figure 8-24](#) and described in [Table 8-34](#).

Return to the [Summary Table](#).

Supply voltage register

**Figure 8-24. VM\_VOLTAGE Register**

|            |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |   |   |   |   |   |   |   |   |   |   |
|------------|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|---|---|---|---|---|---|---|---|---|---|
| 31         | 30 | 29 | 28 | 27 | 26 | 25 | 24 | 23 | 22 | 21 | 20 | 19 | 18 | 17 | 16 | 15 | 14 | 13 | 12 | 11 | 10 | 9 | 8 | 7 | 6 | 5 | 4 | 3 | 2 | 1 | 0 |
| VM_VOLTAGE |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |   |   |   |   |   |   |   |   |   |   |
| R-0h       |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |   |   |   |   |   |   |   |   |   |   |

**Table 8-34. VM\_VOLTAGE Register Field Descriptions**

| Bit  | Field      | Type | Reset | Description                                                                                    |
|------|------------|------|-------|------------------------------------------------------------------------------------------------|
| 31-0 | VM_VOLTAGE | R    | 0h    | 32-bit value indicating DC bus voltage DC Bus Voltage (in Volts) = $VM\_VOLTAGE * 60 / 2^{27}$ |

### 8.5.11 PHASE\_VOLTAGE\_VA Register (Offset = 484h) [Reset = 00000000h]

PHASE\_VOLTAGE\_VA is shown in [Figure 8-25](#) and described in [Table 8-35](#).

Return to the [Summary Table](#).

Phase A Voltage Register

**Figure 8-25. PHASE\_VOLTAGE\_VA Register**

| 31               | 30 | 29 | 28 | 27 | 26 | 25 | 24 | 23 | 22 | 21 | 20 | 19 | 18 | 17 | 16 | 15 | 14 | 13 | 12 | 11 | 10 | 9 | 8 | 7 | 6 | 5 | 4 | 3 | 2 | 1 | 0 |
|------------------|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|---|---|---|---|---|---|---|---|---|---|
| PHASE_VOLTAGE_VA |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |   |   |   |   |   |   |   |   |   |   |
| R-0h             |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |   |   |   |   |   |   |   |   |   |   |

**Table 8-35. PHASE\_VOLTAGE\_VA Register Field Descriptions**

| Bit  | Field            | Type | Reset | Description                                                                                                                                                                                           |
|------|------------------|------|-------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| 31-0 | PHASE_VOLTAGE_VA | R    | 0h    | 32-bit signed value indicating measured A phase voltage during ISD. Negative value represented in two's complement. Phase A voltage (in Volts) = PHASE_VOLTAGE_VA * 60 / (sqrt(3) * 2 <sup>27</sup> ) |

### 8.5.12 PHASE\_VOLTAGE\_VB Register (Offset = 486h) [Reset = 00000000h]

PHASE\_VOLTAGE\_VB is shown in [Figure 8-26](#) and described in [Table 8-36](#).

Return to the [Summary Table](#).

Phase B Voltage Register

**Figure 8-26. PHASE\_VOLTAGE\_VB Register**

|                  |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |   |   |   |   |   |   |   |   |   |   |
|------------------|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|---|---|---|---|---|---|---|---|---|---|
| 31               | 30 | 29 | 28 | 27 | 26 | 25 | 24 | 23 | 22 | 21 | 20 | 19 | 18 | 17 | 16 | 15 | 14 | 13 | 12 | 11 | 10 | 9 | 8 | 7 | 6 | 5 | 4 | 3 | 2 | 1 | 0 |
| PHASE_VOLTAGE_VB |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |   |   |   |   |   |   |   |   |   |   |
| R-0h             |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |   |   |   |   |   |   |   |   |   |   |

**Table 8-36. PHASE\_VOLTAGE\_VB Register Field Descriptions**

| Bit  | Field            | Type | Reset | Description                                                                                                                                                                                           |
|------|------------------|------|-------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| 31-0 | PHASE_VOLTAGE_VB | R    | 0h    | 32-bit signed value indicating measured B phase voltage during ISD. Negative value represented in two's complement. Phase B voltage (in Volts) = PHASE_VOLTAGE_VB * 60 / (sqrt(3) * 2 <sup>27</sup> ) |

### 8.5.13 PHASE\_VOLTAGE\_VC Register (Offset = 488h) [Reset = 00000000h]

PHASE\_VOLTAGE\_VC is shown in [Figure 8-27](#) and described in [Table 8-37](#).

Return to the [Summary Table](#).

Phase C Voltage Register

**Figure 8-27. PHASE\_VOLTAGE\_VC Register**

|                  |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |   |   |   |   |   |   |   |   |   |   |
|------------------|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|---|---|---|---|---|---|---|---|---|---|
| 31               | 30 | 29 | 28 | 27 | 26 | 25 | 24 | 23 | 22 | 21 | 20 | 19 | 18 | 17 | 16 | 15 | 14 | 13 | 12 | 11 | 10 | 9 | 8 | 7 | 6 | 5 | 4 | 3 | 2 | 1 | 0 |
| PHASE_VOLTAGE_VC |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |   |   |   |   |   |   |   |   |   |   |
| R-0h             |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |   |   |   |   |   |   |   |   |   |   |

**Table 8-37. PHASE\_VOLTAGE\_VC Register Field Descriptions**

| Bit  | Field            | Type | Reset | Description                                                                                                                                                                                           |
|------|------------------|------|-------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| 31-0 | PHASE_VOLTAGE_VC | R    | 0h    | 32-bit signed value indicating measured C phase voltage during ISD. Negative value represented in two's complement. Phase C voltage (in Volts) = PHASE_VOLTAGE_VC * 60 / (sqrt(3) * 2 <sup>27</sup> ) |

#### 8.5.14 SIN\_COMMUTATION\_ANGLE Register (Offset = 4BCh) [Reset = 00000000h]

SIN\_COMMUTATION\_ANGLE is shown in [Figure 8-28](#) and described in [Table 8-38](#).

Return to the [Summary Table](#).

Sine of Commutation Angle

**Figure 8-28. SIN\_COMMUTATION\_ANGLE Register**

|                       |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |   |   |   |   |   |   |   |   |   |   |
|-----------------------|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|---|---|---|---|---|---|---|---|---|---|
| 31                    | 30 | 29 | 28 | 27 | 26 | 25 | 24 | 23 | 22 | 21 | 20 | 19 | 18 | 17 | 16 | 15 | 14 | 13 | 12 | 11 | 10 | 9 | 8 | 7 | 6 | 5 | 4 | 3 | 2 | 1 | 0 |
| SIN_COMMUTATION_ANGLE |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |   |   |   |   |   |   |   |   |   |   |
| R-0h                  |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |   |   |   |   |   |   |   |   |   |   |

**Table 8-38. SIN\_COMMUTATION\_ANGLE Register Field Descriptions**

| Bit  | Field                 | Type | Reset | Description                                                                                                                                                                |
|------|-----------------------|------|-------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| 31-0 | SIN_COMMUTATION_ANGLE | R    | 0h    | 32-bit signed value indicating sine of rotor Angle. Negative value represented in two's complement. $\sin(\text{rotor angle}) = (\text{SIN\_COMMUTATION\_ANGLE} / 2^{27})$ |

**8.5.15 COS\_COMMUTATION\_ANGLE Register (Offset = 4BEh) [Reset = 00000000h]**

COS\_COMMUTATION\_ANGLE is shown in [Figure 8-29](#) and described in [Table 8-39](#).

Return to the [Summary Table](#).

Cosine of Commutation Angle

**Figure 8-29. COS\_COMMUTATION\_ANGLE Register**

|                       |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |   |   |   |   |   |   |   |   |   |   |
|-----------------------|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|---|---|---|---|---|---|---|---|---|---|
| 31                    | 30 | 29 | 28 | 27 | 26 | 25 | 24 | 23 | 22 | 21 | 20 | 19 | 18 | 17 | 16 | 15 | 14 | 13 | 12 | 11 | 10 | 9 | 8 | 7 | 6 | 5 | 4 | 3 | 2 | 1 | 0 |
| COS_COMMUTATION_ANGLE |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |   |   |   |   |   |   |   |   |   |   |
| R-0h                  |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |   |   |   |   |   |   |   |   |   |   |

**Table 8-39. COS\_COMMUTATION\_ANGLE Register Field Descriptions**

| Bit  | Field                 | Type | Reset | Description                                                                                                                                                                  |
|------|-----------------------|------|-------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| 31-0 | COS_COMMUTATION_ANGLE | R    | 0h    | 32-bit signed value indicating cosine of rotor angle. Negative value represented in two's complement. $\cos(\text{rotor angle}) = (\text{COS\_COMMUTATION\_ANGLE} / 2^{27})$ |

### 8.5.16 IALPHA Register (Offset = 4DCh) [Reset = 00000000h]

IALPHA is shown in [Figure 8-30](#) and described in [Table 8-40](#).

Return to the [Summary Table](#).

IALPHA Current Register

**Figure 8-30. IALPHA Register**

|        |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |   |   |   |   |   |   |   |   |   |   |
|--------|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|---|---|---|---|---|---|---|---|---|---|
| 31     | 30 | 29 | 28 | 27 | 26 | 25 | 24 | 23 | 22 | 21 | 20 | 19 | 18 | 17 | 16 | 15 | 14 | 13 | 12 | 11 | 10 | 9 | 8 | 7 | 6 | 5 | 4 | 3 | 2 | 1 | 0 |
| IALPHA |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |   |   |   |   |   |   |   |   |   |   |
| R-0h   |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |   |   |   |   |   |   |   |   |   |   |

**Table 8-40. IALPHA Register Field Descriptions**

| Bit  | Field  | Type | Reset | Description                                                                                                                                                                 |
|------|--------|------|-------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| 31-0 | IALPHA | R    | 0h    | 32-bit signed value indicating phase current in alpha- beta domain. Negative value represented in two's complement. IAlpha (in Amps) = (IALPHA / 2 <sup>27</sup> ) * 6.25/8 |

### 8.5.17 IBETA Register (Offset = 4DEh) [Reset = 00000000h]

IBETA is shown in [Figure 8-31](#) and described in [Table 8-41](#).

Return to the [Summary Table](#).

IBETA Current Register

**Figure 8-31. IBETA Register**

| 31    | 30 | 29 | 28 | 27 | 26 | 25 | 24 | 23 | 22 | 21 | 20 | 19 | 18 | 17 | 16 | 15 | 14 | 13 | 12 | 11 | 10 | 9 | 8 | 7 | 6 | 5 | 4 | 3 | 2 | 1 | 0 |
|-------|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|---|---|---|---|---|---|---|---|---|---|
| IBETA |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |   |   |   |   |   |   |   |   |   |   |
| R-0h  |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |   |   |   |   |   |   |   |   |   |   |

**Table 8-41. IBETA Register Field Descriptions**

| Bit  | Field | Type | Reset | Description                                                                                                                                                        |
|------|-------|------|-------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| 31-0 | IBETA | R    | 0h    | 32-bit signed value indicating phase current in alpha- beta domain. Negative value represented in two's complement. IBeta (in Amps) = (IBETA / $2^{27}$ ) * 6.25/8 |

### 8.5.18 VALPHA Register (Offset = 4E0h) [Reset = 00000000h]

VALPHA is shown in [Figure 8-32](#) and described in [Table 8-42](#).

Return to the [Summary Table](#).

VALPHA Voltage Register

**Figure 8-32. VALPHA Register**

|        |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |   |   |   |   |   |   |   |   |   |   |
|--------|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|---|---|---|---|---|---|---|---|---|---|
| 31     | 30 | 29 | 28 | 27 | 26 | 25 | 24 | 23 | 22 | 21 | 20 | 19 | 18 | 17 | 16 | 15 | 14 | 13 | 12 | 11 | 10 | 9 | 8 | 7 | 6 | 5 | 4 | 3 | 2 | 1 | 0 |
| VALPHA |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |   |   |   |   |   |   |   |   |   |   |
| R-0h   |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |   |   |   |   |   |   |   |   |   |   |

**Table 8-42. VALPHA Register Field Descriptions**

| Bit  | Field  | Type | Reset | Description                                                                                                                                  |
|------|--------|------|-------|----------------------------------------------------------------------------------------------------------------------------------------------|
| 31-0 | VALPHA | R    | 0h    | 32-bit signed value indicating applied phase voltage in alpha-beta domain $V_{Alpha} \text{ (in Volts)} = (VALPHA / 2^{27}) * 60 / \sqrt{3}$ |

### 8.5.19 ID Register (Offset = 4ECh) [Reset = 00000000h]

ID is shown in [Figure 8-33](#) and described in [Table 8-43](#).

Return to the [Summary Table](#).

Measured d-axis Current Register

**Figure 8-33. ID Register**

|      |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |   |   |   |   |   |   |   |   |   |   |
|------|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|---|---|---|---|---|---|---|---|---|---|
| 31   | 30 | 29 | 28 | 27 | 26 | 25 | 24 | 23 | 22 | 21 | 20 | 19 | 18 | 17 | 16 | 15 | 14 | 13 | 12 | 11 | 10 | 9 | 8 | 7 | 6 | 5 | 4 | 3 | 2 | 1 | 0 |
| ID   |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |   |   |   |   |   |   |   |   |   |   |
| R-0h |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |   |   |   |   |   |   |   |   |   |   |

**Table 8-43. ID Register Field Descriptions**

| Bit  | Field | Type | Reset | Description                                                                                                                                                                                          |
|------|-------|------|-------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| 31-0 | ID    | R    | 0h    | 32-bit signed value indicating d-axis(flux component) phase current in d-q domain. Negative value represented in two's complement. Flux component phase current (in Amps) = $(ID / 2^{27}) * 6.25/8$ |

### 8.5.20 IQ Register (Offset = 4EEh) [Reset = 00000000h]

IQ is shown in [Figure 8-34](#) and described in [Table 8-44](#).

Return to the [Summary Table](#).

Measured q-axis Current Register

**Figure 8-34. IQ Register**

| 31   | 30 | 29 | 28 | 27 | 26 | 25 | 24 | 23 | 22 | 21 | 20 | 19 | 18 | 17 | 16 | 15 | 14 | 13 | 12 | 11 | 10 | 9 | 8 | 7 | 6 | 5 | 4 | 3 | 2 | 1 | 0 |
|------|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|---|---|---|---|---|---|---|---|---|---|
| IQ   |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |   |   |   |   |   |   |   |   |   |   |
| R-0h |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |   |   |   |   |   |   |   |   |   |   |

**Table 8-44. IQ Register Field Descriptions**

| Bit  | Field | Type | Reset | Description                                                                                                                                                                                              |
|------|-------|------|-------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| 31-0 | IQ    | R    | 0h    | 32-bit signed value indicating q-axis(torque component) phase current in d-q domain. Negative value represented in two's complement. Torque component phase current (in Amps) = $(IQ / 2^{27}) * 6.25/8$ |

### 8.5.21 VD Register (Offset = 4F0h) [Reset = 00000000h]

VD is shown in [Figure 8-35](#) and described in [Table 8-45](#).

Return to the [Summary Table](#).

VD Voltage Register

**Figure 8-35. VD Register**

|      |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |   |   |   |   |   |   |   |   |   |   |
|------|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|---|---|---|---|---|---|---|---|---|---|
| 31   | 30 | 29 | 28 | 27 | 26 | 25 | 24 | 23 | 22 | 21 | 20 | 19 | 18 | 17 | 16 | 15 | 14 | 13 | 12 | 11 | 10 | 9 | 8 | 7 | 6 | 5 | 4 | 3 | 2 | 1 | 0 |
| VD   |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |   |   |   |   |   |   |   |   |   |   |
| R-0h |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |   |   |   |   |   |   |   |   |   |   |

**Table 8-45. VD Register Field Descriptions**

| Bit  | Field | Type | Reset | Description                                                                                                                                                               |
|------|-------|------|-------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| 31-0 | VD    | R    | 0h    | 32-bit signed value indicating applied phase voltage in d-q domain. Negative value represented in two's complement. Vd (in Volts) = $(VD / 2^{27}) * 60 / \text{sqrt}(3)$ |

### 8.5.22 VQ Register (Offset = 4F2h) [Reset = 00000000h]

VQ is shown in [Figure 8-36](#) and described in [Table 8-46](#).

Return to the [Summary Table](#).

VQ Voltage Register

**Figure 8-36. VQ Register**

|      |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |   |   |   |   |   |   |   |   |   |   |
|------|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|---|---|---|---|---|---|---|---|---|---|
| 31   | 30 | 29 | 28 | 27 | 26 | 25 | 24 | 23 | 22 | 21 | 20 | 19 | 18 | 17 | 16 | 15 | 14 | 13 | 12 | 11 | 10 | 9 | 8 | 7 | 6 | 5 | 4 | 3 | 2 | 1 | 0 |
| VQ   |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |   |   |   |   |   |   |   |   |   |   |
| R-0h |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |   |   |   |   |   |   |   |   |   |   |

**Table 8-46. VQ Register Field Descriptions**

| Bit  | Field | Type | Reset | Description                                                                                                                                                            |
|------|-------|------|-------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| 31-0 | VQ    | R    | 0h    | 32-bit signed value indicating applied phase voltage in d-q domain. Negative value represented in two's complement. $V_q$ (in Volts) = $(VQ / 2^{27}) * 60 / \sqrt{3}$ |

### 8.5.23 IQ\_REF\_ROTATOR\_ALIGN Register (Offset = 52Ah) [Reset = 00000000h]

IQ\_REF\_ROTATOR\_ALIGN is shown in [Figure 8-37](#) and described in [Table 8-47](#).

Return to the [Summary Table](#).

Align Current Reference

**Figure 8-37. IQ\_REF\_ROTATOR\_ALIGN Register**

|                      |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |   |   |   |   |   |   |   |   |   |   |
|----------------------|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|---|---|---|---|---|---|---|---|---|---|
| 31                   | 30 | 29 | 28 | 27 | 26 | 25 | 24 | 23 | 22 | 21 | 20 | 19 | 18 | 17 | 16 | 15 | 14 | 13 | 12 | 11 | 10 | 9 | 8 | 7 | 6 | 5 | 4 | 3 | 2 | 1 | 0 |
| IQ_REF_ROTATOR_ALIGN |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |   |   |   |   |   |   |   |   |   |   |
| R-0h                 |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |   |   |   |   |   |   |   |   |   |   |

**Table 8-47. IQ\_REF\_ROTATOR\_ALIGN Register Field Descriptions**

| Bit  | Field                | Type | Reset | Description                                                                                                                                                                                                              |
|------|----------------------|------|-------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| 31-0 | IQ_REF_ROTATOR_ALIGN | R    | 0h    | 32-bit signed value indicating current reference during align state. Negative value represented in two's complement. Current reference during Align State (in Amps) = (IQ_REF_ROTATOR_ALIGN / 2 <sup>27</sup> ) * 6.25/8 |

#### 8.5.24 SPEED\_REF\_OPEN\_LOOP Register (Offset = 540h) [Reset = 00000000h]

SPEED\_REF\_OPEN\_LOOP is shown in [Figure 8-38](#) and described in [Table 8-48](#).

Return to the [Summary Table](#).

Speed at which motor transitions to close loop

**Figure 8-38. SPEED\_REF\_OPEN\_LOOP Register**

|                     |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |   |   |   |   |   |   |   |   |   |   |
|---------------------|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|---|---|---|---|---|---|---|---|---|---|
| 31                  | 30 | 29 | 28 | 27 | 26 | 25 | 24 | 23 | 22 | 21 | 20 | 19 | 18 | 17 | 16 | 15 | 14 | 13 | 12 | 11 | 10 | 9 | 8 | 7 | 6 | 5 | 4 | 3 | 2 | 1 | 0 |
| SPEED_REF_OPEN_LOOP |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |   |   |   |   |   |   |   |   |   |   |
| R-0h                |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |   |   |   |   |   |   |   |   |   |   |

**Table 8-48. SPEED\_REF\_OPEN\_LOOP Register Field Descriptions**

| Bit  | Field               | Type | Reset | Description                                                                                                                                                                                                       |
|------|---------------------|------|-------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| 31-0 | SPEED_REF_OPEN_LOOP | R    | 0h    | 32-bit signed value indicating open loop speed reference. Negative value represented in two's complement. Speed reference during open loop (in Hz) = (SPEED_REF_OPEN_LOOP / 2 <sup>27</sup> ) * MAX_SPEED (in Hz) |

### 8.5.25 IQ\_REF\_OPEN\_LOOP Register (Offset = 550h) [Reset = 00000000h]

IQ\_REF\_OPEN\_LOOP is shown in [Figure 8-39](#) and described in [Table 8-49](#).

Return to the [Summary Table](#).

Open Loop Current Reference

**Figure 8-39. IQ\_REF\_OPEN\_LOOP Register**

| 31               | 30 | 29 | 28 | 27 | 26 | 25 | 24 | 23 | 22 | 21 | 20 | 19 | 18 | 17 | 16 | 15 | 14 | 13 | 12 | 11 | 10 | 9 | 8 | 7 | 6 | 5 | 4 | 3 | 2 | 1 | 0 |
|------------------|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|---|---|---|---|---|---|---|---|---|---|
| IQ_REF_OPEN_LOOP |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |   |   |   |   |   |   |   |   |   |   |
| R-0h             |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |   |   |   |   |   |   |   |   |   |   |

**Table 8-49. IQ\_REF\_OPEN\_LOOP Register Field Descriptions**

| Bit  | Field            | Type | Reset | Description                                                                                                                                                                                                        |
|------|------------------|------|-------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| 31-0 | IQ_REF_OPEN_LOOP | R    | 0h    | 32-bit signed value indicating current reference during open loop. Negative value represented in two's complement. Current reference during open loop (in Amps) = $(\text{IQ\_REF\_OPEN\_LOOP} / 2^{27}) * 6.25/8$ |

### 8.5.26 SPEED\_REF\_CLOSED\_LOOP Register (Offset = 5D2h) [Reset = 00000000h]

SPEED\_REF\_CLOSED\_LOOP is shown in [Figure 8-40](#) and described in [Table 8-50](#).

Return to the [Summary Table](#).

Speed Reference Register

**Figure 8-40. SPEED\_REF\_CLOSED\_LOOP Register**

|                       |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |   |   |   |   |   |   |   |   |   |   |
|-----------------------|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|---|---|---|---|---|---|---|---|---|---|
| 31                    | 30 | 29 | 28 | 27 | 26 | 25 | 24 | 23 | 22 | 21 | 20 | 19 | 18 | 17 | 16 | 15 | 14 | 13 | 12 | 11 | 10 | 9 | 8 | 7 | 6 | 5 | 4 | 3 | 2 | 1 | 0 |
| SPEED_REF_CLOSED_LOOP |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |   |   |   |   |   |   |   |   |   |   |
| R-0h                  |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |   |   |   |   |   |   |   |   |   |   |

**Table 8-50. SPEED\_REF\_CLOSED\_LOOP Register Field Descriptions**

| Bit  | Field                 | Type | Reset | Description                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                        |
|------|-----------------------|------|-------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| 31-0 | SPEED_REF_CLOSED_LOOP | R    | 0h    | 32-bit signed value indicating reference for closed loop. Negative value represented in two's complement. In speed control mode, speed reference in closed loop (in Hz) = $(\text{SPEED\_REF\_CLOSED\_LOOP} / 2^{27}) * \text{MAX\_SPEED}$ (in Hz). In power mode, power reference in closed loop (in Watts) = $(\text{SPEED\_REF\_CLOSED\_LOOP} / 2^{27}) * \text{MAX\_POWER}$ (in Watts) In current mode, Iq current reference in closed loop (in Amps) = $(\text{SPEED\_REF\_CLOSED\_LOOP} / 2^{27}) * \text{ILIMIT}$ (in Amps) |

### 8.5.27 ID\_REF\_CLOSED\_LOOP Register (Offset = 612h) [Reset = 00000000h]

ID\_REF\_CLOSED\_LOOP is shown in [Figure 8-41](#) and described in [Table 8-51](#).

Return to the [Summary Table](#).

Reference for Current Loop Register

**Figure 8-41. ID\_REF\_CLOSED\_LOOP Register**

|                    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |   |   |   |   |   |   |   |   |   |   |
|--------------------|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|---|---|---|---|---|---|---|---|---|---|
| 31                 | 30 | 29 | 28 | 27 | 26 | 25 | 24 | 23 | 22 | 21 | 20 | 19 | 18 | 17 | 16 | 15 | 14 | 13 | 12 | 11 | 10 | 9 | 8 | 7 | 6 | 5 | 4 | 3 | 2 | 1 | 0 |
| ID_REF_CLOSED_LOOP |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |   |   |   |   |   |   |   |   |   |   |
| R-0h               |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |   |   |   |   |   |   |   |   |   |   |

**Table 8-51. ID\_REF\_CLOSED\_LOOP Register Field Descriptions**

| Bit  | Field              | Type | Reset | Description                                                                                                                                                                                                                               |
|------|--------------------|------|-------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| 31-0 | ID_REF_CLOSED_LOOP | R    | 0h    | 32-bit signed value indicating d-axis(flux component) phase current reference in closed loop . Negative value represented in two's complement. Flux component phase current reference in closed loop (in Amps) = $(ID / 2^{27}) * 6.25/8$ |

### 8.5.28 IQ\_REF\_CLOSED\_LOOP Register (Offset = 614h) [Reset = 00000000h]

IQ\_REF\_CLOSED\_LOOP is shown in [Figure 8-42](#) and described in [Table 8-52](#).

Return to the [Summary Table](#).

Reference for Current Loop Register

**Figure 8-42. IQ\_REF\_CLOSED\_LOOP Register**

|                    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |   |   |   |   |   |   |   |   |   |   |
|--------------------|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|---|---|---|---|---|---|---|---|---|---|
| 31                 | 30 | 29 | 28 | 27 | 26 | 25 | 24 | 23 | 22 | 21 | 20 | 19 | 18 | 17 | 16 | 15 | 14 | 13 | 12 | 11 | 10 | 9 | 8 | 7 | 6 | 5 | 4 | 3 | 2 | 1 | 0 |
| IQ_REF_CLOSED_LOOP |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |   |   |   |   |   |   |   |   |   |   |
| R-0h               |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |   |   |   |   |   |   |   |   |   |   |

**Table 8-52. IQ\_REF\_CLOSED\_LOOP Register Field Descriptions**

| Bit  | Field              | Type | Reset | Description                                                                                                                                                                                                                                          |
|------|--------------------|------|-------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| 31-0 | IQ_REF_CLOSED_LOOP | R    | 0h    | 32-bit signed value indicating q-axis(torque component) phase current reference in closed loop. Negative value represented in two's complement. Torque component phase current reference in closed loop (in Amps) = (IQ / 2 <sup>27</sup> ) * 6.25/8 |

### 8.5.29 ISD\_STATE Register (Offset = 6AEh) [Reset = 0000h]

ISD\_STATE is shown in [Figure 8-43](#) and described in [Table 8-53](#).

Return to the [Summary Table](#).

ISD state Register

**Figure 8-43. ISD\_STATE Register**

|           |    |    |    |    |    |   |   |
|-----------|----|----|----|----|----|---|---|
| 15        | 14 | 13 | 12 | 11 | 10 | 9 | 8 |
| ISD_STATE |    |    |    |    |    |   |   |
| R-0h      |    |    |    |    |    |   |   |
| 7         | 6  | 5  | 4  | 3  | 2  | 1 | 0 |
| ISD_STATE |    |    |    |    |    |   |   |
| R-0h      |    |    |    |    |    |   |   |

**Table 8-53. ISD\_STATE Register Field Descriptions**

| Bit  | Field     | Type | Reset | Description                                                                                                                                                                                                         |
|------|-----------|------|-------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| 15-0 | ISD_STATE | R    | 0h    | 16-bit value indicating current ISD state<br>0h = ISD_INIT<br>1h = ISD_MOTOR_STOP_CHECK<br>2h = ISD_ESTIM_INIT<br>3h = ISD_RUN_MOTOR_CHECK<br>4h = ISD_MOTOR_DIRECTION_CHECK<br>5h = ISD_COMPLETE<br>6h = ISD_FAULT |

### 8.5.30 ISD\_SPEED Register (Offset = 6B8h) [Reset = 00000000h]

ISD\_SPEED is shown in [Figure 8-44](#) and described in [Table 8-54](#).

Return to the [Summary Table](#).

ISD Speed Register

**Figure 8-44. ISD\_SPEED Register**

|           |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |   |   |   |   |   |   |   |   |   |   |
|-----------|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|---|---|---|---|---|---|---|---|---|---|
| 31        | 30 | 29 | 28 | 27 | 26 | 25 | 24 | 23 | 22 | 21 | 20 | 19 | 18 | 17 | 16 | 15 | 14 | 13 | 12 | 11 | 10 | 9 | 8 | 7 | 6 | 5 | 4 | 3 | 2 | 1 | 0 |
| ISD_SPEED |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |   |   |   |   |   |   |   |   |   |   |
| R-0h      |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |   |   |   |   |   |   |   |   |   |   |

**Table 8-54. ISD\_SPEED Register Field Descriptions**

| Bit  | Field     | Type | Reset | Description                                                                                                                                                   |
|------|-----------|------|-------|---------------------------------------------------------------------------------------------------------------------------------------------------------------|
| 31-0 | ISD_SPEED | R    | 0h    | 32-bit value indicating calculated absolute speed during ISD state<br>Speed estimated during ISD (in Hz) = (ISD_SPEED / 2 <sup>27</sup> ) * MAX_SPEED (in Hz) |

### 8.5.31 IPD\_STATE Register (Offset = 6EAh) [Reset = 0000h]

IPD\_STATE is shown in [Figure 8-45](#) and described in [Table 8-55](#).

Return to the [Summary Table](#).

IPD state Register

**Figure 8-45. IPD\_STATE Register**

|           |    |    |    |    |    |   |   |
|-----------|----|----|----|----|----|---|---|
| 15        | 14 | 13 | 12 | 11 | 10 | 9 | 8 |
| IPD_STATE |    |    |    |    |    |   |   |
| R-0h      |    |    |    |    |    |   |   |
| 7         | 6  | 5  | 4  | 3  | 2  | 1 | 0 |
| IPD_STATE |    |    |    |    |    |   |   |
| R-0h      |    |    |    |    |    |   |   |

**Table 8-55. IPD\_STATE Register Field Descriptions**

| Bit  | Field     | Type | Reset | Description                                                                                                                                                                                                                                                                                                                                                              |
|------|-----------|------|-------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| 15-0 | IPD_STATE | R    | 0h    | 16-bit value indicating current IPD state<br>0h = IPD_INIT<br>1h = IPD_VECTOR_CONFIG<br>2h = IPD_RUN<br>3h = IPD_SLOW_RISE_CLOCK<br>4h = IPD_SLOW_FALL_CLOCK<br>5h = IPD_WAIT_CURRENT_DECAY<br>6h = IPD_GET_TIMES<br>7h = IPD_SET_NEXT_VECTOR<br>8h = IPD_CALC_SECTOR_RISE<br>9h = IPD_CALC_ROTOR_POSITION<br>Ah = IPD_CALC_ANGLE<br>Bh = IPD_COMPLETE<br>Ch = IPD_FAULT |

### 8.5.32 IPD\_ANGLE Register (Offset = 72Eh) [Reset = 00000000h]

IPD\_ANGLE is shown in [Figure 8-46](#) and described in [Table 8-56](#).

Return to the [Summary Table](#).

Calculated IPD Angle Register

**Figure 8-46. IPD\_ANGLE Register**

|           |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |   |   |   |   |   |   |   |   |   |   |
|-----------|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|---|---|---|---|---|---|---|---|---|---|
| 31        | 30 | 29 | 28 | 27 | 26 | 25 | 24 | 23 | 22 | 21 | 20 | 19 | 18 | 17 | 16 | 15 | 14 | 13 | 12 | 11 | 10 | 9 | 8 | 7 | 6 | 5 | 4 | 3 | 2 | 1 | 0 |
| IPD_ANGLE |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |   |   |   |   |   |   |   |   |   |   |
| R-0h      |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |   |   |   |   |   |   |   |   |   |   |

**Table 8-56. IPD\_ANGLE Register Field Descriptions**

| Bit  | Field     | Type | Reset | Description                                                                                                                                                      |
|------|-----------|------|-------|------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| 31-0 | IPD_ANGLE | R    | 0h    | 32-bit signed value indicating measured IPD angle. Negative value represented in two's complement. IPD Angle (in degrees) = $(\text{IPD\_ANGLE} / 2^{27}) * 360$ |

### 8.5.33 ED Register (Offset = 772h) [Reset = 00000000h]

ED is shown in [Figure 8-47](#) and described in [Table 8-57](#).

Return to the [Summary Table](#).

Estimated BEMF EQ Register

**Figure 8-47. ED Register**

| 31   | 30 | 29 | 28 | 27 | 26 | 25 | 24 | 23 | 22 | 21 | 20 | 19 | 18 | 17 | 16 | 15 | 14 | 13 | 12 | 11 | 10 | 9 | 8 | 7 | 6 | 5 | 4 | 3 | 2 | 1 | 0 |
|------|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|---|---|---|---|---|---|---|---|---|---|
| ED   |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |   |   |   |   |   |   |   |   |   |   |
| R-0h |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |   |   |   |   |   |   |   |   |   |   |

**Table 8-57. ED Register Field Descriptions**

| Bit  | Field | Type | Reset | Description                                                                                                                                                                    |
|------|-------|------|-------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| 31-0 | ED    | R    | 0h    | 32-bit signed value indicating estimated Back EMF along the D-Axis (Ed). Negative value represented in two's complement. Ed (in Volts) = $(ED / 2^{27}) * 60 / \text{sqrt}(3)$ |

### 8.5.34 EQ Register (Offset = 774h) [Reset = 00000000h]

EQ is shown in [Figure 8-48](#) and described in [Table 8-58](#).

Return to the [Summary Table](#).

Estimated BEMF ED Register

**Figure 8-48. EQ Register**

| 31   | 30 | 29 | 28 | 27 | 26 | 25 | 24 | 23 | 22 | 21 | 20 | 19 | 18 | 17 | 16 | 15 | 14 | 13 | 12 | 11 | 10 | 9 | 8 | 7 | 6 | 5 | 4 | 3 | 2 | 1 | 0 |
|------|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|---|---|---|---|---|---|---|---|---|---|
| EQ   |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |   |   |   |   |   |   |   |   |   |   |
| R-0h |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |   |   |   |   |   |   |   |   |   |   |

**Table 8-58. EQ Register Field Descriptions**

| Bit  | Field | Type | Reset | Description                                                                                                                                                                    |
|------|-------|------|-------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| 31-0 | EQ    | R    | 0h    | 32-bit signed value indicating estimated Back EMF along the Q-Axis (Eq). Negative value represented in two's complement. Eq (in Volts) = $(EQ / 2^{27}) * 60 / \text{sqrt}(3)$ |

### 8.5.35 SPEED\_FDBK Register (Offset = 782h) [Reset = 00000000h]

SPEED\_FDBK is shown in [Figure 8-49](#) and described in [Table 8-59](#).

Return to the [Summary Table](#).

Speed Feedback Register

**Figure 8-49. SPEED\_FDBK Register**

|            |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |   |   |   |   |   |   |   |   |   |   |
|------------|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|---|---|---|---|---|---|---|---|---|---|
| 31         | 30 | 29 | 28 | 27 | 26 | 25 | 24 | 23 | 22 | 21 | 20 | 19 | 18 | 17 | 16 | 15 | 14 | 13 | 12 | 11 | 10 | 9 | 8 | 7 | 6 | 5 | 4 | 3 | 2 | 1 | 0 |
| SPEED_FDBK |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |   |   |   |   |   |   |   |   |   |   |
| R-0h       |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |   |   |   |   |   |   |   |   |   |   |

**Table 8-59. SPEED\_FDBK Register Field Descriptions**

| Bit  | Field      | Type | Reset | Description                                                                                                                                                                               |
|------|------------|------|-------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| 31-0 | SPEED_FDBK | R    | 0h    | 32-bit signed value indicating estimated motor speed. Negative value represented in two's complement. Estimated Motor Speed (in Hz) = (SPEED_FDBK / 2 <sup>27</sup> ) * MAX_SPEED (in Hz) |

### 8.5.36 THETA\_EST Register (Offset = 786h) [Reset = 00000000h]

THETA\_EST is shown in [Figure 8-50](#) and described in [Table 8-60](#).

Return to the [Summary Table](#).

Estimated rotor Position Register

**Figure 8-50. THETA\_EST Register**

| 31        | 30 | 29 | 28 | 27 | 26 | 25 | 24 | 23 | 22 | 21 | 20 | 19 | 18 | 17 | 16 | 15 | 14 | 13 | 12 | 11 | 10 | 9 | 8 | 7 | 6 | 5 | 4 | 3 | 2 | 1 | 0 |
|-----------|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|---|---|---|---|---|---|---|---|---|---|
| THETA_EST |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |   |   |   |   |   |   |   |   |   |   |
| R-0h      |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |   |   |   |   |   |   |   |   |   |   |

**Table 8-60. THETA\_EST Register Field Descriptions**

| Bit  | Field     | Type | Reset | Description                                                                                                                                                                                                                                                      |
|------|-----------|------|-------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| 31-0 | THETA_EST | R    | 0h    | 32-bit signed value indicating estimated rotor angle. Angle should be modulo 360 degrees. For example if the estimated Angle value 380 degrees then it means $380 \% 360 = 20$ degrees Estimated rotor Angle (in degrees) = $(\text{THETA\_EST} / 2^{27}) * 360$ |

## 9 Application and Implementation

---

### Note

Information in the following applications sections is not part of the TI component specification, and TI does not warrant its accuracy or completeness. TI's customers are responsible for determining suitability of components for their purposes. Customers should validate and test their design implementation to confirm system functionality.

---

### 9.1 Application Information

The MCF8315D device is used in sensorless 3-phase BLDC motor control. The driver provides a high performance, high-reliability, flexible solution for appliances, fans, pumps, residential and living fans, seat cooling fans, automotive fans and blowers. The following section shows a common application of the MCF8315D device.

### 9.2 Typical Applications

[Figure 9-1](#) shows the typical schematic of MCF8315D.




**Figure 9-1. Example Applications Schematic**

**Note**

- DAC output(s) are available in RGF and RRY packages only. In PWP package, internal variables can be monitored over I<sup>2</sup>C.
- ALARM and DIR pins are available in RGF and RRY packages only. In PWP package, direction can be changed using DIR\_INPUT bitfield in PERI\_CONFIG1 register.
- SOX output is available only in RGF package. In RRY and PWP packages, phase currents can be monitored over I<sup>2</sup>C.

Table 9-1 lists the recommended values of the external components for MCF8315D.

**Table 9-1. MCF8315D External Components**

| COMPONENTS       | PIN 1 | PIN 2 | RECOMMENDED                                                                                                    |
|------------------|-------|-------|----------------------------------------------------------------------------------------------------------------|
| C <sub>VM1</sub> | VM    | PGND  | X7R, 0.1μF, TI recommends a capacitor voltage rating at least twice the normal operating voltage of the device |

**Table 9-1. MCF8315D External Components (continued)**

| COMPONENTS          | PIN 1              | PIN 2  | RECOMMENDED                                                                                                                                                                         |
|---------------------|--------------------|--------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| C <sub>VM2</sub>    | VM                 | PGND   | ≥ 10μF, TI recommends a capacitor voltage rating at least twice the normal operating voltage of the device                                                                          |
| C <sub>CP</sub>     | CP                 | VM     | X7R, 16V, 1μF capacitor                                                                                                                                                             |
| C <sub>FLY</sub>    | CPH                | CPL    | X7R, 47nF, TI recommends a capacitor voltage rating at least twice the normal operating voltage of the pin                                                                          |
| C <sub>AVDD</sub>   | AVDD               | AGND   | X7R, 1μF, ≥ 10V. In order for AVDD to accurately regulate output voltage, capacitor should have effective capacitance between 0.7μF to 1.3μF at 3.3V across operating temperature.  |
| C <sub>DVDD</sub>   | DVDD               | DGND   | X7R, 1μF, ≥ 6.3V. In order for DVDD to accurately regulate output voltage, capacitor should have effective capacitance between 0.7μF to 2.5μF at 1.5V across operating temperature. |
| C <sub>BK</sub>     | FB_BK              | GND_BK | X7R, buck-output rated capacitor                                                                                                                                                    |
| L <sub>BK</sub>     | SW_BK              | FB_BK  | Buck-output inductor                                                                                                                                                                |
| R <sub>FG</sub>     | 1.8 to 5V Supply   | FG     | 5.1kΩ, Pull-up resistor                                                                                                                                                             |
| R <sub>nFAULT</sub> | 1.8 to 5V Supply   | nFAULT | 5.1kΩ, Pull-up resistor                                                                                                                                                             |
| R <sub>SDA</sub>    | 1.8 to 3.3V Supply | SDA    | 5.1kΩ, Pull-up resistor                                                                                                                                                             |
| R <sub>SCL</sub>    | 1.8 to 3.3V Supply | SCL    | 5.1kΩ, Pull-up resistor                                                                                                                                                             |

Recommended application range for MCF8315D is shown in [Table 9-2](#).

**Table 9-2. Recommended Application Range**

| Parameter                                                 | Min   | Max  | Unit  |
|-----------------------------------------------------------|-------|------|-------|
| Motor voltage                                             | 4.5   | 35   | V     |
| Back-EMF constant (see <a href="#">Section 6.3.13.3</a> ) | 0.6   | 2000 | mV/Hz |
| Motor resistance (see <a href="#">Section 6.3.13.1</a> )  | 0.006 | 20   | Ω     |
| Motor inductance (see <a href="#">Section 6.3.13.2</a> )  | 0.006 | 20   | mH    |
| Motor electrical speed                                    | -     | 1500 | Hz    |
| Peak motor phase current                                  | -     | 4    | A     |

## 9.2.1 Application Curves

### 9.2.1.1 Motor startup

[Figure 9-2](#) shows the FG waveform and the phase current waveform at different motor operations.




**Figure 9-2. Motor Startup - FG and Phase current**

#### 9.2.1.2 MPET

Figure 9-3 shows the phase current waveform during motor parameter measurement. Figure 9-4 shows the IPD current waveform during R, L and  $K_e$  measurement. Bottom half of Figure 9-4 shows the IPD current waveform during R and L measurement. R is measured during the rising of phase current and L is measured during the falling of phase current. After R and L measurement, motor spins in open loop. Once the speed reaches MPET open loop speed reference [MPET\_OPEN\_LOOP\_SPEED\_REF], motor is coasted. BEMF voltage of all three phases are measured and  $K_e$  is calculated.




**Figure 9-3. MPET - Phase current**




**Figure 9-4. IPD current waveform during R and L measurement**

#### 9.2.1.3 Dead time compensation

Figure 9-5 shows the phase current waveform when dead time compensation is disabled. Fundamental frequency of phase current is 40 Hz. Fast Fourier transform (FFT) of phase current plot shows harmonics at

160 Hz and 220 Hz. [Figure 9-6](#) shows the phase current waveform when dead time compensation is enabled. Phase current looks more sinusoidal and the FFT of phase current plot does not have any harmonics.




**Figure 9-5. Phase current and FFT - Dead time compensation disabled**




**Figure 9-6. Phase current and FFT - Dead time compensation enabled**

#### 9.2.1.4 Auto handoff

[Figure 9-7](#) shows the auto handoff feature in MCF8315D where the motor transitions seamlessly from open loop to closed loop.




**Figure 9-7. Auto-handoff**

#### 9.2.1.5 Anti voltage surge (AVS)

When motor speed decelerates at a very high deceleration rate, mechanical energy from the motor returns to the power supply which could result in pumping up the supply voltage, VM. [Figure 9-8](#) shows overshoot in power supply voltage when AVS is disabled. Motor decelerates from 100% duty cycle to 10% duty cycle at a deceleration rate of 70,000 Hz/sec. [Figure 9-9](#) shows no overshoot in power supply voltage when AVS is enabled.




**Figure 9-8. Power supply voltage and phase current waveform when AVS is disabled**




**Figure 9-9. Power supply voltage and phase current waveform when AVS is enabled**

#### 9.2.1.6 Real time variable tracking using DACOUT

##### Note

DAC output(s) available in RGF and RRY packages only

MCF8315D has two 12-bit DAC which outputs analog voltage equivalent of digital variables on DACOUT1 and DACOUT2 pins with resolution of 12 bits and max voltage of 3V. Signals available on DACOUT pins can be used for tuning speed controller or other driver configuration or bus current monitoring. Check algorithm variable registers in datasheet for list of all algorithm variables.

The addresses for variables for DACOUT1 and DACOUT2 are configured using register bits DACOUT1\_VAR\_ADDR and DACOUT2\_VAR\_ADDR. This is useful in applications which require tracking algorithm variables in real time without having any delay from the communication bus. Pin 37 and 38 should be configured as DACOUT1 and DACOUT2.

For example, if the user wants to read phase A current from pin 37, configure pin 37 as DACOUT1 and program the phase A current register address (0x00000440) in Hex in [DACOUT1\_VAR\_ADDR]. If the user wants to read estimated rotor angle from pin 38, configure pin 38 as DACOUT2 and program the estimated rotor angle register address (0x00000736) in Hex in [DACOUT2\_VAR\_ADDR].

Figure 9-10 shows the outputs of DACOUT1 and DACOUT2. DACOUT1 is configured to read phase A current and DACOUT2 is configured to read estimated rotor angle.




Figure 9-10. DACOUT1 and DACOUT2

## 9.3 Power Supply Recommendations

### 9.3.1 Bulk Capacitance

Having an appropriate local bulk capacitance is an important factor in motor drive system design. It is generally beneficial to have more bulk capacitance, while the disadvantages are increased cost and physical size.

The amount of local capacitance needed depends on a variety of factors, including:

- The highest current required by the motor system
- The capacitance and current capability of the power supply
- The amount of parasitic inductance between the power supply and motor system
- The acceptable voltage ripple
- The type of motor used (brushed DC, brushless DC, stepper)
- The motor braking method

The inductance between the power supply and the motor drive system limits the rate at which current can change from the power supply. If the local bulk capacitance is too small, the system responds to excessive current demands or dumps from the motor with a change in VM voltage. When adequate bulk capacitance is used, the VM voltage remains stable and high current can be quickly supplied.

The data sheet generally provides a recommended value, but system-level testing is required to determine the appropriate bulk capacitor.




**Figure 9-11. Example Setup of Motor Drive System With External Power Supply**

The voltage rating for bulk capacitors should be higher than the operating voltage, to provide margin for cases when the motor transfers energy to the supply.

## 9.4 Layout

### 9.4.1 Layout Guidelines

The bulk capacitor should be placed to minimize the distance of the high-current path through the motor driver device. The connecting metal trace widths should be as wide as possible, and numerous vias should be used when connecting PCB layers. These practices minimize parasitic inductance and allow the bulk capacitor to deliver high current.

Small-value capacitors should be ceramic, and placed closely to device pins.

The high-current device outputs should use wide metal traces.

To reduce noise coupling and EMI interference from large transient currents into small-current signal paths, grounding should be partitioned between PGND and AGND. TI recommends connecting all non-power stage circuitry (including the thermal pad) to AGND to reduce parasitic effects and improve power dissipation from the device. Optionally, GND\_BK can be split. Ensure grounds are connected through net-ties or wide resistors to reduce voltage offsets and maintain gate driver performance.

The device thermal pad should be soldered to the PCB top-layer ground plane. Multiple vias should be used to connect to a large bottom-layer ground plane. The use of large metal planes and multiple vias helps dissipate the  $I^2 \times R_{DS(on)}$  heat that is generated in the device.

To improve thermal performance, maximize the ground area that is connected to the thermal pad ground across all possible layers of the PCB. Using thick copper pours can lower the junction-to-air thermal resistance and improve thermal dissipation from the die surface.

Separate the SW\_BK and FB\_BK traces with ground separation to reduce buck switching from coupling as noise into the buck outer feedback loop. Widen the FB\_BK trace as much as possible to allow for faster load switching.

Figure 9-12 shows a layout example for the MCF8315D . Also, for layout example, refer to [MCF8315D EVM](#) .

### 9.4.2 Layout Example




Figure 9-12. Recommended Layout Example (PWP)

### 9.4.3 Thermal Considerations

The MCF8315D has thermal shutdown (TSD) as previously described. A die temperature in excess of 150°C (minimally) disables the device until the temperature drops to a safe level.

Any tendency of the device to enter thermal shutdown is an indication of excessive power dissipation, insufficient heatsinking, or too high an ambient temperature.

#### 9.4.3.1 Power Dissipation

The power dissipated in the output FET resistance ( $R_{DS(on)}$ ) dominates power dissipation in MCF8315D.

At start-up and fault conditions, the FET current is much higher than normal operating FET current; remember to take these peak currents and their duration into consideration.

The total device power dissipation is the power dissipated in each of the three half-bridges added together along with standby power, LDO and buck regulator losses.

The maximum amount of power that the device can dissipate depends on ambient temperature and heatsinking.

Note that  $R_{DS(on)}$  increases with temperature, so as the device heats, the power dissipation increases. Take this into consideration when sizing the heatsink.

A summary of equations for calculating each loss is shown below in [Table 9-3](#).

**Table 9-3. Power Losses for MCF8315D**

| Loss type      | MCF8315D                                                                                                                                    |
|----------------|---------------------------------------------------------------------------------------------------------------------------------------------|
| Standby power  | $P_{standby} = V_M \times I_{VM\_TA}$                                                                                                       |
| LDO            | $P_{LDO} = (V_M - V_{AVDD}) \times I_{AVDD}$ , if BUCK_PS_DIS = 1b<br>$P_{LDO} = (V_{BK} - V_{AVDD}) \times I_{AVDD}$ , if BUCK_PS_DIS = 0b |
| FET conduction | $P_{CON} = 3 \times (I_{RMS(FOC)})^2 \times R_{ds,on(TA)}$                                                                                  |
| FET switching  | $P_{SW} = 3 \times I_{PK(FOC)} \times V_{PK(FOC)} \times t_{rise/fall} \times f_{PWM}$                                                      |
| Diode          | $P_{diode} = 3 \times I_{PK(FOC)} \times V_{diode} \times t_{dead} \times f_{PWM}$                                                          |
| Buck           | $P_{BK} = 0.11 \times V_{BK} \times I_{BK}$ ( $\eta_{BK} = 90\%$ )                                                                          |

## 10 Device and Documentation Support

### 10.1 Support Resources

[TI E2E™ support forums](#) are an engineer's go-to source for fast, verified answers and design help — straight from the experts. Search existing answers or ask your own question to get the quick design help you need.

Linked content is provided "AS IS" by the respective contributors. They do not constitute TI specifications and do not necessarily reflect TI's views; see TI's [Terms of Use](#).

### 10.2 Trademarks

TI E2E™ is a trademark of Texas Instruments.

All trademarks are the property of their respective owners.

### 10.3 Electrostatic Discharge Caution



This integrated circuit can be damaged by ESD. Texas Instruments recommends that all integrated circuits be handled with appropriate precautions. Failure to observe proper handling and installation procedures can cause damage.

ESD damage can range from subtle performance degradation to complete device failure. Precision integrated circuits may be more susceptible to damage because very small parametric changes could cause the device not to meet its published specifications.

### 10.4 Glossary

[TI Glossary](#) This glossary lists and explains terms, acronyms, and definitions.

## 11 Revision History

| DATE        | REVISION | NOTES           |
|-------------|----------|-----------------|
| August 2023 | *        | Initial Release |

## 12 Mechanical, Packaging, and Orderable Information

The following pages include mechanical, packaging, and orderable information. This information is the most-current data available for the designated device. This data is subject to change without notice and without revision of this document. For browser-based versions of this data sheet, see the left-hand navigation pane.

PACKAGING INFORMATION

| Orderable part number | Status<br>(1) | Material type<br>(2) | Package   Pins    | Package qty   Carrier | RoHS<br>(3) | Lead finish/<br>Ball material<br>(4) | MSL rating/<br>Peak reflow<br>(5) | Op temp (°C) | Part marking<br>(6) |
|-----------------------|---------------|----------------------|-------------------|-----------------------|-------------|--------------------------------------|-----------------------------------|--------------|---------------------|
| MCF8315DVPWPR         | Active        | Production           | HTSSOP (PWP)   24 | 2000   LARGE T&R      | Yes         | NIPDAU                               | Level-3-260C-168 HR               | -40 to 125   | MCF15DV             |
| MCF8315DVPWPR.A       | Active        | Production           | HTSSOP (PWP)   24 | 2000   LARGE T&R      | Yes         | NIPDAU                               | Level-3-260C-168 HR               | -40 to 125   | MCF15DV             |


- <sup>(1)</sup> **Status:** For more details on status, see our [product life cycle](#).
- <sup>(2)</sup> **Material type:** When designated, preproduction parts are prototypes/experimental devices, and are not yet approved or released for full production. Testing and final process, including without limitation quality assurance, reliability performance testing, and/or process qualification, may not yet be complete, and this item is subject to further changes or possible discontinuation. If available for ordering, purchases will be subject to an additional waiver at checkout, and are intended for early internal evaluation purposes only. These items are sold without warranties of any kind.
- <sup>(3)</sup> **RoHS values:** Yes, No, RoHS Exempt. See the [TI RoHS Statement](#) for additional information and value definition.
- <sup>(4)</sup> **Lead finish/Ball material:** Parts may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead finish/Ball material values may wrap to two lines if the finish value exceeds the maximum column width.
- <sup>(5)</sup> **MSL rating/Peak reflow:** The moisture sensitivity level ratings and peak solder (reflow) temperatures. In the event that a part has multiple moisture sensitivity ratings, only the lowest level per JEDEC standards is shown. Refer to the shipping label for the actual reflow temperature that will be used to mount the part to the printed circuit board.
- <sup>(6)</sup> **Part marking:** There may be an additional marking, which relates to the logo, the lot trace code information, or the environmental category of the part.

Multiple part markings will be inside parentheses. Only one part marking contained in parentheses and separated by a "~" will appear on a part. If a line is indented then it is a continuation of the previous line and the two combined represent the entire part marking for that device.

**Important Information and Disclaimer:**The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.


## TAPE AND REEL INFORMATION



\*All dimensions are nominal

| Device        | Package Type | Package Drawing | Pins | SPQ  | Reel Diameter (mm) | Reel Width W1 (mm) | A0 (mm) | B0 (mm) | K0 (mm) | P1 (mm) | W (mm) | Pin1 Quadrant |
|---------------|--------------|-----------------|------|------|--------------------|--------------------|---------|---------|---------|---------|--------|---------------|
| MCF8315DVPWPR | HTSSOP       | PWP             | 24   | 2000 | 330.0              | 16.4               | 6.95    | 8.3     | 1.6     | 8.0     | 16.0   | Q1            |

## TAPE AND REEL BOX DIMENSIONS



\*All dimensions are nominal

| Device        | Package Type | Package Drawing | Pins | SPQ  | Length (mm) | Width (mm) | Height (mm) |
|---------------|--------------|-----------------|------|------|-------------|------------|-------------|
| MCF8315DVPWPR | HTSSOP       | PWP             | 24   | 2000 | 350.0       | 350.0      | 43.0        |

## GENERIC PACKAGE VIEW


**PWP 24**

**PowerPAD™ TSSOP - 1.2 mm max height**


4.4 x 7.6, 0.65 mm pitch

PLASTIC SMALL OUTLINE

This image is a representation of the package family, actual package may vary.  
Refer to the product data sheet for package details.




4224742/B



## PACKAGE OUTLINE

## PowerPAD™ TSSOP - 1.2 mm max height

## SMALL OUTLINE PACKAGE



NOTES:

---

PowerPAD is a trademark of Texas Instruments.


1. All linear dimensions are in millimeters. Any dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.
2. This drawing is subject to change without notice.
3. This dimension does not include mold flash, protrusions, or gate burrs. Mold flash, protrusions, or gate burrs shall not exceed 0.15 mm per side.
4. Reference JEDEC registration MO-153.
5. Features may differ or may not be present.

# EXAMPLE BOARD LAYOUT


PWP0024J

PowerPAD™ TSSOP - 1.2 mm max height


SMALL OUTLINE PACKAGE



LAND PATTERN EXAMPLE  
EXPOSED METAL SHOWN  
SCALE: 8X



NON-SOLDER MASK  
DEFINED



SOLDER MASK  
DEFINED

SOLDER MASK DETAILS

4225860/A 04/2020

NOTES: (continued)


6. Publication IPC-7351 may have alternate designs.
7. Solder mask tolerances between and around signal pads can vary based on board fabrication site.
8. This package is designed to be soldered to a thermal pad on the board. For more information, see Texas Instruments literature numbers SLMA002 ([www.ti.com/lit/slma002](http://www.ti.com/lit/slma002)) and SLMA004 ([www.ti.com/lit/slma004](http://www.ti.com/lit/slma004)).
9. Size of metal pad may vary due to creepage requirement.
10. Vias are optional depending on application, refer to device data sheet. It is recommended that vias under paste be filled, plugged or tented.

# EXAMPLE STENCIL DESIGN

PWP0024J

PowerPAD™ TSSOP - 1.2 mm max height

SMALL OUTLINE PACKAGE



**SOLDER PASTE EXAMPLE**  
BASED ON 0.125 mm THICK STENCIL  
SCALE: 8X

| STENCIL THICKNESS | SOLDER STENCIL OPENING |
|-------------------|------------------------|
| 0.1               | 3.58 X 5.88            |
| 0.125             | 3.20 X 5.26 (SHOWN)    |
| 0.15              | 2.92 X 4.80            |
| 0.175             | 2.70 X 4.45            |

4225860/A 04/2020

NOTES: (continued)

11. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.
12. Board assembly site may have different recommendations for stencil design.

## IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATASHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, regulatory or other requirements.

These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you fully indemnify TI and its representatives against any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to [TI's Terms of Sale](#), [TI's General Quality Guidelines](#), or other applicable terms available either on [ti.com](http://ti.com) or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products. Unless TI explicitly designates a product as custom or customer-specified, TI products are standard, catalog, general purpose devices.

TI objects to and rejects any additional or different terms you may propose.

Copyright © 2026, Texas Instruments Incorporated

Last updated 10/2025