

SN74AHC244-Q1 Automotive Octal Buffer/Driver with 3-State Outputs

1 Features

- Qualified for automotive applications
- EPIC™ (Enhanced-Performance Implanted CMOS) Process
- Operating range of 2V to 5.5V V_{CC}

2 Description

The SN74AHC244-Q1 contains one inverter gate. The device performs the Boolean function $Y = \bar{A}$.

Package Information

| PART NUMBER | PACKAGE ⁽¹⁾ | PACKAGE SIZE ⁽²⁾ | BODY SIZE ⁽³⁾ |
|---------------|------------------------|-----------------------------|--------------------------|
| SN74AHC244-Q1 | DW (SOIC, 20) | 12.80mm × 10.3mm | 12.8mm × 7.5mm |
| | PW (TSSOP, 20) | 6.50mm × 6.4mm | 6.50mm × 4.40mm |

- (1) For more information, see [Mechanical, Packaging, and Orderable Information](#).
- (2) The package size (length × width) is a nominal value and includes pins, where applicable.
- (3) The body size (length × width) is a nominal value and does not include pins.



Simplified Schematic



Table of Contents

| | | | |
|--|----------|--|-----------|
| 1 Features | 1 | 6.2 Functional Block Diagram..... | 8 |
| 2 Description | 1 | 6.3 Device Functional Modes..... | 9 |
| 3 Pin Configuration and Functions | 3 | 7 Application and Implementation | 10 |
| 4 Specifications | 4 | 7.1 Power Supply Recommendations..... | 10 |
| 4.1 Absolute Maximum Ratings..... | 4 | 7.2 Layout..... | 10 |
| 4.2 ESD Ratings..... | 4 | 7.3 Layout Example..... | 10 |
| 4.3 Recommended Operating Conditions..... | 4 | 8 Device and Documentation Support | 11 |
| 4.4 Thermal Information..... | 5 | 8.1 Documentation Support..... | 11 |
| 4.5 Electrical Characteristics..... | 5 | 8.2 Receiving Notification of Documentation Updates.... | 11 |
| 4.6 Switching Characteristics..... | 5 | 8.3 Support Resources..... | 11 |
| 4.7 Switching Characteristics..... | 6 | 8.4 Trademarks..... | 11 |
| 4.8 Noise Characteristics..... | 6 | 8.5 Electrostatic Discharge Caution..... | 11 |
| 4.9 Operating Characteristics..... | 6 | 8.6 Glossary..... | 11 |
| 5 Parameter Measurement Information | 7 | 9 Revision History | 11 |
| 6 Detailed Description | 8 | 10 Mechanical, Packaging, and Orderable Information | 12 |
| 6.1 Overview..... | 8 | | |

3 Pin Configuration and Functions




Figure 3-1. DW or PW Package, 20-Pin SOIC or TSSOP (Top View)

Table 3-1. Pin Functions

| PIN | | I/O | DESCRIPTION |
|-----|-------------------|-----|-----------------|
| NO. | NAME | | |
| 1 | 1 \overline{OE} | I | Output Enable 1 |
| 2 | 1A1 | I | 1A1 Input |
| 3 | 2Y4 | O | 2Y4 Output |
| 4 | 1A2 | I | 1A2 Input |
| 5 | 2Y3 | O | 2Y3 Output |
| 6 | 1A3 | I | 1A3 Input |
| 7 | 2Y2 | O | 2Y2 Output |
| 8 | 1A4 | I | 1A4 Input |
| 9 | 2Y1 | O | 2Y1 Output |
| 10 | GND | — | Ground pin |
| 11 | 2A1 | I | 2A1 Input |
| 12 | 1Y4 | O | 1Y4 Output |
| 13 | 2A2 | I | 2A2 Input |
| 14 | 1Y3 | O | 1Y3 Output |
| 15 | 2A3 | I | 2A3 Input |
| 16 | 1Y2 | O | 1Y2 Output |
| 17 | 2A4 | I | 2A4 Input |
| 18 | 1Y1 | O | 1Y1 Output |
| 19 | 2 \overline{OE} | I | Output Enable 2 |
| 20 | VCC | — | Power Pin |

4 Specifications

4.1 Absolute Maximum Ratings

over operating free-air temperature range (unless otherwise noted)⁽¹⁾

| | | MIN | MAX | UNIT |
|-----------------------------|---|---|-----------------------|------|
| V _{CC} | Supply voltage range | -0.5 | 7 | V |
| V _I ² | Input voltage range | -0.5 | 7 | V |
| V _O ² | Output voltage range | -0.5 | V _{CC} + 0.5 | V |
| I _{IK} | Input clamp current | (V _I < 0) | -20 | mA |
| I _{OK} | Output clamp current | (V _O < 0 or V _O > V _{CC}) | ±20 | mA |
| I _O | Continuous output current | (V _O = 0 to V _{CC}) | ±25 | mA |
| | Continuous current through V _{CC} or GND | | ±50 | mA |
| T _{stg} | Storage temperature range | -65 | 150 | °C |

- (1) Stresses beyond those listed under “absolute maximum ratings” may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated under “recommended operating conditions” is not implied. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability.
- (2) The input and output voltage ratings may be exceeded if the input and output current ratings are observed.

4.2 ESD Ratings

| | | | | VALUE | UNIT |
|--------------------|-------------------------|---|----------|-------|------|
| V _(ESD) | Electrostatic discharge | Human body model (HBM), per AEC Q100-002 ¹ | All pins | ±1500 | V |

4.3 Recommended Operating Conditions

over operating free-air temperature range (unless otherwise noted)¹

| | | MIN | MAX | UNIT |
|-----------------|------------------------------------|---------------------------------|-----------------|------|
| V _{CC} | Supply voltage | 2 | 5.5 | V |
| V _{IH} | High-level input voltage | V _{CC} = 2 V | 1.5 | V |
| | | V _{CC} = 3 V | 2.1 | |
| | | V _{CC} = 5.5 V | 3.85 | |
| V _{IL} | Low-level input voltage | V _{CC} = 2 V | 0.5 | V |
| | | V _{CC} = 3 V | 0.9 | |
| | | V _{CC} = 5.5 V | 1.65 | |
| V _I | Input voltage | 0 | 5.5 | V |
| V _O | Output voltage | 0 | V _{CC} | V |
| I _{OH} | High-level output current | V _{CC} = 2 V | -50 | μA |
| | | V _{CC} = 3.3 V ± 0.3 V | -4 | mA |
| | | V _{CC} = 5 V ± 0.5 V | -8 | |
| I _{OL} | Low-level output current | V _{CC} = 2 V | 50 | mA |
| | | V _{CC} = 3.3 V ± 0.3 V | 4 | mA |
| | | V _{CC} = 5 V ± 0.5 V | 8 | |
| Δt/Δv | Input transition rise or fall rate | V _{CC} = 3.3 V ± 0.3 V | 100 | ns/V |
| | | V _{CC} = 5 V ± 0.5 V | 20 | |
| T _A | Operating free-air temperature | -40 | 125 | °C |

- (1) All unused inputs of the device must be held at V_{CC} or GND for proper device operation. Refer to the TI application report, *Implications of Slow or Floating CMOS Inputs*, literature number SCBA004.

4.4 Thermal Information

| THERMAL METRIC ⁽¹⁾ | SN74AHC244-Q1 | | UNIT |
|--|---------------|---------|------|
| | DW | PW | |
| | 20 PINS | 20 PINS | |
| $R_{\theta JA}$ Junction-to-ambient thermal resistance | 81.1 | 116.8 | °C/W |

(1) For more information about traditional and new thermal metrics, see the *IC Package Thermal Metrics* application report, [SPRA953](#).

4.5 Electrical Characteristics

over recommended operating free-air temperature range (unless otherwise noted)

| PARAMETER | TEST CONDITIONS | V_{CC} | $T_A = 25^\circ\text{C}$ | | | MIN | MAX | UNIT |
|-----------|---|--------------|--------------------------|-----|------------|------|-----------|---------------|
| | | | MIN | TYP | MAX | | | |
| V_{OH} | $I_{OH} = -50\ \mu\text{A}$ | 2 V | 1.9 | 2 | | 1.9 | | V |
| | | 3 V | 2.9 | 3 | | 2.9 | | |
| | | 4.5 V | 4.4 | 4.5 | | 4.4 | | |
| | $I_{OH} = -4\ \text{mA}$ | 3 V | 2.58 | | | 2.48 | | |
| | $I_{OH} = -8\ \text{mA}$ | 4.5 V | 3.94 | | | 3.8 | | |
| V_{OL} | $I_{OL} = 50\ \mu\text{A}$ | 2 V | | | 0.1 | | 0.1 | V |
| | | 3 V | | | 0.1 | | 0.1 | |
| | | 4.5 V | | | 0.1 | | 0.1 | |
| | $I_{OL} = 4\ \text{mA}$ | 3 V | | | 0.36 | | 0.5 | |
| | $I_{OL} = 8\ \text{mA}$ | 4.5 V | | | 0.36 | | 0.5 | |
| I_I | $V_I = 5.5\ \text{V}$ or GND | 0 V to 5.5 V | | | ± 0.1 | | ± 1 | μA |
| I_{OZ} | $V_O = V_{CC}$ or GND, $V_I (\overline{OE}) = V_{IL}$ or V_{IH} | 5.5 V | | | ± 0.25 | | ± 2.5 | μA |
| I_{CC} | $V_I = V_{CC}$ or GND, $I_O = 0$ | 5.5 V | | | 4 | | 40 | μA |
| C_i | $V_I = V_{CC}$ or GND | 5 V | | 2 | 10 | | | pF |
| C_o | $V_O = V_{CC}$ or GND | 5 V | | 3.5 | | | | pF |

4.6 Switching Characteristics

over recommended operating free-air temperature range, $V_{CC} = 3.3\ \text{V} \pm 0.3\ \text{V}$ (unless otherwise noted) (see [Load Circuit and Voltage Waveforms](#))

| PARAMETER | FROM (INPUT) | TO (OUTPUT) | LOAD CAPACITANCE | $T_A = 25^\circ\text{C}$ | | | MIN | MAX | UNIT |
|-----------|-----------------|-------------|-----------------------|--------------------------|------|------|-----|------|------|
| | | | | MIN | TYP | MAX | | | |
| t_{PLH} | A | Y | $C_L = 15\ \text{pF}$ | | 5.8 | 8.4 | 1 | 10 | ns |
| t_{PHL} | | | | | 5.8 | 8.4 | 1 | 10 | |
| t_{PZH} | \overline{OE} | Y | $C_L = 15\ \text{pF}$ | | 6.6 | 10.6 | 1 | 12.5 | ns |
| t_{PZL} | | | | | 6.6 | 10.6 | 1 | 12.5 | |
| t_{PHZ} | \overline{OE} | Y | $C_L = 15\ \text{pF}$ | | 5 | 9.7 | 1 | 11 | ns |
| t_{PLZ} | | | | | 5 | 9.7 | 1 | 11 | |
| t_{PLH} | A | Y | $C_L = 50\ \text{pF}$ | | 8.3 | 11.9 | 1 | 13.5 | ns |
| t_{PHL} | | | | | 8.3 | 11.9 | 1 | 13.5 | |
| t_{PZH} | \overline{OE} | Y | $C_L = 50\ \text{pF}$ | | 9.1 | 14.1 | 1 | 16 | ns |
| t_{PZL} | | | | | 9.1 | 14.1 | 1 | 16 | |
| t_{PHZ} | \overline{OE} | Y | $C_L = 50\ \text{pF}$ | | 10.3 | 14 | 1 | 16 | ns |
| t_{PLZ} | | | | | 10.3 | 14 | 1 | 16 | |

4.7 Switching Characteristics

over recommended operating free-air temperature range, $V_{CC} = 5\text{ V} \pm 0.5\text{ V}$ (unless otherwise noted) (see [Load Circuit and Voltage Waveforms](#))

| PARAMETER | FROM (INPUT) | TO (OUTPUT) | LOAD CAPACITANCE | $T_A = 25^\circ\text{C}$ | | | MIN | MAX | UNIT |
|-----------|-----------------|-------------|----------------------|--------------------------|-----|-----|-----|------|------|
| | | | | MIN | TYP | MAX | | | |
| t_{PLH} | A | Y | $C_L = 15\text{ pF}$ | 3.9 | 5.5 | | 1 | 6.5 | ns |
| t_{PHL} | | | | 3.9 | 5.5 | | 1 | 6.5 | |
| t_{PZH} | \overline{OE} | Y | $C_L = 15\text{ pF}$ | 4.7 | 7.3 | | 1 | 8.5 | ns |
| t_{PZL} | | | | 4.7 | 7.3 | | 1 | 8.5 | |
| t_{PHZ} | \overline{OE} | Y | $C_L = 15\text{ pF}$ | 5 | 7.2 | | 1 | 8.5 | ns |
| t_{PLZ} | | | | 5 | 7.2 | | 1 | 8.5 | |
| t_{PLH} | A | Y | $C_L = 50\text{ pF}$ | 5.4 | 7.5 | | 1 | 8.5 | ns |
| t_{PHL} | | | | 5.4 | 7.5 | | 1 | 8.5 | |
| t_{PZH} | \overline{OE} | Y | $C_L = 50\text{ pF}$ | 6.2 | 9.3 | | 1 | 10.5 | ns |
| t_{PZL} | | | | 6.2 | 9.3 | | 1 | 10.5 | |
| t_{PHZ} | \overline{OE} | Y | $C_L = 50\text{ pF}$ | 6.7 | 9.2 | | 1 | 10.5 | ns |
| t_{PLZ} | | | | 6.7 | 9.2 | | 1 | 10.5 | |

4.8 Noise Characteristics

$V_{CC} = 5\text{ V}$, $C_L = 50\text{ pF}$, $T_A = 25^\circ\text{C}$ ⁽¹⁾

| PARAMETER | | MIN | TYP | MAX | UNIT |
|-------------|--|-----|------|-----|------|
| $V_{OL(P)}$ | Quiet output, maximum dynamic V_{OL} | | 0.5 | | V |
| $V_{OL(V)}$ | Quiet output, minimum dynamic V_{OL} | | -0.2 | | V |
| $V_{OH(V)}$ | Quiet output, minimum dynamic V_{OH} | | 4.8 | | V |
| $V_{IH(D)}$ | High-level dynamic input voltage | 3.5 | | | V |
| $V_{IL(D)}$ | Low-level dynamic input voltage | | | 1.5 | V |


(1) Characteristics are for surface-mount packages only.

4.9 Operating Characteristics

$V_{CC} = 5\text{ V}$, $T_A = 25^\circ\text{C}$

| PARAMETER | | TEST CONDITIONS | | TYP | UNIT |
|-----------|-------------------------------|-----------------|--------------------|-----|------|
| C_{pd} | Power dissipation capacitance | No load, | $f = 1\text{ MHz}$ | 8.6 | pF |

5 Parameter Measurement Information



- A. C_L includes probe and jig capacitance.
- B. Waveform 1 is for an output with internal conditions such that the output is low except when disabled by the output control. Waveform 2 is for an output with internal conditions such that the output is high except when disabled by the output control.
- C. All input pulses are supplied by generators having the following characteristics: $PRR \leq 1$ MHz, $Z_O = 50 \Omega$, $t_r \leq 3$ ns, $t_f \leq 3$ ns.
- D. The outputs are measured one at a time with one input transition per measurement.

Figure 5-1. Load Circuit and Voltage Waveforms

| TEST | S1 |
|-------------------|----------|
| t_{PLH}/t_{PHL} | Open |
| t_{PLZ}/t_{PZL} | V_{CC} |
| t_{PHZ}/t_{PZH} | GND |
| Open Drain | V_{CC} |

6 Detailed Description

6.1 Overview

This octal buffer/driver is designed specifically to improve the performance and density of 3-state memory-address drivers, clock drivers, and bus-oriented receivers and transmitters.

The SN74AHC244 is organized as two 4-bit buffers/line drivers with separate output-enable (\overline{OE}) inputs. When \overline{OE} is low, the device passes data from the A inputs to the Y outputs. When \overline{OE} is high, the outputs are in the high-impedance state.

For the specified high-impedance state during power up or power down, \overline{OE} must be tied to V_{CC} through a pullup resistor; the minimum value of the resistor is determined by the current-sinking capability of the driver.

6.2 Functional Block Diagram





Figure 6-1. Logic Diagram (Positive Logic)



This symbol is in accordance with ANSI/IEEE Std 91-1984 and IEC Publication 617-12.

Figure 6-2. Logic Symbol

6.3 Device Functional Modes

**Table 6-1. (Each 4-Bit
Buffer/Driver)**

| INPUTS | | OUTPUT Y |
|-----------------|---|----------|
| \overline{OE} | A | |
| L | H | H |
| L | L | L |
| H | X | Z |

7 Application and Implementation

Note

Information in the following applications sections is not part of the TI component specification, and TI does not warrant its accuracy or completeness. TI's customers are responsible for determining suitability of components for their purposes, as well as validating and testing their design implementation to confirm system functionality.

7.1 Power Supply Recommendations

The power supply can be any voltage between the MIN and MAX supply voltage rating located in the [Recommended Operating Conditions](#) table.

Each VCC pin should have a good bypass capacitor to prevent power disturbance. For devices with a single supply, 0.1 μF is recommended; if there are multiple VCC pins, then 0.01 μF or 0.022 μF is recommended for each power pin. It is acceptable to parallel multiple bypass caps to reject different frequencies of noise. A 0.1 μF and a 1 μF are commonly used in parallel. The bypass capacitor should be installed as close to the power pin as possible for best results.

7.2 Layout

7.2.1 Layout Guidelines

When using multiple-bit logic devices, inputs should never float.

In many cases, functions or parts of functions of digital logic devices are unused, for example, when only two inputs of a triple-input AND gate are used or only 3 of the 4 buffer gates are used. Such input pins should not be left unconnected because the undefined voltages at the outside connections result in undefined operational states. [Section 7.3](#) specifies the rules that must be observed under all circumstances. All unused inputs of digital logic devices must be connected to a high or low bias to prevent them from floating. The logic level that should be applied to any particular unused input depends on the function of the device. Generally they will be tied to GND or V_{CC} , whichever makes more sense or is more convenient. It is generally acceptable to float outputs, unless the part is a transceiver. If the transceiver has an output enable pin, it will disable the output section of the part when asserted. This will not disable the input section of the I/Os, so they cannot float when disabled.

7.3 Layout Example




Figure 7-1. Layout Diagram

8 Device and Documentation Support

8.1 Documentation Support

8.1.1 Related Documentation

The table below lists quick access links. Categories include technical documents, support and community resources, tools and software, and quick access to sample or buy.

Table 8-1. Related Links

| PARTS | PRODUCT FOLDER | SAMPLE & BUY | TECHNICAL DOCUMENTS | TOOLS & SOFTWARE | SUPPORT & COMMUNITY |
|---------------|----------------------------|----------------------------|----------------------------|----------------------------|----------------------------|
| SN74AHC244-Q1 | Click here | Click here | Click here | Click here | Click here |

8.2 Receiving Notification of Documentation Updates

To receive notification of documentation updates, navigate to the device product folder on [ti.com](#). Click on *Notifications* to register and receive a weekly digest of any product information that has changed. For change details, review the revision history included in any revised document.

8.3 Support Resources

[TI E2E™ support forums](#) are an engineer's go-to source for fast, verified answers and design help — straight from the experts. Search existing answers or ask your own question to get the quick design help you need.

Linked content is provided "AS IS" by the respective contributors. They do not constitute TI specifications and do not necessarily reflect TI's views; see TI's [Terms of Use](#).

8.4 Trademarks

TI E2E™ is a trademark of Texas Instruments.
All trademarks are the property of their respective owners.

8.5 Electrostatic Discharge Caution



This integrated circuit can be damaged by ESD. Texas Instruments recommends that all integrated circuits be handled with appropriate precautions. Failure to observe proper handling and installation procedures can cause damage.

ESD damage can range from subtle performance degradation to complete device failure. Precision integrated circuits may be more susceptible to damage because very small parametric changes could cause the device not to meet its published specifications.

8.6 Glossary

[TI Glossary](#) This glossary lists and explains terms, acronyms, and definitions.

9 Revision History

NOTE: Page numbers for previous revisions may differ from page numbers in the current version.

| Changes from Revision B (August 2023) to Revision C (July 2024) | Page |
|--|--------------------|
| • Updated packages and added body size to <i>Package Information</i> table..... | 1 |
| • Updated RθJA values: PW = 83 to 116.8, DW = 58 to 81.1, all values in °C/W | 5 |
| • Added <i>Application and Implementation</i> section..... | 10 |

| Changes from Revision A (April 2008) to Revision B (August 2023) | Page |
|---|-------------------|
| • Added <i>Package Information</i> table, <i>Pin Functions</i> table, <i>ESD Ratings</i> table, <i>Thermal Information</i> table, <i>Device Functional Modes</i> , <i>Device and Documentation Support</i> section, and <i>Mechanical, Packaging, and Orderable Information</i> section | 1 |

10 Mechanical, Packaging, and Orderable Information

The following pages include mechanical, packaging, and orderable information. This information is the most current data available for the designated devices. This data is subject to change without notice and revision of this document. For browser-based versions of this data sheet, refer to the left-hand navigation.

PACKAGING INFORMATION

| Orderable part number | Status (1) | Material type (2) | Package Pins | Package qty Carrier | RoHS (3) | Lead finish/ Ball material (4) | MSL rating/ Peak reflow (5) | Op temp (°C) | Part marking (6) |
|------------------------------------|---------------|----------------------|------------------|-----------------------|-------------|--------------------------------------|-----------------------------------|--------------|---------------------|
| SN74AHC244QDGSRQ1 | Active | Production | VSSOP (DGS) 20 | 5000 LARGE T&R | Yes | NIPDAU | Level-1-260C-UNLIM | -40 to 125 | HA244Q |
| SN74AHC244QDWRQ1 | Active | Production | SOIC (DW) 20 | 2000 LARGE T&R | Yes | NIPDAU | Level-1-260C-UNLIM | -40 to 125 | AHC244Q1 |
| SN74AHC244QDWRQ1.A | Active | Production | SOIC (DW) 20 | 2000 LARGE T&R | Yes | NIPDAU | Level-1-260C-UNLIM | -40 to 125 | AHC244Q1 |
| SN74AHC244QPWRG4Q1 | Active | Production | TSSOP (PW) 20 | 2000 LARGE T&R | Yes | NIPDAU | Level-1-260C-UNLIM | -40 to 125 | AHC244Q1 |
| SN74AHC244QPWRG4Q1.A | Active | Production | TSSOP (PW) 20 | 2000 LARGE T&R | Yes | NIPDAU | Level-1-260C-UNLIM | -40 to 125 | AHC244Q1 |
| SN74AHC244QPWRQ1 | Active | Production | TSSOP (PW) 20 | 2000 LARGE T&R | Yes | NIPDAU | Level-1-260C-UNLIM | -40 to 125 | (AHC244, AHC244Q1) |
| SN74AHC244QPWRQ1.A | Active | Production | TSSOP (PW) 20 | 2000 LARGE T&R | Yes | NIPDAU | Level-1-260C-UNLIM | -40 to 125 | (AHC244, AHC244Q1) |
| SN74AHC244QWRKSRQ1 | Active | Production | VQFN (RKS) 20 | 3000 LARGE T&R | Yes | NIPDAU | Level-1-260C-UNLIM | -40 to 125 | AHC244Q |

(1) **Status:** For more details on status, see our [product life cycle](#).

(2) **Material type:** When designated, preproduction parts are prototypes/experimental devices, and are not yet approved or released for full production. Testing and final process, including without limitation quality assurance, reliability performance testing, and/or process qualification, may not yet be complete, and this item is subject to further changes or possible discontinuation. If available for ordering, purchases will be subject to an additional waiver at checkout, and are intended for early internal evaluation purposes only. These items are sold without warranties of any kind.

(3) **RoHS values:** Yes, No, RoHS Exempt. See the [TI RoHS Statement](#) for additional information and value definition.

(4) **Lead finish/Ball material:** Parts may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead finish/Ball material values may wrap to two lines if the finish value exceeds the maximum column width.

(5) **MSL rating/Peak reflow:** The moisture sensitivity level ratings and peak solder (reflow) temperatures. In the event that a part has multiple moisture sensitivity ratings, only the lowest level per JEDEC standards is shown. Refer to the shipping label for the actual reflow temperature that will be used to mount the part to the printed circuit board.

(6) **Part marking:** There may be an additional marking, which relates to the logo, the lot trace code information, or the environmental category of the part.

Multiple part markings will be inside parentheses. Only one part marking contained in parentheses and separated by a "~" will appear on a part. If a line is indented then it is a continuation of the previous line and the two combined represent the entire part marking for that device.

Important Information and Disclaimer: The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative

and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.

OTHER QUALIFIED VERSIONS OF SN74AHC244-Q1 :

- Catalog : [SN74AHC244](#)
- Enhanced Product : [SN74AHC244-EP](#)
- Military : [SN54AHC244](#)

NOTE: Qualified Version Definitions:

- Catalog - TI's standard catalog product
- Enhanced Product - Supports Defense, Aerospace and Medical Applications
- Military - QML certified for Military and Defense Applications

TAPE AND REEL INFORMATION



*All dimensions are nominal

| Device | Package Type | Package Drawing | Pins | SPQ | Reel Diameter (mm) | Reel Width W1 (mm) | A0 (mm) | B0 (mm) | K0 (mm) | P1 (mm) | W (mm) | Pin1 Quadrant |
|--------------------|--------------|-----------------|------|------|--------------------|--------------------|---------|---------|---------|---------|--------|---------------|
| SN74AHC244QDGSRQ1 | VSSOP | DGS | 20 | 5000 | 330.0 | 16.4 | 5.4 | 5.4 | 1.45 | 8.0 | 16.0 | Q1 |
| SN74AHC244QDWRQ1 | SOIC | DW | 20 | 2000 | 330.0 | 24.4 | 10.8 | 13.3 | 2.7 | 12.0 | 24.0 | Q1 |
| SN74AHC244QPWRG4Q1 | TSSOP | PW | 20 | 2000 | 330.0 | 16.4 | 6.95 | 7.0 | 1.4 | 8.0 | 16.0 | Q1 |
| SN74AHC244QPWRG4Q1 | TSSOP | PW | 20 | 2000 | 330.0 | 16.4 | 6.95 | 7.0 | 1.4 | 8.0 | 16.0 | Q1 |
| SN74AHC244QPWRQ1 | TSSOP | PW | 20 | 2000 | 330.0 | 16.4 | 6.95 | 7.0 | 1.4 | 8.0 | 16.0 | Q1 |
| SN74AHC244QWRKSRQ1 | VQFN | RKS | 20 | 3000 | 180.0 | 12.4 | 2.8 | 4.8 | 1.2 | 4.0 | 12.0 | Q1 |

TAPE AND REEL BOX DIMENSIONS



*All dimensions are nominal

| Device | Package Type | Package Drawing | Pins | SPQ | Length (mm) | Width (mm) | Height (mm) |
|--------------------|--------------|-----------------|------|------|-------------|------------|-------------|
| SN74AHC244QDGSRQ1 | VSSOP | DGS | 20 | 5000 | 353.0 | 353.0 | 32.0 |
| SN74AHC244QDWRQ1 | SOIC | DW | 20 | 2000 | 356.0 | 356.0 | 45.0 |
| SN74AHC244QPWRG4Q1 | TSSOP | PW | 20 | 2000 | 353.0 | 353.0 | 32.0 |
| SN74AHC244QPWRG4Q1 | TSSOP | PW | 20 | 2000 | 353.0 | 353.0 | 32.0 |
| SN74AHC244QPWRQ1 | TSSOP | PW | 20 | 2000 | 353.0 | 353.0 | 32.0 |
| SN74AHC244QWRKSRQ1 | VQFN | RKS | 20 | 3000 | 210.0 | 185.0 | 35.0 |



4220724/A 05/2016

NOTES:

1. All linear dimensions are in millimeters. Dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.
2. This drawing is subject to change without notice.
3. This dimension does not include mold flash, protrusions, or gate burrs. Mold flash, protrusions, or gate burrs shall not exceed 0.15 mm per side.
4. This dimension does not include interlead flash. Interlead flash shall not exceed 0.43 mm per side.
5. Reference JEDEC registration MS-013.

EXAMPLE BOARD LAYOUT

DW0020A

SOIC - 2.65 mm max height

SOIC



LAND PATTERN EXAMPLE
SCALE:6X



SOLDER MASK DETAILS

4220724/A 05/2016

NOTES: (continued)

6. Publication IPC-7351 may have alternate designs.

7. Solder mask tolerances between and around signal pads can vary based on board fabrication site.

EXAMPLE STENCIL DESIGN

DW0020A

SOIC - 2.65 mm max height

SOIC



SOLDER PASTE EXAMPLE
BASED ON 0.125 mm THICK STENCIL
SCALE:6X

4220724/A 05/2016

NOTES: (continued)

8. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.
9. Board assembly site may have different recommendations for stencil design.



TSSOP - 1.2 mm max height

SMALL OUTLINE PACKAGE



1. All linear dimensions are in millimeters. Any dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.
2. This drawing is subject to change without notice.
3. This dimension does not include mold flash, protrusions, or gate burrs. Mold flash, protrusions, or gate burrs shall not exceed 0.15 mm per side.
4. This dimension does not include interlead flash. Interlead flash shall not exceed 0.25 mm per side.
5. Reference JEDEC registration MO-153.

EXAMPLE BOARD LAYOUT

PW0020A

TSSOP - 1.2 mm max height

SMALL OUTLINE PACKAGE



LAND PATTERN EXAMPLE
EXPOSED METAL SHOWN
SCALE: 10X



4220206/A 02/2017

NOTES: (continued)

6. Publication IPC-7351 may have alternate designs.

7. Solder mask tolerances between and around signal pads can vary based on board fabrication site.

EXAMPLE STENCIL DESIGN

PW0020A

TSSOP - 1.2 mm max height

SMALL OUTLINE PACKAGE



SOLDER PASTE EXAMPLE
BASED ON 0.125 mm THICK STENCIL
SCALE: 10X

4220206/A 02/2017

NOTES: (continued)

8. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.
9. Board assembly site may have different recommendations for stencil design.



4226367/A 10/2020

NOTES:

PowerPAD is a trademark of Texas Instruments.

1. All linear dimensions are in millimeters. Any dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.
2. This drawing is subject to change without notice.
3. This dimension does not include mold flash, protrusions, or gate burrs. Mold flash, protrusions, or gate burrs shall not exceed 0.15 mm per side.
4. No JEDEC registration as of September 2020.
5. Features may differ or may not be present.

EXAMPLE BOARD LAYOUT

DGS0020A

VSSOP - 1.1 mm max height

SMALL OUTLINE PACKAGE



4226367/A 10/2020

NOTES: (continued)

6. Publication IPC-7351 may have alternate designs.
7. Solder mask tolerances between and around signal pads can vary based on board fabrication site.
8. This package is designed to be soldered to a thermal pad on the board. For more information, see Texas Instruments literature numbers SLMA002 (www.ti.com/lit/slma002) and SLMA004 (www.ti.com/lit/slma004).
9. Size of metal pad may vary due to creepage requirement.
10. Vias are optional depending on application, refer to device data sheet. It is recommended that vias under paste be filled, plugged or tented.

EXAMPLE STENCIL DESIGN

DGS0020A

VSSOP - 1.1 mm max height

SMALL OUTLINE PACKAGE



SOLDER PASTE EXAMPLE
BASED ON 0.125 mm THICK STENCIL
SCALE: 16X

4226367/A 10/2020

NOTES: (continued)

11. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.
12. Board assembly site may have different recommendations for stencil design.

GENERIC PACKAGE VIEW


RKS 20

VQFN - 1 mm max height

2.5 x 4.5, 0.5 mm pitch

PLASTIC QUAD FLATPACK - NO LEAD

This image is a representation of the package family, actual package may vary.
Refer to the product data sheet for package details.



IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATASHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, regulatory or other requirements.

These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you fully indemnify TI and its representatives against any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to [TI's Terms of Sale](#), [TI's General Quality Guidelines](#), or other applicable terms available either on [ti.com](#) or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products. Unless TI explicitly designates a product as custom or customer-specified, TI products are standard, catalog, general purpose devices.

TI objects to and rejects any additional or different terms you may propose.

Copyright © 2025, Texas Instruments Incorporated

Last updated 10/2025