


LMx19 High Speed Dual Comparator


1 Features

- Two Independent Comparators
- Operates from a Single 5-V Supply
- Typically 80-ns Response Time at  $\pm 15$  V
- Minimum Fan-out of 2 Each Side
- Maximum Input Current of 1  $\mu$ A Over Temperature
- Inputs and Outputs can be Isolated from System Ground
- High Common-Mode Slew Rate

Connection Diagram



Typical Application - Relay Driver



2 Description

The LM119 series are precision high-speed dual comparators fabricated on a single monolithic chip. They are designed to operate over a wide range of supply voltages down to a single 5-V logic supply and ground. They have higher gain and lower input currents than devices such as the LM710. The uncommitted collector of the output stage makes the LM119 compatible with RTL, DTL, and TTL, as well as capable of driving lamps and relays at currents of up to 25 mA.

The LM319A offers improved precision over the standard LM319, with tighter tolerances on offset voltage, offset current, and voltage gain.

Although designed primarily for applications requiring operation from digital logic supplies, the LM119 series are fully specified for power supplies up to  $\pm 15$  V. The series features faster response than the LM111, at the expense of higher power dissipation. However, the high-speed, wide operating voltage range and low package count make the LM119 more versatile than older devices such as the LM711.

The LM119 is specified from  $-55^{\circ}\text{C}$  to  $+125^{\circ}\text{C}$ , the LM219 is specified from  $-25^{\circ}\text{C}$  to  $+85^{\circ}\text{C}$ , and the LM319A and LM319 are specified from  $0^{\circ}\text{C}$  to  $+70^{\circ}\text{C}$ .

Device Information<sup>(1)</sup>

| PART NUMBER         | PACKAGE     | BODY SIZE (NOM)           |
|---------------------|-------------|---------------------------|
| LM119, LM219, LM319 | TO-100 (10) | 8.96 mm $\times$ 8.96 mm  |
|                     | CDIP (14)   | 6.67 mm $\times$ 19.56 mm |

(1) For all available packages, see the orderable addendum at the end of the data sheet.

## Table of Contents


|                                                    |          |                                                                 |           |
|----------------------------------------------------|----------|-----------------------------------------------------------------|-----------|
| <b>1 Features</b> .....                            | <b>1</b> | <b>6 Detailed Description</b> .....                             | <b>10</b> |
| <b>2 Description</b> .....                         | <b>1</b> | 6.1 Functional Block Diagram .....                              | 10        |
| <b>3 Revision History</b> .....                    | <b>2</b> | <b>7 Application and Implementation</b> .....                   | <b>11</b> |
| <b>4 Pin Configuration and Functions</b> .....     | <b>3</b> | 7.1 Typical Applications .....                                  | 11        |
| <b>5 Specifications</b> .....                      | <b>4</b> | <b>8 Device and Documentation Support</b> .....                 | <b>12</b> |
| 5.1 Absolute Maximum Ratings .....                 | 4        | 8.1 Related Links .....                                         | 12        |
| 5.2 ESD Ratings .....                              | 4        | 8.2 Community Resources .....                                   | 12        |
| 5.3 Thermal Information .....                      | 4        | 8.3 Trademarks .....                                            | 12        |
| 5.4 Electrical Characteristics LM119, LM219 .....  | 5        | 8.4 Electrostatic Discharge Caution .....                       | 12        |
| 5.5 Electrical Characteristics LM319, LM319A ..... | 6        | 8.5 Glossary .....                                              | 12        |
| 5.6 Typical Characteristics .....                  | 7        | <b>9 Mechanical, Packaging, and Orderable Information</b> ..... | <b>12</b> |

## 3 Revision History


| Changes from Revision A (May 2004) to Revision B                                                                                                                                                   | Page |
|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|------|
| • Changed datasheet to new TI format from National. ....                                                                                                                                           | 1    |
| • Added <i>Pin Functions</i> and <i>Thermal Information</i> tables, the <i>Device and Documentation Support</i> section, and <i>Mechanical, Packaging, and Orderable Information</i> section ..... | 1    |

## 4 Pin Configuration and Functions


**D, J, or NFF Package  
14-Pins CDIP and PDIP  
Top View**



**LME Package  
10-Pins TO-100 (Metal Can Package)  
Top View**



**NAD Package  
10-Pins CFP  
Top View**



### Pin Functions

| PIN      |                       |                 |                 | I/O | DESCRIPTION                           |
|----------|-----------------------|-----------------|-----------------|-----|---------------------------------------|
| NAME     | NO.<br>(D, J, NFF 14) | NO.<br>(LME 10) | NO.<br>(NAD 10) |     |                                       |
| OUTPUT 1 | 1                     | 12              | 1               | O   | Comparator 1 output                   |
| GND 1    | 2                     | 3               | 2               | G   | Comparator 1 ground connection        |
| INPUT 1+ | 3                     | 4               | 3               | I   | Comparator 1 input                    |
| INPUT 1- | 4                     | 5               | 4               | I   | Comparator 1 input                    |
| V-       | 5                     | 6               | 5               | P   | Negative supply voltage               |
| OUTPUT 2 | 6                     | 7               | 6               | O   | Comparator 2 output                   |
| GND 2    | 7                     | 8               | 7               | G   | Comparator 2 ground connection        |
| INPUT 2+ | 8                     | 9               | 8               | I   | Comparator 2 input                    |
| INPUT 2- | 9                     | 10              | 9               | I   | Comparator 2 input                    |
| V+       | 10                    | 11              | 10              | P   | Positive supply voltage               |
| NC       | 1,2,13,14             |                 |                 |     | No connect. Do not connect to ground. |

## 5 Specifications

### 5.1 Absolute Maximum Ratings

 over operating free-air temperature range (unless otherwise noted)<sup>(1)(2)(3)</sup>

|                                       |                                                | MIN | MAX | UNIT |
|---------------------------------------|------------------------------------------------|-----|-----|------|
| Total supply voltage                  |                                                |     | 36  | V    |
| Output to negative supply voltage     |                                                |     | 36  | V    |
| Ground to negative supply voltage     |                                                |     | 25  | V    |
| Ground to positive supply voltage     |                                                |     | 18  | V    |
| Differential input voltage            |                                                | –5  | +5  | V    |
| Input voltage <sup>(4)</sup>          |                                                | –15 | +15 | V    |
| Power dissipation <sup>(5)</sup>      |                                                |     | 500 | mW   |
| Output short circuit duration         |                                                |     | 10  | sec  |
| Lead temperature (soldering, 10 sec.) |                                                |     | 260 | °C   |
| Soldering information <sup>(6)</sup>  | Dual-In-Line Package Soldering (10 seconds)    |     | 260 | °C   |
|                                       | Small Outline Package Vapor Phase (60 seconds) |     | 215 |      |
|                                       | Small Outline Package Infrared (15 seconds)    |     | 220 |      |
| Operating temperature                 | LM119                                          | –55 | 125 | °C   |
|                                       | LM219                                          | –25 | 85  |      |
|                                       | LM319A, LM319                                  | 0   | 70  |      |
| Storage temperature, T <sub>stg</sub> |                                                | –65 | 150 | °C   |

- (1) Stresses beyond those listed under *Absolute Maximum Ratings* may cause permanent damage to the device. These are stress ratings only, which do not imply functional operation of the device at these or any other conditions beyond those indicated under *Recommended Operating Conditions*. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability.
- (2) If Military/Aerospace specified devices are required, please contact the Texas Instruments Sales Office/ Distributors for availability and specifications.
- (3) Refer to RETS119X for LM119H/883 and LM119J/883 specifications.
- (4) For supply voltages less than ±15 V the absolute maximum input voltage is equal to the supply voltage.
- (5) The maximum junction temperature of the LM119 is 150°C, while that of the LM219 is 110°C. For operating at elevated temperatures, devices in the H10 package must be derated based on a thermal resistance of 160°C/W, junction to ambient, or 19°C/W, junction to case. The thermal resistance of the J14 and N14 packages is 100°C/W, junction to ambient.
- (6) See AN-450 "Surface Mounting Methods and Their Effect on Product Reliability" for other methods of soldering surface mount devices.

### 5.2 ESD Ratings

|                    |                         |                                                                   | VALUE | UNIT |
|--------------------|-------------------------|-------------------------------------------------------------------|-------|------|
| V <sub>(ESD)</sub> | Electrostatic discharge | Human body model (HBM), per ANSI/ESDA/JEDEC JS-001 <sup>(1)</sup> | ±800  | V    |

- (1) JEDEC document JEP155 states that 500-V HBM allows safe manufacturing with a standard ESD control process.

### 5.3 Thermal Information

| THERMAL METRIC <sup>(1)</sup> |                                           | LM119, LM219, LM319 |            |          | UNIT |
|-------------------------------|-------------------------------------------|---------------------|------------|----------|------|
|                               |                                           | TO-100 (LME)        | PDIP (NFF) | CDIP (J) |      |
|                               |                                           | 10 PINS             | 14 PINS    | 14 PINS  |      |
| R <sub>θJA</sub>              | Junction-to-ambient thermal resistance    | 160                 | 100        | 100      | °C/W |
| R <sub>θJC(top)</sub>         | Junction-to-case (top) thermal resistance | 19                  | NA         | NA       | °C/W |

- (1) For more information about traditional and new thermal metrics, see the *Semiconductor and IC Package Thermal Metrics* application report, [SPRA953](#).

## 5.4 Electrical Characteristics LM119, LM219

These specifications apply for  $V_S = \pm 15\text{ V}$ , and the Ground pin at ground, and  $-55^\circ\text{C} \leq T_A \leq +125^\circ\text{C}$ , unless otherwise stated. With the LM219, all temperature specifications are limited to  $-25^\circ\text{C} \leq T_A \leq +85^\circ\text{C}$ . The offset voltage, offset current and bias current specifications apply for any supply voltage from a single 5-V supply up to  $\pm 15\text{-V}$  supplies. Do not operate the device with more than 16 V from ground to  $V_S$ .

| PARAMETER                           | TEST CONDITIONS                                                                                                                 | MIN | TYP      | MAX     | UNIT          |
|-------------------------------------|---------------------------------------------------------------------------------------------------------------------------------|-----|----------|---------|---------------|
| Input Offset Voltage <sup>(1)</sup> | $T_A = 25^\circ\text{C}$ , $R_S \leq 5\text{k}$                                                                                 |     | 0.7      | 4       | mV            |
| Input Offset Current <sup>(1)</sup> | $T_A = 25^\circ\text{C}$                                                                                                        |     | 30       | 75      | nA            |
| Input Bias Current                  | $T_A = 25^\circ\text{C}$                                                                                                        |     | 150      | 500     | nA            |
| Voltage Gain                        | $T_A = 25^\circ\text{C}$ <sup>(2)</sup>                                                                                         | 10  | 40       |         | V/mV          |
| Response Time <sup>(3)</sup>        | $T_A = 25^\circ\text{C}$ , $V_S = \pm 15\text{ V}$                                                                              |     | 80       |         | ns            |
| Saturation Voltage                  | $V_{IN} \leq -5\text{ mV}$ , $I_{OUT} = 25\text{ mA}$<br>$T_A = 25^\circ\text{C}$                                               |     | 0.75     | 1.5     | V             |
| Output Leakage Current              | $V_{IN} \geq 5\text{ mV}$ , $V_{OUT} = 35\text{ V}$<br>$T_A = 25^\circ\text{C}$                                                 |     | 0.2      | 2       | $\mu\text{A}$ |
| Input Offset Voltage <sup>(1)</sup> | $R_S \leq 5\text{k}$                                                                                                            |     |          | 7       | mV            |
| Input Offset Current <sup>(1)</sup> |                                                                                                                                 |     |          | 100     | nA            |
| Input Bias Current                  |                                                                                                                                 |     |          | 1000    | nA            |
| Input Voltage Range                 | $V_S = \pm 15\text{ V}$                                                                                                         | -12 | $\pm 13$ | +12     | V             |
|                                     | $V^+ = 5\text{ V}$ , $V^- = 0$                                                                                                  | 1   |          | 3       |               |
| Saturation Voltage                  | $V^+ \geq 4.5\text{ V}$ , $V^- = 0$<br>$V_{IN} \leq -6\text{ mV}$ , $I_{SINK} \leq 3.2\text{ mA}$<br>$T_A \geq 0^\circ\text{C}$ |     | 0.23     | 0.4     | V             |
|                                     | $T_A \leq 0^\circ\text{C}$                                                                                                      |     |          | 0.6     |               |
|                                     |                                                                                                                                 |     |          |         |               |
| Output Leakage Current              | $V_{IN} \geq 5\text{ mV}$ , $V_{OUT} = 35\text{ V}$ , $V^- = V_{GND} = 0\text{ V}$                                              |     | 1        | 10      | $\mu\text{A}$ |
| Differential Input Voltage          |                                                                                                                                 |     |          | $\pm 5$ | V             |
| Positive Supply Current             | $T_A = 25^\circ\text{C}$ , $V^+ = 5\text{ V}$ , $V^- = 0$                                                                       |     | 4.3      |         | mA            |
| Positive Supply Current             | $T_A = 25^\circ\text{C}$ , $V_S = \pm 15\text{ V}$                                                                              |     | 8        | 11.5    | mA            |
| Negative Supply Current             | $T_A = 25^\circ\text{C}$ , $V_S = \pm 15\text{ V}$                                                                              |     | 3        | 4.5     | mA            |

- (1) The offset voltages and offset currents given are the maximum values required to drive the output within a volt of either supply with a 1-mA load. Thus, these parameters define an error band and take into account the worst case effects of voltage gain and input impedance.
- (2) Output is pulled up to 15 V through a 1.4-k $\Omega$  resistor.
- (3) The response time specified is for a 100-mV input step with 5-mV overdrive.

## 5.5 Electrical Characteristics LM319, LM319A

These specifications apply for  $V_S = \pm 15\text{ V}$ , and  $0^\circ\text{C} \leq T_A \leq 70^\circ\text{C}$ , unless otherwise stated. The offset voltage, offset current, and bias current specifications apply for any supply voltage from a single 5-V supply up to  $\pm 15\text{-V}$  supplies. Do not operate the device with more than 16 V from ground to  $V_S$ .

| PARAMETER                           | TEST CONDITIONS                                                                                                 | LM319A |          |      | LM319 |          |      | UNIT          |
|-------------------------------------|-----------------------------------------------------------------------------------------------------------------|--------|----------|------|-------|----------|------|---------------|
|                                     |                                                                                                                 | MIN    | TYP      | MAX  | MIN   | TYP      | MAX  |               |
| Input Offset Voltage <sup>(1)</sup> | $T_A = 25^\circ\text{C}$ , $R_S \leq 5\text{k}$                                                                 |        | 0.5      | 1    |       | 2        | 8    | mV            |
| Input Offset Current <sup>(1)</sup> | $T_A = 25^\circ\text{C}$                                                                                        |        | 20       | 40   |       | 80       | 200  | nA            |
| Input Bias Current                  | $T_A = 25^\circ\text{C}$                                                                                        |        | 150      | 500  |       | 250      | 1000 | nA            |
| Voltage Gain                        | $T_A = 25^\circ\text{C}$ <sup>(2)</sup>                                                                         | 20     | 40       |      | 8     | 40       |      | V/mV          |
| Response Time <sup>(3)</sup>        | $T_A = 25^\circ\text{C}$ , $V_S = \pm 15\text{ V}$                                                              |        | 80       |      |       | 80       |      | ns            |
| Saturation Voltage                  | $V_{IN} \leq -10\text{ mV}$ , $I_{OUT} = 25\text{ mA}$<br>$T_A = 25^\circ\text{C}$                              |        | 0.75     | 1.5  |       | 0.75     | 1.5  | V             |
| Output Leakage Current              | $V_{IN} \geq 10\text{ mV}$ , $V_{OUT} = 35\text{ V}$<br>$V^+ = V_{GND} = 0\text{ V}$ , $T_A = 25^\circ\text{C}$ |        | 0.2      | 10   |       | 0.2      | 10   | $\mu\text{A}$ |
| Input Offset Voltage <sup>(1)</sup> | $R_S \leq 5\text{k}$                                                                                            |        |          | 10   |       |          | 10   | mV            |
| Input Offset Current <sup>(1)</sup> |                                                                                                                 |        |          | 300  |       |          | 300  | nA            |
| Input Bias Current                  |                                                                                                                 |        |          | 1000 |       |          | 1200 | nA            |
| Input Voltage Range                 | $V_S = \pm 15\text{ V}$                                                                                         |        | $\pm 13$ |      |       | $\pm 13$ |      | V             |
|                                     | $V^+ = 5\text{ V}$ , $V^- = 0$                                                                                  | 1      |          | 3    | 1     |          | 3    |               |
| Saturation Voltage                  | $V^+ \geq 4.5\text{ V}$ , $V^- = 0$<br>$V_{IN} \leq -10\text{ mV}$ , $I_{SINK} \leq 3.2\text{ mA}$              |        | 0.3      | 0.4  |       | 0.3      | 0.4  | V             |
| Differential Input Voltage          |                                                                                                                 |        | $\pm 5$  |      |       | $\pm 5$  |      | V             |
| Positive Supply Current             | $T_A = 25^\circ\text{C}$ , $V^+ = 5\text{ V}$ , $V^- = 0$                                                       |        | 4.3      |      |       | 4.3      |      | mA            |
| Positive Supply Current             | $T_A = 25^\circ\text{C}$ , $V_S = \pm 15\text{ V}$                                                              |        | 8        | 12.5 |       | 8        | 12.5 | mA            |
| Negative Supply Current             | $T_A = 25^\circ\text{C}$ , $V_S = \pm 15\text{ V}$                                                              |        | 3        | 5    |       | 3        | 5    | mA            |

- (1) The offset voltages and offset currents given are the maximum values required to drive the output within a volt of either supply with a 1-mA load. Thus, these parameters define an error band and take into account the worst case effects of voltage gain and input impedance.
- (2) Output is pulled up to 15 V through a 1.4-k $\Omega$  resistor.
- (3) The response time specified is for a 100-mV input step with 5-mV overdrive.

## 5.6 Typical Characteristics

### 5.6.1 Typical Characteristics – LM119, LM119A, LM219




Figure 1. Input Currents




Figure 2. Common-Mode Limits




Figure 3. Transfer Function




Figure 4. Response Time for Various Input Overdrives




Figure 5. Response Time for Various Input Overdrives




Figure 6. Input Characteristics




Figure 7. Response Time for Various Input Overdrives




Figure 8. Response Time for Various Input Overdrives

## Typical Characteristics – LM119, LM119A, LM219 (continued)




Figure 9. Output Saturation Voltage




Figure 10. Supply Current




Figure 11. Supply Current




Figure 12. Output Limiting Characteristics

## 5.6.2 Typical Characteristics – LM319, LM319A




Figure 13. Input Currents




Figure 14. Supply Currents




Figure 15. Transfer Function




Figure 16. Response Time for Various Input Overdrives

## Typical Characteristics – LM319, LM319A (continued)




Figure 17. Response Time for Various Input Overdrives




Figure 18. Input Characteristics




Figure 19. Response Time for Various Input Overdrives




Figure 20. Response Time for Various Input Overdrives




Figure 21. Output Saturation Voltage




Figure 22. Supply Current




Figure 23. Common-Mode Limits





Figure 24. Output Limiting Characteristics

## 6 Detailed Description

### 6.1 Functional Block Diagram



DS005705-1

\*Do not operate the LM119 with more than 16V between GND and V<sup>+</sup>

## 7 Application and Implementation

### NOTE

Information in the following applications sections is not part of the TI component specification, and TI does not warrant its accuracy or completeness. TI's customers are responsible for determining suitability of components for their purposes. Customers should validate and test their design implementation to confirm system functionality.

### 7.1 Typical Applications

#### 7.1.1 Relay Driver




Figure 25. Relay Driver

#### 7.1.2 Window Detector




Figure 26. Window Detector

## 8 Device and Documentation Support

### 8.1 Related Links

The table below lists quick access links. Categories include technical documents, support and community resources, tools and software, and quick access to sample or buy.

**Table 1. Related Links**

| PARTS | PRODUCT FOLDER             | SAMPLE & BUY               | TECHNICAL DOCUMENTS        | TOOLS & SOFTWARE           | SUPPORT & COMMUNITY        |
|-------|----------------------------|----------------------------|----------------------------|----------------------------|----------------------------|
| LM119 | <a href="#">Click here</a> | <a href="#">Click here</a> | <a href="#">Click here</a> | <a href="#">Click here</a> | <a href="#">Click here</a> |
| LM219 | <a href="#">Click here</a> | <a href="#">Click here</a> | <a href="#">Click here</a> | <a href="#">Click here</a> | <a href="#">Click here</a> |
| LM319 | <a href="#">Click here</a> | <a href="#">Click here</a> | <a href="#">Click here</a> | <a href="#">Click here</a> | <a href="#">Click here</a> |

### 8.2 Community Resources

The following links connect to TI community resources. Linked contents are provided "AS IS" by the respective contributors. They do not constitute TI specifications and do not necessarily reflect TI's views; see TI's [Terms of Use](#).

**TI E2E™ Online Community** *TI's Engineer-to-Engineer (E2E) Community*. Created to foster collaboration among engineers. At [e2e.ti.com](http://e2e.ti.com), you can ask questions, share knowledge, explore ideas and help solve problems with fellow engineers.

**Design Support** *TI's Design Support* Quickly find helpful E2E forums along with design support tools and contact information for technical support.

### 8.3 Trademarks

E2E is a trademark of Texas Instruments.

All other trademarks are the property of their respective owners.

### 8.4 Electrostatic Discharge Caution



These devices have limited built-in ESD protection. The leads should be shorted together or the device placed in conductive foam during storage or handling to prevent electrostatic damage to the MOS gates.

### 8.5 Glossary

[SLYZ022](#) — *TI Glossary*.

This glossary lists and explains terms, acronyms, and definitions.

## 9 Mechanical, Packaging, and Orderable Information

The following pages include mechanical, packaging, and orderable information. This information is the most current data available for the designated devices. This data is subject to change without notice and revision of this document. For browser-based versions of this data sheet, refer to the left-hand navigation.

## PACKAGING INFORMATION

| Orderable part number         | Status<br>(1) | Material type<br>(2) | Package   Pins    | Package qty   Carrier | RoHS<br>(3) | Lead finish/<br>Ball material<br>(4) | MSL rating/<br>Peak reflow<br>(5) | Op temp (°C) | Part marking<br>(6) |
|-------------------------------|---------------|----------------------|-------------------|-----------------------|-------------|--------------------------------------|-----------------------------------|--------------|---------------------|
| <a href="#">LM119H</a>        | Active        | Production           | TO-100 (LME)   10 | 500   OTHER           | No          | Call TI                              | Call TI                           | -55 to 125   | ( LM119H, LM119H)   |
| <a href="#">LM119H/NOPB</a>   | Active        | Production           | TO-100 (LME)   10 | 500   OTHER           | Yes         | Call TI                              | Level-1-NA-UNLIM                  | -55 to 125   | ( LM119H, LM119H)   |
| <a href="#">LM119J</a>        | Active        | Production           | CDIP (J)   14     | 25   TUBE             | No          | Call TI                              | Call TI                           | -55 to 125   | LM119J              |
| <a href="#">LM319AM/NOPB</a>  | Active        | Production           | SOIC (D)   14     | 55   TUBE             | Yes         | SN                                   | Level-1-260C-UNLIM                | 0 to 70      | LM319AM             |
| LM319AM/NOPB.B                | Active        | Production           | SOIC (D)   14     | 55   TUBE             | Yes         | SN                                   | Level-1-260C-UNLIM                | 0 to 70      | LM319AM             |
| <a href="#">LM319AMX/NOPB</a> | Active        | Production           | SOIC (D)   14     | 2500   LARGE T&R      | Yes         | SN                                   | Level-1-260C-UNLIM                | 0 to 70      | LM319AM             |
| LM319AMX/NOPB.B               | Active        | Production           | SOIC (D)   14     | 2500   LARGE T&R      | Yes         | SN                                   | Level-1-260C-UNLIM                | 0 to 70      | LM319AM             |
| <a href="#">LM319M/NOPB</a>   | Active        | Production           | SOIC (D)   14     | 55   TUBE             | Yes         | SN                                   | Level-1-260C-UNLIM                | 0 to 70      | LM319M              |
| LM319M/NOPB.B                 | Active        | Production           | SOIC (D)   14     | 55   TUBE             | Yes         | SN                                   | Level-1-260C-UNLIM                | 0 to 70      | LM319M              |
| <a href="#">LM319MX/NOPB</a>  | Active        | Production           | SOIC (D)   14     | 2500   LARGE T&R      | Yes         | SN                                   | Level-1-260C-UNLIM                | 0 to 70      | LM319M              |
| LM319MX/NOPB.B                | Active        | Production           | SOIC (D)   14     | 2500   LARGE T&R      | Yes         | SN                                   | Level-1-260C-UNLIM                | 0 to 70      | LM319M              |
| <a href="#">LM319N/NOPB</a>   | Active        | Production           | PDIP (N)   14     | 25   TUBE             | Yes         | NIPDAU                               | Level-1-NA-UNLIM                  | 0 to 70      | LM319N              |
| LM319N/NOPB.B                 | Active        | Production           | PDIP (N)   14     | 25   TUBE             | Yes         | NIPDAU                               | Level-1-NA-UNLIM                  | 0 to 70      | LM319N              |

<sup>(1)</sup> **Status:** For more details on status, see our [product life cycle](#).

<sup>(2)</sup> **Material type:** When designated, preproduction parts are prototypes/experimental devices, and are not yet approved or released for full production. Testing and final process, including without limitation quality assurance, reliability performance testing, and/or process qualification, may not yet be complete, and this item is subject to further changes or possible discontinuation. If available for ordering, purchases will be subject to an additional waiver at checkout, and are intended for early internal evaluation purposes only. These items are sold without warranties of any kind.

<sup>(3)</sup> **RoHS values:** Yes, No, RoHS Exempt. See the [TI RoHS Statement](#) for additional information and value definition.

<sup>(4)</sup> **Lead finish/Ball material:** Parts may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead finish/Ball material values may wrap to two lines if the finish value exceeds the maximum column width.

<sup>(5)</sup> **MSL rating/Peak reflow:** The moisture sensitivity level ratings and peak solder (reflow) temperatures. In the event that a part has multiple moisture sensitivity ratings, only the lowest level per JEDEC standards is shown. Refer to the shipping label for the actual reflow temperature that will be used to mount the part to the printed circuit board.

<sup>(6)</sup> **Part marking:** There may be an additional marking, which relates to the logo, the lot trace code information, or the environmental category of the part.

Multiple part markings will be inside parentheses. Only one part marking contained in parentheses and separated by a "~" will appear on a part. If a line is indented then it is a continuation of the previous line and the two combined represent the entire part marking for that device.

**Important Information and Disclaimer:** The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.

## TAPE AND REEL INFORMATION



\*All dimensions are nominal

| Device        | Package Type | Package Drawing | Pins | SPQ  | Reel Diameter (mm) | Reel Width W1 (mm) | A0 (mm) | B0 (mm) | K0 (mm) | P1 (mm) | W (mm) | Pin1 Quadrant |
|---------------|--------------|-----------------|------|------|--------------------|--------------------|---------|---------|---------|---------|--------|---------------|
| LM319AMX/NOPB | SOIC         | D               | 14   | 2500 | 330.0              | 16.4               | 6.5     | 9.35    | 2.3     | 8.0     | 16.0   | Q1            |
| LM319MX/NOPB  | SOIC         | D               | 14   | 2500 | 330.0              | 16.4               | 6.5     | 9.35    | 2.3     | 8.0     | 16.0   | Q1            |

## TAPE AND REEL BOX DIMENSIONS



\*All dimensions are nominal

| Device        | Package Type | Package Drawing | Pins | SPQ  | Length (mm) | Width (mm) | Height (mm) |
|---------------|--------------|-----------------|------|------|-------------|------------|-------------|
| LM319AMX/NOPB | SOIC         | D               | 14   | 2500 | 367.0       | 367.0      | 35.0        |
| LM319MX/NOPB  | SOIC         | D               | 14   | 2500 | 367.0       | 367.0      | 35.0        |

## TUBE



\*All dimensions are nominal

| Device         | Package Name | Package Type | Pins | SPQ | L (mm) | W (mm) | T (μm) | B (mm) |
|----------------|--------------|--------------|------|-----|--------|--------|--------|--------|
| LM119J         | J            | CDIP         | 14   | 25  | 502    | 14     | 11938  | 4.32   |
| LM319AM/NOPB   | D            | SOIC         | 14   | 55  | 495    | 8      | 4064   | 3.05   |
| LM319AM/NOPB.B | D            | SOIC         | 14   | 55  | 495    | 8      | 4064   | 3.05   |
| LM319M/NOPB    | D            | SOIC         | 14   | 55  | 495    | 8      | 4064   | 3.05   |
| LM319M/NOPB.B  | D            | SOIC         | 14   | 55  | 495    | 8      | 4064   | 3.05   |
| LM319N/NOPB    | N            | PDIP         | 14   | 25  | 502    | 14     | 11938  | 4.32   |
| LM319N/NOPB.B  | N            | PDIP         | 14   | 25  | 502    | 14     | 11938  | 4.32   |





LME0010A

## PACKAGE OUTLINE

TO-CAN - 5.72 mm max height

TRANSISTOR OUTLINE



4220604/B 09/2024

### NOTES:


1. All linear dimensions are in millimeters. Any dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.
2. This drawing is subject to change without notice.
3. Reference JEDEC registration MO-006/TO-100.

# EXAMPLE BOARD LAYOUT

LME0010A

TO-CAN - 5.72 mm max height

TRANSISTOR OUTLINE



LAND PATTERN EXAMPLE  
NON-SOLDER MASK DEFINED  
SCALE: 12X

4220604/B 09/2024

**D0014A****PACKAGE OUTLINE****SOIC - 1.75 mm max height**

SMALL OUTLINE INTEGRATED CIRCUIT



4220718/A 09/2016

**NOTES:**

1. All linear dimensions are in millimeters. Dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.
2. This drawing is subject to change without notice.
3. This dimension does not include mold flash, protrusions, or gate burrs. Mold flash, protrusions, or gate burrs shall not exceed 0.15 mm, per side.
4. This dimension does not include interlead flash. Interlead flash shall not exceed 0.43 mm, per side.
5. Reference JEDEC registration MS-012, variation AB.

# EXAMPLE BOARD LAYOUT

D0014A

SOIC - 1.75 mm max height

SMALL OUTLINE INTEGRATED CIRCUIT



LAND PATTERN EXAMPLE  
SCALE:8X



SOLDER MASK DETAILS

4220718/A 09/2016

NOTES: (continued)

6. Publication IPC-7351 may have alternate designs.

7. Solder mask tolerances between and around signal pads can vary based on board fabrication site.

## EXAMPLE STENCIL DESIGN

D0014A

SOIC - 1.75 mm max height

SMALL OUTLINE INTEGRATED CIRCUIT



SOLDER PASTE EXAMPLE  
BASED ON 0.125 mm THICK STENCIL  
SCALE:8X

4220718/A 09/2016

NOTES: (continued)

8. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.
9. Board assembly site may have different recommendations for stencil design.

**J 14**

## GENERIC PACKAGE VIEW

**CDIP - 5.08 mm max height**

CERAMIC DUAL IN LINE PACKAGE



Images above are just a representation of the package family, actual package may vary.  
Refer to the product data sheet for package details.

4040083-5/G

**J0014A****PACKAGE OUTLINE****CDIP - 5.08 mm max height**

CERAMIC DUAL IN LINE PACKAGE



4214771/A 05/2017

**NOTES:**

1. All controlling linear dimensions are in inches. Dimensions in brackets are in millimeters. Any dimension in brackets or parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.
2. This drawing is subject to change without notice.
3. This package is hermetically sealed with a ceramic lid using glass frit.
4. Index point is provided on cap for terminal identification only and on press ceramic glass frit seal only.
5. Falls within MIL-STD-1835 and GDIP1-T14.

# EXAMPLE BOARD LAYOUT

J0014A

CDIP - 5.08 mm max height

CERAMIC DUAL IN LINE PACKAGE



LAND PATTERN EXAMPLE  
NON-SOLDER MASK DEFINED  
SCALE: 5X



4214771/A 05/2017

## N (R-PDIP-T\*\*)

16 PINS SHOWN

## PLASTIC DUAL-IN-LINE PACKAGE



| PINS **             | 14               | 16               | 18               | 20               |
|---------------------|------------------|------------------|------------------|------------------|
| DIM                 |                  |                  |                  |                  |
| A MAX               | 0.775<br>(19,69) | 0.775<br>(19,69) | 0.920<br>(23,37) | 1.060<br>(26,92) |
| A MIN               | 0.745<br>(18,92) | 0.745<br>(18,92) | 0.850<br>(21,59) | 0.940<br>(23,88) |
| MS-001<br>VARIATION | AA               | BB               | AC               | AD               |



4040049/E 12/2002

- NOTES:
- A. All linear dimensions are in inches (millimeters).
  - B. This drawing is subject to change without notice.
  - Falls within JEDEC MS-001, except 18 and 20 pin minimum body length (Dim A).
  - The 20 pin end lead shoulder width is a vendor option, either half or full width.

## IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATASHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, regulatory or other requirements.

These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you fully indemnify TI and its representatives against any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to [TI's Terms of Sale](#), [TI's General Quality Guidelines](#), or other applicable terms available either on [ti.com](http://ti.com) or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products. Unless TI explicitly designates a product as custom or customer-specified, TI products are standard, catalog, general purpose devices.

TI objects to and rejects any additional or different terms you may propose.

Copyright © 2026, Texas Instruments Incorporated

Last updated 10/2025