

# SN55113, SN75113 DUAL DIFFERENTIAL LINE DRIVERS

SLLS070C – SEPTEMBER 1973 – REVISED MARCH 1997

- Choice of Open-Collector, Open-Emitter, or 3-State Outputs
- High-Impedance Output State for Party-Line Applications
- Single-Ended or Differential AND/NAND Outputs
- Single 5-V Supply
- Dual Channel Operation
- Compatible With TTL
- Short-Circuit Protection
- High-Current Outputs
- Common and Individual Output Controls
- Clamp Diodes at Inputs and Outputs
- Easily Adaptable to SN55114 and SN75114 Applications
- Designed for Use With SN55115 and SN75115


## description

The SN55113 and SN75113 dual differential line drivers with 3-state outputs are designed to provide all the features of the SN55114 and SN75114 line drivers with the added feature of driver output controls. Individual controls are provided for each output pair, as well as a common control for both output pairs. If any output is low, the associated output is in a high-impedance state and the output can neither drive nor load the bus. This permits many devices to be connected together on the same transmission line for party-line applications.


The output stages are similar to TTL totem-pole outputs, but with the sink outputs, YS and ZS, and the corresponding active pullup terminals, YP and ZP, available on adjacent package pins.

The SN55113 is characterized for operation over the full military temperature range of  $-55^{\circ}\text{C}$  to  $125^{\circ}\text{C}$ . The SN75113 is characterized for operation over the temperature range of  $0^{\circ}\text{C}$  to  $70^{\circ}\text{C}$ .

SN55113 . . . J OR W PACKAGE  
SN75113 . . . N PACKAGE  
(TOP VIEW)



SN55113 . . . FK PACKAGE  
(TOP VIEW)



NC – No internal connection



Please be aware that an important notice concerning availability, standard warranty, and use in critical applications of Texas Instruments semiconductor products and disclaimers thereto appears at the end of this data sheet.

PRODUCTION DATA information is current as of publication date. Products conform to specifications per the terms of Texas Instruments standard warranty. Production processing does not necessarily include testing of all parameters.

**TEXAS  
INSTRUMENTS**

POST OFFICE BOX 655303 • DALLAS, TEXAS 75265

Copyright © 1997, Texas Instruments Incorporated

# SN55113, SN75113 DUAL DIFFERENTIAL LINE DRIVERS


SLLS070C – SEPTEMBER 1973 – REVISED MARCH 1997

FUNCTION TABLE


| INPUTS      |               |      |    | OUTPUTS  |           |
|-------------|---------------|------|----|----------|-----------|
| OUTPUT<br>C | CONTROL<br>CC | DATA |    | AND<br>Y | NAND<br>Z |
|             |               | A    | B† |          |           |
| L           | X             | X    | X  | Z        | Z         |
| X           | L             | X    | X  | Z        | Z         |
| H           | H             | L    | X  | L        | H         |
| H           | H             | X    | L  | L        | H         |
| H           | H             | H    | H  | H        | L         |

H = high level, L = low level, X = irrelevant,  
Z = high impedance (off)  
† B input and 4th line of function table are applicable only to driver number 1.

logic symbol‡




logic diagram (positive logic)



‡ This symbol is in accordance with ANSI/IEEE Std 91-1984 and IEC Publication 617-12.  
Pin numbers shown are for the J, N, and W packages.

### schematic



† These components are common to both drivers. Resistor values shown are nominal and in ohms.

### absolute maximum ratings over operating free-air temperature range (unless otherwise noted)‡

|                                                                              |                              |
|------------------------------------------------------------------------------|------------------------------|
| Supply voltage, V <sub>CC</sub> (see Note 1)                                 | 7 V                          |
| Input voltage, V <sub>I</sub>                                                | 5.5 V                        |
| Off-state voltage applied to open-collector outputs                          | 12 V                         |
| Continuous total power dissipation (see Note 2)                              | See Dissipation Rating Table |
| Operating free-air temperature range, T <sub>A</sub> : SN55113               | –55°C to 125°C               |
| SN75113                                                                      | 0°C to 70°C                  |
| Storage temperature range, T <sub>stg</sub>                                  | –65°C to 150°C               |
| Lead temperature 1,6 mm (1/16 inch) from case for 10 seconds: N package      | 260°C                        |
| Case temperature for 60 seconds: FK package                                  | 260°C                        |
| Lead temperature 1,6 mm (1/16 inch) from case for 60 seconds: J or W package | 300°C                        |

‡ Stresses beyond those listed under “absolute maximum ratings” may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated under “recommended operating conditions” is not implied. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability.

DISSIPATION RATING TABLE

| PACKAGE | T <sub>A</sub> ≤ 25°C<br>POWER RATING | DERATING FACTOR<br>ABOVE T <sub>A</sub> = 25°C | T <sub>A</sub> = 70°C<br>POWER RATING | T <sub>A</sub> = 125°C<br>POWER RATING |
|---------|---------------------------------------|------------------------------------------------|---------------------------------------|----------------------------------------|
| FK      | 1375 mW                               | 11.0 mW/°C                                     | 880 mW                                | 275 mW                                 |
| J       | 1375 mW                               | 11.0 mW/°C                                     | 880 mW                                | 275 mW                                 |
| N       | 1150 mW                               | 9.2 mW/°C                                      | 736 mW                                | N/A                                    |
| W       | 1000 mW                               | 8.0 mW/°C                                      | 640 mW                                | 200 mW                                 |

# SN55113, SN75113

## DUAL DIFFERENTIAL LINE DRIVERS

SLLS070C – SEPTEMBER 1973 – REVISED MARCH 1997

### recommended operating conditions

|                                       | SN55113 |     |      | SN75113 |     |      | UNIT |
|---------------------------------------|---------|-----|------|---------|-----|------|------|
|                                       | MIN     | NOM | MAX  | MIN     | NOM | MAX  |      |
| Supply voltage, $V_{CC}$              | 4.5     | 5   | 5.5  | 4.75    | 5   | 5.25 | V    |
| High-level input voltage, $V_{IH}$    | 2       |     |      | 2       |     |      | V    |
| Low-level input voltage, $V_{IL}$     |         |     | 0.8  |         |     | 0.8  | V    |
| High-level output current, $I_{OH}$   |         |     | – 40 |         |     | – 40 | mA   |
| Low-level output current, $I_{OL}$    |         |     | 40   |         |     | 40   | mA   |
| Operating free-air temperature, $T_A$ | – 55    |     | 125  | 0       |     | 70   | °C   |

### electrical characteristics over recommended operating free-air temperature range (unless otherwise noted)

| PARAMETER           |                                                 |         | TEST CONDITIONS†                                                                                |  |                           | SN55113                                                      |       |       | SN75113 |       |       | UNIT |
|---------------------|-------------------------------------------------|---------|-------------------------------------------------------------------------------------------------|--|---------------------------|--------------------------------------------------------------|-------|-------|---------|-------|-------|------|
|                     |                                                 |         |                                                                                                 |  |                           | MIN                                                          | TYP‡  | MAX   | MIN     | TYP‡  | MAX   |      |
| V <sub>IK</sub>     | Input clamp voltage                             |         | V <sub>CC</sub> = MIN, I <sub>I</sub> = – 12 mA                                                 |  |                           | – 0.9                                                        | – 1.5 |       | – 0.9   | – 1.5 |       | V    |
| V <sub>OH</sub>     | High-level output voltage                       |         | V <sub>CC</sub> = MIN, V <sub>IH</sub> = 2 V, V <sub>IL</sub> = 0.8 V                           |  | I <sub>OH</sub> = – 10 mA | 2.4                                                          | 3.4   |       | 2.4     | 3.4   |       | V    |
|                     |                                                 |         |                                                                                                 |  | I <sub>OH</sub> = – 40 mA | 2                                                            | 3.0   |       | 2       | 3.0   |       |      |
| V <sub>OL</sub>     | Low-level output voltage                        |         | V <sub>CC</sub> = MIN, V <sub>IH</sub> = 2 V, I <sub>OL</sub> = 40 mA, V <sub>IL</sub> = 0.8 V, |  |                           | 0.23                                                         | 0.4   |       | 0.23    | 0.4   |       | V    |
| V <sub>OK</sub>     | Output clamp voltage                            |         | V <sub>CC</sub> = MAX, I <sub>O</sub> = – 40 mA                                                 |  |                           | – 1.1                                                        | – 1.5 |       | – 1.1   | – 1.5 |       | V    |
| I <sub>O(off)</sub> | Off-state open-collector output current         |         | V <sub>CC</sub> = MAX                                                                           |  | V <sub>OH</sub> = 12 V    | T <sub>A</sub> = 25°C                                        | 1     | 10    |         |       |       | μA   |
|                     |                                                 |         |                                                                                                 |  |                           | T <sub>A</sub> = 125°C                                       | 200   |       |         |       |       |      |
|                     |                                                 |         |                                                                                                 |  | V <sub>OH</sub> = 5.25 V  | T <sub>A</sub> = 25°C                                        |       |       | 1       | 10    |       |      |
|                     |                                                 |         |                                                                                                 |  |                           | T <sub>A</sub> = 70°C                                        |       |       |         | 20    |       |      |
| I <sub>OZ</sub>     | Off-state (high-impedance-state) output current |         | V <sub>CC</sub> = MAX, Output controls at 0.8 V                                                 |  | T <sub>A</sub> = MAX      | T <sub>A</sub> = 25°C, V <sub>O</sub> = 0 to V <sub>CC</sub> |       | ± 10  |         | ± 10  |       | μA   |
|                     |                                                 |         |                                                                                                 |  |                           | V <sub>O</sub> = 0                                           |       | – 150 |         | – 20  |       |      |
|                     |                                                 |         |                                                                                                 |  |                           | V <sub>O</sub> = 0.4 V                                       |       | ± 80  |         | ± 20  |       |      |
|                     |                                                 |         |                                                                                                 |  |                           | V <sub>O</sub> = 2.4 V                                       |       | ± 80  |         | ± 20  |       |      |
|                     |                                                 |         |                                                                                                 |  |                           | V <sub>O</sub> = V <sub>CC</sub>                             |       | 80    |         | 20    |       |      |
| I <sub>I</sub>      | Input current at maximum input voltage          | A, B, C | V <sub>CC</sub> = MAX, V <sub>I</sub> = 5.5 V                                                   |  |                           | 1                                                            |       |       | 1       |       |       | mA   |
|                     | CC                                              | 2       |                                                                                                 |  |                           | 2                                                            |       |       |         |       |       |      |
| I <sub>IH</sub>     | High-level input current                        | A, B, C | V <sub>CC</sub> = MAX, V <sub>I</sub> = 2.4 V                                                   |  |                           | 40                                                           |       |       | 40      |       |       | μA   |
|                     | CC                                              | 80      |                                                                                                 |  |                           | 80                                                           |       |       |         |       |       |      |
| I <sub>IL</sub>     | Low-level input current                         | A, B, C | V <sub>CC</sub> = MAX, V <sub>I</sub> = 0.4 V                                                   |  |                           | – 1.6                                                        |       |       | – 1.6   |       |       | mA   |
|                     | CC                                              | – 3.2   |                                                                                                 |  |                           | – 3.2                                                        |       |       |         |       |       |      |
| I <sub>OS</sub>     | Short-circuit output current§                   |         | V <sub>CC</sub> = MAX, V <sub>O</sub> = 0, T <sub>A</sub> = 25°C                                |  |                           | – 40                                                         | – 90  | – 120 | – 40    | – 90  | – 120 | mA   |
| I <sub>CC</sub>     | Supply current (both drivers)                   |         | All inputs at 0 V, No load, T <sub>A</sub> = 25°C                                               |  | V <sub>CC</sub> = MAX     | 47                                                           | 65    |       | 47      | 65    |       | mA   |
|                     |                                                 |         |                                                                                                 |  | V <sub>CC</sub> = 7 V     | 65                                                           | 85    |       | 65      | 85    |       |      |

† All parameters with the exception of off-state open-collector output current are measured with the active pullup connected to the sink output. For conditions shown as MIN or MAX, use the appropriate value specified under recommended operating conditions.

‡ All typical values are at  $T_A = 25^\circ\text{C}$  and  $V_{CC} = 5 \text{ V}$ , with the exception of  $V_{CC}$  at 7 V.

§ Only one output should be shorted at a time, and duration of the short-circuit should not exceed one second.



| PARAMETER                                                         | TEST CONDITIONS                      | SN55113 |     |     | SN75113 |     |     | UNIT |
|-------------------------------------------------------------------|--------------------------------------|---------|-----|-----|---------|-----|-----|------|
|                                                                   |                                      | MIN     | TYP | MAX | MIN     | TYP | MAX |      |
| t <sub>PLH</sub> Propagation delay time, low-to-high level output | See Figure 1                         | 13      | 20  | 13  | 30      | ns  |     |      |
| t <sub>PHL</sub> Propagation delay time, high-to-low-level output |                                      | 12      | 20  | 12  | 30      | ns  |     |      |
| t <sub>PZH</sub> Output enable time to high level                 | R <sub>L</sub> = 180 Ω, See Figure 2 | 7       | 15  | 7   | 20      | ns  |     |      |
| t <sub>PZL</sub> Output enable time to low level                  | R <sub>L</sub> = 250 Ω, See Figure 3 | 14      | 30  | 14  | 40      | ns  |     |      |
| t <sub>PHZ</sub> Output disable time from high level              | R <sub>L</sub> = 180 Ω, See Figure 2 | 10      | 20  | 10  | 30      | ns  |     |      |
| t <sub>PLZ</sub> Output disable time from low level               | R <sub>L</sub> = 250 Ω, See Figure 3 | 17      | 35  | 17  | 35      | ns  |     |      |

[illegible]



Timing diagram for a 2-input NAND gate. The diagram shows three signals: Input, NAND Output, and AND Output. The Input signal is a square wave with a rise and fall time of  $\leq 5$  ns. The NAND Output signal is a square wave that transitions from  $V_{OH}$  to  $V_{OL}$  during the input rise and from  $V_{OL}$  to  $V_{OH}$  during the input fall. The AND Output signal is a square wave that transitions from  $V_{OL}$  to  $V_{OH}$  during the input rise and from  $V_{OH}$  to  $V_{OL}$  during the input fall. The propagation delay  $t_{PLH}$  is the time from the input rising to 50% to the output rising to 50%. The propagation delay  $t_{PHL}$  is the time from the input falling to 50% to the output falling to 50%. The output levels are labeled as 3 V, 1.5 V, and 0 V for the Input signal, and  $V_{OH}$  and  $V_{OL}$  for the NAND and AND outputs.

**Figure 1. Test Circuit and Voltage Waveforms  $t_{PLH}$  and  $t_{PHL}$**

# SN55113, SN75113 DUAL DIFFERENTIAL LINE DRIVERS

SLLS070C – SEPTEMBER 1973 – REVISED MARCH 1997



## PARAMETER MEASUREMENT INFORMATION



NOTES: A. The pulse generator has the following characteristics:  $Z_O = 50 \Omega$ ,  $PRR \leq 500 \text{ kHz}$ ,  $t_w = 100 \text{ ns}$ .  
B.  $C_L$  includes probe and jig capacitance.

**Figure 2. Test Circuit and Voltage Waveforms  $t_{PZH}$  and  $t_{PHZ}$**

## PARAMETER MEASUREMENT INFORMATION



VOLTAGE WAVEFORMS





NOTES: A. The pulse generator has the following characteristics:  $Z_O = 50 \Omega$ ,  $PRR \leq 500 \text{ kHz}$ ,  $t_w = 100 \text{ ns}$ .  
B.  $C_L$  includes probe and jig capacitance.

Figure 3. Test Circuit and Voltage Waveforms,  $t_{pZL}$  and  $t_{pLZ}$

# SN55113, SN75113 DUAL DIFFERENTIAL LINE DRIVERS





SLLS070C – SEPTEMBER 1973 – REVISED MARCH 1997

## TYPICAL CHARACTERISTICS†



† Data for temperatures below 0°C and above 70°C and for supply voltages below 4.75 V and above 5.25 V are applicable to SN55113 circuits only. These parameters were measured with the active pullup connected to the sink output.

TYPICAL CHARACTERISTICS†







† Data for temperatures below 0°C and above 70°C and for supply voltages below 4.75 V and above 5.25 V are applicable to SN55113 circuits only. These parameters were measured with the active pullup connected to the sink output.

# SN55113, SN75113 DUAL DIFFERENTIAL LINE DRIVERS

SLLS070C – SEPTEMBER 1973 – REVISED MARCH 1997

## TYPICAL CHARACTERISTICS†



† Data for temperatures below 0°C and above 70°C and for supply voltages below 4.75 V and above 5.25 V are applicable to SN55113 circuits only. These parameters were measured with the active pullup connected to the sink output.

## TYPICAL CHARACTERISTICS†




Figure 16





Figure 17

† Data for temperatures below 0°C and above 70°C and for supply voltages below 4.75 V and above 5.25 V are applicable to SN55113 circuits only. These parameters were measured with the active pullup connected to the sink output.

## APPLICATION INFORMATION



‡  $R_T = Z_0$ . A capacitor may be connected in series with  $R_T$  to reduce power dissipation.

Figure 18. Basic Party-Line or Data-Bus Differential Data Transmission

## PACKAGING INFORMATION

| Orderable part number            | Status<br>(1) | Material type<br>(2) | Package   Pins | Package qty   Carrier | RoHS<br>(3) | Lead finish/<br>Ball material<br>(4) | MSL rating/<br>Peak reflow<br>(5) | Op temp (°C) | Part marking<br>(6)                  |
|----------------------------------|---------------|----------------------|----------------|-----------------------|-------------|--------------------------------------|-----------------------------------|--------------|--------------------------------------|
| <a href="#">5962-88744012A</a>   | Active        | Production           | LCCC (FK)   20 | 55   TUBE             | No          | SNPB                                 | N/A for Pkg Type                  | -55 to 125   | 5962-<br>88744012A<br>SNJ55<br>113FK |
| <a href="#">5962-8874401EA</a>   | Active        | Production           | CDIP (J)   16  | 25   TUBE             | No          | SNPB                                 | N/A for Pkg Type                  | -55 to 125   | 5962-8874401EA<br>SNJ55113J          |
| <a href="#">5962-8874401FA</a>   | Active        | Production           | CFP (W)   16   | 25   TUBE             | No          | SNPB                                 | N/A for Pkg Type                  | -55 to 125   | 5962-8874401FA<br>SNJ55113W          |
| <a href="#">JM38510/10405BEA</a> | Active        | Production           | CDIP (J)   16  | 25   TUBE             | No          | SNPB                                 | N/A for Pkg Type                  | -55 to 125   | JM38510<br>/10405BEA                 |
| JM38510/10405BEA.A               | Active        | Production           | CDIP (J)   16  | 25   TUBE             | No          | SNPB                                 | N/A for Pkg Type                  | -55 to 125   | JM38510<br>/10405BEA                 |
| <a href="#">M38510/10405BEA</a>  | Active        | Production           | CDIP (J)   16  | 25   TUBE             | No          | SNPB                                 | N/A for Pkg Type                  | -55 to 125   | JM38510<br>/10405BEA                 |
| <a href="#">SN55113J</a>         | Active        | Production           | CDIP (J)   16  | 25   TUBE             | No          | SNPB                                 | N/A for Pkg Type                  | -55 to 125   | SN55113J                             |
| SN55113J.A                       | Active        | Production           | CDIP (J)   16  | 25   TUBE             | No          | SNPB                                 | N/A for Pkg Type                  | -55 to 125   | SN55113J                             |
| <a href="#">SN75113N</a>         | Active        | Production           | PDIP (N)   16  | 25   TUBE             | Yes         | NIPDAU                               | N/A for Pkg Type                  | 0 to 70      | SN75113N                             |
| SN75113N.A                       | Active        | Production           | PDIP (N)   16  | 25   TUBE             | Yes         | NIPDAU                               | N/A for Pkg Type                  | 0 to 70      | SN75113N                             |
| SN75113NE4                       | Active        | Production           | PDIP (N)   16  | 25   TUBE             | Yes         | NIPDAU                               | N/A for Pkg Type                  | 0 to 70      | SN75113N                             |
| SN75113NSR                       | Active        | Production           | SOP (NS)   16  | 2000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | 0 to 70      | SN75113                              |
| SN75113NSR.A                     | Active        | Production           | SOP (NS)   16  | 2000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | 0 to 70      | SN75113                              |
| <a href="#">SNJ55113FK</a>       | Active        | Production           | LCCC (FK)   20 | 55   TUBE             | No          | SNPB                                 | N/A for Pkg Type                  | -55 to 125   | 5962-<br>88744012A<br>SNJ55<br>113FK |
| SNJ55113FK.A                     | Active        | Production           | LCCC (FK)   20 | 55   TUBE             | No          | SNPB                                 | N/A for Pkg Type                  | -55 to 125   | 5962-<br>88744012A<br>SNJ55<br>113FK |
| <a href="#">SNJ55113J</a>        | Active        | Production           | CDIP (J)   16  | 25   TUBE             | No          | SNPB                                 | N/A for Pkg Type                  | -55 to 125   | 5962-8874401EA<br>SNJ55113J          |
| SNJ55113J.A                      | Active        | Production           | CDIP (J)   16  | 25   TUBE             | No          | SNPB                                 | N/A for Pkg Type                  | -55 to 125   | 5962-8874401EA<br>SNJ55113J          |

| Orderable part number     | Status<br>(1) | Material type<br>(2) | Package   Pins | Package qty   Carrier | RoHS<br>(3) | Lead finish/<br>Ball material<br>(4) | MSL rating/<br>Peak reflow<br>(5) | Op temp (°C) | Part marking<br>(6)         |
|---------------------------|---------------|----------------------|----------------|-----------------------|-------------|--------------------------------------|-----------------------------------|--------------|-----------------------------|
| <a href="#">SNJ55113W</a> | Active        | Production           | CFP (W)   16   | 25   TUBE             | No          | SNPB                                 | N/A for Pkg Type                  | -55 to 125   | 5962-8874401FA<br>SNJ55113W |
| SNJ55113W.A               | Active        | Production           | CFP (W)   16   | 25   TUBE             | No          | SNPB                                 | N/A for Pkg Type                  | -55 to 125   | 5962-8874401FA<br>SNJ55113W |

<sup>(1)</sup> **Status:** For more details on status, see our [product life cycle](#).

<sup>(2)</sup> **Material type:** When designated, preproduction parts are prototypes/experimental devices, and are not yet approved or released for full production. Testing and final process, including without limitation quality assurance, reliability performance testing, and/or process qualification, may not yet be complete, and this item is subject to further changes or possible discontinuation. If available for ordering, purchases will be subject to an additional waiver at checkout, and are intended for early internal evaluation purposes only. These items are sold without warranties of any kind.

<sup>(3)</sup> **RoHS values:** Yes, No, RoHS Exempt. See the [TI RoHS Statement](#) for additional information and value definition.

<sup>(4)</sup> **Lead finish/Ball material:** Parts may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead finish/Ball material values may wrap to two lines if the finish value exceeds the maximum column width.

<sup>(5)</sup> **MSL rating/Peak reflow:** The moisture sensitivity level ratings and peak solder (reflow) temperatures. In the event that a part has multiple moisture sensitivity ratings, only the lowest level per JEDEC standards is shown. Refer to the shipping label for the actual reflow temperature that will be used to mount the part to the printed circuit board.

<sup>(6)</sup> **Part marking:** There may be an additional marking, which relates to the logo, the lot trace code information, or the environmental category of the part.

Multiple part markings will be inside parentheses. Only one part marking contained in parentheses and separated by a "-" will appear on a part. If a line is indented then it is a continuation of the previous line and the two combined represent the entire part marking for that device.

**Important Information and Disclaimer:**The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.

## OTHER QUALIFIED VERSIONS OF SN55113, SN75113 :

- Catalog : [SN75113](#)

- Military : [SN55113](#)

NOTE: Qualified Version Definitions:

- Catalog - TI's standard catalog product
- Military - QML certified for Military and Defense Applications

## TAPE AND REEL INFORMATION



\*All dimensions are nominal

| Device     | Package Type | Package Drawing | Pins | SPQ  | Reel Diameter (mm) | Reel Width W1 (mm) | A0 (mm) | B0 (mm) | K0 (mm) | P1 (mm) | W (mm) | Pin1 Quadrant |
|------------|--------------|-----------------|------|------|--------------------|--------------------|---------|---------|---------|---------|--------|---------------|
| SN75113NSR | SOP          | NS              | 16   | 2000 | 330.0              | 16.4               | 8.1     | 10.4    | 2.5     | 12.0    | 16.0   | Q1            |

## TAPE AND REEL BOX DIMENSIONS



\*All dimensions are nominal

| Device     | Package Type | Package Drawing | Pins | SPQ  | Length (mm) | Width (mm) | Height (mm) |
|------------|--------------|-----------------|------|------|-------------|------------|-------------|
| SN75113NSR | SOP          | NS              | 16   | 2000 | 353.0       | 353.0      | 32.0        |

**TUBE**


\*All dimensions are nominal

| Device         | Package Name | Package Type | Pins | SPQ | L (mm) | W (mm) | T (μm) | B (mm) |
|----------------|--------------|--------------|------|-----|--------|--------|--------|--------|
| 5962-88744012A | FK           | LCCC         | 20   | 55  | 506.98 | 12.06  | 2030   | NA     |
| 5962-8874401FA | W            | CFP          | 16   | 25  | 506.98 | 26.16  | 6220   | NA     |
| SN75113N       | N            | PDIP         | 16   | 25  | 506    | 13.97  | 11230  | 4.32   |
| SN75113N.A     | N            | PDIP         | 16   | 25  | 506    | 13.97  | 11230  | 4.32   |
| SN75113NE4     | N            | PDIP         | 16   | 25  | 506    | 13.97  | 11230  | 4.32   |
| SNJ55113FK     | FK           | LCCC         | 20   | 55  | 506.98 | 12.06  | 2030   | NA     |
| SNJ55113FK.A   | FK           | LCCC         | 20   | 55  | 506.98 | 12.06  | 2030   | NA     |
| SNJ55113W      | W            | CFP          | 16   | 25  | 506.98 | 26.16  | 6220   | NA     |
| SNJ55113W.A    | W            | CFP          | 16   | 25  | 506.98 | 26.16  | 6220   | NA     |

W (R-GDFP-F16)

CERAMIC DUAL FLATPACK



- NOTES:
- All linear dimensions are in inches (millimeters).
  - This drawing is subject to change without notice.
  - This package can be hermetically sealed with a ceramic lid using glass frit.
  - Index point is provided on cap for terminal identification only.
  - Falls within MIL STD 1835 GDFP2-F16

## GENERIC PACKAGE VIEW

**FK 20**

**LCCC - 2.03 mm max height**

8.89 x 8.89, 1.27 mm pitch

LEADLESS CERAMIC CHIP CARRIER

This image is a representation of the package family, actual package may vary.  
Refer to the product data sheet for package details.



4229370VA\

J (R-GDIP-T\*\*)

14 LEADS SHOWN

# CERAMIC DUAL IN-LINE PACKAGE



| PINS **<br>DIM | 14                     | 16                     | 18                     | 20                     |
|----------------|------------------------|------------------------|------------------------|------------------------|
| A              | 0.300<br>(7,62)<br>BSC | 0.300<br>(7,62)<br>BSC | 0.300<br>(7,62)<br>BSC | 0.300<br>(7,62)<br>BSC |
| B MAX          | 0.785<br>(19,94)       | .840<br>(21,34)        | 0.960<br>(24,38)       | 1.060<br>(26,92)       |
| B MIN          | —                      | —                      | —                      | —                      |
| C MAX          | 0.300<br>(7,62)        | 0.300<br>(7,62)        | 0.310<br>(7,87)        | 0.300<br>(7,62)        |
| C MIN          | 0.245<br>(6,22)        | 0.245<br>(6,22)        | 0.220<br>(5,59)        | 0.245<br>(6,22)        |




4040083/F 03/03

- NOTES:
- A. All linear dimensions are in inches (millimeters).
  - B. This drawing is subject to change without notice.
  - C. This package is hermetically sealed with a ceramic lid using glass frit.
  - D. Index point is provided on cap for terminal identification only on press ceramic glass frit seal only.
  - E. Falls within MIL STD 1835 GDIP1-T14, GDIP1-T16, GDIP1-T18 and GDIP1-T20.


N (R-PDIP-T\*\*)

16 PINS SHOWN

## PLASTIC DUAL-IN-LINE PACKAGE



| PINS **<br>DIM      | 14               | 16               | 18               | 20               |
|---------------------|------------------|------------------|------------------|------------------|
| A MAX               | 0.775<br>(19,69) | 0.775<br>(19,69) | 0.920<br>(23,37) | 1.060<br>(26,92) |
| A MIN               | 0.745<br>(18,92) | 0.745<br>(18,92) | 0.850<br>(21,59) | 0.940<br>(23,88) |
| MS-001<br>VARIATION | AA               | BB               | AC               | AD               |



4040049/E 12/2002

- NOTES:
- A. All linear dimensions are in inches (millimeters).
  - B. This drawing is subject to change without notice.
  -  Falls within JEDEC MS-001, except 18 and 20 pin minimum body length (Dim A).
  -  The 20 pin end lead shoulder width is a vendor option, either half or full width.



# PACKAGE OUTLINE

NS0016A

SOP - 2.00 mm max height

SOP




4220735/A 12/2021

## NOTES:

1. All linear dimensions are in millimeters. Dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.
2. This drawing is subject to change without notice.
3. This dimension does not include mold flash, protrusions, or gate burrs. Mold flash, protrusions, or gate burrs shall not exceed 0.15 mm, per side.
4. This dimension does not include interlead flash. Interlead flash shall not exceed 0.25 mm, per side.





4220735/A 12/2021

NOTES: (continued)

7. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.
8. Board assembly site may have different recommendations for stencil design.

## IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATASHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, regulatory or other requirements.

These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you fully indemnify TI and its representatives against any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to [TI's Terms of Sale](#), [TI's General Quality Guidelines](#), or other applicable terms available either on [ti.com](#) or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products. Unless TI explicitly designates a product as custom or customer-specified, TI products are standard, catalog, general purpose devices.

TI objects to and rejects any additional or different terms you may propose.

Copyright © 2026, Texas Instruments Incorporated

Last updated 10/2025