


Highly Scalable TI DLP® Technology for 3D Machine Vision

Get more speed and accuracy with structured light using TI DLP® technology



3D machine vision is a fast and accurate optical technique used to capture physical measurements of an object. With the digitized 3D scan data, the dimensions of any object—including surface area, volume, and feature size—can be extracted. Structured light is an optical method of 3D scanning where a series of patterns are projected upon an object and a camera or sensor detects distortions of the patterns. Image processing and triangulation algorithms then convert these distortions into a 3D point cloud. The point cloud can be used directly for analysis of the object or easily exported to a variety of CAD modeling formats.

TI DLP technology enables programmable structured light solutions for portable and high resolution applications. DLP systems can produce non-contact, highly accurate 3D data in real-time, facilitating 3D Machine Vision.



Features and benefits

- **Fast, programmable pattern rates up to 32 kHz**
 - Acquire 3D scan data in real-time on moving objects
 - Optimize scan speed and accuracy for multiple objects and environments using adaptive pattern sets
- **Precise depth capture**
 - Achieve measurement accuracy to μm level
- **Digital switching using reflective, reliable MEMS micromirrors**
 - Minimal sensitivity to color, distance, movement and environment improves performance over time and temperature
- **Active illumination with LEDs, lasers, or lamps**
 - Multiple wavelengths for scanning a wide range of materials
 - Enables strong low light performance

Example applications

- Factory Automation
- Industrial Robotics
- Medical Imaging
- Dental Scanning
- Industrial Metrology
- Biometrics

DLP solutions for 3D machine vision

DLP chipsets are available with different DMD (Digital Micromirror Device) sizes, pixel pitches, resolutions, and wavelength range. The best choice for a DLP chipset may depend on the desired object feature size, patterning speed and system form factor. Smaller DMDs offer more compact system designs while high speed.

Recommended Parts


Portability	High Resolution	High Speed
DLP3000	DLP6500FYE	DLP7000
DLP4500 DLP4500NIR	DLP6500FLQ	DLP9500
DLP5500	DLP9000	



Evaluation Modules

Accelerate your design cycle by evaluating DLP technology with a broad selection of evaluation modules (EVMs). Our portfolio of EVMs offer a compelling combination of resolution, brightness, pattern speed, and programmability of DLP technology.

TI provides free software and firmware downloads allowing developers to easily create, store, and display high-speed pattern sequences through USB-based application programming interface (API) and easy-to-use graphical user interface (GUI).



System Block Diagram

The DLP solution for 3D machine vision is shown in the diagram. DLP technology enables 3D machine vision capabilities by providing single or multiple camera 3D image capture. The system utilizes a DMD as a spatial light modulator and a DMD Controller to provide high-speed control of the micromirrors. TI LED drivers provide illumination for the DMD to project the image. From power management to embedded processors to support the system, TI's vast portfolio provides a complete system solution to create your ideal 3D machine vision design.

TI Designs

Accurate point cloud generation

To enable customers to get to market faster, Texas Instruments also provides a TI Design for 3D machine vision applications. A TI Design is a comprehensive reference design that includes schematics, block diagrams, bill of materials, design files, software, and test reports. The 3D machine vision reference design encompasses Texas Instruments DLP structured light Software Development Kit (SDK). This design empowers developers with a framework to construct accurate 3D point clouds quickly by integrating TI's DMD in structured light solutions with cameras, sensors, motors or other peripherals. Get started at ti.com/tool/TIDA-00254

DLP chipsets for 3D machine vision

DMD Number	Micromirror Array	Array Diagonal	Controller	Micromirror Driver	Max Pattern Rate	Optimized Wavelengths	Pixel Pitch	Pixel Orientation	EVM	DMD Package Dimensions (lxwxh)	DMD 100u Price (\$ U.S.)	Controller 100u Price (\$U.S.)	Micromirror Driver 100u Price (\$U.S.)
DLP3000	608 x 684	0.30"	DLPC300	—	4,000 Hz (binary)	420-700 nm	7.6 μm	Diamond	LightCrafter	16.6 x 7 x 3.54 mm	95	16	—
DLP4500	912 x 1140	0.45"	DLPC350	—	4,225 Hz (binary)	420-700 nm	7.6 μm	Diamond	LightCrafter 4500	20.7 x 9.1 x 3.33 mm	143	56	—
DLP4500NIR	912 x 1140	0.45"	DLPC350	—	4,225 Hz (binary)	700 - 2500 nm	7.6 μm	Diamond	NIRscan	20.7 x 9.1 x 3.33 mm	315	56	—
DLP5500	1024 x 768	0.55"	DLPC200	DLPA200	5,000 Hz (binary)	420-700 nm	10.8 μm	Orthogonal	—	32.2 x 22.3 x 3.66 mm	403	140	12.36
DLP6500FYE	1920 x 1080	0.65"	DLPC900	—	9,500 Hz (binary)	420-700 nm	7.6 μm	Orthogonal	LightCrafter 6500	32 x 32 mm	588	160	—
DLP6500FLQ	1920 x 1080	0.65"	DLPC900	—	9,500 Hz (binary)	400-700 nm	7.6 μm	Orthogonal	—	32 x 41 mm	1,137	160	—
DLP7000	1024 x 768	0.7"	DLPC410	DLPA200	32,552 Hz (binary)	400-700 nm	13.6 μm	Orthogonal	Discovery™ 4100	40.64 x 31.75 x 6.01 mm	787	193	12.36
DLP9000	2560 x 1600	0.9"	DLPC900	—	9,500 Hz (binary)	400-700 nm	7.6 μm	Orthogonal	LightCrafter 9000	42.2 x 42.2 x 7 mm	2,783	160	—
DLP9500	1920 x 1080	0.95"	DLPC410	DLPA200	23,148 Hz (binary)	400-700 nm	10.8 μm	Orthogonal	Discovery 4100	42.2 x 42.2 x 7 mm	2,446	193	12.36

Visit ti.com/dlp3DMachineVision for more information.

DLTP021C

IMPORTANT NOTICE

Texas Instruments Incorporated and its subsidiaries (TI) reserve the right to make corrections, enhancements, improvements and other changes to its semiconductor products and services per JESD46, latest issue, and to discontinue any product or service per JESD48, latest issue. Buyers should obtain the latest relevant information before placing orders and should verify that such information is current and complete. All semiconductor products (also referred to herein as "components") are sold subject to TI's terms and conditions of sale supplied at the time of order acknowledgment.

TI warrants performance of its components to the specifications applicable at the time of sale, in accordance with the warranty in TI's terms and conditions of sale of semiconductor products. Testing and other quality control techniques are used to the extent TI deems necessary to support this warranty. Except where mandated by applicable law, testing of all parameters of each component is not necessarily performed.

TI assumes no liability for applications assistance or the design of Buyers' products. Buyers are responsible for their products and applications using TI components. To minimize the risks associated with Buyers' products and applications, Buyers should provide adequate design and operating safeguards.

TI does not warrant or represent that any license, either express or implied, is granted under any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI components or services are used. Information published by TI regarding third-party products or services does not constitute a license to use such products or services or a warranty or endorsement thereof. Use of such information may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

Reproduction of significant portions of TI information in TI data books or data sheets is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. TI is not responsible or liable for such altered documentation. Information of third parties may be subject to additional restrictions.

Resale of TI components or services with statements different from or beyond the parameters stated by TI for that component or service voids all express and any implied warranties for the associated TI component or service and is an unfair and deceptive business practice. TI is not responsible or liable for any such statements.

Buyer acknowledges and agrees that it is solely responsible for compliance with all legal, regulatory and safety-related requirements concerning its products, and any use of TI components in its applications, notwithstanding any applications-related information or support that may be provided by TI. Buyer represents and agrees that it has all the necessary expertise to create and implement safeguards which anticipate dangerous consequences of failures, monitor failures and their consequences, lessen the likelihood of failures that might cause harm and take appropriate remedial actions. Buyer will fully indemnify TI and its representatives against any damages arising out of the use of any TI components in safety-critical applications.

In some cases, TI components may be promoted specifically to facilitate safety-related applications. With such components, TI's goal is to help enable customers to design and create their own end-product solutions that meet applicable functional safety standards and requirements. Nonetheless, such components are subject to these terms.

No TI components are authorized for use in FDA Class III (or similar life-critical medical equipment) unless authorized officers of the parties have executed a special agreement specifically governing such use.

Only those TI components which TI has specifically designated as military grade or "enhanced plastic" are designed and intended for use in military/aerospace applications or environments. Buyer acknowledges and agrees that any military or aerospace use of TI components which have **not** been so designated is solely at the Buyer's risk, and that Buyer is solely responsible for compliance with all legal and regulatory requirements in connection with such use.

TI has specifically designated certain components as meeting ISO/TS16949 requirements, mainly for automotive use. In any case of use of non-designated products, TI will not be responsible for any failure to meet ISO/TS16949.

Products

Audio	www.ti.com/audio
Amplifiers	amplifier.ti.com
Data Converters	dataconverter.ti.com
DLP® Products	www.dlp.com
DSP	dsp.ti.com
Clocks and Timers	www.ti.com/clocks
Interface	interface.ti.com
Logic	logic.ti.com
Power Mgmt	power.ti.com
Microcontrollers	microcontroller.ti.com
RFID	www.ti-rfid.com
OMAP Applications Processors	www.ti.com/omap
Wireless Connectivity	www.ti.com/wirelessconnectivity

Applications

Automotive and Transportation	www.ti.com/automotive
Communications and Telecom	www.ti.com/communications
Computers and Peripherals	www.ti.com/computers
Consumer Electronics	www.ti.com/consumer-apps
Energy and Lighting	www.ti.com/energy
Industrial	www.ti.com/industrial
Medical	www.ti.com/medical
Security	www.ti.com/security
Space, Avionics and Defense	www.ti.com/space-avionics-defense
Video and Imaging	www.ti.com/video

TI E2E Community

e2e.ti.com