



© COPYRIGHT 2013 TEXAS INSTRUMENTS
UNPUBLISHED, ALL RIGHTS RESERVED

REVISIONS

REV	DESCRIPTION	DATE	BY
A	ECO #2136196 - INITIAL RELEASE	09/20/13	

1. REFER TO TI TECHNICAL SPECIFICATION DRAWING #2511460 FOR PROCEDURE FOR STANDARDIZED INSTALLATION OF S241 DMD.



1	6	2513364	PCB MECH FORM FACTOR SPECIFICATION - S241 DMD PCB	
3	5	WASHER, FLAT, 2.20MM ID X 5MM OD	WASHER, FLAT, 2.20MM ID X 5MM OD	
3	4	SCREW M2 x 0.40 x. 5.0MM LG PAN PHIL	SCREW M2 x 0.40 x. 5.0MM LG PAN PHIL	
1	3	2513420	CLAMP, S241 DMD	
1	2	S241 WXGA DMD	S241 WXGA DMD	
1	1	2513419	BRACKET, INTERFACE, S241 DMD	
QTY	ITEM	PART NUMBER	DESCRIPTION	Notes

Part List

UNLESS OTHERWISE SPECIFIED • DIMENSIONS ARE IN MILLIMETERS • TOLERANCES: ANGLES $\pm 1^\circ$ 2 PLACE DECIMALS ± 0.25 1 PLACE DECIMALS ± 0.50 • DIMENSIONAL LIMITS APPLY BEFORE PROCESSES • INTERPRET DIMENSIONS IN ACCORDANCE WITH ASME Y14.5M-1994 • REMOVE ALL BURRS AND SHARP EDGES • PARENTHEetical INFO FOR REF ONLY		DWN R ROWE	DATE 9/13/2013	TEXAS INSTRUMENTS	
		Engr			
		CQE/QA		S241 DMD MODULE ASSEMBLY	
		CM			
NEXT ASSY		USED ON	Apprvd	SCALE 2:1	
APPLICATION					
				SIZE DWG NO	REV
				B 2513362	A
				SHEET 1 OF 1	